EC2/EE2



Overview

The KEMET EC2/EE2 miniature signal relays offer a compact case size in a slim package. Minimal board space is consumed with either a through-hole or surface mount configuration. These relays are recognized by UL and CSA, while also being compliant with Part 68 of the FCC's 1,500 V surge capacity.

Applications

- · Electronic switching systems
- PBX
- · Terminal equipment
- · Telephone systems

Benefits

- Low power consumption (< 200 mW)
- · Compact and lightweight
- · Low magnetic interference
- · Tube or embossed tape and reel packaging
- UL recognized (E73266) and CSA certified (LR46266)
- · Surface mount and through-hole options
- High Breakdown Voltage (NKX) type can withstand 1.5 kVAC at open contacts





Part Number System


EE2-	3	S	NU	-L
Series	Coil Voltage	Latch Type	Lead Type	Packaging
EC2- = Through-hole mount EE2- = Surface mount	3 = 3 VDC 4.5 = 4.5 VDC 5 = 5 VDC 9 = 9 VDC 12 = 12 VDC 24 = 24 VDC	Blank = Non-latch type S = Single coil latch type T = Double coil latch type	NU = Standard NUH = Minimum footprint NUX = High solder joint reliability NKX = High breakdown voltage and high solder joint reliability NQJ = High capability with maximum switch current at 2A NQX = High capability with maximum switch current at 2A and high solder joint reliability type	Blank = Tube -L = Embossed tape on reel L6 = Embossed carrying tape and Moisture barrier bag




Dimensions - Millimeters

EC2 Series

Non-latch type and single coil latch type




Double coil latch type




EE2 Series

Non-latch type and single coil latch type



Double coil latch type




Series	D	Н	В	P ₁	P ₂	P ₃	K
EC2 (NU)	15.0	9.4	7.5	2.54	5.08	_	3.2
EC2 (NQJ)	15.0	9.4	7.5	2.54	5.08	_	2.8
EE2 (NU)	15.0	10.0	7.5	2.54	5.08	9.5	1.0
EE2 (NUH)	15.0	10.0	7.5	2.54	5.08	7.5	1.0
EE2 (NUX, NKX, NQX)	15.0	10.35	7.5	2.54	5.08	9.0	1.35


General tolerance: ±0.2




Pin Configurations

Bottom view







Safety Standards and Ratings

Certification Body	Mark	Specification	File Number	Rating
UL		UL Recognized (UL508) ¹	E73266	30 VDC, 2 A (resistive)
CSA	(F)	CSA Certified (CSA 22.2 #14)	LR46266	110 VDC, 0.3 A (resistive) 125 VAC, 0.5 A (resistive)

¹ Spacing: UL114, UL478

Certification Body	Mark	Lead Type	Specification	File Number	Class	Rating
TUV	<u>A</u>	NU, NUH, NUX (Non-latch and Single coil)	TUV Certified (EN61810)	R 9751153	Basic insulation	Creepage and clearance of coil to contact is more than 2 mm (According to EN60950)

Environmental Compliance

All KEMET relays are RoHS Compliant.





Table 1 - Ratings & Part Number Reference

Part Number	Nominal Coil Voltage	Lead Type	Packaging
() Designates Latch Type	(VDC)		
EC2-4.5(1)NU	4.5	Radial	Tube
EC2-5(1)NU	5	Radial	Tube
EC2-12(1)NU	12	Radial	Tube
EC2-24(1)NU	24	Radial	Tube
EC2-3(1)NQJ	3	Radial, high capability with max.switch current at 2A	Tube
EC2-4.5(1)NQJ	4.5	Radial, high capability with max.switch current at 2A	Tube
EC2-5(1)NQJ	5	Radial, high capability with max.switch current at 2A	Tube
EC2-9(1)NQJ	9	Radial, high capability with max.switch current at 2A	Tube
EC2-12(1)NQJ	12	Radial, high capability with max.switch current at 2A	Tube
EC2-24(1)NQJ	24	Radial, high capability with max.switch current at 2A	Tube
EE2-3(1)NU	3	Surface mount	Tube
EE2-4.5(1)NU	4.5	Surface mount	Tube
EE2-5(1)NU	5	Surface mount	Tube
EE2-12(1)NU	12	Surface mount	Tube
EE2-24(1)NU	24	Surface mount	Tube
EE2-3(1)NU-L	3	Surface mount	Tape on Reel
EE2-4.5(1)NU-L	4.5	Surface mount	Tape on Reel
EE2-5(1)NU-L	5	Surface mount	Tape on Reel
EE2-12(1)NU-L	12	Surface mount	Tape on Reel
EE2-24(1)NU-L	24	Surface mount	Tape on Reel
EE2-3(1)NUH	3	Surface mount, Minimum footprint	Tube
EE2-4.5(1)NUH	4.5	Surface mount, Minimum footprint	Tube
EE2-5(1)NUH	5	Surface mount, Minimum footprint	Tube
EE2-12(1)NUH	12	Surface mount, Minimum footprint	Tube
EE2-24(1)NUH	24	Surface mount, Minimum footprint	Tube
EE2-3(1)NUH-L	3	Surface mount, Minimum footprint	Tape on Reel
EE2-4.5(1)NUH-L	4.5	Surface mount, Minimum footprint	Tape on Reel
EE2-5(1)NUH-L	5	Surface mount, Minimum footprint	Tape on Reel
EE2-12(1)NUH-L	12	Surface mount, Minimum footprint	Tape on Reel
EE2-24(1)NUH-L	24	Surface mount, Minimum footprint	Tape on Reel
EE2-3(1)NUX	3	Surface mount, High solder joint reliability	Tube
EE2-4.5(1)NUX	4.5	Surface mount, High solder joint reliability	Tube Tube
EE2-5(1)NUX	5 12	Surface mount, High solder joint reliability	Tube
EE2-12(1)NUX EE2-24(1)NUX	24	Surface mount, High solder joint reliability Surface mount, High solder joint reliability	Tube
EE2-24(1)NUX-L	3	Surface mount, Fight solder joint reliability Surface mount, High solder joint reliability	Tape on Reel
	4.5		
EE2-4.5(1)NUX-L EE2-5(1)NUX-L	5	Surface mount, High solder joint reliability Surface mount, High solder joint reliability	Tape on Reel Tape on Reel
EE2-3(1)NUX-L	12	Surface mount, Fight solder joint reliability Surface mount, High solder joint reliability	Tape on Reel
EE2-12(1)NUX-L	24	Surface mount, Fight solder joint reliability Surface mount, High solder joint reliability	Tape on Reel
EE2-3NKX ¹	3	Surface mount, High solder joint reliability Surface mount, High breakdown voltage, High solder joint reliability	Tube
EE2-4.5NKX ¹	4.5	Surface mount, High breakdown voltage, High solder joint reliability	Tube
EE2-12NKX ¹	12	Surface mount, High breakdown voltage, High solder joint reliability	Tube
EE2-3NKX-L ¹	3	Surface mount, High breakdown voltage, High solder joint reliability	Tape on Reel
EE2-4.5NKX-L ¹	4.5	Surface mount, High breakdown voltage, High solder joint reliability	Tape on Reel
EE2-12NKX-L ¹	12	Surface mount, High breakdown voltage, High solder joint reliability	Tape on Reel
EE2-3(1)NQX-L6	3	Surface mount, High capability with maximum switch current at 2A, High solder joint reliability	Embossed carrying tape and Moisture barrier bag
EE2-4.5(1)NQX-L6	4.5	Surface mount, High capability with maximum switch current at 2A, High solder joint reliability	Embossed carrying tape and Moisture barrier bag
EE2-5(1)NQX-L6	5	Surface mount, High capability with maximum switch current at 2A, High solder joint reliability	Embossed carrying tape and Moisture barrier bag
EE2-9(1)NQX-L6	9	Surface mount, High capability with maximum switch current at 2A, High solder joint reliability	Embossed carrying tape and Moisture barrier bag
EE2-12(1)NQX-L6	12	Surface mount, High capability with maximum switch current at 2A, High solder joint reliability	Embossed carrying tape and Moisture barrier bag
EE2-24(1)NQX-L6	24	Surface mount, High capability with maximum switch current at 2A, High solder joint reliability	Embossed carrying tape and Moisture barrier bag
Part Number	Nominal Coil Voltage	Lead Type	Packaging

⁽¹⁾ To complete KEMET part number, leave blank for Non-latch, insert S for Single coil, or T for Double coil. Designates latch type.


¹ NKX type only available as Non-latch. Non-standard part, please contact KEMET to special order.



Land Pattern - Millimeters


EC2 Series (bottom view)

Non-latch type and single coil latch type




EE2 Series (top view)

Non-latch type and single coil latch type




Series	V	Х
EC2	5.08	_
EE2 (NU)	7.29	3.0
EE2 (NUH)	6.29	2.0
EE2 (NUX, NKX)	7.02	2.73

Double coil latch type



Double coil latch type





Soldering Process

EC2 - Through-hole Mounting

Automatic Soldering

Preheating: 110-120°C/110 seconds (maximum)

Solder temperature: 260°C maximum Solder time: 5 seconds maximum


Note: KEMET recommends cooling down a printed circuit board to less than 110°C within 40 seconds after soldering.

Manual Soldering

Solder temperature: 350°C maximum Solder time: 3 seconds maximum

EE2 – Surface Mounting

IRS Method



Note: Temperature profile shows printed circuit board surface temperature on the relay terminal portion. Please consult KEMET if you wish to use a temperature profile other than above.



Contact Specifications

ltem		EC2/EE2
Contact Form		2 Form C
Contact Material		Silver alloy with gold alloy overlay
	Maximum Switching Power	60 W, 125 VA
Contact Patings	Maximum Switching Voltage	220 VDC, 250 VAC
Contact Ratings	Maximum Switching Current	2 A
	Maximum Carrying Current	2 A
Minimum Contact Ratings		10 mVDC, 10 μA* ¹
Initial Contact Resistance		75 mΩ maximum (initial)
Operating Time (excluding bounce)		Approximately 2 milliseconds
Release Time (excluding bounce)		Approximately 1 millisecond
Insulation Resistance		1,000 MΩ at 500 VDC
		NU, NUH, NUX: 1,000 VAC (for one minute), 1,500 V surge (10 x 160 μs)*2
	Between Open Contacts	NKX: Make contact: 1,500 VAC (for one minute), 2,500 V surge (2 x 10 μs)*3 Break contact: 1,000 VAC (for one minute), 1,500 V surge (10 x 160 μs)*2
Withstand Voltage	Between Adjacent Contacts	1,000 VAC (for one minute), 1,500 V surge (10 x 160 μs)*2
		Non-latch and single coil latch type: 1,500 VAC (for one minute), 2,500 V surge (2 x 10 µs)*3
	Between Coil and Contacts	Double coil latch type: 1,000 VAC (for one minute), 1,500 V surge (10 x 160 μs)*2
Shock Resistance		735 m/s ² (75 G) – misoperation 980 m/s ² (100 G) – destructive failure
Vibration Resistance		10 to 55 Hz, double amplitude 3 mm (20 G) – misoperation 10 to 55 Hz, double amplitude 5 mm (30 G) – destructive failure
Ambient Temperature		-40 to +85°C
Coil Temperature Rise		18°C at nominal coil voltage (140 mW)
Dunning Specifications	Non-load	1 x 10 ⁸ operations (Non-latch type)*4 1 x 10 ⁷ operations (Latch type)
Running Specifications	Load	50 VDC 0.1 A (resistive), 1 x 10 ⁶ operations at 85°C, 5 Hz 10 VDC 10 mA (resistive), 1 x 10 ⁶ operations at 85°C, 2 Hz
Weight		Approximately 1.9 g

^{*1} This value is a reference value in the resistance load. Minimum capacity changes depending on the switching frequency, environment temperature, and load.

 $^{^{*2}}$ Rise time: 10 µs; decay time to half crest: 160 µs.

 $^{^{*3}}$ Rise time: 2 μ s; decay time to half crest: 10 μ s.

^{*4} This shows the number of operations with fatal defects. Stable characteristics are maintained for 1 x 10^7 operations.



Coil Specifications

Non-latch Type (at 20°C)						
Nominal Coil Voltage (VDC)	Coil Resistance (Ω) ±10%	Operating Voltage ¹ (VDC)	Release Voltage ¹ (VDC)	Nominal Operating Power (mW)		
3.0	64.3	2.25	0.30	140		
4.5	145.0	3.38	0.45	140		
5.0	178.0	3.75	0.50	140		
9.0	579.0	6.75	0.90	140		
12.0	1,028.0	9.00	1.20	140		
24.0	28,800.0	18.00	2.40	200		

¹ Test by pulse voltage.

Single Coil Latch Type (at 20°C) ²						
Nominal Coil Voltage (VDC)	Coil Resistance (Ω) ±10%	Set Voltage ¹ (VDC)	Reset Voltage ¹ (VDC)	Nominal Operating Power (mW)		
3.0	90.0	2.25	2.25	100		
4.5	202.5	3.38	3.38	100		
5.0	250.0	3.75	3.75	100		
9.0	810.0	6.75	6.75	100		
12.0	1,440.0	9.00	9.00	100		
24.0	3,840.0	18.00	18.00	150		

¹ Test by pulse voltage.

² Latch type relays should be initialized to a known position before using. Only the specified polarity should be used to energize the coil.

Double Coil Latch Type (at 20°C) ^{2,3}						
Nominal Coil Voltage (VDC)		sistance £10%	Set Voltage ⁴ (VDC)	Release Voltage ⁴ (VDC)	Nominal Operating Power (mW)	
3	S	64.3	2.25	-	140	
3	R	64.3	-	2.25	140	
4.5	S	145	3.38	_	140	
4.5	R	145	-	3.38		
5	S	178	3.75	-	140	
J J	R	178	-	3.75		
9	S	579	6.75	-	140	
9	R	579	-	6.75	140	
10	S	1,028	9.0	-	140	
12	R	1,028	-	9.0	140	
24	S	2,880	18.0	-	200	
24	R	2,880	-	18.0	200	

² Latch type relays should be initialized to a known position before using. Only the specified polarity should be used to energize the coil.

³ Can not be driven by reverse polarity for reverse operation.

⁴ S = Set coil [pin #1 (+), pin #12 (-)], R = Reset coil [pin #6 (+), pin #7 (-)].



Coil Specifications cont.

Non-latch, High Breakdown Voltage (NKX) Type (at 20°C)					
$ \begin{array}{c ccccccccccccccccccccccccccccccccccc$					
3.0	39.1	2.25	0.30	230	
4.5	88.0	3.38	0.45	230	
12.0	626.0	9.00	1.20	230	


¹ Test by pulse voltage.

Recommended Relay Drive Conditions


Coil Type	Rating	Ambient Temperature
Non-latch	Voltage: ≤ ±5% of nominal voltage	
Single Coil Double Coil	Square pulse (rise and fall time is rapid) Pulse height: ≤ ±5% of nominal voltage Pulse Width: > 10 ms	-40 to +85°C

Marking

EC2 - Top View



EE2 - Top View







Performance Data

Coil Temperature Rise


Temperature is measured by coil resistance






Switching Capacity

Maximum Values




Maximum Coil Voltage


Maximum value of permissible alteration



Applied Voltage vs. Timing

(Sample: EE2-5NU)








Performance Data cont.


Operate and Release Voltage vs. Ambient Temperature

This shows a typical change of operate (release) voltage. The value of must operate is estimated, so coil voltage must be applied higher than this value for safe operation. For hot start operation, please inquire with KEMET.




Running Test (Non-load)

(Load: none; Drive: 5 VDC, 50 Hz, 50% duty; Ambient Temperature: room temperature; Sample: EE2-5NU, 20 pieces)



Running Test (Load)

(Load: 50 VDC, 0.1 A resistive; Drive: 5 VDC, 5 Hz, 50% duty; Ambient Temperature: 85°C; Sample: EE2-5NU, 10 pieces)








Performance Data cont.

Breakdown Voltage

(Sample: EE2-5NU, 10 pieces)











Alteration of Voltage in Dense Mounting


(magnetic interference)















Tube Packing - Millimeters




Tape & Reel Packaging Information (EE2 only) - Millimeters

Appearance




Tape Dimensions



Series	A	В
NU-L, NUX-L, NKX-L	Maximum 10.9	10.0
NUH-L	Maximum 11.1	8.0

Relay Direction Mark and Tape Carrying Direction






Notes on Using Relays

1. Contact Load

Make sure that the contact load is within the specified range; otherwise, the lifetime of the contacts will be shortened considerably. Note that the running performance shown is an example, and that it varies depending on parameters such as the type of load, switching frequency, driver circuit, and ambient temperature under the actual operating conditions.

2. Driving Relays

- If the internal connection diagram of a relay shows + and symbols on the coil, apply the rated voltage to the relay in the specified direction. If a rippled DC current source is used, abnormalities such as heat at the coil may occur.
- The maximum voltage that can be applied to the coil of the relay varies depending on the ambient temperature.
 Generally, the higher the voltage applied to the coil, the shorter the operating time. Note, however, that high voltage also increases the bounce of the contacts and the contact opening and closing frequency, which may shorten the lifetime of the contacts.



- For consistent operation, the driving voltage should have rise and fall times of less than 1 ms.
- For a latching relay, apply a voltage to the coil according to the polarity specified in the internal connection diagram of the relay.
- If a current is applied to the coil over a long period of time, the coil temperature rises, promoting generation of organic gas inside the relay, which may result in faulty contacts. In this case, use of a latching relay is recommended.
- The operating time and release time indicate the time required for each contact to close after the voltage has been
 applied to or removed from the coil. However, because the relay has a mechanical structure, a bounce state exists
 at the end of the operating and release times. Furthermore, because additional time is required until the contact
 stabilizes after being in a high-resistance state, care must be taken when using the relay at high speeds.


3. Operating Environment

- Make sure that the relay mounted in the application set is used within the specified temperature range. Use of a relay at a temperature outside this range may adversely affect insulation or contact performance.
- If the relay is used for a long period of time in highly humid (RH 85% or higher) environment, moisture may be
 absorbed into the relay. This moisture may react with the NOx and SOx generated by glow discharges that occur when
 the contacts are opened or closed, producing nitric or sulfuric acid. If this happens, the acid produced may corrode
 the metallic parts of the relay, causing operational malfunction.
- If any material containing silicon (silicon rubber, silicon oil, and silicon based coating material) is used in the neighborhood of relay, there is some possibility that these materials will emit silicon gas that will penetrate the relay. In this case, the switching contact may generate silicon compounds on the surface of contacts. This silicon compound may result in contact failure. Avoid use of relay in such an environment.



Notes on Using Relays cont.

• Because the operating temperature range varies depending on the humidity, use the relay in the temperature range illustrated in the figure below. Prevent the relay from being frozen and avoid the generation of condensation.



- The relay maintains constant sealability under normal atmospheric pressure (810 to 1,200 hpa). Its sealability may
 be degraded or the relay may be deformed and malfunction if it is used under barometric conditions exceeding the
 specified range.
- The same applies when the relay is stored or transported. Keep the upper-limit value of the temperature to which the relay is exposed after it is removed from the carton box to within 50°C.
- Permanent magnets are used in polarized relays. For this reason, when magnets, transformers, or speakers are located nearby the relay characteristics may change and faulty operations may result.
- If excessive vibration or shock is applied to the relay, it may malfunction and the contacts remain closed. Vibration or shock applied to the relay during operation may cause considerable damage to or wearing of the contacts. Note that operation of a snap switch mounted close to the relay or shock due to the operation of magnetic solenoid may also cause malfunctioning.

4. Mounting

- When mounting a relay onto a PC board using an automatic chip mounter, if excessive force is applied to the cover
 of the relay when the relay is chucked or inserted, the cover may be damaged or the characteristics of the relay
 degraded. Keep the force applied to the relay to within 1 kg.
- Avoid bending the pins to temporarily secure the relay to the PC board. Bending the pins may degrade sealability or adversely affect the internal mechanism.
- Ventilation immediately after soldering is recommended. Avoid immersing the relay in cleaning solvent immediately after soldering due to the danger of thermal shock being applied to the relay.
- Use an alcohol-based or water-based cleaning solvent. Never use thinner and benzene because they may damage the relay housing.
- Do not use ultrasonic cleaning because the vibration energy generated by the ultrasonic waves may cause the
 contacts to remain closed.



Notes on Using Relays cont.

5. Handling and Storage

- Relays are packaged in magazine cases for shipment. If a space is created in the case after some relays have been
 removed, be sure to insert a stopper to secure the remaining relays in the case. If relays are not well secured, vibration
 during transportation may cause malfunctioning of the contacts.
- Exercise care in handling the relay so as to avoid dropping it or allowing it to fall. Do not use a relay that has been dropped. If a relay drops from a workbench to the floor, a shock of 9,800 m/s² (1,000 G) or more is applied to the relay, possibly damaging its functions. Even if a light shock has been applied to the relay, thoroughly evaluate its operation before using it.
- Latching relays are factory-set to reset state for shipment. A latching relay may be set, however, by vibration or shock applied while being transported. Be sure to forcibly reset the relay before using it in the application set. Also note that the relay may be set by unexpected vibration or shock when it is used in a portable set.
- The sealability of a surface mount (SMT) relay may be lost if the relay absorbs and is then heated during soldering. When storing relays, therefore, observe the following points:
 - 1. For standard packing, please use relays within 12 months after delivery (storage conditions: 30°C/60% RH). If the relays have moisture absorption, dehumidify as follows:
 - Tape Packaging: 50 ±5°C, 200-300 hours.
 - Simple Relay: 85 ±5°C, 48 hours.
 - 2. For MBB packing, please use relays within 2 years after delivery (storage conditions: 30°C/60% RH). After opening MBB packing, please use within 3 months (storage conditions: 30°C/60% RH).



KEMET Electronics Corporation Sales Offices

For a complete list of our global sales offices, please visit www.kemet.com/sales.

Disclaimer

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicted or that other measures may not be required.

When providing KEMET products and technologies contained herein to other countries, the customer must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the International Traffic in Arms Regulations (ITAR), the US Export Administration Regulations (EAR) and the Japan Foreign Exchange and Foreign Trade Act.