

SBOS146A - OCTOBER 1986 - REVISED AUGUST 2004

Precision, Low Drift 4-20mA TWO-WIRE TRANSMITTER

FEATURES

- INSTRUMENTATION AMPLIFIER INPUT:
 - Low Offset Voltage, 30μV max
 - Low Voltage Drift, 0.75μV/°C max
 - Low Nonlinearity, 0.01% max
- TRUE TWO-WIRE OPERATION:
 - Power and Signal on One Wire Pair
 - Current Mode Signal Transmission
 - High Noise Immunity
- DUAL MATCHED CURRENT SOURCES
- WIDE SUPPLY RANGE: 11.6V to 40V
- SPECIFICATION RANGE: -40°C to +85°C
- SMALL DIP-14 PACKAGE, CERAMIC AND PLASTIC


APPLICATIONS

- INDUSTRIAL PROCESS CONTROL:
 - Pressure Transmitters
 - Temperature Transmitters
 - Millivolt Transmitters
- RESISTANCE BRIDGE INPUTS
- THERMOCOUPLE INPUTS
- RTD INPUTS
- CURRENT SHUNT (mV) INPUTS
- PRECISION DUAL CURRENT SOURCES
- AUTOMATED MANUFACTURING
- POWER/PLANT ENERGY SYSTEM MONITORING

DESCRIPTION

The XTR101 is a microcircuit, 4-20mA, two-wire transmitter containing a high accuracy instrumentation amplifier (IA), a voltage-controlled output current source, and dual-matched precision current reference. This combination is ideally suited for remote signal conditioning of a wide variety of transducers such as thermocouples, RTDs, thermistors, and strain gauge bridges. State-of-theart design and laser-trimming, wide temperature range operation, and small size make it very suitable for industrial process control applications. In addition, the optional external transistor allows even higher precision.

The two-wire transmitter allows signal and power to be supplied on a single wire pair by modulating the power-supply current with the input signal source. The transmitter is immune to voltage drops from long runs and noise from motors, relays, actuators, switches, transformers, and industrial equipment. It can be used by OEMs producing transmitter modules or by data acquisition system manufacturers.



NOTE: (1) Pins 12 and 13 are used for optional BW control.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

All trademarks are the property of their respective owners.





ABSOLUTE MAXIMUM RATINGS(1)

Power Supply, +V _{CC} 40V
Input Voltage, e_1 or e_2 $\geq V_{OUT}$, $\leq +V_{CC}$
Storage Temperature Range, Ceramic55°C to +165°C
Plastic –55°C to +125°C
Lead Temperature (soldering, 10s) G, P+300°C
(wave soldering, 3s) U+260°C
Output Short-Circuit Duration Continuous +V _{CC} to I _{OUT}
Junction Temperature

(1) Stresses above these ratings may cause permanent damage. Exposure to absolute maximum conditions for extended periods may degrade device reliability. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those specified is not supported.



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe

proper handling and installation procedures can cause damage.


ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

ORDERING INFORMATION

PRODUCT	PACKAGE- LEAD	PACKAGE DESIGNATOR ⁽¹⁾	SPECIFIED TEMPERATURE RANGE	PACKAGE MARKING
	Ceramic	JD		XTR101AG
	DIP-14	00		XTR101BG
XTR101	Plastic DIP-14	N	-40°C to +85°C	XTR101AP
	SO-16	DW		XTR101AU

⁽¹⁾ For the most current package and ordering information, see the Package Option Addendum located at the end of this data sheet.

PIN CONFIGURATION





ELECTRICAL CHARACTERISTICS

At $T_{\Delta} = +25^{\circ}\text{C}$, $+V_{CC} = 24\text{VDC}$, and $R_{L} = 100\Omega$ with external transistor connected, unless otherwise noted.

Full-Scale - 20mA	TI I A = +20 C, +VCC	$T_A = +25^{\circ}C$, $+V_{CC} = 24VDC$, and $R_L = 100\Omega$ with external transistor connected, unless otherwise noted.											ı		
Current Limit Current Limi)	TR101AC	3		XTR101E	3G				ļ	XTR101A	U	
Current Limit	PARAMETER	CONDITIONS	MIN	TYP	MAX	MIN	TYP	MAX	MIN	TYP	MAX	MIN	TYP	MAX	UNIT
Detailed Performance 3.8 22 22 23 24 24 25 26 25 25 25 25 25 25	OUTPUT AND LOAD CHAP	RACTERISTICS													
Current Elizario Companiente Companien	Current	Linear Operating Region	4		20						-				mA
Consequence		Derated Performance	3.8		22	*			*			*			mA
Value Val	Current Limit			28	38		*	*		31	*		31	*	mA
Full-Scale Dulput Current Enr Power-Supply Voltage Compliance (1) Al VCC = 24V, 0 = 20mA Al VCC = 440V, 0 = 4mA 0.018amps/volt (40/Rs) 0 = 20mA Voltourent Equation Reg in Q = 4mA 0.018amps/volt (40/Rs) 0 = 20mA Voltourent Equation Reg in Q = 4mA 0.018amps/volt (40/Rs) 0 = 20mA Voltourent Equation Reg in Q = 4mA 0.018amps/volt (40/Rs) 0 = 20mA Voltourent Equation Reg in Q = 4mA 0.018amps/volt (40/Rs) 0 = 20mA Voltourent Equation Reg in Q = 4mA 0.018amps/volt (40/Rs) 0 = 20mA Voltourent Equation Reg in Q = 4mA 0.018amps/volt (40/Rs) 0 = 20mA Voltourent Equation Reg in Q = 4mA 0.018amps/volt (40/Rs) 0 = 20mA Voltourent Equation Reg in Q = 4mA 0.018amps/volt (40/Rs) 0 = 20mA Voltourent Equation Reg in Q = 4mA 0.018amps/volt (40/Rs) 0 = 20mA Voltourent Equation Reg in Q = 4mA 0.018amps/volt (40/Rs) 0 = 20mA Voltourent Equation Reg in Q = 4mA 0.018amps/volt (40/Rs) 0 = 20mA Voltourent Equation Reg in Q = 4mA 0.018amps/volt (40/Rs) 0 = 20mA Voltourent Equation Reg in Q = 4mA 0.018amps/volt (40/Rs) 0 = 20mA Voltourent Equation Reg in Q = 4mA 0.018amps/volt (40/Rs) 0 = 20mA Voltourent Equation Reg in Q = 4mA 0.018amps/volt (40/Rs) 0 = 20mA Reg in Q = 4mA 0.018amps/volt (40/Rs) 0 = 20mA Reg in Q = 4mA 0.018amps/volt (40/Rs) 0 = 20mA Reg in Q = 4mA 0.018amps/volt (40/Rs) 0 = 20mA Reg in Q = 4mA 0.018amps/volt (40/Rs)	Offset Current Error	I_{OS} , $I_{O} = 4mA$		±3.9	±10		±2.5	±6		±8.5	±19			±19	μΑ
Error Full-Scale = 200A 120 140 150 130 130 130 130 14	vs Temperature	ΔΙΟS/ΔΤ		±10.5	±20		±8	±15		±10.5	±20		*		ppm, FS/°C
Power-Supply Voltage Complanes (1) Com		Full-Scale = 20mA		±20	±40		±15	±30		±30	±60		±30	±60	μА
Compliance (1) 11-10 12-10 12-10 13-10 14-10 1		Vcc. Pins 7 and 8													
Load Resistance Log = 20mA A VCC = ±40V, I V = 20mA A V = ±40V, I V = ±	Tower Supply Voltage	Compliance (1)	+11.6		±40	*		*	*		*	*		*	VDC
AVCC = 440V, I_C = 20mA	Load Resistance				600			*			*			*	Ω
SPAN Output Current Equation RS in Ω, e1 and e2 in V Span Equation RS in Ω RS in Ω Span Equation RS in Ω RS in Ω RS in Ω Span Equation RS in Ω Span Equa		-													
SPAN Rg in Ω, e1 and e2 in V Span Equation Rg in Ω, e1 and e2 in V Span Equation Rg in Ω Span Equation Span Equ					1400			*			*			*	Ω
Output Current Equation Rs in Ω e1 and e2 in V Span Equation Rs in Ω Rs in Ω S = 0.016amps/volt + (40/Rs) e2 e1 S = AV AV AV AV AV AV AV	00411	IO = 20mA													
Span Equation Rs in Ω Excluding TCR of Rs (SPAN -5 -2.5 0.016 arms/volt + (40/Rs)						l	Г		l ,	\1(l ,	l			
Value Valu	Output Current Equation	RS in Ω , e ₁ and e ₂ in V				l _O = 4r			,	-/1.	2 - e ₁)		i i		
Untrimmed Error(2) Respan Properties	Span Equation	R _S in Ω					S = 0		/volt +						A/V
Nonlinearity Non	vs Temperature	Excluding TCR of Rs		±30	±100					-					ppm/°C
NonLine Any NonLine And	Untrimmed Error(2)	€SPAN	-5	-2.5	0	*	*		*	*	-	*	*	-	%
NPUT CHARACTERISTICS New Common-Mode Ace = (e2 - e1)(3)	Nonlinearity	^E NONLINEARITY			0.01			*			*			*	%
Temperature	Hysteresis			0											%
Impedance: Differential Common-Mode Rejection Match Match Match Match Match Match Match Match Match Match Match Match Match Match Match Match Match Match Mat	Dead Band			0			*			*			*		%
Common-Mode Ace (e2 - e1)(3)	INPUT CHARACTERISTICS	3													
Voltage Range, Full-Scale Offset Voltage Range Fu	Impedance: Differential			0.4 3											GΩ pF
Solidage August	Common-Mode			10 3			*			*			*		GΩ pF
Signature AVGS/ΔT ±0.75 ±1.5	Voltage Range, Full-Scale	$\Delta e = (e_2 - e_1)^{(3)}$	0		1	*		*	*		*	*		*	V
Power-Supply Rejection Bias Current Bias Current Bias Current Voc PSRR = Vos Error 110 125	Offset Voltage	Vos		±30	±60		±20	±30		-					μV
B Bias Current B Alg/AT Dots B Bias Current Vs Temperature Alg/AT Dots	vs Temperature	ΔV _{OS} /ΔΤ		±0.75	±1.5			±0.75		*	*		*	*	μV/°C
Value Val	Power-Supply Rejection	$\Delta V_{CC}/PSRR = V_{OS} Error$	110	125		*			*			*			dB
Offset Current vs Temperature Offset Current Offset Current Offset Current Offset Current Vs Temperature Vs Temperature DC DC Offset Current	Bias Current	lΒ		60	150										nA
Vs Temperature	vs Temperature	ΔΙΒ/ΔΤ		0.30	1			*		-	-		-		nA/°C
Common-Mode Rejection(4)	Offset Current	losi		10	±30					-			-		nA
Rejection (4)	vs Temperature	Δl _{OSI} /ΔT		0.1	0.3		*	*		*	*		*	*	nA/°C
Common-Mode Range e ₁ and e ₂ with Respect to Pin 7 4 6 * * * * * * V CURRENT SOURCES Magnitude Accuracy Magnitude VCC VPIN 8 – VPIN 10, 11 = 19V, 		DC	90	100		*	*		*	*		*	*		dB
CURRENT SOURCES Magnitude Accuracy V _{CC} = 24V, V _{PIN 8} – V _{PIN 10, 11} = 19V, R ₂ = 5kΩ, see Figure 5 ±0.06 ±0.1 7 ±0.02 5 ±0.075 5 ±0.2 ±0.37 ±0.2 ±0.37 % vs Temperature vs V _{CC} vs Time With Respect to Pin 7 Tracking 0 V _{CC} – 3.5 * * * * * * * ppm//°C ppm//°C ppm//°C ppm//°C * * * * * * * * * * * * * ppm//°C ppm//°C * <t< td=""><td>*</td><td>e₁ and e₂ with Respect to Pin 7</td><td>4</td><td></td><td>6</td><td>*</td><td></td><td>*</td><td>*</td><td></td><td>*</td><td>*</td><td></td><td>*</td><td>V</td></t<>	*	e ₁ and e ₂ with Respect to Pin 7	4		6	*		*	*		*	*		*	V
Magnitude Accuracy $V_{CC} = 24V$, $V_{PIN 8} - V_{PIN 10, 11} = 19V$, $V_{R2} = 5K\Omega$, see Figure 5 $V_{CC} = 24V$, $V_{PIN 8} - V_{PIN 10, 11} = 19V$, $V_{R2} = 5K\Omega$, see Figure 5 $V_{CC} = 24V$, $V_{PIN 8} - V_{PIN 10, 11} = 19V$, $V_{R2} = 5K\Omega$, see Figure 5 $V_{CC} = 24V$, $V_{PIN 8} - V_{PIN 10, 11} = 19V$, $V_{R2} = 5K\Omega$, see Figure 5 $V_{CC} = 24V$, $V_{PIN 8} - V_{PIN 10, 11} = 19V$, $V_{R2} = 5K\Omega$, see Figure 5 $V_{CC} = 24V$, $V_{PIN 8} - V_{PIN 10, 11} = 19V$, $V_{R2} = 5K\Omega$, see Figure 5 $V_{CC} = 24V$, $V_{PIN 10, 11} = 19V$, $V_{R2} = 5K\Omega$, see Figure 5 $V_{CC} = 24V$, $V_{PIN 10, 11} = 19V$, $V_{R2} = 5K\Omega$, see Figure 5 $V_{CC} = 24V$, $V_{PIN 10, 11} = 19V$, $V_{R2} = 5K\Omega$, see Figure 5 $V_{CC} = 24V$, $V_{$												1			
Accuracy VCC = 24V, VPIN 8 - VPIN 10, 11 = 19V, R2 = 5kΩ, see Figure 5 vs Temperature vs VCC vs Time Compliance Voltage Ratio Match Accuracy (1 - I_REF1/I_REF2) × 100% vs Temperature vs VCC vs Time Compliance Voltage Ratio Match Accuracy (1 - I_REF1/I_REF2) × 100% TEMPERATURE RANGE Specification Operating VCC = 24V, VPIN 8 - VPIN 10, 11 = 19V, R2 = 5kΩ, see Figure 5 ±0.06 ±0.1 7 ±0.06 ±0.1 7 ±0.02 5 ±0.075 ±0.075 ±0.075 ±0.075 ±0.075 ±0.075 * * * * * * * * * * * * *				1			*			*			*		mΑ
VPIN 8 - VPIN 10, 11 = 19V, R2 = 5kΩ, see Figure 5 ±0.06 ±0.1 7 ±0.02 ±0.075 ±0.075 ±0.2 ±0.37 ±0.2 ±0.37 % ppm/°C ±0.8 ±30		Voc = 24V													1117 (
vs Temperature vs Temperature ±50 ±80 ±30 ±50 * * * * * * * * * * * * * * * * * * *	ricouracy	VPIN 8 - VPIN 10, 11 = 19V,		±0.06				±0.075		±0.2	±0.37		±0.2	±0.37	%
vs V _{CC} vs Time With Respect to Pin 7 Tracking 0 V _{CC} − 3.5 * * * * * * * ppm//ν ppm//mon Accuracy (1 − I _{REF1} /I _{REF2}) × 100% ±0.01	vs Temperature	. 12 = 31mm, 300 i iguio 0		+50	+80		+30	+50		*	*		*	*	ppm/°C
vs Time With Respect to Match With Respect to Pin 7 Tracking 0 VCC − 3.5 * * * * * * * ppm/mon Accuracy (1 − I _{REF1} /I _{REF2}) × 100% ±0.01	·							200		*			*		
Compliance Voltage Ratio Match With Respect to Pin 7 Tracking 0 V _{CC} - 3.5 * * * * * * * * V Accuracy (1 - I _{REF1} /I _{REF2}) × 100% 10 ±0.01 / 4 ±0.00 / 9 ±0.04 ±0.031 ±0.088 ±0.031 ±0.088 % vs Temperature vs V _{CC} vs Time ±10 / ±10 * * * * * * ppm/°C Output Impedance 10 20 * * * * 15 * 15 * * * ppm/°C ppm/°C <t< td=""><td></td><td></td><td></td><td></td><td></td><td></td><td>*</td><td></td><td></td><td>*</td><td></td><td></td><td>*</td><td></td><td></td></t<>							*			*			*		
Match Pin 7 Tracking 0 VCC - 3.5 * * * * * V Accuracy (1 - I _{REF1} /I _{REF2}) × 100% ±0.01 / 4 / 6 ±0.00 / 9 ±0.04 ±0.031 / ±0.088 ±0.031 / ±0.088 * ppm/°C vs Temperature vs VCC vs Time ±10 / ±10 / ±11 * * * * * ppm/°C		With Respect to			l	.1.		-1-	.1.		-1-				
Accuracy (1 - IREF1/IREF2) × 100% 4 6 9 ±0.04 ±0.031 ±0.088 ±0.031 ±0.088 % vs Temperature vs V _{CC} ±10	,	'	0			*		*	*		*	*		*	V
±10	Accuracy	(1 - I _{REF1} /I _{REF2}) × 100%						±0.04		±0.031			±0.031		%
vs V _{CC} vs Time ±10 ±1 ±1 ±1 ±1 ±1 ±1 ±1 ±1 ±1 ±1 ±1 ±1 ±1	vs Temperature				±15			10			*			*	ppm/°C
vs Time ±1 * * * * * * ppm/mon MΩ Output Impedance 10 20 * * * 15 * * 15 * MΩ TEMPERATURE RANGE Specification -40 +85 * * * * * * * * * * °C Operating -55 +125 * * -40 +85 -40 +85 °C				±10						*			*		ppm/V
Output Impedance 10 20 * * 15 * 15 MΩ TEMPERATURE RANGE Specification -40 +85 * * * * * * * * °C Operating -55 +125 * * -40 +85 -40 +85 °C										*			*		ppm/month
TEMPERATURE RANGE Specification -40 +85 * * * * * * * °C Operating -55 +125 * -40 +85 -40 +85 °C			10			*	*		*	15		*	15		
Specification -40 +85 * * * * * * 0°C Operating -55 +125 * -40 +85 -40 +85 0°C												1			
Operating			-40		+85	*		*	*		*	*		*	°C
						*		*	-40		+85	-40		+85	
Storage -55 +165 * -55 +125 -55 +125 °C		į		İ	!	*	İ	*	!	1		!	1		!


^{*} Same as XTR101AG.


 [↑] Same as XTR101AG.
 (1) See the Typical Characteristics.
 (2) Span error shown is untrimmed and may be adjusted to zero.
 (3) e₁ and e₂ are signals on the -In and +In terminals with respect to the output, pin 7. While the maximum permissible Δe is 1V, it is primarily intended for much lower signal levels, for instance, 10mV or 50mV full-scale for the XTR101A and XTR101B grades, respectively. 2mV FS is also possible with the B grade, but accuracy will degrade due to possible errors in the low value span resistance and very high amplification of offset, drift, and noise.
 (4) Offset voltage is trimmed with the application of a 5V common-mode voltage. Thus, the associated common-mode error is removed. See the *Application Information* section.





TYPICAL CHARACTERISTICS


At $T_A = +25^{\circ}C$ and $V_{CC} = 24VDC$, unless otherwise noted.



















TYPICAL CHARACTERISTICS (continued)

At $T_A = +25$ °C, $V_{DD} = +3.3$ V, and $V_{IO} = +3.3$ V, unless otherwise noted.









THEORY OF OPERATION

A simplified schematic of the XTR101 is shown in Figure 1. Basically, the amplifiers A_1 and A_2 act as a single power-supply instrumentation amplifier controlling a current source, A_3 and Q_1 . Operation is determined by an internal feedback loop. e_1 applied to pin 3 will also appear at pin 5, and similarly, e_2 will appear at pin 6. Therefore, the current in R_S (the span setting resistor) will be $I_S = (e_2 - e_1)/R_S = e_{IN}/R_S$. This current combines with the current I_3 to form I_1 . The circuit is configured such that I_2 is 19 times I_1 . From this point, the derivation of the transfer function is straightforward but lengthy. The result is shown in Figure 1.

Examination of the transfer function shows that I_O has a lower range-limit of 4mA when $e_{IN}=e_2-e_1=0$ V. This 4mA is composed of 2mA quiescent current exiting pin 7 plus 2mA from the current sources. The upper range limit of I_O is set to 20mA by the proper selection of R_S based on the upper range limit of e_{IN} . Specifically, R_S is chosen for a 16mA output current span for the given full-scale input voltage span.

$$\mbox{For example,} \bigg(0.016 \frac{\mbox{amps}}{\mbox{volt}} + \frac{40}{\mbox{R}_{\mbox{\scriptsize S}}} \bigg) \! \big(\mbox{e}_{\mbox{\scriptsize IN}} \mbox{ full-scale} \big) = \mbox{ 16mA}. \label{eq:energy}$$

Note that since I_O is unipolar, e_2 must be kept larger than e_1 (that is, $e_2 \ge e_1$ or $e_{IN} \ge 0$). Also note that in order not to exceed the output upper range limit of 20mA, e_{IN} must be kept less than 1V when $R_S = \infty$ and proportionately less as R_S is reduced.




Figure 1. Simplified Schematic of the XTR101



INSTALLATION AND OPERATING INSTRUCTIONS BASIC CONNECTION

See Figure 1 for the basic connection of the XTR101. A difference voltage applied between input pins 3 and 4 will cause a current of 4-20mA to circulate in the two-wire output loop (through $R_L,\,V_{PS},\,$ and $D_1).$ For applications requiring moderate accuracy, the XTR101 operates very cost-effectively with just its internal drive transistor. For more demanding applications (high accuracy in high gain), an external NPN transistor can be added in parallel with the internal one. This keeps the heat out of the XTR101 package and minimizes thermal feedback to the input stage. Also, in such applications where the e_{IN} full-scale is small (< 50mV) and R_{SPAN} is small (< 150Ω), caution should be taken to consider errors from the external span circuit plus high amplification of offset drift and noise.

OPTIONAL EXTERNAL TRANSISTOR

The optional external transistor, when used, is connected in parallel with the XTR101 internal transistor. The purpose is to increase accuracy by reducing heat change inside the XTR101 package as the output current spans from 4-20mA. Under normal operating conditions, the internal transistor is never completely turned off, as shown in Figure 2. This maintains frequency stability with varying external transistor characteristics and wiring capacitance. The actual current sharing between internal and external transistors is dependent on two factors:

- 1. relative geometry of emitter areas, and
- 2. relative package dissipation (case size and thermal conductivity).

For best results, the external device should have a larger base-emitter area and smaller package. It will, upon turn-on, take about $[0.95(I_O-3.3mA)]mA$. However, it will heat faster and take a greater share after a few seconds.




Figure 2. Power Calculation of the XTR101 with an External Transistor



Although any NPN of suitable power rating will operate with the XTR101, two readily available transistors are recommended:

- 2N2222 in the TO-18 package. For power-supply voltages above 24V, a 750Ω, 1/2W resistor should be connected in series with the collector. This will limit the power dissipation to 377mW under the worst-case conditions; see Figure 2. Thus, the 2N2222 will safely operate below its 400mW rating at the upper temperature of +85°C. Heat sinking the 2N2222 will result in greatly reduced accuracy improvement and is not recommended.
- TIP29B in the TO-220 package. This transistor will operate over the specified temperature and output voltage range without a series collector resistor. Heat sinking the TIP29B will result in slightly less accuracy improvement. It can be done, however, when mechanical constraints require it.

ACCURACY WITH AND WITHOUT AN EXTERNAL TRANSISTOR

The XTR101 has been tested in a circuit using an external transistor. The relative difference in accuracy with and without an external transistor is shown in Figure 3. Notice that a dramatic improvement in offset voltage change with supply voltage is evident for any value of load resistor.




Figure 3. Thermal Feedback Due to Change in Output Current

MAJOR POINTS TO CONSIDER WHEN USING THE XTR101

- 1. The leads to R_S should be kept as short as possible to reduce noise pick-up and parasitic resistance.
- 2. $+V_{CC}$ should be bypassed with a $0.01\mu F$ capacitor as close to the unit as possible (pin 8 to pin 7).
- Always keep the input voltages within their range of linear operation, +4V to +6V (e₁ and e₂ measured with respect to pin 7).
- 4. The maximum input signal level (e_{INFS}) is 1V with $R_S = \infty$ and proportionally less as R_S decreases.
- Always return the current references (pins 10 and 11) to the output (pin 7) through an appropriate resistor. If the references are not used for biasing or excitation, connect them together to pin 7. Each reference must have between 0V and +(V_{CC} 4V) with respect to pin 7.
- Always choose R_L (including line resistance) so that the voltage between pins 7 and 8 (+V_{CC}) remains within the 11.6V to 40V range as the output changes between the 4-20mA range (as shown in Figure 4).
- 7. It is recommended that a reverse polarity protection diode (D₁ in Figure 1) be used. This will prevent damage to the XTR101 caused by a momentary (such as a transient) or long-term application of the wrong polarity of voltage between pins 7 and 8.
- 8. Consider PC board layout which minimizes parasitic capacitance, especially in high gain.




Figure 4. Power-Supply Operating Range



SELECTING THE RS

 R_{SPAN} is chosen so that a given full-scale input span (e_INFs) will result in the desired full-scale output span of ΔI_{OFS} :

$$\left[\left(0.016 \frac{\text{amps}}{\text{volt}} \right) + \left(\frac{40}{R_S} \right) \right] \Delta e_{\text{IN}} = \Delta I_O = 16 \text{mA}.$$

Solving for R_S:

$$R_{S} = \frac{40}{\Delta I_{O}/\Delta e_{IN} - 0.016 \frac{amps}{volt}}$$
 (1)

For example, if $\Delta e_{INFS} = 100 \text{mV}$ for $\Delta l_{OFS} = 16 \text{mA}$,

$$R_{S} = \frac{40}{(16\text{mA}/100\text{mV}) - 0.016} = \frac{40}{0.16 - 0.016}$$
$$= \frac{40}{0.144} = 278\Omega$$

See the Typical Characteristics for a plot of R_S vs $\Delta e_{\text{INFS}}.$ Note that in order not to exceed the 20mA upper range limit, e_{IN} must be less than 1V when $R_S = \infty$ and proportionately smaller as R_S decreases.

BIASING THE INPUTS

Because the XTR operates from a single supply, both e_1 and e_2 must be biased approximately 5V above the voltage at pin 7 to assure linear response. This is easily done by using one or both current sources and an external resistor, R_2 . Figure 5 shows the simplest case—a floating voltage source e'_2 . The 2mA from the current sources flows through the 2.5k Ω value of R_2 and both e_1 and e_2 are raised by the required 5V with respect to pin 7. For linear operation the constraint is:

$$+4V \le e_1 \le +6V$$

 $+4V \le e_2 \le +6V$

The offset adjustment is used to remove the offset voltage of the input amplifier. When the input differential voltage (e_{IN}) equals zero, adjust for 4mA output.

Figure 6 shows a similar connection for a resistive transducer. The transducer could be excited either by one (as shown) or both current sources. Also, the offset adjustment has higher resolution compared to Figure 5.




Figure 5. Basic Connection for Floating Voltage Source




Figure 6. Basic Connection for Resistive Source

CMV AND CMR

The XTR101 is designed to operate with a nominal 5V common-mode voltage at the input and will function properly with either input operating over the range of 4V to 6V with respect to pin 7. The error caused by the 5V CMV is already included in the accuracy specifications.

If the inputs are biased at some other CMV, then an input offset error term is (CMV - 5)/CMRR, where CMR is in dB, and CMRR is in V/V.



SIGNAL SUPPRESSION AND ELEVATION

In some applications, it is desired to have suppressed zero range (input signal elevation) or elevated zero range (input signal suppression). This is easily accomplished with the XTR101 by using the current sources to create the suppression/elevation voltage. The basic concept is shown in Figure 7 and Figure 8(a). In this example, the sensor voltage is derived from R_T (a thermistor, RTD, or other variable resistance element) and excited by one of the 1mA current sources. The other current source is used to create the elevated zero range voltage. Figure 8(b), (c), and (d) show some of the possible circuit variations. These circuits have the desirable feature of noninteractive span and suppression/elevation adjustments.

Note: It is not recommended to use the optional offset voltage null (pins 1, 2, and 14) for elevation/suppression. This trim capability is used only to null the amplifier's input offset voltage. In many applications the already low offset voltage (typically $20\mu V$) will not need to be nulled at all. Adjusting the offset voltage to non-zero values will disturb the voltage drift by $\pm 0.3\mu V/^{\circ} C$ per $100\mu V$ or induced offset.




Figure 7. Elevation and Suppression Graph




Figure 8. Elevation and Suppression Circuits

APPLICATION INFORMATION

The small size, low offset voltage and drift, excellent linearity, and internal precision current sources make the XTR101 ideal for a variety of two-wire transmitter applications. It can be used by OEMs producing different types of transducer transmitter modules and by data acquisition systems manufacturers who gather transducer data. Current-mode transmission greatly reduces noise interference. The two-wire nature of the device allows economical signal conditioning at the transducer. Thus the XTR101 is, in general, very suitable for individualized and special-purpose applications.



EXAMPLE 1

An RTD transducer is shown in Figure 9.

Given a process with temperature limits of +25°C and +150°C, configure the XTR101 to measure the temperature with a platinum RTD which produces 100Ω at 0°C and 200Ω at +266°C (obtained from standard RTD tables). Transmit 4mA for +25°C and 20mA for +150°C.

COMPUTING RS:

The sensitivity of the RTD is $\Delta R/\Delta T=100\Omega/266^{\circ}C$. When excited with a 1mA current source for a 25°C to 150°C range (a 125°C span), the span of e_{IN} is $1mA \times (100\Omega/266^{\circ}C) \times 125^{\circ}C = 47mV = \Delta e_{IN}$.

From Equation 1,
$$R_S = \frac{40}{\Delta I_O/\Delta e_{IN} - 0.016 \frac{amps}{volt}}$$

$$R_S = \frac{40}{16mA/47mV - 0.016A/V} = \frac{40}{0.3244} = 123.3\Omega$$

Span adjustment (calibration) is accomplished by trimming R_S .

COMPUTING R4:

At
$$+25^{\circ}\text{C}$$
, $\text{e'}_2 = 1\text{mA}(\text{R}_{\text{T}} + \Delta \text{R}_{\text{T}})$
= $1\text{mA} \left[100\Omega + \frac{100\Omega}{266^{\circ}\text{C}} \times 25^{\circ}\text{C} \right]$
= $1\text{mA}(109.4\Omega) = 109.4\text{mV}$

In order to make the lower range limit of 25°C correspond to the output lower range limit of 4mA, the input circuitry shown in Figure 9 is used.

e_{IN}, the XTR101 differential input, is made 0 at 25°C or:

$$e'_{2\ 25^{\circ}C} - V_{4}$$

thus, $V_{4} = e'_{2\ 25^{\circ}C} = 109.4 \text{mV}$
 $R_{4} = \frac{V_{4}}{1 \text{mA}} = \frac{109.4 \text{mV}}{1 \text{mA}} = 109.4 \Omega$

COMPUTING R2 AND CHECKING CMV:

At
$$+25^{\circ}\text{C}$$
, $\text{e'}_2 = 109.4\text{mV}$
At $+150^{\circ}\text{C}$, $\text{e'}_2 = 1\text{mA}(\text{R}_{\text{T}} + \Delta \text{R}_{\text{T}})$
 $= 1\text{mA} \left[100\Omega + \frac{100\Omega}{266^{\circ}\text{C}} \times 150^{\circ}\text{C} \right]$
 $= 156.4\text{mV}$

Since both e'_2 and V_4 are small relative to the desired 5V common-mode voltage, they may be ignored in computing R_2 as long as the CMV is met.

$$R_2 = \frac{5V}{2mA} = 2.5k\Omega$$
 $e_2 min = 5V + 0.1094V$
 $e_2 max = 5V + 0.1564V$
 $e_1 = 5V + 0.1094V$

The 4V to 6V CMV requirement is met.




Figure 9. Circuit for Example 1

EXAMPLE 2

A thermocouple transducer is shown in Figure 10.

Given a process with temperature (T_1) limits of $0^{\circ}C$ and $+1000^{\circ}C$, configure the XTR101 to measure the temperature with a type J thermocouple that produces a 58mV change for $1000^{\circ}C$ change. Use a semiconductor diode for cold junction compensation to make the measurement relative to $0^{\circ}C$. This is accomplished by supplying a compensating voltage (V_{R6}) equal to that normally produced by the thermocouple with its cold junction (T_2) at ambient. At a typical ambient of $+25^{\circ}C$, this is 1.28mV (obtained from standard thermocouple tables with reference junction of $0^{\circ}C$). Transmit 4mA for $T_1 = 0^{\circ}C$ and 20mA for $T_1 = +1000^{\circ}C$. Note: $e_{IN} = e_2 - e_1$ indicates that T_1 is relative to T_2 .




Figure 10. Thermocouple Input Circuit with Two Temperature Regions and Diode (D) Cold Junction Compensation



ESTABLISHING RS:

The input full-scale span is 58mV ($\Delta e_{INFS} = 58mV$).

R_S is found from Equation 1.

$$\begin{split} R_S &= \frac{40}{\Delta I_0/\Delta e_{IN} - 0.016 \frac{amps}{volt}} \\ &= \frac{40}{16mA/58mV - 0.016A/V} = \frac{40}{0.2599} = 153.9 \Omega \end{split}$$

SELECTING R₄:

 R_4 is chosen to make the output 4mA at $T_{TC}=0^{\circ}C$ (V $_{TC}=-1.28$ mV) and $T_D=+25^{\circ}C$ (V $_D=0.6$ V); see Figure 10.

 V_{TC} will be -1.28mV when T_{TC} = 0°C and the reference junction is at +25°C. e_1 must be computed for the condition of T_D = +25°C to make e_{IN} = 0V.

$$\begin{split} V_{D\,25^{0}C} &=\,600\text{mV} \\ e_{1\,25^{0}C} &=\,600\text{mV} \Big(\frac{51}{2051}\Big) =\,14.9\text{mV} \\ e_{IN} &=\,e_{2}\,-\,e_{1} =\,V_{TC}\,+\,V_{4}\,-\,e_{1} \end{split}$$

With
$$e_{IN}$$
 = 0 and V_{TC} = -1.28mV,
$$V_4 = e_1 + e_{IN} - V_{TC}$$
 = 14.9mV + 0V - (- 1.28mV)
$$1mA(R_4) = 16.18mV$$

$$R_4 = 16.18\Omega$$

COLD JUNCTION COMPENSATION:

A temperature reference circuit is shown in Figure 11.

The diode voltage has the form:

$$V_D = \frac{KT}{q} In \frac{I_{DIODE}}{I_{SAT}}$$

Typically at T $_2$ = +25°C, V $_D$ = 0.6V and $\Delta V_D/\Delta T$ = -2mV/°C. R $_5$ and R $_6$ form a voltage divider for the diode voltage V $_D$. The divider values are selected so that the gradient $\Delta V_D/\Delta T$ equals the gradient of the thermocouple at the reference temperature. At +25°C this is approximately 52 μ V/°C (obtained from a standard thermocouple table); therefore,

$$\begin{split} \frac{\Delta T_{C}}{\Delta T} &= \frac{\Delta V_{D}}{\Delta T} \bigg(\frac{R_{6}}{R_{5} + R_{6}} \bigg) \\ \frac{52 \mu V}{^{\circ}C} &= \frac{2000 \mu V}{^{\circ}C} \bigg(\frac{R_{6}}{R_{5} + R_{6}} \bigg) \end{split} \tag{2}$$

 R_5 is chosen as $2k\Omega$ to be much larger than the resistance of the diode. Solving for R_6 yields 51Ω .




Figure 11. Cold Junction Compensation Circuit

THERMOCOUPLE BURN-OUT INDICATION

In process control applications it is desirable to detect when a thermocouple has burned out. This is typically done by forcing the two-wire transmitter current to either limit when the thermocouple impedance goes very high. The circuits of Figure 16 and Figure 17 inherently have downscale indication. When the impedance of the thermocouple gets very large (open) the bias current flowing into the + input (large impedance) will cause $I_{\rm O}$ to go to its lower range limit value (about 3.8mA). If upscale indication is desired, the circuit of Figure 18 should be used. When $T_{\rm C}$ opens, the output will go to its upper range limit value (about 25mA or higher).

OPTIONAL INPUT OFFSET VOLTAGE TRIM

The XTR101 has provisions for nulling the input offset voltage associated with the input amplifiers. In many applications the already low offset voltages ($30\mu V$ max for the B grade and $60\mu V$ max for the A grade) will not need to be nulled at all. The null adjustment can be done with a potentiometer at pins 1, 2, and 14; see Figure 5 and Figure 6. Either of these two circuits may be used. NOTE: It is not recommended to use this input offset voltage nulling capability for elevation or suppression. See the *Signal Suppression and Elevation* section for the proper techniques.



OPTIONAL BANDWIDTH CONTROL

Low-pass filtering is recommended where possible and can be done by either one of two techniques; see Figure 12. C_2 connected to pins 3 and 4 will reduce the bandwidth with a cutoff frequency given by:

$$f_{CO} = \frac{15.9}{(R_1 + R_2 + R_3 + R_4)(C_2 + 3pF)}$$

This method has the disadvantage of having f_{CO} vary with $R_1,\,R_2,\,R_3,\,R_4$, and it may require large values of R_3 and R_4 . The other method, using C_1 , will use smaller values of capacitance and is not a function of the input resistors. It is, however, more subject to nonlinear distortion caused by slew rate limiting. This is normally not a problem with the slow signals associated with most process control transducers. The relationship between C_1 and f_{CO} is shown in the Typical Characteristics.




Figure 12. Optional Filtering

APPLICATION CIRCUITS




Figure 13. 0-20mA Output Converter






Figure 14. Bridge Input, Voltage Excitation




Figure 15. Bridge Input, Current Excitiation




Figure 16. Thermocouple Input with RTD Cold Junction Compensation




Figure 17. Thermocouple Input with Diode Cold Junction Compensation




Figure 18. Thermocouple Input with RTD Cold Junction Compensation






Figure 19. Dual Precision Current Sources Operated from One Supply




Figure 20. Isolated Two-Wire Current Loop



DETAILED ERROR ANALYSIS

The ideal output current is:

$$I_{O IDEAL} = 4mA + K e_{IN}$$
 (3)

where K is the span (gain) term,
$$\left(0.016 \frac{\text{amps}}{\text{volt}} + \left(\frac{40}{R_S}\right)\right)$$

In the XTR101 there are three major components of error:

- 1. σ_O = errors associated with the output stage.
- 2. σ_S = errors associated with span adjustment.
- 3. σ_I = errors associated with the input stage.

The transfer function including these errors is:

$$I_{OACTUAL} = (4mA + \sigma_O) + K(1 + \sigma_S)(e_{IN} + \sigma_I)$$
 (4)

When this expression is expanded, second-order terms (σ_S, σ_I) dropped, and terms collected, the result is:

$$I_{O \text{ ACTUAL}} = (4\text{mA} + \sigma_{O}) + K e_{IN} + K\sigma_{I} + K\sigma_{S} e_{IN}$$
 (5)

The error in the output current is I_{O ACTUAL} – I_{O IDEAL} and can be found by subtracting Equation 3 from Equation 5.

$$I_{OERROR} = \sigma_O + K\sigma_I + K\sigma_S e_{IN}$$
 (6)

This is a general error expression. The composition of each component of error depends on the circuitry inside the XTR101 and the particular circuit in which it is applied. The circuit of Figure 9 will be used to illustrate the principles.

$$\sigma_{\rm O} = I_{\rm OS\,RTO} \tag{7}$$

$$\sigma_{\rm S} = \varepsilon_{\rm NONLINEARITY} + \varepsilon_{\rm SPAN}$$
 (8)

$$\sigma_{I} = V_{OSI} + (I_{B1} + R_4 - I_{B2} R_T) + \frac{\Delta V_{CC}}{PSRR} + \frac{(e_1 + e_2)}{2} - 5V$$
 (9)

The term in parentheses may be written in terms of offset current and resistor mismatches as $I_{B1} \Delta R + I_{OS}' R_4$.

 $V_{OSI}^{(1)}$ = input offset voltage.

 $I_{B1}^{(1)}$, $I_{B2}^{(1)}$ = input bias current.

 $I_{OSI}^{(1)}$ = input offset current.

 $I_{OS RTO}^{(1)}$ = output offset current error.

 $\Delta R = R_T - R_4 = mismatch in resistor.$

 ΔV_{CC} = change supply voltage between pins 7 and 8 away from 24V nominal.

 $PSRR^{(1)}$ = power-supply rejection ratio.

 $CMRR^{(1)} = common-mode rejection ratio.$

 $\varepsilon_{\text{NONLIN}}^{(1)}$ = span nonlinearity.

 $\varepsilon_{\text{SPAN}}^{(1)}$ = span equation error.

Untrimmed error = 5% max. May be trimmed to zero.

(1) These items can be found in the Electrical Characteristics.

EXAMPLE 3

See the circuit in Figure 9 with the XTR101BG specifications and the following conditions: $R_T=109.4\Omega$ at $25^{\circ}C,\,R_T=156.4\Omega$ at $150^{\circ}C,\,I_O=4\text{mA}$ at $25^{\circ}C,\,I_O=20\text{mA}$ at $150^{\circ}C,\,R_S=123.3\Omega,\,R_4=109\Omega,\,R_L=250\Omega,\,R_{LINE}=100\Omega,\,V_{DI}=0.6\text{V},$ and $V_{PS}=24\text{V}\pm0.5\%.$ Determine the % error at the upper and lower range values.

A. AT THE LOWER RANGE VALUE (T = $+25^{\circ}$ C)

$$\sigma_{O}$$
 = $I_{OS\,RTO}$ = \pm 6 μA

$$\sigma_{l} = V_{OSI} + \left(I_{BI} \Delta R + I_{OSI} R_{4}\right) + \frac{\Delta V_{CC}}{PSRR} + \left[\frac{\left[e_{1} + e_{2}\right]}{2} - 5V\right]$$

$$\Delta R = R_{T25^{\circ}C} - R_4 = 109.4 - 109 \approx 0$$

 $\Delta V_{CC} = (24 \times 0.005) + 4\text{mA}(250\Omega + 100\Omega) + 0.6V$
= 120mV + 1400mV + 600mV = 2120mV

$$e_1 = (2mA \times 2.5k\Omega) + (1mA \times 109\Omega)$$

= 5.109V
 $e_1 = (2mA \times 2.5k\Omega) + (1mA \times 109.4\Omega)$

$$\begin{aligned} \mathbf{e_2} &= (2\mathrm{mA} \times 2.5\mathrm{k}\Omega) + (1\mathrm{mA} \times 109.4\Omega) \\ &= 5.1094\mathrm{V} \end{aligned}$$

$$\frac{(e_1 + e_2)}{2} - 5V = 0.1092V$$

$$PSRR = 3.16 \times 10^5 \text{ for } 110dB$$

CMRR =
$$31.6 \times 10^3$$
 for 90dB

$$\begin{split} \sigma_1 &= 30\mu V + (150\text{nA} \times 0 + 20\text{nA} \times 109\Omega) + \\ &\frac{2120\text{mV}}{3.16 \times 10^5} + \frac{0.1092\text{V}}{3.16 \times 10^3} \\ &= 30\mu V + 2.18\mu V + 6.7\mu V + 3.46\mu V \\ &= 42.34\mu V \end{split}$$

$$\begin{split} \sigma_{\text{S}} &= \, \epsilon_{\text{NONLIN}} \, + \, \epsilon_{\text{SPAN}} \\ &= \, 0.0001 \, + \, 0 \, (\text{assumes trim of R}_{\text{S}}) \end{split}$$

$$\begin{split} I_{\text{O ERROR}} &= \, \sigma_{\text{O}} \, + \, K \, \sigma_{\text{I}} \, + \, K \, \sigma_{\text{S}} \, e_{\text{IN}} \\ K &= \, 0.016 \, + \, \frac{40}{R_{\text{S}}} = \, 0.016 \, + \, \frac{40}{123.3\Omega} \\ &= \, 0.340 \frac{\text{amps}}{\text{volts}} \end{split}$$

$$e_{IN} = e_2 - V_4 = I_{REF1} R_{T25^{\circ}C} - I_{REF2} R_4$$

Since $R_{T 25^{\circ}C} = R_4$:

$$e_{IN} = (I_{REF1} - I_{REF2}) R_4 = 0.4 \mu A \times 109 \Omega$$

= 43.6 \(\mu V \)

Since the maximum mismatch of the current references is 0.04% of $1mA = 0.4\mu A$:

$$\begin{split} I_O & \, \text{error} \, = \, 6 \mu A \, + \, \left(0.34 A / V \, \times \, 42.34 \mu V \right) \, + \\ & \left(0.34 A / V \, \times \, 0.0001 \, \times \, 43.6 \mu V \right) \\ & = \, 6 \mu A \, + \, 14.40 \mu A \, + \, 0.0015 \mu A \, = \, 20.40 \mu A \\ \% & \, \text{error} \, = \, \frac{20.40 \mu A}{16 m A} \, \times \, 100\% \end{split}$$

0.13% of span at lower range value.



B. AT THE UPPER RANGE VALUE (T = $+150^{\circ}$ C)

$$\begin{split} \Delta R &= R_{\text{T }150^{\text{O}}\text{C}} - R_4 = 156.4 - 109.4 = 47\Omega \\ \Delta V_{\text{CC}} &= (24 \times 0.005) + 20\text{mA}(250\Omega + 100\Omega) + 0.6V \\ &= 7720\text{mV} \\ \\ e_1 &= 5.109\text{V} \\ e_2 &= (2\text{mA} \times 2.5\text{k}\Omega) + (1\text{mA} \times 156.4\Omega) \\ &= 5.156\text{V} \\ \\ \frac{(e_1 - e_2)}{2} - 5\text{V} &= 0.1325\text{V} \\ \\ \sigma_0 &= 6\mu\text{A} \\ \sigma_1 &= 30\mu\text{V} + (150\text{nA} \times 47\Omega + 20\text{nA} \times 190\Omega) + 0.6V \\ \end{split}$$

$$\begin{split} \frac{7720\text{mV}}{3.16\times10^5} + \frac{0.1325\text{V}}{3.16\times10^3} \\ &= 30\mu\text{V} + 9.23\mu\text{V} + 24\mu\text{V} + 4.19\mu\text{V} \\ &= 67.42\mu\text{V} \\ \sigma_S &= 0.0001 \\ e_{\text{IN}} &= e'_2 - \text{V}_4 = \text{I}_{\text{REF1}} \, \text{R}_{\text{T}\,\text{150°C}} - \text{I}_{\text{REF2}} \, \text{R}_4 \\ &= (1\text{mA}\times156.4\Omega) - (1\text{mA}\times109\Omega) \\ &= 47\text{mV} \end{split}$$

$$\begin{split} I_{O} & \text{error} = \sigma_{O} + K \, \sigma_{I} + K \, \sigma_{S} \, e_{IN} \\ & = 6 \mu A + (0.34 \text{A/V} \times 67.42 \mu \text{V}) + \\ & (0.34 \text{A/V} \times 0.0001 \times 47000 \mu \text{V}) \\ & = 6 \mu A + 22.92 \mu A + 1.60 \mu A \\ & = 30.52 \mu A \\ \% & \text{error} = \frac{30.52 \mu A}{16 \text{mA}} \times 100\% \end{split}$$

0.19% of span at upper range value.

CONCLUSIONS

Lower Range: From Equation 10, it is observed that the predominant error term is the input offset voltage ($30\mu V$ for the B grade). This is of little consequence in many applications. $V_{OS\ RTI}$ can, however, be nulled using the plots shown in Figure 5 and Figure 6. The result is an error of 0.06% of span instead of 0.13% of span.

Upper Range: From Equation 11, the predominant errors are $I_{OS\ RTO}$ (6 μ A), $V_{OS\ RTI}$ (30 μ V), and I_{B} (150nA), max, B grade. Both I_{OS} and V_{OS} can be trimmed to zero; however, the result is an error of 0.09% of span instead of 0.19% of span.

RECOMMENDED HANDLING PROCEDURES FOR INTEGRATED CIRCUITS

All semiconductor devices are vulnerable, in varying degrees, to damage from the discharge of electrostatic energy. Such damage can cause performance degradation or failure, either immediate or latent. As a general practice, we recommend the following handling procedures to reduce the risk of electrostatic damage:

- Remove the static-generating materials (such as untreated plastic) from all areas that handle microcircuits.
- 2. Ground all operators, equipment, and work stations.
- Transport and ship microcircuits, or products incorporating microcircuits, in static-free, shielded containers.
- Connect together all leads of each device by means of a conductive material when the device is not connected into a circuit.
- Control relative humidity to as high a value as practical (50% recommended).

www.ti.com 7-Oct-2021

PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
XTR101AG	NRND	CDIP SB	JD	14	1	RoHS & Green	Call TI	N / A for Pkg Type		XTR101AG	
XTR101AP	ACTIVE	PDIP	N	14	25	RoHS & Green	NIPDAU	N / A for Pkg Type	-40 to 85	XTR101AP	Samples
XTR101AU	ACTIVE	SOIC	DW	16	40	RoHS & Green	NIPDAU	Level-3-260C-168 HR	-40 to 85	XTR101AU	Samples
XTR101AU/1K	ACTIVE	SOIC	DW	16	1000	RoHS & Green	NIPDAU	Level-3-260C-168 HR	-40 to 85	XTR101AU	Samples
XTR101BG	NRND	CDIP SB	JD	14	1	RoHS & Green	Call TI	N / A for Pkg Type	-40 to 85	XTR101BG	

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and



PACKAGE OPTION ADDENDUM

www.ti.com 7-Oct-2021

continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

PACKAGE MATERIALS INFORMATION

www.ti.com 3-Jun-2022

TAPE AND REEL INFORMATION





A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	U	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
XTR101AU/1K	SOIC	DW	16	1000	330.0	16.4	10.75	10.7	2.7	12.0	16.0	Q1

PACKAGE MATERIALS INFORMATION

www.ti.com 3-Jun-2022



*All dimensions are nominal

Ì	Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
ı	XTR101AU/1K	SOIC	DW	16	1000	356.0	356.0	35.0

PACKAGE MATERIALS INFORMATION

www.ti.com 3-Jun-2022

TUBE




*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	T (µm)	B (mm)
XTR101AG	JD	CDIP SB	14	1	506.98	15.24	12290	NA
XTR101AP	N	PDIP	14	25	506	13.97	11230	4.32
XTR101AU	DW	SOIC	16	40	507	12.83	5080	6.6
XTR101BG	JD	CDIP SB	14	1	506.98	15.24	12290	NA

JD (R-CDIP-T14)

CERAMIC SIDE-BRAZE DUAL-IN-LINE



NOTES:

- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. Controlling dimension: inch.
- D. Leads within 0.005 (0,13) radius of true position (TP) at gage plane with maximum material condition and unit installed.
- E Angle applies to spread leads prior to installation.
- F Outlines on which the seating plane is coincident with the plane (standoff = 0), terminals lead standoffs are not required, and lead shoulder may equal lead width along any part of the lead above the seating/base plane.
- G Body width does not include particles of packing materials.
- H. A visual index feature must be located within the cross—hatched area.



7.5 x 10.3, 1.27 mm pitch

SMALL OUTLINE INTEGRATED CIRCUIT

This image is a representation of the package family, actual package may vary. Refer to the product data sheet for package details.





SOIC



NOTES:

- 1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing
- per ASME Y14.5M.

 2. This drawing is subject to change without notice.

 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm, per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm, per side.
- 5. Reference JEDEC registration MS-013.



SOIC



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SOIC



NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.



N (R-PDIP-T**)

PLASTIC DUAL-IN-LINE PACKAGE

16 PINS SHOWN



NOTES:

- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
- The 20 pin end lead shoulder width is a vendor option, either half or full width.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022, Texas Instruments Incorporated