

### **Overview**

The KEMET ESU radial aluminum electrolytic capacitors are designed for long life (up to 12,000 hours) applications.

## **Applications**

Typical applications include electronic lighting and power.

## **Benefits**

#### • Long life, up to 12,000 hours

- Operating temperature of up to +105°C
- · Safety vent on the capacitor base



## **Part Number System**

ESU	336	Μ	160	Α	H8	AA
Series	Capacitance Code (pF)	Tolerance	Rated Voltage (VDC)	Electrical Parameters	Size Code	Packaging
Radial Aluminum Electrolytic	First two digits represent significant figures for capacitance values. Last digit specifies the number of zeros to be added.	M = ±20%	160 = 160 200 = 200 250 = 250 350 = 350 400 = 400 450 = 450	A = Standard	See Dimension Table	See Ordering Options Table

Diameter	Length	Packaging Type	Lead Type	Lead Length (mm)	Lead and Packaging Code						
		Standard Bul	k Packaging Options								
4 - 22	4 - 22AllBulk (bag)Straight20/15 Minimum										
	Tape & Reel										
4 - 5	All	Tape & Reel	Formed to 2.5 mm	H <sub>0</sub> = 16 ±0.75	LA						
4 - 8	All	Tape & Reel	2.5 mm lead spacing	H <sub>0</sub> = 18.5 ±0.75	KA						
4 - 8	All	Tape & Reel	Formed to 5 mm	H <sub>0</sub> = 16 ±0.75	JA						
10	≤ 20	Tape & Reel	Straight	H <sub>0</sub> = 18.5 ±0.75	KA						
		Ar	nmo Pack								
4 - 8	All	Ammo	Formed to 5 mm	H <sub>0</sub> = 16 ±0.75	DA						
4 - 8	All	Ammo	Straight	H <sub>0</sub> = 18.5 ±0.75	EA						
4 - 5	All	Ammo	Formed to 2.5 mm	H <sub>0</sub> = 16 ±0.75	FA						
10 - 13	All	Ammo	5 mm lead spacing	H <sub>0</sub> = 18.5 ±0.75	EA						
16	All	Ammo	7.5 mm lead spacing	H <sub>0</sub> = 18.5 ±0.75	EA						
18	≤ 25	Ammo	7.5 mm lead spacing	H <sub>0</sub> = 18.5 ±0.75	EA						
		Contact KEMET for oth	er lead and packaging op	tions							

# **Ordering Options Table**

## **Environmental Compliance**


As an environmentally conscious company, KEMET is working continuously with improvements concerning the environmental effects of both our capacitors and their production. In Europe (RoHS Directive) and in some other geographical areas like China, legislation has been put in place to prevent the use of some hazardous materials, such as lead (Pb), in electronic equipment. All products in this catalog are produced to help our customers' obligations to guarantee their products and fulfill these legislative requirements. The only material of concern in our products has been lead (Pb), which has been removed from all designs to fulfill the requirement of containing less than 0.1% of lead in any homogeneous material. KEMET will closely follow any changes in legislation world wide and make any necessary changes in its products, whenever needed.

Some customer segments such as medical, military and automotive electronics may still require the use of lead in electrode coatings. To clarify the situation and distinguish products from each other, a special symbol is used on the packaging labels for RoHS compatible capacitors.

Due to customer requirements, there may appear additional markings such as lead free (LF) or lead-free wires (LFW) on the label.



### **Dimensions – Millimeters**



Size Code	I	D		L		Р		d	LL+/LL-
Size Code	Nominal	Tolerance	Nominal	Tolerance	Nominal	Tolerance	Nominal	Tolerance	Minimum
H8	10	±0.5	16	+2.0/-0	5.0	±0.5	0.6	Nominal	20/15
H4	10	±0.5	20	+2.0/-0	5.0	±0.5	0.6	Nominal	20/15
L3	13	±0.5	20	+2.0/-0	5.0	±0.5	0.6	Nominal	20/15
L4	13	±0.5	25	+2.0/-0	5.0	±0.5	0.6	Nominal	20/15
M5	16	±0.5	20	+2.0/-0	7.5	±0.5	0.8	Nominal	20/15
M7	16	±0.5	25	+2.0/-0	7.5	±0.5	0.8	Nominal	20/15
M2	16	±0.5	32	+2.0/-0	7.5	±0.5	0.8	Nominal	20/15
M3	16	±0.5	36	+2.0/-0	7.5	±0.5	0.8	Nominal	20/15
N5	18	±0.5	25	+2.0/-0	7.5	±0.5	0.8	Nominal	20/15
N1	18	±0.5	32	+2.0/-0	7.5	±0.5	0.8	Nominal	20/15
N2	18	±0.5	36	+2.0/-0	7.5	±0.5	0.8	Nominal	20/15
N9	18	±0.5	50	+2.0/-0	7.5	±0.5	0.8	Nominal	20/15

## **Performance Characteristics**

Item	Performance Characteristics					
Capacitance Range	6.3 – 330 μF					
Capacitance Tolerance	±20% at 120 Hz/20°C					
Rated Voltage	160 - 450 VDC					
Life Test	8,000 – 10,000 hours (see conditions in Test Methods & Performance)					
Operating Temperature	-25°C to +105°C					
	I ≤ 0.04 CV +100 μA					
Leakage Current	C = rated capacitance ( $\mu$ F), V = rated voltage (VDC). Voltage applied for 2 minutes at 20°C.					

# Impedance Z Characteristics at 120 Hz

Rated Voltage (VDC)	160	200	250	350	400	450
Z (-25°C)/Z (20°C)	3	3	3	5	5	6

# **Compensation Factor of Ripple Current (RC) vs. Frequency**

Rated Voltage (VDC)	120 Hz	1 kHz	10 kHz	100 kHz	
Coefficient	0.50	0.80	0.90	1.00	

## **Test Method & Performance**

Conditions	Load Li	fe Test	Shelf Life Test	
Temperature	105	5°C	105°C	
Test Duration	Can Ø = 10.0 mm	10,000 hours		
Test Duration	Can Ø ≥ 12.5 mm	1,000 hours		
Ripple Current	Maximum ripple current specified	No ripple current applied		
Voltage	The sum of DC voltage and the pea the rated voltage of the capacitor	ak AC voltage must not exceed	No voltage applied	
Performance	The following specification	s will be satisfied when the ca	apacitor is restored to 20°C:	
Capacitance Change	Within ±20% of the initial value			
Dissipation Factor	Does not exceed 200% of the spec			
Leakage Current	Does not exceed specified value			



## Shelf Life

The capacitance, ESR and impedance of a capacitor will not change significantly after extended storage periods, however, the leakage current will very slowly increase.

KEMET's E aluminum electrolytic capacitors should not be stored in high temperatures or where there is a high level of humidity. The suitable storage condition for KEMET's E aluminum electrolytic capacitors is +5 to +35°C and less than 75% in relative humidity. KEMET's E aluminum electrolytic capacitors should not be stored in damp conditions such as water, saltwater spray or oil spray. KEMET's E aluminum electrolytic capacitors should not be stored in an environment full of hazardous gas (hydrogen sulphide, sulphurous acid gas, nitrous acid, chlorine gas, ammonium, etc.) KEMET's E aluminum electrolytic capacitors to ozone, ultraviolet rays or radiation.

If a capacitor has been stored for more than 18 months under these conditions and it shows increased leakage current, then a treatment by voltage application is recommended.

## **Re-Age (Reforming) Procedure**

Apply the rated voltage to the capacitor at room temperature for a period of one hour, or until the leakage current has fallen to a steady value below the specified limit. During re-aging a maximum charging current of twice the specified leakage current or 5 mA, whichever is greater, is suggested.



### Table 1 – Ratings & Part Number Reference

VDC	Rated Capacitance 120 Hz 20°C (µF)	Case Size D x L (mm)	DF 120 Hz 20°C (tan δ %)	RC 100 kHz 105°C (mA)	LC 20°C 2 Minutes (µA)	Part Number
160	33	10 x 16	15	500	311.2	ESU336M160AH8(1)
160	47	10 x 20	15	580	400.8	ESU476M160AH4(1)
160	68	13 x 20	15	720	535.2	ESU686M160AL3(1)
160	100	13 x 25	15	970	740.0	ESU107M160AL4(1)
160	150	16 x 25	15	1120	1060.0	ESU157M160AM7(1)
160	220	16 x 32	15	1300	1508.0	ESU227M160AM2(1)
160	330	18 x 36	15	1380	2212.0	ESU337M160AN2(1)
160	560	18 x 50	15	2086	3684.0	ESU567M160AN9(1)
200	22	10 x 16	15	500	276.0	ESU226M200AH8(1)
200	33	10 x 20	15	520	364.0	ESU336M200AH4(1)
200	47	13 x 20	15	660	476.0	ESU476M200AL3(1)
200	68	13 x 25	15	720	644.0	ESU686M200AL4(1)
200	100	16 x 25	15 15	1120	900.0	ESU107M200AM7(1)
200 200	150 220	16 x 32 18 x 32	15	1620 2080	1300.0 1860.0	ESU157M200AM2(1)
200	390	18 x 32 18 x 50	15	3380	3220.0	ESU227M200AN1(1) ESU397M200AN9(1)
200	390 10	10 x 16	15	3380	200.0	ESU397M200AN9(1) ESU106M250AH8(1)
250	22	10 x 10	15	500	320.0	ESU226M250AH6(1)
250	33	10 x 20 13 x 20	15	800	430.0	ESU336M250AL3(1)
250	47	13 x 20	15	980	570.0	ESU476M250AL3(1)
250	100	16 x 25	15	1530	1100.0	ESU107M250AP2(1)
250	150	18 x 25	15	1940	1600.0	ESU157M250AN5(1)
250	220	18 x 36	15	2753	2300.0	ESU227M250AN2(1)
250	330	18 x 50	15	3912	3400.0	ESU337M250AN9(1)
350	6.8	10 x 16	20	280	195.2	ESU685M350AH8(1)
350	10	10 x 20	20	350	240.0	ESU106M350AH4(1)
350	22	13 x 20	20	650	408.0	ESU226M350AL3(1)
350	33	13 x 25	20	900	562.0	ESU336M350AL4(1)
350	47	16 x 25	20	1000	758.0	ESU476M350AM7(1)
350	68	16 x 32	20	1100	1052.0	ESU686M350AM2(1)
400	6.8	10 x 16	20	140	208.8	ESU685M400AH8(1)
400	10	10 x 20	20	180	260.0	ESU106M400AH4(1)
400	22	13 x 20	20	430	452.0	ESU226M400AL3(1)
400	33	16 x 25	20	520	628.0	ESU336M400AM7(1)
400	47	16 x 20	20	852	520	ESU476M400AM5(1)
400	47	16 x 32	20	700	852.0	ESU476M400AM2(1)
400	68	18 x 32	20	870	1188.0	ESU686M400AN1(1)
400	100	18 x 50	20	1290	1700.0	ESU107M400AN9(1)
450	10	10 x 20	20	180	280.0	ESU106M450AH4(1)
450	15	13 x 20	20	380	370.0	ESU156M450AL3(1)
450	22	13 x 25	20	500	496.0	ESU226M450AL4(1)
450	33	16 x 25	20	560	694.0	ESU336M450AM7(1)
450	47	16 x 36	20	880	946.0	ESU476M450AM3(1)
450	68	16 x 36	20	1110	1324.0	ESU686M450AM3(1)
450	100	18 x 50	20	1560	1900.0	ESU107M450AN9(1)
VDC	Rated Capacitance	Case Size	DF	RC	LC	Part Number

(1) Insert packaging code. See Ordering Options Table for available options.



## **Mounting Positions (Safety Vent)**

In operation, electrolytic capacitors will always conduct a leakage current, which causes electrolysis. The oxygen produced by electrolysis will regenerate the dielectric layer but, at the same time, the hydrogen released may cause the internal pressure of the capacitor to increase. The overpressure vent, or safety vent, ensures that the gas can escape when the pressure reaches a certain value. All mounting positions must allow the safety vent to work properly.

### Installing

- As a general principle, lower-use temperatures result in a longer, useful life of the capacitor. For this reason, it should be
  ensured that electrolytic capacitors are placed away from heat-emitting components. Adequate space should be allowed
  between components for cooling air to circulate, particularly when high ripple current loads are applied. In any case, the
  maximum category temperature must not be exceeded.
- Do not deform the case of the capacitors or use capacitors with a deformed case.
- Verify that the connections of the capacitors are able to insert on the board without excessive mechanical force.
- If the capacitors require mounting through additional means, the recommended mounting accessories shall be used.
- Verify the correct polarization of the capacitor on the board.
- Verify that the space around the pressure relief device is according to the following guideline:


Case Diameter	Space Around Safety Vent
≤ 16 mm	> 2 mm
> 16 to ≤ 40 mm	> 3 mm
> 40 mm	> 5 mm

It is recommended that capacitors always be mounted with the safety device uppermost or in the upper part of the capacitor.

- If the capacitors are stored for a long time, the leakage current must be verified. If the leakage current is superior to the value listed in this catalog, the capacitors must be reformed. In this case, they can be reformed by application of the rated voltage through a series resistor approximately 1 k $\Omega$  for capacitors with V<sub>R</sub> ≤ 160 V (5 W resistor) and 10 k $\Omega$  for the other rated voltages.
- In the case of capacitors connected in a series, a suitable voltage sharing must be used.
- In the case of balancing resistors, the approximate resistance value can be calculated as: R = 60/C.

KEMET recommends, nevertheless, to ensure that the voltage across each capacitor does not exceed its rated voltage.





Simplified equivalent circuit diagram of an electrolytic capacitor

The capacitive component of the equivalent series circuit, (equivalent series capacitance - ESC), is determined by applying an alternate voltage of  $\leq$  0.5 V at a frequency of 120 or 100 Hz and 20°C (IEC 384-1, 384-4).

### **Temperature Dependence of the Capacitance**

Capacitance of an electrolytic capacitor depends upon temperature: with decreasing temperature the viscosity of the electrolyte increases, thereby reducing its conductivity.

Capacitance will decrease if temperature decreases. Furthermore, temperature drifts cause armature dilatation and, therefore, capacitance changes (up to 20% depending on the series considered, from 0 to 80°C). This phenomenon is more evident for electrolytic capacitors than for other types.


### **Frequency Dependence of the Capacitance**

Effective capacitance value is derived from the impedance curve, as long as impedance is still in the range where the capacitance component is dominant.

C =  $\frac{1}{2\pi fZ}$  C = capacitance (F) f = frequency (Hz) Z = impedance ( $\Omega$ )

### Dissipation Factor tan $\delta$ (DF)

Dissipation Factor tan  $\delta$  is the ratio between the active and reactive power for a sinusoidal waveform voltage. It can be thought of as a measurement of the gap between an actual and ideal capacitor.



Tan  $\delta$  is measured with the same set-up used for the series capacitance ESC.

Tan  $\delta = \omega x$  ESC x ESR where:


ESC = Equivalent series capacitance

ESR = Equivalent series resistance



### **Equivalent Series Inductance (ESL)**

Equivalent series inductance or self inductance results from the terminal configuration and internal design of the capacitor.



### **Equivalent Series Resistance (ESR)**


Equivalent series resistance is the resistive component of the equivalent series circuit. ESR value depends on frequency and temperature, and is related to the tan  $\delta$  by the following equation:

 $ESR = \frac{\tan \delta}{2\pi f ESC}$   $ESR = Equivalent series resistance (\Omega)$  $tan \delta = Dissipation factor$ ESC = Equivalent series capacitance (F)f = Frequency (Hz)

Tolerance limits of the rated capacitance must be taken into account when calculating this value.

#### Impedance (Z)

Impedance of an electrolytic capacitor results from a circuit formed by the following individual equivalent series components:



C<sub>o</sub> = Aluminum oxide capacitance (surface and thickness of the dielectric.)

R<sub>e</sub> = Resistance of electrolyte and paper mixture (other resistances not depending on the frequency are not considered: tabs, plates, etc.)


C<sub>a</sub> = Electrolyte soaked paper capacitance.

L = Inductive reactance of the capacitor winding and terminals.

Impedance of an electrolytic capacitor is not a constant quantity that retains its value under all conditions; it changes depending on frequency and temperature.

Impedance as a function of frequency (sinusoidal waveform) for a certain temperature can be represented as follows:


### Impedance (Z) cont.



- Capacitive reactance predominates at low frequencies.
- With increasing frequency, capacitive reactance Xc = 1/ωC<sub>o</sub> decreases until it reaches the order of magnitude of electrolyte resistance R<sub>o</sub>(A)
- At even higher frequencies, resistance of the electrolyte predominates: Z = R (A B)
- When the capacitor's resonance frequency is reached ( $\omega_0$ ), capacitive and inductive reactance mutually cancel each other  $1/\omega C_a = \omega L$ ,  $\omega_0 = 1/SQR(LC_a)$
- Above this frequency, inductive reactance of the winding and its terminals (XL = Z = ωL) becomes effective and leads to an increase in impedance

Generally speaking, it can be estimated that  $C_a \approx 0.01 C_a$ .

Impedance as a function of frequency (sinusoidal waveform) for different temperature values can be represented as follows (typical values):



R<sub>e</sub> is the most temperature-dependent component of an electrolytic capacitor equivalent circuit. Electrolyte resistivity will decrease if temperature rises.

In order to obtain a low impedance value throughout the temperature range, R<sub>e</sub> must be as little as possible. However, R<sub>e</sub> values that are too low indicate a very aggressive electrolyte, resulting in a shorter life of the electrolytic capacitor at high temperatures. A compromise must be reached.




### Leakage Current (LC)

Due to the aluminum oxide layer that serves as a dielectric, a small current will continue to flow even after a DC voltage has been applied for long periods. This current is called leakage current.

A high leakage current flows after applying voltage to the capacitor then decreases in a few minutes, for example, after prolonged storage without any applied voltage. In the course of continuous operation, the leakage current will decrease and reach an almost constant value.

After a voltage-free storage the oxide layer may deteriorate, especially at a high temperature. Since there are no leakage currents to transport oxygen ions to the anode, the oxide layer is not regenerated. The result is that a higher than normal leakage current will flow when voltage is applied after prolonged storage.

As the oxide layer is regenerated in use, the leakage current will gradually decrease to its normal level. The relationship between the leakage current and voltage applied at constant temperature can be shown schematically as follows:



### Where:

 $V_{F}$  = Forming voltage

If this level is exceeded, a large quantity of heat and gas will be generated and the capacitor could be damaged.

 $V_{p}$  = Rated voltage

This level represents the top of the linear part of the curve.

 $V_s$  = Surge voltage

This lies between  $V_{R}$  and  $V_{F}$ . The capacitor can be subjected to  $V_{S}$  for short periods only.

Electrolytic capacitors are subjected to a reforming process before acceptance testing. The purpose of this preconditioning is to ensure that the same initial conditions are maintained when comparing different products.

### **Ripple Current (RC)**

The maximum ripple current value depends on:

- Ambient temperature
- Surface area of the capacitor (heat dissipation area)
- tan  $\delta$  or ESR
- Frequency

The capacitor's life depends on the thermal stress.



#### **Frequency Dependence of the Ripple Current**

ESR and, thus, the tan  $\delta$  depend on the frequency of the applied voltage. This indicates that the allowed ripple current is also a function of the frequency.

#### **Temperature Dependence of the Ripple Current**


The data sheet specifies maximum ripple current at the upper category temperature for each capacitor.

#### **Expected Life Calculation**

Expected life depends on operating temperature according to the following formula: L = Lo x  $2^{(To-T)/10}$  Where:

- L: Expected life
- Lo: Load life at a maximum permissible operating temperature
- T: Actual operating temperature
- To: Maximum permissible operating temperature

This formula is applicable between 40°C and To.






# **Packaging Quantities**

			Βι	ılk	Auto-ir	sertion
Size Code	Diameter (mm)	Length (mm)	Standard Leads	Cut Leads	Ammo	Tape & Reel
H8	10	16	3,000	4,000	700	1,200
H4	10	20	2,400	3,000	700	1,200
L3	13	20	2,000	2,000	500	
L4	13	25	1,600	1,600 1,600		
M5	16	20	1,000	500	300	
M7	16	25	1,000	500	300	
M2	16	32	800	500	300	
M3	16	36	600	500	300	
N5	18	25	800	500	300	
N1	18	32	500	500		
N2	18	36	500	500		
N9	18	50	500	500		



### Marking




#### \*Y = Year

Code	01	02	03	04	05	06	07	08	09
Year	2011	2012	2013	2014	2015	2016	2017	2018	2019

#### \*M = Month


Code	01	02	03	04	05	06	07	08	09	10	11	12
Month	1	2	3	4	5	6	7	8	9	10	11	12

## Construction







# **Taping for Automatic Insertion Machines**




Straight Leads (Diameter: 4 - 8 mm) Lead and packaging code EA and KA






Straight Leads (Diameter > 8) Lead and packaging code EA and KA




Dimensions (mm)	D	L	S	d	Ρ	<b>P0</b>	<b>P</b> 1	P2	w	WO	<b>W</b> 1	W2	HO	H1	I	DO	t
Tolerance	+0.5		+0.8/-0.2	±0.05	±1.0	±0.3	±0.7	±1.3	+1/-0.5	±0.5	Maximum	Maximum	±0.75	±0.5	Maximum	±0.2	±0.2
-	4	5 - 7	2.5	0.45	12.7	12.7	5.1	6.35	18	12	11	3	16.0	18.5		4	0.7
Formed to 2.5 mm	5	≤ 7	2.5	0.45	12.7	12.7	5.1	6.35	18	12	11	3	16.0	18.5		4	0.7
2.5 11111	Э	> 7	2.5	0.50	12.7	12.7	5.1	6.35	18	12	11	3	16.0	18.5		4	0.7
Formed to 5 mm	4	5 - 7	5.0	0.45	12.7	12.7	3.85	6.35	18	12	11	3	16.0	18.5		4	0.7
	5	≤ 7	5.0	0.45	12.7	12.7	3.85	6.35	18	12	11	3	16.0	18.5		4	0.7
	5	>7	5.0	0.50	12.7	12.7	3.85	6.35	18	12	11	3	16.0	18.5		4	0.7
	6	≤ 7	5.0	0.50	12.7	12.7	3.85	6.35	18	12	11	3	16.0	18.5		4	0.7
		> 7	5.0	0.50	12.7	12.7	3.85	6.35	18	12	11	3	16.0	18.5		4	0.7
	8	≤ 7	5.0	0.50	12.7	12.7	3.85	6.35	18	12	11	3	16.0	18.5		4	0.7
	0	> 7	5.0	0.50	12.7	12.7	3.85	6.35	18	12	11	3	16.0	18.5		4	0.7
	4	5 - 7	1.5	0.45	12.7	12.7	5.6	6.35	18	12	11	3	18.5			4	0.7
	5	≤ 7	2.0	0.45	12.7	12.7	5.35	6.35	18	12	11	3	18.5			4	0.7
Straight leads		> 7	2.0	0.50	12.7	12.7	5.35	6.35	18	12	11	3	18.5			4	0.7
	6	≤ 7	2.5	0.50	12.7	12.7	5.1	6.35	18	12	11	3	18.5			4	0.7
		> 7	2.5	0.50	12.7	12.7	5.1	6.35	18	12	11	3	18.5			4	0.7
	8	≤ 7	3.5	0.50	12.7	12.7	4.6	6.35	18	12	11	3	18.5			4	0.7
		> 7	3.5	0.50	12.7	12.7	4.6	6.35	18	12	11	3	18.5			4	0.7
	10	≤ 20	5.0	0.60	12.7	12.7	3.85	6.35	18	12	11	3	18.5		1	4	1.0



# Lead Taping & Packaging





Reel

			Ammo		Reel				
Diameter	Length	Н	W	Т	D	Н	<b>W</b> +1/-0.1		
			Maximum	Maximum	±2	±0.5			
4	All	230	340	42		30			
5	≤ 7	230	340	42			50		
5	11	275	340	42					
6.3	≤ 7	235	340	45					
6.3	11	230	340	48	350				
8	≤ 7	270	340	48	350				
8	11	235	340	48					
8	>11 ≤ 20	240	340	57					
10	≤ 13	250	340	52					
10	>13 ≤ 20	256	340	57					
10	>20	250	340	60					
12	All	270	340	57					
13	All	285	340	62	NA	NA	NA		
16	16 All		340	62					
18	All	288 340		65					



## **Construction Data**

The manufacturing process begins with the anode foil being electrochemically etched to increase the surface area and then "formed" to produce the aluminum oxide layer. Both the anode and cathode foils are then interleaved with absorbent paper and wound into a cylinder. During the winding process, aluminum tabs are attached to each foil to provide the electrical contact.

The deck, complete with terminals, is attached to the tabs and then folded down to rest on top of the winding. The complete winding is impregnated with electrolyte before being housed in a suitable container, usually an aluminum can, and sealed. Throughout the process, all materials inside the housing must be maintained at the highest purity and be compatible with the electrolyte.

Each capacitor is aged and tested before being sleeved and packed. The purpose of aging is to repair any damage in the oxide layer and thus reduce the leakage current to a very low level. Aging is normally carried out at the rated temperature of the capacitor and is accomplished by applying voltage to the device while carefully controlling the supply current. The process may take several hours to complete.

Damage to the oxide layer can occur due to variety of reasons:

- Slitting of the anode foil after forming
- · Attaching the tabs to the anode foil
- · Minor mechanical damage caused during winding


A sample from each batch is taken by the quality department after completion of the production process. This sample size is controlled by the use of recognized sampling tables defined in BS 6001.

The following tests are applied and may be varied at the request of the customer. In this case the batch, or special procedure, will determine the course of action.

#### Electrical:

- Leakage current
- Capacitance
- ESR
- Impedance
- Tan Delta

- Mechanical/Visual:
  - Overall dimensions
  - Torque test of mounting stud
  - Print detail
  - Box labels
  - Packaging, including packed quantity





## **KEMET Electronics Corporation Sales Offices**

For a complete list of our global sales offices, please visit www.kemet.com/sales.

### Disclaimer

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicted or that other measures may not be required.

KEMET is a registered trademark of KEMET Electronics Corporation.