

#### **1** General description

The 74LVC1G34 provides a low-power, low-voltage single buffer.

The input can be driven from either 3.3 V or 5 V devices. This feature allows the use of this device in a mixed 3.3 V and 5 V environment.

This device is fully specified for partial power-down applications using  $I_{OFF}$ . The  $I_{OFF}$  circuitry disables the output, preventing the damaging backflow current through the device when it is powered down.

Schmitt trigger action at all inputs makes the circuit highly tolerant of slower input rise and fall times.

#### 2 Features and benefits

- Wide supply voltage range from 1.65 V to 5.5 V
- 5 V tolerant inputs for interfacing with 5 V logic
- High noise immunity
- · Complies with JEDEC standard:
  - JESD8-7 (1.65 V to 1.95 V)
  - JESD8-5 (2.3 V to 2.7 V)
  - JESD8-B/JESD36 (2.7 V to 3.6 V).
- ESD protection:
  - HBM: ANSI/ESDA/JEDEC JS-001 Class 2 exceeds 2000 V
  - MM: JESD22-A115-A exceeds 200 V
- ±24 mA output drive (V<sub>CC</sub> = 3.0 V)
- CMOS low power consumption
- Latch-up performance exceeds 250 mA
- · Direct interface with TTL levels
- Inputs accept voltages up to 5 V
- Multiple package options
- Specified from -40 °C to +85 °C and -40 °C to +125 °C

# ne<mark>x</mark>peria

### **3** Ordering information

Type number	Package			
	Temperature range	Name	Description	Version
74LVC1G34GW	-40 °C to +125 °C	TSSOP5	plastic thin shrink small outline package; 5 leads; body width 1.25 mm	SOT353-1
74LVC1G34GV	-40 °C to +125 °C	SC-74A	plastic surface-mounted package; 5 leads	SOT753
74LVC1G34GM	-40 °C to +125 °C	XSON6	plastic extremely thin small outline package; no leads; 6 terminals; body 1 x 1.45 x 0.5 mm	SOT886
74LVC1G34GF	-40 °C to +125 °C	XSON6	plastic extremely thin small outline package; no leads; 6 terminals; body 1 x 1 x 0.5 mm	SOT891
74LVC1G34GN	-40 °C to +125 °C	XSON6	extremely thin small outline package; no leads; 6 terminals; body 0.9 x 1.0 x 0.35 mm	SOT1115
74LVC1G34GS	-40 °C to +125 °C	XSON6	extremely thin small outline package; no leads; 6 terminals; body 1.0 x 1.0 x 0.35 mm	SOT1202
74LVC1G34GX	-40 °C to +125 °C	X2SON5	plastic thermal enhanced extremely thin small outline package; no leads; 5 terminals; body 0.8 x 0.8 x 0.35 mm	SOT1226
74LVC1G34GX4	-40 °C to +125 °C	X2SON4	plastic thermal enhanced extremely thin small outline package; no leads; 4 terminals; body 0.6 x 0.6 x 0.32 mm	SOT1269-2


#### 4 Marking

Table 2. Marking	
Type number	Marking code <sup>[1]</sup>
74LVC1G34GW	YN
74LVC1G34GV	YN
74LVC1G34GM	YN
74LVC1G34GF	YN
74LVC1G34GN	YN
74LVC1G34GS	YN
74LVC1G34GX	YN
74LVC1G34GX4	YN

[1] The pin 1 indicator is located on the lower left corner of the device, below the marking code.


Single buffer

#### 5 Functional diagram



#### 6 **Pinning information**

#### 6.1 Pinning



#### 6.2 Pin description

Symbol	Pin			Description
	TSSOP5, SC-74A and X2SON	5 XSON6	X2SON4	
n.c.	1	1, 5	-	not connected
A	2	2	1	data input
GND	3	3	2	ground (0 V)
Y	4	4	3	data output
V <sub>CC</sub>	5	6	4	supply voltage

Table 3. Pin description

74LVC1G34 Product data sheet © Nexperia B.V. 2018. All rights reserved.

#### **Functional description** 7

#### Table 4. Function table

H = HIGH voltage level; L = LOW voltage level.

Input	Output
A	Y
L	L
Н	Н

#### **Limiting values** 8

#### Table 5. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions		Min	Max	Unit
V <sub>CC</sub>	supply voltage			-0.5	+6.5	V
I <sub>IK</sub>	input clamping current	V <sub>1</sub> < 0 V		-50	-	mA
VI	input voltage		[1]	-0.5	+6.5	V
I <sub>ОК</sub>	output clamping current	$V_{\rm O}$ > $V_{\rm CC}$ or $V_{\rm O}$ < 0 V		-	±50	mA
Vo	output voltage	Active mode	[1]	-0.5	V <sub>CC</sub> + 0.5	V
		Power-down mode; $V_{CC}$ = 0 V	[1]	-0.5	+6.5	V
lo	output current	$V_{O}$ = 0 V to $V_{CC}$		-	±50	mA
I <sub>CC</sub>	supply current			-	100	mA
I <sub>GND</sub>	ground current			-100	-	mA
T <sub>stg</sub>	storage temperature			-65	+150	°C
P <sub>tot</sub>	total power dissipation	T <sub>amb</sub> = -40 °C to +125 °C				
		TSSOP5, SC-74A, XSON6 and X2SON5 package	[2]	-	250	mW
		X2SON4 package	[3]	-	150	mW

The minimum input and output voltage ratings may be exceeded if the input and output current ratings are observed.
 For TSSOP5 and SC-74A packages: above 87.5 °C the value of P<sub>tot</sub> derates linearly with 4.0 mW/K.

For XSON6 and X2SON5 package: above 118 °C the value of P<sub>tot</sub> derates linearly with 7.8 mW/K. [3] For X2SON4 package: above 57 °C the value of P<sub>tot</sub> derates linearly with 1.7 mW/K.

Single buffer

#### 9 Recommended operating conditions

#### Table 6. Recommended operating conditions

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
V <sub>CC</sub>	supply voltage		1.65	-	5.5	V
VI	input voltage		0	-	5.5	V
Vo	output voltage	Active mode	0	-	V <sub>CC</sub>	Vo
		Power-down mode; $V_{CC}$ = 0 V	0	-	5.5	Vo
T <sub>amb</sub>	ambient temperature		-40	-	+125	°C
Δt/ΔV	input transition rise and fall rate	$V_{CC}$ = 1.65 V to 2.7 V	-	-	20	ns/V
		V <sub>CC</sub> = 2.7 V to 5.5 V	-	-	10	ns/V

#### **10 Static characteristics**

#### Table 7. Static characteristics

At recommended operating conditions. Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	Min	Typ <sup>[1]</sup>	Max	Unit
T <sub>amb</sub> = -4	10 °C to +85 °C					
VIH	HIGH-level input voltage	V <sub>CC</sub> = 1.65 V to 1.95 V	$0.65 \times V_{CC}$	-	-	V
		V <sub>CC</sub> = 2.3 V to 2.7 V	1.7	-	-	V
		V <sub>CC</sub> = 2.7 V to 3.6 V	2.0	-	-	V
		V <sub>CC</sub> = 4.5 V to 5.5 V	$0.7 \times V_{CC}$	-	-	V
VIL	LOW-level input voltage	V <sub>CC</sub> = 1.65 V to 1.95 V	-	-	0.35 × V <sub>CC</sub>	V
		V <sub>CC</sub> = 2.3 V to 2.7 V	-	-	0.7	V
		V <sub>CC</sub> = 2.7 V to 3.6 V	-	-	0.8	V
		V <sub>CC</sub> = 4.5 V to 5.5 V	-	-	0.3 × V <sub>CC</sub>	V
V <sub>OH</sub>	HIGH-level output voltage	$V_{I} = V_{IH} \text{ or } V_{IL}$				
		$I_{O}$ = -100 µA; $V_{CC}$ = 1.65 V to 5.5 V	V <sub>CC</sub> - 0.1	-	-	V
		I <sub>O</sub> = -4 mA; V <sub>CC</sub> = 1.65 V	1.2	1.54	-	V
		$I_{\rm O}$ = -8 mA; $V_{\rm CC}$ = 2.3 V	1.9	2.15	-	V
		$I_{O}$ = -12 mA; $V_{CC}$ = 2.7 V	2.2	2.50	-	V
		$I_{O}$ = -24 mA; $V_{CC}$ = 3.0 V	2.3	2.62	-	V
		$I_{\rm O}$ = -32 mA; $V_{\rm CC}$ = 4.5 V	3.8	4.11	-	V
V <sub>OL</sub>	LOW-level output voltage	$V_{I} = V_{IH} \text{ or } V_{IL}$				-
		$I_{O}$ = 100 µA; $V_{CC}$ = 1.65 V to 5.5 V	-	-	0.10	V
		I <sub>O</sub> = 4 mA; V <sub>CC</sub> = 1.65 V	-	0.07	0.45	V
		I <sub>O</sub> = 8 mA; V <sub>CC</sub> = 2.3 V	-	0.12	0.30	V
		$I_0$ = 12 mA; $V_{CC}$ = 2.7 V	-	0.17	0.40	V
		I <sub>O</sub> = 24 mA; V <sub>CC</sub> = 3.0 V	-	0.33	0.55	V
		I <sub>O</sub> = 32 mA; V <sub>CC</sub> = 4.5 V	-	0.39	0.55	V

#### Nexperia

### 74LVC1G34

#### Single buffer

Symbol	Parameter	Conditions	Min	Typ <sup>[1]</sup>	Max	Unit
l <sub>l</sub>	input leakage current	$V_{CC} = 0 V \text{ to } 5.5 V; V_1 = 5.5 V \text{ or GND}$ <sup>[2]</sup>	-	±0.1	±1	μA
I <sub>OFF</sub>	power-off leakage current	$V_{CC}$ = 0 V; V <sub>I</sub> or V <sub>O</sub> = 5.5 V	-	±0.1	±2	μA
I <sub>CC</sub>	supply current	$V_{CC}$ = 1.65 V to 5.5 V; I <sub>O</sub> = 0 A; V <sub>I</sub> = 5.5 V or GND	-	0.1	4	μA
ΔI <sub>CC</sub>	additional supply current	$V_{CC}$ = 2.3 V to 5.5 V; V <sub>I</sub> = V <sub>CC</sub> - 0.6 V; <sup>[2]</sup> I <sub>O</sub> = 0 A	-	5	500	μA
Cı	input capacitance	$V_{CC}$ = 3.3 V; $V_{I}$ = GND to $V_{CC}$	-	4	-	pF
T <sub>amb</sub> = -4	0 °C to +125 °C					
V <sub>IH</sub>	HIGH-level input voltage	V <sub>CC</sub> = 1.65 V to 1.95 V	$0.65 \times V_{CC}$	-	-	V
		V <sub>CC</sub> = 2.3 V to 2.7 V	1.7	-	-	V
		V <sub>CC</sub> = 2.7 V to 3.6 V	2.0	-	-	V
		V <sub>CC</sub> = 4.5 V to 5.5 V	$0.7 \times V_{CC}$	-	-	V
VIL	LOW-level input voltage	V <sub>CC</sub> = 1.65 V to 1.95 V	-	-	$0.35 \times V_{CC}$	V
		V <sub>CC</sub> = 2.3 V to 2.7 V	-	-	0.7	V
		V <sub>CC</sub> = 2.7 V to 3.6 V	-	-	0.8	V
		V <sub>CC</sub> = 4.5 V to 5.5 V	-	-	$0.3 \times V_{CC}$	V
V <sub>OH</sub>	HIGH-level output voltage	$V_{I} = V_{IH} \text{ or } V_{IL}$				
		$I_{O}$ = -100 µA; $V_{CC}$ = 1.65 V to 5.5 V	V <sub>CC</sub> - 0.1	-	-	V
		I <sub>O</sub> = -4 mA; V <sub>CC</sub> = 1.65 V	0.95	-	-	V
		I <sub>O</sub> = -8 mA; V <sub>CC</sub> = 2.3 V	1.7	-	-	V
		$I_{\rm O}$ = -12 mA; $V_{\rm CC}$ = 2.7 V	1.9	-	-	V
		I <sub>O</sub> = -24 mA; V <sub>CC</sub> = 3.0 V	2.0	-	-	V
		I <sub>O</sub> = -32 mA; V <sub>CC</sub> = 4.5 V	3.4	-	-	V
V <sub>OL</sub>	LOW-level output voltage	$V_{I} = V_{IH} \text{ or } V_{IL}$				
		$I_{O}$ = 100 µA; $V_{CC}$ = 1.65 V to 5.5 V	-	-	0.10	V
		I <sub>O</sub> = 4 mA; V <sub>CC</sub> = 1.65 V	-	-	0.70	V
		I <sub>O</sub> = 8 mA; V <sub>CC</sub> = 2.3 V	-	-	0.45	V
		I <sub>O</sub> = 12 mA; V <sub>CC</sub> = 2.7 V	-	-	0.60	V
		I <sub>O</sub> = 24 mA; V <sub>CC</sub> = 3.0 V	-	-	0.80	V
		I <sub>O</sub> = 32 mA; V <sub>CC</sub> = 4.5 V	-	-	0.80	V
l <sub>l</sub>	input leakage current	$V_{CC}$ = 0 V to 5.5 V; $V_{I}$ = 5.5 V or GND	-	-	±1	μA
I <sub>OFF</sub>	power-off leakage current	$V_{CC}$ = 0 V; V <sub>1</sub> or V <sub>0</sub> = 5.5 V	-	-	±2	μA
I <sub>CC</sub>	supply current	$V_{CC}$ = 1.65 V to 5.5 V; I <sub>O</sub> = 0 A; V <sub>I</sub> = 5.5 V or GND	-	-	4	μA
ΔI <sub>CC</sub>	additional supply current	$V_{CC}$ = 2.3 V to 5.5 V; V <sub>I</sub> = V_{CC} - 0.6 V; $I_{O}$ = 0 A	-	-	500	μA

#### **Dynamic characteristics** 11

#### Table 8. Dynamic characteristics


Voltages are referenced to GND (ground = 0 V). For test circuit see Figure 9.

Symbol	Parameter	Conditions	-40	°C to +85	5 °C	-40 °C to	+125 °C	Unit
			Min	Typ <sup>[1]</sup>	Мах	Min	Max	
t <sub>pd</sub>	propagation delay	A to Y; see Figure 8 [2]						
		V <sub>CC</sub> = 1.65 V to 1.95 V	1.0	4.0	8.6	1.0	11.0	ns
		V <sub>CC</sub> = 2.3 V to 2.7 V	0.5	2.6	4.4	0.5	5.6	ns
		V <sub>CC</sub> = 2.7 V	0.5	2.3	4.5	0.5	5.6	ns
		V <sub>CC</sub> = 3.0 V to 3.6 V	0.5	2.0	4.1	0.5	5.2	ns
		V <sub>CC</sub> = 4.5 V to 5.5 V	0.5	1.6	3.2	0.5	4.1	ns
C <sub>PD</sub>	power dissipation capacitance	$V_{I}$ = GND to $V_{CC}$ ; $V_{CC}$ = 3.3 V <sup>[3]</sup>	-	15	-	-	-	pF

[1] Typical values are measured at T<sub>amb</sub> = 25 °C and V<sub>CC</sub> = 1.8 V, 2.5 V, 2.7 V, 3.3 V, and 5.0 V respectively.

[2]  $t_{pd}$  is the same as  $t_{PLH}$  and  $t_{PHL}$ . [3]  $C_{PD}$  is used to determine the dynamic power dissipation ( $P_D$  in  $\mu$ W).  $P_D = C_{PD} \times V_{CC}^2 \times f_i \times N + \sum (C_L \times V_{CC}^2 \times f_o)$  where:  $f_i$  = input frequency in MHz;  $f_o$  = output frequency in MHz;  $C_{L}$  = output load capacitance in pF; V<sub>CC</sub> = supply voltage in V; N = number of inputs switching;  $\Sigma(C_L \times V_{CC}^2 \times f_0)$  = sum of outputs.

#### 11.1 Waveform and test circuit



Measurement points are given in Table 9.

 $V_{\text{OL}}$  and  $V_{\text{OH}}$  are typical output voltage levels that occur with the output load.

Figure 8. The data input (A) to output (Y) propagation delays


#### Nexperia

## 74LVC1G34

Single buffer

#### Table 9. Measurement points

Supply voltage	Input	Output
V <sub>cc</sub>	V <sub>M</sub>	V <sub>M</sub>
1.65 V to 1.95 V	0.5 x V <sub>CC</sub>	$0.5 \times V_{CC}$
2.3 V to 2.7 V	0.5 x V <sub>CC</sub>	$0.5 \times V_{CC}$
2.7 V	1.5 V	1.5 V
3.0 V to 3.6 V	1.5 V	1.5 V
4.5 V to 5.5 V	0.5 x V <sub>CC</sub>	$0.5 \times V_{CC}$



Test data is given in <u>Table 10</u>.

Definitions for test circuit:

R<sub>L</sub> = Load resistance.

 $C_L$  = Load capacitance including jig and probe capacitance.

 $R_T$  = Termination resistance should be equal to the output impedance  $Z_o$  of the pulse generator.

V<sub>EXT</sub> = External voltage for measuring switching times.

Figure 9. Test circuit for measuring switching times

#### Table 10. Test data

Supply voltage	voltage Input		Load		V <sub>EXT</sub>
V <sub>cc</sub>	VI	t <sub>r</sub> = t <sub>f</sub>	CL	RL	t <sub>PLH</sub> , t <sub>PHL</sub>
1.65 V to 1.95 V	V <sub>CC</sub>	≤ 2.0 ns	30 pF	1 kΩ	open
2.3 V to 2.7 V	V <sub>CC</sub>	≤ 2.0 ns	30 pF	500 Ω	open
2.7 V	2.7 V	≤ 2.5 ns	50 pF	500 Ω	open
3.0 V to 3.6 V	2.7 V	≤ 2.5 ns	50 pF	500 Ω	open
4.5 V to 5.5 V	V <sub>CC</sub>	≤ 2.5 ns	50 pF	500 Ω	open

74LVC1G34 Single buffer

### 12 Package outline


	5: plas	tic thi	in shr	ink sr	nall o	utline	packa	age; 5	lead	s; boc	ly wid	th 1.2	5 mm	1			SC	DT353
		ŧ	y						с	¥ •				X	) (m) A			
		-		- Z		4 	(1)				A₁ ¥	detail	Lp +L + X	(A <sub>3</sub> )	A A A A A A A A A A A A A A A A A A A			
					0		1.5  sca			3 mm 								
IMENS	ions (m	nm are t	the orig	inal din	nension	s)												
DIMENS	IONS (n A max	nm are t A <sub>1</sub>	the orig A <sub>2</sub>	inal din A <sub>3</sub>	nension b <sub>p</sub>	s) c	D <sup>(1)</sup>	E <sup>(1)</sup>	e	e <sub>1</sub>	н <sub>Е</sub>	L	Lp	v	w	у	Z <sup>(1)</sup>	θ
	1		<b>A<sub>2</sub></b> 1.0		<b>b</b> р 0.30	<b>c</b> 0.25	2.25	1.35	<b>e</b> 0.65	<mark>е</mark> 1 1.3	H <sub>E</sub> 2.25 2.0	<b>L</b> 0.425	Lp 0.46 0.21	<b>v</b> 0.3	<b>w</b> 0.1	<b>y</b> 0.1	<b>Z<sup>(1)</sup></b> 0.60 0.15	7°
UNIT mm Note	A max. 1.1	<b>A<sub>1</sub></b> 0.1 0	<b>A<sub>2</sub></b> 1.0 0.8	<b>A</b> 3 0.15	<b>b</b> р 0.30 0.15	<b>c</b> 0.25 0.08	2.25 1.85	1.35 1.15	0.65		2.25		0.46				0.60	
UNIT mm Note	A max.	<b>A<sub>1</sub></b> 0.1 0	<b>A<sub>2</sub></b> 1.0 0.8	<b>A</b> 3 0.15	<b>b</b> р 0.30 0.15	<b>c</b> 0.25 0.08	2.25 1.85 side are	1.35 1.15	0.65 luded.		2.25		0.46		0.1	0.1	0.60 0.15	7° 0°
UNIT mm lote . Plastic	A max. 1.1 c or meta	<b>A<sub>1</sub></b> 0.1 0	A2 1.0 0.8 sions of	<b>A</b> 3 0.15	<b>b</b> р 0.30 0.15	<b>c</b> 0.25 0.08	2.25 1.85 side are	1.35 1.15 e not inc	0.65 luded.		2.25		0.46 0.21	0.3	0.1 PEAN	0.1	0.60	7° 0°

74LVC1G34 Product data sheet


9 / 20

© Nexperia B.V. 2018. All rights reserved.


#### Single buffer




#### Single buffer




#### Single buffer




#### Single buffer




#### Single buffer



Single buffer



#### Single buffer



#### **13 Abbreviations**

Table 11. Abbreviations				
Acronym	Description			
CMOS	Complementary Metal-Oxide Semiconductor			
DUT	Device Under Test			
ESD	ElectroStatic Discharge			
НВМ	Human Body Model			
MM	Machine Model			
TTL	Transistor-Transistor Logic			

### 14 Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes			
74LVC1G34 v.7	20180608	Product data sheet	-	74LVC1G34 v.6			
Modifications:	Nexperia. <ul> <li>Legal texts has</li> </ul>						
74LVC1G34 v.6	20161205	Product data sheet	-	74LVC1G34 v.5			
Modifications:	• <u>Section 10</u> : T	• Section 10: The maximum limits for leakage current and supply current have changed.					
74LVC1G34 v.5	20120702	Product data sheet	-	74LVC1G34 v.4			
Modifications:	<ul> <li>Added type number 74LVC1G34GX (SOT1226)</li> <li>Package outline drawing of SOT886 (Figure 12) modified.</li> </ul>						
74LVC1G34 v.4	20111206	Product data sheet	-	74LVC1G34 v.3			
Modifications:	Legal pages updated						
74LVC1G34 v.3	20100902	Product data sheet	-	74LVC1G34 v.2			
74LVC1G34 v.2	20070521	Product data sheet	-	74LVC1G34 v.1			
74LVC1G34 v.1	20050907	Product data sheet	-	-			

#### 15 Legal information

#### 15.1 Data sheet status

Document status <sup>[1][2]</sup>	Product status <sup>[3]</sup>	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

Please consult the most recently issued document before initiating or completing a design. [1]

The term 'short data sheet' is explained in section "Definitions".

[2] [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nexperia.com.

#### **15.2 Definitions**

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

#### 15.3 Disclaimers

Limited warranty and liability - Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia. In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory. Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia

Right to make changes - Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use - Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification. Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products. Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale - Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nexperia.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer

No offer to sell or license - Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

#### Single buffer

Non-automotive qualified products — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications. In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the product for such automotive applications, use and specifications beyond Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer

design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

**Translations** — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

#### **15.4 Trademarks**

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

#### Nexperia

## 74LVC1G34

Single buffer

#### Contents

1	General description	1
2	Features and benefits	1
3	Ordering information	2
4	Marking	2
5	Functional diagram	3
6	Pinning information	
6.1	Pinning	
6.2	Pin description	3
7	Functional description	4
8	Limiting values	4
9	Recommended operating conditions	5
10	Static characteristics	5
11	Dynamic characteristics	7
11.1	Waveform and test circuit	7
12	Package outline	9
13	Abbreviations	17
14	Revision history	17
15	Legal information	

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

© Nexperia B.V. 2018.

All rights reserved.

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com

Date of release: 8 June 2018 Document identifier: 74LVC1G34