


2μA I_Q, 300mA Low-Dropout Linear Regulator

General Description


The RT9078 is a low-dropout (LDO) voltage regulator with enable function that operates from a 1.2V to 5.5V supply. It provides up to 300mA of output current in miniaturized packaging.

The feature of $2\mu A$ low quiescent current and $0.5\mu A$ shutdown current are ideal for the battery application with long service life. The other features include current limit function, over temperature protection and output discharge function.

Pin Configuration



TSOT-23-5



ZQFN-4L 1x1 (ZDFN-4L 1x1)

Features


- Input Voltage Range: 1.2V to 5.5V
- 2μA Ground Current (IQ) at no Load
- PSRR = 75dB at 1kHz
- Adjustable Output Voltage Range :
 - → 0.8V to 5V (TSOT-23-5 Package with SNS Pin Only)
- ±2% Output Accuracy
- Low (0.1μA) Shutdown Current
- Dropout Voltage: 0.15V at 300mA when V_{OUT} ≥ 3V
- Support Fixed Output Voltage 0.8V, 1.0V, 1.05V, 1.1V, 1.2V, 1.25V, 1.3V, 1.5V, 1.8V, 1.85V, 2V, 2.5V, 2.8V, 2.85V, 3V, 3.1V, 3.3V, 3.45V
- Current Limit Protection
- Over Temperature Protection
- Output Active Discharge Function
- TSOT-23-5 and ZQFN-4L 1x1 (ZDFN-4L 1x1) Packages Available

Applications

- Portable, Battery Powered Equipment
- Ultra Low Power Microcontrollers
- Notebook Computers



Ordering Information



Note:

Richtek products are:

- ▶ RoHS compliant and compatible with the current requirements of IPC/JEDEC J-STD-020.
- ▶ Suitable for use in SnPb or Pb-free soldering processes.

Marking Information

For marking information, contact our sales representative directly or through a Richtek distributor located in your area.

www.richtek.com

^{***}Empty means Pin1 orientation is Quadrant 1

^{**}Available for output target adjustment (Ex: RT9078N-08GJ5 with 0.8V reference level for output target adjustment)




Functional Pin Description

Pin No.		Pin Name	Pin Function		
TSOT-23-5	ZQFN-4L 1x1 (ZDFN-4L 1x1)	FIII Name	Fill FullCuon		
1	4	VIN	Regulator input pin. Input capacitor should be placed directly at this pin.		
2	2	GND	Ground.		
3	3	EN	Chip enable pin. Pulling this pin below 0.4V turns the regulator off, reducing the quiescent current to a fraction of its operating value.		
4		SNS	Output voltage sense. (RT9078N only)		
4		NC	No internal connection.		
5	1	VOUT	Regulator output pin. Output capacitor should be place directly at this pin.		
	5 (Exposed Pad)	SGND	Substrate of chip. Tie to GND plane for maximum thermal dissipation.		

Copyright ©2019 Richtek Technology Corporation. All rights reserved. **RICHTEK** is a registered trademark of Richtek Technology Corporation.



Functional Block Diagram



Operation

Basic Operation

The RT9078 is a low guiescent current linear regulator designed especially for low external components system. The input voltage range is from 1.2V to 5.5V.

The minimum required output capacitance for stable operation is 1µF capacitance after consideration of the temperature and voltage coefficient of the capacitor.

Pass Transistor

The RT9078 builds in a P-MOSFET pass transistor which provides a low switch-on resistance for low dropout voltage applications.

Error Amplifier

The Error Amplifier compares the internal reference voltage with the output feedback voltage from the internal divider, and controls the gate voltage of P-MOSFET.

Chip Enable and Shutdown

The RT9078 provides an EN pin, as an external chip enable control, to enable or disable the device. The V_{EN} below 0.4V turns the regulator off and enters the shutdown mode, while V_{EN} above 0.9V turns the regulator on. When the regulator is shutdown, the ground current is reduced to a maximum of 0.5μA.

Current-Limit Protection

The RT9078 contains an independent current limiter, which monitors and controls the pass transistor's gate voltage, limiting the output current to 0.6A (typ.). The current limiting level is reduced to around 0.3A named fold-back current limit when the output voltage is further decreased. The output can be shorted to ground indefinitely without damaging the part.

Over-Temperature Protection

The over-temperature protection function will turn off the P-MOSFET when the junction temperature exceeds 150°C (typ.), and the output current exceeds 80mA. Once the junction temperature cools down by approximately 20°C, the regulator will automatically resume operation.

Output Active Discharge

When the RT9078 is operating at shutdown mode, the device has an internal active pull down circuit that connects the output to GND through a resistor for output discharging purpose.



Absolute Maximum Ratings (Note 1)

• VIN, VOUT, SNS, EN to GND	0.3V to 6.5V
• VOUT to VIN	6.5V to 0.3V
 Power Dissipation, P_D @ T_A = 25°C 	
TSOT-23-5	- 0.43W
ZQFN-4L 1x1 (ZDFN-4L 1x1)	- 0.44W
Package Thermal Resistance (Note 2)	
TSOT-23-5, θ_{JA}	- 230.6°C/W
TSOT-23-5, θ_{JC}	- 21.8°C/W
ZQFN-4L 1x1 (ZDFN-4L 1x1), θ_{JA}	
ZQFN-4L 1x1 (ZDFN-4L 1x1), θ_{JC}	
• Lead Temperature (Soldering, 10 sec.)	
• Junction Temperature	
Storage Temperature Range	- −65°C to 150°C
• ESD Susceptibility (Note 3)	
HBM (Human Body Model)	- 2kV
Recommended Operating Conditions (Note 4)	
• Input Voltage, VIN	- 1.2V to 5.5V

• Junction Temperature Range ----- -40°C to 125°C

Electrical Characteristics

 $(V_{OUT} + 1 < V_{IN} < 5.5V, T_A = 25^{\circ}C, unless otherwise specified)$

Parameter	Symbol	Test Conditions	Min	Тур	Max	Unit	
Fixed Output Voltage Range	Vout		0.8		3.45	V	
DC Output Accuracy		I _{LOAD} = 1mA	-2		2	%	
SNS Reference Voltage (for RT9078N-08GJ5 only)	VREF	I _{LOAD} = 1mA	0.784	0.8	0.816	V	
	V _{DR} OP	$0.8V \le V_{OUT} < 1.05V$		0.7	0.97	V	
		1.05V ≤ V _{OUT} < 1.2V		0.5	0.92		
		$1.2V \leq V_{OUT} < 1.5V$		0.4	0.57		
		$1.5V \leq V_{OUT} < 1.8V$		0.3	0.47		
Dropout Voltage (I _{LOAD} = 300mA) (Note 5)		1.8V ≤ V _{OUT} < 2.1V		0.24	0.33		
(ILUAD - SOUTIA) (Note 3)		$2.1V \leq V_{OUT} < 2.5V$		0.21	0.3		
		$2.5V \le V_{OUT} < 2.8V$		0.18	0.25	-	
		$2.8V \le V_{OUT} < 3V$		0.16	0.23		
		$3V \leq V_{OUT}$		0.15	0.2		
Dropout Voltage (I _{LOAD} = 200mA) (Note 6)	V _{DROP}	1.8V ≤ V _{OUT} < 2.1V		0.16	0.2	V	
V _{CC} Consumption Current	IQ	I_{LOAD} = 0mA, $V_{OUT} \le 5.5V$ $V_{IN} \ge V_{OUT} + V_{DROP}$		2	4	μА	

Copyright ©2019 Richtek Technology Corporation. All rights reserved. **RICHTEK** is a registered trademark of Richtek Technology Corporation.



Paramet	Parameter Symbol Test Conditions		Min	Тур	Max	Unit			
Shutdown GND Cu (Note 7)	rrent		V _{EN} = 0V			-	0.1	0.5	μА
Shutdown Leakage Current (Note 7)			V _{EN} = 0V, V _{OUT} = 0V			0.1	0.5	μΑ	
EN Input Current		I _{EN}	V _{EN} = 5.5V		ı		0.1	μΑ	
			I _{LOAD} = 1mA	1.2	$V \le V_{IN} < 1.5V$	I	0.3	0.6	%
Line Regulation		ΔLINE		1.5	$V \le V_{IN} < 1.8V$	-	0.15	0.3	
				1.8	$V \le V_{IN} \le 5.5V$		0.13	0.35	
Load Regulation		ΔLOAD	1mA < I _{LOAD} < 300mA			0.5	1	%	
Power Supply Rejection Ratio		PSRR	V_{IN} = 3V, I_{LOAD} = 50mA, C_{OUT} = 1 μ F, V_{OUT} = 2.5V, f = 1kHz			75		dB	
Outrot Valle as Naise			$C_{OUT} = 1\mu F,$ $I_{LOAD} = 150 mA,$ $BW = 10 Hz to$ $V_{OUT} = 0.8 V$ $V_{OUT} = 1.2 V$		-	38			
					V _{OUT} = 1.2V	I	46	I	u\/pwc
Output Voltage Noi	SE		100kHz, V _{OUT} = 1.8V		V _{OUT} = 1.8V	ı	48	ı	μVRMS
					V _{OUT} = 3.3V	ı	51	l	
Output Current Lim	it	I _{LIM}	V _{OUT} = 90% of V _{OUT(NOM)}		350	600	I	mA	
Enable Threshold	H-Level	V _{ENH}	V _{IN} = 5V		0.5	0.7	0.9	\ \	
Voltage L-Level		V _{ENL}	V _{IN} = 5V		0.4	0.65	0.85	V	
Thermal Shutdown Temperature		T _{SD}	I _{LOAD} = 30mA, V _{IN} ≥ 1.5V			150		°C	
Thermal Shutdown Hysteresis		ΔT _{SD}				20		°C	
Discharge Resistance			EN = 0V, V _{OUT} = 0.1V			80		Ω	

- Note 1. Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions may affect device reliability.
- Note 2. θ_{JA} is measured in the natural convection at T_A = 25°C on a two-layer Richtek Evaluation Board for ZQFN-4L 1x1 (ZDFN-4L1x1) Package.
 - θ_{JA} is measured at T_A = 25°C on a high effective thermal conductivity four-layer test board per JEDEC 51-7 for TSOT-23-5 Package.
- Note 3. Devices are ESD sensitive. Handling precaution is recommended.
- Note 4. The device is not guaranteed to function outside its operating conditions.
- Note 5. The dropout voltage is defined as $V_{IN} V_{OUT}$, when V_{OUT} is 98% of the normal value of V_{OUT} .
- Note 6. For the application under following condition:
 - $1.8V \le V_{OUT} < 2.1V$, $I_{LOAD} = 200$ mA, $T_A = 85$ °C, the maximum dropout voltage is guaranteed by design that not over 0.28V.
- Note 7. The specification is tested at wafer stage and guaranteed by design after assembly.

www.richtek.com

Typical Application Circuit




Figure 1. Application with Sense Function




Figure 2. Application without Sense Function




Figure 3. Adjustable Output Voltage Application Circuit

Table 1. Recommended External Components

Component	Description	Vendor P/N	
C _{IN}	1μF, 10V, X5R, 0402	GRM155R61A105KE15 (Murata)	
	1μF, 6.3V, X5R, 0402	GRM153R60J105ME95(Murata) CGB2A3X5R0J105M033BB(TDK)	
* Cout	2.2μF, 6.3V, X5R, 0402	GRM153R60J225ME95 (Murata) C1005X5R0J225M050BC (TDK)	
	4.7μF, 6.3V, X5R, 0402	GRM153R60J475ME15 (Murata) C1005X5R0J475K050BE(TDK)	


^{*:} Considering the effective capacitance derated with biased voltage level, the C_{OUT} component needs satisfy the effective capacitance at least $0.7\mu F$ or above at targeted output level for stable and normal operation.


DS9078-16 June 2019 www.richtek.com


7





Typical Operating Characteristics


















Copyright ©2019 Richtek Technology Corporation. All rights reserved. RICHTEK is a registered trademark of Richtek Technology Corporation.





















Copyright ©2019 Richtek Technology Corporation. All rights reserved. RICHTEK is a registered trademark of Richtek Technology Corporation.





















Copyright ©2019 Richtek Technology Corporation. All rights reserved. RICHTEK is a registered trademark of Richtek Technology Corporation.













Application Information

Like any low dropout linear regulator, the RT9078's external input and output capacitors must be properly selected for stability and performance. Use a 1µF or larger input capacitor and place it close to the IC's VIN and GND pins. Any output capacitor meeting the minimum $1m\Omega$ ESR (Equivalent Series Resistance) and capacitance larger than 1µF requirement may be used. Place the output capacitor close to the IC's VOUT and GND pins. Increasing capacitance and decreasing ESR can improve the circuit's PSRR and line transient response.

Dropout Voltage

The dropout voltage refers to the voltage difference between the VIN and VOUT pins while operating at specific output current. The dropout voltage V_{DROP} also can be expressed as the voltage drop on the pass-FET at specific output current (I_{RATED}) while the pass-FET is fully operating at ohmic region and the pass-FET can be characterized as an resistance R_{DS(ON)}. Thus the dropout voltage can be defined as $(V_{DROP} = V_{IN} - V_{OUT} = R_{DS(ON)} x I_{RATED})$. For normal operation, the suggested LDO operating range is $(V_{IN} > V_{OUT} + V_{DROP})$ for good transient response and PSRR ability. Vice versa, while operating at the ohmic region will degrade the performance severely.

Adjustable Output Voltage Setting

Because of the small input current at the SNS pin, the RT9078N with SNS pin also can work as an adjustable output voltage LDO. Figure 3 gives the connections for the adjustable output voltage application. The resistor divider from VOUT to SNS sets the output voltage when in regulation.

The voltage on the SNS pin sets the output voltage and is determined by the values of R1 and R2. The adjustable output voltage can be calculated using the formula given in equation 1:

$$V_{OUT} = \frac{R1 + R2}{R2} \times V_{SNS} \tag{1}$$

where V_{SNS} is determined by the output voltage selections in the ordering information of the RT9078N (Ex: For the RT9078N-08GJ5, V_{SNS} is 0.8V).

The maximum adjustable output voltage can be as high as input voltage deducted by the dropout voltage. The Resistive divider total value of R1 and R2 are suggested not over $50k\Omega$.

Thermal Considerations

For continuous operation, do not exceed absolute maximum junction temperature. The maximum power dissipation depends on the thermal resistance of the IC package, PCB layout, rate of surrounding airflow, and difference between junction and ambient temperature. The maximum power dissipation can be calculated by the following formula:

$$P_{D(MAX)} = (T_{J(MAX)} - T_A) / \theta_{JA}$$

where $T_{J(MAX)}$ is the maximum junction temperature, T_A is the ambient temperature, and θ_{JA} is the junction to ambient thermal resistance.

For recommended operating condition specifications the maximum junction temperature is 125°C and TA is the ambient temperature. The junction to ambient thermal resistance, θ_{JA} , is layout dependent. For TSOT-23-5 package, the thermal resistance, θ_{JA} , is 230.6°C/W on a standard JEDEC 51-7 four-layer thermal test board. For ZQFN-4L 1x1 (ZDFN-4L 1x1) package, the thermal resistance, θ_{JA} , is 226°C/W on a two-layer Richtek evaluation board. The maximum power dissipation at T_A = 25°C can be calculated by the following formula:

 $P_{D(MAX)} = (125^{\circ}C - 25^{\circ}C) / (230.6^{\circ}C/W) = 0.43W$ for TSOT-23-5 package

 $P_{D(MAX)} = (125^{\circ}C - 25^{\circ}C) / (226^{\circ}C/W) = 0.44W$ for ZQFN-4L 1x1 (ZDFN-4L 1x1) package

The maximum power dissipation depends on the operating ambient temperature for fixed $T_{J(MAX)}$ and thermal resistance, θ_{JA} . The derating curve in Figure 4 allows the designer to see the effect of rising ambient temperature on the maximum power dissipation.

www.richtek.com




Figure 4. Derating Curve of Maximum Power Dissipation

Layout Considerations

For best performance of the RT9078, the PCB layout suggestions below are highly recommend:

- Input capacitor must be placed as close as possible to IC to minimize the power loop area.
- Minimize the power trace length and avoid using vias for the input and output capacitors connection.

Figure 5 and Figure 6 shows the examples for the layout reference which helps the inductive parasitic components minimization, load transient reduction and good circuit stability.




Figure 5. PCB Layout Guide for ZQFN-4L 1x1 package





Figure 6. PCB Layout Guide for TSOT-23-5 package




Outline Dimension




Symbol	Dimensions I	n Millimeters	Dimensions In Inches		
Symbol	Min	Max	Min	Max	
А	0.700	1.000	0.028	0.039	
A1	0.000	0.100	0.000	0.004	
В	1.397	1.803	0.055	0.071	
b	0.300	0.559	0.012	0.022	
С	2.591	3.000	0.102	0.118	
D	2.692	3.099	0.106	0.122	
е	0.838	1.041	0.033	0.041	
Н	0.080	0.254	0.003	0.010	
L	0.300	0.610	0.012	0.024	

TSOT-23-5 Surface Mount Package







DETAIL A

Pin #1 ID and Tie Bar Mark Options

Note: The configuration of the Pin #1 identifier is optional, but must be located within the zone indicated.

Symbol	Dimensions	In Millimeters	Dimensions In Inches		
Symbol	Min	Max	Min	Max	
А	0.300	0.400	0.012	0.016	
A1	0.000	0.050	0.000	0.002	
А3	0.117	0.162	0.005	0.006	
b	0.175	0.275	0.007	0.011	
D	0.900	1.100	0.035	0.043	
D2	0.450	0.550	0.018	0.022	
E	0.900	1.100	0.035	0.043	
E2	0.450	0.550	0.018	0.022	
е	0.625		0.025		
L	0.200	0.300	0.008	0.012	
Н	0.039		0.002		
H1	0.064		0.003		

Z-Type 4L QFN 1x1 Package

Richtek Technology Corporation

14F, No. 8, Tai Yuen 1st Street, Chupei City Hsinchu, Taiwan, R.O.C.

Tel: (8863)5526789

Richtek products are sold by description only. Customers should obtain the latest relevant information and data sheets before placing orders and should verify that such information is current and complete. Richtek cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Richtek product. Information furnished by Richtek is believed to be accurate and reliable. However, no responsibility is assumed by Richtek or its subsidiaries for its use; nor for any infringements of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Richtek or its subsidiaries.