

AT42QT1012 Data Sheet

Introduction

The AT42QT1012 (QT1012) is a single key device featuring a touch on/touch off (toggle) output with a programmable auto switch-off capability. The device is One-channel Toggle-mode QTouch® Touch Sensor IC with Power Management Functions.

The QT1012 features a digital burst mode charge-transfer sensor designed specifically for touch controls and a unique "green" feature - the timeout function, which can turn off power after a time delay.

Features

- Number of Keys:
 - One, toggle mode (touch-on / touch-off), plus programmable auto-off delay and external
 - Configurable as either a single key or a proximity sensor
- Technology:
 - Patented spread-s 6 mm x 6 mm or larger (panel thickness dependent); widely different sizes and shapes possible
- Electrode design:
 - Solid or ring electrode shapes
- PCB Layers required:
 - One
- Electrode materials:
 - Etched copper, silver, carbon, Indium Tin Oxide (ITO)
- Electrode substrates:
 - PCB, FPCB, plastic films, glass
- Panel materials:
 - Plastic, glass, composites, painted surfaces (low particle density metallic paints possible)
- Panel thickness:
 - Up to 12 mm glass, 6 mm plastic (electrode size and Cs dependent)
- Key sensitivity:
- Settable via external capacitor (Cs)
- Interface:
 - Digital output, active high or active low (hardware configurable)
- Moisture tolerance:
 - Increased moisture tolerance based on hardware design and firmware tuning
- Power:

Datasheet DS40001948A-page 1

- 1.8 V 5.5 V; 32 μA at 1.8 V
- Package:
 - 6-pin SOT23-6 (3 x 3 mm) RoHS compliant
 - 8-pin UDFN/USON (2 x 2 mm) RoHS compliant
- Signal processing:
 - Self-calibration, auto drift compensation, noise filtering

Table of Contents


Int	roduc	tion	1			
Fe	atures	3	1			
1.	Pinout and Schematic					
	1.1.	Pinout Configurations	5			
	1.2.	Pin Descriptions				
	1.3.	Schematics				
2.	Ove	rview of the AT42QT1012	7			
	2.1.	Introduction	7			
	2.2.	Basic Operation	7			
	2.3.	Electrode Drive	7			
	2.4.	Sensitivity	8			
	2.5.	Moisture Tolerance	8			
3.	Ope	ration Specifics	10			
	3.1.	Acquisition Modes	10			
	3.2.	Detect Threshold				
	3.3.	Detect Integrator	11			
	3.4.	Recalibration Timeout				
	3.5.	Forced Sensor Recalibration	11			
	3.6.	Drift Compensation	11			
	3.7.	Response Time	12			
	3.8.	Spread Spectrum	12			
	3.9.	Output Polarity Selection	12			
	3.10.	Output Drive	13			
	3.11.	Auto-Off Delay	13			
	3.12.	Examples of Typical Applications	21			
4.	Circu	uit Guidelines	22			
	4.1.	More Information	22			
	4.2.	Sample Capacitor	22			
	4.3.	Rs Resistor	22			
	4.4.	Power Supply and PCB Layout	22			
	4.5.	Power On	23			
5.	Spec	cifications	24			
	5.1.	Absolute Maximum Specifications	24			
	5.2.	Recommended Operating Conditions	24			
	5.3.	AC Specifications	24			
	5.4.	Signal Processing	25			
	5.5.	DC Specifications	25			
	5.6.	Mechanical Dimensions	26			
	5.7.	Part Marking	28			

	5.8.	Part Number	
	5.9.	Moisture Sensitivity Level (MSL)	29
6.	Asso	ociated Documents	.30
7.	Revi	sion History	31
Th	е Міс	rochip Web Site	. 32
Cu	stom	er Change Notification Service	32
Cu	stom	er Support	. 32
Mi	croch	p Devices Code Protection Feature	. 32
Le	gal N	otice	33
Tra	adema	arks	. 33
Qι	ality l	Management System Certified by DNV	34
Wo	orldwi	de Sales and Service	.35


1. Pinout and Schematic

1.1 Pinout Configurations

1.1.1 6-pin SOT23-6



1.1.2 8-pin UDFN/USON



1.2 Pin Descriptions

Table 1-1. Pin Listing

6-Pin	8-Pin	Name	Туре	Description	If Unused, Connect To
1	5	OUT	O ⁽¹⁾	Output state. To switched circuit and output polarity selection resistor (Rop)	
2	4	VSS	Р	Ground	
3	1	SNSK	I/O	Sense pin. To Cs capacitor and to sense electrode	Cs + key
4	8	SNS	I/O	Sense pin. To Cs capacitor and multiplier configuration resistor (Rm). Rm must be fitted and connected to either VSS or VDD. See Section 3.11.4 for details.	Cs
5	7	VDD	Р	Power	
6	6	TIME	I	Timeout configuration pin. Must be connected to either VSS, VDD, OUT or an RC network. See Section 3.11 for details.	
_	2	N/C	_	Not connected	Do not connect
_	3	N/C	_	Not connected	Do not connect


⁽¹⁾ I/O briefly on power-up I Input only O Output only, push-pull

I/O Input/output P Ground or power

1.3 Schematics


1.3.1 6-pin SOT23-6

Figure 1-1. Basic Circuit Configuration (active high output, toggle on/off, no auto switch off)



1.3.2 8-pin UDFN/USON

Figure 1-2. Basic Circuit Configuration (active high output, toggle on/off, no auto switch off)



For component values in Figure 1-1 and Figure 1-2, check the following sections:

- Cs capacitor (Cs) see Section 4.2 on page 20
- Sample resistor (Rs) see Section 4.3 on page 20
- Voltage levels see Section 4.4 on page 20
- Output polarity selection resistor (Rop) see Section 3.9 on page 10
- Rm resistor see Section 3.11.2 on page 11
- Bypass capacitor (Cby) see page 20

2. Overview of the AT42QT1012

2.1 Introduction

The AT42QT1012 (QT1012) is a single key device featuring a touch on/touch off (toggle) output with a programmable auto switch-off capability.

The QT1012 is a digital burst mode charge-transfer sensor designed specifically for touch controls. It includes all hardware and signal processing functions necessary to provide stable sensing under a wide variety of changing conditions; only low cost, noncritical components are required for operation. With its tiny low-cost packages, this device can suit almost any product needing a power switch or other toggle-mode controlled function, especially power control of small appliances and battery-operated products.

A unique "green" feature of the QT1012 is the timeout function, which can turn off power after a time delay.

Like all QTouch[®] devices, the QT1012 features automatic self-calibration, drift compensation, and spread-spectrum burst modulation in order to provide for the most reliable touch sensing possible.

2.2 Basic Operation

Figure 1-1 and Figure 1-2 show basic circuits for the 6-pin and 8-pin devices.

The QT1012 employs bursts of charge-transfer cycles to acquire its signal. Burst mode permits power consumption in the microamp range, dramatically reduces RF emissions, lowers susceptibility to EMI, and yet permits excellent response time. Internally the signals are digitally processed to reject impulse noise, using a "consensus" filter which requires four consecutive confirmations of a detection before the output is activated.

The QT switches and charge measurement hardware functions are all internal to the QT1012.

2.3 Electrode Drive

Figure 2-1 shows the sense electrode connections (SNS, SNSK) for the QT1012.

For optimum noise immunity, the electrode should only be connected to the SNSK pin.

In all cases the sample capacitor Cs should be much larger than the load capacitance (Cx). Typical values for Cx are 5 - 20 pF while Cs is usually 2.2 - 50 nF.

Note: Cx is not a physical discrete component on the PCB, it is the capacitance of the touch electrode and wiring. It is show in Figure 2-1 to aid understanding of the equivalent circuit.


Increasing amounts of Cx decrease gain, therefore it is important to limit the amount of load capacitance on both SNS terminals. This can be done, for example, by minimizing trace lengths and widths and keeping these traces away from power or ground traces or copper pours.

The traces, and any components associated with SNS and SNSK, will become touch sensitive and should be treated with caution to limit the touch area to the desired location.

To endure that the correct output mode is selected at power-up, the OUT trace should also be carefully routed.

A series resistor, Rs, should be placed in line with SNSK to the electrode to suppress electrostatic discharge (ESD) and electromagnetic compatibility (EMC) effects.

Figure 2-1. Sense Connections



2.4 Sensitivity

2.4.1 Introduction

The sensitivity on the QT1012 is a function of things like the value of Cs, electrode size and capacitance, electrode shape and orientation, the composition and aspect of the object to be sensed, the thickness and composition of any overlaying panel material, and the degree of ground coupling of both sensor and object.

2.4.2 **Increasing Sensitivity**

In some cases it may be desirable to increase sensitivity; for example, when using the sensor with very thick panels having a low dielectric constant, or when the device is used as a proximity sensor. Sensitivity can often be increased by using a larger electrode or reducing panel thickness. Increasing electrode size can have diminishing returns, as high values of Cx will reduce sensor gain.

The value of Cs also has a dramatic effect on sensitivity, and this can be increased in value with the trade-off of a slower response time and more power. Increasing the electrode's surface area will not substantially increase touch sensitivity if its diameter is already much larger in surface area than the object being detected. Panel material can also be changed to one having a higher dielectric constant, which will better help to propagate the field.

Ground planes around and under the electrode and its SNSK trace will cause high Cx loading and decrease gain. The possible signal-to-noise ratio benefits of ground area are more than negated by the decreased gain from the circuit, and so ground areas around electrodes are discouraged. Metal areas near the electrode will reduce the field strength and increase Cx loading and should be avoided, if possible. Keep ground away from the electrodes and traces.

2.4.3 **Decreasing Sensitivity**

In some cases the QT1012 may be too sensitive. In this case gain can easily be lowered further by decreasing Cs.

2.5 **Moisture Tolerance**

The presence of water (condensation, sweat, spilt water, and so on) on a sensor can alter the signal values measured and thereby affect the performance of any capacitive device. The moisture tolerance of QTouch devices can be improved by designing the hardware and fine-tuning the firmware following the

Datasheet DS40001948A-page 8 © 2017 Microchip Technology Inc.

recommendations in the application note Atmel AVR3002: Moisture Tolerant QTouch Design (downloadable from www.microchip.com).

3. Operation Specifics

3.1 Acquisition Modes

3.1.1 Introduction

The OUT pin of the QT1012 can be configured to be active high or active low.

- If active high then:
 - "on" is high
 - "off" is low
- · If active low then:
 - "on" is low
 - "off" is high

3.1.2 OUT Pin

The QT1012 runs in Low Power (LP) mode. In this mode it sleeps for approximately 80 ms at the end of each burst, saving power but slowing response. On detecting a possible key touch, it temporarily switches to fast mode until either the key touch is confirmed or found to be spurious (via the detect integration process).

- If the touch is confirmed, the OUT pin is toggled and the QT1012 returns to LP mode (see figure "Low Power Mode: Touch Confirmed" below).
- If the touch is not valid then the chip returns to LP mode but the OUT pin remains unchanged (see figure "Low Power Mode: Touch Denied" below).

Figure 3-1. Low Power Mode: Touch Confirmed (Output in Off Condition)





Figure 3-2. Low Power Mode: Touch Denied (Output in Off Condition)



3.2 Detect Threshold

The device detects a touch when the signal has crossed a threshold level. The threshold level is fixed at 10 counts.

3.3 Detect Integrator

It is desirable to suppress detections generated by electrical noise or from quick brushes with an object. To accomplish this, the QT1012 incorporates a detect integration (DI) counter that increments with each detection until a limit is reached, after which the output is activated. If no detection is sensed prior to the final count, the counter is reset immediately to zero. In the QT1012, the required count is four.

The DI can also be viewed as a "consensus filter" that requires four successive detections to create an output.

3.4 Recalibration Timeout

If an object or material obstructs the sense electrode the signal may rise enough to create a detection, preventing further operation. To stop this, the sensor includes a timer which monitors detections. If a detection exceeds the timer setting, the sensor performs a full recalibration. This does not toggle the output state but ensures that the QT1012 will detect a new touch correctly. The timer is set to activate this feature after ~60 s. This will vary slightly with Cs.

3.5 Forced Sensor Recalibration

The QT1012 has no recalibration pin; a forced recalibration is accomplished when the device is powered up or after the recalibration timeout. However, supply drain is low so it is a simple matter to treat the entire IC as a controllable load; driving the QT1012 VDD pin directly from another logic gate or a microcontroller port will serve as both power and "forced recalibration". The source resistance of most CMOS gates and microcontrollers is low enough to provide direct power without a problem.


3.6 Drift Compensation

Signal drift can occur because of changes in Cx and Cs over time. It is crucial that drift be compensated for, otherwise false detections, nondetections, and sensitivity shifts will follow.

Drift compensation (Figure 3-3) is performed by making the reference level track the raw signal at a slow rate, but only while there is no detection in effect. The rate of adjustment must be performed slowly, otherwise legitimate detections could be ignored. The QT1012 drift compensates using a slew-rate limited change to the reference level; the threshold and hysteresis values are slaved to this reference.

Once an object is sensed, the drift compensation mechanism ceases since the signal is legitimately high, and therefore should not cause the reference level to change.

Figure 3-3. Drift Compensation



The QT1012 drift compensation is asymmetric; the reference level drift-compensates in one direction faster than it does in the other. Specifically, it compensates faster for decreasing signals than for

increasing signals. Increasing signals should not be compensated for quickly, since an approaching finger could be compensated for partially or entirely before even approaching the sense electrode. However, an obstruction over the sense pad, for which the sensor has already made full allowance, could suddenly be removed leaving the sensor with an artificially elevated reference level and thus become insensitive to touch. In this latter case, the sensor will compensate for the object's removal very quickly.

With large values of Cs and small values of Cx, drift compensation will appear to operate more slowly than with the converse. Note that the positive and negative drift compensation rates are different.

3.7 Response Time

The QT1012 response time is highly dependent on the run mode and burst length, which in turn is dependent on Cs and Cx. With increasing Cs, response time slows, while increasing levels of Cx reduce response time.

3.8 Spread Spectrum

The QT1012 modulates its internal oscillator by $\pm 7.5\%$ during the measurement burst. This spreads the generated noise over a wider band, reducing emission levels. This also reduces susceptibility since there is no longer a single fundamental burst frequency.

3.9 Output Polarity Selection

The output (OUT pin) of the QT1012 can be configured to have an active high or active low output by means of the output configuration resistor Rop. The resistor is connected between the output and either Vss or Vdd (see Figure 3-4 and Table 3-1). A typical value for Rop is 100 k Ω .

Figure 3-4. Output Polarity (6-pin SOT23)





Table 3-1. Output Configuration

Name (Vop)	Function (Output Polarity)			
Vss	Active high			
Vdd	Active low			

Note: Some devices, such as Digital Transistors, have an internal biasing network that will naturally pull the OUT pin to its inactive state. If these are being used then the resistor Rop is not required (see Figure 3-5).

Figure 3-5. Output Connected to Digital Transistor (6-pin SOT23)



3.10 **Output Drive**

The OUT pin can sink or source up to 2 mA. When a large value of Cs (>20 nF) is used the OUT current should be limited to <1 mA to prevent gain-shifting side effects, which happen when the load current creates voltage drops on the die and bonding wires; these small shifts can materially influence the signal level to cause detection instability.

3.11 **Auto-Off Delay**

3.11.1 Introduction

In addition to toggling the output on/off with a key touch, the QT1012 can automatically switch the output off after a time, typically ±10 percent of the nominal stated time. This feature can be used to save power in situations where the switched device could be left on inadvertently.

The QT1012 has:

- three predefined delay times (Section 3.11.2)
- the ability to set a user-programmed delay (Section 3.11.3)
- the ability to override the auto-off delay (Section 3.11.5)

DS40001948A-page 13 **Datasheet** © 2017 Microchip Technology Inc.

The TIME and SNS pins are used to configure the Auto-off delay and must always be connected in one of the ways described in Section 3.11.2.

3.11.2 Auto-off – Predefined Delay

To configure the predefined delay the TIME pin is hard wired to Vss, Vdd or OUT as shown in Table 3-2 and Table 3-3. This provides nominal values of 15 minutes, 60 minutes or infinity (remains on until toggled off).

A single 1 $M\Omega$ resistor (Rm) is connected between the SNS pin and the logic level Vm to provide three auto-off functions: delay multiplication, delay override and delay retriggering. On power-up the logic level at Vm is assessed and the delay multiplication factor is set to x1 or x24 accordingly (see Figure 3-6, Table 3-2 and Table 3-3). At the end of each acquisition cycle the logic level of Vm is monitored to see if an Auto-off delay override is required (see Section 3.11.5).

Setting the delay multiplier to x24 will decrease the key sensitivity. To compensate, it may be necessary to increase the value of Cs.

Figure 3-6. Predefined Delay




Table 3-2. Predefined Auto-off Delay (Active High Output)

Vt	Auto-off Delay (t _o)
Vss	Infinity (remain on until toggled to off)
Vdd	15 minutes
OUT	60 minutes

Table 3-3. Predefined Auto-off Delay (Active Low Output)

Vt	Auto-off Delay (t _o)
Vss	15 minutes
Vdd	Infinity (remain on until toggled to off)
OUT	60 minutes


Table 3-4. Auto-off Delay Multiplier

Vm	Auto-off Delay Multiplier
Vss	t _o × 1
Vdd	t _o × 24

3.11.3 Auto-off – User-programmed Delay

If a user-programmed delay is required, a RC network (resistor and capacitor) can be used to set the auto-off delay (see Table 3-5 and Figure 3-7). The delay time is dependent on the RC time constant (Rt × Ct), the output polarity and the supply voltage. Section 3.11.4 gives full details of how to configure the QT1012 to have auto-off delay times ranging from minutes to hours.

Figure 3-7. Programmable Delay



3.11.4 Configuring the User-programmed Auto-off Delay

The QT1012 can be configured to give auto-off delays ranging from minutes to hours by means of a simple RC network and the delay multiplier input.

With the delay multiplier set at x1 the auto-off delay is calculated as follows:

Delay value = integer value of $\frac{Rt \times Ct}{K}$ x 15 seconds

and Rt × Ct =
$$\frac{\text{Delay} \times K}{15}$$

Note: Rt is in $k\Omega$, Ct is in nF, Delay is in seconds. K values are obtained from Figure 3-8.

To ensure correct operation it is recommended that the value of $\frac{Rt \times Ct}{K}$ is between 4 and 240.

Values outside this range may be interpreted as the hard wired options TIME linked to OUT and TIME linked to "off" respectively, causing the QT1012 to use the relevant predefined auto-off delays.


Table 3-5. Programmable Auto-off Delay (Example)Vm = Vss (delay multiplier = 1), Vdd = 3.5 V


Output Type	Auto-off Delay (Seconds)			
Active high	(Rt × Ct × 15) / 19			
Active low	(Rt × Ct × 15) / 22			

K values (19 and 22) are obtained from Figure 3-8.

Note: Rt is in $k\Omega$, Ct is in nF.

Figure 3-8. Typical Values of K Versus Supply Voltage





The charts in Figure 3-8 show typical values of K versus supply voltage for a QT1012 with active high or active low output.

Example using the formula to calculate Rt and Ct


Requirements:


- Active high output (Vop connected to VSS)
- Auto-off delay nominal 45 minutes
- VDD = 3.5 V

Proceed as follows:

- 1. Calculate Auto-off delay in seconds 45 x 60 = 2700
- 2. Obtain K from Figure 3-8, K = 22.8
- 3. Calculate Rt × Ct = $\frac{2700 \times 22.8}{15}$ = 4104
- 4. Decide on a value for Rt or Ct (for example, Ct = 47 nF)
- 5. Calculate Rt = $\frac{4104}{47}$ = 87 k
- 6. Verify that $\frac{RtxCt}{K}$ = 179 (which is between 4 and 240)

As an alternative to calculation, Figure 3-9 and Figure 3-10 show charts of typical curves of auto-off delay against resistor and capacitor values for active high and active low outputs at various values of VDD (delay multiplier = x1).





Example using a chart to calculate Rt and Ct

Requirements:

- Active low output (Vop connected to VSS)
- Auto-off delay 25 minutes
- VDD = 4 V
- 1. Calculate Auto-off delay in seconds $25 \times 60 = 1500$.
- 2. Find $\frac{1500}{1}$ = 1500 on the 4 V chart in Figure 3-10.
- 3. This shows the following suitable Ct / Rt combinations:
 - 100 nF / 20 kΩ
 - 47 nF / 40 k Ω
 - 22 nF / 90 kO
 - 10 nF / 190 kΩ

Note: The Auto-off delay times shown are nominal and will vary from chip to chip and with capacitor and resistor tolerance.

3.11.5 Auto-off – Overriding the Auto-off Delay

In normal operation the QT1012 output is turned off automatically after the auto-off delay. In some applications it may be useful to extend the auto-off delay ("sustain" function) or to switch the output off immediately ("cancel" function). This can be achieved by pulsing the voltage on the delay multiplier resistor Rm as shown in Figure 3-11 and Figure 3-12 on page 18.

To ensure the pulse is detected it must be present for typical times as shown in Table 3-6.

Table 3-6. Time Delay Pulse

Pulse Duration	Action
tp – series of short pulses, typically 65 ms	"Sustain"/retrigger (reload auto-off delay counter)
tp – long pulse, typically 250 ms	"Cancel"/switch output to off state and inhibit further touch detection until Vm returns to original state

While Vm is held in the override state the QT1012 inhibits bursts and waits for Vm to return to its original state. When Vm returns to its original state the QT1012 performs a sensor recalibration before continuing in its current output state.

Figure 3-11. Override Pulse (Delay Multiplier x1)




Figure 3-12. Override Pulse (Delay Multiplier x24)





Figure 3-13 shows override pulses being applied to a QT1012 with delay multiplier set to x1.

Figure 3-13. Overriding Auto-off




- P override (reload auto off delay) O switch output off (toff burst time + 50ms) C sensor recalibration

Datasheet DS40001948A-page 20 © 2017 Microchip Technology Inc.

3.12 Examples of Typical Applications

Figure 3-14. Application 1:

Active low, driving PNP transistor, auto-off time 375 s x 24 = 9000 s = 2.5 hours




Auto-off time obtained from 3 V chart in Figure 3-10 on page 16

Auto-off time obtained from 3 V chart in Figure 3-10

Figure 3-15. Application 2:

Active high, driving high impedance, auto-off time 315 s \times 1 = 5.25 minutes



Auto-off time obtained from 5 V chart in Figure 3-9 on page 15

Auto-off time obtained from 5 V chart in Figure 3-9

4. Circuit Guidelines

4.1 More Information

Refer to Application Note QTAN0002, Secrets of a Successful QTouch Design and the Touch Sensors Design Guide (both downloadable from the Microchip website), for more information on construction and design methods.

4.2 Sample Capacitor

Cs is the charge sensing sample capacitor. The required Cs value depends on the thickness of the panel and its dielectric constant. Thicker panels require larger values of Cs. Typical values are 2.2 nF to 50 nF depending on the sensitivity required; larger values of Cs demand higher stability and better dielectric to ensure reliable sensing.

The Cs capacitor should be a stable type, such as X7R ceramic or PPS film. For more consistent sensing from unit to unit, 5% tolerance capacitors are recommended. X7R ceramic types can be obtained in 5% tolerance at little or no extra cost. In applications where high sensitivity (long burst length) is required the use of PPS capacitors is recommended.

For battery powered operation a higher value sample capacitor may be required.

4.3 Rs Resistor

Series resistor Rs is in line with the electrode connection and should be used to limit ESD currents and to suppress radio frequency interference (RFI). It should be approximately 4.7 k Ω to 33 k Ω .

Although this resistor may be omitted, the device may become susceptible to external noise or RFI. See Application Note QTAN0002, Secrets of a Successful QTouch Design, for details of how to select these resistors.

4.4 Power Supply and PCB Layout

See Section 5.2 for the power supply range.

If the power supply is shared with another electronic system, care should be taken to ensure that the supply is free of digital spikes, sags, and surges which can adversely affect the QT1012. The QT1012 will track slow changes in Vdd, but it can be badly affected by rapid voltage fluctuations. It is highly recommended that a separate voltage regulator be used just for the QT1012 to isolate it from power supply shifts caused by other components.

If desired, the supply can be regulated using a Low Dropout (LDO) regulator, although such regulators often have poor transient line and load stability. See Application Note QTAN0002, Secrets of a Successful QTouch Design, for further information on power supply considerations.

Parts placement: The chip should be placed to minimize the SNSK trace length to reduce low frequency pickup, and to reduce stray Cx which degrades gain. The Cs and Rs resistors (see Figure 1-1) should be placed as close to the body of the chip as possible so that the trace between Rs and the SNSK pin is very short, thereby reducing the antenna-like ability of this trace to pick up high frequency signals and feed them directly into the chip. A ground plane can be used under the chip and the associated discrete components, but the trace from the Rs resistor and the electrode should not run near ground, to reduce loading.

For best EMC performance the circuit should be made entirely with SMT components.

Electrode trace routing: Keep the electrode trace (and the electrode itself) away from other signal, power, and ground traces including over or next to ground planes. Adjacent switching signals can induce noise onto the sensing signal; any adjacent trace or ground plane next to, or under, the electrode trace will cause an increase in Cx load and desensitize the device.

Bypass Capacitor: Important – For proper operation a 100 nF ($0.1 \mu F$) ceramic bypass capacitor must be used directly between Vdd and Vss, to prevent latch-up if there are substantial Vdd transients; for example, during an ESD event. The bypass capacitor should be placed very close to the VSS and VDD pins.

4.5 Power On

On initial power up, the QT1012 requires approximately 250 ms to power on to allow power supplies to stabilize. During this time the OUT pin state is not valid and should be ignored.

Note that recalibration takes approximately 200 ms, so the QT1012 takes approximately 450 ms in total from initial power on to become active.

5. Specifications

5.1 Absolute Maximum Specifications

Operating temperature	-40°C to +85°C		
Storage temperature	-55°C to +125°C		
Vdd	0 to +6.5 V		
Max continuous pin current, any control or drive pin	±20 mA		
Short circuit duration to Vss, any pin	Infinite		
Short circuit duration to Vdd, any pin	Infinite		
Voltage forced onto any pin	-0.6 V to (Vdd + 0.6) V		

CAUTION: Stresses beyond those listed under Absolute Maximum Specifications may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or other conditions beyond those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum specification conditions for extended periods may affect device reliability

5.2 Recommended Operating Conditions

Vdd	+1.8 to +5.5 V
Short-term supply ripple + noise	±20 mV
Long-term supply stability	±100 mV
Cs value	2.2 to 50 nF
Cx value	5 to 20 pF

5.3 AC Specifications

Table 5-1. Vdd = 3.0V, Cs = 10 nF, Cx = 5 pF, Ta = recommended range, unless otherwise noted

Parameter	Description	Min	Тур	Max	Units	Notes
Trc	Recalibration time	_	200	_	ms	Cs, Cx dependent
Трс	Charge duration	_	3	_	μs	±7.5% spread spectrum variation
Tpt	Transfer duration	_	6	_	μs	±7.5% spread spectrum variation
Tg1	Time between end of burst and start of the next (Fast mode)	_	2.6	_	ms	
Tg2	Time between end of burst and start of the next (LP mode)	_	80	_	ms	Increases with decreasing Vdd

Parameter	Description	Min	Тур	Max	Units	Notes
Tbl	Burst length	_	1.86	_	ms	Vdd, Cs and Cx dependent. See Section 4.2 for capacitor selection.
Tr	Response time	_	_	100	ms	

5.4 Signal Processing

Table 5-2. Vdd = 3.0V, Cs = 10 nF, Cx = 5 pF, Ta = recommended range, unless otherwise noted

Description	Min	Тур	Max	Units	Notes
Threshold differential	10			counts	
Hysteresis	2			counts	
Consensus filter length	4			samples	


5.5 DC Specifications

Table 5-3. Vdd = 3.0V, Cs = 4.7 nF, Cx = 5 pF, short charge pulse, Ta = recommended range, unless otherwise noted

Parameter	Description	Min	Тур	Max	Units	Notes
Vdd	Supply voltage	1.8		5.5	V	
Idd	Supply current	_	32 36 59 88 124	_	μΑ	1.8 V 2.0 V 3.0 V 4.0 V 5.0 V
Vdds	Supply turn-on slope	100	_	_	V/s	Required for proper start-up
Vil	Low input logic level	_	_	0.2 × Vdd 0.3 × Vdd	V	Vdd = 1.8 V - 2.4 V Vdd = 2.4 V - 5.5 V
Vhl	High input logic level	0.7 × Vdd 0.6 × Vdd	_		V	Vdd = 1.8 V - 2.4 V Vdd = 2.4 V - 5.5 V
Vol	Low output voltage	_	_	0.6	V	OUT, 4 mA sink
Voh	High output voltage	Vdd - 0.7	_	_	V	OUT, 1 mA source
lil	Input leakage current	_	_	±1	μΑ	
Сх	Load capacitance range	0	_	100	pF	
Ar	Acquisition resolution	_	9	14	bits	


5.6 Mechanical Dimensions

5.6.1 6-pin SOT23-6



Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging


5.6.2 8-pin UDFN/USON



Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging


5.7 Part Marking

5.7.1 AT42QT1012- 6-pin SOT23-6



Note: Samples of the AT42QT1012 may also be marked T10E.

5.7.2 AT42QT1012 – 8-pin UDFN/USON



Note: Samples of the AT42QT1012 may also be marked T10

5.8 Part Number

Part Number	Description
AT42QT1012 ⁽¹⁾	6-pin SOT23 RoHS compliant IC
AT42QT1012-TSHR	6-pin SOT23 RoHS compliant IC
AT42QT1012-MAH	8-pin UDFN/USON RoHS compliant IC

Notes: 1. Marking details: Top mark 1st line: ddddTY Top mark 2nd line: wwxxx

dddd= device, special code

T= Type

Y= Year last digit

ww= calendar workweek

xxx = trace code

5.9 Moisture Sensitivity Level (MSL)

MSL Rating	Peak Body Temperature	Specifications
MSL1	260°C	IPC/JEDEC J-STD-020

6. Associated Documents

For additional information, refer to the following document (downloadable from the Touch Technology area of the Microchip website, www.microchip.com):

- Touch Sensors Design Guide
- QTAN0002 Secrets of a Successful QTouch[®] Design

7. Revision History

Revision No.	History
Revision A – May 2009	Initial release
Revision B – August 2009	Update for chip revision 2.2
Revision C – August 2009	Minor update for clarity
Revision D – January 2010	Power specifications updated for revision 2.4.1
Revision E – January 2010	Part markings updated
Revision F – February 2010	MSL specification revised Other minor updates
Revision G – March 2010	Update for chip revision 2.6
Revision H – May 2010	UDFN/USON package added
Revision I – May 2013	Applied new template
DS40001948A – August 2017	Part marking clarification added. Replaces Atmel document 9543I.

The Microchip Web Site

Microchip provides online support via our web site at http://www.microchip.com/. This web site is used as a means to make files and information easily available to customers. Accessible by using your favorite Internet browser, the web site contains the following information:

- Product Support Data sheets and errata, application notes and sample programs, design resources, user's guides and hardware support documents, latest software releases and archived software
- General Technical Support Frequently Asked Questions (FAQ), technical support requests, online discussion groups, Microchip consultant program member listing
- Business of Microchip Product selector and ordering guides, latest Microchip press releases, listing of seminars and events, listings of Microchip sales offices, distributors and factory representatives

Customer Change Notification Service

Microchip's customer notification service helps keep customers current on Microchip products. Subscribers will receive e-mail notification whenever there are changes, updates, revisions or errata related to a specified product family or development tool of interest.

To register, access the Microchip web site at http://www.microchip.com/. Under "Support", click on "Customer Change Notification" and follow the registration instructions.

Customer Support

Users of Microchip products can receive assistance through several channels:

- Distributor or Representative
- Local Sales Office
- Field Application Engineer (FAE)
- Technical Support

Customers should contact their distributor, representative or Field Application Engineer (FAE) for support. Local sales offices are also available to help customers. A listing of sales offices and locations is included in the back of this document.

Technical support is available through the web site at: http://www.microchip.com/support

Microchip Devices Code Protection Feature

Note the following details of the code protection feature on Microchip devices:

- Microchip products meet the specification contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is one of the most secure families of its kind on the market today, when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods used to breach the code protection feature. All of these methods, to our knowledge, require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Most likely, the person doing so is engaged in theft of intellectual property.
- Microchip is willing to work with the customer who is concerned about the integrity of their code.

 Neither Microchip nor any other semiconductor manufacturer can guarantee the security of their code. Code protection does not mean that we are guaranteeing the product as "unbreakable."

Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

Legal Notice

Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION, INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

Trademarks

The Microchip name and logo, the Microchip logo, AnyRate, AVR, AVR logo, AVR Freaks, BeaconThings, BitCloud, CryptoMemory, CryptoRF, dsPIC, FlashFlex, flexPWR, Heldo, JukeBlox, KeeLoq, KeeLoq logo, Kleer, LANCheck, LINK MD, maXStylus, maXTouch, MediaLB, megaAVR, MOST, MOST logo, MPLAB, OptoLyzer, PIC, picoPower, PICSTART, PIC32 logo, Prochip Designer, QTouch, RightTouch, SAM-BA, SpyNIC, SST, SST Logo, SuperFlash, tinyAVR, UNI/O, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

ClockWorks, The Embedded Control Solutions Company, EtherSynch, Hyper Speed Control, HyperLight Load, IntelliMOS, mTouch, Precision Edge, and Quiet-Wire are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, Anyln, AnyOut, BodyCom, chipKIT, chipKIT logo, CodeGuard, CryptoAuthentication, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, EtherGREEN, In-Circuit Serial Programming, ICSP, Inter-Chip Connectivity, JitterBlocker, KleerNet, KleerNet logo, Mindi, MiWi, motorBench, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MultiTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, PureSilicon, QMatrix, RightTouch logo, REAL ICE, Ripple Blocker, SAM-ICE, Serial Quad I/O, SMART-I.S., SQI, SuperSwitcher, SuperSwitcher II, Total Endurance, TSHARC, USBCheck, VariSense, ViewSpan, WiperLock, Wireless DNA, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

Silicon Storage Technology is a registered trademark of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2017, Microchip Technology Incorporated, Printed in the U.S.A., All Rights Reserved.

ISBN: 978-1-5224-2071-2

Quality Management System Certified by DNV

ISO/TS 16949

Microchip received ISO/TS-16949:2009 certification for its worldwide headquarters, design and wafer fabrication facilities in Chandler and Tempe, Arizona; Gresham, Oregon and design centers in California and India. The Company's quality system processes and procedures are for its PIC® MCUs and dsPIC® DSCs, KEELOQ® code hopping devices, Serial EEPROMs, microperipherals, nonvolatile memory and analog products. In addition, Microchip's quality system for the design and manufacture of development systems is ISO 9001:2000 certified.



Worldwide Sales and Service

Corporate Office	AMERICAS	ASIA/PACIFIC	ASIA/PACIFIC	EUROPE
Chandler, AZ 88224-6199 Tower 6, The Gateway Fax: 88-592-2388-130 Fax: 43-7242-2244-393 Text: 480-792-7277 Technical Support Tel: 882-2943-5100 Tel: 88-59-59-210049 Fax: 484-485-2829 Tel: 191-80-3009-1424 Tel: 582-594-5100 Tel: 88-25-59-210049 Fax: 454-485-2829 Final	Corporate Office	Asia Pacific Office	China - Xiamen	Austria - Wels
Tel: 480-720-7200	2355 West Chandler Blvd.	Suites 3707-14, 37th Floor	Tel: 86-592-2388138	Tel: 43-7242-2244-39
Fax: 480-792-7277	Chandler, AZ 85224-6199	Tower 6, The Gateway	Fax: 86-592-2388130	Fax: 43-7242-2244-393
Technical Support	Tel: 480-792-7200	Harbour City, Kowloon	China - Zhuhai	Denmark - Copenhagen
Nttp://www.microchip.com/ support Fax: 852-2401-3431 India - Bangalore Finland - Espoo Support Australia - Sydnoy Tel: 91-80-3090-4144 Tel: 356-94520 Tel: 91-80-3090-4123 Tel: 31-80-3090-4123 Tel: 31-80-3090-4123 Tel: 31-80-3090-4123 Tel: 31-80-3090-4123 Tel: 31-80-3090-4123 Tel: 31-80-309-309 Tel: 31-80-309-309 Tel: 31-80-309-309 Tel: 31-80-309-309 Tel: 31-80-309-309 Tel: 31-80-309-309 Tel: 615-87-9614 Fax: 68-10-8528-2104 India - New Delhi Tel: 31-10-80-30-07-90 Tel: 678-957-1455 China - Chengdu Tel: 91-20-3019-1500 Germany - Garching Germany - Garching Germany - Garching Tel: 615-257-307 Tel: 68-28-8665-5811 Japan - Osaka Tel: 91-20-3019-1500 Germany - Garching Tel: 615-257-307 Tel: 68-28-8665-5891 Tel: 81-6152-7160 Germany - Health Tel: 91-20-3019-1500 Germany - Garching Tel: 49-2129-3766400 Germany - Health Tel: 81-3-8890-9500 Tel: 81-3-8890-9500 Tel: 81-3-8890-9500 Tel: 81-3-8890-9500 Tel: 81-3-8890-9770 Tel: 49-7131-67-3638 Tel: 68-79-9702-9880 Kora - Daegu Tel: 49-7131-67-3638 Tel: 68-79-9702-9880 Kora - Daegu Tel: 49-714-67-3638 Tel: 68-79-9702-9880 Kora - Daegu Tel: 49-714-67-3638 Tel: 68-29-875-8029 Tel: 82-53-744-4301 Germany - Munich Tel: 82-53-744-4301 Tel: 82-53-744-3001 Tel: 82-5	Fax: 480-792-7277	Hong Kong	Tel: 86-756-3210040	Tel: 45-4450-2828
Support Australia - Sydney Tel: 91-80-3090-4444 Tel: 358-9-4520-820 Web Address: Tel: 61-2-9868-6733 Fax: 91-80-3090-4123 France - Paris India - New Delhi Tel: 33-1-69-369-079 Tel: 91-11-4160-8631 Fax: 33-1-69-309-79 Tel: 91-11-4160-8631 Fax: 33-1-69-309-79 Tel: 91-9-8967-9614 Fax: 86-10-8568-7000 Fax: 91-11-4160-8631 Fax: 33-1-69-309-79 Tel: 91-9-8967-9614 Fax: 86-10-8528-2104 India - Pune Tel: 33-1-30-80-70-700 Tel: 678-867-967-1445 Tel: 91-30-91-1500 Germany - Garching Germany - Heilbronn Tel: 49-8931-9700 Tel: 49-8931-9700 Tel: 49-8931-9700 Tel: 49-8931-9700 Tel: 49-8931-9700 Tel: 49-8931-9700 Tel: 49-89-21-376-8400 Tel: 74-776-0007 Fax: 86-2-8880-9888 Japan - Tokyo Germany - Heilbronn Tel: 74-776-00087 Fax: 86-2-8980-9509 Tel: 81-8-6-8890-3771 Tel: 49-2-128-376-8400 Tel: 87-879-8702-8880 Tel: 81-8-689-3771 Tel: 49-89-27-144-14 Tel: 630-2285-0071 Tel: 68-0-28-758-9029 Fax: 81-3-6880-3771 Germany - Munitch Tel: 630-2285-0075 China - Hangghou Korea - Seoul Fax: 86-3-37-44-4301 Tel: 49-89-627-144-14 Tel: 98-2-856-971 Tel: 88-6-71-8792-8115 Tel: 82-2-58-7920 Tel: 49-89-627-144-14 Tel: 98-8-627-144-14 Tel: 98-8-627-144-14 Tel: 98-8-8627-144-14 Tel: 98-8-8627-144-14 Tel: 98-8-98-98 Tel: 98-98-98 Tel: 98-98	Technical Support:	Tel: 852-2943-5100	Fax: 86-756-3210049	Fax: 45-4485-2829
Web Address:	http://www.microchip.com/	Fax: 852-2401-3431	India - Bangalore	Finland - Espoo
Name	support	Australia - Sydney	Tel: 91-80-3090-4444	Tel: 358-9-4520-820
Allanta	Web Address:	Tel: 61-2-9868-6733	Fax: 91-80-3090-4123	France - Paris
Duluth, GA	www.microchip.com	Fax: 61-2-9868-6755	India - New Delhi	Tel: 33-1-69-53-63-20
Tel: 678-957-9614	Atlanta	China - Beijing	Tel: 91-11-4160-8631	Fax: 33-1-69-30-90-79
Fax: 678-957-1455	Duluth, GA	Tel: 86-10-8569-7000	Fax: 91-11-4160-8632	France - Saint Cloud
Austin, TX	Tel: 678-957-9614	Fax: 86-10-8528-2104	India - Pune	Tel: 33-1-30-60-70-00
Tel: 512-257-3370	Fax: 678-957-1455	China - Chengdu	Tel: 91-20-3019-1500	Germany - Garching
Boston China - Chongqing Fax: 81-6-6152-9310 Tel: 49-2129-3766400 Tel: 36-23-8809-9580 Tel: 74-760-0087 Fax: 86-23-8909-9500 Tel: 81-3-6880-3770 Tel: 49-7131-67-3636 Fax: 774-760-0088 China - Dongguan Fax: 81-3-6880-3771 Germany - Karlsruhe Tel: 49-7131-67-3636 Tel: 49-7131-67-3636 Tel: 85-769-8702-9880 Korea - Daegu Tel: 49-7131-67-3636 Tel: 630-285-0071 Tel: 86-20-8755-8029 Fax: 82-53-744-4301 Tel: 49-89-627-144-0 Tel: 630-285-0075 China - Hangzhou Korea - Seoul Fax: 49-89-627-144-0 Fax: 530-285-0075 China - Hangzhou Korea - Seoul Fax: 49-89-627-144-0 Fax: 530-285-0075 China - Hong Kong SAR See-258-5932 Tel: 49-80-627-144-4 Tel: 86-571-8792-8116 Fax: 82-2-584-7200 Tel: 49-8031-354-560 Tel: 49-8031-364-600 Tel: 58-25-8473-2460 Malaysia - Penang Fax: 60-3-6201-9859 Tel: 39-0331-742611 Tel: 28-25-8938 Tel: 39-0331-466781 Tel: 58-25-8938 Tel: 39-0331-466781 Tel: 39-034-7625286 Tel: 39-049-7625286 Tel: 49-80340 Tel: 4	Austin, TX	Tel: 86-28-8665-5511	Japan - Osaka	Tel: 49-8931-9700
Tel: 74-760-0087	Tel: 512-257-3370	Fax: 86-28-8665-7889	Tel: 81-6-6152-7160	Germany - Haan
Tel: 774-760-0087	Boston	China - Chongqing	Fax: 81-6-6152-9310	Tel: 49-2129-3766400
Fax: 774-760-0088	Westborough, MA	Tel: 86-23-8980-9588	Japan - Tokyo	Germany - Heilbronn
Chicago Tel: 86-769-8702-9880 Korea - Daegu Tel: 49-721-625370 China - Guangzhou Tel: 82-53-744-4301 Germany - Muninch Tel: 630-285-0075 China - Hangzhou Korea - Seoul Fax: 49-89-627-144-40 Fax: 630-285-0075 China - Hangzhou Korea - Seoul Fax: 49-89-627-144-40 China - Hong Kong SAR Seoul - Seoul Fax: 86-57-8792-8116 Fax: 82-2-558-5932 Tel: 49-8031-354-560 Sermany - Rosenheim China - Hong Kong SAR Seoul - S	Tel: 774-760-0087	Fax: 86-23-8980-9500	Tel: 81-3-6880- 3770	Tel: 49-7131-67-3636
Tel: 830-285-0071 Tel: 86-20-8755-8029 Fax: 82-53-744-4302 Tel: 49-89-627-144-0 Tel: 86-20-8755-8029 Fax: 82-53-744-4302 Tel: 49-89-627-144-0 Tel: 86-50-8755-8029 Fax: 82-55-744-4302 Fax: 49-89-627-144-0 Tel: 86-50-8755-8029 Fax: 82-55-744-4302 Fax: 49-89-627-144-4 Tel: 86-20-8755-8029 Fax: 82-55-87400 Fax: 49-89-627-144-4 Tel: 80-28-571-8792-8115 Tel: 82-2-554-7200 Germany - Rosenheim Addison, TX	Fax: 774-760-0088	China - Dongguan	Fax: 81-3-6880-3771	Germany - Karlsruhe
Tel: 86-20-875-8029 Fax: 82-53-744-4302 Tel: 49-89-627-144-0 Fax: 630-285-0075 China - Hangzhou Korea - Seoul Fax: 49-88-627-144-44 Dallas Tel: 86-571-8792-8115 Tel: 82-2-558-5932 Tel: 972-818-7423 China - Hong Kong SAR Tel: 872-818-7423 China - Hong Kong SAR Tel: 852-2943-5100 Malaysia - Kuala Lumpur Tel: 972-818-2924 Tel: 852-2943-5100 Malaysia - Kuala Lumpur Tel: 37-744-7705 Detroit Novi, MI China - Nanjing Fax: 60-3-6201-9859 Tel: 39-0331-742611 Tel: 28-848-4000 Tel: 86-25-8473-2460 Malaysia - Penang Fax: 39-0331-742611 Tel: 28-894-5983 China - Olingdao Indianapolis Tel: 86-25-8473-2470 Tel: 60-3-6201-8870 Italy - Padova Tel: 81-894-5983 Indianapolis Tel: 86-532-8502-7205 Tel: 31-773-8323 China - Shanghai Fax: 39-532-8502-7205 Tel: 31-773-8323 Tel: 31-332-8002 Tel: 31-773-5453 Tel: 86-21-3326-8001 Tel: 31-773-8453 Tel: 86-21-3326-8001 Tel: 31-753-8-2380 Fax: 86-21-3326-8001 Tel: 31-8-24-2334-2893 Tel: 31-8-8-25-8503 Tel: 31-8-23-8502 Tel: 31-8-8-25-8503 Tel: 31-8-23-8502 Tel: 31-8-23	Chicago	Tel: 86-769-8702-9880	Korea - Daegu	Tel: 49-721-625370
Fax: 630-285-0075	Itasca, IL	China - Guangzhou	Tel: 82-53-744-4301	Germany - Munich
Dallas	Tel: 630-285-0071	Tel: 86-20-8755-8029	Fax: 82-53-744-4302	Tel: 49-89-627-144-0
Fax: 86-571-8792-8116	Fax: 630-285-0075	China - Hangzhou	Korea - Seoul	Fax: 49-89-627-144-44
Tel: 972-818-7423	Dallas	Tel: 86-571-8792-8115	Tel: 82-2-554-7200	Germany - Rosenheim
Tel: 852-2943-5100	Addison, TX	Fax: 86-571-8792-8116	Fax: 82-2-558-5932 or	Tel: 49-8031-354-560
Detroit	Tel: 972-818-7423	China - Hong Kong SAR	82-2-558-5934	Israel - Ra'anana
Novi, MI	Fax: 972-818-2924	Tel: 852-2943-5100	Malaysia - Kuala Lumpur	Tel: 972-9-744-7705
Tel: 248-848-4000 Houston, TX Fax: 86-25-8473-2460 Fax: 86-25-8473-2470 Tel: 60-4-227-8870 Tel: 60-4-227-8870 Tel: 60-4-227-4068 Indianapolis Tel: 86-53-8502-7355 Philippines - Manila Noblesville, IN Fax: 86-532-8502-7205 Tel: 31-773-8323 China - Shanghai Fax: 36-2-634-9069 Fax: 317-773-8323 Tel: 86-21-3326-8000 Fax: 317-773-5453 Tel: 36-2-1-3326-8001 Tel: 65-6334-8870 Tel: 47-7289-7561 Los Angeles China - Shenyang Mission Viejo, CA Tel: 86-24-2334-2829 Tel: 949-462-9523 Fax: 86-24-2334-2333 Tel: 86-24-2334-2333 Tel: 86-25-848-2200 Tel: 951-273-7800 Tel: 951-273-7800 Tel: 96-755-8864-2200 Tel: 96-755-8864-2200 Tel: 919-844-7510 New York, NY Tel: 86-27-5980-5118 Tel: 63-2-694-1351 Tel: 48-3-500-4654 Tel: 48-735-9110 Tel: 48-29-8833-7256 Tel: 40-2-694-1350 Tel: 44-118-921-5800 Tel: 44-118-921-5800 Tel: 44-118-921-5800 Tel: 905-695-1980	Detroit	Fax: 852-2401-3431	Tel: 60-3-6201-9857	Italy - Milan
Houston, TX	Novi, MI	China - Nanjing	Fax: 60-3-6201-9859	Tel: 39-0331-742611
Tel: 281-894-5983	Tel: 248-848-4000	Tel: 86-25-8473-2460	Malaysia - Penang	Fax: 39-0331-466781
Indianapolis Tel: 86-532-8502-7355 Philippines - Manila Netherlands - Drunen	Houston, TX	Fax: 86-25-8473-2470	Tel: 60-4-227-8870	Italy - Padova
Noblesville, IN	Tel: 281-894-5983	China - Qingdao	Fax: 60-4-227-4068	Tel: 39-049-7625286
Tel: 317-773-8323 China - Shanghai Fax: 63-2-634-9069 Fax: 31-416-690340 Fax: 317-773-5453 Tel: 86-21-3326-8000 Singapore Norway - Trondheim Tel: 317-536-2380 Fax: 86-21-3326-8021 Tel: 65-6334-8870 Tel: 47-7289-7561 Los Angeles China - Shenyang Fax: 65-6334-8850 Poland - Warsaw Mission Viejo, CA Tel: 86-24-2334-2829 Taiwan - Hsin Chu Tel: 48-22-3325737 Tel: 949-462-9523 Fax: 86-24-2334-2393 Tel: 886-3-5778-366 Romania - Bucharest Fax: 949-462-9608 China - Shenzhen Fax: 886-3-5770-955 Tel: 40-21-407-87-50 Tel: 951-273-7800 Tel: 86-755-8864-2200 Taiwan - Kaohsiung Spain - Madrid Raleigh, NC Fax: 86-755-8203-1760 Tel: 886-7-213-7830 Tel: 34-91-708-08-90 Tel: 919-844-7510 China - Wuhan Taiwan - Taipei Fax: 34-91-708-08-91 New York, NY Tel: 86-27-5980-5300 Tel: 886-22-508-8600 Sweden - Gothenberg Tel: 408-735-9110 Tel: 86-29-8833-7252 Tel: 66-2-694-1351 Tel: 46-31-704-60-40 San Jose, CA China - Xian Thailand - Bangkok S	Indianapolis	Tel: 86-532-8502-7355	Philippines - Manila	Netherlands - Drunen
Fax: 317-773-5453 Tel: 86-21-3326-8000 Singapore Norway - Trondheim Tel: 317-536-2380 Fax: 86-21-3326-8021 Tel: 65-6334-8870 Tel: 47-7289-7561 Los Angeles China - Shenyang Fax: 65-6334-8850 Poland - Warsaw Mission Viejo, CA Tel: 86-24-2334-2829 Taiwan - Hsin Chu Tel: 48-22-3325737 Tel: 949-462-9523 Fax: 86-24-2334-2393 Tel: 886-3-5778-366 Romania - Bucharest Fax: 949-462-9608 China - Shenzhen Fax: 886-3-5770-955 Tel: 40-21-407-87-50 Tel: 951-273-7800 Tel: 86-755-8864-2200 Taiwan - Kaohsiung Spain - Madrid Raleigh, NC Fax: 86-755-8203-1760 Tel: 886-7-213-7830 Tel: 34-91-708-08-90 Tel: 919-844-7510 China - Wuhan Taiwan - Taipei Fax: 34-91-708-08-91 New York, NY Tel: 86-27-5980-5300 Tel: 886-2-2508-8600 Sweden - Gothenberg Tel: 631-435-6000 Fax: 86-27-5980-5118 Fax: 886-2-2508-0102 Tel: 46-31-704-60-40 San Jose, CA China - Xian Thailand - Bangkok Sweden - Stockholm Tel: 408-436-4270 Fax: 86-29-8833-7256 Fax: 66-2-694-1350	Noblesville, IN	Fax: 86-532-8502-7205	Tel: 63-2-634-9065	Tel: 31-416-690399
Tel: 317-536-2380 Fax: 86-21-3326-8021 Tel: 65-6334-8870 Tel: 47-7289-7561 Los Angeles China - Shenyang Fax: 65-6334-8850 Poland - Warsaw Mission Viejo, CA Tel: 86-24-2334-2829 Taiwan - Hsin Chu Tel: 48-22-3325737 Tel: 949-462-9523 Fax: 86-24-2334-2393 Tel: 886-3-5778-366 Romania - Bucharest Fax: 949-462-9608 China - Shenzhen Fax: 886-3-5770-955 Tel: 40-21-407-87-50 Tel: 951-273-7800 Tel: 86-755-8864-2200 Taiwan - Kaohsiung Spain - Madrid Raleigh, NC Fax: 86-755-8203-1760 Tel: 886-7-213-7830 Tel: 34-91-708-08-90 Tel: 919-844-7510 China - Wuhan Taiwan - Taipei Fax: 34-91-708-08-91 New York, NY Tel: 86-27-5980-5300 Tel: 886-2-2508-8600 Sweden - Gothenberg Tel: 631-435-6000 Fax: 86-27-5980-5118 Fax: 886-2-2508-0102 Tel: 46-31-704-60-40 San Jose, CA China - Xian Thailand - Bangkok Sweden - Stockholm Tel: 408-735-9110 Tel: 86-29-8833-7256 Fax: 66-2-694-1351 Tel: 46-8-5090-4654 Tel: 408-436-4270 Fax: 86-29-8833-7256 Fax: 66-2-694-1350 UK - Wokingham Tel: 44-118-921-5800 Tel: 905-695-1980	Tel: 317-773-8323	China - Shanghai	Fax: 63-2-634-9069	Fax: 31-416-690340
China - Shenyang Fax: 65-6334-8850 Poland - Warsaw	Fax: 317-773-5453	Tel: 86-21-3326-8000	Singapore	Norway - Trondheim
Mission Viejo, CA Tel: 86-24-2334-2829 Taiwan - Hsin Chu Tel: 48-22-3325737 Tel: 949-462-9523 Fax: 86-24-2334-2393 Tel: 886-3-5778-366 Romania - Bucharest Fax: 949-462-9608 China - Shenzhen Fax: 886-3-5770-955 Tel: 40-21-407-87-50 Tel: 951-273-7800 Tel: 86-755-8864-2200 Taiwan - Kaohsiung Spain - Madrid Raleigh, NC Fax: 86-755-8203-1760 Tel: 886-7-213-7830 Tel: 34-91-708-08-90 Tel: 919-844-7510 China - Wuhan Taiwan - Taipei Fax: 34-91-708-08-91 New York, NY Tel: 86-27-5980-5300 Tel: 886-2-2508-8600 Sweden - Gothenberg Tel: 631-435-6000 Fax: 86-27-5980-5118 Fax: 886-2-2508-0102 Tel: 46-31-704-60-40 San Jose, CA China - Xian Thailand - Bangkok Sweden - Stockholm Tel: 408-735-9110 Tel: 86-29-8833-7252 Tel: 66-2-694-1351 Tel: 46-8-5090-4654 Tel: 408-436-4270 Fax: 86-29-8833-7256 Fax: 66-2-694-1350 UK - Wokingham Canada - Toronto Tel: 905-695-1980 Fax: 44-118-921-5820	Tel: 317-536-2380	Fax: 86-21-3326-8021	Tel: 65-6334-8870	Tel: 47-7289-7561
Tel: 949-462-9523 Fax: 86-24-2334-2393 Tel: 886-3-5778-366 Romania - Bucharest Fax: 949-462-9608 China - Shenzhen Fax: 886-3-5770-955 Tel: 40-21-407-87-50 Tel: 951-273-7800 Tel: 86-755-8864-2200 Taiwan - Kaohsiung Spain - Madrid Raleigh, NC Fax: 86-755-8203-1760 Tel: 886-7-213-7830 Tel: 34-91-708-08-90 Tel: 919-844-7510 China - Wuhan Taiwan - Taipei Fax: 34-91-708-08-91 New York, NY Tel: 86-27-5980-5300 Tel: 886-2-2508-8600 Sweden - Gothenberg Tel: 631-435-6000 Fax: 86-27-5980-5118 Fax: 886-2-2508-0102 Tel: 46-31-704-60-40 San Jose, CA China - Xian Thailand - Bangkok Sweden - Stockholm Tel: 408-735-9110 Tel: 86-29-8833-7252 Tel: 66-2-694-1351 Tel: 46-8-5090-4654 Tel: 408-436-4270 Fax: 86-29-8833-7256 Fax: 66-2-694-1350 UK - Wokingham Canada - Toronto Tel: 905-695-1980 Fax: 44-118-921-5820	Los Angeles	China - Shenyang	Fax: 65-6334-8850	Poland - Warsaw
Fax: 949-462-9608 China - Shenzhen Fax: 886-3-5770-955 Tel: 40-21-407-87-50 Tel: 951-273-7800 Tel: 86-755-8864-2200 Taiwan - Kaohsiung Spain - Madrid Raleigh, NC Fax: 86-755-8203-1760 Tel: 886-7-213-7830 Tel: 34-91-708-08-90 Tel: 919-844-7510 China - Wuhan Taiwan - Taipei Fax: 34-91-708-08-91 New York, NY Tel: 86-27-5980-5300 Tel: 886-2-2508-8600 Sweden - Gothenberg Tel: 631-435-6000 Fax: 86-27-5980-5118 Fax: 886-2-2508-0102 Tel: 46-31-704-60-40 San Jose, CA China - Xian Thailand - Bangkok Sweden - Stockholm Tel: 408-735-9110 Tel: 86-29-8833-7252 Tel: 66-2-694-1351 Tel: 46-8-5090-4654 Tel: 408-436-4270 Fax: 86-29-8833-7256 Fax: 66-2-694-1350 UK - Wokingham Canada - Toronto Tel: 905-695-1980 Fax: 44-118-921-5800	Mission Viejo, CA	Tel: 86-24-2334-2829	Taiwan - Hsin Chu	Tel: 48-22-3325737
Tel: 951-273-7800 Raleigh, NC Fax: 86-755-8864-2200 Tel: 919-844-7510 New York, NY Tel: 631-435-6000 San Jose, CA Tel: 408-735-9110 Tel: 408-436-4270 Tel: 408-436-4270 Tel: 905-695-1980 Tel: 86-755-8864-2200 Tel: 86-755-8203-1760 Tel: 886-7-213-7830 Tel: 886-2-2508-8600 Tel: 886-2-2508-8600 Tel: 886-2-2508-8600 Tel: 886-2-2508-0102 Tel: 46-31-704-60-40 Sweden - Gothenberg Tel: 46-31-704-60-40 Sweden - Stockholm Tel: 408-436-4270 Fax: 86-29-8833-7256 Fax: 66-2-694-1351 Tel: 46-8-5090-4654 UK - Wokingham Tel: 44-118-921-5800 Fax: 44-118-921-5820	Tel: 949-462-9523	Fax: 86-24-2334-2393	Tel: 886-3-5778-366	Romania - Bucharest
Raleigh, NC Fax: 86-755-8203-1760 Tel: 886-7-213-7830 Tel: 34-91-708-08-90 Tel: 919-844-7510 China - Wuhan Taiwan - Taipei Fax: 34-91-708-08-91 New York, NY Tel: 86-27-5980-5300 Tel: 886-2-2508-8600 Sweden - Gothenberg Tel: 631-435-6000 Fax: 86-27-5980-5118 Fax: 886-2-2508-0102 Tel: 46-31-704-60-40 San Jose, CA China - Xian Thailand - Bangkok Sweden - Stockholm Tel: 408-735-9110 Tel: 86-29-8833-7252 Tel: 66-2-694-1351 Tel: 46-8-5090-4654 Tel: 408-436-4270 Fax: 86-29-8833-7256 Fax: 66-2-694-1350 UK - Wokingham Canada - Toronto Tel: 905-695-1980 Fax: 44-118-921-5820	Fax: 949-462-9608	China - Shenzhen	Fax: 886-3-5770-955	Tel: 40-21-407-87-50
Tel: 919-844-7510 China - Wuhan Taiwan - Taipei Fax: 34-91-708-08-91 New York, NY Tel: 86-27-5980-5300 Tel: 886-2-2508-8600 Sweden - Gothenberg Tel: 631-435-6000 Fax: 86-27-5980-5118 Fax: 886-2-2508-0102 Tel: 46-31-704-60-40 San Jose, CA China - Xian Thailand - Bangkok Sweden - Stockholm Tel: 408-735-9110 Tel: 86-29-8833-7252 Tel: 66-2-694-1351 Tel: 46-8-5090-4654 Tel: 408-436-4270 Fax: 86-29-8833-7256 Fax: 66-2-694-1350 UK - Wokingham Canada - Toronto Tel: 905-695-1980 Fax: 44-118-921-5820	Tel: 951-273-7800	Tel: 86-755-8864-2200	Taiwan - Kaohsiung	Spain - Madrid
New York, NY Tel: 86-27-5980-5300 Tel: 886-2-2508-8600 Sweden - Gothenberg Tel: 631-435-6000 Fax: 86-27-5980-5118 Fax: 886-2-2508-0102 Tel: 46-31-704-60-40 San Jose, CA China - Xian Thailand - Bangkok Sweden - Stockholm Tel: 408-735-9110 Tel: 86-29-8833-7252 Tel: 66-2-694-1351 Tel: 46-8-5090-4654 Tel: 408-436-4270 Fax: 86-29-8833-7256 Fax: 66-2-694-1350 UK - Wokingham Canada - Toronto Tel: 905-695-1980 Fax: 44-118-921-5820	Raleigh, NC	Fax: 86-755-8203-1760	Tel: 886-7-213-7830	Tel: 34-91-708-08-90
Tel: 631-435-6000 Fax: 86-27-5980-5118 Fax: 886-2-2508-0102 Tel: 46-31-704-60-40 San Jose, CA China - Xian Thailand - Bangkok Sweden - Stockholm Tel: 408-735-9110 Tel: 86-29-8833-7252 Tel: 66-2-694-1351 Tel: 46-8-5090-4654 Tel: 408-436-4270 Fax: 86-29-8833-7256 Fax: 66-2-694-1350 UK - Wokingham Canada - Toronto Tel: 905-695-1980 Fax: 44-118-921-5820	Tel: 919-844-7510	China - Wuhan	Taiwan - Taipei	Fax: 34-91-708-08-91
San Jose, CA China - Xian Thailand - Bangkok Sweden - Stockholm Tel: 408-735-9110 Tel: 86-29-8833-7252 Tel: 66-2-694-1351 Tel: 46-8-5090-4654 Tel: 408-436-4270 Fax: 86-29-8833-7256 Fax: 66-2-694-1350 UK - Wokingham Canada - Toronto Tel: 44-118-921-5800 Fax: 44-118-921-5820	New York, NY	Tel: 86-27-5980-5300	Tel: 886-2-2508-8600	Sweden - Gothenberg
Tel: 408-735-9110 Tel: 86-29-8833-7252 Tel: 66-2-694-1351 Tel: 46-8-5090-4654 Tel: 408-436-4270 Fax: 86-29-8833-7256 Fax: 66-2-694-1350 UK - Wokingham Tel: 44-118-921-5800 Fax: 44-118-921-5820	Tel: 631-435-6000	Fax: 86-27-5980-5118	Fax: 886-2-2508-0102	Tel: 46-31-704-60-40
Tel: 408-436-4270 Fax: 86-29-8833-7256 Fax: 66-2-694-1350 UK - Wokingham Canada - Toronto Tel: 44-118-921-5800 Tel: 905-695-1980 Fax: 44-118-921-5820	San Jose, CA	China - Xian	Thailand - Bangkok	Sweden - Stockholm
Canada - Toronto Tel: 44-118-921-5800 Tel: 905-695-1980 Fax: 44-118-921-5820	Tel: 408-735-9110	Tel: 86-29-8833-7252	Tel: 66-2-694-1351	Tel: 46-8-5090-4654
Tel: 905-695-1980 Fax: 44-118-921-5820	Tel: 408-436-4270	Fax: 86-29-8833-7256	Fax: 66-2-694-1350	UK - Wokingham
	Canada - Toronto			Tel: 44-118-921-5800
Fax: 905-695-2078	Tel: 905-695-1980			Fax: 44-118-921-5820
	Fax: 905-695-2078			