Dual supply translating transceiver; 3-state Rev. 9 — 13 August 2018

### 1. General description

The 74LVC2T45; 74LVCH2T45 are dual bit, dual supply translating transceivers with 3-state outputs that enable bidirectional level translation. They feature two 2-bits input-output ports (nA and nB), a direction control input (DIR) and dual supply pins ( $V_{CC(A)}$  and  $V_{CC(B)}$ ). Both  $V_{CC(A)}$  and  $V_{CC(B)}$  can be supplied at any voltage between 1.2 V and 5.5 V making the device suitable for translating between any of the low voltage nodes (1.2 V, 1.5 V, 1.8 V, 2.5 V, 3.3 V and 5.0 V). Pins nA and DIR are referenced to  $V_{CC(A)}$  and pins nB are referenced to  $V_{CC(B)}$ . A HIGH on DIR allows transmission from nA to nB and a LOW on DIR allows transmission from nB to nA.

The devices are fully specified for partial power-down applications using  $I_{OFF}$ . The  $I_{OFF}$  circuitry disables the output, preventing any damaging backflow current through the device when it is powered down. In suspend mode when either  $V_{CC(A)}$  or  $V_{CC(B)}$  are at GND level, both A port and B port are in the high-impedance OFF-state.

Active bus hold circuitry in the 74LVCH2T45 holds unused or floating data inputs at a valid logic level.

### 2. Features and benefits

- Wide supply voltage range:
  - V<sub>CC(A)</sub>: 1.2 V to 5.5 V
  - V<sub>CC(B)</sub>: 1.2 V to 5.5 V
- High noise immunity
- Complies with JEDEC standards:
  - JESD8-7 (1.2 V to 1.95 V)
  - JESD8-5 (1.8 V to 2.7 V)
  - JESD8C (2.7 V to 3.6 V)
  - JESD36 (4.5 V to 5.5 V)
- ESD protection:
  - HBM JESD22-A114F Class 3A exceeds 4000 V
  - MM JESD22-A115-A exceeds 200 V
  - CDM JESD22-C101E exceeds 1000 V
- Maximum data rates:
  - 420 Mbps (3.3 V to 5.0 V translation)
  - 210 Mbps (translate to 3.3 V))
  - 140 Mbps (translate to 2.5 V)
  - 75 Mbps (translate to 1.8 V)
  - 60 Mbps (translate to 1.5 V)
- Suspend mode
- Latch-up performance exceeds 100 mA per JESD 78 Class II
- ±24 mA output drive (V<sub>CC</sub> = 3.0 V)
- Inputs accept voltages up to 5.5 V
- Low power consumption: 16 µA maximum I<sub>CC</sub>
- I<sub>OFF</sub> circuitry provides partial Power-down mode operation
- Multiple package options
- Specified from -40 °C to +85 °C and -40 °C to +125 °C

# ne<mark>x</mark>peria

# 3. Ordering information


Type number	Package				
	Temperature range	Name	Description	Version	
74LVC2T45DC	-40 °C to +125 °C	VSSOP8	plastic very thin shrink small outline package;	SOT765-1	
74LVCH2T45DC			8 leads; body width 2.3 mm		
74LVC2T45GT	-40 °C to +125 °C	XSON8	plastic extremely thin small outline package;	SOT833-1	
74LVCH2T45GT			no leads; 8 terminals; body 1 × 1.95 × 0.5 mm		
74LVC2T45GF	-40 °C to +125 °C	XSON8	extremely thin small outline package; no leads;	SOT1089	
74LVCH2T45GF			8 terminals; body 1.35 × 1 × 0.5 mm		
74LVC2T45GM	-40 °C to +125 °C	XQFN8	plastic, extremely thin quad flat package;	SOT902-2	
74LVCH2T45GM			no leads; 8 terminals; body 1.6 × 1.6 × 0.5 mm		
74LVC2T45GN	-40 °C to +125 °C	XSON8	extremely thin small outline package; no leads;	SOT1116	
74LVCH2T45GN			8 terminals; body 1.2 × 1.0 × 0.35 mm		
74LVC2T45GS	-40 °C to +125 °C	XSON8	extremely thin small outline package; no leads;	SOT1203	
74LVCH2T45GS			8 terminals; body 1.35 × 1.0 × 0.35 mm		

# 4. Marking

Table 2. Marking	
Type number	Marking code [1]
74LVC2T45DC	V45
74LVCH2T45DC	X45
74LVC2T45GT	V45
74LVCH2T45GT	X45
74LVC2T45GF	V5
74LVCH2T45GF	X5
74LVC2T45GM	V45
74LVCH2T45GM	X45
74LVC2T45GN	V5
74LVCH2T45GN	X5
74LVC2T45GS	V5
74LVCH2T45GS	X5


[1] The pin 1 indicator is located on the lower left corner of the device, below the marking code.

# 5. Functional diagram



### 6. Pinning information

### 6.1. Pinning



Symbol	Pin		Description
	SOT765-1, SOT833-1, SOT1089, SOT1116 and SOT1203	SOT902-2	
V <sub>CC(A)</sub>	1	7	supply voltage A (port A and DIR)
1A	2	6	data input or output
2A	3	5	data input or output
GND	4	4	ground (0 V)
DIR	5	3	direction control
2B	6	2	data input or output
1B	7	1	data input or output
V <sub>CC(B)</sub>	8	8	supply voltage B (port B)

### 6.2. Pin description

# 7. Functional description

#### Table 4. Function table

H = HIGH voltage level; L = LOW voltage level; X = don't care; Z = high-impedance OFF-state.

Supply voltage	Input	Input/output [1]			
V <sub>CC(A)</sub> , V <sub>CC(B)</sub>	DIR	nA	nB		
1.2 V to 5.5 V	L	nA = nB	input		
1.2 V to 5.5 V	Н	input	nB = nA		
GND [2]	Х	Z	Z		

[1] The input circuit of the data I/O is always active.

[2] When either  $V_{CC(A)}$  or  $V_{CC(B)}$  is at GND level, the device goes into suspend mode.

74LVC\_LVCH2T45

### 8. Limiting values

#### Table 5. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	Min	Max	Unit
V <sub>CC(A)</sub>	supply voltage A		-0.5	+6.5	V
V <sub>CC(B)</sub>	supply voltage B		-0.5	+6.5	V
I <sub>IK</sub>	input clamping current	V <sub>I</sub> < 0 V	-50	-	mA
VI	input voltage	]	-0.5	+6.5	V
I <sub>OK</sub>	output clamping current	V <sub>O</sub> < 0 V	-50	-	mA
Vo	output voltage	Active mode [1][2][3	-0.5	V <sub>CCO</sub> + 0.5	V
		Suspend or 3-state mode [	] -0.5	+6.5	V
I <sub>O</sub>	output current	$V_{O} = 0 V \text{ to } V_{CCO}$ [2	2] -	±50	mA
I <sub>CC</sub>	supply current	I <sub>CC(A)</sub> or I <sub>CC(B)</sub>	-	100	mA
I <sub>GND</sub>	ground current		-100	-	mA
T <sub>stg</sub>	storage temperature		-65	+150	°C
P <sub>tot</sub>	total power dissipation	T <sub>amb</sub> = -40 °C to +125 °C [4	l] -	250	mW

[1] The minimum input voltage ratings and output voltage ratings may be exceeded if the input and output current ratings are observed.

[2]  $V_{CCO}$  is the supply voltage associated with the output port.

[3] V<sub>CCO</sub> + 0.5 V should not exceed 6.5 V.

[4] For VSSOP8 packages: above 110 °C the value of P<sub>tot</sub> derates linearly with 8.0 mW/K.

For XSON8 and XQFN8 packages: above 118 °C the value of P<sub>tot</sub> derates linearly with 7.8 mW/K.

### 9. Recommended operating conditions

#### Table 6. Recommended operating conditions

Symbol	Parameter	Conditions	Min	Мах	Unit
V <sub>CC(A)</sub>	supply voltage A		1.2	5.5	V
V <sub>CC(B)</sub>	supply voltage B		1.2	5.5	V
VI	input voltage		0	5.5	V
Vo	output voltage	Active mode [1]	0	V <sub>cco</sub>	V
		Suspend or 3-state mode	0	5.5	V
T <sub>amb</sub>	ambient temperature		-40	+125	°C
Δt/ΔV	input transition rise and fall rate	V <sub>CCI</sub> = 1.2 V [2]	-	20	ns/V
		V <sub>CCI</sub> = 1.4 V to 1.95 V	-	20	ns/V
		V <sub>CCI</sub> = 2.3 V to 2.7 V	-	20	ns/V
		V <sub>CCI</sub> = 3 V to 3.6 V	-	10	ns/V
		V <sub>CCI</sub> = 4.5 V to 5.5 V	-	5	ns/V

[1]  $V_{CCO}$  is the supply voltage associated with the output port.

[2] V<sub>CCI</sub> is the supply voltage associated with the input port.

# **10. Static characteristics**

#### Table 7. Typical static characteristics at T<sub>amb</sub> = 25 °C

At recommended operating conditions; voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions		Min	Тур	Max	Unit
V <sub>OH</sub>	HIGH-level output voltage	$V_{I} = V_{IH} \text{ or } V_{IL}; I_{O} = -3 \text{ mA}; V_{CCO} = 1.2 \text{ V}$	[1]	-	1.09	-	V
V <sub>OL</sub>	LOW-level output voltage	$V_I = V_{IH} \text{ or } V_{IL}; I_O = 3 \text{ mA}; V_{CCO} = 1.2 \text{ V}$	[1]	-	0.07	-	V
I <sub>I</sub>	input leakage current	DIR input; V <sub>I</sub> = 0 V to 5.5 V; V <sub>CCI</sub> = 1.2 V to 5.5 V	[2]	-	-	±1	μA
I <sub>BHL</sub>	bus hold LOW current	A or B port; $V_{I}$ = 0.42 V; $V_{CCI}$ = 1.2 V	[2]	-	19	-	μA
I <sub>BHH</sub>	bus hold HIGH current	A or B port; V <sub>I</sub> = 0.78 V; V <sub>CCI</sub> = 1.2 V	[2]	-	-19	-	μA
I <sub>BHLO</sub>	bus hold LOW overdrive current	A or B port; V <sub>CCI</sub> = 1.2 V	[2][3]	-	19	-	μA
I <sub>BHHO</sub>	bus hold HIGH overdrive current	A or B port; V <sub>CCI</sub> = 1.2 V	[2][3]	-	-19	-	μA
I <sub>OZ</sub>	OFF-state output current	A or B port; $V_0 = 0$ V or $V_{CCO}$ ; $V_{CCO} = 1.2$ V to 5.5 V	[1]	-	-	±1	μA
I <sub>OFF</sub>	power-off leakage current	A port; V <sub>1</sub> or V <sub>O</sub> = 0 V to 5.5 V; V <sub>CC(A)</sub> = 0 V; V <sub>CC(B)</sub> = 1.2 V to 5.5 V		-	-	±1	μA
		B port; V <sub>I</sub> or V <sub>O</sub> = 0 V to 5.5 V; V <sub>CC(B)</sub> = 0 V; V <sub>CC(A)</sub> = 1.2 V to 5.5 V		-	-	±1	μA
CI	input capacitance	DIR input; V <sub>I</sub> = 0 V or 3.3 V; V <sub>CC(A)</sub> = V <sub>CC(B)</sub> = 3.3 V		-	2.2	-	pF
C <sub>I/O</sub>	input/output capacitance	A and B port; suspend mode; V <sub>O</sub> = 3.3 V or 0 V; V <sub>CC(A)</sub> = V <sub>CC(B)</sub> = 3.3 V		-	6.0	-	pF

[1]  $V_{CCO}$  is the supply voltage associated with the output port.

[2] V<sub>CCI</sub> is the supply voltage associated with the data input port.

[3] To guarantee the node switches, an external driver must source/sink at least  $I_{BHLO}/I_{BHHO}$  when the input is in the range  $V_{IL}$  to  $V_{IH}$ .

#### **Table 8. Static characteristics**

At recommended operating conditions; voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	-40 °C to	+85 °C	-40 °C to	+125 °C	Unit
			Min	Max	Min	Мах	
V <sub>IH</sub>	HIGH-level	data input [1]					
	input voltage	V <sub>CCI</sub> = 1.2 V	0.8V <sub>CCI</sub>	-	0.8V <sub>CCI</sub>	-	V
		V <sub>CCI</sub> = 1.4 V to 1.95 V	0.65V <sub>CCI</sub>	-	0.65V <sub>CCI</sub>	-	V
		V <sub>CCI</sub> = 2.3 V to 2.7 V	1.7	-	1.7	-	V
		V <sub>CCI</sub> = 3.0 V to 3.6 V	2.0	-	2.0	-	V
		V <sub>CCI</sub> = 4.5 V to 5.5 V	0.7V <sub>CCI</sub>	-	0.7V <sub>CCI</sub>	-	V
		DIR input					
		V <sub>CCI</sub> = 1.2 V	0.8V <sub>CC(A)</sub>	-	0.8V <sub>CC(A)</sub>	-	V
		V <sub>CCI</sub> = 1.4 V to 1.95 V	0.65V <sub>CC(A)</sub>	-	0.65V <sub>CC(A)</sub>	-	V
		V <sub>CCI</sub> = 2.3 V to 2.7 V	1.7	-	1.7	-	V
		V <sub>CCI</sub> = 3.0 V to 3.6 V	2.0	-	2.0	-	V
		V <sub>CCI</sub> = 4.5 V to 5.5 V	0.7V <sub>CC(A)</sub>	-	0.7V <sub>CC(A)</sub>	-	V

### Dual supply translating transceiver; 3-state

Symbol	Parameter	Conditions		-40 °C t	o +85 °C	-40 °C to	• +125 °C	Unit
				Min	Max	Min	Max	
VIL	LOW-level input	data input	[1]					
	voltage	V <sub>CCI</sub> = 1.2 V		-	0.2V <sub>CCI</sub>	-	0.2V <sub>CCI</sub>	V
		V <sub>CCI</sub> = 1.4 V to 1.95 V		-	0.35V <sub>CCI</sub>	-	0.35V <sub>CCI</sub>	V
		V <sub>CCI</sub> = 2.3 V to 2.7 V		-	0.7	-	0.7	V
		V <sub>CCI</sub> = 3.0 V to 3.6 V		-	0.8	-	0.8	V
		V <sub>CCI</sub> = 4.5 V to 5.5 V		-	0.3V <sub>CCI</sub>	-	0.3V <sub>CCI</sub>	V
		DIR input						
		V <sub>CCI</sub> = 1.2 V		-	0.2V <sub>CC(A)</sub>	-	0.2V <sub>CC(A)</sub>	V
		V <sub>CCI</sub> = 1.4 V to 1.95 V		-	0.35V <sub>CC(A)</sub>	-	0.35V <sub>CC(A)</sub>	V
		V <sub>CCI</sub> = 2.3 V to 2.7 V		-	0.7	-	0.7	V
		V <sub>CCI</sub> = 3.0 V to 3.6 V		-	0.8	-	0.8	V
		V <sub>CCI</sub> = 4.5 V to 5.5 V		-	0.3V <sub>CC(A)</sub>	-	0.3V <sub>CC(A)</sub>	V
V <sub>OH</sub>	HIGH-level	$V_{I} = V_{IH}$						
	output voltage	I <sub>O</sub> = -100 μA; V <sub>CCO</sub> = 1.2 V to 4.5 V	[2]	V <sub>CCO</sub> - 0.1	-	V <sub>CCO</sub> - 0.1	-	V
		I <sub>O</sub> = -6 mA; V <sub>CCO</sub> = 1.4 V		1.0	-	1.0	-	V
		I <sub>O</sub> = -8 mA; V <sub>CCO</sub> = 1.65 V		1.2	-	1.2	-	V
		I <sub>O</sub> = -12 mA; V <sub>CCO</sub> = 2.3 V		1.9	-	1.9	-	V
		I <sub>O</sub> = -24 mA; V <sub>CCO</sub> = 3.0 V		2.4	-	2.4	-	V
		I <sub>O</sub> = -32 mA; V <sub>CCO</sub> = 4.5 V		3.8	-	3.8	-	V
V <sub>OL</sub>	LOW-level output voltage	$V_{I} = V_{IL}$	[2]					
		I <sub>O</sub> = 100 μA; V <sub>CCO</sub> = 1.2 V to 4.5 V		-	0.1	-	0.1	V
		I <sub>O</sub> = 6 mA; V <sub>CCO</sub> = 1.4 V		-	0.3	-	0.3	V
		I <sub>O</sub> = 8 mA; V <sub>CCO</sub> = 1.65 V		-	0.45	-	0.45	V
		I <sub>O</sub> = 12 mA; V <sub>CCO</sub> = 2.3 V		-	0.3	-	0.3	V
		I <sub>O</sub> = 24 mA; V <sub>CCO</sub> = 3.0 V		-	0.55	-	0.55	V
		I <sub>O</sub> = 32 mA; V <sub>CCO</sub> = 4.5 V		-	0.55	-	0.55	V
I	input leakage current	DIR input; V <sub>I</sub> = 0 V to 5.5 V; V <sub>CCI</sub> = 1.2 V to 5.5 V		-	±2	-	±10	μA
I <sub>BHL</sub>	bus hold LOW	A or B port	[1]					
	current	V <sub>I</sub> = 0.49 V; V <sub>CCI</sub> = 1.4 V		15	-	10	-	μA
		V <sub>I</sub> = 0.58 V; V <sub>CCI</sub> = 1.65 V		25	-	20	-	μA
		V <sub>I</sub> = 0.70 V; V <sub>CCI</sub> = 2.3 V		45	-	45	-	μA
		V <sub>I</sub> = 0.80 V; V <sub>CCI</sub> = 3.0 V		100	-	80	-	μA
		V <sub>I</sub> = 1.35 V; V <sub>CCI</sub> = 4.5 V		100	-	100	-	μA
внн	bus hold HIGH	A or B port	[1]					
	current	V <sub>I</sub> = 0.91 V; V <sub>CCI</sub> = 1.4 V		-15	-	-10	-	μA
		V <sub>I</sub> = 1.07 V; V <sub>CCI</sub> = 1.65 V		-25	-	-20	-	μA
		V <sub>I</sub> = 1.60 V; V <sub>CCI</sub> = 2.3 V		-45	-	-45	-	μA
		V <sub>I</sub> = 2.00 V; V <sub>CCI</sub> = 3.0 V		-100	-	-80	-	μA
		V <sub>I</sub> = 3.15 V; V <sub>CCI</sub> = 4.5 V		-100	_	-100	-	μA

### Dual supply translating transceiver; 3-state

Symbol	Parameter	Conditions	-40 °C t	o +85 °C	-40 °C to +125 °C		Unit
			Min	Max	Min	Мах	
BHLO	bus hold LOW	A or B port [1][3]					
	overdrive	V <sub>CCI</sub> = 1.6 V	125	-	125	-	μA
	current	V <sub>CCI</sub> = 1.95 V	200	-	200	-	μA
		V <sub>CCI</sub> = 2.7 V	300	-	300	-	μA
		V <sub>CCI</sub> = 3.6 V	500	-	500	-	μA
		V <sub>CCI</sub> = 5.5 V	900	-	900	-	μA
I <sub>BHHO</sub>	bus hold HIGH	A or B port [1][3]					
	overdrive	V <sub>CCI</sub> = 1.6 V	-125	-	-125	-	μA
	current	V <sub>CCI</sub> = 1.95 V	-200	-	-200	-	μA
		V <sub>CCI</sub> = 2.7 V	-300	-	-300	_	μA
		V <sub>CCI</sub> = 3.6 V	-500	-	-500	-	μA
		V <sub>CCI</sub> = 5.5 V	-900	-	-900	_	μA
I <sub>OZ</sub>	OFF-state output current	A or B port; $V_0 = 0$ V or $V_{CCO}$ ; [2] $V_{CCO} = 1.2$ V to 5.5 V	-	±2	-	±10	μA
OFF power-off leakage current	A port; V <sub>1</sub> or V <sub>0</sub> = 0 V to 5.5 V; V <sub>CC(A)</sub> = 0 V; V <sub>CC(B)</sub> = 1.2 V to 5.5 V	-	±2	-	±10	μA	
		B port; $V_1$ or $V_0 = 0$ V to 5.5 V; $V_{CC(B)} = 0$ V; $V_{CC(A)} = 1.2$ V to 5.5 V	-	±2	-	±10	μA
I <sub>CC</sub>	supply current	A port; $V_1 = 0 V \text{ or } V_{CCI}$ ; $I_0 = 0 A$ [1]					
		$V_{CC(A)}$ , $V_{CC(B)}$ = 1.2 V to 5.5 V	-	8	-	8	μA
		$V_{CC(A)}$ , $V_{CC(B)}$ = 1.65 V to 5.5 V	-	3	-	3	μA
		V <sub>CC(A)</sub> = 5.5 V; V <sub>CC(B)</sub> = 0 V	-	2	-	2	μA
		V <sub>CC(A)</sub> = 0 V; V <sub>CC(B)</sub> = 5.5 V	-2	-	-2	-	μA
		B port; $V_I = 0 V$ or $V_{CCI}$ ; $I_O = 0 A$					
		V <sub>CC(A)</sub> , V <sub>CC(B)</sub> = 1.2 V to 5.5 V	-	8	-	8	μA
		V <sub>CC(A)</sub> , V <sub>CC(B)</sub> = 1.65 V to 5.5 V	-	3	-	3	μA
		V <sub>CC(B)</sub> = 0 V; V <sub>CC(A)</sub> = 5.5 V	-2	-	-2	-	μA
		V <sub>CC(B)</sub> = 5.5 V; V <sub>CC(A)</sub> = 0 V	-	2	-	2	μA
		A plus B port ( $I_{CC(A)} + I_{CC(B)}$ ); $I_O = 0 A$ ; $V_I = 0 V \text{ or } V_{CCI}$					
		V <sub>CC(A)</sub> , V <sub>CC(B)</sub> = 1.2 V to 5.5 V	-	16	-	16	μA
		V <sub>CC(A)</sub> , V <sub>CC(B)</sub> = 1.65 V to 5.5 V	-	4	-	4	μA
ΔI <sub>CC</sub>	additional supply current	per input; V <sub>CC(A)</sub> , V <sub>CC(B)</sub> = 3.0 V to 5.5 V					
		A port; A port at $V_{CC(A)}$ - 0.6 V; [4] DIR at $V_{CC(A)}$ ; B port = open	-	50	-	75	μA
		DIR input; DIR at $V_{CC(A)}$ - 0.6 V; A port at $V_{CC(A)}$ or GND; B port = open	-	50	-	75	μA
		B port; B port at V <sub>CC(B)</sub> - 0.6 V; [4] DIR at GND; A port = open	-	50	-	75	μA

 $V_{\text{CCI}}$  is the supply voltage associated with the data input port. [1]

 $V_{CCO}$  is the supply voltage associated with the output port. To guarantee the node switches, an external driver must source/sink at least  $I_{BHLO}/I_{BHHO}$  when the input is in the range  $V_{IL}$  to  $V_{IH}$ . [2] [3]

[4] For non bus hold parts only (74LVC2T45).

# **11. Dynamic characteristics**

Symbol	Parameter	Conditions		V <sub>CC(B)</sub>					
			1.2 V	1.5 V	1.8 V	2.5 V	3.3 V	5.0 V	
t <sub>PLH</sub>	LOW to HIGH	A to B	10.6	8.1	7.0	5.8	5.3	5.1	ns
l	propagation delay	B to A	10.6	9.5	9.0	8.5	8.3	8.2	ns
t <sub>PHL</sub>	HIGH to LOW propagation delay	A to B	10.1	7.1	6.0	5.3	5.2	5.4	ns
		B to A	10.1	8.6	8.1	7.8	7.6	7.6	ns
t <sub>PHZ</sub>	HIGH to OFF-state	DIR to A	9.4	9.4	9.4	9.4	9.4	9.4	ns
	propagation delay	DIR to B	12.0	9.4	9.0	7.8	8.4	7.9	ns
t <sub>PLZ</sub>	LOW to OFF-state	DIR to A	7.1	7.1	7.1	7.1	7.1	7.1	ns
	propagation delay	DIR to B	9.5	7.8	7.7	6.9	7.6	7.0	ns
t <sub>PZH</sub>	OFF-state to HIGH	DIR to A [1]	20.1	17.3	16.7	15.4	15.9	15.2	ns
	propagation delay	DIR to B [1]	17.7	15.2	14.1	12.9	12.4	12.2	ns
t <sub>PZL</sub>	OFF-state to LOW	DIR to A [1]	22.1	18.0	17.1	15.6	16.0	15.5	ns
	propagation delay	DIR to B [1]	19.5	16.5	15.4	14.7	14.6	14.8	ns

Table 9. Typical dynamic characteristics at  $V_{CC(A)} = 1.2 \text{ V}$  and  $T_{amb} = 25 \text{ °C}$ Voltages are referenced to GND (ground = 0 V); for test circuit see Fig. 8; for waveforms see Fig. 6 and Fig. 7

[1]  $t_{PZH}$  and  $t_{PZL}$  are calculated values using the formula shown in <u>Section 13.4</u>.

#### Table 10. Typical dynamic characteristics at $V_{CC(B)}$ = 1.2 V and $T_{amb}$ = 25 $^{\circ}C$

Voltages are referenced to GND (ground = 0 V); for test circuit see Fig. 8; for waveforms see Fig. 6 and Fig. 7.

Symbol	Parameter	Conditions			Vc	C(A)			Unit
			1.2 V	1.5 V	1.8 V	2.5 V	3.3 V	5.0 V	
t <sub>PLH</sub>	LOW to HIGH	A to B	10.6	9.5	9.0	8.5	8.3	8.2	ns
	propagation delay	B to A	10.6	8.1	7.0	5.8	5.3	5.1	ns
t <sub>PHL</sub>	HIGH to LOW	A to B	10.1	8.6	8.1	7.8	7.6	7.6	ns
	propagation delay	B to A	10.1	7.1	6.0	5.3	5.2	5.4	ns
t <sub>PHZ</sub>	HIGH to OFF-state propagation delay	DIR to A	9.4	6.5	5.7	4.1	4.1	3.0	ns
		DIR to B	12.0	6.1	5.4	4.6	4.3	4.0	ns
t <sub>PLZ</sub>	LOW to OFF-state	DIR to A	7.1	4.9	4.5	3.2	3.4	2.5	ns
	propagation delay	DIR to B	9.5	7.3	6.6	5.9	5.7	5.6	ns
t <sub>PZH</sub>	OFF-state to HIGH	DIR to A [1]	20.1	15.4	13.6	11.7	11.0	10.7	ns
	propagation delay	DIR to B [1]	17.7	14.4	13.5	11.7	11.7	10.7	ns
t <sub>PZL</sub>	OFF-state to LOW	DIR to A [1]	22.1	13.2	11.4	9.9	9.5	9.4	ns
	propagation delay	DIR to B [1]	19.5	15.1	13.8	11.9	11.7	10.6	ns

[1]  $t_{PZH}$  and  $t_{PZL}$  are calculated values using the formula shown in <u>Section 13.4</u>.

#### Dual supply translating transceiver; 3-state

#### Table 11. Typical power dissipation capacitance at $V_{CC(A)}$ = $V_{CC(B)}$ and $T_{amb}$ = 25 $^{\circ}C$

Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions		V <sub>CC(A)</sub> ar	nd V <sub>CC(B)</sub>		Unit
			1.8 V	2.5 V	3.3 V	5.0 V	
C <sub>PD</sub>	power dissipation capacitance[1] [2]	A port: (direction A to B); B port: (direction B to A)	2	3	3	4	pF
		A port: (direction A to B); B port: (direction B to A)	15	16	16	18	pF

[1]  $C_{PD}$  is used to determine the dynamic power dissipation (P<sub>D</sub> in  $\mu$ W).

 $P_D = C_{PD} \times V_{CC}^2 \times f_i \times N + \Sigma (C_L \times V_{CC}^2 \times f_o)$  where:

f<sub>i</sub> = input frequency in MHz;

 $f_o = output frequency in MHz;$ 

C<sub>L</sub> = load capacitance in pF;

V<sub>CC</sub> = supply voltage in V;

N = number of inputs switching;

 $\Sigma(C_L \times V_{CC}^2 \times f_0)$  = sum of the outputs.

[2]  $f_i = 10 \text{ MHz}$ ;  $V_I = \text{GND}$  to  $V_{CC}$ ;  $t_r = t_f = 1 \text{ ns}$ ;  $C_L = 0 \text{ pF}$ ;  $R_L = \infty \Omega$ .

#### Table 12. Dynamic characteristics for temperature range -40 °C to +85 °C

Voltages are referenced to GND (ground = 0 V); for test circuit see Fig. 8; for waveforms see Fig. 6 and Fig. 7.

Symbol	Parameter	Conditions					Vcc	(B)					Unit
			1.5 V :	± 0.1 V	1.8 V ±	: 0.15 V	2.5 V :	± 0.2 V	3.3 V :	± 0.3 V	5.0 V ±	± 0.5 V	
			Min	Max	Min	Max	Min	Max	Min	Max	Min	Мах	
V <sub>CC(A)</sub> =	1.4 V to 1.6 V		1										
t <sub>PLH</sub>	LOW to HIGH	A to B	2.8	21.3	2.4	17.6	2.0	13.5	1.7	11.8	1.6	10.5	ns
	propagation delay	B to A	2.8	21.3	2.6	19.1	2.3	14.9	2.3	12.4	2.2	12.0	ns
t <sub>PHL</sub>	HIGH to LOW	A to B	2.6	19.3	2.2	15.3	1.8	11.8	1.7	10.9	1.7	10.8	ns
	propagation delay	B to A	2.6	19.3	2.4	17.3	2.3	13.2	2.2	11.3	2.3	11.0	ns
t <sub>PHZ</sub>	HIGH to OFF-state	DIR to A	3.0	18.7	3.0	18.7	3.0	18.7	3.0	18.7	3.0	18.7	ns
	propagation delay	DIR to B	3.5	24.8	3.5	23.6	3.0	11.0	3.3	11.3	2.8	10.3	ns
t <sub>PLZ</sub>	LOW to OFF-state	DIR to A	2.4	11.4	2.4	11.4	2.4	11.4	2.4	11.4	2.4	11.4	ns
	propagation delay	DIR to B	2.8	18.3	3.0	17.2	2.5	9.4	3.0	10.1	2.5	9.4	ns
t <sub>PZH</sub>	OFF-state to HIGH	DIR to A [1]	-	39.6	-	36.3	-	24.3	-	22.5	-	21.4	ns
	propagation delay	DIR to B [1]	-	32.7	-	29.0	-	24.9	-	23.2	-	21.9	ns
t <sub>PZL</sub>	OFF-state to LOW	DIR to A [1]	-	44.1	-	40.9	-	24.2	-	22.6	-	21.3	ns
	propagation delay	DIR to B [1]	-	38.0	-	34.0	-	30.5	-	29.6	-	29.5	ns

### Dual supply translating transceiver; 3-state

Symbol	Parameter	Conditions					Vcc	;(В)					Unit
			1.5 V :	± 0.1 V	1.8 V ±	: 0.15 V	2.5 V :	± 0.2 V	3.3 V :	± 0.3 V	5.0 V :	± 0.5 V	
			Min	Max	Min	Max	Min	Max	Min	Max	Min	Max	
V <sub>CC(A)</sub> =	1.65 V to 1.95 V												
t <sub>PLH</sub>	LOW to HIGH	A to B	2.6	19.1	2.2	17.7	2.2	9.3	1.7	7.2	1.4	6.8	ns
	propagation delay	B to A	2.4	17.6	2.2	17.7	2.3	16.0	2.1	15.5	1.9	15.1	ns
t <sub>PHL</sub>	HIGH to LOW	A to B	2.4	17.3	2.0	14.3	1.6	8.5	1.8	7.1	1.7	7.0	ns
	propagation delay	B to A	2.2	15.3	2.0	14.3	2.1	12.9	2.0	12.6	1.8	12.2	ns
t <sub>PHZ</sub>	HIGH to OFF-state	DIR to A	2.9	17.1	2.9	17.1	2.9	17.1	2.9	17.1	2.9	17.1	ns
	propagation delay	DIR to B	3.2	24.1	3.2	21.9	2.7	11.5	3.0	10.3	2.5	8.2	ns
t <sub>PLZ</sub>	LOW to OFF-state	DIR to A	2.4	10.5	2.4	10.5	2.4	10.5	2.4	10.5	2.4	10.5	ns
	propagation delay	DIR to B	2.5	17.6	2.6	16.0	2.2	9.2	2.7	8.4	2.4	7.1	ns
t <sub>PZH</sub>	OFF-state to HIGH	DIR to A [1]	-	35.2	-	33.7	-	25.2	-	23.9	-	22.2	ns
	propagation delay	DIR to B [1]	-	29.6	-	28.2	-	19.8	-	17.7	-	17.3	ns
t <sub>PZL</sub>	OFF-state to LOW	DIR to A [1]	-	39.4	-	36.2	-	24.4	-	22.9	-	20.4	ns
	propagation delay	DIR to B [1]	-	34.4	-	31.4	-	25.6	-	24.2	-	24.1	ns
V <sub>CC(A)</sub> =	2.3 V to 2.7 V												
t <sub>PLH</sub>	LOW to HIGH	A to B	2.3	17.9	2.3	16.0	1.5	8.5	1.3	6.2	1.1	4.8	ns
	propagation delay	B to A	2.0	13.5	2.2	9.3	1.5	8.5	1.4	8.0	1.0	7.5	ns
t <sub>PHL</sub>	HIGH to LOW	A to B	2.3	15.8	2.1	12.9	1.4	7.5	1.3	5.4	0.9	4.6	ns
	propagation delay	B to A	1.8	11.8	1.9	8.5	1.4	7.5	1.3	7.0	0.9	6.2	ns
t <sub>PHZ</sub>	HIGH to OFF-state	DIR to A	2.1	8.1	2.1	8.1	2.1	8.1	2.1	8.1	2.1	8.1	ns
	propagation delay	DIR to B	3.0	22.5	3.0	21.4	2.5	11.0	2.8	9.3	2.3	6.9	ns
t <sub>PLZ</sub>	LOW to OFF-state	DIR to A	1.7	5.8	1.7	5.8	1.7	5.8	1.7	5.8	1.7	5.8	ns
	propagation delay	DIR to B	2.3	14.6	2.5	13.2	2.0	9.0	2.5	8.4	1.8	5.8	ns
t <sub>PZH</sub>	OFF-state to HIGH	DIR to A [1]	-	28.1	-	22.5	-	17.5	-	16.4	-	13.3	ns
	propagation delay	DIR to B [1]	-	23.7	-	21.8	-	14.3	-	12.0	-	10.6	ns
t <sub>PZL</sub>	OFF-state to LOW	DIR to A [1]	-	34.3	-	29.9	-	18.5	-	16.3	-	13.1	ns
	propagation delay	DIR to B [1]	-	23.9	-	21.0	-	15.6	-	13.5	-	12.7	ns
$V_{CC(A)} =$	3.0 V to 3.6 V												
t <sub>PLH</sub>	LOW to HIGH	A to B	2.3	17.1	2.1	15.5	1.4	8.0	0.8	5.6	0.7	4.4	ns
	propagation delay	B to A	1.7	11.8	1.7	7.2	1.3	6.2	0.7	5.6	0.6	5.4	ns
t <sub>PHL</sub>	HIGH to LOW	A to B	2.2	15.6	2.0	12.6	1.3	7.0	0.8	5.0	0.7	4.0	ns
	propagation delay	B to A	1.7	10.9	1.8	7.1	1.3	5.4	0.8	5.0	0.7	4.5	ns
t <sub>PHZ</sub>	HIGH to OFF-state	DIR to A	2.3	7.3	2.3	7.3	2.3	7.3	2.3	7.3	2.7	7.3	ns
	propagation delay	DIR to B	2.9	18.0	2.9	16.5	2.3	10.1	2.7	8.6	2.2	6.3	ns
t <sub>PLZ</sub>	LOW to OFF-state	DIR to A	2.0	5.6	2.0	5.6	2.0	5.6	2.0	5.6	2.0	5.6	ns
	propagation delay	DIR to B	2.3	13.6	2.4	12.5	1.9	7.8	2.3	7.1	1.7	4.9	ns
t <sub>PZH</sub>	OFF-state to HIGH	DIR to A [1]	-	25.4	-	19.7	-	14.0	-	12.7	-	10.3	ns
	propagation delay	DIR to B [1]	-	22.7	-	21.1	-	13.6	-	11.2	-	10.0	ns
t <sub>PZL</sub>	OFF-state to LOW	DIR to A [1]	-	28.9	-	23.6	-	15.5	-	13.6	-	10.8	ns
	propagation delay	DIR to B [1]	-	22.9	-	19.9	-	14.3	-	12.3	-	11.3	ns

#### Dual supply translating transceiver; 3-state

Symbol	Parameter	Conditions					Vcc	:(В)					Unit
			1.5 V :	± 0.1 V	1.8 V ±	0.15 V	2.5 V :	± 0.2 V	3.3 V :	± 0.3 V	5.0 V ±	± 0.5 V	
			Min	Max	Min	Мах	Min	Max	Min	Max	Min	Max	
V <sub>CC(A)</sub> =	4.5 V to 5.5 V								1				
t <sub>PLH</sub>	LOW to HIGH	A to B	2.2	16.6	1.9	15.1	1.0	7.5	0.7	5.4	0.5	3.9	ns
	propagation delay	B to A	1.6	10.5	1.4	6.8	1.0	4.8	0.7	4.4	0.5	3.9	ns
t <sub>PHL</sub>	HIGH to LOW	A to B	2.3	15.3	1.8	12.2	1.0	6.2	0.7	4.5	0.5	3.5	ns
	propagation delay	B to A	1.7	10.8	1.7	7.0	0.9	4.6	0.7	4.0	0.5	3.5	ns
t <sub>PHZ</sub>	HIGH to OFF-state	DIR to A	1.7	5.4	1.7	5.4	1.7	5.4	1.7	5.4	1.7	5.4	ns
	propagation delay	DIR to B	2.9	17.3	2.9	16.1	2.3	9.7	2.7	8.0	2.5	5.7	ns
t <sub>PLZ</sub>	LOW to OFF-state	DIR to A	1.4	3.7	1.4	3.7	1.3	3.7	1.0	3.7	0.9	3.7	ns
	propagation delay	DIR to B	2.3	13.1	2.4	12.1	1.9	7.4	2.3	7.0	1.8	4.5	ns
t <sub>PZH</sub>	OFF-state to HIGH	DIR to A [1]	-	23.6	-	18.9	-	12.2	-	11.4	-	8.4	ns
	propagation delay	DIR to B [1]	-	20.3	-	18.8	-	11.2	-	9.1	-	7.6	ns
t <sub>PZL</sub>	OFF-state to LOW	DIR to A [1]	-	28.1	-	23.1	-	14.3	-	12.0	-	9.2	ns
	propagation delay	DIR to B [1]	-	20.7	-	17.6	-	11.6	-	9.9	-	8.9	ns

[1]  $t_{PZH}$  and  $t_{PZL}$  are calculated values using the formula shown in <u>Section 13.4</u>.

#### Table 13. Dynamic characteristics for temperature range -40 °C to +125 °C

Voltages are referenced to GND (ground = 0 V); for test circuit see  $\underline{Fig. 8}$ ; for waveforms see  $\underline{Fig. 6}$  and  $\underline{Fig. 7}$ .

Symbol	Parameter	Conditions					Vcc	(B)					Unit
			1.5 V :	± 0.1 V	1.8 V ±	0.15 V	2.5 V :	± 0.2 V	3.3 V :	± 0.3 V	5.0 V :	± 0.5 V	
			Min	Max	Min	Max	Min	Max	Min	Max	Min	Max	
V <sub>CC(A)</sub> =	1.4 V to 1.6 V	I						1	1				
t <sub>PLH</sub>	LOW to HIGH	A to B	2.5	23.5	2.1	19.4	1.8	14.9	1.5	13.0	1.4	11.6	ns
	propagation delay	B to A	2.5	23.5	2.3	21.1	2.0	16.4	2.0	13.7	1.9	13.2	ns
t <sub>PHL</sub>	HIGH to LOW	A to B	2.3	21.3	1.9	16.9	1.6	13.0	1.5	12.0	1.5	11.9	ns
	propagation delay	B to A	2.3	21.3	2.1	19.1	2.0	14.6	1.9	12.5	2.0	12.1	ns
t <sub>PHZ</sub>	HIGH to OFF-state	DIR to A	2.7	20.6	2.7	20.6	2.7	20.6	2.7	20.6	2.7	20.6	ns
	propagation delay	DIR to B	3.1	27.3	3.1	26.0	2.7	12.1	2.9	12.5	2.5	11.4	ns
t <sub>PLZ</sub>	LOW to OFF-state	DIR to A	2.1	12.6	2.1	12.6	2.1	12.6	2.1	12.6	2.1	12.6	ns
	propagation delay	DIR to B	2.5	20.2	2.7	19.0	2.2	10.4	2.7	11.2	2.2	10.4	ns
t <sub>PZH</sub>	OFF-state to HIGH	DIR to A [1]	-	43.7	-	40.1	-	26.8	-	24.9	-	23.6	ns
	propagation delay	DIR to B [1]	-	36.1	-	32.0	-	27.5	-	25.6	-	24.2	ns
t <sub>PZL</sub>	OFF-state to LOW	DIR to A [1]	-	48.6	-	45.1	-	26.7	-	25.0	-	23.5	ns
	propagation delay	DIR to B [1]	-	41.9	-	37.5	-	33.6	-	32.6	-	32.5	ns

### Dual supply translating transceiver; 3-state

Symbol	Parameter	Conditions					Vcc	(В)					Unit
			1.5 V :	± 0.1 V	1.8 V ±	: 0.15 V	2.5 V :	± 0.2 V	3.3 V :	± 0.3 V	5.0 V :	± 0.5 V	1
			Min	Max	Min	Max	Min	Max	Min	Max	Min	Max	
V <sub>CC(A)</sub> =	1.65 V to 1.95 V			1	1	1				1		1	
t <sub>PLH</sub>	LOW to HIGH	A to B	2.3	21.1	1.9	19.5	1.9	10.3	1.5	8.0	1.2	7.5	ns
	propagation delay	B to A	2.1	19.4	1.9	19.5	2.0	17.6	1.8	17.1	1.7	16.7	ns
t <sub>PHL</sub>	HIGH to LOW	A to B	2.1	19.1	1.8	15.8	1.4	9.4	1.6	7.9	1.5	7.7	ns
	propagation delay	B to A	1.9	16.9	1.8	15.8	1.8	14.2	1.8	13.9	1.6	13.5	ns
t <sub>PHZ</sub>	HIGH to OFF-state	DIR to A	2.6	18.9	2.6	18.9	2.6	18.9	2.6	18.9	2.6	18.9	ns
	propagation delay	DIR to B	2.8	26.6	2.8	24.1	2.4	12.7	2.7	11.4	2.2	9.1	ns
t <sub>PLZ</sub>	LOW to OFF-state	DIR to A	2.1	11.6	2.1	11.6	2.1	11.6	2.1	11.6	2.1	11.6	ns
	propagation delay	DIR to B	2.2	19.4	2.3	17.6	1.9	10.2	2.4	9.3	2.1	7.9	ns
t <sub>PZH</sub>	OFF-state to HIGH	DIR to A [1]	-	38.8	-	37.1	-	27.8	-	26.4	-	24.6	ns
	propagation delay	DIR to B [1]	-	32.7	-	31.1	-	21.9	-	19.6	-	19.1	ns
t <sub>PZL</sub>	OFF-state to LOW	DIR to A [1]	-	43.5	-	39.9	-	26.9	-	25.3	-	22.6	ns
	propagation delay	DIR to B [1]	-	38.0	-	34.7	-	28.3	-	26.8	-	26.6	ns
V <sub>CC(A)</sub> =	2.3 V to 2.7 V												
t <sub>PLH</sub>	LOW to HIGH	A to B	2.0	19.7	2.0	17.6	1.3	9.4	1.1	6.9	0.9	5.3	ns
	propagation delay	B to A	1.8	14.9	1.9	10.3	1.3	9.4	1.2	8.8	0.9	8.3	ns
t <sub>PHL</sub>	HIGH to LOW	A to B	2.0	17.4	1.8	14.2	1.2	8.3	1.1	6.0	0.8	5.1	ns
	propagation delay	B to A	1.6	13.0	1.7	9.4	1.2	8.3	1.1	7.7	0.8	6.9	ns
t <sub>PHZ</sub>	HIGH to OFF-state	DIR to A	1.8	9.0	1.8	9.0	1.8	9.0	1.8	9.0	1.8	9.0	ns
	propagation delay	DIR to B	2.7	24.8	2.7	23.6	2.2	12.1	2.5	10.3	2.0	7.6	ns
t <sub>PLZ</sub>	LOW to OFF-state	DIR to A	1.5	6.4	1.5	6.4	1.5	6.4	1.5	6.4	1.5	6.4	ns
	propagation delay	DIR to B	2.0	16.1	2.2	14.6	1.8	9.9	2.2	9.3	1.6	6.4	ns
t <sub>PZH</sub>	OFF-state to HIGH	DIR to A [1]	-	31.0	-	24.9	-	19.3	-	18.1	-	14.7	ns
	propagation delay	DIR to B [1]	-	26.1	-	24.0	-	15.8	-	13.3	-	11.7	ns
t <sub>PZL</sub>	OFF-state to LOW	DIR to A [1]	-	37.8	-	33.0	-	20.4	-	18.0	-	14.5	ns
	propagation delay	DIR to B [1]	-	26.4	-	23.2	-	17.3	-	15.0	-	14.1	ns
V <sub>CC(A)</sub> =	3.0 V to 3.6 V												
t <sub>PLH</sub>	LOW to HIGH	A to B	2.0	18.9	1.8	17.1	1.2	8.8	0.7	6.2	0.6	4.9	ns
	propagation delay	B to A	1.5	13.0	1.5	8.0	1.1	6.9	0.6	6.2	0.5	6.0	ns
t <sub>PHL</sub>	HIGH to LOW	A to B	1.9	17.2	1.8	13.9	1.1	7.7	0.7	5.5	0.6	4.4	ns
	propagation delay	B to A	1.5	12.0	1.6	7.9	1.1	6.0	0.7	5.5	0.6	5.0	ns
t <sub>PHZ</sub>	HIGH to OFF-state	DIR to A	2.0	8.1	2.0	8.1	2.0	8.1	2.0	8.1	2.4	8.1	ns
	propagation delay	DIR to B	2.6	19.8	2.6	18.2	2.0	11.2	2.4	9.5	1.9	7.0	ns
t <sub>PLZ</sub>	LOW to OFF-state	DIR to A	1.8	6.2	1.8	6.2	1.8	6.2	1.8	6.2	1.8	6.2	ns
	propagation delay	DIR to B	2.0	15.0	2.1	13.8	1.7	8.6	2.0	7.9	1.5	5.4	ns
t <sub>PZH</sub>	OFF-state to HIGH	DIR to A [1]	-	28.0	-	21.8	-	15.5	-	14.1	-	11.4	ns
	propagation delay	DIR to B [1]	-	25.1	-	23.3	-	15.0	-	12.4	-	11.1	ns
t <sub>PZL</sub>	OFF-state to LOW	DIR to A [1]	-	31.8	-	26.1	-	17.2	-	15.0	-	12.0	ns
	propagation delay	DIR to B [1]	-	25.3	-	22.0	-	15.8	-	13.6	-	12.5	ns

#### Dual supply translating transceiver; 3-state


Symbol	Parameter	Conditions					Vcc	;(B)					Unit
			1.5 V :	± 0.1 V	1.8 V ±	0.15 V	2.5 V :	± 0.2 V	3.3 V :	± 0.3 V	5.0 V ±	± 0.5 V	
			Min	Max	Min	Мах	Min	Max	Min	Max	Min	Мах	
V <sub>CC(A)</sub> =	4.5 V to 5.5 V												
t <sub>PLH</sub>	LOW to HIGH	A to B	1.9	18.3	1.7	16.7	0.9	8.3	0.6	6.0	0.4	4.3	ns
	propagation delay	B to A	1.4	11.6	1.2	7.5	0.9	5.3	0.6	4.9	0.4	4.3	ns
t <sub>PHL</sub>	HIGH to LOW	A to B	2.0	16.9	1.6	13.5	0.9	6.9	0.6	5.0	0.4	3.9	ns
	propagation delay	B to A	1.5	11.9	1.5	7.7	0.8	5.1	0.6	4.4	0.4	3.9	ns
t <sub>PHZ</sub>	HIGH to OFF-state	DIR to A	1.5	6.0	1.5	6.0	1.5	6.0	1.5	6.0	1.5	6.0	ns
	propagation delay	DIR to B	2.6	19.1	2.6	17.8	2.0	10.7	2.4	8.8	2.2	6.3	ns
t <sub>PLZ</sub>	LOW to OFF-state	DIR to A	1.2	4.1	1.2	4.1	1.1	4.1	0.9	4.1	0.8	4.1	ns
	propagation delay	DIR to B	2.0	14.5	2.1	13.4	1.7	8.2	2.0	7.7	1.6	5.0	ns
t <sub>PZH</sub>	OFF-state to HIGH	DIR to A [1]	-	26.1	-	20.9	-	13.5	-	12.6	-	9.3	ns
	propagation delay	DIR to B [1]	-	22.4	-	20.8	-	12.4	-	10.1	-	8.4	ns
t <sub>PZL</sub>	OFF-state to LOW	DIR to A [1]	-	31.0	-	25.5	-	15.8	-	13.2	-	10.2	ns
	propagation delay	DIR to B [1]	-	22.9	-	19.5	-	12.9	-	11.0	-	9.9	ns

[1]  $t_{PZH}$  and  $t_{PZL}$  are calculated values using the formula shown in <u>Section 13.4</u>.

74LVC\_LVCH2T45

#### Dual supply translating transceiver; 3-state

### 11.1. Waveforms and test circuit




### Table 14. Measurement points

Supply voltage	Input [1]	Output [2]		
V <sub>CC(A)</sub> , V <sub>CC(B)</sub>	V <sub>M</sub>	V <sub>M</sub>	V <sub>X</sub>	V <sub>Y</sub>
1.2 V to 1.6 V	0.5V <sub>CCI</sub>	0.5V <sub>CCO</sub>	V <sub>OL</sub> + 0.1 V	V <sub>OH</sub> - 0.1 V
1.65 V to 2.7 V	0.5V <sub>CCI</sub>	0.5V <sub>CCO</sub>	V <sub>OL</sub> + 0.15 V	V <sub>OH</sub> - 0.15 V
3.0 V to 5.5 V	0.5V <sub>CCI</sub>	0.5V <sub>CCO</sub>	V <sub>OL</sub> + 0.3 V	V <sub>OH</sub> - 0.3 V

[1]  $V_{CCI}$  is the supply voltage associated with the data input port.

[2]  $V_{CCO}$  is the supply voltage associated with the output port.

#### Dual supply translating transceiver; 3-state



### Table 15. Test data

Supply voltage	Input		Load	Load		V <sub>EXT</sub>			
$V_{CC(A)}, V_{CC(B)}$	V <sub>I</sub> [1]	Δt/ΔV [2]	CL	RL	t <sub>PLH</sub> , t <sub>PHL</sub>	t <sub>PZH</sub> , t <sub>PHZ</sub>	t <sub>PZL</sub> , t <sub>PLZ</sub> [3]		
1.2 V to 5.5 V	V <sub>CCI</sub>	≤ 1.0 ns/V	15 pF	2 kΩ	open	GND	2V <sub>CCO</sub>		


[1]  $V_{CCI}$  is the supply voltage associated with the data input port.

[2] dV/dt ≥ 1.0 V/ns.

[3]  $V_{CCO}$  is the supply voltage associated with the output port.

74LVC\_LVCH2T45


#### Dual supply translating transceiver; 3-state




# 12. Typical propagation delay characteristics

74LVC\_LVCH2T45

#### Dual supply translating transceiver; 3-state




#### Dual supply translating transceiver; 3-state



**Product data sheet** 


#### Dual supply translating transceiver; 3-state



74LVC\_LVCH2T45


20 / 34

#### Dual supply translating transceiver; 3-state



74LVC\_LVCH2T45

#### Dual supply translating transceiver; 3-state



# **13. Application information**

#### 13.1. Unidirectional logic level-shifting application

The circuit given in <u>Fig. 15</u> is an example of the 74LVC2T45; 74LVCH2T45 being used in a unidirectional logic level-shifting application.





Fig. 15. Unidirectional logic level-shifting application

Table 16. Descriptio	n of unidirectional	loaic level-shifting	application
			approation

Pin	Name	Function	Description
1	V <sub>CC(A)</sub>	V <sub>CC1</sub>	supply voltage of system-1 (1.2 V to 5.5 V)
2	1A	OUT	output level depends on $V_{CC1}$ voltage
3	2A	OUT	output level depends on $V_{CC1}$ voltage
4	GND	GND	device GND
5	DIR	DIR	the GND (LOW level) determines B port to A port direction
6	2B	IN	input threshold value depends on $V_{CC2}$ voltage
7	1B	IN	input threshold value depends on $V_{\text{CC2}}$ voltage
8	V <sub>CC(B)</sub>	V <sub>CC2</sub>	supply voltage of system-2 (1.2 V to 5.5 V)

### 13.2. Bidirectional logic level-shifting application

Fig. 16 shows the 74LVC2T45; 74LVCH2T45 being used in a bidirectional logic level-shifting application. Since the device does not have an output enable pin, the system designer should take precautions to avoid bus contention between system-1 and system-2 when changing directions.



<u>Table 17</u> gives a sequence that will illustrate data transmission from system-1 to system-2 and then from system-2 to system-1.

#### Table 17. Description of bidirectional logic level-shifting application

- H = HIGH voltage level;
- L = LOW voltage level;

Z = high-impedance OFF-state.

State	DIR CTRL	I/O-1	I/O-2	Description
1	Н	output	input	system-1 data to system-2
2	Н	Z	Z	system-2 is getting ready to send data to system-1. I/O-1 and I/O-2 are disabled. The bus-line state depends on bus hold
3	L	Z	Z	DIR bit is set LOW. I/O-1 and I/O-2 still are disabled. The bus-line state depends on bus hold
4	L	input	output	system-2 data to system-1

#### 13.3. Power-up considerations

The device is designed such that no special power-up sequence is required other than GND being applied first.

Table 18.	<b>Typicaltotal</b>	supply current	$(I_{CC(A)} +$	· I <sub>CC(B)</sub> )
-----------	---------------------	----------------	----------------	------------------------

V <sub>CC(A)</sub>	V <sub>CC(B)</sub>	V <sub>CC(B)</sub>					
	0 V	1.8 V	2.5 V	3.3 V	5.0 V		
0 V	0	< 1	< 1	< 1	< 1	μA	
1.8 V	< 1	< 2	< 2	< 2	2	μA	
2.5 V	< 1	< 2	< 2	< 2	< 2	μA	
3.3 V	< 1	< 2	< 2	< 2	< 2	μA	
5.0 V	< 1	2	< 2	< 2	< 2	μA	

#### 13.4. Enable times


Calculate the enable times for the 74LVC2T45; 74LVCH2T45 using the following formulas:

- $t_{PZH}$  (DIR to A) =  $t_{PLZ}$  (DIR to B) +  $t_{PLH}$  (B to A)
- t<sub>PZL</sub> (DIR to A) = t<sub>PHZ</sub> (DIR to B) + t<sub>PHL</sub> (B to A)
- $t_{PZH}$  (DIR to B) =  $t_{PLZ}$  (DIR to A) +  $t_{PLH}$  (A to B)
- $t_{PZL}$  (DIR to B) =  $t_{PHZ}$  (DIR to A) +  $t_{PHL}$  (A to B)

In a bidirectional application, these enable times provide the maximum delay from the time the DIR bit is switched until an output is expected. For example, if the 74LVC2T45; 74LVCH2T45 initially is transmitting from A to B, then the DIR bit is switched, the B port of the device must be disabled before presenting it with an input. After the B port has been disabled, an input signal applied to it appears on the corresponding A port after the specified propagation delay.

#### Dual supply translating transceiver; 3-state

# 14. Package outline





74LVC\_LVCH2T45

#### Dual supply translating transceiver; 3-state





Fig. 18. Package outline SOT833-1 (XSON8)


#### Dual supply translating transceiver; 3-state



# XSON8: extremely thin small outline package; no leads;

Fig. 19. Package outline SOT1089 (XSON8)

#### Dual supply translating transceiver; 3-state




XQFN8: plastic, extremely thin quad flat package; no leads;

Fig. 20. Package outline SOT902-2 (XQFN8)

#### Dual supply translating transceiver; 3-state

#### XSON8: extremely thin small outline package; no leads; 8 terminals; body 1.2 x 1.0 x 0.35 mm





#### Dual supply translating transceiver; 3-state

#### XSON8: extremely thin small outline package; no leads; 8 terminals; body 1.35 x 1.0 x 0.35 mm SOT1203 b (4×)<sup>(2)</sup> 4 2 3 е 8 6 e<sub>1</sub>e<sub>1</sub> e<sub>1</sub> $(8 \times)^{(2)}$ А С С ٦ D E terminal 1 index area 0.5 1 mm 0 1 1 . scale Dimensions Unit A<sup>(1)</sup> A<sub>1</sub> b D Е L е e<sub>1</sub> $L_1$ 0.35 0.04 0.20 1.40 1.05 0.35 0.40 max 0.15 1.00 $0.55 \quad 0.35 \quad 0.30 \quad 0.35$ mm nom 1.35 min 0.12 1.30 0.95 0.27 0.32 Note 1. Including plating thickness. 2. Visible depending upon used manufacturing technology. sot1203\_po References Outline European Issue date version projection IEC JEDEC JEITA 10-04-02 SOT1203 $\blacksquare$ 10-04-06

Fig. 22. Package outline SOT1203 (XSON8)

# **15. Abbreviations**

Table 19. Abbreviati		
Acronym	Description	
CDM	Charged Device Model	
DUT	Device Under Test	
ESD	ElectroStatic Discharge	
HBM	Human Body Model	
MM	Machine Model	

### 16. Revision history

#### Table 20. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes	
74LVC_LVCH2T45 v.9	20180813	Product data sheet	-	74LVC_LVCH2T45 v.8	
Modifications:	of Nexperia <ul> <li>Legal texts</li> <li>Type number</li> </ul>	<ul> <li>The format of this data sheet has been redesigned to comply with the identity guidelines of Nexperia.</li> <li>Legal texts have been adapted to the new company name where appropriate.</li> <li>Type numbers 74LVC2T45GD and 74LVCH2T45GD (SOT996-2) removed.</li> <li>Package outline drawing (SOT765-1) modified.</li> </ul>			
74LVC_LVCH2T45 v.8	20130329	Product data sheet	-	74LVC_LVCH2T45 v.7	
Modifications:	<ul> <li>For type numbers 74LVC2T45GD and 74LVCH2T45GD XSON8U has changed to XSON8.</li> </ul>				
74LVC_LVCH2T45 v.7	20120619	Product data sheet	-	74LVC_LVCH2T45 v.6	
Modifications:	For type null SOT902-2.	mbers 74LVC2T45GM ar	nd 74LVCH2T45GM	the SOT code has changed to	
74LVC_LVCH2T45 v.6	20111209	Product data sheet	-	74LVC_LVCH2T45 v.5	
Modifications:	Legal pages	updated.			
74LVC_LVCH2T45 v.5	20110927	Product data sheet	-	74LVC_LVCH2T45 v.4	
74LVC_LVCH2T45 v.4	20100820	Product data sheet	-	74LVC_LVCH2T45 v.3	
74LVC_LVCH2T45 v.3	20100119	Product data sheet	-	74LVC_LVCH2T45 v.2	
74LVC_LVCH2T45 v.2	20090205	Product data sheet	-	74LVC_LVCH2T45 v.1	
74LVC_LVCH2T45 v.1	20081118	Product data sheet	-	-	

# 17. Legal information

#### Data sheet status

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

 Please consult the most recently issued document before initiating or completing a design.

- [2] The term 'short data sheet' is explained in section "Definitions".
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at <u>https://www.nexperia.com</u>.

#### **Definitions**

**Draft** — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

**Product specification** — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

#### **Disclaimers**

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

**Right to make changes** — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal

#### Dual supply translating transceiver; 3-state

injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <u>http://www.nexperia.com/profile/terms</u>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

**Translations** — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

#### **Trademarks**

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

### Contents

1. General description	1
2. Features and benefits	1
3. Ordering information	2
4. Marking	2
5. Functional diagram	3
6. Pinning information	3
6.1. Pinning	3
6.2. Pin description	4
7. Functional description	4
8. Limiting values	5
9. Recommended operating conditions	5
10. Static characteristics	6
11. Dynamic characteristics	9
11.1. Waveforms and test circuit	15
12. Typical propagation delay characteristics	17
13. Application information	23
13.1. Unidirectional logic level-shifting application	23
13.2. Bidirectional logic level-shifting application	24
13.3. Power-up considerations	24
13.4. Enable times	25
14. Package outline	26
15. Abbreviations	32
16. Revision history	32
17. Legal information	33

© Nexperia B.V. 2018. All rights reserved

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com Date of release: 13 August 2018