

ISL21010

Micropower Voltage Reference

FN7896

Rev 4.00

February 12, 2016

The [ISL21010](#) is a precision, low dropout micropower bandgap voltage reference in a space-saving SOT-23 package. It operates from a single 2.2V to 5.5V supply (minimum voltage is dependent on voltage option) and provides a $\pm 0.2\%$ accurate reference. The ISL21010 provides up to 25mA output current sourcing with low 150mV dropout voltage.

Output voltage options include 1.024V, 1.2V, 1.5V, 2.048V, 2.5V, 3.0V, 3.3V and 4.096V. The low supply current and low dropout voltage combined with high accuracy make the ISL21010 ideal for precision battery powered applications.

Applications

- Battery management/monitoring
- Low power standby voltages
- Portable instrumentation
- Consumer/medical electronics
- Lower cost industrial and instrumentation
- Power regulation circuits
- Control loops and compensation networks
- LED/diode supply

Features

- Reference output voltages 1.024V, 1.25V, 1.5V, 2.048V, 2.5V, 3.0V, 3.3V, 4.096V
- Precision 0.2% initial accuracy
- Input voltage range:
 - ISL21010-10, -12, -15 -20 2.2V to 5.5V
 - ISL21010-25 2.6V to 5.5V
 - ISL21010-30 3.1V to 5.5V
 - ISL21010-33 3.4V to 5.5V
 - ISL21010-41 4.2V to 5.5V
- Output current source capability 25mA
- Operating temperature range -40°C to +125°C
- Output voltage noise ($V_{OUT} = 2.048V$) 58 μ V_{P-P} (0.1Hz to 10Hz)
- Supply current 48 μ A (typ)
- Tempco 50ppm/°C
- Package 3 Ld SOT-23
- Pb-free (RoHS compliant)

Related Literature

[AN1819](#), "ISL21010XXEV1Z User Guide"

[AN1883](#), "Low-Side Low Cost Current Sense Amplifier"





FIGURE 1. TYPICAL APPLICATION DIAGRAM

Table of Contents

Pin Configuration.....	3
Pin Descriptions.....	3
Ordering Information	3
Absolute Maximum Ratings.....	4
Thermal Information	4
Recommended Operating Conditions	4
Electrical Specifications (ISL21010-10, V_{OUT} = 1.024V)	4
Electrical Specifications (ISL21010-12, V_{OUT} = 1.25V)	5
Electrical Specifications (ISL21010-15, V_{OUT} = 1.5V).....	5
Electrical Specifications (ISL21010-20, V_{OUT} = 2.048V)	6
Electrical Specifications (ISL21010-25, V_{OUT} = 2.5V).....	6
Electrical Specifications (ISL21010-30, V_{OUT} = 3.0V)	7
Electrical Specifications (ISL21010-33, V_{OUT} = 3.3V)	7
Electrical Specifications (ISL21010-41, V_{OUT} = 4.096V)	8
Typical Performance Characteristics Curves (V_{OUT} = 1.024V).....	9
Typical Performance Characteristics Curves (V_{OUT} = 1.25V)	12
Typical Performance Characteristics Curves (V_{OUT} = 1.5V)	15
Typical Performance Characteristics Curves (V_{OUT} = 2.048V)	18
Typical Performance Characteristics Curves (V_{OUT} = 2.5V)	21
Typical Performance Characteristics Curves (V_{OUT} = 3.0V)	24
Typical Performance Characteristics Curves (V_{OUT} = 3.3V)	27
Typical Performance Characteristics Curves (V_{OUT} = 4.096V)	30
Applications Information	33
Micropower Operation.....	33
Board Mounting Considerations	33
Board Assembly Considerations	33
Noise Performance and Reduction	33
Typical Application Circuit	33
Revision History.....	34
About Intersil	34
Package Outline Drawing.....	35

Pin Configuration



Pin Descriptions

PIN NUMBER	PIN NAME	DESCRIPTION
1	V _{IN}	Input Voltage Connection
2	V _{OUT}	Voltage Reference Output
3	GND	Ground Connection

Ordering Information

PART NUMBER <small>(Notes 1, 2, 3, 4)</small>	PART MARKING	TAPE & REEL QUANTITY (UNITS)	V _{OUT} OPTION (V)	INITIAL ACCURACY (%)	TEMP. RANGE (°C)	PACKAGE (RoHS Compliant)	PKG. DWG. #
ISL21010DFH310Z-TK	BEBA	1k	1.024	±0.2	-40 to +125	3 Ld SOT-23	P3.064
ISL21010DFH310Z-T7A	BEBA	250	1.024	±0.2	-40 to +125	3 Ld SOT-23	P3.064
ISL21010DFH312Z-TK	BECA	1k	1.25	±0.2	-40 to +125	3 Ld SOT-23	P3.064
ISL21010DFH312Z-T7A	BECA	250	1.25	±0.2	-40 to +125	3 Ld SOT-23	P3.064
ISL21010CFH315Z-TK	BDRA	1k	1.5	±0.2	-40 to +125	3 Ld SOT-23	P3.064
ISL21010CFH315Z-T7A	BDRA	250	1.5	±0.2	-40 to +125	3 Ld SOT-23	P3.064
ISL21010CFH320Z-TK	BDSA	1k	2.048	±0.2	-40 to +125	3 Ld SOT-23	P3.064
ISL21010CFH320Z-T7A	BDSA	250	2.048	±0.2	-40 to +125	3 Ld SOT-23	P3.064
ISL21010CFH325Z-TK	BDTA	1k	2.5	±0.2	-40 to +125	3 Ld SOT-23	P3.064
ISL21010CFH325Z-T7A	BDTA	250	2.5	±0.2	-40 to +125	3 Ld SOT-23	P3.064
ISL21010CFH330Z-TK	BDVA	1k	3.0	±0.2	-40 to +125	3 Ld SOT-23	P3.064
ISL21010CFH330Z-T7A	BDVA	250	3.0	±0.2	-40 to +125	3 Ld SOT-23	P3.064
ISL21010CFH333Z-TK	BDWA	1k	3.3	±0.2	-40 to +125	3 Ld SOT-23	P3.064
ISL21010CFH333Z-T7A	BDWA	250	3.3	±0.2	-40 to +125	3 Ld SOT-23	P3.064
ISL21010CFH341Z-TK	BDYA	1k	4.096	±0.2	-40 to +125	3 Ld SOT-23	P3.064
ISL21010CFH341Z-T7A	BDYA	250	4.096	±0.2	-40 to +125	3 Ld SOT-23	P3.064

NOTES:

1. Please refer to [TB347](#) for details on reel specifications.
2. These Intersil Pb-free plastic packaged products employ special Pb-free material sets, molding compounds/die attach materials, and 100% matte tin plate plus anneal (e3 termination finish, which is RoHS compliant and compatible with both SnPb and Pb-free soldering operations). Intersil Pb-free products are MSL classified at Pb-free peak reflow temperatures that meet or exceed the Pb-free requirements of IPC/JEDEC J STD-020.
3. For Moisture Sensitivity Level (MSL), please see device information page for [ISL21010](#). For more information on MSL please see Tech Brief [TB363](#).
4. The part marking is located on the bottom of the part.

Absolute Maximum Ratings

Max Voltage	
V_{IN} to GND	-0.5V to +6.5V
V_{OUT} (pin) to GND (10s).....	-0.5V to V_{IN} +0.5V
Input Voltage Slew Rate (Max).....	.1V/ μ s
Temperature Range (Industrial)	-40°C to +125°C
ESD Rating	
Human Body Model	5.5kV
Machine Model	300V
Charged Device Model.....	2kV

Thermal Information

Thermal Resistance (Typical)	θ_{JA} (°C/W)	θ_{JC} (°C/W)
3 Ld SOT-23 Package (Notes 5, 6).....	275	110
Continuous Power Dissipation ($T_A = +125^\circ C$)99mW	
Storage Temperature Range.....	-65°C to +150°C	
Pb-Free Reflow Profile		see TB493

Recommended Operating Conditions

Temperature	-40°C to +125°C
Supply Voltage	
$V_{OUT} = 1.024V, 1.25V, 1.5V, 2.048V$	2.2V to 5.5V
$V_{OUT} = 2.5V$	2.6V to 5.5V
$V_{OUT} = 3.0V$	3.1V to 5.5V
$V_{OUT} = 3.3V$	3.4V to 5.5V
$V_{OUT} = 4.096V$	4.2V to 5.5V

CAUTION: Do not operate at or near the maximum ratings listed for extended periods of time. Exposure to such conditions may adversely impact product reliability and result in failures not covered by warranty.

NOTES:

5. θ_{JA} is measured with the component mounted on a high effective thermal conductivity test board in free air. See Tech Brief [TB379](#) for details.
6. For θ_{JC} , the “case temp” location is taken at the package top center.
7. Post-reflow drift for the ISL21010 devices may shift up to 4.0mV based on simulated reflow at 260°C peak temperature, three passes. The system design engineer must take this into account when considering the reference voltage after assembly.

Electrical Specifications (ISL21010-10, $V_{OUT} = 1.024V$) $V_{IN} = 3.0V$, $T_A = +25^\circ C$, $I_{OUT} = 0A$, unless otherwise specified. Boldface limits apply across the operating temperature range, -40°C to +125°C.

PARAMETER	DESCRIPTION	TEST CONDITIONS	MIN (Note 8)	TYP	MAX (Note 8)	UNIT
V_{OUT}	Output Voltage		1.024			V
V_{OA}	V_{OUT} Accuracy at $T_A = +25^\circ C$ (Note 7)		-0.2		+0.2	%
TC V_{OUT}	Output Voltage Temperature Coefficient (Note 9)			15	50	ppm/°C
V_{IN}	Input Voltage Range		2.2		5.5	V
I_{IN}	Supply Current	$T_A = +25^\circ C$		46	80	μA
		$T_A = -40^\circ C$ to +125°C		60	100	μA
$\Delta V_{OUT}/\Delta V_{IN}$	Line Regulation	$2.2V \leq V_{IN} \leq 5.5V$		5	100	μV/V
$\Delta V_{OUT}/\Delta I_{OUT}$	Load Regulation	Sourcing: $0mA \leq I_{OUT} \leq 25mA$		15	110	μV/mA
		Sinking: $-1mA \leq I_{OUT} \leq 0mA$		17		μV/mA
I_{SC}	Short-Circuit Current	$T_A = +25^\circ C$, V_{OUT} tied to GND		118		mA
t_R	Turn-On Settling Time	$V_{OUT} = \pm 0.1\%$, $C_{OUT} = 1\mu F$	300			μs
	Ripple Rejection	$f = 120Hz$		70		dB
e_N	Output Voltage Noise	$0.1Hz \leq f \leq 10Hz$		24		μV _{P-P}
V_N	Broadband Voltage Noise	$10Hz \leq f \leq 1kHz$		14		μV _{RMS}
$\Delta V_{OUT}/\Delta T_A$	Thermal Hysteresis (Note 11)	$\Delta T_A = +165^\circ C$		100		ppm
$\Delta V_{OUT}/\Delta t$	Long Term Stability	1000 hours, $T_A = +25^\circ C$		110		ppm

Electrical Specifications (ISL21010-12, V_{OUT} = 1.25V) V_{IN} = 3.0V, T_A = +25°C, I_{OUT} = 0A, unless otherwise specified.
Boldface limits apply across the operating temperature range, -40°C to +125°C.

PARAMETER	DESCRIPTION	TEST CONDITIONS	MIN (Note 8)	TYP	MAX (Note 8)	UNIT
V _{OUT}	Output Voltage		1.25		V	
V _{OA}	V _{OUT} Accuracy at T _A = +25°C (Note 7)		-0.2		+0.2	%
TC V _{OUT}	Output Voltage Temperature Coefficient (Note 9)		15	50	ppm/°C	
V _{IN}	Input Voltage Range		2.2		5.5	V
I _{IN}	Supply Current	T _A = +25°C		46	80	µA
		T _A = -40°C to +125°C			100	µA
ΔV _{OUT} /ΔV _{IN}	Line Regulation	2.2 V ≤ V _{IN} ≤ 5.5V		1	100	µV/V
ΔV _{OUT} /ΔI _{OUT}	Load Regulation	Sourcing: 0mA ≤ I _{OUT} ≤ 25mA		35	110	µV/mA
		Sinking: -1mA ≤ I _{OUT} ≤ 0mA		50		µV/mA
I _{SC}	Short-Circuit Current	T _A = +25°C, V _{OUT} tied to GND		118		mA
t _R	Turn-On Settling Time	V _{OUT} = ±0.1%, C _{OUT} = 1µF		300		µs
	Ripple Rejection	f = 120Hz		68		dB
e _N	Output Voltage Noise	0.1Hz ≤ f ≤ 10Hz		27		µV _{P-P}
V _N	Broadband Voltage Noise	10Hz ≤ f ≤ 1kHz		17		µV _{RMS}
ΔV _{OUT} /ΔT _A	Thermal Hysteresis (Note 11)	ΔT _A = +165°C		100		ppm
ΔV _{OUT} /Δt	Long Term Stability	1000 hours, T _A = +25°C		110		ppm

Electrical Specifications (ISL21010-15, V_{OUT} = 1.5V) V_{IN} = 3.0V, T_A = +25°C, I_{OUT} = 0A, unless otherwise specified.
Boldface limits apply across the operating temperature range, -40°C to +125°C.

PARAMETER	DESCRIPTION	TEST CONDITIONS	MIN (Note 8)	TYP	MAX (Note 8)	UNIT
V _{OUT}	Output Voltage		1.5		V	
V _{OA}	V _{OUT} Accuracy at T _A = +25°C (Note 7)		-0.2		+0.2	%
TC V _{OUT}	Output Voltage Temperature Coefficient (Note 9)		15	50	ppm/°C	
V _{IN}	Input Voltage Range		2.2		5.5	V
I _{IN}	Supply Current	T _A = +25°C		46	80	µA
		T _A = -40°C to +125°C			100	µA
ΔV _{OUT} /ΔV _{IN}	Line Regulation	2.2 V ≤ V _{IN} ≤ 5.5V		9	100	µV/V
ΔV _{OUT} /ΔI _{OUT}	Load Regulation	Sourcing: 0mA ≤ I _{OUT} ≤ 25mA		37	110	µV/mA
		Sinking: -1mA ≤ I _{OUT} ≤ 0mA		50		µV/mA
I _{SC}	Short-Circuit Current	T _A = +25°C, V _{OUT} tied to GND		118		mA
t _R	Turn-On Settling Time	V _{OUT} = ±0.1%, C _{OUT} = 1µF		300		µs
	Ripple Rejection	f = 120Hz		66		dB
e _N	Output Voltage Noise	0.1Hz ≤ f ≤ 10Hz		35		µV _{P-P}
V _N	Broadband Voltage Noise	10Hz ≤ f ≤ 1kHz		20		µV _{RMS}
ΔV _{OUT} /ΔT _A	Thermal Hysteresis (Note 11)	ΔT _A = +165°C		100		ppm
ΔV _{OUT} /Δt	Long Term Stability	1000 hours, T _A = +25°C		110		ppm

Electrical Specifications (ISL21010-20, V_{OUT} = 2.048V) V_{IN} = 3.0V, T_A = +25°C, I_{OUT} = 0A, unless otherwise specified. Boldface limits apply across the operating temperature range, -40°C to +125°C.

PARAMETER	DESCRIPTION	TEST CONDITIONS	MIN (Note 8)	TYP	MAX (Note 8)	UNIT
V _{OUT}	Output Voltage			2.048		V
V _{OA}	V _{OUT} Accuracy at T _A = +25°C (Note 7)		-0.2		+0.2	%
TC V _{OUT}	Output Voltage Temperature Coefficient (Note 9)			15	50	ppm/°C
V _{IN}	Input Voltage Range		2.2		5.5	V
I _{IN}	Supply Current	T _A = +25°C		46	80	µA
		T _A = -40°C to +125°C			100	µA
ΔV _{OUT} /ΔV _{IN}	Line Regulation	2.2 V ≤ V _{IN} ≤ 5.5V		37	130	µV/V
ΔV _{OUT} /ΔI _{OUT}	Load Regulation	Sourcing: 0mA ≤ I _{OUT} ≤ 25mA		18	110	µV/mA
		Sinking: -1mA ≤ I _{OUT} ≤ 0mA		10		µV/mA
I _{SC}	Short-Circuit Current	T _A = +25°C, V _{OUT} tied to GND		118		mA
t _R	Turn-On Settling Time	V _{OUT} = ±0.1%, C _{OUT} = 1µF	300			µs
	Ripple Rejection	f = 120Hz	66			dB
e _N	Output Voltage Noise	0.1Hz ≤ f ≤ 10Hz	58			µV _{P-P}
V _N	Broadband Voltage Noise	10Hz ≤ f ≤ 1kHz	26			µV _{RMS}
ΔV _{OUT} /ΔT _A	Thermal Hysteresis (Note 11)	ΔT _A = +165°C	100			ppm
ΔV _{OUT} /Δt	Long Term Stability	1000 hours, T _A = +25°C	50			ppm

Electrical Specifications (ISL21010-25, V_{OUT} = 2.5V) V_{IN} = 3.0V, T_A = +25°C, I_{OUT} = 0A, unless otherwise specified. Boldface limits apply across the operating temperature range, -40°C to +125°C.

PARAMETER	DESCRIPTION	TEST CONDITIONS	MIN (Note 8)	TYP	MAX (Note 8)	UNIT
V _{OUT}	Output Voltage			2.5		V
V _{OA}	V _{OUT} Accuracy at T _A = +25°C (Note 7)		-0.2		+0.2	%
TC V _{OUT}	Output Voltage Temperature Coefficient (Note 9)			15	50	ppm/°C
V _{IN}	Input Voltage Range		2.6		5.5	V
I _{IN}	Supply Current	T _A = +25°C		46	80	µA
		T _A = -40°C to +125°C			100	µA
ΔV _{OUT} /ΔV _{IN}	Line Regulation	2.6 V ≤ V _{IN} ≤ 5.5V	62	245	µV/V	
ΔV _{OUT} /ΔI _{OUT}	Load Regulation	Sourcing: 0mA ≤ I _{OUT} ≤ 25mA	29	110	µV/mA	
		Sinking: -1mA ≤ I _{OUT} ≤ 0mA	50			µV/mA
V _{INDO}	Dropout Voltage (Note 10)	I _{OUT} = 10mA	60	150	mV	
I _{SC}	Short-Circuit Current	T _A = +25°C, V _{OUT} tied to GND	118			mA
t _R	Turn-On Settling Time	V _{OUT} = ±0.1%, C _{OUT} = 1µF	300			µs
	Ripple Rejection	f = 120Hz	62			dB
e _N	Output Voltage Noise	0.1Hz ≤ f ≤ 10Hz	67			µV _{P-P}
V _N	Broadband Voltage Noise	10Hz ≤ f ≤ 1kHz	37			µV _{RMS}
ΔV _{OUT} /ΔT _A	Thermal Hysteresis (Note 11)	ΔT _A = +165°C	100			ppm
ΔV _{OUT} /Δt	Long Term Stability	1000 hours, T _A = +25°C	110			ppm

Electrical Specifications (ISL21010-30, V_{OUT} = 3.0V) V_{IN} = 5.0V, T_A = +25°C, I_{OUT} = 0A, unless otherwise specified.
Boldface limits apply across the operating temperature range, -40°C to +125°C.

PARAMETER	DESCRIPTION	TEST CONDITIONS	MIN (Note 8)	TYP	MAX (Note 8)	UNIT
V _{OUT}	Output Voltage			3.0		V
V _{OA}	V _{OUT} Accuracy at T _A = +25°C (Note 7)		-0.2		+0.2	%
TC V _{OUT}	Output Voltage Temperature Coefficient (Note 9)			15	50	ppm/°C
V _{IN}	Input Voltage Range		3.1		5.5	V
I _{IN}	Supply Current	T _A = +25°C		48	80	µA
		T _A = -40°C to +125°C			100	µA
ΔV _{OUT} /ΔV _{IN}	Line Regulation	3.1 V ≤ V _{IN} ≤ 5.5V		73	230	µV/V
ΔV _{OUT} /ΔI _{OUT}	Load Regulation	Sourcing: 0mA ≤ I _{OUT} ≤ 25mA		48	110	µV/mA
		Sinking: -1mA ≤ I _{OUT} ≤ 0mA		10		µV/mA
V _{INDO}	Dropout Voltage (Note 10)	I _{OUT} = 10mA		60	150	mV
I _{SC}	Short-Circuit Current	T _A = +25°C, V _{OUT} tied to GND		126		mA
t _R	Turn-On Settling Time	V _{OUT} = ±0.1%, C _{OUT} = 1µF		300		µs
	Ripple Rejection	f = 120Hz		62		dB
e _N	Output Voltage Noise	0.1Hz ≤ f ≤ 10Hz		86		µV _{P-P}
V _N	Broadband Voltage Noise	10Hz ≤ f ≤ 1kHz		36		µV _{RMS}
ΔV _{OUT} /ΔT _A	Thermal Hysteresis (Note 11)	ΔT _A = +165°C		100		ppm
ΔV _{OUT} /Δt	Long Term Stability	1000 hours, T _A = +25°C		50		ppm

Electrical Specifications (ISL21010-33, V_{OUT} = 3.3V) V_{IN} = 5.0V, T_A = +25°C, I_{OUT} = 0A, unless otherwise specified.
Boldface limits apply across the operating temperature range, -40°C to +125°C.

PARAMETER	DESCRIPTION	TEST CONDITIONS	MIN (Note 8)	TYP	MAX (Note 8)	UNIT
V _{OUT}	Output Voltage			3.3		V
V _{OA}	V _{OUT} Accuracy at T _A = +25°C (Note 7)		-0.2		+0.2	%
TC V _{OUT}	Output Voltage Temperature Coefficient (Note 9)			15	50	ppm/°C
V _{IN}	Input Voltage Range		3.4		5.5	V
I _{IN}	Supply Current	T _A = +25°C		48	80	µA
		T _A = -40°C to +125°C			100	µA
ΔV _{OUT} /ΔV _{IN}	Line Regulation	3.4 V ≤ V _{IN} ≤ 5.5V		80	320	µV/V
ΔV _{OUT} /ΔI _{OUT}	Load Regulation	Sourcing: 0mA ≤ I _{OUT} ≤ 25mA		45	110	µV/mA
		Sinking: -1mA ≤ I _{OUT} ≤ 0mA		10		µV/mA
V _{INDO}	Dropout Voltage (Note 10)	I _{OUT} = 10mA		60	150	mV
I _{SC}	Short-Circuit Current	T _A = +25°C, V _{OUT} tied to GND		126		mA
t _R	Turn-On Settling Time	V _{OUT} = ±0.1%, C _{OUT} = 1µF		300		µs
	Ripple Rejection	f = 120Hz		61		dB
e _N	Output Voltage Noise	0.1Hz ≤ f ≤ 10Hz		95		µV _{P-P}
V _N	Broadband Voltage Noise	10Hz ≤ f ≤ 1kHz		40		µV _{RMS}
ΔV _{OUT} /ΔT _A	Thermal Hysteresis (Note 11)	ΔT _A = +165°C		100		ppm
ΔV _{OUT} /Δt	Long Term Stability	1000 hours, T _A = +25°C		50		ppm

Electrical Specifications (ISL21010-41, V_{OUT} = 4.096V) V_{IN} = 5.0V, T_A = +25°C, I_{OUT} = 0A, unless otherwise specified. Boldface limits apply across the operating temperature range, -40°C to +125°C.

PARAMETER	DESCRIPTION	TEST CONDITIONS	MIN (Note 8)	TYP	MAX (Note 8)	UNIT
V _{OUT}	Output Voltage		4.096			V
V _{OA}	V _{OUT} Accuracy at T _A = +25°C (Note 7)		-0.2		+0.2	%
TC V _{OUT}	Output Voltage Temperature Coefficient (Note 9)			15	50	ppm/°C
V _{IN}	Input Voltage Range			4.2	5.5	V
I _{IN}	Supply Current	T _A = +25°C		48	80	µA
		T _A = -40°C to +125°C			100	µA
ΔV _{OUT} /ΔV _{IN}	Line Regulation	4.2 V ≤ V _{IN} ≤ 5.5V		106	550	µV/V
ΔV _{OUT} /ΔI _{OUT}	Load Regulation	Sourcing: 0mA ≤ I _{OUT} ≤ 25mA		50	140	µV/mA
		Sinking: -1mA ≤ I _{OUT} ≤ 0mA		50		µV/mA
V _{INDO}	Dropout Voltage (Note 10)	I _{OUT} = 10mA		60	150	mV
I _{SC}	Short-Circuit Current	T _A = +25°C, V _{OUT} tied to GND		126		mA
t _R	Turn-On Settling Time	V _{OUT} = ±0.1%, C _{OUT} = 1µF		300		µs
	Ripple Rejection	f = 120Hz		58		dB
e _N	Output Voltage Noise	0.1Hz ≤ f ≤ 10Hz		112		µV _{P-P}
V _N	Broadband Voltage Noise	10Hz ≤ f ≤ 1kHz		56		µV _{RMS}
ΔV _{OUT} /ΔT _A	Thermal Hysteresis (Note 11)	ΔT _A = +165°C		100		ppm
ΔV _{OUT} /Δt	Long Term Stability	1000 hours, T _A = +25°C		110		ppm

NOTES:

8. Compliance to datasheet limits is assured by one or more methods: production test, characterization and/or design.
9. Over the specified temperature range. Temperature coefficient is measured by the box method whereby the change in V_{OUT} is divided by the temperature range; in this case, -40°C to +125°C = +165°C.
10. Dropout Voltage is the minimum V_{IN} - V_{OUT} differential voltage measured at the point where V_{OUT} drops 1mV from V_{IN} = nominal at T_A = +25°C.
11. Thermal Hysteresis is the change of V_{OUT} measured at T_A = +25°C after temperature cycling over a specified range, ΔT_A. V_{OUT} is read initially at T_A = +25°C for the device under test. The device is temperature cycled and a second V_{OUT} measurement is taken at +25°C. The difference between the initial V_{OUT} reading and the second V_{OUT} reading is then expressed in ppm. For ΔT_A = +165°C, the device under test is cycled from +25°C to -40°C to +125°C to +25°C.

Typical Performance Characteristics Curves ($V_{OUT} = 1.024V$)

$I_{OUT} = 0mA$, $T_A = +25^\circ C$ unless otherwise specified.




FIGURE 2. I_{IN} VS V_{IN} , THREE UNITSFIGURE 3. I_{IN} VS V_{IN} , OVER-TEMPERATURE

FIGURE 4. LINE REGULATION, THREE UNITS






FIGURE 5. LINE REGULATION OVER-TEMPERATURE

FIGURE 6. LINE TRANSIENT RESPONSE WITH $0.22\mu F$ LOADFIGURE 7. LINE TRANSIENT RESPONSE WITH $10\mu F$ LOAD

Typical Performance Characteristics Curves ($V_{OUT} = 1.024V$) $V_{IN} = 3.0V$,

$I_{OUT} = 0mA$, $T_A = +25^\circ C$ unless otherwise specified. (Continued)




FIGURE 8. LOAD REGULATION OVER-TEMPERATURE




FIGURE 9. LOAD TRANSIENT RESPONSE AT 25mA LOAD AT $1\mu F$ FIGURE 10. LOAD TRANSIENT RESPONSE AT 1mA LOAD AT $1\mu F$ 

FIGURE 11. TURN-ON TIME



FIGURE 12. Z_{OUT} VS FREQUENCY

FIGURE 13. RIPPLE REJECTION AT DIFFERENT CAPACITIVE LOADS

Typical Performance Characteristics Curves ($V_{OUT} = 1.024V$) $V_{IN} = 3.0V$, $I_{OUT} = 0mA$, $T_A = +25^\circ C$ unless otherwise specified. (Continued)




FIGURE 14. DROPOUT (10mA SOURCED LOAD)




FIGURE 15. DROPOUT ZOOMED (10mA SOURCED LOAD)




FIGURE 16. V_{OUT} VS TEMPERATURE

FIGURE 17. SHORT CIRCUIT TO GND

FIGURE 18. V_{OUT} VS NOISE, 0.1Hz TO 10Hz

Typical Performance Characteristics Curves ($V_{OUT} = 1.25V$)

$I_{OUT} = 0mA$, $T_A = +25^\circ C$ unless otherwise specified.




FIGURE 19. I_{IN} vs V_{IN} , THREE UNITS




FIGURE 20. I_{IN} vs V_{IN} , OVER-TEMPERATURE




FIGURE 21. LINE REGULATION, THREE UNITS




FIGURE 22. LINE REGULATION OVER-TEMPERATURE




FIGURE 23. LINE TRANSIENT RESPONSE WITH $0.1\mu F$ LOAD




FIGURE 24. LINE TRANSIENT RESPONSE WITH $10\mu F$ LOAD

Typical Performance Characteristics Curves ($V_{OUT} = 1.25V$)

$I_{OUT} = 0mA$, $T_A = +25^\circ C$ unless otherwise specified. (Continued)




FIGURE 25. LOAD REGULATION OVER-TEMPERATURE




FIGURE 26. LOAD TRANSIENT RESPONSE AT 25mA LOAD AT $1\mu F$




FIGURE 27. LOAD TRANSIENT RESPONSE AT 1mA LOAD AT $1\mu F$




FIGURE 28. TURN-ON TIME




FIGURE 29. Z_{OUT} VS FREQUENCY




FIGURE 30. RIPPLE REJECTION AT DIFFERENT CAPACITIVE LOADS

Typical Performance Characteristics Curves ($V_{OUT} = 1.25V$) $V_{IN} = 3.0V$,

$I_{OUT} = 0mA$, $T_A = +25^\circ C$ unless otherwise specified. (Continued)




FIGURE 31. DROPOUT (10mA SOURCED LOAD)




FIGURE 32. DROPOUT ZOOMED (10mA SOURCED LOAD)




FIGURE 33. V_{OUT} VS TEMPERATURE

FIGURE 34. SHORT-CIRCUIT TO GND

FIGURE 35. V_{OUT} VS NOISE, 0.1Hz TO 10Hz

Typical Performance Characteristics Curves ($V_{OUT} = 1.5V$)

$V_{IN} = 3.0V$, $I_{OUT} = 0mA$,
 $T_A = +25^\circ C$ unless otherwise specified.




FIGURE 36. I_{IN} vs V_{IN} , THREE UNITSFIGURE 37. I_{IN} vs V_{IN} , OVER-TEMPERATURE

FIGURE 38. LINE REGULATION, THREE UNITS






FIGURE 39. LINE REGULATION OVER-TEMPERATURE

FIGURE 40. LINE TRANSIENT RESPONSE WITH $0.1\mu F$ LOADFIGURE 41. LINE TRANSIENT RESPONSE WITH $10\mu F$ LOAD

Typical Performance Characteristics Curves ($V_{OUT} = 1.5V$) $V_{IN} = 3.0V$, $I_{OUT} = 0mA$, $T_A = +25^\circ C$ unless otherwise specified. (Continued)




FIGURE 42. LOAD REGULATION OVER-TEMPERATURE




FIGURE 43. LOAD TRANSIENT RESPONSE AT 25mA LOAD AT $1\mu F$ FIGURE 44. LOAD TRANSIENT RESPONSE AT 1mA LOAD AT $1\mu F$ 

FIGURE 45. TURN-ON TIME



FIGURE 46. Z_{OUT} VS FREQUENCY

FIGURE 47. RIPPLE REJECTION AT DIFFERENT CAPACITIVE LOADS

Typical Performance Characteristics Curves ($V_{OUT} = 1.5V$)

$V_{IN} = 3.0V$, $I_{OUT} = 0mA$,
 $T_A = +25^\circ C$ unless otherwise specified. (Continued)




FIGURE 48. DROPOUT (10mA SOURCED LOAD)




FIGURE 49. DROPOUT ZOOMED (10mA SOURCED LOAD)




FIGURE 50. V_{OUT} VS TEMPERATURE

FIGURE 51. SHORT-CIRCUIT TO GND

FIGURE 52. V_{OUT} VS NOISE, 0.1Hz TO 10Hz

Typical Performance Characteristics Curves ($V_{OUT} = 2.048V$)

$V_{IN} = 3.0V$,
 $I_{OUT} = 0mA$, $T_A = +25^\circ C$ unless otherwise specified.




FIGURE 53. I_{IN} vs V_{IN} , THREE UNITSFIGURE 54. I_{IN} vs V_{IN} , OVER-TEMPERATURE

FIGURE 55. LINE REGULATION, THREE UNITS






FIGURE 56. LINE REGULATION OVER-TEMPERATURE

FIGURE 57. LINE TRANSIENT RESPONSE WITH $0.1\mu F$ LOADFIGURE 58. LINE TRANSIENT RESPONSE WITH $10\mu F$ LOAD

Typical Performance Characteristics Curves ($V_{OUT} = 2.048V$) $V_{IN} = 3.0V$, $I_{OUT} = 0mA$, $T_A = +25^\circ C$ unless otherwise specified. (Continued)




FIGURE 59. LOAD REGULATION OVER-TEMPERATURE




FIGURE 60. LOAD TRANSIENT RESPONSE AT 25mA LOAD AT $1\mu F$ FIGURE 61. LOAD TRANSIENT RESPONSE AT 1mA LOAD AT $1\mu F$ 

FIGURE 62. TURN-ON TIME



FIGURE 63. Z_{OUT} vs FREQUENCY

FIGURE 64. RIPPLE REJECTION AT DIFFERENT CAPACITIVE LOADS

Typical Performance Characteristics Curves ($V_{OUT} = 2.048V$) $V_{IN} = 3.0V$, $I_{OUT} = 0mA$, $T_A = +25^\circ C$ unless otherwise specified. (Continued)




FIGURE 65. DROPOUT (10mA Sourced Load)




FIGURE 66. DROPOUT ZOOMED (10mA Sourced Load)




FIGURE 67. V_{OUT} vs TEMPERATURE

FIGURE 68. SHORT CIRCUIT TO GND

FIGURE 69. V_{OUT} vs NOISE, 0.1Hz TO 10Hz

Typical Performance Characteristics Curves ($V_{OUT} = 2.5V$)

$V_{IN} = 3.0V$, $I_{OUT} = 0mA$,
 $T_A = +25^\circ C$ unless otherwise specified.




FIGURE 70. I_{IN} vs V_{IN} , THREE UNITSFIGURE 71. I_{IN} vs V_{IN} , OVER-TEMPERATURE

FIGURE 72. LINE REGULATION, THREE UNITS






FIGURE 73. LINE REGULATION OVER-TEMPERATURE

FIGURE 74. LINE TRANSIENT RESPONSE WITH $0.1\mu F$ LOADFIGURE 75. LINE TRANSIENT RESPONSE WITH $10\mu F$ LOAD

Typical Performance Characteristics Curves ($V_{OUT} = 2.5V$)

$V_{IN} = 3.0V$, $I_{OUT} = 0mA$, $T_A = +25^\circ C$ unless otherwise specified. (Continued)




FIGURE 76. LOAD REGULATION OVER-TEMPERATURE




FIGURE 77. LOAD TRANSIENT RESPONSE AT 25mA LOAD AT 1μF




FIGURE 78. LOAD TRANSIENT RESPONSE AT 1mA LOAD AT 1μF




FIGURE 79. TURN-ON TIME



FIGURE 80. Z_{OUT} VS FREQUENCY

FIGURE 81. RIPPLE REJECTION AT DIFFERENT CAPACITIVE LOADS

Typical Performance Characteristics Curves ($V_{OUT} = 2.5V$)

$V_{IN} = 3.0V$, $I_{OUT} = 0mA$,
 $T_A = +25^\circ C$ unless otherwise specified. (Continued)




FIGURE 82. DROPOUT (10mA SOURCED LOAD)




FIGURE 83. DROPOUT ZOOMED (10mA SOURCED LOAD)




FIGURE 84. V_{OUT} VS TEMPERATURE

FIGURE 85. SHORT-CIRCUIT TO GND

FIGURE 86. V_{OUT} VS NOISE, 0.1Hz TO 10Hz

Typical Performance Characteristics Curves ($V_{OUT} = 3.0V$)

$V_{IN} = 5.0V$, $I_{OUT} = 0mA$,
 $T_A = +25^\circ C$ unless otherwise specified.




FIGURE 87. I_{IN} vs V_{IN} , THREE UNITSFIGURE 88. I_{IN} vs V_{IN} , OVER-TEMPERATURE

FIGURE 89. LINE REGULATION, THREE UNITS






FIGURE 90. LINE REGULATION OVER-TEMPERATURE

FIGURE 91. LINE TRANSIENT WITH $0.1\mu F$ LOADFIGURE 92. LINE TRANSIENT RESPONSE WITH $10\mu F$ LOAD

Typical Performance Characteristics Curves ($V_{OUT} = 3.0V$)

$V_{IN} = 5.0V$, $I_{OUT} = 0mA$,
 $T_A = +25^\circ C$ unless otherwise specified. (Continued)




FIGURE 93. LOAD REGULATION OVER-TEMPERATURE




FIGURE 94. LOAD TRANSIENT RESPONSE AT 25mA LOAD AT 1μF




FIGURE 95. LOAD TRANSIENT RESPONSE AT 1mA LOAD AT 1μF




FIGURE 96. TURN-ON TIME



FIGURE 97. Z_{OUT} VS FREQUENCY

FIGURE 98. RIPPLE REJECTION AT DIFFERENT CAPACITIVE LOADS

Typical Performance Characteristics Curves ($V_{OUT} = 3.0V$)

$V_{IN} = 5.0V$, $I_{OUT} = 0mA$,
 $T_A = +25^\circ C$ unless otherwise specified. (Continued)




FIGURE 99. DROPOUT (10mA Sourced Load)




FIGURE 100. DROPOUT ZOOMED (10mA Sourced Load)




FIGURE 101. V_{OUT} vs TEMPERATURE

FIGURE 102. SHORT-CIRCUIT TO GND

FIGURE 103. V_{OUT} vs NOISE, 0.1Hz TO 10Hz

Typical Performance Characteristics Curves ($V_{OUT} = 3.3V$)

$V_{IN} = 5.0V$, $I_{OUT} = 0mA$,
 $T_A = +25^\circ C$ unless otherwise specified.




FIGURE 104. I_{IN} vs V_{IN} , THREE UNITSFIGURE 105. I_{IN} vs V_{IN} , OVER-TEMPERATURE

FIGURE 106. LINE REGULATION, THREE UNITS






FIGURE 107. LINE REGULATION OVER-TEMPERATURE

FIGURE 108. LINE TRANSIENT WITH $0.1\mu F$ LOADFIGURE 109. LINE TRANSIENT RESPONSE WITH $10\mu F$ LOAD

Typical Performance Characteristics Curves ($V_{OUT} = 3.3V$)

$V_{IN} = 5.0V$, $I_{OUT} = 0mA$, $T_A = +25^\circ C$ unless otherwise specified. (Continued)




FIGURE 110. LOAD REGULATION OVER-TEMPERATURE




FIGURE 111. LOAD TRANSIENT RESPONSE AT 25mA LOAD AT 1μF




FIGURE 112. LOAD TRANSIENT RESPONSE AT 1mA LOAD AT 1μF




FIGURE 113. TURN-ON TIME



FIGURE 114. Z_{OUT} VS FREQUENCY

FIGURE 115. RIPPLE REJECTION AT DIFFERENT CAPACITIVE LOADS

Typical Performance Characteristics Curves ($V_{OUT} = 3.3V$)

$V_{IN} = 5.0V$, $I_{OUT} = 0mA$,
 $T_A = +25^\circ C$ unless otherwise specified. (Continued)




FIGURE 116. DROPOUT (10mA SOURCED LOAD)




FIGURE 117. DROPOUT ZOOMED (10mA SOURCED LOAD)




FIGURE 118. V_{OUT} VS TEMPERATURE

FIGURE 119. SHORT-CIRCUIT TO GND

FIGURE 120. V_{OUT} VS NOISE, 0.1Hz TO 10Hz

Typical Performance Characteristics Curves ($V_{OUT} = 4.096V$)

$I_{OUT} = 0mA$, $T_A = +25^\circ C$ unless otherwise specified.




FIGURE 121. I_{IN} vs V_{IN} , THREE UNITS




FIGURE 122. I_{IN} vs V_{IN} , OVER-TEMPERATURE




FIGURE 123. LINE REGULATION, THREE UNITS




FIGURE 124. LINE REGULATION OVER-TEMPERATURE




FIGURE 125. LINE TRANSIENT RESPONSE WITH $0.1\mu F$ LOAD




FIGURE 126. LINE TRANSIENT RESPONSE WITH $10\mu F$ LOAD

Typical Performance Characteristics Curves ($V_{OUT} = 4.096V$) $V_{IN} = 3.0V$, $I_{OUT} = 0mA$, $T_A = +25^\circ C$ unless otherwise specified. (Continued)




FIGURE 127. LOAD REGULATION OVER-TEMPERATURE




FIGURE 128. LOAD TRANSIENT RESPONSE AT 25mA LOAD AT $1\mu F$ FIGURE 129. LOAD TRANSIENT RESPONSE AT 1mA LOAD AT $1\mu F$ 

FIGURE 130. TURN-ON TIME



FIGURE 131. Z_{OUT} VS FREQUENCY

FIGURE 132. RIPPLE REJECTION AT DIFFERENT CAPACITIVE LOADS

Typical Performance Characteristics Curves ($V_{OUT} = 4.096V$) $V_{IN} = 3.0V$,

$I_{OUT} = 0mA$, $T_A = +25^\circ C$ unless otherwise specified. (Continued)




FIGURE 133. DROPOUT (10mA SOURCED LOAD)




FIGURE 134. DROPOUT ZOOMED (10mA SOURCED LOAD)




FIGURE 135. V_{OUT} VS TEMPERATURE

FIGURE 136. SHORT-CIRCUIT TO GND

FIGURE 137. V_{OUT} VS NOISE, 0.1Hz TO 10Hz

Applications Information

Micropower Operation

The ISL21010 consumes very low supply current due to the proprietary bandgap technology. Low noise performance is achieved using optimized biasing techniques. Supply current is typically $48\mu A$ and noise in the 0.1Hz to 10Hz bandwidth is $58\mu V_{P-P}$ to $100\mu V_{P-P}$ ($V_{OUT} = 2.048V$, 3.0V and 3.3V) benefiting precision, low noise portable applications such as handheld meters and instruments.

Data Converters in particular can utilize the ISL21010 as an external voltage reference. Low power DAC and ADC circuits will realize maximum resolution with lowest noise. The device maintains output voltage during conversion cycles with fast response, although it is helpful to add an output capacitor, typically $1\mu F$.

Board Mounting Considerations

For applications requiring the highest accuracy, board mounting location should be reviewed. The device uses a plastic SOIC package, which will subject the die to mild stresses when the Printed Circuit (PC) board is heated and cooled, slightly changing the shape. Placing the device in areas subject to slight twisting can cause degradation of the accuracy of the reference voltage

due to these die stresses. It is normally best to place the device near the edge of a board, or the shortest side, as the axis of bending is most limited at that location. Mounting the device in a cutout also minimizes flex. Obviously mounting the device on flexprint or extremely thin PC material will likewise cause loss of reference accuracy.

Board Assembly Considerations

Bandgap references provide high accuracy and low temperature drift but some PC board assembly precautions are necessary. Normal output voltage shifts of $100\mu V$ to $4mV$ can be expected with Pb-free reflow profiles or wave solder on multilayer FR4 PC boards. Precautions should be taken to avoid excessive heat or extended exposure to high reflow or wave solder temperatures, this may reduce device initial accuracy.

Noise Performance and Reduction

The recommended capacitive load range for the ISL21010 is from $0.1\mu F$ to $10.0\mu F$ ($0.22\mu F$ minimum required for 1.024V option) to ensure stability and best transient performance. Parallel $0.1\mu F$ ($0.22\mu F$ for 1.024V) and $10\mu F$ capacitors can be used to optimize performance as well. The noise specification stated in the Electrical Specification tables (starting on [page 4](#)) is for $0.1\mu F$ ($0.22\mu F$ for 1.024V option) capacitive load, and larger values will reduce the output noise level.

Typical Application Circuit




FIGURE 138. KELVIN SENSED LOAD

© Copyright Intersil Americas LLC 2011-2016. All Rights Reserved.
All trademarks and registered trademarks are the property of their respective owners.

For additional products, see www.intersil.com/en/products.html

Intersil products are manufactured, assembled and tested utilizing ISO9001 quality systems as noted in the quality certifications found at www.intersil.com/en/support/qualandreliability.html

Intersil products are sold by description only. Intersil may modify the circuit design and/or specifications of products at any time without notice, provided that such modification does not, in Intersil's sole judgment, affect the form, fit or function of the product. Accordingly, the reader is cautioned to verify that datasheets are current before placing orders. Information furnished by Intersil is believed to be accurate and reliable. However, no responsibility is assumed by Intersil or its subsidiaries for its use; nor for any infringements of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Intersil or its subsidiaries.

For information regarding Intersil Corporation and its products, see www.intersil.com

Revision History

The revision history provided is for informational purposes only and is believed to be accurate, but not warranted. Please go to web to make sure you have the latest Rev.

DATE	REVISION	CHANGE
February 12, 2016	FN7896.4	<ul style="list-style-type: none"> Removed DAQ on a stick reference from "Related Literature" on page 1. Updated "Ordering Information" on page 3 by adding column for tape and reel option. Updated HBM value to kV (5500V to 5.5kV) in "Absolute Maximum Ratings" on page 4.
January 8, 2015	FN7896.3	<ul style="list-style-type: none"> On page 1, in the Related Literature section added AN1853 and AN1883. On page 3, updated the ordering information table by adding the (-T7A) products. Changed the y-axis units on Figure 18 on page 11 from "(V)" to "(µV)".
June 23, 2014	FN7896.2	<ul style="list-style-type: none"> Added Curves for Voltage Refs 1.25V, 1.024V, 1.5V, 2.5V and 4.096V Updated POD with following changes: In Detail A, changed lead width dimension from 0.13+/-0.05 to 0.085-0.19 Changed dimension of foot of lead from 0.31+/-0.10 to 0.38+/-0.10 In Land Pattern, added 0.4 Rad Typ dimension In Side View, changed height of package from 0.91+/-0.03 to 0.95+/-0.07
November 28, 2011	FN7896.1	<ul style="list-style-type: none"> On page 1, Features: removed "Coming Soon" from ISL21010-10, -12, -15; ISL21010-25; and ISL21010-40 voltage options; combined -20 option with -10, -12, -15; changed -40 to -41 On page 3, Ordering Information: added parts ISL21010DFH310Z-TK, ISL21010DFH312Z-TK, ISL21010CFH315Z-TK, ISL21010CFH325Z-TK, ISL21010CFH341Z-TK On page 4, Recommended Operating Conditions: added V_{OUT} = 1.024V, 1.25V, 1.5V, 2.048V2.2V to 5.5V; V_{OUT} = 2.5V.....2.6V to 5.5V; V_{OUT} = 4.096V.....4.2V to 5.5V On page 4 through page 8, added Electrical Specifications tables for (ISL21010-10, V_{OUT} = 1.024V), (ISL21010-12, V_{OUT} = 1.25V), (ISL21010-15, V_{OUT} = 1.5V), (ISL21010-41, V_{OUT} = 4.096V) On page 6, Electrical Specifications (ISL21010-20, V_{OUT} = 2.048V): changed V_{OUT}/ TA, Thermal Hysteresis, TYP from 50 to 100 On page 8, Note 10: changed "... where V_{OUT} drops 1mV from V_{IN} = 5.0V at T_A = +25 °C." to "... where V_{OUT} drops 1mV from V_{IN} = nominal at T_A = +25 °C." On page 25, Figure 94, changed title from "LOAD REGULATION OVER-TEMPERATURE" to "LOAD TRANSIENT RESPONSE AT 25mA LOAD". Figure 27, changed title from "LOAD TRANSIENT RESPONSE" to "LOAD TRANSIENT RESPONSE AT 1mA LOAD". On page 26, Figure 99, and page 29, Figure 116, changed figure titles to indicate 10mA instead of 1mA source load. On page 28, Figure 111, changed title from LOAD REGULATION OVER-TEMPERATURE" to "LOAD TRANSIENT RESPONSE AT 25mA LOAD". Figure 112, changed title from "LOAD TRANSIENT RESPONSE" to "LOAD TRANSIENT RESPONSE AT 1mA LOAD" On page 33, under "Noise Performance and Reduction", added reference to capacitative load range for 1.024V option.
August 9, 2011	FN7896.0	Initial Release

About Intersil

Intersil Corporation is a leading provider of innovative power management and precision analog solutions. The company's products address some of the largest markets within the industrial and infrastructure, mobile computing and high-end consumer markets.

For the most updated datasheet, application notes, related documentation and related parts, please see the respective product information page found at www.intersil.com.

You may report errors or suggestions for improving this datasheet by visiting www.intersil.com/ask.





Reliability reports are also available from our website at www.intersil.com/support.

Package Outline Drawing

P3.064

3 LEAD SMALL OUTLINE TRANSISTOR PLASTIC PACKAGE (SOT23-3)

Rev 3, 3/12



NOTES:

- Dimensions are in millimeters.
Dimensions in () for Reference Only.
- Dimensioning and tolerancing conform to AMSEY14.5m-1994.
- Reference JEDEC TO-236.
- Dimension does not include interlead flash or protrusions.
Interlead flash or protrusions shall not exceed 0.25mm per side.
- Footlength is measured at reference to gauge plane.