

R3152N Series

AEC-Q100 Compliant

42 V Input Window Voltage Detector for Automotive Applications

No. EC-405-200904

OVERVIEW

The R3152N is a window voltage detector suited for achieving the functional safety. This device monitors over- and under- voltage of the output voltage from the power supply IC for a microprocessor and a sensor, and can prevent malfunction of system caused by abnormal voltage.

KEY BENEFITS

- A stable voltage with supplying the battery voltage can provide the power supply and the voltage supervising separately.
- High-accuracy detection enables with Overvoltage/Undervoltage Detection Accuracy of -1.25% to 0.75% and Hysteresis of 1.5%.
- Small package of SOT-23-6 is adopted, and a safe and secure pin assignment with considering a short among adjacent pins.

KEY SPECIFICATIONS

- Operating Voltage Range (Max. Rating): 3.0 V to 42.0 V (50.0 V)
- Operating Temperature Range: −40°C to 125°C
- Supply Current: Typ. 1.5 μA
- Overvoltage Detection: 1.1 V to 5.9 V (0.01 V step)
- Undervoltage Detection:1.0 V to 4.8 V (0.01 V step)
- Detection Release Hysteresis: A, Typ. 1.0% with hysteresis
 B, No hysteresis
- Detection Voltage Accuracy:

 $\pm 0.5\%$ (Ta = 25°C)

-1.25% to 0.75% (-40°C to 125°C)

- Release Delay Time: Typ. 4 ms (C_D = 0.01 μF)
- Output Type: Nch. Open Drain

SELECTION GUIDE

Product Name	Package	Quantity per Reel			
R3152Nxxx\$-TR-#E	SOT-23-6	3,000 pcs			

xxx: The combination of an overvoltage detection setting voltage (Vovset) and an undervoltage detection setting voltage (Vuvset)


Refer to *Product-specific Electrical Characteristics* for more details.

\$: Hysteresis

\$	Hysteresis
Α	Yes
В	No

#: Quality Class Refer to SELECTION GUIDE for details.

TYPICAL APPLICATIONS



 $\ensuremath{\text{\textbf{C}}}_{\ensuremath{\text{\textbf{D}}}} \ensuremath{\text{\textbf{:}}}$ a capacitor set according to the release delay times

PACKAGE



SOT-23-6 2.9 x 2.8 x 1.1 (mm)

APPLICATIONS

- Power Supply Voltage Monitoring for ASIL-B/C/D Systems Including ECU and ADAS
- Power Supply Voltage Monitoring for Control Units Including EV Inverters and Charge Controllers

No. EC-405-200904

SELECTION GUIDE

The overvoltage detection setting voltage (V_{OVSET}) and the undervoltage detection setting voltage (V_{UVSET}) are user-selectable options.

Selection Guide

Product Name	Package	Quantity per Reel	Pb Free	Halogen Free
R3152Nxxx\$-TR-#E	SOT-23-6	3,000 pcs	Yes	Yes

xxx: The combination of an overvoltage detection setting voltage (Vovset) and an undervoltage detection setting voltage (Vuvset).

Refer to Product-specific Electrical Characteristics for more details.


\$: Hysteresis

\$	Hysteresis
Α	Yes
В	No

#: Quality Class


#	Operating Temp. Range	Test Temp.
Α	-40°C to 125°C	25°C, High
K	-40°C to 125°C	Low, 25°C, High

BLOCK DIAGRAM



R3152N Block Diagram

PIN DESCRIPTIONS




SOT-23-6 Pin Configuration

Pin Description


Pin No.	Symbol	Description
1	VDD	Supply Voltage Pin
2	CD	VD Release Delay Time Set Pin (for connecting with external capacitor for delay)
3	UV	Undervoltage Detection Output Pin ("Low" at detection)
4	OV	Overvoltage Detection Output Pin ("Low" at detection)
5	GND	GND Pin
6	SENSE	SENSE Pin

Internal Equivalent Circuit for Each Pin







CD Pin



OV Pin



SENSE Pin



No. EC-405-200904

ABSOLUTE MAXIMUM RATINGS

Absolute Maximum Ratings

Symbol	Parameter	Rating	Unit
	Supply Voltage	-0.3 to 50.0	V
V_{DD}	Peak Voltage ⁽¹⁾	60	V
VcD	CD Pin Output Voltage	-0.3 to 50.0	V
V _{UVOUT}	UV Pin Output Voltage	-0.3 to 7.0	V
Vovouт	OV Pin Output Voltage	-0.3 to 7.0	V
V _{SENSE}	SENSE Pin Input Voltage	-0.3 to 7.0	V
Iuvouт	UV Pin Output Current	30	mA
Іочоит	OV Pin Output Current	30	mA
P _D	Power Dissipation ⁽²⁾ (JEDEC STD.51-7)	830	mW
Tj	Junction Temperature Range	-40 to 150	°C
Tstg	Storage Temperature Range	-55 to 150	°C

ABSOLUTE MAXIMUM RATINGS

Electronic and mechanical stress momentarily exceeded absolute maximum ratings may cause permanent damage and may degrade the life time and safety for both device and system using the device in the field. The functional operation at or over these absolute maximum ratings are not assured.

RECCOMENDED OPERATING CONDITIONS

Recommend Operating Conditions

- toooiiiiiioiia o	peraurig corrainerie		
Symbol	Parameter	Rating	Unit
V_{DD}	Operating Voltage	3.0 to 42	V
VSENSE	SENSE Pin Input Voltage	0 to 6.0	V
Ta	Operating Temperature Range	-40 to 125	°C

RECOMMENDED OPERATING CONDITIONS

All of electronic equipment should be designed that the mounted semiconductor devices operate within the recommended operating conditions. The semiconductor devices cannot operate normally over the recommended operating conditions, even if they are used over such ratings by momentary electronic noise or surge. And the semiconductor devices may receive serious damage when they continue to operate over the recommended operating conditions.

⁽¹⁾ Duration Time: 200 ms

 $^{^{(2)}}$ Refer to POWER DISSIPATION for detailed information.

ELECTRICAL CHARACTERISTICS

V_{DD} = 14 V, C_D = 0.01 μF , pulled-up to 5 V with 100 $k\Omega$, unless otherwise specified.							
The specifications surrounded by	are guaranteed by design engineering at -40°C ≤ Ta ≤ 125°C.						

R3152N (-AE) Electrical Characteristics (Ta= 25°C) **Test Conditions/Comments** Symbol **Parameter** Min. Max. Unit Typ. Ta = 25°C x0.995 x1.005 V Overvoltage (OV) Detector V_{OVDET} Threshold -40°C ≤ Ta ≤ 125°C x0.9875 x1.0075 V $Ta = 25^{\circ}C$ x0.995 x1.005 V Undervoltage (UV) Detector VUVDET Threshold x1.0075 –40°C ≤ Ta ≤ 125°C x0.9875 V Vovdet VOVDET VOVDET With Hysteresis Overvoltage (OV) Threshold $\times 0.005$ ×0.01 ×0.015 Vovers Hysteresis 0 10 No Hysteresis m۷ VUVDET V_{UVDET} VUVDET With Hysteresis V Undervoltage (UV) $\times 0.005$ ×0.015 ×0.01 Vuvhys Threshold Hysteresis 0 No Hysteresis 10 m۷ 3.2 Consumption Current VUVDET < SENSE < VOVDET 1.5 Iss μΑ 7 V_{UVDET}≥1.6V, V_{OVDET}≥2.0V 14 28 RSENSE SENSE Pin Resistance ΜΩ Vuvdet < 1.6V, Vovdet < 3.0 12 6 2.0V 2.8 1.8 V V_{UVLO} **UVLO Detector Threshold UVLO Threshold Hysteresis** 0.1 0.2 V Vuvlohys Overvoltage (OV) 6.0 V V_{OVOUT} pulled-up output voltage Undervoltage (UV) ٧ 6.0 V_{UVOUT} pulled-up output voltage Overvoltage (OV) 1.7 VDDLOV Low-operating Voltage⁽¹⁾ Undervoltage (UV) 1.7 V V_{DDLUV} Low-operating Voltage(1) OV Pin Nch. Driver Output Current $V_{DD} = 3.0, V_{DS} = 0.1 V$ 8.0 1.8 mA Гоит $V_{DD} = 3.0, V_{DS} = 0.1 V$ UV Pin Nch. Driver Output Current 8.0 1.8 mΑ 0.3 **OV Pin Nch.Driver Leak Current** $V_{OVOUT} = 5.5 V$ μΑ **I**LEAK 0.3

All test items listed under Electrical Characteristics are done under the pulse load condition (Tj≈Ta = 25°C).

UV Pin Nch Driver Leak Current

Release Delay Time

tDELAY

RICOH

 $V_{UVOUT} = 5.5 V$

2.5

5

μΑ

ms

⁽¹⁾ Minimum value of power supply voltage when an output voltage will become less than 0.1V at detection. (Pulled-up resistance: 100 kΩ, Pulled-up voltage: 5 V)

No. EC-405-200904

 V_{DD} = 14 V, C_D = 0.01 μF , pulled-up to 5 V with 100 $k\Omega$, unless otherwise specified.

R3152N (-KE) Electrical Characteristics

(-40°C ≤ Ta ≤ 125°C)

11313211	(40 0 2 1a 2 1						
Symbol	Parameter	Test Conditions/Comments	Min.	Тур.	Max.	Unit	
VOVDET	Overvoltage (OV) Detector	Ta = 25°C	x0.995		x1.005	V	
V OVDET	Threshold	–40°C ≤ Ta ≤ 125°C	x0.9875		x1.0075	V	
~	Undervoltage (UV) Detector	Ta = 25°C	x0.995		x1.005	V	
VUVDET	Threshold	–40°C ≤ Ta ≤ 125°C	x0.9875		x1.0075	V	
Vovers	Overvoltage (OV) Threshold	With Hysteresis	V _{OVDET} ×0.005	V _{OVDET} ×0.01	V _{OVDET} ×0.015	V	
	Hysteresis	No Hysteresis	0		10	mV	
Vuvhys	Undervoltage (UV)	With Hysteresis	V _{UVDET} ×0.005	V _{UVDET} ×0.01	V _{UVDET} ×0.015	V	
	Threshold Hysteresis	No Hysteresis	0		10	mV	
Iss	Consumption Current	VUVDET < SENSE < VOVDET		1.5	3.2	μΑ	
		V _{UVDET} ≥1.6V, V _{OVDET} ≥2.0V	7	14	28	ΜΩ	
RSENSE	SENSE Pin Resistance	Vuvdet < 1.6V, Vovdet < 2.0V	3.0	6	12		
V _{UVLO}	UVLO Detector Threshold			1.8	2.8	V	
Vuvlohys	UVLO Threshold Hysteresis			0.1	0.2	V	
Vovouт	Overvoltage (OV) pulled-up output voltage				6.0	V	
Vuvouт	Undervoltage (UV) pulled-up output voltage				6.0	V	
V _{DDLOV}	Overvoltage (OV) Low-operating Voltage ⁽¹⁾				1.7	V	
V _{DDLUV}	Undervoltage (UV) Low-operating Voltage ⁽¹⁾				1.7	V	
la	OV Pin Nch. Driver Output Current	$V_{DD} = 3.0, V_{DS} = 0.1 V$	0.8	1.8		mA	
I _{OUT}	UV Pin Nch. Driver Output Current	$V_{DD} = 3.0, V_{DS} = 0.1 V$	0.8	1.8		mA	
I	OV Pin Nch.Driver Leak Current	Vovout = 5.5 V		-	0.3	μΑ	
I _{LEAK}	UV Pin Nch Driver Leak Current	Vuvouт = 5.5 V			0.3	μΑ	
tDELAY	Release Delay Time		2.5	4	8	ms	

All test items listed under Electrical Characteristics are done under the pulse load condition ($Tj \approx Ta = 25$ °C).

6

 $^{^{(1)}}$ Minimum value of power supply voltage when an output voltage will become less than 0.1V at detection. (Pulled-up resistance: 100 k Ω , Pulled-up voltage: 5 V)

 $V_{DD} = 14 \text{ V, } C_D = 0.01 \text{ } \mu\text{F, pulled-up to 5 V with 100 k} \Omega, \text{ unless otherwise specfied.}$ The specifications surrounded by _____ are guaranteed by design engineering at -40°C ≤ Ta ≤ 125°C.

R3152N (-AE) Product-specific Electrical Characteristics

 $(Ta = 25^{\circ}C)$

Product Vovdet (V)		/)	V _{UVDET} (V)			Vovhys (V)			Vuvhys (V)			
Name	Min.	Тур.	Max.	Min.	Тур.	Max.	Min.	Тур.	Max.	Min.	Тур.	Max.
R3152N001A	5.27350	5.30	5.32650	4.67650	4.70	4.72350	0.02650	0.05300	0.07950	0.02350	0.04700	0.07050
R3152N002A	3.52230	3.54	3.55770	3.03475	3.05	3.06525	0.01770	0.03540	0.05310	0.01525	0.03050	0.04575
R3152N003B	3.55215	3.57	3.58785	2.48750	2.50	2.51250	0	-	0.01000	0	-	0.01000
R3152N004A	1.86065	1.87	1.87935	1.73130	1.74	1.74870	0.00935	0.01870	0.02805	0.00870	0.01740	0.02610
R3152N005A	3.41285	3.43	3.44715	3.17405	3.19	3.20595	0.01715	0.03430	0.05145	0.01595	0.03190	0.04785
R3152N013A	1.32335	1.33	1.33665	1.16415	1.17	1.17585	0.00665	0.01330	0.01995	0.00585	0.01170	0.01755
R3152N014A	1.16415	1.17	1.17585	1.06963	1.075	1.08037	0.00585	0.01170	0.01755	0.00538	0.01075	0.01613
R3152N015A	1.28355	1.29	1.29645	1.15420	1.16	1.16580	0.00645	0.01290	0.01935	0.00580	0.01160	0.01740
R3152N017A	3.55215	3.57	3.58785	2.72630	2.74	2.75370	0.01785	0.03570	0.05355	0.01370	0.02740	0.04110
R3152N020A	1.24375	1.25	1.25625	1.11440	1.12	1.12560	0.00625	0.01250	0.01875	0.00560	0.01120	0.01680
R3152N201B	1.23380	1.24	1.24620	1.16415	1.17	1.17585	0	-	0.01000	0	-	0.01000
R3152N101B	2.58700	2.60	2.61300	2.39795	2.41	2.42205	0	-	0.01000	O	-	0.01000
R3152N102B	3.41285	3.43	3.44715	3.16410	3.18	3.19590	0	-	0.01000	0	-	0.01000
R3152N203A	1.39300	1.40	1.40700	0.99500	1.00	1.00500	0.00700	0.01400	0.02100	0.00500	0.01000	0.01500
R3152N204A	1.62185	1.63	1.63815	1.40295	1.41	1.41705	0.00815	0.01630	0.02445	0.00705	0.01410	0.02115
R3152N103A	5.77100	5.80	5.82900	4.75610	4.78	4.80390	0.02900	0.05800	0.08700	0.02390	0.04780	0.07170
R3152N104A	3.38300	3.40	3.41700	1.59200	1.60	1.60800	0.01700	0.03400	0.05100	0.00800	0.01600	0.02400

No. EC-405-200904

 V_{DD} = 14 V, C_D = 0.01 $\mu F,$ pulled-up to 5 V with 100 $k\Omega,$ unless otherwise specfied.

The specifications surrounded by are guaranteed by design engineering at -40° C \leq Ta \leq 125 $^{\circ}$ C.

R3152N (-AE) Product-specific Electrical Characteristics

(-40°C ≤ Ta ≤ 125°C)

Product	V _{OVDET} (V)			V _{UVDET} (V)			Vovers (V)			Vuvhys (V)		
Name	Min.	Тур.	Max.	Min.	Тур.	Max.	Min.	Тур.	Max.	Min.	Тур.	Max.
R3152N001A	5.23375	5.30	5.33975	4.64125	4.70	4.73525	0.02650	0.0530	0.07950	0.02350	0.04700	0.07050
R3152N002A	3.49575	3.54	3.56655	3.01188	3.05	3.07287	0.01770	0.0354	0.05310	0.01525	0.03050	0.04575
R3152N003B	3.52538	3.57	3.59678	2.46875	2.50	2.51875	O	-	0.01000	O	-	0.01000
R3152N004A	1.84663	1.87	1.88403	1.71825	1.74	1.75305	0.00935	0.01870	0.02805	0.00870	0.01740	0.02610
R3152N005A	3.38713	3.43	3.45573	3.15013	3.19	3.21392	0.01715	0.03430	0.05145	0.01595	0.0319	0.04785
R3152N013A	1.31338	1.33	1.33997	1.15538	1.17	1.17877	0.00665	0.01330	0.01995	0.00585	0.01170	0.01755
R3152N014A	1.15537	1.17	1.17878	1.06156	1.075	1.08307	0.00585	0.01170	0.01755	0.00538	0.01075	0.01613
R3152N015A	1.27387	1.29	1.29968	1.14550	1.16	1.16870	0.00645	0.01290	0.01935	0.00580	0.01160	0.01740
R3152N017A	3.52537	3.57	3.59678	2.70575	2.74	2.76055	0.01785	0.03570	0.05355	0.01370	0.02740	0.04110
R3152N020A	1.23438	1.25	1.25937	1.10600	1.12	1.12840	0.00625	0.01250	0.01875	0.00560	0.01120	0.01680
R3152N201B	1.22450	1.24	1.24930	1.15538	1.17	1.17877	0	-	0.01000	0	ı	0.01000
R3152N101B	2.56750	2.60	2.61950	2.37988	2.41	2.42807	0	-	0.01000	0	ı	0.01000
R3152N102B	3.38713	3.43	3.45572	3.14025	3.18	3.20385	0	-	0.01000	0	ı	0.01000
R3152N203A	1.38250	1.40	1.41050	0.98750	1.00	1.00750	0.00700	0.01400	0.02100	0.00500	0.01000	0.01500
R3152N204A	1.60963	1.63	1.64222	1.39238	1.41	1.42057	0.00815	0.01630	0.02445	0.00705	0.01410	0.02115
R3152N103A	5.72750	5.80	5.84350	4.72025	4.78	4.81585	0.02900	0.05800	0.08700	0.02390	0.04780	0.07170
R3152N104A	3.35750	3.40	3.42550	1.58000	1.60	1.61200	0.01700	0.03400	0.05100	0.00800	0.01600	0.02400

 V_{DD} = 14 V, C_D = 0.01 $\mu F,$ pulled-up to 5 V with 100 $k\Omega,$ unless otherwise specfied.

R3152N (-KE) Product-specific Electrical Characteristics

 $(Ta = 25^{\circ}C)$

	,										,	/
Product	V _{OVDET} (V)			VUVDET (V)			Vovers (V)			Vuvhys (V)		
Name	Min.	Тур.	Max.	Min.	Тур.	Max.	Min.	Тур.	Max.	Min.	Тур.	Max.
R3152N001A	5.27350	5.30	5.32650	4.67650	4.70	4.72350	0.02650	0.05300	0.07950	0.02350	0.04700	0.07050
R3152N002A	3.52230	3.54	3.55770	3.03475	3.05	3.06525	0.01770	0.03540	0.05310	0.01525	0.03050	0.04575
R3152N003B	3.55215	3.57	3.58785	2.48750	2.50	2.51250	0	-	0.01000	0	-	0.01000
R3152N004A	1.86065	1.87	1.87935	1.73130	1.74	1.74870	0.00935	0.01870	0.02805	0.00870	0.01740	0.02610
R3152N005A	3.41285	3.43	3.44715	3.17405	3.19	3.20595	0.01715	0.03430	0.05145	0.01595	0.03190	0.04785
R3152N013A	1.32335	1.33	1.33665	1.16415	1.17	1.17585	0.00665	0.01330	0.01995	0.00585	0.01170	0.01755
R3152N014A	1.16415	1.17	1.17585	1.06963	1.075	1.08037	0.00585	0.01170	0.01755	0.00538	0.01075	0.01613
R3152N015A	1.28355	1.29	1.29645	1.15420	1.16	1.16580	0.00645	0.01290	0.01935	0.00580	0.01160	0.01740
R3152N017A	3.55215	3.57	3.58785	2.72630	2.74	2.75370	0.01785	0.03570	0.05355	0.01370	0.02740	0.04110
R3152N020A	1.24375	1.25	1.25625	1.11440	1.12	1.12560	0.00625	0.01250	0.01875	0.00560	0.01120	0.01680
R3152N201B	1.23380	1.24	1.24620	1.16415	1.17	1.17585	0	-	0.01000	0	-	0.01000
R3152N101B	2.58700	2.60	2.61300	2.39795	2.41	2.42205	0	-	0.01000	0	-	0.01000
R3152N102B	3.41285	3.43	3.44715	3.16410	3.18	3.19590	0	-	0.01000	0	-	0.01000
R3152N203A	1.39300	1.40	1.40700	0.99500	1.00	1.00500	0.00700	0.01400	0.02100	0.00500	0.01000	0.01500
R3152N204A	1.62185	1.63	1.63815	1.40295	1.41	1.41705	0.00815	0.01630	0.02445	0.00705	0.01410	0.02115
R3152N103A	5.77100	5.80	5.82900	4.75610	4.78	4.80390	0.02900	0.05800	0.08700	0.02390	0.04780	0.07170
R3152N104A	3.38300	3.40	3.41700	1.59200	1.60	1.60800	0.01700	0.03400	0.05100	0.00800	0.01600	0.02400

No. EC-405-200904


 V_{DD} = 14 V, C_D = 0.01 $\mu F,$ pulled-up to 5 V with 100 $k\Omega,$ unless otherwise specfied.

R3152N (-KE) Product-specific Electrical Characteristics

 $(-40^{\circ}\text{C} \le \text{Ta} \le 125^{\circ}\text{C})$

Product	V _{OVDET} (V)			VUVDET (V)		Vovers (V)			Vuvhys (V)			
Name	Min.	Тур.	Max.	Min.	Тур.	Max.	Min.	Тур.	Max.	Min.	Тур.	Max.
R3152N001A	5.23375	5.30	5.33975	4.64125	4.70	4.73525	0.02650	0.0530	0.07950	0.02350	0.04700	0.07050
R3152N002A	3.49575	3.54	3.56655	3.01188	3.05	3.07287	0.01770	0.0354	0.05310	0.01525	0.03050	0.04575
R3152N003B	3.52538	3.57	3.59678	2.46875	2.50	2.51875	0	-	0.01000	0	-	0.01000
R3152N004A	1.84663	1.87	1.88403	1.71825	1.74	1.75305	0.00935	0.01870	0.02805	0.00870	0.01740	0.02610
R3152N005A	3.38713	3.43	3.45573	3.15013	3.19	3.21392	0.01715	0.03430	0.05145	0.01595	0.0319	0.04785
R3152N013A	1.31338	1.33	1.33997	1.15538	1.17	1.17877	0.00665	0.01330	0.01995	0.00585	0.01170	0.01755
R3152N014A	1.15537	1.17	1.17878	1.06156	1.075	1.08307	0.00585	0.01170	0.01755	0.00538	0.01075	0.01613
R3152N015A	1.27387	1.29	1.29968	1.14550	1.16	1.16870	0.00645	0.01290	0.01935	0.00580	0.01160	0.01740
R3152N017A	3.52537	3.57	3.59678	2.70575	2.74	2.76055	0.01785	0.03570	0.05355	0.01370	0.02740	0.04110
R3152N020A	1.23438	1.25	1.25937	1.10600	1.12	1.12840	0.00625	0.01250	0.01875	0.00560	0.01120	0.01680
R3152N201B	1.22450	1.24	1.24930	1.15538	1.17	1.17877	0	-	0.01000	0	-	0.01000
R3152N101B	2.56750	2.60	2.61950	2.37988	2.41	2.42807	0	-	0.01000	0	-	0.01000
R3152N102B	3.38713	3.43	3.45572	3.14025	3.18	3.20385	0	-	0.01000	0	-	0.01000
R3152N203A	1.38250	1.40	1.41050	0.98750	1.00	1.00750	0.00700	0.01400	0.02100	0.00500	0.01000	0.01500
R3152N204A	1.60963	1.63	1.64222	1.39238	1.41	1.42057	0.00815	0.01630	0.02445	0.00705	0.01410	0.02115
R3152N103A	5.72750	5.80	5.84350	4.72025	4.78	4.81585	0.02900	0.05800	0.08700	0.02390	0.04780	0.07170
R3152N104A	3.35750	3.40	3.42550	1.58000	1.60	1.61200	0.01700	0.03400	0.05100	0.00800	0.01600	0.02400

THEORY OF OPERATION




- (1) When the SENSE pin voltage (V_{SENSE}) exceed the undervoltage release voltage (V_{UVREL}), the UV pin output becomes "High" after the release delay time (t_{DELAY}).
- (2) When V_{SENSE} exceed the overvoltage detection voltage (V_{OVDET}) by increasing in voltage, the OV pin output becomes "Low" after the detection delay time (Typ.10 µs) and enters the overvoltage detecting state
- (3) When V_{SENSE} decreases less than the overvoltage release voltage (V_{OVREL}), the OV pin output becomes "High" after the release delay time (t_{DELAY}).
- (4) When V_{SENSE} decreases less than the undervoltage detection voltage (V_{UVDET}), the UV pin output becomes "Low" after the detection delay time (Typ.10 µs).
- (5) When the VDD pin voltage (V_{DD}) decreases less than the UVLO detection voltage (V_{UVLO}), the OV and UV pins output become "Low".

Note: A certain tilting angle of power supply voltage of the R3152NxxxB may cause chattering at detection or at release. To prevent the occurrence of chattering, connect a 10-nF or more capacitor to the CD pin.

Delay in Operation and Delay Time (tDELAY)

At Undervoltage Detection

When supplying a voltage higher than the undervoltage release voltage (V_{UVREL}) to the SENSE pin, a charging to an external capacitor starts and the CD pin voltage (V_{CD}) increases. The UV pin voltage (V_{UV}) maintains "Low" until V_{CD} reaches the CD pin threshold voltage (V_{TCD}). When V_{CD} exceeds V_{TCD} , V_{UV} is inverted from "Low" to "High". The release delay time (t_{DELAY}) is the period from the SENSE pin voltage (V_{SENSE}) exceeds V_{UVREL} to a rising edge of V_{UV} . When the output voltage turns from "Low" to "High", a charge carrier of the external capacitor starts discharging. When the voltage lower than V_{UV} is supplied to the SENSE pin, the detection delay time (t_{PHL}), which is the period that V_{UV} is inverted from "High" to "Low", remains constant independent of the external capacitor.




Undervoltage Release Delay Timing Diagram

Calculation of Release Delay Time (t_{DELAY})

The following equation can calculate a typical value of the release delay time (t_{DELAY}) with using the external capacitor (C_D).


$$t_{DELAY}$$
 (s) = 0.73 × C_D (F) / (1.5×10⁻⁶)

 t_{DELAY} is the period from supplying a pulse voltage of 1.0 V \rightarrow (V_{UVDET}) + 1.0 V to the SENSE pin to the UV pins reached 2.5 V.



At Overvoltage Detection

When supplying a voltage lower than the overvoltage release voltage (V_{OVREL}) to the SENSE pin, a charging to an external capacitor starts and the CD pin voltage (V_{CD}) increases. The OV pin voltage (V_{OV}) maintains "Low" until V_{CD} reaches the CD pin threshold voltage (V_{TCD}). When V_{CD} exceeds V_{TCD} , V_{OV} is inverted from "Low" to "High". The release delay time (t_{DELAY}) is the period from the SENSE pin voltage (V_{SENSE}) falls below V_{OVREL} to a rising edge of V_{OV} . When the output voltage turns from "Low" to "High", a charge carrier of the external capacitor starts discharging. When the voltage higher than V_{OV} is supplied to the SENSE pin, the detection delay time (t_{PHL}), which is the period that V_{OV} is inverted from "High" to "Low", remains constant independent of the external capacitor.




Overvoltage Release Delay Timing Diagram

Calculation of Release Delay Time (tDELAY)


The following equation can calculate a typical value of the release delay time (t_{DELAY}) with using the external capacitor (C_D).

$$t_{DELAY}$$
 (s) = 0.73 × C_D (F) / (1.5×10⁻⁶)

 t_{DELAY} is the period from supplying a pulse voltage of 1.0 V \rightarrow (VovReL) + 1.0 V to the SENSE pin to the OV pin reached 2.5 V after the OV pin is pulled up to 5V by connecting with a resistor of $100k\Omega$.



APPLICATION INFORMATION



R3152N Typical Application Circuit

Recommended External Components


Symbol	Description
	A capacitor corresponding to setting of Release Delay Time is required. Refer to "Delay in
С	Operation and Released Delay Time (t _{DELAY})" in Operation Description for details.
	A resistor is required to set with consideration of the output current at Nch. driver's ON and the
R1	leakage current at Nch. driver's OFF. Refer to "Electrical Characteristic" for details – provided
	the evaluation result with using a resistor of $100k\Omega$.


TYPICAL CHARACTERISTICS

Typical Characteristics are intended to be used as reference data, they are not guaranteed.

1) Load Dump


 $V_{UVSET} = 3.0 \text{ V}$, $V_{OVSET} = 3.6 \text{ V}$, $V_{SENSE} = 3.3 \text{ V}$, Pulled-up to 5.0 V






2) Cranking


 $V_{UVSET} = 3.0 \text{ V}$, $V_{OVSET} = 3.6 \text{ V}$, $V_{SENSE} = 3.3 \text{ V}$, Pulled-up to 5.0 V







3) Supply Current vs. VDD

 $V_{\text{UVSET}} = 1.6 \text{ V}, V_{\text{OVSET}} = 2.0 \text{ V}$









No. EC-405-200904


 $V_{\text{UVSET}} = 4.7 \text{ V}, V_{\text{OVSET}} = 5.3 \text{ V}$




4) Supply Current vs. V_{SENSE} $V_{\text{UVSET}} = 1.6 \text{ V}, V_{\text{OVSET}} = 2.0 \text{ V}$




$V_{\text{UVSET}} = 3.0 \text{ V}, V_{\text{OVSET}} = 3.6 \text{ V}$




 $V_{UVSET} = 4.7 V$, $V_{OVSET} = 5.3 V$




5) UV/OV Detection Voltage vs. Ambient Temperature



$$V_{UVSET} = 3.0 \text{ V}, V_{OVSET} = 3.6 \text{ V}$$




$V_{UVSET} = 4.7 \text{ V}, V_{OVSET} = 5.3 \text{ V}$




6) UV/OV Release Voltage vs. Ambient Temperature

$$V_{\text{UVSET}} = 1.6 \text{ V}, V_{\text{OVSET}} = 2.0 \text{ V}$$









No. EC-405-200904


 $V_{UVSET} = 4.7 V$, $V_{OVSET} = 5.3 V$




7) UV/OV Detection Voltage vs. V_{DD}


Vuvset = 1.6 V, Vovset = 2.0 V







 $V_{UVSET} = 3.0 \text{ V}, V_{OVSET} = 3.6 \text{ V}$






 $V_{UVSET} = 4.7 V$, $V_{OVSET} = 5.3 V$







8) UV/OV Release Voltage vs. V_{DD}


 $V_{\text{UVSET}} = 1.6 \text{ V}, V_{\text{OVSET}} = 2.0 \text{ V}$






VUVSET = 3.0V, VOVSET = 3.6 V






No. EC-405-200904


 $V_{UVSET} = 4.7 V$, $V_{OVSET} = 5.3 V$







9) UV/OV Voltage vs. V_{DD} (Ta = 25°C)

 V_{UVSET} = 1.6 V, V_{OVSET} = 2.0 V, Pulled-up to 5.0 V









10) UV/OV Voltage vs. V_{SENSE} (Ta = 25°C)

V_{UVSET} = 1.6 V, V_{OVSET} = 2.0 V, Pulled-up to 5.0 V





 $V_{UVSET} = 4.7 \text{ V}$, $V_{OVSET} = 5.3 \text{ V}$, Pulled-up to 5.0 V



11) Driver Output Current vs. V_{DD}


 $V_{\text{UVSET}} = 4.7 \text{ V}, V_{\text{OVSET}} = 5.3 \text{ V}$







12) Driver Output Current vs. V_{DS} (Ta = 25°C)


 $V_{\text{UVSET}} = 1.6 \text{ V}, V_{\text{OVSET}} = 2.0 \text{ V}$





 $V_{\text{UVSET}} = 4.7 \text{ V}, V_{\text{OVSET}} = 5.3 \text{ V}$






No. EC-405-200904


13) Release Delay Time vs. Ambient Temperature


 $V_{\text{UVSET}} = 4.7 \text{ V}, V_{\text{OVSET}} = 5.3 \text{ V}$



14) Release Delay Time vs. VDD

 $V_{UVSET} = 4.7 \text{ V}, V_{OVSET} = 5.3 \text{ V}$






15) Detection / Release Delay Time vs. External Capacitor for CD Pin


(Ta = 25°C)

 $V_{UVSET} = 4.7 \text{ V}, V_{OVSET} = 5.3 \text{ V}$



16) SENSE Pulse Width vs. Over Drive Voltage

(Ta = 25°C)



Ver. A

The power dissipation of the package is dependent on PCB material, layout, and environmental conditions. The following measurement conditions are based on JEDEC STD. 51-7.

Measurement Conditions

Item	Measurement Conditions				
Environment	Mounting on Board (Wind Velocity = 0 m/s)				
Board Material	Glass Cloth Epoxy Plastic (Four-Layer Board)				
Board Dimensions	76.2 mm × 114.3 mm × 0.8 mm				
Copper Ratio	Outer Layer (First Layer): Less than 95% of 50 mm Square Inner Layers (Second and Third Layers): Approx. 100% of 50 mm Square Outer Layer (Fourth Layer): Approx. 100% of 50 mm Square				
Through-holes	φ 0.3 mm × 7 pcs				


Measurement Result

 $(Ta = 25^{\circ}C, Tjmax = 150^{\circ}C)$


Item	Measurement Result		
Power Dissipation	830 mW		
Thermal Resistance (θja)	θja = 150°C/W		
Thermal Characterization Parameter (ψjt)	ψjt = 51°C/W		

θja: Junction-to-Ambient Thermal Resistance

ψjt: Junction-to-Top Thermal Characterization Parameter




Power Dissipation vs. Ambient Temperature



Measurement Board Pattern

Ver. A



SOT-23-6 Package Dimensions



- 1. The products and the product specifications described in this document are subject to change or discontinuation of production without notice for reasons such as improvement. Therefore, before deciding to use the products, please refer to Ricoh sales representatives for the latest information thereon.
- 2. The materials in this document may not be copied or otherwise reproduced in whole or in part without prior written consent of Ricoh.
- 3. Please be sure to take any necessary formalities under relevant laws or regulations before exporting or otherwise taking out of your country the products or the technical information described herein.
- 4. The technical information described in this document shows typical characteristics of and example application circuits for the products. The release of such information is not to be construed as a warranty of or a grant of license under Ricoh's or any third party's intellectual property rights or any other rights.
- 5. The products in this document are designed for automotive applications. However, when using the products for automotive applications, please make sure to contact Ricoh sales representative in advance due to confirming the quality level.
- 6. We are making our continuous effort to improve the quality and reliability of our products, but semiconductor products are likely to fail with certain probability. In order to prevent any injury to persons or damages to property resulting from such failure, customers should be careful enough to incorporate safety measures in their design, such as redundancy feature, fire containment feature and fail-safe feature. We do not assume any liability or responsibility for any loss or damage arising from misuse or inappropriate use of the products.
- 7. Anti-radiation design is not implemented in the products described in this document.
- 8. The X-ray exposure can influence functions and characteristics of the products. Confirm the product functions and characteristics in the evaluation stage.
- 9. WLCSP products should be used in light shielded environments. The light exposure can influence functions and characteristics of the products under operation or storage.
- 10. There can be variation in the marking when different AOI (Automated Optical Inspection) equipment is used. In the case of recognizing the marking characteristic with AOI, please contact Ricoh sales or our distributor before attempting to use AOI.
- 11. Please contact Ricoh sales representatives should you have any questions or comments concerning the products or the technical information.



Ricoh is committed to reducing the environmental loading materials in electrical devices with a view to contributing to the protection of human health and the environment.

Ricoh has been providing RoHS compliant products since April 1, 2006 and Halogen-free products since April 1, 2012.

RICOH RICOH ELECTRONIC DEVICES CO., LTD.

Official website

https://www.n-redc.co.jp/en/

Contact us

https://www.n-redc.co.jp/en/buy/