

SCDS177A-OCTOBER 2004-REVISED DECEMBER 2007

## **FEATURES**

- Specified Break-Before-Make Switching
- Low ON-State Resistance
- High Bandwidth
- Control Inputs Are 5.5-V Tolerant
- Low Charge Injection
- Excellent ON-State Resistance Matching
- Low Total Harmonic Distortion (THD)
- 1.65-V to 5.5-V Single-Supply Operation
- Latch-Up Performance Exceeds 100 mA Per JESD 78, Class II
- ESD Performance Tested Per JESD 22
  - 2000-V Human-Body Model (A114-B, Class II)
  - 1000-V Charged-Device Model (C101)

## APPLICATIONS

- Cell Phones
- PDAs
- Portable Instrumentation

# SC-70 (DCU) PACKAGE (TOP VIEW)



#### FUNCTION TABLE

| IN1 | IN2 | COM TO NO0 | COM TO NO0 COM TO NO1 |     |
|-----|-----|------------|-----------------------|-----|
| L   | L   | OFF        | OFF                   | OFF |
| Н   | L   | ON         | OFF                   | OFF |
| L   | н   | OFF        | ON                    | OFF |
| н   | н   | OFF        | OFF                   | ON  |

# **DESCRIPTION/ORDERING INFORMATION**

The TS5A3357 is a high-performance, single-pole triple throw (SP3T) analog switch that is designed to operate from 1.65 V to 5.5 V. The device offers a low ON-state resistance and low input/output capacitance and, thus, causes a very low signal distortion. The break-before-make feature allows transferring of a signal from one port to another, with a minimal signal distortion. This device also offers a low charge injection which makes this device suitable for high-performance audio and data acquisition systems.

#### Summary of Characteristics<sup>(1)</sup>

| Configuration  | Triple 3:1 Multiplexer/<br>Demultiplexer<br>(1 × SP3T) |
|--|--|
| Number of channels   | 1  |
| ON-state resistance (r <sub>on</sub> )                     | 5 Ω  |
| ON-state resistance match ( $\Delta r_{on}$ )              | 0.1 Ω  |
| ON-state resistance flatness (ron(flat))                   | 6.5 Ω  |
| Turn-on/turn-off time (t <sub>ON</sub> /t <sub>OFF</sub> ) | 6.5 ns/3.7 ns  |
| Break-before-make time (t <sub>BBM</sub> )                 | 0.5 ns   |
| Charge injection (Q <sub>C</sub> )                         | 3.4 pC   |
| Bandwidth (BW)   | 334 MHz  |
| OFF isolation (O <sub>ISO</sub> )                          | –82 dB at 10 MHz                                       |
| Crosstalk (X <sub>TALK</sub> )                             | –62 dB at 10 MHz                                       |
| Total harmonic distortion (THD)                            | 0.05%  |
| Leakage current (I <sub>COM(OFF)</sub> )                   | ±1 μA  |
| Package option   | 8-pin DCU (US8)  |

(1)  $V_+ = 5 V, T_A = 25^{\circ}C$ 



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

SCDS177A-OCTOBER 2004-REVISED DECEMBER 2007



#### **ORDERING INFORMATION**

| T <sub>A</sub>                  | PACKAGE <sup>(1)(2)</sup> |               | ORDERABLE PART NUMBER | TOP-SIDE MARKING <sup>(3)</sup> |
|---------------------------------|---------------------------|---------------|-----------------------|---------------------------------|
| $-40^{\circ}C$ to $85^{\circ}C$ | SOT (SC-70) – DCU         | Tape and reel | TS5A3357DCUR          | JA9_                            |

Package drawings, thermal data, and symbolization are available at www.ti.com/packaging.
For the most current package and ordering information, see the Package Option Addendum at the end of this document, or see the TI website at www.ti.com.

(3) DCU: The actual top-side marking has one additional character that designates the assembly/test site.

## ABSOLUTE MINIMUM AND MAXIMUM RATINGS<sup>(1)(2)</sup>

over operating free-air temperature range (unless otherwise noted)

|                                     |   |  | MIN  | MAX | UNIT |
|-------------------------------------|---|--|------|-----|------|
| V+                                  | Supply voltage range <sup>(3)</sup>           |  | -0.5 | 6.5 | V    |
| V <sub>NO</sub><br>V <sub>COM</sub> | Analog voltage range <sup>(3)(4)(5)</sup>     |  |      |     | V    |
| Ι <sub>Κ</sub>                      | Analog port diode current                     | $V_{NO}$ , $V_{COM}$ < 0 or $V_{NO}$ , $V_{COM}$ > $V_{+}$ | -50  | 50  | mA   |
| I <sub>NO</sub><br>I <sub>COM</sub> | On-state switch current                       | $V_{NO}$ , $V_{COM} = 0$ to $V_{+}$                        | -100 | 100 | mA   |
| VI                                  | Digital input voltage range <sup>(3)(4)</sup> |  | -0.5 | 6.5 | V    |
| I <sub>IK</sub>                     | Digital input clamp current                   | V <sub>1</sub> < 0   | -50  |     | mA   |
| I+                                  | Continuous current through V <sub>+</sub>     |  |      | 100 | mA   |
| I <sub>GND</sub>                    | Continuous current through GND                |  | -100 | 100 | mA   |
| T <sub>stg</sub>                    | Storage temperature range                     |  | -65  | 150 | °C   |

(1) Stresses above these ratings may cause permanent damage. Exposure to absolute maximum conditions for extended periods may degrade device reliability. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those specified is not implied.

(2) The algebraic convention, whereby the most negative value is a minimum and the most positive value is a maximum.

(3) All voltages are with respect to ground, unless otherwise specified.

(4) The input and output voltage ratings may be exceeded if the input and output clamp-current ratings are observed.

(5) This value is limited to 5.5 V maximum.

## PACKAGE THERMAL IMPEDANCE

|               |  | MAX | UNIT |
|---------------|--|-----|------|
| $\theta_{JA}$ | Package thermal impedance <sup>(1)</sup> | 165 | °C/W |

(1) The package thermal impedance is calculated in accordance with JESD 51-7.

2

SCDS177A-OCTOBER 2004-REVISED DECEMBER 2007

#### **ELECTRICAL CHARACTERISTICS FOR 5-V SUPPLY**<sup>(1)</sup>

 $V_{+} = 4.5 \text{ V}$  to 5.5 V,  $T_{A} = -40^{\circ}\text{C}$  to 85°C (unless otherwise noted)

| PARAMETER  | SYMBOL                    | TEST CO   | NDITIONS                    | TA   | ۷.    | MIN               | TYP | MAX                | UNIT |
|--|---------------------------|---|-----------------------------|------|-------|-------------------|-----|--------------------|------|
| Analog Switch                                    |                           | 1   |                             |      |       |                   |     |                    |      |
| Analog signal range                              | $V_{COM}, V_{NO}$         |   |                             |      |       | 0                 |     | V <sub>+</sub>     | V    |
| Peak ON resistance                               | r <sub>peak</sub>         | $0 \le V_{NO} \le V_+,$<br>$I_{COM} = -30 \text{ mA},$  | Switch ON,<br>See Figure 13 | Full | 4.5 V |                   |     | 15                 | Ω    |
|  |                           | $V_{NO} = 0,$   |                             | 25°C |       |                   | 5   | 7                  |      |
|  |                           | $I_{COM} = 30 \text{ mA}$   |                             | Full |       |                   |     | 7                  |      |
| ON-state resistance                              | r                         | $V_{NO} = 2.4 V,$   | Switch ON,                  | 25°C | 45 V  |                   | 6   | 12                 | Ω    |
|  | on                        | $I_{COM} = -30 \text{ mA}$  | See Figure 13               | Full | 4.5 V |                   |     | 12                 |      |
|  |                           | $V_{NO} = 4.5 V,$   |                             | 25°C |       |                   | 7   | 15                 |      |
|  |                           | $I_{COM} = -30 \text{ mA}$  |                             | Full |       |                   |     | 15                 |      |
| ON-state resistance<br>match between<br>channels | ∆r <sub>on</sub>          | $V_{NO} = 3.15 V,$<br>$I_{COM} = -30 mA,$   | Switch ON,<br>See Figure 13 | 25°C | 4.5 V |                   | 0.1 |                    | Ω    |
| ON-state<br>resistance flatness                  | r <sub>on(flat)</sub>     | $\begin{array}{l} 0 \leq V_{\rm NO} \leq V_{+}, \\ I_{\rm COM} = -30 \ {\rm mA}, \end{array}$ | Switch ON,<br>See Figure 13 | 25°C | 5 V   |                   | 6.5 |                    | Ω    |
| NO   |                           | $V_{NO} = 0$ to $V_{+}$ ,   | Switch OFF,                 | 25°C | E E V | -0.1              |     | 0.1                | μA   |
| OFF leakage current                              | INO(OFF)                  | $V_{COM} = V_{+}$ to 0  | See Figure 14               | Full | 5.5 V | -1                |     | 1                  |      |
| СОМ  | 1                         | $V_{COM} = 0$ to $V_+$ ,  | Switch OFF,                 | 25°C | 0     | -0.1              |     | 0.1                | ۸    |
| OFF leakage current                              | COM(OFF)                  | $V_{NO} = V_+$ to 0,  | See Figure 14               | Full | 0     | -1                |     | 1                  | μΑ   |
| NO   | 1                         | $V_{NO} = 0$ to $V_{+}$ ,   | Switch ON,                  | 25°C | E E V | -0.1              |     | 0.1                | ۸    |
| ON leakage current                               | NO(ON)                    | V <sub>COM</sub> = Open,  | See Figure 14               | Full | 5.5 V | -1                |     | 1                  | μΑ   |
| СОМ  | 1                         | V <sub>NO</sub> = Open,   | Switch ON,                  | 25°C | 5 5 V | -0.1              |     | 0.1                | ۸    |
| ON leakage current                               | COM(ON)                   | $V_{COM} = 0$ to $V_+$ ,  | See Figure 14               | Full | 5.5 V | -1                |     | 1                  | μΑ   |
| <b>Digital Control Input</b>                     | s (IN1, IN2) <sup>(</sup> | 2)  |                             |      |       |                   |     |                    |      |
| Input logic high                                 | V <sub>IH</sub>           |   |                             | Full |       | $V_{+} 	imes 0.7$ |     | 5.5                | V    |
| Input logic low                                  | V <sub>IL</sub>           |   |                             | Full |       | 0                 |     | $V_{+} \times 0.3$ | V    |
| Input leakage                                    | las la                    | $V_{\rm c} = 5.5 V_{\rm or} 0$  | 25°C                        | 55.  |       |                   | 0.1 | ıιΔ                |      |
| current  | ıH, ıL                    | vj = 3.5 v 0i 0   |                             | Full | 5.5 V |                   |     | 1                  | μΛ   |

(1) The algebraic convention, whereby the most negative value is a minimum and the most positive value is a maximum

(2) All unused digital inputs of the device must be held at V<sub>+</sub> or GND to ensure proper device operation. Refer to the TI application report, *Implications of Slow or Floating CMOS Inputs*, literature number SCBA004.

SCDS177A-OCTOBER 2004-REVISED DECEMBER 2007



# **ELECTRICAL CHARACTERISTICS FOR 5-V SUPPLY (continued)**

 $V_{+}$  = 4.5 V to 5.5 V,  $T_{A}$  = –40°C to 85°C (unless otherwise noted)

| PARAMETER                    | SYMBOL                | TEST CO  | NDITIONS                     | T <sub>A</sub> | V.             | MIN | TYP  | MAX | UNIT |
|------------------------------|-----------------------|--|------------------------------|----------------|----------------|-----|------|-----|------|
| Dynamic                      |                       |  |                              |                |                |     |      |     |      |
| Turne an time a              |                       | $V_{NO} = V_{+}$ or GND,                                   | $C_{1} = 50 \text{ pF},$     | 25°C           | 5 V            | 1.5 |      | 6.5 |      |
| rum-on time                  | LON                   | $R_L = 500 \Omega$ ,                                       | See Figure 16                | Full           | 4.5 V to 5.5 V | 1.5 |      | 7   | ns   |
| Turne off times              |                       | $V_{NO} = V_{+}$ or GND,                                   | $C_{1} = 50 \text{ pF},$     | 25°C           | 5 V            | 0.8 |      | 3.7 |      |
| Turn-off time                | <sup>I</sup> OFF      | $R_L = 500 \Omega$ ,                                       | See Figure 16                | Full           | 4.5 V to 5.5 V | 0.8 |      | 7   | ns   |
| Break-before-                |                       | $V_{NO} = V_+,$  | $C_{L} = 50 \text{ pF},$     | 25°C           | 5 V            | 0.5 |      |     | 20   |
| make time                    | LBBM                  | $R_L = 50 \Omega$ ,  | See Figure 17                | Full           | 4.5 V to 5.5 V | 0.5 |      |     | ns   |
| Charge injection             | Q <sub>C</sub>        | V <sub>GEN</sub> = 0,<br>C <sub>L</sub> = 0.1 nF,          | See Figure 21                | 25°C           | 5 V            |     | 3.4  |     | рС   |
| NO<br>OFF capacitance        | C <sub>NO(OFF)</sub>  | $V_{NO} = V_{+} \text{ or GND},$<br>Switch OFF,            | See Figure 15                | 25°C           | 5 V            |     | 4.5  |     | pF   |
| COM<br>OFF capacitance       | C <sub>COM(OFF)</sub> | $V_{NO} = V_+ \text{ or GND},$<br>Switch OFF,              | See Figure 15                | 25°C           | 5 V            |     | 10.5 |     | pF   |
| NO<br>ON capacitance         | C <sub>NO(ON)</sub>   | $V_{NO} = V_{+}$ or GND,<br>Switch ON,                     | See Figure 15                | 25°C           | 5 V            |     | 17   |     | pF   |
| COM<br>ON capacitance        | C <sub>COM(ON)</sub>  | V <sub>COM</sub> = V <sub>+</sub> or<br>GND,<br>Switch ON, | See Figure 15                | 25°C           | 5 V            |     | 17   |     | pF   |
| Digital input<br>capacitance | Cl                    | $V_I = V_+ \text{ or } GND,$                               | See Figure 15                | 25°C           | 5 V            |     | 3    |     | pF   |
| Bandwidth                    | BW                    | $R_L = 50 \Omega$ ,<br>Switch ON,                          | See Figure 18                | 25°C           | 4.5 V to 5.5 V |     | 334  |     | MHz  |
| OFF isolation                | O <sub>ISO</sub>      | $R_L = 50 \Omega,$<br>f = 10 MHz,                          | Switch OFF,<br>See Figure 19 | 25°C           | 4.5 V to 5.5 V |     | -82  |     | dB   |
| Crosstalk                    | X <sub>TALK</sub>     | $R_L = 50 \Omega,$<br>f = 10 MHz,                          | Switch ON,<br>See Figure 20  | 25°C           | 4.5 V to 5.5 V |     | -62  |     | dB   |
| Supply                       |                       |  |                              |                |                |     |      |     |      |
| Positive supply              | 1                     | Swit   | Switch ON or                 | 25°C           | 5.5.V          |     |      | 1   | ۸    |
| current                      | <sup>1</sup> +        | $v_{\parallel} = v_{+} \cup U \cup U \cup U$               | OFF                          | Full           | 5.5 V          |     |      | 10  | μА   |

4

Copyright © 2004–2007, Texas Instruments Incorporated

SCDS177A-OCTOBER 2004-REVISED DECEMBER 2007

#### ELECTRICAL CHARACTERISTICS FOR 3.3-V SUPPLY<sup>(1)</sup>

 $V_{\star}$  = 3 V to 3.6 V,  $T_{A}$  = –40°C to 85°C (unless otherwise noted)

| PARAMETER  | SYMBOL                          | TEST C   | ONDITIONS                                | T <sub>A</sub>            | ۷.          | MIN                | TYP MAX            | UNIT |     |  |
|--|---------------------------------|--|--|---------------------------|-------------|--------------------|--------------------|------|-----|--|
| Analog Switch                                    |                                 | 1  |  |                           |             |                    |                    |      |     |  |
| Analog signal range                              | $V_{COM}, V_{NO}$               |  |  |                           |             | 0                  | V <sub>+</sub>     | V    |     |  |
| Peak ON resistance                               | r <sub>peak</sub>               | $0 \le V_{NO} \le V_+,$<br>$I_{COM} = -24 \text{ mA},$ | Switch ON,<br>See <mark>Figure 13</mark> | Full                      | 3 V         |                    | 25                 | Ω    |     |  |
|  |                                 | $V_{NO} = 0 V,$  |  | 25°C                      |             |                    | 6.5 9              |      |     |  |
| ON-state resistance                              | r                               | $I_{COM} = 24 \text{ mA}$                              | Switch ON,                               | Full                      | 3 \/        |                    | 9                  | 0    |     |  |
|  | on                              | $V_{NO} = 3 V,$  | See Figure 13                            | 25°C                      | 5 v         |                    | 9 20               | 12   |     |  |
|  |                                 | $I_{COM} = -24 \text{ mA}$                             |  | Full                      |             |                    | 20                 |      |     |  |
| ON-state resistance<br>match between<br>channels | ∆r <sub>on</sub>                | V <sub>NO</sub> = 2.1 V,<br>I <sub>COM</sub> = -24 mA, | Switch ON,<br>See Figure 13              | 25°C                      | 3 V         |                    | 0.1                | Ω    |     |  |
| ON-state<br>resistance flatness                  | r <sub>on(flat)</sub>           | $0 \le V_{NO} \le V_+,$<br>$I_{COM} = -24 \text{ mA},$ | Switch ON,<br>See Figure 13              | 25°C                      | 3.3 V       |                    | 13.5               | Ω    |     |  |
| NO   |                                 | I  | hieross                                  | $V_{NO} = 0$ to $V_{+}$ , | Switch OFF, | 25°C               | 361/               | -0.1 | 0.1 |  |
| OFF leakage current                              | NO(OFF)                         | $V_{COM} = V_+$ to 0 See Figure 14                     | See Figure 14                            | Full                      | 3.0 V       | -1                 | 1                  | μ.,  |     |  |
| СОМ  | 1                               | $V_{COM} = 0$ to $V_+$ ,                               | Switch OFF,                              | 25°C                      | 261/        | -0.1               | 0.1                |      |     |  |
| OFF leakage current                              | COM(OFF)                        | $V_{NO} = V_+$ to 0,                                   | See Figure 14                            | Full                      | 3.0 V       | -1                 | 1                  | μА   |     |  |
| NO   |                                 | $V_{NO} = 0$ to $V_{+}$ ,                              | Switch ON,                               | 25°C                      | 261/        | -0.1               | 0.1                |      |     |  |
| ON leakage current                               | NO(ON)                          | $V_{COM} = V_{+}$ to 0,                                | See Figure 14                            | Full                      | 3.0 V       | -1                 | 1                  | μА   |     |  |
| СОМ  |                                 | V <sub>NO</sub> = Open,                                | Switch ON,                               | 25°C                      | 261/        | -0.1               | 0.1                |      |     |  |
| ON leakage current                               | COM(ON)                         | $V_{COM} = 0$ to $V_+$ ,                               | See Figure 14                            | Full                      | 3.0 V       | -1                 | 1                  | μΑ   |     |  |
| Digital Control Input                            | s (IN1, IN2)                    | (2)  |  |                           |             |                    |                    |      |     |  |
| Input logic high                                 | V <sub>IH</sub>                 |  |  | Full                      |             | $V_{+} \times 0.7$ | 5.5                | V    |     |  |
| Input logic low                                  | VIL                             |  |  | Full                      |             | 0                  | $V_{+} \times 0.3$ | V    |     |  |
| Input leakage                                    |                                 |  | 25°C                                     |                           | -1          | 0.1                | μA                 |      |     |  |
| current  | ι <sub>Η</sub> , ι <sub>Γ</sub> | vi = 5.5 v 0i 0  |  | Full                      | 3.0 V       |                    | 1                  | μΑ   |     |  |

(1) The algebraic convention, whereby the most negative value is a minimum and the most positive value is a maximum

 (2) All unused digital inputs of the device must be held at V<sub>+</sub> or GND to ensure proper device operation. Refer to the TI application report, Implications of Slow or Floating CMOS Inputs, literature number SCBA004.

SCDS177A-OCTOBER 2004-REVISED DECEMBER 2007



# **ELECTRICAL CHARACTERISTICS FOR 3.3-V SUPPLY (continued)**

 $V_{\star}$  = 3 V to 3.6 V,  $T_{A}$  = –40°C to 85°C (unless otherwise noted)

| PARAMETER                    | SYMBOL                | TEST CO  | ONDITIONS                    | T <sub>A</sub> | V.           | MIN | TYP  | MAX | UNIT |
|------------------------------|-----------------------|--|------------------------------|----------------|--------------|-----|------|-----|------|
| Dynamic                      |                       | ·  |                              |                |              |     |      |     |      |
|                              |                       | $V_{NO} = V_{+} \text{ or}$                                | $C_{\rm L} = 50  \rm pF$     | 25°C           | 3.3 V        | 2   |      | 9.5 |      |
| Turn-on time                 | t <sub>ON</sub>       | GND,<br>R <sub>L</sub> = 500 Ω,                            | See Figure 16                | Full           | 3 V to 3.6 V | 2   |      | 11  | ns   |
|                              | _                     | $V_{NO} = V_{+}$ or  | $C_{L} = 50 \text{ pF}.$     | 25°C           | 3.3 V        | 1.3 |      | 5.1 |      |
| I urn-off time               | tOFF                  | GND,<br>R <sub>L</sub> = 500 Ω,                            | See Figure 16                | Full           | 3 V to 3.6 V | 1.5 |      | 5.5 | ns   |
| Break-before-                | <b>t</b>              | $V_{NO} = V_+,$  | C <sub>L</sub> = 50 pF,      | 25°C           | 3.3 V        | 0.5 |      |     | nc   |
| make time                    | <sup>4</sup> BBM      | $R_L = 50 \Omega$ ,  | See Figure 17                | Full           | 3 V to 3.6 V | 0.5 |      |     | 115  |
| Charge injection             | Q <sub>C</sub>        | V <sub>GEN</sub> = 0,<br>C <sub>L</sub> = 0.1 nF,          | See Figure 21                | 25°C           | 3.3 V        |     | 1.75 |     | рС   |
| NO<br>OFF capacitance        | C <sub>NO(OFF)</sub>  | V <sub>NO</sub> = V <sub>+</sub> or<br>GND,<br>Switch OFF, | See Figure 15                | 25°C           | 3.3 V        |     | 4.5  |     | pF   |
| COM<br>OFF capacitance       | C <sub>COM(OFF)</sub> | V <sub>NO</sub> = V <sub>+</sub> or<br>GND,<br>Switch OFF, | See Figure 15                | 25°C           | 3.3 V        |     | 10.5 |     | pF   |
| NO<br>ON capacitance         | C <sub>NO(ON)</sub>   | V <sub>NO</sub> = V <sub>+</sub> or<br>GND,<br>Switch ON,  | See Figure 15                | 25°C           | 3.3 V        |     | 17   |     | pF   |
| COM<br>ON capacitance        | C <sub>COM(ON)</sub>  | V <sub>COM</sub> = V <sub>+</sub> or<br>GND,<br>Switch ON, | See Figure 15                | 25°C           | 3.3 V        |     | 17   |     | pF   |
| Digital input<br>capacitance | CI                    | $V_I = V_+ \text{ or GND},$                                | See Figure 15                | 25°C           | 3.3 V        |     | 3    |     | pF   |
| Bandwidth                    | BW                    | $R_L = 50 \Omega$ ,<br>Switch ON,                          | See Figure 18                | 25°C           | 3 V to 3.6 V |     | 327  |     | MHz  |
| OFF isolation                | O <sub>ISO</sub>      | $R_L = 50 \Omega,$<br>f = 10 MHz,                          | Switch OFF,<br>See Figure 19 | 25°C           | 3 V to 3.6 V |     | -82  |     | dB   |
| Crosstalk                    | X <sub>TALK</sub>     | $R_L = 50 \Omega$ ,<br>f = 10 MHz,                         | Switch ON,<br>See Figure 20  | 25°C           | 3 V to 3.6 V |     | -62  |     | dB   |
| Supply                       |                       |  |                              |                |              |     |      |     |      |
| Positive supply              | Positive supply       |  | Switch ON or OFF             | 25°C           | 361/         |     |      | 1   |      |
| current                      | '+                    | $v_1 = v_+ \text{ or GND},$                                | Switch ON OFF                | Full           | 5.0 v        |     |      | 10  | μл   |

6

SCDS177A-OCTOBER 2004-REVISED DECEMBER 2007

#### **ELECTRICAL CHARACTERISTICS FOR 2.5-V SUPPLY**<sup>(1)</sup>

 $V_{\star}$  = 2.3 V to 2.7 V,  $T_{A}$  = –40°C to 85°C (unless otherwise noted)

| PARAMETER   | SYMBOL   | TEST CO  | ONDITIONS                   | T <sub>A</sub> | ۷,    | MIN                | TYP | MAX                        | UNIT |
|---|--|--|-----------------------------|----------------|-------|--------------------|-----|----------------------------|------|
| Analog Switch                                       |  |  |                             |                |       |                    |     |                            |      |
| Analog signal<br>range                              | $V_{COM}, V_{NO}$                              |  |                             |                |       | 0                  |     | V <sub>+</sub>             | V    |
| Peak ON<br>resistance                               | r <sub>peak</sub>                              | $\begin{array}{l} 0 \leq V_{\rm NO} \leq V_+, \\ I_{\rm COM} = -8 \ {\rm mA}, \end{array}$   | Switch ON,<br>See Figure 13 | Full           | 2.3 V |                    |     | 50                         | Ω    |
|   |  | $V_{NO} = 0 V,$  |                             | 25°C           |       |                    | 8   | 12                         |      |
| ON-state  | r  | I <sub>COM</sub> = 8 mA  | Switch ON,                  | Full           | 221/  |                    |     | 12                         | 0    |
| resistance  | Ion  | $V_{NO} = 2.3 V,$<br>$I_{COM} = -8 mA$   | See Figure 13               | 25°C           | 2.3 V |                    | 11  | 30                         | 12   |
|   |  |  |                             | Full           |       |                    |     | 30                         |      |
| ON-state<br>resistance<br>match between<br>channels | ∆r <sub>on</sub>                               | V <sub>NO</sub> = 1.8 V,<br>I <sub>COM</sub> = -8 mA,  | Switch ON,<br>See Figure 13 | 25°C           | 2.3 V |                    | 0.3 |                            | Ω    |
| ON-state<br>resistance flatness                     | r <sub>on(flat)</sub>                          | $\begin{array}{l} 0 \leq V_{\rm NO} \leq V_{+}, \\ I_{\rm COM} = -8 \ {\rm mA}, \end{array}$ | Switch ON,<br>See Figure 13 | 25°C           | 2.5 V |                    | 39  |                            | Ω    |
| NO  |  | $V_{\rm No} = 0$ to V  | Switch OFF                  | 25°C           |       | -0.1               |     | 0.1                        | μA   |
| OFF leakage<br>current                              | I <sub>NO(OFF)</sub>                           | $V_{\text{COM}} = V_+ \text{ to } 0$   | See Figure 14               | Full           | 2.7 V | -1                 |     | 1                          |      |
| COM   |  | $V_{COM} = 0$ to $V_{+}$ .   | Switch OFF.                 | 25°C           | 0714  | -0.1               |     | 0.1                        |      |
| OFF leakage<br>current                              | ICOM(OFF)                                      | $V_{\rm NO} = V_+$ to 0,   | See Figure 14               | Full           | 2.7 V | -1                 |     | 1                          | μΑ   |
| NO  |  | $V_{NO} = 0$ to $V_{+}$ .  | Switch ON.                  | 25°C           | 071   | -0.1               |     | 0.1                        |      |
| ON leakage<br>current                               | I <sub>NO(ON)</sub>                            | $V_{COM} = V_+$ to 0,  | See Figure 14               | Full           | 2.7 V | -1                 |     | 1                          | μΑ   |
| COM   |  | V <sub>NO</sub> = Open.  | Switch ON.                  | 25°C           | \ /   | -0.1               |     | 0.1                        |      |
| ON leakage<br>current                               | I <sub>COM(ON)</sub>                           | $V_{COM} = 0$ to $V_+$ ,   | See Figure 14               | Full           | 2.7 V | -1                 |     | 1                          | μA   |
| <b>Digital Control Inp</b>                          | uts (IN1, IN2                                  | ) <sup>(2)</sup>   |                             |                |       |                    |     |                            |      |
| Input logic high                                    | VIH  |  |                             | Full           |       | $V_{+} 	imes 0.75$ |     | 5.5                        | V    |
| Input logic low                                     | V <sub>IL</sub>                                |  |                             | Full           |       | 0                  |     | $V_{\text{+}} \times 0.25$ | V    |
| Input leakage                                       | $I_{IH}, I_{IL}$ $V_{I} = 5.5 V \text{ or } 0$ |  | 25°C                        | 2.7 V          |       |                    | 0.1 | μA                         |      |
| current   |  | $V_1 = 5.5 V \text{ or } 0$  |                             | Full           | 2.1 V |                    |     | 1                          | · ·  |

(1) The algebraic convention, whereby the most negative value is a minimum and the most positive value is a maximum

 (2) All unused digital inputs of the device must be held at V<sub>+</sub> or GND to ensure proper device operation. Refer to the TI application report, Implications of Slow or Floating CMOS Inputs, literature number SCBA004.

SCDS177A-OCTOBER 2004-REVISED DECEMBER 2007



# **ELECTRICAL CHARACTERISTICS FOR 2.5-V SUPPLY (continued)**

 $V_{+}$  = 2.3 V to 2.7 V,  $T_{A}$  = –40°C to 85°C (unless otherwise noted)

| PARAMETER                    | SYMBOL                | TEST CO  | NDITIONS                     | TA   | V.             | MIN | TYP  | MAX  | UNIT |
|------------------------------|-----------------------|--|------------------------------|------|----------------|-----|------|------|------|
| Dynamic                      |                       |  |                              |      |                |     |      |      |      |
|                              |                       | $V_{NO} = V_{+} \text{ or}$  | $C_{\rm L} = 50  \rm pF$     | 25°C | 2.5 V          | 3   |      | 15   |      |
| Turn-on time                 | t <sub>ON</sub>       | GND,<br>R <sub>L</sub> = 500 Ω,                                      | See Figure 16                | Full | 2.3 V to 2.7 V | 3   |      | 16.5 | ns   |
|                              |                       | $V_{NO} = V_{+}$ or  | $C_{L} = 50 \text{ pF}.$     | 25°C | 2.5 V          | 2   |      | 7.2  |      |
| Turn-off time                | t <sub>OFF</sub>      | GND,<br>R <sub>L</sub> = 500 Ω,                                      | See Figure 16                | Full | 2.3 V to 2.7 V | 2   |      | 7.8  | ns   |
| Break-before-                | 4                     | $V_{NO} = V_+,$  | C <sub>L</sub> = 50 pF,      | 25°C | 2.5 V          | 0.5 |      |      | 20   |
| make time                    | <sup>I</sup> BBM      | $R_L = 50 \Omega$ ,  | See Figure 17                | Full | 2.3 V to 2.7 V | 0.5 |      |      | 115  |
| Charge<br>injection          | Q <sub>C</sub>        | V <sub>GEN</sub> = 0,<br>C <sub>L</sub> = 0.1 nF,                    | See Figure 21                | 25°C | 2.5 V          |     | 1.15 |      | рС   |
| NO<br>OFF capacitance        | $C_{NO(OFF)}$         | V <sub>NO</sub> = V <sub>+</sub> or<br>GND,<br>Switch OFF,           | See Figure 15                | 25°C | 2.5 V          |     | 4.5  |      | pF   |
| COM<br>OFF capacitance       | C <sub>COM(OFF)</sub> | V <sub>NO</sub> = V <sub>+</sub> or<br>GND,<br>Switch OFF,           | See Figure 15                | 25°C | 2.5 V          |     | 10.5 |      | pF   |
| NO<br>ON capacitance         | C <sub>NO(ON)</sub>   | $V_{NO} = V_+ \text{ or}$<br>GND,<br>Switch ON,                      | See Figure 15                | 25°C | 2.5 V          |     | 17   |      | pF   |
| COM<br>ON capacitance        | C <sub>COM(ON)</sub>  | V <sub>COM</sub> = V <sub>+</sub> or<br>GND,<br>Switch ON,           | See Figure 15                | 25°C | 2.5 V          |     | 17   |      | pF   |
| Digital input<br>capacitance | CI                    | $V_1 = V_+ \text{ or GND},$  | See Figure 15                | 25°C | 2.5 V          |     | 3    |      | pF   |
| Bandwidth                    | BW                    | $R_L = 50 \Omega$ ,<br>Switch ON,                                    | See Figure 18                | 25°C | 2.3 V to 2.7 V |     | 320  |      | MHz  |
| OFF isolation                | O <sub>ISO</sub>      | $\begin{array}{l} R_{L} = 50 \ \Omega, \\ f = 10 \ MHz, \end{array}$ | Switch OFF,<br>See Figure 19 | 25°C | 2.3 V to 2.7 V |     | -81  |      | dB   |
| Crosstalk                    | X <sub>TALK</sub>     | $\begin{array}{l} R_{L} = 50 \ \Omega, \\ f = 10 \ MHz, \end{array}$ | Switch ON,<br>See Figure 20  | 25°C | 2.3 V to 2.7 V |     | -61  |      | dB   |
| Supply                       |                       |  |                              |      |                |     |      |      |      |
| Positive supply              |                       |  | Switch ON or                 | 25°C | 271            |     |      | 1    |      |
| current                      | '+                    | $v_1 = v_+ \text{ or GND},$  | OFF                          | Full | 2.1 V          |     |      | 10   | μΛ   |

8

SCDS177A-OCTOBER 2004-REVISED DECEMBER 2007

#### **ELECTRICAL CHARACTERISTICS FOR 1.8-V SUPPLY**<sup>(1)</sup>

 $V_{+} = 1.65$  V to 1.95 V,  $T_{A} = -40^{\circ}$ C to 85°C (unless otherwise noted)

| PARAMETER   | SYMBOL  | TEST CO  | ONDITIONS                   | TA     | ٧,      | MIN                | TYP | MAX                        | UNIT |
|---|---|--|-----------------------------|--------|---------|--------------------|-----|----------------------------|------|
| Analog Switch                                       |   | ·  |                             |        |         | ·                  |     |                            |      |
| Analog signal<br>range                              | V <sub>COM</sub> , V <sub>NO</sub>                            |  |                             |        |         | 0                  |     | V <sub>+</sub>             | V    |
| Peak ON<br>resistance                               | r <sub>peak</sub>   | $0 \le V_{NO} \le V_+,$<br>$I_{COM} = -4 \text{ mA},$  | Switch ON,<br>See Figure 13 | Full   | 1.65 V  |                    |     | 150                        | Ω    |
|   |   | $V_{NO} = 0 V,$  |                             | 25°C   |         |                    | 10  | 20                         |      |
| ON-state  | r   | $I_{COM} = 4 \text{ mA}$   | Switch ON,                  | Full   | 1.65.\/ |                    |     | 20                         | 0    |
| resistance  | on  | $V_{NO} = 1.8 V,$  | See Figure 13               | 25°C   | 1.05 V  |                    | 17  | 50                         | 12   |
|   |   | $I_{COM} = -4 \text{ mA}$  |                             | Full   |         |                    |     | 50                         |      |
| ON-state<br>resistance<br>match between<br>channels | Δr <sub>on</sub>  | V <sub>NO</sub> = 1.15 V,<br>I <sub>COM</sub> = -4 mA,                                       | Switch ON,<br>See Figure 13 | 25°C   | 1.65 V  |                    | 0.3 |                            | Ω    |
| ON-state<br>resistance flatness                     | r <sub>on(flat)</sub>   | $\begin{array}{l} 0 \leq V_{\rm NO} \leq V_{+}, \\ I_{\rm COM} = -4 \ {\rm mA}, \end{array}$ | Switch ON,<br>See Figure 13 | 25°C   | 1.8 V   |                    | 140 |                            | Ω    |
| NO  | _   | $V_{NO} = 0$ to $V_{L}$  | Switch OFF.                 | 25°C   |         | -0.1               |     | 0.1                        |      |
| OFF leakage<br>current                              | I <sub>NO(OFF)</sub>  | $V_{COM} = V_+$ to 0   | See Figure 14               | Full   | 1.95 V  | -1                 |     | 1                          | μA   |
| COM   |   | $V_{COM} = 0$ to $V_{+}$ .   | Switch OFF.                 | 25°C   | 4.05.14 | -0.1               |     | 0.1                        |      |
| OFF leakage<br>current                              | ICOM(OFF)   | $V_{NO} = V_+$ to 0,   | See Figure 14               | Full   | 1.95 V  | -1                 |     | 1                          | μA   |
| NO  |   | $V_{NO} = 0$ to $V_{L}$  | Switch ON.                  | 25°C   |         | -0.1               |     | 0.1                        |      |
| ON leakage<br>current                               | I <sub>NO(ON)</sub>   | $V_{COM} = V_+$ to 0,  | See Figure 14               | Full   | 1.95 V  | -1                 |     | 1                          | μA   |
| COM   |   | V <sub>NO</sub> = Open.  | Switch ON.                  | 25°C   |         | -0.1               |     | 0.1                        |      |
| ON leakage<br>current                               | I <sub>COM(ON)</sub>  | $V_{COM} = 0$ to $V_+$ ,   | See Figure 14               | Full   | 1.95 V  | -1                 |     | 1                          | μA   |
| <b>Digital Control Inp</b>                          | uts (IN1, IN2   | ) <sup>(2)</sup>   |                             |        |         |                    |     |                            |      |
| Input logic high                                    | VIH   |  |                             | Full   |         | $V_{+} 	imes 0.75$ |     | 5.5                        | V    |
| Input logic low                                     | V <sub>IL</sub>   |  |                             | Full   |         | 0                  |     | $V_{\text{+}} \times 0.25$ | V    |
| Input leakage                                       | iput leakage $l_{\rm H}$ $l_{\rm H}$ $V_{\rm r}$ = 5.5 V or 0 | :  | 25°C                        | 1 95 V |         |                    | 0.1 | ıιΔ                        |      |
| current   | surrent   |  |                             | Full   | 1.35 V  |                    |     | 1                          | μΛ   |

(1) The algebraic convention, whereby the most negative value is a minimum and the most positive value is a maximum

 (2) All unused digital inputs of the device must be held at V<sub>+</sub> or GND to ensure proper device operation. Refer to the TI application report, Implications of Slow or Floating CMOS Inputs, literature number SCBA004.

SCDS177A-OCTOBER 2004-REVISED DECEMBER 2007



## **ELECTRICAL CHARACTERISTICS FOR 1.8-V SUPPLY (continued)**

 $V_{+}$  = 1.65 V to 1.95 V,  $T_{A}$  =  $-40^{\circ}C$  to 85°C (unless otherwise noted)

| PARAMETER                    | SYMBOL  | TEST CON  | T <sub>A</sub>                           | ۷.                  | MIN                 | TYP | MAX  | UNIT |     |
|------------------------------|---|---|--|---------------------|---------------------|-----|------|------|-----|
| Dynamic                      |   | 1   |  |                     |                     |     |      |      |     |
| Turn-on time                 |   | $V_{NO} = V_{+} \text{ or GND},$<br>$R_{L} = 500 \Omega,$ | C <sub>L</sub> = 50 pF,<br>See Figure 16 | 25°C                | 1.8 V               | 5   |      | 32   |     |
|                              | t <sub>ON</sub>                                   |   |  | Full                | 1.65 V to<br>1.95 V | 5   |      | 34   | ns  |
|                              |   | $V_{NO} = V_{+} \text{ or GND},$<br>$R_{L} = 500 \Omega,$ | C <sub>L</sub> = 50 pF,<br>See Figure 16 | 25°C                | 1.8 V               | 3   |      | 14   |     |
| Turn-off time                | t <sub>OFF</sub>                                  |   |  | Full                | 1.65 V to<br>1.95 V | 3   |      | 14.5 | ns  |
| Dreek hefere                 |   |   | 0 50 -5                                  | 25°C                | 1.8 V               | 0.5 |      |      |     |
| Break-before-<br>make time   | $v_{\rm NO} = v_+,$<br>$R_{\rm L} = 50 \ \Omega,$ | C <sub>L</sub> = 50 pF,<br>See Figure 17                  | Full                                     | 1.65 V to<br>1.95 V | 0.5                 |     |      | ns   |     |
| Charge<br>injection          | Q <sub>C</sub>                                    | $V_{GEN} = 0,$<br>$C_L = 0.1 \text{ nF},$                 | See Figure 21                            | 25°C                | 1.8 V               |     | 0.3  |      | рС  |
| NO<br>OFF capacitance        | C <sub>NO(OFF)</sub>                              | $V_{NO} = V_{+} \text{ or GND},$<br>Switch OFF,           | See Figure 15                            | 25°C                | 1.8 V               |     | 4.5  |      | pF  |
| COM<br>OFF capacitance       | C <sub>COM(OFF)</sub>                             | $V_{NO} = V_{+} \text{ or GND},$<br>Switch OFF,           | See Figure 15                            | 25°C                | 1.8 V               |     | 10.5 |      | pF  |
| NO<br>ON capacitance         | C <sub>NO(ON)</sub>                               | $V_{NO} = V_{+} \text{ or GND},$<br>Switch ON,            | See Figure 15                            | 25°C                | 1.8 V               |     | 17   |      | pF  |
| COM<br>ON capacitance        | C <sub>COM(ON)</sub>                              | $V_{COM} = V_+ \text{ or GND},$<br>Switch ON,             | See Figure 15                            | 25°C                | 1.8 V               |     | 17   |      | pF  |
| Digital input<br>capacitance | CI  | $V_I = V_+ \text{ or } GND,$                              | See Figure 15                            | 25°C                | 1.8 V               |     | 3    |      | pF  |
| Bandwidth                    | BW  | $R_L = 50 \Omega$ ,<br>Switch ON,                         | See Figure 18                            | 25°C                | 1.65 V to<br>1.95 V |     | 341  |      | MHz |
| OFF isolation                | O <sub>ISO</sub>                                  | $R_L = 50 \Omega,$<br>f = 10 MHz,                         | Switch OFF,<br>See Figure 19             | 25°C                | 1.65 V to<br>1.95 V |     | 81   |      | dB  |
| Crosstalk                    | X <sub>TALK</sub>                                 | $R_L = 50 \Omega,$<br>f = 10 MHz,                         | Switch ON,<br>See Figure 20              | 25°C                | 1.65 V to<br>1.95 V |     | -61  |      | dB  |
| Supply                       | <u>u</u>  |   |  | •                   |                     |     |      |      |     |
| Positive supply              | 1   | $V_I = V_+$ or GND,                                       | Switch ON or<br>OFF                      | 25°C                | 1.05.1/             |     |      | 1    |     |
| current                      | I <sub>+</sub>                                    |   |  | Full                | 1.95 V              |     |      | 10   | μА  |



SCDS177A-OCTOBER 2004-REVISED DECEMBER 2007

**TYPICAL PERFORMANCE** 



SCDS177A-OCTOBER 2004-REVISED DECEMBER 2007



**TYPICAL PERFORMANCE (continued)** 



SCDS177A-OCTOBER 2004-REVISED DECEMBER 2007

#### **PIN DESCRIPTION**

| PIN NO. | NAME           | DESCRIPTION                          |
|---------|----------------|--------------------------------------|
| 1       | NO0            | Normally open                        |
| 2       | NO1            | Normally open                        |
| 3       | NO2            | Normally open                        |
| 4       | GND            | Digital ground                       |
| 5       | IN2            | Digital control to connect COM to NO |
| 6       | IN1            | Digital control to connect COM to NO |
| 7       | COM            | Common                               |
| 8       | V <sub>+</sub> | Power supply                         |

#### PARAMETER DESCRIPTION

| SYMBOL                            | DESCRIPTION  |  |  |  |  |  |  |
|-----------------------------------|--|--|--|--|--|--|--|
| V <sub>COM</sub>                  | Voltage at COM   |  |  |  |  |  |  |
| V <sub>NO</sub>                   | Voltage at NO  |  |  |  |  |  |  |
| r <sub>on</sub>                   | Resistance between COM and NC or COM and NO ports when the channel is ON   |  |  |  |  |  |  |
| r <sub>peak</sub>                 | Peak on-state resistance over a specified voltage range  |  |  |  |  |  |  |
| ∆r <sub>on</sub>                  | Difference of r <sub>on</sub> between channels in a specific device  |  |  |  |  |  |  |
| r <sub>on(flat)</sub>             | Difference between the maximum and minimum value of ron in a channel over the specified range of conditions  |  |  |  |  |  |  |
| I <sub>NO(OFF)</sub>              | Leakage current measured at the NO port, with the corresponding channel (NO to COM) in the OFF state   |  |  |  |  |  |  |
| I <sub>NO(ON)</sub>               | Leakage current measured at the NO port, with the corresponding channel (NO to COM) in the ON state and the output (COM) open  |  |  |  |  |  |  |
| I <sub>COM(ON)</sub>              | Leakage current measured at the COM port, with the corresponding channel (COM to NO or COM to NC) in the ON state and the output (NC or NO) open   |  |  |  |  |  |  |
| I <sub>COM(OFF)</sub>             | Leakage current measured at the COM port during the power-down condition, $V_{+} = 0$  |  |  |  |  |  |  |
| V <sub>IH</sub>                   | Minimum input voltage for logic high for the control input (IN)  |  |  |  |  |  |  |
| VIL                               | Maximum input voltage for logic low for the control input (IN)   |  |  |  |  |  |  |
| VI                                | Voltage at the control input (IN)  |  |  |  |  |  |  |
| I <sub>IH</sub> , I <sub>IL</sub> | Leakage current measured at the control input (IN)   |  |  |  |  |  |  |
| t <sub>ON</sub>                   | Turn-on time for the switch. This parameter is measured under the specified range of conditions and by the propagation delay between the digital control (IN) signal and analog output (COM or NO) signal when the switch is turning ON.   |  |  |  |  |  |  |
| t <sub>OFF</sub>                  | Turn-off time for the switch. This parameter is measured under the specified range of conditions and by the propagation delay between the digital control (IN) signal and analog output (COM or NO) signal when the switch is turning OFF.   |  |  |  |  |  |  |
| t <sub>BBM</sub>                  | Break-before-make time. This parameter is measured under the specified range of conditions and by the propagation delay between the output of two adjacent analog channels (NC and NO) when the control signal changes state.  |  |  |  |  |  |  |
| Q <sub>C</sub>                    | Charge injection is a measurement of unwanted signal coupling from the control (IN) input to the analog (NO or COM) output. This is measured in coulomb (C) and measured by the total charge induced due to switching of the control input. Charge injection, $Q_C = C_L \times \Delta V_{COM}$ , $C_L$ is the load capacitance and $\Delta V_{COM}$ is the change in analog output voltage. |  |  |  |  |  |  |
| C <sub>NO(OFF)</sub>              | Capacitance at the NO port when the corresponding channel (NO to COM) is OFF   |  |  |  |  |  |  |
| C <sub>NO(ON)</sub>               | Capacitance at the NO port when the corresponding channel (NO to COM) is ON  |  |  |  |  |  |  |
| C <sub>COM(ON)</sub>              | Capacitance at the COM port when the corresponding channel (COM to NO) is ON   |  |  |  |  |  |  |
| C <sub>COM(OFF)</sub>             | Capacitance at the COM port when the corresponding channel (COM to NO) is OFF  |  |  |  |  |  |  |
| Cl                                | Capacitance of control input (IN)  |  |  |  |  |  |  |
| O <sub>ISO</sub>                  | OFF isolation of the switch is a measurement of OFF-state switch impedance. This is measured in dB in a specific frequency, with the corresponding channel (NC to COM or NO to COM) in the OFF state.  |  |  |  |  |  |  |
| X <sub>TALK</sub>                 | Crosstalk is a measurement of unwanted signal coupling from an ON channel to an OFF channel (NC to NO or NO to NC). This is measured in a specific frequency and in dB.  |  |  |  |  |  |  |
| BW                                | Bandwidth of the switch. This is the frequency in which the gain of an ON channel is -3 dB below the DC gain.  |  |  |  |  |  |  |
| I+                                | Static power-supply current with the control (IN) pin at V <sub>+</sub> or GND   |  |  |  |  |  |  |

SCDS177A-OCTOBER 2004-REVISED DECEMBER 2007



Figure 13. ON-State Resistance (ron)



Figure 14. ON- and OFF-State Leakage Current (I<sub>COM(ON)</sub>, I<sub>COM(OFF)</sub>, I<sub>NO(ON)</sub>, I<sub>NO(OFF)</sub>)





RUMENTS



SCDS177A-OCTOBER 2004-REVISED DECEMBER 2007



## PARAMETER MEASUREMENT INFORMATION (continued)

- A. All input pulses are supplied by generators having the following characteristics: PRR  $\leq$  10 MHz, Z<sub>0</sub> = 50  $\Omega$ , t<sub>r</sub> < 5 ns, t<sub>f</sub> < 5 ns.
- B. C<sub>L</sub> includes probe and jig capacitance.





- A. All input pulses are supplied by generators having the following characteristics: PRR  $\leq$  10 MHz, Z<sub>O</sub> = 50  $\Omega$ , t<sub>r</sub> < 5 ns, t<sub>f</sub> < 5 ns.
- B. C<sub>L</sub> includes probe and jig capacitance.

#### Figure 17. Break-Before-Make Time (t<sub>BBM</sub>)



SCDS177A-OCTOBER 2004-REVISED DECEMBER 2007

#### PARAMETER MEASUREMENT INFORMATION (continued)



#### Figure 18. Bandwidth (BW)



#### Figure 19. OFF Isolation (O<sub>ISO</sub>)



#### Figure 20. Crosstalk (X<sub>TALK</sub>)



SCDS177A-OCTOBER 2004-REVISED DECEMBER 2007

### PARAMETER MEASUREMENT INFORMATION (continued)



A. All input pulses are supplied by generators having the following characteristics: PRR  $\leq$  10 MHz, Z<sub>O</sub> = 50  $\Omega$ , t<sub>r</sub> < 5 ns, t<sub>f</sub> < 5 ns.

B. C<sub>L</sub> includes probe and jig capacitance.

#### Figure 21. Charge Injection (Q<sub>c</sub>)

# PACKAGE MATERIALS INFORMATION

www.ti.com

Texas Instruments

### TAPE AND REEL INFORMATION





## QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



| *All dimensions are nominal |                 |                    |      |      |                          |                          |            |            |            |            |           |                  |
|-----------------------------|-----------------|--------------------|------|------|--------------------------|--------------------------|------------|------------|------------|------------|-----------|------------------|
| Device                      | Package<br>Type | Package<br>Drawing | Pins | SPQ  | Reel<br>Diameter<br>(mm) | Reel<br>Width<br>W1 (mm) | A0<br>(mm) | B0<br>(mm) | K0<br>(mm) | P1<br>(mm) | W<br>(mm) | Pin1<br>Quadrant |
| TS5A3357DCUR                | VSSOP           | DCU                | 8    | 3000 | 180.0                    | 8.4                      | 2.25       | 3.35       | 1.05       | 4.0        | 8.0       | Q3               |
| TS5A3357DCURG4              | VSSOP           | DCU                | 8    | 3000 | 180.0                    | 8.4                      | 2.25       | 3.35       | 1.05       | 4.0        | 8.0       | Q3               |

TEXAS INSTRUMENTS

www.ti.com

# PACKAGE MATERIALS INFORMATION

24-Nov-2017



\*All dimensions are nominal

| Device Package Type |       | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |  |
|---------------------|-------|-----------------|------|------|-------------|------------|-------------|--|
| TS5A3357DCUR        | VSSOP | DCU             | 8    | 3000 | 202.0       | 201.0      | 28.0        |  |
| TS5A3357DCURG4      | VSSOP | DCU             | 8    | 3000 | 202.0       | 201.0      | 28.0        |  |

DCU (R-PDSO-G8)

PLASTIC SMALL-OUTLINE PACKAGE (DIE DOWN)



NOTES: A. All linear dimensions are in millimeters.

B. This drawing is subject to change without notice.

C. Body dimensions do not include mold flash or protrusion. Mold flash and protrusion shall not exceed 0.15 per side.

D. Falls within JEDEC MO-187 variation CA.





- NOTES: A. All linear dimensions are in millimeters. В. This drawing is subject to change without notice.
  - C. Publication IPC-7351 is recommended for alternate designs.
  - D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525 for other stencil recommendations.
  - E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.



#### **IMPORTANT NOTICE**

Texas Instruments Incorporated (TI) reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete.

TI's published terms of sale for semiconductor products (http://www.ti.com/sc/docs/stdterms.htm) apply to the sale of packaged integrated circuit products that TI has qualified and released to market. Additional terms may apply to the use or sale of other types of TI products and services.

Reproduction of significant portions of TI information in TI data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such reproduced documentation. Information of third parties may be subject to additional restrictions. Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyers and others who are developing systems that incorporate TI products (collectively, "Designers") understand and agree that Designers remain responsible for using their independent analysis, evaluation and judgment in designing their applications and that Designers have full and exclusive responsibility to assure the safety of Designers' applications and compliance of their applications (and of all TI products used in or for Designers' applications) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to their applications, Designer has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any applications that include TI products, Designer will thoroughly test such applications and the functionality of such TI products as used in such applications.

TI's provision of technical, application or other design advice, quality characterization, reliability data or other services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using TI Resources in any way, Designer (individually or, if Designer is acting on behalf of a company, Designer's company) agrees to use any particular TI Resource solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

Designer is authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNER AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

Unless TI has explicitly designated an individual product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949 and ISO 26262), TI is not responsible for any failure to meet such industry standard requirements.

Where TI specifically promotes products as facilitating functional safety or as compliant with industry functional safety standards, such products are intended to help enable customers to design and create their own applications that meet applicable functional safety standards and requirements. Using products in an application does not by itself establish any safety features in the application. Designers must ensure compliance with safety-related requirements and standards applicable to their applications. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

TI may expressly designate certain products as completing a particular qualification (e.g., Q100, Military Grade, or Enhanced Product). Designers agree that it has the necessary expertise to select the product with the appropriate qualification designation for their applications and that proper product selection is at Designers' own risk. Designers are solely responsible for compliance with all legal and regulatory requirements in connection with such selection.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's noncompliance with the terms and provisions of this Notice.

> Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated