
Cree® XLamp® XP-G2 LEDs



XP-G2 Standard LED



XP-G2 High Efficacy LED

PRODUCT DESCRIPTION

The original XLamp® XP-G2 LED pioneered a broad set of LED applications for the industry, including outdoor and area lighting, and has since served as a preferred choice by manufacturers that require advanced output, efficacy and optical control. The compact and proven 3.45-mm XP platform has an excellent ecosystem of optics and system solutions available, enabling lighting manufacturers to simplify their design process and shorten time to market.

XP-G2 LEDs are now available in two different White versions: Standard and High Efficacy (HE). XP-G2 Standard is the same breakthrough product that enabled a broad set of new LED applications for ceramic high-power LEDs.

The new High Efficacy version extends this legacy with a drop-in upgrade for existing designs optimized around XP-G2 LEDs. XP-G2 HE LEDs leverage Cree's latest high-power chip technology to deliver 25 percent more light output via a higher maximum current of 2000 mA and higher efficacy and lower thermal resistance.

FEATURES

- Available in white, outdoor white and 80-, 85- and 90-CRI white
- ANSI-compatible chromaticity bins
- · Binned at 85 °C
- Maximum drive current: Standard: 1500 mA, HE: 2000 mA
- Low thermal resistance: Standard: 4 °C/W, HE: 3 °C/W
- Wide viewing angle: Standard: 120°, HE: 125°
- Unlimited floor life at ≤ 30 °C/85% RH
- · Reflow solderable JEDEC J-STD-020C
- Electrically neutral thermal path
- · RoHS and REACh compliant
- UL® recognized component (E349212)





TABLE OF CONTENTS

Characteristics	3
Flux Characteristics - High Efficacy	4
Flux Characteristics - Standard	9
Relative Spectral Power Distribution	15
Relative Flux vs. Junction Temperature	15
Electrical Characteristics - High Efficacy	16
Electrical Characteristics - Standard	16
Relative Flux vs. Current - High Efficacy	17
Relative Flux vs. Current - Standard	17
Relative Chromaticity vs Current and Temperature - High Efficacy	18
Relative Chromaticity vs Current and Temperature - Standard	19
Typical Spatial Distribution - High Efficacy	20
Typical Spatial Distribution - Standard	20
Thermal Design - High Efficacy	21
Thermal Design - Standard	21
Performance Groups – Luminous Flux	22
Performance Groups - Chromaticity	23
Cree's Standard Cool White Kits Plotted on ANSI Standard Chromaticity Regions	26
Cree's Standard Warm and Neutral White Kits Plotted on ANSI Standard Chromaticity Regions	28
Cree's Standard Chromaticity Kits	30
Bin and Order Code Formats	31
Reflow Soldering Characteristics	32
Notes	33
Mechanical Dimensions	35
Tape and Reel	37
Packaging	38



CHARACTERISTICS

Characteristics	Unit	Minimum	Typical	Maximum
Thermal resistance, junction to solder point - High Efficacy	°C/W		3	
Thermal resistance, junction to solder point - Standard	°C/W		4	
Viewing angle (FWHM) - High Efficacy	degrees		125	
Viewing angle (FWHM) - Standard	degrees		120	
Temperature coefficient of voltage - High Efficacy	mV/°C		-1.3	
Temperature coefficient of voltage - Standard	mV/°C		-1.4	
ESD withstand voltage (HBM per Mil-Std-883D)	٧			8000
DC forward current - High Efficacy	mA			2000
DC forward current - Standard	mA			1500
Reverse voltage	V			5
Forward voltage (@ 350 mA, 85 °C) - High Efficacy	٧		2.70	2.90
Forward voltage (@ 350 mA, 85 °C) - Standard	V		2.74	3.1
Forward voltage (@ 700 mA, 85 °C) - High Efficacy	٧		2.80	
Forward voltage (@ 700 mA, 85 °C) - Standard	V		2.85	
Forward voltage (@ 1000 mA, 85 °C) - High Efficacy	٧		2.87	
Forward voltage (@ 1000 mA, 85 °C) - Standard	V		2.93	
Forward voltage (@ 1500 mA, 85 °C) - High Efficacy	٧		2.97	
Forward voltage (@ 1500 mA, 85 °C) - Standard	V		3.1	
LED junction temperature	°C			150



FLUX CHARACTERISTICS - HIGH EFFICACY (T, = 85 °C)

The following table provides order codes for XLamp High-Efficacy XP-G2 LEDs. For a complete description of the order code nomenclature, please see the Bin and Order Code Formats section (page 31). For definitions of the chromaticity kits, please see the Cree's Standard Chromaticity Kits section (page 30).

Chrom	aticity	Minimu	ım Luminous F @ 350 mA	lux (lm)		Order Codes	
Kit	сст	Code	Flux (lm) @ 85 °C	Flux (lm) @ 25 °C*	70 CRI Minimum	80 CRI Minimum	90 CRI Minimum
		S4	164	180	XPGBWT-BE-0000-00LDT		
DT	7000 1/	S3	156	171	XPGBWT-BE-0000-00KDT	XPGBWT-HE-0000-00KDT	
DT	7000 K	S2	148	163	XPGBWT-BE-0000-00JDT	XPGBWT-HE-0000-00JDT	
		R5	139	153		XPGBWT-HE-0000-00HDT	
		S4	164	180	XPGBWT-BE-0000-00LE1		
F1	(F00 I/	S3	156	171	XPGBWT-BE-0000-00KE1	XPGBWT-HE-0000-00KE1	
E1	6500 K	S2	148	163	XPGBWT-BE-0000-00JE1	XPGBWT-HE-0000-00JE1	
		R5	139	153		XPGBWT-HE-0000-00HE1	
		S4	164	180	XPGBWT-BE-0000-00L51		
		S3	156	171	XPGBWT-BE-0000-00K51	XPGBWT-HE-0000-00K51	
		S2	148	163	XPGBWT-BE-0000-00J51	XPGBWT-HE-0000-00J51	
51	6200 K	R5	139	153		XPGBWT-HE-0000-00H51	
		R4	130	143			
		R3	122	134			XPGBWT-UE-0000-00F51
		R2	114	125			XPGBWT-UE-0000-00E51
		S4	164	180	XPGBWT-BE-0000-00LDV		
		S3	156	171	XPGBWT-BE-0000-00KDV	XPGBWT-HE-0000-00KDV	
		S2	148	163	XPGBWT-BE-0000-00JDV	XPGBWT-HE-0000-00JDV	
DV	6000 K	R5	139	153		XPGBWT-HE-0000-00HDV	
		R4	130	143			
		R3	122	134			XPGBWT-UE-0000-00FDV
		R2	114	125			XPGBWT-UE-0000-00EDV

- Cree maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 33).
- Cree XLamp XP-G2 LED order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than
 the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions
 specified by the order code.
- * Flux values @ 25 °C are calculated and for reference only.



Chrom	aticity	Minimu	ım Luminous F @ 350 mA	lux (lm)		Order Codes	
Kit	сст	Code	Flux (lm) @ 85 °C	Flux (lm) @ 25 °C*	70 CRI Minimum	80 CRI Minimum	90 CRI Minimum
		S4	164	180	XPGBWT-BE-0000-00L50		
		S3	156	171	XPGBWT-BE-0000-00K50	XPGBWT-HE-0000-00K50	
		S2	148	163	XPGBWT-BE-0000-00J50	XPGBWT-HE-0000-00J50	
50	6000 K	R5	139	153		XPGBWT-HE-0000-00H50	
		R4	130	143			
		R3	122	134			XPGBWT-UE-0000-00F50
		R2	114	125			XPGBWT-UE-0000-00E50
		S4	164	180	XPGBWT-BE-0000-00LE2		
	5700 K	S3	156	171	XPGBWT-BE-0000-00KE2	XPGBWT-HE-0000-00KE2	
		S2	148	163	XPGBWT-BE-0000-00JE2	XPGBWT-HE-0000-00JE2	
E2		R5	139	153		XPGBWT-HE-0000-00HE2	
		R4	130	143			XPGBWT-UE-0000-00GE2
		R3	122	134			XPGBWT-UE-0000-00FE2
		R2	114	125			XPGBWT-UE-0000-00EE2
		S4	164	180	XPGBWT-BE-0000-00LE3		
		S3	156	171	XPGBWT-BE-0000-00KE3	XPGBWT-HE-0000-00KE3	
		S2	148	163	XPGBWT-BE-0000-00JE3	XPGBWT-HE-0000-00JE3	
E3	5000 K	R5	139	153		XPGBWT-HE-0000-00HE3	
		R4	130	143			
		R3	122	134			XPGBWT-UE-0000-00FE3
		R2	114	125			XPGBWT-UE-0000-00EE3
		S4	164	180	XPGBWT-BE-0000-00LF4		
		S3	156	171	XPGBWT-BE-0000-00KF4	XPGBWT-HE-0000-00KF4	
		S2	148	163	XPGBWT-BE-0000-00JF4	XPGBWT-HE-0000-00JF4	
Γ4	47E0 K	R5	139	153		XPGBWT-HE-0000-00HF4	
F4	4750 K	R4	130	143			
		R3	122	134			XPGBWT-UE-0000-00FF4
		R2	114	125			XPGBWT-UE-0000-00EF4
		Q5	107	118			XPGBWT-UE-0000-00DF4

- Cree maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 33).
- Cree XLamp XP-G2 LED order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than
 the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions
 specified by the order code.
- * Flux values @ 25 °C are calculated and for reference only.



Chrom	aticity	Minimu	ım Luminous F @ 350 mA	lux (lm)		Order Codes				
Kit	ССТ	Code	Flux (lm) @ 85 °C	Flux (lm) @ 25 °C*	70 CRI Minimum	80 CRI Minimum	90 CRI Minimum			
		S4	164	180	XPGBWT-BE-0000-00LE4					
		S3	156	171	XPGBWT-BE-0000-00KE4	XPGBWT-HE-0000-00KE4				
		S2	148	163	XPGBWT-BE-0000-00JE4	XPGBWT-HE-0000-00JE4				
E4	45001/	R5	139	153		XPGBWT-HE-0000-00HE4				
E4	4500 K	R4	130	143						
		R3	122	134			XPGBWT-UE-0000-00FE4			
		R2	114	125			XPGBWT-UE-0000-00EE4			
		Q5	107	118			XPGBWT-UE-0000-00DE4			
	4250 K	S4	164	180	XPGBWT-BE-0000-00LF5					
		S3	156	171	XPGBWT-BE-0000-00KF5	XPGBWT-HE-0000-00KF5				
		S2	148	163	XPGBWT-BE-0000-00JF5	XPGBWT-HE-0000-00JF5				
F5		R5	139	153		XPGBWT-HE-0000-00HF5				
F5	4250 K	R4	130	143						
		R3	122	134			XPGBWT-UE-0000-00FF5			
		R2	114	125			XPGBWT-UE-0000-00EF5			
		Q5	107	118			XPGBWT-UE-0000-00DF5			
		S4	164	180	XPGBWT-BE-0000-00LE5					
		S3	156	171	XPGBWT-BE-0000-00KE5	XPGBWT-HE-0000-00KE5				
		S2	148	163	XPGBWT-BE-0000-00JE5	XPGBWT-HE-0000-00JE5				
E5	4000 K	R5	139	153		XPGBWT-HE-0000-00HE5				
E3	4000 K	R4	130	143						
		R3	122	134			XPGBWT-UE-0000-00FE5			
		R2	114	125			XPGBWT-UE-0000-00EE5			
		Q5	107	118			XPGBWT-UE-0000-00DE5			

- Cree maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 33).
- Cree XLamp XP-G2 LED order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than
 the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions
 specified by the order code.
- * Flux values @ 25 °C are calculated and for reference only.



Chrom	aticity	Minimu	ım Luminous F @ 350 mA	lux (lm)		Order Codes	
Kit	ССТ	Code	Flux (lm) @ 85 °C	Flux (lm) @ 25 °C*	70 CRI Minimum	80 CRI Minimum	90 CRI Minimum
		S4	164	180	XPGBWT-BE-0000-00LF6		
		S3	156	171	XPGBWT-BE-0000-00KF6		
		S2	148	163	XPGBWT-BE-0000-00JF6	XPGBWT-HE-0000-00JF6	
		R5	139	153		XPGBWT-HE-0000-00HF6	
F6	3750 K	R4	130	143			
		R3	122	134			XPGBWT-UE-0000-00FF6
		R2	114	125			XPGBWT-UE-0000-00EF6
		Q5	107	118			XPGBWT-UE-0000-00DF6
		Q4	100	110			XPGBWT-UE-0000-00CF6
		S4	164	180	XPGBWT-BE-0000-00LE6		
		S3	156	171	XPGBWT-BE-0000-00KE6		
		S2	148	163	XPGBWT-BE-0000-00JE6	XPGBWT-HE-0000-00JE6	
		R5	139	153		XPGBWT-HE-0000-00HE6	
E6	3500 K	R4	130	143			
		R3	122	134			XPGBWT-UE-0000-00FE6
		R2	114	125			XPGBWT-UE-0000-00EE6
		Q5	107	118			XPGBWT-UE-0000-00DE6
		Q4	100	110			XPGBWT-UE-0000-00CE6
		S3	156	171	XPGBWT-BE-0000-00KF7		
		S2	148	163	XPGBWT-BE-0000-00JF7		
		R5	139	153	XPGBWT-BE-0000-00HF7	XPGBWT-HE-0000-00HF7	
F7	3250 K	R4	130	143		XPGBWT-HE-0000-00GF7	
F/	3230 K	R3	122	134			XPGBWT-UE-0000-00FF7
		R2	114	125			XPGBWT-UE-0000-00EF7
		Q5	107	118			XPGBWT-UE-0000-00DF7
		Q4	100	110			XPGBWT-UE-0000-00CF7

- Cree maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 33).
- Cree XLamp XP-G2 LED order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than
 the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions
 specified by the order code.
- * Flux values @ 25 °C are calculated and for reference only.



Chrom	aticity	Minimum Luminous Flux (lm) @ 350 mA			Order Codes				
Kit	сст	Code	Flux (lm) @ 85 °C	Flux (lm) @ 25 °C*	70 CRI Minimum	80 CRI Minimum	90 CRI Minimum		
		S3	156	171	XPGBWT-BE-0000-00KE7				
		S2	148	163	XPGBWT-BE-0000-00JE7				
		R5	139	153	XPGBWT-BE-0000-00HE7	XPGBWT-HE-0000-00HE7			
		R4	130	143		XPGBWT-HE-0000-00GE7			
E7	3000 K	R3	122	134			XPGBWT-UE-0000-00FE7		
		R2	114	125			XPGBWT-UE-0000-00EE7		
		Q5	107	118			XPGBWT-UE-0000-00DE7		
		Q4	100	110			XPGBWT-UE-0000-00CE7		
	205016	S3	156	171	XPGBWT-BE-0000-00KF8				
		S2	148	163	XPGBWT-BE-0000-00JF8				
		R5	139	153	XPGBWT-BE-0000-00HF8	XPGBWT-HE-0000-00HF8			
F0		R4	130	143		XPGBWT-HE-0000-00GF8			
F8	2850 K	R3	122	134					
		R2	114	125			XPGBWT-UE-0000-00EF8		
		Q5	107	118			XPGBWT-UE-0000-00DF8		
		Q4	100	110			XPGBWT-UE-0000-00CF8		
		S3	156	171	XPGBWT-BE-0000-00KE8				
		S2	148	163	XPGBWT-BE-0000-00JE8				
		R5	139	153	XPGBWT-BE-0000-00HE8	XPGBWT-HE-0000-00HE8			
E8	2700 K	R4	130	143		XPGBWT-HE-0000-00GE8			
E8	2700 K	R3	122	134					
		R2	114	125			XPGBWT-UE-0000-00EE8		
		Q5	107	118			XPGBWT-UE-0000-00DE8		
		Q4	100	110			XPGBWT-UE-0000-00CE8		

- Cree maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 33).
- Cree XLamp XP-G2 LED order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than
 the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions
 specified by the order code.
- * Flux values @ 25 °C are calculated and for reference only.



FLUX CHARACTERISTICS - STANDARD (T, = 85 °C)

The following table provides order codes for XLamp Standard XP-G2 LEDs. For a complete description of the order code nomenclature, please see the Bin and Order Code Formats section (page 31). For definitions of the chromaticity kits, please see the Cree's Standard Chromaticity Kits section (page 30).

Chron	naticity	Minimur	n Luminous I @ 350 mA	Flux (lm)	Order Codes	
Kit	сст	Code	Flux (lm) @ 85 °C	Flux (lm) @ 25 °C*	70 CRI Typical	
		S4	164	180	XPGBWT-L1-0000-00L51	
		S3	156	171	XPGBWT-L1-0000-00K51	
F1	6000 K	S2	148	163	XPGBWT-L1-0000-00J51	
51	6200 K	R5	139	153	XPGBWT-L1-0000-00H51	
		R4	130	143	XPGBWT-L1-0000-00G51	
		R3	122	134	XPGBWT-L1-0000-00F51	
		S4	164	180	XPGBWT-L1-0000-00L53	
		S3	156	171	XPGBWT-L1-0000-00K53	
53	6000 K	S2	148	163	XPGBWT-L1-0000-00J53	
53	0000 K	R5	139	153	XPGBWT-L1-0000-00H53	
		R4	130	143	XPGBWT-L1-0000-00G53	
		R3	122	134	XPGBWT-L1-0000-00F53	
		S4	164	180	XPGBWT-L1-0000-00L50	
		S3	156	171	XPGBWT-L1-0000-00K50	
50	6200 K	S2	148	163	XPGBWT-L1-0000-00J50	
50	0200 K	R5	139	153	XPGBWT-L1-0000-00H50	
		R4	130	143	XPGBWT-L1-0000-00G50	
		R3	122	134	XPGBWT-L1-0000-00F50	
		S4	164	180	XPGBWT-L1-0000-00LE1	
		S3	156	171	XPGBWT-L1-0000-00KE1	
E1	6500 K	S2	148	163	XPGBWT-L1-0000-00JE1	
EI	0000 K	R5	139	153	XPGBWT-L1-0000-00HE1	
		R4	130	143	XPGBWT-L1-0000-00GE1	
		R3	122	134	XPGBWT-L1-0000-00FE1	

- Cree maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 33).
- Cree XLamp XP-G2 LED order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- * Flux values @ 25 °C are calculated and for reference only.



Chrom	Chromaticity		n Luminous I @ 350 mA	Flux (lm)	Order Codes				
Kit	сст	Code	Flux (lm) @ 85 °C	Flux (lm) @ 25 °C*	70 CRI Typical				
		S4	164	180	XPGBWT-L1-0000-00LE2				
	F700 K	F700 K	F700 K	F700 K	5700 K	S3	156	171	XPGBWT-L1-0000-00KE2
E2						E700 V	5700 K	S2	148
EZ	5/00 K	R5	139	153	XPGBWT-L1-0000-00HE2				
		R4	130	143	XPGBWT-L1-0000-00GE2				
		R3	122	134	XPGBWT-L1-0000-00FE2				

Chror	maticity	Minimu	n Luminous I @ 350 mA	Flux (lm)	Order Codes		
Kit	Kit CCT Code		Flux (lm) @ 85 °C	Flux (lm) @25 °C*	70 CRI Typical	80 CRI Minimum	
		S4	164	180	XPGBWT-01-0000-00LE3		
		S3	156	171	XPGBWT-01-0000-00KE3		
		S2	148	163	XPGBWT-01-0000-00JE3		
E3	5000 K	R5	139	153	XPGBWT-01-0000-00HE3		
		R4	130	143	XPGBWT-01-0000-00GE3		
		R3	122	134	XPGBWT-01-0000-00FE3		
		R2	114	125	XPGBWT-01-0000-00EE3		
		S4	164	180	XPGBWT-01-0000-00LF4		
		S3	156	171	XPGBWT-01-0000-00KF4		
		S2	148	163	XPGBWT-01-0000-00JF4		
F4	4750 K	R5	139	153	XPGBWT-01-0000-00HF4		
		R4	130	143	XPGBWT-01-0000-00GF4		
		R3	122	134	XPGBWT-01-0000-00FF4		
		R2	114	125	XPGBWT-01-0000-00EF4		

- Cree maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 33).
- Cree XLamp XP-G2 LED order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than
 the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions
 specified by the order code.
- * Flux values @ 25 °C are calculated and for reference only.



Chror	naticity	Minimur	n Luminous I @ 350 mA	Flux (lm)	Order Codes		
Kit	сст	Code	Flux (lm) @ 85 °C	Flux (lm) @25 °C*	70 CRI Typical	80 CRI Minimum	
		S4	164	180	XPGBWT-01-0000-00LE4		
		S3	156	171	XPGBWT-01-0000-00KE4		
		S2	148	163	XPGBWT-01-0000-00JE4		
E4	4500 K	R5	139	153	XPGBWT-01-0000-00HE4		
		R4	130	143	XPGBWT-01-0000-00GE4		
		R3	122	134	XPGBWT-01-0000-00FE4		
		R2	114	125	XPGBWT-01-0000-00EE4		
		S4	164	180	XPGBWT-01-0000-00LF5		
		S3	156	171	XPGBWT-01-0000-00KF5		
		S2	148	163	XPGBWT-01-0000-00JF5		
F5	4250 K	R5	139	153	XPGBWT-01-0000-00HF5		
		R4	130	143	XPGBWT-01-0000-00GF5		
		R3	122	134	XPGBWT-01-0000-00FF5		
		R2	114	125	XPGBWT-01-0000-00EF5		
		S4	164	180	XPGBWT-01-0000-00LE5		
		S3	156	171	XPGBWT-01-0000-00KE5		
		S2	148	163	XPGBWT-01-0000-00JE5		
E5	4000 K	R5	139	153	XPGBWT-01-0000-00HE5	XPGBWT-H1-0000-00HE5	
	4000 K	R4	130	143	XPGBWT-01-0000-00GE5	XPGBWT-H1-0000-00GE5	
		R3	122	134	XPGBWT-01-0000-00FE5	XPGBWT-H1-0000-00FE5	
		R2	114	125	XPGBWT-01-0000-00EE5	XPGBWT-H1-0000-00EE5	
		Q5	107	118		XPGBWT-H1-0000-00DE5	
		R5	139	153		XPGBWT-H1-0000-00HZ5	
		R4	130	143		XPGBWT-H1-0000-00GZ5	
Z5	4000 K	R3	122	134		XPGBWT-H1-0000-00FZ5	
		R2	114	125		XPGBWT-H1-0000-00EZ5	
		Q5	107	118		XPGBWT-H1-0000-00DZ5	

- Cree maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 33).
- Cree XLamp XP-G2 LED order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than
 the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions
 specified by the order code.
- * Flux values @ 25 °C are calculated and for reference only.



Chro	omaticity	Minimu	m Luminous I @ 350 mA	Flux (lm)		Order	Codes	
Kit	сст	Code	Flux (lm) @ 85 °C	Flux (lm) @25 °C*	70 CRI Typical	80 CRI Typical	80 CRI Minimum	90 CRI Minimum
		S2	148	163	XPGBWT-01-0000-00JF6			
		R5	139	153	XPGBWT-01-0000-00HF6	XPGBWT-L1-0000-00HF6	XPGBWT-H1-0000-00HF6	
F6	3750 K	R4	130	143	XPGBWT-01-0000-00GF6	XPGBWT-L1-0000-00GF6	XPGBWT-H1-0000-00GF6	
го	3730 K	R3	122	134	XPGBWT-01-0000-00FF6	XPGBWT-L1-0000-00FF6	XPGBWT-H1-0000-00FF6	
			R2	114	125	XPGBWT-01-0000-00EF6	XPGBWT-L1-0000-00EF6	XPGBWT-H1-0000-00EF6
		Q5	107	118	XPGBWT-01-0000-00DF6	XPGBWT-L1-0000-00DF6	XPGBWT-H1-0000-00DF6	
		S2	148	163	XPGBWT-01-0000-00JE6			
		R5	139	153	XPGBWT-01-0000-00HE6	XPGBWT-L1-0000-00HE6	XPGBWT-H1-0000-00HE6	
E6	3500 K	R4	130	143	XPGBWT-01-0000-00GE6	XPGBWT-L1-0000-00GE6	XPGBWT-H1-0000-00GE6	
□ □0	3500 K	R3	122	134	XPGBWT-01-0000-00FE6	XPGBWT-L1-0000-00FE6	XPGBWT-H1-0000-00FE6	
		R2	114	125	XPGBWT-01-0000-00EE6	XPGBWT-L1-0000-00EE6	XPGBWT-H1-0000-00EE6	
		Q5	107	118	XPGBWT-01-0000-00DE6	XPGBWT-L1-0000-00DE6	XPGBWT-H1-0000-00DE6	
		R4	130	143		XPGBWT-L1-0000-00GZ6	XPGBWT-H1-0000-00GZ6	
Z6	3500 K	R3	122	134		XPGBWT-L1-0000-00FZ6	XPGBWT-H1-0000-00FZ6	
20	3500 K	R2	114	125		XPGBWT-L1-0000-00EZ6	XPGBWT-H1-0000-00EZ6	
		Q5	107	118		XPGBWT-L1-0000-00DZ6	XPGBWT-H1-0000-00DZ6	
		S2	148	163	XPGBWT-01-0000-00JF7			
		R5	139	153	XPGBWT-01-0000-00HF7	XPGBWT-L1-0000-00HF7	XPGBWT-H1-0000-00HF7	
F7	3250 K	R4	130	143	XPGBWT-01-0000-00GF7	XPGBWT-L1-0000-00GF7	XPGBWT-H1-0000-00GF7	
	3230 K	R3	122	134	XPGBWT-01-0000-00FF7	XPGBWT-L1-0000-00FF7	XPGBWT-H1-0000-00FF7	
		R2	114	125	XPGBWT-01-0000-00EF7	XPGBWT-L1-0000-00EF7	XPGBWT-H1-0000-00EF7	
		Q5	107	118		XPGBWT-L1-0000-00DF7	XPGBWT-H1-0000-00DF7	

- Cree maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 33).
- Cree XLamp XP-G2 LED order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- * Flux values @ 25 °C are calculated and for reference only.



Chro	omaticity	Minimum Luminous Flux (lm) @ 350 mA			Order Codes					
Kit	сст	Code	Flux (lm) @ 85 °C	Flux (lm) @25 °C*	70 CRI Typical	80 CRI Typical	80 CRI Minimum	90 CRI Minimum		
		S2	148	163	XPGBWT-01-0000-00JE7					
		R5	139	153	XPGBWT-01-0000-00HE7	XPGBWT-L1-0000-00HE7	XPGBWT-H1-0000-00HE7			
		R4	130	143	XPGBWT-01-0000-00GE7	XPGBWT-L1-0000-00GE7	XPGBWT-H1-0000-00GE7			
		R3	122	134	XPGBWT-01-0000-00FE7	XPGBWT-L1-0000-00FE7	XPGBWT-H1-0000-00FE7			
		R2	114	125	XPGBWT-01-0000-00EE7	XPGBWT-L1-0000-00EE7	XPGBWT-H1-0000-00EE7	XPGBWT-U1-0000-00EE7		
E7	3000 K	Q5	107	118		XPGBWT-L1-0000-00DE7	XPGBWT-H1-0000-00DE7	XPGBWT-U1-0000-00DE7		
		Q4	100	110		XPGBWT-L1-0000-00CE7	XPGBWT-H1-0000-00CE7	XPGBWT-U1-0000-00CE7		
		Q3	93.9	103				XPGBWT-U1-0000-00BE7		
		Q2	87.4	96.1				XPGBWT-U1-0000-00AE7		
		P4	80.6	88.6				XPGBWT-U1-0000-009E7		
		P3	73.9	81.2				XPGBWT-U1-0000-008E7		
		R4	130	143		XPGBWT-L1-0000-00GZ7	XPGBWT-H1-0000-00GZ7			
		R3	122	134		XPGBWT-L1-0000-00FZ7	XPGBWT-H1-0000-00FZ7			
		R2	114	125		XPGBWT-L1-0000-00EZ7	XPGBWT-H1-0000-00EZ7			
		Q5	107	118		XPGBWT-L1-0000-00DZ7	XPGBWT-H1-0000-00DZ7	XPGBWT-U1-0000-00DZ7		
Z 7	3000 K	Q4	100	110		XPGBWT-L1-0000-00CZ7	XPGBWT-H1-0000-00CZ7	XPGBWT-U1-0000-00CZ7		
		Q3	93.9	103				XPGBWT-U1-0000-00BZ7		
		Q2	87.4	96.1				XPGBWT-U1-0000-00AZ7		
		P4	80.6	88.6				XPGBWT-U1-0000-009Z7		
		P3	73.9	81.2				XPGBWT-U1-0000-008Z7		

- Cree maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 33).
- Cree XLamp XP-G2 LED order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than
 the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions
 specified by the order code.
- * Flux values @ 25 °C are calculated and for reference only.




Chro	maticity	Minimum Luminous Flux (lm) @ 350 mA			Order Codes				
Kit	сст	Code	Flux (lm) @ 85 °C	Flux (lm) @25 °C*	70 CRI Typical	80 CRI Typical	80 CRI Minimum	90 CRI Minimum	
		R4	130	143		XPGBWT-L1-0000-00GF8	XPGBWT-H1-0000-00GF8		
		R3	122	134		XPGBWT-L1-0000-00FF8	XPGBWT-H1-0000-00FF8		
		R2	114	125		XPGBWT-L1-0000-00EF8	XPGBWT-H1-0000-00EF8		
		Q5	107	118		XPGBWT-L1-0000-00DF8	XPGBWT-H1-0000-00DF8	XPGBWT-U1-0000-00DF8	
F8	20E0 K	Q4	100	110		XPGBWT-L1-0000-00CF8	XPGBWT-H1-0000-00CF8	XPGBWT-U1-0000-00CF8	
Fδ	2850 K	Q3	93.9	103		XPGBWT-L1-0000-00BF8	XPGBWT-H1-0000-00BF8	XPGBWT-U1-0000-00BF8	
		Q2	87.4	96.1				XPGBWT-U1-0000-00AF8	
		P4	80.6	88.6				XPGBWT-U1-0000-009F8	
		P3	73.9	81.2				XPGBWT-U1-0000-008F8	
		P2	67.2	73.9				XPGBWT-U1-0000-007F8	
		R4	130	143		XPGBWT-L1-0000-00GE8	XPGBWT-H1-0000-00GE8		
		R3	122	134		XPGBWT-L1-0000-00FE8	XPGBWT-H1-0000-00FE8		
		R2	114	125		XPGBWT-L1-0000-00EE8	XPGBWT-H1-0000-00EE8		
		Q5	107	118		XPGBWT-L1-0000-00DE8	XPGBWT-H1-0000-00DE8		
E8	2700 K	Q4	100	110		XPGBWT-L1-0000-00CE8	XPGBWT-H1-0000-00CE8	XPGBWT-U1-0000-00CE8	
EO	2700 K	Q3	93.9	103		XPGBWT-L1-0000-00BE8	XPGBWT-H1-0000-00BE8	XPGBWT-U1-0000-00BE8	
		Q2	87.4	96.1				XPGBWT-U1-0000-00AE8	
		P4	80.6	88.6				XPGBWT-U1-0000-009E8	
		P3	73.9	81.2				XPGBWT-U1-0000-008E8	
		P2	67.2	73.9				XPGBWT-U1-0000-007E8	
		R3	122	134		XPGBWT-L1-0000-00FZ8	XPGBWT-H1-0000-00FZ8		
		R2	114	125		XPGBWT-L1-0000-00EZ8	XPGBWT-H1-0000-00EZ8		
		Q5	107	118		XPGBWT-L1-0000-00DZ8	XPGBWT-H1-0000-00DZ8		
		Q4	100	110		XPGBWT-L1-0000-00CZ8	XPGBWT-H1-0000-00CZ8		
Z8	2700 K	Q3	93.9	103		XPGBWT-L1-0000-00BZ8	XPGBWT-H1-0000-00BZ8	XPGBWT-U1-0000-00BZ8	
		Q2	87.4	96.1				XPGBWT-U1-0000-00AZ8	
		P4	80.6	88.6				XPGBWT-U1-0000-009Z8	
		P3	73.9	81.2				XPGBWT-U1-0000-008Z8	
		P2	67.2	73.9				XPGBWT-U1-0000-007Z8	


- Cree maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 33).
- Cree XLamp XP-G2 LED order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than
 the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions
 specified by the order code.
- * Flux values @ 25 °C are calculated and for reference only.



RELATIVE SPECTRAL POWER DISTRIBUTION




RELATIVE FLUX VS. JUNCTION TEMPERATURE (I_E = 350 mA)






ELECTRICAL CHARACTERISTICS - HIGH EFFICACY (T, = 85 °C)




ELECTRICAL CHARACTERISTICS - STANDARD (T, = 85 °C)






RELATIVE FLUX VS. CURRENT - HIGH EFFICACY (T, = 85 °C)





RELATIVE FLUX VS. CURRENT - STANDARD (T₁ = 85 °C)






RELATIVE CHROMATICITY VS CURRENT AND TEMPERATURE - HIGH EFFICACY (WARM WHITE)








RELATIVE CHROMATICITY VS CURRENT AND TEMPERATURE - STANDARD (WARM WHITE*)







^{*} Warm White XLamp XP-G2 LEDs have a typical CRI of 80.



TYPICAL SPATIAL DISTRIBUTION - HIGH EFFICACY




TYPICAL SPATIAL DISTRIBUTION - STANDARD






THERMAL DESIGN - HIGH EFFICACY

The maximum forward current is determined by the thermal resistance between the LED junction and ambient. It is crucial for the end product to be designed in a manner that minimizes the thermal resistance from the solder point to ambient in order to optimize lamp life and optical characteristics.



THERMAL DESIGN - STANDARD





PERFORMANCE GROUPS - LUMINOUS FLUX

XLamp XP-G2 LEDs are tested for luminous flux and placed into one of the following luminous-flux groups:

Group Code	Minimum Luminous Flux (lm) @ 350 mA	Maximum Luminous Flux (lm) @ 350 mA
P2	67.2	73.9
P3	73.9	80.6
P4	80.6	87.4
Q2	87.4	93.9
Q3	93.9	100
Q4	100	107
Q5	107	114
R2	114	122
R3	122	130
R4	130	139
R5	139	148
S2	148	156
S3	156	164
S4	164	172
S5	172	180



PERFORMANCE GROUPS - CHROMATICITY

Region	х	у	Region	х	у	Region	х	у	Region	х	у
	0.2950	0.2970		0.2920	0.3060		0.2984	0.3133		0.2984	0.3133
0A	0.2920	0.3060	0B	0.2895	0.3135	0C	0.2962	0.3220	0D	0.3048	0.3207
UA	0.2984 0.3133	ОВ	0.2962	0.3220	00	0.3028	0.3304	0D	0.3068	0.3113	
	0.3009	0.3042		0.2984	0.3133		0.3048	0.3207		0.3009	0.3042
	0.2980	0.2880		0.2895	0.3135		0.2962	0.3220		0.3037	0.2937
0R	0.2950	0.2970	08	0.2870	0.3210	0T	0.2937	0.3312	0U	0.3009	0.3042
UK	0.3009	0.3042	03	0.2937	0.3312	01	0.3005	0.3415	00	0.3068	0.3113
	0.3037	0.2937		0.2962	0.3220		0.3028	0.3304		0.3093	0.2993
	0.3048	0.3207		0.3028	0.3304		0.3115	0.3391		0.3130	0.3290
1A	0.3130	0.3290	1B	0.3115	0.3391	1C	0.3205	0.3481	1D	0.3213	0.3373
IA	0.3144	0.3186	16	0.3130	0.3290	10	0.3213	0.3373	10	0.3221	0.3261
	0.3068	0.3113		0.3048	0.3207		0.3130	0.3290		0.3144	0.3186
	0.3068	0.3113		0.3005	0.3415		0.3099	0.3509		0.3144	0.3186
1R	0.3144	0.3186	18	0.3099	0.3509	1T	0.3196	0.3602	1U	0.3221	0.3261
IK	0.3161	0.3059	13	0.3115	0.3391	11	0.3205	0.3481	10	0.3231	0.3120
	0.3093	0.2993		0.3028	0.3304		0.3115	0.3391		0.3161	0.3059
	0.3215	0.3350		0.3207	0.3462	2C	0.3290	0.3538		0.3290	0.3417
2A	0.3290	0.3417	2B	0.3290	0.3538		0.3376	0.3616	2D	0.3371	0.3490
ZA	0.3290	0.3300		0.3290	0.3417		0.3371	0.3490	25	0.3366	0.3369
	0.3222	0.3243		0.3215	0.3350		0.3290	0.3417		0.3290	0.3300
	0.3222	0.3243		0.3196	0.3602		0.3290	0.3690		0.3290	0.3300
2R	0.3290	0.3300	28	0.3290	0.3690	2T	0.3381	0.3762	2U	0.3366	0.3369
ZN	0.3290	0.3180	23	0.3290	0.3538	21	0.3376	0.3616	20	0.3361	0.3245
	0.3231	0.3120		0.3207	0.3462		0.3290	0.3538		0.3290	0.3180
	0.3371	0.3490		0.3376	0.3616		0.3463	0.3687		0.3451	0.3554
3A	0.3451	0.3554	3B	0.3463	0.3687	3C	0.3551	0.3760	3D	0.3533	0.3620
3A	0.3440	0.3427	30	0.3451	0.3554	30	0.3533	0.3620	30	0.3515	0.3487
	0.3366	0.3369		0.3371	0.3490		0.3451	0.3554		0.3440	0.3427
	0.3366	0.3369		0.3381	0.3762						
2D	0.3440	0.3428	20	0.3480	0.3840						
3R	0.3429	0.3307	3S	0.3463	0.3687						
	0.3361	0.3245		0.3376	0.3616						
	0.3530	0.3597		0.3548	0.3736		0.3641	0.3804		0.3615	0.3659
40	0.3615	0.3659	ΛD	0.3641	0.3804	40	0.3736	0.3874	4D	0.3702	0.3722
4A	0.3590	0.3521	4B	0.3615	0.3659	4C	0.3702	0.3722	40	0.3670	0.3578
	0.3512	0.3465		0.3530 0.3597		0.3615	0.3659		0.3590	0.3521	



PERFORMANCE GROUPS - CHROMATICITY (CONTINUED)

Region	х	у	Region	x	у	Region	х	у	Region	х	у
	0.3670	0.3578		0.3686	0.3649		0.3744	0.3685		0.3726	0.3612
FA1	0.3686	0.3649	540	0.3702	0.3722	FA0	0.3763	0.3760	FA 4	0.3744	0.3685
5A1	0.3744	0.3685	5A2	0.3763	0.3760	5A3	0.3825	0.3798	5A4	0.3804	0.3721
	0.3726	0.3612		0.3744	0.3685		0.3804	0.3721		0.3783	0.3646
	0.3702	0.3722		0.3719	0.3797		0.3782	0.3837		0.3763	0.3760
5B1	0.3719	0.3797	5B2	0.3736	0.3874	5B3	0.3802	0.3916	5B4	0.3782	0.3837
JDT	0.3782	0.3837	362	0.3802	0.3916	363	0.3869	0.3958	304	0.3847	0.3877
	0.3763	0.3760		0.3782	0.3837		0.3847	0.3877		0.3825	0.3798
	0.3825	0.3798		0.3847	0.3877		0.3912	0.3917		0.3887	0.3836
5C1	0.3847	0.3877	5C2	0.3869	0.3958	5C3	0.3937	0.4001	5C4	0.3912	0.3917
301	0.3912	0.3917	302	0.3937	0.4001	303	0.4006	0.4044	304	0.3978	0.3958
	0.3887	0.3836		0.3912	0.3917		0.3978	0.3958		0.3950	0.3875
	0.3783	0.3646		0.3804	0.3721		0.3863	0.3758		0.3840	0.3681
5D1	0.3804	0.3721	5D2	0.3825	0.3798	5D3	0.3887	0.3836	5D4	0.3863	0.3758
351	0.3863	0.3758	302	0.3887	0.3836	303	0.3950	0.3875	304	0.3924	0.3794
	0.3840	0.3681		0.3863	0.3758		0.3924	0.3794		0.3898	0.3716
	0.3889	0.3690	6A2	0.3915	0.3768	6A3	0.3981	0.3800		0.3953	0.3720
6A1	0.3915	0.3768		0.3941	0.3848		0.4010	0.3882	6A4	0.3981	0.3800
UAT	0.3981	0.3800		0.4010	0.3882		0.4080	0.3916	0,	0.4048	0.3832
	0.3953	0.3720		0.3981	0.3800		0.4048	0.3832		0.4017	0.3751
	0.3941	0.3848		0.3968	0.3930		0.4040	0.3966		0.4010	0.3882
6B1	0.3968	0.3930	6B2	0.3996	0.4015	6B3	0.4071	0.4052	6B4	0.4040	0.3966
ODI	0.4040	0.3966	ODZ	0.4071	0.4052	003	0.4146	0.4089	054	0.4113	0.4001
	0.4010	0.3882		0.4040	0.3966		0.4113	0.4001		0.4080	0.3916
	0.4080	0.3916		0.4113	0.4001		0.4186	0.4037		0.4150	0.3950
6C1	0.4113	0.4001	6C2	0.4146	0.4089	6C3	0.4222	0.4127	6C4	0.4186	0.4037
001	0.4186	0.4037	002	0.4222	0.4127	003	0.4299	0.4165	004	0.4259	0.4073
	0.4150	0.3950		0.4186	0.4037		0.4259	0.4073		0.4221	0.3984
	0.4017	0.3751		0.4048	0.3832		0.4116	0.3865		0.4082	0.3782
6D1	0.4048	0.3832	6D2	0.4080	0.3916	6D3	0.4150	0.3950	6D4	0.4116	0.3865
ODI	0.4116	0.3865	6D2	0.4150	0.3950	003	0.4221	0.3984	004	0.4183	0.3898
	0.4082	0.3782		0.4116	0.3865		0.4183	0.3898		0.4147	0.3814
	0.4147	0.3814		0.4183	0.3898		0.4242	0.3919		0.4203	0.3833
7A1	0.4183	0.3898	7A2	0.4221	0.3984	7A3	0.4281	0.4006	7A4	0.4242	0.3919
/AT	0.4242	0.3919	/AZ	0.4281	0.4006	743	0.4342	0.4028	7.44	0.4300	0.3939
	0.4203	0.3833		0.4242	0.3919		0.4300	0.3939		0.4259	0.3853




PERFORMANCE GROUPS - CHROMATICITY (CONTINUED)

Region	х	у	Region	х	у	Region	х	у	Region	х	у
	0.4221	0.3984		0.4259	0.4073		0.4322	0.4096		0.4281	0.4006
7B1	0.4259 0.4073	0.4299	0.4165	7B3	0.4364	0.4188	7B4	0.4322	0.4096		
701	0.4322	0.4096	7B2	0.4364	0.4188	763	0.4430	0.4212	7 D4	0.4385	0.4119
	0.4281	0.4006		0.4322	0.4096		0.4385	0.4119		0.4342	0.4028
	0.4342	0.4028		0.4385	0.4119		0.4449	0.4141		0.4403	0.4049
7C1	0.4385	0.4119	7C2	0.4430	0.4212	7C3	0.4496	0.4236	7C4	0.4449	0.4141
701	0.4449	0.4141	762	0.4496	0.4236	703	0.4562	0.4260	704	0.4513	0.4164
	0.4403	0.4049		0.4449	0.4141		0.4513	0.4164		0.4465	0.4071
	0.4259	0.3853		0.4300	0.3939		0.4359	0.3960		0.4316	0.3873
7D1	0.4300	0.3939	7D2	0.4342	0.4028	7D3	0.4403	0.4049	7D4	0.4359	0.3960
701	0.4359	0.3960	702	0.4403	0.4049	703	0.4465	0.4071	704	0.4418	0.3981
	0.4316	0.3873		0.4359	0.3960		0.4418	0.3981		0.4373	0.3893
	0.4373	0.3893		0.4418	0.3981		0.4475	0.3994		0.4428	0.3906
8A1	0.4418	0.3981	040	0.4465	0.4071	8A3	0.4523	0.4085	8A4	0.4475	0.3994
OAT	0.4475	0.3994	8A2	0.4523	0.4085	OAS	0.4582	0.4099		0.4532	0.4008
	0.4428	0.3906		0.4475	0.3994		0.4532	0.4008		0.4483	0.3919
	0.4465	0.4071		0.4513	0.4164		0.4573	0.4178		0.4523	0.4085
8B1	0.4513	0.4164	8B2	0.4562	0.4260	8B3	0.4624	0.4274	8B4	0.4573	0.4178
ODI	0.4573	0.4178	ODZ	0.4624	0.4274	003	0.4687	0.4289	004	0.4634	0.4193
	0.4523	0.4085		0.4573	0.4178		0.4634	0.4193		0.4582	0.4099
	0.4582	0.4099		0.4634	0.4193		0.4695	0.4207		0.4641	0.4112
8C1	0.4634	0.4193	8C2	0.4687	0.4289	8C3	0.4750	0.4304	8C4	0.4695	0.4207
001	0.4695	0.4207	002	0.4750 0.4	0.4304	003	0.4813	0.4319	004	0.4756	0.4221
	0.4641	0.4112		0.4695	0.4207		0.4756	0.4221		0.4700	0.4126
	0.4483	0.3919		0.4532	0.4008		0.4589	0.4021		0.4538	0.3931
0D1	0.4532	0.4008	000	0.4582	0.4099	902	0.4641	0.4112	0D4	0.4589	0.4021
8D1	0.4589	0.4021	8D2	0.4641	0.4112	8D3	0.4700	0.4126	8D4	0.4646	0.4034
	0.4538	0.3931		0.4589	0.4021		0.4646	0.4034		0.4593	0.3944


CREE 💠

CREE'S STANDARD COOL WHITE KITS PLOTTED ON ANSI STANDARD CHROMATICITY REGIONS






CREE'S STANDARD COOL WHITE KITS PLOTTED ON ANSI STANDARD CHROMATICITY REGIONS - CONTINUED






CREE'S STANDARD WARM AND NEUTRAL WHITE KITS PLOTTED ON ANSI STANDARD CHROMATICITY REGIONS





CREE'S STANDARD WARM AND NEUTRAL WHITE KITS PLOTTED ON ANSI STANDARD CHROMATICITY REGIONS - CONTINUED





CREE'S STANDARD CHROMATICITY KITS


The following table provides the chromaticity bins associated with chromaticity kits.


Color	ССТ	Kit	Chromaticity Bins
	7000 K	DT	0A, 0B, 0C, 0D, 0R, 0S, 0T, 0U, 1A, 1B, 1C, 1D, 1R, 1S, 1T, 1U
	6200 K	51	0A, 0B, 0C, 0D, 0R, 0S, 0T, 0U, 1A, 1B, 1C, 1D, 1R, 1S, 1T, 1U, 2A, 2B, 2C, 2D, 2R, 2S, 2T, 2U, 3A, 3B, 3R, 3S
	6000 K	53	1A, 1B, 1C, 1D, 1R, 1S, 1T, 1U, 2A, 2B, 2C, 2D, 2R, 2S, 2T, 3A, 3B, 3S
Cool White	6000 K	50	1A, 1B, 1C, 1D, 2A, 2B, 2C, 2D
	6500 K	E1	1A, 1B, 1C, 1D
	6000 K	DV	1A, 1B, 1C, 1D, 1R, 1S, 1T, 1U, 2A, 2B, 2C, 2D, 2R, 2S, 2T, 2U
	5700 K	E2	2A, 2B, 2C, 2D
	5000 K	E3	3A, 3B, 3C, 3D
	4750 K	F4	3C, 3D, 4A, 4B
Neutral	4500 K	E4	4A, 4B, 4C, 4D
White	4250 K	F5	4C, 4D, 5A1, 5A2, 5A3, 5A4, 5B1, 5B2, 5B3, 5B4
	4000 K	E5	5A1, 5A2, 5A3, 5A4, 5B1, 5B2, 5B3, 5B4, 5C1, 5C2, 5C3, 5C4, 5D1, 5D2, 5D3, 5D4
	4000 K	Z5	5A3, 5B4, 5C1, 5D2
	3750 K	F6	5C1, 5C2, 5C3, 5C4, 5D1, 5D2, 5D3, 5D4, 6A1, 6A2, 6A3, 6A4, 6B1, 6B2, 6B3, 6B4
	3500 K	E6	6A1, 6A2, 6A3, 6A4, 6B1, 6B2, 6B3, 6B4, 6C1, 6C2, 6C3, 6C4, 6D1, 6D2, 6D3, 6D4
	3500 K	Z6	6A3, 6B4, 6C1, 6D2
	3250 K	F7	6C1, 6C2, 6C3, 6C4, 6D1, 6D2, 6D3, 6D4, 7A1, 7A2, 7A3, 7A4, 7B1, 7B2, 7B3, 7B4
Warm White	3000 K	E7	7A1, 7A2, 7A3, 7A4, 7B1, 7B2, 7B3, 7B4, 7C1, 7C2, 7C3, 7C4, 7D1, 7D2, 7D3, 7D4
	3000 K	Z 7	7A3, 7B4, 7C1, 7D2
	2850 K	F8	7C1, 7C2, 7C3, 7C4, 7D1, 7D2, 7D3, 7D4, 8A1, 8A2, 8A3, 8A4, 8B1, 8B2, 8B3, 8B4
	2700 K	E8	8A1, 8A2, 8A3, 8A4, 8B1, 8B2, 8B3, 8B4, 8C1, 8C2, 8C3, 8C4, 8D1, 8D2, 8D3, 8D4
	2700 K	Z8	8A3, 8B4, 8C1, 8D2



BIN AND ORDER CODE FORMATS

XP-G2 bin codes and order codes are configured in the following manner:








REFLOW SOLDERING CHARACTERISTICS

In testing, Cree has found XLamp XP-G2 LEDs to be compatible with JEDEC J-STD-020C, using the parameters listed below. As a general guideline, Cree recommends that users follow the recommended soldering profile provided by the manufacturer of the solder paste used, and therefore it is the lamp or luminaire manufacturer's responsibility to determine applicable soldering requirements.

Note that this general guideline may not apply to all PCB designs and configurations of reflow soldering equipment.



IPC/JEDEC J-STD-020C

Profile Feature	Lead-Free Solder
Average Ramp-Up Rate $(Ts_{max} to T_p)$	1.2 °C/second
Preheat: Temperature Min (Ts _{min})	120 °C
Preheat: Temperature Max (Ts _{max})	170 °C
Preheat: Time (ts _{min} to ts _{max})	65-150 seconds
Time Maintained Above: Temperature (T _L)	217 °C
Time Maintained Above: Time (t _L)	45-90 seconds
Peak/Classification Temperature (Tp)	235 - 245 °C
Time Within 5 °C of Actual Peak Temperature (tp)	20-40 seconds
Ramp-Down Rate	1 - 6 °C/second
Time 25 °C to Peak Temperature	4 minutes max.

Note: All temperatures refer to topside of the package, measured on the package body surface.



NOTES

Measurements

The luminous flux, radiant power, chromaticity, forward voltage and CRI measurements in this document are binning specifications only and solely represent product measurements as of the date of shipment. These measurements will change over time based on a number of factors that are not within Cree's control and are not intended or provided as operational specifications for the products. Calculated values are provided for informational purposes only and are not intended or provided as specifications.

Pre-Release Qualification Testing

Please read the LED Reliability Overview for details of the qualification process Cree applies to ensure long-term reliability for XLamp LEDs and details of Cree's pre-release qualification testing for XLamp LEDs.

Lumen Maintenance

Cree now uses standardized IES LM-80-08 and TM-21-11 methods for collecting long-term data and extrapolating LED lumen maintenance. For information on the specific LM-80 data sets available for this LED, refer to the public LM-80 results document.

Please read the Long-Term Lumen Maintenance application note for more details on Cree's lumen maintenance testing and forecasting. Please read the Thermal Management application note for details on how thermal design, ambient temperature, and drive current affect the LED junction temperature.

Moisture Sensitivity

Cree recommends keeping XLamp LEDs in the provided, resealable moisture-barrier packaging (MBP) until immediately prior to soldering. Unopened MBPs that contain XLamp LEDs do not need special storage for moisture sensitivity.

Once the MBP is opened, XLamp XP-G2 LEDs may be stored as MSL 1 per JEDEC J-STD-033, meaning they have unlimited floor life in conditions of \leq 30 °C/85% relative humidity (RH). Regardless of the storage condition, Cree recommends sealing any unsoldered LEDs in the original MBP.

RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Cree representative or from the Product Ecology section of the Cree website.

REACh Compliance

REACh substances of very high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact a Cree representative to insure you get the most up-to-date REACh Declaration. REACh banned substance information (REACh Article 67) is also available upon request.



NOTES - CONTINUED

UL® Recognized Component

This product meets the requirements to be considered a UL Recognized Component with Level 4 enclosure consideration. The LED package or a portion thereof has been investigated as a fire and electrical enclosure per ANSI/UL 8750.

Vision Advisory


WARNING: Do not look at an exposed lamp in operation. Eye injury can result. For more information about LEDs and eye safety, please refer to the LED Eye Safety application note.




MECHANICAL DIMENSIONS ($T_A = 25$ °C)

Thermal vias, if present, are not shown on these drawings.


All measurements are ±.13 mm unless otherwise indicated.







MECHANICAL DIMENSIONS ($T_A = 25 \, ^{\circ}\text{C}$) - CONTINUED




- Cree recommends using thermal pad kickouts to maximize component thermal performance.
- Cree recommends using white solder mask material to minimize system optical loss.
- * This stencil has been tested and optimized for the avoidance of voiding when using ALPHA® LUMET® P30 Maxrel solder paste. For other solder pastes, a "window pane" design for the thermal pad stencil may result in a lower voiding percentage. Contact your local Cree Field Applications Engineer for consultation regarding your specific application.

CREE 💠

TAPE AND REEL


All Cree carrier tapes conform to EIA-481D, Automated Component Handling Systems Standard.





All dimensions in mm.

Ao	3.70	+/- 0.1
Во	3.70	+/- 0.1
Ко	2.40	+0.0/-0.1
F	5.50	+/- 0.05
P 1	8.00	+/- 0.1
W	12.00	+0.3/-0.1

- Measured from centerline of sprocket hole to centerline of pocket.
- Cumulative tolerance of 10 sprocket holes is ± 0.20 .
- Measured from centerline of sprocket hole to centerline of pocket.
- (IV) Other material available.









PACKAGING

Unpackaged Reel Label with Cree Bin Code,

Quantity, Reel ID

