#### THS5641A 8-BIT, 100 MSPS, CommsDAC<sup>TM</sup> DIGITAL-TO-ANALOG CONVERTER SLAS277A - MARCH 2000 - REVISED SEPTEMBER 2002

- Member of the Pin-Compatible CommsDAC<sup>™</sup> Product Family
- 100 MSPS Update Rate
- 8-Bit Resolution
- Signal-to-Noise and Distortion Ratio (SINAD) at 5 MHz: 50 dB
- Integral Nonlinearity INL: 0.25 LSB
- Differential Nonlinearity DNL: 0.25 LSB
- 1 ns Setup/Hold Time
- Glitch Energy: 5 pV-s
- Settling Time to 0.1%: 35 ns
- Differential Scalable Current Outputs: 2 mA to 20 mA
- On-Chip 1.2-V Reference
- 3-V and 5-V Single Supply Operation
- Straight Binary or Twos Complement Input
- Power Dissipation: 100 mW at 3.3 V, Sleep Mode: 17 mW at 3.3 V
- Package: 28-Pin SOIC and TSSOP

#### description

SOIC (DW) OR TSSOP (PW) PACKAGE (TOP VIEW) U D7 🞞 1 28 2 27 D6 🗖 26 D5 🗖 3 DGND 25 D4 🗖 4 D3 🗖 5 24 D2 🗖 6 23 COMP2 22 D1 💷 7 21 8 NC 🗖 20 AGND 9 NC 🗆 10 19 COMP1 18 🔲 BIASJ 11 12 NC 🗖 17 NC 🗖 13 16 🔟 EXTLO NC 🗖 14 15 SLEEP

NC - No internal connection

The THS5641A is an 8-bit resolution digital-to-analog converter (DAC) optimized for video applications and digital data transmission in wired and wireless communication systems. The 8-bit DAC is a member of the CommsDAC<sup>™</sup> series of high-speed, low-power CMOS digital-to-analog converters. The CommsDAC<sup>™</sup> family consists of pin compatible 14-, 12-, 10-, and 8-bit DACs. All devices offer identical interface options, small outline package and pinout. The THS5641A offers superior ac and dc performance while supporting update rates up to 100 MSPS.

The THS5641A operates from an analog and digital supply of 3 V to 5.5 V. Its inherent low power dissipation of 100 mW ensures that the device is well suited for portable and low power applications. Lowering the full-scale current output reduces the power dissipation without significantly degrading performance. The device features a SLEEP mode, which reduces the standby power to approximately 17 mW, thereby optimizing the power consumption for system needs.

The THS5641A is manufactured in Texas Instruments advanced high-speed mixed-signal CMOS process. A current-source-array architecture combined with simultaneous switching shows excellent dynamic performance. On-chip edge-triggered input latches and a 1.2 V temperature compensated bandgap reference provide a complete monolithic DAC solution. The digital supply range of 3 V to 5.5 V supports 3 V and 5 V CMOS logic families. Minimum data input setup and hold times allow for easy interfacing with external logic. The THS5641A supports both a straight binary and twos complement input word format, enabling flexible interfacing with digital signal processors.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

CommsDAC is a trademark of Texas Instruments.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.



Copyright © 2002, Texas Instruments Incorporated

## THS5641A 8-BIT, 100 MSPS, CommsDAC™ DIGITAL-TO-ANALOG CONVERTER

SLAS277A - MARCH 2000 - REVISED SEPTEMBER 2002


#### description (continued)

The THS5641A provides a nominal full-scale differential output current of 20 mA and >300 k $\Omega$  output impedance, supporting both single-ended and differential applications. The output current can be directly fed to the load (e.g., external resistor load or transformer), with no additional external output buffer required. An accurate on-chip reference and control amplifier allows the user to adjust this output current from 20 mA down to 2 mA, with no significant degradation of performance. This reduces power consumption and provides 20 dB gain range control capabilities. Alternatively, an external reference voltage and control amplifier may be applied in applications using a multiplying DAC.

The THS5641A is available in both a 28-pin SOIC and TSSOP package. The device is characterized for operation over the industrial temperature range of -40°C to 85°C.

AVAILABLE OPTIONS										
	PACKAGE									
TA	28-TSSOP (PW)	28-SOIC (DW)								
-40°C to 85°C	THS5641AIPW	THS5641AIDW								

#### functional block diagram





#### **Terminal Functions**

TERMINAL					
NAME	NO.	1/0	DESCRIPTION		
AGND	20	Ι	Analog ground return for the internal analog circuitry		
AVDD	24	Ι	Positive analog supply voltage (3 V to 5.5 V)		
BIASJ	18	0	Full-scale output current bias		
CLK	28	Ι	External clock input. Input data latched on rising edge of the clock.		
COMP1	19	Ι	Compensation and decoupling node, requires a 0.1 µF capacitor to AV <sub>DD</sub> .		
COMP2	23	Ι	Internal bias node, requires a 0.1 µF decoupling capacitor to AGND.		
D[7:0] [1:8] I Data bits 0 through 7.   D7 is most significant data bit (MSB), D0 is least significant data bit (LSB).					
DGND	26	Ι	Digital ground return for the internal digital logic circuitry		
DVDD	27	Ι	Positive digital supply voltage (3 V to 5.5 V)		
EXTIO	17	I/O	Used as external reference input when internal reference is disabled (i.e., EXTLO = $AV_{DD}$ ). Used as internal reference output when EXTLO = AGND, requires a 0.1 $\mu$ F decoupling capacitor to AGND when used as reference output		
EXTLO	16	0	Internal reference ground. Connect to AV <sub>DD</sub> to disable the internal reference source		
IOUT1	22	0	DAC current output. Full scale when all input bits are set 1		
IOUT2	21	0	Complementary DAC current output. Full scale when all input bits are 0		
MODE	25	I	Mode select. Internal pulldown. Mode 0 is selected if this pin is left floating or connected to DGND. See timing diagram.		
NC	[9:14]	Ν	No connection		
SLEEP	15	I	Asynchronous hardware power down input. Active High. Internal pulldown. Requires 5 $\mu s$ to power down but 3 ms to power up.		

#### absolute maximum ratings over operating free-air temperature (unless otherwise noted)<sup>†</sup>

Supply voltage range, AV <sub>DD</sub> (see Note 1) DV <sub>DD</sub> (see Note 2)	
Voltage between AGND and DGND	–0.3 V to 0.5 V
Supply voltage range, AV <sub>DD</sub> to DV <sub>DD</sub>	
CLK, SLEEP, MODE (see Note 2)	
Digital input D7–D0 (see Note 2)	
IOUT1, IOUT2 (see Note 1)	–1 V to AV <sub>DD</sub> + 0.3 V
COMP1, COMP2 (see Note 1)	–0.3 V to AV <sub>DD</sub> + 0.3 V
EXTIO, BIASJ (see Note 1)	0.3 V to AV <sub>DD</sub> + 0.3 V
EXTLO (see Note 1)	–0.3 V to 0.3 V
Peak input current (any input)	20 mA
Peak total input current (all inputs)	–30 mA
Operating free-air temperature range, T <sub>A</sub> : THS5641AI	–40°C to 85°C
Storage temperature range	–65°C to 150°C
Lead temperature 1,6 mm (1/16 inch) from the case for 10 seconds .	260°C

<sup>†</sup> Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

NOTES: 1. Measured with respect to AGND.

2. Measured with respect to DGND.



# electrical characteristics over recommended operating free-air temperature range, $AV_{DD} = 5 V$ , $DV_{DD} = 5 V$ , $IOUT_{FS} = 20 mA$ (unless otherwise noted)

#### dc specifications

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT	
Resolution			8			Bits	
DC accu	racy†						
INL	Integral nonlinearity	T. 40%C to 95%C	-0.25	±0.1	0.25	LSB	
DNL	Differential nonlinearity		-0.25	±0.05	0.25	LSB	
Monoton	icity		N	lonotonic			
Analog o	output						
	Offset error			0.02		%FSR	
		Without internal reference		2.3			
	Gain error	With internal reference		1.3		%FSR	
	Full scale output current‡		2		20	mA	
	Outrast compliance reaso	$AV_{DD} = 5 V$ , IOUT <sub>FS</sub> = 20 mA	-1		1.25	V	
	Output compliance range	$AV_{DD} = 3.3 \text{ V}$ IOUT <sub>FS</sub> = 20 mA	-1		0.6	V	
	Output resistance			300		kΩ	
	Output capacitance			5		pF	
Reference	e output	·	<u>.</u>				
	Reference voltage		1.18	1.22	1.32	V	
	Reference output current§			100		nA	
Reference	e input	•					
VEXTIO	Input voltage range		0.1		1.25	V	
	Input resistance			1		MΩ	
	Small signal bandwidth¶	Without C <sub>COMP1</sub>		1.3		MHz	
	Input capacitance			100		pF	
Tempera	ture coefficients						
	Offset drift			0			
		Without internal reference		±40		nom of	
	Gain drift	With internal reference		±120		ppm of FSR/°C	
	Reference voltage drift			±35			
Power su	Jpply		<b>_</b>				
AV <sub>DD</sub>	Analog supply voltage		3		5.5	V	
DVDD	Digital supply voltage		3		5.5	V	
	Analog supply current			25	30	mA	
IAVDD	Sleep mode supply current	Sleep mode		3	5	mA	
IDVDD	Digital supply current <sup>#</sup>			5	6	mA	
		$AV_{DD} = 5 V$ , $DV_{DD} = 5 V$ IOUT <sub>FS</sub> = 20 mA		175			
	Power dissipation	$AV_{DD} = 3.3 \text{ V}, DV_{DD} = 3.3 \text{ V}, IOUT_{FS} = 20 \text{ mA}$		100		mW	
AV <sub>DD</sub>	<b>_</b>						
DVDD	Power supply rejection ratio		±0.025		%FSR/V		
	Operating range		-40		85	°C	

<sup>†</sup> Measured at IOUT1 in virtual ground configuration.

<sup>‡</sup> Nominal full-scale current IOUT<sub>FS</sub> equals 32X the IBIAS current.

§ Use an external buffer amplifier with high impedance input to drive any external load.

 $\P$  Reference bandwidth is a function of external cap at COMP1 pin and signal level.

<sup>#</sup>Measured at  $f_{CLK}$  = 50 MSPS and  $f_{OUT}$ = 1 MHz.

II Measured for 50  $\Omega$  RLOAD at IOUT1 and IOUT2, f<sub>CLK</sub> = 50 MSPS and f<sub>OUT</sub> = 20 MHz.

Specifications subject to change



#### THS5641A 8-BIT, 100 MSPS, CommsDAC<sup>TM</sup> DIGITAL-TO-ANALOG CONVERTER SLAS277A - MARCH 2000 - REVISED SEPTEMBER 2002

electrical characteristics over recommended operating free-air temperature range,  $AV_{DD} = 5 V$ ,  $DV_{DD} = 5 V$ ,  $IOUT_{FS} = 20 mA$ , single-ended output IOUT1, 50  $\Omega$  doubly terminated load (unless otherwise noted)

#### ac specifications

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT				
Analog o	utput									
for u	Maximum autaut undata rata	DV <sub>DD</sub> = 4.5 V to 5.5 V	100			MODO				
fCLK	Maximum output update rate	DV <sub>DD</sub> = 3 V to 3.6 V	67			MSPS				
<sup>t</sup> s(DAC)	Output settling time to 0.1% <sup>†</sup>			35		ns				
<sup>t</sup> pd	Output propagation delay			1		ns				
GE	Glitch energy‡	Worst case LSB transition (code 127 – code 128)		5		pV–s				
<sup>t</sup> r(IOUT)	Output rise time 10% to 90% <sup>†</sup>			1		ns				
tf(IOUT)	Output fall time 90% to 10% <sup>†</sup>			1		ns				
		IOUT <sub>FS</sub> = 20 mA		15						
	Output noise	IOUT <sub>FS</sub> = 2 mA		10		pA/√H				
AC linear	rity (to Nyquist)	·	•							
		f <sub>CLK</sub> = 5 MSPS, f <sub>OUT</sub> = 1 MHz, T <sub>A</sub> = 25°C		50						
		f <sub>CLK</sub> = 25 MSPS, f <sub>OUT</sub> = 1 MHz, T <sub>A</sub> = 25°C		50						
		f <sub>CLK</sub> = 25 MSPS, f <sub>OUT</sub> = 5 MHz, T <sub>A</sub> = 25°C		50						
		f <sub>CLK</sub> = 25 MSPS, f <sub>OUT</sub> = 10 MHz, T <sub>A</sub> = 25°C		48		-				
	Signal-to-noise and distortion ratio	f <sub>CLK</sub> = 50 MSPS, f <sub>OUT</sub> = 1 MHz, T <sub>A</sub> = 25°C		50		I				
		f <sub>CLK</sub> = 50 MSPS, f <sub>OUT</sub> = 5 MHz, T <sub>A</sub> = 25°C		50						
SINAD		f <sub>CLK</sub> = 50 MSPS, f <sub>OUT</sub> = 20 MHz, T <sub>A</sub> = 25°C		47		dB				
		$f_{CLK} = 70$ MSPS, $f_{OUT} = 5$ MHz, $T_A = 25^{\circ}C$		50						
		f <sub>CLK</sub> = 70 MSPS, f <sub>OUT</sub> = 10 MHz, T <sub>A</sub> = 25°C		50		-				
		f <sub>CLK</sub> = 70 MSPS, f <sub>OUT</sub> = 20 MHz, T <sub>A</sub> = 25°C		46						
		f <sub>CLK</sub> = 100 MSPS, f <sub>OUT</sub> = 10 MHz, T <sub>A</sub> = 25°C		47						
		f <sub>CLK</sub> = 100 MSPS, f <sub>OUT</sub> = 22 MHz, T <sub>A</sub> = 25°C		47						
		f <sub>CLK</sub> = 100 MSPS, f <sub>OUT</sub> = 40 MHz, T <sub>A</sub> = 25°C		45						
		$f_{CLK} = 5 \text{ MSPS}, f_{OUT} = 1 \text{ MHz}, T_A = 25^{\circ}\text{C}$		-69						
		f <sub>CLK</sub> = 25 MSPS, f <sub>OUT</sub> = 1 MHz, T <sub>A</sub> = 25°C		-67						
		$f_{CLK} = 25$ MSPS, $f_{OUT} = 5$ MHz, $T_A = 25^{\circ}C$		-69						
		f <sub>CLK</sub> = 25 MSPS, f <sub>OUT</sub> = 10 MHz, T <sub>A</sub> = 25°C		-57						
		f <sub>CLK</sub> = 50 MSPS, f <sub>OUT</sub> = 1 MHz, T <sub>A</sub> = 25°C		-67						
		$f_{CLK} = 50$ MSPS, $f_{OUT} = 1$ MHz, $T_A = -40^{\circ}C$ to $85^{\circ}C$			-64					
		$f_{CLK} = 50$ MSPS, $f_{OUT} = 5$ MHz, $T_A = 25^{\circ}C$		-66						
THD	Total harmonic distortion	$f_{CLK} = 50$ MSPS, $f_{OUT} = 20$ MHz, $T_A = 25^{\circ}C$		-52		dBc				
		$f_{CLK} = 70$ MSPS, $f_{OUT} = 5$ MHz, $T_A = 25^{\circ}C$		-64						
		$f_{CLK} = 70 \text{ MSPS}, f_{OUT} = 10 \text{ MHz}, T_A = 25^{\circ}\text{C}$		-60						
		$f_{CLK} = 70$ MSPS, $f_{OUT} = 20$ MHz, $T_A = 25^{\circ}C$		-48						
		$f_{CLK} = 100 \text{ MSPS}, f_{OUT} = 10 \text{ MHz}, T_A = 25^{\circ}\text{C}$		-53						
		$f_{CLK} = 100 \text{ MSPS}, f_{OUT} = 22 \text{ MHz}, T_A = 25^{\circ}\text{C}$		-53		-				
		$f_{CLK} = 100$ MSPS, $f_{OUT} = 40$ MHz, $T_A = 25^{\circ}C$		-47						

<sup>†</sup> Measured single ended into 50  $\Omega$  load at IOUT1.

<sup>‡</sup>Single-ended output IOUT1, 50  $\Omega$  doubly terminated load.

## **THS5641A** 8-BIT, 100 MSPS, CommsDAC™ DIGITAL-TO-ANÁLOG CONVERTER SLAS277A – MARCH 2000 – REVISED SEPTEMBER 2002

# electrical characteristics over recommended operating free-air temperature range, AV<sub>DD</sub> = 5 V, DV<sub>DD</sub> = 5 V, IOUT<sub>FS</sub> = 20 mA, single-ended output IOUT1, 50 $\Omega$ doubly terminated load (unless otherwise noted) (continued)

#### ac specifications

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT			
AC linea	arity (to Nyquist)	•							
		$f_{CLK} = 5$ MSPS, $f_{OUT} = 1$ MHz, $T_A = 25^{\circ}C$		68					
	$f_{CLK} = 25$ MSPS, $f_{OUT} = 1$ MHz, $T_A = 25^{\circ}C$		69						
		$f_{CLK} = 25$ MSPS, $f_{OUT} = 5$ MHz, $T_A = 25^{\circ}C$		68					
		$f_{CLK} = 25$ MSPS, $f_{OUT} = 10$ MHz, $T_A = 25^{\circ}C$		56					
	$f_{CLK} = 50$ MSPS, $f_{OUT} = 1$ MHz, $T_A = 25^{\circ}C$		67						
		$f_{CLK}$ = 50 MSPS, $f_{OUT}$ = 5 MHz, $T_A$ = 25°C		67					
SFDR	Spurious free dynamic range	$f_{CLK}$ = 50 MSPS, $f_{OUT}$ = 20 MHz, $T_A$ = 25°C		53		dBc			
		$f_{CLK}$ = 70 MSPS, $f_{OUT}$ = 5 MHz, $T_A$ = 25°C		65					
		$f_{CLK}$ = 70 MSPS, $f_{OUT}$ = 10 MHz, $T_A$ = 25°C		63					
		$f_{CLK}$ = 70 MSPS, $f_{OUT}$ = 20 MHz, $T_A$ = 25°C		48					
		$f_{CLK}$ = 100 MSPS, $f_{OUT}$ = 10 MHz, $T_A$ = 25°C		55					
		$f_{CLK}$ = 100 MSPS, $f_{OUT}$ = 22 MHz, $T_A$ = 25°C		55					
		$f_{CLK}$ = 100 MSPS, $f_{OUT}$ = 40 MHz, $T_A$ = 25°C	= 25°C 48						

#### digital specifications

	PARAME	ETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Interface				•			
			DV <sub>DD</sub> = 5 V	3.5	5		
VIH	H High-level input voltage		DV <sub>DD</sub> = 3.3 V	2.1	3.3		V
	Law law literation to a literat		DV <sub>DD</sub> = 5 V		0	1.3	
VIL	Low-level input voltage		DV <sub>DD</sub> = 3.3 V		0	0.9	V
ΊΗ	High-level input current	MODE and SLEEP	$DV_{DD} = 3 V \text{ to } 5.5 V$	-15		15	
		All other digital pins	DV <sub>DD</sub> = 3 V to 5.5 V	-10		10	μA
		MODE and SLEEP	DV <sub>DD</sub> = 3 V to 5.5 V	-15		15	
۱IL	Low-level input current	All other digital pins	$DV_{DD} = 3 V \text{ to } 5.5 V$	-10		10	μA
Cl	Input capacitance			1		5	pF
Timing							
<sup>t</sup> su(D)	Input setup time			1			ns
<sup>t</sup> h(D)	Input hold time			1			ns
<sup>t</sup> w(LPH)	Input latch pulse high time	Input latch pulse high time		4			ns
<sup>t</sup> d(D)	Digital delay time					1	clk

Specifications subject to change




#### SPURIOUS FREE DYNAMIC RANGE TOTAL HARMONIC DISTORTION VS vs **OUTPUT FREQUENCY OUTPUT FREQUENCY** 78 -42 Fclock = 5 MSPS **100 MSPS** 70 MSPS $AV_{DD} = 5 V$ 72 -48 $DV_{DD} = 5 V$ Fclock = 25 MSPS 66 -54 Fclock = 50 MSPS SFDR - dBc THD - dBc 50 MSPS 60 -60 25 MSPS Fclock = 70 MSPS 54 Fclock = 100 MSPS -66 $AV_{DD} = 5 V$ 48 -72 $DV_{DD} = 5 V$ 5 MSPS 42 -78 10 20 30 40 50 0 0 10 20 30 40 50 Fout - MHz Fout – MHz Figure 1 Figure 2 SIGNAL-TO-NOISE AND DISTORTION RATIO SPURIOUS FREE DYNAMIC RANGE vs vs **OUTPUT FREQUENCY OUTPUT FREQUENCY** 54 78 5 MSPS $AV_{DD} = 3.3 V$ $AV_{DD} = 5 V$ 5 MSPS 72 51 DV<sub>DD</sub> = 3.3 V 25 MSPS $DV_{DD} = 5 V$ 25 MSPS SINAD - dB 66 SFDR - dBc 50 MSPS 50 MSPS 48 **100 MSPS** 60 45 70 MSPS 67 MSPS 54 42 48 0 10 20 40 50 30 0 5 10 15 20 25 30 35 Fout – MHz Fout – MHz Figure 3 Figure 4

**TYPICAL CHARACTERISTICS<sup>†</sup>** 

<sup>†</sup> AV<sub>DD</sub> and DV<sub>DD</sub> specified for each chart seperately, IOUT<sub>FS</sub> = 20 mA, single-ended output IOUT1, 50  $\Omega$  doubly terminated load, T<sub>A</sub> = 25°C (unless otherwise noted.)








<sup>†</sup> AV<sub>DD</sub> and DV<sub>DD</sub> specified for each chart seperately, IOUT<sub>FS</sub> = 20 mA, single-ended output IOUT1, 50 Ω doubly terminated load,  $T_A = 25^{\circ}C$  (unless otherwise noted.)



#### THS5641A 8-BIT, 100 MSPS, CommsDAC<sup>TM</sup> DIGITAL-TO-ANALOG CONVERTER SLAS277A - MARCH 2000 - REVISED SEPTEMBER 2002

**TYPICAL CHARACTERISTICS<sup>†</sup>** 



<sup>†</sup> AV<sub>DD</sub> and DV<sub>DD</sub> specified for each chart seperately, IOUT<sub>FS</sub> = 20 mA, single-ended output IOUT1, 50  $\Omega$  doubly terminated load, T<sub>A</sub> = 25°C (unless otherwise noted.)



#### TYPICAL CHARACTERISTICS<sup>†</sup>





Figure 15

<sup>†</sup> AV<sub>DD</sub> and DV<sub>DD</sub> specified for each chart seperately, IOUT<sub>FS</sub> = 20 mA, single-ended output IOUT1, 50 Ω doubly terminated load, T<sub>A</sub> = 25°C (unless otherwise noted.)




## TYPICAL CHARACTERISTICS<sup>†</sup>



<sup>†</sup> AV<sub>DD</sub> and DV<sub>DD</sub> specified for each chart seperately, IOUT<sub>FS</sub> = 20 mA, single-ended output IOUT1, 50  $\Omega$  doubly terminated load, T<sub>A</sub> = 25°C (unless otherwise noted.)



#### **TYPICAL CHARACTERISTICS<sup>†</sup>**



<sup>†</sup> AV<sub>DD</sub> and DV<sub>DD</sub> specified for each chart seperately, IOUT<sub>FS</sub> = 20 mA, single-ended output IOUT1, 50  $\Omega$  doubly terminated load, T<sub>A</sub> = 25°C (unless otherwise noted.)



The THS5641A architecture is based on current steering, combining high update rates with low power consumption. The CMOS device consists of a segmented array of PMOS transistor current sources, which are capable of delivering a full-scale current up to 20 mA. High-speed differential current switches direct the current of each current source to either one of the output nodes, IOUT1 or IOUT2. The complementary output currents thus enable differential operation, canceling out common mode noise sources (on-chip and PCB noise), dc offsets, even order distortion components, and increase signal output power by a factor of two. Major advantages of the segmented architecture are minimum glitch energy, excellent DNL, and very good dynamic performance. The DAC's high output impedance of >300 k $\Omega$  and fast switching result in excellent dynamic linearity (spurious free dynamic range SFDR).

The full-scale output current is set using an external resistor  $R_{BIAS}$  in combination with an on-chip bandgap voltage reference source (1.2 V) and control amplifier. The current  $I_{BIAS}$  through resistor  $R_{BIAS}$  is mirrored internally to provide a full-scale output current equal to 32 times  $I_{BIAS}$ . The full-scale current can be adjusted from 20 mA down to 2 mA.

#### data interface and timing

The THS5641A comprises separate analog and digital supplies, i.e.  $AV_{DD}$  and  $DV_{DD}$ . The analog and digital supply voltage can be set independently from 5.5 V down to 3 V. The THS5641A provides two operating modes, as shown in Table 1. Mode 0 (mode pin connected to DGND) supports a straight binary input data word format, whereas mode 1 (mode pin connected to DV<sub>DD</sub>) sets a twos complement input configuration.

Figure 23 shows the timing diagram. Internal edge-triggered flip-flops latch the input word on the rising edge of the input clock. The THS5641A provides for minimum setup and hold times (> 1 ns), allowing for noncritical external interface timing. Conversion latency is one clock cycle for both modes. The clock duty cycle can be chosen arbitrarily under the timing constraints listed in the digital specifications table. However, a 50% duty cycle will give optimum dynamic performance. Figure 24 shows a schematic of the equivalent digital inputs of the THS5641A, valid for pins D7–D0, SLEEP, and CLK. The digital inputs are CMOS-compatible with logic thresholds of  $DV_{DD}/2 \pm 20\%$ . Since the THS5641A is capable of being updated up to 100 MSPS, the quality of the clock and data input signals are important in achieving the optimum performance. The drivers of the digital data interface circuitry should be specified to meet the minimum setup and hold times of the THS5641A, as well as its required min/max input logic level thresholds. Typically, the selection of the slowest logic family that satisfies the above conditions will result in the lowest data feed-through and noise. Additionally, operating the THS5641A with reduced logic swings and a corresponding digital supply (DV<sub>DD</sub>) will reduce data feed-through. Note that the update rate is limited to 67 MSPS for a digital supply voltage DV<sub>DD</sub> of 3 V to 3.6 V.



## **THS5641A** 8-BIT, 100 MSPS, CommsDAC™ DIGITAL-TO-ANÁLOG CONVERTER SLAS277A – MARCH 2000 – REVISED SEPTEMBER 2002

## **APPLICATION INFORMATION**




Figure 23. Timing Diagram

#### **Table 1. Input Interface Modes**

	MODE 0	MODE 1			
FUNCTION/MODE	MODE PIN CONNECTED TO DGND	MODE PIN CONNECTED TO DV <sub>DD</sub>			
Input code format	Binary	Twos complement			




Figure 24. Digital Equivalent Input



#### **DAC transfer function**

The THS5641A delivers complementary output currents IOUT1 and IOUT2. Output current IOUT1 equals the approximate full-scale output current when all input bits are set high in mode 0 (straight binary input), i.e. the binary input word has the decimal representation 255. For mode 1, the MSB is inverted (twos complement input format). Full-scale output current will flow through terminal IOUT2 when all input bits are set low (mode 0, straight binary input). The relation between IOUT1 and IOUT2 can thus be expressed as:

$$IOUT1 = IOUT_{FS} - IOUT2$$

where  $\mathsf{IOUT}_{\mathsf{FS}}$  is the full-scale output current. The output currents can be expressed as:

$$IOUT1 = IOUT_{FS} \times \frac{CODE}{256}$$
$$IOUT2 = IOUT_{FS} \times \frac{(255 - CODE)}{256}$$

where CODE is the decimal representation of the DAC data input word. Output currents IOUT1 and IOUT2 drive resistor loads  $R_{LOAD}$  or a transformer with equivalent input load resistance  $R_{LOAD}$ . This would translate into single-ended voltages VOUT1 and VOUT2 at terminal IOUT1 and IOUT2, respectively, of:

$$\text{VOUT1} = \text{IOUT1} \times \text{R}_{\text{LOAD}} = \frac{\text{CODE}}{256} \times \text{IOUT}_{\text{FS}} \times \text{R}_{\text{LOAD}}$$

$$\text{VOUT2} = \text{IOUT2} \times \text{R}_{\text{LOAD}} = \frac{(255\text{--CODE})}{256} \times \text{IOUT}_{\text{FS}} \times \text{R}_{\text{LOAD}}$$

The differential output voltage VOUT<sub>DIFF</sub> can thus be expressed as:

$$VOUT_{DIFF} = VOUT1-VOUT2 = \frac{(2CODE-255)}{256} \times IOUT_{FS} \times R_{LOAD}$$

The latter equation shows that applying the differential output will result in doubling of the signal power delivered to the load. Since the output currents of IOUT1 and IOUT2 are complementary, they become additive when processed differentially. Care should be taken not to exceed the compliance voltages at node IOUT1 and IOUT2, which would lead to increased signal distortion.



#### reference operation

The THS5641A comprises a bandgap reference and control amplifier for biasing the full-scale output current. The full-scale output current is set by applying an external resistor  $R_{BIAS}$ . The bias current  $I_{BIAS}$  through resistor  $R_{BIAS}$  is defined by the on-chip bandgap reference voltage and control amplifier. The full-scale output current equals 32 times this bias current. The full-scale output current IOUT<sub>FS</sub> can thus be expressed as:

$$IOUT_{FS} = 32 \times I_{BIAS} = \frac{32 \times V_{EXTIO}}{R_{BIAS}}$$

where V<sub>EXTIO</sub> is the voltage at terminal EXTIO. The bandgap reference voltage delivers an accurate voltage of 1.2 V. This reference is active when terminal EXTLO is connected to AGND. An external decoupling capacitor  $C_{EXT}$  of 0.1 µF should be connected externally to terminal EXTIO for compensation. The bandgap reference can additionally be used for external reference operation. In that case, an external buffer with high impedance input should be applied in order to limit the bandgap load current to a maximum of 100 nA. The internal reference can be disabled and overridden by an external reference by connecting EXTLO to AV<sub>DD</sub>. Capacitor  $C_{EXT}$  may hence be omitted. Terminal EXTIO thus serves as either input or output node.

The full-scale output current can be adjusted from 20 mA down to 2 mA by varying resistor R<sub>BIAS</sub> or changing the externally applied reference voltage. The internal control amplifier has a wide input range, supporting the full-scale output current range of 20 dB. The bandwidth of the internal control amplifier is defined by the internal 1 nF compensation capacitor at pin COMP1 and the external compensation capacitor C1. The relatively weak internal control amplifier may be overridden by an externally applied amplifier with sufficient drive for the internal 1 nF load, as shown in Figure 25. This provides the user with more flexibility and higher bandwidths, which are specifically attractive for gain control and multiplying DAC applications. Pin SLEEP should be connected to AGND or left disconnected when an external control amplifier is used.




Figure 25. Bypassing the Internal Reference and Control Amplifier



#### analog current outputs

Figure 26 shows a simplified schematic of the current source array output with corresponding switches. Differential PMOS switches direct the current of each individual PMOS current source to either the positive output node IOUT1 or its complementary negative output node IOUT2. The output impedance is determined by the stack of the current sources and differential switches, and is typically >300 k $\Omega$  in parallel with an output capacitance of 5 pF.

Output nodes IOUT1 and IOUT2 have a negative compliance voltage of -1 V, determined by the CMOS process. Beyond this value, transistor breakdown may occur, resulting in reduced reliability of the THS5641A device. The positive output compliance depends on the full-scale output current IOUT<sub>FS</sub> and positive supply voltage AV<sub>DD</sub>. The positive output compliance equals 1.25 V for AV<sub>DD</sub> = 5 V and IOUT<sub>FS</sub> = 20 mA. For AV<sub>DD</sub> = 3.3 V the output compliance is limited to 0.6 V. Exceeding the positive compliance voltage adversely affects distortion performance and integral nonlinearity. The optimum distortion performance for a single-ended or differential output is achieved when the maximum full-scale signal at IOUT1 and IOUT2 does not exceed 0.5 V (e.g. when applying a 50  $\Omega$  doubly terminated load for 20 mA full-scale output current). Applications requiring the THS5641A output (i.e., OUT1 and/or OUT2) to extend its output compliance should size R<sub>LOAD</sub> accordingly.






Figure 27(a) shows the typical differential output configuration with two matched externally resistor loads. The nominal resistor load of 50  $\Omega$  will give a differential output swing of 2 V<sub>PP</sub> when applying a 20 mA full-scale output current. The output impedance of the THS5641A depends slightly on the output voltage at nodes IOUT1 and IOUT2. Consequently, for optimum dc integral nonlinearity, the configuration of Figure 27(b) should be chosen. In this I–V configuration, terminal IOUT1 is kept at virtual ground by the inverting operational amplifier. The complementary output should be connected to ground to provide a dc current path for the current sources switched to IOUT2. Note that the INL/DNL specifications for the THS5641A are measured with IOUT1 maintained at virtual ground. The amplifier's maximum output swing and the DAC's full-scale output current output, thereby reducing the operational amplifier slew-rate requirements. In this configuration, the op amp should operate on a dual supply voltage due to its positive and negative output swing. Node IOUT1 should be selected if a single-ended unipolar output is desirable.



## THS5641A 8-BIT, 100 MSPS, CommsDAC™ DIGITAL-TO-ANALOG CONVERTER

SLAS277A - MARCH 2000 - REVISED SEPTEMBER 2002

#### **APPLICATION INFORMATION**






Figure 27. Differential and Single-Ended Output Configuration

The THS5641A can be easily configured to drive a doubly terminated 50  $\Omega$  cable. Figure 28(a) shows the single-ended output configuration, where the output current IOUT1 flows into an equivalent load resistance of 25  $\Omega$ . Node IOUT2 should be connected to ground or terminated with a resistor of 25  $\Omega$ . Differential-to-single conversion (e.g., for measurement purposes) can be performed using a properly selected RF transformer, as shown in Figure 28(b). This configuration provides maximum rejection of common-mode noise sources and even order distortion components, thereby doubling the power to the output. The center tap on the primary side of the transformer is connected to AGND, enabling a dc current flow for both IOUT1 and IOUT2. Note that the ac performance of the THS5641A is optimum using this differential transformer coupled output, limiting the voltage swing at IOUT1 and IOUT2 to  $\pm 0.5$  V.







#### sleep mode

The THS5641A features a power-down mode that turns off the output current and reduces the supply current to less than 5 mA over the analog supply range of 3 V to 5.5 V and temperature range. The power-down mode is activated by applying a logic level 1 to the SLEEP pin (e.g., by connecting pin SLEEP to AVDD). An internal pulldown circuit at node SLEEP ensures that the THS5641A is enabled if the input is left disconnected. Power-up and power-down activation times depend on the value of external capacitor at node SLEEP. For a nominal capacitor value of 0.1  $\mu$ F power down takes less than 5  $\mu$ s, and approximately 3 ms to power backup. The SLEEP mode should not be used when an external control amplifier is used, as shown in Figure 25.

#### definitions of specifications and terminology

#### integral nonlinearity (INL)

The relative accuracy or integral nonlinearity (INL), sometimes referred to as linearity error, is the maximum deviation of the output from the line between zero and full scale excluding the effects of zero code and full-scale errors.

#### differential nonlinearity (DNL)

The differential nonlinearity (DNL), sometimes referred to as differential error, is the difference between the measured and ideal 1 LSB amplitude change of any two adjacent codes. Monotonic means the output voltage changes in the same direction (or remains constant) as a change in the digital input code.

#### offset error

Offset error is defined as the deviation of the output current from the ideal of zero at a digital input value of 0.

#### gain error

Gain error is the error in slope of the DAC transfer function.

#### signal-to-noise and distortion ratio (S/N+D or SINAD)

S/N+D or SINAD is the ratio of the rms value of the output signal to the rms sum of all other spectral components below the Nyquist frequency, including harmonics but excluding dc. The value for S/N+D is expressed in decibels.

#### spurious free dynamic range (SFDR)

SFDR is the difference between the rms value of the output signal and the rms value of the largest spurious signal within a specified bandwidth. The value for SFDR is expressed in decibels.

#### total harmonic distortion (THD)

THD is the ratio of the rms sum of the first six harmonic components to the rms value of the fundamental signal and is expressed in decibels.

#### output compliance range

The maximum and minimum allowable voltage of the output of the DAC, beyond which either saturation of the output stage or breakdown may occur.

#### settling time

The time required for the output to settle within a specified error band.

#### glitch energy

The time integral of the analog value of the glitch transient.



#### offset drift

The change in offset error versus temperature from the ambient temperature ( $T_A = 25^{\circ}C$ ) in ppm of full-scale range per  $^{\circ}C$ .

#### gain drift

The change in gain error versus temperature from the ambient temperature ( $T_A = 25^{\circ}C$ ) in ppm of full-scale range per  $^{\circ}C$ .

#### reference voltage drift

The change in reference voltage error versus temperature from the ambient temperature ( $T_A = 25^{\circ}C$ ) in ppm of full-scale range per °C.

#### **THS5641A** evaluation board

An evaluation module (EVM) board for the THS5641A digital-to-analog converter is available for evaluation. This board allows the user the flexibility to operate the THS5641A in various configurations. Possible output configurations include transformer coupled, resistor terminated, and inverting/noninverting amplifier outputs. The digital inputs are designed to interface with the TMS320 C5000 or C6000 family of DSPs or to be driven directly from various pattern generators with the onboard option to add a resistor network for proper load termination.

See the THS56x1 Evaluation Module User's Guide for more details (SLAU032).






Figure 29. Schematic







Figure 31. Board Layout, Layer 2



## **THS5641A** 8-BIT, 100 MSPS, CommsDAC™ DIGITAL-TO-ANALOG CONVERTER

SLAS277A -MARCH 2000 - REVISED SEPTEMBER 2002



#### **APPLICATION INFORMATION**




Figure 33. Board Layout, Layer 4






Figure 34. Board Layout, Layer 5

Table 2. Bill of Materials

QTY	REF. DES	PART NUMBER	DESCRIPTION	MFG.
3	C1, C22, C31	1206ZC105KAT2A	Ceranucm 1 µF, 10 V, X7R, 10%	AVX
4	C18, C19, C28, C35	ECSTOJY475	6.3 V, 4.7 μF, tantalum	Panasonic
3	C15, C24, C4	ECSTOJY106	6.3 V, 10 μF, tantalum	Panasonic
0	C25, C32		Ceramic, not installed, 50 V, X7R, 10%	
6	C14, C2, C20, C26, C29, C33	12065C103KAT2A	Ceramic, 0.01 µF, 50 V, X7R, 10%	AVX
17	C10, C11, C12, C13, C16, C17, C21, C23, C27, C3, C30, C34, C5, C6, C7, C8, C9	12065C104KAT2A	Ceramic, 0.1 μF, 50 V, X7R, 10%	AVX
2	D1, D2	AND/AND5GA or equivalent	GREEN LED, 1206 size SM chip LED	
4	FB1, FB2, FB3, FB4	27-43-037447	Fair-Rite SM beads #27-037447	FairRite
1	J1	TSW-117-07-L-D or equivalent	34-Pin header for IDC	Samtec
1	J2	KRMZ2 or equivalent	2 Terminal screw connector, 2TERM_CON	Lumberg
1	J3	TSW-112-07-L-S or equivalent	Single row 12-pin header	Samtec
1	J4	KRMZ3 or equivalent	3 Terminal screw connector	Lumberg
3	J5, J6, J7	142-0701-206 or equivalent	PCB Mount SMA jack, SMA_PCB_MT	Johnson Components
0	J8, J9	142-0701-206 or equivalent	PCB Mount SMA jack, not installed	Johnson Components
3	L1, L2, L3	DO1608C-472	DO1608C-series, DS1608C-472	Coil Craft
1	R1	1206	1206 Chip resistor, 1.5K, 1/4 W, 1%	
4	R10, R11, R4, R5	CTS/CTS766-163-(R)330-G-TR	8 Element isolated resistor pack, 33 $\Omega$	



## **THS5641A** 8-BIT, 100 MSPS, CommsDAC™ DIGITAL-TO-ANALOG CONVERTER SLAS277A –MARCH 2000 – REVISED SEPTEMBER 2002

## **APPLICATION INFORMATION**

#### Table 2. Bill of Materials (Continued)

QTY	REF. DES	PART NUMBER	DESCRIPTION	MFG.
4	R12, R19, R7, R9	1206	1206 Chip resistor, 33 Ω, 1/4 W, 1%	
5	R13, R17. R2, R21, R8	1206	1206 Chip resistor, 0 Ω, 1/4 W, 1%	
1	R14	3214W-1-502 E or equivalent	4 mm SM Pot, 5K	Bourns
1	R15	1206	1206 Chip resistor, 2.94K, 1/4 W, 1%	
1	R16	1206	1206 Chip resistor, 3K, 1/4 W, 1%	
3	R18, R24, R29	1206	1206 Chip resistor, 49.94K, 1/4 W, 1%	
3	R20, R3, R6	1206	1206 Chip resistor, 10K, 1/4 W, 1%	
1	R22	1206	1206 Chip resistor, 10K, 1/4 W, 1%	
1	R23	1206	1206 Chip resistor, 100K, 1/4 W, 1%	
1	R25	1206	1206 Chip resistor, TBD, 1/4 W, 1%	
4	R26, R27, R28, R30	1206	1206 Chip resistor, 750K, 1/4 W, 1%	
1	T1	T1-1T-KK81	RF Transformer, T1-1T-KK81	MiniCircuits
2	U1, U2	SN74LVT245BDW	Octal bus transceiver, 3-state, SN74LVT245B	TI
1	U3	SN74AHCT1G00DBVR/ SN74AHC1G00DBVR	Single gate NAND, SN74AHC1G00	TI
1	U4	SN74AHCT1G32DBVR/ SN74AHCC1G32DBVR	Single 2 input positive or gate, SN74AHC1G32	TI
	THS5641A	THS5641AIDW	DAC, 3–5.5 V, 8 Bit, 100 MSPS	ТІ
	THS5651A	THS5651AIDW	DAC, 3–5.5 V, 10 Bit, 125 MSPS	ТІ
	THS5661A	THS5661AIDW	DAC, 3–5.5 V, 12 Bit, 125 MSPS	TI
	THS5671A	THS5647AIDW	DAC, 3–5.5 V, 14 Bit, 125 MSPS	TI
1	SN74ALVC08	SN74ALVC08D	Quad AND gate	TI
1	LT1004D	LT1004CD-1-2/LT1004ID-1-2	Precision 1.2 V reference	TI
0	NOT INSTALLED	AD1580BRT	Precision voltage reference, not installed	
1	THS3001	THS3001CD/THS2001ID	THS3001 high-speed op amp	ТІ
4	W2	TSW-102-07-L-S or equivalent	2 position jumper1" spacing, W2	Samtec
3	W3	TSW-102-07-L-S or equivalent	3 position jumper1" spacing, W3	Samtec
2	2X3_JUMPER	TSW-102-07-L-S or equivalent	6-Pin header dual row, 0.025×0.1, 2X3_JUMPER	Samtec




## **THS5641A** 8-BIT, 100 MSPS, CommsDAC™ **DIGITAL-TO-ANALOG CONVERTER**

SLAS277A -MARCH 2000 - REVISED SEPTEMBER 2002

#### **MECHANICAL DATA**

#### PLASTIC SMALL-OUTLINE PACKAGE



NOTES: A. All linear dimensions are in inches (millimeters).

- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion not to exceed 0.006 (0,15).

A MIN

0.400

(10, 16)

0.453

(11, 51)

0.500

(12,70)

0.600

(15, 24)

0.700

(17, 78)

D. Falls within JEDEC MS-013



4040000/E 08/01


#### **THS5641A** 8-BIT, 100 MSPS, CommsDAC™ DIGITAL-TO-ANALOG CONVERTER SLAS277A -MARCH 2000 - REVISED SEPTEMBER 2002

#### **MECHANICAL DATA**

#### PW (R-PDSO-G\*\*)

#### PLASTIC SMALL-OUTLINE PACKAGE

**14 PINS SHOWN** 



NOTES: A. All linear dimensions are in millimeters.

B. This drawing is subject to change without notice.

C. Body dimensions do not include mold flash or protrusion not to exceed 0,15.

D. Falls within JEDEC MO-153



www.ti.com

#### PACKAGING INFORMATION

RUMENTS

Orderable Device	Status <sup>(1)</sup>	Package Type	Package Drawing	Pins	Package Qty	Eco Plan <sup>(2)</sup>	Lead/Ball Finish	MSL Peak Temp <sup>(3)</sup>
THS5641AIDW	ACTIVE	SOIC	DW	28	20	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
THS5641AIDWG4	ACTIVE	SOIC	DW	28	20	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
THS5641AIDWR	ACTIVE	SOIC	DW	28	1000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
THS5641AIDWRG4	ACTIVE	SOIC	DW	28	1000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
THS5641AIPW	ACTIVE	TSSOP	PW	28	50	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
THS5641AIPWG4	ACTIVE	TSSOP	PW	28	50	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
THS5641AIPWR	ACTIVE	TSSOP	PW	28	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
THS5641AIPWRG4	ACTIVE	TSSOP	PW	28	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM

<sup>(1)</sup> The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details. TBD: The Pb-Free/Green conversion plan has not been defined.

**Pb-Free (RoHS):** TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

**Pb-Free (RoHS Exempt):** This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

<sup>(3)</sup> MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

**Important Information and Disclaimer:**The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

### TAPE AND REEL INFORMATION





## QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE




*All dimensions are nominal												
Device		Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
THS5641AIDWR	SOIC	DW	28	1000	330.0	32.4	11.35	18.67	3.1	16.0	32.0	Q1
THS5641AIPWR	TSSOP	PW	28	2000	330.0	16.4	6.9	10.2	1.8	12.0	16.0	Q1



## PACKAGE MATERIALS INFORMATION

11-Mar-2008



\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
THS5641AIDWR	SOIC	DW	28	1000	346.0	346.0	49.0
THS5641AIPWR	TSSOP	PW	28	2000	346.0	346.0	33.0

#### **IMPORTANT NOTICE**

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Amplifiers	amplifier.ti.com	Audio	www.ti.com/audio
Data Converters	dataconverter.ti.com	Automotive	www.ti.com/automotive
DLP® Products	www.dlp.com	Broadband	www.ti.com/broadband
DSP	dsp.ti.com	Digital Control	www.ti.com/digitalcontrol
Clocks and Timers	www.ti.com/clocks	Medical	www.ti.com/medical
Interface	interface.ti.com	Military	www.ti.com/military
Logic	logic.ti.com	Optical Networking	www.ti.com/opticalnetwork
Power Mgmt	power.ti.com	Security	www.ti.com/security
Microcontrollers	microcontroller.ti.com	Telephony	www.ti.com/telephony
RFID	www.ti-rfid.com	Video & Imaging	www.ti.com/video
RF/IF and ZigBee® Solutions	www.ti.com/lprf	Wireless	www.ti.com/wireless

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2009, Texas Instruments Incorporated