

60 A VRPower® Integrated Power Stage


DESCRIPTION

The SiC620 and SiC620A are integrated power stage solutions optimized for synchronous buck applications to offer high current, high efficiency, and high power density performance. Packaged in Vishay's proprietary 5 mm x 5 mm MLP package, SiC620 and SiC620A enables voltage regulator designs to deliver up to 60 A continuous current per phase.

The internal power MOSFETs utilizes Vishay's state-of-the-art Gen IV TrenchFET technology that delivers industry benchmark performance to significantly reduce switching and conduction losses.

The SiC620 and SiC620A incorporates an advanced MOSFET gate driver IC that features high current driving capability, adaptive dead-time control, an integrated bootstrap Schottky diode, a thermal warning (THWn) that alerts the system of excessive junction temperature, and zero current detect to improve light load efficiency. The drivers are also compatible with a wide range of PWM controllers and supports tri-state PWM, 3.3 V (SiC620A) / 5 V (SiC620) PWM logic.

FEATURES





- Vishay's Gen IV MOSFET technology and a low-side MOSFET with integrated Schottky diode
- Delivers up to 60 A continuous current
- 95 % peak efficiency
- High frequency operation up to 1.5 MHz
- Power MOSFETs optimized for 12 V input stage
- 3.3 V (SiC620A) / 5 V (SiC620) PWM logic with tri-state and hold-off
- Zero current detect control for light load efficiency improvement
- Low PWM propagation delay (< 20 ns)
- Thermal monitor flag
- Under voltage lockout for V_{CIN}
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

APPLICATIONS

• Multi-phase VRDs for CPU, GPU, and memory

TYPICAL APPLICATION DIAGRAM




Fig. 1 - SiC620 and SiC620A Typical Application Diagram



PINOUT CONFIGURATION




Fig. 2 - SiC620 and SiC620A Pin Configuration

PIN CONFIG	PIN CONFIGURATION				
PIN NUMBER	NAME	FUNCTION			
1	PWM	PWM control input			
2	ZCD_EN#	ZCD control. Active low			
3	V_{CIN}	Supply voltage for internal logic circuitry			
4, 32	C_GND	Analog ground for the driver IC			
5	BOOT	High-side driver bootstrap voltage			
6	GH	High-side gate signal			
7	PHASE	Return path of high-side gate driver			
8 to 11, 34	V_{IN}	Power stage input voltage. Drain of high-side MOSFET			
12 to 15, 28, 35	P_{GND}	Power ground			
16 to 26	V_{SWH}	Switch node of the power stage			
27, 33	GL	Low-side gate signal			
29	V_{DRV}	Supply voltage for internal gate driver			
30	THWn	Thermal warning open drain output			
31	DSBL#	Disable pin. Active low			

ORDERING INFORMATION					
PART NUMBER	PACKAGE	MARKING CODE	OPTION		
SiC620CD-T1-GE3	PowerPAK MLP55-31L	SiC620	5 V PWM optimized		
SiC620ACD-T1-GE3	PowerPAK MLP55-31L	SiC620A	3.3 V PWM optimized		
SiC620DB / SiC620ADB		Reference board			

Vishay Siliconix

ABSOLUTE MAXIMUM RATING	S		
ELECTRICAL PARAMETER	CONDITIONS	LIMIT	UNIT
Input Voltage	V _{IN}	-0.3 to +25	
Control Logic Supply Voltage	V _{CIN}	-0.3 to +7	
Drive Supply Voltage	V _{DRV}	-0.3 to +7	
Switch Node (DC voltage)	V	-0.3 to +25	
Switch Node (AC voltage) (1)	V _{SWH}	-7 to +30	
BOOT Voltage (DC voltage)	V	32	V
BOOT Voltage (AC voltage) (2)	V _{BOOT}	38	
BOOT to PHASE (DC voltage)		-0.3 to +7	
BOOT to PHASE (AC voltage) (3)	V _{BOOT-PHASE}	-0.3 to +8	
All Logic Inputs and Outputs (PWM, DSBL#, and THWn)		-0.3 to V _{CIN} +0.3	
Output Current, I _{OUT(AV)} (4)	f _S = 300 kHz, V _{IN} = 12 V, V _{OUT} = 1.8 V	60	Α
Output Current, IOUT(AV)	f _S = 1 MHz, V _{IN} = 12 V, V _{OUT} = 1.8 V	50	7
Max. Operating Junction Temperature	T _J	150	
Ambient Temperature	T _A	-40 to +125	°C
Storage Temperature	T _{stg}	-65 to +150	
Electrostatic Discharge Protection	Human body model, JESD22-A114	3000	V
Electrostatic Discharge Protection	Charged device model, JESD22-C101	1000	V

Notes

- Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings
 only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the
 specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.
- $^{(1)}$ The specification values indicated "AC" is V_{SWH} to P_{GND} -8 V (< 20 ns, 10 μ J), min. and 30 V (< 50 ns), max.
- (2) The specification value indicates "AC voltage" is V_{BOOT} to P_{GND}, 38 V (< 50 ns) max.
- (3) The specification value indicates "AC voltage" is V_{BOOT} to V_{PHASE}, 8 V (< 20 ns) max.
- (4) Output current rated with testing evaluation board at T_A = 25 °C with natural convection cooling. The rating is limited by the peak evaluation board temperature, T_J

RECOMMENDED OPERATING RANGE							
ELECTRICAL PARAMETER	MINIMUM	TYPICAL	MAXIMUM	UNIT			
Input Voltage (V _{IN})	4.5	-	18				
Drive Supply Voltage (V _{DRV})	4.5	5	5.5				
Control Logic Supply Voltage (V _{CIN})	4.5	5	5.5	V			
Switch Node (V _{SWH} , DC voltage)	-	-	18				
BOOT to PHASE (V _{BOOT-PHASE} , DC voltage)	4	4.5	5.5				
Thermal Resistance from Junction to Ambient	-	10.6	-	°C/W			
Thermal Resistance from Junction to Case	-	1.6	-	C/VV			



Vishay Siliconix

DADAMETER	CVACCO	TEGT OCHIDITION	LIMITS			114117	
PARAMETER	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNII	
POWER SUPPLY							
Control Logic Supply Current		$V_{DSBL\#} = 0 V$, no switching	-	12	-	Ι	
Control Logic Supply Current	I _{VCIN}	$V_{DSBL\#} = 5 \text{ V}$, no switching, $V_{PWM} = FLOAT$	-	300	-	μΑ	
		$V_{DSBL\#} = 5 \text{ V}, f_S = 300 \text{ kHz}, D = 0.1$	-	380	-		
		$f_S = 300 \text{ kHz}, D = 0.1$	-	15	25	mΔ	
Drive Supply Current	I _{VDRV}	$f_S = 1 \text{ MHz}, D = 0.1$	-	50	-	ША	
Brive Supply Surrent	IVDRV	$V_{DSBL\#} = 0 V$, no switching	-	25	-	пΑ	
		$V_{DSBL\#} = 5 V$, no switching	-	60	-	μ, τ	
BOOTSTRAP SUPPLY							
Bootstrap Diode Forward Voltage	V _F	$I_F = 2 \text{ mA}$			0.4	V	
PWM CONTROL INPUT (SiC620)							
Rising Threshold	V _{TH_PWM_R}		3.4	3.8	4.2		
Falling Threshold	$V_{TH_PWM_F}$		0.72	0.9	1.1		
Tri-state Voltage	V _{TRI}	$V_{PWM} = FLOAT$	-	2.3	-	V	
Tri-state Rising Threshold	V _{TRI_TH_R}		0.9	1.15	1.38		
Tri-state Falling Threshold	$V_{TRI_TH_F}$		3	3.3	3.6		
Tri-state Rising Threshold Hysteresis	V _{HYS_TRI_R}		-	225	-	m\/	
Tri-state Falling Threshold Hysteresis	V _{HYS_TRI_F}		-		-	1110	
PWM Input Current	I _{PWM}	$V_{PWM} = 5 V$	-	-	350	υΑ	
·		$V_{PWM} = 0 V$	-	-	-350	P" 1	
PWM CONTROL INPUT (SiC620A)			1	1	1	ı	
Rising Threshold	V _{TH_PWM_R}		2.2	2.45	2.7		
Falling Threshold	$V_{TH_PWM_F}$		0.72	0.9	1.1		
Tri-state Voltage	V_{TRI}	V _{PWM} = FLOAT	-	1.8	-	V	
Tri-state Rising Threshold	$V_{TRI_TH_R}$		0.9	1.15	1.38		
Tri-state Falling Threshold	$V_{TRI_TH_F}$		1.95	2.2	2.45		
Tri-state Rising Threshold Hysteresis	V _{HYS_TRI_R}		-	250	-	mV	
Tri-state Falling Threshold Hysteresis	V _{HYS_TRI_F}		-	300	-		
PWM Input Current	I _{PWM}	$V_{PWM} = 3.3 \text{ V}$	-	-	225	Δ	
1 WW Input Guirent	PWM	$V_{PWM} = 0 V$	-	-	-225	μΑ μΑ ν ν ν ν ν ν ν ν ν ν ν ν ν ν ν ν ν	
TIMING SPECIFICATIONS							
Tri-State to GH/GL Rising Propagation Delay	t _{PD_TRI_R}		-	30	-		
Tri-state Hold-Off Time	t _{TSHO}		-	130	-		
GH - Turn Off Propagation Delay	t _{PD_OFF_GH}		=.	15	-		
GH - Turn On Propagation Delay (Dead time rising)	t _{PD_ON_GH}	No load, see fig. 4	-	10	-		
GL - Turn Off Propagation Delay	t _{PD_OFF_GL}		-	12	-	ns	
GL - Turn On Propagation Delay (Dead time falling)	t _{PD_ON_GL}		-	10	-		
DSBL# Lo to GH/GL Falling Propagation Delay	t _{PD_DSBL#_} F	Fig. 5	_	15	-		
PWM Minimum On-Time	t _{PWM_ON_MIN}		30	-	-	1	

ELECTRICAL SPECIFICATION (DSBL# = ZCD_EN# = 5 V, V		$_{\rm RV}$ and $\rm V_{CIN}$ = 5 V, $\rm T_A$ = 25 °C)				
PARAMETER	SYMBOL	TEST CONDITION		LIMITS		
PARAMETER	STIMBUL	1EST CONDITION	MIN.	TYP.	MAX.	UNIT
DSBL# ZCD_EN# INPUT						
DCDI # Logio logi: t Voltago	V _{IH_DSBL#}	Input logic high	2	-	-	
DSBL# Logic Input Voltage	V _{IL_DSBL#}	Input logic low	-	-	0.8	V
ZCD FNH Logic logist Voltage	V _{IH_ZCD_EN#}	Input logic high	2	-	-	\ \ \
ZCD_EN# Logic Input Voltage	V _{IL_ZCD_EN#}	Input logic low	-	-	0.8	Ì
PROTECTION						
Under Voltage Leekeut	V	V _{CIN} rising, on threshold	-	3.7	4.1	V
Under Voltage Lockout	V_{UVLO}	V _{CIN} falling, off threshold	2.7	3.1	-	'
Under Voltage Lockout Hysteresis	V _{UVLO_HYST}		-	575	-	mV
THWn Flag Set (2)	T _{THWn_SET}		-	160	-	
THWn Flag Clear (2)	T _{THWn_CLEAR}		-	135	-	°C
THWn Flag Hysteresis (2)	T _{THWn_HYST}		-	25	-	ĺ
THWn Output Low	V _{OL_THWn}	I _{THWn} = 2 mA	-	0.02	-	V

Notes

DETAILED OPERATIONAL DESCRIPTION

PWM Input with Tri-state Function

The PWM input receives the PWM control signal from the VR controller IC. The PWM input is designed to be compatible with standard controllers using two state logic (H and L) and advanced controllers that incorporate tri-state logic (H, L and tri-state) on the PWM output. For two state logic, the PWM input operates as follows. When PWM is driven above $V_{\text{PWM TH R}}$ the low-side is turned on and the high-side is turned on. When PWM input is driven below V_{PWM TH F} the high-side is turned OFF and the low-side is turned ON. For tri-state logic, the PWM input operates as previously stated for driving the MOSFETs. However, there is an third state that is entered as the PWM output of tri-state compatible controller enters its high impedance state during shut-down. The high impedance state of the controller's PWM output allows the SiC620 and SiC620A to pull the PWM input into the tri-state region (see PWM Timing Diagram). If the PWM input stays in this region for the tri-state hold-off period, t_{TSHO} , both high-side and low-side MOSFETs are turned OFF. This function allows the VR phase to be disabled without negative output voltage swing caused by inductor ringing and saves a Schottky diode clamp. The PWM and tri-state regions are separated by hysteresis to prevent false triggering. The SiC620A incorporates PWM voltage thresholds that are compatible with 3.3 V logic and the SiC620 thresholds are compatible with 5 V logic.

Disable (DSBL#)

In the low state, the DSBL# pin shuts down the driver IC and disables both high-side and low-side MOSFETs. In this state, standby current is minimized. If DSBL# is left unconnected, an internal pull-down resistor will pull the pin to $C_{\mbox{\footnotesize GND}}$ and shut down the IC.

Diode Emulation Mode (ZCD EN#)

When ZCD_EN# pin is logic Low and PWM signal switches Low, GL is forced on (after normal BBM time). During this time, it is under control of the ZCD (zero crossing detect) comparator. If, after the internal blanking delay, the inductor current becomes zero, the low-side is turned off. This improves light load efficiency by avoiding discharge of output capacitors. If PWM enters tri-state, then device will go into normal tri-state mode after tri-state delay. The GL output will be turned off regardless of Inductor current, this is an alternative method of improving light load efficiency by reducing switching losses.

Thermal Shutdown Warning (THWn)

The THWn pin is an open drain signal that flags the presence of excessive junction temperature. Connect with a maximum of $20~\text{k}\Omega$, to $V_{\text{CIN}}.$ An internal temperature sensor detects the junction temperature. The temperature threshold is 160 °C. When this junction temperature is exceeded the THWn flag is set. When the junction temperature drops below 135 °C the device will clear the THWn signal. The SiC620 and SiC620A do not stop operation when the flag is set. The decision to shutdown must be made by an external thermal control function.

Voltage Input (V_{IN})

This is the power input to the drain of the high-side power MOSFET. This pin is connected to the high power intermediate BUS rail.

⁽¹⁾ Typical limits are established by characterization and are not production tested.

⁽²⁾ Guaranteed by design.

Switch Node (V_{SWH} and PHASE)

The switch node, V_{SWH} , is the circuit power stage output. This is the output applied to the power inductor and output filter to deliver the output for the buck converter. The PHASE pin is internally connected to the switch node V_{SWH} . This pin is to be used exclusively as the return pin for the BOOT capacitor. A 20 k Ω resistor is connected between GH and PHASE to provide a discharge path for the HS MOSFET in the event that V_{CIN} goes to zero while V_{IN} is still applied.

Ground Connections (C_{GND} and P_{GND})

 P_{GND} (power ground) should be externally connected to C_{GND} (control signal ground). The layout of the printed circuit board should be such that the inductance separating C_{GND} and P_{GND} is minimized. Transient differences due to inductance effects between these two pins should not exceed 0.5 V

Control and Drive Supply Voltage Input (VDRV, VCIN)

 V_{CIN} is the bias supply for the gate drive control IC. V_{DRV} is the bias supply for the gate drivers. It is recommended to separate these pins through a resistor. This creates a low pass filtering effect to avoid coupling of high frequency gate drive noise into the IC.

Bootstrap Circuit (BOOT)

The internal bootstrap diode and an external bootstrap capacitor form a charge pump that supplies voltage to the BOOT pin. An integrated bootstrap diode is incorporated so that only an external capacitor is necessary to complete the bootstrap circuit. Connect a boot strap capacitor with one leg tied to BOOT pin and the other tied to PHASE pin.

Shoot-Through Protection and Adaptive Dead Time

The SiC620 and SiC620A have an internal adaptive logic to avoid shoot through and optimize dead time. The shoot through protection ensures that both high-side and low-side MOSFETs are not turned ON at the same time. The adaptive dead time control operates as follows. The HS and LS gate voltages are monitored to prevent the one turning ON from tuning ON until the other's gate voltage is sufficiently low (< 1 V). Built in delays also ensure that one power MOS is completely OFF, before the other can be turned ON. This feature helps to adjust dead time as gate transitions change with respect to output current and temperature. Change with respect to output current and temperature.

Under Voltage Lockout (UVLO)

During the start up cycle, the UVLO disables the gate drive holding high-side and low-side MOSFET gates low until the supply voltage rail has reached a point at which the logic circuitry can be safely activated. The SiC620, SiC620A also incorporates logic to clamp the gate drive signals to zero when the UVLO falling edge triggers the shutdown of the device. As an added precaution, a 20 k Ω resistor is connected between GH and PHASE to provide a discharge path for the HS MOSFET.

FUNCTIONAL BLOCK DIAGRAM




Fig. 3 - SiC620 and SiC620A Functional Block Diagram

ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishav.com/doc?91000



DEVICE TRUTH T	DEVICE TRUTH TABLE							
DSBL#	ZCD_EN#	PWM	GH	GL				
Open	X	Х	L	L				
L	X	X	L	L				
н	L	L	L	H, I _L > 0 A L, I _L < 0 A				
Н	L	Н	Н	L				
Н	L	Tri-state	L	L				
Н	Н	L	L	Н				
Н	Н	Н	Н	L				
Н	Н	Tri-state	L	L				

PWM TIMING DIAGRAM




Fig. 4 - Definition of PWM Logic and Tri-state

DSBL# PROPAGATION DELAY




Fig. 5 - DSBL# Falling Propagation Delay



ELECTRICAL CHARACTERISTICS

Test condition: $V_{IN} = 12 \text{ V}$, $V_{DRV} = V_{CIN} = 5 \text{ V}$, $ZCD_EN\# = 5 \text{ V}$, $V_{OUT} = 1.8 \text{ V}$, $V_{OUT} = 250 \text{ nH}$ (DCR = $0.32 \text{ m}\Omega$), $T_A = 25 ^{\circ}C$, natural convection cooling (All power loss and normalized power loss curves show SiC620 and SiC620A losses only unless otherwise stated)




Fig. 6 - Efficiency vs. Output Current




Fig. 7 - Power Loss vs. Output Current




Fig. 8 - Power Loss vs. Input Voltage




Fig. 9 - Safe Operating Area




Fig. 10 - Power Loss vs. Switching Frequency




Fig. 11 - Power Loss vs. Drive Supply Voltage






Fig. 12 - Power Loss vs. Output Voltage




Fig. 13 - Driver Supply Current vs. Driver Supply Voltage




Fig. 14 - Driver Supply Current vs. Output Current




Fig. 15 - Power Loss vs. Output Inductor




Fig. 16 - Driver Supply Current vs. Switching Frequency




Fig. 17 - UVLO Threshold vs. Temperature






Fig. 18 - PWM Threshold vs. Temperature (SiC620A)




Fig. 19 - PWM Threshold vs. Temperature (SiC620)




Fig. 20 - DSBL# Threshold vs. Temperature




Fig. 21 - PWM Threshold vs. Driver Supply Voltage (SiC620A)




Fig. 22 - PWM Threshold vs. Driver Supply Voltage (SiC620)




Fig. 23 - ZCD_EN# Threshold vs. Driver Supply Voltage






Fig. 24 - DSBL# vs. Driver Input Voltage




Fig. 25 - DSBL# Pull-Down Current vs. Temperature




Fig. 26 - Boot Diode Forward Voltage vs. Temperature




Fig. 27 - Driver Shutdown Current vs. Temperature





Fig. 28 - Driver Supply Current vs. Temperature




PCB LAYOUT RECOMMENDATIONS

Step 1: V_{IN}/GND Planes and Decoupling




- 1. Layout V_{IN} and P_{GND} planes as shown above
- 2. Ceramic capacitors should be placed right between V_{IN} and $P_{\text{GND}},$ and very close to the device for best decoupling effect
- Difference values / packages of ceramic capacitors should be used to cover entire decoupling spectrum e.g. 1210, 0805, 0603 and 0402
- Smaller capacitance value, closer to device V_{IN} pin(s)
 better high frequency noise absorbing

Step 2: V_{SWH} Plane




- Connect output inductor to DrMOS with large plane to lower the resistance
- If any snubber network is required, place the components as shown above and the network can be placed at bottom

Step 3: V_{CIN}/V_{DRV} Input Filter



- The V_{CIN}/V_{DRV} input filter ceramic cap should be placed very close to IC. It is recommended to connect two caps separately.
- 2. C_{VCIN} cap should be placed between pin 3 and pin 4 (C_{GND} of driver IC) to achieve best noise filtering.
- 3. C_{VDRV} cap should be placed between pin 28 (P_{GND} of driver IC) and pin 29 to provide maximum instantaneous driver current for low-side MOSFET during switching cycle
- 4. For connecting C_{VCIN} analog ground, it is recommended to use large plane to reduce parasitic inductance.


Step 4: BOOT Resistor and Capacitor Placement



- These components need to be placed very close to IC, right between PHASE (pin 7) and BOOT (pin 5).
- To reduce parasitic inductance, chip size 0402 can be used.


Vishay Siliconix

Step 5: Signal Routing




- 1. Route the PWM / ZCD_EN# / DSBL# / THWn signal traces out of the top left corner next DrMOS pin 1.
- PWM signal is very important signal, both signal and return traces need to pay special attention of not letting this trace cross any power nodes on any layer.
- 3. It is best to "shield" traces form power switching nodes, e.g. V_{SWH} , to improve signal integrity.
- GL (pin 27) has been connected with GL pad internally and does not need to connect externally.

Step 6: Adding Thermal Relief Vias



- Thermal relief vias can be added on the V_{IN} and P_{GND} pads to utilize inner layers for high-current and thermal dissipation.
- 2. To achieve better thermal performance, additional vias can be put on V_{IN} plane and P_{GND} plane.
- 3. V_{SWH} pad is a noise source and not recommended to put vias on this plane.
- 4. 8 mil drill for pads and 10 mils drill for plane can be the optional via size. Vias on pad may drain solder during assembly and cause assembly issue. Please consult with the assembly house for guideline.

Step 7: Ground Connection



- It is recommended to make single connection between C_{GND} and P_{GND} and this connection can be done on top layer.
- It is recommended to make the whole inner 1 layer (next to top layer) ground plane and separate them into C_{GND} and P_{GND} plane.
- 3. These ground planes provide shielding between noise source on top layer and signal trace on bottom layer.

Multi-Phases VRPower PCB Layout

Following is an example for 6 phase layout. As can be seen, all the VRPower stages are lined in X-direction compactly with decoupling caps next to them. The inductors are placed as close as possible to the SiC620 and SiC620A to minimize the PCB copper loss. Vias are applied on all PADs (V_{IN} , P_{GND} , C_{GND}) of the SiC620 and SiC620A to ensure that both electrical and thermal performance are excellent. Large copper planes are used for all the high current loops, such as V_{IN} , V_{SWH} , V_{OUT} and P_{GND} . These copper planes are duplicated in other layers to minimize the inductance and resistance. All the control signals are routed from the SiC620 and SiC620A to a controller placed to the north of the power stage through inner layers to avoid the overlap of high current loops. This achieves a compact design with the output from the inductors feeding a load located to the south of the design as shown in the figure.




Fig. 29 - Multi - Phase VRPower Layout Top View






Fig. 30 - Multi - Phase VRPower Layout Bottom View


RECOMMENDED LAND PATTERN POWERPAK MLP55-31L








Land pattern for MLP55-31L




All dimensions in millimeters



PACKAGE OUTLINE DRAWING MLP55-31L



5114	MILLIMETERS		INCHES			
DIM.	MIN.	NOM.	MAX.	MIN.	NOM.	MAX.
A (8)	0.70	0.75	0.80	0.027	0.029	0.031
A1	0.00	-	0.05	0.000	-	0.002
A2		0.20 ref.			0.008 ref.	
b ⁽⁴⁾	0.20	0.25	0.30	0.008	0.010	0.012
D		5.00 BSC			0.196 BSC	
е		0.50 BSC			0.019 BSC	
E		5.00 BSC			0.196 BSC	
L	0.35	0.40	0.45	0.013	0.015	0.017
N (3)		32		32		
Nd ⁽³⁾		8		8		
Ne ⁽³⁾		8		8		
D2-1	0.98	1.03	1.08	0.039	0.041	0.043
D2-2	0.98	1.03	1.08	0.039	0.041	0.043
D2-3	1.87	1.92	1.97	0.074	0.076	0.078
D2-4		0.30 BSC		0.012 BSC		
D2-5	1.00	1.05	1.10	0.039	0.041	0.043
E2-1	1.27	1.32	1.37	0.050	0.052	0.054
E2-2	1.93	1.98	2.03	0.076	0.078	0.080
E2-3	3.75	3.80	3.82	0.148	0.150	0.152
E2-4	0.45 BSC				0.018 BSC	
K1		0.67 BSC		0.026 BSC		
K2		0.22 BSC			0.008 BSC	
K3		1.25 BSC			0.049 BSC	






Vishay Siliconix

DIM.	MILLIMETERS			INCHES			
DIM.	MIN.	NOM.	MAX.	MIN.	NOM.	MAX.	
K4		0.05 BSC			0.002 BSC		
K5	0.38 BSC			0.015 BSC			
K6	0.12 BSC			0.005 BSC			
K7	0.40 BSC			0.016 BSC			
K8		0.40 BSC			0.016 BSC		
K9		0.40 BSC			0.016 BSC		
K10	0.85 BSC				0.033 BSC		
K11	0.40 BSC 0.016 BSC						
K12		0.40 BSC			0.016 BSC		

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see www.vishay.com/ppg?62922.

PowerPAK® MLP55-31L Case Outline



lop view	Side view	Bottom view
=		

DIM	MILLIMETERS		INCHES			
DIM.	MIN.	NOM.	MAX.	MIN.	NOM.	MAX.
A (8)	0.70	0.75	0.80	0.027	0.029	0.031
A1	0.00	-	0.05	0.000	-	0.002
A2		0.20 ref.			0.008 ref.	
b ⁽⁴⁾	0.20	0.25	0.30	0.008	0.010	0.012
D	4.90	5.00	5.10	0.193	0.196	0.200
е		0.50 BSC			0.019 BSC	
Е	4.90	5.00	5.10	0.193	0.196	0.200
L	0.35	0.40	0.45	0.013	0.015	0.017
N ⁽³⁾		32			32	
Nd ⁽³⁾		8			8	
Ne ⁽³⁾		8			8	
D2-1	0.98	1.03	1.08	0.039	0.041	0.043
D2-2	0.98	1.03	1.08	0.039	0.041	0.043
D2-3	1.87	1.92	1.97	0.074	0.076	0.078
D2-4		0.30 BSC		0.012 BSC		
D2-5	1.00	1.05	1.10	0.039	0.041	0.043
E2-1	1.27	1.32	1.37	0.050	0.052	0.054
E2-2	1.93	1.98	2.03	0.076	0.078	0.080
E2-3	3.75	3.80	3.82	0.148	0.150	0.152
E2-4		0.45 BSC			0.018 BSC	
F1		0.20 BSC		0.008 BSC		
F2		0.20 BSC			0.008 BSC	
K1	0.67 BSC			0.026 BSC		
K2	0.22 BSC			0.008 BSC		
K3	1.25 BSC			0.049 BSC		
K4	0.05 BSC			0.002 BSC		
K5		0.38 BSC			0.015 BSC	
K6		0.12 BSC			0.005 BSC	

Revision: 24-Oct-16 1 Document Number: 64909



Package Information

www.vishay.com

Vishay Siliconix

DIM.	MILLIMETERS			INCHES			
	MIN.	NOM.	MAX.	MIN.	NOM.	MAX.	
K7	0.40 BSC			0.40 BSC 0.016 BSC			
K8		0.40 BSC			0.016 BSC		
K9		0.40 BSC			0.016 BSC		
K10	0.85 BSC 0.033 BSC		0.85 BSC				
K11		0.40 BSC			0.016 BSC		
K12	0.40 BSC 0.016 BSC						

ECN: T16-0644-Rev. E, 24-Oct-16

DWG: 6025

Notes

- 1. Use millimeters as the primary measurement
- 2. Dimensioning and tolerances conform to ASME Y14.5M. 1994
- 3. N is the number of terminals,

Nd is the number of terminals in X-direction, and

Ne is the number of terminals in Y-direction

📐 The pin #1 identifier must be existed on the top surface of the package by using indentation mark or other feature of package body

Exact shape and size of this feature is optional


7. Package warpage max. 0.08 mm


Applied only for terminals

ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000




Recommended Land Pattern PowerPAK® MLP55-31L for SiC620, SiC620A





All dimensions in millimeters



Revision: 24-Jul-17 1 Document Number: 66944



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.