# **74AXP1G57**

# Low-power configurable multiple function gate

Rev. 4 — 7 October 2021

Product data sheet

### 1. General description

The 74AXP1G57 is a configurable multiple function gate with Schmitt-trigger inputs. The device can be configured as any of the following logic functions AND, OR, NAND, NOR, XNOR, inverter and buffer. All inputs can be connected directly to  $V_{CC}$  or GND.

This device ensures very low static and dynamic power consumption across the entire  $V_{CC}$  range from 0.7 V to 2.75 V. This device is fully specified for partial power down applications using  $I_{OFF}$ . The  $I_{OFF}$  circuitry disables the output, preventing the potentially damaging backflow current through the device when it is powered down.

#### 2. Features and benefits

- Wide supply voltage range from 0.7 V to 2.75 V
- Low input capacitance; C<sub>I</sub> = 0.5 pF (typical)
- Low output capacitance; C<sub>O</sub> = 1.0 pF (typical)
- Low dynamic power consumption; C<sub>PD</sub> = 2.7 pF at V<sub>CC</sub> = 1.2 V (typical)
- Low static power consumption; I<sub>CC</sub> = 0.6 μA (85 °C maximum)
- High noise immunity
- Complies with JEDEC standard:
  - JESD8-12A.01 (1.1 V to 1.3 V)
  - JESD8-11A.01 (1.4 V to 1.6 V)
  - JESD8-7A (1.65 V to 1.95 V)
  - JESD8-5A.01 (2.3 V to 2.7 V)
- · ESD protection:
  - HBM ANSI/ESDA/JEDEC JS-001 Class 2 exceeds 2 kV
  - CDM JESD22-C101E exceeds 1000 V
- Latch-up performance exceeds 100 mA per JESD 78 Class II
- Inputs accept voltages up to 2.75 V
- Low noise overshoot and undershoot < 10 % of V<sub>CC</sub>
- I<sub>OFF</sub> circuitry provides partial power-down mode operation
- · Multiple package options
- Specified from -40 °C to +85 °C



#### Low-power configurable multiple function gate

# 3. Ordering information

**Table 1. Ordering information** 

Type number	Package							
	Temperature range	Name	Description	Version				
74AXP1G57GM	-40 °C to +85 °C	XSON6	plastic extremely thin small outline package; no leads; 6 terminals; body 1 × 1.45 × 0.5 mm	SOT886				
74AXP1G57GN	-40 °C to +85 °C	XSON6	extremely thin small outline package; no leads; 6 terminals; body 0.9 × 1.0 × 0.35 mm	SOT1115				
74AXP1G57GS	-40 °C to +85 °C	XSON6	extremely thin small outline package; no leads; 6 terminals; body 1.0 × 1.0 × 0.35 mm	SOT1202				
74AXP1G57GX	-40 °C to +85 °C	X2SON6	plastic thermal enhanced extremely thin small outline package; no leads; 6 terminals; body 1.0 × 0.8 × 0.32 mm	SOT1255-2				


## 4. Marking

#### Table 2. Marking

Type number	Marking code[1]
74AXP1G57GM	RC
74AXP1G57GN	RC
74AXP1G57GS	RC
74AXP1G57GX	RC

<sup>[1]</sup> The pin 1 indicator is located on the lower left corner of the device, below the marking code.


# 5. Functional diagram



Low-power configurable multiple function gate

# 6. Pinning information

#### 6.1. Pinning



### 6.2. Pin description

Table 3. Pin description

Symbol	Pin	Description
В	1	data input
GND	2	ground (0 V)
A	3	data input
Υ	4	data output
V <sub>CC</sub>	5	supply voltage
С	6	data input

# 7. Functional description

#### Table 4. Function table

 $H = HIGH \ voltage \ level; \ L = LOW \ voltage \ level.$ 

Input	nput		
С	В	A	Y
L	L	L	Н
L	L	Н	L
L	Н	L	Н
L	Н	Н	L
Н	L	L	L
Н	L	Н	L
Н	Н	L	Н
Н	Н	Н	Н

#### Low-power configurable multiple function gate

### 7.1. Logic configurations

**Table 5. Function selection table** 

table 6.1 unction selection table				
Logic function	Figure			
2-input AND	see <u>Fig. 5</u>			
2-input AND with both inputs inverted	see <u>Fig. 8</u>			
2-input NAND with inverted input	see <u>Fig. 6</u> and <u>Fig. 7</u>			
2-input OR with inverted input	see <u>Fig. 6</u> and <u>Fig. 7</u>			
2-input NOR	see <u>Fig. 8</u>			
2-input NOR with both inputs inverted	see <u>Fig. 5</u>			
2-input XNOR	see <u>Fig. 9</u>			
Inverter	see <u>Fig. 10</u>			
Buffer	see <u>Fig. 11</u>			




Fig. 5. 2-input AND gate or 2-input NOR gate with both inputs inverted




Fig. 6. 2-input NAND gate with input B inverted or 2-input OR gate with inverted C input




Fig. 7. 2-input NAND gate with input C inverted or 2-input OR gate with inverted A input





Fig. 8. 2-input NOR gate or 2-input AND gate with both inputs inverted









Fig. 10. Inverter

#### Low-power configurable multiple function gate



### 8. Limiting values

#### Table 6. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	Min	Max	Unit
V <sub>CC</sub>	supply voltage		-0.5	3.3	V
I <sub>IK</sub>	input clamping current	V <sub>I</sub> < 0 V	-50	-	mA
VI	input voltage	[1]	-0.5	3.3	V
I <sub>OK</sub>	output clamping current	V <sub>O</sub> < 0 V	-50	-	mA
Vo	output voltage	[1]	-0.5	3.3	V
Io	output current	V <sub>O</sub> = 0 V to V <sub>CC</sub>	-	±20	mA
I <sub>CC</sub>	supply current		-	50	mA
I <sub>GND</sub>	ground current		-50	-	mA
T <sub>stg</sub>	storage temperature		-65	+150	°C
P <sub>tot</sub>	total power dissipation	$T_{amb} = -40  ^{\circ}\text{C} \text{ to } +85  ^{\circ}\text{C}$ [2]	-	250	mW

<sup>[1]</sup> The minimum input and output voltage ratings may be exceeded if the input and output current ratings are observed.

For SOT1115 (XSON6) package: P<sub>tot</sub> derates linearly with 3.2 mW/K above 71 °C.

For SOT1202 (XSON6) package: Ptot derates linearly with 3.3 mW/K above 74 °C.

For SOT1255-2 (X2SON6) package:  $P_{tot}$  derates linearly with 3.3 mW/K above 75 °C.

# 9. Recommended operating conditions

### Table 7. Recommended operating conditions

Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	Min	Max	Unit
V <sub>CC</sub>	supply voltage		0.7	2.75	V
VI	input voltage		0	2.75	V
V <sub>O</sub>	output voltage	Active mode	0	V <sub>CC</sub>	V
		Power-down mode; $V_{CC} = 0 \text{ V}$	0	2.75	V
T <sub>amb</sub>	ambient temperature		-40	+85	°C

<sup>[2]</sup> For SOT886 (XSON6) package: P<sub>tot</sub> derates linearly with 3.3 mW/K above 74 °C.

#### Low-power configurable multiple function gate

## 10. Static characteristics

**Table 8. Static characteristics** 


At recommended operating conditions, unless otherwise specified; voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions		Ta	<sub>mb</sub> = 25	°C	$T_{amb}$ = -40 °C to +85 °C		Unit
				Min	Тур	Max	Min	Max	
V <sub>T+</sub>	positive-going	see Fig. 12 and Fig. 13							
	threshold voltage	V <sub>CC</sub> = 0.75 V to 0.85 V		0.3V <sub>CC</sub>	-	0.8V <sub>CC</sub>	0.3V <sub>CC</sub>	0.8V <sub>CC</sub>	V
		V <sub>CC</sub> = 1.1 V to 1.95 V		0.4V <sub>CC</sub>	-	0.7V <sub>CC</sub>	0.4V <sub>CC</sub>	0.7V <sub>CC</sub>	V
		V <sub>CC</sub> = 2.3 V to 2.7 V		0.9	-	1.7	0.9	1.7	V
V <sub>T-</sub>	negative-going	see <u>Fig. 12</u> and <u>Fig. 13</u>							
	threshold voltage	V <sub>CC</sub> = 0.75 V to 0.85 V		0.2V <sub>CC</sub>	-	0.7V <sub>CC</sub>	0.2V <sub>CC</sub>	0.7V <sub>CC</sub>	V
		V <sub>CC</sub> = 1.1 V to 1.95 V		$0.3V_{CC}$	-	0.6V <sub>CC</sub>	0.3V <sub>CC</sub>	0.6V <sub>CC</sub>	V
		V <sub>CC</sub> = 2.3 V to 2.7 V		0.7	-	1.5	0.7	1.5	V
V <sub>H</sub>	hysteresis	see <u>Fig. 12</u> and <u>Fig. 13</u>							
	voltage	V <sub>CC</sub> = 0.75 V to 0.85 V		0.06V <sub>CC</sub>	-	0.5V <sub>CC</sub>	0.06V <sub>CC</sub>	0.5V <sub>CC</sub>	V
		V <sub>CC</sub> = 1.1 V to 1.95 V		0.1V <sub>CC</sub>	-	0.4V <sub>CC</sub>	0.1V <sub>CC</sub>	0.4V <sub>CC</sub>	V
		V <sub>CC</sub> = 2.3 V to 2.7 V		0.2	-	1.0	0.2	1.0	V
V <sub>OH</sub>	HIGH-level	$I_O = -20 \mu A; V_{CC} = 0.7 V$		-	0.69	-	-	-	V
	output voltage	I <sub>O</sub> = -100 μA; V <sub>CC</sub> = 0.75 V		0.65	-	-	0.65	-	V
		I <sub>O</sub> = -2 mA; V <sub>CC</sub> = 1.1 V		0.825	-	-	0.825	-	V
		$I_O = -3 \text{ mA}; V_{CC} = 1.4 \text{ V}$		1.05	-	-	1.05	-	V
		I <sub>O</sub> = -4.5 mA; V <sub>CC</sub> = 1.65 V		1.2	-	-	1.2	-	V
		$I_O = -8 \text{ mA}; V_{CC} = 2.3 \text{ V}$		1.7	-	-	1.7	-	V
V <sub>OL</sub>		$I_O = 20 \mu A; V_{CC} = 0.7 V$		-	0.01	-	-	-	V
	voltage	I <sub>O</sub> = 100 μA; V <sub>CC</sub> = 0.75 V		-	-	0.1	-	0.1	V
		I <sub>O</sub> = 2 mA; V <sub>CC</sub> = 1.1 V		-	-	0.275	-	0.275	V
		I <sub>O</sub> = 3 mA; V <sub>CC</sub> = 1.4 V		-	-	0.35	-	0.35	V
		I <sub>O</sub> = 4.5 mA; V <sub>CC</sub> = 1.65 V		-	-	0.45	-	0.45	V
		$I_O = 8 \text{ mA}; V_{CC} = 2.3 \text{ V}$		-	-	0.7	-	0.7	V
I <sub>I</sub>	input leakage current	V <sub>I</sub> = 0 V to 2.75 V; V <sub>CC</sub> = 0 V to 2.75 V	[1]	-	0.001	±0.1	-	±0.5	μΑ
l <sub>OFF</sub>	power-off leakage current	$V_1 \text{ or } V_0 = 0 \text{ V to } 2.75 \text{ V};$ $V_{CC} = 0 \text{ V}$	[1]	-	0.01	±0.1	-	±0.5	μΑ
ΔI <sub>OFF</sub>	additional power- off leakage current	V <sub>I</sub> or V <sub>O</sub> = 0 V or 2.75 V; V <sub>CC</sub> = 0 V to 0.1 V	[1]	-	0.02	±0.1	-	±0.5	μΑ
I <sub>CC</sub>	supply current	$V_I = 0 \text{ V or } V_{CC}; I_O = 0 \text{ A}$	[1]	-	0.01	0.3	-	0.6	μΑ
ΔI <sub>CC</sub>	additional supply current	$V_I = V_{CC} - 0.5 \text{ V}; I_O = 0 \text{ A};$ $V_{CC} = 2.5 \text{ V}$		-	2	100	-	150	μΑ

<sup>[1]</sup> All typical values are measured at  $V_{CC}$  = 1.2 V.

#### Low-power configurable multiple function gate

#### 10.1. Waveform transfer characteristics



## 11. Dynamic characteristics

#### **Table 9. Dynamic characteristics**

Voltages are referenced to GND (ground = 0 V); for test circuit, see Fig. 20.

Symbol	Parameter	Conditions	T,	<sub>amb</sub> = 25	°C	T <sub>amb</sub> = -40 °	°C to +85 °C	Unit
			Min	Min Typ[1] Max		Min	Max	1
t <sub>pd</sub>	propagation delay	A, B and C to Y; see Fig. 14 [2]						
		V <sub>CC</sub> = 0.75 V to 0.85 V	3.5	13	50	2.9	125	ns
		V <sub>CC</sub> = 1.1 V to 1.3 V	1.8	5.0	8.4	1.6	8.4	ns
		V <sub>CC</sub> = 1.4 V to 1.6 V	1.6	3.8	5.4	1.4	5.8	ns
		V <sub>CC</sub> = 1.65 V to 1.95 V	1.3	3.2	4.4	1.2	4.8	ns
		V <sub>CC</sub> = 2.3 V to 2.7 V	0.9	2.6	3.4	0.8	3.7	ns
t <sub>t</sub>	transition time	V <sub>CC</sub> = 2.7 V; see <u>Fig. 14</u> [4]	-	-	-	1.0	-	ns
Cı	input capacitance	V <sub>I</sub> = 0 V or V <sub>CC</sub> ; V <sub>CC</sub> = 0 V to 2.75 V	-	0.5	-	-	-	pF
Co	output capacitance	V <sub>O</sub> = 0 V; V <sub>CC</sub> = 0 V	-	1.0	-	-	-	pF
C <sub>PD</sub>		$f_i = 1 \text{ MHz}; V_i = 0 \text{ V to } V_{CC}$ [5]						
	capacitance	V <sub>CC</sub> = 0.75 V to 0.85 V	-	2.6	-	-	-	pF
		V <sub>CC</sub> = 1.1 V to 1.3 V	-	2.7	-	-	-	pF
		V <sub>CC</sub> = 1.4 V to 1.6 V	-	2.8	-	-	-	pF
		V <sub>CC</sub> = 1.65 V to 1.95 V	-	2.9	-	-	125 n 8.4 n 5.8 n 4.8 n 3.7 n - n - p - p - p	pF
		V <sub>CC</sub> = 2.3 V to 2.7 V	-	3.3	-	-	-	pF

- [1] All typical values are measured at nominal  $V_{CC}$ .
- [2]  $t_{pd}$  is the same as  $t_{PLH}$  and  $t_{PHL}$ .
- [3] For additional propagation delay values at different load capacitances see Fig. 15 to Fig. 19.
- [4]  $t_t$  is the same as  $t_{THL}$  and  $t_{TLH}$ .
- [5]  $C_{PD}$  is used to determine the dynamic power dissipation ( $P_D$  in  $\mu$ W).

 $P_D = C_{PD} \times V_{CC}^2 \times f_i \times N + C_L \times V_{CC}^2 \times f_o$  where:

f<sub>i</sub> = input frequency in MHz;

f<sub>o</sub> = output frequency in MHz;

C<sub>L</sub> = output load capacitance in pF;


 $V_{CC}$  = supply voltage in V;

N = number of inputs switching.

7 / 17


#### Low-power configurable multiple function gate

### 11.1. Waveforms, graphs and test circuit




**Table 10. Measurement points** 

Supply voltage	Output	Input		
V <sub>CC</sub>	V <sub>M</sub>	V <sub>M</sub>	V <sub>I</sub>	$t_r = t_f$
0.75 V to 2.7 V	0.5V <sub>CC</sub>	0.5V <sub>CC</sub>	V <sub>CC</sub>	≤ 3.0 ns



#### Low-power configurable multiple function gate




 $T_{amb}$  = -40 °C to +85 °C unless otherwise specified.

(1) Minimum:  $V_{CC} = 1.6 \text{ V}$ 

(2) Typical:  $T_{amb}$  = 25 °C;  $V_{CC}$  = 1.5 V

(3) Maximum:  $V_{CC} = 1.4 \text{ V}$ 

Fig. 17. Additional t<sub>pd</sub> versus load capacitance




 $T_{amb}$  = -40 °C to +85 °C unless otherwise specified.

(1) Minimum:  $V_{CC} = 1.3 \text{ V}$ 

(2) Typical:  $T_{amb}$  = 25 °C;  $V_{CC}$  = 1.2 V

(3) Maximum:  $V_{CC} = 1.1 \text{ V}$ 

Fig. 18. Additional t<sub>pd</sub> versus load capacitance



 $T_{amb}$  = -40 °C to +85 °C unless otherwise specified.


(1) Minimum:  $V_{CC} = 0.85 \text{ V}$ 

(2) Typical:  $T_{amb}$  = 25 °C;  $V_{CC}$  = 0.8 V

(3) Maximum:  $V_{CC} = 0.75 \text{ V}$ 

Fig. 19. Additional t<sub>pd</sub> versus load capacitance

#### Low-power configurable multiple function gate



Test data is given in Table 11.

Definitions for test circuit:

 $R_L$  = Load resistance.

 $C_L$  = Load capacitance including jig and probe capacitance.

 $R_T$  = Termination resistance should be equal to the output impedance  $Z_o$  of the pulse generator.

 $V_{\text{EXT}}$  = External voltage for measuring switching times.

#### Fig. 20. Test circuit for measuring switching times

#### Table 11. Test data

Supply voltage	Load		V <sub>EXT</sub>		
V <sub>CC</sub>	CL	R <sub>L</sub>	t <sub>PLH</sub> , t <sub>PHL</sub> t <sub>PZH</sub> , t <sub>PHZ</sub> t <sub>PZL</sub> , t <sub>PLZ</sub>		t <sub>PZL</sub> , t <sub>PLZ</sub>
0.75 V to 2.7 V	5 pF	10 kΩ	0 V	0 V	2 × V <sub>CC</sub>

### Low-power configurable multiple function gate

# 12. Package outline




Fig. 21. Package outline SOT886 (XSON6)

#### Low-power configurable multiple function gate




Fig. 22. Package outline SOT1115 (XSON6)

#### Low-power configurable multiple function gate




Fig. 23. Package outline SOT1202 (XSON6)

#### Low-power configurable multiple function gate




Fig. 24. Package outline SOT1255-2 (X2SON6)

### Low-power configurable multiple function gate

### 13. Abbreviations

#### **Table 12. Abbreviations**

Acronym	Description
CDM	Charged Device Model
DUT	Device Under Test
ESD	ElectroStatic Discharge
НВМ	Human Body Model

# 14. Revision history

### **Table 13. Revision history**

Document ID	Release date	Data sheet status	Change notice	Supersedes		
74AXP1G57 v.4	20211007	Product data sheet	-	74AXP1G57 v.3		
Modifications:	Nexperia. • Legal texts ha • SOT1255 (X25	<ul> <li>The format of this data sheet has been redesigned to comply with the identity guidelines of Nexperia.</li> <li>Legal texts have been adapted to the new company name where appropriate.</li> <li>SOT1255 (X2SON6) package changed to SOT1255-2 (X2SON6) package.</li> <li>Table 6: Derating values for P<sub>tot</sub> total power dissipation updated.</li> </ul>				
74AXP1G57 v.3	20150916	Product data sheet	-	74AXP1G57 v.2		
Modifications:	Added type number 74AXP1G57GX (SOT1255/X2SON6).					
74AXP1G57 v.2	20131212	Product data sheet	-	74AXP1G57 v.1		
Modifications:	Specification status changed to product data sheet.					
74AXP1G57 v.1	20130625	Preliminary data sheet	-	-		

### 15. Legal information

#### **Data sheet status**

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions".
- The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at <a href="https://www.nexperia.com">https://www.nexperia.com</a>.

#### **Definitions**

**Draft** — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

#### **Disclaimers**

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal

#### Low-power configurable multiple function gate

injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <a href="http://www.nexperia.com/profile/terms">http://www.nexperia.com/profile/terms</a>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by sustained.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

**Translations** — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

#### **Trademarks**

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

74AXP1G57

All information provided in this document is subject to legal disclaimers

© Nexperia B.V. 2021. All rights reserved

### Low-power configurable multiple function gate

## **Contents**

1. General description	1
2. Features and benefits	1
3. Ordering information	
4. Marking	
5. Functional diagram	
6. Pinning information	
6.1. Pinning	
6.2. Pin description	3
7. Functional description	3
7.1. Logic configurations	
8. Limiting values	5
9. Recommended operating conditions	5
10. Static characteristics	6
10.1. Waveform transfer characteristics	7
11. Dynamic characteristics	7
11.1. Waveforms, graphs and test circuit	8
12. Package outline	
13. Abbreviations	
14. Revision history	15
15. Legal information	16

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com Date of release: 7 October 2021

<sup>©</sup> Nexperia B.V. 2021. All rights reserved