
ZD25LQ16A

DATASHEET



Contents

1	FE	ATURES	4
2	GE	NERAL DESCRIPTION	5
3	ME	EMORY ORGANIZATION	7
4	DE	VICE OPERATION	8
5		ATA PROTECTION	
6	ST	ATUS REGISTER	11
7	CC	DMMANDS DESCRIPTION	13
	7.1	Write Enable (WREN) (06H)	16
	7.2	WRITE DISABLE (WRDI) (04H)	16
	7.3	Write Enable for Volatile Status Register (50H)	16
	7.4	READ STATUS REGISTER (RDSR) (05H OR 35H)	17
	7.5	Write Status Register (WRSR) (01H)	17
	7.6	READ DATA BYTES (READ) (03H)	18
	7.7	READ DATA BYTES AT HIGHER SPEED (FAST READ) (OBH)	18
	7.8	DUAL OUTPUT FAST READ (3BH)	19
	7.9	Quad Output Fast Read (6BH)	
	7.10	Dual I/O Fast Read (BBH)	20
	7.11	Quad I/O Fast Read (EBH)	
	7.12	SET BURST WITH WRAP (77H)	
	7.13	PAGE PROGRAM (PP) (02H)	25
	7.14	Quad Page Program (32H)	
	7.15	SECTOR ERASE (SE) (20H)	28
	7.16	32KB BLOCK ERASE (BE) (52H)	28
	7.17	64KB BLOCK ERASE (BE) (D8H)	29
	7.18	CHIP ERASE (CE) (60/C7H)	29
	7.19	ENABLE/DISABLE SO TO OUTPUT RY/BY#(ESRY/DSRY) (70H/80H)	30
	7.20	DEEP POWER-DOWN (DP) (B9H)	31
	7.21	RELEASE FROM DEEP POWER-DOWN AND READ DEVICE ID (RDI) (ABH)	31
	7.22	READ MANUFACTURE ID/ DEVICE ID (REMS) (90H)	32
	7.23	READ MANUFACTURE ID/ DEVICE ID DUALI/O (92H)	33
	7.24	READ MANUFACTURE ID/ DEVICE ID QUADI/O (94H)	34
	7.25	READ IDENTIFICATION (RDID) (9FH)	34
	7.26	PROGRAM/ERASE SUSPEND (PES) (75H)	35
	7.27	PROGRAM/ERASE RESUME (PER) (7AH)	
	7.28	Erase Security Registers (44H)	
	7.29	Program Security Registers (42H)	37
	7.30	READ SECURITY REGISTERS (48H)	38

ZD25LQ16A

7.31	ENABLE RESET (66H) AND RESET (99H)	38
7.32	READ SERIAL FLASH DISCOVERABLE PARAMETER (5AH)	39
8 ELI	ECTRICAL CHARACTERISTICS	44
8.1	POWER-ON TIMING	44
8.2	Initial Delivery State	44
8.3	ABSOLUTE MAXIMUM RATINGS	44
8.4	CAPACITANCE MEASUREMENT CONDITIONS	45
8.5	DC CHARACTERISTICS	
8.6	AC CHARACTERISTICS	47
9 OR	DERING INFORMATION	49
10 F	PACKAGE INFORMATION	51
10.1	PACKAGE SOP8 150MIL	51
10.2	PACKAGE SOP8 208MIL	52
10.3	PACKAGE VSOP8 150MIL	53
10.4	PACKAGE VSOP8 208MIL	54
10.5	PACKAGE WSON 8 (6*5mm)	55
10.6	PACKAGE USON8 (3*4mm)	56
10.7	PACKAGE USON8 (4*4mm, 0.45 THICKNESS)	57
10.8	PACKAGE USON8 (3*3MM)	58
10.9	Раскаде LGA8 3*2мм	59
10.10	PACKAGE WLCSP	60
11 F	REVISION HISTORY	61



FEATURES

- · 16M-bit Serial Flash
 - -2048K-byte
 - -256 bytes per programmable page
- · Standard, Dual, Quad SPI
 - -Standard SPI: SCLK, CS#, SI, SO, WP#, HOLD#
 - -Dual SPI: SCLK, CS#, IO0, IO1, WP#, HOLD#
 - -Quad SPI: SCLK, CS#, IO0, IO1, IO2, IO3
- High Speed Clock Frequency
 - -104MHz for fast read with 30PF load
 - -Dual I/O Data transfer up to 208Mbits/s
 - -Quad I/O Data transfer up to 416Mbits/s
- Allows XIP(execute in place)operation⁽¹⁾
 - -Continuous Read With 8/16/32/64-byte Wrap
- Software/Hardware Write Protection
 - -Write protect all/portion of memory via software
 - -Enable/Disable protection with WP# Pin
 - -Top/Bottom Block selection
- Minimum 100,000 Program/Erase Cycles

Note: 1.Please contact Zetta for details.


- · Fast Program/Erase Speed
 - -Page Program time: 0.7ms typical
 - -Sector Erase time: 40ms typical
 - -Block Erase time: 0.15/0.18s typical
 - -Chip Erase time: 5s typical
- Flexible Architecture
 - -Uniform Sector of 4K-byte
 - -Uniform Block of 32/64k-byte
 - -Erase/Program Suspend/Resume
- Low Power Consumption
 - -8mA maximum active current
 - -5uA maximum power down current
- · Advanced security Features
 - -3*512-Byte Security Registers With OTP Lock
- · Single Power Supply Voltage
 - -Full voltage range:1.65~2.1V
- · Data retention
- -20-year data retention typical



GENERAL DESCRIPTION 2


The ZD25LQ16A (16M-bit) Serial flash supports the standard Serial Peripheral Interface (SPI), and supports the Dual/Quad SPI: Serial Clock, Chip Select, Serial Data I/O0 (SI), I/O1 (SO), I/O2 (WP#), and I/O3 (HOLD#). The Dual I/O data is transferred with speed of 208Mbits/s, the Quad I/O & Quad output data is transferred with speed of416Mbits/s.

CONNECTION DIAGRAM



8 - LEAD VSOP/SOP

BLOCK DIAGRAM





3 MEMORY ORGANIZATION

ZD25LQ16A

Each device has	Each block has	Each sector has	Each page has	
2M	64/32K	4K	256	bytes
8K	256/128	16	-	pages
512	16/8	-	-	sectors
32/64	-	-	-	blocks

UNIFORM BLOCK SECTOR ARCHITECTURE

ZD25LQ16A 64K Bytes Block Sector Architecture

Block	Sector	Address range		
	511	1FF000H	1FFFFFH	
31				
	496	1F0000H	1F0FFFH	
	495	1EF000H	1EFFFFH	
30				
	480	1E0000H	1E0FFFH	
	47	02F000H	02FFFFH	
2				
	32	020000H	020FFFH	
	31	01F000H	01FFFFH	
1				
	16	010000H	010FFFH	
	15	00F000H	00FFFFH	
0				
	0	000000H	000FFFH	

DEVICE OPERATION

SPI Mode

Standard SPI

The ZD25LQ16A features a serial peripheral interface on 4 signals bus: Serial Clock (SCLK), Chip Select (CS#), Serial Data Input (SI) and Serial Data Output (SO). Both SPI bus mode 0 and 3 are supported. Input data is latched on the rising edge of SCLK and data shifts out on the falling edge of SCLK.

Dual SPI

The ZD25LQ16A supports Dual SPI operation when using the "Dual Output Fast Read" and "Dual I/O Fast Read" (3BH and BBH) commands. These commands allow data to be transferred to or from the device at twice the rate of the standard SPI. When using the Dual SPI command the SI and SO pins become bidirectional I/O pins: IO0 and IO1.

Quad SPI

The ZD25LQ16A supports Quad SPI operation when using the "Quad Output Fast Read", "Quad I/O Fast Read", "Quad I/O Word Fast Read" (6BH, EBH, E7H) commands. These commands allow data to be transferred to or from the device at four times the rate of the standard SPI. When using the Quad SPI command the SI and SO pins become bidirectional I/O pins: IO0 and IO1, and WP# and HOLD# pins become IO2 and IO3. Quad SPI commands require the non-volatile Quad Enable bit (QE) in Status Register to be set.

Hold

The HOLD# signal goes low to stop any serial communications with the device, but doesn't stop the operation of write status register, programming, or erasing in progress.

The operation of HOLD, need CS# keep low, and starts on falling edge of the HOLD# signal, with SCLK signal being low (if SCLK is not being low, HOLD operation will not start until SCLK being low). The HOLD condition ends on rising edge of HOLD# signal with SCLK being low (If SCLK is not being low, HOLD operation will not end until SCLK beinglow).

The SO is high impedance, both SI and SCLK don't care during the HOLD operation, if CS# drives high during HOLD operation, it will reset the internal logic of the device. To re-start communication with chip, the HOLD# must be at high and then CS# must be at low.




Figure 1. Hold Condition

Data Protection

The ZD25LQ16A provide the following data protection methods:

- ♦ Write Enable (WREN) command: The WREN command is set the Write Enable Latch bit (WEL). The WEL bit will return to reset by the following situation:
 - -Power-Up
 - -Write Disable (WRDI)
 - -Write Status Register (WRSR)
 - -Page Program (PP)
 - -Sector Erase (SE) / Block Erase (BE) / Chip Erase (CE)
 - -software reset (66H+99H)
- Software Protection Mode: The Block Protect (BP4, BP3, BP2, BP1, and BP0) bits define the section of the memory array that can be read but not change.
- Hardware Protection Mode: WP# goes low to protect the BP0~BP4 bits and SRP0~1 bits.
- Deep Power-Down Mode: In Deep Power-Down Mode, all commands are ignored except the Release from Deep Power-Down Mode command and software reset (66H+99H).

Table1. ZD25LQ16A Protected area size (CMP=0)

;	Status F	Register	Conten	it	Memory Content					
BP4	BP3	BP2	BP1	BP0	Blocks	Addresses	Density	Portion		
Х	Х	0	0	0	NONE	NONE	NONE	NONE		
0	0	0	0	1	31	1F0000H-1FFFFFH	64KB	Upper 1/32		
0	0	0	1	0	30 to 31	1E0000H-1FFFFFH	128KB	Upper 1/16		
0	0	0	1	1	28 to 31	1C0000H-1FFFFFH	256KB	Upper 1/8		
0	0	1	0	0	24 to 31	180000H-1FFFFFH	512KB	Upper 1/4		
0	0	1	0	1	16 to 31	100000H-1FFFFFH	1M	Upper 1/2		
0	1	0	0	1	0	000000H-00FFFFH	64KB	Lower 1/32		
0	1	0	1	0	0 to 1	000000H-01FFFFH	128KB	Lower 1/16		
0	1	0	1	1	0 to 3	000000H-03FFFFH	256KB	Lower 1/8		
0	1	1	0	0	0 to 7	000000H-07FFFFH	512KB	Lower 1/4		
0	1	1	0	1	0 to 15	000000H-0FFFFFH	1M	Lower 1/2		
Х	Х	1	1	Х	0 to 31	000000H-1FFFFFH	2M	ALL		
1	0	0	0	1	31	1FF000H-1FFFFFH	4KB	Top Block		
1	0	0	1	0	31	1FE000H-1FFFFFH	8KB	Top Block		
1	0	0	1	1	31	1FC000H-1FFFFFH	16KB	Top Block		
1	0	1	0	Х	31	1F8000H-1FFFFFH	32KB	Top Block		
1	1	0	0	1	0	000000H-000FFFH	4KB	Bottom Block		
1	1	0	1	0	0	000000H-001FFFH	8KB	Bottom Block		
1	1	0	1	1	0	000000H-003FFFH	16KB	Bottom Block		
1	1	1	0	Х	0	000000H-007FFFH	32KB	Bottom Block		



ZD25LQ16A

Table1a. ZD25LQ16A Protected area size (CMP=1)

Status Register Content						Memory Content						
BP4	BP3	BP2	BP1	BP0	Blocks	Blocks Addresses		Portion				
Х	Х	0	0	0	0 to 31	000000H-1FFFFFH	2M	ALL				
0	0	0	0	1	0 to 30	000000H-1EFFFFH	1984KB	Lower 31/32				
0	0	0	1	0	0 to 29	000000H-1DFFFFH	1920KB	Lower 15/16				
0	0	0	1	1	0 to 27	000000H-1BFFFFH	1792KB	Lower 7/8				
0	0	1	0	0	0 to 23	000000H-17FFFFH	1536KB	Lower 3/4				
0	0	1	0	1	0 to 15	000000H-0FFFFFH	1M	Lower 1/2				
0	1	0	0	1	1 to 31	010000H-1FFFFFH	1984KB	Upper 31/32				
0	1	0	1	0	2 to 31	020000H-1FFFFFH	1920KB	Upper 15/16				
0	1	0	1	1	4 to 31	040000H-1FFFFFH	1792KB	Upper 7/8				
0	1	1	0	0	8 to 31	080000H-1FFFFFH	1536KB	Upper 3/4				
0	1	1	0	1	16 to 31	100000H-1FFFFFH	1M	Upper 1/2				
Х	Х	1	1	Х	NONE	NONE	NONE	NONE				
1	0	0	0	1	0 to 31	000000H-1FEFFFH	2044KB	L - 511/512				
1	0	0	1	0	0 to 31	000000H-1FDFFFH	2040KB	L - 255/256				
1	0	0	1	1	0 to 31	000000H-1FBFFFH	2032KB	L - 127/128				
1	0	1	0	Х	0 to 31	000000H-1F7FFFH	2016KB	L - 63/64				
1	1	0	0	1	0 to 31	001000H-1FFFFFH	2044KB	U - 511/512				
1	1	0	1	0	0 to 31	002000H-1FFFFFH	2040KB	U - 255/256				
1	1	0	1	1	0 to 31	004000H-1FFFFFH	2032KB	U - 127/128				
1	1	1	0	Х	0 to 31	008000H-1FFFFFH	2016KB	U - 63/64				



Status Register

S15	S14	S13	S12	S11	S10	S9	S8
SUS1	СМР	LB3	LB2	LB1	SUS2	QE	SRP1
S 7	S6	S5	S4	S 3	S2	S1	S0
SRP0	BP4	BP3	BP2	BP1	BP0	WEL	WIP

The status and control bits of the Status Register are as follows:

WIP bit

The Write in Progress (WIP) bit indicates whether the memory is busy in program/erase/write status register progress. When WIP bit sets to 1, means the device is busy in program/erase/write status register progress, when WIP bit sets 0, means the device is not in program/erase/write status register progress.

WEL bit

The Write Enable Latch (WEL) bit indicates the status of the internal Write Enable Latch. When set to 1 the internal Write Enable Latch is set, when set to 0 the internal Write Enable Latch is reset and no Write Status Register, Program or Erase command is accepted.

BP4, BP3, BP2, BP1, BP0 bits

The Block Protect (BP4, BP3, BP2, BP1, and BP0) bits are non-volatile. They define the size of the area to be software protected against Program and Erase commands. These bits are written with the Write Status Register (WRSR) command. When the Block Protect (BP4, BP3, BP2, BP1, BP0) bits are set to 1, the relevant memory area (as defined in Table1).becomes protected against Page Program (PP), Sector Erase (SE) and Block Erase (BE) commands. The Block Protect (BP4, BP3, BP2, BP1, and BP0) bits can be written provided that the Hardware Protected mode has not been set. The Chip Erase (CE) command is executed, if the Block Protect (BP2, BP1, and BP0) bits are 0 and CMP=0 or the Block Protect (BP2, BP1, and BP0) bits are 1 and CMP=1.

SRP1, SRP0 bits

The Status Register Protect (SRP1 and SRP0) bits are non-volatile Read/Write bits in the status register. The SRP bits control the method of write protection: software protection, hardware protection, power supply lock-down or one time programmable protection.

SRP1	SRP0	#WP	Status Register	Description	
0	0	Х	Software Protected	The Status Register can be written to after a Write Enable command, WEL=1.(Default)	
				WP#=0, the Status Register locked and cannot be written	
0	1	0	Hardware Protected	to.	
				WP#=1, the Status Register is unlocked and can be written	
0	1	1	Hardware Unprotected	to after a Write Enable command, WEL=1.	
1	0	V	Х	(D () () ()	Status Register is protected and cannot be written to again
'	0	^	Power Supply Lock-Down(1	until the next Power-Down, Power-Up cycle.	
1	1	Х	One Time Program(1)	Status Register is permanently protected and cannot be written to.	

NOTE:

1. When SRP1, SRP0= (1, 0), a Power-Down, Power-Up cycle will change SRP1, SRP0 to (0, 0) state.



ZD25LQ16A



The Quad Enable (QE) bit is a non-volatile Read/Write bit in the Status Register that allows Quad operation. When the QE bit is set to 0 (Default) the WP# pin and HOLD# pin are enable. When the QE pin is set to 1, the Quad IO2 and IO3 pins are enabled. (The QE bit should never be set to 1 during standard SPI or Dual SPI operation if the WP# or HOLD# pins are tied directly to the power supply or ground)

LB3, LB2, LB1, bits

The LB3, LB2, LB1, bits are non-volatile One Time Program (OTP) bits in Status Register (S13-S11) that provide the write protect control and status to the Security Registers. The default state of LB3-LB1 are 0, the security registers are unlocked. The LB3-LB1 bits can be set to 1 individually using the Write Register instruction. The LB3-LB1 bits are One Time Programmable, once they are set to 1, the Security Registers will become read-only permanently.

CMP bit

The CMP bit is a non-volatile Read/Write bit in the Status Register (S14). It is used in conjunction with the BP4-BP0 bits to provide more flexibility for the array protection. Please see the Status registers Memory Protection table for details. The default setting is CMP=0.

SUS1, SUS2 bit

The SUS1 and SUS2 bit are read only bit in the status register (S15 and S10) that are set to 1 after executing an Program/Erase Suspend (75H) command (The Erase Suspend will set the SUS1 to 1, and the Program Suspend will set the SUS2 to 1). The SUS1 and SUS2 bit are cleared to 0 by Program/Erase Resume (7AH) command as well as a power-down, power-up cycle.

7 COMMANDS DESCRIPTION

All commands, addresses and data are shifted in and out of the device, beginning with the most significant bit on the first rising edge of SCLK after CS# is driven low. Then, the one-byte command code must be shifted in to the device, with most significant bit first on SI, and each bit is latched on the rising edges of SCLK.

See Table2, every command sequence starts with a one-byte command code. Depending on the command, this might be followed by address bytes, or by data bytes, or by both or none. CS# must be driven high after the last bit of the command sequence has been completed. For the command of Read, Fast Read, Read Status Register or Release from Deep Power-Down, and Read Device ID, the shifted-in command sequence is followed by a data-out sequence. CS# can be driven high after any bit of the data-out sequence is being shifted out.

For the command of Page Program, Sector Erase, Block Erase, Chip Erase, Write Status Register, Write Enable, Write Disable or Deep Power-Down command, CS# must be driven high exactly at a byte boundary, otherwise the command is rejected, and is not executed. That is CS# must be driven high when the number of clock pulses after CS# being driven low is an exact multiple of eight. For Page Program, if at any time the input byte is not a full byte, nothing will happen and WEL will not be reset.

Table2. Commands (Standard/Dual/Quad SPI)

Command Name	Byte 1	Byte 2	Byte 3	Byte 4	Byte 5	Byte 6	n-Bytes
Write Enable	06H						
Write Disable	04H						
Volatile SR	50H						
Write Enable							
Read Status Register	05H	(S7-S0)					(continuous)
Read Status Register-1	35H	(S15-S8)					(continuous)
Write Status Register	01H	S7-S0	S15-S8				
Read Data	03H	A23-A16	A15-A8	A7-A0	(D7-D0)	(Next	(continuous)
						byte)	
Fast Read	0BH	A23-A16	A15-A8	A7-A0	dummy	(D7-D0)	(continuous)
Dual Output	3BH	A23-A16	A15-A8	A7-A0	dummy	(D7-D0) ⁽¹⁾	(continuous)
Fast Read							
Dual I/O	ввн	A23-A8 ⁽²⁾	A7-A0	(D7-D0) ⁽¹⁾			(continuous)
Fast Read			M7-M0 ⁽²⁾				
Quad Output	6BH	A23-A16	A15-A8	A7-A0	dummy	(D7-	(continuous)
Fast Read						D0) ⁽³⁾	
Quad I/O	EBH	A23-A0	dummy ⁽⁵⁾	(D7-D0) ⁽³⁾			(continuous)
Fast Read		M7-M0 ⁽⁴⁾					
Quad I/O Word	E7H	A23-A0	dummy ⁽⁶⁾	(D7-D0) ⁽³⁾			(continuous)
Fast Read ⁽⁷⁾		M7-M0 ⁽⁴⁾					
Page Program	02H	A23-A16	A15-A8	A7-A0	D7-D0	Next byte	
Quad Page Program	32H	A23-A16	A15-A8	A7-A0	D7-D0		
Sector Erase	20H	A23-A16	A15-A8	A7-A0			
Block Erase(32K)	52H	A23-A16	A15-A8	A7-A0			
Block Erase(64K)	D8H	A23-A16	A15-A8	A7-A0			
Chip Erase	C7/60H						



ZD25LQ16A

	411G Q	add Octile					0=4:07:
Enable Reset	66H						
Reset	99H						
Set Burst with Wrap	77H	W6-W4					
Program/Erase	75H						
Suspend							
Program/Erase Resume	7AH						
Enable SO to output	7011						
RY/BY#	70H						
Disable SO to output	0011						
RY/BY#	80H						
Deep Power-Down	В9Н						
Release From Deep	ABH	dummy	dummy	dummy	(ID7-ID0)		(continuous)
Power-Down, And							
Read Device ID							
Release From Deep	ABH						
Power-Down							
Manufacturer/	90H	dummy	dummy	00H	(M7-M0)	(ID7-ID0)	(continuous)
Device ID							
Manufacturer/	92H	A23-A8	A7-A0,	(M7-M0)			(continuous)
Device ID by Dual I/O	920	AZ3-A0	M[7:0]	(ID7-ID0)			(continuous)
Manufacturer/	94H	A23-A0,	d	(M7-M0)			(ti)
Device ID by Quad I/O	9411	M[7:0]	dummy	(ID7-ID0)			(continuous)
Read Serial Flash Discoverable Parameter	5AH	A23-A16	A15-A8	A7-A0	dummy	(D7-D0)	(continuous)
Read Identification	9FH	(M7-M0)	(ID15-ID8)	(ID7-ID0)			(continuous)
Erase Security	44H	A23-A16	A15-A8	A7-A0			
Registers							
Program Security	42H	A23-A16	A15-A8	A7-A0	D7-D0	D7-D0	
Registers							
Read Security Registers	48H	A23-A16	A15-A8	A7-A0	dummy	D7-D0	

NOTE:

1. Dual Output data

IO0 = (D6, D4, D2, D0)

IO1 = (D7, D5, D3, D1)

2. Dual Input Address

IO0 = A22, A20, A18, A16, A14, A12, A10, A8 A6, A4, A2, A0, M6, M4, M2, M0

IO1 = A23, A21, A19, A17, A15, A13, A11, A9 A7, A5, A3, A1, M7, M5, M3, M1

3. Quad Output Data

IO0 = (D4, D0,)

IO1 = (D5, D1,)

IO2 = (D6, D2,)

IO3 = (D7, D3,....)

4. Quad Input Address

IO0 = A20, A16, A12, A8, A4, A0, M4, M0

IO1 = A21, A17, A13, A9, A5, A1, M5, M1

IO2 = A22, A18, A14, A10, A6, A2, M6, M2

IO3 = A23, A19, A15, A11, A7, A3, M7, M3

5. Fast Read Quad I/O Data

IO0 = (x, x, x, x, D4, D0,...)

IO1 = (x, x, x, x, D5, D1,...)

IO2 = (x, x, x, x, D6, D2,...)

IO3 = (x, x, x, x, D7, D3,...)

6. Fast Word Read Quad I/O Data

IO0 = (x, x, D4, D0,...)

IO1 = (x, x, D5, D1,...)

IO2 = (x, x, D6, D2,...)

IO3 = (x, x, D7, D3,...)

7. Fast Word Read Quad I/O Data: the lowest address bit must be 0.

8. Security Registers Address:

Security Register0: A23-A16=00H, A15-A8=00H, A7-A0= Byte Address;

Security Register1: A23-A16=00H, A15-A8=10H, A7-A0= Byte Address;

Security Register2: A23-A16=00H, A15-A8=20H, A7-A0= Byte Address;

Security Register3: A23-A16=00H, A15-A8=30H, A7-A0= Byte Address.

TABLE OF ID DEFINITIONS


ZD25LQ16A

Operation Code	M7-M0	ID15-ID8	ID7-ID0
9FH	C8	60	15
90H	C8		14
ABH			14

7.1 Write Enable (WREN) (06H)

The Write Enable (WREN) command is for setting the Write Enable Latch (WEL) bit. The Write Enable Latch (WEL) bit must be set prior to every Page Program (PP), Sector Erase (SE), Block Erase (BE), Chip Erase (CE), Write Status Register (WRSR) and Erase/Program Security Registers command. The Write Enable (WREN) command sequence: CS# goes low → sending the Write Enable command → CS# goes high.


Figure 2. Write Enable Sequence Diagram



7.2 Write Disable (WRDI) (04H)

The Write Disable command is for resetting the Write Enable Latch (WEL) bit. The Write Disable command sequence: CS# goes low →Sending the Write Disable command →CS# goes high. The WEL bit is reset by following condition: Power-up and upon completion of the Write Status Register, Page Program, Sector Erase, Block Erase, Chip Erase, Erase/Program Security Registers and Reset commands.


Figure 3. Write Disable Sequence Diagram



7.3 Write Enable for Volatile Status Register (50H)

The non-volatile Status Register bits can also be written to as volatile bits. This gives more flexibility to change the system configuration and memory protection schemes quickly without waiting for the typical non-volatile bit write cycles or affecting the endurance of the Status Register non-volatile bits. The Write Enable for Volatile Status Register command must be issued prior to a Write Status Register command and any other commands can't be inserted between them. Otherwise, Write Enable for Volatile Status Register will be cleared. The Write Enable for Volatile Status Register command will not set the Write Enable Latch bit, it is only valid for the Write Status Register command to change the volatile Status Register bit values.

Figure 4. Write Enable for Volatile Status Register Sequence Diagram



7.4 Read Status Register (RDSR) (05H or 35H)

The Read Status Register (RDSR) command is for reading the Status Register. The Status Register may be read at any time, even while a Program, Erase or Write Status Register cycle is in progress. When one of these cycles is in progress, it is recommended to check the Write in Progress (WIP) bit before sending a new command to the device. It is also possible to read the Status Register continuously. For command code "05H", the SO will output Status Register bits S7~S0. The command code "35H", the SO will output Status Register bits S15~S8.

CS#

SCLK

O 1 2 3 4 5 6 7 8 9 10 11 12 13 14 15

SI

Command

Command

O5H or 35H

SO

High-Z

S7~S0 or S15~S8 out

F7 6 5 4 3 2 1 0 7 6 5 4 3 2 1 0 7

MSB

MSB

MSB

Figure 5. Read Status Register Sequence Diagram

7.5 Write Status Register (WRSR) (01H)

The Write Status Register (WRSR) command allows new values to be written to the Status Register. Before it can be accepted, a Write Enable (WREN) command must previously have been executed. After the Write Enable (WREN) command has been decoded and executed, the device sets the Write Enable Latch (WEL).

The Write Status Register (WRSR) command has no effect on S15, S10, S1 and S0 of the Status Register. CS# must be driven high after the eighth or sixteen bit of the data byte has been latched in. If not, the Write Status Register (WRSR) command is not executed. If CS# is driven high after eighth bit of the data byte, the CMP and QE and SRP1 bits will be cleared to 0. As soon as CS# is driven high, the self-timed Write Status Register cycle (whose duration is tw) is initiated. While the Write Status Register cycle is in progress, the Status Register may still be read to check the value of the Write In Progress (WIP) bit. The Write In Progress (WIP) bit is 1 during the self-timed Write Status Register cycle, and is 0 when it is completed. When the cycle is completed, the Write Enable Latch (WEL) is reset.

The Write Status Register (WRSR) command allows the user to change the values of the Block Protect (BP4, BP3, BP2, BP1, and BP0) bits, to define the size of the area that is to be treated as read-only, as defined in Table1. The Write Status

SO

1.8V Uniform Sector **Dual and Quad Serial Flash**

Register (WRSR) command also allows the user to set or reset the Status Register Protect (SRP1 and SRP0) bits in accordance with the Write Protect (WP#) signal. The Status Register Protect (SRP1 and SRP0) bits and Write Protect (WP#) signal allow the device to be put in the Hardware Protected Mode. The Write Status Register (WRSR) command is not executed once the Hardware Protected Mode is entered.

CS# 8 10 11 12 13 14 15 16 17 18 19 20 21 22 23 **SCLK** Command ≪Status Register in SI 0X1\$ 01H (3) **MSB** High-Z

Figure 6. Write Status Register Sequence Diagram

Read Data Bytes (READ) (03H)

The Read Data Bytes (READ) command is followed by a 3-byte address (A23-A0), and each bit is latched-in on the rising edge of SCLK. Then the memory content, at that address, is shifted out on SO, and each bit is shifted out, at a Max frequency f_R, on the falling edge of SCLK. The first byte addressed can be at any location. The address is automatically incremented to the next higher address after each byte of data is shifted out. The whole memory can, therefore, be read with a single Read Data Bytes (READ) command. Any Read Data Bytes (READ) command, while an Erase, Program or Write cycle is in progress, is rejected without having any effects on the cycle that is in progress.




Figure 7. Read Data Bytes Sequence Diagram

Read Data Bytes at Higher Speed (Fast Read) (0BH)

The Read Data Bytes at Higher Speed (Fast Read) command is for quickly reading data out. It is followed by a 3-byte address (A23-A0) and a dummy byte, and each bit is latched-in on the rising edge of SCLK. Then the memory content, at that address, is shifted out on SO, and each bit is shifted out, at a Max frequency fc, on the falling edge of SCLK. The first byte addressed can be at any location. The address is automatically incremented to the next higher address after each byte of data is shifted out.

CS# 28 29 30 31 9 10 **SCLK** 24-bit address Command SI 0BH High-Z SO CS# 32 33 34 35 36 37 38 39 40 41 42 43 44 45 **SCLK** SI Data Out1 Data Out2 SO

Figure 8. Read Data Bytes at Higher Speed Sequence Diagram

7.8 Dual Output Fast Read (3BH)

The Dual Output Fast Read command is followed by 3-byte address (A23-A0) and a dummy byte, and each bit is latched in on the rising edge of SCLK, then the memory contents are shifted out 2-bit per clock cycle from SI and SO.

The command sequence is shown in followed Figure 9. The first byte addressed can be at any location. The address is automatically incremented to the next higher address after each byte of data is shifted out.




Figure9. Dual Output Fast Read Sequence Diagram

7.9 Quad Output Fast Read (6BH)

The Quad Output Fast Read command is followed by 3-byte address (A23-A0) and a dummy byte, and each bit is latched in on the rising edge of SCLK, then the memory contents are shifted out 4-bit per clock cycle from IO3, IO2, IO1 and IO0. The command sequence is shown in followed Figure 10. The first byte addressed can be at any location. The address is automatically incremented to the next higher address after each byte of data is shifted out. The Quad Enable bit (QE) of Status Register (S9) must be set to enable for the Quad Output Fast Read command.




Figure 10. Quad Output Fast Read Sequence Diagram

7.10 Dual I/O Fast Read (BBH)

The Dual I/O Fast Read command is similar to the Dual Output Fast Read command but with the capability to input the 3-byte address (A23-0) and a "Continuous Read Mode" byte 2-bit per clock by SI and SO, and each bit is latched in on the rising edge of SCLK, then the memory contents are shifted out 2-bit per clock cycle from SI and SO. The command sequence is shown in followed Figure 11. The first byte addressed can be at any location. The address is automatically incremented to the next higher address after each byte of data is shifted out.

Dual I/O Fast Read with "Continuous Read Mode"

The Dual I/O Fast Read command can further reduce command overhead through setting the "Continuous Read Mode" bits (M7-0) after the input 3-byte address (A23-A0). If the "Continuous Read Mode" bits (M5-4) = (1, 0), then the next Dual I/O Fast Read command (after CS# is raised and then lowered) does not require the BBH command code. The command sequence is shown in followed Figure11. If the "Continuous Read Mode" bits (M5-4) do not equal (1, 0), the next command requires the command code, thus returning to normal operation. A "Continuous Read Mode" Reset command can be used to reset (M5-4) before issuing normal command.

Figure 11. Dual I/O Fast Read Sequence Diagram (M5-4≠ (1, 0))





Figure 11a. Dual I/O Fast Read Sequence Diagram (M5-4= (1, 0))



7.11 Quad I/O Fast Read (EBH)

The Quad I/O Fast Read command is similar to the Dual I/O Fast Read command but with the capability to input the 3-byte address (A23-0) and a "Continuous Read Mode" byte and 4-dummy clock 4-bit per clock by IO0, IO1, IO3, IO4, and each bit is latched in on the rising edge of SCLK, then the memory contents are shifted out 4-bit per clock cycle from IO0, IO1, IO2, IO3. The command sequence is shown in followed Figure 12. The first byte addressed can be at any location. The address is automatically incremented to the next higher address after each byte of data is shifted out. The Quad Enable bit (QE) of Status Register (S9) must be set to enable for the Quad I/O Fast read command.


Quad I/O Fast Read with "Continuous Read Mode"

The Quad I/O Fast Read command can further reduce command overhead through setting the "Continuous Read Mode" bits (M7-0) after the input 3-byte address (A23-A0). If the "Continuous Read Mode" bits (M5-4) = (1, 0), then the next Quad I/O Fast Read command (after CS# is raised and then lowered) does not require the EBH command code. The command sequence is shown in followed Figure 12a. If the "Continuous Read Mode" bits (M5-4) do not equal to (1, 0), the next command requires the command code, thus returning to normal operation. A "Continuous Read Mode" Reset command can be used to reset (M5-4) before issuing normal command.

CS# 10 11 12 13 14 15 16 17 18 19 **SCLK** Command SI(IO0) EBH SO(IO1) WP#(IO2) HOLD#(IO3)_ A23-16 Dummy Byte1 Byte2

Figure 12. Quad I/O Fast Read Sequence Diagram (M5-4≠ (1, 0))

Figure 12a. Quad I/O Fast Read Sequence Diagram (M5-4= (1, 0))



Quad I/O Fast Read with "8/16/32/64-Byte Wrap Around" in Standard SPI mode

The Quad I/O Fast Read command can be used to access a specific portion within a page by issuing "Set Burst with Wrap" (77H) commands prior to EBH. The "Set Burst with Wrap" (77H) command can either enable or disable the "Wrap Around" feature for the following EBH commands. When "Wrap Around" is enabled, the data being accessed can be limited to either an 8/16/32/64-byte section of a 256-byte page. The output data starts at the initial address specified in the command, once it reaches the ending boundary of the 8/16/32/64-byte section, the output will wrap around the beginning boundary automatically until CS# is pulled high to terminate the command.

The Burst with Wrap feature allows applications that use cache to quickly fetch a critical address and then fill the cache afterwards within a fixed length (8/16/32/64-byte) of data without issuing multiple read commands. The "Set Burst with Wrap" command allows three "Wrap Bits" W6-W4 to be set. The W4 bit is used to enable or disable the "Wrap Around" operation while W6-W5 is used to specify the length of the wrap around section within a page.

Quad I/O Word Fast Read (E7H)

The Quad I/O Word Fast Read command is similar to the Quad I/O Fast Read command except that the lowest address bit (A0) must be equal 0 and there are only 2-dummy clock. The command sequence is shown in followed Figure 13. The first byte addressed can be at any location. The address is automatically incremented to the next higher address after each byte of data is shifted out. The Quad Enable bit (QE) of Status Register (S9) must be set to enable for the Quad I/O Word Fast read command

Quad I/O Word Fast Read with "Continuous Read Mode"

The Quad I/O Word Fast Read command can further reduce command overhead through setting the "Continuous Read Mode" bits (M7-0) after the input 3-byte address (A23-A0). If the "Continuous Read Mode" bits (M5-4) = (1, 0), then the next Quad I/O Word Fast Read command (after CS# is raised and then lowered) does not require the E7H command code. The command sequence is shown in followed Figure 13a. If the "Continuous Read Mode" bits (M5-4) do not equal to (1, 0), the next command requires the first E7H command code, thus returning to normal operation. A "Continuous Read Mode" Reset command can be used to reset (M5-4) before issuing normal command.





Figure 13. Quad I/O Word Fast Read Sequence Diagram (M5-4≠ (1, 0))



Figure 13a. Quad I/O Word Fast Read Sequence Diagram (M5-4= (1, 0))



Quad I/O Word Fast Read with "8/16/32/64-Byte Wrap Around" in Standard SPI mode

The Quad I/O Word Fast Read command can be used to access a specific portion within a page by issuing "Set Burst with Wrap" (77H) commands prior to E7H. The "Set Burst with Wrap" (77H) command can either enable or disable the "Wrap Around" feature for the following E7H commands. When "Wrap Around" is enabled, the data being accessed can be limited to either an 8/16/32/64-byte section of a 256-byte page. The output data starts at the initial address specified in the command, once it reaches the ending boundary of the 8/16/32/64-byte section, the output will wrap around the beginning boundary automatically until CS# is pulled high to terminate the command.

The Burst with Wrap feature allows applications that use cache to quickly fetch a critical address and then fill the cache afterwards within a fixed length (8/16/32/64-byte) of data without issuing multiple read commands. The "Set Burst with Wrap" command allows three "Wrap Bits" W6-W4 to be set. The W4 bit is used to enable or disable the "Wrap Around" operation while W6-W5 is used to specify the length of the wrap around section within a page.

7.12 Set Burst with Wrap (77H)

The Set Burst with Wrap command is used in conjunction with "Quad I/O Fast Read" and "Quad I/O Word Fast Read" command to access a fixed length of 8/16/32/64-byte section within a 256-byte page, in standard SPI mode.

The Set Burst with Wrap command sequence: CS# goes low \rightarrow Send Set Burst with Wrap command \rightarrow Send 24 dummy bits \rightarrow Send 8 bits "Wrap bits" \rightarrow CS# goes high.

VAIG VAIE	W	1=0	W4=1 (default)		
W6,W5	Wrap Around	Wrap Length	Wrap Around	Wrap Length	
0, 0	Yes	8-byte	No	N/A	
0, 1	Yes	16-byte	No	N/A	
1, 0	Yes	32-byte	No	N/A	
1, 1	Yes	64-byte	No	N/A	

If the W6-W4 bits are set by the Set Burst with Wrap command, all the following "Quad I/O Fast Read" and "Quad I/O Word Fast Read" command will use the W6-W4 setting to access the 8/16/32/64-byte section within any page. To exit the "Wrap Around" function and return to normal read operation, another Set Burst with Wrap command should be issued to set W4=1.

Figure 14. Set Burst with Wrap Sequence Diagram

7.13 Page Program (PP) (02H)

The Page Program (PP) command is for programming the memory. A Write Enable (WREN) command must previously have been executed to set the Write Enable Latch (WEL) bit before sending the Page Program command.

The Page Program (PP) command is entered by driving CS# Low, followed by the command code, three address bytes and at least one data byte on SI. If the 8 least significant address bits (A7-A0) are not all zero, all transmitted data that goes beyond the end of the current page are programmed from the start address of the same page (from the address whose 8 least significant bits (A7-A0) are all zero). CS# must be driven low for the entire duration of the sequence. The Page Program command sequence: CS# goes low \rightarrow sending Page Program command \rightarrow 3-byte address on SI \rightarrow at least 1 byte data on SI \rightarrow CS# goes high. The command sequence is shown in Figure 15. If more than 256 bytes are sent to the device, previously latched data are discarded and the last 256 data bytes are guaranteed to be programmed correctly within the same page. If less than 256 data bytes are sent to device, they are correctly programmed at the requested addresses without having



any effects on the other bytes of the same page. CS# must be driven high after the eighth bit of the last data byte has been latched in; otherwise the Page Program (PP) command is not executed.

As soon as CS# is driven high, the self-timed Page Program cycle (whose duration is t_{PP}) is initiated. While the Page Program cycle is in progress, the Status Register may be read to check the value of the Write in Progress (WIP) bit. The Write in Progress (WIP) bit is 1 during the self-timed Page Program cycle, and is 0 when it is completed. At some unspecified time before the cycle is completed, the Write Enable Latch (WEL) bit is reset.

A Page Program (PP) command applied to a page which is protected by the Block Protect (BP4, BP3, BP2, BP1, and BP0) is not executed.




Figure 15. Page Program Sequence Diagram

7.14 Quad Page Program (32H)

The Quad Page Program command is for programming the memory using four pins: IO0, IO1, IO2, and IO3. To use Quad Page Program the Quad enable in status register Bit9 must be set (QE=1). A Write Enable (WREN) command must previously have been executed to set the Write Enable Latch (WEL) bit before sending the Page Program command. The quad Page Program command is entered by driving CS# Low, followed by the command code (32H), three address bytes and at least one data byte on IO pins.

The command sequence is shown in Figure 16. If more than 256 bytes are sent to the device, previously latched data are discarded and the last 256 data bytes are guaranteed to be programmed correctly within the same page. If less than 256 data bytes are sent to device, they are correctly programmed at the requested addresses without having any effects on the other bytes of the same page. CS# must be driven high after the eighth bit of the last data byte has been latched in; otherwise the Quad Page Program (PP) command is not executed.

As soon as CS# is driven high, the self-timed Quad Page Program cycle (whose duration is tpp) is initiated. While the Quad Page Program cycle is in progress, the Status Register may be read to check the value of the Write In Progress (WIP) bit. The Write in Progress (WIP) bit is 1 during the self-timed Quad Page Program cycle, and is 0 when it is completed. At some unspecified time before the cycle is completed, the Write Enable Latch (WEL) bit is reset.

A Quad Page Program command applied to a page which is protected by the Block Protect (BP4, BP3, BP2, BP1, and BP0) is not executed.




Figure 16. Quad Page Program Sequence Diagram

7.15 Sector Erase (SE) (20H)

The Sector Erase (SE) command is for erasing the all data of the chosen sector. A Write Enable (WREN) command must previously have been executed to set the Write Enable Latch (WEL) bit. The Sector Erase (SE) command is entered by driving CS# low, followed by the command code, and 3-address byte on SI. Any address inside the sector is a valid address for the Sector Erase (SE) command. CS# must be driven low for the entire duration of the sequence.

The Sector Erase command sequence: CS# goes low \rightarrow sending Sector Erase command \rightarrow 3-byte address on SI \rightarrow CS# goes high. The command sequence is shown in Figure17. CS# must be driven high after the eighth bit of the last address byte has been latched in; otherwise the Sector Erase (SE) command is not executed. As soon as CS# is driven high, the self-timed Sector Erase cycle (whose duration is t_{SE}) is initiated. While the Sector Erase cycle is in progress, the Status Register may be read to check the value of the Write in Progress (WIP) bit. The Write in Progress (WIP) bit is 1 during the self-timed Sector Erase cycle, and is 0 when it is completed. At some unspecified time before the cycle is completed, the Write Enable Latch (WEL) bit is reset. A Sector Erase (SE) command applied to a sector which is protected by the Block Protect (BP4, BP3, BP2, BP1, and BP0) bit (see Table1&1a) is not executed.




Figure 17. Sector Erase Sequence Diagram

7.16 32KB Block Erase (BE) (52H)

The 32KB Block Erase (BE) command is for erasing the all data of the chosen block. A Write Enable (WREN) command must previously have been executed to set the Write Enable Latch (WEL) bit. The 32KB Block Erase (BE) command is entered by driving CS# low, followed by the command code, and three address bytes on SI. Any address inside the block is a valid address for the 32KB Block Erase (BE) command. CS# must be driven low for the entire duration of the sequence. The 32KB Block Erase command sequence: CS# goes low \rightarrow sending 32KB Block Erase command \rightarrow 3-byte address on SI \rightarrow CS# goes high. The command sequence is shown in Figure 18. CS# must be driven high after the eighth bit of the last address byte has been latched in; otherwise the 32KB Block Erase (BE) command is not executed. As soon as CS# is driven high, the self-timed Block Erase cycle (whose duration is t_{SE}) is initiated. While the Block Erase cycle is in progress, the Status Register may be read to check the value of the Write in Progress (WIP) bit. The Write in Progress (WIP) bit is 1 during the self-timed Block Erase cycle, and is 0 when it is completed. At some unspecified time before the cycle is completed, the Write Enable Latch (WEL) bit is reset. A 32KB Block Erase (BE) command applied to a block which is protected by the Block Protect (BP4, BP3, BP2, BP1, and BP0) bits (see Table1&1a) is not executed.





Figure 18. 32KB Block Erase Sequence Diagram

7.17 64KB Block Erase (BE) (D8H)

The 64KB Block Erase (BE) command is for erasing the all data of the chosen block. A Write Enable (WREN) command must previously have been executed to set the Write Enable Latch (WEL) bit. The 64KB Block Erase (BE) command is entered by driving CS# low, followed by the command code, and three address bytes on SI. Any address inside the block is a valid address for the 64KB Block Erase (BE) command. CS# must be driven low for the entire duration of the sequence. The 64KB Block Erase command sequence: CS# goes low \rightarrow sending 64KB Block Erase command \rightarrow 3-byte address on SI \rightarrow CS# goes high. The command sequence is shown in Figure 19. CS# must be driven high after the eighth bit of the last address byte has been latched in; otherwise the 64KB Block Erase (BE) command is not executed. As soon as CS# is driven high, the self-timed Block Erase cycle (whose duration is t_{SE}) is initiated. While the Block Erase cycle is in progress, the Status Register may be read to check the value of the Write in Progress (WIP) bit. The Write in Progress (WIP) bit is 1 during the self-timed Block Erase cycle, and is 0 when it is completed. At some unspecified time before the cycle is completed, the Write Enable Latch (WEL) bit is reset. A 64KB Block Erase (BE) command applied to a block which is protected by the Block Protect (BP4, BP3, BP2, BP1, and BP0) bits (see Table1&1a) is not executed.


Figure 19. 64KB Block Erase Sequence Diagram



7.18 Chip Erase (CE) (60/C7H)

The Chip Erase (CE) command is for erasing the all data of the chip. A Write Enable (WREN) command must previously have been executed to set the Write Enable Latch (WEL) bit . The Chip Erase (CE) command is entered by driving CS# Low, followed by the command code on Serial Data Input (SI). CS# must be driven Low for the entire duration of the sequence. The Chip Erase command sequence: CS# goes low \rightarrow sending Chip Erase command \rightarrow CS# goes high. The command sequence is shown in Figure 20. CS# must be driven high after the eighth bit of the command code has been latched in; otherwise the Chip Erase command is not executed. As soon as CS# is driven high, the self-timed Chip Erase cycle (whose duration is t_{CE}) is initiated. While the Chip Erase cycle is in progress, the Status Register may be read to check the value of the Write in Progress (WIP) bit. The Write in Progress (WIP) bit is 1 during the self-timed Chip Erase cycle, and is 0 when it is completed. At some unspecified time before the cycle is completed, the Write Enable Latch (WEL) bit is reset. The Chip Erase (CE) command is executed, if the Block Protect (BP2, BP1, and BP0) bits are 0 and CMP=0 or the Block Protect (BP2, BP1, and BP0) bits are 1 and CMP=1.

Figure 20. Chip Erase Sequence Diagram




7.19 Enable/Disable SO to Output RY/BY# (ESRY/DSRY) (70H/80H)

Besides SO pin is used to output data, it also can be used as the status pin of ready/busy. The ESRY command is for outputting the ready/busy status to SO. When the device is in the process of power on, enter or exit deep power down mode and erase/program, its status is busy, and the SO output 0. When the device is in the standby mode, the status of device is ready, then SO output 1. The DSRY command is for resetting ESRY. The ready/busy status will not output to SO after DSRY issued.

The Enable/Disable SO to Output RY/BY# command sequence: CS# goes low → sending ESRY command code → CS# goes high. The command sequence is shown in Figure 21. CS# must be driven high after the eighth bit of the command code has been latched in; otherwise the Enable/Disable SO to Output RY/BY# command is not executed.

Figure 21. Enable/Disable SO to Output RY/BY# Diagram



Dual and Quad Serial Flash

7.20 Deep Power-Down (DP) (B9H)

Executing the Deep Power-Down (DP) command is the only way to put the device in the lowest consumption mode (the Deep Power-Down Mode). It can also be used as an extra software protection mechanism, while the device is not in active use, since in this mode, the device ignores all Write, Program and Erase commands. Driving CS# high deselects the device, and puts the device in the Standby Mode (if there is no internal cycle currently in progress). But this mode is not the Deep Power-Down Mode. The Deep Power-Down Mode can only be entered by executing the Deep Power-Down (DP) command. Once the device has entered the Deep Power-Down Mode, all commands are ignored except the Release from Deep Power-Down and Read Device ID (RDI) command or software reset command. The Release from Deep Power-Down and Read Device ID (RDI) command releases the device from Deep Power-Down mode, also allows the Device ID of the device to be output on SO.

The Deep Power-Down Mode automatically stops at Power-Down, and the device always in the Standby Mode after Power-Up.

The Deep Power-Down command sequence: CS# goes low → sending Deep Power-Down command → CS# goes high. The command sequence is shown in Figure 22. CS# must be driven high after the eighth bit of the command code has been latched in; otherwise the Deep Power-Down (DP) command is not executed. As soon as CS# is driven high, it requires a delay of top before the supply current is reduced to Icc2 and the Deep Power-Down Mode is entered. Any Deep Power-Down (DP) command, while an Erase, Program or Write cycle is in progress, is rejected without having any effects on the cycle that is in progress.

CS# tpp 2 5 0 3 4 6 SCLK -Command Stand-by mode Deep Power-down mode SI **B9H**

Figure 22. Deep Power-Down Sequence Diagram

7.21 Release from Deep Power-Down and Read Device ID (RDI) (ABH)

The Release from Power-Down and Read Device ID command is a multi-purpose command. It can be used to release the device from the Power-Down state or obtain the devices electronic identification (ID) number.

To release the device from the Power-Down state, the command is issued by driving the CS# pin low, shifting the instruction code "ABH" and driving CS# high as shown in Figure 23. Release from Power-Down will take the time duration of t_{RES1} (See AC Characteristics) before the device will resume normal operation and other command are accepted. The CS# pin must remain high during the tRES1 time duration.

When used only to obtain the Device ID while not in the Power-Down state, the command is initiated by driving the CS# pin low and shifting the instruction code "ABH" followed by 3-dummy byte. The Device ID bits are then shifted out on the falling edge of SCLK with most significant bit (MSB) first as shown in Figure 24. The Device ID value is listed in Manufacturer and Device Identification table. The Device ID can be read continuously. The command is completed by driving CS# high.

When used to release the device from the Power-Down state and obtain the Device ID, the command is the same as previously described, and shown in Figure 24, except that after CS# is driven high it must remain high for a time duration of tres2 (See AC Characteristics). After this time duration the device will resume normal operation and other command will be accepted. If the Release from Power-Down / Device ID command is issued while an Erase, Program or Write cycle is in process (when WIP equal 1) the command is ignored and will not have any effects on the current cycle.

Figure 23. Release Power-Down Sequence Diagram





Figure 24. Release Power-Down/Read Device ID Sequence Diagram



7.22 Read Manufacture Id/ Device Id (REMS) (90H)

The Read Manufacturer/Device ID command is an alternative to the Release from Power-Down / Device ID command that provides both the JEDEC assigned Manufacturer ID and the specific Device ID.

The command is initiated by driving the CS# pin low and shifting the command code "90H" followed by a 24-bit address (A23-A0) of 000000H. After which, the Manufacturer ID and the Device ID are shifted out on the falling edge of SCLK with most significant bit (MSB) first as shown in Figure 25. If the 24-bit address is initially set to 000001H, the Device ID will be read first.

CS# 28 29 30 31 8 **SCLK** Command 24-bit address SI 90H High-Z SO CS# 35 36 37 38 39 40 41 42 43 44 45 46 47 **SCLK** SI Device ID Manufacturer ID SO **MSB MSB**

Figure 25. Read Manufacture ID/ Device ID Sequence Diagram

7.23 Read Manufacture ID/ Device ID Dual I/O (92H)

The Read Manufacturer/Device ID Dual I/O command is an alternative to the Release from Power-Down / Device ID command that provides both the JEDEC assigned Manufacturer ID and the specific Device ID by dual I/O.

The command is initiated by driving the CS# pin low and shifting the command code "92H" followed by a 24-bit address (A23-A0) of 000000H. After which, the Manufacturer ID and the Device ID are shifted out on the falling edge of SCLK with most significant bit (MSB) first as shown in Figure 26. If the 24-bit address is initially set to 000001H, the Device ID will be read first.




Figure 26. Read Manufacture ID/ Device ID Dual I/O Sequence Diagram



7.24 Read Manufacture ID/ Device ID Quad I/O (94H)

The Read Manufacturer/Device ID Quad I/O command is an alternative to the Release from Power-Down / Device ID command that provides both the JEDEC assigned Manufacturer ID and the specific Device ID by guad I/O.

The command is initiated by driving the CS# pin low and shifting the command code "94H" followed by a 24-bit address (A23-A0) of 000000H. After which, the Manufacturer ID and the Device ID are shifted out on the falling edge of SCLK with most significant bit (MSB) first as shown in Figure 27. If the 24-bit address is initially set to 000001H, the Device ID will be read first.




Figure 27. Read Manufacture ID/ Device ID Quad I/O Sequence Diagram

7.25 Read Identification (RDID) (9FH)

The Read Identification (RDID) command allows the 8-bit manufacturer identification to be read, followed by two bytes of device identification. The device identification indicates the memory type in the first byte, and the memory capacity of the device in the second byte. The Read Identification (RDID) command while an Erase or Program cycle is in progress, is not decoded, and has no effect on the cycle that is in progress. The Read Identification (RDID) command should not be issued while the device is in Deep Power-Down Mode.

The device is first selected by driving CS# low. Then, the 8-bit command code for the command is shifted in. This is followed

by the 24-bit device identification, stored in the memory. Each bit is shifted out on the falling edge of Serial Clock. The command sequence is shown in Figure 28. The Read Identification (RDID) command is terminated by driving CS# high at any time during data output. When CS# is driven high, the device is in the Standby Mode. Once in the Standby Mode, the device waits to be selected, so that it can receive, decode and execute commands.





Figure 28. Read Identification ID Sequence Diagram

7.26 Program/Erase Suspend (PES) (75H)

The Program/Erase Suspend command "75H", allows the system to interrupt a page program or sector/block erase operation and then read data from any other sector or block. The Write Status Register command (01H/31H/11H) and Erase/Program Security Registers command (44H,42H) and Erase commands (20H, 52H, D8H, C7H, 60H) and Page Program command (02H/32H) are not allowed during Program suspend. The Write Status Register command (01H/31H/11H) and Erase Security Registers command (44H) and Erase commands (20H, 52H, D8H, C7H, 60H) are not allowed during Erase suspend. Program/Erase Suspend is valid only during the page program or sector/block erase operation. A maximum of time of "tsus" (See AC Characteristics) is required to suspend the program/erase operation.

The Program/Erase Suspend command will be accepted by the device only if the SUS2/SUS1 bit in the Status Register equal to 0 and WIP bit equal to 1 while a Page Program or a Sector or Block Erase operation is on-going. If the SUS2/SUS1 bit equal to 1 or WIP bit equal to 0, the Suspend command will be ignored by the device. The WIP bit will be cleared form 1 to 0 within "tsus" and the SUS2/SUS1 bit will be set from 0 to 1 immediately after Program/Erase Suspend. A power-off during the suspend period will reset the device and release the suspend state. The command sequence is show in Figure 29.


Figure 29. Program/Erase Suspend Sequence Diagram



7.27 Program/Erase Resume (PER) (7AH)

The Program/Erase Resume command must be written to resume the program or sector/block erase operation after a Program/Erase Suspend command. The Program/Erase Resume command will be accepted by the device only if the SUS2/SUS1 bit equal to 1 and the WIP bit equal to 0. After issued the SUS2/SUS1 bit in the status register will be cleared from 1 to 0 immediately, the WIP bit will be set from 0 to 1 within 200ns and the Sector or Block will complete the erase operation or the page will complete the program operation. The Program/Erase Resume command will be ignored unless a Program/Erase Suspend is active. The command sequence is show in Figure 30.

Figure 30. Program/Erase Resume Sequence Diagram



7.28 Erase Security Registers (44H)

The ZD25LQ16A provides three 512-byte Security Registers which can be erased and programmed individually. These registers may be used by the system manufacturers to store security and other important information separately from the main memory array.

The Erase Security Registers command is similar to Sector/Block Erase command. A Write Enable (WREN) command must previously have been executed to set the Write Enable Latch (WEL) bit.


The Erase Security Registers command sequence: CS# goes low \rightarrow sending Erase Security Registers command \rightarrow The Erase Security Registers command sequence: CS# goes low \rightarrow sending Erase Security Registers command \rightarrow 3-byte address on SI \rightarrow CS# goes high. The command sequence is shown below. CS# must be driven high after the eighth bit of the last address byte has been latched in; otherwise the Erase Security Registers command is not executed. As soon as CS# is driven high, the self-timed Erase Security Registers cycle (whose duration is t_{SE}) is initiated. While the Erase Security Registers cycle is in progress, the Status Register may be read to check the value of the Write in Progress (WIP) bit. The Write in Progress (WIP) bit is 1 during the self-timed Erase Security Registers cycle, and is 0 when it is completed. At some unspecified time before the cycle is completed, the Write Enable Latch (WEL) bit is reset. The Security Registers Lock Bit (LB3-1) in the Status Register can be used to OTP protect the security registers. Once the LB bit is set to 1, the Security



Registers will be permanently locked; the Erase Security Registers command will be ignored.

Address	A23-16	A15-12	A11-9	A8-0
Security Register #1	00H	0001	000	Do not care
Security Register #2	00H	0010	000	Do not care
Security Register #3	00H	0011	000	Do not care

Figure 31. Erase Security Registers command Sequence Diagram




7.29 Program Security Registers (42H)

The Program Security Registers command is similar to the Page Program command. Each security register contains four pages content. A Write Enable (WREN) command must previously have been executed to set the Write Enable Latch (WEL) bit before sending the Program Security Registers command. The Program Security Registers command is entered by driving CS# Low, followed by the command code (42H), three address bytes and at least one data byte on SI. As soon as CS# is driven high, the self-timed Program Security Registers cycle (whose duration is t_{PP}) is initiated. While the Program Security Registers cycle is in progress, the Status Register may be read to check the value of the Write in Progress (WIP) bit. The Write in Progress (WIP) bit is 1 during the self-timed Program Security Registers cycle, and is 0 when it is completed. At some unspecified time before the cycle is completed, the Write Enable Latch (WEL) bit is reset.

If the Security Registers Lock Bit (LB3-1) is set to 1, the Security Registers will be permanently locked. Program Security Registers command will be ignored.

Address	A23-16	A15-12	A11-9	A8-0
Security Register #1	00H	0001	000	Byte Address
Security Register #2	00H	0010	000	Byte Address
Security Register #3	00H	0011	000	Byte Address

Figure 32. Program Security Registers command Sequence Diagram





7.30 Read Security Registers (48H)

The Read Security Registers command is similar to Fast Read command. The command is followed by a 3-byte address (A23-A0) and a dummy byte, and each bit is latched-in on the rising edge of SCLK. Then the memory content, at that address, is shifted out on SO, and each bit is shifted out, at a Max frequency fc, on the falling edge of SCLK. The first byte addressed can be at any location. The address is automatically incremented to the next higher address after each byte of data is shifted out. Once the A8-A0 address reaches the last byte of the register (Byte 1FFH), it will reset to 000H, the command is completed by driving CS# high.

Address	A23-16	A15-12	A11-9	A8-0
Security Register #1	00H	0001	000	Byte Address
Security Register #2	00H	0010	000	Byte Address
Security Register #3	00H	0011	000	Byte Address





Figure 33. Read Security Registers command Sequence Diagram

7.31 Enable Reset (66H) and Reset (99H)

If the Reset command is accepted, any on-going internal operation will be terminated and the device will return to its default power-on state and lose all the current volatile settings, such as Volatile Status Register bits, Write Enable Latch status (WEL), Program/Erase Suspend status, Read Parameter setting (P7-P0), Deep Power Down Mode, Continuous Read Mode bit setting (M7-M0) and Wrap Bit Setting (W6-W4).

The "Enable Reset (66H)" and the "Reset (99H)" commands can be issued in either SPI mode. The "Reset (99H)" command sequence as follow: CS# goes low \rightarrow Sending Enable Reset command \rightarrow CS# goes high \rightarrow CS# goes low \rightarrow Sending Reset command \rightarrow CS# goes high. Once the Reset command is accepted by the device, the device will take approximately t_{RSTF_R} to reset. During this period, no command will be accepted. Data corruption may happen if there is an on-going or suspended internal Erase or Program operation when Reset command sequence is accepted by the device. It is recommended to check the BUSY bit and the SUS bit in Status Register before issuing the Reset command sequence.


Figure 34. Enable Reset and Reset command Sequence Diagram



7.32 Read Serial Flash Discoverable Parameter (5AH)

The Serial Flash Discoverable Parameter (SFDP) standard provides a consistent method of describing the functional and feature capabilities of serial flash devices in a standard set of internal parameter tables. These parameter tables can be interrogated by host system software to enable adjustments needed to accommodate divergent features from multiple vendors. The concept is similar to the one found in the Introduction of JEDEC Standard, JESD68 on CFI. SFDP is a standard of JEDEC Standard No.216.

Figure 35. Read Serial Flash Discoverable Parameter command Sequence Diagram





ZD25LQ16A

Table3. Signature and Parameter Identification Data Values

					Data
		(Byte)	(Bit)		
SFDP Signature	Fixed:50444653H	00H	07:00	53H	53H
		01H	15:08	46H	46H
		02H	23:16	44H	44H
		03H	31:24	50H	50H
SFDP Minor Revision Number	Start from 00H	04H	07:00	00H	00H
SFDP Major Revision Number	Start from 01H	05H	15:08	01H	01H
Number of Parameters Headers	Start from 00H	06H	23:16	01H	01H
Unused	Contains 0xFFH and can never be	07H	31:24	FFH	FFH
	changed				
ID number (JEDEC)	00H: It indicates a JEDEC	08H	07:00	00H	00H
	specified header				
Parameter Table Minor Revision	Start from 0x00H	09H	15:08	00H	00H
Number					
Parameter Table Major Revision	Start from 0x01H	0AH	23:16	01H	01H
Number					
Parameter Table Length	How many DWORDs in the	0BH	31:24	09H	09H
(in double word)	Parameter table				
Parameter Table Pointer (PTP)	First address of JEDEC Flash	0CH	07:00	30H	30H
	Parameter table	0DH	15:08	00H	00H
		0EH	23:16	00H	00H
Unused	Contains 0xFFH and can never be changed	0FH	31:24	FFH	FFH
Parameter Table Minor Revision	Start from 0x00H	11H	15:08	00H	00H
Number					
Parameter Table Major Revision	Start from 0x01H	12H	23:16	01H	01H
Number					
Parameter Table Length	How many DWORDs in the	13H	31:24	03H	03H
(in double word)	Parameter table				
Parameter Table Pointer (PTP)	First address of Zetta Flash	14H	07:00	60H	60H
	Parameter table				
Unused	Contains 0xFFH and can never be	15H	15:08	00H	00H
	changed	16H	23:16	00H	00H
		17H	31:24	FFH	FFH



Table4. Parameter Table (0): JEDEC Flash Parameter Tables

	rafameter fable (0). 3LDLC i lasif				
Description	Comment	Add(H)	DW Add	Data	Data
		(Byte)	(Bit)		
	00: Reserved; 01: 4KB erase;				
Block/Sector Erase Size	10: Reserved;		01:00	01b	
	11: not support 4KB erase				
Write Granularity	0: 1Byte, 1: 64Byte or larger		02	1b	
Write Enable Instruction	0: Nonvolatile status bit				
Requested for Writing to Volatile	1: Volatile status bit		03	0b	
Status Registers	(BP status register bit)	30H			E5H
	0: Use 50H Opcode,	0011			
Write Enable Opcode Select for	1: Use 06H Opcode,				
Writing to Volatile Status	Note: If target flash status register		04	0b	
Registers	is Nonvolatile, then bits 3 and 4				
	must be set to 00b.				
Unused	Contains 111b and can never be		07:05	111b	
Onusea	changed		07.05	וווט	
4KB Erase Opcode		31H	15:08	20H	20H
(1-1-2) Fast Read	0=Not support, 1=Support		16	1b	
Address Bytes Number used in	00: 3Byte only, 01: 3 or 4Byte,		18:17	00b	
addressing flash array	10: 4Byte only, 11: Reserved		10.17	000	
Double Transfer Rate (DTR)	0=Not support, 1=Support		19	0b	
clocking	0-Not support, 1-Support	32H	19	OD	F1H
(1-2-2) Fast Read	0=Not support, 1=Support		20	1b	
(1-4-4) Fast Read	0=Not support, 1=Support		21	1b	
(1-1-4) Fast Read	0=Not support, 1=Support		22	1b	
Unused			23	1b	
Unused		33H	31:24	FFH	FFH
Flash Memory Density		37H:34H	31:00	00FFFF	FFH
(1-4-4) Fast Read Number of	0 0000b: Wait states (Dummy		04:00	00100b	
Wait states	Clocks) not support	38H	04.00	001000	446
(1-4-4) Fast Read Number of	000b:Mode Bits not support	3011	07:05	010h	44H
Mode Bits	OUOD.Mode Bits not support		07:05	010b	
(1-4-4) Fast Read Opcode		39H	15:08	EBH	EBH
(1-1-4) Fast Read Number of	0 0000b: Wait states (Dummy		20.46	040006	
Wait states	Clocks) not support	3AH	20:16	01000b	08H
(1-1-4) Fast Read Number of	000b:Mode Bits not support	JAH	23:21	000b	∪0⊓
Mode Bits	ooob.iviode bits not support		۷۵.۷۱	auuu	
(1-1-4) Fast Read Opcode		3BH	31:24	6BH	6BH
(1-1-2) Fast Read Number of	0 0000b: Wait states (Dummy		04:00	010006	
Wait states	Clocks) not support	3CH	04:00	01000b	08H
(1-1-2) Fast Read Number	000b: Mode Bits not support		07:05 000	000b	1



ZD25LQ16A

Dadi alia (guau Seriari iasii															
of Mode Bits																
(1-1-2) Fast Read Opcode		3DH	15:08	3BH	звн											
(1-2-2) Fast Read Number	0 0000b: Wait states (Dummy		20.46	000405												
of Wait states	Clocks) not support	3EH	20:16	00010b	42H											
(1-2-2) Fast Read Number	000b: Mode Bits not support	JEII	23:21	010b	4211											
of Mode Bits	OOOD. Wode Bits flot support		20.21	0100												
(1-2-2) Fast Read Opcode		3FH	31:24	BBH	BBH											
(2-2-2) Fast Read	0=not support 1=support		00	0b												
Unused		40H	03:01	111b	EEH											
(4-4-4) Fast Read	0=not support 1=support	4011	04	0b												
Unused			07:05	111b												
Unused		43H:41H	31:08	0xFFH	0xFFH											
Unused		45H:44H	15:00	0xFFH	0xFFH											
(2-2-2) Fast Read Number	0 0000b: Wait states (Dummy		20:16	00000b												
of Wait states	Clocks) not support	46H	20.10	000000	00H											
(2-2-2) Fast Read Number	000b: Mode Bits not support	4011	23:21	000b	0011											
of Mode Bits	ooob. Wode Bits not support		20.21	0000												
(2-2-2) Fast Read Opcode		47H	31:24	FFH	FFH											
Unused		49H:48H	15:00	0xFFH	0xFFH											
(4-4-4) Fast Read Number of	0 0000b: Wait states (Dummy		20:16	00000b												
Wait states	Clocks) not support	4AH	20.10	000000	00H											
(4-4-4) Fast Read Number	000b: Mode Bits not support	7/11	7 4 1				., ., .		,, ,, ,	7 4 1	,,,,,	7 4 1	,, ,, ,	23:21	000b	0011
of Mode Bits	11		-													
(4-4-4) Fast Read Opcode		4BH	31:24	FFH	FFH											
Sector Type 1 Size	Sector/block size=2^N bytes	4CH	07:00	0CH	0CH											
	0x00b: this sector type don't exist															
Sector Type 1 erase Opcode		4DH	15:08	20H	20H											
Sector Type 2 Size	Sector/block size=2^N bytes	4EH	23:16	0FH	0FH											
	0x00b: this sector type don't exist															
Sector Type 2 erase Opcode		4FH	31:24	52H	52H											
Sector Type 3 Size	Sector/block size=2^N bytes	50H	07:00	10H	10H											
	0x00b: this sector type don't exist		17.00	500												
Sector Type 3 erase Opcode		51H	15:08	D8H	D8H											
Sector Type 4 Size	Sector/block size=2^N bytes	52H	23:16	00H	00H											
Ocates Time 4 a Continue	0x00b: this sector type don't exist	5011	04.04	FFU												
Sector Type 4 erase Opcode		53H	31:24	FFH	FFH											

ZD25LQ16A

Table5. Parameter Table (1): Zetta Flash Parameter Tables

Description	Comment	Add(H) (Byte)	DW Add (Bit)	Data	Data
Vcc Supply Maximum Voltage	2000H=2.000V 2100H=2.100V 2700H=2.700V 3600H=3.600V	61H:60H	15:00	2100H	2100H
Vcc Supply Minimum Voltage	1650H=1.650V 2250H=2.250V 2350H=2.350V 2700H=2.700V	63H:62H	31:16	1650H	1650H
HW Reset# pin	0=not support 1=support		00	0b	
HW Hold# pin	0=not support 1=support		01	1b	
Deep Power Down Mode	0=not support 1=support		02	1b	
SW Reset	0=not support 1=support		03	1b	
SW Reset Opcode	Should be issue Reset Enable(66H) before Reset cmd.	65H:64H	11:04	99H	F99EH
Program Suspend/Resume	0=not support 1=support		12	1b	
Erase Suspend/Resume	0=not support 1=support		13	1b	
Unused			14	1b	
Wrap-Around Read mode	0=not support 1=support		15	1b	
Wrap-Around Read mode Opcode		66H	23:16	77H	77H
Wrap-Around Read data length	08H:support 8B wrap-around read 16H:8B&16B 32H:8B&16B&32B 64H:8B&16B&32B&64B	67H	31:24	64H	64H
Individual block lock	0=not support 1=support		00	0b	
Individual block lock bit (Volatile/Nonvolatile)	0=Volatile 1=Nonvolatile		01	0b	
Individual block lock Opcode			09:02	FFH	
Individual block lock Volatile protect bit default protect status	0=protect 1=unprotect	6BH:68	10	0b	EBFC H
Secured OTP	0=not support 1=support	Н	11	1b	
Read Lock	0=not support 1=support		12	0b	
Permanent Lock	0=not support 1=support		13	1b]
Unused			15:14	11b	
Unused			31:16	FFFFH	FFFFH



ELECTRICAL CHARACTERISTICS

8.1 POWER-ON TIMING

Figure 36. Power-On Timing Sequence Diagram




Table 6. Power-Up Timing and Write Inhibit Threshold

Symbol	Parameter	Min.	Max.	Unit
tVSL	VCC(min.)to device operation	5		ms
VWI	Write Inhibit Voltage	1	1.4	V
VPWD	VCC voltage needed to below VPWD for ensuring initialization will occur		0.5	V
tPWD	The minimum duration for ensuring initialization will occur	300		us


8.2 Initial Delivery State

The device is delivered with the memory array erased: all bits are set to 1(each byte contains FFH). The Status Register contains 00H (all Status Register bits are 0).

8.3 Absolute Maximum Ratings

Parameter	Value	Unit
Ambient Operating Temperature	-40 to 85	$^{\circ}\!\mathbb{C}$
Storage Temperature	-65 to 150	$^{\circ}\!\mathbb{C}$
Transient Input / Output Voltage(note: overshoot)	-2.0 to VCC+2.0	V
Applied Input/Output Voltage	-0.6 to VCC+0.5	V
VCC	-0.6 to 2.5	V

Figure 37. Input Test Waveform and Measurement Level






8.4 Capacitance Measurement Conditions


Symbol	Parameter	Min.	Тур.	Max.	Unit	Conditions
CIN	Input Capacitance			6	pF	VIN=0V
COUT	Output Capacitance			8	pF	VOUT=0V
CL	Load Capacitance		30		pF	
	Input Rise And Fall time			5	ns	
	Input Pause Voltage	0.2VCC to 0.8VCC		V		
	Input Timing Reference Voltage	0.3VC	C to 0.7V0	CC	V	
	Output Timing Reference Voltage		0.5VCC		V	

Figure 38. Absolute Maximum Ratings Diagram

Maximum Negative Overshoot Waveform



Maximum Positive Overshoot Waveform





8.5 DC CHARACTERISTICS

(T= -40 $^{\circ}\text{C}$ ~85 $^{\circ}\text{C}$, VCC=1.65~2.1V)

Symbol	Parameter	Test Condition	Min.	Тур.	Max.	Unit.	
ILI	Input Leakage Current				±2	μΑ	
ILO	Output Leakage Current				±2	μA	
,	Ctorodhy Cymrant	CS#=VCC,		0	25		
Icc ₁	Standby Current	V _{IN} =VCC or VSS		9	25	μA	
	Danie Davies Davies Command	CS#=VCC,		0.2	_		
I _{CC2}	Deep Power-Down Current	V _{IN} =VCC or VSS			5	μA	
		CLK=0.1VCC /					
		0.9VCC		5	8	A	
		at 104MHz,		5	0	mA	
		Q=Open(*1,*2,*4 I/O)					
		CLK=0.1VCC /			6		
I _{CC3}	Operating Current (Read)	0.9VCC		4		m A	
1003	Operating Outrent (read)	at 80MHz,		4		mA	
		Q=Open(*1,*2,*4 I/O)					
		CLK=0.1VCC /			6		
		0.9VCC		3		mA	
		at 48MHz,		3		ША	
		Q=Open(*1,*2,*4 I/O)					
I _{CC4}	Operating Current (PP)	CS#=VCC		15	20	mA	
Icc5	Operating Current(WRSR)	CS#=VCC		15	20	mA	
Icc6	Operating Current (SE)	CS#=VCC		15	20	mA	
I _{CC7}	Operating Current (BE)	CS#=VCC		15	20	mA	
I _{CC8}	Operating Current (CE)	CS#=VCC		15	20	mA	
VIL	Input Low Voltage				0.2VCC	V	
ViH	Input High Voltage		0.7VCC			V	
V_{OL}	Output Low Voltage	I _{OL} =100uA			0.2	V	
V _{OH}	Output High Voltage	Ι _{ΟΗ} =-100μΑ	VCC-0.2			V	



8.6 AC CHARACTERISTICS

(T= -40 °C ~85 °C, VCC=1.65~2.1V, C∟=30pf)

Symbol	Parameter	Min.	Тур.	Max.	Unit.
F	Serial Clock Frequency For: 0BH, 3BH, BBH, 6BH,	DO		404	
Fc	EBH, E7H	DC.		104	MHz
f _R	Serial Clock Frequency For: Read(03H)	DC.		80	MHz
t _{CLH}	Serial Clock High Time	4			ns
t _{CLL}	Serial Clock Low Time	4			ns
tclch	Serial Clock Rise Time (Slew Rate)	0.1			V/ns
tchcl	Serial Clock Fall Time (Slew Rate)	0.1			V/ns
tslch	CS# Active Setup Time	5			ns
tcнsн	CS# Active Hold Time	5			ns
tshch	CS# Not Active Setup Time	5			ns
t _{CHSL}	CS# Not Active Hold Time	5			ns
t _{SHSL}	CS# High Time (read/write)	20			ns
tshqz	Output Disable Time			6	ns
t _{CLQX}	Output Hold Time	1.2			ns
tovch	Data In Setup Time	2			ns
t _{CHDX}	Data In Hold Time	2			ns
thlch	Hold# Low Setup Time (relative to Clock)	5			ns
tннсн	HOLD# High Setup Time (relative to Clock)	5			ns
tchhl	Hold# High Hold Time (relative to Clock)	5			ns
t _{CHHH}	Hold# Low Hold Time (relative to Clock)	5			ns
t _{HLQZ}	Hold# Low To High-Z Output			6	ns
t _{HHQX}	Hold# Low To Low-Z Output			6	ns
tcLQV	Clock Low To Output Valid			7	ns
twhsl	Write Protect Setup Time Before CS# Low	20			ns
tshwL	Write Protect Hold Time After CS# High	100			ns
t _{DP}	CS# High To Deep Power-Down Mode			3	μs
	CS# High To Standby Mode Without Electronic			_	
t _{RES1}	Signature Read			3	μs
	CS# High To Standby Mode With Electronic Signature				
t _{RES2}	Read			1.8	μs
t _{RES3}	CS# High to Next Program/Erase Command			12	μs
tsus	CS# High To Next Command After Suspend			20	μs
t _{RST_R}	CS# High To Next Command After Reset (from read)			20	μs
	CS# High To Next Command After Reset (from			00	
trst_p	program)			20	μs
t _{RST_E}	CS# High To Next Command After Reset (from erase)			12	ms
t _W	Write Status Register Cycle Time		1	20	ms
t _{BP1}	Byte Program Time(First Byte)		15	30	μs
t _{BP2}	Addition Byte Program Time(After First Byte)		2.5	5	μs
t _{PP}	Page Programming Time		0.7	2.4	ms



ZD25LQ16A

tse	Sector Erase Time	40	150/300 ⁽¹⁾	ms
t _{BE}	Block Erase Time(32K Bytes)	0.15	0.8	s
t _{BE}	Block Erase Time(64K Bytes)	0.18	1	s
tce	Chip Erase Time(ZD25LQ16A)	5	10	s

Note:

1.Max Value 4KB t_{sE} with < 50K cycles is 150ms and > 50K& < 100K cycles is 300ms.

Figure 39. Serial Input Timing




Figure 40. Output Timing






Figure 41. Hold Timing






ORDERING INFORMATION








10 PACKAGE INFORMATION

10.1 Package SOP8 150MIL










Dimensions

Symb	ol		A1	A2	h	С	D	Е	E1			14	۵	~	0
Unit		A	AI	AZ	b		0	_	E1	е	L	L1	θ	α	β
	Min	1.35	0.05	1.35	0.31	0.15	4.77	5.80	3.80	-	0.40	0.85	0°	6°	11°
mm	Nom	-	-	-	-	-	4.90	6.00	3.90	1.27	-	1.06	-	7°	12°
	Max	1.75	0.25	1.55	0.51	0.25	5.03	6.20	4.00	-	0.90	1.27	8°	8°	13°
	Min	0.053	0.002	0.053	0.012	0.006	0.188	0.228	0.149	-	0.016	0.033	0°	6°	11°
Inch	Nom	-	-	-	0.016	-	0.193	0.236	0.154	0.050	-	0.042	-	7°	12°
	Max	0.069	0.010	0.061	0.020	0.010	0.198	0.244	0.158	-	0.035	0.050	8°	8°	13°

- 1. Both package length and width include mold flash.
- 2. Seating plane: Max 0.1mm.




10.2 Package SOP8 208MIL




Dimensions

Sym	bol	Α	A 4	A2	h	С	D	E	E1			1.4	θ
Unit		Α	A1	AZ	b		ט		E1	е	_ _	L1	ן פ
	Min	1.75	0.05	1.70	0.31	0.18	5.13	7.70	5.18		0.50	1.21	0
mm	Nom	1.95	0.15	1.80	0.41	0.21	5.23	7.90	5.28	1.27	0.67	1.31	5
	Max	2.16	0.25	1.91	0.51	0.25	5.33	8.10	5.38		0.85	1.41	8
	Min	0.069	0.002	0.067	0.012	0.007	0.202	0.303	0.204		0.020	0.048	0
Inch	Nom	0.077	0.006	0.071	0.016	0.008	0.206	0.311	0.208	0.050	0.026	0.052	5
	Max	0.085	0.010	0.075	0.020	0.010	0.210	0.319	0.212		0.033	0.056	8

- 1. Both package length and width include mold flash.
- 2. Seating plane: Max 0.1mm.



10.3 Package VSOP8 150MIL




Dimensions

Symb	ool			40		_	_	_	F4	_		1.4	_		
Unit		A	A1	A2	b	С	D	E	E1	е	L	L1	θ	α	β
	Min	-	0.05	0.65	0.35	0.09	4.80	5.80	3.80	-	0.40	-	0°	-	-
mm	Nom	-	0.10	0.70	0.42	-	4.90	6.00	3.90	1.27	0.71	1.05	-	10°	10°
	Max	0.90	0.15	0.75	0.48	0.20	5.00	6.20	4.00	-	1.27	-	10°	-	-
	Min	-	0.002	0.026	0.014	0.004	0.189	0.228	0.150	-	0.016	-	0°	-	-
Inch	Nom	-	0.004	0.028	0.017	-	0.193	0.236	0.154	0.050	0.028	0.041	-	10°	10°
	Max	0.035	0.006	0.030	0.019	0.008	0.197	0.244	0.157	-	0.050	-	10°	-	-

- 1. Both package length and width include mold flash.
- 2. Seating plane: Max 0.1mm.



10.4 Package VSOP8 208MIL




Dimensions

Syı	mbol	Α	A1	A2	b	D	E	E1			L1	С	θ
U	Jnit	A	AI	AZ	D	ט	_	<u> </u>	е	L	LI	C	0
	Min	0.80	0.05	0.75	0.35	5.18	7.70	5.18	-	0.50		0.09	0°
mm	Nom	0.90	0.10	0.80	0.42	5.28	7.90	5.28	1.27BSC	0.65	1.31REF	-	-
	Max	1.00	0.15	0.85	0.48	5.38	8.10	5.38	-	0.80		0.2	10°
	Min	0.032	0.002	0.030	0.014	0.204	0.303	0.204	-	0.020		0.004	0°
Inch	Nom	0.035	0.004	0.031	0.017	0.208	0.311	0.208	0.050BSC	0.026	0.052REF	0	-
	Max	0.04	0.006	0.033	0.019	0.212	0.319	0.212	-	0.031		0.008	10°

- 1. Both package length and width include mold flash.
- 2. Seating plane: Max 0.1mm.

10.5 Package WSON 8 (6*5mm)




Bottom View

Dimensions


Symb	ool		A 4	A2	h	D	D1	E	E1			
Unit		Α	A1	AZ	b		וש		E1	е	У	L
	Min	0.70		0.19	0.35	5.90	3.25	4.90	3.85		0.00	0.50
mm	Nom	0.75		0.22	0.42	6.00	3.37	5.00	3.97	1.27 BSC	0.04	0.60
	Max	0.80	0.05	0.25	0.48	6.10	3.50	5.10	4.10		0.08	0.75
	Min	0.028		0.007	0.014	0.232	0.128	0.193	0.151		0.000	0.020
Inch	Nom	0.030		0.009	0.016	0.236	0.133	0.197	0.156	0.05 BSC	0.001	0.024
	Max	0.032	0.002	0.010	0.019	0.240	0.138	0.201	0.161		0.003	0.030

- 1. Both package length and width do not include mold flash.
- 2. The exposed metal pad area on the bottom of the package is connected to device ground (GND pin), so both Floating and connecting GND of exposed pad are also available.


10.6 Package USON8 (3*4mm)







Bottom View




Dimensions

Syml	bol	A	A1	A2	A 3	b	D	E	e	J	K1	K2	
Unit		_ ^	A1	AZ	AS			_	6	J	KI	IX2	_
	Min	0.50	0.00	0.35		0.25	2.90	3.90		0.10	0.70	0.70	0.55
mm	Nom	0.55		0.40	0.15	0.30	3.00	4.00	0.80	0.20	0.80	0.80	0.60
	Max	0.60	0.05	0.45	REF	0.35	3.10	4.10	BSC	0.30	0.90	0.90	0.65
	Min	0.020	0.000	0.001		0.010	0.114	0.153		0.000	0.002	0.002	0.001
Inch	Nom	0.022		0.001	0.15	0.012	0.118	0.157	0.80	0.001	0.002	0.002	0.001
	Max	0.024	0.002	0.001	REF	0.014	0.122	0.161	BSC	0.001	0.002	0.002	0.002

- 1. Both package length and width do not include mold flash.
- 2. The exposed metal pad area on the bottom of the package is connected to device ground (GND pin), so both Floating and connecting GND of exposed pad are also available.
- 3. Coplanarity ≤0.08mm. Package edge tolerance≤0.10mm.

10.7 Package USON8 (4*4mm, 0.45 thickness)




Dimensions

Symb	ol		A 4	A 2	A 2	b	D	_			V	
Unit		A	A1	A2	A3	b	0	E	e	J	K	L
	Min	0.40	0.00		0.25	0.25	3.90	3.90		2.20	2.90	0.35
mm	Nom	0.45			0.30	0.30	4.00	4.00		2.30	3.00	0.40
	Max	0.50	0.05	0.15	0.35	0.35	4.10	4.10	0.8	2.40	3.10	0.45
	Min	0.015	0.000	REF	0.009	0.009	0.153	0.153	BSC	0.086	0.114	0.013
Inch	Nom	0.017			0.011	0.011	0.157	0.157		0.090	0.118	0.015
	Max	0.019	0.001		0.013	0.013	0.161	0.161		0.094	0.122	0.017

- 1. Both package length and width do not include mold flash.
- 2. The exposed metal pad area on the bottom of the package is connected to device ground (GND pin), so both Floating and connecting GND of exposed pad are also available.
- 3. Coplanarity ≤0.08mm. Package edge tolerance≤0.10mm.

10.8 Package USON8 (3*3mm)




Bottom View

Dimensions

Syml	bol							_	_		D4	F4
Unit		A	A1	A2	A3	b	D	E	е	_ L	D1	E1
	Min	0.40	0.00	0.25		0.20	2.95	2.95		0.35	1.65	2.15
mm	Nom	0.45		0.30	0.15	0.25	3.00	3.00	0.50	0.40	1.70	2.20
	Max	0.50	0.05	0.35	REF	0.30	3.05	3.05	BSC	0.45	1.75	2.25
	Min	0.016	0.000	0.010		0.008	0.116	0.116		0.014	0.065	0.085
Inch	Nom	0.018		0.012	0.006	0.010	0.118	0.118	0.020	0.016	0.067	0.087
	Max	0.020	0.002	0.014	REF	0.012	0.120	0.120	BSC	0.018	0.069	0.089

- 1. Both package length and width do not include mold flash.
- 2. The exposed metal pad area on the bottom of the package is connected to device ground (GND pin), so both Floating and connecting GND of exposed pad are also available.
- 3. Coplanarity ≤0.08mm. Package edge tolerance≤0.10mm.


10.9 Package LGA8 3*2mm





Dimensions

Cumahal		mm			inch			
Symbol	Min	Nom	Max	Min	Nom	Max		
А	0.340	0.420	0.500	0.013	0.017	0.020		
С	0.140	0.170	0.200	0.006	0.007	0.008		
D	2.950	3.000	3.050	0.116	0.118	0.120		
Е	1.950	2.000	2.050	0.077	0.079	0.081		
D1	0.150	0.200	0.250	0.006	0.008	0.010		
E1	1.550	1.600	1.650	0.061	0.063	0.065		
Н		0.150			0.006			
H1		0.150			0.006			
L	0.275	0.350	0.425	0.011	0.014	0.017		
L1		0.100			0.004			
L2	0.050	0.125	0.200	0.002	0.005	0.008		
е		0.500			0.020			
В	0.200	0.250	0.300	0.008	0.010	0.012		
aaa		0.100			0.004			
bbb		0.150			0.006			
ccc		0.100		0.004				
ddd		0.080		0.003				
eee		0.150			0.006			

10.10 Package WLCSP







Dimensions

Syr	nbol	_	A1	A2	А3	D	D1	E	E1	•	b	X1	X2	Y1	Y2
U	nit	Α	AI	AZ	AS		וט		E1	е	D	ΛI	^2	11	12
	Min	0.444	0.147	0.250	0.025	2.396	1.500	1.038	0.500	0.500	0.209	0.279	0.279	0.458	0.458
mm	Nom	0.472	0.177	0.270	BSC	2.416	BSC	1.058	BSC	BSC	0.239	REF	REF	REF	REF
	Max	0.500	0.207	0.290	ВЗС	2.436	ВЗС	1.078	ВЗС	50	0.269	KLI	KEF	NEF	NEF
	Min	0.017	0.006	0.010	0.001	0.094	0.059	0.041	0.019	0.019	0.008	0.011	0.011	0.018	0.018
Inch	Nom	0.019	0.007	0.011	BSC	0.095	BSC	0.042	7BSC	7BSC	0.009	REF	REF	REF	REF
	Max	0.020	0.008	0.012	DSC	0.096	DSC	0.042	1030	7000	0.011	NEF	NEF	NEF	NEF

ZD25LQ16A

11 REVISION HISTORY

Version No	Description	Page	Date
1.0	Initial release	All	2017-7-7
1.1	Modify lcc2 max. value from 1 to 5	P46	2017-7-25
1.1	Modify tw max. value from 15ms to 20ms	P47	2017-7-25
1.2	Delete Security Register #0 in 48H command	P38	2017-8-21