- Fully Synchronous Operation for Counting and Programming
- Internal Carry Look-Ahead Circuitry for Fast Counting
- Carry Output for n-Bit Cascading
- Fully Independent Clock Circuit
- Package Options Include Plastic Small-Outline (D) Packages, Ceramic Chip Carriers (FK), and Standard Plastic (N) and Ceramic (J) 300-mil DIPs


#### description

These synchronous 4-bit up/down binary presettable counters feature an internal carry look-ahead circuitry for cascading in high-speed counting applications. Synchronous operation is provided by having all flip-flops clocked simultaneously so that the outputs change coincident with each other when so instructed by the count-enable (ENP, ENT) inputs and internal gating. This mode of operation eliminates the output counting spikes normally associated with asynchronous (ripple-clock) counters. A buffered clock (CLK) input triggers the four flip-flops on the rising (positive-going) edge of the clock waveform.


These counters are fully programmable; that is, they may be preset to either level. The load-input circuitry allows loading with the carry-enable output of cascaded counters. Because loading is synchronous, setting up a low level at the load  $(\overline{LOAD})$  input disables the counter and causes the outputs to agree with the data inputs after the next clock pulse.

SN54ALS169B, SN54AS169A... J PACKAGE SN74ALS169B, SN74AS169A... D OR N PACKAGE (TOP VIEW)

SDAS125B - MARCH 1984 - REVISED DECEMBER 1994



## SN54ALS169B, SN54AS169A . . . FK PACKAGE (TOP VIEW)



NC - No internal connection

The internal carry look-ahead circuitry provides for cascading counters for n-bit synchronous application without additional gating. ENP and ENT inputs and a ripple-carry output (RCO) are instrumental in accomplishing this function. Both ENP and ENT must be low to count. The direction of the count is determined by the level of the up/down ( $U/\overline{D}$ ) input. When  $U/\overline{D}$  is high, the counter counts up; when low, it counts down. ENT is fed forward to enable RCO. RCO, thus enabled, produces a low-level pulse while the count is zero (all inputs low) counting down or maximum (15) counting up. This low-level overflow ripple-carry pulse can be used to enable successive cascaded stages. Transitions at ENP or ENT are allowed regardless of the level of the clock input. All inputs are diode clamped to minimize transmission-line effects, thereby simplifying system design.

These counters feature a fully independent clock circuit. Changes at control inputs ( $\overline{\text{ENP}}$ ,  $\overline{\text{ENT}}$ ,  $\overline{\text{LOAD}}$ , or U/D) that modify the operating mode have no effect on the contents of the counter until clocking occurs. The function of the counter (whether enabled, disabled, loading, or counting) is dictated solely by the conditions meeting the stable setup and hold times.


The SN54ALS169B and SN54AS169A are characterized for operation over the full military temperature range of –55°C to 125°C. The SN74ALS169B and SN74AS169A are characterized for operation from 0°C to 70°C.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.



SDAS125B - MARCH 1984 - REVISED DECEMBER 1994


#### logic symbol<sup>†</sup>



<sup>†</sup> This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12. Pin numbers shown are for the D, J, and N packages.



SDAS125B - MARCH 1984 - REVISED DECEMBER 1994



logic diagram (positive logic)

Pin numbers shown are for the D, J, and N packages.




SDAS125B - MARCH 1984 - REVISED DECEMBER 1994

#### typical load, count, and inhibit sequences

The following sequence is illustrated below:

- 1. Load (preset) to binary 13
- 2. Count up to 14, 15 (maximum), 0, 1, and 2
- 3. Inhibit
- 4. Count down to 1, 0 (minimum), 15, 14, and 13



#### absolute maximum ratings over operating free-air temperature range (unless otherwise noted)<sup>†</sup>

Supply voltage, V <sub>CC</sub>	7 V
Input voltage, V	7V
Operating free-air temperature range, T <sub>A</sub> : SN54ALS169B	–55°C to 125°C
SN74ALS169B	0°C to 70°C
Storage temperature range	–65°C to 150°C

<sup>†</sup> Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.



SDAS125B - MARCH 1984 - REVISED DECEMBER 1994

#### recommended operating conditions

			SN	54ALS16	9B	SN7	4ALS16	9B	
			MIN	NOM	MAX	MIN	NOM	MAX	UNIT
VCC	Supply voltage		4.5	5	5.5	4.5	5	5.5	V
VIH	High-level input voltage		2			2			V
VIL	Low-level input voltage				0.7			0.8	V
ЮН	High-level output current				-0.4			-0.4	mA
IOL	Low-level output current				4			8	mA
fclock	Clock frequency		0		22	0		40	MHz
t <sub>W</sub>	Pulse duration, CLK high or low		14			12.5			ns
		A, B, C, or D	20			15			
		ENP or ENT	25			15			
t <sub>su</sub>	Setup time before CLK↑	LOAD	20			15			ns
		U/D	28			15			
t <sub>h</sub>	Hold time, data after $CLK^\uparrow$		0			0			ns
Т <sub>А</sub>	Operating free-air temperature		-55		125	0		70	°C

# electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

	7507.0	TEST CONDITIONS			9B	SN7	'4ALS16	9B	
PARAMETER	TEST C	ONDITIONS	MIN	түр†	MAX	MIN	TYP†	MAX	UNIT
VIK	$V_{CC} = 4.5 V,$	l <sub>l</sub> = – 18 mA			-1.5			-1.5	V
VOH	$V_{CC} = 4.5 V$ to 5.5 V,	I <sub>OH</sub> = -0.4 mA	V <sub>CC</sub> -2	2		V <sub>CC</sub> -2	2		V
		$I_{OL} = 4 \text{ mA}$		0.25	0.4		0.25	0.4	V
VOL	$V_{CC} = 4.5 V$	I <sub>OL</sub> = 8 mA					0.35	0.5	V
lı	V <sub>CC</sub> = 5.5 V,	V <sub>I</sub> = 7 V			0.1			0.1	mA
IIH	$V_{CC} = 5.5 V,$	V <sub>I</sub> = 2.7 V			20			20	μΑ
١ <sub>١L</sub>	V <sub>CC</sub> = 5.5 V,	V <sub>I</sub> = 0.4 V			-0.2			-0.2	mA
10 <sup>‡</sup>	V <sub>CC</sub> = 5.5 V,	V <sub>O</sub> = 2.25 V	-20		-112	-30		-112	mA
ICC	V <sub>CC</sub> = 5.5 V			15	25		15	25	mA

<sup>†</sup> All typical values are at V<sub>CC</sub> = 5 V, T<sub>A</sub> = 25°C.

<sup>‡</sup> The output conditions have been chosen to produce a current that closely approximates one half of the true short-circuit output current, IOS.



SDAS125B - MARCH 1984 - REVISED DECEMBER 1994

#### switching characteristics (see Figure 1)

PARAMETER	FROM (INPUT)	ТО (ОИТРИТ)	C <sub>I</sub> R	$V_{CC}$ = 4.5 V to 5.5 V, $C_{L}$ = 50 pF, $R_{L}$ = 500 Ω, $T_{A}$ = MIN to MAX <sup>†</sup>					
	(			S169B	SN74AL	S169B			
			MIN	MAX	MIN	MAX			
f <sub>max</sub>			22		40		MHz		
<sup>t</sup> PLH	OLK.	<b>B00</b>	3	20	3	20			
<sup>t</sup> PHL	CLK	RCO	6	25	6	20	ns		
<sup>t</sup> PLH		Am. 0	2	20	2	15			
<sup>t</sup> PHL	CLK	Any Q	5	23	5	20	ns		
<sup>t</sup> PLH		<b>B00</b>	2	16	2	13			
<sup>t</sup> PHL	ENT	RCO	3	24	3	16	ns		
<sup>t</sup> PLH	U/D	RCO	4	22	5	19			
<sup>t</sup> PHL	U/D	RCO	5	26	5	19	ns		

<sup>†</sup> For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.

#### absolute maximum ratings over operating free-air temperature range (unless otherwise noted)<sup>‡</sup>

Supply voltage, V <sub>CC</sub>	
Input voltage, V <sub>I</sub>	7V
Operating free-air temperature range, T <sub>A</sub> : SN54AS169A	–55°C to 125°C
SN74AS169A	0°C to 70°C
Storage temperature range	-65°C to 150°C

‡ Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

#### recommended operating conditions

			SN	54AS16	9A	SN	74AS169	9A	
			MIN	NOM	MAX	MIN	NOM	MAX	UNIT
VCC	Supply voltage		4.5	5	5.5	4.5	5	5.5	V
VIH	High-level input voltage		2			2			V
VIL	Low-level input voltage				0.8			0.8	V
ЮН	High-level output current				-2			-2	mA
IOL	Low-level output current				20			20	mA
fclock*	Clock frequency		0		60	0		75	MHz
tw*	Pulse duration, CLK high or low		7.7			6.7			ns
		A, B, C, or D	10			8			
1 *	Cotum times hatara CLK <sup>1</sup>	ENP or ENT	10			8			
t <sub>su</sub> *	Setup time before CLK↑	LOAD	10			8			ns
		U/D	14			11			
<sup>t</sup> h*	Hold time, data after $CLK^\uparrow$		2			0			ns
ТА	Operating free-air temperature		-55		125	0		70	°C

\* On products compliant to MIL-STD-883, Class B, this parameter is based on characterization data but is not production tested.



SDAS125B - MARCH 1984 - REVISED DECEMBER 1994

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

		7507.001		SN	54AS16	9A	SN	74AS169	A	
	PARAMETER	TEST CON	DITIONS	MIN	TYP†	MAX	MIN	TYP†	MAX	UNIT
VIK		$V_{CC} = 4.5 V,$	lj = – 18 mA			-1.2			-1.2	V
VOH		$V_{CC}$ = 4.5 V to 5.5 V,	$I_{OH} = -2 \text{ mA}$	V <sub>CC</sub> -2	2		V <sub>CC</sub> -2	2		V
VOL		$V_{CC} = 4.5 V,$	I <sub>OL</sub> = 20 mA		0.25	0.5		0.25	0.5	V
	LOAD, ENT, U/D					0.2			0.2	
1	All others	V <sub>CC</sub> = 5.5 V,	V <sub>I</sub> = 7 V			0.1			0.1	mA
	LOAD, ENT, U/D		V 07V			40			40	•
ЧН	All others	V <sub>CC</sub> = 5.5 V,	V <sub>I</sub> = 2.7 V			20			20	μA
	LOAD, ENT, U/D		N 0.4 M			-1			-1	
ΊL	All others	V <sub>CC</sub> = 5.5 V,	$V_{I} = 0.4 V$			-0.5			-0.5	mA
IO‡		V <sub>CC</sub> = 5.5 V,	V <sub>O</sub> = 2.25 V	-30		-112	-30		-112	mA
ICC		V <sub>CC</sub> = 5.5 V			41	63		41	63	mA

<sup>†</sup> All typical values are at V<sub>CC</sub> = 5 V, T<sub>A</sub> = 25°C. <sup>‡</sup> The output conditions have been chosen to produce a current that closely approximates one half of the true short-circuit output current, I<sub>OS</sub>.


#### switching characteristics (see Figure 1)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	VC CL RL TA	UNIT			
	(	(,	SN54A	S169A	SN74A	S169A	
			MIN	MAX	MIN	MAX	
<sup>f</sup> max <sup>*</sup>			60		75		MHz
<sup>t</sup> PLH		RCO	3	17.5	3	16.5	
<sup>t</sup> PHL	CLK	(LOAD high or low)	2	14	2	13	ns
<sup>t</sup> PLH		A	1	7.5	1	7	
<sup>t</sup> PHL	CLK	Any Q	2	14	2	13	ns
<sup>t</sup> PLH		<del></del>	1.5	10	1.5	9	
<sup>t</sup> PHL	ENT	RCO	1.5	10	1.5	9	ns
<sup>t</sup> PLH	U/D	RCO	2	14	2	12	
<sup>t</sup> PHL	0,0	KCU	2	14.5	2	13	ns

\* On products compliant to MIL-STD-883, Class B, this parameter is based on characterization data but is not production tested. § For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.



SDAS125B - MARCH 1984 - REVISED DECEMBER 1994



NOTES: A. CL includes probe and jig capacitance.

- B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
   C. When measuring propagation delay items of 3-state outputs, switch S1 is open.
- . When measuring propagation delay items of 3-state outputs, switch S1 is open.
- D. All input pulses have the following characteristics: PRR  $\leq$  1 MHz,  $t_{f}$  =  $t_{f}$  = 2 ns, duty cycle = 50%.
- E. The outputs are measured one at a time with one transition per measurement.

#### Figure 1. Load Circuits and Voltage Waveforms





#### PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material (6)	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
8302501EA	ACTIVE	CDIP	J	16	1	Non-RoHS & Green	SNPB	N / A for Pkg Type	-55 to 125	8302501EA SNJ54ALS169BJ	Samples
JM38510/38003BEA	ACTIVE	CDIP	J	16	1	Non-RoHS & Green	SNPB	N / A for Pkg Type	-55 to 125	JM38510/ 38003BEA	Samples
M38510/38003BEA	ACTIVE	CDIP	J	16	1	Non-RoHS & Green	SNPB	N / A for Pkg Type	-55 to 125	JM38510/ 38003BEA	Samples
SN54ALS169BJ	ACTIVE	CDIP	J	16	1	Non-RoHS & Green	SNPB	N / A for Pkg Type	-55 to 125	SN54ALS169BJ	Samples
SN74ALS169BD	LIFEBUY	SOIC	D	16	40	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	0 to 70	ALS169B	
SN74ALS169BDR	ACTIVE	SOIC	D	16	2500	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	0 to 70	ALS169B	Samples
SN74ALS169BN	ACTIVE	PDIP	Ν	16	25	RoHS & Green	NIPDAU	N / A for Pkg Type	0 to 70	SN74ALS169BN	Samples
SN74ALS169BNSR	ACTIVE	SO	NS	16	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	0 to 70	ALS169B	Samples
SN74AS169AN	ACTIVE	PDIP	N	16	25	RoHS & Green	NIPDAU	N / A for Pkg Type	0 to 70	SN74AS169AN	Samples
SNJ54ALS169BJ	ACTIVE	CDIP	J	16	1	Non-RoHS & Green	SNPB	N / A for Pkg Type	-55 to 125	8302501EA SNJ54ALS169BJ	Samples

<sup>(1)</sup> The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

<sup>(2)</sup> **RoHS:** TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

<sup>(3)</sup> MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.



#### www.ti.com

### PACKAGE OPTION ADDENDUM

<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

<sup>(5)</sup> Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

<sup>(6)</sup> Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:**The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

#### OTHER QUALIFIED VERSIONS OF SN54ALS169B, SN74ALS169B :

- Catalog : SN74ALS169B
- Military : SN54ALS169B

NOTE: Qualified Version Definitions:

- Catalog TI's standard catalog product
- Military QML certified for Military and Defense Applications



Texas

STRUMENTS

#### TAPE AND REEL INFORMATION





#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal												
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
SN74ALS169BDR	SOIC	D	16	2500	330.0	16.4	6.5	10.3	2.1	8.0	16.0	Q1
SN74ALS169BNSR	SO	NS	16	2000	330.0	16.4	8.2	10.5	2.5	12.0	16.0	Q1



www.ti.com

### PACKAGE MATERIALS INFORMATION

3-Jun-2022



\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
SN74ALS169BDR	SOIC	D	16	2500	340.5	336.1	32.0
SN74ALS169BNSR	SO	NS	16	2000	356.0	356.0	35.0

#### TEXAS INSTRUMENTS

www.ti.com

3-Jun-2022

#### TUBE



### - B - Alignment groove width

#### \*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	Τ (μm)	B (mm)
SN74ALS169BD	D	SOIC	16	40	507	8	3940	4.32
SN74ALS169BN	N	PDIP	16	25	506	13.97	11230	4.32
SN74ALS169BN	N	PDIP	16	25	506	13.97	11230	4.32
SN74AS169AN	N	PDIP	16	25	506	13.97	11230	4.32
SN74AS169AN	N	PDIP	16	25	506	13.97	11230	4.32

## **NS0016A**



### **PACKAGE OUTLINE**

SOP - 2.00 mm max height

SOP



#### NOTES:

- 1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing
- Per ASME Y14.5M.
  This drawing is subject to change without notice.
  This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm, per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm, per side.



## NS0016A

### **EXAMPLE BOARD LAYOUT**

### SOP - 2.00 mm max height

SOP



NOTES: (continued)

5. Publication IPC-7351 may have alternate designs.

6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



### NS0016A

### **EXAMPLE STENCIL DESIGN**

### SOP - 2.00 mm max height

SOP



NOTES: (continued)

7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

8. Board assembly site may have different recommendations for stencil design.



D (R-PDSO-G16)

PLASTIC SMALL OUTLINE



NOTES: A. All linear dimensions are in inches (millimeters).

- B. This drawing is subject to change without notice.
- Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.006 (0,15) each side.
- Body width does not include interlead flash. Interlead flash shall not exceed 0.017 (0,43) each side.
- E. Reference JEDEC MS-012 variation AC.



#### MECHANICAL DATA

#### PLASTIC SMALL-OUTLINE PACKAGE

#### 0,51 0,35 ⊕0,25⊛ 1,27 8 14 0,15 NOM 5,60 8,20 5,00 7,40 $\bigcirc$ Gage Plane ₽ 0,25 7 1 1,05 0,55 0-10 Δ 0,15 0,05 Seating Plane — 2,00 MAX 0,10PINS \*\* 14 16 20 24 DIM 10,50 10,50 12,90 15,30 A MAX A MIN 9,90 9,90 12,30 14,70 4040062/C 03/03

NOTES: A. All linear dimensions are in millimeters.

NS (R-PDSO-G\*\*)

**14-PINS SHOWN** 

- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.



J (R-GDIP-T\*\*) 14 LEADS SHOWN

CERAMIC DUAL IN-LINE PACKAGE



NOTES: A. All linear dimensions are in inches (millimeters).

- B. This drawing is subject to change without notice.
- C. This package is hermetically sealed with a ceramic lid using glass frit.
- D. Index point is provided on cap for terminal identification only on press ceramic glass frit seal only.
- E. Falls within MIL STD 1835 GDIP1-T14, GDIP1-T16, GDIP1-T18 and GDIP1-T20.

### N (R-PDIP-T\*\*)

PLASTIC DUAL-IN-LINE PACKAGE

16 PINS SHOWN



NOTES:

- A. All linear dimensions are in inches (millimeters).B. This drawing is subject to change without notice.
- Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
- $\triangle$  The 20 pin end lead shoulder width is a vendor option, either half or full width.



#### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2023, Texas Instruments Incorporated