


4 A - 800 V overvoltage protected AC switch





Features

- Triac with overvoltage protection
- Low I_{GT} (<10 mA) or high immunity (I_{GT} < 35 mA) version
- High noise immunity: static dV/dt > 1000 V/µs
- TO-220FPAB insulated package:
 - complies with UL standards (File ref : E81734)
 - insulation voltage: 2000 V_{RMS}
- · Benefits:
 - Enables equipment to meet IEC 61000-4-5
 - High off-state reliability with planar technology
 - Needs no external overvoltage protection
 - Reduces the power passive component count
 - High immunity against fast transients described in IEC 61000-4-4 standards

Applications

- · AC mains static switching in appliance and industrial control systems
- Drive of medium power AC loads such as:
 - Universal drum motor of washing machine
 - Compressor of fridge or air conditioner

Product status link ACST4

Product summary		
I _{T(RMS)}	4 A	
V_{DRM}/V_{RRM}	800 V	
I _{GT} (ACST410)	10 mA	
I _{GT} (ACST435)	35 mA	

Description

The ACST4 series belongs to the ACS / ACST power switch family. This high performance device is suited to home appliances or industrial systems and drives loads up to 4 A.

This ACST4 switch embeds a Triac structure with a high voltage clamping device to absorb the inductive turn-off energy and withstand line transients such as those described in the IEC 61000-4-5 standards. The ACST410 needs a low gate current to be activated ($I_{\rm GT}$ < 10 mA) and still shows a high electrical noise immunity complying with IEC standards such as IEC 61000-4-4 (fast transient burst test).



1 Characteristics

Table 1. Absolute ratings (limiting values)

Symbol	Parameter			Value	Unit
		TO-220FPAB	T _c = 102 °C	4	
I _{T(RMS)}	On-state rms current (full sine wave)	DPAK	T _c = 112 °C	4	Α
		DPAK with 0.5 cm copper	T _{amb} = 60 °C	1	
L	Non repetitive surge peak on-state current	f = 50 Hz	t _p = 20 ms	32	_
I _{TSM}	T _j initial = 25 °C, (full cycle sine wave)	f = 60 Hz	t _p = 16.7 ms	30	Α
I ² t	I ² t for fuse selection	<u>'</u>	t _p = 10 ms	6	A ² s
dl/dt	Critical rate of rise on-state current $I_G = 2 \times I_{GT}$, tr \leq 100 ns		T _j = 125 °C	100	A/µs
V _{PP} ⁽¹⁾	Non repetitive line peak pulse voltage ⁽¹⁾	T _j = 25 °C	2	kV	
P _{G(AV)}	Average gate power dissipation	0.1	W		
P _{GM}	Peak gate power dissipation (t _p = 20 μs)	T _j = 125 °C	10	W	
I _{GM}	Peak gate current (t_p = 20 μ s) T_j = 125 °C				Α
T _{stg}	Storage temperature range	-40 to +150	°C		
Tj	Operating junction temperature range	-40 to +125	°C		
TL	Lead temperature for soldering during 10 s (at 3 mm from	260	°C		
V _{ins}	Insulation rms voltage (60 seconds)		2000	V	

^{1.} according to test described by standard IEC 61000-4-5, see Figure 17 for conditions

Table 2. Electrical characteristics (T_j = 25 °C, unless otherwise specified)

Symbol	Test conditions	Quadrant		Value		Unit
Symbol	iest conditions	Quaurant		ACST410	ACST435	OIIII
I _{GT} ⁽¹⁾	V _{OUT} = 12 V, R _I = 33 Ω	1 - 11 - 111	Max.	10	35	mA
V _{GT}	VOUT = 12 V, NC = 33 12	1-11-111	Max.	1.0	1.1	V
V _{GD}	$V_{OUT} = V_{DRM}$, $R_L = 3.3 \text{ k}\Omega$, $T_j = 125 ^{\circ}\text{C}$ I - II - III			0.	.2	V
IH ⁽²⁾	I _{OUT} = 500 mA			20	25	mA
IL	I _G = 1.2 x I _{GT}	1 - 11 - 111	Max.	40	60	mA
dV/dt ⁽²⁾	V _{OUT} = 67% V _{DRM} , gate open, T _j = 125 °C			500	1000	V/µs
(dl/dt)c ⁽²⁾	Without snubber, T _j = 125 °C				5	A/ms
(dl/dt)c ⁽²⁾	(dV/dt)c = 15 V/µs, T _j = 125 °C			2		A/ms
V _{CL}	$I_{CL} = 0.1 \text{ mA}, t_p = 1 \text{ ms}$			85	50	V

^{1.} Minimum I_{GT} is guaranteed at 5% of I_{GT} max

DS2762 - Rev 12 page 2/16

^{2.} For both polarities of OUT pin referenced to COM pin



Table 3. Static characteristics

Symbol	Test condition	Test conditions			Unit
V _{TM} ⁽¹⁾	I_{OUT} = 5.6 A, t_p = 500 μ s	T _j = 25 °C	Max.	1.7	V
V _{T0} ⁽¹⁾	Threshold voltage	T _j = 125 °C	Max.	0.9	V
R _D ⁽¹⁾	Dynamic resistance	T _j = 125 °C	Max.	110	mΩ
I _{DRM}	V _{OUT} = V _{DRM} / V _{RRM}	T _j = 25 °C	Max.	20	μA
I _{RRM}	VOUI - VDRM/ VRRM	T _j = 125 °C	IVIAX.	0.5	mA

^{1.} For both polarities of OUT pin referenced to COM pin

Table 4. Thermal characteristics

Symbol	Parameter			Unit
D	Junction to case for full cycle sine wave conduction	DPAK	2.6	
R _{th(j-c)}	Junicilon to case for full cycle sine wave conduction	TO-220FPAB	4.6	0000
В	Junction to ambient	TO-220FPAB	60	°C/W
R _{th(j-a)}	Junction to ambient, S _{CU} = 0.5 cm ² (1)	DPAK	70	

^{1.} $S_{CU} = copper surface under tab$

DS2762 - Rev 12 page 3/16



1.1 Characteristics (curves)

Figure 1. Maximum power dissipation versus RMS onstate current




Figure 2. On-state RMS current versus case temperature (full cycle)




Figure 3. On-state RMS current versus ambient temperature (free air convection, full cycle)




Figure 4. Relative variation of thermal impedance junction to case versus pulse duration




Figure 5. Relative variation of gate trigger current and gate trigger voltage versus junction temperature (typical values)





Figure 6. Relative variation of holding current and latching current versus junction temperature (typical values)



DS2762 - Rev 12 page 4/16



Figure 7. Surge peak on-state current versus number of cycles




Figure 8. Non repetitive surge peak on-state current for a sinusoidal pulse width




Figure 9. On-state characteristics (maximum values)




Figure 10. Relative variation of critical rate of decrease of main current (dl/dt)c versus junction temperature




Figure 11. Relative variation of static dV/dt immunity versus junction temperature (gate open)





Figure 12. Relative variation of Leakage current versus junction temperature



DS2762 - Rev 12 page 5/16



Figure 13. Relative variation of the clamping voltage versus junction temperature (minimum values)





Figure 14. Thermal resistance junction to ambient versus copper surface under tab (typical values)



DS2762 - Rev 12 page 6/16

Start switch


≷ Rg



Application information


2.1 Typical application descriptions


The ACST4 device has been designed to control medium power load, such as AC motors in home appliances. Thanks to its thermal and turn off commutation performances, the ACST4 switch is able to drive an inductive load up to 4 A with no turn off additional snubber. It also provides high thermal performances in static and transient modes such as the compressor inrush current or high torque operating conditions of an AC motor. Thanks to its low gate triggering current level, the ACST4 can be driven directly by an MCU through a simple gate resistor as shown Figure 15 and Figure 16.



Compressor with integrated e-starter

Figure 15. Compressor control - typical diagrams





DS2762 - Rev 12 page 7/16






Figure 16. Universal drum motor control – typical diagram

DS2762 - Rev 12 page 8/16



2.2 AC line transient voltage ruggedness

In comparison with standard Triacs, which are not robust against surge voltage, the ACST4 is self-protected against over-voltage, specified by the new parameter V_{CL} . The ACST4 switch can safely withstand AC line transient voltages either by clamping the low energy spikes, such as inductive spikes at switch off, or by switching to the on state (for less than 10 ms) to dissipate higher energy shocks through the load. This safety feature works even with high turn-on current ramp up.

The test circuit of represents the ACST4 application, and is used to stress the ACST switch according to the IEC 61000-4-5 standard conditions. With the additional effect of the load which is limiting the current, the ACST switch withstands the voltage spikes up to 2 kV on top of the peak line voltage. The protection is based on an overvoltage crowbar technology. The ACST4 folds back safely to the on state as shown in . The ACST4 recovers its blocking voltage capability after the surge and the next zero current crossing.

Such a non repetitive test can be done at least 10 times on each AC line voltage polarity.

Figure 17. Overvoltage ruggedness test circuit for resistive and inductive loads for IEC 61000-4-5 standards





Figure 18. Typical voltage and current waveforms across the ACST4 during IEC 61000-4-5 standard test



DS2762 - Rev 12 page 9/16



3 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.

3.1 TO-220FPAB package information

- Epoxy meets UL94, V0
- Recommended torque: 0.4 to 0.6 N·m

Dia L6 L2 *L7* L3 L4 F2

Figure 19. TO-220FPAB package outline

DS2762 - Rev 12 page 10/16



Table 5. TO-220FPAB package mechanical data

	Dimensions					
Ref.	Millim	Millimeters		nes		
	Min.	Max.	Min.	Max.		
А	4.40	4.60	0.1739	0.1818		
В	2.5	2.7	0.0988	0.1067		
D	2.50	2.75	0.0988	0.1087		
E	0.45	0.70	0.0178	0.0277		
F	0.75	1.0	0.0296	0.0395		
F1	1.15	1.70	0.0455	0.0672		
F2	1.15	1.70	0.0455	0.0672		
G	4.95	5.20	0.1957	0.2055		
G1	2.40	2.70	0.0949	0.1067		
Н	10.00	10.40	0.3953	0.4111		
L2	16.00	typ.	0.6324 typ.			
L3	28.60	30.60	1.1304	1.2095		
L4	9.80	10.6	0.3874	0.4190		
L5	2.90	3.60	0.1146	0.1423		
L6	15.90	16.40	0.6285	0.6482		
L7	9.00	9.30	0.3557	0.3676		
Dia	3.0	3.20	0.1186	0.1265		


DS2762 - Rev 12 page 11/16



3.2 DPAK package information

- Molding compouned resin is halogen free and meets UL94 flammability standard, level V0
- · Lead-free package leads plating

Figure 20. DPAK package outline



DS2762 - Rev 12 page 12/16



	Dimensions						
Ref.		Millimeters			Inches ⁽¹⁾		
	Min.	Тур.	Max.	Min.	Тур.	Max.	
А	2.18		2.40	0.0858		0.0945	
A1	0.90		1.10	0.0354		0.0433	
A2	0.03		0.23	0.0012		0.0091	
b	0.64		0.90	0.0252		0.354	
b4	4.95		5.46	0.1949		0.2150	
С	0.46		0.61	0.0181		0.0240	
c2	0.46		0.60	0.0181		0.0236	
D	5.97		6.22	0.2350		0.2449	
D1	4.95		5.60	0.1949		0.2205	
E	6.35		6.73	0.2500		0.2650	
E1	4.32		5.50	0.1701		0.2165	
е		2.286			0.0900		
e1	4.40		4.70	0.1732		0.1850	
Н	9.35		10.40	0.3681		0.4094	
L	1.00		1.78	0.0394		0.0701	
L2			1.27			0.0500	
L4	0.60		1.02	0.0236		0.0402	
V2 ⁽²⁾	-8°		+8°	-8°		+8°	

Table 6. DPAK package mechanical data

- 1. Dimensions in inches are given for reference only
- 2. Degree

Note:

This package drawing may slightly differ from the physical package. However, all the specified dimensions are guaranteed.




Figure 21. DPAK recommended footprint (dimensions are in mm)

The device must be positioned within $\bigcirc 0.05 \ | A|B$

DS2762 - Rev 12 page 13/16



4 Ordering information

Figure 22. Ordering information scheme




Table 7. Ordering information

Order code	Marking	Package	Weight	Base qty.	Packing mode
ACST410-8B	ACST4108	DPAK	1.5 g	50	Tube
ACST410-8BTR		DPAK		2500	Tape and reel
ACST410-8FP		TO-220FPAB	2.4 g	50	Tube
ACST435-8B		DPAK	150	50	Tube
ACST435-8BTR	ACST4358	DPAK	1.5 g	2500	Tape and reel
ACST435-8FP		TO-220FPAB	2.4 g	50	Tube

DS2762 - Rev 12 page 14/16



Revision history

Table 8. Document revision history

Date	Version	Changes
Jan-2003	3A	Previous update.
04-Jul-2007	4	Reformatted to current standard. Added package.
18-Dec-2009	5	V _{DRM} /V _{RRM} updated to 800 V. Order codes updated.
02-Jun-2014	6	Updated DPAK package information and reformatted to current standard.
21-Oct-2014	7	Updated Table 2, Table 3, Table 4, Features and Description.
18-May-2017	8	Updated Features in cover page, Table 2 and Figure 14.
19-Dec-2019	9	Update DPAK package information.
03-Sep-2020	10	Updated Table 7. Ordering information .
12-May-2021	11	Updated Features.
03-Aug-2021	12	Updated Table 7.

DS2762 - Rev 12 page 15/16



IMPORTANT NOTICE - PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2021 STMicroelectronics - All rights reserved

DS2762 - Rev 12 page 16/16