

# MIC5800/1

# 4/8-Bit Parallel-Input Latched Drivers

#### **Features**

- · 4.4 MHz Minimum Data Input Rate
- · High-Voltage, High-Current Sink Outputs
- · Output Transient Protection
- CMOS, PMOS, NMOS, and TTL Compatible Inputs
- · Internal Pull-Down Resistors
- · Low-Power CMOS Latches


### **General Description**

The MIC5800 and MIC5801 latched drivers are high-voltage, high-current integrated circuits comprised of four or eight CMOS data latches, a bipolar Darlington transistor driver for each latch, and CMOS control circuitry for the common CLEAR, STROBE, and OUTPUT ENABLE functions.


The bipolar/MOS combination provides an extremely low-power latch with maximum interface flexibility. MIC5800 contains four latched drivers; MIC5801 contains eight latched drivers.

Data input rates are greatly improved in these devices. With a 5V supply, they will typically operate at better than 5 MHz. With a 12V supply, significantly higher speeds are obtained. The CMOS inputs are compatible with standard CMOS, PMOS, and NMOS circuits. TTL or DTL circuits may require the use of appropriate pull-up resistors. The bipolar outputs are suitable for use with relays, solenoids, stepping motors, LED or incandescent displays, and other high-power loads. Both units have open-collector outputs and integral diodes for inductive load transient suppression. The output transistors are capable of sinking 500 mA and will sustain at least 50V in the OFF state. Because of limitations on package power dissipation, the simultaneous operation of all drivers at maximum rated current can only be accomplished by a reduction in duty cycle. Outputs may be connected in parallel for higher load current capability.


## **Package Types**



# **Typical Application Circuit**



## **Functional Block Diagram**



### 1.0 ELECTRICAL CHARACTERISTICS

## **Absolute Maximum Ratings †**

Output Voltage (V <sub>CF</sub> )	+50V
Supply Voltage (V <sub>DD</sub> )	+15V
Input Voltage Range (V <sub>IN</sub> )	
Continuous Collector Current (I <sub>C</sub> )	
ESD Rating (Note 1)	

## **Operating Ratings ††**

**Note 1:** Microchip CMOS devices have input-static protection, but are susceptible to damage when exposed to extremely high static electrical charges.

### **ELECTRICAL CHARACTERISTICS**

<b>Electrical Characteristics:</b> V <sub>DD</sub> = 5V, T <sub>A</sub> = +25°C, V <sub>A</sub> ≤ +85°C unless otherwise noted. Note 1							
Parameter	Sym.	Min.	Тур.	Max.	Units	Conditions	
Output Laskana Cumant		1	_	50		V <sub>CE</sub> = 50V, T <sub>A</sub> = +25°C	
Output Leakage Current	I <sub>CEX</sub>	1	_	100	μA	V <sub>CE</sub> = 50V, T <sub>A</sub> = +70°C	
		1	0.9	1.1		I <sub>C</sub> = 100 mA	
Collector-Emitter Saturation Voltage	V <sub>CE(SAT)</sub>	1	1.1	1.3	V	I <sub>C</sub> = 200 mA	
Saturation voltage		1	1.3	1.6		I <sub>C</sub> = 350 mA, V <sub>DD</sub> = 7.0V	
Input Voltage (Low)	V <sub>IN(0)</sub>	1	_	1.0	V	_	
	V <sub>IN(1)</sub>	10.5	_	_	V	V <sub>DD</sub> = 12V	
Input Voltage (High)		8.5	_	_		V <sub>DD</sub> = 10V	
		3.5		-		V <sub>DD</sub> = 5V, Note 2	
		50	200	_		V <sub>DD</sub> = 12V	
Input Resistance	R <sub>IN</sub>	50	300	-	kΩ	V <sub>DD</sub> = 10V	
		50	600	-		V <sub>DD</sub> = 5V	
			1.0	2.0		V <sub>DD</sub> = 12V, Outputs Open	
Supply Current ON (Each Stage)	I <sub>DD(ON)</sub>	1	0.9	1.7	mA	V <sub>DD</sub> = 10V, Outputs Open	
- Clago,			0.7	1.0		V <sub>DD</sub> = 5V, Outputs Open	
Supply Current OFF				200		V <sub>DD</sub> = 12V, Outputs Open, Inputs = 0V	
(Total)	IDD(OFF)	1	50	100	μA	V <sub>DD</sub> = 5V, Outputs Open, Inputs = 0V	

Note 1: Specification for packaged product only.

<sup>†</sup> Notice: Exceeding the absolute maximum ratings may damage the device.

**<sup>††</sup> Notice:** The device is not guaranteed to function outside its operating ratings.

<sup>2:</sup> Operation of these devices with standard TTL or DTL may require the use of appropriate pull-up resistors to ensure a minimum logic "1".

## **ELECTRICAL CHARACTERISTICS (CONTINUED)**

<b>Electrical Characteristics:</b> V <sub>DD</sub> = 5V, T <sub>A</sub> = +25°C, V <sub>A</sub> ≤ +85°C unless otherwise noted. Note 1									
Parameter Sym. Min. Typ. Max. Units Conditions									
Clamp Diode Leakage		_	_	50		V <sub>R</sub> = 50V, T <sub>A</sub> = +25°C			
Current	<sup>I</sup> R	_	_	100	μA	V <sub>R</sub> = 50V, T <sub>A</sub> = +70°C			
Clamp Diode Forward Voltage	V <sub>F</sub>		1.7 2.0 V I <sub>F</sub> = 350 mA		I <sub>F</sub> = 350 mA				

- Note 1: Specification for packaged product only.
  - 2: Operation of these devices with standard TTL or DTL may require the use of appropriate pull-up resistors to ensure a minimum logic "1".

#### TRUTH TABLE

INI	Cémaha	Class	/OE	OUT <sub>N</sub>		
IN <sub>N</sub>	Strobe	Clear	/OE	t – 1	t	
0	1	0	0	Х	OFF	
1	1	0	0	X	ON	
Х	Х	1	X	X	OFF	
Х	X	X	1	X	OFF	
X	0	0	0	ON	ON	
Х	0	0	0	OFF	OFF	

**Legend:** X = Irrelevant; t - 1 = Previous output state; t = Present output state.

Information present at an input is transferred to its latch when the STROBE is high. A high CLEAR input will set all latches to the output OFF condition regardless of the data or STROBE input levels. A high /OE will set all outputs to the off condition, regardless of any other input conditions. When the /OE is low, the outputs depend on the state of their respective latches.

### **TEMPERATURE SPECIFICATIONS**

Parameters	Sym.	Min.	Тур.	Max.	Units	Conditions
Temperature Ranges						
Storage Temperature Range	T <sub>S</sub>	-65	_	+125	°C	_
Operating Temperature Range	T <sub>A</sub>	-40		+85	°C	_

Note 1: The maximum allowable power dissipation is a function of ambient temperature, the maximum allowable junction temperature and the thermal resistance from junction to air (i.e., T<sub>A</sub>, T<sub>J</sub>, θ<sub>JA</sub>). Exceeding the maximum allowable power dissipation will cause the device operating junction temperature to exceed the maximum +125°C rating. Sustained junction temperatures above +125°C can impact the device reliability.

## 2.0 PIN DESCRIPTIONS

The descriptions of the pins are listed in Table 2-1 and Table 2-2.

TABLE 2-1: MIC5800 PIN FUNCTION TABLE

Pin Number	Pin Name	Description					
1	CLEAR	Resets all latches and turns all outputs OFF (open).					
2	STROBE	nput strobe pin. Loads output latches when high.					
3, 4, 5, 6	IN <sub>N</sub>	Parallel inputs, 1 through 4.					
7	GND	Logic and Output Ground pin.					
8	COM	Transient suppression diode common cathode pin.					
9, 10, 11, 12	OUT <sub>N</sub>	Parallel outputs, 4 through 1.					
13	VDD	Logic Supply Voltage.					
14	/OE	Output Enable. When low, outputs are active. When high, outputs are inactive and device is reset from a fault condition. An undervoltage condition emulates a high OE input.					

TABLE 2-2: MIC5801 PIN FUNCTION TABLE

Pin Number SOIC	Pin Number PLCC	Pin Name	Description			
1	28	/OE	Output Enable. When low, outputs are active. When high, outputs are inactive and device is reset from a fault condition. An undervoltage condition emulates a high OE input.			
2	1	CLEAR	Resets all latches and turns all outputs OFF (open).			
3	3	STROBE	Input strobe pin. Loads output latches when high.			
4, 5, 6, 7, 8, 9, 10, 11	5, 6, 7, 8, 9, 10, 11, 12	IN <sub>N</sub>	Parallel inputs, 1 through 8.			
12	15	GND	Logic and Output Ground pin.			
13	17	COM	Transient suppression diode common cathode pin.			
14, 23	2, 4, 13, 14, 16, 26	NC	No Connection. Leave floating.			
15, 16, 17, 18, 19, 20, 21, 22	18, 19, 20, 21, 22, 23, 24, 25	OUT <sub>N</sub>	Parallel outputs, 8 through 1.			
24	27	VDD	Logic Supply Voltage.			




FIGURE 2-1: Typical Input.

## 3.0 TIMING




FIGURE 3-1: Timing Diagram.

TABLE 3-1: TIMING CONDITIONS

<b>Characteristics:</b> $T_A = +25$ °C; Logic levels are $V_{DD}$ and Ground; $V_{DD} = 5V$ .						
Condition	Min.	Тур.	Max.			
A. Minimum data active time before strobe enabled (data set-up time)	50 ns	_	_			
B. Minimum data active time after strobe disabled (data hold time)	50 ns	_	_			
C. Minimum strobe pulse width	125 ns	_	_			
D. Typical time between strobe activation and output on to off transition	_	500 ns	_			
E. Typical time between strobe activation and output off to on transition	_	500 ns	_			
F. Minimum clear pulse width	300 ns	_	_			
G. Minimum data pulse width	225 ns	_	_			

## 4.0 TYPICAL APPLICATIONS




FIGURE 4-1: MIC5800 Unipolar Stepper-Motor Drive.




FIGURE 4-2: Unipolar Wave Drive.




FIGURE 4-3: Unipolar 2-Phase Drive.




FIGURE 4-4: MIC5801 Relay Driver.





FIGURE 4-5: MIC5800 Incandescent/Halogen Lamp Driver.

## 5.0 PACKAGING INFORMATION

## 5.1 Package Marking Information



Legend: XX...X Product code or customer-specific information Year code (last digit of calendar year) Υ ΥY Year code (last 2 digits of calendar year) WW Week code (week of January 1 is week '01') NNN Alphanumeric traceability code Pb-free JEDEC® designator for Matte Tin (Sn) (e3) This package is Pb-free. The Pb-free JEDEC designator (@3) can be found on the outer packaging for this package. •, ▲, ▼ Pin one index is identified by a dot, delta up, or delta down (triangle mark). Note:

e: In the event the full Microchip part number cannot be marked on one line, it will be carried over to the next line, thus limiting the number of available characters for customer-specific information. Package may or may not include the corporate logo.


Underbar (\_) and/or Overbar (¯) symbol may not be to scale.

**Note:** If the full seven-character YYWWNNN code cannot fit on the package, the following truncated codes are used based on the available marking space:

6 Characters = YWWNNN; 5 Characters = WWNNN; 4 Characters = WNNN; 3 Characters = NNN;


2 Characters = NN; 1 Character = N

## 14-Lead Plastic Small Outline SOIC Package Outline and Recommended Land Pattern



# 14-Lead Plastic Small Outline (D3X, UEB, M5B, UEB) - Narrow, 3.90 mm Body [SOIC] Atmel Legacy Global Package Code SVQ

**lote:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	MILLIMETERS			
Dimension	Limits	MIN	NOM	MAX
Number of Pins	N		14	
Pitch	е		1.27 BSC	
Overall Height	Α	-	-	1.75
Molded Package Thickness	A2	1.25	-	-
Standoff §	A1	0.10	-	0.25
Overall Width	Е		6.00 BSC	
Molded Package Width	E1		3.90 BSC	
Overall Length	D		8.65 BSC	
Chamfer (Optional)	h	0.25	-	0.50
Foot Length	L	0.40	-	1.27
Footprint	L1		1.04 REF	
Lead Angle	Θ	0°	-	-
Foot Angle	φ	0°	-	8°
Lead Thickness	С	0.10	-	0.25
Lead Width	0.31	-	0.51	
Mold Draft Angle Top	α	5°	=	15°
Mold Draft Angle Bottom	β	5°	-	15°


#### Notes:

- 1. Pin 1 visual index feature may vary, but must be located within the hatched area.
- 2. § Significant Characteristic
- Dimension D does not include mold flash, protrusions or gate burrs, which shall not exceed 0.15 mm per end. Dimension E1 does not include interlead flash or protrusion, which shall not exceed 0.25 mm per side.
- 4. Dimensioning and tolerancing per ASME Y14.5M
  - BSC: Basic Dimension. Theoretically exact value shown without tolerances.
  - REF: Reference Dimension, usually without tolerance, for information purposes only.
- 5. Datums A & B to be determined at Datum H.

Microchip Technology Drawing No. C04-065-D3X Rev D Sheet 2 of 2

# 14-Lead Plastic Small Outline (D3X, UEB, M5B, UEB) - Narrow, 3.90 mm Body [SOIC] Atmel Legacy Global Package Code SVQ

**bte:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



## RECOMMENDED LAND PATTERN

	MILLIMETERS			
Dimension	MIN	NOM	MAX	
Contact Pitch	Е		1.27 BSC	
Contact Pad Spacing	С		5.40	
Contact Pad Width (X14)	Х			0.60
Contact Pad Length (X14)	Y			1.55

#### Notes:

1. Dimensioning and tolerancing per ASME Y14.5M


BSC: Basic Dimension. Theoretically exact value shown without tolerances.


Microchip Technology Drawing No. C04-2065-D3X Rev D


# 14-Lead PDIP Package Outline and Recommended Land Pattern


# TITLE 14 LEAD PDIP PACKAGE OUTLINE & RECOMMENDED LAND PATTERN

DRAWING # PDIP-14LD-PL-1 UNIT INCH
LEAD FRAME Copper LEAD FINISH Matte Tin











Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging.

## 28-Lead PLCC Package Outline and Recommended Land Pattern



## 24-Lead SOICW Package Outline and Recommended Land Pattern





NOTES:

## APPENDIX A: REVISION HISTORY

## Revision A (April 2019)

- Converted Micrel document MIC5800/1 to Microchip data sheet template DS20006184A.
- Minor grammatical text changes throughout.

# Revision B (February 2022)

 Corrected the device marking specification in section 5.1 "Package Marking Information".



NOTES:

# PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or delivery, contact your local Microchip representative or sales office.

				Examp	les:	
<b>Device</b> Part No.	<b>X</b> Junction Temp. Range	<u>XX</u> Package	- <u>XX</u> Media Type	a) MIC5	800YM:	MIC5800, –40°C to +85°C Temperature Range, 14-Lead SOIC, 54/Tube
Device:	C	-Bit Parallel-Input, Hig urrent Latched Driver	0,0	b) MIC5	800YM-TR:	MIC5800, –40°C to +85°C Temperature Range, 14-Lead SOIC, 2,500/Reel
		-Bit Parallel-Input, Hig urrent Latched Driver	t Parallel-Input, High-Voltage, High- rent Latched Driver		800YN:	MIC5800, –40°C to +85°C Temperature Range, 14-Lead PDIP, 25/Tube
Junction Temperature Range:	Y = -40°C t	o +85°C, Industrial		d) MIC5	801YV:	MIC5801, –40°C to +85°C Temperature Range, 28-Lead PLCC, 38/Tube
Package:	N = 14-Lead V = 28-Lead	SOIC (MIC5800) PDIP (MIC5800) PLCC (MIC5801)		e) MIC5	801YV-TR:	MIC5801, -40°C to +85°C Temperature Range, 28-Lead PLCC, 750/Reel
	<black>= 54/Tube</black>		1)	f) MIC5	301YWM:	MIC5801, -40°C to +85°C Temperature Range, 24-Lead Wide SOIC, 31/Tube
Media Type:		e (V, MIC5801)		g) MIC5	801YWM-TR:	MIC5801, -40°C to +85°C Temperature Range, 24-Lead Wide SOIC, 1,000/Reel
		eel (M, MIC5800)		Note 1:	catalog part nu used for orderi the device pac	identifier only appears in the imber description. This identifier is ng purposes and is not printed on kage. Check with your Microchip r package availability with the option.



NOTES:

#### Note the following details of the code protection feature on Microchip products:

- Microchip products meet the specifications contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is secure when used in the intended manner, within operating specifications, and under normal conditions.
- Microchip values and aggressively protects its intellectual property rights. Attempts to breach the code protection features of Microchip product is strictly prohibited and may violate the Digital Millennium Copyright Act.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of its code. Code protection does not
  mean that we are guaranteeing the product is "unbreakable". Code protection is constantly evolving. Microchip is committed to
  continuously improving the code protection features of our products.

This publication and the information herein may be used only with Microchip products, including to design, test, and integrate Microchip products with your application. Use of this information in any other manner violates these terms. Information regarding device applications is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. Contact your local Microchip sales office for additional support or, obtain additional support at <a href="https://www.microchip.com/en-us/support/design-help/client-support-services">https://www.microchip.com/en-us/support/design-help/client-support-services</a>.

THIS INFORMATION IS PROVIDED BY MICROCHIP "AS IS". MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTIES OF NON-INFRINGEMENT, MERCHANTABILITY, AND FITNESS FOR A PARTICULAR PURPOSE, OR WARRANTIES RELATED TO ITS CONDITION, QUALITY, OR PERFORMANCE.

IN NO EVENT WILL MICROCHIP BE LIABLE FOR ANY INDIRECT, SPECIAL, PUNITIVE, INCIDENTAL, OR CONSEQUENTIAL LOSS, DAMAGE, COST, OR EXPENSE OF ANY KIND WHATSOEVER RELATED TO THE INFORMATION OR ITS USE, HOWEVER CAUSED, EVEN IF MICROCHIP HAS BEEN ADVISED OF THE POSSIBILITY OR THE DAMAGES ARE FORESEEABLE. TO THE FULLEST EXTENT ALLOWED BY LAW, MICROCHIP'S TOTAL LIABILITY ON ALL CLAIMS IN ANY WAY RELATED TO THE INFORMATION OR ITS USE WILL NOT EXCEED THE AMOUNT OF FEES, IF ANY, THAT YOU HAVE PAID DIRECTLY TO MICROCHIP FOR THE INFORMATION.

Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

For information regarding Microchip's Quality Management Systems, please visit www.microchip.com/quality.

#### **Trademarks**

The Microchip name and logo, the Microchip logo, Adaptec, AnyRate, AVR, AVR logo, AVR Freaks, BesTime, BitCloud, CryptoMemory, CryptoRF, dsPIC, flexPWR, HELDO, IGLOO, JukeBlox, KeeLoq, Kleer, LANCheck, LinkMD, maXStylus, maXTouch, MediaLB, megaAVR, Microsemi, Microsemi logo, MOST, MOST logo, MPLAB, OptoLyzer, PIC, picoPower, PICSTART, PIC32 logo, PolarFire, Prochip Designer, QTouch, SAM-BA, SenGenuity, SpyNIC, SST, SST Logo, SuperFlash, Symmetricom, SyncServer, Tachyon, TimeSource, tinyAVR, UNI/O, Vectron, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

AgileSwitch, APT, ClockWorks, The Embedded Control Solutions Company, EtherSynch, Flashtec, Hyper Speed Control, HyperLight Load, IntelliMOS, Libero, motorBench, mTouch, Powermite 3, Precision Edge, ProASIC, ProASIC Plus, ProASIC Plus logo, Quiet-Wire, SmartFusion, SyncWorld, Temux, TimeCesium, TimeHub, TimePictra, TimeProvider, TrueTime, WinPath, and ZL are registered trademarks of Microchip Technology Incorporated in the LLS A

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, Augmented Switching, BlueSky, BodyCom, CodeGuard, CryptoAuthentication, CryptoAutomotive, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, Espresso T1S, EtherGREEN, GridTime, IdealBridge, In-Circuit Serial Programming, ICSP, INICnet, Intelligent Paralleling, Inter-Chip Connectivity, JitterBlocker, Knob-on-Display, maxCrypto, maxView, memBrain, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MultiTRAK, NetDetach, NVM Express, NVMe, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, PowerSmart, PureSilicon, QMatrix, REAL ICE, Ripple Blocker, RTAX, RTG4, SAM-ICE, Serial Quad I/O, simpleMAP, SimpliPHY, SmartBuffer, SmartHLS, SMART-I.S., storClad, SQI, SuperSwitcher, SuperSwitcher II, Switchtec, SynchroPHY, Total Endurance, TSHARC, USBCheck, VariSense, VectorBlox, VeriPHY, ViewSpan, WiperLock, XpressConnect, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

 $\ensuremath{\mathsf{SQTP}}$  is a service mark of Microchip Technology Incorporated in the U.S.A.

The Adaptec logo, Frequency on Demand, Silicon Storage Technology, Symmcom, and Trusted Time are registered trademarks of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2019 - 2022, Microchip Technology Incorporated and its subsidiaries.

All Rights Reserved.

ISBN: 978-1-5224-9831-5



# **Worldwide Sales and Service**

#### **AMERICAS**

Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200

Tel: 480-792-7200 Fax: 480-792-7277 Technical Support:

http://www.microchip.com/ support

Web Address:

www.microchip.com
Atlanta

Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455

**Austin, TX** Tel: 512-257-3370

Boston

Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL

Tel: 630-285-0071 Fax: 630-285-0075

**Dallas** Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

**Detroit** Novi, MI

Tel: 248-848-4000

Houston, TX Tel: 281-894-5983

Indianapolis Noblesville, IN Tel: 317-773-8323

Tel: 317-773-8323 Fax: 317-773-5453 Tel: 317-536-2380

Los Angeles Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608 Tel: 951-273-7800

**Raleigh, NC** Tel: 919-844-7510

New York, NY Tel: 631-435-6000

**San Jose, CA** Tel: 408-735-9110 Tel: 408-436-4270

**Canada - Toronto** Tel: 905-695-1980 Fax: 905-695-2078

#### ASIA/PACIFIC

Australia - Sydney Tel: 61-2-9868-6733

**China - Beijing** Tel: 86-10-8569-7000

China - Chengdu Tel: 86-28-8665-5511

China - Chongqing Tel: 86-23-8980-9588

**China - Dongguan** Tel: 86-769-8702-9880

China - Guangzhou Tel: 86-20-8755-8029

China - Hangzhou Tel: 86-571-8792-8115

China - Hong Kong SAR Tel: 852-2943-5100

**China - Nanjing** Tel: 86-25-8473-2460

China - Qingdao Tel: 86-532-8502-7355

China - Shanghai Tel: 86-21-3326-8000

**China - Shenyang** Tel: 86-24-2334-2829

**China - Shenzhen** Tel: 86-755-8864-2200

China - Suzhou Tel: 86-186-6233-1526

**China - Wuhan** Tel: 86-27-5980-5300

China - Xian Tel: 86-29-8833-7252

China - Xiamen
Tel: 86-592-2388138

**China - Zhuhai** Tel: 86-756-3210040

#### ASIA/PACIFIC

India - Bangalore Tel: 91-80-3090-4444

India - New Delhi Tel: 91-11-4160-8631

India - Pune Tel: 91-20-4121-0141

**Japan - Osaka** Tel: 81-6-6152-7160

Japan - Tokyo

Tel: 81-3-6880- 3770

**Korea - Daegu** Tel: 82-53-744-4301

Korea - Seoul Tel: 82-2-554-7200

Malaysia - Kuala Lumpur Tel: 60-3-7651-7906

Malaysia - Penang Tel: 60-4-227-8870

Philippines - Manila Tel: 63-2-634-9065

**Singapore** Tel: 65-6334-8870

**Taiwan - Hsin Chu** Tel: 886-3-577-8366

Taiwan - Kaohsiung Tel: 886-7-213-7830

**Taiwan - Taipei** Tel: 886-2-2508-8600

Thailand - Bangkok Tel: 66-2-694-1351

Vietnam - Ho Chi Minh Tel: 84-28-5448-2100

#### **EUROPE**

Austria - Wels Tel: 43-7242-2244-39 Fax: 43-7242-2244-393

**Denmark - Copenhagen** Tel: 45-4485-5910 Fax: 45-4485-2829

Finland - Espoo Tel: 358-9-4520-820

France - Paris
Tel: 33-1-69-53-63-20
Fax: 33-1-69-30-90-79

Germany - Garching Tel: 49-8931-9700

**Germany - Haan** Tel: 49-2129-3766400

Germany - Heilbronn Tel: 49-7131-72400

Germany - Karlsruhe Tel: 49-721-625370

**Germany - Munich** Tel: 49-89-627-144-0 Fax: 49-89-627-144-44

Germany - Rosenheim Tel: 49-8031-354-560

Israel - Ra'anana Tel: 972-9-744-7705

Italy - Milan Tel: 39-0331-742611 Fax: 39-0331-466781

Italy - Padova Tel: 39-049-7625286

**Netherlands - Drunen** Tel: 31-416-690399 Fax: 31-416-690340

Norway - Trondheim Tel: 47-7288-4388

**Poland - Warsaw** Tel: 48-22-3325737

Romania - Bucharest Tel: 40-21-407-87-50

**Spain - Madrid** Tel: 34-91-708-08-90 Fax: 34-91-708-08-91

**Sweden - Gothenberg** Tel: 46-31-704-60-40

Sweden - Stockholm Tel: 46-8-5090-4654

**UK - Wokingham** Tel: 44-118-921-5800 Fax: 44-118-921-5820