


TLC252, TLC252A, TLC252B, TLC252Y, TLC25L2, TLC25L2A, TLC25L2B TLC25L2Y, TLC25M2, TLC25M2A, TLC25M2B, TLC25M2Y LinCMOS™ DUAL OPERATIONAL AMPLIFIERS

SLOS002I – JUNE 1983 – REVISED MARCH 2001

- A-Suffix Versions Offer 5-mV V_{IO}
- B-Suffix Versions Offer 2-mV V_{IO}
- Wide Range of Supply Voltages
1.4 V to 16 V
- True Single-Supply Operation
- Common-Mode Input Voltage Includes the Negative Rail
- Low Noise . . . 30 nV/ $\sqrt{\text{Hz}}$ Typ at $f = 1 \text{ kHz}$
(High-Bias Versions)




symbol (each amplifier)

description

The TLC252, TLC25L2, and TLC25M2 are low-cost, low-power dual operational amplifiers designed to operate with single or dual supplies. These devices utilize the Texas Instruments silicon gate LinCMOS™ process, giving them stable input offset voltages that are available in selected grades of 2, 5, or 10 mV maximum, very high input impedances, and extremely low input offset and bias currents. Because the input common-mode range extends to the negative rail and the power consumption is extremely low, this series is ideally suited for battery-powered or energy-conserving applications. The series offers operation down to a 1.4-V supply, is stable at unity gain, and has excellent noise characteristics.

These devices have internal electrostatic-discharge (ESD) protection circuits that prevent catastrophic failures at voltages up to 2000 V as tested under MIL-STD-883C, Method 3015.1. However, care should be exercised in handling these devices as exposure to ESD may result in a degradation of the device parametric performance.



AVAILABLE OPTIONS

TA	$V_{IO\max}$ AT 25°C	PACKAGED DEVICES			CHIP FORM (Y)
		SMALL OUTLINE (D)	PLASTIC DIP (P)	TSSOP (PW)	
0°C to 70°C	10 mV	TLC252CD	TLC252CP	TLC252CPW	TLC252Y
	5 mV	TLC252ACD	TLC252ACP	TLC252ACPW	—
	2 mV	TLC252BCD	TLC252BCP	TLC252BCPW	—
	10 mV	TLC25L2CD	TLC25L2CP	TLC25L2CPW	TLC25L2Y
	5 mV	TLC25L2ACD	TLC25L2ACP	TLC25L2ACPW	—
	2 mV	TLC25L2BCD	TLC25L2BCP	TLC25L2BCPW	—
	10 mV	TLC25M2CD	TLC25M2CP	—	TLC25M2Y
	5 mV	TLC25M2ACD	TLC25M2ACP	—	—
	2 mV	TLC25M2BCD	TLC25M2BCP	—	—

The D package is available taped and reeled. Add the suffix R to the device type (e.g., TLC252CDR). Chips are tested at 25°C.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

LinCMOS is a trademark of Texas Instruments.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

**TEXAS
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

Copyright © 2001, Texas Instruments Incorporated

**TLC252, TLC252A, TLC252B, TLC252Y, TLC25L2, TLC25L2A, TLC25L2B
TLC25L2Y, TLC25M2, TLC25M2A, TLC25M2B, TLC25M2Y**
LinCMOS™ DUAL OPERATIONAL AMPLIFIERS


SLOS002I – JUNE 1983 – REVISED MARCH 2001

description (continued)

Because of the extremely high input impedance and low input bias and offset currents, applications for the TLC252/25_2 series include many areas that have previously been limited to BIFET and NFET product types. Any circuit using high-impedance elements and requiring small offset errors is a good candidate for cost-effective use of these devices. Many features associated with bipolar technology are available with LinCMOS™ operational amplifiers without the power penalties of traditional bipolar devices. General applications such as transducer interfacing, analog calculations, amplifier blocks, active filters, and signal buffering are all easily designed with the TLC252/25_2 series devices. Remote and inaccessible equipment applications are possible using their low-voltage and low-power capabilities. The TLC252/25_2 series is well suited to solve the difficult problems associated with single-battery and solar-cell-powered applications. This series includes devices that are characterized for the commercial temperature range and are available in 8-pin plastic dip and the small-outline package. The device is also available in chip form.

The TLC252/25_2 series is characterized for operation from 0°C to 70°C.

equivalent schematic (each amplifier)




**TLC252, TLC252A, TLC252B, TLC252Y, TLC25L2, TLC25L2A, TLC25L2B
TLC25L2Y, TLC25M2, TLC25M2A, TLC25M2B, TLC25M2Y**
LinCMOS™ DUAL OPERATIONAL AMPLIFIERS

SLOS002I – JUNE 1983 – REVISED MARCH 2001

TLC252Y, TLC25L2Y, and TLC25M2Y chip information

These chips, properly assembled, display characteristics similar to the TLC252/25_2. Thermal compression or ultrasonic bonding may be used on the doped-aluminum bonding pads. Chips may be mounted with conductive epoxy or a gold-silicon preform.



**TLC252, TLC252A, TLC252B, TLC252Y, TLC25L2, TLC25L2A, TLC25L2B
TLC25L2Y, TLC25M2, TLC25M2A, TLC25M2B, TLC25M2Y
LinCMOS™ DUAL OPERATIONAL AMPLIFIERS**

SLOS002I – JUNE 1983 – REVISED MARCH 2001

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)†

Supply voltage, V_{DD} (see Note 1)	18 V
Differential input voltage, V_{ID} (see Note 2)	± 18 V
Input voltage range, V_I (any input)	-0.3 V to 18 V
Duration of short circuit at (or below) 25°C free-air temperature (see Note 3)	unlimited
Continuous total dissipation	See Dissipation Rating Table
Operating free-air temperature range, T_A	0°C to 70°C
Storage temperature range	-65°C to 150°C
Lead temperature 1,6 mm (1/16 inch) from case for 10 seconds	260°C

† Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

NOTES: 1. All voltage values, except differential voltages, are with respect to V_{DD-}/GND .

2. Differential voltages are at IN+, with respect to IN-.

3. The output may be shorted to either supply. Temperature and/or supply voltages must be limited to ensure the maximum dissipation rating is not exceeded.

DISSIPATION RATING TABLE

PACKAGE	$T_A \leq 25^\circ\text{C}$ POWER RATING	DERATING FACTOR ABOVE $T_A = 25^\circ\text{C}$	$T_A = 70^\circ\text{C}$ POWER RATING
D	725 mW	5.8 mW/ $^\circ\text{C}$	464 mW
P	1000 mW	8.0 mW/ $^\circ\text{C}$	640 mW
PW	525 mW	4.2 mW/ $^\circ\text{C}$	336 mW

recommended operating conditions

		MIN	MAX	UNIT
Supply voltage, V_{DD}		1.4	16	V
Common-mode input voltage, V_{IC}	$V_{DD} = 1.4$ V	0	0.2	V
	$V_{DD} = 5$ V	-0.2	4	
	$V_{DD} = 10$ V	-0.2	9	
	$V_{DD} = 16$ V	-0.2	14	
Operating free-air temperature, T_A		0	70	°C



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

**TLC252, TLC252A, TLC252B, TLC252Y, TLC25L2, TLC25L2A, TLC25L2B
TLC25L2Y, TLC25M2, TLC25M2A, TLC25M2B, TLC25M2Y**
LinCMOS™ DUAL OPERATIONAL AMPLIFIERS

SLOS002I – JUNE 1983 – REVISED MARCH 2001

electrical characteristics at specified free-air temperature, $V_{DD} = 1.4$ V (unless otherwise noted)

PARAMETER		TEST CONDITIONS [†]	TLC252_C			TLC25L2_C			TLC25M2_C			UNIT	
			MIN	TYP	MAX	MIN	TYP	MAX	MIN	TYP	MAX		
V_{IO}	Input offset voltage	$V_O = 0.2$ V, $R_S = 50 \Omega$	25°C		10			10			10	mV	
			0°C to 70°C		12			12			12		
			25°C		5			5			5		
	TLC25_2AC		0°C to 70°C		6.5			6.5			6.5		
			25°C		2			2			2		
			0°C to 70°C		3			3			3		
α_{VIO}	Average temperature coefficient of input offset voltage		25°C to 70°C		1			1			1	μV/°C	
I_{IO}	Input offset current	$V_O = 0.2$ V	25°C	1	60	1	60	1	60	1	60	pA	
			0°C to 70°C		300			300			300		
I_{IB}	Input bias current	$V_O = 0.2$ V	25°C	1	60	1	60	1	60	1	60	pA	
			0°C to 70°C		600			600			600		
V_{ICR}	Common-mode input voltage range		25°C	0 to 0.2		0 to 0.2		0 to 0.2				V	
V_{OM}	Peak output voltage swing [‡]	$V_{ID} = 100$ mV	25°C	450	700	450	700	450	700	450	700	mV	
AVD	Large-signal differential voltage amplification	$V_O = 100$ to 300 mV, $R_S = 50 \Omega$	25°C		10			20			20	V/mV	
CMRR	Common-mode rejection ratio	$V_O = 0.2$ V, $V_{IC} = V_{ICR\min}$	25°C	60	77	60	77	60	77	60	77	dB	
I_{DD}	Supply current	$V_O = 0.2$ V, No load	25°C	300	375	25	34	200	250	200	250	μA	

[†]All characteristics are measured under open-loop conditions with zero common-mode input voltage unless otherwise specified. Unless otherwise noted, an output load resistor is connected from the output to ground and has the following value: for low bias $R_L = 1 \text{ M}\Omega$, for medium bias $R_L = 100 \text{ k}\Omega$, and for high bias $R_L = 10 \text{ k}\Omega$.

[‡]The output swings to the potential of V_{DD-}/GND .

operating characteristics, $V_{DD} = 1.4$ V, $T_A = 25^\circ\text{C}$

PARAMETER		TEST CONDITIONS	TLC252_C			TLC25L2_C			TLC25M2_C			UNIT
			MIN	TYP	MAX	MIN	TYP	MAX	MIN	TYP	MAX	
B1	Unity-gain bandwidth	$A_V = 40$ dB, $C_L = 10$ pF, $R_S = 50 \Omega$		12			12			12		kHz
SR	Slew rate at unity gain	See Figure 1		0.1			0.001			0.01		V/μs
	Overshoot factor	See Figure 1		30%			35%			35%		

**TLC252, TLC252A, TLC252B, TLC252Y, TLC25L2, TLC25L2A, TLC25L2B
TLC25L2Y, TLC25M2, TLC25M2A, TLC25M2B, TLC25M2Y
LinCMOS™ DUAL OPERATIONAL AMPLIFIERS**

SLOS002I – JUNE 1983 – REVISED MARCH 2001

electrical characteristics at specified free-air temperature, $V_{DD} = 5$ V (unless otherwise noted)

PARAMETER		TEST CONDITIONS	T_A^\dagger	TLC252C, TLC252AC, TLC252BC			UNIT
				MIN	TYP	MAX	
V_{IO}	Input offset voltage	TLC252C	$V_O = 1.4$ V, $R_S = 50 \Omega$,	25°C	1.1	10	mV
			$V_{IC} = 0$, $R_L = 10 \text{ k}\Omega$	Full range		12	
		TLC252AC	$V_O = 1.4$ V, $R_S = 50 \Omega$,	25°C	0.9	5	
			$V_{IC} = 0$, $R_L = 10 \text{ k}\Omega$	Full range		6.5	
		TLC252BC	$V_O = 1.4$ V, $R_S = 50 \Omega$,	25°C	0.23	2	
			$V_{IC} = 0$, $R_L = 10 \text{ k}\Omega$	Full range		3	
α_{VIO}	Average temperature coefficient of input offset voltage			25°C to 70°C		1.8	$\mu\text{V}/^\circ\text{C}$
I_{IO}	Input offset current (see Note 4)	$V_O = 2.5$ V,	$V_{IC} = 2.5$ V	25°C	0.1	60	pA
				70°C	7	300	
I_{IB}	Input bias current (see Note 4)	$V_O = 2.5$ V,	$V_{IC} = 2.5$ V	25°C	0.6	60	pA
				70°C	40	600	
V_{ICR}	Common-mode input voltage range (see Note 5)			25°C	-0.2	-0.3 to 4	V
					to 4	4.2	
			Full range		-0.2	to 3.5	V
V_{OH}	High-level output voltage	$V_{ID} = 100$ mV,	$R_L = 10 \text{ k}\Omega$	25°C	3.2	3.8	V
				0°C	3	3.8	
				70°C	3	3.8	
V_{OL}	Low-level output voltage	$V_{ID} = -100$ mV,	$I_{OL} = 0$	25°C	0	50	mV
				0°C	0	50	
				70°C	0	50	
A_{VD}	Large-signal differential voltage amplification	$V_O = 0.25$ V to 2 V,	$R_L = 10 \text{ k}\Omega$	25°C	5	23	V/mV
				0°C	4	27	
				70°C	4	20	
$CMRR$	Common-mode rejection ratio	$V_{IC} = V_{ICR\min}$		25°C	65	80	dB
				0°C	60	84	
				70°C	60	85	
k_{SVR}	Supply-voltage rejection ratio ($\Delta V_{DD}/\Delta V_O$)	$V_{DD} = 5$ V to 10 V,	$V_O = 1.4$ V	25°C	65	95	dB
				0°C	60	94	
				70°C	60	96	
I_{DD}	Supply current (two amplifiers)	$V_O = 2.5$ V, No load	$V_{IC} = 2.5$ V,	25°C	1.4	3.2	mA
				0°C	1.6	3.6	
				70°C	1.2	2.6	

† Full range is 0°C to 70°C.

NOTES: 4. The typical values of input bias current and input offset current below 5 pA were determined mathematically.
5. This range also applies to each input individually.



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

**TLC252, TLC252A, TLC252B, TLC252Y, TLC25L2, TLC25L2A, TLC25L2B
TLC25L2Y, TLC25M2, TLC25M2A, TLC25M2B, TLC25M2Y**
LinCMOS™ DUAL OPERATIONAL AMPLIFIERS

SLOS002I – JUNE 1983 – REVISED MARCH 2001

electrical characteristics at specified free-air temperature, $V_{DD} = 10$ V (unless otherwise noted)

PARAMETER		TEST CONDITIONS	T_A^\dagger	TLC252C, TLC252AC, TLC252BC			UNIT
				MIN	TYP	MAX	
V_{IO}	Input offset voltage	TLC252C	$V_O = 1.4$ V, $R_S = 50 \Omega$,	25°C	1.1	10	mV
			$V_{IC} = 0$, $R_L = 10 k\Omega$	Full range		12	
		TLC252AC	$V_O = 1.4$ V, $R_S = 50 \Omega$,	25°C	0.9	5	
			$V_{IC} = 0$, $R_L = 10 k\Omega$	Full range		6.5	
		TLC252BC	$V_O = 1.4$ V, $R_S = 50 \Omega$,	25°C	0.29	2	
			$V_{IC} = 0$, $R_L = 10 k\Omega$	Full range		3	
α_{VIO}	Average temperature coefficient of input offset voltage			25°C to 70°C		2	$\mu V/^\circ C$
I_{IO}	Input offset current (see Note 4)	$V_O = 2.5$ V,	$V_{IC} = 2.5$ V	25°C	0.1	60	pA
				70°C	7	300	
I_{IB}	Input bias current (see Note 4)	$V_O = 2.5$ V,	$V_{IC} = 2.5$ V	25°C	0.6	60	pA
				70°C	50	600	
V_{ICR}	Common-mode input voltage range (see Note 5)			25°C	-0.2 to 9	-0.3 to 9.2	V
				Full range	-0.2 to 8.5		
V_{OH}	High-level output voltage	$V_{ID} = 100$ mV,	$R_L = 10 k\Omega$	25°C	8	8.5	V
				0°C	8	8.5	
				70°C	7.8	8.4	
V_{OL}	Low-level output voltage	$V_{ID} = -100$ mV,	$I_{OL} = 0$	25°C	0	50	mV
				0°C	0	50	
				70°C	0	50	
A_{VD}	Large-signal differential voltage amplification	$V_O = 1$ V to 6 V,	$R_L = 10 k\Omega$	25°C	10	36	V/mV
				0°C	7.5	42	
				70°C	7.5	32	
$CMRR$	Common-mode rejection ratio	$V_{IC} = V_{ICR\min}$		25°C	65	85	dB
				0°C	60	88	
				70°C	60	88	
k_{SVR}	Supply-voltage rejection ratio ($\Delta V_{DD}/\Delta V_{DD}$)	$V_{DD} = 5$ V to 10 V,	$V_O = 1.4$ V	25°C	65	95	dB
				0°C	60	94	
				70°C	60	96	
I_{DD}	Supply current (two amplifiers)	$V_O = 5$ V, No load	$V_{IC} = 5$ V,	25°C	1.9	4	mA
				0°C	2.3	4.4	
				70°C	1.6	3.4	

† Full range is 0°C to 70°C.

NOTES: 4. The typical values of input bias current and input offset current below 5 pA were determined mathematically.
5. This range also applies to each input individually.

**TLC252, TLC252A, TLC252B, TLC252Y, TLC25L2, TLC25L2A, TLC25L2B
TLC25L2Y, TLC25M2, TLC25M2A, TLC25M2B, TLC25M2Y**
LinCMOS™ DUAL OPERATIONAL AMPLIFIERS

SLOS002I – JUNE 1983 – REVISED MARCH 2001

operating characteristics, $V_{DD} = 5 \text{ V}$

PARAMETER	TEST CONDITIONS	T_A	TLC252C, TLC252AC, TLC252BC			UNIT
			MIN	TYP	MAX	
SR Slew rate at unity gain	$R_L = 10 \text{ k}\Omega$, $C_L = 20 \text{ pF}$, See Figure 1	$V_I(\text{PP}) = 1 \text{ V}$	25°C	3.6		$\text{V}/\mu\text{s}$
			0°C	4		
			70°C	3		
			25°C	2.9		
	$V_O = V_{OH}$, See Figure 1	$V_I(\text{PP}) = 2.5 \text{ V}$	0°C	3.1		
			70°C	2.5		
V_n Equivalent input noise voltage	$f = 1 \text{ kHz}$, $R_S = 20 \Omega$,	See Figure 2	25°C	25		$\text{nV}/\sqrt{\text{Hz}}$
B _{OM} Maximum output-swing bandwidth			25°C	320		kHz
$V_O = V_{OH}$, See Figure 1	$C_L = 20 \text{ pF}$, $R_L = 100 \text{ k}\Omega$,	0°C	340			
		70°C	260			
B ₁ Unity-gain bandwidth	$V_I = 10 \text{ mV}$, $C_L = 20 \text{ pF}$, See Figure 3	See Figure 3	25°C	1.7		MHz
			0°C	2		
			70°C	1.3		
ϕ_m Phase margin	$V_I = 10 \text{ mV}$, See Figure 3	$f = B_1$, $C_L = 20 \text{ pF}$,	25°C	46°		
			0°C	47°		
			70°C	43°		

operating characteristics, $V_{DD} = 10 \text{ V}$

PARAMETER	TEST CONDITIONS	T_A	TLC252C, TLC252AC, TLC252BC			UNIT
			MIN	TYP	MAX	
SR Slew rate at unity gain	$R_L = 10 \text{ k}\Omega$, $C_L = 20 \text{ pF}$, See Figure 1	$V_I(\text{PP}) = 1 \text{ V}$	25°C	5.3		$\text{V}/\mu\text{s}$
			0°C	5.9		
			70°C	4.3		
			25°C	4.6		
	$V_O = V_{OH}$, See Figure 1	$V_I(\text{PP}) = 5.5 \text{ V}$	0°C	5.1		
			70°C	3.8		
V_n Equivalent input noise voltage	$f = 1 \text{ kHz}$, $R_S = 20 \Omega$,	See Figure 2	25°C	25		$\text{nV}/\sqrt{\text{Hz}}$
B _{OM} Maximum output-swing bandwidth			25°C	200		kHz
$V_O = V_{OH}$, See Figure 1	$C_L = 20 \text{ pF}$, $R_L = 100 \text{ k}\Omega$,	0°C	220			
		70°C	140			
B ₁ Unity-gain bandwidth	$V_I = 10 \text{ mV}$, $C_L = 20 \text{ pF}$, See Figure 3	See Figure 3	25°C	2.2		MHz
			0°C	2.5		
			70°C	1.8		
ϕ_m Phase margin	$V_I = 10 \text{ mV}$, See Figure 3	$f = B_1$, $C_L = 20 \text{ pF}$,	25°C	49°		
			0°C	50°		
			70°C	46°		



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

**TLC252, TLC252A, TLC252B, TLC252Y, TLC25L2, TLC25L2A, TLC25L2B
TLC25L2Y, TLC25M2, TLC25M2A, TLC25M2B, TLC25M2Y**
LinCMOS™ DUAL OPERATIONAL AMPLIFIERS

SLOS002I – JUNE 1983 – REVISED MARCH 2001

electrical characteristics at specified free-air temperature, $V_{DD} = 5$ V (unless otherwise noted)

PARAMETER		TEST CONDITIONS	T_A^\dagger	TLC25L2C TLC25L2AC TLC25L2BC			UNIT	
				MIN	TYP	MAX		
V_{IO}	Input offset voltage	TLC252C	$V_O = 1.4$ V, $R_S = 50 \Omega$,	$V_{IC} = 0$, $R_L = 1 M\Omega$	25°C	1.1	10	mV
					Full range		12	
		TLC252AC	$V_O = 1.4$ V, $R_S = 50 \Omega$,	$V_{IC} = 0$, $R_L = 1 M\Omega$	25°C	0.9	5	
					Full range		6.5	
		TLC252BC	$V_O = 1.4$ V, $R_S = 50 \Omega$,	$V_{IC} = 0$, $R_L = 1 M\Omega$	25°C	0.204	2	
					Full range		3	
αV_{IO}	Average temperature coefficient of input offset voltage				25°C to 70°C		1.1	$\mu V/^\circ C$
I_{IO}	Input offset current (see Note 4)		$V_O = 2.5$ V,	$V_{IC} = 2.5$ V	25°C	0.1	60	pA
					70°C	7	300	
I_{IB}	Input bias current (see Note 4)		$V_O = 2.5$ V,	$V_{IC} = 2.5$ V	25°C	0.6	60	pA
					70°C	50	600	
V_{ICR}	Common-mode input voltage range (see Note 5)				25°C	-0.2 to 4	-0.3 to 4.2	V
					Full range	-0.2 to 3.5		
V_{OH}	High-level output voltage		$V_{ID} = 100$ mV,	$R_L = 1 M\Omega$	25°C	3.2	4.1	V
					0°C	3	4.1	
					70°C	3	4.2	
V_{OL}	Low-level output voltage		$V_{ID} = -100$ mV,	$I_{OL} = 0$	25°C	0	50	mV
					0°C	0	50	
					70°C	0	50	
AVD	Large-signal differential voltage amplification		$V_O = 0.25$ V to 2 V,	$R_L = 1 M\Omega$	25°C	50	700	V/mV
					0°C	50	700	
					70°C	50	380	
$CMRR$	Common-mode rejection ratio		$V_{IC} = V_{ICR\min}$		25°C	65	94	dB
					0°C	60	95	
					70°C	60	95	
k_{SVR}	Supply-voltage rejection ratio ($\Delta V_{DD}/\Delta V_{DD}$)		$V_{DD} = 5$ V to 10 V,	$V_O = 1.4$ V	25°C	70	97	dB
					0°C	60	97	
					70°C	60	98	
I_{DD}	Supply current (two amplifiers)		$V_O = 2.5$ V, No load	$V_{IC} = 2.5$ V,	25°C	20	34	μA
					0°C	24	42	
					70°C	16	28	

† Full range is 0°C to 70°C.

NOTES: 4. The typical values of input bias current and input offset current below 5 pA were determined mathematically.
5. This range also applies to each input individually.

**TLC252, TLC252A, TLC252B, TLC252Y, TLC25L2, TLC25L2A, TLC25L2B
TLC25L2Y, TLC25M2, TLC25M2A, TLC25M2B, TLC25M2Y**
LinCMOS™ DUAL OPERATIONAL AMPLIFIERS

SLOS002I – JUNE 1983 – REVISED MARCH 2001

electrical characteristics at specified free-air temperature, $V_{DD} = 10$ V (unless otherwise noted)

PARAMETER		TEST CONDITIONS	T_A^\dagger	TLC25L2C TLC25L2AC TLC25L2BC			UNIT		
				MIN	TYP	MAX			
V_{IO}	Input offset voltage	TLC252C	$V_O = 1.4$ V, $R_S = 50 \Omega$,	$V_{IC} = 0$, $R_L = 1 M\Omega$	25°C	1.1	10	mV	
					Full range		12		
		TLC252AC	$V_O = 1.4$ V, $R_S = 50 \Omega$,	$V_{IC} = 0$, $R_L = 1 M\Omega$	25°C	0.9	5		
					Full range		6.5		
		TLC252BC	$V_O = 1.4$ V, $R_S = 50 \Omega$,	$V_{IC} = 0$, $R_L = 1 M\Omega$	25°C	0.235	2		
					Full range		3		
α_{VIO}	Average temperature coefficient of input offset voltage				25°C to 70°C	1	$\mu V/^\circ C$		
I_{IO}	Input offset current (see Note 4)		$V_O = 5$ V,	$V_{IC} = 5$ V	25°C	0.1	60	pA	
					70°C	8	300		
I_{IB}	Input bias current (see Note 4)		$V_O = 5$ V,	$V_{IC} = 5$ V	25°C	0.7	60	pA	
					70°C	50	600		
V_{ICR}	Common-mode input voltage range (see Note 5)			25°C	-0.2	-0.3	V		
					to 9	to 9.2			
				Full range	-0.2	8.5	V		
V_{OH}	High-level output voltage		$V_{ID} = 100$ mV,	$R_L = 1 M\Omega$	25°C	8	8.9	V	
					0°C	7.8	8.9		
					70°C	7.8	8.9		
V_{OL}	Low-level output voltage		$V_{ID} = -100$ mV,	$I_{OL} = 0$	25°C	0	50	mV	
					0°C	0	50		
					70°C	0	50		
A_{VD}	Large-signal differential voltage amplification		$V_O = 1$ V to 6 V,	$R_L = 1 M\Omega$	25°C	50	860	V/mV	
					0°C	50	1025		
					70°C	50	660		
$CMRR$	Common-mode rejection ratio		$V_{IC} = V_{ICRmin}$		25°C	65	97	dB	
					0°C	60	97		
					70°C	60	97		
k_{SVR}	Supply-voltage rejection ratio ($\Delta V_{DD}/\Delta V_{DD}$)		$V_{DD} = 5$ V to 10 V,	$V_O = 1.4$ V	25°C	70	97	dB	
					0°C	60	97		
					70°C	60	98		
I_{DD}	Supply current (two amplifiers)		$V_O = 5$ V, No load	$V_{IC} = 5$ V,	25°C	29	46	μA	
					0°C	36	66		
					70°C	22	40		

† Full range is 0°C to 70°C.

NOTES: 4. The typical values of input bias current and input offset current below 5 pA were determined mathematically.
5. This range also applies to each input individually.



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

**TLC252, TLC252A, TLC252B, TLC252Y, TLC25L2, TLC25L2A, TLC25L2B
TLC25L2Y, TLC25M2, TLC25M2A, TLC25M2B, TLC25M2Y**
LinCMOS™ DUAL OPERATIONAL AMPLIFIERS

SLOS002I – JUNE 1983 – REVISED MARCH 2001

operating characteristics, $V_{DD} = 5\text{ V}$

PARAMETER	TEST CONDITIONS	TA	TLC25L2C			UNIT
			MIN	TYP	MAX	
SR Slew rate at unity gain	$R_L = 1\text{ M}\Omega$, $C_L = 20\text{ pF}$, See Figure 1	$V_I(\text{PP}) = 1\text{ V}$	25°C	0.03		V/ μs
			0°C	0.04		
			70°C	0.03		
			25°C	0.03		
		$V_I(\text{PP}) = 2.5\text{ V}$	0°C	0.03		
			70°C	0.02		
			25°C	68		
			0°C			
BOM Maximum output-swing bandwidth	$V_O = V_{OH}$, $C_L = 20\text{ pF}$, $R_L = 1\text{ M}\Omega$, See Figure	25°C	5			kHz
		0°C	6			
		70°C	4.5			
B ₁ Unity-gain bandwidth	$V_I = 10\text{ mV}$, $C_L = 20\text{ pF}$, See Figure 3	25°C	85			MHz
		0°C	100			
		70°C	65			
ϕ_m Phase margin	$V_I = 10\text{ mV}$, $f = B_1$, See Figure 3	25°C	34°			
		0°C	36°			
		70°C	30°			

operating characteristics, $V_{DD} = 10\text{ V}$

PARAMETER	TEST CONDITIONS	TA	TLC25L2C			UNIT
			MIN	TYP	MAX	
SR Slew rate at unity gain	$R_L = 1\text{ M}\Omega$, $C_L = 20\text{ pF}$, See Figure 1	$V_I(\text{PP}) = 1\text{ V}$	25°C	0.05		V/ μs
			0°C	0.05		
			70°C	0.04		
			25°C	0.04		
		$V_I(\text{PP}) = 5.5\text{ V}$	0°C	0.05		
			70°C	0.04		
			25°C	68		
			0°C			
BOM Maximum output-swing bandwidth	$V_O = V_{OH}$, $C_L = 20\text{ pF}$, $R_L = 1\text{ M}\Omega$, See Figure 1	25°C	1			kHz
		0°C	1.3			
		70°C	0.9			
B ₁ Unity-gain bandwidth	$V_I = 10\text{ mV}$, $C_L = 20\text{ pF}$, See Figure 3	25°C	110			MHz
		0°C	125			
		70°C	90			
ϕ_m Phase margin	$V_I = 10\text{ mV}$, $f = B_1$, See Figure 3	25°C	38°			
		0°C	40°			
		70°C	34°			

**TLC252, TLC252A, TLC252B, TLC252Y, TLC25L2, TLC25L2A, TLC25L2B
TLC25L2Y, TLC25M2, TLC25M2A, TLC25M2B, TLC25M2Y
LinCMOS™ DUAL OPERATIONAL AMPLIFIERS**

SLOS002I – JUNE 1983 – REVISED MARCH 2001

electrical characteristics at specified free-air temperature, $V_{DD} = 5$ V (unless otherwise noted)

PARAMETER		TEST CONDITIONS	T_A^\dagger	TLC25M2C TLC25M2AC TLC25M2BC			UNIT	
				MIN	TYP	MAX		
V_{IO}	Input offset voltage	TLC252C	$V_O = 1.4$ V, $R_S = 50 \Omega$,	$V_{IC} = 0$, $R_L = 100 \text{ k}\Omega$	25°C	1.1	10	mV
					Full range		12	
		TLC252AC	$V_O = 1.4$ V, $R_S = 50 \Omega$,	$V_{IC} = 0$, $R_L = 100 \text{ k}\Omega$	25°C	0.9	5	
					Full range		6.5	
		TLC252BC	$V_O = 1.4$ V, $R_S = 50 \Omega$,	$V_{IC} = 0$, $R_L = 100 \text{ k}\Omega$	25°C	0.22	2	
					Full range		3	
α_{VIO}	Average temperature coefficient of input offset voltage				25°C to 70°C	1.7	$\mu\text{V}/^\circ\text{C}$	
I_{IO}	Input offset current (see Note 4)		$V_O = 2.5$ V,	$V_{IC} = 2.5$ V	25°C	0.1	60	pA
					70°C	7	300	
I_{IB}	Input bias current (see Note 4)		$V_O = 2.5$ V,	$V_{IC} = 2.5$ V	25°C	0.6	60	pA
					70°C	40	600	
V_{ICR}	Common-mode input voltage range (see Note 5)				25°C	-0.2	-0.3	V
						to 4	to 4.2	
					Full range	-0.2	to 3.5	V
V_{OH}	High-level output voltage	$V_{ID} = 100$ mV,	$R_L = 100 \text{ k}\Omega$	25°C	3.2	3.9	V	
				0°C	3	3.9		
				70°C	3	4		
V_{OL}	Low-level output voltage	$V_{ID} = -100$ mV,	$I_{OL} = 0$	25°C	0	50	mV	
				0°C	0	50		
				70°C	0	50		
A_{VD}	Large-signal differential voltage amplification	$V_O = 0.25$ V to 2 V,	$R_L = 100 \text{ k}\Omega$	25°C	25	170	V/mV	
				0°C	15	200		
				70°C	15	140		
$CMRR$	Common-mode rejection ratio	$V_{IC} = V_{ICR\min}$		25°C	65	91	dB	
				0°C	60	91		
				70°C	60	92		
k_{SVR}	Supply-voltage rejection ratio ($\Delta V_{DD}/\Delta V_{DD}$)	$V_{DD} = 5$ V to 10 V,	$V_O = 1.4$ V	25°C	70	93	dB	
				0°C	60	92		
				70°C	60	94		
I_{DD}	Supply current (two amplifiers)	$V_O = 2.5$ V, No load	$V_{IC} = 2.5$ V,	25°C	210	560	μA	
				0°C	250	640		
				70°C	170	440		

† Full range is 0°C to 70°C.

NOTES: 4. The typical values of input bias current and input offset current below 5 pA were determined mathematically.
5. This range also applies to each input individually.



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

**TLC252, TLC252A, TLC252B, TLC252Y, TLC25L2, TLC25L2A, TLC25L2B
TLC25L2Y, TLC25M2, TLC25M2A, TLC25M2B, TLC25M2Y
LinCMOS™ DUAL OPERATIONAL AMPLIFIERS**

SLOS002I – JUNE 1983 – REVISED MARCH 2001

electrical characteristics at specified free-air temperature, $V_{DD} = 10$ V (unless otherwise noted)

PARAMETER		TEST CONDITIONS	T_A^\dagger	TLC25M2C			UNIT
				MIN	TYP	MAX	
V_{IO}	Input offset voltage	TLC252C	$V_O = 1.4$ V, $R_S = 50 \Omega$,	$V_{IC} = 0$,	25°C	1.1	10
				$R_L = 100 \text{ k}\Omega$	Full range		12
		TLC252AC	$V_O = 1.4$ V, $R_S = 50 \Omega$,	$V_{IC} = 0$,	25°C	0.9	5
				$R_L = 100 \text{ k}\Omega$	Full range		6.5
		TLC252BC	$V_O = 1.4$ V, $R_S = 50 \Omega$,	$V_{IC} = 0$,	25°C	0.224	2
				$R_L = 100 \text{ k}\Omega$	Full range		3
αV_{IO}	Average temperature coefficient of input offset voltage				25°C to 70°C	2.1	$\mu\text{V}/^\circ\text{C}$
I_{IO}	Input offset current (see Note 4)		$V_O = 5$ V,	$V_{IC} = 5$ V	25°C	0.1	60
					70°C	7	300
I_{IB}	Input bias current (see Note 4)		$V_O = 5$ V,	$V_{IC} = 5$ V	25°C	0.7	60
					70°C	50	600
V_{ICR}	Common-mode input voltage range (see Note 5)				25°C	-0.2 to 9	-0.3 to 9.2
					Full range	-0.2 to 8.5	-0.3 to 9.2
V_{OH}	High-level output voltage		$V_{ID} = 100 \text{ mV},$	$R_L = 100 \text{ k}\Omega$	25°C	8	8.7
					0°C	7.8	8.7
					70°C	7.8	8.7
V_{OL}	Low-level output voltage		$V_{ID} = -100 \text{ mV},$	$I_{OL} = 0$	25°C	0	50
					0°C	0	50
					70°C	0	50
AVD	Large-signal differential voltage amplification		$V_O = 1 \text{ V to } 6 \text{ V},$	$R_L = 100 \text{ k}\Omega$	25°C	25	275
					0°C	15	320
					70°C	15	230
$CMRR$	Common-mode rejection ratio		$V_{IC} = V_{ICR\min}$		25°C	65	94
					0°C	60	94
					70°C	60	94
k_{SVR}	Supply-voltage rejection ratio ($\Delta V_{DD}/\Delta V_{DD}$)		$V_{DD} = 5 \text{ V to } 10 \text{ V},$	$V_O = 1.4 \text{ V}$	25°C	70	93
					0°C	60	92
					70°C	60	94
I_{DD}	Supply current (two amplifiers)		$V_O = 5 \text{ V},$ No load	$V_{IC} = 5 \text{ V},$	25°C	285	600
					0°C	345	800
					70°C	220	560

† Full range is 0°C to 70°C.

NOTES: 4. The typical values of input bias current and input offset current below 5 pA were determined mathematically.
5. This range also applies to each input individually.

**TLC252, TLC252A, TLC252B, TLC252Y, TLC25L2, TLC25L2A, TLC25L2B
TLC25L2Y, TLC25M2, TLC25M2A, TLC25M2B, TLC25M2Y**
LinCMOS™ DUAL OPERATIONAL AMPLIFIERS

SLOS002I – JUNE 1983 – REVISED MARCH 2001

operating characteristics, $V_{DD} = 5 \text{ V}$

PARAMETER	TEST CONDITIONS	T_A	TLC25M2C TLC25M2AC TLC25M2BC			UNIT
			MIN	TYP	MAX	
SR Slew rate at unity gain	$R_L = 100 \text{ k}\Omega$, $C_L = 20 \text{ pF}$, See Figure 1	$V_I(\text{PP}) = 1 \text{ V}$	25°C	0.43		$\text{V}/\mu\text{s}$
			0°C	0.46		
			70°C	0.36		
			25°C	0.40		
		$V_I(\text{PP}) = 2.5 \text{ V}$	0°C	0.43		
			70°C	0.34		
V_n Equivalent input noise voltage	$f = 1 \text{ kHz}$, $R_S = 20 \Omega$, See Figure 2	25°C	32		$\text{nV}/\sqrt{\text{Hz}}$	
B _{OM} Maximum output-swing bandwidth	$V_O = V_{OH}$, $C_L = 20 \text{ pF}$, $R_L = 100 \text{ k}\Omega$, See Figure	25°C	55		kHz	
		0°C	60			
		70°C	50			
B ₁ Unity-gain bandwidth	$V_I = 10 \text{ mV}$, $C_L = 20 \text{ pF}$, See Figure 3	25°C	525		MHz	
		0°C	600			
		70°C	400			
ϕ_m Phase margin	$V_I = 10 \text{ mV}$, $f = B_1$, $C_L = 20 \text{ pF}$, See Figure 3	25°C	40°			
		0°C	41°			
		70°C	39°			

operating characteristics, $V_{DD} = 10 \text{ V}$

PARAMETER	TEST CONDITIONS	T_A	TLC25M2C TLC25M2AC TLC25M2BC			UNIT
			MIN	TYP	MAX	
SR Slew rate at unity gain	$R_L = 100 \text{ k}\Omega$, $C_L = 20 \text{ pF}$, See Figure 1	$V_I(\text{PP}) = 1 \text{ V}$	25°C	0.62		$\text{V}/\mu\text{s}$
			0°C	0.67		
			70°C	0.51		
		$V_I(\text{PP}) = 5.5 \text{ V}$	25°C	0.56		
			0°C	0.61		
			70°C	0.46		
V_n Equivalent input noise voltage	$f = 1 \text{ kHz}$, $R_S = 20 \Omega$, See Figure 2	25°C	32		$\text{nV}/\sqrt{\text{Hz}}$	
B _{OM} Maximum output-swing bandwidth	$V_O = V_{OH}$, $C_L = 20 \text{ pF}$, $R_L = 100 \text{ k}\Omega$, See Figure 1	25°C	35		kHz	
		0°C	40			
		70°C	30			
B ₁ Unity-gain bandwidth	$V_I = 10 \text{ mV}$, $C_L = 20 \text{ pF}$, See Figure 3	25°C	635		MHz	
		0°C	710			
		70°C	510			
ϕ_m Phase margin	$V_I = 10 \text{ mV}$, $f = B_1$, $C_L = 20 \text{ pF}$, See Figure 3	25°C	43°			
		0°C	44°			
		70°C	42°			

**TLC252, TLC252A, TLC252B, TLC252Y, TLC25L2, TLC25L2A, TLC25L2B
TLC25L2Y, TLC25M2, TLC25M2A, TLC25M2B, TLC25M2Y**
LinCMOS™ DUAL OPERATIONAL AMPLIFIERS

SLOS002I – JUNE 1983 – REVISED MARCH 2001

electrical characteristics, $V_{DD} = 5 \text{ V}$, $T_A = 25^\circ\text{C}$

PARAMETER	TEST CONDITIONS	TLC252Y			TLC25L2Y			TLC25M2Y			UNIT	
		MIN	TYP	MAX	MIN	TYP	MAX	MIN	TYP	MAX		
V_{IO}	$V_O = 1.4 \text{ V}$, $V_{IC} = 0 \text{ V}$, $R_S = 50 \Omega$, See Note 6		1.1	10		1.1	10		1.1	10	mV	
αV_{IO}	Average temperature coefficient of input offset voltage			1.8			1.1			1.7	$\mu\text{V}/^\circ\text{C}$	
I_{IO}	$I_{IO} = V_{DD}/2$, $V_{IC} = V_{DD}/2$		0.1	60		0.1	60		0.1	60	pA	
I_{IB}	$I_{IB} = V_{DD}/2$, $V_{IC} = V_{DD}/2$		0.6	60		0.6	60		0.6	60	pA	
V_{ICR}	Common-mode input voltage range (see Note 5)		-0.2 to 4	-0.3 to 4.2		-0.2 to 4	-0.3 to 4.2		-0.2 to 4	-0.3 to 4.2	V	
V_{OH}	High-level output voltage	$V_{ID} = 100 \text{ mV}$, See Note 6	3.2	3.8		3.2	4.1		3.2	3.9	V	
V_{OL}	Low-level output voltage	$V_{ID} = -100 \text{ mV}$, $I_{OL} = 0$		0	50		0	50		0	50	mV
A_{VD}	Large-signal differential voltage amplification	$V_O = 0.25 \text{ V}$, See Note 6	5	23		50	700		25	170	V/mV	
CMRR	Common-mode rejection ratio	$V_{IC} = V_{ICR\min}$	65	80		65	94		65	91	dB	
k_{SVR}	Supply-voltage rejection ratio ($\Delta V_{DD}/\Delta V_{IO}$)	$V_{DD} = 5 \text{ V}$ to 10 V , $V_O = 1.4 \text{ V}$	65	95		70	97		70	93	dB	
I_{DD}	Supply current	$V_O = V_{DD}/2$, $V_{IC} = V_{DD}/2$, No load		1.4	3.2		0.02	0.034		0.21	0.56	mA

operating characteristics, $V_{DD} = 5 \text{ V}$, $T_A = 25^\circ\text{C}$

PARAMETER	TEST CONDITIONS	TLC252Y			TLC25L2Y			TLC25M2Y			UNIT
		MIN	TYP	MAX	MIN	TYP	MAX	MIN	TYP	MAX	
Slew rate at unity gain	$C_L = 20 \text{ pF}$, See Note 6	$V_I(\text{PP}) = 1 \text{ V}$	3.6		0.03		0.43				$\text{V}/\mu\text{s}$
		$V_I(\text{PP}) = 2.5 \text{ V}$	2.9		0.03		0.40				
V_n	Equivalent input noise voltage	$f = 1 \text{ kHz}$, $R_S = 20 \Omega$		2.5		68		32			$\text{nV}/\sqrt{\text{Hz}}$
B_{OM}	Maximum output-swing bandwidth	$V_O = V_{OH}$, $R_L = 10 \text{ k}\Omega$		320		5		55			kHz
B_1	Unity-gain bandwidth	$V_I = 10 \text{ mV}$, $C_L = 20 \text{ pF}$		1.7		0.085		0.525			MHz
ϕ_m	Phase margin	$f = B_1$, $C_L = 20 \text{ pF}$		46°		34°		40°			

NOTES: 4. The typical values of input bias current and input offset current below 5 pA were determined mathematically.

5. This range also applies to each input individually.

6. For low-bias mode, $R_L = 1 \text{ M}\Omega$; for medium-bias mode, $R_L = 100 \text{ k}\Omega$, and for high-bias mode, $R_L = 10 \text{ k}\Omega$.

**TLC252, TLC252A, TLC252B, TLC252Y, TLC25L2, TLC25L2A, TLC25L2B
TLC25L2Y, TLC25M2, TLC25M2A, TLC25M2B, TLC25M2Y
LinCMOS™ DUAL OPERATIONAL AMPLIFIERS**

SLOS002I – JUNE 1983 – REVISED MARCH 2001

PARAMETER MEASUREMENT INFORMATION

single-supply versus split-supply test circuits

Because the TLC252, TLC25L2, and TLC25M2 are optimized for single-supply operation, circuit configurations used for the various tests often present some inconvenience since the input signal, in many cases, must be offset from ground. This inconvenience can be avoided by testing the device with split supplies and the output load tied to the negative rail. A comparison of single-supply versus split-supply test circuits is shown below. The use of either circuit gives the same result.





Figure 1. Unity-Gain Amplifier





Figure 2. Noise-Test Circuit





Figure 3. Gain-of-100 Inverting Amplifier

**TLC252, TLC252A, TLC252B, TLC252Y, TLC25L2, TLC25L2A, TLC25L2B
TLC25L2Y, TLC25M2, TLC25M2A, TLC25M2B, TLC25M2Y**
LinCMOS™ DUAL OPERATIONAL AMPLIFIERS

SLOS002I – JUNE 1983 – REVISED MARCH 2001

TYPICAL CHARACTERISTICS

Table of Graphs

			FIGURE
I_{DD}	Supply current	vs Supply voltage vs Free-air temperature	4 5
A_{VD}	Large-signal differential voltage amplification	Low bias vs Frequency	6
		Medium bias vs Frequency	7
		High bias vs Frequency	8
	Phase shift	Low bias vs Frequency	6
		Medium bias vs Frequency	7
		High bias vs Frequency	8




Figure 4




Figure 5

**TLC252, TLC252A, TLC252B, TLC252Y, TLC25L2, TLC25L2A, TLC25L2B
TLC25L2Y, TLC25M2, TLC25M2A, TLC25M2B, TLC25M2Y**
LinCMOS™ DUAL OPERATIONAL AMPLIFIERS

SLOS002I – JUNE 1983 – REVISED MARCH 2001

TYPICAL CHARACTERISTICS




Figure 6




Figure 7

**TLC252, TLC252A, TLC252B, TLC252Y, TLC25L2, TLC25L2A, TLC25L2B
TLC25L2Y, TLC25M2, TLC25M2A, TLC25M2B, TLC25M2Y**
LinCMOS™ DUAL OPERATIONAL AMPLIFIERS

SLOS002I – JUNE 1983 – REVISED MARCH 2001

TYPICAL CHARACTERISTICS

**HIGH-BIAS LARGE-SIGNAL
DIFFERENTIAL VOLTAGE AMPLIFICATION
AND PHASE SHIFT**
vs
FREQUENCY




Figure 8

**TLC252, TLC252A, TLC252B, TLC252Y, TLC25L2, TLC25L2A, TLC25L2B
TLC25L2Y, TLC25M2, TLC25M2A, TLC25M2B, TLC25M2Y
LinCMOS™ DUAL OPERATIONAL AMPLIFIERS**

SLOS002I – JUNE 1983 – REVISED MARCH 2001

APPLICATION INFORMATION

latch-up avoidance

Junction-isolated CMOS circuits have an inherent parasitic PNPN structure that can function as an SCR. Under certain conditions, this SCR may be triggered into a low-impedance state, resulting in excessive supply current. To avoid such conditions, no voltage greater than 0.3 V beyond the supply rails should be applied to any pin. In general, the operational amplifier supplies should be applied simultaneously with, or before, application of any input signals.

output stage considerations

The amplifier's output stage consists of a source-follower-connected pullup transistor and an open-drain pulldown transistor. The high-level output voltage (V_{OH}) is virtually independent of the I_{DD} selection and increases with higher values of V_{DD} and reduced output loading. The low-level output voltage (V_{OL}) decreases with reduced output current and higher input common-mode voltage. With no load, V_{OL} is essentially equal to the potential of V_{DD-}/GND .

supply configurations

Even though the TLC252/25_2C series is characterized for single-supply operation, it can be used effectively in a split-supply configuration if the input common-mode voltage (V_{ICR}), output swing (V_{OL} and V_{OH}), and supply voltage limits are not exceeded.

circuit layout precautions

The user is cautioned that whenever extremely high circuit impedances are used, care must be exercised in layout, construction, board cleanliness, and supply filtering to avoid hum and noise pickup, as well as excessive dc leakages.

PACKAGING INFORMATION

Orderable Device	Status ⁽¹⁾	Package Type	Package Drawing	Pins	Package Qty	Eco Plan ⁽²⁾	Lead/Ball Finish	MSL Peak Temp ⁽³⁾
TLC252ACD	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TLC252ACDG4	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TLC252ACP	OBsolete	SOIC	D	8		TBD	Call TI	Call TI
TLC252BCD	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TLC252BCDG4	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TLC252BCP	ACTIVE	PDIP	P	8	50	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type
TLC252BCPE4	ACTIVE	PDIP	P	8	50	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type
TLC252CD	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TLC252CDG4	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TLC252CDR	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TLC252CDRG4	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TLC252CP	ACTIVE	PDIP	P	8	50	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type
TLC252CPE4	ACTIVE	PDIP	P	8	50	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type
TLC252CPWR	ACTIVE	TSSOP	PW	8	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TLC252CPWRG4	ACTIVE	TSSOP	PW	8	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TLC25L2ACD	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TLC25L2ACDG4	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TLC25L2BCD	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TLC25L2BCDG4	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TLC25L2BCDR	PREVIEW	SOIC	D	8		TBD	Call TI	Call TI
TLC25L2BCP	ACTIVE	PDIP	P	8	50	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type
TLC25L2BCPE4	ACTIVE	PDIP	P	8	50	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type
TLC25L2CD	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TLC25L2CDG4	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TLC25L2CDR	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TLC25L2CDRG4	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM

Orderable Device	Status ⁽¹⁾	Package Type	Package Drawing	Pins	Package Qty	Eco Plan ⁽²⁾	Lead/Ball Finish	MSL Peak Temp ⁽³⁾
no Sb/Br)								
TLC25L2CP	ACTIVE	PDIP	P	8	50	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type
TLC25L2CPE4	ACTIVE	PDIP	P	8	50	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type
TLC25L2CPSR	ACTIVE	SO	PS	8	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TLC25L2CPSRG4	ACTIVE	SO	PS	8	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TLC25L2CPWWR	ACTIVE	TSSOP	PW	8	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TLC25L2CPWRG4	ACTIVE	TSSOP	PW	8	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TLC25M2ACD	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TLC25M2ACDG4	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TLC25M2ACP	ACTIVE	PDIP	P	8	50	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type
TLC25M2ACPE4	ACTIVE	PDIP	P	8	50	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type
TLC25M2BCD	OBSOLETE	SOIC	D	8		TBD	Call TI	Call TI
TLC25M2BCP	OBSOLETE	PDIP	P	8		TBD	Call TI	Call TI
TLC25M2CD	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TLC25M2CDG4	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TLC25M2CDR	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TLC25M2CDRG4	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TLC25M2CP	ACTIVE	PDIP	P	8	50	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type
TLC25M2CPE4	ACTIVE	PDIP	P	8	50	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type
TLC25M2CPWLE	OBSOLETE	TSSOP	PW	8		TBD	Call TI	Call TI

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

⁽²⁾ Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check <http://www.ti.com/productcontent> for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

Pb-Free (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

Pb-Free (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)


(³) MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.


In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

TAPE AND REEL INFORMATION

REEL DIMENSIONS




TAPE DIMENSIONS




A_0	Dimension designed to accommodate the component width
B_0	Dimension designed to accommodate the component length
K_0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P_1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A_0 (mm)	B_0 (mm)	K_0 (mm)	P_1 (mm)	W (mm)	Pin1 Quadrant
TLC252CDR	SOIC	D	8	2500	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1
TLC252CDR	SOIC	D	8	2500	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1
TLC252CPWR	TSSOP	PW	8	2000	330.0	12.4	7.0	3.6	1.6	8.0	12.0	Q1
TLC25L2CDR	SOIC	D	8	2500	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1
TLC25L2CPSR	SO	PS	8	2000	330.0	16.4	8.2	6.6	2.5	12.0	16.0	Q1
TLC25L2CPWR	TSSOP	PW	8	2000	330.0	12.4	7.0	3.6	1.6	8.0	12.0	Q1
TLC25M2CDR	SOIC	D	8	2500	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1

TAPE AND REEL BOX DIMENSIONS


*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TLC252CDR	SOIC	D	8	2500	340.5	338.1	20.6
TLC252CDR	SOIC	D	8	2500	346.0	346.0	29.0
TLC252CPWR	TSSOP	PW	8	2000	346.0	346.0	29.0
TLC25L2CDR	SOIC	D	8	2500	340.5	338.1	20.6
TLC25L2CPSR	SO	PS	8	2000	346.0	346.0	33.0
TLC25L2CPWR	TSSOP	PW	8	2000	346.0	346.0	29.0
TLC25M2CDR	SOIC	D	8	2500	340.5	338.1	20.6

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Amplifiers	amplifier.ti.com	Audio	www.ti.com/audio
Data Converters	dataconverter.ti.com	Automotive	www.ti.com/automotive
DLP® Products	www.dlp.com	Communications and Telecom	www.ti.com/communications
DSP	dsp.ti.com	Computers and Peripherals	www.ti.com/computers
Clocks and Timers	www.ti.com/clocks	Consumer Electronics	www.ti.com/consumer-apps
Interface	interface.ti.com	Energy	www.ti.com/energy
Logic	logic.ti.com	Industrial	www.ti.com/industrial
Power Mgmt	power.ti.com	Medical	www.ti.com/medical
Microcontrollers	microcontroller.ti.com	Security	www.ti.com/security
RFID	www.ti-rfid.com	Space, Avionics & Defense	www.ti.com/space-avionics-defense
RF/IF and ZigBee® Solutions	www.ti.com/lprf	Video and Imaging	www.ti.com/video
		Wireless	www.ti.com/wireless-apps