SLVS206B – JULY 1999 – REVISED JUNE 2000

- Fully Integrated xVCC and xVPP Switching
- xVPP Programmed Independent of xVCC
- 3.3-V, 5-V, and/or 12-V Power Distribution
- Low r_{DS(on)} (60-mΩ xVCC Switch Typical)
- Short Circuit and Thermal Protection
- 150-μA (Maximum) Quiescent Current
- Standby Mode: 50-mA Current Limit (Typ)
- 12-V Supply Can Be Disabled
- 3.3-V Low-Voltage Mode
- Meets PC Card[™] Standards
- TTL-Logic Compatible Inputs
- Break-Before-Make Switching
- Internal Power-On Reset

description

(TOP VIEW) 5V 🗖 10 **D** 5V 24 5V 🎞 2 23 DATA T 3 22 CLOCK 4 21 LATCH C 5 20 🗖 12V RESET C 6 D BVPP 19 7 12V 🗖 18 AVPP BVCC 8 17 AVCC 🗖 STBY 9 16 AVCC 🗖 10 15 GND 🗖 3.3V 11 14 RESET 1 3.3V 12 13

DB PACKAGE

 The TPS2214 is identical to the TPS2216 in all respects except packaging and pin assignments.
NC – No internal connection

The TPS2214 PC Card power-interface switch provides an integrated power-management solution for two PC Cards. All of the discrete power MOSFETs, a logic section, current limiting, and thermal protection for PC Card control are combined on a single integrated circuit. This device allows the distribution of 3.3-V, 5-V, and/or 12-V power to the card. The current-limiting feature eliminates the need for fuses. Current-limit reporting can help the user isolate a system fault.

The TPS2214 features a 3.3-V low-voltage mode that allows for 3.3-V switching without the need for 5-V power. This feature facilitates low-power system designs such as sleep modes where only 3.3 V is available. This device also has the ability to program the xVPP outputs independent of the xVCC outputs. A standby mode that changes all output-current limits to 50 mA (typical) has been incorporated.

End-equipment applications for the TPS2214 include: notebook computers, desktop computers, personal digital assistants (PDAs), digital cameras, and bar-code scanners.

	PACKAGED DEVICES [†]						
Тј	PLASTIC SMALL OUTLINE (DB)						
–40°C to 125°C	TPS2214DB(R)						
+							

AVAILABLE OPTIONS

[†]The DB package is available in tubes and left-end taped and reeled. Add R suffix to device type (e.g., TPS2214DBR) for taped and reeled.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

PC Card is a trademark of PCMCIA (Personal Computer Memory Card International Association)

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.



Copyright © 2000, Texas Instruments Incorporated


Terminal Functions

TERMINAL		1/0	DESCRIPTION
NAME	NO.		DESCRIPTION
3.3V	13,14	Ι	3.3-V input for card power and/or chip power if 5 V is not present
5V	1, 2, 24	I	5-V input for card power and/or chip power
12V	7, 20	Ι	12-V V _{pp} input card power
AVCC	9, 10	0	VCC output: 3.3-V, 5-V, GND or high impedance to card
AVPP	8	0	VPP output: 3.3-V, 5-V, 12-V, GND or high impedance to card
BVCC	17, 18	0	VCC output: 3.3-V, 5-V, GND or high impedance to card
BVPP	19	0	VPP output: 3.3-V, 5-V, 12-V, GND or high impedance to card
GND	11		Ground
MODE	22	I	TPS2206 operation when floating or pulled low; must be pulled high externally for TPS2214 operation. MODE is internally pulled low with a 150-k Ω pulldown resistor.
OC	15	0	Logic-level output that goes low when an overcurrent or overtemperature condition exists.
RESET	6	I	Logic-level reset input active high. Do not connect if \overrightarrow{RESET} pin is used. RESET is internally pulled low with a 150-k Ω pulldown resistor.
RESET	12	I	Logic-level reset input active low. Do not connect if RESET pin is used. The pin is internally pulled high with a 150-k Ω pullup resistor.
STBY	16	1	Logic-level active low input sets the TPS2214 to standby mode and sets all current limits to 50 mA. The pin is internally pulled high with a 150-k Ω pullup resistor.
CLOCK	4	1	Logic-level clock for serial data word
DATA	3	Ι	Logic-level serial data word
LATCH	5	Ι	Logic-level latch for serial data word
NC	21, 23		No internal connection



SLVS206B - JULY 1999 - REVISED JUNE 2000

functional block diagram



[†]Both 12V pins must be connected together.



SLVS206B – JULY 1999 – REVISED JUNE 2000

absolute maximum ratings over operating virtual free-air temperature (unless otherwise noted)[†]

Input voltage range for card power: $V_{I(3.3V)}$ $V_{I(5V)}$	–0.3 V to 6 V
V _{I(12V)}	–0.3 V to 14 V
Logic input voltage	–0.3 V to 6 V
Output voltage range: V _{O(xVCC)}	–0.3 V to 6 V
V _{O(xVPP)}	
Continuous total power dissipation	See Dissipation Rating Table
Output current: I _{O(xVCC)}	Internally limited
I _{O(xVPP)}	Internally limited
Operating virtual junction temperature range, T _J	–40°C to 125°C
Storage temperature range, T _{stg}	
Lead temperature 1,6 mm (1/16 inch) from case for 10 seconds	

[†] Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

DISSIPATION RATING TABLE

PACKAGE	$T_A \le 25^{\circ}C$	DERATING FACTOR [‡]	T _A = 70°C	T _A = 85°C
	POWER RATING	ABOVE T _A = 25°C	POWER RATING	POWER RATING
DB	890 mW	8.90 mW/°C	489 mW	356 mW

[‡] These devices are mounted on an JEDEC low-k board (2 oz. traces on surface), 1-W power applied.

recommended operating conditions

		MIN	MAX	UNIT
	V _{I(3.3V)}	2.7	5.25	V
Input voltage, V _I	V _{I(5V)}	2.7	5.25	V
	V _{I(12V)}	2.7	13.5	V
	$I_{O(VCC)}$ at $T_{A} = 70^{\circ}C$		1	А
Output current, IO	$I_{O(VPP)}$ at $T_A = 70^{\circ}C$		200	mA
Clock frequency			2.5	MHz
	Data	200		
Pulse duration	Latch	250		ns
	Clock	100		
Data hold time§		100		ns
Data setup time§		100		ns
Latch delay time§		100		ns
Clock delay time§		250		ns
Operating virtual junc	tion temperature, TJ	-40	125	°C

§ Refer to Figures 2 and 3.



SLVS206B - JULY 1999 - REVISED JUNE 2000

electrical characteristics, $T_J = 25^{\circ}C$, $V_{I(5V)} = 5 V$, $V_{I(3.3V)} = 3.3 V$, $V_{I(12V)} = 12 V$, STBY floating, all outputs unloaded (unless otherwise noted)

power switch

PARAMETER			TEST CONDITI	ONS	MIN	TYP	MAX	UNIT			
			TJ = 25°C,	I _O = 1 A			60	85			
		3.3 V to xVCC, with	n one	T _J = 125°С,	I _O = 1 A			90	120		
		switch on		TJ = 25°C,	$V_{I(5V)} = 0,$	I _O = 1 A		65	85		
				TJ = 125°C,	$V_{I(5V)} = 0,$	I _O = 1 A		90	130		
		5 V to xVCC, with o	one	TJ = 25°C,	I _O = 1 A			60	85		
		switch on		TJ = 125°C,	I _O = 1 A			90	120		
				TJ = 25°C,	I _O = 1 A each			65	105	mΩ	
		3.3 V to xVCC, with	n two	T _J = 125°С,	I _O = 1 A each			95	140		
	Switch	switches on		TJ = 25°C,	$V_{I(5V)} = 0,$	I _O = 1 A each		70	105		
	resistance [†]			TJ = 125°C,	$V_{I(5V)} = 0,$	I _O = 1 A each		100	140		
		5 V to xVCC, with t	WO	TJ = 25°C,	I _O = 1 A each			70	105		
		switches on		T _J = 125°С,	I _O = 1 A each			100	140		
				Тј = 25°С,	I <u>O</u> = 50 mA			0.7	1		
		3.3 V/5 V/12 V to x	VPP	TJ = 125°C,	I _O = 50 mA			1.4	2.5		
				Т _Ј = 25°С,	STBY = low,	I _O = 30 mA		1.4	2		
		3.3 V/5 V to xVCC		T _J = 125°C,	STBY = low,	I _O = 30 mA		2	3	Ω	
		3.3 V/5 V/12 V to xVPP		TJ = 25°C,	$\overline{\text{STBY}} = \text{low},$	I _O = 30 mA		5	7		
				TJ = 125°C,	STBY = low,	I _O = 30 mA		10	16		
	Clamp low	V _{O(xVCC)}		IO(xVCC) at	10 mA, After res	et		0.275	0.8		
	voltage	VO(xVPP)	I _{O(xVPP)} at 10 mA, After reset					0.275	0.8	V	
	IO(xVCC) High-impedance		$T_J = 25^{\circ}C$				1	10			
		state IO(xVPP) High-impedance state		T _J = 125°C T _J = 25°C				2	50		
lkg	Leakage current							1	10	μA	
				TJ = 125°C				2	50		
		IO(xVCC)		T . 05% output noward into a shart to CND		1		2.2	А		
	Short-circuit	IO(xVPP)		$T_J = 85^{\circ}C$, output powered into a short to GND		250		500	mA		
los	output current	Standby mode IO()		Т.J = 85°С,			35	50	65		
	limit [†]	· · · · · · · · · · · · · · · · · · ·		Output powered into a short to GND,						mA	
		Standby mode IO()	(VPP)	STBY = 0 V			30	50	60		
	Current limit	xVCC switch		$100 \text{-m}\Omega$ shor	t circuit			100		μs	
	response time‡	xVPP switch			t on our			16		μο	
			II(3.3V)					0.01	2		
		Normal anaration	ll(5V)	V _{O(xVCC)} =	$V_{O(xVPP)} = 5$	/		100	120	μΑ	
		Normal operation and in reset	l _{l(12V)}					6	10		
		mode	II(3.3V)	$V_{I(5V)} = 0,$				100	120	μA	
I	Input current§		II(5V)	VO(xVCC) =	3.3 V,			0			
			l _{l(12V)}	$V_O(xVPP) = 12 V$				22	30		
			II(3.3V)						1		
		Shutdown mode	I _{I(5V)}	VO(xVCC) =	Hi-Z, VO(xVPF	p ₎ = Hi-Z			1	μA	
		II(12V)							1		
	Thermal	Trip point, T _J						155		°C	
	shutdown‡	Hysteresis]				10		-0	

[†] Pulse-testing techniques maintain junction temperature close to ambient temperature (250-µs-wide pulse, less than 0.5% duty cycle); thermal effects must be taken into account separately.

[‡] Specified by design, not tested in production.

§ Input currents do not include logic input currents (presented in electrical characteristics for logic section); clock is inactive.

NOTE: $V_{I(3.3V)}$ or $V_{I(5V)}$ must be biased for switches to function.



SLVS206B - JULY 1999 - REVISED JUNE 2000

logic section (CLOCK, DATA, LATCH, MODE, RESET, RESET, STBY, OC)

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT		
		$V_{I(RESET)} = 5 V \text{ or } V_{I(RESET)} = 0 V$		30	50			
	II(RESET) or II(RESET)	$V_{I(RESET)} = 0 V \text{ or } V_{I(RESET)} = 5 V$			1			
	have	$V_{I(MODE)} = 5 V$		30	50			
Logic input current	II(MODE) [†]	$V_{I(MODE)} = 0 V$			1	μA		
	1	$V_{I}(\overline{STBY}) = 5 V$			1			
	II(STBY) [†]	$V_{I}(\overline{STBY}) = 0 V$		30	50			
	II(CLOCK) or II(DATA) or II(LATCH)				1			
Logic input high love	1	V _{I(5V)} = 5 V	2			V		
Logic input high leve	1	V _{I(5V)} = 0 V	2			v		
Logic input low level					0.8	V		
Logic output high level, OC		$V_{I(5V)} = 5 V$, $I_{O} = 1 mA$	V _{I(5V)} -0.4			v		
		$V_{I(5V)} = 0 V,$ $I_{O} = 1 mA$	V _{I(3.3V)} -0.4			v		
Logic output low leve	el, OC	$I_{O} = 1 \text{ mA}$			0.4	V		

[†]RESET and MODE have internal 150-k Ω pulldown resistors; RESET and STBY have internal 150-k Ω pullup resistors.



switching characteristics

	PARAMETER [†]	LOAD CONDITION [†]	TEST CONDITION	nst	MIN	TYP	MAX	UNIT	
		$C_{L(xVCC)} = 0.1 \ \mu F,$ $C_{L(xVPP)} = 0.1 \ \mu F,$	VO(xVCC)			1			
÷	Output rise times‡	$I_{O(xVCC)} = 0$ $I_{O(xVPP)} = 0$	VO(xVPP)		0.8				
tr		$C_{L(xVCC)} = 150 \ \mu F,$ $C_{L(xVPP)} = 10 \ \mu F,$	VO(xVCC)			1.2		ms	
		$I_O(xVCC) = 1 A,$ $I_O(xVPP) = 50 mA$	VO(xVPP)			2.5			
		$C_{L(XVCC)} = 0.1 \ \mu\text{F},$ $C_{L(XVPP)} = 0.1 \ \mu\text{F},$	VO(xVCC)			0.01			
ŧf	Output fall times‡	$I_{O(xVCC)} = 0$ $I_{O(xVPP)} = 0$	V _{O(xVPP)}			0.01		ms	
T	Output fair times+	$C_{L(xVCC)} = 150 \ \mu F,$ $C_{L(xVPP)} = 10 \ \mu F,$	VO(xVCC)			3		115	
		$I_{O(xVCC)} = 1 \text{ A},$ $I_{O(xVPP)} = 50 \text{ mA}$	V _O (xVPP)			8			
			Latch↑ to xVPP (12 V)	^t pd(on)		3			
				^t pd(off)		25			
		C _{L(XVCC)} = 0.1 μF,	Latch [↑] to xVPP (5 V)	^t pd(on)		0.6			
				^t pd(off)		8.5			
			Latch [↑] to xVPP (3.3 V),	^t pd(on)		0.6			
			V _{I(5V)} = 5 V	^t pd(off)		9			
		$C_{L(xVPP)} = 0.1 \mu F,$	Latch [↑] to xVPP (3.3 V), $V_{I(5V)} = 0 V$ Latch [↑] to xVCC (5 V) Latch [↑] to xVCC (3.3 V),	^t pd(on)		1.4			
		$I_O(xVCC) = 0$ $I_O(xVPP) = 0$		^t pd(off)		9			
				^t pd(on)		0.3			
				^t pd(off)		15			
				^t pd(on)		0.2			
			V _{I(5V)} = 5 V	^t pd(off)		15			
			Latch [↑] to xVCC (3.3 V),	^t pd(on)		0.4			
1	Propagation delay‡		V _{I(5V)} = 0 V	^t pd(off)		15		ms	
bd	r topagation delay+		Latch [↑] to xVPP (12 V)	^t pd(on)		4.5		1115	
				^t pd(off)		13			
				^t pd(on)		3.3			
			Latch [↑] to xVPP (5 V)	^t pd(off)		8			
			Latch [↑] to xVPP (3.3 V),	^t pd(on)		3			
			$V_{I(5V)} = 5 V$	^t pd(off)		9			
		$C_{L(XVCC)} = 150 \ \mu\text{F},$ $C_{L(XVPP)} = 10 \ \mu\text{F},$	Latch↑ to xVPP (3.3 V),	^t pd(on)		3			
		$I_O(xVCC) = 1 A,$	$V_{I(5V)} = 0 V$	^t pd(off)		9			
		$I_{O(xVPP)} = 50 \text{ mA}$		^t pd(on)		1			
			Latch↑ to xVCC (5 V)	^t pd(off)		12			
			Latch↑ to xVCC (3.3 V),	^t pd(on)		0.6			
			$V_{I(5V)} = 5 V$	^t pd(off)		12			
			Latch [↑] to xVCC (3.3 V),	tpd(on)		1			
			$V_{I(5V)} = 0 V$	^t pd(off)		12			


[†]Refer to Parameter Measurement Information

[‡] Specified by design: not tested in production.


No card inserted, assumes 0.1- μ F recommended output capacitor (see Figure 34).



SLVS206B - JULY 1999 - REVISED JUNE 2000




PARAMETER MEASUREMENT INFORMATION






SLVS206B - JULY 1999 - REVISED JUNE 2000

PARAMETER MEASUREMENT INFORMATION



NOTE: Data is clocked in on the positive edge of the clock. The positive edge of the latch signal should occur before the next positive edge of the clock. For definition of D0 to D10, see the control logic table.

Figure 2. Serial-Interface Timing for Independent xVPP Switching When MODE = 5 V or 3.3 V



NOTE: Data is clocked in on the positive edge of the clock. The positive edge of the latch signal should occur before the next positive edge of the clock. For definition of D0 to D8, see the control logic table.

Figure 3. Serial-Interface Timing When MODE = 0 V or Floating


Table of Timing Diagrams[†]

FIGURE
4
5
6
7
-

[†] Timing tests are conducted at free-air temperature, $V_{I(5V)} = 5 V$, $V_{I(3.3V)} = 3.3 V$, $V_{I(12V)} = 12 V$, $C_L = 0.1 \mu$ F on each output, STBY floating.




SLVS206B - JULY 1999 - REVISED JUNE 2000



PARAMETER MEASUREMENT INFORMATION











Figure 5. Short-Circuit Response, Short Applied to Powered-On 12-V xVPP-Switch Output








TYPICAL CHARACTERISTICS

Table of Graphs

			FIGURE
^t pd(on)	Turnon propagation delay time, 3.3-V xVCC switch	vs Load capacitance	8
^t pd(off)	Turnoff propagation delay time, 3.3-V xVCC switch	vs Load capacitance	9
^t pd(on)	Turnon propagation delay time, 5-V xVCC switch	vs Load capacitance	10
^t pd(off)	Turnoff propagation delay time, 5-V xVCC switch	vs Load capacitance	11
^t pd(on)	Turnon propagation delay time, 12-V xVPP switch	vs Load capacitance	12
^t pd(off)	Turnoff propagation delay time, 12-V xVPP switch	vs Load capacitance	13
t _r	Rise time, 3.3-V xVCC switch	vs Load capacitance	14
t _f	Fall time, 3.3-V xVCC switch	vs Load capacitance	15
t _r	Rise time, 5-V xVCC switch	vs Load capacitance	16
t _f	Fall time, 5-V xVCC switch	vs Load capacitance	17
t _r	Rise time, 12-V xVPP switch	vs Load capacitance	18
t _f	Fall time, 12-V xVPP switch	vs Load capacitance	19
	Input current at V _{O(xVCC)} = V _{O(xVPP)} =3.3 V	vs Junction temperature	20
lj	Input current at V _{O(xVCC)} = V _{O(xVPP)} =5 V	vs Junction temperature	21
	Input current at V _{O(xVCC)} = 5 V, V _{O(xVPP)} =12 V	vs Junction temperature	22
	Static drain-source on-state resistance, 3.3-V xVCC switch ($V_{I(5V)}=0$)	vs Junction temperature	23
pd(off) pd(on) pd(off) pd(off) r f r f r f r f r f r f 'r f 'DS(on)	Static drain-source on-state resistance, 3.3-V xVCC switch	vs Junction temperature	24
	Static drain-source on-state resistance, 5-V xVCC switch	vs Junction temperature	25
	Static drain-source on-state resistance, 12-V xVPP switch	vs Junction temperature	26
	dc input-to-output voltage (drop), 3.3-V xVCC switch (VI(5V)=0)	vs Load current	27
VIO(xVCC)	dc input-to-output voltage (drop), 3.3-V xVCC switch	vs Load current	28
	dc input-to-output voltage (drop), 5-V xVCC switch	vs Load current	29
VIO(xVPP)	dc input-to-output voltage (drop), 12-V xVPP switch	vs Load current	30
	Short-circuit current limit, 3.3-V xVCC switch	vs Junction temperature	31
los	Short-circuit current limit, 5-V xVCC switch	vs Junction temperature	32
	Short-circuit current limit, 12-V xVPP switch	vs Junction temperature	33


NOTE: Electrical characteristics tests are conducted at V_{I(5V)} = 5 V, V_{I(3.3V)} = 3.3 V, V_{I(12V)} = 12 V, C_L = 0.1 μF on each output, STBY floating (unless otherwise noted on Figures).








SLVS206B - JULY 1999 - REVISED JUNE 2000











SLVS206B – JULY 1999 – REVISED JUNE 2000










SLVS206B - JULY 1999 - REVISED JUNE 2000





SHORT-CIRCUIT CURRENT LIMIT, 5-V xVCC SHORT-CIRCUIT CURRENT LIMIT, 12-V xVPP SWITCH SWITCH vs vs JUNCTION TEMPERATURE JUNCTION TEMPERATURE 1.9 0.4 OS – Short-Circuit Current Limit – A l OS – Short-Circuit Current Limit – A 1.85 0.38 1.8 0.36 1.75 0.34 1.7 0.32 1.65 1.6 0.3 -50 0 50 100 150 -50 0 50 100 150 T_J – Junction Temperature – °C Junction Temperature – °C Tj-Figure 32 Figure 33

TYPICAL CHARACTERISTICS

APPLICATION INFORMATION

overview

PC Cards were initially introduced as a means to add EEPROM (flash memory) to portable computers with limited onboard memory. The idea of add-in cards quickly took hold; modems, wireless LANs, Global Positioning Satellite System (GPS), multimedia, and hard-disk versions were soon available. As the number of PC Card applications grew, the engineering community quickly recognized the need for a standard to ensure compatibility across platforms. To this end, the PCMCIA (Personal Computer Memory Card International Association), comprising members from leading computer, software, PC Card, and semiconductor manufacturers, was established. One key goal was to realize the plug-and-play concept. Cards and hosts from different vendors should be compatible or able to communicate with one another transparently.

PC Card power specification

System compatibility also means power compatibility. The most current set of specifications (PC Card Standard) set forth by the PCMCIA committee states that power is to be transferred between the host and the card through eight of the 68 terminals of the PC Card connector. This power interface consists of two V_{CC}, two V_{pp}, and four ground terminals. Multiple V_{CC} and ground terminals minimize connector terminal and line resistance. The two V_{pp} terminals were originally specified as separate signals, but are commonly tied together in the host to form a single node to minimize voltage losses. Card primary power is supplied through the V_{CC} terminals; flash-memory programming and erase voltage is supplied through the V_{pp} terminals.



APPLICATION INFORMATION

designing for voltage regulation

The current PCMCIA specification for output voltage regulation, $V_{O(reg)}$, of the 5-V output is 5% (250 mV). In a typical PC power-system design, the power supply has an output-voltage regulation, $V_{PS(reg)}$, of 2% (100 mV). Also, a voltage drop from the power supply to the PC Card will result from resistive losses, V_{PCB} , in the PCB traces and the PCMCIA connector. A typical design would limit the total of these resistive losses to less than 1% (50 mV) of the output voltage. Therefore, the allowable voltage drop, V_{DS} , for the TPS2214 would be the PCMCIA voltage regulation less the power supply regulation and less the PCB and connector resistive drops:

Typically, this would leave 100 mV for the allowable voltage drop across the 5-V switch. The specification for output voltage regulation of the 3.3-V output is 300 mV; so, using the same equation by deducting the voltage drop percentages (2%) for power-supply regulation and PCB resistive loss (1%), the allowable voltage drop for the 3.3-V switch is 200 mV. The voltage drop is the output current multiplied by the switch resistance of the TPS2214. Therefore, the maximum output current, I_O max, that can be delivered to the PC Card in regulation is the allowable voltage drop across the IC, divided by the output-switch resistance.

$$I_{O}$$
max = $\frac{V_{DS}}{r_{DS(on)}}$

The xVCC outputs can deliver 1 A continuously at 5 V and 3.3 V within regulation over the operating temperature range. The xVPP outputs of the IC can deliver 200 mA continuously.

overcurrent and overtemperature protection

PC Cards are inherently subject to damage that can result from mishandling. Host systems require protection against short-circuited cards that could lead to power-supply or PCB trace damage. Even systems robust enough to withstand a short circuit would still undergo rapid battery discharge into the damaged PC Card, resulting in the rather sudden and unacceptable loss of system power. Most hosts include fuses for protection. However, the reliability of fused systems is poor, as blown fuses require troubleshooting and repair, usually by the manufacturer.

The TPS2214 takes a two-pronged approach to overcurrent protection, which is designed to activate if an output is shorted or when an overcurrent condition is present when switches are powered up. First, instead of fuses, sense FETs monitor each of the xVCC and xVPP power outputs. Unlike sense resistors or polyfuses, these FETs do not add to the series resistance of the switch; therefore voltage and power losses are reduced. Overcurrent sensing is applied to each output separately. Excessive current generates an error signal that limits the output current of only the affected output, preventing damage to the host. Each xVCC output overcurrent limits from 1 A to 2.2 A, typically around 1.6 A; the xVPP outputs limit from 250 mA to 500 mA, typically around 375 mA.

Second, when an overcurrent condition is detected, the TPS2214 asserts an active low \overline{OC} signal that can be monitored by the microprocessor or controller to initiate diagnostics and/or send the user a warning message. In the event that an overcurrent condition persists, causing the IC to exceed its maximum junction temperature, thermal-protection circuitry activates. This shuts down all power outputs until the device cools to within a safe operating region, which is ensured by a thermal shutdown hysteresis.



SLVS206B - JULY 1999 - REVISED JUNE 2000

APPLICATION INFORMATION

12-V supply not required

Many PC Card switches use the externally supplied 12 V to power gate drive and other chip functions; this requires that power be present at all times. The TPS2214 offers considerable power savings by using an internal charge pump to generate the required higher gate drive voltages from the 5-V or 3.3-V power supplies. Therefore, the external 12-V supply can be disabled except when needed for flash-memory functions, thereby extending battery lifetime. Additional power savings are realized by the IC during shutdown mode, in which quiescent current drops to a maximum of 1 μ A.

3.3-V low-voltage mode

The TPS2214 will operate in 3.3-V low-voltage mode when 3.3 V is the only available input voltage ($V_{I(5V)} = 0$, V_{I(12V)} = 0). This feature allows host and PC Cards to be operated in low-power 3.3-V-only modes such as sleep modes. Note that in this operation mode, the IC will derive its bias current from the 3.3-V input pin and can only provide 3.3 V to the outputs.

voltage transitioning requirement

PC Cards are migrating from 5 V to 3.3 V to minimize power consumption, optimize board space, and increase logic speeds. The TPS2214 meets all combinations of power delivery as currently defined in the PCMCIA standard. The latest protocol accommodates mixed 3.3-V/5-V systems by first powering the card with 5 V, then polling it to determine its 3.3-V compatibility. The PCMCIA specification requires that the capacitors on 3.3-V-compatible cards be discharged to below 0.8 V before applying 3.3-V power. This action ensures that sensitive 3.3-V circuitry is not subjected to any residual 5-V charge and functions as a power reset. PC Card specification requires that V_{CC} be discharged within 100 ms. PC Card resistance can not be relied on to provide a discharge path for voltages stored on PC Card capacitance because of possible high-impedance isolation by power-management schemes. The TPS2214 includes discharge transistors on all xVCC and xVPP outputs to meet the specification requirement.

shutdown mode

In the shutdown mode, which can be controlled by bit D8 of the input serial DATA word, each of the xVCC and xVPP outputs is forced to a high-impedance state. In this mode, the chip quiescent current is limited to 1 µA or less to conserve battery power.

standby mode

The TPS2214 can be put in standby mode by pulling STBY low to conserve power during low-power operation. In this mode, all of the power outputs (xVCC and xVPP) will have a nominal current limit of 50 mA. STBY has an internal 150-k Ω pullup resistor. The output-switch status of the device must be set, allowing the output capacitors to charge, prior to enabling the standby mode. Changing the setting of the output switches with the device in standby mode may cause an overcurrent response to be generated.

mode

The mode pin programs the switches in either TPS2214 or TPS2206 mode. An internal 150-kΩ pulldown resistor is connected to the pin. Floating or pulling the mode pin low sets the switches in TPS2206 mode; pulling the mode pin high sets the switches in TPS2214 mode. In TPS2206 mode, xVPP outputs are dependent on xVCC outputs. In TPS2214 mode, xVPP is programmed independent of xVCC. Refer to TPS2214 control-logic tables for more information.



APPLICATION INFORMATION

power supply considerations

The TPS2214 has multiple pins for each of its 3.3-V and 5-V power inputs and for the switched xVCC outputs. Any individual pin can conduct the rated input or output current. Unless all pins are connected in parallel, the series resistance is higher than that specified, resulting in increased voltage drops and less power. It is recommended that all input and output power pins be paralleled for optimum operation. Because the two 12-V pins are not internally connected, they must be tied together externally.

To increase the noise immunity of the TPS2214, the power-supply inputs should be bypassed with a 1- μ F electrolytic or tantalum capacitor paralleled by a 0.047- μ F to 0.1- μ F ceramic capacitor. It is strongly recommended that the switched outputs be bypassed with a 0.1- μ F (or larger) ceramic capacitor; doing so improves the immunity of the IC to electrostatic discharge (ESD). Care should be taken to minimize the inductance of PCB traces between the IC and the load. High switching currents can produce large negative voltage transients, which forward biases substrate diodes, resulting in unpredictable performance. Similarly, no pin should be taken, or allowed to fall, below –0.3 V.

RESET and RESET inputs

To ensure that cards are in a known state after power brownouts or system initialization, the PC Cards should be reset at the same time as the host by applying low impedance paths from xVCC and xVPP terminals to ground. A low-impedance output state allows discharging of residual voltage remaining on PC Card filter capacitance, permitting the system (host and PC Cards) to be powered up concurrently. The active-high RESET or active low RESET input will close internal switches S1, S4, S7, and S11 with all other switches left open. The TPS2214 remains in the low-impedance output state until the signal is deasserted and further data is clocked in and latched. The input serial data can not be latched during Reset mode. RESET and RESET are provided for direct compatibility with systems that use either an active-low or active-high reset voltage supervisor. The RESET pin has an internal 150-k Ω pulldown resistor and the RESET pin has an internal 150-k Ω pullup resistor. The device will be reset automatically when powered up.

calculating junction temperature

The switch resistance, $r_{DS(on)}$, is dependent on the junction temperature, T_J , of the die. The junction temperature is dependent on both $r_{DS(on)}$ and the current through the switch. To calculate T_J , first find $r_{DS(on)}$ from Figures 23 through 26, using an initial temperature estimate about 50°C above ambient. Then calculate the power dissipation for each switch, using the formula:

$$P_D = r_{DS(on)} \times l^2$$

Next, sum the power dissipation of all switches and calculate the junction temperature:

$$\mathsf{T}_{\mathsf{J}} = \left(\sum \mathsf{P}_{\mathsf{D}} \times \mathsf{R}_{\theta \mathsf{J} \mathsf{A}}\right) + \mathsf{T}_{\mathsf{A}}$$

Where:

 $R_{\theta JA}$ is the inverse of the derating factor given in the dissipation rating table.

Compare the calculated junction temperature with the initial temperature estimate. If the temperatures are not within a few degrees of each other, recalculate using the calculated temperature as the initial estimate.

logic inputs and outputs

The serial interface consists of DATA, CLOCK, and LATCH leads. The data is clocked in on the positive edge of the clock (see Figures 2 and 3). The 11-bit (D0–D10) serial data word is loaded during the positive edge of the latch signal. The positive edge of the latch signal should occur before the next positive edge of the clock occurs.



SLVS206B - JULY 1999 - REVISED JUNE 2000

APPLICATION INFORMATION

logic inputs and outputs (continued)

The TPS2214 serial interfaces are compatible with serial-interface PCMCIA controllers and current PCMCIA and Japan Electronic Industry Development Association (JEIDA) standards.

An overcurrent output (OC) is provided to indicate an overcurrent or overtemperature condition in any of the xVCC and xVPP outputs as previously discussed.

TPS2214 control logic

TPS2214 mode (MODE pulled high)

xVPP

	AVPP (CONTROL SIG	GNALS	OUTPUT	BVPP CONTROL SIGNALS				OUTPUT
D8 (SHDN)	D0	D1	D9	V_AVPP	D8 (SHDN)	D4	D5	D10	V_BVPP
1	0	0	Х	0 V	1	0	0	Х	0 V
1	0	1	0	3.3 V	1	0	1	0	3.3 V
1	0	1	1	5 V	1	0	1	1	5 V
1	1	0	Х	12 V	1	1	0	Х	12 V
1	1	1	Х	Hi-Z	1	1	1	Х	Hi-Z
0	Х	Х	Х	Hi-Z	0	Х	Х	Х	Hi-Z

xVCC

	AVCC CONTROL SIGNALS		OUTPUT	BVCC CONTROL SIGNALS				OUTPUT
D8 (SHDN)	D3	D2	V_AVCC	D8 (SHDN)	D6	D7	V_BVCC	
1	0	0	0 V	1	0	0	0 V	
1	0	1	3.3 V	1	0	1	3.3 V	
1	1	0	5 V	1	1	0	5 V	
1	1	1	0 V	1	1	1	0 V	
0	Х	Х	Hi-Z	0	Х	Х	Hi-Z	

TPS2206 mode (MODE floating or pulled low)

xVPP

	AVPP CONTROL SIGNALS		OUTPUT	BVPF	OUTPUT			
D8 (SHDN)	D0	D1	V_AVPP	D8 (SHDN)	D4	D5	V_BVPP	
1	0	0	0 V	1	0	0	0 V	
1	0	1	V_AVCC	1	0	1	V_BVCC	
1	1	0	12 V	1	1	0	12 V	
1	1	1	Hi-Z	1	1	1	Hi-Z	
0	Х	Х	Hi-Z	0	Х	Х	Hi-Z	

xVCC


	AVCC CONTROL SIGNALS		OUTPUT	BVCC	OUTPUT			
D8 (SHDN)	D3	D2	V_AVCC	D8 (SHDN)	D6	D7	V_BVCC	
1	0	0	0 V	1	0	0	0 V	
1	0	1	3.3 V	1	0	1	3.3 V	
1	1	0	5 V	1	1	0	5 V	
1	1	1	0 V	1	1	1	0 V	
0	Х	Х	Hi-Z	0	Х	Х	Hi-Z	



APPLICATION INFORMATION

ESD protections (see Figure 34)

All TPS2214 inputs and outputs incorporate ESD-protection circuitry designed to withstand a 2-kV human-body-model discharge as defined in MIL-STD-883C, Method 3015. The xVCC and xVPP outputs can be exposed to potentially higher discharges from the external environment through the PC Card connector. Bypassing the outputs with $0.1-\mu$ F capacitors protects the devices from discharges up to 10 kV.



[†] Maximum recommended output capacitance for xVCC is 220 μ F and for xVPP is 10 μ F without \overline{OC} glitch when switches are powered on.

Figure 34. Detailed Interconnections and Capacitor Recommendations




SLVS206B - JULY 1999 - REVISED JUNE 2000

APPLICATION INFORMATION

12-V flash memory supply

The TPS6734 is a fixed 12-V output boost converter capable of delivering 120 mA from inputs as low as 2.7 V. The device is pin-for-pin compatible with the MAX734 regulator and offers the following advantages: lower supply current, wider operating input-voltage range, and higher output currents. As shown in Figure 35, the only external components required are: an inductor, a Schottky rectifier, an output filter capacitor, an input filter capacitor, and a small capacitor for loop compensation. The entire converter occupies less than 0.7 in² of PCB space when implemented with surface-mount components. An enable input is provided to shut the converter down and reduce the supply current to 3 µA when 12 V is not needed.

The TPS6734 is a 170-kHz current-mode PWM (pulse-width modulation) controller with an n-channel MOSFET power switch. Gate drive for the switch is derived from the 12-V output after start-up to minimize the die area needed to realize the 0.7-Ω MOSFET and improve efficiency at input voltages below 5 V. Soft start is accomplished with the addition of one small capacitor. A 1.22-V reference (pin 2) is brought out for external use. For additional information, see the TPS6734 data sheet (SLVS127).



NOTE A: The enable terminal can be tied to a general-purpose I/O terminal on the PCMCIA controller or tied high.

Figure 35. TPS2214 with TPS6734 12-V, 120-mA Supply





16-Aug-2014

PACKAGING INFORMATION

Orderable Device	Status	Package Type	-	Pins	-	Eco Plan	Lead/Ball Finish	MSL Peak Temp	Op Temp (°C)	Device Marking	Samples
	(1)		Drawing		Qty	(2)	(6)	(3)		(4/5)	
TPS2214DB	ACTIVE	SSOP	DB	24		TBD	Call TI	Call TI	-40 to 85	TPS2214	Samples

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

Pb-Free (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

Pb-Free (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(⁵⁾ Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

⁽⁶⁾ Lead/Ball Finish - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



www.ti.com

PACKAGE OPTION ADDENDUM

16-Aug-2014

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have *not* been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products		Applications					
Audio	www.ti.com/audio	Automotive and Transportation	www.ti.com/automotive				
Amplifiers	amplifier.ti.com	Communications and Telecom	www.ti.com/communications				
Data Converters	dataconverter.ti.com	Computers and Peripherals	www.ti.com/computers				
DLP® Products	www.dlp.com	Consumer Electronics	www.ti.com/consumer-apps				
DSP	dsp.ti.com	Energy and Lighting	www.ti.com/energy				
Clocks and Timers	www.ti.com/clocks	Industrial	www.ti.com/industrial				
Interface	interface.ti.com	Medical	www.ti.com/medical				
Logic	logic.ti.com	Security	www.ti.com/security				
Power Mgmt	power.ti.com	Space, Avionics and Defense	www.ti.com/space-avionics-defense				
Microcontrollers	microcontroller.ti.com	Video and Imaging	www.ti.com/video				
RFID	www.ti-rfid.com						
OMAP Applications Processors	www.ti.com/omap	TI E2E Community	e2e.ti.com				
Wireless Connectivity	www.ti.com/wirelessconne	vww.ti.com/wirelessconnectivity					

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2014, Texas Instruments Incorporated