SPRS009C-JANUARY 1987-REVISED JULY 1991

- Performance Up to 8.77 MIPs
- All TMS320C1x Devices are Object Code Compatible
- 144/256-Word On-Chip Data RAM
- 1.5K/4K/8K-Word On-Chip Program ROM
- 4K-Word On-Chip Program EPROM (TMS320E14/P14/E15/P15/E17/P17)
- One-Time Programmable (OTP) Versions Available (TMS320P14/P15/P17)
- EPROM Code Protection for Copyright Security
- 4K / 64K-Word Total External Memory at Full Speed
- 32-Bit ALU/Accumulator
- 16 × 16-Bit Multiplier With a 32-Bit Product
- 0 to 16-Bit Barrel Shifter
- Eight Input/Output Channels
- Dual-Channel Serial Port
- Simple Memory and I/O Interface
- 5-V and 3.3-V Versions Available (TMS320LC15/LC17)

introduction

The TMS32010 digital signal processor (DSP), introduced in 1983, was the first DSP in the TMS320 family. From it has evolved this TMS320C1x generation of 16-bit DSPs. All 'C1x DSPs are object code compatible with the TMS32010 DSP. The 'C1x DSPs combine the flexibility of a high-speed controller with the numerical capability of an array processor, thereby offering an inexpensive alternative to multichip bit-slice processors. The highly paralleled architecture and efficient instruction set provide speed and flexibility to produce a CMOS microprocessor generation capable of executing up to 8.77 MIPS (million instructions per second) ('C16). These 'C1x devices utilize a modified Harvard architecture to optimize speed and flexibility, implementing functions in hardware that other processors implement through microcode or software.

The 'C1x generation's powerful instruction set, inherent flexibility, high-speed number-handling capabilities, reduced power consumption, and innovative architecture have made these cost-effective DSPs the ideal solution for many telecommunications, computer, commercial, industrial, and military applications.

This data sheet provides detailed design documentation for the 'C1x DSPs. It facilitates the selection of devices best suited for various user applications by providing specifications and special features for each 'C1x DSP.

This data sheet is arranged as follows: introduction, quick reference table of device parameters and packages, summary overview of each device, architecture overview, and the 'C1x device instruction set summary. These are followed by data sheets for each 'C1x device providing available package styles, terminal function tables, block diagrams, and electrical and timing parameters. An index is provided to facilitate data sheet usage.



- Commercial and Military Versions Available
- Operating Free-Air Temperature ... 0°C to 70°C
- Packaging: DIP, PLCC, Quad Flatpack, and CER-QUAD
- CMOS Technology:

Device	Cycle Time
— TMS320C10	200-ns
— TMS320C10-14	280-ns
— TMS320C10-25	160-ns
— TMS320C14	160-ns
— TMS320E14	160-ns
— TMS320P14	160-ns
— TMS320C15	200-ns
— TMS320C15-25	160-ns
— TMS320E15	200-ns
— TMS320E15-25	160-ns
— TMS320LC15	250-ns
— TMS320P15	200-ns
— TMS320C16	114-ns
— TMS320C17	200-ns
— TMS320E17	200-ns
— TMS320LC17	278-ns
— TMS320P17	200-ns

SPRS009C-JANUARY 1987-REVISED JULY 1991

Table 1 provides an overview of 'C1x processors with comparisons of memory, I/O, cycle timing, military support, and package types. For specific availability, contact the nearest TI Field Sales Office.

		ME	MORY			/0	CYCLE		PACKAGE	(1)
DEVICE	RAM	ROM	EPROM	PROG.	SERIAL	PARALLEL	(ns)	DIP	PLCC	CER-QUAD
TMS320C10 (2)	144	1.5K	—	4K	—	8×16	200	40	44	—
TMS320C10-14	144	1.5K	—	4K	—	8×16	280	40	44	—
TMS320C10-25	144	1.5K	—	4K	—	8×16	160	40	44	—
TMS320C14 (3)	256	4K	—	4K	1	7×16 (4)	160	—	68	—
TMS320E14 (3)	256	—	4K	4K	1	7×16 (4)	160	—	—	68 CER
TMS320P14 [†]	256	—	4K	4K	1	7×16 (4)	160	—	68	—
TMS320C15 (3)	256	4K	—	4K	—	8×16	200	40	44	—
TMS320C15-25	256	4K	—	4K	—	8×16	160	40	44	—
TMS320E15 (3)	256	—	4K	4K	—	8×16	200	40	—	44 CER
TMS320E15-25	256	—	4K	4K	—	8×16	160	40	—	44 CER
TMS320LC15	256	4K	—	4K	—	8×16	250	40	44	—
TMS320P15 [†]	256	—	4K	4K	—	8×16	200	40	44	—
TMS320C16	256	8K	—	64K	—	8×16	114	—	—	64 QFP
TMS320C17	256	4K	_	_	2	6×16 (5)	200	40	44	—
TMS320E17 (5)	256	_	4K	_	2	6×16 (5)	200	40	—	44 CER
TMS320LC17 (5)	256	4K	—	_	2	6×16 (5)	278	40	44	—
TMS320P17 (5) [†]	256	_	4K	_	2	6×16 (5)	200	40	40 44	

Table 1. TMS320C1x Device Overview

[†]One-time programmable (OTP) device is in a windowless plastic package and cannot be erased.

NOTES: 1. DIP = dual in-line package. PLCC = plastic-leaded chip carrier. CER = ceramic-leaded chip carrier. QFP = plastic quad flat pack. 2. Military version available.

3. Military versions planned; contact nearest TI Field Sales Office for availability.

4. On-chip 16-bit I/O, four capture inputs, and six compare outputs are available.

5. On-chip 16-bit coprocessor interface is optional by pin selection.



description

TMS320C10

The 'C10 provides the core CPU used in all other 'C1x devices. Its microprocessor operates at 5 MIPS. It provides a parallel I/O of 8×16 bits. Three versions with cycle times of 160, 200, and 280 ns are available as illustrated in Table 1. The 'C10 versions are offered in plastic 40-pin DIP or a 44-lead PLCC packages.

TMS320C14/E14/P14

The 'C14/E14/P14 devices, using the 'C10 core CPU, offer expanded on-chip RAM, and ROM or EPROM ('E14/P14), 16 pins of bit selectable parallel I/O, an I/O mapped asynchronous serial port, four 16-bit timers, and external/internal interrupts. The 'C14 devices can provide for microcomputer/microprocessor operating modes. Three versions with cycle times of 160-ns are available as illustrated in Table 1. These devices are offered in 68-pin plastic PLCC or ceramic CER-QUAD packages.

TMS320C15/E15/P15

The 'C15/E15/P15 devices are a version of the 'C10, offering expanded on-chip RAM, and ROM or EPROM ('E15/P15). The 'P15 is a one-time programmable (OTP), windowless EPROM version. These devices can operate in the microcomputer or microprocessor modes. Five versions are available with cycle times of 160 to 200 ns (see Table 1). These devices are offered in 40-pin DIP, 44-pin PLCC, or 44-pin ceramic packages.

TMS320LC15

The 'LC15 is a low-power version of the 'C15, utilizing a V_{DD} of only 3.3-V. This feature results in a 2.3: 1 power requirement reduction over the typical 5-V 'C1x device. It operates at a cycle time of 250 ns. The device is offered in 40-pin DIP or 44-lead PLCC packages.

TMS320C16

The 'C16 offers on-chip RAM of 256-words, an expanded program memory of 64K-words, and a fast instruction cycle time of 114 ns (8.77 MIPS). It is offered in a 64-pin quad flat-pack package.

TMS320C17/E17/P17

The 'C17/E17/P17 versions consist of five major functional units: the 'C15 microcomputer, a system control register, a full-duplex dual channel serial port, μ -law/A-law companding hardware, and a coprocessor port. The dual-channel serial port is capable of full-duplex serial communication and offers direct interface to two combo-codecs. The hardware companding logic can operate in either μ -law or A-law format with either sign-magnitude or twos complement numbers in either serial or parallel modes. The coprocessor port allows the 'C17/E17/P17 to act as a slave microcomputer or as a master to a peripheral microcomputer.


The 'P17 utilizes a one-time programmable (OTP) windowless EPROM version of the 'E17.

TMS320LC17

The 'LC17 is a low-power version of the 'C17, utilizing a V_{DD} of only 3.3-V. This feature results in a 2.3: 1 power requirement reduction over the typical 5-V 'C1x device. It operates at a cycle time of 278 ns.



SPRS009C-JANUARY 1987-REVISED JULY 1991



architecture

The 'C1x DSPs use a modified Harvard architecture for speed and flexibility. In a strict Harvard architecture, program and data memory lie in two separate spaces, permitting a full overlap of instruction fetch and one-cycle execution. The 'C1x DSPs modification allows transfers between program and data spaces, thereby increasing the flexibility of the device. This modification permits coefficients stored in program memory to be read into the RAM, eliminating the need for a separate coefficient ROM.

32-bit accumulator

All 'C1x devices contain a 32-bit ALU and accumulator for support of double-precision, twos-complement arithmetic. The ALU is a general-purpose arithmetic unit that operates on 16-bit words taken from the data RAM or derived from immediate instructions. In addition to the usual arithmetic instructions, the ALU can perform Boolean operations, providing the bit manipulation ability required of a high-speed controller. The accumulator stores the output from the ALU and is often an input to the ALU. It operates with a 32-bit word length. The accumulator is divided into a high-order word (bits 31 through 16) and a low-order word (bits 15 through 0). Instructions are provided for storing the high- and low-order accumulator words in memory.

shifters

Two shifters are available for manipulating data. The ALU barrel shifter performs a left-shift of 0 to 16 places on data memory words loaded into the ALU. This shifter extends the high-order bit of the data word and zero-fills the low-order bits for twos-complement arithmetic. The accumulator parallel shifter performs a left-shift of 0, 1 or 4 places on the entire accumulator and places the resulting high-order accumulator bits into data RAM. Both shifters are useful for scaling and bit extraction.

16×16 -bit parallel multiplier

The multiplier performs a 16×16 -bit twos-complement multiplication with a 32-bit result in a single instruction cycle. The multiplier consists of three units: the T Register, P Register, and a multiplier array. The 16-bit T Register stores the multiplicand, and the P Register stores the 32-bit product. Multiplier values either come from the data memory or are derived immediately from the MPYK (multiply immediate) instruction word. The fast on-chip multiplier allows the device to perform fundamental operations such as convolution, correlation, and filtering.

data and program memory

Since the 'C1x devices use a Harvard type architecture, data and program memory reside in two separate spaces. These DSP devices have 144-or 256-words of on-chip data RAM and 1.5K- to 8K-words of on-chip program ROM. On-chip program EPROM of 4K-words is provided in the 'E14/E15/E17 devices. An on-chip one-time programmable 4K-word EPROM is provided in the 'P14/P15/P17 devices. The EPROM cell utilizes standard PROM programmers and is programmed identically to a 64K CMOS EPROM (TMS27C64). (Reference Table 1.)

program memory expansion

All 'C1x devices except the 'C17/E17/LC17/P17 devices are capable of executing from off-chip external memory at full speed for those applications requiring external program memory space. This allows for external RAM-based systems to provide multiple functionality. The 'C17/E17/LC17/P17 devices provide no external memory expansion. (Reference Table 1.)

microcomputer/microprocessor operating modes

All devices except the 'x17 offer two modes of operation defined by the state of the MC/ $\overline{\text{MP}}$ pin: the microcomputer mode (MC/ $\overline{\text{MP}}$ = 1) or the microprocessor mode (MC/ $\overline{\text{MP}}$ = 0). In the microcomputer mode, on-chip ROM is mapped into the program memory space. In the microprocessor mode, all words of program memory are external.



SPRS009C-JANUARY 1987-REVISED JULY 1991

interrupts and subroutines

All devices except the 'C16 contain a four-level stack for saving the contents of the program counter during interrupts and subroutine calls. Because of the larger 64K program space, the 'C16's hardware stack has been increased to eight levels. Instructions are available for saving the device's complete context. PUSH and POP instructions permit a level of nesting restricted only by the amount of available RAM. The interrupts used in these devices are maskable.

input/output

The 16-bit parallel data bus can be utilized to perform I/O functions in two cycles. The I/O ports are addressed by the three LSBs on the address lines. In addition, a polling input for bit test and jump operations (\overline{BIO}) and an interrupt pin (\overline{INT}) have been incorporated for multitasking. The bit selectable I/O of the 'C14 is suitable for microcontroller applications.

serial port (TMS320C17/E17)

Two of the I/O ports on the 'C17/E17 are dedicated to the serial port and companding hardware. I/O port 0 is dedicated to control register 0, which controls the serial port, interrupts, and companding hardware. I/O port 1 accesses control register 1, as well as both serial port channels, and companding hardware. The six remaining I/O ports are available for external parallel interfaces.

serial port (TMS320C14/E14)

The 'C14/E14 devices include one I/O-mapped serial port that operates asynchronously. I/O-mapped control registers are used to configure port parameters such as inter-processor communication protocols and baud rate.

companding hardware (TMS320C17/E17)

On-chip hardware enables the 'C17/E17 to compand (COMpress/exPAND) data in either µ-law or A-law format. The companding logic operation is configured via the system control register. Data may be companded in either serial mode for operation on serial port data (converting between linear and logarithmic PCM) or a parallel mode for computation inside the device. The 'C17/E17 allows the hardware companding logic to operate with either sign-magnitude or twos-complement numbers.

coprocessor port (TMS320C17/E17)

The coprocessor port on the 'C17/E17 provides a direct connection to most microcomputers and microprocessors. The port is accessed through I/O port 5 using IN and OUT instructions. The coprocessor interface allows the device to act as a peripheral (slave) microcomputer to a microprocessor, or as a master to a peripheral microcomputer. In the microcomputer mode, the 16 data lines are used for the 6 parallel 16-bit I/O ports. In the coprocessor mode, the 16-bit parallel port is reconfigured to operate as a 16-bit latched bus interface. For peripheral transfer, an 8-bit or 16-bit length of the coprocessor port can be selected.



instruction set

A comprehensive instruction set supports both numeric-intensive operations, such as signal processing, and general-purpose operations, such as high-speed control. All of the 'C1x devices are object-code compatible and use the same 60 instructions. The instruction set consists primarily of single-cycle single-word instructions, permitting execution rates of more than six million instructions per second. Only infrequently used branch and I/O instructions are multicycle. Instructions that shift data as part of an arithmetic operation execute in a single cycle and are useful for scaling data in parallel with other operations.

NOTE

The BIO pin on other 'C1x devices is not available for use in the 'C14/E14/P14. An attempt to execute the BIOZ (Branch on BIO low) instruction will result in a two cycle NOP action.

Three main addressing modes are available with the instruction set: direct, indirect, and immediate addressing.

direct addressing

In direct addressing, seven bits of the instruction word concatenated with the 1-bit data page pointer form the data memory address. This implements a paging scheme in which the first page contains 128 words, and the second page contains up to 128 words.

indirect addressing

Indirect addressing forms the data memory address from the least-significant eight bits of one of the two auxiliary registers, AR0-AR1. The Auxiliary Register Pointer (ARP) selects the current auxiliary register. The auxiliary registers can be automatically incremented or decremented and the ARP changed in parallel with the execution of any indirect instruction to permit single-cycle manipulation of data tables. Indirect addressing can be used with all instructions requiring data operands, except for the immediate operand instructions.

immediate addressing

Immediate instructions derive data from part of the instruction word rather than from the data RAM. Some useful immediate instructions are multiply immediate (MPYK), load accumulator immediate (LACK), and load auxiliary register immediate (LARK).

instruction set summary

Table 2 lists the symbols and abbreviations used in Table 3, the instruction set summary. Table 3 contains a short description and the opcode for each 'C1x instruction. The summary is arranged according to function and alphabetized within each functional group.

SYMBOL	MEANING
ACC	Accumulator
D	Data memory address field
Μ	Addressing mode bit
К	Immediate operand field
PA	3-bit port address field
R	1-bit operand field specifying auxiliary register
S	4-bit left-shift code
Х	3-bit accumulator left-shift field

Table 2. Instruction Symbols



SPRS009C-JANUARY 1987-REVISED JULY 1991

	ACCUM	ULATOR IN	STRUCTION	S														
			NO							OP	COL	ЭE						
MNEMONIC	DESCRIPTION	NO. CYCLES	NO. WORDS					IN	STRU	істі	ON I	REG	ISTE	R				
				15	14	13	12	11	10	9	8	7	6	5	4	3	2	1 (
ABS	Absolute value of accumulator	1	1	0	1	1	1	1	1	1	1	1	0	0	0	1	0	0 0
ADD	Add to accumulator with shift	1	1	0	0	0	0	•		— s	•	М	◀			- D—		-
ADDH	Add to high-order accumulator bits	1	1	0	1	1	0	0	0	0	0	М	◀			- D-		-
ADDS	Add to accumulator with no sign extension	1	1	0	1	1	0	0	0	0	1	М	◀			- D—		-
AND	AND with accumulator	1	1	0	1	1	1	1	0	0	1	М	◀			- D—		
LAC	Load accumulator with shift	1	1	0	0	1	0	•		— s	•	М	◀			– D—		-
LACK	Load accumulator immediate	1	1	0	1	1	1	1	1	1	0					- K—		-
OR	OR with accumulator	1	1	0	1	1	1	1	0	1	0	М	◀			– D—		-
SACH	Store high-order accumulator bits with shift	1	1	0	1	0	1	1	-	— X	•	М	◀			- D—		-
SACL	Store low-order accumulator bits	1	1	0	1	0	1	0	0	0	0	М	◀			- D—		-
SUB	Subtract from accumulator with shift	1	1	0	0	0	1	•		— s	-	М	◀			- D—		
SUBC	Conditional subtract (for divide)	1	1	0	1	1	0	0	1	0	0	М	◀			- D—		-
SUBH	Subtract from high-order accumulator bits	1	1	0	1	1	0	0	0	1	0	М	◀			- D—		-
SUBS	Subtract from accumulator with no sign extension	1	1	0	1	1	0	0	0	1	1	М	◀			– D—		-
XOR	Exclusive OR with accumulator	1	1	0	1	1	1	1	0	0	0	М	◀			– D—		
ZAC	Zero accumulator	1	1	0	1	1	1	1	1	1	1	1	0	0	0	1	0	0 1
ZALH	Zero accumulator and load high-order bits	1	1	0	1	1	0	0	1	0	1	М	◀			- D—		
ZALS	Zero accumulator and load low-order bits with no sign extension	1	1	0	1	1	0	0	1	1	0	М	◀			- D—		-
	AUXILIARY REGISTER A	ND DATA PA	GE POINTE	R IN	STRU	стіс	NS											
										OP	COL	ЭE						
MNEMONIC	DESCRIPTION	NO. CYCLES	NO. WORDS					IN	STRU	істі	ON I	REG	ISTE	R				
				15	14	13	12	11	10	9	8	7	6	5	4	3	2	1 (
LAR	Load auxiliary register	1	1	0	0	1	1	1	0	0	R	М	•			— D-		_
LARK	Load auxiliary register immediate	1	1	0	1	1	1	0	0	0	R	•	-			— K-		
LARP	Load auxiliary register pointer immediate	1	1	0	1	1	0	1	0	0	0	1	0	0	0	0	0	0 1
LDP	Load data memory page pointer	1	1	0	1	1	0	1	1	1	1	М	4			— D-		
LDPK	Load data memory page pointer immediate	1	1	0	1	1	0	1	1	1	0	0	0	0	0	0	0	0 1
MAR	Modify auxiliary register and pointer	1	1	0	1	1	0	1	0	0	0	М	4			— D-		
SAR	Store auxiliary register	1	1	0	0	1	1	0	0	0	R	М	•			— D-		

Table 3. TMS320C1x Instruction Set Summary



SPRS009C-JANUARY 1987-REVISED JULY 1991

	BRA	NCH INSTR	UCTIONS																_
										OP	со	DE							
MNEMONIC	DESCRIPTION	NO. CYCLES	NO. WORDS	INSTRUCTION REGISTER															
				15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	
В	Branch unconditionally	2	2	1	1	1	1	1	0	0	1	0	0	0	0	0	0	0	(
D	Branch unconditionally	2	2	0	0	0	0	•				BRA	NCH	I ADD	RES	3S —			-
BANZ	Branch on auxiliary register not zero	2	2	1	1	1	1	0	1	0	0	0	0	0	0	0	0	0	(
				0	0	0	0	•			_	BRA	NCH	I ADD	RES	3S —			-
BGEZ	Branch if accumulator ≥ 0	2	2	1	1	1	1	1	1	0	1	0	0	0	0	0	0	0	(
DGEZ		2	2	0	0	0	0	-				BRA	NCH	I ADD	RES	3S —			-
807	Presch if a supplicition of			1	1	1	1	1	1	0	0	0	0	0	0	0	0	0	(
BGZ	Branch if accumulator > 0	2	2	0	0	0	0	•			_	BRA	NCH	I ADD	RES	3S —			•
807	Branch on $\overline{BIO} = 0^{\dagger}$			1	1	1	1	0	1	1	0	0	0	0	0	0	0	0	(
BIOZ	Branch on BIO = 0 1	2	2	0	0	0	0	-				BRA	NCH	I ADD	RES	3S —			•
				1	1	1	1	1	0	1	1	0	0	0	0	0	0	0	(
BLEZ	Branch if accumulator ≤ 0	2	2	0	0	0	0	-				BRA	NCH	I ADD	RES	3S —			-)
DI 7	Presch if a supplicition of			1	1	1	1	1	0	1	0	0	0	0	0	0	0	0	
BLZ	Branch if accumulator < 0	2	2	0	0	0	0	-				BRA	NCH	I ADD	RES	3S —			-
				1	1	1	1	1	1	1	0	0	0	0	0	0	0	0	(
BNZ	Branch if accumulator $\neq 0$	2	2	0	0	0	0	-				BRA	NCH	I ADD	RES	3S —			-)
				1	1	1	1	0	1	0	1	0	0	0	0	0	0	0	(
BV	Branch on overflow	2	2	0	0	0	0	-				BRA	NCH	I ADD	RES	3S —			•
				1	1	1	1	1	1	1	1	0	0	0	0	0	0	0	
BZ	Branch if accumulator = 0	2	2	0	0	0	0	-				BRA	NCH	I ADD	RES	3S —			-)
CALA	Call subroutine from accumulator	2	1	0	1	1	1	1	1	1	1	1	0	0	0	1	1	0	(
				1	1	1	1	1	0	0	0	0	0	0	0	0	0	0	(
CALL	Call subroutine immediately	2	2	0	0	0	0	-				BRA	NCH	I ADD	RES	3S —			•
RET	Return from subroutine or interrupt routine	2	1	0	1	1	1	1	1	1	1	1	0	0	0	1	1	0	
	T REGISTER, P REGI	STER, AND	MULTIPLY I	NSTR	UCT	IONS													
										OP	со	DE							
MNEMONIC	DESCRIPTION	NO. CYCLES	NO. WORDS					IN	STRU	сті	ON	REG	ISTE	R					
				15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	(
APAC	Add P register to accumulator	1	1	0	1	1	1	1	1	1	1	1	0	0	0	1	1	1	
LT	Load T Register	1	1	0	1	1	0	1	0	1	0	Μ	◀			- D-			•
LTA	LTA combines LT and APAC into one instruction	1	1	0	1	1	0	1	1	0	0	Μ	◀			– D–			-)
LTD	LTD combines LT, APAC, and DMOV into one instruction	1	1	0	1	1	0	1	0	1	1	Μ	◀			- D-			-)
MPY	Multiply with T register, store product in P register	1	1	0	1	1	0	1	1	0	1	Μ	◀			– D–			-
МРҮК	Multiply T register with immediate operand; store product in P register	1	1	1	0	0	•						– K-						-1
PAC	Load accumulator from P register	1	1	0	1	1	1	1	1	1	1	1	0	0	0	1	1	1	
SPAC	Subtract P register from accumulator	1	1	0	1	1	1	1	1	1	1	1	0	0	1	0	0	0	

Table 3. TMS320C1x Instruction Set Summary (continued)

 † This instruction is a NOP on the '320C14/E14/P14.



SPRS009C-JANUARY 1987-REVISED JULY 1991

	CON	TROL INSTR	UCTIONS																
MNEMONIC	DESCRIPTION	NO. CYCLES	NO. WORDS		1		IN	OPCODE											
				15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
DINT	Disable interrupt	1	1	0	1	1	1	1	1	1	1	1	0	0	0	0	0	0	1
EINT	Enable interrupt	1	1	0	1	1	1	1	1	1	1	1	0	0	0	0	0	1	0
LST	Load status register	1	1	0	1	1	1	1	0	1	1	М	◀			- D-			►
NOP	No operation	1	1	0	1	1	1	1	1	1	1	1	0	0	0	0	0	0	0
POP	POP stack to accumulator	2	1	0	1	1	1	1	1	1	1	1	0	0	1	1	1	0	1
PUSH	PUSH stack from accumulator	2	1	0	1	1	1	1	1	1	1	1	0	0	1	1	1	0	0
ROVM	Reset overflow mode	1	1	0	1	1	1	1	1	1	1	1	0	0	0	1	0	1	0
SOVM	Set overflow mode	1	1	0	1	1	1	1	1	1	1	1	0	0	0	1	0	1	1
SST	Store status register	1	1	0	1	1	1	1	1	0	0	М	◀			- D-			►
	I/O AND D/	ATA MEMOR	Y OPERATI	ONS															_
										OP	COD	E							
MNEMONIC	DESCRIPTION	NO. CYCLES	NO. WORDS					IN	STRI	JCTI	ON I	REG	ISTE	R					
				15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
DMOV	Copy contents of data memory location into next higher location	1	1	0	1	1	0	1	0	0	1	М	◀			- D-		—	►
IN	Input data from port	2	1	0	1	0	0	0	-	PA-		М	◄			- D-			►
OUT	Output data to port	2	1	0	1	0	0	1	-	PA-		М	◀			- D-			►
TBLR	Table read from program memory to data RAM	3	1	0	1	1	0	0	1	1	1	М	◀			- D-			►
TBLW	Table write from data RAM to program memory 3 1 0 1 1 1 0 1 M Image: D									►									

Table 3. TMS320C1x Instruction Set Summary (concluded)



SPRS009C-JANUARY 1987-REVISED JULY 1991

Key Features: TMS320C10

- Instruction Cycle Timing
 - 160-ns (TMS320C10-25)
 - 200-ns (TMS32010)
 - 280-ns (TMS320C10-14)
- 144 Words of On-Chip Data RAM
- 1.5K Words On-Chip Program ROM
- External Memory Expansion up to 4K Words at Full Speed
- 16 × 16-Bit Multiplier With 32-Bit Product
- 0 to 16-Bit Barrel Shifter
- On-Chip Clock Oscillator
- Device Packaging:
 - 40-Pin DIP
 - 44-Lead PLCC
- Single 5-V Supply
- Operating Free-Air Temperature Range ...0°C to 70°C

A1/PA1

A0/PA0

MC/MP

RS

INT

X1

BIO 🗌

VSS

D8

D9

D10

D11 🗌

D12

D13

D7

D6

D14

D15

CLKOUT

X2/CLKIN

TMS320C10 N/JD Package (Top View)

J40

39 ____ A3

38 _____ A4

37

36

35

34

33

32

31

27 14

> 26

25

21

_____ A2/PA2

A5

A6

A7

A8

MEN

V_{CC}

A9

A10

A11

D0

D1

D2

D3

D4

D5

DEN

WE

1

2

3

4

5

6

7

8

9

10

11 30

12 29

13 28

15


16

17 24

18 23

19 22

20



	TMS320C10 FN/FZ Package (Top View) VSS VSS A1/PA1 D A2/PA2 A3 A4 A5 A5 A5 A5 A5 A5 A5 A5 A5 A5 A5 A5 A5		
	6 5 4 3 2 1 44 43 42 41 40		
CLKOUT X1 X2/CL <u>KIN</u> BIO NC V _{SS} D8 D9 D10 D11 D12	O 7 8 9 10 11 12 13 14 15	39 [38 [37 [36 [35 [33 [33 [33 [30 [29 [A7 A8 <u>MEN</u> WE Vcc A9 A10 A11 D0 D1
	18 19 20 21 22 23 24 25 26 27 28 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0		



SPRS009C-JANUARY 1987-REVISED JULY 1991

NAME	ı/o†	DEFINITION
A11-A0/PA2-PA0	0	External address bus. I/O port address multiplexed over PA2-PA0.
BIO	1	External polling input
CLKOUT	0	System clock output, 1/4 crystal/CLKIN frequency
D15-D0	I/O	16-bit parallel data bus
DEN	0	Data enable for device input data on D15-D0
INT	1	External interrupt input
MC/MP	1	Memory mode select pin. High selects microcomputer mode. Low selects microprocessor mode.
MEN	0	Memory enable indicates that D15-D0 will accept external memory instruction.
NC	0	No connection
RS	1	Reset for initializing the device
VCC	1	+ 5 V supply
VSS	1	Ground
VSS WE	0	Write enable for device output data on D15-D0
X1	0	Crystal output for internal oscillator
X2/CLKIN	1	Crystal input internal oscillator or external system clock input


TERMINAL FUNCTIONS

† Input/Output/High-impedance state.



SPRS009C-JANUARY 1987-REVISED JULY 1991

functional block diagram





SPRS009C-JANUARY 1987-REVISED JULY 1991

electrical specifications

This section contains the electrical specifications for all speed versions of the 'C10 Digital Signal Processors, including test parameter measurement information.

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)[†]

Supply voltage range V _{CC} (see Note 6)	0.3 V to 7 V
Input voltage range	–0.3 V to 7 V
Output voltage range	
Continuous power dissipation	0.5 mW
Operating free-air temperature: L suffix	
A suffix	– 40°C to 85°C
Storage temperature	$\dots \dots -55 \degree C$ to 150 $\degree C$

† Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only, and functional operation of the device at these or any other conditions beyond those indicated in the "Recommended Operating Conditions" section of this specification is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability. NOTE 6: All voltage values are with respect to V_{SS}.

recommended operating conditions

			MIN	NOM	MAX	UNIT
VCC	Supply voltage		4.5	5	5.25	V
VSS	Supply voltage			0		V
Maria		CLKIN	3			V
VIH	High-level input voltage	All remaining inputs	2			V
	Low level input voltage	MC/MP			0.6	V
VIL	Low-level input voltage	All remaining inputs			0.8	V
ЮН	High-level output current, all outputs				-300	μA
IOL	Low-level output current				2	mA
-	Operating free air temperature	L suffix	0		70	°C
ТА	Operating free-air temperature	A suffix	- 40		85	°C



SPRS009C-JANUARY 1987-REVISED JULY 1991

	PARAMETER		TEST C	ONDITIONS	MIN	TYP [†]	MAX	UNIT	
Vou	High-level output voltage		I _{OH} = MAX	OH = MAX				N	
∨он	night-level output voltage		I_{OH} = 20 μ A (see No	te 7)	V _{CC} - 0.4			V	
VOL	Low-level output voltage		I _{OL} = MAX			0.3	0.5	V	
	Off state subsut sums at		V _{CC} = MAX	V _O = 2.4 V			20		
loz	Off-state output current			V _O = 0.4 V			-20	μA	
	la mart a summa a t			All inputs except CLKIN			±20	۵	
1	Input current		$V_{CC} = V_{SS}$ to V_{CC}	CLKIN			±50	μA	
	land an a flam as	Data bus		•		25‡			
Ci	Input capacitance	All others				15‡		pF	
C		Data bus	f = 1 MHz, all other p	DITS U V		25‡		~ [
Co	Output capacitance	All others	1			10‡		pF	

electrical characteristics over specified temperature range (unless otherwise noted)

[†] All typical values are at $V_{CC} = 5 \text{ V}$, $T_A = 25^{\circ}\text{C}$.

[‡] Values derived from characterization data and not tested.

NOTE 7: This voltage specification is included for interface to HC logic. However, note that all of the other timing parameters defined in this data sheet are specified for TTL logic levels and will differ for HC logic levels.

INTERNAL CLOCK OPTION





Figure 1. Internal Clock Option

PARAMETER MEASUREMENT INFORMATION





SPRS009C-JANUARY 1987-REVISED JULY 1991

electrical characteristics over specified temperature range (unless otherwise noted)

	PARAMET	ER	TEST CONDITIONS (SEE FIGURE 2)	MIN	түр†	MAX	UNIT
leet	Supply current	TMS320C10	f = 20.5 MHz, V _{CC} = 5.5 V, T _A = -40° C to 85° C		33	55	
100+	ICC [‡] Supply current	TMS320C10-25	f = 25.6 MHz, V _{CC} = 5.5 V T _A = -0° C to 70 $^{\circ}$ C		40	65	mA

[†] All typical values are at $T_A = 70^{\circ}$ C and are used for thermal resistance calculations.

[‡]I_{CC} characteristics are inversely proportional to temperature. For I_{CC} dependence on temperature, frequency, and loading.

CLOCK CHARACTERISTICS AND TIMING

The 'C10/C10-25 can use either its internal oscillator or an external frequency source for a clock.

internal clock option

The internal oscillator is enabled by connecting a crystal across X1 and X2/CLKIN (see Figure 1). The frequency of CLKOUT is one-fourth the crystal fundamental frequency. The crystal should be fundamental mode, and parallel resonant, with an effective series resistance of 30 ohms, a power dissipation of 1 mW, and should be specified at a load capacitance of 20 pF.

PARAMET	ER	TEST CONDITIONS		NOM	MAX	UNIT
Crystal frequency, f _x	TMS320C10	$T_A = -40^{\circ}C$ to $85^{\circ}C$	6.7		20.5	MHz
	TMS320C10-25	$T_A = 0^{\circ}C$ to $70^{\circ}C$	6.7		25.6	
C1, C2		$T_A = -40^{\circ}C$ to $85^{\circ}C$		10		pF

external clock option

An external frequency source can be used by injecting the frequency directly into X2/CLKIN with X1 left unconnected. The external frequency injected must conform to the specifications listed in the table below.

switching characteristics over recommended operating conditions

	PARAMETER	TEST CONDITIONS	Т	TMS320C10			TMS320C10-25			
	FARAMETER	TEST CONDITIONS	MIN	NOM	MAX	MIN	NOM	MAX	UNIT	
t _{c(C)}	CLKOUT cycle time§		195.12	200		156.25	160		ns	
^t r(C)	CLKOUT rise time	D 005 0		10¶			10¶		ns	
^t f(C)	CLKOUT fall time	R _L = 825 Ω, C _I = 100 pF		8¶			8¶		ns	
^t w(CL)	Pulse duration, CLKOUT low	(see Figure 2)		92¶			72¶		ns	
^t w(CH)	Pulse duration, CLKOUT high			90¶			70¶		ns	
td(MCC)	Delay time, CLKIN \uparrow to CLKOUT \downarrow		25¶		60¶	25		50¶	ns	

 $t_{C(C)}$ is the cycle time of CLKOUT, i.e., $4t_{C(MC)}$ (4 times CLKIN cycle time if an external oscillator is used). I Values derived from characterization data and not tested.

timing requirements over recommended operating conditions

		1	MS320C1	0	TN	IS320C10-	25	UNIT
		MIN	NOM	MAX	MIN	NOM	MAX	UNIT
^t c(MC)	Master clock cycle time	48.78	50	150	39.06	40	150¶	ns
^t r(MC)	Rise time, master clock input		5¶	10¶		5¶	10¶	ns
^t f(MC)	Fall time, master clock input		5¶	10¶		5¶	10¶	ns
^t w(MCP)	Pulse duration, master clock	0.4t _{c(MC}	c)¶ 0.6	^{€t} c(MC) [¶]	0.45t _{c(M}	C) [¶] 0.55	^{it} c(MC) [¶]	ns
^t w(MCL)	Pulse duration, master clock low		20¶			15¶		ns
^t w(MCH)	Pulse duration, master clock high		20¶			15¶		ns

 \P Values derived from characterization data and not tested.



SPRS009C-JANUARY 1987-REVISED JULY 1991

MEMORY AND PERIPHERAL INTERFACE TIMING

switching characteristics over recommended operating conditions

		TEST	TMS	320C10	TMS3	20C10-25	
	PARAMETER	CONDITIONS	MIN	TYP MAX	MIN	TYP MAX	UNIT
^t d1	Delay time, CLKOUT↓ to address bus valid		10†	50	10†	40	ns
t _{d2}	Delay time, CLKOUT↓ to MEN↓		1/4t _{C(C)} - 5 [†]	1/4t _{c(C)} + 15	1/4t _{C(C)} - 5 [†]	$1/4t_{C(C)} + 12$	ns
t _{d3}	De <u>lay ti</u> me, CLKOUT↓ to MEN↑		-10†	15	-10†	12	ns
t _{d4}	Delay time, CLKOUT↓ to DEN↓		1/4t _{c(C)} - 5†	¹ / ₄ t _{c(C)} + 15	1/4t _{c(C)} - 5 [†]	$1/4t_{C(C)} + 12$	ns
^t d5	De <u>lay ti</u> me, CLKOUT↓ to DEN↑		-10†	15	-10†	12	ns
^t d6	Delay time, CLKOUT \downarrow to $\overline{WE}\downarrow$	R _I = 825 Ω	$1/2t_{C(C)} - 5^{\dagger}$	1/2t _{c(C)} + 15	1/2t _{C(C)} -5 [†]	1/2t _{C(C)} + 12	ns
^t d7	Delay time, CLKOUT \downarrow to $\overline{WE}\uparrow$	C_= 100 pF,	-10†	15	-10†	12	ns
t _{d8}	Delay time, CLKOUT \downarrow to data bus OUT valid	(see Figure 2)		1/4t _{C(C)} + 65		1/4t _{c(C)} + 52 [†]	ns
t _{d9}	Time after CLKOUT \downarrow that data bus starts to be driven		1/4t _{c(C)} - 5†		1/4t _{c(C)} - 5 [†]		ns
^t d10	Time after CLKOUT \downarrow that data bus stops being driven			$1/4t_{C(C)} + 40^{\dagger}$		$1/4t_{C(C)} + 40^{\dagger}$	ns
t _V	Data bus OUT valid after CLKOUT \downarrow		1/4t _{C(C)} -10		1/4t _{C(C)} -10		ns
^t h(A-WMD)	Address hold time after $\overline{\text{WE}}\uparrow$, MEN \uparrow , or DEN \uparrow (see Note 8)		-10†		-10†		ns
^t su(A-MD)	Address bus setup time prior to MEN↓ or DEN↓		1/4t _{C(C)} -45		1/4t _{C(C)} -35		ns

[†] Values derived from characterization data and not tested. NOTE 8: For interfacing I/O devices, see Figure 3.



SPRS009C-JANUARY 1987-REVISED JULY 1991

timing requirements over recommended operating conditions

		TEST CONDITION	TN	/IS320C1	0	TMS	S320C10	-25	
		TEST CONDITION	MIN	NOM	MAX	MIN	NOM	MAX	UNIT
tsu(D)	Setup time, data bus valid prior to <code>CLKOUT</code> \downarrow	R _L = 825 Ω,	50			40			ns
^t h(D)	Hold time, data bus held valid after CLKOUT \downarrow (see Note 9)	CL = 100 pF (see Figure 2)	0			0			ns

NOTE 9: Data may be removed from the data bus upon $\overline{\text{MEN}}$ or $\overline{\text{DEN}}$ preceding CLKOUT \downarrow .

SUGGESTED I/O DECODE CIRCUIT

The circuit shown in Figure 3 is a design example for interfacing I/O devices to the 'C10/C10-25. This circuit decodes the address for output operations using the OUT instruction. The same circuit can be used to decode input and output operations if the inverter ('ALS04) is replaced with a NAND gate and both DEN and WE are connected. Inputs and outputs can be decoded at the same port provided the output of the decoder ('AS137) is gated with the appropriate signal (DEN or WE) to select read or write (using an 'ALS32). Access times can be increased when the circuit shown in Figure 3 is repeated to support IN instructions with DEN connected rather than \overline{WE} .

The table write (TBLW) function requires a different circuit. A detailed discussion of an example circuit for this function is described in the application report, "Interfacing External Memory to the TMS32010", published in the book, *Digital Signal Processing Applications with the TMS320 Family* (SPRA012A).




Figure 3. I/O Decode Circuit



SPRS009C-JANUARY 1987-REVISED JULY 1991

RESET (RS) TIMING

switching characteristics over recommended operating conditions

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
^t d11	Delay time, \overline{DEN} , \overline{WE} , and \overline{MEN} from \overline{RS}	R _L 825 Ω, C _L = 100 pF,		1/2t _C ((C)+50†	ns
^t dis(R)	Data bus disable time after RS	(see Figure 2)		1/4t _C ((C)+50 [†]	ns

[†] Values derived from characterization data and not tested.

timing requirements over recommended operating conditions

		TMS320C10			T			
	PARAMETER	MIN	NOM	MAX	MIN	NOM	MAX	UNIT
t _{su(R)}	Reset (\overline{RS}) setup time prior to CLKOUT (see Note 10)	50			40			ns
^t w(R)	RS pulse duration	5t _{C(C)}			5t _C (C)			ns

NOTE 10: RS can occur anytime during a clock cycle. Time given is minimum to ensure synchronous operation.

INTERRUPT (INT) TIMING

timing requirements over recommended operating conditions

			TMS320C10		TMS320C10-25			
		MIN	NOM	MAX	MIN	NOM	MAX	UNIT
^t f(INT)	Fall time, INT			15			15	ns
^t w(INT)	Pulse duration, INT	^t c(C)			^t c(C)			ns
^t su(INT)	Setup time, $\overline{INT}\downarrow$ before CLKOUT \downarrow	50			40			ns

IO (BIO) TIMING

timing requirements over recommended operating conditions

		1	FMS320C10		TMS320C10-25			
		MIN	NOM	MAX	MIN	NOM	MAX	UNIT
^t f(IO)	Fall time, BIO			15			15	ns
^t w(IO)	Pulse duration, BIO	^t c(C)			^t c(C)			ns
t _{su(IO)}	Setup time, $\overline{BIO}\downarrow$ before CLKOUT \downarrow	50			40			ns



SPRS009C-JANUARY 1987-REVISED JULY 1991

electrical characteristics over specified temperature range (unless otherwise noted)

	PARAMETER	TEST CONDITIONS N		TYP [†]	MAX	UNIT
ICC [‡]	Supply current	f = 14.4, MHz, V _{CC} = 5.5 V, T _A = 0°C to 70°C		28	65	mA

[†] All typical values are at $T_A = 70^{\circ}$ C and are used for thermal resistance calculations.

[‡]I_{CC} characteristics are inversely proportional to temperature; i.e., I_{CC} decreases approximately linearly with temperature.

CLOCK CHARACTERISTICS AND TIMING

The TMS320C10-14 can use either its internal oscillator or an external frequency source for a clock.

internal clock option

The internal oscillator is enabled by connecting a crystal across X1 and X2/CLKIN (see Figure 1). The frequency of CLKOUT is one-fourth the crystal fundamental frequency. The crystal should be fundamental mode, and parallel resonant, with an effective series resistance of 30 ohms, a power dissipation of 1 mW, and be specified at a load capacitance of 20 pF.

PARAMETER	TEST CONDITIONS	MIN	NOM	MAX	UNIT
Crystal frequency, f _X	$T_A = 0^{\circ}C$ to $70^{\circ}C$	6.7		14.4	MHz
C1, C2	$T_A = 0^{\circ}C$ to $70^{\circ}C$		10		pF

external clock option

An external frequency source can be used by injecting the frequency directly into X2/CLKIN with X1 left unconnected. The external frequency injected must conform to the specifications listed in the table below.

switching characteristics over recommended operating conditions

		TEST CONDITIONS	MIN	NOM	MAX	UNIT
^t c(C)	CLKOUT cycle time§		277.78			ns
tr(C)	CLKOUT rise time	1		10		ns
^t f(C)	CLKOUT fall time	R _L = 825 Ω, C _L = 100 pF,		8		ns
^t w(CL)	Pulse duration, CLKOUT low	(see Figure 2)		131		ns
^t w(CH)	Pulse duration, CLKOUT high]		129		ns
^t d(MCC)	Delay time, CLKIN \uparrow to CLKOUT \downarrow		25¶		60¶	ns

 $t_{c(C)}$ is the cycle time of CLKOUT, i.e., $4t_{c(MC)}$ (4 times CLKIN cycle time if an external oscillator is used). If Values derived from characterization data and not tested.

timing requirements over recommended operating conditions

		MIN	NOM	MAX	UNIT
^t c(MC)	Master clock cycle time	69.5		150	ns
^t r(MC)	Rise time, master clock input		5¶	10¶	ns
^t f(MC)	Fall time, master clock input		5¶	10¶	ns
^t w(MCP)	Pulse duration, master clock	$0.4t_{c(MC)}$ $0.6t_{c(MC)}$		^{6t} c(MC) [¶]	ns
^t w(MCL)	Pulse duration, master clock low, $t_{C(MC)} = 50 \text{ ns}$	20¶		ns	
^t w(MCH)	Pulse duration, master clock high, $t_{C(MC)} = 50$ ns	20¶			ns

 \P Values derived from characterization data and not tested.



SPRS009C-JANUARY 1987-REVISED JULY 1991

MEMORY AND PERIPHERAL INTERFACE TIMING

	PARAMETER	TEST CONDITIONS	MIN N	OM MAX	UNIT
^t d1	Delay time, CLKOUT \downarrow to address bus valid		10†	50	ns
^t d2	Delay time, CLKOUT \downarrow to $\overline{MEN}\downarrow$	1	$1/_{4}t_{c(C)} - 5^{\dagger}$	1/4t _{c(C)} +15	ns
td3	Delay time, CLKOUT↓ to MEN↑	1	-10 [†]	15	ns
^t d4	Delay time, CLKOUT \downarrow to $\overline{DEN}\downarrow$	1	$1/_{4}t_{c(C)} - 5^{\dagger}$	¹ / ₄ t _{c(C)} +15	ns
td5	Delay time, CLKOUT↓ to DEN↑	1	-10†	15	ns
^t d6	Delay time, CLKOUT \downarrow to $\overline{WE}\downarrow$	R _I = 825 Ω,	$1/2t_{C(C)} - 5^{\dagger}$	1/2tc(C)+15	ns
^t d7	Delay time, CLKOUT↓ to WE↑	$C_{L} = 100 pF$	-10†	15	ns
t _{d8}	Delay time, CLKOUT \downarrow to data bus OUT valid	(see Figure 2)		1/4t _{C(C)} +65	ns
t _{d9}	Time after CLKOUT \downarrow that data bus starts to be driven	1	$1/4t_{C(C)} - 5^{\dagger}$		ns
^t d10	Time after CLKOUT \downarrow that data bus stops being driven	1		1/4t _{c(C)} + 40 [†]	ns
t _V	Data bus OUT valid after <code>CLKOUT</code> \downarrow	1	$1/4t_{c(C)} - 10$		ns
^t h(A-WMD)	Address hold time after $\overline{\text{WE}}\uparrow$, $\overline{\text{MEN}}\uparrow$, or $\overline{\text{DEN}}\uparrow$ (see Note 8)		-10†		ns
^t su(A-MD)	Address bus setup time prior to $\overline{MEN}\downarrow$ or $\overline{DEN}\downarrow$]	$1/4t_{C(C)} - 45$		ns

switching characteristics over recommended operating conditions

[†] Values derived from characterization data and not tested.

NOTE 8: For interfacing I/O devices, see Figure 3.

timing requirements over recommended operating conditions

		TEST CONDITIONS	MIN	NOM MAX	UNIT
t _{su(D)}	Setup time, data bus valid prior to <code>CLKOUT</code> \downarrow	R _L = 825 Ω, C _L = 100 pF	50		ns
^t h(D)	Hold time, data bus held valid after CLKOUT \downarrow (see Note 9)	(see Figure 2)	0		ns

NOTE 9: Data may be removed from the data bus upon $\overline{\text{MEN}}$ or $\overline{\text{DEN}}$ preceding CLKOUT \downarrow .



SPRS009C-JANUARY 1987-REVISED JULY 1991

RESET (RS) TIMING

switching characteristics over recommended operating conditions

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
^t d11	Delay time, $\overline{\text{DEN}}\uparrow$, $\overline{\text{WE}}\uparrow$, and $\overline{\text{MEN}}\uparrow$ from $\overline{\text{RS}}$	R _L = 825 Ω, C _L = 100 pF		1/2t _{C(C)} + 50†		ns
^t dis(R)	Data bus disable time after \overline{RS}	(see Figure 2)		1/4t _C ((C)+50 [†]	ns

[†] Values were derived from characterization data and not tested.

timing requirements over recommended operating conditions

		MIN	NOM	MAX	UNIT
^t su(R)	Reset (\overline{RS}) setup time prior to CLKOUT (see Note 10)	50			ns
^t w(R)	RS pulse duration	5t _{c(C)}			ns

NOTE 10: RS can occur anytime during a clock cycle. Time given is minimum to ensure synchronous operation.

INTERRUPT (INT) TIMING

timing requirements over recommended operating conditions

		MIN	NOM	MAX	UNIT
^t f(INT)	Fall time, INT			15	ns
^t w(INT)	Pulse duration, INT	^t c(C)			ns
t _{su} (INT)	Setup time, INT↓ before CLKOUT↓	50			ns

IO (BIO) TIMING

timing requirements over recommended operating conditions

		MIN	NOM	MAX	UNIT
^t f(IO)	Fall time, BIO			15	ns
^t w(IO)	Pulse duration, BIO	^t c(C)			ns
t _{su(IO)}	Setup time, $\overline{BIO}\downarrow$ before CLKOUT \downarrow	50			ns




SPRS009C-JANUARY 1987-REVISED JULY 1991


TIMING DIAGRAMS

Timing measurements are referenced to and from a low voltage of 0.8 volts and a high voltage of 2 volts, unless otherwise noted.

clock timing




 $^{\dagger}\,t_{d(MCC)}$ and $t_{w(MCP)}$ are referenced to an intermediate level of 1.5 V on the CLKIN waveform.



memory read timing



SPRS009C-JANUARY 1987-REVISED JULY 1991



Address Bus Valid

Instruction Valid

Instruction Valid

11. Data Input Valid

12. Instruction Valid


8.

9.

10.

- 1. TBLR Instruction Prefetch
- Dummy Prefetch 2.
- 3. Data Fetch
- 4. Next Instruction Prefetch
- 5. Address Bus Valid
- 6. Address Bus Valid

TBLW instruction timing




- TBLW Instruction Prefetch
 Dummy Prefetch
- 3. Next Instruction Prefetch
- 4. Address Bus Valid
- 5. Address Bus Valid
- 6. Address Bus Valid

- Address Bus Valid 7.
- Instruction Valid 8.
- 9. Instruction Valid
- 10. Data Output Valid
- 11. Instruction Valid



SPRS009C-JANUARY 1987-REVISED JULY 1991




- 4. Peripheral Address Valid
- 8. Instruction Valid



SPRS009C-JANUARY 1987-REVISED JULY 1991


reset timing




NOTES: A. RS forces DEN, WE, and MEN high and places data bus D0 through D15 in a high-impedance state. AB outputs (and program counter) are synchronously cleared to zero after the next complete CLK cycle from RSJ.

- B. \overline{RS} must be maintained for a minimum of five clock cycles.
- C. Resumption of normal program will commence after one complete CLK cycle from \overline{RS} [↑].
- D. Due to the synchronization action on RS, time to execute the function can vary dependent upon when RS↑ or RS↓ occur in the CLK cycle.
- E. Diagram shown is for definition purpose only. DEN, WE, and MEN are mutually exclusive.
- F. During a write cycle, RS may produce an invalid write address.

interrupt timing




BIO timing





SPRS009C-JANUARY 1987-REVISED JULY 1991



TYPICAL POWER VS. FREQUENCY GRAPHS


Figure 4. Typical CMOS I_{CC} vs Frequency




SPRS009C-JANUARY 1987-REVISED JULY 1991

Key Features: TMS320C14/E14/P14

- 160-ns Instruction Cycle
- 256 Words of On-Chip Data RAM
- 4K Words of On-Chip Program ROM (TMS320C14)
- 4K Words of On-Chip Program EPROM (TMS320E14/P14)
- One-Time Programmable (OTP) Windowless EPROM Version Available ('320P14)
- EPROM Code Protection for Copyright Security
- External Memory Expansion up to 4K-Words at Full Speed (Microprocessor Mode)
- 16 imes 16-Bit Multipler With 32-Bit Product
- 0 to 16-Bit Barrel Shifter
- Seven Input and Seven Output External Ports
- Bit Selectable I/O Port (16 Pins)
- 16-Bit Bidirectional Data Bus With Greater than 50-Mbps Transfer Rate
- Asynchronous Serial Port
- 15 Internal/External Interrupts
- Event Manager With Capture Inputs and Compare Outputs
- Four Independent Timers [Watchdog, General Purpose (2), Serial Port]
- Four-Level Hardware Stack
- Packaging: 68-Pin PLCC (FN Suffix) or CLCC (FZ Suffix)
- Single 5-V Supply
- Operating Free-Air Temperature ... 0°C to 70°C







SPRS009C-JANUARY 1987-REVISED JULY 1991

introduction

The 'C14/E14/P14 are 16/32-bit single-chip digital signal processing (DSP) microcontrollers that combine the high performance of a DSP with on-chip peripherals. With a 160-ns instruction cycle, these devices are capable of executing up to 6.4 million instructions per second (MIPS). The 'C14/E14/P14 DSPs are ideal for applications such as automotive control systems, computer peripherals, industrial controls, and military command/control system applications.

Control-specific on-chip peripherals include: An event manager with 6 channel PWM D/A/, 6-bit I/O pins, an asynchronous serial port, four 16-bit timers, and internal/external interrupts.

With 4K-words of on-chip ROM, the 'C14 is a mask programmable device. Code is provided by the customer, and TI incorporates the customer's code into the photomask. It is offered in a 68-pin plastic chip carrier package (FN suffix), rated for operation from 0°C to 70°C.

The 'E14 is provided with a 4K-word on-chip EPROM. This EPROM version is excellent for prototyping and for customized applications. It is programmable with standard EPROM programmers. It is offered in a 68-pin (windowed) cerquad package (FZ suffix), rated for operation from 0°C to 70°C.

The 'P14 features a one-time programmable 4K-word on-chip EPROM. The 'P14 is provided in an unprogrammed state and is programmed as if it were a blank 'E14. It is offered in a low-cost, volume-production-oriented, 68-pin plastic leaded chip carrier (PLCC) package (FN suffix), rated for operation from 0°C to 70°C.



SPRS009C-JANUARY 1987-REVISED JULY 1991

Each device can execute programs form either internal (MC/MP=0) or external program memory (MC/MP=1).

For proprietary code security, the 'E14 and 'P14 incorporate an EPROM protect bit (RBIT). If this bit is programmed, the device's internal program memory cannot be accessed by any external means.

PIN		1/0/z†	DESCRIPTION
NAME NO.			ADDRESS/DATA BUSES
A11	5	O/Z	Program memory address bus A11 (MSB) through A0 (LSB) and port addresses PA2 (MSB) through
A10	6		PA0 (LSB). Addresses A11 through A0 are always active and never go to high impedance except
A9	9		during reset. During execution of the IN and OUT instructions, pins 26, 27, and 28 carry the port addresses. Pins A3 through A11 are held high when port accesses are made on pins PA0 through
A8	12		PA2.
A7	13		
A6	14		
A5	20		
A4	21		
A3	25		
A2/PA2	26		
A1/PA1	27		
A0/PA0	28		
D15 MSB	35	I/O/Z	Parallel data bus D15 (MSB) through D0 (LSB). The data bus is always in the high-impedance state
D14	36		except when \overline{WE} is active (low). The data bus is also active when internal peripherals are written to.
D13	39		
D12	40		
D11	43		
D10	46		
D9	49		
D8	50		
D7	57		
D6	58		
D5	59		
D4	60		
D3	61		
D2	62		
D1	63		
D0 LSB	64		
			INTERRUPT AND MISCELLANEOUS SIGNALS
INT	18	I	External interrupt input. The interrupt signal is generated by a high-to-low transition on this pin.
NMI/MC/MP	22	Ι	Non-maskable interrupt. When this pin is brought low, the device is interrupted irrespective of the state of the INTM bit in status register ST.
			Microcomputer/microprocessor select. This pin is also sampled when \overline{RS} is low. If high during reset, internal program memory is selected. If low during reset, external memory will be selected.
WE	15	0	Write enable. When active low, WE indicates that device will output data on the bus.
REN	16	0	Read enable. When active low, REN indicates that device will accept data from the bus.
RS	17	I	Reset. When this pin is low, the device is reset and PC is set to zero.

TERMINAL FUNCTIONS

Continued next page.

[†] Input/Output/High-impedance state.



SPRS009C-JANUARY 1987-REVISED JULY 1991

TERMINAL FUNCTIONS (concluded)


	PIN		1/0/z†	DESCRIPTION
NAME NO.			1/0/21	SUPPLY/OSCILLATOR SIGNALS
CLKOUT	-	19	0	System clock output (one fourth CLKIN frequency).
VCC		4,33	I	5-V supply pins.
V _{SS}		3,34	I	Ground pins.
CLKIN		24	I	Master clock input from external clock source.
				SERIAL PORT AND TIMER SIGNALS
RXD		48	I	Asynchronous mode receive input.
TXD		47	O/Z	Asynchronous mode transmit output.
TCLK1		10	I	Timer 1 clock. If external clock is selected, it serves as clock input to Timer 1.
TCLK2		11	1	Timer 2 clock. If external clock is selected, it serves as clock input to Timer 2.
WDT		23	0	Watchdog timer output. An active low is generated on this pin when the watchdog timer times out
				BIT I/O PINS
IOP15	MSB	29	I/O	16 bit I/O lines that can be individually configured as inputs or outputs and also individually set of
IOP14	mob	30	1,0	reset
IOP13		31		when configured as outputs.
IOP12		32		
IOP11		37		
IOP10		38		
IOP9		41		
IOP8		42		
IOP7		44		
IOP6		45		
IOP5		51		
IOP4		52		
IOP3		53		
IOP2		54		
IOP1		55		
IOP0	LSB	56		
				COMPARE AND CAPTURE SIGNALS
CMP0		8	0	Compare outputs. The states of these pins are determined by the combination of compare and action
CMP1		7		registers.
CMP2		2		
CMP3		1		
CAP0		68	Ι	Capture inputs. A transition on these pins causes the timer register to be captured in FIFO stack
CAP1		67		
CMP4/CA	P2	66	I/O	This pin can be configured as compare output or capture input.
CMP5/CA	P3	65	I/O	This pin can be configured as compare output or capture input.

† Input/Output/High-impedance state.



SPRS009C-JANUARY 1987-REVISED JULY 1991

functional block diagram



architecture

The 'C1x family utilizes a modified Harvard architecture for speed and flexibility. In a strict Harvard architecture, program and data memory lie in two separate spaces, permitting a full overlap of instruction fetch and execution. The 'C1x family's modification of a Harvard architecture allows transfers between program and data spaces, thereby increasing the flexibility of the device. This modification permits coefficients stored in program memory to be read into the RAM, eliminating the need for a separate coefficient ROM. It also makes available immediate instructions and subroutines based on computed values.

32-bit ALU/accumulator

The 'C14/E14/P14 devices contain a 32-bit ALU and accumulator for support of double-precision, twos-complement arithmetic. The ALU is a general-purpose arithmetic unit that operates on 16-bit words taken from the data RAM or derived from immediate instructions. In addition to the usual arithmetic instructions, the ALU can perform Boolean operations, providing the bit manipulation ability required of a high-speed controller.



SPRS009C-JANUARY 1987-REVISED JULY 1991

The accumulator stores the output from the ALU and is often an input to the ALU. It operates with a 32-bit wordlength. The accumulator is divided into a high-order word (bits 31 through 16) and a low-order word (bits 15 through 0). Instructions are provided for storing the high- and low- order accumulator words in memory.

shifters

Two shifters are available for manipulating data. The ALU barrel shifter performs a left-shift of 0 to16 places on data memory words loaded into the ALU. This shifter extends the high-order bit of the data word and zero-fills the low-order bits for twos-complement arithmetic. The accumulator parallel shifter performs a left-shift of 0, 1, or 4 places on the entire accumulator and places the resulting high-order accumulator bits into data RAM. Both shifters are useful for scaling and bit extraction

16×16 -bit parallel multiplier

The multiplier performs a 16×16 -bit twos-complement multiplication with a 32-bit result in a single instruction cycle. The multiplier consists of three units: the T Register, P Register, and the multiplier array. The 16-bit T Register temporarily stores the multiplicand; the P Register stores the 32-bit product. Multiplier values either come from the data memory or are derived immediately from the MPYK (multiply immediate) instruction word. The fast on-chip multiplier allows the device to perform fundamental operations such as convolution, correlation, and filtering.

data and program memory

Since the 'C14/E14/P14 devices use a Harvard architecture, data and program memory reside in two separate spaces. These devices have 256 words of on-chip data RAM and 4K words of on-chip program ROM ('C14) or EPROM ('E14 and the OTP 'P14). The EPROM cell utilizes standard PROM programmers and is programmed identically to a 64K-bit CMOS EPROM (TMS27C64).

program memory expansion

The 'C1x devices are capable of executing up to 4K words of external memory at full speed for those applications requiring external program memory space. This allows for external RAM-based systems to provide multiple functionality.

microcomputer/microprocessor operating modes

The 'C14/E14/P14 devices offer two modes of operation defined by the state of the NMI/MC/MP pin during reset: the microcomputer mode (NMI/MC/MP is high) or the microprocessor mode (NMI/MC/MP is low). In the microcomputer mode, the on-chip ROM is mapped into the program memory space. In the microprocessor mode, all 4K words of memory are external.

interrupts and subroutines

The 'C14/E14/P14 devices contain a four-level hardware stack for saving the contents of the program counter during interrupts and subroutine calls. Instructions are available for saving the complete context of the device. PUSH and POP instructions permit a level of nesting restricted only by the amount of available RAM. The 'C14/E14/P14 have a total of 15 internal/external interrupts. Fourteen of these are maskable; NMI is the fifteenth.

input/output

The 16-bit parallel data bus can be utilized to access external peripherals. However, only the lower three address lines are active. The upper nine address lines are driven high.

bit I/O

The 'C14/E14/P14 has 16 pins of bit I/O that can be individually configured as inputs or outputs. Each of the pins can be set or cleared without affecting the others. The input pins can also detect and match patterns and generate a maskable interrupt signal to the CPU.

serial port

The 'C14/E14/P14 includes an I/O-mapped asynchronous serial port.



SPRS009C-JANUARY 1987-REVISED JULY 1991

event manager

An event manager is included that provides up to four capture inputs and up to six compare outputs. This peripheral operates with the timers to provide a form of programmable event logging/detection. The six compare outputs can also be configured to produce six channels of high precision PWM.

timers 1 and 2

Two identical 16-bit timers are provided for general purpose applications. Both timers include a 16-bit period register and buffer latch, and can generate a maskable interrupt.

serial port timer

The serial port timer is a 16-bit timer primarily intended for baud rate generation for the serial port. Its architecture is the same as timers 1 and 2, therefore it can serve as a general purpose timer if not needed for serial communication.

watchdog timer

The 'C14/E14/P14 contain a 16-bit watchdog timer that can produce a timeout (WDT) signal for various applications such as software development and event monitoring. The watchdog timer also generates, at the point of the timeout, a maskable interrupt signal to the CPU.

instruction set

A comprehensive instruction set supports both numeric-intensive operations, such as signal processing, and general-purpose operations, such as high-speed control. All of the first-generation devices are object-code compatible and use the same 60 instructions. The instruction set consists primarily of single-cycle single-word instructions, permitting execution rates of more than six million instructions per second. Only infrequently used branch and I/O instructions are multicycle. Instructions that shift data as part of an arithmetic operation execute in a single cycle and are useful for scaling data in parallel with other operations.

NOTE

The BIO pin on other 'C1x devices is not available for use in the 'C14/E14/P14 devices. An attempt to execute the BIOZ (Branch on BIO low) instruction will result in a two cycle NOP action.

Three main addressing modes are available with the instruction set: direct, indirect, and immediate addressing.

direct addressing

In direct addressing, seven bits of the instruction word concatenated with the 1-bit data page pointer from the data memory address. This implements a paging scheme in which each page contains 128 words.

indirect addressing

Indirect addressing forms the data memory address from the least-significant eight bits of one of the two auxiliary registers, AR0 and AR1. The Auxiliary Register Pointer (ARP) selects the current auxiliary register. The auxiliary registers can be automatically incremented or decremented and the ARP changed in parallel with the execution of any indirect instruction to permit single-cycle manipulation of data tables. Indirect addressing can be used with all instructions requiring data operands, except for the immediate operand instructions.

immediate addressing

Immediate instructions derive data from part of the instruction word rather than from part of the data RAM. Some useful immediate instructions are multiply immediate (MPYK), load accumulator immediate (LACK), and load auxiliary register immediate (LARK).



SPRS009C-JANUARY 1987-REVISED JULY 1991

electrical specifications

This section contains all the electrical specifications for the 'C14/E14/P14 devices, including test parameter measurement information. Parameters with $_{PP}$ subscripts apply only to the 'E14 and 'P14 in the EPROM programming mode.

absolute maximum ratings over specified temperature range (unless otherwise noted)[†]

Supply voltage range, V _{CC} (see Note 6) –0.3 V to 7 V
Supply voltage range, V _{PP} (see Note 6) –0.6 V to 14 V
Input voltage range
Output voltage range
Continuous power dissipation
Air temperature range above operating device: L version
Storage temperature $-55 \degree C + 150 \degree C$

† Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only, and functional operation of the device at these or any other conditions beyond those indicated in the "Recommended Operating Conditions" section of this specification is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability. NOTE 6: All voltage values are with respect to V_{SS}.

recommended operating conditions

			MIN	NOM	MAX	UNIT
		Operating voltage	4.75	5	5.25	V
Vcc	Supply voltage	Fast programming	5.75	6	6.25	V
		SNAP! Pulse programming	6.25	6.5	6.75	V
VPP	/PP Supply voltage for Fast programming (see Note 11)				12.75	V
VPP	Supply voltage for SNAP! Pulse programming (see Note 11)			13	13.25	V
VSS	Supply voltage			0		V
Maria	High-level input voltage	CLKIN, CAP0, CAP1, CMP4/CAP2, CMP5/CAP3, RS	3			Ň
VIH		All remaining inputs	2			V
VIL	Low-level input voltage, all inputs				0.8	V
ЮН	High-level output current, all outputs				-300	μΑ
IOL	Low-level output current, all outputs				2	mA
Т _А	Operating free-air temperature		0		70	°C

NOTE 11: VPP can be applied only to programming pins designed to accept VPP as an input. During programming the total supply current is IPP + I_{CC}.



SPRS009C-JANUARY 1987-REVISED JULY 1991

PARAMETER			TES	MIN	TYP†	MAX	UNIT	
Varia		ltogo	IOH = MAX		2.4	3		V
Vон	High-level output vo	Jilage	I _{OH} = 20 μA (see N	lote 7)	V _{CC} – 0.4 [†]			V
VOL	Low-level output vo	Itage	I _{OL} = MAX			0.3	0.5	V
107		togo	VCC = MAX	V _O = 2.4 V			20	
IOZ	Off-state output voltage		VCC = MAX	V _O = 0.4 V			-20	μA
1.	Input current			All other inputs except CLKIN			±20	
lj			VI = VSS to VCC CLKIN	CLKIN			±50	μA
ICC §	Supply current		f = 25.6 MHz, V _{CC}	= 5.25 V, $T_A = 0^{\circ}C$ to $70^{\circ}C$		70	90	mA
IPP1	Vpp supply current		VPP = VCC = 5.5 \	1			100	μΑ
IPP2	VPP supply current (during program pu		Vpp = 13 V			30	50	mA
<u>^</u>		Data bus				25‡		
Cl	Input capacitance	All others]			15‡		pF
0	Output	Data bus	f = 1 MHz, All othe	r pins 0 V		25‡		
CO capacitance		All others	rs			10‡		pF

electrical characteristics over specified temperature range (unless otherwise noted)


[†] All typical values are at $V_{CC} = 5 \text{ V}$, $T_A = 25^{\circ}\text{C}$, except I_{CC} at 70°C.


[‡] Values derived from characterization data and not tested.

 $\$ I_CC characteristics are inversely proportional to temperature.

NOTE 7: This voltage specification is included for interface to HC logic. However, note that all of the other timing parameters defined in this data sheet are specified for TTL logic levels and will differ for HC logic levels.

PARAMETER MEASUREMENT INFORMATION





EXTERNAL CLOCK REQUIREMENTS

The TMS320C14/E14/P14 use an external frequency source for a clock. This source is applied to the CLKIN pin, and must conform to the specifications in the table below.

PARAMETERS	TEST CONDITIONS	MIN	NOM	MAX	UNIT
CLKIN Input clock frequency	$T_A = 0^{\circ}C$ to $70^{\circ}C$	6.7		25.6	MHz



SPRS009C-JANUARY 1987-REVISED JULY 1991

CLOCK TIMING

switching characteristics over recommended operating conditions

	PARAMETER	TEST CONDITIONS	MIN	NOM	MAX	UNIT
^t c(C)	CLKOUT cycle time [‡]		156.25		600	ns
^t r(C)	CLKOUT rise time	D 005 0		10†		ns
^t f(C)	CLKOUT fall time	R _L = 825 Ω, C _L = 100 pF,		8†		ns
^t w(CL)	Pulse duration, CLKOUT low	(see Figure 2)		72†		ns
^t w(CH)	Pulse duration, CLKOUT high	1		70†		ns
^t d(MCC)	Delay time CLKIN \uparrow to CLKOUT \downarrow	1		45†		ns

[†] Values were derived from characterization data and not tested.

timing requirements over recommended operating conditions

		MIN	NOM	MAX	UNIT
^t c(MC)	Master clock cycle time‡	39.06	40	150	ns
^t r(MC)	Rise time, master clock input		5†	10†	ns
^t f(MC)	Fall time, master clock input		5†	10†	ns
^t w(MCP)	Pulse duration, master clock	0.45 c(MC) [†]		0.55 _{C(MC)} †	ns
^t w(MCL)	Pulse duration, master clock low		15†	130	ns
^t w(MCH)	Pulse duration, master clock high		15†	130	ns

[†] Values were derived from characterization data and not tested. [‡] t_{C(C)} is the cycle time of CLKOUT, i.e., $4t_{C(MC)}$ (4 times CLKIN cycle time if an external oscillator is used).



SPRS009C-JANUARY 1987-REVISED JULY 1991

MEMORY READ AND INSTRUCTION TIMING

switching characteristics over recommended operating conditions

	PARAMETER	TEST CONDITIONS	MIN	NOM	МАХ	UNIT
^t su(A)R	Address bus valid before $\overline{REN}\downarrow$		0.25 t _{C(C)} -39			ns
^t su(A)W	Address bus valid before $\overline{WE} \downarrow$		0.50 t _{C(C)} -45			ns
^t h(A)	Address bus valid after \overline{REN} or \overline{WE}		5†			ns
^t en(D)W	Data starts being driven before $\overline{WE} \downarrow$				0.25 t _{c(C)} †	ns
^t su(D)W	Data valid prior to $\overline{WE} \downarrow$	RL = 825 Ω,	0.25 t _{C(C)} -45			ns
^t h(D)W	Data valid after WE↑	C _L = 100 pF, (see Figure 2)	0.25 t _{C(C)} -10			ns
^t dis(D)W	Data in high impedance after \overline{WE}^\uparrow	()		C).25 t _{C(C)} + 25†	ns
^t w(WEL)	WE-low duration		0.50 t _{c(C)} -15			ns
^t w(RENL)	REN-low duration		0.75 t _{C(C)} -15			ns
trec(WE)	Write recovery time, time between $\overline{\text{WE}}\uparrow$ and $\overline{\text{REN}}\downarrow$		0.25 t _{C(C)} -5			ns
^t rec(REN)	Read recovery time, time between $\overline{\text{REN}} \uparrow$ and $\overline{\text{WE}} \downarrow$		0.50 t _{C(C)} -10			ns
^t d(WE-CLK)	Time from WE↑ to CLKOUT↑		0.50 t _{C(C)} -15			ns

[†] Values were derived from characterization data and not tested.

timing requirements over recommended operating conditions

		TEST CONDITIONS	MIN	NOM	MAX	UNIT
^t su(D)R	Data set-up prior to REN↑		52			ns
^t h(D)R	Data hold after REN↑	PL - 825 O	0			ns
^t a(A)	Access time for read cycle data valid after valid address	R _L = 825 Ω, C _L = 100 pF, (see Figure 2)			t _{c(C)} -90	ns
toe(REN)	Access time for read cycle from $\overline{\text{REN}}\downarrow$				0.75 t _{c(C)} -60	ns
^t dis(D)R	Data in high impedance after \overline{REN}^\uparrow				0.25 t _{c(C)} †	ns

RESET (RS) TIMING

switching characteristics over recommended operating conditions

	PARAMETER	TEST CONDITIONS	MIN	NOM	MAX	UNIT
^t d(RS-RW)	Delay from $\overline{RS}\downarrow$ to $\overline{REN}\uparrow$ and $\overline{WE}\uparrow$				0.75 t _{C(C)} + 20†	ns
^t dis(RS-RW)	Delay from RS↓ to REN and WE into high impedance	R _L = 825 Ω, C _L = 100 pF,			1.25 t _{c(C)} †	ns
^t dis(RS-DB)	Data bus disable after $\overline{RS}\downarrow$	(see Figure 2)			1.25 t _{c(C)} †	ns
^t dis(RS-AB)	Address bus disable after $\overline{RS}\downarrow$	1			t _{c(C)} †	ns
ten(RS-AB)	Address bus enable after \overline{RS}				t _{c(C)} †	ns

timing requirements over recommended operating conditions

		TEST CONDITIONS	MIN	NOM	MAX	UNIT
^t su(RS)	\overline{RS} setup prior to CLKOUT \downarrow (see Note 10)	R _L = 825 Ω, C _L = 100 pF,	60			ns
^t w(RS)	RS pulse duration	(see Figure 2)	5t _{c(C)}			ns

NOTE 10: RS can occur anytime during the clock cycle. Time given is minimum to ensure synchronous operation.



SPRS009C-JANUARY 1987-REVISED JULY 1991

MICROCOMPUTER/MICROPROCESSOR MODE (NMI/MC/MP)

timing requirements over recommended operating conditions

	MIN	NOM	MAX	UNIT
$t_{h(MC/MP)}$ Hold time after \overline{RS} high	tc(C)			ns

[†] Values were derived from characterization data and not tested.

[‡] Hold time to put device in microprocessor mode.

INTERRUPT (INT)/NONMASKABLE INTERRUPT (NMI)

timing requirements over recommended operating conditions

		MIN	NOM	MAX	UNIT
^t f(INT)	Fall time, INT			15†	ns
^t f(NMI)	Fall time, NMI			15†	ns
^t w(INT)	Pulse duration, INT	^t c(C)			ns
^t w(NMI)	Pulse duration, MI	^t c(C)			ns
^t su(INT)	Setup time, INT before CLKOUT low (see Note 12)	60			ns
t _{su(NMI)}	Setup time, NMI before CLKOUT low (see Note 12)	60			ns

NOTE 12: INT and NMI are synchronous inputs and can occur at any time during the cycle. NMI and INT are edge triggered only.

BIT I/O TIMING

switching characteristics over recommended operating conditions

	PARAMETER	TEST CONDITIONS	MIN	NOM	MAX	UNIT
^t rfo(IOP)	Rise and fall time outputs	R _L = 825 Ω, C _L = 100 pF,			20†	ns
^t d(IOP)	CLKOUT low to data valid outputs	(see Figure 2)			0.75 t _{c(C)} +80	ns

timing requirements over recommended operating conditions

	TEST CONDITIONS	MIN	NOM	MAX	UNIT
t _{rfl(IOP)} Rise and fall time inputs	R ₁ = 825 Ω,			20†	ns
t _{su(IOP)} Data setup time before CLKOUT time	$C_{L} = 100 \text{ pF},$	40			ns
tw(IOP) Input pulse duration	(see Figure 2)	tc(C)			ns

GENERAL PURPOSE TIMERS

timing requirements over recommended operating conditions

		TEST CONDITIONS	MIN	NOM	MAX	UNIT
^t r(TIM)	TCLK1, TCLK2 rise time	R _L = 825 Ω,			20†	ns
^t f(TIM)	TCLK1, TCLK2 fall time				20†	ns
^t wl(TIM)	TCLK1, TCLK2 low time	CL = 100 pF, (see Figure 2)	t _{c(C)} +20			ns
^t wh(TIM)	TCLK1, TCLK2 high time	(see Figure 2)	t _{c(C)} +20			ns
^t clk(TIM)	Input pulse duration		$2t_{c(C)} + 40$			ns

[†] Values were derived from characterization data and not tested.



SPRS009C-JANUARY 1987-REVISED JULY 1991

WATCHDOG TIMER TIMING

switching characteristics over recommended operating conditions

	PARAMETER	TEST CONDITIONS	MIN	NOM	MAX	UNIT
^t f(WDT)	Fall time, WDT	R _I = 825 Ω,			20†	ns
^t d(WDT)	CLKOUT to WDT valid	$C_{L} = 100 \text{ pF},$	0.25 t _{C(C)} +20			ns
^t w(WDT)	WDT output pulse duration	(see Figure 2)	7 t _{c(C})			ns

EVENT MANAGER TIMER

switching characteristics over recommended operating conditions

	PARAMETER	TEST CONDITIONS	MIN	NOM	MAX	UNIT
^t f(CMP)	Fall time, CMP0-CMP5	$R_L = 825 \Omega,$			20†	ns
^t r(CMP)	Rise time, CMP0-CMP5	C _L = 100 pF, (see Figure 2)			20†	ns

timing requirements over recommended operating conditions

		TEST CONDITIONS	MIN	NOM	MAX	UNIT
^t w(CAP)	CAP0-CAP3 input pulse duration	R _L = 825 Ω, C _L = 100 pF,	t _{c(C)} +20			ns
t _{su} (CAP)	Capture input setup time before CLKOUT low	(see Figure 2)	20†			ns

[†] Values were derived from characterization data and not tested.




SPRS009C-JANUARY 1987-REVISED JULY 1991

TIMING DIAGRAMS


Timing measurements are referenced to and from a low voltage of 0.8 volts and a high voltage of 2 volts, unless otherwise noted.

clock timing



 $t_{d(MCC)}$ and $t_{w(MCP)}$ are referenced to an intermediate level of 1.5 V on the CLKIN waveform.


memory read timing





SPRS009C-JANUARY 1987-REVISED JULY 1991


TBLR instruction timing



Legend:

- 1. TBLR Instruction Prefetch 7. Address Bus Valid
- 2. Dummy Prefetch 8.
- 3. Data Fetch
- Address Bus Valid Instruction Input Valid 9.
- 4. Next Instruction Prefetch 10. Instruction Input Valid
- 5. Address Bus Valid 11.
- 6. Address Bus Valid
- Data Input Valid 12. Instruction Input Valid


TBLW instruction timing




- 5. Address Bus Valid 6. Address Bus Valid
- 11. Instruction Input Valid



SPRS009C-JANUARY 1987-REVISED JULY 1991



- 1. IN Instruction Prefetch
- Data Fetch
 Next Instruction Prefetch
- 6. Address Bus Valid
- 7. Instruction Input Valid
 - Bata Input Valid
 Instruction Input Valid
- 4. Address Bus Valid
- 5. Peripheral Address Valid




Legend:

- 1. OUT Instruction Prefetch
- 2. Next Instruction Prefetch
- 3. Address Bus Valid
 - alid 7. Data
- 4. Peripheral Address Valid
- Address Bus Valid
 Instruction Input Valid
- Instruction input va 7. Data Output Valid
- 7. Data Output v



SPRS009C-JANUARY 1987-REVISED JULY 1991


reset timing



NOTES: A. RS forces REN, and WE high and then places data bus D0-D15, REN, WE, and address bus A0-A11 in a high-impedance state. AB outputs (and program counter) are synchronously cleared to zero after the next complete CLK cycle from RS[↑].


- B. RS must be maintained for a minimum of five clock cycles.
- C. Resumption of normal program will commence after one complete CLK cycle from \overline{RS} [↑].
- D. Due to the synchronization action on RS, time to execute the function can vary dependent upon when RS↑ or RS↓ occur in the CLK cycle.
- E. Diagram shown is for definition purpose only. WE and REN are mutually exclusive.

microcomputer/microprocessor mode timing






SPRS009C-JANUARY 1987-REVISED JULY 1991





SPRS009C-JANUARY 1987-REVISED JULY 1991

event manager





SPRS009C-JANUARY 1987-REVISED JULY 1991

PROGRAMMING THE TMS320E14/P14 EPROM CELL

The 'E14 and 'P14 include a $4K \times 16$ -bit industry-standard EPROM cell for prototyping and low-volume production. The 'C14 with a 4K-word masked ROM then provides a migration path for cost-effective production. An EPROM adapter socket (part # TMDX3270110), shown in Figure 5, is available to provide 68-pin to 28-pin conversion for programming the 'E14 and 'P14.

Key features of the EPROM cell include the normal programming operation as well as verification. The EPROM cell also includes a code protection feature that allows code to be protected against copyright violations.

The 'E14/P14 EPROM cells are programmed using the same family and device codes as the TMS27C64 8K \times 8-bit EPROM. The TMS27C64 EPROM series are ultraviolet-light erasable, electrically programmable, read-only memories, fabricated using HVCMOS technology. They are pin compatible with existing 28-pin ROMs and EPROMs. These EPROMs operate from a 5-V supply in the read mode; however, a 12.5-V supply is needed for programming. All programming signals are TTL level. For programming outside the system, existing EPROM programmers can be used. Locations may be programmed singly, in blocks, or at random.




Figure 5. EPROM Adapter Socket

The 'E14/P14 devices use 13 address lines to address the 4K-word memory in byte format (8K-byte memory). In word format, the most-significant byte of each word is assigned an even address and the least-significant byte an odd address in the byte format. Programming information should be downloaded to EPROM programmer memory in a high-byte to low-byte order for proper programming of the devices (see Figure 6).



SPRS009C-JANUARY 1987-REVISED JULY 1991






Figure 7 shows the wiring conversion to program the 'E14 and 'P14 using the 28-pin pinout of the TMS27C64. The table of pin nomenclature provides a description of the TMS27C64 pins.

CAUTION

The 'E14 and 'P14 do not support the signature mode available with some EPROM programmers. The signature mode places high voltage (12.5 V_{dc}) on pin A9. The 'E14 and 'P14 EPROM cells are not designed for this feature and will be damaged if subjected to it. A 3.9 k Ω resistor is standard on the TI programmer socket between pin A9 and programmer. This protects the device from unintentional use of the signature mode.




Figure 7. TMS320E14/P14 EPROM Programming Conversion to TMS27C64 EPROM Pinout



SPRS009C-JANUARY 1987-REVISED JULY 1991

NAME	I/O	DEFINITION
A12(MSB)-A0(LSB)	I	On-chip EPROM programming address lines
CLKIN	I	Clock oscillator input
Ē	1	EPROM chip enable
EPT	I	EPROM test mode select
G	I	EPROM output enable
GND	I	Ground
PGM	I	EPROM write/program select
Q8(MSB)-Q1(LSB)	I/O	Data lines for byte-wide programming of on-chip 8K bytes of EPROM
RS	I	Reset for initializing the device
VCC	1	5-V to 6.5-V power supply
V _{PP}	I	12.5-V to 13-V power supply

TERMINAL FUNCTIONS (TMS320E14/P14)

Table 4 shows the programming levels required for programming, verifying, reading, and protecting the EPROM cell.

SIGNAL NAME [†]	TMS320E14/P14 PIN	TMS27C64 PIN	PROGRAM	PROGRAM VERIFY	READ	EPROM PROTECT	PROTECT VERIFY
E	19	20	VIL	VIL	VIL	VIH	VIL
G	23	22	VIH	PULSE	PULSE	VIH	VIL
PGM	16	27	PULSE	VIH	VIH	VIH	VIH
V _{PP}	18	1	V _{PP}	V _{PP}	V _{CC}	V _{PP}	V _{CCP}
V _{CC}	4,33	28	VCCP	VCCP	V _{CC}	VCCP	VCCP
V _{SS}	3,34	14	V _{SS}	V _{SS}	V _{SS}	V _{SS}	V _{SS}
CLKIN	24	14	V _{SS}	V _{SS}	V _{SS}	V _{SS}	V _{SS}
EPT	17	26	V _{SS}	V _{SS}	V _{SS}	VPP	VPP
Q1-Q8	42, 41, 38, 37, 32-29	11–13, 15-19,	Data In	Data Out	Data Out	$Q_8 = \overline{PULSE}$	Q ₈ = RBIT
A12-A7	15, 11, 10, 8, 7, 2	2, 23, 21, 24, 25, 3	ADDR	ADDR	ADDR	х	х
A6	1	4	ADDR	ADDR	ADDR	Х	VIL
A5	68	5	ADDR	ADDR	ADDR	Х	Х
A4	67	6	ADDR	ADDR	ADDR	VIH	Х
A3-A0	66, 65, 56, 55	7-10	ADDR	ADDR	ADDR	Х	Х

Table 4. TMS320E14/P14 Programming Mode Levels

[†] Signal names shown for 'E14/P14 EPROM programming mode only.

Legend:

 $V_{IH} = TTL \text{ high level; } V_{IL} = TTL \text{ low level; ADDR} = byte \text{ address bit; } V_{PP} = 12.5 \text{ V} \pm 0.25 \text{ V} \text{ (FAST) or } 13 \text{ V} \pm 0.25 \text{ V} \text{ (SNAP! Pulse)}.$

 $V_{CC} = 5 V \pm 0.25 V$; X = don't care; \overline{PULSE} = low-going TTL pulse.

 D_{IN} = byte to be programmed at ADDR; Q_{OUT} = byte stored at ADDR.; RBIT = ROM protect bit V_{CCP} = 6 V ± 0.25 V (FAST) or 6.5 V ± 0.25 V (SNAP! Pulse).

programming

Since every memory in the cell is at a logic high, the programming operation reprograms selected bits to low. Once the '320E14 is programmed, these bits can only be erased using ultraviolet light. The correct byte is placed on the data bus with V_{PP} set to the 12.5-V level. The \overline{PGM} pin is then pulsed low to program in the zeros.



SPRS009C-JANUARY 1987-REVISED JULY 1991

erasure

Before programming, the 'E14 must be erased by exposing it to ultraviolet light. The recommended minimum exposure dose (UV-intensity \times exposure-time) is 15 W•s/cm². A typical 12-mW•s/cm², filterless UV lamp will erase the device in 21 minutes. The lamp should be located about 2.5 cm above the chip during erasure. After exposure, all bits are in the high state.

verify/read

To verify correct programming, the EPROM cell can be read using either the verify or read line definitions shown in Table 5, assuming the inhibit bit (RBIT) has not been programmed.

program inhibit

Programming may be inhibited by maintaining a high level input on the \overline{E} pin or \overline{PGM} pin.

standard programming procedure

Before programming, the 'E14 must first be completely erased. The device can then be programmed with the correct code. It is advisable to program unused sections with zeros as a further security measure. After the programming is complete, the code programmed into the cell should be verified. If the cell passes verification, the next step is to program the ROM protect bit (RBIT). Once the RBIT programming is verified, an opaque label should be placed over the window to protect the EPROM cell from inadvertent erasure by ambient light. At this point, the programming is complete, and the device is ready to be placed into its destination circuit.

Refer to other appendices of the TMS320C1x User's Guide for additional information on EPROM programming.


recommended timing requirements for programming: V_{CC} = 6 V and V_{PP} = 12.5 V (FAST) or V_{CC} = 6.5 V and V_{PP} = 13 V (SNAP! PULSE), T_A = 25°C (see Note 13)

			MIN	NOM	MAX	UNIT
		Fast programming algorithm	0.95	1	1.05	ms
^t w(PGM)	Initial program pulse duration	SNAP! Pulse programming algorithm	95	100	105	μs
^t w(FPGM)	Final pulse duration	Fast programming only	2.85		78.75	ms
^t su(A)	Address setup time		2			μs
^t su(E)	E setup time		2			μs
^t su(G)	G setup time		2			μs
^t su(D)	Data setup time		2			μs
^t su(VPP)	VPP setup time		2			μs
^t su(VCC)	V _{CC} setup time		2			μs
^t h(A)	Address hold time		0			μs
^t h(D)	Data hold time		2			μs

NOTE 13: For all switching characteristics and timing measurements, input pulse levels are 0.4 V to 2.4 V and Vpp = 12.5 V ± 0.5 V during programming.



SPRS009C-JANUARY 1987-REVISED JULY 1991



program cycle timing


 $^{\dagger}t_{dis(G)}$ and $t_{en(G)}$ are characteristics of the device but must be accommodated by the programmer.




SPRS009C-JANUARY 1987-REVISED JULY 1991

Key Features: TM320C15/E15/LC15/P15

- Instruction Cycle Timing:
 - 160-ns (TMS320C15-25/E15-25)
 - 200-ns (TMS320C15/E15/P15)
 - 250-ns (TMS320LC15)
- 256 Words of On-Chip Data RAM
- 4K Words of On-Chip Program ROM (TMS320C15/C15-25/LC15)
- 4K Words of On-Chip Program EPROM (TMS320E15/E15-25)
- One-Time Programmable (OTP) Windowless EPROM Version Available (TMS320P15)
- EPROM Code Protection for Copyright Security
- External Memory up to 4K-Words at Full Speed
- 16 × 16-Bit Multiplier With 32-Bit Product
- 0 to 16-Bit Barrel Shifter
- On-Chip Clock Oscillator
- 3.3-V Low-Power Version Available (TMS320LC15)
- Device Packaging:
 - 40-Pin Dip (All Devices)
 - 44-Lead PLCC (TMS320C15/C15-25/LC15/P15)
 - 44-Lead-QUAD (TMS320E15/E15-25)








+5 V

SPRS009C-JANUARY 1987-REVISED JULY 1991

functional block diagram





SPRS009C-JANUARY 1987-REVISED JULY 1991

NAME	ı/o‡	DEFINITION
A11-A0/PA2-PA0	0	External address bus. I/O port address multiplexed over PA2-PA0.
BIO	I.	External polling input
CLKOUT	0	System clock output, 1/4 crystal/CLKIN frequency
D15-D0	I/O	16-bit parallel data bus
DEN	0	Data enable for device input data on D15-D0
INT	I.	External interrupt input
MC/MP	I.	Memory mode select pin. High selects microcomputer mode. Low selects microprocessor mode.
MEN	0	Memory enable indicates that D15-D0 will accept external memory instruction.
NC	0	No connection
RS	I.	Reset for initializing the device
V _{CC}	1	+ 5 V supply
VSS	1	Ground
	0	Write enable for device output data on D15-D0
X1	0	Crystal output for internal oscillator
X2/CLKIN	1	Crystal input internal oscillator or external system clock input

TERMINAL FUNCTIONS (TMS320C15/E15/LC15/P15)[†]

[†] See EPROM programming section.[‡] Input/Output/High-impedance state.



SPRS009C-JANUARY 1987-REVISED JULY 1991

electrical specifications

This section contains the electrical specifications for the 'C15/E15/P15 digital signal processors, including test parameter measurement information. Parameters with PP subscripts apply only to the 'E15/P15 in the EPROM programming mode (see Note 11).

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)[†]

	-
Supply voltage range, V _{CC} (see Note 6)	0.3 V to 7 V
Supply voltage range, V _{PP}	-0.6 V to 14 V
Input voltage range	-0.3 V to 14 V
Output voltage range	0.3 V to 7 V
Continuous power dissipation	0.5 mW
Operating free-air temperature: L suffix	0°C to 70°C
A suffix	– 40°C to 85°C
Storage temperature	-55 °C to 150 °C

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only, and functional operation of the device at these or any other conditions beyond those indicated in the "Recommended Operating Conditions" section of this specification is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
 NOTE 6: All voltage values are with respect to V_{SS}.

recommended operating conditions

			MIN	NOM	MAX	UNIT
Vaa	Supplyveltere	EPROM devices	4.75	5	5 5.25 5 5.5	V
Vcc	Supply voltage	All other devices	4.5	5		V
VPP	Supply voltage (see Note 11)		12.25	12.5	12.75	V
VSS	Supply voltage			0		V
	Lish lovel input veltere	CLKIN	3			V
VIH	High-level input voltage	All remaining inputs	2		0.6	V
VIL	Low-level input voltage	MC/MP			5.25 5.5 12.75 0.6 0.8 - 300 2 70	V
۲IL	Low level input voltage	All remaining inputs				V
IOH	High-level output current, all outputs				- 300	μΑ
IOL	Low-level output current (All outputs except fo	r TMS320LC15)			2	mA
т.	Operating free-air temperature	L suffix	0		70	°C
TA		A suffix	- 40		85	°C

NOTE 11: VPP can be applied only to programming pins designed to accept VPP as an input. During programming the total supply current is IPP + I_{CC}.



SPRS009C-JANUARY 1987-REVISED JULY 1991

electrical characteristics over specified temperature range (unless otherwise noted)

	PARAMETER	२	TEST C	ONDITIONS	MIN	TYP [†]	MAX	UNIT	
Veri	High-level output volta		I _{OH} = MAX		2.4	3		V	
∨он		age	I_{OH} = 20 μ A (see Note 8	3)	V _{CC} - 0.4			V	
VOL	Low-level output voltage	ge	I _{OL} = MAX			0.3	0.5	V	
107	Off-state output curre	nt	V _{CC} = MAX	V _O = 2.4 V			20		
loz	On state output current		V _O = 0.4 V				-20	μA	
	loout ourroot			All inputs except CLKIN			±20		
4	Input current		$V_I = V_{SS}$ to V_{CC}	CLKIN			±50	μΑ	
		TMS320C15	f = 20.5 MHz, V _{CC} = 5.5	5 V, T _A = 0°C to 70°C		45	55		
list	Supply current	TMS320C15-25	f = 25.6 MHz, V_{CC} = 5.5 V, T_A = 0°C to 70°C			50	65		
ICC+	Supply current	TMS320E15	f = 20.5 MHz, V _{CC} = 5.2	25 V, $T_A = -40^{\circ}C$ to $85^{\circ}C$		55	75	mA	
		TMS320E15-25	f = 25.6 MHz, V _{CC} = 5.2	25 V, $T_A = 0^{\circ}C$ to $70^{\circ}C$		65	85		
0	lanut conceltance	Data bus				25‡			
Ci	Input capacitance All other		4	,		15‡		pF	
Co	Output capacitance	Data bus	f = 1 MHz, all other pins 0 V			25‡			
0	Culpul capacitalice	All others				10‡		pF	

[†] All typical values are at V_{CC} = 5 V, T_A = 70°C and are used for thermal resistance calculations.

[‡] I_{CC} characteristics are inversely proportional to temperature. For I_{CC} dependence on temperature, frequency, and loading, see Figure 3.
 NOTE 7: This voltage specification is included for interface to HC logic. However, note that all of the other timing parameters defined in this data sheet are specified for TTL logic levels and will differ for HC logic levels.

CLOCK CHARACTERISTICS AND TIMING

The TMS320C15/E15/P15 can use either its internal oscillator or an external frequency source for a clock.

internal clock option

The internal oscillator is enabled by connecting a crystal across X1 and X2/CLKIN (see Figure 1). The frequency of CLKOUT is one-fourth the crystal fundamental frequency. The crystal should be fundamental mode, and parallel resonant, with an effective series resistance of 30 ohms, a power dissipation of 1 mW, and should be specified at a load capacitance of 20 pF.

PARAMETER		TEST CONDITIONS	MIN	NOM	MAX	UNIT
Crystal frequency, f _X	TMS320C15	$T_A = 0^{\circ}C$ to $70^{\circ}C$	6.7		20.5	
	TMS320E15/P15	$T_A = -40^{\circ}C$ to $85^{\circ}C$	6.7		20.5	MHz
	TMS320C15-25/E15-25	$T_A = 0^{\circ}C$ to $70^{\circ}C$	6.7		25.6	
C1, C2		$T_A = 0^{\circ}C$ to $70^{\circ}C$		10		рF



SPRS009C-JANUARY 1987-REVISED JULY 1991

external clock option

An external frequency source can be used by injecting the frequency directly into X2/CLKIN with X1 left unconnected. The external frequency injected must conform to the specifications listed in the table below.

switching characteristics over recommended operating conditions

	DADAMETED	TEST CONDITIONS	TMS320C15/E15/P15			TMS320C15-25/E15-25			
	PARAMETER	TEST CONDITIONS	MIN	NOM	MAX	MIN	NOM	MAX	UNIT
t _{c(C)}	CLKOUT cycle time [‡]		195.12	200		156.25	160		ns
tr(C)	CLKOUT rise time	D. 005 O		10†			10†		ns
^t f(C)	CLKOUT fall time	R _L = 825 Ω, C _L = 100 pF		8†			8†		ns
tw(CL)	Pulse duration, CLKOUT low	(see Figure 2)		92†			72†		ns
^t w(CH)	Pulse duration, CLKOUT high			90†			70†		ns
td(MCC)	Delay time, CLKIN \uparrow to CLKOUT \downarrow		25†		60†	25†		50†	ns

[†] Values derived from characterization data and not tested.

 $t_{c(C)}$ is the cycle time of CLKOUT, i.e., $4t_{c(MC)}$ (4 times CLKIN cycle time if an external oscillator is used).



SPRS009C-JANUARY 1987-REVISED JULY 1991

timing requirements over recommended operating conditions

		TMS32	0C15/E15	5/P15	TMS320C15-25/E15-25			UNIT
		MIN	NOM	MAX	MIN	NOM	MAX	UNIT
^t c(MC)	Master clock cycle time	48.78	50	150	39.06	40	150	ns
^t r(MC)	Rise time, master clock input		5†	10†		5†	10†	ns
^t f(MC)	Fall time, master clock input		5†	10†		5†	10†	ns
^t w(MCP) [†]	Pulse duration, master clock	0.4t _{c(MC)}	0.6	^t c(MC) [†]	0.45t _C (MC)	0.551	^t c(MC) [†]	ns
^t w(MCL)	Pulse duration, master clock low		20†			15 [†]		ns
^t w(MCH)	Pulse duration, master clock high		20†			15†		ns

[†] Values derived from characterization data and not tested.

MEMORY AND PERIPHERAL INTERFACE TIMING

switching characteristics over recommended operating conditions

		TEST	TMS3	20C15/E	15/P15	TMS3	320C15-25	5/E15-25	
	PARAMETER	CONDITIONS	MIN	NOM	MAX	MIN	NOM	MAX	UNIT
^t d1	Delay time, CLKOUT↓ to address bus valid		10†		50	10‡		40	ns
^t d2	Delay time, CLKOUT \downarrow to $\overline{MEN}\downarrow$	1	1/4t _C (C) ·	- 5† 1/	4t _{c(C)} +15	1/4t _{c(C)}) - 5† 1/	/4t _{c(C)} +12	ns
td3	Delay time, CLKOUT \downarrow to \overline{MEN}	1	-10†		15	-10†		12	ns
^t d4	Delay time, CLKOUT \downarrow to $\overline{DEN}\downarrow$	1	1/4t _{c(C)}	- 5† 1/	4t _{c(C)} +15	¹ /4 ^t c(C)) - 5† 1/	4 ^t c(C)+12	ns
td5	Delay time, CLKOUT \downarrow to \overline{DEN}	1	-10†		15	-10†		12	ns
^t d6	Delay time, CLKOUT \downarrow to $\overline{WE}\downarrow$	1	1/2t _{c(C)} ·	- 5† 1/	2t _{c(C)} +15	1/2t _{c(C)}) - 5† 1/	^{/2t} c(C)+12	ns
td7	Delay time, CLKOUT \downarrow to \overline{WE}	1	-10†		15	-10†		12	ns
^t d8	Delay time, CLKOUT↓ to data bus OUT valid	Rι = 825 Ω,		1/	^{4t} c(C) +65		1/	^{/4t} c(C) +52	ns
t _{d9}	Time after CLKOUT \downarrow that data bus starts to be driven	$C_L = 100 \text{ pF}$ (see Figure 2)	1/4t _{c(C)}	- 5†		1/4t _{c(C)}) - 5†		ns
^t d10	Time after CLKOUT↓ that data bus stops being driven (TMS320C15/C15-25 only)			1/4t	c(C) + 40†		1/4t	c(C) + 40†	ns
^t d10	Time after CLKOUT↓ that data bus stops being driven (TMS320E15/E15-25 only)			1/4t _C	(C) + 70†		1/4	^t c(C) +70 [†]	ns
t _V	Data bus OUT valid after CLKOUT \downarrow	1	1/4t _{c(C)}	- 10		1/4t _{c(C)}) – 10		ns
^t h(A-WMD)	Address hold time after $\overline{WE}\uparrow$, $\overline{MEN}\uparrow$, or $\overline{DEN}\uparrow$ (see Note 15)		0†	2†		0†	2†		ns
^t su(A-MD)	Address bus setup time prior to $\overline{\text{DEN}}\downarrow$		1/4t _{c(C)} -	-45		1/4t _{C(C)})-35		ns

[†] Values derived from characterization data and not tested. NOTE 14: Address bus will be valid upon \overline{WE} , \overline{MEN} , or \overline{DEN} .

timing requirements over recommended operating conditions

		TEST	TMS3	TMS320C15/E15/P15		TMS320C15-25/E15-25			
		CONDITIONS	MIN	NOM	MAX	MIN	NOM	MAX	UNIT
t _{su(D)}	Setup time, data bus valid prior to CLKOU-T \downarrow	R _L = 825 Ω, C _L = 100 pF	50			40			ns
^t h(D)	Hold time, data bus held valid after CLKOUT↓ (see Note 9)	(see Figure 2)	0			0			ns

NOTE 9: Data may be removed from the data bus upon $\overline{MEN}^{\uparrow}$ or $\overline{DEN}^{\uparrow}$ preceding CLKOUT \downarrow .



SPRS009C-JANUARY 1987-REVISED JULY 1991

RESET (RS) TIMING

switching characteristics over recommended operating conditions

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
^t d11	Delay time, $\overline{\text{DEN}}\uparrow$, $\overline{\text{WE}}\uparrow$, and $\overline{\text{MEN}}\uparrow$ from $\overline{\text{RS}}$	R _L = 825 Ω, C _L = 100 pF		1/2tc((C) + 50 [†]	ns
^t dis(R)	Data bus disable time after RS	(see Figure 2)		1/4t _{c(}	(C) + 50 [†]	ns

[†] Values derived from characterization data and not tested.

timing requirements over recommended operating conditions

		TMS	320C15/E1	5/P15	TMS3	20C15-25/E	E15-25	
		MIN	NOM	MAX	MIN	NOM	MAX	UNIT
t _{su(R)}	Reset (RS) setup time prior to CLKOUT (see Note 10)	50			40			ns
^t w(R)	RS pulse duration	5t _{C(C)}			5t _{C(C)}			ns

NOTE 10: RS can occur anytime during a clock cycle. Time given is minimum to ensure synchronous operation.

INTERRUPT (INT) TIMING

timing requirements over recommended operating conditions

		TMS320C15/E15/P15			TMS320C15-25/E15-25			
		MIN	NOM	MAX	MIN	NOM	MAX	UNIT
^t f(INT)	Fall time, INT			15			15	ns
^t w(INT)	Pulse duration, INT	^t c(C)			^t c(C)			ns
^t su(INT)	Setup time, $\overline{INT}\downarrow$ before CLKOUT \downarrow	50			40			ns

IO (BIO) TIMING

timing requirements over recommended operating conditions

		TMS	320C15/E15	5/P15	TMS320C15-25/E15-25			
		MIN	NOM	MAX	MIN	NOM	MAX	UNIT
^t f(IO)	Fall time, BIO			15			15	ns
^t w(IO)	Pulse duration, BIO	^t c(C)			^t c(C)			ns
t _{su(IO)}	Setup time, $\overline{BIO}\downarrow$ before CLKOUT \downarrow	50			40			ns




SPRS009C-JANUARY 1987-REVISED JULY 1991


TIMING DIAGRAMS

Timing measurements are referenced to and from a low voltage of 0.8 volts and a high voltage of 2.0 volts, unless otherwise noted.

clock timing




 $^{\dagger}\,t_{d(MCC)}$ and $t_{w(MCP)}$ are referenced to an intermediate level of 1.5 V on the CLKIN waveform.



memory read timing



SPRS009C-JANUARY 1987-REVISED JULY 1991




Legend:

- 1. TBLW Instruction Prefetch
- 2. Dummy Prefetch
- 3. Next Instruction Prefetch
- 4. Address Bus Valid
- 5. Address Bus Valid
- 6. Address Bus Valid

- 7. Address Bus Valid
- 8. Instruction Valid
- 9. Instruction Valid
- 10. Data Output Valid
- 11. Instruction Valid




SPRS009C-JANUARY 1987-REVISED JULY 1991



- 2. Next Instruction Prefetch
- 3. Address Bus Valid
- 4. Peripheral Address Valid
- 6. Instruction Valid
- 7. Data Output Valid
- 8. Instruction Input Valid




SPRS009C-JANUARY 1987-REVISED JULY 1991




- NOTES: A. RS forces DEN, WE, and MEN high and places data bus D0 through D15 in a high-impedance state. AB outputs (and program counter) are synchronously cleared to zero after the next complete CLK cycle from RS↓.
 - B. RS must be maintained for a minimum of five clock cycles.
 - C. Resumption of normal program will commence after one complete CLK cycle from \overline{RS} [↑].
 - D. Due to the synchronization action on RS, time to execute the function can vary dependent upon when RS↑ or RS↓ occur in the CLK cycle.
 - E. Diagram shown is for definition purpose only. DEN, WE, and MEN are mutually exclusive.
 - F. During a write cycle, RS may produce an invalid write address.

interrupt timing



BIO timing





SPRS009C-JANUARY 1987-REVISED JULY 1991

absolute maximum ratings over specified temperature range (unless otherwise noted)[†]

Supply voltage range, V_{PP} (see Note 6) –0.6 V to 14 V

† Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only, and functional operation of the device at these or any other conditions beyond those indicated in the "Recommended Operating Conditions" section of this specification is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability. NOTE 6: All voltage values are with respect to V_{SS}.

recommended operating conditions

		MIN	NOM	MAX	UNIT
VPP	Supply voltage (see Note 11)	12.25	12.5	12.75	V

NOTE 11: V_{PP} can be applied only to programming pins designed to accept V_{PP} as an input. During programming the total supply current is I_{PP} + I_{CC}.

electrical characteristics over specified temperature range (unless otherwise noted)

PARAMETER	TEST CONDITIONS	MIN	TYP‡	MAX	UNIT
IPP1 VPP supply current	VPP = VCC 5.5 V			100	V
IPP2 VPP supply current (during program pulse)	Vpp = 12.75 V		30	50	V

[‡] All typical values except for I_{CC} are at V_{CC} = 5 V, T_A = 25°C.

recommended timing requirements for programming, $T_A = 25^{\circ}C$, $V_{CC} = 6$, $V_{PP} = 12.5$ V, (see Note 13)

		MIN	NOM	MAX	UNIT
^t w(IPGM)	Initial program pulse duration	0.95	1	1.05	ms
^t w(FPGM)	Final pulse duration	3.8		63	ms
t _{su(A)}	Address setup time	2			μs
^t su(E)	E setup time	2			μs
^t su(G)	G setup time	2			μs
^t dis(G)	Output disable time from \overline{G} (see Note 15)	0		130§	ns
^t en(G)	Output enable time from G	0		150§	ns
^t su(D)	Data setup time	2			μs
t _{su(VPP)}	VPP setup time	2			μs
tsu(VCC)	V _{CC} setup time	2			μs
^t h(A)	Address hold time	0			μs
^t h(D)	Data hold time	2			μs

§ Values derived from characterization data and not tested.

NOTES: 13. For all switching characteristics and timing measurements, input pulse levels are 0.4 V to 2.4 V and V_{PP} = 12.5 V ± 0.5 V during programming.

15. Common test conditions apply for tdis(G) except during programming.



SPRS009C-JANUARY 1987-REVISED JULY 1991

PROGRAMMING THE TMS320E15/P15 EPROM CELL

'E15/P15 devices include a $4K \times 16$ -bit industry-standard EPROM cell for prototyping, early field testing, and low-volume production. In conjunction with this EPROM, the 'E15/P15 with a 4K-word masked ROM, then, provide more migration paths for cost-effective production.

EPROM adapter sockets are available that provide pin-to-pin conversions for programming any 'E15/P15 devices. One adapter socket (part number RTC/PGM320C-06), shown in Figure 8, converts a 40-pin DIP device into an equivalent 28-pin device. Another socket (part number RTC/PGM320A-06), not shown, permits 44- to 28-pin conversion.




Figure 8. EPROM Adapter Socket (40-pin to 28-pin DIP Conversion)


Key features of the EPROM cell include the normal programming operation as well as verification. The EPROM cell also includes a code protection feature that allows code to be protected against copyright violations.

The 'E15/P15 EPROM cell is programmed using the same family and device pinout codes as the TMS27C64 8K \times 8-bit EPROM. The TMS27C64 EPROM series are unltraviolet-light erasable, electrically programmable, read-only memories, fabricated using HVCMOS technology. They are pin-compatible with existing 28-pin ROMs and EPROMs. These EPROMs operate from a single 5-V supply in the read mode; however, a 12.5-V supply is needed for programming. All programming signals are TTL level. For programming outside the system, existing EPROM programmers can be used. Locations may be programmed singly, in blocks, or at random.

Figure 9 shows the wiring conversion to program the 'E15/P15 using the 28-pin pinout of the TMS27C64. Table 5 on pin nomenclature provides a description of the TMS27C64 pins. The code to be programmed into the device should be in serial mode. The 'E15/P15 devices use 13 address lines to address 4K-word memory in byte format.



SPRS009C-JANUARY 1987-REVISED JULY 1991



CAUTION

Although acceptable by some EPROM programmers, the signature mode cannot be used on any 'E1x device. The signature mode will input a high-level voltage (12.5 V_{dc}) onto pin A9. Since this pin is not designed for high voltage, the cell will be damaged. To prevent an accidental application of voltage, Texas Instruments has inserted a 3.9 k Ω resistor between pin A9 of the TI programmer socket and the programmer itself.

Pin Nomenclature (TMS320E15/P15)

NAME	I/O	DEFINITION
A0-A12	1	On-chip EPROM programming address lines
CLKIN		Clock oscillator input
Ē	1	EPROM chip select
EPT		EPROM test mode select
G	1	EPROM read/verify select
GND	1	Ground
PGM	1	EPROM write/program select
Q1-Q8	I/O	Data lines for byte-wide programming of on-chip 8K bytes of EPROM
RS	1 1	Reset for initializing the device
Vcc		5-V power supply
VPP	I	12.5-V power supply

Figure 9. TMS320E15/P15 EPROM Programming Conversion to TMS27C64 EPROM Pinout



SPRS009C-JANUARY 1987-REVISED JULY 1991

Table 5 shows the programming levels required for programming, verifying, reading, and protecting the EPROM cell.

SIGNAL NAME	TMS320E15 PIN	TMS27C64 PIN	PROGRAM	VERIFY	READ	PROTECT VERIFY	EPROM PROTECT
Ē	25	20	VIL	VIL	VIL	VIL	VIH
G	24	22	VIH	PULSE	PULSE	VIL	VIH
PGM	23	27	PULSE	VIH	VIH	VIH	VIH
VPP	3	1	VPP	VPP	VCC	V _{CC} + 1	Vpp
VCC	30	28	VCC	VCC	VCC	V _{CC} + 1	V _{CC} + 1
V _{SS}	10	14	V _{SS}	VSS	VSS	V _{SS}	V _{SS}
CLKIN	8	14	V _{SS}	V _{SS}	V _{SS}	V _{SS}	V _{SS}
RS	4	14	VSS	VSS	VSS	V _{SS}	V _{SS}
EPT	5	26	VSS	VSS	VSS	Vpp	Vpp
Q1-Q8	11-18	11-13, 15-19	D _{IN}	Q _{OUT}	QOUT	Q8=RBIT	Q8=PULSE
A0-A3	2, 1, 40, 39	10-7	ADDR	ADDR	ADDR	Х	Х
A4	38	6	ADDR	ADDR	ADDR	Х	VIH
A5	37	5	ADDR	ADDR	ADDR	Х	Х
A6	36	4	ADDR	ADDR	ADDR	VIL	Х
A7-A9	35, 34, 29	3, 25, 24	ADDR	ADDR	ADDR	Х	Х
A10-A12	28-26	21, 23, 2	ADDR	ADDR	ADDR	Х	Х

Table 5. TMS320E15/P15 Programming Mode Levels

Legend:

 V_{IH} = TTL high level; V_{IL} = TTL low level; ADDR = byte address bit V_{PP} = 12.5 V ± 0.25 V; V_{CC} = 5 V ± 0.25 V; X = don't care

PULSE = low-going TTL level pulse; DIN = byte to be programmed at ADDR

Q_{OUT} = byte stored at ADDR; RBIT = ROM protect bit.

programming

Since every memory bit in the cell is a logic 1, the programming operation reprograms certain bits to 0. Once programmed, these bits can only be erased using ultraviolet light. The correct byte is placed on the data bus with V_{PP} set to the 12.5 V level. The \overrightarrow{PGM} pin is then pulsed low to program in the zeros.

erasure

Before programming, the device must be erased by exposing it to ultraviolet light. The recommended minimum exposure dose (UV-intensity × exposure-time) is 15 W•s/cm². A typical 12-mW/cm², filterless UV lamp will erase the device in 21 minutes. The lamp should be located about 2.5 cm above the chip during erasure. After exposure, all bits are in the high state.

verify/read

To verify correct programming, the EPROM cell can be read using either the verify or read line definitions shown in Table 5, assuming the inhibit bit has not been programmed.

program inhibit

Programming may be inhibited by maintaining a high level input on the \overline{E} pin or \overline{PGM} pin.

read

The EPROM contents may be read independent of the programming cycle, provided the RBIT (ROM protect bit) has not been programmed. The read is accomplished by setting \overline{E} to zero and pulsing \overline{G} low. The contents of the EPROM location selected by the value on the address inputs appear on Q8-Q1.



SPRS009C-JANUARY 1987-REVISED JULY 1991

output disable

During the EPROM programming process, the EPROM data outputs may be disabled, if desired, by establishing the output disable state. This state is selected by setting \overline{G} and \overline{E} pins high. While output disable is selected, Q8-Q1are placed in the high-impedance state.


EPROM protection

To protect the proprietary algorithms existing in the code programmed on-chip, the ability to read or verify code from external accesses can be completely disabled. Programming the RBIT disables external access of the EPROM cell and disables the microprocessor mode, making it impossible to access the code resident in the EPROM cell. The only way to remove this protection is to erase the entire EPROM cell, thus removing the proprietary information. The signal requirements for programming this bit are shown in Table 5. The cell can be determined as protected by verifying the programming of the RBIT shown in the table.

standard programming procedure

Before programming, the device must first be completely erased. Then the device can be programmed with the correct code. It is advisable to program unused sections with zeroes as a further security measure. After the programming is complete, the code programmed into the cell should be verified. If the cell passes verification, the next step is to program the ROM protect bit (RBIT). Once the RBIT programming is verified, an opaque label should be placed over the window to protect the EPROM cell from inadvertent erasure by ambient light. At this point, the programming is complete, and the device is ready to be placed into its destination circuit.

program cycle timing





TMS320LC15 DIGITAL SIGNAL PROCESSOR

SPRS009C-JANUARY 1987-REVISED JULY 1991

absolute maximum ratings over specified temperature range (unless otherwise noted)[†]

Supply voltage range, V _{CC} (see Note 6)	–0.3 V to 4.6 V
Input voltage range	–0.3 V to V _{CC} + 0.5
Output voltage range	$\dots -0.3 \text{ V to V}_{CC} + 0.5$
Continuous power dissipation	
Air temperature range above operating devices: L version	0°C to 70°C
A version	–40°C to 85°C
Storage temperature range	–55°C to +150°C

† Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only, and functional operation of the device at these or any other conditions beyond those indicated in the "Recommended Operating Conditions" section of this specification is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability. NOTE 6: All voltage values are with respect to V_{SS}.

recommended operating conditions

		MIN	NOM	MAX	UNIT	
V _{CC} Supply voltage		3.0	3.3	3.6	V	
V _{SS} Supply voltage			0		V	
VIH	High-level input voltage All input	All inputs except CLKIN	2.0			V
		CLKIN	2.5			V
VIL	Low-level input voltage All inputs				0.55	V
IOH High-level output current (all outputs)				-300	μA	
IOL	IOL Low-level output current (all outputs)				1.5	mA
т _А	Operating free-air temperature	L version	0		70	°C
	A version		-40		85	°C

electrical characteristics over specified temperature range (unless otherwise noted)

PARAMETER			TEST CONDITIONS	MIN	TYP†	MAX	UNIT	
Vou High-level output voltage			I _{OH} = MAX	2.0			V	
			I _{OH} = 20 μA (see Note 7)	V _{CC} - 0.4	ŧ		V	
V _{OL} Low-level output voltage			I _{OL} = MAX			0.5	V	
			$V_{CC} = MAX, V_O = V_{CC}$			20	μΑ	
IOZ	IOZ Off-state ouput current		$V_{O} = V_{SS}$			-20		
	I Input current		$V_I = V_{SS}$ to V_{CC} All inputs except CLKIN			±20		
I Input current			$V_I = V_{SS}$ to V_{CC} CLKIN			±50	μA	
		Data bus			25‡		- 5	
Ci	Input capacitance	All others f = 1 MHz, All other pins 0 V	f = 1 MHz All other pips 0 V		15‡		pF	
Co	Output capacitance	Data bus			25‡		рF	
	Ouipui capacitance	All others			10‡		Ρľ	

[†] All typical values are at $V_{CC} = 3.3$ V, $T_A = 25^{\circ}$ C.


[‡] Values derived from characterization data and not tested.

NOTE 7: This voltage specification is included for interface to HC logic. However, note that all of the other timing parameters defined in this data sheet are specified for TTL logic levels and will differ for HC logic levels.




TMS320LC15 DIGITAL SIGNAL PROCESSOR


SPRS009C-JANUARY 1987-REVISED JULY 1991



INTERNAL CLOCK OPTION



PARAMETER MEASUREMENT INFORMATION







CLOCK CHARACTERISTICS AND TIMING

The 'LC15 can use either its internal oscillator or an external frequency source for a clock.

internal clock option

The internal oscillator is enabled by connecting a crystal across X1 and X2/CLKIN (see Figure 1). The frequency of CLKOUT is one-fourth the crystal fundamental frequency. The crystal should be fundamental mode, and parallel resonant, with an effective series resistance of 30 ohms, a power dissipation of 1 mW, and be specified at a load capacitance of 20 pF.

PARAMETER	TEST CONDITIONS	MIN	NOM	MAX	UNIT
Crystal frequency f _X	$T_A = -40^{\circ}C$ to $85^{\circ}C$			16	MHz
C1, C2			10		рF

external clock option

An external frequency source can be used by injecting the frequency directly into X2/CLKIN with X1 left unconnected. The external frequency injected must conform to the specifications listed in the table below.

switching characteristics over recommended operating conditions

	PARAMETER		MIN	NOM	MAX	UNIT
t _{c(C)}	CLKOUT cycle time [†]		250		1000	ns
tr(C)	CLKOUT rise time	R _L = 825 Ω,		10‡		ns
^t f(C)	CLKOUT fall time	C _L = 100 pF,		8‡		ns
^t w(CL)	Pulse duration, CLKOUT low	(see Figure 2)		117‡		ns
^t w(CH)	Pulse duration, CLKOUT high			115‡		ns
td(MCC)	Delay time, CLKIN \uparrow to CLKOUT \downarrow		20		70	ns

timing requirements over recommended operating conditions

		MIN	NOM	MAX	UNIT
^t c(MC)	Master clock cycle time	62.5		150	ns
^t r(MC)	Rise time, master clock input		5‡	10†	ns
^t f(MC)	Fall time, master clock input		5‡	10†	ns
^t w(MCP)	Pulse duration, master clock	$0.4t_{c(MC)}^{\ddagger}$ $0.6t_{c(MC)}^{\ddagger}$		ns	
^t w(MCL)	Pulse duration, master clock low at $t_{C(MC)}$ min	26		ns	
^t w(MCH)	Pulse duration, master clock high at t _{c(MC)} min	26		ns	

 $t_{c(C)}$ is the cycle time of CLKOUT, i.e., $4t_{c(MC)}$ (4 times CLKIN cycle time if an external oscillator is used) t_{Values} derived from characterization data and not tested.



TMS320LC15 DIGITAL SIGNAL PROCESSOR

SPRS009C-JANUARY 1987-REVISED JULY 1991


electrical characteristics over specified temperature range (unless otherwise noted)

PARAMETER TEST CONDITIONS		MIN	TYP†	MAX	UNIT
ICC [‡]	f = 16.0 MHz, V_{CC} = 3.6 V, T_A = 0°C to 70°C		15	20	mA

[†] All typical values are at $T_A = 70^{\circ}$ C and are used for thermal resistance calculations.

[‡]I_{CC} characteristics are inversely proportional to temperature. For I_{CC} dependence on frequency, see figure below.

typical power vs. frequency graph (outputs unloaded)§



S Device operation is not guaranteed below 4 MHz CLKIN. Graph is for device in RESET; i.e., only clock-out is driven.



SPRS009C-JANUARY 1987-REVISED JULY 1991

MEMORY AND PERIPHERAL INTERFACE TIMING

	PARAMETER	TEST CONDITIONS	MIN	MAX	UNIT
^t d1	Delay time CLKOUT \downarrow to address bus valid		10†	75	n <i>s</i>
^t d2	Delay time CLKOUT \downarrow to $\overline{MEN}\downarrow$]	1/4 t _{c(C)} -5†	1/4 t _{c(C)} +25	ns
td3	Delay time CLKOUT↓ to MEN↑	1	-10†	30	ns
^t d4	Delay time CLKOUT↓ to DEN↓	1	1/4 t _{c(C)} -5†	1/4 t _{c(C)} +25	ns
^t d5	Delay time CLKOUT↓ to DEN↑]	-10†	30	ns
^t d6	Delay time CLKOUT \downarrow to $\overline{WE}\downarrow$	R _L = 825Ω, C _L = 100 pF, (see Figure 2)	1/2 t _{c(C)} -5†	1/2 t _{c(C)} +25	ns
^t d7	Delay time CLKOUT↓ to WE↑		-10†	30	ns
t _{d8}	Delay time CLKOUT \downarrow to data bus OUT valid			1/4 t _{c(C)} +75	ns
t _{d9}	Time after CLKOUT \downarrow that data bus starts to be driven	1	1/4 t _{c(C)} -5 [†]		ns
^t d10	Time after CLKOUT \downarrow that data bus stops being driven	1		1/4 t _{c(C)} +60	ns
t _v	Data bus OUT valid after CLKOUT \downarrow	1	1/4 t _{c(C)} -10		ns
^t h(A-WMD)	Address hold time after WE↑, MEN↑, or DEN↑ (see Note 14)]	0†		ns
t _{su(A-MD)}	Address bus setup time to $\overline{DEN}\downarrow$	1	_ 4†		ns

switching characteristics over recommended operating conditions

[†] Values derived from characterization data and not tested. NOTE 14: Address bus will be valid upon $\overline{WE}\uparrow$, $\overline{MEN}\uparrow$, or $\overline{DEN}\uparrow$.

timing requirements over recommended operating conditions

		TEST CONDITIONS	MIN	NOM	MAX	UNIT
tsu(D)	Setup time data bus valid prior to <code>CLKOUT</code> \downarrow	R _L = 825Ω, C _L = 100 pF.	56			ns
^t h(D)	Hold time, data bus held valid after CLKOUT \downarrow (see Note 9)	(see Figure 2)	0			ns

NOTE 9: Data may be removed from the data bus upon $\overline{\text{MEN}}$ or $\overline{\text{DEN}}$ preceding CLKOUT \downarrow .



SPRS009C-JANUARY 1987-REVISED JULY 1991

RESET (RS**) TIMING**

switching characteristics over recommended operating conditions

		TEST CONDITIONS	MIN	NOM	MAX	UNIT
^t d11	Delay time, $\overline{DEN}\uparrow$, $\overline{WE}\uparrow$, and $\overline{MEN}\uparrow$ from \overline{RS}	R _L = 825Ω, C _L = 100 pF,		1/2t ₀	c(C)+75	ns
tdis(R)	Data bus disable time after RS	(see Figure 2)		1/4t ₀	c(C)+75	ns

[†] These parameters do not apply to this device.

timing requirements over recommended operating conditions

		MIN	NOM	MAX	UNIT
t _{su(R)}	Reset (\overline{RS}) setup time prior to CLKOUT (see Note 10)	85			ns
^t w(R)	RS pulse duration	5t _{c(C)}			ns

NOTE 10: RS can occur anytime during a clock cycle. Time given is minimum to ensure synchronous operation.

INTERRUPT (INT) TIMING

timing requirements over recommended operating conditions

		MIN	NOM	MAX	UNIT
^t F(INT)	Fall time, INT			15	ns
^t w(INT)	Pulse duration, INT	tc(C)			ns
tsu(INT)	Setup time, $\overline{INT} \downarrow$ before CLKOUT \downarrow	85			ns


I/O (BIO) TIMING

timing requirements over recommended operating conditions

		MIN	NOM	MAX	UNIT
t _f (IO)	Fall time BIO			15	ns
t _{w(IO)}	Pulse duration BIO	^t c(C)			ns
t _{su} (IO)	Setup time $\overline{BIO}\downarrow$ before CLKOUT \downarrow	85			ns




SPRS009C-JANUARY 1987-REVISED JULY 1991



 $^{\dagger}\,t_{d(MCC)}$ and $t_{w(MCP)}$ are referenced to an intermediate level of 1.5 V on the CLKIN waveform.

IN instruction timing




Legend:

- IN Instruction Prefetch
 Next Instruction Prefetch
- 5. Address Bus Valid
- Instruction Valid
 Data Input Valid
- Address Bus Valid
 Peripheral Address Valid
- 8. Instruction Valid

TEXAS INSTRUMENTS

SPRS009C-JANUARY 1987-REVISED JULY 1991


OUT instruction timing



Legend:

- 1. OUT Instruction Prefetch 5. Address Bus Valid
- 2. Next Instruction Prefetch
 - Prefetch 6. Instruction Valid d 7. Data Output Valid
- Address Bus Valid
 Peripheral Address Valid
 Ir
 - 8. Instruction Valid


external memory read timing





SPRS009C-JANUARY 1987-REVISED JULY 1991

TBLR instruction timing



Legend:


- 7. Address Bus Valid 1. TBLR Instruction Prefetch
- 2. Dummy Prefetch
- 3. Data Fetch
- 8. Address Bus Valid Instruction Valid 9.

Instruction Valid

- Next Instruction Prefetch
- 4. 5. Address Bus Valid
 - 11. Data Input Valid Instruction Valid 12.

10.

- 6. Address Bus Valid
- **TBLW** instruction timing




Legend:

- 1. TBLW Instruction Prefetch 2. Dummy Prefetch
- 7. Address Bus Valid
- 3. Next Instruction Prefetch
- 4. Address Bus Valid
- 5. Address Bus Valid
- 6. Address Bus Valid
- Instruction Valid 8.
- 9. Instruction Valid
 - 10. Data Output Valid
 - 11. Instruction Valid




SPRS009C-JANUARY 1987-REVISED JULY 1991

reset timing




- NOTES: A. RS forces DEN, WE, and MEN high and places data bus D0 through D15 in a high-impedance state. AB outputs (and program counter) are synchronously cleared to zero after the next complete CLK cycle from RS↓.
 - B. RS must be maintained for a minimum of five clock cycles.
 - C. Resumption of normal program will commence after one complete CLK cycle from \overline{RS} [↑].
 - D. Due to the synchronization action on RS, time to execute the function can vary dependent upon when RS↑ or RS↓ occur in the CLK cycle.
 - E. Diagram shown is for definition purpose only. DEN, WE, and MEN are mutually exclusive.
 - F. During a write cycle, RS may produce an invalid write address.

interrupt timing



BIO timing






SPRS009C-JANUARY 1987-REVISED JULY 1991

Key Features: TMS320C16

- 114-ns Instruction Cycle Time
- 256 Words of On-Chip Data RAM
- 8K Words of On-Chip Program ROM
- 64K Words Total External Memory at Full Speed
- 8 Level Stack
- 32-Bit ALU/Accumulator
- 16 × 16-Bit Multiplier With 32-Bit Product
- 16-Bit Barrel Shifter
- Eight Input and Eight Output Channels
- Simple Memory and I/O Interface:
 Memory Write Enable Signal MWE
 I/O Write Enable Signal IOWE
- Single 5-V Supply
- 64-Pin Quad Flatpack (PG Suffix)
- Operating Free-Air Temperature Range ... 0°C to 70°C





SPRS009C-JANUARY 1987-REVISED JULY 1991

TERMINAL FUNCTIONS

PIN		1/0/z†	DESCRIPTION
NAME	NO.		ADDRESS/DATA BUSES
A15 MSB	32	I/O/Z	Program memory address bus A15 (MSB) through A0 (LSB) and port addresses PA2 (MSB) through
A14	34		PA0 (LSB). Addresses A15 through A0 are always active and never go to high impedance. During
A13	35		execution of the IN and OUT instructions, pins A2 through A0 carry the port addresses. (Address pins A15 through A3 are always driven low on IN and OUT instruction.
A12	36		
A11	37		
A10	38		
A9	39		
A8	40		
A7	41		
A6	43		
A5	44		
A4	45		
A3	46		
A2/PA2	47		
A1/PA1	48		
A0/PA0	49		
D15 MSB	10	I/O/Z	Parallel data bus D15 (MSB) through D0 (LSB). The data bus is always in the high-impedance state
D14	11		except when IOWE or MWE are active (low).
D13	13		
D12	14		
D11	15		
D10	16		
D9	17		
D8	20		
D7	21		
D6	22		
D5	23		
D4	25		
D3	27		
D2	28		
D1	30		
D0 LSB	31		

[†] Input/Output/High-impedance state.



SPRS009C-JANUARY 1987-REVISED JULY 1991

TERMINAL FUNCTIONS (concluded)


	PIN		DESCRIPTION				
NAME	NO.	1/0/Z†	INTERRUPT AND MISCELLANEOUS SIGNALS				
BIO	64	I	External polling input. Polled by BIOZ instruction. If low, the device branches to the address specified by the instruction.				
IOEN	54	0	Data enable for device input data. When active (low), IOEN indicates that the device will accept data from the data bus. IOEN is active only during the IN instruction. When IOEN is active, MEN, IOWE, and MWE will always be inactive (high).				
IOWE	52	0	Write enable for device output data. When active (low), IOWE indicates that data will be output from the device on the data bus. IOWE is active only during the OUT instruction. When IOWE is active, MEN, IOEN, and MWE will always be inactive (high).				
INT	63	I	External interrupt input. The interrupt signal is generated by applying a negative-going edge to the INT pin. The edge is used to latch the interrupt flag register (INTF) until an interrupt is granted by the device. An active low level will also be sensed.				
MC/MP	62	I	Memory mode select pin. High selects the microcomputer mode, in which 8K words of on-chip program memory are available. A low on MC/MP pin enables the microprocessor mode. In this mode, the entire memory space is external; i.e., addresses 0 through 65535.				
MEN	56	0	Memory enable. MEN is an active (low) control signal generated by the device to enable instruction fetches from program memory. MEN will be active on instructions fetched from both internal and external memory. When MEN is active, MWE, IOWE, and IOEN will be inactive (high).				
MWE	53	0	Write enable for device output data. When active (low), MWE indicates that data will be output from the device on the data bus. MWE is active only during the TBLW instruction. When MWE is active, MEN, IOEN, and IOWE will always be inactive (high).				
NC	1, 12, 18, 19, 24, 29, 33, 50, 51, 55	_	No connection.				
RS	2	I	Schmitt-triggered input for initializing the device. When held active for a minimum of five clock cycles. IOEN, IOWE, MWE, and MEN are forced high; and, the data bus (D15 through D0) is not driven. The program counter (PC) and the address bus (A15 through A0) are then synchronously cleared after the next complete clock cycle from the falling edge of RS. Reset also disables the interrupt, clears the interrupt flag register, and leaves the overflow mode register unchanged. The device can be held in the reset state indefinitely.				
	-		SUPPLY/OSCILLATOR SIGNALS				
I	PIN	1/0/z†	DESCRIPTION				
NAME	NO.	1/0/21					
CLKOUT	9	0	System clock output (one-fourth crystal/CLKIN frequency).				
V _{DD}	26, 57, 58, 59, 60	I	5-V suppy pins.				
V _{SS}	5, 6, 7, 8, 42, 61	I	Ground pins.				
X1	3	0	Crystal output pin for internal oscillator. If the internal oscillator is not used, this pin should be left unconnected.				
X2/CLKIN	4	I	Input pin to the internal oscillator (X2) from the crystal. Alternatively, an input pin for an external oscillator (CLKIN).				

† Input/Output/High-impedance state.



SPRS009C-JANUARY 1987-REVISED JULY 1991

functional block diagram





SPRS009C-JANUARY 1987-REVISED JULY 1991

Supply voltage range, V _{CC} (see Note 6)	3 V to 7 V
Input voltage range	3 V to 7 V
Output voltage range	3 V to 7 V
Continuous power dissipation	0.5 W
Operating free-air temperature:	
Storage temperature	to 150 °C

† Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only, and functional operation of the device at these or any other conditions beyond those indicated in the "Recommended Operating Conditions" section of this specification is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability. NOTE 6: All voltage values are with respect to VSS.

recommended operating conditions

			MIN	NOM	MAX	UNIT
VCC	Supply voltage		4.75	5	5.25	V
VSS	Supply voltage			0		V
VIH	High-level input voltage	All inputs except CLKIN	2			V
ЧН	righteverniput voltage	CLKIN	3			V
\/	Low lovel input veltage	All inputs except MC/MP			0.8	V
VIL	Low-level input voltage MC/MP				0.6	V
IOH	High-level output current, all outputs				-300	μA
IOL	Low-level output current				2	mA
ТА	Operating free-air temperature				70	°C

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

	PARAMETER		TEST CONDITIONS		MIN	TYP	MAX	UNIT
Varia	Vou High-level output voltage		I _{OH} = MAX		2.4	3		
VOH			I _{OH} = 20 μA		$V_{CC} - 0.4$			V
VOL	Low-level output voltage		I _{OL} = MAX	-		0.3	0.5	V
	0		V _{CC} = MAX	V _O = 2.4 V			20	
loz	Off-state output current		VCC = MAX	V _O = 0.4 V			-20	μA
1.			All inp	All inputs except CLKIN			±20	
1	Input current		$V_{CC} = V_{SS}$ to V_{CC}	CLKIN			±50	μΑ
ICC	Supply current		f = 35 MHz, V _{CC} = 5.25 V			60	75	mA
<u></u>	lanut con ocitor co	Data bus				25		- 5
Ci	Input capacitance	All others	f = 1 MHz, all other pins 0 V			15		pF
C	Output capacitance	Data bus				25		pF
Co	Ouipui capacitance	All others	1			10		μr



SPRS009C-JANUARY 1987-REVISED JULY 1991

internal clock option

PARAMETER	TEST CONDITIONS	MIN	NOM	MAX	UNIT
Crystal frequency, f _X	$T_A = 0^{\circ}C$ to $70^{\circ}C$	6.7		35.1	MHz
C1, C2	$T_A = 0^{\circ}C$ to $70^{\circ}C$		10		рF

timing requirements over recommended operating conditions

		MIN	NOM	MAX	UNIT
^t c(MC)	Master clock cycle time	28.49	28.57	150	ns
^t r(MC)	Rise time, master clock input		5	10	ns
^t f(MC)	Fall time, master clock input		5	10	ns
^t w(MCP)	Pulse duration, master clock	0.45t _C (C)		0.55t _{C(C)}	ns
^t w(MCL)	Pulse duration, master clock low		10		ns
^t w(MCH)	Pulse duration, master clock high		10		ns

switching characteristics over recommended operating conditions

	PARAMETER	MIN	NOM	MAX	UNIT
t _{c(C)}	CLKOUT cycle time	113.96	114.3	600	ns
tr(C)	CLKOUT rise time		10		ns
t _{f(C)}	CLKOUT fall time		8		ns
tw(CL)	Pulse duration, CLKOUT low		49		ns
^t w(CH)	Pulse duration, CLKOUT high		47		ns
td(MCC)	Delay time, CLKIN \uparrow to CLKOUT \downarrow	5		50	ns



SPRS009C-JANUARY 1987-REVISED JULY 1991

MEMORY AND PERIPHERAL INTERFACE TIMING

switching characteristics over recommended operating conditions

	PARAMETER	MIN	NOM	MAX	UNIT
^t d1	Delay time, $\overline{\text{MEN}}$, $\overline{\text{MWE}}$, $\overline{\text{IOEN}}$, $\overline{\text{IOWE}}$, to next address bus valid	0		35	ns
t _{d2}	Delay time, CLKOUT \downarrow to $\overline{MEN}\downarrow$	$1/_{4t_{C(C)}} - 5$		¹ / ₄ t _{c(C)} +12	ns
t _{d3}	Delay time, CLKOUT↓ to MEN↑	- 3		6	ns
t _{d4}	Delay time, CLKOUT \downarrow to $\overline{IOEN}\downarrow$	$1/_{4t_{C(C)}} - 5$		¹ / ₄ t _{c(C)} +12	ns
t _{d5}	Delay time, CLKOUT↓ to IOEN↑	- 3		6	ns
^t d6	Delay time, CLKOUT \downarrow to $\overline{MWE}\downarrow$, $\overline{IOWE}\downarrow$	$1/2t_{c(C)} - 5$		¹ /2 ^t c(C)+12	ns
t _{d7}	Delay time, CLKOUT↓ to MWE↑, IOWE↑	- 3		6	ns
t _{d8}	Delay time, $\overline{MWE}\downarrow$, $\overline{IOwE}\downarrow$, data bus out valid			0	ns
td9(CLK)	Delay time, CLKOUT \downarrow to data bus starts to be driven	$1/_{4t_{C(C)}} - 5$			ns
^t d9(MEN)	Delay time, \overline{MEN} to data bus starts to be driven	¹ /4 ^t c(C)			ns
^t d10(CLK)	Delay time, CLKOUT \downarrow to data bus stops being driven			15	ns
^t d10(WE)	Delay time, \overline{MWE} , \overline{IOWE} , data bus stops being driven			20	ns
t _V	Data bus OUT valid after MWE↑, IOWE↑	5	10		ns
^t h(A-WMD)	Address bus hold time after \overline{MWE} , \overline{MEN} , \overline{IOWE} , or \overline{IOEN}	0	2		ns
^t su(A-MD)	Address bus setup time prior to $\overline{MEN}\downarrow,\overline{IOEN}\downarrow$	5			ns

timing requirements over recommended operating conditions

		MIN	MAX	UNIT
tsu(D)	Setup time, data bus valid prior to MEN↑, IOEN↑	35		ns
^t h(D)	Hold time, data bus held valid after MEN↑, IOEN↑	0		ns

RESET (RS**) TIMING**

switching characteristics over recommended operating conditions

PARAMETER MIN MAX		UNIT	
^t d11	Delay time, IOEN↑, IOWE↑, MWE↑, and MEN↑ from RS	1/2tc(C)+50	ns
^t dis(R)	Data bus disable time after RS	$1/4t_{c(C)}+50$	ns

timing requirements over recommended operating conditions

		MIN MAX	UNIT
t _{su(R)}	Reset (RS) setup time prior to CLKOUT	30	ns
^t w(R)	RS pulse duration	5t _{C(C)}	ns



SPRS009C-JANUARY 1987-REVISED JULY 1991

INTERRUPT (INT) TIMING

timing requirements over recommended operating conditions

		MIN MAX	UNIT
^t f(INT)	Fall time, INT	1	ō ns
^t w(INT)	Pulse duration, INT	^t c(C)	ns
tsu(INT)	Setup time, $\overline{\text{INT}}\downarrow$ before CLKOUT \downarrow	30	ns

IO (BIO) TIMING


timing requirements over recommended operating conditions

		MIN MAX	UNIT
^t f(IO)	Fall time, BIO	15	ns
tw(IO)	Pulse duration, BIO	^t c(C)	ns
t _{su(IO)}	Setup time, $\overline{BIO}\downarrow$ before CLKOUT \downarrow	30	ns

TIMING DIAGRAMS

Timing measurements are referenced to and from a low voltage of 0.8 volts and a high voltage of 2.0 volts, unless otherwise noted.


clock timing



 $t_{d(MCC)}$ and $t_{w(MCP)}$ are referenced to an intermediate level of 1.5 V on the CLKIN waveform.



SPRS009C-JANUARY 1987-REVISED JULY 1991




- 2. Next instruction prefetch
- 3. Address bus valid
- 4. Peripheral address valid
- 6. Instruction input valid
- 7. Data input valid
- 8. Instruction input valid



SPRS009C-JANUARY 1987-REVISED JULY 1991


OUT instruction timing




Legend:

- OUT instruction prefetch
 Next instruction prefetch
- 3. Address bus valid
- 4. Peripheral address valid
- 5. Address bus valid Instruction valid 6. Data output valid 7.
- 8. Instruction valid

TBLR instruction timing




TBLW instruction timing






SPRS009C-JANUARY 1987-REVISED JULY 1991




- NOTES: A. RS forces IOEN, IOWE, MWE, and MEN high and places data bus D0 through D15 in a high-impedance state. AB outputs (and program counter) are synchronously cleared to zero after the next complete CLK cycle from RS↓.
 - B. RS must be maintained for a minimum of five clock cycles.
 - C. Resumption of normal program will commence after one complete CLK cycle from RS[↑].
 - D. Due to the synchronization action on RS, time to execute the function can vary dependent upon when RS↑ or RS↓ occur in the CLK cycle.
 - E. Diagram shown is for definition purpose only. IOEN, IOWE, MWE, and MEN are mutually exclusive.
 - F. During a write cycle, RS may produce an invalid write address.

interrupt timing



BIO timing





SPRS009C-JANUARY 1987-REVISED JULY 1991

design considerations for interfacing to SRAM, EPROM and peripherals

The 'C16 differs somewhat from the other members of the 'C1x family of digital signal processors (DSPs). Additional control signals are available for easier interface to external memory or peripherals, and the memory write cycle timings have been changed.

The discussion here will center around changes in t_v and its impact upon SRAM, EPROM and peripherals/latches interfaces.

Access time requirements for interface may be defined relative to :

- 1. Valid address (t_a);
- 2. MEN/IOEN, [(ta(MEN)];

Figure 11 and the following examples summarize these timings at 35 MHz CLKIN.




Figure 11.

where:

 $\begin{array}{l} t_a & : (access time from address valid) = t_{C(C)} - t_{d1} - t_{su(D)} = 44.3 \text{ ns} \\ t_{a(MEN)} & : (access time from \overline{MEN} valid) = t_{C(C)} - t_{d2} - t_{su(D)} + t_{d3} = 35.73 \text{ ns} \end{array}$


and where (for 35 MHz CLKIN):

 $\begin{array}{l} t_{c(C)} = 114.3 \text{ ns} \\ t_{d1} = 35 \text{ ns} \\ t_{d2} = [1/4 \times (114.3) + 12] \text{ ns} \\ t_{su(D)} = 35 \text{ ns} \\ t_{w(CH)} = 47 \text{ ns nominal} \\ t_{f(C)} = 8 \text{ ns nominal} \end{array}$



SPRS009C-JANUARY 1987-REVISED JULY 1991

In addition to the above timings, t_v must be taken into account. t_v is the time that the data bus is guaranteed to be held after the rising edge of \overline{MWE} or \overline{IOWE} . In other 'C1x devices, the value of t_v was referenced to CLKOUT \downarrow and not \overline{WE} (see Figure 12). For the 'C16, t_v is a minimum of 5 ns. This implies that \overline{MWE} and \overline{IOWE} must be tied directly to the external device. If required, decode logic must be added to an input other than the read/write input — for example, the chip select on SRAMs. If the external device does not have two inputs, then transparent latches must be added to extend the time data is held on the data bus. These latches must be off the bus prior to the next instruction (see Figure 12).






where:

 $t_v = 5 \text{ ns (min)}$ $t_{d10} = 15 \text{ ns (max)}$

There is a potential for bus conflict on the prefetch and execution of a TBLW or an OUT instruction. Figure 13 details the timings to be considered. In addition to the timings for the 'C16, timing definitions for interface are also included.





where:



SPRS009C-JANUARY 1987-REVISED JULY 1991

 t_{conf} (data bus conflict time) = $t_{ddeco} + t_{dmemh} - t_{d9(MEN)}$

with:

 $t_{ddeco} : decode delay time to make the CE or OE signal$ $t_{dmemh} : memory data hold time from CE or OE$: delay time, MEN to data bus starts being driven: (at 35 MHz CLKIN) = [1/4t_{C(C)}] = [1/4(114.3)] = 28.58 ns

If t_{conf} is less than or equal to zero, data bus conflict does not occur. If t_{conf} is greater than zero, data conflict occurs.

Note that the following discussion is for CLKIN of 35 MHz.

static memory with output enable and write enable/chip select

The following SRAMs are able to interface directly to the 'C16, needing only to directly connect the 'C16 memory control signals MEN and MWE to the memory. Device select decode is accomplished with address decode and then input to the device chip select.

PRODUCT	t _{ddeco}	^t dmemh	t _{dconf}	UNITS
TC55645-35	0	15	-13.58	ns
TC55328-35	0	15	-13.58	ns
TMS6789-35	0	8	-20.58	ns
TC5588-35	0	10	-18.58	ns
TMS6716-35	0	10	-18.58	ns





Figure 14.



SPRS009C-JANUARY 1987-REVISED JULY 1991

static memory with chip enable and write enable

Without a separate output enable, a faster SRAM is required. Logic is added to decode address and memory control to perform a read/write cycle. The $\overline{\text{MWE}}$ signal is directly connected to the WE input of the SRAM to meet the t_v specification (see Figure 15).





EPROM interface

The following high-speed EPROMs can be used directly:

Product	^t ddeco	t _{dmemh}	t _{dconf}	Units
CY7C291-35	0	25	- 3.58	ns
TMS27C291-35	0	25	- 3.58	ns




Figure 16.



SPRS009C-JANUARY 1987-REVISED JULY 1991

interfacing latches to the TMS320C16

As with the previous devices, the memory control signal must be directly connected to the latch and the latch needs to have a separate chip select. There are several devices with this feature, including the SN74ALS996. The SN74ALS996 is an 8-bit D-type edge-triggered read-back latch with three-state outputs, connected to the 'C16 as illustrated in Figure 17.





Figure 17.




SPRS009C-JANUARY 1987-REVISED JULY 1991

Key Features: TMS320C17/E17/LC17/P17

- 200-ns Instruction Cycle Timing (TMS320C17/E17/P17)
- 278-ns Instruction Cycle Timing (TMS320LC17)
- 256 Words of On-Chip Data RAM
- 4K Words of On-Chip Program ROM (TMS320C17/LC17)
- 4K Words of On-Chip Program EPROM (TMS320E17/P17)
- One-Time Programmable (OTP) Windowless EPROM Version Available (TMS320P17)
- EPROM Code Protection for Copyright Security
- Dual-Channel Serial Port for Full-Duplex Serial Communication
- Serial Port Timer for Standalone Serial Communication
- On-Chip Companding Hardware for µ-law/A-law PCM Conversions



- Device Packaging:
 40-Pin DIP (All Devices)
 - 44-Lead PLCC (TMS320C17/LC17/P17
 - 44-Lead CER-QUAD (TMS320E17/LET7)
- 3.3 -V Low-Power Version Available (TMS320LC17)
- Operating Free-Air Temperature Range ... 0°C to 70°C
- 16-Bit Coprocessor Interface for Common 4/8/16/32-Bit Microcomputers/Microprocessors





SPRS009C-JANUARY 1987-REVISED JULY 1991

architecture

The 'C17/E17/LC17/P17 consists of five major functional units: the 'C15 microcomputer, a system control register, a full-duplex dual-channel serial port, companding hardware, and a coprocessor port.

Three of the I/O ports are used by the serial port, companding hardware, and the coprocessor port. Their operation is determined by the 32 bits of the system control register (see Table 6 for the control register bit definitions). Port 0 accesses control register 0 and consists of the lower 16 register bits (CR15-CR0), and is used to control the interrupts, serial port connections, and companding hardware operation. Port 1 accesses control register 1, consisting of the upper 16 control bits (CR31-CR16), as well as both serial port channels, the companding hardware, and the coprocessor port channels. Communication with the control register is via IN and OUT instructions to ports 0 and 1.

Interrupts fully support the serial port interface. Four maskable interrupts (EXINT, FR, FSX, and FSR) are mapped into I/O port 0 via control register 0. When disabled, these interrupts may be used as single-bit logic inputs polled by software.

serial port

The dual-channel serial port is capable of full-duplex serial communication and offers direct interface to two combo-codecs. Two receive and two transmit registers are mapped into I/O port 1, and operate with 8-bit data samples. Internal and external framing signals for serial port transfers (MSB first) are selected via the system control register. The serial port clock, SCLK, provides the bit timing for transfers with the serial port, and may be either an input or output. As an input, an external clock provides the timing for data transfers and framing pulse synchronization. As an output, SCLK provides the timing for standalone serial communication and is derived from the 'C17/E17/P17 system clock, X2/CLKIN, and system control register bits CR27-CR24 (see Table 7 for the available divide ratios). The internal framing (FR) pulse frequency is derived from the serial port clock (SCLK) and system control register bits CR23-CR16. This framing pulse signal provides framing pulses for combo-codecs, for a sample clock for voice-band systems, or for a timer used in control applications.

μ-law/A-law companding hardware

The 'C17/E17/LC17/P17 features hardware companding logic and can operate in either μ-law or A-law format with either sign-magnitude or twos-complement numbers. Data may be companded in either a serial mode for operation on serial port data or a parallel mode for computation inside the device. The companding logic operation is selected through CR14. No bias is required when operating in twos-complement. A bias of 33 is required for sign-magnitude in μ-law companding. Upon reset, the device is programmed to operate in sign-magnitude mode. This mode can be changed by modifying control bit 29 (CR29) in control register 1. For further information on companding, see the *TCM29C13/TCM29C14/TCM29C16/TCM29C17 Combined Single-Chip PCM Codec and Filter Data Sheet*, and the application report, "*Companding Routines for the TMS32010/TMS32020*," in the book *Digital Signal Processing Applications with the TMS320 Family* (SPRA012A), both documents published by Texas Instruments.


In the serial mode, sign-magnitude linear PCM (13 magnitude bits plus 1 sign bit for µ-law format or 12 magnitude bits plus 1 sign bit for A-law format) is compressed to 8-bit sign-magnitude logarithmic PCM by the encoder and sent to the transmit register for transmission on an active framing pulse. The decoder converts 8-bit sign-magnitude log PCM from the serial port receive registers to sign-magnitude linear PCM.

In the parallel mode, the serial port registers are disabled to allow parallel data from internal memory to be encoded or decoded for computation inside the device. In the parallel encode mode, the encoder is enabled and a 14-bit sign-magnitude value written to port 1. The encoded value is returned with an IN instruction from port 1. In the parallel decode mode, the decoder is enabled and an 8-bit sign-magnitude log PCM value is written to port 1. On the successive IN instruction from port 1, the decoded value is returned. At least one instruction should be inserted between an OUT and the successive IN when companding is performed with twos-complement values.



SPRS009C-JANUARY 1987-REVISED JULY 1991

Table 6. Control Register Configuration



Reserved

BIT	DESCRIPTION AND CONFIGURATION
0	EXINT Interrupt flag [†]
1	FSR interrupt flag [†]
2	FSX interrupt flag [†]
3	FR interrupt flag [†]
4	EXINT interrupt enable mask. When set to logic 1, an interrupt on EXINT activates device interrupt circuitry.
5	FSR interrupt enable mask. Same as EXINT control.
6	FSX interrupt enable mask. Same as EXINT control.
7	FR interrupt enable mask. Same as EXINT control.
8	Port 1 configuration control: $0 = \text{port 1 connects to either serial-port registers or companding hardware.}$ 1 = port 1 accesses CR31-CR16.
9	External framing enable: $0 = \text{serial-port data transfers controlled by active FR.}$ 1 = serial-port data transfers controlled by active FSX/FSR.
10	XF external logic output flag latch
11	0 = Parallel companding mode; serial port disabled. Serial-port enable: 1 = serial companding mode; serial port registers enabled.
12	0 = disabled. μ -law/A-law encoder enable: 1 = data written to port 1 is μ -law or A-law encoded.
13	0 = disabled. μ -law/A-law decoder enable: 1 = data written to port 1 is μ -law or A-law decoded.
14	μ -law/A-law decoder encode/decoded select: 0 = companding hardware performs μ -law conversion. 1 = companding hardware performs A-law conversion.
15	0 = SCLK is an output, derived from the prescaler in timing logic. Serial clock control: 1 = SCLK is an input that provides the clock for serial port and frame counter in timing logic.
23-16	Frame counter modulus. Controls FR frequency = SCLK/(CNT + 2) where CNT is binary value fo CR23-CR16 [‡]
27-24	SCLK prescale cotnrol bits. (See Table 7 for divide ratios.)
28	0 = fixed-data rate; FR is 1 SCLK cycle wide. 1 = variable-data rate; FR is 8 SCLK cycles wide.
29	0 = sign-magnitude companding 1 = twos-complement u-law/A-law conversion enable
30	0 = 8-bit byte length 1 = 16-bit word length
31	Reserved for future expansion: Should be set to zero.

[†] Interrupt flag is cleared by writing a logic 1 to the bit with an OUT instruction to port 0.

[‡] All ones in CR23-CR16 indicate a degenerative state and should be avoided. Bits are operational whether SCLK is an input or an output. CNT must be greater than 7.




SPRS009C-JANUARY 1987-REVISED JULY 1991

CR27	CR26	CR25	CR24	DIVIDE RATIO	SCLK FREQUENCY	UNIT
0	0	0	0	32	0.640	MHz
0	0	0	1	28	0.731	MHz
0	0	1	0	24	0.853	MHz
0	1	0	0	20	1.024	MHz
1	0	0	0	16	1.280	MHz
1	0	0	1	14	1.463	MHz
1	0	1	0	12	1.706	MHz
1	1	0	0	10	2.048	MHz

Table 7. Serial Clock (SCLK) Divide Ratios (X2/CLKIN = 20.48 MHz)

The specification for μ -law and A-law log PCM coding is part of the CCITT G.711 recommendation. The following diagram shows a 'C17/E17/P17 interface to two codecs as used for μ -law or A-law companding format.



coprocessor port

The coprocessor port, accessed through I/O port 5 using IN and OUT instructions, provides a direct connection to most 4/8-bit microcomputers and 16/32-bit microprocessors. The coprocessor interface allows the 'C17/E17/P17 to act as a peripheral (slave) microcomputer to a microprocessor, or a master to a peripheral microcomputer such as TMS7042. The coprocessor port is enabled by setting MC/PM and MC low. The microcomputer mode is enabled by setting these two pins high. (Note that MC/PM \neq MC is undefined.) In the microcomputer mode, the 16 data lines are used for the 6 parallel 16-bit I/O ports.

In the coprocessor mode, the 16-bit coprocessor port is reconfigured to operate as a 16-bit latched bus interface. Control bit 30 (CR30) in control register 1 is used to configure the coprocessor port to either an 8-bit or a 16-bit length. When CR30 is high, the coprocessor port is 16 bits wide thereby making all 16 bits of the data port available for 16-bit transfers to 16 and 32-bit microprocessors. When CR30 is low, the port is 8-bits wide and mapped to the low byte of the data port for interfacing to 8-bit microcomputers. When operating in the 8-bit mode, both halves of the 16-bit latch can be addressed using the HI/LO pin, thus allowing 16-bit transfers over 8 data lines. When not in the coprocessor mode, port 5 can be used as a generic I/O port.



TMS320C17, TMS320E17 DIGITAL SIGNAL PROCESSORS

coprocessor port (continued)

The external processor recognizes the coprocessor interface in which both processors run asynchronously as a memory-mapped I/O operation. The external processor lowers the WR line and places data on the bus. It next raises the WR line to clock the data into the on-chip latch. The rising edge of WR automatically creates an interrupt to the 'C17/E17/P17, and the falling edge of WR clears the RBLE (receive buffer latch empty) flag. When the 'C17/E17/P17 reads the coprocessor port, it causes the RBLE signal to transition to a logic low state that clears the data in the latch, and allows the interrupt condition to be cleared internally. Likewise, the external processor reads form the latch by driving the RD line active low, thus enabling the output latch to drive the latched data. When the data has been read, the external device will again bring the RD line high. This activates the BIO line to signal that the transfer is complete and the latch is available for the next transfer. The falling edge of RD resets the TBLF (transmit buffer latch full) flag. Note that the EXINT and BIO lines are reserved for coprocessor interface and cannot be driven externally when in the coprocessor mode.

An example of the use of a coprocessor interface is shown in Figure 18, in which the 'C17/E17/P17 are DSPs interfaced to the TMS70C42, an 8-bit microcontroller.




Figure 18. Coprocessor Interface



SPRS009C-JANUARY 1987-REVISED JULY 1991

TERMINAL FUNCTIONS[†]


NAME	I/O‡	DEFINITION
BIO	I	External polling input
CLKOUT	0	System clock output, 1/4 crystal/CLKIN frequency
D15/LD15-D0/LD0	I/O	16-bit parallel data bus/data lines for coprocessor latch
DEN/RD	I/O	Data enable for device input data/external read for output latch
DR1, DR0	I	Serial-port receive-channel inputs
DX1, DX0	0	Serial-port transmit-channel outputs
EXINT	I	External interrupt input
FR	0	Internal serial-port framing output
FSR	I	External serial-port receive framing input
FSX	I	External serial-port transmit framing input
MC	I	Microcomputer select (must be same state as MC/PM)
MC/PM	I	Microcomputer/peripheral coprocessor select (must be same state as MC)
PA0/HI/LO	I/O	I/O port address output/latch byte select pin
PA1/RBLE	0	I/O port address output/receive buffer latch empty flag
PA2/TBLF	0	I/O port address output/transmit buffer latch full flag
RS	I	Reset for initializing the device
SCLK	I/O	Serial-port clock
VCC	I	+ 5 V Supply
V _{SS}	I	Ground
WE/WR	0	Write enable for device output data/external write for input latch
X1	0	Crystal output for internal oscillator
X2/CLKIN	I	Crystal input for internal oscillator or external oscillator system clock input
XF	0	External-flag output pin

[†] See EPROM programming section.[‡] Input/Output/High-impedance state.



SPRS009C-JANUARY 1987-REVISED JULY 1991

functional block diagram





SPRS009C-JANUARY 1987-REVISED JULY 1991

electrical specifications

This section contains the electrical specifications for all versions of the 'C17/E17/P17 digital signal processors, including test parameter measurement information. Parameters with PP subscripts apply only to the 'E17/P17 in the EPROM programming mode (see Note 11).

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)[†]

Supply voltage range, V _{CC} , except for the '320LC17 (see Note 6) .	0.3 V to 7 V
Supply voltage range, VPP	\dots -0.6 V to 14 V
Input voltage range	\ldots -0.3 V to 14 V
Output voltage range	\ldots -0.3 V to 7 V
Continuous power dissipation	1.5 W
Operating free-air temperature: L suffix	
A suffix	– 40°C to 85°C
Storage temperature	$\dots -55 \degree C$ to 150 $\degree C$

† Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only, and functional operation of the device at these or any other conditions beyond those indicated in the "Recommended Operating Conditions" section of this specification is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability. NOTE 6: All voltage values are with respect to V_{SS}.

recommended operating conditions

			MIN	NOM	MAX	UNIT
Vcc	Supply voltage	EPROM devices	4.75	5	5.25	V
100	Supply voltage	All other devices	4.5	5		V
VPP	Supply voltage (see Note 11)		12.25	12.5	12.75	V
VSS	Supply voltage			0		V
VIH	High-level input voltage	All inputs except CLKIN	2			V
ЧН	nigh-level input voltage	CLKIN	3	V		
VIL	Low-level input voltage	All inputs except MC/MP			0.8	V
VIL	Low-level input voltage	MC/MP			5 5.25 5 5.5 5 12.75 0 0 0 0.8 0.6 -300 2 70	V
ЮН	High-level output current, all outputs				-300	μA
IOL	Low-level output current (All outputs)				2	mA
ТА	Operating free-air temperature	L suffix	0		70	°C
'A		A suffix	- 40		85	°C

NOTE 11: VPP can be applied only to programming pins designed to accept VPP as an input. During programming the total supply current is IPP + I_{CC}.



SPRS009C-JANUARY 1987-REVISED JULY 1991

electrical characteristics over specified temperature range (unless otherwise noted)

PARAMETER		TEST CONDITIONS	MIN	TYP [†]	MAX	UNIT
	TMS320C17	f = 20.5 MHz, V _{CC} = 5.5 V, T _A = 0°C to 70°C		50	65	
I _{CC} [‡] Supply current	TMS320E17/P1 7	f = 25.6 MHz, V _{CC} = 5.5 V, T _A = – 40°C to 85°C		55	75	mA

[†] All typical values are at $T_A = 70^{\circ}$ C and are used for thermal resistance calculations.

[‡]I_{CC} characteristics are inversely proportional to temperature. For I_{CC} dependance on temperature, frequency, and loading, see Figure 3.

CLOCK CHARACTERISTICS AND TIMING

The 'C17/E17/P17 can use either its internal oscillator or an external frequency source for a clock.

internal clock option

The internal oscillator is enabled by connecting a crystal across X1 and X2/CLKIN (see Figure 1). The frequency of CLKOUT is one-fourth the crystal fundamental frequency. The crystal should be fundamental mode, and parallel resonant, with an effective series resistance of 30 ohms, a power dissipation of 1 mW, and should be specified at a load capacitance of 20 pF.

Crystal frequency, 12	ER	TEST CONDITIONS	MIN	NOM	MAX	
	TMS320C17	$T_A = 0^{\circ}C$ to $70^{\circ}C$	6.7		20.5	
	TMS320E17/P1 7	$T_A = -40^{\circ}C$ to $85^{\circ}C$	6.7		20.5	
C1, C2		$T_A = 0^{\circ}C$ to $70^{\circ}C$		10		pF

external clock option

An external frequency source can be used by injecting the frequency directly into X2/CLKIN with X1 left unconnected. The external frequency injected must conform to the specifications listed in the table below.

switching characteristics over recommended operating conditions

	PARAMETER	TEST CONDITIONS	MIN	NOM	MAX	UNIT
^t c(C)	CLKOUT cycle time§		195.12	200		ns
tr(C)	CLKOUT rise time	RL = 825 Ω,		10¶		ns
^t f(C)	CLKOUT fall time	C _L = 100 pF		8¶		ns
tw(CL)	Pulse duration, CLKOUT low	(see Figure 2)		92¶		ns
^t w(CH)	Pulse duration, CLKOUT high			90¶		ns
td(MCC)	Delay time, CLKIN \uparrow to CLKOUT \downarrow		25¶		60¶	ns

 $t_{c(C)}$ is the cycle time of CLKOUT, i.e., $4t_{c(MC)}$ (4 times CLKIN cycle time if an external oscillator is used). If Values derived from characterization data and not tested.



SPRS009C-JANUARY 1987-REVISED JULY 1991

timing requirements over recommended operating conditions

			MIN	NOM	MAX	UNIT
^t c(MC)	Master clock cycle time		48.78	50	150	ns
^t r(MC)	Rise time, master clock input			5†	10†	ns
^t f(MC)	Fall time, master clock input	ĺ		5†	10†	ns
^t w(MCP)	Pulse duration, master clock		0.45t _{c(M}	C) [†] 0.	^{6t} c(MC) [†]	ns
^t w(MCL)	Pulse duration, master clock low			20†		ns
^t w(MCH)	Pulse duration, master clock high			20†		ns

[†] Values derived from characterization data and not tested.

MEMORY AND PERIPHERAL INTERFACE TIMING

switching characteristics over recommended operating conditions

	PARAMETER	TEST CONDITIONS	MIN	TYP MAX	UNIT
^t d1	Delay time, CLKOUT \downarrow to address bus valid		10†	50	ns
t _{d4}	Delay time, CLKOUT \downarrow to $\overline{DEN}\downarrow$		1/4t _{c(C)} - 5†	1/4t _{c(C)} + 15	ns
t _{d5}	Delay time, CLKOUT↓ to DEN↑	1	-10†	15	ns
t _{d6}	Delay time, CLKOUT \downarrow to $\overline{WE}\downarrow$	1	$1/2t_{C(C)} - 5^{\dagger}$	1/2t _{C(C)} + 15	ns
t _{d7}	Delay time, CLKOUT↓ to WE↑	R _I = 825 Ω	-10†	15	ns
t _{d8}	Delay time, CLKOUT \downarrow to data bus OUT valid	$C_{L} = 100 \text{ pF},$		$1/4t_{C(C)} + 65$	ns
t _{d9}	Time after CLKOUT \downarrow that data bus starts to be driven	(see Figure 2)	$1/4t_{C(C)} - 5^{\dagger}$		ns
^t d10	Time after CLKOUT \downarrow that data bus stops bieng driven	1		1/4t _{C(C)} +70 [†]	ns
t _V	Data bus OUT valid after CLKOUT \downarrow	1	1/4t _{c(C)} -10		ns
^t h(A-WMD)	Address hold time after \overline{WE} , or \overline{DEN} (see Note 14)		0†	2†	ns
^t su(A-MD)	Address bus setup time prior to $\overline{DEN}\downarrow$]	1/4t _{C(C)} -45		ns

[†] Values derived from characterization data and not tested.

NOTE 14: Address bus will be valid upon $\overline{WE}\uparrow$, $\overline{MEN}\uparrow$, or $\overline{DEN}\uparrow$.

timing requirements over recommended operating conditions

		TEST CONDITIONS	MIN	NOM	MAX	UNIT
t _{su(D)}	Setup time, data bus valid prior to <code>CLKOUT</code> \downarrow	R _L = 825 Ω,	50			ns
^t h(D)	Hold time, data bus held valid after CLKOUT \downarrow (see Note 16)	C _L = 100 pF (see Figure 2)	0			ns

NOTE 16: Data may be removed from the data bus upon $\overline{\text{DEN}}$ preceding CLKOUT \downarrow .



SPRS009C-JANUARY 1987-REVISED JULY 1991

RESET (RS**) TIMING**

switching characteristics over recommended operating conditions

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
^t d11	Delay time, \overline{DEN} , and \overline{WE} from \overline{RS}			1/2t _{c(C)} +50†		
^t dis(R)	Data bus disable time after RS	R _L 825 Ω, C _L = 100 pF,		1/4tc(C)+50 [†]	ns
^t d12	Delay time from $\overline{RS} \downarrow$ to high-impedance SCLK	(see Figure 2)			200†	ns
td13	Delay time from $\overline{RS} \downarrow$ to high-impedance DX1, DX0				200†	ns

[†] Values derived form characterization data and not tested.

timing requirements over recommended operating conditions

		MIN	NOM	MAX	UNIT
t _{su(R)}	Reset (RS) setup time prior to CLKOUT (see Note 10)	50			ns
^t w(R)	RS pulse duration	5t _{c(C)}			ns

NOTE 10: RS can occur anytime during a clock cycle. Time given is minimum to ensure synchronous operation.

INTERRUPT (EXINT) TIMING

timing requirements over recommended operating conditions

		MIN	NOM	MAX	UNIT
^t f(INT)	Fall time, EXINT			15	ns
^t w(INT)	Pulse duration, EXINT	^t c(C)			ns
^t su(INT)	Setup time, $\overline{EXINT}\downarrow$ before CLKOUT \downarrow	50			ns

IO (BIO) TIMING

timing requirements over recommended operating conditions

		MIN	NOM	MAX	UNIT
^t f(IO)	Fall time, BIO			15	ns
^t w(IO)	Pulse duration, BIO	^t c(C)			ns
t _{su(IO)}	Setup time, $\overline{BIO}\downarrow$ before CLKOUT \downarrow	50			ns

switching characteristics over recommended operating conditions

PARAMETER	TEST CONDITIONS	MIN	TYP MA	X UN
$t_{d(XF)}$ Delay time CLOCKOUT \uparrow to valid XF	RL 825 Ω, CL = 100 pF, (see Figure 2)	5†	1	15 ns

[†] Values derived form characterization data and not tested.



SPRS009C-JANUARY 1987-REVISED JULY 1991

SERIAL PORT TIMING

switching characteristics over recommended operating conditions

	PARAMETER	MIN	NOM	MAX	UNIT
^t d(CH-FR)	Internal framing (FR) delay from SCLK rising edge			70	ns
^t d(DX1-XL)	DX bit 1 valid before SCLK falling edge	20			ns
^t d(DX2-XL)	DX bit 2 valid before SCLK falling edge	20			ns
^t h(DX)	DX hold time after SCLK falling edge	^t c(SCLK)	/2		ns

timing requirements over recommended operating conditions

		MIN	NOM	MAX	UNIT
^t c(SCLK)	Serial port clock (SCLK) cycle time (see Note 17)	390		4770	ns
^t f(SCLK)	Serial port clock (SCLK) fall time			30†	ns
^t r(SCLK)	Serial port clock (SCLK) rise time			30†	ns
^t w(SCLKL)	Serial port clock (SCLK) low-pulse duration (see Note 17)	185		2500	ns
^t w(SCLKH)	Serial port clock (SCLK) high-pulse duration (see Note 17)	185		2500	ns
^t su(FS)	FSX/FSR setup time before SCLK falling edge	100			ns
^t su(DR)	DR setup time before SCLK falling edge	20			ns
^t h(DR)	DR hold time after SCLK falling edge	20			ns

[†] Values derived from characterization data and not tested.

NOTES: 17. Minimum cycle time is $2t_{C(C)}$ where $t_{C(C)}$ is CLKOUT cycle time.

18. The duty cycle of the serial port clock must be within 45 to 55 percent.

COPROCESSOR INTERFACE TIMING

switching characteristics over recommended operating conditions

	PARAMETER	MIN	NOM	MAX	UNIT
^t d(R-A)	RD low to TBLF high			75	ns
^t d(W-A)	WR low to RBLE high			75	ns
^t a(RD)	RD low to data valid			80	ns
^t h(RD)	Data hold time after RD high	25			ns

timing requirements over recommended operating conditions

		MIN	NOM	MAX	UNIT
^t h(HL)	HI/LO hold time after WR or RD high	25			ns
^t su(HL)	HI/\overline{LO} setup time after \overline{WR} or \overline{RD} low	40			ns
^t su(WR)	Data setup time prior to WR high	30			ns
^t h(WR)	Data hold time after WR high	25			ns
^t w(RDL)	RD low-pulse duration	80			ns
^t w(WRL)	WR low-pulse duration	60			ns




SPRS009C-JANUARY 1987-REVISED JULY 1991


TIMING DIAGRAMS

Timing measurements are referenced to and from a low voltage of 0.8 volts and a high voltage of 2 volts, unless otherwise noted.

clock timing



 $t_{d(MCC)}$ and $t_{w(MCP)}$ are referenced to an intermediate level of 1.5 V on the CLKIN waveform.



memory read timing




SPRS009C-JANUARY 1987-REVISED JULY 1991

IN instruction timing CLKOUT MEN 1 2 ^{− t}su(A-MD) ^{– t}su(D) A11-A0 3 4 5 I d₄ ^{– t}d5 DEN ^{- t}h(D) D15-D0 6 7 8

Legend:

- 1. IN Instruction Prefetch
 - Address Bus Valid 5. Instruction Input Valid 6.
- 2. Next Instruction Prefetch 3. Address Bus Valid
 - 7. Data Input Valid
- 4. Peripheral Address Valid
- 8. Instruction Valid
- **OUT** instruction timing




Legend:

- 1. OUT Instruction Prefetch
- 5. Address Bus Valid
- 2. Next Instruction Prefetch
- 3. Address Bus Valid 4. Peripheral Address Valid
- 6. Instruction Input Valid
- Data Output Valid 7.
- 8. Instruction Valid


INSTRUMENTS POST OFFICE BOX 1443 • HOUSTON, TEXAS 77001

SPRS009C-JANUARY 1987-REVISED JULY 1991


reset timing



interrupt timing




BIO timing





SPRS009C-JANUARY 1987-REVISED JULY 1991


XF timing



Legend:

- 1. Port Address Valid
- 3. Port Data Valid
- 2. Out Opcode Valid 4. Next Instruction Opcode Valid


external framing: transmit timing



NOTES: A. Data valid on transmit output until SCLK rises. B. The most significant bit is shifted first.




SPRS009C-JANUARY 1987-REVISED JULY 1991



external framing: receive timing

NOTE: The most significant bit is shifted first.

internal framing: variable-data rate




NOTE: The most significant bit is shifted first.




SPRS009C-JANUARY 1987-REVISED JULY 1991

internal framing: fixed-data rate




NOTE: The most significant bit is shifted first.

coprocessor timing: external write to coprocessor port





SPRS009C-JANUARY 1987-REVISED JULY 1991







SPRS009C-JANUARY 1987-REVISED JULY 1991

EPROM PROGRAMMING

absolute maximum ratings over specified temperature range (unless otherwise noted)[†]

[†] Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only, and functional operation of the device at these or any other conditions beyond those indicated in the "Recommended Operating Conditions" section of this specification is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability. NOTE 6: All voltage values are with respect to GND.

recommended operating conditions

	MIN	NOM	MAX	UNIT
VPP Supply voltage (see Note 11)		12.5	12.75	V

NOTE 11: VPP can be applied only to programming pins designed to accept VPP as an input. During programming the total supply current is IPP + ICC.

electrical characteristics over specified temperature range (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP†	MAX	UNIT
IPP1	VPP supply current	$V_{PP} = V_{CC} = 5.5 V$			100	μA
IPP2	VPP supply current (during program pulse)	V_{PP} = 12.75 V, V_{CC} = 5.5 V		30	50	mA

recommended timing requirements for programming, $T_A = 25^{\circ}C$, $V_{CC} = 6$ V, $V_{PP} = 12.5$ V, (see Note 13)

		MIN	NOM	MAX	UNIT
^t w(IPGM)	Initial program pulse duration	0.95	1	1.05	ms
^t w(FPGM)	Final pulse duration	3.8		63	ms
^t su(A)	Address setup time	2			μs
t _{su(E)}	E setup time	2			μs
t _{su(G)}	G setup time	2			μs
^t dis(G)	Output disable time from \overline{G} (see Note 15)	0		130‡	ns
^t en(G)	Output enable time from \overline{G}			150‡	ns
t _{su(D)}	Data setup time	2			μs
t _{su(VPP)}	VPP setup time	2			μs
t _{su(VCC)}	V _{CC} setup time	2			μs
^t h(A)	Address hold time	0			μs
^t h(D)	Data hold time	2			μs

[†] Values derived from characterization data and not tested.

NOTES: 13. For all switching characteristics and timing measurements, input pulse levels are 0.4 V to 2.4 V and Vpp = 12.5 V ± 0.25 V during programming.

15. Common test conditions apply for t_{dis(G)} except during programming.



SPRS009C-JANUARY 1987-REVISED JULY 1991

PROGRAMMING THE TMS320E17/P17 EPROM CELL

Each 'E17/P17 devices include a $4K \times 16$ -bit industry-standard EPROM cell for prototyping, early field testing, and low-volume production. In conjunction with this EPROM, the TMS320C17 with a 4K-word masked ROM, then, provides more migration paths for cost-effective production.

Note: The TMS320P17 is a one-time programmable (OTP) EPROM device.

EPROM adapter sockets are available that provide pin-to-pin conversions for programming any 'E17/P17 devices. One adapter socket (part number RTC/PGM320C-06), shown in Figure 19, converts a 40-pin DIP into an equivalent 28-pin device. Another socket (part number RTC/PGM320C-06), not shown, permits 44- to 28-pin conversion.




Figure 19. EPROM Adapter Socket (40-Pin to 28-Pin DIP Conversion)


Key features of the EPROM cell include the normal programming operation as well as verification. The EPROM cell also includes a code protection feature that allows code to be protected against copyright violations.

The 'E17/P17 EPROM cell is programmed using the same family and device pinout codes as the TMS27C64 8K × 8-bit EPROM. The TMS27C64 EPROM series are unltraviolet-light erasable, electrically programmable, read-only memories, fabricated using HVCMOS technology. They are pin-compatible with existing 28-pin ROMs and EPROMs. These EPROMs operate from a single 5-V supply in the read mode; however, a 12.5-V supply is needed for programming. All programming signals are TTL level. For programming outside the system, existing EPROM programmers can be used. Locations may be programmed singly, in blocks, or at random.

Figure 20 shows the wiring conversion to program the 'E17/P17 using the 28-pin pinout of the TMS27C64. Table 8 on pin nomenclature provides a description of the TMS27C64 pins. The code to be programmed into the device should be in serial mode. The 'E17/P17 devices use 13 address lines to address 4K-word memory in byte format.



SPRS009C-JANUARY 1987-REVISED JULY 1991



CAUTION

Although acceptable by some EPROM programmers, the signature mode cannot be used on any TMS320E1x device. The signature mode will input a high-level voltage (12.5 V_{dc}) onto pin A9. Since this pin is not designed for high voltage, the cell will be damaged. To prevent an accidental application of voltage, Texas Instruments has inserted a 3.9 k Ω resistor between pin A9 of the TI programmer socket and the programmer itself.

Pin Nomenclature (TMS320E17/P17)

NAME	I/O	DEFINITION
A0-A12	1	On-chip EPROM programming address lines
CLKIN	1	Clock oscillator input
Ē	1	EPROM chip select
EPT	1	EPROM test mode select
G	1	EPROM read/verify select
GND	1	Ground
PGM	1	EPROM write/program select
Q1-Q8	I/O	Data lines for byte-wide programming of on-chip 8K bytes of EPROM
RS	1	Reset for initializing the device
Vcc	1	5-V power supply
VPP	1	12.5-V power supply

Figure 20. TMS320E17/P17 EPROM Programming Conversion to TMS27C64 EPROM Pinout



SPRS009C-JANUARY 1987-REVISED JULY 1991

Table 8 shows the programming levels required for programming, verifying, reading, and protecting the EPROM cell.

SIGNAL NAME	TMS320E17 PIN	TMS27C64 PIN	PROGRAM	VERIFY	READ	PROTECT VERIFY	EPROM PROTECT
Ē	25	20	VIL	VIL	VIL	VIL	VIH
G	24	22	VIH	PULSE	PULSE	VIL	VIH
PGM	23	27	PULSE	VIH	VIH	VIH	VIH
VPP	3	1	VPP	VPP	VCC	V _{CC} + 1	Vpp
VCC	30	28	VCC	VCC	VCC	V _{CC} + 1	V _{CC} + 1
V _{SS}	10	14	V _{SS}	VSS	VSS	V _{SS}	V _{SS}
CLKIN	8	14	V _{SS}	V _{SS}	V _{SS}	V _{SS}	V _{SS}
RS	4	14	VSS	VSS	VSS	V _{SS}	V _{SS}
EPT	5	26	VSS	VSS	VSS	Vpp	Vpp
Q1-Q8	11-18	11-13, 15-19	D _{IN}	Q _{OUT}	Q _{OUT}	Q8=RBIT	Q8=PULSE
A0-A3	2, 1, 40, 39	10-7	ADDR	ADDR	ADDR	Х	Х
A4	38	6	ADDR	ADDR	ADDR	Х	VIH
A5	37	5	ADDR	ADDR	ADDR	Х	Х
A6	36	4	ADDR	ADDR	ADDR	VIL	Х
A7-A9	35, 34, 29	3, 25, 24	ADDR	ADDR	ADDR	Х	Х
A10-A12	28-26	21, 23, 2	ADDR	ADDR	ADDR	Х	Х

Table 8. TMS320E17/P17 Programming Mode Levels

Legend:

V_{IH} = TTL high level; V_{IL} = TTL low level; ADDR = byte address bit V_{PP} = 12.5 V \pm 0.25 V; V_{CC} = 5 V \pm 0.25 V; X = don't care

PULSE = low-going TTL level pulse; D_{IN} = byte to be programmed at ADDR

Q_{OUT} = byte stored at ADDR; RBIT = ROM protect bit.

programming

Since every memory bit in the cell is a logic 1, the programming operation reprograms certain bits to 0. Once programmed, these bits can be erased only by using ultraviolet light. The correct byte is placed on the data bus with V_{PP} set to the 12.5 V level. The PGM pin is then pulsed low to program in the zeroes.

erasure

Before programming, the device must be erased by exposing it to ultraviolet light. The recommended minimum exposure dose (UV-intensity × exposure-time) is 15 W•s/cm². A typical 12-mW/cm², filterless UV lamp will erase the device in 21 minutes. The lamp should be located about 2.5 cm above the chip during erasure. After exposure, all bits are in the high state.

verify/read

To verify correct programming, the EPROM cell can be read using either the verify or read line definitions shown in Table 8 assuming the inhibit bit has not been programmed.

program inhibit

Programming may be inhibited by maintaining a high level input on the \overline{E} pin or \overline{PGM} pin.

read

The EPROM contents may be read independent of the programming cycle, provided the RBIT (ROM protect bit) has not been programmed. The read is accomplished by setting \overline{E} to zero and pulsing \overline{G} low. The contents of the EPROM location selected by the value on the address inputs appear on Q8-Q1.



SPRS009C-JANUARY 1987-REVISED JULY 1991

output disable

During the EPROM programming process, the EPROM data outputs may be disabled, if desired, by establishing the output disable state. This state is selected by setting \overline{G} and \overline{E} pins high. While output disable is selected, Q8-Q1are placed in the high-impedance state.


EPROM protection

To protect the proprietary algorithms existing in the code programmed on-chip, the ability to read or verify code from external accesses can be completely disabled. Programming the RBIT disables external access of the EPROM cell, making it impossible to access the code resident in the EPROM cell. The only way to remove this protection is to erase the entire EPROM cell, thus removing the proprietary information. The signal requirements for programming this bit are shown in Table 8. The cell can be determined as protected by verifying the programming of the RBIT shown in the table.

standard programming procedure

Before programming, the device must first be completely erased. The device can then be programmed with the correct code. It is advisable to program unused sections with zeroes as a further security measure. After the programming is complete, the code programmed into the cell should be verified. If the cell passes verification, the next step is to program the ROM protect bit (RBIT). Once the RBIT programming is verified, an opaque label should be placed over the window to protect the EPROM cell from inadvertent erasure by ambient light. At this point, the programming is complete, and the device is ready to be placed into its destination circuit.

program cycle timing





SPRS009C-JANUARY 1987-REVISED JULY 1991

absolute maximum ratings over specified temperature range (unless otherwise noted)[†]

Supply voltage range, V _{CC} (see Note 6)	$\dots \dots $
Input voltage range	$\dots \dots \dots -0.3$ V to V _{CC} to 0.5 V
Output voltage range	$\dots \dots \dots \dots \dots -0.3 \text{ V}$ to V _{CC} to 0.5 V
Continuous power dissipation	75 mW
Air temperature range above operating devices: L version	
A version	40°C to 85°C
Storage temperature range	55°C to +150°C

† Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only, and functional operation of the device at these or any other conditions beyond those indicated in the "Recommended Operating Conditions" section of this specification is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability. NOTE 6: All voltage values are with respect to V_{SS}.

recommended operating conditions

			MIN	NOM	MAX	UNIT
VCC	V _{CC} Supply voltage		3.0	3.3	3.6	V
VSS	V _{SS} Supply voltage			0		V
\/		All inputs except CLKIN	2.0			V
VIH	High-level input voltage	CLKIN	2.5			V
VIL	Low-level input voltage	All inputs			0.55	V
ЮН	High-level output current (all outputs)				-300	μA
IOL	Low-level output current (all outputs)	-			1.5	mA
ТА	Operating free-air temperature	L version	0		70	°C
'A	A version		-40		85	°C

electrical characteristics over specified temperature range (unless otherwise noted)

	PARAMETER		TEST CONDITIONS	MIN TYP§	MAX	UNIT
∨он	High-level output voltage		I _{OH} = MAX	2.0		V
ЧОП	nigh lovel output voltage		I _{OH} = 20 μA (see Note 19)	$V_{CC}-0.4$ ¶		V
VOL	Low-level output voltage		I _{OL} = MAX		0.5	V
	IOZ Off-state ouput current		V _{CC} = MAX, V _O = V _{CC}		20	^
102			$V_{O} = V_{SS}$		-20	μA
	Input current		$V_I = V_{SS}$ to V_{CC} , All inputs except CLKIN		±20	μA
'I	input current		$V_I = V_{SS}$ to V_{CC} , CLKIN		±50	μΛ
Ci	Input capacitance	Data bus		25¶		_
	input capacitance	All others	f = 1 MHz, All other pins 0 V	15¶		pF
<u> </u>	Co Output capacitance Data bus			25¶		рF
<u> </u>	C ₀ Output capacitance	All others]	10¶		ρr


[§] All typical values are at V_{CC} = 3.3 V, T_A = 25°C.

¶ Values derived from characterization data and not tested.

NOTE 19: This voltage specification is included for interface to HC logic. All other timing parameters defined in this data sheet are specified for the test load circuit shown in Figure 2.



SPRS009C-JANUARY 1987-REVISED JULY 1991



electrical characteristics over specified ranges (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP [†]	MAX	UNIT
ICC‡	Supply current	f = 14.4 MHz, V_{CC} = 3.6 V, T_A = 0°C to 70°C		15	20	mA

[†] All typical values are at $T_A = 70^{\circ}$ C and are used for thermal resistance calculations.

[‡]I_{CC} characteristics are inversely proportional to temperature. For I_{CC} dependence on frequency, see Figure 3.

clock characteristics and timing

The TMS320LC17 can use either its internal oscillator or an external frequency source for a clock.

internal clock option

The internal oscillator is enabled by connecting a crystal across X1 and X2/CLKIN (see Figure 1). The frequency of CLKOUT is one-fourth the crystal fundamental frequency. The crystal should be fundamental mode, and parallel resonant, with an effective series resistance of 30 ohms, a power dissipation of 1 mW, and be specified at a load capacitance of 20 pF.

PARAMETER	TEST CONDITIONS	MIN	NOM	MAX	UNIT
Crystal frequency f _X	T _A = − 40°C to 85°C	4.0		14.4	MHz
C1, C2			10		pF



external clock option

An external frequency source can be used by injecting the frequency directly into X2/CLKIN with X1 left unconnected. The external frequency injected must conform to the specifications listed in the table below.

switching characteristics over recommended operating conditions

	PARAMETER	TEST CONDITIONS	MIN	NOM	MAX	UNIT
^t c(C)	CLKOUT cycle time§		277.78		1000	ns
^t r(C)	CLKOUT rise time			10¶		ns
^t f(C)	CLKOUT fall time	R _L = 825 Ω, C _L = 100 pF,		8¶		ns
^t w(CL)	Pulse duration, CLKOUT low	(see Figure 2)	131			ns
^t w(CH)	Pulse duration, CLKOUT high		129		ns	
td(MCC)	Delay time CLKIN \uparrow to CLKOUT \downarrow		25		75	ns

 $\$\,t_{c(C)}$ is the cycle time of CLKOUT, i.e., $4t_{c(MC)}$ (4 times CLKIN cycle time if an external oscillator is used). \P Values derived from characterization data and not tested

timing requirements over recommended operating conditions

		MIN	NOM	MAX	UNIT
^t c(MC)	Master clock cycle time	69.5		150	ns
^t r(MC)	Rise time, master clock input		5†	10†	ns
^t f(MC)	Fall time, master clock input		5†	10†	ns
^t w(MCP)	Pulse duration, master clock	0.4t _{c(MC}) [†]	0.6	tc(MC) [†]	ns
^t w(MCL)	Pulse duration, master clock low at $t_{C(MC)}$ min	30		ns	
^t w(MCH)	Pulse duration, master clock high at $t_{C(MC)}$ min	30			ns

[†] Values derived from characterization data and not tested.

MEMORY AND PERIPHERAL INTERFACE TIMING

switching characteristics over recommended operating conditions

	PARAMETER	TEST CONDITIONS	MIN MAX	UNIT
^t d1	Delay time CLKOUT \downarrow to address bus valid		10† 100	n <i>s</i>
t _{d4}	Delay time CLKOUT \downarrow to $\overline{DEN}\downarrow$		$1/4 t_{C(C)} = 5^{\dagger} - 1/4 t_{C(C)} + 25$	ns
t _{d5}	Delay time CLKOUT↓ to DEN↑		-10† 30	ns
t _{d6}	Delay time CLKOUT \downarrow to $\overline{WE}\downarrow$]	1/2 t _{C(C)} -5† 1/2 t _{C(C)} +25	ns
t _{d7}	Delay time CLKOUT↓ to WE↑	$R_{L} = 825 \Omega,$	-10† 30	ns
t _{d8}	Delay time CLKOUT \downarrow to data bus OUT valid	C _L = 100 pF, (see Figure 2)	1/4 t _{c(C)} +130	ns
t _d 9	Time after CLKOUT \downarrow that data bus starts to be driven		1/4 t _{c(C)} -5†	ns
^t d10	Time after CLKOUT \downarrow that data bus stops being driven]	1/4 t _{c(C)} +90	ns
t _V	Data bus OUT valid after CLKOUT \downarrow]	1/4 t _{C(C)} -10	ns
^t h(A-WMD)	Address hold time after WE \uparrow , \overline{MEN} \uparrow , or \overline{DEN} \uparrow (see Note 14)]	0†	ns
^t su(A-MD)	Address bus setup time or $\overline{DEN}\downarrow$		0	ns

[†] Values derived from characterization data and not tested.

NOTE 14: Address bus will be valid upon $\overline{WE}\uparrow$, $\overline{MEN}\uparrow$, or $\overline{DEN}\uparrow$.



SPRS009C-JANUARY 1987-REVISED JULY 1991

timing requirements over recommended operating conditions

		TEST CONDITIONS	MIN	NOM	MAX	UNIT
t _{su(D)}	Setup time data bus valid prior to <code>CLKOUT</code> \downarrow	R _L = 825 Ω, C _L = 100 pF,	80			ns
^t h(D)	Hold time data bus held valid after CLKOUT \downarrow (see Note 9)	(see Figure 2)	0			ns

NOTE 9: Data may be removed from the data bus upon $\overline{\text{MEN}}$ or $\overline{\text{DEN}}$ preceding CLKOUT \downarrow .

RESET (RS) TIMING

switching characteristics over recommended operating conditions

	PARAMETER	TEST CONDITIONS	MIN	NOM	MAX	UNIT
^t d11	Delay time \overline{DEN} , \overline{WE} , and \overline{MEN} from \overline{RS}			1/2t ₀	c(C)+75	ns
tdis(R)	Data bus disable time after RS	R _L = 825 Ω, C _I = 100 pF,		1/4t ₀	c(C)+75	ns
td12	Delay time from $\overline{RS} \downarrow$ to high-impedance SCLK	(see Figure 2)			200†	ns
td13	Delay time from $\overline{RS} \downarrow$ to high-impedance DX1, DX0				200†	ns

[†] These values were derived from characterization data and not tested.

timing requirements over recommended operating conditions

		MIN	NOM	MAX	UNIT
t _{su(R)}	Reset (RS) setup time prior to CLKOUT (see Note 10)	85			ns
^t w(R)	RS pulse duration	5t _{c(C)}			ns

NOTE 10: RS can occur anytime during a clock cycle. Time given is minimum to ensure synchronous operation.

INTERRUPT (EXINT) TIMING

timing requirements over recommended operating conditions

		MIN	NOM	MAX	UNIT
^t f(INT)	Fall time EXINT			15	ns
^t w(INT)	Pulse duration EXINT	^t c(C)			ns
t _{su} (INT)	Setup time $\overline{EXINT}\downarrow$ before CLKOUT \downarrow	85			ns

I/O (BIO) TIMING

timing requirements over recommended operating conditions

		MIN	NOM	MAX	UNIT
^t f(IO)	Fall time BIO			15	ns
tw(IO)	Pulse duration BIO	^t c(C)			ns
tsu(IO)	Setup time $\overline{BIO}\downarrow$ before CLKOUT \downarrow	85			ns



SPRS009C-JANUARY 1987-REVISED JULY 1991

I/O (BIO) TIMING

switching characteristics over recommended operating conditions

PARAMETER		TEST CONDITIONS	MIN	NOM	MAX	UNIT
^t d(XF)	Delay time CLKOUT \downarrow to valid XF	$R_L = 825 \Omega,$ $C_L = 100 pF,$ (see Figure 2)	5†		115	ns

[†] Values derived from characterization data and not tested.

SERIAL PORT TIMING

switching characteristics over recommended operating conditions

		MIN	NOM	MAX	UNIT
^t d(CH-FR)	Internal framing (FR) delay from SCLK rising edge			120	ns
td(DX1-CL)	DX bit 1 valid before SCLK falling edge	20			ns
td(DX2-CL)	DX bit 2 valid before SCLK falling edge	20			ns
^t h(DX)	DX hold time after SCLK falling edge	tc(SCLK)	2		ns

timing requirements over recommended operating conditions

		MIN	NOM	MAX	UNIT
^t c(SCLK)	Serial port clock (SCLK) cycle time [‡]	555		8000	ns
^t f(SCLK)	Serial port clock (SCLK) fall time			30†	ns
^t r(SCLK)	Serial port clock (SCLK) rise time			30†	ns
^t w(SCLK)	Serial port clock (SCLK) low, pulse duration§	250		4400	ns
^t w(SCLKH)	Serial port clock (SCLK) high, pulse duration§	250		4400	ns
t _{su(FS)}	FSX/FSR setup time before SCLK falling edge	130			ns
^t su(DR)	DR setup time before SCLK falling edge	20			ns
^t h(DR)	DR hold time after SCLK falling edge	20			ns

[†] Values derived from characterization data and not tested.

[‡] Minimum cycle time is $2t_{C(C)}$ where $t_{C(C)}$ is CLKOUT cycle time. [§] The duty cycle of the serial port clock must be within 45 to 55%.



SPRS009C-JANUARY 1987-REVISED JULY 1991

COPROCESSOR INTERFACE TIMING

switching characteristics over recommended operating conditions

		MIN	NOM	MAX	UNIT
^t d(R-A)	RD low to TBLF high			150	ns
^t d(W-A)	WR low to RBLF high			150	ns
^t a(RD)	RD low to data valid			150	ns
^t h(RD)	Data hold time after RD high	25			


timing requirements over recommended operating conditions

		MIN	NOM	MAX	UNIT
^t h(HL)	HI/RD hold time after WR or RD high	25			ns
t _{su(HL)}	HI/ \overline{RD} setup time prior to \overline{WR} or \overline{RD} low	40			ns
t _{su(WR)}	Data setup time prior to WR high	50			ns
^t h(WR)	Data hold time after WR high	35			ns
^t w(RDL)	Pulse duration, RD low	150			ns
^t w(WRL)	Pulse duration, WR low	150			ns




SPRS009C-JANUARY 1987-REVISED JULY 1991

clock timing



 $t_{d(MCC)}$ and $t_{w(MCP)}$ are referenced to an intermediate level of 1.5 V on the CLKIN waveform.

IN instruction timing




Legend:

- IN Instruction Prefetch
 Next Instruction Prefetch
- 5. Address Bus Valid
- 6. Instruction Valid
- 3. Address Bus Valid
- 4. Peripheral Address Valid
- 7. Data Input Valid
- 8. Instruction Valid



SPRS009C-JANUARY 1987-REVISED JULY 1991

OUT instruction timing




Legend:

- 1. OUT Instruction Prefetch
- 2. Next Instruction Prefetch
 - tch 6. Instruction Valid 7. Data Output Valid
- Address Bus Valid
 Peripheral Address Valid
- 8. Instruction Valid


5. Address Bus Valid

reset timing





SPRS009C-JANUARY 1987-REVISED JULY 1991




- Port Address Valid
 Out Opcode Valid
- 3. Port Data Valid
- 4. Next Instruction Opcode Valid




SPRS009C-JANUARY 1987-REVISED JULY 1991

external framing: transmit timing



NOTES: A. Data valid on transmit output until SCLK rises. B. The most significant bit is shifted first.


external framing: receive timing



NOTE B: The most significant bit is shifted first.




SPRS009C-JANUARY 1987-REVISED JULY 1991



internal framing: variable-data rate

NOTE: The most significant bit is shifted first.

internal framing: fixed-data rate




NOTE: The most significant bit is shifted first.




SPRS009C-JANUARY 1987-REVISED JULY 1991

coprocessor timing: external write to coprocessor port



coprocessor timing: external read to coprocessor port





SPRS009C-JANUARY 1987-REVISED JULY 1991

THERMAL RESISTANCE CHARACTERISTICS

DEVICE		R _θ JC (°C/W)						
	PDIP (N)	CDIP (JD)	PLCC (FN)	CLCC (FZ)	QFP (PG)			
TMS320C10	26		17					
TMS320C10-14	26		17					
TMS320C10-25	26		17					
TMS320C14			11					
TMS320E14				8				
TMS320P14			11					
TMS320C15	26		17					
TMS320C15-25	26		17					
TMS320E15		8		8				
TMS320E15-25		8		8				
TMS320LC15	26		17					
TMS320P15	13		13					
TMS320C16					25			
TMS320C17	26		17					
TMS320E17		8		8				
TMS320LC17	26		17					
TMS320P17	13		13					

Commercial Devices Device/Package Thermal Resistance Junction To Case



SPRS009C-JANUARY 1987-REVISED JULY 1991

THERMAL RESISTANCE CHARACTERISTICS

DEVICE	R _{θJA} (°C/W)							
	PDIP (N)	CDIP (JD)	PLCC (FN)	CLCC (FZ)	QFP (PG)			
TMS320C10	84		60					
TMS320C10-14	84		60					
TMS320C10-25	84		60					
TMS320C14			46					
TMS320E14				49				
TMS320P14			46					
TMS320C15	84		60					
TMS320C15-25	84		60					
TMS320E15		40		64				
TMS320E15-25		40		64				
TMS320LC15	84		60					
TMS320P15	40		55					
TMS320C16					120			
TMS320C17	84		60					
TMS320E17		40		64				
TMS320LC17	84		60					
TMS320P17	40		55					


Commercial Devices Device/Package Thermal Resistance Junction To Ambient



SPRS009C-JANUARY 1987-REVISED JULY 1991


MECHANICAL DATA

40-pin plastic dual-in-line package



NOTE A: Each pin centerline is located within 0,254 (0.010) of its true longitudinal position.






NOTE A: Each pin centerline is located within 0,254 (0.010) of its true longitudinal position.



SPRS009C-JANUARY 1987-REVISED JULY 1991


44-lead plastic chip carrier (FN suffix)





SPRS009C-JANUARY 1987-REVISED JULY 1991








SPRS009C-JANUARY 1987-REVISED JULY 1991

MECHANICAL DATA


68-lead plastic chip carrier package (FN suffix)





SPRS009C-JANUARY 1987-REVISED JULY 1991

MECHANICAL DATA



68-lead ceramic chip carrier package (FZ suffix)



SPRS009C-JANUARY 1987-REVISED JULY 1991

INDEX

accumulator/ALU 5
architecture (TMS320C1x family) 5, 6 TMS320C14 32 TMS320C17 96
functional block diagram 13 TMS320C10 13 TMS320C14 32 TMS320C15 53 TMS320C16 82 TMS320C17 95
codec interface TMS320C17 3, 6, 96 – 98 companding hardware
TMS320C17 3, 96, 97 control register
TMS320C1797coprocessor interface98
data memory 2, 3, 5, 33 description
TMS320C102, 3, 11TMS320C142, 3, 28, 29TMS320C152, 3, 52TMS320LC152, 3, 70TMS320C162, 3, 79TMS320C172, 3, 95TMS320LC172, 3, 120
electrical specifications 14 TMS320C10 14 TMS320C14 35 TMS320C15 55 TMS320LC15 69 TMS320C16 83 TMS320C17 102 TMS320LC17 120
EPROM programming 47 TMS320E14/P14 47 TMS320E15/P15 65 TMS320E17/P17 114
framing pulses TMS320C17/LC17/E17/P17 97
instruction set
I/O channels 2, 3, 6, 28, 79, 95

TMS320C10 TMS320C14 TMS320C15 TMS320C16 TMS320C17	28 52 79 95
mechanical data 133 – 1	37
TMS320C15 TMS320C16	11 28
microcomputer/microprocessor mode 5, microcomputer/coprocessor 7, multiplier	98 6
package types (TMS320C1x)	4
TMS320C10 4, TMS320C14 4, TMS320C15 4, TMS320LC15 4, TMS320LC15 4, TMS320LC15 4, TMS320LC16 4,	70 79 95
serial port TMS320C17/E176, shifterssubroutines	5
TMS320C14 TMS320C15 TMS320C16	12 30 54 80 00
thermal data 27, 131, 1	32
timing diagrams TMS320C10	51 68 78 91 18



IMPORTANT NOTICE

Texas Instruments and its subsidiaries (TI) reserve the right to make changes to their products or to discontinue any product or service without notice, and advise customers to obtain the latest version of relevant information to verify, before placing orders, that information being relied on is current and complete. All products are sold subject to the terms and conditions of sale supplied at the time of order acknowledgement, including those pertaining to warranty, patent infringement, and limitation of liability.

TI warrants performance of its semiconductor products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are utilized to the extent TI deems necessary to support this warranty. Specific testing of all parameters of each device is not necessarily performed, except those mandated by government requirements.

CERTAIN APPLICATIONS USING SEMICONDUCTOR PRODUCTS MAY INVOLVE POTENTIAL RISKS OF DEATH, PERSONAL INJURY, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE ("CRITICAL APPLICATIONS"). TI SEMICONDUCTOR PRODUCTS ARE NOT DESIGNED, AUTHORIZED, OR WARRANTED TO BE SUITABLE FOR USE IN LIFE-SUPPORT DEVICES OR SYSTEMS OR OTHER CRITICAL APPLICATIONS. INCLUSION OF TI PRODUCTS IN SUCH APPLICATIONS IS UNDERSTOOD TO BE FULLY AT THE CUSTOMER'S RISK.

In order to minimize risks associated with the customer's applications, adequate design and operating safeguards must be provided by the customer to minimize inherent or procedural hazards.

TI assumes no liability for applications assistance or customer product design. TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right of TI covering or relating to any combination, machine, or process in which such semiconductor products or services might be or are used. TI's publication of information regarding any third party's products or services does not constitute TI's approval, warranty or endorsement thereof.

Copyright © 1998, Texas Instruments Incorporated

😻 Texas Instruments	THE WORLD	LEADER I	N DSP AND	ANALOG
Products GO	Development	Tools 💌	Applicati	ions 🔽
Search GO	Advanced Search Tech Support	🗆 TI Home 🗖 Comments	□ TI&ME □ Site Map	🖬 Employment 🖬 Tl Global

PRODUCT FOLDER | PRODUCT INFO: FEATURES | DESCRIPTION | DATASHEETS | PRICING/AVAILABILITY | APPLICATION NOTES | USER MANUALS | RELATED DOCUMENTS

PRODUCT SUPPORT: <u>APPLICATIONS | TECHNICAL SUPPORT | TRAINING</u>

TMS320C10, Digital Signal Processor

DEVICE STATUS: NOT RECOMMENDED FOR NEW DESIGNS

FEATURES

Back to Top

- Performance Up to 8.77 MIPs
- All TMS320C1x Devices are Object Code Compatible
- 144/256-Word On-Chip Data RAM
- 1.5K/4K/8K-Word On-Chip Program ROM
- 4K-Word On-Chip Program EPROM (TMS320E14/P14/E15/P15/E17/P17)
- One-Time Programmable (OTP) Versions Available (TMS320P14/P15/P17)
- EPROM Code Protection for Copyright Security
- 4K/64K-Word Total External Memory at Full Speed
- 32-Bit ALU/Accumulator
- 16 × 16-Bit Multiplier With a 32-Bit Product
- 0 to 16-Bit Barrel Shifter
- Eight Input/Output Channels
- Dual-Channel Serial Port
- Simple Memory a>

Transfer interrupted!

3-V Versions Available (TMS320LC15/LC17)

- Commercial and Military Versions Available
- Operating Free-Air Temperature . . . 0°C to 70°C
- Packaging: DIP, PLCC, Quad Flatpack, and CER-QUAD
- CMOS Technology:
 - o Device.....Cycle Time
 - o TMS320C10 200-ns
 - o TMS320C10-14 . . 280-ns
 - o TMS320C10-25 . . 160-ns
 - o TMS320C14160-ns
 - o TMS320E14 160-ns

DESCRIPTION

Back to Top

TMS320C10

The 'C10 provides the core CPU used in all other 'C1x devices. Its microprocessor operates at 5 MIPS. It provides a parallel I/O of 8 \times 16 bits. Three versions with cycle times of 160, 200, and 280 ns are available as illustrated in Table 1. The 'C10 versions are offered in plastic 40-pin DIP or a 44-lead PLCC packages.

TMS320C14/E14/P14

The 'C14/E14/P14 devices, using the 'C10 core CPU, offer expanded on-chip RAM, and ROM or EPROM ('E14/P14), 16 pins of bit selectable parallel I/O, and I/O mapped asynchronous serial port, four 16-bit timers, and external/internal interrupts. The 'C14 devices can provide for microcomputer/microprocessor operating modes. Three versions with cycle times of 160-ns are available as illustrated in Table 1. These devices are offered in 68-pin plastic PLCC or ceramic CER-QUAD packages.

TMS320C15/E15/P15

The 'C15/E15/P15 devices are a version of the 'C10, offering expanded on-chip RAM, and ROM or EPROM ('E15/P15). The 'P15 is a one-time programmable (OTP), windowless EPROM version. These devices can operate in the microcomputer or microprocessor modes. Five versions are available with cycle times of 160 to 200 ns (see Table 1). These devices are offered in 40-pin DIP, 44-pin PLCC, or 44-pin ceramic packages.

TMS320LC15

The 'LC15 is a low-power version of the 'C15, utilizing a V_{DD} of only 3.3-V. This feature results

in a 2.3: 1 power requirement reduction over the typical 5-V' C1x device. It operates at a cycle time of 250 ns. The device is offered in 40-pin DIP or 44-lead PLCC packages.

TMS320C16

The 'C16 offers on-chip RAM of 256-words, an expanded program memory of 65K-words, and

a fast instruction cycle time of 114 ns (8.77 MIPS). It is offered in a 64-pin guad flat-pack package.

TMS320C17/E17/P17

The 'C17/E17/P17 versions consist of five major functional units: the 'C15 microcomputer, a system control register, a full-duplex dual channel serial port, u-law/A-law companding hardware, and a coprocessor port. The dual-channel serial port is capable of full-duplex serial communication and offers direct interface to two combo-codecs. The hardware companding logic can operate in either u-law or A-law format with either sign-magnitude or twos complement numbers in either serial or parallel modes. The coprocessor port allows the 'C17/E17/P17 to act as a slave microcomputer or as a master to a peripheral microcomputer.

The 'P17 utilizes a one-time programmable (OTP) windowless EPROM version of the 'E17.

TMS320LC17

The 'LC17 is a low-power version of the 'C17, utilizing a V_{DD} of only 3.3-V. This feature results in a 2.3: 1 power requirement reduction over the typical 5-V 'C1x device. It operates at a cycle time of 278 ns.

TECHNICAL DOCUMENTS

To view the following documents, Acrobat Reader 3.x is required.

To download a document to your hard drive, right-click on the link and choose 'Save'.

DATASHEET

Full datasheet in Acrobat PDF: sprs009c.pdf (972 KB) (Updated: 07/01/1991) Full datasheet in Zipped PostScript: sprs009c.psz (1350 KB)

APPLICATION NOTES

View Application Reports for TMS320C1X Fixed Point DSP

- Electrostatic Discharge Application Note (SSYA008 Updated: 01/20/1999)
- Emulation Fundamentals for TI 's DSP Solutions (SPRA439 Updated: 02/01/1998)
- Minimizing Quantization Effects Using the TMS320 DSP Family (SPRA035 Updated: 07/01/1994)
- TMS320C1x Evaluation Module Analog Interface (SPRA029 Updated: 01/01/1993)
- Using the TPS56300 for Powering DSPs (SLVA088 Updated: 03/07/2000)

RELATED DOCUMENTS

• TMS320 DSP Product Overview (SPRZ094D, 922 KB - Updated: 03/01/1998)

USER MANUALS

- DSP Glossary (SPRU258A Updated: 09/01/1997)
- Fixed-Point DSP Assembly Language Tools User's Guide (SPRU018D Updated: 09/01/1994)
- TMS320C1x User's Guide (SPRU013C, 18268 KB Updated: 07/01/1991)
- TMS320C1x/C2x/C2xx/C5x Code Generation Tools Release 6.60 Getting Started Guide (SPRU121 - Updated: 03/01/1995)

Back to Top

PRICING/AVAILABILITY

Back to Top

ORDERABLE DEVICE	PACKAGE	<u>PINS</u>	<u>TEMP</u> <u>(°C)</u>	<u>STATUS</u>	<u>BUDGETARY</u> <u>PRICE</u> <u>US\$/UNIT</u> <u>QTY=1000+</u>	<u>PACK</u> <u>QTY</u>	PRICING/AVAILABILITY
TMS320C10FNA		44		OBSOLETE			
TMS320C10FNL	<u>FN</u>	44	0 TO 70	OBSOLETE			
TMS320C10FNL25	<u>FN</u>	44	0 TO 70	NRND	7.50	26	Check stock or order
TMS320C10NA	<u>N</u>	40	-40 TO 85	OBSOLETE			
TMS320C10NL	<u>N</u>	40	S	NRND	6.28	9	Check stock or order
TMS320C10NL-25	<u>N</u>	40	0 TO 70	NRND	7.50	9	Check stock or order
TMS320C10NL25		0	S	OBSOLETE			

Table Data Updated on: 11/30/2000

© Copyright 2000 Texas Instruments Incorporated. All rights reserved. <u>Trademarks | Privacy Policy</u> | <u>Important Notice</u>

😻 Texas Instruments	THE WORLI	D LEADER I	N DSP AND	ANALOG
Products 💌	Developmen	t Tools 🔄	Applicat	tions 💌
Search GO	Advanced Search Tech Support	□ TI Home □ Comments	🗆 TI&ME 🖿 Site Map	🖬 Employment 🖿 Tl Global

PRODUCT FOLDER | PRODUCT INFO: FEATURES | DESCRIPTION | DATASHEETS | PRICING/AVAILABILITY | APPLICATION NOTES | USER MANUALS | RELATED DOCUMENTS

PRODUCT SUPPORT: <u>APPLICATIONS | TECHNICAL SUPPORT | TRAINING</u>

TMS320C15, Digital Signal Processors

DEVICE STATUS: NOT RECOMMENDED FOR NEW DESIGNS

FEATURES

Back to Top

- Performance Up to 8.77 MIPs
- All TMS320C1x Devices are Object Code Compatible
- 144/256-Word On-Chip Data RAM
- 1.5K/4K/8K-Word On-Chip Program ROM
- 4K-Word On-Chip Program EPROM (TMS320E14/P14/E15/P15/E17/P17)
- One-Time Programmable (OTP) Versions Available (TMS320P14/P15/P17)
- EPROM Code Protection for Copyright Security
- 4K/64K-Word Total External Memory at Full Speed
- 32-Bit ALU/Accumulator
- 16 × 16-Bit Multiplier With a 32-Bit Product
- 0 to 16-Bit Barrel Shifter
- Eight Input/Output Channels
- Dual-Channel Serial Port
- Simple Memory and I/O Interface
- 5-V and 3.3-V Versions Available (TMS320LC15/LC17)
- Commercial and Military Versions Available
- Operating Free-Air Temperature . . . 0°C to 70°C
- Packaging: DIP, PLCC, Quad Flatpack, and CER-QUAD
- CMOS Technology:
 - o Device.....Cycle Time
 - o TMS320C10 200-ns
 - o TMS320C10-14 . . 280-ns
 - o TMS320C10-25 . . 160-ns
 - o TMS320C14160-ns
 - o TMS320E14 160-ns
 - o TMS320P14 160-ns
 - o TMS320C15 200-ns
 - \circ TMS320C15-25 . . 160-ns
 - o TMS320E15 200-ns

TMS320E15-25...160-ns
TMS320LC15....250-ns
TMS320P15....200-ns
TMS320C16....114-ns
TMS320C17....200-ns
TMS320E17....200-ns
TMS320LC17....278-ns
TMS320P17....200-ns

DESCRIPTION

Back to Top

TMS320C10

The 'C10 provides the core CPU used in all other 'C1x devices. Its microprocessor operates at 5 MIPS. It provides a parallel I/O of 8 \times 16 bits. Three versions with cycle times of 160, 200, and 280 ns are available as illustrated in Table 1. The 'C10 versions are offered in plastic 40-pin DIP or a 44-lead PLCC packages.

TMS320C14/E14/P14

The 'C14/E14/P14 devices, using the 'C10 core CPU, offer expanded on-chip RAM, and ROM or EPROM ('E14/P14), 16 pins of bit selectable parallel I/O, and I/O mapped asynchronous serial port, four 16-bit timers, and external/internal interrupts. The 'C14 devices can provide for microcomputer/microprocessor operating modes. Three versions with cycle times of 160-ns are available as illustrated in Table 1. These devices are offered in 68-pin plastic PLCC or ceramic CER-QUAD packages.

TMS320C15/E15/P15

The 'C15/E15/P15 devices are a version of the 'C10, offering expanded on-chip RAM, and ROM or EPROM ('E15/P15). The 'P15 is a one-time programmable (OTP), windowless EPROM version. These devices can operate in the microcomputer or microprocessor modes. Five versions are available with cycle times of 160 to 200 ns (see Table 1). These devices are offered in 40-pin DIP, 44-pin PLCC, or 44-pin ceramic packages.

TMS320LC15

The 'LC15 is a low-power version of the 'C15, utilizing a V_{DD} of only 3.3-V. This feature results

in a 2.3: 1 power requirement reduction over the typical 5-V' C1x device. It operates at a cycle time of 250 ns. The device is offered in 40-pin DIP or 44-lead PLCC packages.

TMS320C16

The 'C16 offers on-chip RAM of 256-words, an expanded program memory of 65K-words, and a fast instruction cycle time of 114 ns (8.77 MIPS). It is offered in a 64-pin quad flat-pack package.

TMS320C17/E17/P17

The 'C17/E17/P17 versions consist of five major functional units: the 'C15 microcomputer, a system control register, a full-duplex dual channel serial port, u-law/A-law companding hardware, and a coprocessor port. The dual-channel serial port is capable of full-duplex serial communication and offers direct interface to two combo-codecs. The hardware companding logic can operate in either u-law or A-law format with either sign-magnitude or twos complement numbers in either serial or parallel modes. The coprocessor port allows the 'C17/E17/P17 to act as a slave microcomputer or as a master to a peripheral microcomputer.

The 'P17 utilizes a one-time programmable (OTP) windowless EPROM version of the 'E17.

TMS320LC17

3 of 4

The 'LC17 is a low-power version of the 'C17, utilizing a V_{DD} of only 3.3-V. This feature results in a 2.3: 1 power requirement reduction over the typical 5-V 'C1x device. It operates at a cycle time of 278 ns.

TECHNICAL DOCUMENTS

To view the following documents, Acrobat Reader 3.x is required. To download a document to your hard drive, right-click on the link and choose 'Save'.

DATASHEET

Full datasheet in Acrobat PDF: sprs009c.pdf (972 KB) (Updated: 07/01/1991) Full datasheet in Zipped PostScript: sprs009c.psz (1350 KB)

APPLICATION NOTES

View Application Reports for TMS320C1X Fixed Point DSP

- Electrostatic Discharge Application Note (SSYA008 Updated: 01/20/1999)
- Emulation Fundamentals for TI 's DSP Solutions (SPRA439 Updated: 02/01/1998)
- Minimizing Quantization Effects Using the TMS320 DSP Family (SPRA035 Updated: 07/01/1994)
- TMS320C1x Evaluation Module Analog Interface (SPRA029 Updated: 01/01/1993)
- Using the TPS56300 for Powering DSPs (SLVA088 Updated: 03/07/2000)

RELATED DOCUMENTS

• TMS320 DSP Product Overview (SPRZ094D, 922 KB - Updated: 03/01/1998)

USER MANUALS

- DSP Glossary (SPRU258A Updated: 09/01/1997)
- Fixed-Point DSP Assembly Language Tools User's Guide (SPRU018D Updated: 09/01/1994)
- TMS320C1x User's Guide (SPRU013C, 18268 KB Updated: 07/01/1991)
- TMS320C1x/C2x/C2xx/C5x Code Generation Tools Release 6.60 Getting Started Guide (SPRU121 - Updated: 03/01/1995)

PRICING/AVAILABILITY

Back to Top

Back to Top

Back to Top

▲Back to Top

Back to Top

Back to Top

4 of 4	
--------	--

					<u>QTY=1000+</u>		
TMS320C15FNA	<u>FN</u>	44	-40 TO 85	OBSOLETE			
TMS320C15FNL	<u>FN</u>	44	0 TO 70	OBSOLETE			
TMS320C15FNL25	<u>FN</u>	44	0 TO 70	NRND	8.62	26	Check stock or order
TMS320C15NA	<u>N</u>	40	-40 TO 85	OBSOLETE			
TMS320C15NL	<u>N</u>	40		OBSOLETE			
TMS320C15NL-25	<u>N</u>	40	0 TO 70	NRND	8.62	9	Check stock or order
TMS320C15NL25	<u>NL</u>	40	S	OBSOLETE			
TMS320C15PEL	<u>PE</u>	44	0 TO 70	OBSOLETE			

Table Data Updated on: 11/30/2000

© Copyright 2000 Texas Instruments Incorporated. All rights reserved. <u>Trademarks | Privacy Policy</u> | <u>Important Notice</u>

1 of 3

🛷 Texas Instruments	THE WORLI	D LEADER I	N DSP AN	D ANALOG
Products GO	Developmen	t Tools 📃 🐨	Applica	ations 💌
Search GO	Advanced Search Tech Support	□ TI Home □ Comments	□ TI&ME □ Site Map	🖬 Employment 🖿 Tl Global

PRODUCT FOLDER | PRODUCT INFO: <u>FEATURES</u> | <u>DESCRIPTION</u> | <u>DATASHEETS</u> | <u>PRICING/AVAILABILITY</u> | <u>APPLICATION NOTES</u> | <u>USER MANUALS</u>

PRODUCT SUPPORT: <u>APPLICATIONS | TECHNICAL SUPPORT | TRAINING</u>

TMS320SS16, Transcoder DSP

DEVICE STATUS: **OBSOLETE**

FEATURES

Back to Top

- Performance Up to 8.77 MIPs
- All TMS320C1x Devices are Object Code Compatible
- 144/256-Word On-Chip Data RAM
- 1.5K/4K/8K-Word On-Chip Program ROM
- 4K-Word On-Chip Program EPROM (TMS320E14/P14/E15/P15/E17/P17)
- One-Time Programmable (OTP) Versions Available (TMS320P14/P15/P17)
- EPROM Code Protection for Copyright Security
- 4K/64K-Word Total External Memory at Full Speed
- 32-Bit ALU/Accumulator
- 16 × 16-Bit Multiplier With a 32-Bit Product
- 0 to 16-Bit Barrel Shifter
- Eight Input/Output Channels
- Dual-Channel Serial Port
- Simple Memory and I/O Interface
- 5-V and 3.3-V Versions Available (TMS320LC15/LC17)
- Commercial and Military Versions Available
- Operating Free-Air Temperature . . . 0°C to 70°C
- Packaging: DIP, PLCC, Quad Flatpack, and CER-QUAD
- CMOS Technology:
 - o Device.....Cycle Time
 - o TMS320C10 200-ns
 - o TMS320C10-14 . . 280-ns
 - o TMS320C10-25 . . 160-ns
 - o TMS320C14160-ns
 - o TMS320E14 160-ns
 - o TMS320P14 160-ns
 - o TMS320C15 200-ns
 - o TMS320C15-25 . . 160-ns
 - o TMS320E15 200-ns

TMS320E15-25...160-ns
TMS320LC15....250-ns
TMS320P15....200-ns
TMS320C16....114-ns
TMS320C17....200-ns
TMS320E17....200-ns
TMS320LC17....278-ns
TMS320P17....200-ns

DESCRIPTION

Back to Top

TMS320C10

The 'C10 provides the core CPU used in all other 'C1x devices. Its microprocessor operates at 5 MIPS. It provides a parallel I/O of 8 \times 16 bits. Three versions with cycle times of 160, 200, and 280 ns are available as illustrated in Table 1. The 'C10 versions are offered in plastic 40-pin DIP or a 44-lead PLCC packages.

TMS320C14/E14/P14

The 'C14/E14/P14 devices, using the 'C10 core CPU, offer expanded on-chip RAM, and ROM or EPROM ('E14/P14), 16 pins of bit selectable parallel I/O, and I/O mapped asynchronous serial port, four 16-bit timers, and external/internal interrupts. The 'C14 devices can provide for microcomputer/microprocessor operating modes. Three versions with cycle times of 160-ns are available as illustrated in Table 1. These devices are offered in 68-pin plastic PLCC or ceramic CER-QUAD packages.

TMS320C15/E15/P15

The 'C15/E15/P15 devices are a version of the 'C10, offering expanded on-chip RAM, and ROM or EPROM ('E15/P15). The 'P15 is a one-time programmable (OTP), windowless EPROM version. These devices can operate in the microcomputer or microprocessor modes. Five versions are available with cycle times of 160 to 200 ns (see Table 1). These devices are offered in 40-pin DIP, 44-pin PLCC, or 44-pin ceramic packages.

TMS320LC15

The 'LC15 is a low-power version of the 'C15, utilizing a V_{DD} of only 3.3-V. This feature results

in a 2.3: 1 power requirement reduction over the typical 5-V' C1x device. It operates at a cycle time of 250 ns. The device is offered in 40-pin DIP or 44-lead PLCC packages.

TMS320C16

The 'C16 offers on-chip RAM of 256-words, an expanded program memory of 65K-words, and a fast instruction cycle time of 114 ns (8.77 MIPS). It is offered in a 64-pin quad flat-pack package.

TMS320C17/E17/P17

3 of 3

The 'C17/E17/P17 versions consist of five major functional units: the 'C15 microcomputer, a system control register, a full-duplex dual channel serial port, u-law/A-law companding hardware, and a coprocessor port. The dual-channel serial port is capable of full-duplex serial communication and offers direct interface to two combo-codecs. The hardware companding logic can operate in either u-law or A-law format with either sign-magnitude or twos complement numbers in either serial or parallel modes. The coprocessor port allows the 'C17/E17/P17 to act as a slave microcomputer or as a master to a peripheral microcomputer.

The 'P17 utilizes a one-time programmable (OTP) windowless EPROM version of the 'E17.

TMS320LC17

The 'LC17 is a low-power version of the 'C17, utilizing a V_{DD} of only 3.3-V. This feature results in a 2.3: 1 power requirement reduction over the typical 5-V 'C1x device. It operates at a cycle time of 278 ns.

TECHNICAL DOCUMENTS

To view the following documents, Acrobat Reader 3.x is required. To download a document to your hard drive, right-click on the link and choose 'Save'.

DATASHEET

Full datasheet in Acrobat PDF: sprs009c.pdf (972 KB) (Updated: 07/01/1991) Full datasheet in Zipped PostScript: sprs009c.psz (1350 KB)

APPLICATION NOTES

View Application Reports for TMS320C1X Fixed Point DSP

- Electrostatic Discharge Application Note (SSYA008 Updated: 01/20/1999)
- Emulation Fundamentals for TI 's DSP Solutions (SPRA439 Updated: 02/01/1998)
- Using the TPS56300 for Powering DSPs (SLVA088 Updated: 03/07/2000)

USER MANUALS

- DSP Glossary (SPRU258A Updated: 09/01/1997)
- Fixed-Point DSP Assembly Language Tools User's Guide (SPRU018D Updated: 09/01/1994)
- TMS320C1x/C2x/C2xx/C5x Code Generation Tools Release 6.60 Getting Started Guide (SPRU121 - Updated: 03/01/1995)

PRICING/AVAILABILITY

PRICING/AVAILA	BILITY			<u>Back to Top</u>				
ORDERABLE DEVICE	<u>PACKAGE</u>	<u>PINS</u>	<u>TEMP</u> (°C)	<u>STATUS</u>	<u>BUDGETARY</u> <u>PRICE</u> <u>US\$/UNIT</u> <u>QTY=1000+</u>	<u>PACK</u> <u>QTY</u>	PRICING/AVAILABILITY	
TMS320SS16NL	<u>N</u>	40		OBSOLETE				

Table Data Updated on: 11/30/2000

© Copyright 2000 Texas Instruments Incorporated. All rights reserved. Trademarks | Privacy Policy Important Notice

Back to Top

Back to Top

Back to Top

Back to Top

🐺 Texas Instrumen	TS THE	WORLD	LEA	DER	IN DS	PANDA	NALO	
Semiconductor Products	SEAR	сн			Spec	cify an area	•	
Find Development Tools		SUPPOR	7		NOWIE	DGEBASE		MYWORKSPACE
Find Applications	30				-			
> TI Home > DSP Developers' Village > D	HOME SP Products > Othe	COMPAN r TMS320 D				/IPLOYMENT Point DSP > TN		LOBAL CONTACT
	TMS320C14 DEVICE STATUS:							
DATASHEET	PRICING/A	VAILABILI	ТҮ					·
sprs009c.pdf (972 kb)	ORDERABLE DEVICE	PACKAGE	<u>PINS</u>	<u>TEMP</u> (°C)	<u>STATUS</u>	BUDGETARY PRICE US\$/UNIT QTY=1000+	<u>PACK</u> <u>QTY</u>	PRICING/AVAILABIL
ADD TO myWORKSPACE	TMS320C14FNL	<u>FN</u>	68	0 TO 70	NRND	11.91	18	Check stock or ord
PRODUCT INFORMATION	E <u>View/Print</u>	complete	e pro	duct f	older			
 <u>Features</u> Description 								
Pricing/Availability								
TECHNICAL DOCUMENTATION								
<u>Application Notes</u>								
<u>User Manuals</u>								
© Copyright 2001 Texas Instruments Inc	orporated. All rights	reserved. Tra	ademar	<u>ks Priv</u>	acy Policy	Important Noti	ce	т 🖏 т

 $file://F:\export\projects\bitting2\imaging\BITTING\mail_pdf\recode\TMS320C14.htm$ 3/15/01

🐺 Texas Instrumen	ITS THE	WORLD	LEA	DER	IN DS	PANDA	NALO	G
Semiconductor Products	GO SEAF	ксн			Spec	cify an area	•	
Find Development Tools	GO (TECH	I SUPPOR	Τ	K		DGEBASE		MYWORKSPACE
Find Applications	GO HOME	COMPAN			-		TIG	LOBAL CONTACT
> <u>TI Home</u> > <u>DSP Developers' Village</u> > <u>D</u>	DSP Products > Othe							
	TMS320C16 DEVICE STATUS							
DATASHEET	PRICING/A			NDED	OR NEW	DESIGNS		
Image: Sprs009c.pdf (972 kb)	ORDERABLE DEVICE	PACKAGE	<u>PINS</u>	<u>TEMP</u> (°C)	<u>STATUS</u>	BUDGETARY PRICE US\$/UNIT	PACK QTY	PRICING/AVAILABIL
ADD TO myWORKSPACE	TMS320C16PGL	. <u>PG</u>	64	0 TO 70	NRND	<u>QTY=1000+</u> 9.42	50	Check stock or ord
PRODUCT INFORMATION	Liew/Print	complete	e pro	duct f	older		-	
 <u>Features</u> <u>Description</u> Pricing/Availability 								
<u>- Hongy (Valiability</u>								
TECHNICAL DOCUMENTATION								
<u>Application Notes</u> <u>User Manuals</u>								
								Ja 7

-Фрт

🐺 Texas Instrumen	NTS THE	WORLD	LEA	DER	IN DSP	AND AND	A L O G	
Semiconductor Products	GO SEAR	сн			Specify	y an area	-	
Find Development Tools	GO (TECH	SUPPOR	RT)	К	NOWLEDO	GEBASE	M	
Find Applications	GO HOME	COMPAN					TI GLO	
> <u>TI Home</u> > <u>DSP Developers' Village</u> >	DSP Products > Othe	r TMS320 D	<u>SPs</u> > <u>1</u>	MS3200	C1X Fixed Poi	int DSP > TMS3	20C17	Product Folder
	TMS320C17 DEVICE STATUS:			nal P	rocessor	S		
DATASHEET	PRICING/A	VAILABILI	TY					
sprs009c.pdf (972 kb)	ORDERABLE DEVICE	<u>PACKAGE</u>	<u>PINS</u>	<u>TEMP</u> (°C)	<u>STATUS</u>	BUDGETARY PRICE US\$/UNIT QTY=1000+	<u>PACK</u> <u>QTY</u>	PRICING/AVAILA
ADD TO myWORKSPACE	TMS320C17FNL	<u>FN</u>	44	0 TO 70	OBSOLETE			
PRODUCT INFORMATION	TMS320C17NL	<u>N</u>	40		OBSOLETE			
 <u>Features</u> <u>Description</u> <u>Pricing/Availability</u> 	■ <u>View/Print</u>	complete	e pro	duct f	older			
TECHNICAL DOCUMENTATION								
<u>Application Notes</u> <u>User Manuals</u>								

🜵 Texas Instrumen	NTS THE	WORLD	LEA	DER	N DSP	AND ANA	L 0 G	
Semiconductor Products	GO SEAR	сн			Specify	an area	- G	ADVANCED
Find Development Tools	GO TECH	SUPPOR	T	K	OWLEDG	EBASE	MY	WORKSPACE
Find Applications	GO HOME	COMPANY					I GLOB	
> TI Home > DSP Developers' Village >	TMS320LC1! DEVICE STATUS:	5, Digita obsolete	l Sig				ULU15	FIOQUET FOIGER
ADD TO myWORKSPACE	ORDERABLE DEVICE	PACKAGE		<u>TEMP</u> (°C)	<u>STATUS</u>	BUDGETARY PRICE US\$/UNIT QTY=1000+	PACK QTY	PRICING/AVAIL!
VIEW / PRINTCOMPLETE PRODUCT FOLDER	TMS320LC15FNL	<u>FN</u>	44	0 TO 70	OBSOLETE			
PRODUCT INFORMATION	TMS320LC15NL	<u>N</u>	40		OBSOLETE			
 <u>Features</u> <u>Description</u> <u>Pricing/Availability</u> 	<u>■ View/Print o</u>	complete	prod	uct fo	<u>older</u>			
TECHNICAL DOCUMENTATION								
<u>Application Notes</u> <u>User Manuals</u>								

TEXAS INSTRUMEN	115	INE	WORLD	LEA	DER	IN DSP	AND AN.	A L U G	ananga i
Semiconductor Products	60	SEAR	СН			Specify	y an area	-	ADVANCE
Find Development Tools 💌	60	TECH	SUPPOR	RT	K	NOWLED	GERASE	M	WORKSPACE
Find Applications	60								
, I Home > DSP Developers' Village >	DSP Pro	HOME	COMPAN					TI GLO	
<u></u>	20. 110	<u>aaoto</u> / <u>otto</u>		<u></u> .		<u></u>	<u></u> ,		
					nal P	rocessor	S		
		CE STATUS:		_					
DATASHEET	P	RICING/A	VAILABIL					1	
sprs009c.pdf (972 kb)	OR	<u>DERABLE</u>	PACKAGE	DINC	<u>TEMP</u>	<u>STATUS</u>	BUDGETARY PRICE	PACK	PRICING/AVAIL
	<u> </u>	DEVICE	PACKAGE	PINS	<u>(°C)</u>	<u>51ATU5</u>	<u>US\$/UNIT</u> QTY=1000+	<u>QTY</u>	PRICING/AVAIL
					0 TO				
MEW / PRINT COMPLETE PRODUCT FOLDER	TMS.	320P14FNL	<u>FN</u>	68	70	OBSOLETE			
PRODUCT INFORMATION	= \/:					Se lala a			
		ew/Print	complete	e pro		older			
 <u>Features</u> Description 									
Pricing/Availability									
TECHNICAL DOCUMENTATION									
 Application Notes 									

🐺 Texas Instruments	THE WORLD LEADER IN DSP AND ANALOG
Semiconductor Products 💌 👩	SEARCH Specify an area GO ADVANCED
Find Development Tools 🗾 🚳	(TECH SUPPORT) (KNOWLEDGEBASE) (MYWORKSPACE)
Find Applications	HOME COMPANY INFORMATION EMPLOYMENT TI GLOBAL CONTACT
> TI Home > DSP Developers' Village > DSP Pro	ducts > Other TMS320 DSPs > TMS320C1X Fixed Point DSP > TMS320P15 Product Folder

TMS320P15, Digital Signal Processors DEVICE STATUS: LIFETIME BUY

DATASHEET	PRICING/AVA		Y					
ADD TO myWORKSPACE	ORDERABLE DEVICE	PACKAGE	<u>PINS</u>	<u>TEMP</u> <u>(°C)</u>	<u>STATUS</u>	BUDGETARY PRICE US\$/UNIT QTY=1000+	PACK OTY	PRICING/AVAII
	TMS320P15FNL	<u>FN</u>	44	0 TO 70	OBSOLETE			
PRODUCT INFORMATION	TMS320P15FNL25	<u>FN</u>	44	0 TO 70	OBSOLETE			
<u>Features</u> <u>Description</u>	TMS320P15NA	N	40	-40 TO 85	OBSOLETE			
<u>Pricing/Availability</u>	TMS320P15NL	<u>N</u>	40		OBSOLETE			
TECHNICAL DOCUMENTATION	TMS320P15NL25	<u>N</u>	40	0 TO 70	OBSOLETE			
<u>Application Notes</u> <u>User Manuals</u>	■ View/Print cc	mplete	orodu	<u>uct fol</u>	lder			

© Copyright 2001 Texas Instruments Incorporated. All rights reserved. Trademarks | Privacy Policy | Important Notice

😻 Texas Instruments	THE WORLD LEADER IN DSP AND ANALOG
Semiconductor Products 💌 👩	SEARCH Specify an area GO ADVANCED
Find Development Tools 💌 👩	(TECH SUPPORT) (KNOWLEDGEBASE) (MYWORKSPACE)
Find Applications	HOME COMPANY INFORMATION EMPLOYMENT TI GLOBAL CONTACT
> <u>TI Home</u> > <u>DSP Developers' Village</u> > <u>DSP Pro</u>	<u>oducts > Other TMS320 DSPs > TMS320C1X Fixed Point DSP > TMS320P17 Product Folder</u>
	320P17, Digital Signal Processors CE STATUS: LIFETIME BUY
PATASUEET	RICING/AVAILABILITY

DATASHEET	PRICING/AV	PRICING/AVAILABILITY								
Sprs009c.pdf (972 kb)	ORDERABLE DEVICE	PACKAGE	<u>PINS</u>	<u>TEMP</u> <u>(°C)</u>	<u>STATUS</u>	BUDGETARY PRICE US\$/UNIT QTY=1000+	<u>PACK</u> <u>QTY</u>	PRICING/AVAIL		
VIEW / PRINT COMPLETE PRODUCT FOLDER	TMS320P17FNA	<u>FN</u>	44	-40 TO 85	OBSOLETE					
PRODUCT INFORMATION	TMS320P17FNL	<u>FN</u>	44	0 TO 70	OBSOLETE					
<u>Features</u> <u>Description</u>	TMS320P17FNLR	<u>FN</u>	44	0 TO 70	OBSOLETE					
<u>Pricing/Availability</u>	TMS320P17NL	<u>N</u>	40		OBSOLETE					
TECHNICAL DOCUMENTATION	<u> ■ View/Print c</u>	omplete	prod	uct fo	older					
<u>Application Notes</u>										

User Manuals

© Copyright 2001 Texas Instruments Incorporated. All rights reserved. Trademarks | Privacy Policy | Important Notice