
- Low r_{DS(on)}:
 0.1 Ω Typ (Full H-Bridge)
 0.4 Ω Typ (Triple Half H-Bridge)
- Pulsed Current:
 - 12 A Per Channel (Full H-Bridge) 6 A Per Channel (Triple Half H-Bridge)
- Matched Sense Transistor for Class A-B Linear Operation
- Fast Commutation Speed


description

The TPIC1501A is a monolithic power array that consists of ten electrically isolated N-channel enhancement-mode power DMOS transistors, four of which are configured as a full H-bridge and six as a triple half H-bridge. The lower stage of the full H-bridge features an integrated sense FET to allow biasing of the bridge in class A-B operation.



The TPIC1501A is offered in a 24-pin wide-body surface-mount (DW) package and is characterized for operation over the case temperature range of -40°C to 125°C.

schematic



NOTES: A. Pins 2 and 23 must be externally connected.

- B. Pins 14 and 24 must be externally connected.
- C. No output may be taken greater than 0.5 V below GND.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.



absolute maximum ratings, $T_C = 25^{\circ}C$ (unless otherwise noted)[†]

Supply-to-GND voltage 20 V Source-to-GND voltage (Q3A, Q4A, Q5A) 20 V
500100 to 5110 voltage (457, 457) 20 v
Output-to-GND voltage
Sense-to-GND voltage
Gate-to-source voltage range, V _{GS} (Q1A, Q1B, Q2A, Q2B, Q3A, Q3B, Q4A, Q4B, Q5A, Q5B) ±20 V
Gate-to-source voltage range, V _{GS} (Q2C)
Continuous drain current, each output (Q1A, Q1B, Q2A, Q2B)
Continuous drain current, each output (Q3A, Q3B, Q4A, Q4B, Q5A, Q5B) 1.5 A
Continuous drain current (Q2C)
Continuous source-to-drain diode current (Q1A, Q1B, Q2A, Q2B)
Continuous source-to-drain diode current (Q3A, Q3B, Q4A, Q4B, Q5A, Q5B) 1.5 A
Continuous source-to-drain diode current (Q2C)
Pulsed drain current, each output, I _{max} (Q1A, Q1B, Q2A, Q2B) (see Note 1 and Figure 24) 12 A
Pulsed drain current, each output, I _{max} (Q3A, Q3B, Q4A, Q4B, Q5A, Q5B)
(see Note 1 and Figure 25) 6 A
Pulsed drain current, I _{max} (Q2C) (see Note 1)
Continuous total power dissipation, $T_C = 70^{\circ}C$ (see Note 2 and Figures 24 and 25)
Operating virtual junction temperature range, T _J
Operating case temperature range, T _C –40°C to 125°C
Storage temperature range, T _{stq} –65°C to 150°C
Lead temperature 1,6 mm (1/16 inch) from case for 10 seconds

[†] Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

- NOTES: 1. Pulse duration = 10 ms, duty cycle = 2%
 - 2. Package is mounted in intimate contact with infinite heat sink.



electrical characteristics, Q1A, Q1B, Q2A, Q2B, $T_C = 25^{\circ}C$ (unless otherwise noted)

		1					
PARAMETER		TEST CON	MIN	TYP	MAX	UNIT	
V(BR)DSX	Drain-to-source breakdown voltage	$I_D = 250 \mu A$,	V _{GS} = 0	20			V
VGS(th)	Gate-to-source threshold voltage	I _D = 1 mA, See Figure 5	$V_{DS} = V_{GS}$	1.4	1.7	2.1	V
VGS(th)match	Gate-to-source threshold voltage matching	I _D = 1 mA,	$V_{DS} = V_{GS}$			40	mV
V _(BR)	Reverse drain-to-GND breakdown voltage	Drain-to-GND curren (D1, D2)	t = 250 μA	20			V
V _{DS(on)}	Drain-to-source on-state voltage	I _D = 2 A, See Notes 3 and 4	V _{GS} = 10 V,		0.2	0.24	V
VF	Forward on-state voltage, GND-to-V _{DD1} , GND-to-V _{DD2}	I _D = 3 A (D1, D2) See Notes 3 and 4			1.8		V
V	Forward on otata valtage accuracy to ducin	I _S = 2 A, See Notes 3 and 4 ar	V _{GS} = 0, nd Figure 19		0.85	1.05	V
VF(SD)	Forward on-state voltage, source-to-drain	I _S = 3 A, See Notes 3 and 4 ar	V _{GS} = 0, nd Figure 19		0.9	1.1	V
	Zana mata waltana duala awanat	V _{DS} = 16 V,	T _C = 25°C		0.05	1	
IDSS	Zero-gate-voltage drain current	VGS = 0	T _C = 125°C		0.5	10	μΑ
IGSSF	Forward-gate current, drain short circuited to source	V _{GS} = 16 V,	V _{DS} = 0		10	100	nA
IGSSR	Reverse-gate current, drain short circuited to source	V _{SG} = 16 V,	V _{DS} = 0		10	100	nA
1	Leakage current, V _{DD1} -to-GND, V _{DD2} -to-GND, gate shorted to source	V _{DGND} = 16 V	T _C = 25°C		0.05	1	μΑ
llkg			T _C = 125°C		0.5	10	μΑ
	Static drain-to-source on-state resistance	V _{GS} = 10 V, I _D = 2 A, See Notes 3 and 4 and Figure 9	T _C = 25°C		0.1	0.12	
IDS(on)			T _C = 125°C		0.14	0.18	Ω
rDS(on)		$V_{GS} = 10 \text{ V},$ $I_{D} = 3 \text{ A},$	T _C = 25°C		0.1	0.12	32
		See Notes 3 and 4 and Figures 7 and 9	T _C = 125°C		0.14	0.18	
	Command transport directions	V _{DS} = 14 V, See Notes 3 and 4	I _D = 1 A,	1.5	2.5		6
9fs	Forward transconductance	V _{DS} = 14 V, See Notes 3 and 4 ar	I _D = 1.5 A, nd Figure 13	2	3.1		S
C _{iss}	Short-circuit input capacitance, common source				240		
C _{oss}	Short-circuit output capacitance, common source	V _{DS} = 14 V, f = 1 MHz,	V _{GS} = 0, See Figure 17		170		pF
C _{rss}	Short-circuit reverse transfer capacitance, common source	1		-	130		
α_{S}	Sense-FET drain current ratio	V _{DS} = 6 V,	$I_{D(Q2C)} = 40 \mu A$	75	130	200	

NOTES: 3. Technique should limit $T_J - T_C$ to 10°C maximum.



^{4.} These parameters are measured with voltage-sensing contacts separate from the current-carrying contacts.

TPIC1501A QUAD AND HEX POWER DMOS ARRAY

SLIS046A - MAY 1995 - REVISED JUNE 1996

source-to-drain diode characteristics, Q1A, Q2A, $T_C = 25^{\circ}C$

	PARAMETER	TEST COI	MIN	TYP	MAX	UNIT	
t _{rr}	Reverse-recovery time	Is = 1.5 A,	Vgs = 0,		70		ns
Q _{RR}	Total diode charge	V _{DS} = 14 V, See Figures 1 and 23	$di/dt = 100 A/\mu s$,		90		nC
t _{rr}	Reverse-recovery time	I _S = 2 A,	V _{GS} = 0,		75		ns
Q _{RR}	Total diode charge	$V_{DS} = 14 V,$	$di/dt = 100 A/\mu s$		110		nC

resistive-load switching characteristics, Q1A, Q1B, Q2A, Q2B, T_C = 25°C

	PARAMETER	TEST CONDITIONS	MIN TYP	MAX	UNIT
t _d (on)	Turn-on delay time		20		
td(off)	Turn-off delay time	$V_{DD} = 14 \text{ V}, R_L = 9.3 \Omega, t_{en} = 10 \text{ ns},$	30		
t _r	Rise time	t _{dis} = 10 ns, See Figure 3			ns
tf	Fall time		25		
Qg	Total gate charge		5.6	7	
Q _{gs(th)}	Threshold gate-to-source charge	$V_{DS} = 14 \text{ V}, I_{D} = 1.5 \text{ A}, V_{GS} = 10 \text{ V}$ See Figure 4	0.8	1	nC
Q _{gd}	Gate-to-drain charge		1.4	1.75	
L(drain)	Internal drain inductance		5		nH
L _(source)	Internal source inductance		5		шп
r(gate)	Internal gate resistance		0.25		Ω

electrical characteristics, Q3A, Q3B, Q4A, Q4B, Q5A, Q5B, T_C = 25°C (unless otherwise noted)

	PARAMETER	TEST CONDITIONS		MIN	TYP	MAX	UNIT
V(BR)DSX	Drain-to-source breakdown voltage	I _D = 250 μA,	V _{GS} = 0 V	20			V
VGS(th)	Gate-to-source threshold voltage	I _D = 1 mA, See Figure 6	V _{DS} = V _{GS} ,	1.4	1.7	2.1	V
VGS(th)match	Gate-to-source threshold voltage matching	$I_D = 1 \text{ mA},$	$V_{DS} = V_{GS}$			40	mV
V _(BR)	Reverse drain-to-GND breakdown voltage	Drain-to-GND current	= 250 μA (D3)	20			V
V _{DS(on)}	Drain-to-source on-state voltage	I _D = 1.5 A, See Notes 3 and 4	V _{GS} = 10 V,		0.6	0.68	V
VF	Forward on-state voltage, GND-to-V _{DD3}	I _D = 1.5 A (D3) See Notes 3 and 4			1.7		V
.,		I _S = 1.5 A, See Notes 3 and 4 and	V _G S = 0, d Figure 20		1	1.2	.,
VF(SD)	Forward on-state voltage, source-to-drain	I _S = 2 A, See Notes 3 and 4 and	V _{GS} = 0, d Figure 20		1.1	1.3	V
		V _{DS} = 16 V,	T _C = 25°C		0.05	1	
IDSS	Zero-gate-voltage drain current	V _{GS} = 0	T _C = 125°C		0.5	10	μΑ
I _{GSSF}	Forward-gate current, drain short circuited to source	V _{GS} = 16 V,	V _{DS} = 0		10	100	nA
IGSSR	Reverse-gate current, drain short circuited to source	V _{SG} = 16 V,	V _{DS} = 0		10	100	nA
	Leakage current, VDD3-to-GND,	V= 0.15 - 16 V	T _C = 25°C		0.05	1	μА
likg	gate shorted to source	V _{DGND} = 16 V	T _C = 125°C		0.5	10	μΑ
	Static drain-to-source on-state resistance	V _{GS} = 10 V, I _D = 0.3 A,	T _C = 25°C		0.35	0.39	
rDS(on)		See Notes 3 and 4 and Figure 10	T _C = 125°C		0.5	0.56	Ω
105(on)		V _{GS} = 10 V, I _D = 1.5 A,	T _C = 25°C		0.4	0.45	32
		See Notes 3 and 4 and Figures 8 and 10	T _C = 125°C		0.56	0.65	
	Forward transponductors	V _{DS} = 14 V, See Notes 3 and 4	$I_D = 500 \text{ mA},$	0.3	0.8		S
9fs	Forward transconductance	V _{DS} = 14 V, See Notes 3 and 4 and	I _D = 750 mA, d Figure 14	0.4	0.93		3
C _{iss}	Short-circuit input capacitance, common source				96		
C _{oss}	Short-circuit output capacitance, common source	V _{DS} = 14 V, f = 1 MHz,	V _{GS} = 0, See Figure 18		98		pF
C _{rss}	Short-circuit reverse transfer capacitance, common source				65		

NOTES: 3. Technique should limit $T_J - T_C$ to 10°C maximum.

4. These parameters are measured with voltage-sensing contacts separate from the current-carrying contacts.



TPIC1501A QUAD AND HEX POWER DMOS ARRAY

SLIS046A - MAY 1995 - REVISED JUNE 1996

source-to-drain diode characteristics, Q3A, Q4A, Q5A, $T_C = 25^{\circ}C$

	PARAMETER	TEST CON	MIN	TYP	MAX	UNIT	
t _{rr}	Reverse-recovery time	Is = 750 mA,	VGS = 0,		60		ns
Q _{RR}	Total diode charge	V _{DS} = 14 V, See Figures 2 and 23	di/dt = 100 A/μs,		55		nC
t _{rr}	Reverse-recovery time	I _S = 1.5 A,	V _{GS} = 0,		120		ns
Q _{RR}	Total diode charge	$V_{DS} = 14 V$,	$di/dt = 100 A/\mu s$		150		nC

resistive-load switching characteristics, Q3A, Q3B, Q4A, Q4B, Q5A, Q5B, T_C = 25°C

	PARAMETER	TEST CONDITIONS	MIN TYP	MAX	UNIT
td(on)	Turn-on delay time		18		
td(off)	Turn-off delay time	$V_{DD} = 14 \text{ V}, R_L = 18.7 \Omega, t_{en} = 10 \text{ ns},$	25		no
t _r	Rise time	t _{dis} = 10 ns, See Figure 3	13		ns
tf	Fall time		20		
Qg	Total gate charge		1.6	2	
Q _{gs(th)}	Threshold gate-to-source charge	$V_{DS} = 14 \text{ V}$, $I_{D} = 750 \text{ mA}$, $V_{GS} = 10 \text{ V}$, See Figure 4	0.26	0.32	nC
Q _{gd}	Gate-to-drain charge	gara i	0.42	0.52	
L(drain)	Internal drain inductance		5		nH
L _(source)	Internal source inductance		5		ПП
r(gate)	Internal gate resistance		0.25		Ω


thermal resistance

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
$R_{\theta JA}$	Junction-to-ambient thermal resistance	See Notes 5 and 8		90		
$R_{\theta JB}$	Junction-to-board thermal resistance	See Notes 6 and 8		38		°C/W
$R_{\theta JP}$	Junction-to-pin thermal resistance	See Notes 7 and 8		28		

NOTES: 5. Package is mounted on a FR4 printed-circuit board with no heat sink.

- 6. Package is mounted on a 24 in², 4-layer FR4 printed-circuit board.
- 7. Package is mounted in intimate contact with infinite heat sink.
- 8. All outputs have equal power.


PARAMETER MEASUREMENT INFORMATION



† I_{RM} = maximum recovery current


Figure 1. Reverse-Recovery-Current Waveform of Source-to-Drain Diodes

PARAMETER MEASUREMENT INFORMATION



† I_{RM} = maximum recovery current

Figure 2. Reverse-Recovery-Current Waveform of Source-to-Drain Diodes



NOTE A: C_L includes probe and jig capacitance.

Figure 3. Resistive-Switching Test Circuit and Voltage Waveforms



PARAMETER MEASUREMENT INFORMATION






Figure 4. Gate-Charge Test Circuit and Voltage Waveform

TYPICAL CHARACTERISTICS



STATIC DRAIN-TO-SOURCE ON-STATE RESISTANCE

STATIC DRAIN-TO-SOURCE ON-STATE RESISTANCE






Figure 7

Figure 8

STATIC DRAIN-TO-SOURCE ON-STATE RESISTANCE

DRAIN CURRENT 10 T_J = 25°C Q1A, Q1B, Q2A, Q2B rDS(on) - Static Drain-to-Source On-State Resistance – Ω V_{GS} = 10 V 0.1 V_{GS} = 15 V V_{GS} = 12 V 0.01 0.01 0.1 100 10 ID - Drain Current - A

Figure 9

STATIC DRAIN-TO-SOURCE ON-STATE RESISTANCE




Figure 10




Figure 11




Figure 13




Figure 12

DISTRIBUTION OF FORWARD TRANSCONDUCTANCE




Figure 14




Figure 15




Figure 17




Figure 16




Figure 18




Figure 19

DRAIN-TO-SOURCE VOLTAGE AND

GATE-TO-SOURCE VOLTAGE

VS **GATE CHARGE** 16 16 $I_D = 1.5 A$ TJ = 25°C 14 14 Q1A, Q1B, Q2A, Q2B V_{DS} – Drain-to-Source Voltage – V See Figure 4 VGS - Gate-to-Source Voltage -12 12 $V_{DD} = 10 V$ 10 10 8 8 6 6 $V_{DD} = 12 V$ $V_{DD} = 14 \text{ V}$ 2 2 V_{DD} = 12 V 0 0 7 0 1 2 4 5 6 Q_q - Gate Charge - nC

Figure 21

SOURCE-TO-DRAIN DIODE CURRENT vs SOURCE-TO-DRAIN VOLTAGE




Figure 20

DRAIN-TO-SOURCE VOLTAGE AND GATE-TO-SOURCE VOLTAGE




Figure 22

REVERSE RECOVERY TIME vs




Figure 23

THERMAL INFORMATION

MAXIMUM DRAIN CURRENT vs




Figure 24

MAXIMUM DRAIN CURRENT vs DRAIN-TO-SOURCE VOLTAGE




Figure 25


[†]Less than 10% duty cycle


[‡] Device is mounted on a 24 in², 4 layer FR4 printed-circuit board.

[§] Device is mounted in intimate contact with infinite heat sink.

THERMAL INFORMATION

DW PACKAGE† JUNCTION-TO-BOARD THERMAL RESISTANCE





† Device is mounted on 24 in², 4-layer FR4 printed-circuit board with no heat sink.

NOTE A: $Z_{\theta B}(t) = r(t) R_{\theta JB}$ $t_W = \text{pulse duration}$ $t_C = \text{cycle time}$ $d = \text{duty cycle} = t_W/t_C$

Figure 26





PACKAGE OPTION ADDENDUM

2-Apr-2012

PACKAGING INFORMATION

Orderable Device	Status (1) Pa	ackage Type	Package Drawing	Pins	Package Qty	Eco Plan ⁽²⁾	Lead/ Ball Finish	MSL Peak Temp ⁽³⁾	Samples (Requires Login)
TPIC1501ADW	OBSOLETE	SOIC	DW	24		TBD	Call TI	Call TI	

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

Pb-Free (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

Pb-Free (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

(3) MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

DW (R-PDSO-G24)

PLASTIC SMALL OUTLINE



NOTES: A. All linear dimensions are in inches (millimeters). Dimensioning and tolerancing per ASME Y14.5M-1994.

- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion not to exceed 0.006 (0,15).
- D. Falls within JEDEC MS-013 variation AD.



IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

Applications

Automotive and Transportation www.ti.com/automotive

e2e.ti.com

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

		•	
Amplifiers	amplifier.ti.com	Communications and Telecom	www.ti.com/communications
Data Converters	dataconverter.ti.com	Computers and Peripherals	www.ti.com/computers
DLP® Products	www.dlp.com	Consumer Electronics	www.ti.com/consumer-apps
DSP	dsp.ti.com	Energy and Lighting	www.ti.com/energy
Clocks and Timers	www.ti.com/clocks	Industrial	www.ti.com/industrial
Interface	interface.ti.com	Medical	www.ti.com/medical
Logic	logic.ti.com	Security	www.ti.com/security
Power Mgmt	power.ti.com	Space, Avionics and Defense	www.ti.com/space-avionics-defense
Microcontrollers	microcontroller.ti.com	Video and Imaging	www.ti.com/video

RFID <u>www.ti-rfid.com</u>
OMAP Mobile Processors www.ti.com/omap

Products

Audio

Wireless Connectivity www.ti.com/wirelessconnectivity

www.ti.com/audio

TI E2E Community Home Page

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2012, Texas Instruments Incorporated