LM4121

LM4121 Precision Micropower Low Dropout Voltage Reference



Literature Number: SNVS073B



LM4121

Precision Micropower Low Dropout Voltage Reference

General Description

The LM4121 is a precision bandgap voltage reference available in a fixed 1.25V and adjustable version with up to 5 mA current source and sink capability.

This series reference operates with input voltages as low as 1.8V and up to 12V consuming 160 μ A (Typ.) supply current. In power down mode, device current drops to less than 2 μ A.

The LM4121 comes in two grades A and Standard. The best grade devices (A) have an initial accuracy of 0.2%, while the standard have an initial accuracy of 0.5%, both with a tempco of 50ppm/°C guaranteed from -40°C to +125°C.

The very low operating voltage, low supply current and power-down capability of the LM4121 makes this product an ideal choice for battery powered and portable applications.

The device performance is guaranteed over the industrial temperature range (-40°C to +85°C), while certain specs are guaranteed over the extended temperature range (-40°C to +125°C). Please contact National for full specifications over the extended temperature range. The LM4121 is available in a standard 5-pin SOT-23 package.


Features (LM4121-1.2)

- Small SOT23-5 package
- Low voltage operation
 - High output voltage accuracy: 0.2%
- Source and Sink current output: ±5 mA
- Supply current: 160 µA Typ.
- Low Temperature Coefficient: 50 ppm/°C
- Enable pin
- Output voltages: 1.25V and Adjustable
- Industrial temperature Range: -40°C to +85°C
- (For extended temperature range, -40°C to 125°C, contact National Semiconductor)

Applications

- Portable, battery powered equipment
- Instrumentation and process control
- Automotive & Industrial
- Test equipment
- Data acquisition systems
- Precision regulators
- Battery chargers
- Base stationsCommunications
- Medical equipment


Block Diagram




^{*} Resistors are removed on the LM4121-ADJ †LM4121-ADJ only

LM4121-1.2 Block Diagram

Connection Diagrams





Refer to the Ordering Information Table in this Data Sheet for Specific Part Number

SOT23-5 Surface Mount Package

Ordering Information

Industrial Temperature Range (-40°C to + 85°C)

Initial Output Voltage Accuracy at 25°C And Temperature Coefficient	LM4121 Supplied as 1000 Units, Tape and Reel	LM4121 Supplied as 3000 Units, Tape and Reel	Top Marking
0.2%, 50 ppm/°C max (A grade)	LM4121AIM5-1.2	LM4121AIM5X-1.2	R19A
0.2 %, 30 ppm/ C max (A grade)	LM4121AIM5-ADJ	LM4121AIM5X-ADJ	R20A
0.5% 50.ppm/°C mov	LM4121IM5-1.2	LM4121IM5X-1.2	R19B
0.5%, 50 ppm/°C max	LM4121IM5-ADJ	LM4121IM5X-ADJ	R20B

SOT-23 Package Marking Information

Only four fields of marking are possible on the SOT-23's small surface. This table gives the meaning of the four fields.

table gives the meaning of the four fields.				
Field Information				
First Field:				
R = Reference				
Second and third Field:				
19 = 1.250V Voltage Option				
20 = Adjustable				
Fourth Field:				
A-B = Initial Reference Voltage Tolerance				
$A = \pm 0.2\%$				
$B = \pm 0.5\%$				

Absolute Maximum Ratings (Note 1)

If Military/Aerospace specified devices are required, please contact the National Semiconductor Sales Office/ Distributors for availability and specifications.

Maximum Voltage on input or

enable pins -0.3V to 14V

Output Short-Circuit Duration Indefinite

Power Dissipation ($T_A = 25^{\circ}C$) (Note 2):

MA05B package – θ_{JA} 280°C/W

Power Dissipation 350 mW

ESD Susceptibility (Note 3)

Human Body Model

2 kV Machine Model 200V

Lead Temperature:

Soldering, (10 sec.) +260°C Vapor Phase (60 sec.) +215°C Infrared (15 sec.) +220°C

Operating Range (Note 1)

Storage Temperature

-65°C to +150°C Range

Ambient Temperature

Range -40°C to +85°C

Junction Temperature

-40°C to +125°C Range

Electrical Characteristics

 $\textbf{LM4121-1.250V} \quad \text{Unless otherwise specified V}_{\text{IN}} = 3.3 \text{V}, \ I_{\text{LOAD}} = 0, \ C_{\text{OUT}} = 0.01 \mu\text{F}, \ T_{\text{A}} = T_{j} = 25 ^{\circ}\text{C}. \ \text{Limits with the local points} = 0.01 \mu\text{F}, \ T_{\text{A}} = 0.01 \mu\text$ standard typeface are for $T_i = 25^{\circ}C$, and limits in **boldface type** apply over the $-40^{\circ}C \le T_A \le +85^{\circ}C$ temperature range.

Symbol	Parameter	Conditions	Min (Note 5)	Typ (Note 4)	Max (Note 5)	Units
V _{OUT}	Output Voltage Initial Accuracy LM4121A-1.250			1.250	±0.2	%
	LM4121-1.250				±0.5	
TCV _{OUT} /°C	Temperature Coefficient	$-40^{\circ}\text{C} \le \text{T}_{\text{A}} \le +125^{\circ}\text{C}$		14	50	ppm/°c
$\Delta V_{OUT}/\Delta V_{IN}$	Line Regulation	$1.8V \le V_{IN} \le 12V$		0.0007	0.009 0.012	%/V
		$0 \text{ mA} \le I_{LOAD} \le 1 \text{ mA}$		0.03	0.08 0.17	
$\Delta V_{OUT}/\Delta I_{LOAD}$	Load Regulation	1 mA ≤ I _{LOAD} ≤ 5 mA		0.01	0.04 0.1	%/mA
		-1 mA ≤ I _{LOAD} ≤ 0 mA		0.04	0.12	
		$-5 \text{ mA} \le I_{LOAD} \le -1 \text{ mA}$		0.01		
Min-V _{IN}	Minimum Operating Voltage	I _{LOAD} = 5mA		1.5	1.8	V
V _N	Output Noise Voltage	0.1 Hz to 10 Hz		20		μV_{PP}
		10 Hz to 10 kHz		30		μV_{RMS}
l _s	Supply Current			160	250 275	μΑ
I _{SS}	Power-down Supply Current	V _{IN} = 12V Enable = 0.4V Enable = 0.2V			1 2	μΑ
V _H	Logic High Input Voltage		1.6	1.5		V
V_L	Logic Low Input Voltage			0.4	0.2	V
I _H	Logic High Input Current			7	15	μΑ
IL	Logic Low Input Current			0.1		μΑ

Electrical Characteristics

LM4121-1.250V Unless otherwise specified $V_{IN} = 3.3V$, $I_{LOAD} = 0$, $C_{OUT} = 0.01 \mu F$, $T_A = T_j = 25^{\circ}C$. Limits with standard typeface are for $T_j = 25^{\circ}C$, and limits in **boldface type** apply over the $-40^{\circ}C \le T_A \le +85^{\circ}C$ temperature range. (Continued)

Symbol	Parameter	Conditions	Min (Note 5)	Typ (Note 4)	Max (Note 5)	Units
0.2						
		$V_{IN} = 3.3V, V_{OUT} = 0$		15		
I _{sc}	Short Circuit Current		6		30	mA
		$V_{IN} = 12V, V_{OUT} = 0$		17		IIIA
			6		30	
Hyst	Thermal Hysteresis	-40°C ≤ T _A ≤ 125°C		0.5		mV/V
	(Note 8)					
ΔV_{OUT}	Long Term Stability	1000 hrs. @ 25°C		100		ppm
	(Note 9)					

Electrical Characteristics

LM4121-ADJ Unless otherwise specified $V_{IN}=3.3V$, $V_{OUT}=V_{REF}$, $I_{LOAD}=0$, $C_{OUT}=0.01\mu F$, $T_A=T_j=25^{\circ}C$. Limits with standard typeface are for $T_j=25^{\circ}C$, and limits in **boldface type** apply over the $-40^{\circ}C \le T_A \le +85^{\circ}C$ temperature range.

Symbol	Parameter	Conditions	Min (Note 5)	Typ (Note 4)	Max (Note 5)	Units
V _{OUT} = V _{REF}	Output Voltage Initial Accuracy LM4121A-ADJ			1.216	±0.2	%
	LM4121-ADJ				±0.5	
TCV _{REF} /°C	Temperature Coefficient	$-40^{\circ}\text{C} \le \text{T}_{\text{A}} \le +125^{\circ}\text{C}$		14	50	ppm/°c
$\Delta V_{REF} / \Delta V_{IN}$	Line Regulation	$1.8V \le V_{IN} \le 12V$		0.0007	0.009 0.012	%/V
		0 mA ≤ I _{LOAD} ≤ 1 mA		0.03	0.08 0.17	
$\Delta V_{OUT}/\Delta I_{LOAD}$	Load Regulation	1 mA ≤ I _{LOAD} ≤ 5 mA		0.01	0.04 0.1	%/mA
		$-1 \text{ mA} \le I_{LOAD} \le 0 \text{ mA}$		0.04	0.12	
		$-5 \text{ mA} \le I_{LOAD} \le -1 \text{ mA}$		0.01		
Min-V _{IN}	Minimum Operating Voltage	I _{LOAD} = 5 mA		1.5	1.8	V
V _N	Output Noise Voltage	0.1 Hz to 10 Hz		20		μV_{PP}
	(Note 6)	10 Hz to 10 kHz		30		μV _{RMS}
I _S	Supply Current			160	250 275	μΑ
I _{SS}	Power-down Supply Current	$V_{IN} = 12V$ Enable = 0.4V Enable = 0.2V			1 2	μΑ
I _{BIAS}	Reference Pin Bias Current	(Note 7)	15	40		nA
V _H	Logic High Input Voltage		1.6	1.5		V
V_L	Logic Low Input Voltage			0.4	0.2	V
I _H	Logic High Input Current			7	15	μΑ

Electrical Characteristics

LM4121-ADJ Unless otherwise specified $V_{IN} = 3.3V$, $V_{OUT} = V_{REF}$, $I_{LOAD} = 0$, $C_{OUT} = 0.01\mu F$, $T_A = T_j = 25^{\circ}C$. Limits with standard typeface are for $T_j = 25^{\circ}C$, and limits in **boldface type** apply over the $-40^{\circ}C \le T_A \le +85^{\circ}C$ temperature range. (Continued)

Symbol	Parameter	Conditions	Min (Note 5)	Typ (Note 4)	Max (Note 5)	Units
I _L	Logic Low Input Current			0.1		μA
I _{sc}	Short Circuit Current	V _{OUT} = 0		15		
			6		30	mA
		$V_{IN} = 12V, V_{OUT} = 0$		17		ША
			6		30	
Hyst	Thermal Hysteresis (Note 8)	-40°C ≤ T _A ≤ 125°C		0.5		mV/V
ΔV_{OUT}	Long Term Stability (Note 9)	1000 hrs. @ 25°C		100		ppm

Note 1: "Absolute Maximum Ratings" indicate limits beyond which damage to the device may occur. Operating Ratings indicate conditions for which the device is intended to be functional, but do not guarantee specific performance limits. For guaranteed specifications and test conditions, see Electrical Characteristics. The guaranteed specifications apply only for the test conditions listed. Some performance characteristics may degrade when the device is not operated under the listed test conditions.

Note 2: Without PCB copper enhancements. The maximum power dissipation must be de-rated at elevated temperatures and is limited by T_{JMAX} (maximum junction temperature), θ_{J-A} (junction to ambient thermal resistance) and T_A (ambient temperature). The maximum power dissipation at any temperature is: PDiss_{MAX} = $(T_{JMAX} - T_A)/\theta_{J-A}$ up to the value listed in the Absolute Maximum Ratings.

Note 3: The human body model is a 100 pF capacitor discharged through a 1.5 k Ω resistor into each pin. The machine model is a 200 pF capacitor discharged directly into each pin.

Note 4: Typical numbers are at 25°C and represent the most likely parametric norm.

Note 5: Limits are 100% production tested at 25°C. Limits over the operating temperature range are guaranteed through correlation using Statistical Quality Control (SQC) methods. The limits are used to calculate National's Averaging Outgoing Quality Level (AOQL).

Note 6: Output noise for 1.25V option. Noise is proportional to V_{OUT} .


Note 7: Bias Current flows out of the Adjust pin.


Note 8: Thermal hysteresis is defined as the change in +25°C output voltage before and after exposing the device to temperature extremes.

Note 9: Long term stability is change in V_{RFF} at 25°C measured continuously during 1000 hrs.


LM4121- (All Options) Typical Operating Characteristics


Unless otherwise specified, V_{IN} = 3.3V, V_{OUT} = 1.25V, I_{LOAD} = 0, C_{OUT} = 0.022 μ F, T_A = 25 $^{\circ}$ C and V_{EN} = V_{IN}.






LM4121- (All Options) Typical Operating Characteristics Unless otherwise specified, $V_{\text{IN}} = 3.3 \text{V}, \ V_{\text{OUT}} = 1.25 \text{V}, \ I_{\text{LOAD}} = 0, \ C_{\text{OUT}} = 0.022 \mu\text{F}, \ T_{\text{A}} = 25 ^{\circ}\text{C} \ \text{and} \ V_{\text{EN}} = V_{\text{IN}}. \ \text{(Continued)}$








Short Circuit vs Temperature 16 15 SHORT CIRCUIT CURRENT (mA) 14 $V_{IN}^{-1} = 12V$ 13 12 $V_{1N} = 3.3V$ 11 10 9 8 -50 -25 25 50 75 100 125 150 TEMPERATURE (°C)





LM4121- (All Options) Typical Operating Characteristics Unless otherwise specified, $V_{\text{IN}} = 3.3 \text{V}$, $V_{\text{OUT}} = 1.25 \text{V}$, $I_{\text{LOAD}} = 0$, $C_{\text{OUT}} = 0.022 \mu \text{F}$, $T_{\text{A}} = 25 ^{\circ} \text{C}$ and $V_{\text{EN}} = V_{\text{IN}}$. (Continued)












Load Step Response



0

0

40

80

120


TIME (μs)


160

200


10129123


Load Step Response







LM4121- (All Options) Typical Operating Characteristics Unless otherwise specified, $V_{\text{IN}} = 3.3 \text{V}$, $V_{\text{OUT}} = 1.25 \text{V}$, $I_{\text{LOAD}} = 0$, $C_{\text{OUT}} = 0.022 \mu \text{F}$, $T_{\text{A}} = 25 ^{\circ} \text{C}$ and $V_{\text{EN}} = V_{\text{IN}}$. (Continued)






Noise Spectural Density (10Hz-10kHz)







LM4121-1.25 Typical Operating Characteristics

Unless otherwise specified, V $_{\rm IN}$ = 3.3V, V $_{\rm OUT}$ = 1.25V, I $_{\rm LOAD}$ = 0, C $_{\rm OUT}$ = 0.022 μ F, T $_{\rm A}$ = 25°C and V $_{\rm EN}$ = V $_{\rm IN}$.






Line Regulation




10129130


Load Regulation




LM4121-ADJ Typical Operating Characteristics

Unless otherwise specified, $V_{IN}=3.3V,\ V_{OUT}=1.2V,\ I_{LOAD}=0,\ C_{OUT}=0.022\mu F,\ T_A=25^{\circ}C$ and $V_{EN}=V_{IN}.$







Dropout Voltage vs Output Error




Dropout Voltage vs Load Current




LM4121-ADJ Typical Operating Characteristics Unless otherwise specified, V_{IN} = 3.3V, V_{OUT} = 1.2V, I_{LOAD} = 0, C_{OUT} = 0.022 μ F, T_A = 25°C and V_{EN} = V_{IN} . (Continued)







Adjust Pin Bias Current 25 20 15 10 -50 -25 0 25 50 75 100 125 150 TEMPERATURE (°C)



LM4121-ADJ Typical Operating Characteristics Unless otherwise specified, V_{IN} = 3.3V, V_{OUT} = 1.2V, I_{LOAD} = 0, C_{OUT} = 0.022 μ F, T_A = 25°C and V_{EN} = V_{IN} . (Continued)





Pin Functions

Output (Pin 5): Reference Output.

Input (Pin 4): Positive Supply.

Ground (Pin 2): Negative Supply or Ground Connection.

Enable (Pin 3):Pulled to input for normal operation. Forcing this pin to ground will turn-off the output.

REF (Pin 1):REF Pin (1.25V option only). This pin should be left unconnected for 1.25V option.

 ${\bf Adj}$ (Pin 1):V $_{\rm OUT}$ Adj Pin (Adjustable option only). See Application Hints section.

Application Hints

The standard application circuit for the LM4121 is shown in *Figure 1*. The output voltage is set with the two feedback resistors, according to the following formula:

$$V_{OUT} = [V_{ref}(1+ R1/R2] - I_{bias} \bullet R1$$

Values for R1 and R2 should be chosen to be less than 1 $M\Omega.$ $I_{\rm bias}$ typically flows out of the adjust pin. Values for $V_{\rm ref}$ and $I_{\rm bias}$ are found in the Electrical Characteristics Spec. table. For best accuracy, be sure to take into account the variation of $V_{\rm REF}$ with input voltage, load and output voltage.

variation of $\ensuremath{V_{\text{REF}}}$ with input voltage, load and output voltage. The LM4121 is designed to be stable with ceramic output capacitors in the range of 0.022µF to 0.047µF. Note that 0.022µF is the minimum required output capacitor. These capacitors typically have an ESR of about 0.1 to 0.5 Ω . Smaller ESR can be tolerated, however larger ESR can not. The output capacitor can be increased to improve load transient response, up to about 1µF. However, values above 0.047µF must be tantalum. With tantalum capacitors, in the 1µF range, a small capacitor between the output and the reference (Adj) pin is required. This capacitor will typically be in the 50pF range. Care must be taken when using output capacitors of 1µF or larger. These application must be thoroughly tested over temperature, line and load. Also, when the LM4121 is used as a controller, with external active components, each application must be carefully tested to ensure a stable design. The adjust pin is sensitive to noise and capacitive loading. The trace to this pin must be as short as possible and the feedback resistiors should be close to this pin. Also, a single point ground to the LM4121 will help ensure good accuracy at high load currents.

An input capacitor is typically not required. However, a $0.1\mu F$ ceramic can be used to help prevent line transients from entering the LM4121. Larger input capacitors should be tantalum or aluminium.

The enable pin is an analog input with very little hysteresis. About $6\mu A$ into this pin is required to turn the part on, and it must be taken close to GND to turn the part off (see spec. table for thresholds). There is a *minimum* slew rate on this pin of about $0.003V/\mu S$ to prevent glitches on the output. All of these conditions can easily be met with ordinary CMOS or TTL logic. If the shutdown feature is not required, then this pin can safely be connected directly to the input supply. Floating this pin is not recommended.




FIGURE 1. Standard Application Circuit


PRINTED CIRCUIT BOARD LAYOUT CONSIDERATION

The mechanical stress due to PC board mounting can cause the output voltage to shift from its initial value. References in SOT packages are generally less prone to assembly stress than devices in Small Outline (SOIC) package.


To reduce the stress-related output voltage shifts, mount the reference on the low flex areas of the PC board such as near to the edge or the corner of the PC board.

Typical Application Circuits

Voltage Reference with Negative Output




100mA Quasi-LDO Regulator




10129104


Boosted Output Current with Negative Voltage Reference




Voltage Reference with Complimentary Output




Two Terminal Constant Current Source



Precision Voltage Reference with Force and Sense Output



Programmable Current Source




10129110


Typical Application Circuits

(Continued)

Precision Comparator with Hysteresis




10129111




10129145

Power Supply Splitter




Li + Low Battery Detector



10129144

Physical Dimensions inches (millimeters)

unless otherwise noted



National does not assume any responsibility for use of any circuitry described, no circuit patent licenses are implied and National reserves the right at any time without notice to change said circuitry and specifications.

For the most current product information visit us at www.national.com.

LIFE SUPPORT POLICY

NATIONAL'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT AND GENERAL COUNSEL OF NATIONAL SEMICONDUCTOR CORPORATION. As used herein:

- Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
- A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

BANNED SUBSTANCE COMPLIANCE

National Semiconductor certifies that the products and packing materials meet the provisions of the Customer Products Stewardship Specification (CSP-9-111C2) and the Banned Substances and Materials of Interest Specification (CSP-9-111S2) and contain no "Banned Substances" as defined in CSP-9-111S2.



National Semiconductor Americas Customer Support Center

Email: new.feedback@nsc.com Tel: 1-800-272-9959

www.national.com

National Semiconductor Europe Customer Support Center Fax: +49 (0) 180-530 85 86

Email: europe.support@nsc.com
Deutsch Tel: +49 (0) 69 9508 6208
English Tel: +44 (0) 870 24 0 2171
Français Tel: +33 (0) 1 41 91 8790

National Semiconductor Asia Pacific Customer Support Center Email: ap.support@nsc.com National Semiconductor Japan Customer Support Center Fax: 81-3-5639-7507 Email: jpn.feedback@nsc.com Tel: 81-3-5639-7560

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products	Applications
----------	--------------

Audio www.ti.com/audio Communications and Telecom www.ti.com/communications **Amplifiers** amplifier.ti.com Computers and Peripherals www.ti.com/computers dataconverter.ti.com Consumer Electronics www.ti.com/consumer-apps **Data Converters DLP® Products** www.dlp.com **Energy and Lighting** www.ti.com/energy DSP dsp.ti.com Industrial www.ti.com/industrial Clocks and Timers www.ti.com/clocks Medical www.ti.com/medical Interface interface.ti.com Security www.ti.com/security

Logic logic.ti.com Space, Avionics and Defense www.ti.com/space-avionics-defense

Power Mgmt power.ti.com Transportation and Automotive www.ti.com/automotive
Microcontrollers microcontroller.ti.com Video and Imaging www.ti.com/video

RFID <u>www.ti-rfid.com</u>
OMAP Mobile Processors www.ti.com/omap

Wireless Connectivity www.ti.com/wirelessconnectivity

TI E2E Community Home Page e2e.ti.com

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2011, Texas Instruments Incorporated