





**INA350** 

## INA350 Cost and Size Optimized, Low Power, 1.8-V to 5.5-V Selectable Gain **Instrumentation Amplifier**

## 1 Features

Texas

INSTRUMENTS


- Ideal for size, cost, and power conscious designs
- Selectable gain options
  - G = 10 or G = 20 (INA350ABS)
  - G = 30 or G = 50 (INA350CDS)
- Space saving ultra-small package options
  - 10-pin X2QFN (RUG) 3 mm<sup>2</sup>
  - 8-pin WSON (DSG) 4 mm<sup>2</sup>
  - 8-pin SOT23-THN (DDF) 4.64 mm<sup>2</sup>
- Optimized performance for 10-bit to 14-bit systems
  - CMRR: 95 dB (typical) across all gains
  - Offset voltage: 0.2 mV (typical) across all gains
  - Gain error (typical):
    - 0.05% for G = 10; 0.06% for G = 20
  - 0.075% for G = 30; 0.082% for G = 50
  - Bandwidth: 100 kHz for G = 10 (typical)
- Drives 500 pF with less than 20% overshoot • (typical)
- Optimized quiescent current: 100 µA (typical)
- Shutdown option for power conscious applications
- Supply range: 1.8 V (±0.9 V) to 5.5 V (±2.75 V)
- Specified temperature range: -40°C to 125°C •

## 2 Applications

- Bridge network sensing ٠
- Differential to single-ended conversion
- Weigh scale

•

- Analog input module
- Flow transmitter ٠
- Wearable fitness and activity monitor ٠
- Blood glucose monitor
- Pressure and temperature sensing



Note: 90 kO for INA350ABS and 145 kO for INA350CDS

## Simplified Internal Schematic

## **3 Description**

INA350 is a selectable-gain instrumentation amplifier that offers four gain options across INA350ABS and INA350CDS variants available in small packages. INA350ABS has gain options of 10 or 20 and INA350CDS has gain options of 30 or 50. These gain options can be selected by toggling the gain select (GS) pin. INA350 is ideal for bridge-type sensing and for differential to single-ended conversion applications.

Built with precision matched integrated resistors, INA350 saves on bill of materials (BOM) costs, pick-and-place machine handling costs, and board space by removing the need for precise or closelymatched external resistors. The device interface directly to low-speed, 10-bit to 14-bit, analog-to-digital converters (ADC) and is ideal for replacing discrete implementation of instrumentation amplifiers built with commodity amplifiers and discrete resistors.

Designed with the three-amplifier architecture, INA350 is optimized for delivering performance. It achieves 85 dB of minimum CMRR and 0.6% of maximum gain error, along with 1.2 mV of maximum offset across all gain options, while consuming just 125 µA of maximum quiescent current. It has an integrated shutdown option to turn off the amplifier when idle for additional power savings in battery powered applications.

#### Package Information PART NUMBER PACKAGE<sup>(1)</sup> BODY SIZE (NOM) DSG (WSON, 8) 2.00 mm × 2.00 mm INA350ABS, DDF (SOT-23, 8) 1.60 mm × 2.90 mm INA350CDS RUG (X2QFN, 10) 1.50 mm × 2.00 mm

(1)For all available packages, see the package option addendum at the end of the data sheet.





## **Table of Contents**

1 Features	1
2 Applications	1
3 Description	1
4 Revision History	2
5 Device Comparison Table	3
6 Pin Configuration and Functions	4
7 Specifications	6
7.1 Absolute Maximum Ratings	
7.2 ESD Ratings	
7.3 Recommended Operating Conditions	<mark>6</mark>
7.4 Thermal Information	6
7.5 Electrical Characteristics	7
7.6 Typical Characteristics	9
8 Detailed Description	19
8.1 Overview	
8.2 Functional Block Diagram	
8.3 Feature Description	

8.4 Device Functional Modes	.24
9 Application and Implementation	.25
9.1 Application Information	
9.2 Typical Applications	27
9.3 Power Supply Recommendations	.29
9.4 Layout	. 30
10 Device and Documentation Support	.31
10.1 Device Support	31
10.2 Documentation Support	
10.3 Receiving Notification of Documentation Updates.	.31
10.4 Support Resources	. 31
10.5 Trademarks	
10.6 Electrostatic Discharge Caution	.31
10.7 Glossary	
11 Mechanical, Packaging, and Orderable	
Information	. 31

## **4 Revision History**

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Ch	anges from Revision B (April 2022) to Revision C (May 2023)	Page
•	Removed the preview note for X2QFN (10) from the Package Information table	1
•	Removed the preview note for X2QFN (RUG) from the Device Comparison Table	3
•	Updated the Thermal Information table for X2QFN (RUG) production release	<mark>6</mark>
Ch	anges from Revision A (December 2021) to Revision B (April 2022)	Page
•	Removed the preview note for INA350CDS from the Package Information table	1
•	Removed the preview note for INA350CDS from the Device Comparison Table	3
•	Updated the Electrical Characteristics table for INA350CDS production release	6
	Included G = 30 and G = 50 data into the EMIRR Testing curve	
	Included G = 30 and G = 50 data into the Input Common-Mode Voltage vs Output Voltage curve	
	Removed the note about external resistor, RG	


Cł	hanges from Revision * (November 2021) to Revision A (December 2021)	Page
•	Changed the device status from Advance Information to Production Data	1




## **5 Device Comparison Table**

	NO. OF		PACKAGE LEADS	
DEVICE	CHANNELS	SOT-23-8 DDF	WSON DSG	X2QFN RUG
INA350ABS	1	8	8	8
INA350CDS	1	8	8	8

## **6** Pin Configuration and Functions





#### Table 6-1. Pin Functions

PIN NAME NO.		<b>TYPE</b> <sup>(1)</sup>	DESCRIPTION	
			DESCRIPTION	
IN–	2	I	Negative (inverting) input	
IN+	3	0	sitive (non-inverting) input	
OUT	6	_	utput	
REF	5	_	eference input. This pin must be driven by a low impedance source.	
GS	1	I	Gain select – logic low (G = 10 for INA350ABS and G = 30 for INA350CDS) Gain select – logic high (G = 20 for INA350ABS and G = 50 for INA350CDS) Gain select – no connect (G = 20 for INA350ABS and G = 50 for INA350CDS)	
SHDN	8	1	Shutdown – logic high (device enabled) Shutdown – logic low (device disabled) Shutdown – no connect (device enabled)	
V–	4	_	Negative supply	
V+	7	_	Positive supply	

(1) I = input, O = output






Figure 6-3. RUG Package, 10-Pin X2QFN (Top View)

Table 6-2. Pin Functions

PIN NAME NO.		TYPE <sup>(1)</sup>	DESCRIPTION	
			DESCRIPTION	
IN–	2	I	Negative (inverting) input	
IN+	3	0	Positive (noninverting) input	
OUT	7	_	Output	
REF	6	_	Reference input. This pin must be driven by a low impedance source.	
GS	1	I	Gain select – logic low (G = 10 for INA350ABS and G = 30 for INA350CDS) Gain select – logic high (G = 20 for INA350ABS and G = 50 for INA350CDS) Gain select – no connect (G = 20 for INA350ABS and G = 50 for INA350CDS)	
SHDN	9	I	Shutdown – logic high (device enabled) Shutdown – logic low (device disabled) Shutdown – no connect (device enabled)	
V–	4		ative supply	
V+	8	_	Positive supply	
NC	5, 10	_	No connect	

(1) I = input, O = output



## 7 Specifications

#### 7.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)<sup>(1)</sup>

		MIN	MAX	UNIT
Supply voltage, $V_S = (V+) - (V-)$		0	6	V
Signal input pins	Common mode voltage <sup>(2)</sup>	(V–) – 0.5	(V+) + 0.5	V
	Differential voltage <sup>(3)</sup>		V <sub>S</sub> + 0.2	V
	Current <sup>(2)</sup>	-10	10	mA
Output short-circuit <sup>(4)</sup>		Continuo	JS	
Operating Temperature, T <sub>A</sub>		-55	150	
Junction Temperature, T <sub>J</sub>			150	°C
Storage Temperature, T <sub>stg</sub>		-65	150	

(1) Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) Input pins are diode-clamped to the power-supply rails. Input signals that may swing more than 0.5 V beyond the supply rails must be current limited to 10 mA or less

(3) Differential input voltages greater than 0.5 V applied continuously can result in a shift to the input offset voltage above the maximum specification of this parameter. The magnitude of this effect increases as the ambient operating temperature rises.

(4) Short-circuit to  $V_S$  / 2.

### 7.2 ESD Ratings

				VALUE	UNIT
		Electrostatic discharge	Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(1)</sup>	±2000	V
	V <sub>(ESD)</sub> Electrostatic discharge		Charged-device model (CDM), per JEDEC specification JESD22-C101 <sup>(2)</sup>	±1000	v

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

### 7.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

		MIN	MAX	UNIT
Supply voltage $V_S = (V+) - (V-)$	Single-supply	1.8	5.5	V
	Dual-supply	±0.9	±2.75	v
Input Voltage Range		(V–)	(V+)	V
Specified temperature	Specified temperature	-40	125	°C

### 7.4 Thermal Information

		INA			
	THERMAL METRIC <sup>(1)</sup>		DDF (SOT-23- THN) DSG (WSON) RUG (X2QFN)		
		8 PINS	8 PINS	10 PINS	
R <sub>θJA</sub>	Junction-to-ambient thermal resistance	169.1	89.2	199.0	°C/W
R <sub>0JC(top)</sub>	Junction-to-case (top) thermal resistance	101.7	111.8	78.3	°C/W
R <sub>θJB</sub>	Junction-to-board thermal resistance	84.8	55.8	123.2	°C/W
Ψ <sub>JT</sub>	Junction-to-top characterization parameter	12.6	9.3	2.1	°C/W
Ψ <sub>JB</sub>	Junction-to-board characterization parameter	84.3	55.7	122.7	°C/W
R <sub>0JC(bot)</sub>	Junction-to-case (bottom) thermal resistance	n/a	31.0	n/a	°C/W

(1) For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.

## **7.5 Electrical Characteristics**

		/ <sub>IN+</sub> ) + (V <sub>IN</sub> )] / 2 = V <sub>S</sub> / 2, V <sub>IN</sub> TEST CONDIT		MIN	TYP	MAX	UNIT
NPUT							
/ <sub>OSI</sub>	Offset Voltage, RTI <sup>(1)</sup>	V <sub>S</sub> = 5.5 V	T <sub>A</sub> = 25°C		±0.2	±1.2	mV
/ <sub>OSI</sub>	Offset Voltage over T, RTI <sup>(1)</sup>	V <sub>S</sub> = 5.5 V	$T_A = -40^{\circ}C$ to $125^{\circ}C$			±1.3	mV
/ <sub>OSI</sub>	Offset temp drift, RTI <sup>(2)</sup>	V <sub>S</sub> = 5.5 V	$T_A = -40^{\circ}C$ to 125°C		±0.6		µV/°C
PSRR	Power-supply rejection ratio		T <sub>A</sub> = 25°C		20	75	μV/V
Z <sub>IN-DM</sub>	Differential Impedance				100    5		GΩ∥pF
Z <sub>IN-CM</sub>	Common Mode Impedance				100    9		GΩ∥pF
V <sub>СМ</sub>	Input Stage Common Mode Range <sup>(3)</sup>			(V–)		(V+)	V
CMRR DC	Common-mode rejection ratio, RTI	V <sub>CM</sub> = (V–) + 0.1 V to (V+) – 1 V, High CMRR Region	V <sub>S</sub> = 5.5 V, V <sub>REF</sub> = V <sub>S</sub> /2	85	95		dB
CMRR DC	Common-mode rejection ratio, RTI	$V_{CM} = (V_{-}) + 0.1 V$ to $(V_{+}) - 1 V$ , High CMRR Region	V <sub>S</sub> = 3.3 V, V <sub>REF</sub> = V <sub>S</sub> /2		94		dB
CMRR DC	Common-mode rejection ratio, RTI	$V_{CM} = (V_{-}) + 0.1 V$ to $(V_{+}) - 0.1 V$	$V_{\rm S}$ = 5.5 V, $V_{\rm REF}$ = $V_{\rm S}/2$	62	75		dB
BIAS CU	RRENT						
I <sub>B</sub>	Input bias current	$V_{CM} = V_S / 2$			±0.65		pА
los	Input offset current	$V_{CM} = V_S / 2$			±0.25		pА
NOISE V	OLTAGE						
PNI	Input referred voltage noise density <sup>(5)</sup>		f = 1 kHz		36		nV/√Hz
9 <sub>NI</sub>	Input referred voltage noise density <sup>(5)</sup>		f = 10 kHz		34		nV/√Hz
E <sub>NI</sub>	Input referred voltage noise <sup>(5)</sup>	f <sub>B</sub> = 0.1 Hz to 10 Hz			3.2		μV <sub>PP</sub>
n	Input current noise	f = 1 kHz	f = 1 kHz		22		fA/√Hz
GAIN	1		1 1			I	
		G = 10, V <sub>REF</sub> = V <sub>S</sub> /2			±0.05	±0.50	
05	Gain error <sup>(4)</sup>	G = 20, V <sub>REF</sub> = V <sub>S</sub> /2	V <sub>O</sub> = (V–) + 0.1 V to		±0.06	±0.60	0/
GE		G = 30, V <sub>REF</sub> = V <sub>S</sub> /2	(V+) – 0.1V		±0.075	±0.60	%
	Gain error <sup>(4)</sup>	G = 50, V <sub>REF</sub> = V <sub>S</sub> /2			±0.082	±0.60	
OUTPUT						I	
/ <sub>он</sub>	Positive rail headroom	$R_L$ = 10 k $\Omega$ to $V_S/2$			15	30	mV
/ <sub>OL</sub>	Negative rail headroom	$R_L = 10 \text{ k}\Omega \text{ to } V_S/2$			15	30	mV
C <sub>L</sub> Drive	Load capacitance drive	V <sub>O</sub> = 100 mV step, Overshoot < 20%	%		500		pF
Zo	Closed-loop output impedance	f = 10 kHz			51		Ω
SC	Short-circuit current	V <sub>S</sub> = 5.5 V			±20		mA
REQUE							
		G = 10			100		
	Bandwidth, –3 dB	G = 20			50		
ЗW		G = 30	$-V_{IN} = 10 \text{ mV}_{pk-pk}$		40		kHz
	Bandwidth, –3 dB	G = 50	1		25		
THD + N	Total harmonic distortion + noise	$V_{\rm S}$ = 5.5 V, $V_{\rm CM}$ = 2.75 V, $V_{\rm O}$ = 1 $V_{\rm R}$ f = 1 kHz, 80-kHz measurement BV			0.04		%
ΓHD + N	Total harmonic distortion + noise	$V_{\rm S}$ = 5.5 V, $V_{\rm CM}$ = 2.75 V, $V_{\rm O}$ = 1 V <sub>RMS</sub> , G = 50, R <sub>L</sub> = 100 kΩ f = 1 kHz, 80-kHz measurement BW	$\label{eq:V_S} \begin{array}{ c c c } V_{\rm S} = 5.5 \ V, \ V_{\rm CM} = 2.75 \\ V, \ V_{\rm O} = 1 \ V_{\rm RMS}, \ G = \\ 50, \ R_{\rm L} = 100 \ k\Omega \\ f = 1 \ {\rm kHz}, \ 80 {\rm \cdot kHz} \\ {\rm measurement} \ BW \end{array}$		0.15		%

For  $V_S = (V+) - (V-) = 1.8 V$  to 5.5 V (±0.9 V to ±2.75 V) at  $T_A = 25^{\circ}$ C,  $V_{REF} = V_S/2$ , G = 10, 20, 30, and 50,  $R_L = 10 \text{ k}\Omega$ 



## 7.5 Electrical Characteristics (continued)

For  $V_S = (V+) - (V-) = 1.8 \text{ V}$  to 5.5 V (±0.9 V to ±2.75 V) at  $T_A = 25^{\circ}$ C,  $V_{REF} = V_S/2$ , G = 10, 20, 30, and 50,  $R_L = 10 \text{ k}\Omega$  connected to  $V_S / 2$ ,  $V_{CM} = [(V_{IN+}) + (V_{IN-})] / 2 = V_S / 2$ ,  $V_{IN} = (V_{IN+}) - (V_{IN-}) = 0$  V and  $V_{OUT} = V_S / 2$  (unless otherwise noted)

				MIN	TYP	MAX	UNIT			
EMIRR	Electro-magnetic interference rejection ratio	f = 1 GHz, V <sub>IN_EMIRR</sub> = 100 mV			96		dB			
SR	Slew rate	V <sub>S</sub> = 5 V, V <sub>O</sub> = 2 V step			0.24		V/µs			
		G = 10, To 0.1%, V <sub>S</sub> = 5.5 V, V <sub>STEP</sub> =	= 2 V, C <sub>L</sub> = 10 pF		17					
		G = 10, To 0.01%, V <sub>S</sub> = 5.5 V, V <sub>STEP</sub>	= 2 V, C <sub>L</sub> = 10 pF		38					
	Settling time	G = 20, To 0.1%, V <sub>S</sub> = 5.5 V, V <sub>STEP</sub> =	= 2 V, C <sub>L</sub> = 10 pF		20					
		G = 20, To 0.01%, V <sub>S</sub> = 5.5 V, V <sub>STEP</sub>	= 2 V, C <sub>L</sub> = 10 pF		27					
t <sub>S</sub>		G = 30, To 0.1%, V <sub>S</sub> = 5.5 V, V <sub>STEP</sub> =	= 2 V, C <sub>L</sub> = 10 pF		30		μs			
		G = 30, To 0.01%, V <sub>S</sub> = 5.5 V, V <sub>STEP</sub>	= 2 V, C <sub>L</sub> = 10 pF		57					
	Settling time	G = 50, To 0.1%, V <sub>S</sub> = 5.5 V, V <sub>STEP</sub> =	= 2 V, C <sub>L</sub> = 10 pF		44					
		G = 50, To 0.01%, V <sub>S</sub> = 5.5 V, V <sub>STEP</sub>	= 2 V, C <sub>L</sub> = 10 pF		85					
	Overload recovery	V <sub>IN</sub> = 1 V, G = 10			16		μs			
	Overload recovery	V <sub>IN</sub> = 1 V, G = 50	V <sub>IN</sub> = 1 V, G = 50		6.5		μs			
REFERE				1						
R <sub>IN</sub>	Input impedance				60		kΩ			
	Voltage range			(V–)		(V+)	V			
	Gain to output				1		V/V			
	Reference gain error				±0.004		%			
POWER	SUPPLY	1				I				
Vs	Power-supply voltage	Single-supply		1.7		5.5	V			
Vs	Power-supply voltage	Dual-supply		±0.85		±2.75	V			
		V <sub>IN</sub> = 0 V			100	125				
lq	Quiescent current	T <sub>A</sub> = -40°C to 125°C				135	μΑ			
I <sub>QSD</sub>	Quiescent current per amplifier	All amplifiers disabled, SHDN = V–			0.70	1.25	μΑ			
V <sub>IL</sub>	Logic low threshold voltage (Gain Select)	G = 10 for INA350ABS, G = 30 for IN	A350CDS		(\	√–) + 0.2 V	V			
V <sub>IH</sub>	Logic high threshold voltage (Gain Select)	G = 20 for INA350ABS, G = 50 for IN	A350CDS	(V–) + 1 V			V			
t <sub>ON</sub>	Amplifier enable time (full shutdown) <sup>(6)</sup>	$V_{CM} = V_S / 2$ , $V_O = 0.9 \times V_S / 2$ , R <sub>L</sub> connected to V–			100		μs			
t <sub>OFF</sub>	Amplifier disable time <sup>(6)</sup>	$V_{CM} = V_S / 2$ , $V_O = 0.1 \times V_S / 2$ , R <sub>L</sub> connected to V–			4		μs			
	SHDN pin input bias current (per pin)	$(V+) \ge \overline{SHDN} \ge (V-) + 1 V$			10		nA			
	SHDN pin input bias current (per pin)	(V–) ≤ <del>SHDN</del> ≤ (V–) + 0.2 V			175		nA			

(1) Total offset, referred-to-input (RTI):  $V_{OS} = (V_{OSI}) + (V_{OSO} / G)$ .

(2) Offset drifts are uncorrelated. Input-referred offset drift is calculated using:  $\Delta V_{OS(RTI)} = \sqrt{[\Delta V_{OSI}]^2 + (\Delta V_{OSO}/G)^2]}$ 

(3) Input common mode voltage range of the just the input stage of the instrumentation amplifier. The entire INA350x input range depends on the combination input common-mode voltage, differential voltage, gain, reference voltage and power supply voltage. *Typical Characteristic* curves will be added with more information.

(4) Min and Max values are specified by characterization.


(5) Total RTI voltage noise is equal to:  $e_{N(RTI)} = \sqrt{[e_{NI}^2 + (e_{NO}/G)^2]}$ 

(6) Disable time  $(t_{OFF})$  and enable time  $(t_{ON})$  are defined as the time interval between the 50% point of the signal applied to the SHDN pin and the point at which the output voltage reaches the 10% (disable) or 90% (enable) level.




### 7.6 Typical Characteristics

at  $T_A = 25^{\circ}C$ ,  $V_S = (V+) - (V-) = 5.5 V$ ,  $V_{IN} = (V_{IN+}) - (V_{IN-}) = 0 V$ ,  $R_L = 10 k\Omega$ ,  $C_L = 10 pF$ ,  $V_{REF} = V_S / 2$ ,  $V_{CM} = [(V_{IN+}) + (V_{IN-})] / 2 = V_S / 2$ ,  $V_{OUT} = V_S / 2$  and G = 10 (unless otherwise noted)






at  $T_A = 25^{\circ}$ C,  $V_S = (V+) - (V-) = 5.5$  V,  $V_{IN} = (V_{IN+}) - (V_{IN-}) = 0$  V,  $R_L = 10$  k $\Omega$ ,  $C_L = 10$  pF,  $V_{REF} = V_S / 2$ ,  $V_{CM} = [(V_{IN+}) + (V_{IN-})] / 2 = V_S / 2$ ,  $V_{OUT} = V_S / 2$  and G = 10 (unless otherwise noted)






at  $T_A = 25^{\circ}C$ ,  $V_S = (V+) - (V-) = 5.5 V$ ,  $V_{IN} = (V_{IN+}) - (V_{IN-}) = 0 V$ ,  $R_L = 10 k\Omega$ ,  $C_L = 10 pF$ ,  $V_{REF} = V_S / 2$ ,  $V_{CM} = [(V_{IN+}) + (V_{IN-})] / 2 = V_S / 2$ ,  $V_{OUT} = V_S / 2$  and G = 10 (unless otherwise noted)




at  $T_A = 25^{\circ}C$ ,  $V_S = (V+) - (V-) = 5.5 V$ ,  $V_{IN} = (V_{IN+}) - (V_{IN-}) = 0 V$ ,  $R_L = 10 k\Omega$ ,  $C_L = 10 pF$ ,  $V_{REF} = V_S / 2$ ,  $V_{CM} = [(V_{IN+}) + (V_{IN-})] / 2 = V_S / 2$ ,  $V_{OUT} = V_S / 2$  and G = 10 (unless otherwise noted)






at  $T_A = 25^{\circ}$ C,  $V_S = (V_+) - (V_-) = 5.5 \text{ V}$ ,  $V_{IN} = (V_{IN+}) - (V_{IN-}) = 0 \text{ V}$ ,  $R_L = 10 \text{ k}\Omega$ ,  $C_L = 10 \text{ pF}$ ,  $V_{REF} = V_S / 2$ ,  $V_{CM} = [(V_{IN+}) + (V_{IN-})] / 2 = V_S / 2$ ,  $V_{OUT} = V_S / 2$  and G = 10 (unless otherwise noted)






at  $T_A = 25^{\circ}$ C,  $V_S = (V+) - (V-) = 5.5$  V,  $V_{IN} = (V_{IN+}) - (V_{IN-}) = 0$  V,  $R_L = 10$  k $\Omega$ ,  $C_L = 10$  pF,  $V_{REF} = V_S / 2$ ,  $V_{CM} = [(V_{IN+}) + (V_{IN-})] / 2 = V_S / 2$ ,  $V_{OUT} = V_S / 2$  and G = 10 (unless otherwise noted)








at  $T_A = 25^{\circ}$ C,  $V_S = (V+) - (V-) = 5.5$  V,  $V_{IN} = (V_{IN+}) - (V_{IN-}) = 0$  V,  $R_L = 10$  k $\Omega$ ,  $C_L = 10$  pF,  $V_{REF} = V_S / 2$ ,  $V_{CM} = [(V_{IN+}) + (V_{IN-})] / 2 = V_S / 2$ ,  $V_{OUT} = V_S / 2$  and G = 10 (unless otherwise noted)




15

at  $T_A = 25^{\circ}C$ ,  $V_S = (V+) - (V-) = 5.5 \text{ V}$ ,  $V_{IN} = (V_{IN+}) - (V_{IN-}) = 0 \text{ V}$ ,  $R_L = 10 \text{ k}\Omega$ ,  $C_L = 10 \text{ pF}$ ,  $V_{REF} = V_S / 2$ ,  $V_{CM} = [(V_{IN+}) + (V_{IN-})] / 2 = V_S / 2$ ,  $V_{OUT} = V_S / 2$  and G = 10 (unless otherwise noted)






at  $T_A = 25^{\circ}C$ ,  $V_S = (V+) - (V-) = 5.5 V$ ,  $V_{IN} = (V_{IN+}) - (V_{IN-}) = 0 V$ ,  $R_L = 10 k\Omega$ ,  $C_L = 10 pF$ ,  $V_{REF} = V_S / 2$ ,  $V_{CM} = [(V_{IN+}) + (V_{IN-})] / 2 = V_S / 2$ ,  $V_{OUT} = V_S / 2$  and G = 10 (unless otherwise noted)





at  $T_A = 25^{\circ}$ C,  $V_S = (V+) - (V-) = 5.5 \text{ V}$ ,  $V_{IN} = (V_{IN+}) - (V_{IN-}) = 0 \text{ V}$ ,  $R_L = 10 \text{ k}\Omega$ ,  $C_L = 10 \text{ pF}$ ,  $V_{REF} = V_S / 2$ ,  $V_{CM} = [(V_{IN+}) + (V_{IN-})] / 2 = V_S / 2$ ,  $V_{OUT} = V_S / 2$  and G = 10 (unless otherwise noted)





## 8 Detailed Description


#### 8.1 Overview

INA350 is a selectable gain instrumentation amplifier mainly targeted to provide an integrated small size, cost effective solution for applications employing general purpose INAs or discrete implementation of INAs using commodity amplifiers and resistors. It incorporates a three op amp INA architecture integrating three operational amplifiers and seven precision matched integrated resistors. It is mainly targeted for use in 10-bit to 14-bit systems, but calibrating offset and gain error at a system level can further improve system resolution and accuracy enabling use in precision applications.

One of the key features of INA350 is that it does not need any external resistors to set the gain. Often these external resistors warrant tighter tolerance and need to be routed carefully which adds to the system complexity and cost. INA350 is offered in four gain options across two variants. INA350ABS has two gain options of 10 and 20. INA350CDS has two other gain options of 30 and 50. Gains can be selected by connecting the GS pin to logic high or logic low. Note that the GS pin can be left floating as well, as it is designed with an internal pull up to default to the same configuration as GS tied logic high.

The INA350 is developed for industrial applications in factory automation and appliances sector where pressure sensing and temperature sensing are done using bridge-type sensor networks and load cells. It can also be used in tight spaces in medical applications such as patient monitoring, sleep diagnostics, electronic hospital beds, blood glucose monitoring, and so forth for voltage sensing and differential to single-ended conversion. INA350 can enable these applications to reduce their overall size through the use of tiny packages, including a 2-mm × 1.5-mm X2QFN package and a 2-mm × 2-mm WSON package.

### 8.2 Functional Block Diagram



Note: 90 k $\Omega$  for INA350ABS and 145 k $\Omega$  for INA350CDS

### Simplified Internal Schematic



#### 8.3 Feature Description

#### 8.3.1 Gain-Setting

The gain equation of INA350ABS can be given by Equation 1:

$$G = 1 + \frac{180 \, k\Omega}{R_G} \tag{1}$$

The value of the internal gain resistor R<sub>G</sub> for INA350ABS can then be derived from the gain equation:

$$R_G = \frac{180 \, k\Omega}{G - 1} \tag{2}$$

Similarly The gain equation of INA350CDS can be given by Equation 3:

$$G = 1 + \frac{290 \, k\Omega}{R_G} \tag{3}$$

The value of the internal gain resistor  $R_G$  for INA350CDS can then be derived from the gain equation:

$$R_G = \frac{290 \, k\Omega}{G - 1} \tag{4}$$

Table 8-1 provides how to choose different gain options across INA350ABS and INA350CDS. The 60-k $\Omega$ , 90-k $\Omega$ , and 145-k $\Omega$  resistors mentioned are all typical values of the on-chip resistors.

Table 8-1. Gain Selection Table								
DEVICE	SELECTED GAIN							
INA350ABS	High or No Connect	20						
INAGOUADO	Low	10						
INA350CDS	High or No Connect	50						
INASSUCDS	Low	30						

#### 8.3.1.1 Gain Error and Drift

Gain error in INA350 is limited by the mismatch of the integrated precision resistors and it is specified based on characterization results. Gain error of maximum 0.5% can be expected for the gains of 10 and 0.6% for the gains of 20, 30 and 50. Gain drift in INA350 is limited by the slight mismatch of the temperature coefficient of the integrated resistors. Since these integrated resistors are precision matched with low temperature coefficient resistors to begin with, the overall gain drift would be much better in comparison to discrete implementation of the instrumentation amplifiers built using external resistors.


#### 8.3.2 Input Common-Mode Voltage Range

INA350 has two gain stages, the first stage has a common-mode gain of 1 and a differential gain set by the GS pin. The second stage is configured in a difference-amplifier configuration with differential gain of 1 and ideally rejects all of the input common mode completely. The second stage also provides a gain of 1 from REF pin to set the output common-mode voltage.

The linear input voltage range of the INA350, even for a rail-to-rail first stage is dictated by the signal swing at output of the first stage as well as the input common-mode voltage range output swing of the second stage. It is imperative that the INA350 stays linear for a particular combination of gain, reference, and input common-mode voltage for a chosen input differential. Input common-mode voltage ( $V_{CM}$ ) vs output voltage graphs ( $V_{OUT}$ ) in this section show a particular reference voltage and gain configuration to outline the linear performance region of INA350. A good common-mode rejection can be expected when operating with in the limits of the V<sub>CM</sub> vs V<sub>OUT</sub> graph. Note, that the INA350 linear input voltage cannot be close to or extend beyond the supply rails as the output of the first stage will be driven into saturation.




The common-mode range for the most common operating conditions is outlined as follows. Figure 8-1 shows the region of operation where a minimum of 85 dB can be achieved. Figure 8-2 has much wider region of operation with a lower minimum CMRR of 62 dB, because the input signal crosses over the transition region of the input pairs to achieve rail-to-rail operation. The common-mode range for other operating conditions is best calculated with the INA  $V_{CM}$  vs  $V_{OUT}$  tool located under the *Amplifiers and Comparators* section of the Analog Engineer's Calculator on ti.com. INA350-HCM model can be specifically used for applications requiring high CMRR and corresponds to performance shown in Figure 8-1. INA350xxS model can be used for applications where the input common mode can be expected to vary rail-to-rail and it corresponds to performance shown in Figure 8-2 where CMRR drops to 62-dB minimum.



#### 8.3.3 EMI Rejection

The INA350 uses integrated electromagnetic interference (EMI) filtering to reduce the effects of EMI from sources such as wireless communications and densely-populated boards with a mix of analog signal chain and digital components. EMI immunity can be improved with circuit design techniques; the INA350 benefits from these design improvements. Texas Instruments has developed the ability to accurately measure and quantify the immunity of an operational amplifier over a broad frequency spectrum extending from 10 MHz to 6 GHz. Figure 8-3 shows the results of this testing on the INA350. Table 8-2 provides the EMIRR IN+ values for the INA350 at particular frequencies commonly encountered in real-world applications. The *EMI Rejection Ratio of Operational Amplifiers* application report contains detailed information on the topic of EMIRR performance as it relates to op amps and is available for download from www.ti.com.






#### Figure 8-3. EMIRR Testing

#### Table 8-2. INA350 EMIRR IN+ for Frequencies of Interest

FREQUENCY	APPLICATION OR ALLOCATION	EMIRR IN+
400 MHz	Mobile radio, mobile satellite, space operation, weather, radar, ultra-high frequency (UHF) applications	60 dB
900 MHz	Global system for mobile communications (GSM) applications, radio communication, navigation, GPS (to 1.6 GHz), GSM, aeronautical mobile, UHF applications	92 dB
1.8 GHz	GSM applications, mobile personal communications, broadband, satellite, L-band (1 GHz to 2 GHz)	90 dB
2.4 GHz	802.11b, 802.11g, 802.11n, Bluetooth <sup>®</sup> , mobile personal communications, industrial, scientific and medical (ISM) radio band, amateur radio and satellite, S-band (2 GHz to 4 GHz)	95 dB
3.6 GHz	Radiolocation, aero communication and navigation, satellite, mobile, S-band	108 dB
5 GHz	802.11a, 802.11n, aero communication and navigation, mobile communication, space and satellite operation, C-band (4 GHz to 8 GHz)	105 dB

#### 8.3.4 Typical Specifications and Distributions

Designers often have questions about a typical specification of an amplifier in order to design a more robust circuit. Due to natural variation in process technology and manufacturing procedures, every specification of an amplifier will exhibit some amount of deviation from the ideal value, like an amplifier's input offset voltage. These deviations often follow *Gaussian (bell curve)*, or *normal* distributions, and circuit designers can leverage this information to guard band their system, even when there is not a minimum or maximum specification in the *Electrical Characteristics* table.



#### Figure 8-4. Ideal Gaussian Distribution

Figure 8-4 shows an example distribution, where  $\mu$ , or mu, is the mean of the distribution, and where  $\sigma$ , or *sigma*, is the standard deviation of a system. For a specification that exhibits this kind of distribution, approximately two-thirds (68.26%) of all units can be expected to have a value within one standard deviation, or one sigma, of the mean (from  $\mu - \sigma$  to  $\mu + \sigma$ ).

Depending on the specification, values listed in the *typical* column of the *Electrical Characteristics* table are represented in different ways. As a general rule, if a specification naturally has a nonzero mean (for example, like gain bandwidth), then the typical value is equal to the mean ( $\mu$ ). However, if a specification naturally has a mean near zero (like input offset voltage), then the typical value is equal to the mean plus one standard deviation ( $\mu + \sigma$ ) in order to most accurately represent the typical value.

You can use this chart to calculate approximate probability of a specification in a unit; for example, the INA350 typical input voltage offset is 200  $\mu$ V, so 68.2% of all INA350 devices are expected to have an offset from –200  $\mu$ V to +200  $\mu$ V. At 4  $\sigma$  (±800  $\mu$ V), 99.9937% of the distribution has an offset voltage less than ±800  $\mu$ V, which means 0.0063% of the population is outside of these limits, which corresponds to about 1 in 15,873 units.

Specifications with a value in the minimum or maximum column are assured by TI, and units outside these limits will be removed from production material. For example, the INA350 family has a maximum offset voltage of 1.2 mV at 25°C, and even though this corresponds to 6  $\sigma$  (≈1 in 500 million units), which is extremely unlikely, TI assures that any unit with larger offset than 1.2 mV will be removed from production material.

For specifications with no value in the minimum or maximum column, consider selecting a sigma value of sufficient guard band for your application, and design worst-case conditions using this value. As stated earlier, the 6- $\sigma$  value corresponds to about 1 in 500 million units, which is an extremely unlikely chance, and could be an option as a wide guard band to design a system around. In this case, the INA350 family does not have a maximum or minimum for offset voltage drift, but based on Figure 7-2 and the typical value of 0.6  $\mu$ V/°C in the *Electrical Characteristics* table, it can be calculated from that the 6- $\sigma$  value for offset voltage drift is about 2  $\mu$ V/°C. When designing for worst-case system conditions, this value can be used to estimate the worst possible offset drift without having an actual minimum or maximum value.

However, process variation and adjustments over time can shift typical means and standard deviations, and unless there is a value in the minimum or maximum specification column, TI cannot assure the performance of a device. This information should be used only to estimate the performance of a device.



#### 8.3.5 Electrical Overstress

Designers often ask questions about the capability of an operational amplifier to withstand electrical overstress. These questions tend to focus on the device inputs, but can involve the supply voltage pins or even the output pin. Each of these different pin functions have electrical stress limits determined by the voltage breakdown characteristics of the particular semiconductor fabrication process and specific circuits connected to the pin. Additionally, internal electrostatic discharge (ESD) protection is built into these circuits to protect them from accidental ESD events both before and during product assembly.

Having a good understanding of this basic ESD circuitry and its relevance to an electrical overstress event is helpful. Figure 8-5 shows the ESD circuits contained in the INA350 devices. The ESD protection circuitry involves several current-steering diodes connected from the input and output pins and routed back to the internal power supply lines, where they meet at an absorption device internal to the operational amplifier. This protection circuitry is intended to remain inactive during normal circuit operation.




Figure 8-5. Equivalent Internal ESD Circuitry

#### 8.4 Device Functional Modes

The INA350 has a shutdown or disable mode to enable power savings in battery powered applications. The shutdown mode has a maximum quiescent current of just 1.25  $\mu$ A, which is 100 times lower from the quiescent current when the amplifier is powered-on or enabled.

INA350 enters disable mode when the SHDN pin is tied low. INA350 is enabled when the SHDN pin is tied high. A no connection or a floating SHDN pin enables or powers-on the INA as the pin has an internal pull up current to default to the same configuration as SHDN pin tied high.



## 9 Application and Implementation

#### Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

#### 9.1 Application Information

#### 9.1.1 Reference Pin

The output voltage of the INA350 is developed with respect to the voltage on the reference pin (REF). Often in dual-supply operation, REF pin connects to the low-impedance system ground. In single-supply operation, offsetting the output signal to a precise mid-supply level is useful (for example, 2.75-V in a 5.5-V supply environment). To accomplish this level shift, a voltage source must be connected to the REF pin to level-shift the output so that the INA350 can drive a single-supply ADC.

The voltage source applied to the reference pin must have a low output impedance. Any resistance at the reference pin ( $R_{REF}$ ) in is in series with the internal 60-k $\Omega$  resistor.

The parasitic resistance at the reference pin ( $R_{REF}$ ) creates an imbalance in the four resistors of the internal difference amplifier that results in a degraded common-mode rejection ratio (CMRR). For the best performance, keep the source impedance to the REF pin ( $R_{REF}$ ) less than 5  $\Omega$ .

Voltage reference devices are an excellent option for providing a low-impedance voltage source for the reference pin. However, if a resistor voltage divider generates a reference voltage, buffer the divider by an op amp, as shown in Figure 9-1, to avoid CMRR degradation.





Figure 9-1. Use an Op Amp to Buffer Reference Voltages

#### 9.1.2 Input Bias Current Return Path

The input impedance of the INA350 is extremely high, but a path must be provided for the input bias current of both inputs. This input bias current is typically a few pico amps but at high temperature this can be a few nano amps. High input impedance means that the input bias current changes little with varying input voltage.

For proper operation, input circuitry must provide a path for this input bias current. Figure 9-2 shows various provisions for an input bias current path. Without a bias current path, the inputs float to a potential that exceeds the common-mode range of the INA350, and the input amplifiers saturate. If the differential source resistance is low, the bias current return path connects to one input (as shown in the thermocouple example in Figure 9-2). With a higher source impedance, use two equal resistors to provide a balanced input, with the possible advantages of a lower input offset voltage as a result of bias current, and better high-frequency common-mode rejection.





Copyright © 2017, Texas Instruments Incorporated

Figure 9-2. Providing an Input Common-Mode Current Path



#### 9.2 Typical Applications

#### 9.2.1 Resistive-Bridge Pressure Sensor


The INA350 is an integrated instrumentation amplifier that measures small differential voltages while simultaneously rejecting larger common-mode voltages. The device offers a low power consumption of 100  $\mu$ A (typical) and has a smaller form factor.

The device is designed for portable applications where sensors measure physical parameters, such as changes in fluid, pressure, temperature, or humidity. An example of a pressure sensor used in the medical sector is in portable infusion pumps or dialysis machines.

The pressure sensor is made of a piezo-resistive element that can be derived as a classical 4-resistor Wheatstone bridge.

Occlusion (infusion of fluids, medication, or nutrients) happens only in one direction, and therefore can only cause the resistive element (R) to expand. This expansion causes a change in voltage on one leg of the Wheatstone bridge, which induces a differential voltage V<sub>DIFF</sub>.

Figure 9-3 shows an example circuit for an occlusion pressure sensor application, as required in infusion pumps. When blockage (occlusion) occurs against a set-point value, the tubing depresses, thus causing the piezo-resistive element to expand (Node AD:  $R + \Delta R$ ). The signal chain connected to the bridge downstream processes the pressure change and can trigger an alarm.





Low-tolerance bridge resistors must be used to minimize the offset and gain errors.

Given that there is only a positive differential voltage applied, this circuit is laid out in single-ended supply mode. The excitation voltage,  $V_{EXT}$ , to the bridge must be precise and stable; otherwise, measurement errors can be introduced.



#### 9.2.1.1 Design Requirements

Table 9-1. Design Requirements									
DESCRIPTION VALUE									
Single supply voltage	V <sub>S</sub> = 5.5 V								
Excitation voltage	V <sub>EXT</sub> = 5.0 V								
Occlusion pressure range	P = 1 psi to 12 psi, increments of P = 0.5 psi								
Occlusion pressure sensitivity	S = 2 ±0.5 (25%) mV/V/psi								
Occlusion pressure impedance (R)	R = 4.99 kΩ ±50 Ω (0.1%)								
Total pressure sampling rate	Sr = 20 Hz								
Full-scale range of ADC	$V_{ADC(fs)} = V_{OUT} = 3.0 V$								

For this application, the design requirements are as provided in Table 9-1.

#### 9.2.1.2 Detailed Design Procedure

This section provides basic calculations to lay out the instrumentation amplifier with respect to the given design requirements.

One of the key considerations in resistive-bridge sensors is the common-mode voltage,  $V_{CM}$ . If the bridge is balanced (no pressure, thus no voltage change),  $V_{CM(zero)}$  is half of the bridge excitation ( $V_{EXT}$ ). In this example  $V_{CM(zero)}$  is 2.5 V. For the maximum pressure of 12 psi, the bridge common-mode voltage,  $V_{CM(MAX)}$ , is calculated by:

$$V_{CM(MAX)} = \frac{V_{DIFF}}{2} + V_{CM(zero)}$$
(5)

where

$$V_{DIFF} = S_{MAX} \times V_{EXT} \times P_{MAX} = 2.5 \frac{mV}{V \times psi} \times 5V \times 12 psi = 150 mV$$
(6)

Thus, the maximum common-mode voltage applied results in:

$$V_{CM(MAX)} = \frac{150 \, mV}{2} + 2.5 \, V = 2.575 \, V \tag{7}$$

Similarly, the minimum common-mode voltage can be calculated as,

$$V_{CM(MIN)} = \frac{-150 \, mV}{2} + \, 2.5 \, V = 2.425 \, V \tag{8}$$

The next step is to calculate the gain required for the given maximum sensor output voltage span,  $V_{DIFF}$ , in respect to the required  $V_{OUT}$ , which is the full-scale range of the ADC.

The following equation calculates the gain value using the maximum input voltage and the required output voltage:

$$G = \frac{V_{OUT}}{V_{DIFF(MAX)}} = \frac{3.0 V}{150 mV} = 20 V/V$$
(9)

Considering, INA350 is a selectable gain INA with gain options of 10, 20, 30, 50, the INA350ABS with GS tied high enables G = 20 ensuring the maximum output signal swing for the ADC.

Next, let us make sure that the INA350 can operate within this range checking the *Input Common-Mode Voltage vs Output Voltage* curves in the *Typical Characteristics* section. The relevant figure is also in this section for convenience. Looking at Figure 9-4, we can confirm that a output signal swing of 3 V is supported for the input signal swing between 2.425 V and 2.575 V, thus making sure of the linear operation.








Figure 9-4. Input Common-Mode Voltage vs Output Voltage (High CMRR Region)

Additional series resistor in the Wheatstone bridge string (R1) may or may not be required. This is decided based on the intended output voltage swing for a particular combination of supply voltage, reference voltage and the selected gain for an input common mode voltage range. R1 helps adjust the input common-mode voltage range, and thus can help accommodate the intended output voltage swing. In this particular example, it are not required and can be shorted out.

#### 9.2.1.3 Application Curves

The following typical characteristic curve is for the circuit in Figure 9-3.





#### **9.3 Power Supply Recommendations**

The nominal performance of the INA350 is specified with a supply voltage of  $\pm 2.75$  V and midsupply reference voltage. The device also operates using power supplies from  $\pm 0.85$  V (1.7 V) to  $\pm 2.75$  V (5.5 V) and non-midsupply reference voltages with excellent performance. Parameters can vary significantly with operating voltage and reference voltage.



## 9.4 Layout

### 9.4.1 Layout Guidelines

Attention to good layout practices is always recommended. For best operational performance of the device, use the following PCB layout practices:

- Make sure that both input paths are well-matched for source impedance and capacitance to avoid converting common-mode signals into differential signals.
- Use bypass capacitors to reduce the coupled noise by providing low-impedance power sources local to the analog circuitry.
  - Connect low-ESR, 0.1-µF ceramic bypass capacitors between each supply pin and ground, placed as close to the device as possible. A single bypass capacitor from V+ to ground is applicable for singlesupply applications.
- Route the input traces as far away from the supply or output traces as possible to reduce parasitic coupling. If
  these traces cannot be kept separate, crossing the sensitive trace perpendicular is much better than crossing
  in parallel with the noisy trace.
- · Place the external components as close to the device as possible.
- Keep the traces as short as possible.

#### 9.4.2 Layout Example




Figure 9-6. Example Schematic and Associated PCB Layout



## **10 Device and Documentation Support**

#### **10.1 Device Support**

#### 10.1.1 Development Support

- SPICE-based analog simulation program TINA-TI software folder
- Analog Engineers Calculator

#### 10.1.1.1 PSpice<sup>®</sup> for TI

PSpice<sup>®</sup> for TI is a design and simulation environment that helps evaluate performance of analog circuits. Create subsystem designs and prototype solutions before committing to layout and fabrication, reducing development cost and time to market.

#### **10.2 Documentation Support**

#### **10.2.1 Related Documentation**

For related documentation see the following:

• Texas Instruments, EMI Rejection Ratio of Operational Amplifiers application report

#### **10.3 Receiving Notification of Documentation Updates**

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Subscribe to updates* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

#### **10.4 Support Resources**

TI E2E<sup>™</sup> support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

#### 10.5 Trademarks

TI E2E<sup>™</sup> is a trademark of Texas Instruments.

Bluetooth® is a registered trademark of Bluetooth SIG, Inc.

PSpice<sup>®</sup> is a registered trademark of Cadence Design Systems, Inc.

All trademarks are the property of their respective owners.

#### **10.6 Electrostatic Discharge Caution**



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

#### 10.7 Glossary

TI Glossary This glossary lists and explains terms, acronyms, and definitions.

### 11 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.



### PACKAGING INFORMATION

Orderable Device	Status	Package Type	•	Pins	Package	Eco Plan	Lead finish/	MSL Peak Temp	Op Temp (°C)	Device Marking	Samples
	(1)		Drawing		Qty	(2)	Ball material	(3)		(4/5)	
							(6)				
INA350ABSIDDFR	ACTIVE	SOT-23-THIN	DDF	8	3000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	IN35A	Samples
INA350ABSIDSGR	ACTIVE	WSON	DSG	8	3000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	135A	Samples
INA350ABSIRUGR	ACTIVE	X2QFN	RUG	10	3000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	1NC	Samples
INA350CDSIDDFR	ACTIVE	SOT-23-THIN	DDF	8	3000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	IN35C	Samples
INA350CDSIDSGR	ACTIVE	WSON	DSG	8	3000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	135C	Samples
INA350CDSIRUGR	ACTIVE	X2QFN	RUG	10	3000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	1ND	Samples

<sup>(1)</sup> The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

<sup>(2)</sup> RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

<sup>(3)</sup> MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

<sup>(5)</sup> Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

<sup>(6)</sup> Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.



www.ti.com

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.




Texas

STRUMENTS

### TAPE AND REEL INFORMATION





#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal												
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
INA350ABSIDDFR	SOT-23- THIN	DDF	8	3000	180.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
INA350ABSIDSGR	WSON	DSG	8	3000	180.0	8.4	2.3	2.3	1.15	4.0	8.0	Q2
INA350ABSIRUGR	X2QFN	RUG	10	3000	180.0	8.4	1.75	2.25	0.55	4.0	8.0	Q1
INA350CDSIDDFR	SOT-23- THIN	DDF	8	3000	180.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
INA350CDSIDSGR	WSON	DSG	8	3000	180.0	8.4	2.3	2.3	1.15	4.0	8.0	Q2
INA350CDSIRUGR	X2QFN	RUG	10	3000	180.0	8.4	1.75	2.25	0.55	4.0	8.0	Q1



www.ti.com

## PACKAGE MATERIALS INFORMATION

23-Jul-2023



Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
INA350ABSIDDFR	SOT-23-THIN	DDF	8	3000	210.0	185.0	35.0
INA350ABSIDSGR	WSON	DSG	8	3000	210.0	185.0	35.0
INA350ABSIRUGR	X2QFN	RUG	10	3000	210.0	185.0	35.0
INA350CDSIDDFR	SOT-23-THIN	DDF	8	3000	210.0	185.0	35.0
INA350CDSIDSGR	WSON	DSG	8	3000	210.0	185.0	35.0
INA350CDSIRUGR	X2QFN	RUG	10	3000	210.0	185.0	35.0

## **MECHANICAL DATA**



B. This drawing is subject to change without notice.
C. QFN (Quad Flatpack No-Lead) package configuration.
D. This package complies to JEDEC MO-288 variation X2EFD.



## DSG 8

2 x 2, 0.5 mm pitch

## **GENERIC PACKAGE VIEW**

## WSON - 0.8 mm max height

PLASTIC SMALL OUTLINE - NO LEAD

This image is a representation of the package family, actual package may vary. Refer to the product data sheet for package details.





## DSG0008A



## **PACKAGE OUTLINE**

## WSON - 0.8 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.

3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.



## DSG0008A

# **EXAMPLE BOARD LAYOUT**

## WSON - 0.8 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



NOTES: (continued)

 This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).

 Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.



## DSG0008A

# **EXAMPLE STENCIL DESIGN**

## WSON - 0.8 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



# **DDF0008A**



## **PACKAGE OUTLINE**

## SOT-23 - 1.1 mm max height

PLASTIC SMALL OUTLINE



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M. 2. This drawing is subject to change without notice. 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.



## **DDF0008A**

# **EXAMPLE BOARD LAYOUT**

## SOT-23 - 1.1 mm max height

PLASTIC SMALL OUTLINE



4. Publication IPC-7351 may have alternate designs.

5. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



## **DDF0008A**

## **EXAMPLE STENCIL DESIGN**

## SOT-23 - 1.1 mm max height

PLASTIC SMALL OUTLINE



6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

7. Board assembly site may have different recommendations for stencil design.



### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2023, Texas Instruments Incorporated