debounced input.

DALLAS JUJXIJU SEMICONDUCTOR JUJXIJU Low-Voltage SPI/3-Wire RTCs with Trickle Charger

General Description

The low-voltage serial-peripheral interface (SPI™)

DS1390/DS1391/DS1394 and the low-voltage 3-wire

DS1392/DS1393 real-time clocks (RTCs) are clocks/cal-

endars that provide hundredths of a second, seconds,

minutes, hours, day, date, month, and year information.

The date at the end of the month is automatically

adjusted for months with fewer than 31 days, including

corrections for leap year. The clock operates in either

the 24-hour or 12-hour format with an AM/PM indicator.

One programmable time-of-day alarm is provided. A temperature-compensated voltage reference monitors

the status of V_{CC} and automatically disables the bus

interface and switches to the backup supply if a power

failure is detected. On the DS1390, a single open-drain output provides a CPU interrupt or a square wave at

one of four selectable frequencies. The DS1391

replaces the SQW/INT pin with a RST output/

The DS1390, DS1391, and DS1394 are programmed

serially through an SPI-compatible, bidirectional bus.

The DS1392 and DS1393 communicate over a 3-wire

serial bus, and the extra pin is used for either a separate interrupt pin or a RST output/debounced input.

All five devices are available in a 10-pin μ SOP package, and are rated over the industrial temperature range.

_Features

- Real-Time Clock Counts Hundredths of Seconds, Seconds, Minutes, Hours, Day, Date, Month, and Year with Leap-Year Compensation Valid Up to 2100
- Output Pin Configurable as Interrupt or Square Wave with Programmable Frequency of 32.768kHz, 8.192kHz, 4.096kHz, or 1Hz (DS1390/DS1393/DS1394 Only)
- One Time-of-Day Alarm
- Power-Fail Detect and Switch Circuitry
- Reset Output/Debounced Input (DS1391/DS1393)
- Separate SQW and INT Output (DS1392)
- Trickle-Charge Capability
- SPI Supports Modes 0 and 2 (DS1394)
- SPI Supports Modes 1 and 3 (DS1390/DS1391)
- ♦ 3-Wire Interface (DS1392/DS1393)
- ♦ 4MHz at 3.0V and 3.3V
- 1MHz at 1.8V
- Three Operating Voltages: 1.8V ±5%, 3.0V ±10%, and 2.97 to 5.5V (DS1394: 3.3V ±10%)
- ♦ Industrial Temperature Range: -40°C to +85°C
- Underwriters Laboratories (UL) Recognized

Ordering Information

PART	TYP OPERATING VOLTAGE (V)	PIN- PACKAGE	TOP MARK [†]
DS1390U-18+	1.8	10 µSOP	1390 rr-18
DS1390U-3+	3.0	10 µSOP	1390 rr-3
DS1390U-33+	3.3	10 µSOP	1390 rr-33
DS1391U-18+	1.8	10 µSOP	1391 rr-18
DS1391U-3+	3.0	10 µSOP	1391 rr-3
DS1391U-33+	3.3	10 µSOP	1391 rr-33
DS1392U-18+	1.8	10 µSOP	1393 rr-18
DS1392U-3+	3.0	10 µSOP	1392 rr-3
DS1392U-33+	3.3	10 µSOP	1392 rr-33
DS1393U-18+	1.8	10 µSOP	1393 rr-18
DS1393U-3+	3.0	10 µSOP	1393 rr-3
DS1393U-33+	3.3	10 µSOP	1393 rr-33
DS1394U-33+	3.3	10 µSOP	1394 rr-33

Note: All devices are rated for the -40°C to +85°C operating temperature range.

+Denotes a lead-free/RoHS-compliant package.

†A "+" anywhere on the top mark denotes a lead-free/RoHS-compliant package.

rr = Revision code on second line of top mark.

SPI is a trademark of Motorola, Inc.

Hand-Held Devices GPS/Telematics Devices Embedded Time Stamping

Medical Devices

end of the data sheet.



_ Maxim Integrated Products 1

DS1390-DS1394

hree Operating Voltage nd 2.97 to 5.5V (DS1394 Idustrial Temperature F nderwriters Laboratori

Typical Operating Circuits and Pin Configurations appear at

For pricing, delivery, and ordering information, please contact Maxim Direct at 1-888-629-4642, or visit Maxim's website at www.maxim-ic.com.

Applications

ABSOLUTE MAXIMUM RATINGS

Voltage Range on V_{CC} Pin Relative to Ground-0.3V to +6.0V Voltage Range on Inputs Relative

to Ground-0.3V to (V_{CC} + 0.3V) Operating Temperature Range-40°C to +85°C

Storage Temperature Range	55°C to +125°C
Soldering Temperature	
0	J-STD-020 Specification.

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

RECOMMENDED DC OPERATING CONDITIONS

 $(V_{CC} = V_{CC(MIN)} \text{ to } V_{CC(MAX)}, T_A = -40^{\circ}\text{C} \text{ to } +85^{\circ}\text{C}, \text{ unless otherwise noted}. Typical values are at nominal supply voltage and T_A = +25^{\circ}\text{C}, unless otherwise noted.})$ (Note 1)

PARAMETER	SYMBOL	CONDITIONS	MIN	ТҮР	MAX	UNITS
		DS139x-33	2.97	3.3	5.50	
Supply Voltage (Note 2)	Vcc	DS139x-3	2.7	3.0	3.3	V
		DS139x-18	1.71	1.8	1.89	
Logic 1	VIH	(Note 2)	0.7 x V _{CC}		V _{CC} + 0.5	V
Logic 0	VIL	(Note 2)	-0.3		+0.3 x V _{CC}	V
Supply Voltage, Pullup SQW/INT, SQW, INT, V _{CC} = 0V	VPU	(Note 2)			5.5	V
		-33	1.3	3.0	VCC(MAX)	
VBACKUP Voltage (Note 2)	VBACKUP	-3	1.3	3.0	3.7	V
		-18	1.3	3.0	3.7	
		-33	2.70	2.88	2.97	
Power-Fail Voltage (Note 2)	VPF	-3	2.45	2.6	2.70	V
		-18	1.51	1.6	1.71	
	R1	(Notes 3, 4)		250		
Trickle-Charge Current-Limiting Resistors	R2	(Notes 3, 5)		2000		Ω
The sistors	R3	(Notes 3, 6)		4000		
Input Leakage	ILI	(Note 7)	-1		+1	μA
I/O Leakage	ILO	(Note 8)	-1		+1	μA
RST Pin I/O Leakage	ILORST	(Note 9)	-200		+10	μA
DOUT Logic 1 Output		-33, -3 (V _{OH} = 0.85 x V _{CC})			-1	mA
	IOHDOUT	-18 (V _{OH} = 0.80 × V _{CC})			0.750	ША
DOUT Logic 0 Output		-33, -3 (V _{OL} = 0.15 x V _{CC})			3	mA
	IOHDOUT	-18 (V _{OL} = 0.20 × V _{CC})			2	ША
Logic 0 Output (DS1390/DS1393/DS1394	IOLSIR	$V_{CC} > 1.71V; V_{OL} = 0.4V$			3.0	mA
SQW/INT; DS1392 SQW, INT; DS1391/DS1393 RST)	ULSIK	$1.3V < V_{CC} < 1.71V; V_{OL} = 0.4V$			250	μA
V _{CC} Active Supply Current		-33			2	mA
(Note 10)	ICCA	-3			2	11// \
(-18			500	μA

RECOMMENDED DC OPERATING CONDITIONS (continued)

 $(V_{CC} = V_{CC(MIN)}$ to $V_{CC(MAX)}$, $T_A = -40^{\circ}C$ to $+85^{\circ}C$, unless otherwise noted. Typical values are at nominal supply voltage and $T_A = +25^{\circ}C$, unless otherwise noted.) (Note 1)

PARAMETER	SYMBOL	CONDITIONS	MIN	ТҮР	МАХ	UNITS
V _{CC} Standby Current (Note 11)		-33		115	175	
	Iccs	-3		80	125	μA
		-18		60	100	
VBACKUP Leakage Current (VBACKUP = 3.7V, VCC = VCC(MAX))	IBACKUPLKG			15	100	nA

DC ELECTRICAL CHARACTERISTICS

(V_CC = 0V, V_BACKUP = 3.7V, T_A = -40 ^{\circ}C to +85 ^{\circ}C, unless otherwise noted.) (Note 1)

PARAMETER	SYMBOL	CONDITIONS	MIN	ТҮР	MAX	UNITS
VBACKUP Current OSC On, SQW Off	IBACKUP1	(Note 12)		500	1000	nA
V _{BACKUP} Current OSC On, SQW On (32kHz)	IBACKUP2	(Note 12)		600	1150	nA
V_{BACKUP} Current OSC On, SQW On, $V_{BACKUP} = 3.0V$, $T_A = +25^{\circ}C$	Іваскирз	(Note 12)		600	1000	nA
V _{BACKUP} Current, OSC Off (Data Retention)	IBACKUPDR	(Note 12)		25	100	nA

AC ELECTRICAL CHARACTERISTICS—SPI INTERFACE

(V_{CC} = V_{CC(MIN)} to V_{CC(MAX)}, T_A = -40°C to +85°C, unless otherwise noted.) (Note 1)

PARAMETER	SYMBOL	CONDITION	MIN	ТҮР	MAX	UNITS	
	f	$2.7V \le V_{CC} \le 5.5V$	0		4	NAL I-	
SCLK Frequency (Note 13)	fsclk	$1.71V \le V_{CC} \le 1.89V$	0		1	MHz	
Data to SCLK Setup	tDC	(Notes 13, 14)	30			ns	
SCLK to Data Hold	tCDH	(Notes 13, 14)	30			ns	
SCLK to Data Valid	topp	$2.7V \le V_{CC} \le 5.5V$			80		
(Notes 13, 14, 15)	tCDD	$1.71V \le V_{CC} \le 1.89V$			160	ns	
	to	$2.7V \le V_{CC} \le 5.5V$	110				
SCLK Low Time (Note 13)	tcl	$1.71V \le V_{CC} \le 1.89V$	400			ns	
SCLK High Time (Note 13)	•	$2.7V \le V_{CC} \le 5.5V$	110			ns	
SOLK HIGH HIME (NOLE 13)	t _{CH}	$1.71V \le V_{CC} \le 1.89V$	400			115	
SCLK Rise and Fall	t _R , t _F				200	ns	
CS to SCLK Setup (Note 13)	tcc		400			ns	
SCLK to CS Hold (Note 13)	tссн		100			ns	
	tour	$2.7V \le V_{CC} \le 5.5V$	400				
CS Inactive Time (Note 13)	tCMH	$1.71V \le V_{CC} \le 1.89V$	500			ns	
CS to Output High Impedance	tCDZ	(Notes 13, 14)			40	ns	



DS1390-DS1394





Figure 1a. Timing Diagram—SPI Read Transfer (Mode 3)





BALLAS ANALY




Figure 2a. Timing Diagram—SPI Write Transfer (Mode 3)




Figure 2b. Timing Diagram—SPI Write Transfer (Mode 0)

BALLAS / XI/V

5

DS1390-DS1394

AC ELECTRICAL CHARACTERISTICS—3-WIRE INTERFACE

(V_{CC} = V_{CC(MIN)} to V_{CC(MAX)}, T_A = -40°C to +85°C.) (Note 1) (Figures 3, 4)

PARAMETER	SYMBOL	CONDITION	MIN T	TYP MAX	UNITS
SCLK Fraguenay (Note 12)	facuur	$2.7V \le V_{CC} \le 5.5V$	0	4	
SCLK Frequency (Note 13)	fsclk	$1.71V \le V_{CC} \le 1.89V$	0	1	- MHz
Data to SCLK Setup	tDC	(Notes 13, 14)	30		ns
SCLK to Data Hold	tCDH	(Notes 13, 14)	30		ns
SCLK to Data Valid (Notes 13,	topp	$2.7V \le V_{CC} \le 5.5V$		80	
14, 15)	tCDD	$1.71V \le V_{CC} \le 1.89V$		160	ns
COLIC Law Time (Nate 12)		$2.7V \le V_{CC} \le 5.5V$	110		
SCLK Low Time (Note 13)	tCL	$1.71V \le V_{CC} \le 1.89V$	400		- ns
COLK Lligh Time (Nate 12)		$2.7V \le V_{CC} \le 5.5V$	110		
SCLK High Time (Note 13)	tСН	$1.71V \le V_{CC} \le 1.89V$	400		ns
SCLK Rise and Fall	t _R , t _F			200	ns
CS to SCLK Setup	tcc	(Note 13)	400		ns
SCLK to CS Hold	tCCH	(Note 13)	100		ns
CS Inactive Time (Note 13)		$2.7V \le V_{CC} \le 5.5V$	400		
	tCMH	$1.71V \le V_{CC} \le 1.89V$	500		ns
CS to Output High Impedance	tCDZ	(Note 13, 14)		40	ns

AC ELECTRICAL CHARACTERISTICS

(V_CC = V_CC(MIN) to V_CC(MAX), T_A = -40°C to +85°C, unless otherwise noted.) (Note 1)

PARAMETER	SYMBOL	CONDITIONS	MIN	ТҮР	МАХ	UNITS
Pushbutton Debounce	PBDB			160	200	ms
Reset Active Time	trst			160	200	ms
Oscillator Stop Flag (OSF) Delay	tosf	(Note 16)		100		ms




Figure 3. Timing Diagram—3-Wire Read Transfer




Figure 4. Timing Diagram—3-Wire Write Transfer

7

POWER-UP/POWER-DOWN CHARACTERISTICS

 $(T_A = -40^{\circ}C \text{ to } +85^{\circ}C)$ (Figures 5, 6)

PARAMETER	SYMBOL	CONDITIONS	MIN	ТҮР	МАХ	UNITS
V _{CC} Detect to Recognize Inputs (V _{CC} Rising)	^t RST	(Note 17)		160	200	ms
V _{CC} Fall Time; V _{PF(MAX)} to V _{PF(MIN)}	tF		300			μs
V _{CC} Rise Time; V _{PF(MIN)} to V _{PF(MAX)}	t _R		0			μs




Figure 5. Power-Up/Down Timing




Figure 6. Pushbutton Reset Timing

BALLAS ANALY

CAPACITANCE


 $(T_A = +25^{\circ}C)$

PARAMETER	SYMBOL	CONDITIONS	MIN	ТҮР	МАХ	UNITS
Capacitance on All Input Pins	CIN				10	pF
Capacitance on All Output Pins (High Impedance)	CIO				10	pF


WARNING: Negative undershoots below -0.3V while the part is in battery-backed mode can cause loss of data.


- Note 1: Limits at -40°C are guaranteed by design and not production tested.
- **Note 2:** All voltages are referenced to ground.
- **Note 3:** The use of the 250Ω trickle-charge resistor is not allowed at V_{CC} > 3.63V and should not be enabled. Use of the diode is not recommended for V_{CC} < 3.0V.
- **Note 4:** Measured at V_{CC} = typ, V_{BACKUP} = 0V, register 0Fh = A5h.
- **Note 5:** Measured at V_{CC} = typ, V_{BACKUP} = 0V, register 0Fh = A6h.
- **Note 6:** Measured at V_{CC} = typ, V_{BACKUP} = 0V, register 0Fh = A7h.
- Note 7: SCLK, DIN, CS on DS1390/DS1391/DS1394; SCLK, and CE on DS1392/DS1393.
- Note 8: DOUT, SQW/INT (DS1390/DS1393/DS1394), SQW, and INT (DS1392).
- **Note 9:** The RST pin has an internal $50k\Omega$ (typ) pullup resistor to V_{CC}.
- **Note 10:** I_{CCA}—SCLK clocking at max frequency = 4MHz for 3V and 3.3V versions; 1MHz for 1.8V version; RST (DS1391/DS1393) inactive. Outputs are open.
- Note 11: Specified with bus inactive.
- Note 12: Measured with a 32.768kHz crystal attached to X1 and X2. Typical values measured at +25°C and 3.0VBACKUP.
- Note 13: With 50pF load.
- **Note 14:** Measured at $V_{IH} = 0.7 \times V_{DD}$ or $V_{IL} = 0.2 \times V_{DD}$, 10ns rise/fall times.
- Note 15: Measured at V_{OH} = 0.7 x V_{DD} or V_{OL} = 0.2 x V_{DD}. Measured from the 50% point of SCLK to the V_{OH} minimum of SDO.
- Note 16: The parameter t_{OSF} is the time that the oscillator must be stopped for the OSF flag to be set over the voltage range of $0 \le V_{CC} \le V_{CC(MAX)}$ and $1.3V \le V_{BACKUP} \le 5.5V$.
- Note 17: This delay applies only if the oscillator is enabled and running. If the EOSC bit is 1, the startup time of the oscillator is added to this delay.


DS1390-DS1394















_Pin Description

	PIN				
DS1390/ DS1394	DS1391	DS1392	DS1393	NAME	FUNCTION
1	1	1	1	X1	Connections for Standard 32.768kHz Quartz Crystal. The internal oscillator circuitry is designed for operation with a crystal having a 6pF specified load capacitance (CL). Pin X1 is the input to the oscillator and can optionally be
2	2	2	2	X2	connected to an external 32.768kHz oscillator. The output of the internal oscillator, pin X2, is floated if an external oscillator is connected to pin X1.
3	3	3	3	VBACKUP	DC Backup Power Input for Primary Cell. This pin is a rechargeable battery/super cap or a secondary supply. UL recognized to ensure against reverse charging current when used with a lithium battery (www.maxim - ic.com/qa/info/w/). This pin must be grounded if not used. Diodes in series between the battery and the V _{BACKUP} pin may prevent proper operation.
4	4			CS	SPI Chip-Select Input. This pin is used to select or deselect the part.
—		4	4	CE	Chip Enable for 3-Wire Interface
5	5	5	5	GND	Ground
6	6	—	—	DIN	SPI Data Input. This pin is used to shift address and data into the part.
_		6		ĪNT	Interrupt Output. This pin is used to output the interrupt signal, if enabled by the control register. The maximum voltage on this pin is 5.5V, independent of V _{CC} or V _{BACKUP} . If enabled, \overline{INT} functions when the device is powered by either V _{CC} or V _{BACKUP} .
_	9	_	6	RST	Reset. This active-low, open-drain output indicates the status of V _{CC} relative to the V _{PF} specification. As Vcc falls below V _{PF} , the $\overline{\text{RST}}$ pin is driven low. When Vcc exceeds V _{PF} , for t _{RST} , the $\overline{\text{RST}}$ pin is driven high impedance. This pin is combined with a debounced pushbutton input function. This pin can be activated by a pushbutton reset request. This pin has an internal, $50 \text{k}\Omega$ (typ) pullup resistor to V _{CC} . No external pullup resistors should be connected. If the crystal oscillator is disabled, the startup time of the oscillator is added to the t _{RST} delay.
7	7	_	_	DOUT	SPI Data Output. Data is output on this pin when the part is in read mode. CMOS push-pull driver.
		7	7	I/O	Input/Output for 3-Wire Interface. CMOS push-pull driver.
8	8	8	8	SCLK	Serial Clock Input. This pin is used to control the timing of data into and out of the part.
9			9	SQW/INT	Square-Wave/Interrupt Output. This pin is used to output the programmable square wave or interrupt signal. When enabled by setting the $\overline{\text{ESQW}}$ bit to logic 1, the SQW/INT pin outputs one of four frequencies: 32.768kHz, 8.192kHz, 4.096kHz, or 1Hz. This pin is open drain and requires an external pullup resistor. The maximum voltage on this pin is 5.5V, independent of V _{CC} or V _{BACKUP} . If enabled, SQW/INT functions when the device is powered by either V _{CC} or V _{BACKUP} . If not used, this pin can be left open.
_		9		SQW	Square-Wave Output. This pin is open drain and requires an external pullup resistor. The maximum voltage on this pin is 5.5V, independent of V _{CC} or V _{BACKUP} . If enabled, SQW functions when the device is powered by either V _{CC} or V _{BACKUP} . If not used, this pin can be left open.
10	10	10	10	Vcc	DC Power Pin for Primary Power Supply



BALLAS ////X///

_Functional Diagram



Detailed Description

The DS1390–DS1394 RTCs are low-power clocks/calendars with alarms. Address and data are transferred serially through a 4-wire SPI interface for the DS1390 and DS1391 and through a 3-wire interface for the DS1392, DS1393, and DS1394. The DS1390/DS1391 operate as a slave device on the SPI serial bus. The DS1392/DS1393 operate using a 3-wire synchronous serial bus. Access is obtained by selecting the part by the CS pin (CE on DS1392/DS1393) and clocking data into/out of the part using the SCLK and DIN/DOUT pins (I/O on DS1392/DS1393). Multiple-byte transfers are supported within one CS low period (see the *SPI Serial-Data Bus* section). The clocks/calendars provide hundredths of seconds, seconds, minutes, hours, day, date, month, and year information. The alarm functions are performed off all timekeeping registers, allowing the user to set high resolution alarms. The date at the end of the month is automatically adjusted for months with fewer than 31 days, including corrections for leap year. The clocks operate in either the 24-hour or 12-hour format with an AM/PM indicator. All five devices have a built-in temperature-compensated voltage reference that detects power failures and automatically switches to the battery supply. Additionally, the devices can provide trickle charging of the backup voltage source, with selectable charging resistance and diode voltage drops.

DS1390-DS1394

Power Control

The power-control function is provided by a precise, temperature-compensated voltage reference and a comparator circuit that monitors the V_{CC} level. The device is fully accessible and data can be written and read when VCC is greater than VPF. However, when V_{CC} falls below V_{PF}, the internal clock registers are blocked from any access. If VPF is less than VBACKUP, the device power is switched from VCC to VBACKUP when V_{CC} drops below V_{PF}. If V_{PF} is greater than VBACKUP, the device power is switched from VCC to VBACKUP when VCC drops below VBACKUP. Timekeeping operation and register data are maintained from the VBACKUP source until VCC is returned to nominal levels (Table 1). After V_{CC} returns above V_{PF}, read and write access is allowed after RST goes high (Figure 5).

Table 1. Power Control

SUPPLY CONDITION	READ/WRITE ACCESS)	POWERED BY	
V _{CC} < V _{PF} , V _{CC} < V _{BACKUP}	No	VBACKUP	
V _{CC} < V _{PF} , V _{CC} > V _{BACKUP}	No	Vcc	
V _{CC} > V _{PF} , V _{CC} < V _{BACKUP}	Yes	Vcc	
V _{CC} > V _{PF} , V _{CC} > V _{BACKUP}	Yes	Vcc	

_Oscillator Circuit

All five devices use an external 32.768kHz crystal. The oscillator circuit does not require any external resistors or capacitors to operate. Table 2 specifies several crystal parameters for the external crystal. If a crystal is used with the specified characteristics, the startup time is usually less than one second.


Table 2. Crystal Specifications*

PARAMETER	SYMBOL	MIN	ТҮР	МАХ	UNITS
Nominal Frequency	fo		kHz		
Series Resistance	ESR			55	kΩ
Load Capacitance	CL		6		рF

*The crystal, traces, and crystal input pins should be isolated from RF generating signals. Refer to Application Note 58: Crystal Considerations for Maxim Real-Time Clocks for additional specifications.

Clock Accuracy

The accuracy of the clock is dependent upon the accuracy of the crystal and the accuracy of the match between the capacitive load of the oscillator circuit and the capacitive load for which the crystal was trimmed. Additional error is added by crystal frequency drift caused by temperature shifts. External circuit noise coupled into the oscillator circuit can result in the clock running fast. Figure 7 shows a typical PC board layout for isolation of the crystal and oscillator from noise. Refer to Application Note 58: *Crystal Considerations with Maxim Real-Time Clocks* for detailed information.



Address Map

Table 3 shows the address map for the DS1390– DS1393 RTC and RAM registers. The RTC registers are located in address locations 00h to 0Fh in read mode, and 80h to 8Fh in write mode. During a multibyte access, when the address pointer reaches 0Fh, it wraps around to location 00h. On the falling edge of the CS pin (DS1390/DS1391/DS1394) or the rising edge of CE (DS1392/DS1393), the current time is transferred to a second set of registers. The time information is read from these secondary registers, while the clock may continue to run. This eliminates the need to re-read the registers if the main registers update during a read. To avoid rollover issues when writing to the time and date registers, all registers should be written before the hundredths-of-seconds registers reaches 99 (BCD).

When reading from the hundredths of seconds register, there is a possibility that the data transfer happens at the same time as an increment of the register. If this occurs, the data in the buffer may be incorrect. The chances of this happening is approximately 170ppb. There are two ways to deal with this. The first method is to synchronize enabling the device (CE or \overline{CS}) with the square wave or interrupt output (DS1390–DS1394). Enabling the device, either after detecting the falling edge of the interrupt output or the rising edge of the square-wave output, ensures that the two events are not simultaneous.

The second method is to read the hundredths of seconds register until the data for two consecutive reads match. With this method, the master must be able to read the register at least twice within the 10ms update period of the hundredths of seconds register.

Either of the described methods ensures that the data in all the registers is correct. If the hundredths of seconds register is not used, it is also possible for the same problem to occur when reading the seconds register. The probability of an error is inversely proportional to the rate of the register's update frequency in relation to the hundredth of seconds register, so the error rate for the seconds register would be approximately 1.7ppb. The same methods used for the hundredth of seconds register would be used for the seconds register.

		•									
WRITE ADDRESS	READ ADDRESS	BIT 7	BIT 6	BIT 5	BIT 4	BIT 3	BIT 2	BIT 1	BIT 0	FUNCTION	RANGE
80h	00h	-	Tenths o	enths of Seconds			Hundredths of Seconds			Hundredths of Seconds	0–99 BCD
81h	01h	0		10 Second	S		Sec	onds		Seconds	00-59 BCD
82h	02h	0		10 Minutes	S		Min	utes		Minutes	00-59 BCD
83h	03h	0	12/24	AM/PM 10 Hour	10 Hour	Hour			Hours	1–12 +AM/PM 00–23 BCD	
84h	04h	0	0	0	0	0 Day		Day	1-7 BCD		
85h	05h	0	0	10 D	ate		Date			Date	01-31 BCD
86h	06h	Century	0	0	10 Month		Мс	onth		Month/ Century	01–12 + Century BCD
87h	07h		10	Year			Ye	ear		Year	00-99 BCD
88h	08h	-	Tenths o	f Seconds		Hundredths of Seconds			Alarm Hundredths of Seconds	0–99 BCD	
89h	09h	AM1		10 Second	S		Sec	onds		Alarm	00-59 BCD
8Ah	0Ah	AM2		10 Minutes	s		Min	utes		Alarm	00–59 BCD

Table 3. Address Map

WRITE ADDRESS	READ ADDRESS	BIT 7	BIT 6	BIT 5	BIT 4	BIT 3	BIT 2	BIT 1	FUNCTION	RANGE	
8Bh	0Bh	AM3	12/24	AM/PM	10 Hour	Hour			Alarm Hours	1–12 + AM/PM 00–23 BCD	
				10 Hour							
8Ch	0Ch	AM4	DY/DT	10 D	ato	Day				Alarm Day	1-7 BCD
0011	0011		וטוטו	10 D	ale		Da	ate		Alarm Date	01-31 BCD
			0	BBSQI	RS2	RS1	INTCN	0	AIE		DS1390/93/94
8Dh	0Dh	EOSC	0	Х	Х	Х	Х	0	Х	Control	DS1391
			0	BBSQI	RS2	RS1	ESQW	0	AIE		DS1392
8Eh	0Eh	OSF	0	0	0	0	0	0	AF	Status	
8Fh	0Fh	TCS3	TCS2	TCS1	TCS0	DS1	DS0	ROUT1	ROUTO	Trickle Charger	_

Table 3. Address Map (continued)

Note: Unless otherwise specified, the state of the registers is not defined when power (V_{CC} and V_{BACKUP}) is first applied. X = General-purpose read/write bit.

0 = Always reads as zero.

Hundredths-of-Seconds Generator

The hundredths-of-seconds generator circuit shown in the functional diagram is a state machine that divides the incoming frequency (4096Hz) by 41 for 24 cycles and 40 for one cycle. This produces a 100Hz output that is slightly off during the short term, and is exactly correct every 250ms. The divide ratio is given by:

Ratio = [41 x 24 + 40 x 1] / 25 = 40.96

Thus, the long-term average frequency output is exactly the desired 100Hz.

Clock and Calendar

The time and calendar information is obtained by reading the appropriate register bytes. See Table 3 for the RTC registers. The time and calendar are set or initial-

ized by writing the appropriate register bytes. The contents of the time and calendar registers are in the binary-coded decimal (BCD) format. The day-of-week register increments at midnight. Values that correspond to the day-of-week are user-defined but must be sequential (i.e., if 1 equals Sunday, then 2 equals Monday, and so on). Illogical time and date entries result in undefined operation. The DS1390-DS1393 can run in either 12-hour or 24-hour mode. Bit 6 of the hours register is defined as the 12- or 24-hour mode-select bit. When high, the 12-hour mode is selected. In the 12hour mode, bit 5 is the AM/PM bit with logic high being PM. In the 24-hour mode, bit 5 is the second 10-hour bit (20 to 23 hours). Changing the 12/24-hour modeselect bit requires that the hours data be re-entered, including the alarm register (if used). The century bit (bit 7 of the month register) is toggled when the years register overflows from 99 to 00.

Alarms

All five devices contain one time-of-day/date alarm. Writing to registers 88h through 8Ch sets the alarm. The alarm can be programmed (by the alarm enable and INTCN bits of the control register) to activate the SQW/INT or INT output on an alarm-match condition. The alarm can activate the SQW/INT or INT output while the device is running from VBACKUP if BBSQI is enabled. Bit 7 of each of the time-of-day/date alarm registers are mask bits (Table 4). When all the mask bits for each alarm are logic 0, an alarm only occurs when the values in the timekeeping registers 00h to 06h match the values stored in the time-of-day/date alarm registers. The alarms can also be programmed to repeat every second, minute, hour, day, or date. Table 4 shows the possible settings. Configurations not listed in the table result in illogical operation.

The DY/ \overline{DT} bits (bit 6 of the alarm day/date registers) control whether the alarm value stored in bits 0 to 5 of that register reflects the day of the week or the date of the month. If DY/ \overline{DT} is written to logic 0, the alarm is the result of a match with date of the month. If DY/ \overline{DT} is written to a logic 1, the alarm is the result of a match with day of the week.

When the RTC register values match alarm register settings, the alarm-flag (AF) bit is set to logic 1. If the alarm-interrupt enable (AIE) is also set to logic 1 and the INTCN bit is set to logic 1, the alarm condition activates the SQW/ $\overline{\rm INT}$ signal.

Since the contents of register 08h are expected to normally contain a match value of 00–99 decimal, the codes F[0–9], and FF have been used to tell the part to mask the tenths or hundredths of seconds accordingly.

Power-Up/Down, Reset, and Pushbutton Reset Functions

A precision temperature-compensated reference and comparator circuit monitors the status of V_{CC}. When an out-of-tolerance condition occurs, an internal power-fail signal is generated that blocks read/write access to the device and forces the $\overline{\text{RST}}$ pin (DS1391/DS1393 only) low. When V_{CC} returns to an in-tolerance condition, the internal power-fail signal is held active for t_{RST} to allow the power supply to stabilize, and the $\overline{\text{RST}}$ (DS1391/DS1393 only) DS1393 only) pin is held low. If the $\overline{\text{EOSC}}$ bit is set to logic 1 (to disable the oscillator in battery-backup mode), the internal power-fail signal and the $\overline{\text{RST}}$ pin is kept active for t_{RST} plus the startup time of the oscillator.

The DS1391/DS1393 provide for a pushbutton switch to be connected to the RST output pin. When the DS1391/DS1393 are not in a reset cycle, it continuously monitors the RST signal for a low-going edge. If an edge is detected, the part debounces the switch by pulling the RST pin low and inhibits read/write access. After PB_{DB} has expired, the part continues to monitor the RST line. If the line is still low, it continues to monitor the line looking for a rising edge. Upon detecting release, the part forces the RST pin low and holds it low for an additional PB_{DB}.

REGISTE	DY/DT	ALARM	REGISTER	MASK BIT	S (BIT 7)			
R 08H	וט(זט	AM4	AM3	AM2	AM1			
FFh	Х	1	1	1	1	Alarm every 1/100th of a second		
F[0–9]h	Х	1	1	1	1	Alarm when hundredths of seconds match		
[0–9][0–9]	Х	1	1	1	1	Alarm when tenths, hundredths of seconds match		
[0–9][0–9]	Х	1	1	1	0	Alarm when seconds, tenths, and hundredths of second match		
[0–9][0–9]	Х	1	1	0	0	Alarm when minutes, seconds, tenths, and hundredths of seconds match		
[0–9][0–9]	х	1	0	0	0	Alarm when hours, minutes, seconds, tenths, and hundredths of seconds match		
[0–9][0–9]	0	0	0	0	0	Alarm when date, hours, minutes, seconds, tenths, and hundredths of seconds match		
[0–9][0–9]	1	0	0	0	0	Alarm when day, hours, minutes, seconds, tenths, and hundredths of seconds match		

Table 4. Alarm Mask Bits

Special-Purpose Registers

The DS1390–DS1394 have three additional registers (control, status, and trickle charger) that control the RTC, alarms, square-wave output, and trickle charger.

Control Register (0D/8Dh)	(DS1390/DS1393/DS1394 Only)
---------------------------	-----------------------------

BIT 7	BIT 6	BIT 5	BIT 4	BIT 3	BIT 2	BIT 1	BIT 0
EOSC	0	BBSQI	RS2	RS1	INTCN	0	AIE

Bit 7: Enable Oscillator (EOSC). When set to logic 0, this bit starts the oscillator. When this bit is set to logic 1, the oscillator is stopped whenever the device is powered by V_{BACKUP} . The oscillator is always enabled when V_{CC} is valid. This bit is enabled (logic 0) when V_{CC} is first applied.

Bit 5: Battery-Backed Square-Wave and Interrupt Enable (BBSQI). This bit when set to logic 1 enables the square wave or interrupt output when V_{CC} is absent and the DS1390/DS1392/DS1393/DS1394 are being powered by the V_{BACKUP} pin. When BBSQI is logic 0, the SQW/INT pin (or SQW and INT pins) goes high impedance when V_{CC} falls below the power-fail trip point. This bit is disabled (logic 0) when power is first applied.

Bits 4 and 3: Rate Select (RS2 and RS1). These bits control the frequency of the square-wave output when the square wave has been enabled. The table below shows the square-wave frequencies that can be selected with the RS bits. These bits are both set to logic 1 (32kHz) when power is first applied.

RS2	RS1	SQUARE-WAVE OUTPUT FREQUENCY
0	0	1Hz
0	1	4.096kHz
1	0	8.192kHz
1	1	32.768kHz

Bit 2: Interrupt Control (INTCN). This bit controls the SQW/INT signal. When the INTCN bit is set to logic 0, a square wave is output on the SQW/INT pin. The oscillator must also be enabled for the square wave to be output. When the INTCN bit is set to logic 1, a match between the timekeeping registers and either of the alarm registers then activates the SQW/INT (provided the alarm is also enabled). The corresponding alarm flag is always set, regardless of the state of the INTCN bit. The INTCN bit is set to logic 0 when power is first applied.

Bit 0: Alarm Interrupt Enable (AIE). When set to logic 1, this bit permits the alarm flag (AF) bit in the status register to assert SQW/ \overline{INT} (when INTCN = 1). When the AIE bit is set to logic 0 or INTCN is set to logic 0, the AF bit does not initiate the SQW/ \overline{INT} signal. The AIE bit is disabled (logic 0) when power is first applied.

Control	Register	(00/20h)	/DS1301	Only)
Control	negister	[00/0011]	031331	UIIIVI

BIT 7	BIT 6	BIT 5	BIT 4	BIT 3	BIT 2	BIT 1	BIT 0
EOSC	0	Х	Х	Х	Х	0	Х

Control bits used in the DS1390 become general-purpose, battery-backed, nonvolatile SRAM bits in the DS1391.

Control Register (0D/8Dh) (DS1392 Only)

BIT 7	BIT 6	BIT 5	BIT 4	BIT 3	BIT 2	BIT 1	BIT 0
EOSC	0	BBSQI	RS2	RS1	ESQW	0	AIE

The INTCN bit used in the DS1390/DS1393/DS1394 becomes the SQW pin-enable bit in the DS1392. This

bit powers up a zero, making SQW active.

Status Register (0E/8Eh)

BIT 7	BIT 6	BIT 5	BIT 4	BIT 3	BIT 2	BIT 1	BIT 0
OSF	0	0	0	0	0	0	AF

Bit 7: Oscillator Stop Flag (OSF). A logic 1 in this bit indicates that the oscillator has stopped or was stopped for some time and may be used to judge the validity of the clock and calendar data. This bit is edge-triggered and is set to logic 1 when the internal circuitry senses the oscillator has transitioned from a normal run state to a STOP condition. The following are examples of conditions that can cause the OSF bit to be set:

- 1) The first time power is applied.
- 2) The voltage present on V_{CC} and V_{BACKUP} is insufficient to support oscillation.
- 3) The EOSC bit is turned off.
- 4) External influences on the crystal (i.e., noise, leakage, etc.).

This bit remains at logic 1 until written to logic 0. This bit can only be written to logic 0. Attempting to write OSF to logic 1 leaves the value unchanged.

Bit 6: Alarm Flag (AF). A logic 1 in the AF bit indicates that the time matched the alarm registers. If the AIE bit

is logic 1 and the INTCN bit is set to logic 1, the SQW/INT pin is also asserted. AF is cleared when written to logic 0. This bit can only be written to logic 0. Attempting to write to logic 1 leaves the value unchanged.

_Trickle-Charge Register (0F/8Fh)

The simplified schematic in Figure 8 shows the basic components of the trickle charger. The trickle-charge select (TCS) bits (bits 4 to 7) control the selection of the trickle charger. To prevent accidental enabling, only a pattern on 1010 enables the trickle charger. All other patterns disable the trickle charger. The trickle charger is disabled when power is first applied. The diode-select (DS) bits (bits 2 and 3) select whether or not a diode is connected between V_{CC} and V_{BACKUP}. If DS is 01, no diode is selected or if DS is 10, a diode is selected. The ROUT bits (bits 0 and 1) select the value of the resistor connected between V_{CC} and V_{BACKUP}. Table 5 shows the resistor selected by the resistor-select (ROUT) bits and the diode selected by the diode-select (DS) bits.

TCS3	TCS2	TCS1	TCS0	DS1	DS0	ROUT1	ROUT0	FUNCTION
Х	Х	Х	Х	0	0	Х	Х	Disabled
Х	Х	Х	Х	1	1	Х	Х	Disabled
Х	Х	Х	Х	Х	Х	0	0	Disabled
1	0	1	0	0	1	0	1	No diode, 250 Ω resistor
1	0	1	0	1	0	0	1	One diode, 250 Ω resistor
1	0	1	0	0	1	1	0	No diode, $2k\Omega$ resistor
1	0	1	0	1	0	1	0	One diode, $2k\Omega$ resistor
1	0	1	0	0	1	1	1	No diode, $4k\Omega$ resistor
1	0	1	0	1	0	1	1	One diode, $4k\Omega$ resistor
0	0	0	0	0	0	0	0	Initial default value—disabled

Table 5. Trickle-Charge Register




Figure 8. DS1390–DS1394 Programmable Trickle Charger

Table 6. SPI Pin Function

MODE	СРНА	CS	SCLK	SDI	SDO	
Disable	Х	High	Input Disabled	Input Disabled	High-Z High-Z	
Write	0	Low	CPOL* = 0, SCLK Rising; CPOL = 1, SCLK Falling	Data Bit Latch		
Read	0	Low	CPOL = 0, SCLK Falling; CPOL = 1, SCLK Rising	Х	Next Data Bit Shift**	
Write	1	Low	CPOL* = 1, SCLK Rising; CPOL = 0, SCLK Falling	Data Bit Latch	High-Z	
Read	1	Low	CPOL = 1, SCLK Falling; CPOL = 0, SCLK Rising	Х	Next Data Bit Shift**	

*CPOL is the clock-polarity bit set in the control register of the host microprocessor.

**SDO remains at high-Z until 8 bits of data are ready to be shifted out during a read.

The user determines diode and resistor selection according to the maximum current desired for battery or super cap charging. The maximum charging current can be calculated as illustrated in the following example. Assume that a system power supply of 3.3V is applied to V_{CC} and a super cap is connected to V_{BACKUP}. Also, assume that the trickle charger has been enabled with a diode and resistor R2 between

 V_{CC} and $V_{BACKUP}.$ The maximum current I_{MAX} would therefore be calculated as follows:

$$I_{MAX} = (3.3V - diode \ drop) \ / \ R2 \approx (3.3V - 0.7V) \ / \\ 2k\Omega \approx 1.3mA$$

As the super cap changes, the voltage drop between V_{CC} and V_{BACKUP} decreases and therefore the charge current decreases.

DS1390-DS1394

SPI Serial-Data Bus

The DS1390/DS1391/DS1394 provide a 4-wire SPI serial-data bus to communicate in systems with an SPI host controller. The DS1390/DS1391 support SPI modes 1 and 3, while the DS1394 supports SPI modes 0 and 2. Both devices support single-byte and multiple-byte data transfers for maximum flexibility. The DIN and DOUT pins are the serial-data input and output pins. respectively. The \overline{CS} input initiates and terminates a data transfer. The SCLK pin synchronizes data movement between the master (microcontroller) and the slave (DS1390/DS1391) devices. The shift clock (SCLK), which is generated by the microcontroller, is active only during address and data transfer to any device on the SPI bus. Input data (DIN) is latched on the internal strobe edge and output data (DOUT) is shifted out on the shift edge (Figure 9). There is one clock for each bit transferred. Address and data bits are transferred in groups of eight.

Address and data bytes are shifted MSB first into the serial-data input (DIN) and out of the serial-data output (DOUT). Any transfer requires the address of the byte to specify a write or read, followed by one or more bytes of data. Data is transferred out of the DOUT pin

for a read operation and into the DIN for a write operation (Figures 10 and 11).

The address byte is always the first byte entered after \overline{CS} is driven low. The most significant bit (W/ \overline{R}) of this byte determines if a read or write takes place. If W/ \overline{R} is 0, one or more read cycles occur. If W/ \overline{R} is 1, one or more write cycles occur.

Data transfers can occur one byte at a time or in multiple-byte burst mode. After \overline{CS} is driven low, an address is written to the DS1390/DS1391/DS1394. After the address, one or more data bytes can be written or read. For a single-byte transfer, one byte is read or written and then \overline{CS} is driven high. For a multiple-byte transfer, however, multiple bytes can be read or written after the address has been written. Each read or write cycle causes the RTC register address to automatically increment. Incrementing continues until the device is disabled. The address wraps to 00h after incrementing to OFh (during a read) and wraps to 80h after incrementing to 8Fh (during a write). Note, however, that an updated copy of the time is only loaded into the useraccessible copy upon the falling edge of \overline{CS} . Reading the RTC registers in a continuous loop does not show the time advancing.




Figure 9. Serial Clock as a Function of Microcontroller Clock-Polarity Bit




Figure 10. SPI Single-Byte Write




Figure 11. SPI Single-Byte Read




Figure 12. SPI Multiple-Byte Burst Transfer




Figure 13. 3-Wire Single-Byte Read




Figure 14. 3-Wire Single-Byte Write

3-Wire Serial-Data Bus

The DS1392/DS1393 provide a 3-wire serial-data bus, and support both single-byte and multiple-byte data transfers for maximum flexibility. The I/O pin is the serial-data input/output pin. The CE input is used to initiate and terminate a data transfer. The SCLK pin is used to synchronize data movement between the master (microcontroller) and the slave (DS1392/DS1393) devices. Input data is latched on the SCLK rising edge and output data is shifted out on the SCLK falling edge. There is one clock for each bit transferred. Address and data bits are transferred in groups of eight. Address and data bytes are shifted LSB first into the I/O pin. Data is transferred out LSB first on the I/O pin for a read operation.

The address byte is always the first byte entered after CE is driven high. The MSB (W/ \overline{R}) of this byte determines if a read or write takes place. If W/ \overline{R} is 0, one or more read cycles occur. If W/ \overline{R} is 1, one or more write cycles occur.

Data transfers can be one byte at a time or in multiplebyte burst mode. After CE is driven high, an address is written to the DS1392/DS1393. After the address, one or more data bytes can be written or read. For a singlebyte transfer, one byte is read or written and then CE is driven low (Figures 13 and 14). For a multiple-byte transfer, however, multiple bytes can be read or written after the address has been written (Figure 15). Each read or write cycle causes the RTC register address to automatically increment. Incrementing continues until the device is disabled. The address wraps to 00h after




Figure 15. 3-Wire Multiple-Byte Burst Transfer

incrementing to 0Fh (during a read) and wraps to 80h after incrementing to 8Fh (during a write). Note, however, that an updated copy of the time is only loaded into the user-accessible copy upon the rising edge of CE. Reading the RTC registers in a continuous loop does not show the time advancing.

Chip Information

TRANSISTOR COUNT: 11,525 PROCESS: CMOS SUBSTRATE CONNECTED TO GROUND


Thermal Information

Theta-JA: 180°C/W Theta-JC: 41.9°C/W

DS1390-DS1394 TOP VIEW X1 1 10 V_{CC} X1 1 10 V_{CC} DALLAS SEMICONDUCTOR X2 2 9 SQW/INT X2 2 9 RST DS1391 DS1390/ 8 SCLK 8 SCLK VBACKUP 3 VBACKUP 3 DS1394 7 DOUT CS 4 7 DOUT CS 4 6 DIN 6 DIN GND 5 GND 5 μ**SOP** μ**SOP** 10 V_{CC} 10 V_{CC} X1 1 X1 1 9 SQW 9 SQW/INT X2 2 X2 2 DS1392 DS1393 V_{BACKUP} 3 8 SCLK V_{BACKUP} 8 SCLK 3 7 1/0 7 1/0 CE 4 4 CE 6 INT 6 RST GND 5 GND 5 μ**SOP** μ**SOP**

Pin Configurations

Typical Operating Circuits



Package Information

For the latest package outline information and land patterns, go to www.maxim-ic.com/packages.

PACKAGE TYPE	PACKAGE CODE	DOCUMENT NO.
10 µSOP		<u>21-0061</u>

BALLAS JUINKI

DS1390-DS1394

REVISION NUMBER	REVISION DATE	DESCRIPTION	PAGES CHANGED
0	7/04	Initial release.	—
	1/07	Added text to the <i>General Description</i> section to indicate that the bus interface is disabled when the part switches to V _{BACKUP} ; replaced <i>Ordering Information</i> table with lead-free packages.	1
-		Added 0MHz (min) spec for SCLK frequency for SPI, 3-wire AC timing.	3, 5
1		Added the "High Impedance" label for DOUT to Figure 1 and added DOUT trace to Figure 2.	4
		Changed all references of VBAT to VBACKUP.	8, 10
		Replaced the Operation section with the Power Control section and added new Table 1.	11, 12
2	8/08	Added the DS1394.	All
		In the <i>Address Map</i> section, added the description on how to avoid misreads of the time registers.	15

Revision History

Maxim cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim product. No circuit patent licenses are implied. Maxim reserves the right to change the circuitry and specifications without notice at any time.

26

_Maxim Integrated Products, 120 San Gabriel Drive, Sunnyvale, CA 94086 408-737-7600

© 2008 Maxim Integrated Products

is a registered trademark of Maxim Integrated Products, Inc.

DALLAS is a registered trademark of Dallas Semiconductor Corporation.