Photocouplers Infrared LED & Photo Darlington Transistor

TLP627M,TLP627MF

1. Applications

- Programmable Logic Controllers (PLCs)
- I/O Interface Boards
- Home Electric Appliances

2. General

TLP627M is a photocoupler that consists of an infrared emitting diode optically coupled to a photo darlington transistor. Housed in a 4pin DIP, it has a high noise immunity and high insulation. With the high breakdown voltage between the collector and emitter, TLP627M is suitable in applications such as 100 V DC output modules of programmable controllers.

TLP627MF is a lead forming type for the long creepage mounting of TLP627M.

3. Features


- (1) Collector-emitter voltage: 300 V (min)
- (2) Current transfer ratio: 1000 % (min) (@I_F = 1 mA, V_{CE} = 1 V)
- (3) Isolation voltage: 5000 Vrms (min)
- (4) Operating temperature: -55 to 110 °C
- (5) Safety standards

UL-recognized: UL 1577, File No.E67349 cUL-recognized: CSA Component Acceptance Service No.5A File No.E67349 VDE-approved: EN 60747-5-5, EN 62368-1 (Note 1) CQC-approved: GB4943.1, GB8898 Japan Factory (Pending)




Note 1: When a VDE approved type is needed, please designate the Option (D4).

4. Packaging (Note)



Note: Through-hole type: TLP627M, TLP627MF Lead forming option: (LF1), (LF4), (LF5) Taping option: (TP1), (TP4), (TP5)

5. Pin Assignment



6. Mechanical Parameters

Characteristics	7.62 mm pitch TLP627M type (Min)	10.16 mm pitch TLP627MF type (Min)	Unit
Creepage distances	7.0	8.0	mm
Clearance	7.0	8.0	
Internal isolation thickness	0.4	0.4	

7. Absolute Maximum Ratings (Note) (Unless otherwise specified, $T_a = 25$ °C)

	Characteristics		Symbol	Note	Rating	Unit
LED	Input forward current		١ _F		50	mA
	Input forward current derating	(T _a ≥ 90 °C)	$\Delta I_F / \Delta T_a$		-1.42	mA/°C
	Input forward current (pulsed)		I _{FP}	(Note 1)	1	Α
	Input reverse voltage		V _R		5	V
	Input power dissipation		PD		100	mW
	Input power dissipation derating	(T _a ≥ 90 °C)	$\Delta P_D / \Delta T_a$		-2.85	mW/°C
	Junction temperature		Тj		125	°C
Detector	Collector-emitter voltage		V _{CEO}		300	V
	Emitter-collector voltage		V _{ECO}		0.3	V
	Collector current		Ι _C		150	mA
	Collector power dissipation		P _C		150	mW
	Collector power dissipation derating	(T _a ≥ 25 °C)	$\Delta P_C / \Delta T_a$		-1.5	mW/°C
	Junction temperature		Тj		125	°C
Common	Operating temperature		T _{opr}		-55 to 110	°C
	Storage temperature		T _{stg}		-55 to 125	°C
	Lead soldering temperature	(10 s)	T _{sol}		260	°C
	Total power dissipation		PT		250	mW
	Total power dissipation derating	(T _a ≥ 25 °C)	$\Delta P_T / \Delta T_a$		-2.5	mW/°C
	Isolation voltage	(AC, 60 s, R.H. \leq 60 %)	BVS	(Note 2)	5000	Vrms

Note: Using continuously under heavy loads (e.g. the application of high temperature/current/voltage and the significant change in temperature, etc.) may cause this product to decrease in the reliability significantly even if the operating conditions (i.e. operating temperature/current/voltage, etc.) are within the absolute maximum ratings.

Please design the appropriate reliability upon reviewing the Toshiba Semiconductor Reliability Handbook ("Handling Precautions"/"Derating Concept and Methods") and individual reliability data (i.e. reliability test report and estimated failure rate, etc).

Note 1: Pulse width (PW) \leq 0.1 ms, f = 100 Hz

Note 2: This device is considered as a two-terminal device: Pins 1 and 2 are shorted together, and pins 3 and 4 are shorted together.

8. Electrical Characteristics (Unless otherwise specified, T_a = 25 °C)

	Characteristics	Symbol	Note	Test Condition	Min	Тур.	Max	Unit
LED	Input forward voltage	V _F		I _F = 10 mA	1.1	1.25	1.4	V
	Input reverse current	I _R		V _R = 5 V	_	_	10	μA
	Input capacitance	Ct		V = 0 V, f = 1 MHz	_	30	—	pF
Detector	Collector-emitter breakdown voltage	V _{(BR)CEO}		I _C = 0.1 mA	300	_	—	V
	Emitter-collector breakdown voltage	V _{(BR)ECO}		I _E = 0.1 mA	0.3	_	_	V
	Dark Current	I _{DARK}		V _{CE} = 200 V	_	0.002	0.2	μA
				V _{CE} = 200 V, T _a = 85 °C	_	_	20	
	Collector-emitter capacitance	C _{CE}		V = 0 V, f = 1 MHz	_	900	—	pF

9. Coupled Electrical Characteristics (Unless otherwise specified, $T_a = 25$ °C)

Characteristics	Symbol	Note	Test Condition	Min	Тур.	Max	Unit
Current transfer ratio	I _C /I _F		I _F = 1 mA, V _{CE} = 1 V	1000	6000	—	%
Saturated current transfer ratio	$I_C/I_{F(sat)}$		I _F = 10 mA, V _{CE} = 1 V	500	_	—	%
Collector-emitter saturation voltage	V _{CE(sat)}		I _C = 10 mA, I _F = 1 mA	_	_	1.0	V
			I _C = 100 mA, I _F = 10 mA	0.3	_	1.2	
OFF-state collector current	I _{C(off)}		V_{F} = 0.7 V, V_{CE} = 200 V	_	_	20	μA

10. Isolation Characteristics (Unless otherwise specified, $T_a = 25$ °C)

Characteristics	Symbol	Note	Test Condition	Min	Тур.	Max	Unit
Total capacitance (input to output)	CS	(Note 1)	V _S = 0 V, f = 1 MHz	_	0.6	—	pF
Isolation resistance	R _S	(Note 1)	V_S = 500 V, R.H. \leq 60 %	1 × 10 ¹²	1014	—	Ω
Isolation voltage	BVS	(Note 1)	AC, 60 s	5000	_	_	Vrms

Note 1: This device is considered as a two-terminal device: Pins 1 and 2 are shorted together, and pins 3 and 4 are shorted together.

11. Switching Characteristics (Unless otherwise specified, T_a = 25 °C)

Characteristics	Symbol	Note	Test Condition	Min	Тур.	Max	Unit
Rise time	tr		V _{CC} = 10 V, I _C = 10 mA,	_	60	_	μS
Fall time	t _f		R _L = 100 Ω	_	30	—	
Turn-on time	t _{on}			_	110	—	
Turn-off time	t _{off}			_	30	_	
Turn-on time	t _{on}		See Fig. 11.1.	_	2	—	
Storage time	ts		R _L = 180 Ω, V _{CC} = 10 V, I _F = 16 mA	_	25	—	
Turn-off time	t _{off}			_	80	_	







Fig. 11.1 Switching Time Test Circuit and Waveform

12. Characteristics Curves (Note)







Note: The above characteristics curves are presented for reference only and not guaranteed by production test, unless otherwise noted.

13. Soldering and Storage

13.1. Precautions for Soldering

The soldering temperature should be controlled as closely as possible to the conditions shown below, irrespective of whether a soldering iron or a reflow soldering method is used.


• When using soldering reflow.

The soldering temperature profile is based on the package surface temperature.

(See the figure shown below, which is based on the package surface temperature.)

Reflow soldering must be performed once or twice.

The mounting should be completed with the interval from the first to the last mountings being 2 weeks.



	Symbol	Min	Max	Unit
Preheat temperature	Ts	150	200	°C
Preheat time	t _s	60	120	s
Ramp-up rate $(T_L \text{ to } T_P)$			3	°C/s
Liquidus temperature	TL	2	217	
Time above T_{L}	tL	60	150	S
Peak temperature	Τ _Ρ		260	°C
Time during which T_c is between (T _P – 5) and T_P	t _P		30	s
Ramp-down rate (T _P to T _L)			6	°C/s

An Example of a Temperature Profile When Lead(Pb)-Free Solder Is Used

• When using soldering flow

Preheat the device at a temperature of 150 $^{\circ}$ C (package surface temperature) for 60 to 120 seconds. Mounting condition of 260 $^{\circ}$ C within 10 seconds is recommended.

Flow soldering must be performed once.

When using soldering Iron


Complete soldering within 10 seconds for lead temperature not exceeding 260 °C or within 3 seconds not exceeding 350 °C

Heating by soldering iron must be done only once per lead.

13.2. Precautions for General Storage

- Avoid storage locations where devices may be exposed to moisture or direct sunlight.
- Follow the precautions printed on the packing label of the device for transportation and storage.
- Keep the storage location temperature and humidity within a range of 5 °C to 35 °C and 45 % to 75 %, respectively.
- Do not store the products in locations with poisonous gases (especially corrosive gases) or in dusty conditions.
- Store the products in locations with minimal temperature fluctuations. Rapid temperature changes during storage can cause condensation, resulting in lead oxidation or corrosion, which will deteriorate the solderability of the leads.
- When restoring devices after removal from their packing, use anti-static containers.
- Do not allow loads to be applied directly to devices while they are in storage.
- If devices have been stored for more than two years under normal storage conditions, it is recommended that you check the leads for ease of soldering prior to use.

14. Marking (Note)



Note: A different marking is used for photocouplers that have been qualified according to option (D4) of EN 60747. See Fig.15.4 and Fig.15.5.

15. EN 60747-5-5 Option (D4) Specification

- Part number: TLP627M, TLP627MF (Note 1)
- The following part naming conventions are used for the devices that have been qualified according to option (D4) of EN 60747.

Example: TLP627M(D4-TP1,E

D4: EN 60747 option TP1: Tape type E: [[G]]/RoHS COMPATIBLE **(Note 2)**

Note 1: Use TOSHIBA standard type number for safety standard application.

e.g., TLP627M(D4-TP1,E \rightarrow TLP627M

Note 2: Please contact your Toshiba sales representative for details on environmental information such as the product's RoHS compatibility.

RoHS is the Directive 2011/65/EU of the European Parliament and of the Council of 8 June 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment.

Description	Symbol	Rating	Unit		
Application classification for rated mains voltage ≤ 600 Vrms for rated mains voltage ≤ 1000 Vrms		- V -	_		
Climatic classification			55 / 110 / 21	_	
Pollution degree			2	_	
	TLPxxxx type		890	., .	
Maximum operating insulation voltage	TLPxxxxF type	VIORM	1140	Vpeak	
Input to output test voltage, Method A	TLPxxxx type	Vpr	1424	Vpeak	
$V_{pr} = 1.6 \times VIORM$, type and sample test $t_p = 10 \text{ s}$, partial discharge $< 5 \text{ pC}$	TLPxxxxF type		1824		
Input to output test voltage, Method B	TLPxxxx type	- Vpr	1670	Vpeak	
$V_{pr} = 1.875 \times V_{IORM}$, 100 % production test $t_p = 1 \text{ s}$, partial discharge < 5 pC	TLPxxxxF type		2140		
Highest permissible overvoltage (transient overvoltage, t _{pr} = 60 s)		VTR	8000	Vpeak	
Safety limiting values (max. permissible ratings in case of also refer to thermal derating cu current (input current IF, Pso = 0) power (output or total power dissipation) temperature	lsi Pso Ts	400 700 150	mA mW °C		
Insulation resistance VIO = 500 V, Ta = 25 °C VIO = 500 V, Ta = 100 °C VIO = 500 V, Ta = 100 °C VIO = 500 V, Ta = Ts VIO = 500 V, Ta = Ts	Rsi	≥ 10 ¹² ≥ 10 ¹¹ ≥ 10 ⁹	Ω		

Fig. 15.1 EN 60747 Insulation Characteristics

10


		7.62 mm pitch TLPxxx type	10.16 mm pitch TLPxxxF type	
Minimum creepage distance	Cr	7.0 mm	8.0 mm	
Minimum clearance	CI	7.0 mm	8.0 mm	
Minimum insulation thickness	ti	0.4 mm		
Comparative tracking index	СТІ	175		



- Note: If a printed circuit is incorporated, the creepage distance and clearance may be reduced below this value. (e.g., at a standard distance between soldering eye centers of 7.5 mm). If this is not permissible, the user shall take suitable measures.
- Note: This photocoupler is suitable for **safe electrical isolation** only within the safety limit data. Maintenance of the safety data shall be ensured by means of protective circuits.





Fig. 15.3 Marking on packing for EN 60747



Note: The above marking is applied to the photocouplers that have been qualified according to option (D4) of EN 60747.

Figure		-	nent procedure according to EN 60747 tion and sampling tests.
	<u>Method A</u>		. Vinitial (8 kV)
(for type and destructive te	sampling tests, sts)	V	Vpr (1424 V for TLPxxxx) (1824 V for TLPxxxxF)
t1, t2	= 1 t	o 10 s	VIORM (890 V for TLPxxxx)
t3, t4	= 1 s		(1140 V for TLPxxxxF)
tp (Measuring	time for		
partial dis	scharge) = 10	s 0	$\begin{array}{c c} & & & \\ \hline \\$
tb	= 12	s	t_3 t_p t_4
tini	= 60	S	t1 tini t2 tb








Package Dimensions

TLP627M,TLP627MF

Unit: mm



Weight: 0.24 g (typ.)


Package Name(s) TOSHIBA: 11-5B2S



Package Dimensions

TLP627M,TLP627MF

Unit: mm




Weight: 0.24 g (typ.)

Package Name(s)

TOSHIBA: 11-5B201S

Package Dimensions

Unit: mm




Weight: 0.24 g (typ.)

Package Name(s) TOSHIBA: 11-5B205S

Package Dimensions

TLP627M,TLP627MF

Unit: mm




Weight: 0.24 g (typ.)

	Package Name(s)
TOSHIBA: 11-5B202S	

Package Dimensions

Unit: mm



Weight: 0.24 g (typ.)

Package Name(s) TOSHIBA: 11-5B204S

RESTRICTIONS ON PRODUCT USE

Toshiba Corporation and its subsidiaries and affiliates are collectively referred to as "TOSHIBA". Hardware, software and systems described in this document are collectively referred to as "Product".

- TOSHIBA reserves the right to make changes to the information in this document and related Product without notice.
- This document and any information herein may not be reproduced without prior written permission from TOSHIBA. Even with TOSHIBA's written permission, reproduction is permissible only if reproduction is without alteration/omission.
- Though TOSHIBA works continually to improve Product's quality and reliability, Product can malfunction or fail. Customers are responsible for complying with safety standards and for providing adequate designs and safeguards for their hardware, software and systems which minimize risk and avoid situations in which a malfunction or failure of Product could cause loss of human life, bodily injury or damage to property, including data loss or corruption. Before customers use the Product, create designs including the Product, or incorporate the Product into their own applications, customers must also refer to and comply with (a) the latest versions of all relevant TOSHIBA information, including without limitation, this document, the specifications, the data sheets and application notes for Product and the precautions and conditions set forth in the "TOSHIBA Semiconductor Reliability Handbook" and (b) the instructions for the applications, including but not limited to (a) determining the appropriateness of the use of this Product in such design or applications; (b) evaluating and determining the applicability of any information contained in this document, or in charts, diagrams, programs, algorithms, sample application circuits, or any other referenced documents; and (c) validating all operating parameters for such designs and applications.
- PRODUCT IS NEITHER INTENDED NOR WARRANTED FOR USE IN EQUIPMENTS OR SYSTEMS THAT REQUIRE EXTRAORDINARILY HIGH LEVELS OF QUALITY AND/OR RELIABILITY, AND/OR A MALFUNCTION OR FAILURE OF WHICH MAY CAUSE LOSS OF HUMAN LIFE, BODILY INJURY, SERIOUS PROPERTY DAMAGE AND/OR SERIOUS PUBLIC IMPACT ("UNINTENDED USE").

Except for specific applications as expressly stated in this document, Unintended Use includes, without limitation, equipment used in nuclear facilities, equipment used in the aerospace industry, lifesaving and/or life supporting medical equipment, equipment used for automobiles, trains, ships and other transportation, traffic signaling equipment, equipment used to control combustions or explosions, safety devices, elevators and escalators, and devices related to power plant.

IF YOU USE PRODUCT FOR UNINTENDED USE, TOSHIBA ASSUMES NO LIABILITY FOR PRODUCT. For details, please contact your TOSHIBA sales representative or contact us via our website.

- · Do not disassemble, analyze, reverse-engineer, alter, modify, translate or copy Product, whether in whole or in part.
- Product shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any
 applicable laws or regulations.
- The information contained herein is presented only as guidance for Product use. No responsibility is assumed by TOSHIBA for any infringement of patents or any other intellectual property rights of third parties that may result from the use of Product. No license to any intellectual property right is granted by this document, whether express or implied, by estoppel or otherwise.
- ABSENT A WRITTEN SIGNED AGREEMENT, EXCEPT AS PROVIDED IN THE RELEVANT TERMS AND CONDITIONS OF SALE FOR PRODUCT, AND TO THE MAXIMUM EXTENT ALLOWABLE BY LAW, TOSHIBA (1) ASSUMES NO LIABILITY WHATSOEVER, INCLUDING WITHOUT LIMITATION, INDIRECT, CONSEQUENTIAL, SPECIAL, OR INCIDENTAL DAMAGES OR LOSS, INCLUDING WITHOUT LIMITATION, LOSS OF PROFITS, LOSS OF OPPORTUNITIES, BUSINESS INTERRUPTION AND LOSS OF DATA, AND (2) DISCLAIMS ANY AND ALL EXPRESS OR IMPLIED WARRANTIES AND CONDITIONS RELATED TO SALE, USE OF PRODUCT, OR INFORMATION, INCLUDING WARRANTIES OR CONDITIONS OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, ACCURACY OF INFORMATION, OR NONINFRINGEMENT.
- GaAs (Gallium Arsenide) is used in Product. GaAs is harmful to humans if consumed or absorbed, whether in the form of dust or vapor. Handle with care and do not break, cut, crush, grind, dissolve chemically or otherwise expose GaAs in Product.
- Do not use or otherwise make available Product or related software or technology for any military purposes, including without limitation, for the design, development, use, stockpiling or manufacturing of nuclear, chemical, or biological weapons or missile technology products (mass destruction weapons). Product and related software and technology may be controlled under the applicable export laws and regulations including, without limitation, the Japanese Foreign Exchange and Foreign Trade Law and the U.S. Export Administration Regulations. Export and re-export of Product or related software or technology are strictly prohibited except in compliance with all applicable export laws and regulations.
- Please contact your TOSHIBA sales representative for details as to environmental matters such as the RoHS compatibility of Product. Please use Product in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. TOSHIBA ASSUMES NO LIABILITY FOR DAMAGES OR LOSSES OCCURRING AS A RESULT OF NONCOMPLIANCE WITH APPLICABLE LAWS AND REGULATIONS.

TOSHIBA ELECTRONIC DEVICES & STORAGE CORPORATION

https://toshiba.semicon-storage.com/