


Automotive-grade N-channel 60 V, 1.2 mΩ typ., 120 A STripFET™ F7 Power MOSFET in a PowerFLAT™ 5x6 package

PowerFLAT™ 5x6

Figure 1: Internal schematic diagram



Datasheet - production data

Features

Order code	V ds	R _{DS(on)} max	ID
STL225N6F7AG	60 V	1.4 mΩ	120 A

- AEC-Q101 qualified
- Among the lowest R_{DS(on)} on the market
- Excellent FoM (figure of merit)
- Low Crss/Ciss ratio for EMI immunity
- High avalanche ruggedness
- Wettable flank package

Applications

• DC-DC converter for H.E.V. (hybrid electric vehicle)

Description

This N-channel Power MOSFET utilizes STripFET™ F7 technology with an enhanced trench gate structure that results in very low onstate resistance, while also reducing internal capacitance and gate charge for faster and more efficient switching.

Table 1: Device summary

Order code Ma		Marking	Package	Packaging
	STL225N6F7AG	225N6F7	PowerFLAT [™] 5x6	Tape and reel

DocID028557 Rev 3

This is information on a product in full production.

Contents

Contents

1	Electric	al ratings	3
2	Electric	al characteristics	4
	2.1	Electrical characteristics (curves)	6
3	Test cir	cuits	8
4	Packag	e mechanical data	9
	4.1	PowerFLAT 5x6 package mechanical data	9
	4.2	Packing information	12
5	Revisio	n history	14



°C/W

0.8

1 Electrical ratings

Table 2: Absolute maximum ratings

Symbol	Parameter	Value	Unit
Vds	Drain-source voltage	60	V
V _{GS}	Gate-source voltage	±20	V
I _D ⁽¹⁾	Drain current (continuous) at T _C = 25 °C	120	А
ID ⁽¹⁾	Drain current (continuous) at T _c = 100 °C	120	А
I _{DM} ⁽¹⁾⁽²⁾	Drain current (pulsed)	480	А
Ртот	Total dissipation at $T_C = 25 \ ^{\circ}C$	188	W
Tj	T _j Operating junction temperature range		*0
T _{stg}	-55 to 1		°C

Notes:

⁽¹⁾This value is limited by package.

 $^{(2)}\mbox{Pulse}$ width limited by safe operating area

Table 3: Thermal data				
Symbol Parameter		Value	Unit	
Rthj-pcb ⁽¹⁾	Thermal resistance junction-pcb		°C/W	

Notes:

R_{thj-case}

 $^{(1)}\!When$ mounted on FR-4 board of 1 inch², 2oz Cu, t < 10 s.

Thermal resistance junction-case



2 Electrical characteristics

(Tc = 25 °C unless otherwise specified)

Table 4: On /off states						
Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit
V _{(BR)DSS}	Drain-source breakdown voltage	$I_D = 1$ mA, $V_{GS} = 0$ V	60			V
IDSS	Zero gate voltage drain current	V _{GS} = 0 V V _{DS} = 60 V			1	μA
Igss	Gate-body leakage current	$V_{GS} = 20 \text{ V}, \text{ V}_{DS} = 0 \text{ V}$			100	nA
$V_{GS(th)}$	Gate threshold voltage	V_{DS} = V_{GS} , I_D = 250 μ A	2		4	V
R _{DS(on)}	Static drain-source on-resistance	$V_{GS}=10~V,~I_{D}=60~A$		1.2	1.4	mΩ

Table 5: Dynamic

Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit
Ciss	Input capacitance		-	6500	-	pF
Coss	Output capacitance	$V_{DS} = 25 V, f = 1 MHz,$	-	3200	-	pF
C _{rss}	Reverse transfer capacitance	V _{GS} = 0 V		230	-	рF
Qg	Total gate charge	$V_{DD} = 30 \text{ V}, I_D = 120 \text{ A},$	-	98	-	nC
Qgs	Gate-source charge	V _{GS} = 0 to 10 V	-	38	-	nC
Q _{gd}	Gate-drain charge	(see Figure 14: "Test circuit for gate charge behavior").		28	-	nC

Table 6: Switching times

Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit
t _{d(on)}	Turn-on delay time	$V_{DD} = 30 V, I_D = 60 A,$	-	41	-	ns
tr	Rise time	$R_{G} = 4.7 \Omega, V_{GS} = 10 V$	-	45	-	ns
t _{d(off)}	Turn-off delay time	(see Figure 13: "Test circuit for resistive load switching times"	-	68	-	ns
t _f	Fall time	and Figure 18: "Switching time waveform").	-	35	-	ns




Electrical characteristics


	Table 7: Source-drain diode						
Symbol	Parameter Test conditions		Min.	Тур.	Max.	Unit	
V _{SD} ⁽¹⁾	Forward on voltage	I _{SD} = 60 A, V _{GS} = 0 V	-		1.2	V	
trr	Reverse recovery time	I _D = 60 A, di/dt = 100 A/µs	-	69		ns	
Qrr	Reverse recovery charge	V _{DD} = 48 V (see <i>Figure 15: "Test circuit for</i>		103		nC	
Irrm	Reverse recovery current	inductive load switching and diode recovery times").	-	3		А	


Notes:

 $^{(1)}\text{Pulsed:}$ pulse duration = 300 $\mu\text{s},$ duty cycle 1.5%











DocID028557 Rev 3




57

Electrical characteristics










DocID028557 Rev 3

3 Test circuits









4 Package mechanical data

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK[®] packages, depending on their level of environmental compliance. ECOPACK[®] specifications, grade definitions and product status are available at: *www.st.com*. ECOPACK[®] is an ST trademark.

4.1 PowerFLAT 5x6 package mechanical data




Figure 19: PowerFLAT™ 5x6 WF type C package outline






Package mechanical data

STL225N6F7AG

nechanical data	chanical data STL225N6F7AG				
T	able 8: PowerFLAT™ 5x6	6 WF type C mechanical	data		
Dim.		mm			
Dini.	Min.	Тур.	Max.		
A	0.80		1.00		
A1	0.02		0.05		
A2		0.25			
b	0.30		0.50		
С	5.80	6.00	6.10		
D	5.00	5.20	5.40		
D2	4.15		4.45		
D3	4.05	4.20	4.35		
D4	4.80	5.00	5.10		
D5	0.25	0.40	0.55		
D6	0.15	0.30	0.45		
е		1.27			
E	6.20	6.40	6.60		
E2	3.50		3.70		
E3	2.35		2.55		
E4	0.40		0.60		
E5	0.08		0.28		
E6	0.20	0.325	0.45		
E7	0.85	1.00	1.15		
E9	4.00	4.20	4.40		
E10	3.55	3.70	3.85		
К	1.05		1.35		
L	0.90	1.00	1.10		
L1	0.175	0.275	0.375		
θ	0°		12°		




Package mechanical data



57


DocID028557 Rev 3

11/15




4.2 Packing information

Figure 22: PowerFLAT™ 5x6 package orientation in carrier tape









5 Revision history

Table 9: Document revision history

Date	Revision	Changes
23-Oct-2015	1	First release.
09-Jun-2016	2	Updated title and features in cover page. Updated Table 2: "Absolute maximum ratings", Table 5: "Dynamic", Table 6: "Switching times" and Table 7: "Source-drain diode" Minor text changes.
17-Mar-2017	3	Datasheet promoted from preliminary data to production data. Modified title and features on cover page. Modified Table 2: "Absolute maximum ratings". Modified Table 5: "Dynamic", Table 6: "Switching times" and Table 7: "Source-drain diode". Added Section 2.1: "Electrical characteristics (curves)". Minor text changes.



IMPORTANT NOTICE – PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2017 STMicroelectronics - All rights reserved



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

STMicroelectronics: STL225N6F7AG