

Si5348 Rev E Data Sheet


Network Synchronizer for SyncE/ 1588 PTP Telecom Boundary (T-BC) and Slave (T-SC) Clocks

The Si5348 combines the industry's smallest footprint and lowest power network synchronizer clock with unmatched frequency synthesis flexibility and ultra-low jitter. The Si5348 is ideally suited for wireless backhaul, IP radio, small and macro cell wireless communications systems, and data center switches requiring both traditional and packet based network synchronization.

The three independent DSPLLs[™] are individually configurable as a SyncE PLL, IEEE 1588 DCO or a general-purpose PLL for processor/FPGA clocking. The Si5348 can also be used in legacy SETS systems needing Stratum 3/3E compliance. The optional digitally controlled oscillator (DCO) mode provides precise timing adjustment to 1 ppt for 1588 (PTP) clock steering applications. The unique design of the Si5348 allows the TCXO/OCXO reference input to determine the device's frequency accuracy and stability. The Si5348 is programmable via a serial interface with in-circuit programmable non-volatile memory so it always powers up into a known configuration. Programming the Si5348 is easy with ClockBuilder Pro[™] software. Factory pre-programmed devices are also available.

Applications:

- Synchronous Ethernet (SyncE) ITU-T G.8262 EEC Option 1 & 2
- Telecom Boundary Clock (T-BC) as defined by ITU-T G.8273.2
- · IEEE 1588 (PTP) slave clock synchronization
- Stratum 3/3E, G.812, G.813 network synchronization



KEY FEATURES

- Three independent DSPLLs in a single monolithic IC supporting flexible SyncE/ IEEE 1588 and SETS architectures
- · Ultra-low jitter of 95 fs
- Enhanced hitless switching minimizes output phase transients
- · Input frequency range:
 - · External crystal: 48 to 54 MHz
 - REF clock: 5 to 250 MHz
 - · Diff clock: 8 kHz to 750 MHz
 - · LVCMOS clock: 8 kHz to 250 MHz
- · Output frequency range:
 - Differential: 1 PPS to 718.5 MHz
 - · LVCMOS: 1 PPS to 250 MHz
- Meets the requirements of:
 - ITU-T G.8262 (SyncE) EEC Options 1 and 2
 - ITU-T G.812 Type III, IV
- ITU-T G.813 Option 1
- Telcordia GR-1244, GR-253 (Stratum-3/3E)

1. Feature List

The Si5348 features are listed below:

- Three independent DSPLLs in a single monolithic IC supporting flexible SyncE/IEEE 1588 and SETS architectures
- Ultra-Low Jitter
 - 95 fs typ (12 kHz to 20 MHz)
- Meets the requirements of:
 - ITU-T G.8273.2 T-BC
 - ITU-T G.8262 (SyncE) EEC Options 1 & 2
 - ITU-T G.812 Type III, IV
 - ITU-T G.813 Option 1
 - Telcordia GR-1244, GR-253 (Stratum-3/3E)
- Each DSPLL generates any output frequency from any input frequency
- Input frequency range:
 - External crystal: 48–54 MHz
 - REF clock: 5–250 MHz
 - Diff clock: 8 kHz–750 MHz
 - LVCMOS clock: 8 kHz-250 MHz
- Output frequency range:
 - Differential: 1 PPS to 718.5 MHz
 - LVCMOS: 1 PPS to 250 MHz
- Independent Frequency-on-the-fly for each DSPLL
- Enhanced hitless switching minimizes output phase transients for 8 kHz, 19.44 MHz, 25 MHz, and all other input frequencies.

- Pin or software controllable DCO on each DSPLL with typical resolution to 1 ppt/step
- TCXO/OCXO reference input determines DSPLL free-run/holdover accuracy and stability
- Programmable jitter attenuation bandwidth per DSPLL: 0.001 Hz to 4 kHz
- Highly configurable output drivers: LVDS, LVPECL, LVCMOS, HCSL, CML
- Core voltage:
 - VDD: 1.8 V ±5%
 - VDDA: 3.3 V ±5%
- Independent output supply pins: 3.3 V, 2.5 V, or 1.8 V
- Built-in power supply filtering
- Status monitoring: LOS, OOF, LOL
- Serial Interface: I²C or SPI (3-wire or 4-wire)
- ClockBuilder Pro software simplifies device configuration
- 5 input, 7 output, 64 QFN
- Temperature range: –40 to +85 °C
- Pb-free, RoHS-6 compliant

2. Related Documents

| Document/Resource | Description/URL |
|---|--|
| Si5348 Rev E Family Reference Manual | To be used in conjunction with this data sheet, which contains more detailed explanations about the operation of the device. https://www.skyworksinc.com/-/media/Skyworks/SL/documents/public/reference-manuals/si5348-e-family.pdf |
| Crystal Reference Manual | https://www.skyworksinc.com/-/media/Skyworks/SL/documents/public/reference-manuals/si534x-8x-9x-recommended-crystals-rm.pdf |
| Quality and Reliability | https://www.skyworksinc.com/Quality |
| Development Kits | https://www.skyworksinc.com/en/Products/Timing |
| ClockBuilder Pro (CBPro) Software | https://www.skyworksinc.com/en/Application-Pages/Clockbuilder-Pro-Soft- ware |
| AN1077: Selecting the Right Clocks for Timing Synchro- nization Applications | https://www.skyworksinc.com/-/media/Skyworks/SL/documents/public/appli- cation-notes/an1077-selecting-clocks-for-timing-synchronization.pdf |
| UG123: SiOCXO1-EVB Evaluation Board Users Guide | https://www.skyworksinc.com/-/media/Skyworks/SL/documents/public/user- guides/UG123.pdf |
| UG362: Si5348 EVB User Guide | https://www.skyworksinc.com/-/media/Skyworks/SL/documents/public/user- guides/ug362-si5348-e-evb.pdf |
| UG364: SiTCXO1-EVB Evaluation Board User's Guide | https://www.skyworksinc.com/-/media/Skyworks/SL/documents/public/user- guides/ug364-sitcxo1-evb-ug.pdf |
| AN1170: Holdover Consideration for Si5348 Network Synchronizer Clocks | https://www.skyworksinc.com/-/media/Skyworks/SL/documents/public/appli- cation-notes/an1170-si5348-holdover-considerations.pdf |
| AN1173: Si5348 Rev D to Rev E Changes | https://www.skyworksinc.com/-/media/Skyworks/SL/documents/public/appli- cation-notes/an1173-si5348-revd-to-reve-changes.pdf |

Table 2.1. Related Documentation and Software

3. Ordering Guide


Table 3.1. Si5348 Ordering Guide

| Ordering Part Number | # of DSPLLs | Output Clock Frequency Range | Package | RoHS-6 Pb-Free | Temperature Range | |
|------------------------------|----------------|---------------------------------|--------------------------|-------------------|----------------------|--|
| Si5348A-E-GM ^{1, 2} | 3 | 1 Hz to 718.5 MHz | 64-Lead 9x9 QFN | Yes | –40 to 85 °C | |
| Si5348B-E-GM ^{1, 2} | 3 | 1 Hz to 350 MHz | | res | | |
| Si5348-E-EVB | _ | _ | Evaluation Board | _ | _ | |
| SiOCXO1-EVB | _ | 12.800 MHz | OCXO Evaluation Board | _ | _ | |
| SITCXO1-EVB | | 40 MHz | TCXO Evaluation Board | _ | _ | |

Note:

1. Add an "R" at the end of the device part number to denote tape and reel ordering options.

2. Custom, factory pre-programmed devices are available. Ordering part numbers are assigned by the ClockBuilder Pro software. Part number format is: Si5348A-Dxxxxx-GM, where "xxxxx" is a unique numerical sequence representing the pre-programmed configuration.



*See Ordering Guide table for current product revision ** 5 digits; assigned by ClockBuilder Pro

Figure 3.1. Ordering Part Number Fields

Table of Contents

| 1. | Feature List | • | . 2 |
|----|--|---|-----|
| 2. | Related Documents | - | . 3 |
| 3. | Ordering Guide | | . 4 |
| 4. | Functional Description. | | . 7 |
| | 4.1 Standards Compliance | | . 7 |
| | 4.2 Frequency Configuration | | . 7 |
| | 4.3 DSPLL Loop Bandwidth | | . 7 |
| | 4.3.1 Fastlock Feature | | |
| | 4.4 Modes of Operation | | |
| | 4.4.1 Initialization and Reset . < | | |
| | 4.4.2 Free-run Mode | | |
| | 4.4.4 Locked Mode | | |
| | 4.4.5 Holdover Mode | | |
| | 4.4.6 Frequency on the Fly | | |
| | 4.5 Digitally-Controlled Oscillator (DCO) Mode | | |
| | | | |
| | 4.6 External Reference (XA/XB, REF/REFb) | | |
| | 4.6.1 External Crystal (XA/XB) | | |
| | 4.6.2 External Reference (REF/REFb) | | |
| | 4.7 Inputs (IN0, IN1, IN2, REF, IN3, IN4) | | |
| | 4.7.1 Input Selection | | |
| | 4.7.2 Manual Input Selection | | |
| | 4.7.3 Automatic Input Selection | | |
| | 4.7.4 Input Configuration and Terminations | | |
| | 4.7.5 Hitless Input Switching | | |
| | 4.7.6 Ramped Input Switching | | |
| | 4.7.7 Glitchless Input Switching | | |
| | 4.7.6 Typical Hitless Switching Scenarios | | |
| | | | |
| | 4.8 Fault Monitoring | | |
| | 4.8.1 Input LOS Detection | | |
| | 4.8.2 XA/XB LOS Detection | | |
| | 4.8.3 OOF Detection | | |
| | 4.8.5 Fast OOF Monitor | | |
| | 4.8.6 LOL Detection. | | |
| | 4.8.7 Interrupt Pin (INTRb) | | |
| | | | |
| | 4.9 Outputs | | |
| | 4.9.1 Output Closspoint | | |
| | 4.9.3 Output Terminations. | | |
| | 4.9.4 Output Signal Format | | |
| | ······································ | | |

Skyworks Solutions, Inc. • Phone [781] 376-3000 • Fax [781] 376-3100 • sales@skyworksinc.com • www.skyworksinc.com Rev. 0.95 • Skyworks Proprietary Information • Products and Product Information are Subject to Change Without Notice • December 3, 2021

| 4.9.5 Programmable Common Mode Voltage For Differential Outputs | .20 |
|---|------|
| 4.9.6 LVCMOS Output Impedance Selection | .21 |
| 4.9.7 LVCMOS Output Signal Swing | .21 |
| 4.9.8 LVCMOS Output Polarity | |
| 4.9.9 Output Enable/Disable | |
| 4.9.10 Output Disable During LOL | |
| 4.9.11 Output Disable During XAXB_LOS | |
| 4.9.12 Output Driver State When Disabled | |
| 4.9.13 Synchronous/Asynchronous Output Disable | |
| 4.9.14 Output Divider (R) Synchronization | |
| 4.10 Power Management. | .22 |
| 4.11 In-Circuit Programming | .22 |
| 4.12 Serial Interface | .22 |
| 4.13 Custom Factory Preprogrammed Parts | .22 |
| 5. Register Map | 23 |
| 6. Electrical Specifications | 24 |
| | |
| 7. Typical Application Schematic | 39 |
| 8. Detailed Block Diagram | 40 |
| 9. Typical Operating Characteristics (Jitter and Phase Noise) | . 41 |
| 10. Pin Descriptions. | 42 |
| 11. Package Outline | |
| | |
| 12. PCB Land Pattern | . 47 |
| 13. Top Marking | 49 |
| 14. Device Errata | 50 |
| 15. Revision History. | 51 |
| | |

4. Functional Description

The Si5348 offers three DSPLLs that can be independently configured and controlled through the serial interface. Each of the DSPLLs support locked, free-run, and holdover modes of operation with an optional DCO mode for IEEE 1588 applications. The device requires an external crystal and an external reference (TCXO or OCXO) to operate. The reference input (REF/REFb) determines the frequency accuracy and stability while in free-run and holdover modes. The external crystal completes the internal oscillator circuit (OSC) which is used by the DSPLL for intrinsic jitter performance. There are three main inputs (IN0 - IN2) for synchronizing the DSPLLs. Input selection can be manual or automatically controlled using an internal state machine. Two additional manually selected inputs are available to DSPLL D. Any of the output clocks (OUT0 to OUT6) can be configured to any of the DSPLLs using a flexible crosspoint connection. Output 6 is the only output that can be configured for a 1 Hz output to support 1 PPS.

4.1 Standards Compliance

Each of the DSPLLs meet the requirements of ITU-T G.8262 (SyncE), G.812, G.813, G.8273.2 (T-BC), in addition to Telcordia GR-1244 and GR-253 as shown in the compliance report. The DCO feature enables IEEE1588 (PTP) implementations in addition to hybrid SyncE + IEEE1588 (T-BC). The following table lists the Si5348 compliance reports for these standards.

| Standard | Compliance Report | |
|----------------|---|--|
| G.8262 (SyncE) | https://www.skyworksinc.com/en/Markets/Optical-Networking | |
| G.812 | tps://www.skyworksinc.com/en/Markets/Optical-Networking | |
| G.813 | https://www.skyworksinc.com/en/Markets/Optical-Networking | |
| GR-1244 | https://www.skyworksinc.com/en/Markets/Optical-Networking | |
| GR-253 | https://www.skyworksinc.com/en/Markets/Optical-Networking | |

Table 4.1. Si5348 Standards Compliance Reports

4.2 Frequency Configuration

The frequency configuration for each of the DSPLLs is programmable through the serial interface and can also be stored in non-volatile memory. The combination of fractional input dividers (Pn/Pd), fractional frequency multiplication (Mn/Md), and integer output division (Rn) allows each of the DSPLLs to lock to any input frequency and generate virtually any output frequency. All divider values for a specific frequency plan are easily determined using the ClockBuilder Pro software. Each PLL can be reconfigured during operation without affecting the others. See 4.4.6 Frequency on the Fly for more information.

4.3 DSPLL Loop Bandwidth

The DSPLL loop bandwidth determines the amount of input clock jitter and wander attenuation. Register configurable DSPLL loop bandwidth settings of 1 mHz to 4 kHz are available for selection for each of the DSPLLs. Since the loop bandwidth is controlled digitally, each of the DSPLLs will always remain stable with less than 0.1 dB of peaking regardless of the loop bandwidth selection.

| Table 4.2. Lo | op Bandwidth Requirements for North America |
|---------------|---|
| | |

| SONET (Telcordia) | SDH (ITU-T) | SyncE (ITU-T) | Loop Bandwidth |
|-------------------|----------------|---------------------|----------------|
| GR-253 Stratum 3E | G.812 Type III | _ | 0.001 Hz |
| GR-253 Stratum 3 | G.812 Type IV | G.8262 EEC Option 2 | <0.1 Hz |
| _ | G.813 Option 1 | G.8262 EEC Option 1 | 1 - 10 Hz |

4.3.1 Fastlock Feature

Selecting a low DSPLL loop bandwidth (e.g. 0.1 Hz) will generally lengthen the lock acquisition time. The fastlock feature allows setting a temporary Fastlock Loop Bandwidth that is used during the lock acquisition process. Higher fastlock loop bandwidth settings will enable the DSPLLs to lock faster. Fastlock Loop Bandwidth settings in the range of 100 Hz to 4 kHz are available for selection. Once lock acquisition has completed, the DSPLL's loop bandwidth will automatically revert to the nominal DSPLL Loop Bandwidth setting. The fastlock feature can be enabled or disabled independently for each of the DSPLLs.

4.4 Modes of Operation

Once initialization is complete, each of the DSPLLs operates independently in one of four modes: Free-run Mode, Lock Acquisition Mode, Locked Mode, or Holdover Mode. A state diagram showing the modes of operation is shown in the figure below. The following sections describe each of these modes in greater detail.




Figure 4.1. Modes of Operation

4.4.1 Initialization and Reset

Once power is applied, the device begins an initialization period where it downloads default register values and configuration data from NVM and performs other initialization tasks. Communicating with the device through the serial interface is possible once this initialization period is complete. No clocks will be generated until the initialization is complete. There are two types of resets available. A hard reset is functionally similar to a device power-up. All registers will be restored to the values stored in NVM, and all circuits will be restored to their initial state including the serial interface. A hard reset is initiated using the RSTb pin or by asserting the hard reset bit. A soft reset bypasses the NVM download. It is simply used to initiate register configuration changes. A hard reset affects all DSPLLs, while a soft reset can either affect all or each DSPLL individually.

4.4.2 Free-run Mode

Once power is applied to the Si5348 and initialization is complete, all three DSPLLs will automatically enter freerun mode. The frequency accuracy of the generated output clocks in freerun mode is entirely dependent on the frequency accuracy of the clock source at the reference inputs (REF/REFb). A TCXO or OCXO is recommended for applications that need frequency accuracy and stability to meet the synchronization standards as shown in the following table:

| SONET (Telcordia) | SDH (ITU-T) | SyncE (ITU-T) | Free-run Accuracy |
|-------------------|----------------|---------------------|-------------------|
| GR-253 Stratum 3E | G.812 Type III | _ | ±4.6 ppm |
| GR-253 Stratum 3 | G.812 Type IV | G.8262 EEC Option 2 | |
| _ | G.813 Option 1 | G.8262 EEC Option 1 | |

Table 4.3. Free-run Accuracy for North American and European Synchronization Standards

4.4.3 Lock Acquisition Mode


Each of the DSPLLs independently monitors its configured inputs for a valid clock. If at least one valid clock is available for synchronization, a DSPLL will automatically start the lock acquisition process. If the fast lock feature is enabled, a DSPLL will acquire lock using the Fastlock Loop Bandwidth setting and then transition to the DSPLL Loop Bandwidth setting when lock acquisition is complete. During lock acquisition the outputs will generate a clock that follows the VCO frequency change as it pulls-in to the input clock frequency.

4.4.4 Locked Mode

Once locked, a DSPLL will generate output clocks that are both frequency and phase locked to their selected input clocks. At this point, any XTAL frequency drift will not affect the output frequency. Each DSPLL has its own LOLb pin and status bit to indicate when lock is achieved. Refer to 4.8.6 LOL Detection for more details on the operation of the loss of lock circuit.

4.4.5 Holdover Mode

Any of the DSPLLs will automatically enter Holdover Mode when the selected input clock becomes invalid and no other valid input clocks are available for selection. Each DSPLL uses an averaged input clock frequency as its final holdover frequency to minimize the disturbance of the output clock phase and frequency when an input clock suddenly fails. The holdover circuit for each DSPLL stores up to 120 seconds of historical frequency data while locked to a valid clock input. The final averaged holdover frequency value is calculated from a programmable window within the stored historical frequency data. Both the window size and delay are programmable as shown in the figure below. The window size determines the amount of holdover frequency averaging. The delay value allows ignoring frequency data that may be corrupt just before the input clock failure.





When entering holdover, a DSPLL will pull its output clock frequency to the calculated averaged holdover frequency. While in holdover, the output frequency drift is entirely dependent on the external reference clock connected to the REF/REFb pins. If the clock input becomes valid, a DSPLL will automatically exit the holdover mode and re-acquire lock to the new input clock. This process involves pulling the output clock frequencies to achieve frequency and phase lock with the input clock. This pull-in process is glitchless.

The DSPLL output frequency when exiting holdover can be ramped (recommended). Just before the exit is initiated, the difference between the current holdover frequency and the new desired frequency is measured. Using the calculated difference and a user-select-able ramp rate, the output is linearly ramped to the new frequency. The ramp rate can be 0.2 ppm/s, 40,000 ppm/s, or any of about 40 values in between. The DSPLL loop BW does not limit or affect ramp rate selections (and vice versa). CBPro defaults to ramped exit from holdover. The same ramp rate settings are used for both exit from holdover and ramped input switching. For more information on ramped input switching see 4.7.6 Ramped Input Switching.

Note: If ramped holdover exit is not selected, the holdover exit is governed either by (1) the DSPLL loop BW or (2) a user-selectable holdover exit BW.

4.4.6 Frequency on the Fly

The Si5348 Rev E uses register writes to support configuration on the fly to allow certain characteristics to be changed on one DSPLL without affecting the clocks generated from other DSPLLs. These characteristics include Input/Output Frequencies, PLL bandwidth, LOL, and OOF settings. This feature is limited to DSPLLs A, C, and D and can only be used on DSPLLs that do not share a common input with other DSPLLs. See the Si5348 Rev E Reference Manual for more details.

4.5 Digitally-Controlled Oscillator (DCO) Mode

The DSPLLs support a DCO mode where their output frequencies are adjustable in pre-defined steps defined by frequency step words (FSW). The frequency adjustments are controlled through the serial interface or by pin control using frequency increments (FINC) or decrements (FDEC). A FINC will add the frequency step word to the DSPLL output frequency, while a FDEC will decrement it. The DCO mode is available when the DSPLL is operating in locked mode. The DCO mode is mainly used in IEEE1588 (PTP) applications where a clock needs to be generated based on recovered timestamps. In this case timestamps are recovered by the PHY/MAC. A processor containing servo software controls the DCO to close the timing loop between the master and slave nodes. The processor has the option of using the FINC/FDEC pin controls to update the DCO frequency or by controlling it through the serial interface.

4.6 External Reference (XA/XB, REF/REFb)

The external crystal at the XA/XB pins determines jitter performance of the output clocks, and the external reference clock at the REF/REFb pins determines the frequency accuracy, wander and stability during free-run or holdover modes. Jitter from the external clock on the REF/REFb pins will have little effect on the output jitter performance, depending upon the selected bandwidth.




Figure 4.3. External Reference Connections

Note: XA, XB, REF, and REFb must not exceed the maximum input voltage listed in Table 6.3 Input Clock Specifications on page 25.

4.6.1 External Crystal (XA/XB)

The external crystal (XTAL) is used in combination with the internal oscillator (OSC) to produce an ultra low jitter reference clock for the DSPLLs. The device includes internal XTAL loading capacitors which eliminate the need for external capacitors and also has the benefit of reduced noise coupling from external sources. A crystal in the range of 48 to 54 MHz is recommended for best jitter performance. Although the device includes built-in XTAL load capacitors (CL) of 8 pF, crystals with load capacitances up to 18 pF can also be accommodated. The Si5348 Rev E Reference Manual provides additional information on PCB layout recommendations for the crystal to ensure optimum jitter performance. Although *not* recommended, the device can also accommodate an external clock at the XA/XB pins instead of a crystal. Selection between the external crystal or clock is controlled by register configuration. The internal crystal loading capacitors (CL) are disabled in this mode. Refer to Table 6.12 Crystal Specifications¹ on page 37 for reference clock requirements when using this mode. The Si5348 Rev E Reference Manual provides additional information on PCB layout recommendations on PCB layout recommended in the internal crystal back of the crystal to ensure optimum jitter performance.





Figure 4.4. Crystal Resonator Connections

Note: XA and XB must not exceed the maximum input voltage listed in Table 6.3 Input Clock Specifications on page 25.


4.6.2 External Reference (REF/REFb)

The external reference at the REF/REFb pins is used to determine output frequency accuracy and stability during free-run and holdover modes. This reference is usually from a TCXO or OCXO and can be connected differentially or single-ended as shown in the figure below. See the Si5348 Rev E Reference Manual and the Si534x/8x Recommended Crystal, TCXO and OCXOs Reference Manual for more information.

Differential Reference Connection



Single-Ended AC-Coupled Reference Connections



Use R1 and R2 if necessary to keep the signal at REF < 3.6 Vpp_se. See Reference Manual for details.

Figure 4.5. External Reference Connections

Note: REF and REFb must not exceed the maximum input voltage listed in Table 6.3 Input Clock Specifications on page 25.

4.7 Inputs (IN0, IN1, IN2, REF, IN3, IN4)

There are four inputs that can be used to synchronize DSPLLs A, C and six inputs for DSPLL D. The inputs accept both differential and single-ended clocks. A crosspoint between the inputs and the DSPLLs allows any of the inputs (IN0, IN1, IN2, REF) to be connected to DSPLLA, DSPLLC or DSPLLD as shown in the figure below. DSPLL D has two additional inputs (IN3 and IN4) that support the single-ended LVCMOS input format only. Refer to the Si5348 Rev E Reference Manual for details.




Figure 4.6. DSPLL Input Selection Crosspoint

4.7.1 Input Selection

Input selection for each of the DSPLLs can be made manually through register control or automatically using an internal state machine when fewer than five inputs are used.

4.7.2 Manual Input Selection

In manual mode the input selection is made by writing to a register. IN0-IN2 and REF is available to DSPLL A and C, IN0-IN4 and REF is available to DSPLL D. If there is no clock signal on the selected input, the DSPLL will automatically enter holdover mode.

4.7.3 Automatic Input Selection

When configured in this mode, the DSPLLs automatically select a valid input that has the highest configured priority. The priority scheme is independently configurable for each DSPLL and supports revertive or non-revertive selection. Refer to the Si5348 Rev E Reference Manual for details.

4.7.4 Input Configuration and Terminations

Each of the differential inputs IN0–IN2, and REF are compatible with standard LVDS, LVPECL, HCSL, CML, and single-ended LVCMOS formats, or as a low duty cycle pulsed CMOS format. The standard format inputs have a nominal 50% duty cycle, must be ac-coupled and use the "Standard" Input Buffer selection as these pins are internally dc-biased to approximately 0.83 V. The pulsed CMOS input format allows pulse-based inputs, such as frame-sync and other synchronization signals having a duty cycle much less than 50%. These pulsed CMOS signals are dc-coupled and use the "Pulsed CMOS" Input Buffer selection. In all cases, the inputs should be terminated near the device input pins as shown in the figure below. The resistor divider values given below will work with up to 1 MHz pulsed inputs. In general, following the "Standard AC Coupled Single Ended" arrangement shown below will give superior jitter performance. Inputs must not exceed the maximum input voltages listed in Table 6.3 Input Clock Specifications on page 25. See Section 5.2 of the Si5348 Rev E Reference Manual for input circuit recommendations.

4.7.5 Hitless Input Switching

Hitless switching is a feature that prevents a phase offset from propagating to the output when switching between two clock inputs that have a fixed phase relationship. A hitless switch can only occur when the two input frequencies are frequency locked, meaning that they have to be exactly at the same frequency, or at an integer frequency relationship to each other. When hitless switching is enabled, the DSPLL simply absorbs the phase difference between the two input clocks during an input switch. When disabled, the phase difference between the two input clocks during an input switch. When disabled, the phase difference between the two input switch. The hitless switching feature supports clock frequencies down to the minimum input frequency of 8 kHz. Hitless switching can be enabled on a per DSPLL basis.

4.7.6 Ramped Input Switching

The ramped input switching feature is enabled/disabled depending on both the Pfd frequency and difference in input frequencies (Zero-PPM vs non-zero PPM). The table below shows the selection criteria to enable ramped input switching. The same ramp rate settings are used for both holdover exit and clock switching. For more information on ramped exit from holdover, see 4.4.5 Holdover Mode and the Si5348 Rev E Reference Manual.

Table 4.4. Recommended Ramped Input Switching Settings for Internal Clock Switches

| Maximum Input Frequency Difference | Fpfd < 500 kHz | Fpfd ≥ 500 kHz | | |
|------------------------------------|--|---------------------------|--|--|
| 0 ppm Frequency Locked | Ramped Exit from Holdover | | | |
| ≤ 10 ppm | Ramped Input Switching and Ramped Exit from Holdover | Ramped Exit from Holdover | | |
| > 10 ppm | Ramped Input Switching and Ramped Exit from Holdover | | | |

4.7.7 Glitchless Input Switching

The DSPLLs have the ability of switching between two input clock frequencies that are up to ±500 ppm apart. The DSPLL will pull-in to the new frequency using the DSPLL Loop Bandwidth or using the Fastlock Loop Bandwidth if it is enabled. The loss of lock (LOL) indicator will assert while the DSPLL is pulling-in to the new clock frequency. There will be no output runt pulses generated at the output during the transition. All clock inputs, including IN3 and IN4, support glitchless input switching.

4.7.8 Typical Hitless Switching Scenarios




Figure 4.7. Output Frequency Transient-Ramped Switching between Two 8 kHz Inputs (±4.6 ppm Offset)




Figure 4.8. Output Phase Transient—Hitless Switching between Two 25 MHz Inputs (0 ppm, 180 Degree Phase Shift)

Si5348 Rev E Data Sheet • Functional Description

4.7.9 Synchronizing to Gapped Input Clocks

Each of the DSPLLs support locking to an input clock that has missing periods. This is also referred to as a gapped clock. The purpose of gapped clocking is to modulate the frequency of a periodic clock by selectively removing some of its cycles. Gapping a clock severely increases its jitter, so a phase-locked loop with high jitter tolerance and low loop bandwidth is required to produce a low-jitter periodic clock. The resulting output will be a periodic non-gapped clock with an average frequency of the input with its missing cycles. For example, an input clock of 100 MHz with one cycle removed every 10 cycles will result in a 90 MHz periodic non-gapped output clock. This is shown in the figure below:




Figure 4.9. Generating an Averaged Clock Output Frequency from a Gapped Clock Input

A valid gapped clock input must have a minimum frequency of 10 MHz with a maximum of two missing cycles out of every eight. Locking to a gapped clock will not trigger the LOS, OOF, and LOL fault monitors. Clock switching between gapped clocks may violate the hitless switching specification in Table 6.8 Performance Characteristics on page 32 when the switch occurs during a gap in either input clock.

Si5348 Rev E Data Sheet • Functional Description

4.8 Fault Monitoring

Three input clocks (IN0, IN1, IN2) and the reference input (REF/REFb) are monitored for loss-of-signal (LOS) and out-of-frequency (OOF) as shown in the figure below. The reference at the XA/XB pins is also monitored for LOS since it provides a critical reference clock for the DSPLLs. Each of the DSPLLs also has an LOL indicator, which is asserted when synchronization is lost with their selected input clock. IN3 and IN4 can be monitored, only for LOS, on DSPLL D.




Figure 4.10. Si5348 Fault Monitors

4.8.1 Input LOS Detection

The loss of signal monitor measures the period of each input clock cycle to detect phase irregularities or missing clock edges. Each of the input LOS circuits has its own programmable sensitivity which allows ignoring missing edges or intermittent errors. Loss of signal sensitivity is configurable using the ClockBuilder Pro software. Refer to the Si5348 Rev E Reference Manual for details.




Figure 4.11. LOS Status Indicators

4.8.2 XA/XB LOS Detection

A LOS monitor is available to ensure that the external crystal or reference clock is valid. By default the output clocks are disabled when XAXB_LOS is detected. This feature can be disabled such that the device will continue to produce output clocks when XAXB_LOS is detected.

4.8.3 OOF Detection

Input clocks IN0, IN1, IN2 are monitored for frequency accuracy with respect to an OOF reference, which it considers as its "0_ppm" reference. Since a TCXO or OCXO will be connected to the REF input, most applications will declare the REF input to be the OOF reference. The final OOF status is determined by the combination of both a precise OOF monitor and a fast OOF monitor as shown in the figure below. An option to disable either monitor is also available. The live OOF register always displays the current OOF state and its sticky register bit stays asserted until cleared.




Figure 4.12. OOF Status Indicator

4.8.4 Precision OOF Monitor

The precision OOF monitor circuit measures the frequency of all input clocks to within $\pm 1/16$ ppm accuracy with respect to the selected OOF frequency reference. A valid input clock frequency is one that remains within the OOF frequency range, which is register configurable up to ± 500 ppm in steps of 1/16 ppm. A configurable amount of hysteresis is also available to prevent the OOF status from toggling at the failure boundary. An example is shown in the figure below. In this case, the OOF monitor is configured with a valid frequency range of ± 6 ppm and with 2 ppm of hysteresis. An option to use one of the input pins (INO – IN2) as the 0 ppm OOF reference instead of the REF/REFb pins is available. This option is register-configurable. XA/XB can also be used as the 0 ppm reference.




Figure 4.13. Example of Precise OOF Monitor Assertion and De-assertion Triggers

4.8.5 Fast OOF Monitor

Because the precision OOF monitor needs to provide 1/16 ppm of frequency measurement accuracy, it must measure the monitored input clock frequencies over a relatively long period of time. This may be too slow to detect an input clock that is quickly ramping in frequency. An additional level of OOF monitoring called the Fast OOF monitor runs in parallel with the precision OOF monitors to quickly detect a ramping input frequency. The Fast OOF monitor asserts OOF on an input clock frequency that has changed by greater than ±4000 ppm.

4.8.6 LOL Detection

There is an LOL monitor for each of the DSPLLs. The LOL monitor asserts the LOL register bit when a DSPLL has lost synchronization with its selected input clock. There is also a dedicated loss of lock pin that reflects the loss of lock condition for each of the DSPLLs (LOL_Ab, LOL_Cb, LOL_Db) and also for the reference. There are two LOL frequency monitors, one that sets the LOL indicator (LOL Set) and another that clears the indicator (LOL Clear). An optional timer is available to delay clearing of the LOL indicator to allow additional time for the DSPLL to completely lock to the input clock. The timer is also useful to prevent the LOL indicator from toggling or chattering as the DSPLL completes lock acquisition. A block diagram of the LOL monitor is shown in the figure below. The live LOL register always displays the current LOL state and a sticky register always stays asserted until cleared. The LOLb pin reflects the current state of the LOL monitor.






Figure 4.14. LOL Status Indicators

Each of the LOL frequency monitors has adjustable sensitivity, which is register-configurable from 0.1 ppm to 10,000 ppm. Having two separate frequency monitors allows for hysteresis to help prevent chattering of LOL status. An example configuration where LOCK is indicated when there is less than 0.1 ppm frequency difference at the inputs of the phase detector and LOL is indicated when there is more than 1 ppm frequency difference is shown in Figure 4.15 LOL Set and Clear Thresholds on page 19.



Phase Detector Frequency Difference (ppm)



An optional timer is available to delay clearing of the LOL indicator to allow additional time for the DSPLL to completely lock to the input clock. The timer is also useful to prevent the LOL indicator from toggling or chattering as the DSPLL completes lock acquisition. The

Si5348 Rev E Data Sheet • Functional Description

configurable delay value depends on frequency configuration and loop bandwidth of the DSPLL and is automatically calculated using the ClockBuilder Pro software.

4.8.7 Interrupt Pin (INTRb)

An interrupt pin (INTRb) indicates a change in state with any of the status indicators for any of the DSPLLs. All status indicators are maskable to prevent assertion of the interrupt pin. The state of the INTRb pin is reset by clearing the sticky status registers.

4.9 Outputs

The Si5348 supports seven differential output drivers. Each driver has a configurable voltage amplitude and common mode voltage covering a wide variety of differential signal formats including LVPECL, LVDS, HCSL, and CML. In addition to supporting differential signals, any of the outputs can be configured as single-ended LVCMOS (3.3 V, 2.5 V, or 1.8 V) providing up to 14 single-ended outputs, or a combination of differential and single-ended outputs.

4.9.1 Output Crosspoint

A crosspoint allows any of the output drivers to connect with any of the DSPLLs as shown in the figure below. The crosspoint configuration is programmable and can be stored in NVM so that the desired output configuration is ready at power-up.

4.9.2 Support For 1 Hz Output

Output 6 of the Si5348 can be configured to generate a 1 Hz clock by cascading the R5 and R6 dividers. Output 5 is still usable in this case but is limited to a maximum frequency of 33.5 MHz. ClockBuilder Pro automatically determines the optimum configuration when generating a 1 Hz output (1 PPS).




Figure 4.16. Generating a 1 Hz Output using the Si5348

4.9.3 Output Terminations

The outputs of the Si5348 can be configured in a variety of formats including: LVDS, LVCMOS, LVPECL, CML, and HCSL. For output termination circuit configuration recommendations, see the Si5348 Rev E Reference Manual.

4.9.4 Output Signal Format

The differential output amplitude and common mode voltage are both programmable and compatible with a wide variety of signal formats, including LVDS and LVPECL. In addition to supporting differential signals, any of the outputs can be configured as LVCMOS (3.3 V, 2.5 V, or 1.8 V) drivers providing up to 14 single-ended outputs or a combination of differential and single-ended outputs.

4.9.5 Programmable Common Mode Voltage For Differential Outputs

The common mode voltage (V_{CM}) for the differential modes is programmable and depends on the voltage available at the output's VDDO pin. Setting the common mode voltage is useful when dc-coupling the output drivers.

4.9.6 LVCMOS Output Impedance Selection

Each LVCMOS driver has a configurable output impedance to accommodate different trace impedances and drive strengths. A source termination resistor is recommended to help match the selected output impedance to the trace impedance. There are three programmable output impedance selections for each VDDO options as shown in the table below. Note that selecting a lower source impedance may result in higher output power consumption.

| VDDO | CMOS_DRIVE_Selection | | | | |
|-------|----------------------|-----------------|-----------------|--|--|
| | OUTx_CMOS_DRV=1 | OUTx_CMOS_DRV=2 | OUTx_CMOS_DRV=3 | | |
| 3.3 V | 38 Ω | 30 Ω | 22 Ω | | |
| 2.5 V | 43 Ω | 35 Ω | 24 Ω | | |
| 1.8 V | _ | 46 Ω | 31 Ω | | |

Table 4.5. Typical Output Impedance (Z_S)

4.9.7 LVCMOS Output Signal Swing

The signal swing (V_{OL}/V_{OH}) of the LVCMOS output drivers is set by the voltage on the VDDO pins. Each output driver has its own VDDO pin allowing a unique output voltage swing for each of the LVCMOS drivers.

4.9.8 LVCMOS Output Polarity

When a driver is configured as an LVCMOS output, it generates a clock signal on both pins (OUTx and OUTxb). By default the clock on the OUTxb pin is generated with the same polarity (in phase) with the clock on the OUTx pin. The polarity of these clocks is configurable, which enables complementary clock generation and/or inverted polarity with respect to other output drivers.

4.9.9 Output Enable/Disable

The Si5348 allows enabling/disabling outputs by pin or register control, or a combination of both. Three output enable pins are available (OE0b, OE1b, OE2b). The output enable pins can be mapped to any of the outputs (OUTx) through register configuration. By default OE0b controls all of the outputs while OE1b and OE2b remain unmapped and has no effect until configured. The figure below shows an example of an output enable mapping scheme that is register configurable and can be stored in NVM as the default at power-up.

Enabling and disabling outputs can also be controlled by register control. This allows disabling one or more output when the OEb pin(s) has them enabled. By default the output enable register settings are configured to allow the OEb pins to have full control.

4.9.10 Output Disable During LOL

By default a DSPLL that is out of lock will generate either free-running clocks or generate clocks in holdover mode. There is an option to disable the outputs when a DSPLL is LOL. This option can be useful to force a downstream PLL into holdover.

4.9.11 Output Disable During XAXB_LOS

The internal oscillator circuit (OSC) in combination with the external crystal (XTAL) provides a critical function for the operation of the DSPLLs. In the event of a crystal failure the device will assert an XAXB_LOS alarm. By default all outputs will be disabled during assertion of the XAXB_LOS alarm. There is an option to leave the outputs enabled during an XAXB_LOS alarm, but the frequency accuracy and stability will be indeterminate during this fault condition.

4.9.12 Output Driver State When Disabled

The disabled state of an output driver is register configurable as disable low or high.

4.9.13 Synchronous/Asynchronous Output Disable

Outputs can be configured to disable synchronously or asynchronously. In synchronous disable mode the output will wait until a clock period has completed before the driver is disabled. This prevents unwanted runt pulses from occurring when disabling an output. In asynchronous disable mode, the output clock will disable immediately without waiting for the period to complete.

4.9.14 Output Divider (R) Synchronization

All the output R dividers are reset to a known state during the power-up initialization period. This ensures consistent and repeatable phase alignment across all output drivers. Resetting the device using the RSTb pin or asserting the hard reset bit will have the same result.

4.10 Power Management

Unused inputs, output drivers, and DSPLLs can be powered down when unused.

4.11 In-Circuit Programming

The Si5348 is fully configurable using the serial interface (I²C or SPI). At power-up the device downloads its default register values from internal non-volatile memory (NVM). Application specific default configurations can be written into NVM allowing the device to generate specific clock frequencies at power-up. Writing default values to NVM is in-circuit programmable with normal operating power supply voltages applied to its V_{DD} and V_{DDA} pins. The NVM is two time writable. Once a new configuration has been written to NVM, the old configuration is no longer accessible.

4.12 Serial Interface

Configuration and operation of the Si5348 is controlled by reading and writing registers using the I^2C or SPI interface. The I2C_SEL pin selects I^2C or SPI operation. Communication with both 3.3 V and 1.8 V host is supported. The SPI mode operates in either 4-wire or 3-wire mode.

4.13 Custom Factory Preprogrammed Parts

For applications where a serial interface is not available for programming the device, custom pre-programmed parts can be ordered with a specific configuration written into NVM. A factory pre-programmed part will generate clocks at power-up. Custom, factory-pre-programmed devices are available. Use the ClockBuilder Pro custom part number wizard to quickly and easily request and generate a custom part number for your configuration.

In less than three minutes, you will be able to generate a custom part number with a detailed data sheet addendum matching your design's configuration. Once you receive the confirmation email with the data sheet addendum, simply place an order with your local Skyworks sales representative. Samples of your pre-programmed device will typically ship in about two weeks.

Si5348 Rev E Data Sheet • Register Map

5. Register Map

Refer to the Si5348 Rev E Reference Manual for a complete list of register descriptions and settings.

6. Electrical Specifications

Table 6.1. Recommended Operating Conditions

| Parameter | Symbol | Min | Тур | Мах | Unit |
|------------------------------|-------------------|------|------|---|------|
| Ambient Temperature | T _A | -40 | 25 | 85 | °C |
| Junction Temperature | TJ _{MAX} | _ | _ | 125 | °C |
| Core Supply Voltage | V _{DD} | 1.71 | 1.80 | 1.89 | V |
| Core Supply Voltage | V _{DDA} | 3.14 | 3.30 | 125 1.89 3.47 3.47 2.62 1.89 3.47 | V |
| | | 3.14 | 3.30 | 3.47 | V |
| Output Driver Supply Voltage | V _{DDO} | 2.37 | 2.50 | 2.62 | V |
| | | 1.71 | 1.80 | 1.89 | V |
| Status Pin Supply Voltage | V _{DDS} | 3.14 | 3.30 | 3.47 | V |
| | suu vuus | 1.71 | 1.80 | 1.89 | V |
| Note: | | | | | |

1. All minimum and maximum specifications are guaranteed and apply across the recommended operating conditions. Typical values apply at nominal supply voltages and an operating temperature of 25 °C unless otherwise noted.

| Parameter | Symbol | Test Condition | Min | Тур | Мах | Unit |
|---|-------------------|----------------------------------|-----|---------|-------|------------|
| | I _{DD} | | _ | 250 | 460 | mA |
| Core Supply Current ¹ | I _{DDA} | | _ | 125 | 145 | mA |
| | | LVPECL Output ² | | 22 | 26 | m (|
| | | @ 156.25 MHz | _ | 22 | 26 | mA |
| | | LVDS Output ² | | 15 | 18 | mA |
| | | @ 156.25 MHz | _ | | | IIIA |
| | | 3.3 V LVCMOS ³ output | | — 22 30 | 22 30 | 0 |
| Output Buffer Supply Current | I _{DDOx} | @ 156.25 MHz | _ | | | 22 30 1114 |
| | | 2.5 V LVCMOS ³ output | _ | 18 | | |
| | | @ 156.25 MHz | | | 23 | mA |
| | | 1.8 V LVCMOS ³ output | | 10 | 16 | |
| | | @ 156.25 MHz | _ | 12 | | mA |
| Total Power Dissipation ^{1, 4} | Pd | Si5348 | _ | 1250 | 1650 | mW |

Table 6.2. DC Characteristics

Note:

- 1. Si5348 test configuration: 7 x 2.5 V LVDS outputs enabled @156.25 MHz. Excludes power in termination resistors.
- 2. Differential outputs terminated into an ac-coupled 100 Ω split termination load. See the Si5348 Rev E Reference Manual for additional information.
- 3. LVCMOS outputs measured into a 5-inch 50 Ω PCB trace with 4.7 pF load. The LVCMOS outputs were set to OUTx_CMOS_DRV = 3, which is the strongest driver setting. Refer to the Si5348 Rev E Reference Manual for more details on register settings.
- 4. Detailed power consumption for any configuration can be estimated using the ClockBuilder Pro software when an evaluation board (EVB) is not available. All EVBs support detailed current measurements for any configuration.

LVCMOS Output Test Configuration




Table 6.3. Input Clock Specifications

| Parameter | Symbol | Test Condition | Min | Тур | Max | Unit |
|----------------------------------|---------------|------------------------------|-----------|-----|-----|------|
| Standard Differential or Single- | Ended AC-Coup | bled Input Buffer (IN0, IN1, | IN2, REF) | | | |

Si5348 Rev E Data Sheet • Electrical Specifications


| Parameter | Symbol | Test Condition | Min | Тур | Max | Unit |
|---------------------------------|------------------------------|-------------------------------------|--------------------------------------|-----|--------------------------------------|---------|
| | | Differential | 0.008 | _ | 750 | |
| Input Frequency Range | f _{IN} | Single-ended/LVCMOS | 0.008 | — | 250 | MHz |
| | | REF | 5 | _ | 250 | |
| | | Differential AC-coupled | 100 | | 1800 | mVpp_se |
| | | f _{IN} < 250 MHz | 100 | — | 1000 | |
| Vallana Quina 1 | Vec | Differential AC-coupled | 225 | | 1900 | m)/nn |
| Voltage Swing ¹ | V _{IN} | 250 MHz < f _{IN} < 750 MHz | 225 | — | 1800 | mVpp_se |
| | | Single-ended AC-coupled | 100 | | 2000 | |
| | | f _{IN} < 250 MHz | 100 | — | 3600 | mVpp_se |
| Slew Rate ^{2,3} | SR | | 400 | _ | _ | V/µs |
| Duty Cycle | DC | | 40 | | 60 | % |
| Input Capacitance | C _{IN} | Single input pin | _ | 2.4 | _ | pF |
| Input Resistance Differential | R _{IN-Diff} | | _ | 16 | _ | kΩ |
| Input Resistance Single-ended | R _{IN_SE} | | _ | 8 | _ | kΩ |
| LVCMOS / Pulsed CMOS DC-Co | oupled Input But | ffer (IN0, IN1, IN2) ⁴ | 11 | | -11 | |
| | f _{IN_LVCMOS} | | 0.008 | _ | 250 | MHz |
| Input Frequency | f _{IN_PULSED_CM} OS | | 0.008 | _ | 1 | MHz |
| Input Voltage (see Si5348 Rev | V _{IL} | CMOS_HI_THR = 0 | -0.2 | _ | 0.4 | V |
| E Reference Manual for details) | V _{IH} | | 0.8 | | _ | V |
| | V _{IL} | CMOS_HI_THR = 1 | -0.2 | — | 0.8 | V |
| | V _{IH} | | 1 | _ | _ | V |
| Slew Rate ^{2,3} | SR | | 400 | _ | _ | V/µs |
| Minimum Pulse Width | PW | For Pulsed Input only | 1.6 | _ | _ | ns |
| Input Resistance | R _{IN} | | _ | 8 | _ | kΩ |
| LVCMOS DC-Coupled Input Bu | ffer (IN3, IN4) | | 11 | | | |
| Input Frequency | f _{IN_LVCMOS} | | 0.008 | | 2.048 | MHz |
| | VIL | | _ | | 0.3 x V _{DDIO} ⁵ | V |
| Input Voltage | V _{IH} | | 0.7 x V _{DDIO} ⁵ | _ | _ | V |
| Minimum Pulse Width | PW | Pulse Input | 50 | | _ | ns |
| Input Resistance | R _{IN} | | _ | 20 | _ | kΩ |

| XA/XB (Crystal Re | ecommended) |
|-------------------|-------------|
|-------------------|-------------|

| XA/XB Frequency | f _{IN_REF} | Full operating range. Jit- ter performance may be reduced. | 24.97 | _ | 54.06 | MHz |
|-------------------------------------|----------------------|--|-------|----|-------|-----------|
| | | Range for best jitter. | 48 | _ | 54 | MHz |
| | | TCXO frequency for SyncE applications. Jitter performance may be re- duced. | _ | 40 | _ | MHz |
| Input Single-ended Voltage Swing | V _{IN_SE} | | 365 | _ | 2000 | mVpp_se |
| Input Differential Voltage Swing | V _{IN_DIFF} | | 365 | | 2500 | mVpp_diff |
| Slew Rate ^{2, 3} | SR | | 400 | _ | _ | V/µs |
| Input Duty Cycle | DC | | 40 | _ | 60 | % |

Note:

1. Voltage swing is specified as single-ended mVpp.



2. Recommended for specified jitter performance. Jitter performance could degrade if the minimum slew rate specification is not met (see the Si5348 Rev E Reference Manual).

3. Rise and fall times can be estimated using the following simplified equation: $tr/tf_{80-20} = ((0.8 - 0.2) \times V_{IN_Vpp_se}) / SR$.

4. Pulsed CMOS mode is intended primarily for single-ended LVCMOS input clocks < 1 MHz that must be dc-coupled because they have a duty cycle significantly less than 50%. A typical application example is a low-frequency video frame sync pulse.

5. VDDIO is determined by the IO_VDD_SEL bit to be either VDDA or VDD.

| Parameter | Symbol | Test Condition | Min | Тур | Мах | Unit |
|------------------------------|-------------------|-----------------------|---|------------|---|------|
| Si5348 Control Input Pins (I | 2C_SEL, A0/CSb, A | 1/SDO, SDA/SDIO, SCLM | (, RSTb, OE0b, (| DE1b, OE2b | , FINC) | |
| In muth Violte an | V _{IL} | | _ | _ | 0.3 × V _{DDIO} ¹ | V |
| Input Voltage | V _{IH} | | 0.7 × V _{DDIO} ¹ | _ | - | V |
| Input Capacitance | C _{IN} | | _ | 1.5 | _ | pF |
| Input Resistance | RL | | _ | 20 | _ | kΩ |
| Minimum Pulse Width | PW | RSTb, FINC | 100 | _ | _ | ns |
| Update Rate | F _{UR} | FINC | _ | _ | 1 | MHz |
| Si5348 Control Input Pin (F | DEC) | | | | | |
| | V _{IL} | | _ | _ | 0.3 × V _{DDS} | V |
| Input Voltage | V _{IH} | | 0.7 × V _{DDS} | _ | _ | V |
| Input Capacitance | C _{IN} | | _ | 1.5 | _ | pF |
| Minimum Pulse Width | PW | FDEC | 100 | _ | _ | ns |
| Update Rate | F _{UR} | FDEC | _ | _ | 1 | MHz |

Table 6.4. Control Input Pin Specifications

Table 6.5. Differential Clock Output Specifications

| Parameter | Symbol | Test Con | dition | Min | Тур | Мах | Unit |
|--|---------------------|---|--------|-----|-----|-------|-----------|
| | f _{OUT} | | | | | 718.5 | MHz |
| Output Frequency | fout1Hz | 1 PPS signal only available on Output 6 | | | 1 | | Hz |
| | | f _{OUT} < 40 | 0 MHz | 48 | | 52 | % |
| Duty Cycle | DC | 400 MHz < f _{OUT} < 718.5 MHz | | 45 | _ | 55 | % |
| Output-Output Skew Using Same DSPLL | T _{SKS} | Output clocks at 370 MHz in LVDS differential format connected to the same DSPLL. | | _ | _ | 75 | ps |
| OUT-OUTb Skew | T _{SK_OUT} | Measured from to negative o | | _ | 0 | 50 | ps |
| Output Voltage Amplitude ¹ | | V _{DDO} = 3.3 V, 2.5 V, or 1.8 V | LVDS | 350 | 430 | 510 | m)(nn ee |
| | V _{OUT} | V _{DDO} = 3.3 V, or 2.5 V | LVPECL | 640 | 750 | 900 | - mVpp_se |

Si5348 Rev E Data Sheet • Electrical Specifications

| Parameter | Symbol | Test Cor | dition | Min | Тур | Max | Unit |
|---|--------------------------------|--------------------------|--------------------------|------|------|------|------|
| | V _{CM} | V _{DDO} = 3.3 V | LVDS | 1.10 | 1.20 | 1.30 | N |
| | | | LVPECL | 1.90 | 2.00 | 2.10 | V |
| Common Mode Voltage ¹ | | V _{DDO} = 2.5 V | LVPECL, LVDS | 1.10 | 1.20 | 1.30 | V |
| | | V _{DDO} = 1.8 V | sub-LVDS | 0.80 | 0.90 | 1.00 | V |
| Rise and Fall Times | t _R /t _F | | | _ | 100 | 150 | ps |
| (20% to 80%) | ιR/ιF | | | | | | - |
| Differential Output Impedance | ZO | | | _ | 100 | _ | Ω |
| | | 10 kHz sinusoidal noise | | — | -101 | _ | dBc |
| | | 100 kHz sinus | oidal noise | _ | -96 | | dBc |
| Power Supply Noise Rejection ² | PSRR | 500 kHz sinus | 500 kHz sinusoidal noise | | -99 | _ | dBc |
| | | 1 MHz sinusoidal noise | | _ | -97 | _ | dBc |
| Output-output Crosstalk ³ | XTALK | | | _ | -72 | | dBc |

Note:

1. Output amplitude and common mode settings are programmable through register settings and can be stored in NVM. Each output driver can be programmed independently. Note that the maximum LVDS single-ended amplitude can be up to 110 mV higher than the TIA/EIA-644 maximum. Refer to the Si5348 Rev E Reference Manual for recommended settings. Not all combinations of voltage amplitude and common mode voltages settings are possible.

2. Measured for 156.25 MHz carrier frequency. 100 mVpp of sinewave noise added to VDDO running at 3.3 V and noise spur amplitude measured.

3. Measured across two adjacent outputs, both in LVDS mode, with the victim running at 155.52 MHz and the aggressor at 156.25 MHz. Refer to application note, AN862: Optimizing Si534x Jitter Performance in Next Generation Internet Infrastructure Systems, guidance on crosstalk minimization. Note that all active outputs must be terminated when measuring crosstalk.



Table 6.6. LVCMOS Clock Output Specifications

| Parameter | Symbol | Test Conditi | ion | Min | Тур | Мах | Unit | | |
|---|---------------------|------------------------------|--------------------------|-------------------------|-----|---------------------------|------|--|--|
| | f _{OUT} | | | 0.0001 | _ | 250 | MHz | | |
| Output Frequency | f _{OUT1Hz} | Only Available on | Output 6 | | 1 | | Hz | | |
| | DC | f _{OUT} <100 M | Hz | 48 | _ | 52 | 0/ | | |
| Duty Cycle | DC | 100 MHz < f _{OUT} < | 250 MHz | 45 | _ | 55 | % | | |
| | | V _{DDO} = 3.3 V | | | | | | | |
| | | OUTx_CMOS_DRV=1 | I _{OH =} –10 mA | | _ | _ | | | |
| | | OUTx_CMOS_DRV=2 | I _{OH =} –12 mA | V _{DDO} × 0.85 | _ | _ | V | | |
| | | OUTx_CMOS_DRV=3 | I _{OH =} –17 mA | | _ | _ | | | |
| | | V _{DDO} = 2.5 V | | | | | | | |
| Output Voltage High ^{1 , 2, 3} | V _{OH} | OUTx_CMOS_DRV=1 | I _{OH =} –6 mA | | _ | _ | V | | |
| | | OUTx_CMOS_DRV=2 | I _{OH =} –8 mA | V _{DDO} × 0.85 | _ | _ | | | |
| | | OUTx_CMOS_DRV=3 | I _{OH =} –11 mA | | _ | _ | | | |
| | | | V | _{DDO} = 1.8 V | | | | | |
| | | OUTx_CMOS_DRV=2 | I _{OH =} –4 mA | V × 0.05 | _ | _ | | | |
| | | OUTx_CMOS_DRV=3 | I _{OH =} –5 mA | V _{DDO} × 0.85 | _ | _ | V | | |
| | | V _{DDO} = 3.3 V | | | | | | | |
| | | OUTx_CMOS_DRV=1 | I _{OL} = 10 mA | — | _ | V _{DDO} × 0.15 | V | | |
| | | OUTx_CMOS_DRV=2 | I _{OL} = 12 mA | — | _ | | | | |
| | | OUTx_CMOS_DRV=3 | I _{OL} = 17 mA | — | | | | | |
| | | | V | _{DDO} = 2.5 V | | | | | |
| Output Voltage Low ^{1 , 2, 3} | V _{OL} | OUTx_CMOS_DRV=1 | I _{OL} = 6 mA | _ | _ | | | | |
| | | OUTx_CMOS_DRV=2 | I _{OL} = 8 mA | _ | _ | V _{DDO} × 0.15 | V | | |
| | | OUTx_CMOS_DRV=3 | I _{OL} = 11 mA | _ | _ | | | | |
| | | | V | _{DDO} = 1.8 V | | | | | |
| | | OUTx_CMOS_DRV=2 | I _{OL} = 4 mA | _ | _ | | | | |
| | | OUTx_CMOS_DRV=3 | I _{OL} = 5 mA | _ | _ | - V _{DDO} × 0.15 | V | | |
| LVCMOS Rise and Fall | | V _{DDO} = 3.3 | V | — | 400 | 600 | ps | | |
| Times ³ | tr/tf | V _{DDO} = 2.5 | V | _ | 450 | 600 | ps | | |
| (20% to 80%) | | V _{DDO} = 1.8 | V | _ | 550 | 750 | ps | | |

Si5348 Rev E Data Sheet • Electrical Specifications




Table 6.7. Output Status Pin Specifications

| Parameter | Symbol | Test Condition Min | | Тур | Мах | Unit | | |
|--|-----------------|-------------------------|---------------------------------------|-----|--|------|--|--|
| Si5348 Status Output Pins (LOL_Cb, LOL_Db, INTRb, LOS1b, LOS2b, SDA/SDIO ² , A1/SDO) | | | | | | | | |
| Output Voltage | V _{OH} | I _{OH} = -2 mA | V _{DDIO} ¹ × 0.85 | _ | _ | V | | |
| | V _{OL} | I _{OL} = 2 mA | _ | _ | V _{DDIO} ¹ × 0.15 | V | | |
| Si5348 Status Output Pins (LO | L_Ab, LOS0b) | | | | | | | |
| Output Voltage | V _{OH} | I _{OH} = –2 mA | V _{DDS} × 0.85 | — | — | V | | |
| Output Voltage | V _{OL} | I _{OL} = 2 mA | _ | | V _{DDS} × 0.15 | V | | |
| Note: | | | | | | | | |

Note:

1. V_{DDIO} is determined by the IO_VDD_SEL bit. It is selectable as V_{DDA} or V_{DD}. Users normally select this option in the ClockBuilder Pro GUI. Alternatively, refer to the Si5348 Rev E Reference Manual for more details on register settings.

2. The V_{OH} specification does not apply to the open-drain SDA/SDIO output when the serial interface is in I²C mode or is unused with I2C_SEL pulled high. V_{OL} remains valid in all cases.

| Table 6.8. I | Performance | Characteristics |
|--------------|-------------|-----------------|
|--------------|-------------|-----------------|

| Parameter | Symbol | Test Condition | Min | Тур | Мах | Unit |
|--|---------------------|---|-------|-------|------|----------|
| PLL Loop Bandwidth Program- ming Range ¹ | f _{BW} | | 0.001 | _ | 4000 | Hz |
| Initial Start-Up Time | tstart | Time from power-up to when the device gener- ates free-running clocks | _ | 30 | 45 | ms |
| PLL Lock Time ² | t _{ACQ} | With Fastlock enabled | _ | 280 | 300 | ms |
| POR to Serial Interface Ready ³ | t _{RDY} | | _ | _ | 15 | ms |
| Jitter Peaking | J _{РК} | Measured with a frequen- cy plan running a 25 MHz input, 25 MHz output, and a loop bandwidth of 4 Hz | _ | _ | 0.1 | dB |
| Jitter Tolerance ⁴ | J _{TOL} | Compliant with G.8262 Options 1&2 Carrier Frequency = 10.3125 GHz (10 Gbe) Jitter Modulation Frequen- cy = 10 Hz | _ | >5000 | _ | UI pk-pk |
| | | Single automatic switch between two 8 kHz inputs, DSPLL BW = 400 Hz | _ | 0.5 | 1.2 | ns |
| Maximum Phase Transient Dur- | t | Single automatic switch between two 2 MHz in- puts, DSPLL BW = 400 Hz | _ | 0.2 | 0.3 | ns |
| ing a Hitless Switch ⁵ | ^t switch | Single manual switch be- tween two 8 kHz inputs, DSPLL BW = 400 Hz | _ | 0.5 | 1.0 | ns |
| | | Single manual switch be- tween two 2 MHz inputs, DSPLL BW = 400 Hz | _ | 0.2 | 0.25 | ns |
| Pull-in Range | ω _P | | _ | 500 | _ | ppm |
| RMS Phase Jitter ⁶ | J _{GEN} | 12 kHz to 20 MHz | _ | 95 | 125 | fs rms |

Note:

1. Actual loop bandwidth might be lower; refer to CBPro for actual value on your frequency plan.

- 2. Lock Time can vary significantly depending on several parameters, such as bandwidths, LOL thresholds, etc. For this case, lock time was measured with fastlock bandwidth set to 100 Hz, LOL set/clear thresholds of 6/0.6 ppm respectively, using INO as clock reference by removing the reference and enabling it again, then measuring the delta time between the first rising edge of the clock reference and the LOL indicator de-assertion.
- 3. Measured as time from valid VDD/VDDA rails (90% of their value) to when the serial interface is ready to respond to commands.
- 4. For details on this test, see the jitter tolerance test results in the Si5348 Rev. E ITU-T G.8262 Compliance Report.
- 5. Maximum Phase Transient during Hitless Switch will degrade with lower Fpfd. Fpfd frequencies greater than 500 kHz will result in lower phase transients. Consult your CBPro Design report for the Fpfd frequency of your configuration. Measurements taken with cover placed over crystal to reduce wander. See the Si5348 Rev E Reference Manual for further details.
- 6. Jitter generation test conditions: f_{IN} = 19.44 MHz, f_{OUT} = 156.25 MHz LVPECL.

| | | | | Standard Mode | | Fast Mode | |
|--|---------------------|----------------|-----|---------------|-----|-----------|------|
| Parameter | Symbol | Test Condition | 100 | kbps | 400 | kbps | Unit |
| | | | Min | Max | Min | Max | |
| SCL Clock Frequency | f _{SCL} | | _ | 100 | — | 400 | kHz |
| SMBus Timeout | _ | | 25 | 35 | 25 | 35 | ms |
| Hold time (repeated) START condition | t _{HD:STA} | | 4.0 | _ | 0.6 | _ | μs |
| Low period of the SCL clock | t _{LOW} | | 4.7 | _ | 1.3 | _ | μs |
| HIGH period of the SCL clock | t _{ніGH} | | 4.0 | _ | 0.6 | _ | μs |
| Set-up time for a repeated START condition | t _{SU:STA} | | 4.7 | _ | 0.6 | _ | μs |
| Data hold time | t _{HD:DAT} | | 100 | | 100 | _ | ns |
| Data set-up time | t _{SU:DAT} | | 250 | _ | 100 | _ | ns |
| Rise time of both SDA and SCL signals | t _r | | _ | 1000 | 20 | 300 | ns |
| Fall time of both SDA and SCL signals | t _f | | _ | 300 | _ | 300 | ns |
| Set-up time for STOP condi- tion | t _{SU:STO} | | 4.0 | _ | 0.6 | _ | μs |
| Bus free time between a STOP and START condition | t _{BUF} | | 4.7 | _ | 1.3 | _ | μs |
| Data valid time | t _{VD:DAT} | | _ | 3.45 | | 0.9 | μs |
| Data valid acknowledge time | t _{VD:ACK} | | _ | 3.45 | | 0.9 | μs |

Table 6.9. I²C Timing Specifications (SCL,SDA)




Figure 6.1. I²C Serial Port Timing Standard and Fast Modes

| Table 6.10. | SPI Timing | Specifications | (4-Wire) |
|-------------|------------|----------------|----------|
|-------------|------------|----------------|----------|

| Parameter | Symbol | Min | Тур | Мах | Unit |
|--|------------------|-----|-----|-----|----------------|
| SCLK Frequency | f _{SPI} | _ | _ | 20 | MHz |
| SCLK Duty Cycle | T _{DC} | 40 | _ | 60 | % |
| SCLK Period | T _C | 50 | _ | | ns |
| Delay Time, SCLK Fall to SDIO Turn-on | T _{D1} | _ | _ | 18 | ns |
| Delay Time, SCLK Fall to SDIO Next-bit | T _{D2} | _ | _ | 15 | ns |
| Delay Time, CSb Rise to SDIO Tri-State | T _{D3} | _ | _ | 15 | ns |
| Setup Time, CSb to SCLK | T _{SU1} | 5 | _ | _ | ns |
| Hold Time, SCLK fall to CSb | T _{H1} | 5 | _ | _ | ns |
| Setup Time, SDI to SCLK Rise | T _{SU2} | 5 | _ | _ | ns |
| Hold Time, SDI to SCLK Rise | T _{H2} | 5 | _ | _ | ns |
| Delay Time Between Chip Selects (CSb) | T _{CS} | 2 | _ | _ | T _C |




Figure 6.2. 4-Wire SPI Serial Interface Timing

| Table 6.11. SPI | Timing Specifications | (3-Wire) |
|-----------------|------------------------------|----------|
|-----------------|------------------------------|----------|

| Parameter | Symbol | Min | Тур | Мах | Units |
|--|------------------|-----|-----|-----|----------------|
| SCLK Frequency | f _{SPI} | _ | _ | 20 | MHz |
| SCLK Duty Cycle | T _{DC} | 40 | _ | 60 | % |
| SCLK Period | T _C | 50 | _ | _ | ns |
| Delay Time, SCLK Fall to SDIO Turn-on | T _{D1} | _ | _ | 20 | ns |
| Delay Time, SCLK Fall to SDIO Next-bit | T _{D2} | _ | _ | 15 | ns |
| Delay Time, CSb Rise to SDIO Tri-State | T _{D3} | _ | _ | 15 | ns |
| Setup Time, CSb to SCLK | T _{SU1} | 5 | _ | _ | ns |
| Hold Time, SCLK Fall to CSb | T _{H1} | 5 | _ | _ | ns |
| Setup Time, SDI to SCLK Rise | T _{SU2} | 5 | _ | _ | ns |
| Hold Time, SDI to SCLK Rise | T _{H2} | 5 | _ | _ | ns |
| Delay Time Between Chip Selects (CSb) | T _{CS} | 2 | | _ | T _C |




Figure 6.3. 3-Wire SPI Serial Interface Timing

Table 6.12. Crystal Specifications¹

| Parameter | Symbol | Test Condition | Min | Тур | Max | Unit |
|------------------------------|-------------------|---|-----|-----|-------|------|
| Crystal Frequency Range | f _{XTAL} | | 48 | _ | 54 | MHz |
| Load Capacitance | CL | | _ | 8 | _ | pF |
| Crystal Drive Level | dL | | _ | _ | 200 | μW |
| Equivalent Series Resistance | r _{ESR} | Refer to the Si5348 Rev E Reference Manual to determine ESR and shunt capacitance requirements. | | | shunt | |
| Shunt Capacitance | Co | | | | | |
| Noto | | | | | | |

Note:

1. Refer to the Si534x/8x Recommended Crystal, TCXO and OCXOs Reference Manual for recommended 48 to 54 MHz crystals. The Si5348 is designed to work only with crystals that meet these specifications, and not with XOs.

Table 6.13. Thermal Characteristics

| Parameter | Symbol | Test Condition ¹ | Value | Unit |
|---------------------------------------|----------------------------|--------------------------------|-----------|------|
| Si5348-64QFN | | | | |
| The survey Decision and | | Still Air | 22 | |
| Thermal Resistance | θ _{JA} | Air Flow 1 m/s | 19.4 | - |
| Junction to Ambient | | Air Flow 2 m/s | 18.3 | - |
| Thermal Resistance | 0 | | | - |
| Junction to Case | θ _{JC} | | 9.5 | °C/W |
| Thermal Resistance | θ _{JB} | | 9.4 | - |
| Junction to Board | Ψ _{JB} | | 9.3 | - |
| Thermal Resistance | | | 0.0 | |
| Junction to Top Center | Ψ_{JT} | | 0.2 | |
| Note: | | , | 1 | |
| 1. Based on PCB Dimension: 3" x 4.5", | PCB Thickness: 1.6 mm, PCI | 3 Land/Via: 36, Number of Cu L | ayers: 4. | |

Table 6.14. Absolute Maximum Ratings^{1, 2, 3, 4}

| Parameter | Symbol | Test Condition | Value | Unit |
|--|-------------------|---|-----------------------------------|-----------|
| Storage Temperature Range | T _{STG} | | –55 to 150 | °C |
| | V _{DD} | | -0.5 to 3.8 | V |
| | V _{DDA} | | -0.5 to 3.8 | V |
| DC Supply Voltage | V _{DDO} | | -0.5 to 3.8 | V |
| | V _{DDS} | | -0.5 to 3.8 | V |
| | V _{I1} 5 | IN0 - IN4, REF | -1.0 to V _{DDA} + 0.3 | V |
| | | RSTb, OE0b, OE1b, OE2b, | | |
| Input Voltage Range | V _{I2} | I2C_SEL,FINC, FDEC, A1/ SDO, SDA/SDIO, SCLK, A0/ CSb, | –0.5 to V _{DDA} + 0.3 | V |
| | V _{I3} | XA/XB | -0.5 to 2.7 | V |
| Latch-up Tolerance | LU | | JESD78 (| Compliant |
| ESD Tolerance | НВМ | 100 pF, 1.5 kΩ | 2.0 | kV |
| Max Junction Temperature in Operation | T _{JCT} | | 125 | °C |
| Soldering Temperature (Pb-free profile) ³ | T _{PEAK} | | 260 | °C |
| Soldering Temperature Time at T _{PEAK} (Pb- free profile) ⁴ | T _P | | 20-40 | S |

Note:

1. Permanent device damage may occur if the absolute maximum ratings are exceeded. Functional operation should be restricted to the conditions as specified in the operational sections of this data sheet. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

2.64-QFN package is RoHS-6 compliant.


3. For detailed MSL and packaging information, go to https://www.skyworksinc.com/quality.

4. The device is compliant with JEDEC J-STD-020.

5. The minimum voltage at these pins can be as low as –1.0 V when an ac input signal of 8 kHz or greater is applied. See Table 6.3 Input Clock Specifications on page 25 spec for Single-Ended AC-Coupled f_{IN} < 250 MHz.

Si5348 Rev E Data Sheet • Typical Application Schematic

7. Typical Application Schematic



Telecom Boundary Clock (T-BC)

Figure 7.1. Using the Si5348 as a Telecom Boundary Clock

Si5348 Rev E Data Sheet • Detailed Block Diagram

8. Detailed Block Diagram




Figure 8.1. Si5348-E Detailed Block Diagram

9. Typical Operating Characteristics (Jitter and Phase Noise)




Figure 9.1. Input = 25 MHz; Output = 156.25 MHz, 2.5 V LVDS with Rakon 12.8 MHz Reference

10. Pin Descriptions




Figure 10.1. Si5348 Pin Descriptions

| Table 10.1. | Si5348 P | in Descriptions ¹ |
|-------------|----------|------------------------------|
|-------------|----------|------------------------------|

| Pin Name ¹ | Pin Number | Pin Type ² | Function | |
|-----------------------|------------|-----------------------|--|--|
| Inputs | | | | |
| ХА | 8 | 1 | Crystal Input. Input pin for external crystal (XTAL). | |
| ХВ | 9 | | | |
| X1 | 7 | I | XTAL Shield. Connect these pins directly to the XTAL ground pins. The | |
| X2 | 10 | I | XTAL ground pins should be separated from the PCB ground plane. Reference to the Si5348 Rev E Reference Manual for layout guidelines. | |
| IN0 | 63 | l | Clock Inputs. IN0-IN2 accept an input clock for synchronizing the device | |
| IN0b | 64 | I | They support both differential and single-ended clock signals. Refer to Input Configuration and Terminations for information on input terminatior | |
| IN1 | 1 | I | options. These pins are high-impedance and must be terminated exter- nally. The negative side of the differential input must be grounded throug | |
| IN1b | 2 | I | a capacitor when accepting a single-ended clock. IN3 and IN4 only sup- | |
| IN2 | 14 | I | port single-ended LVCMOS signals. These pins are high-impedance and must be terminated externally. Unused inputs can be disabled by register | |
| IN2b | 15 | I | configuration and the pins left unconnected. | |
| IN3 | 4 | I | | |
| IN4 | 5 | I | | |
| REF | 61 | I | Reference Input. This input accepts a reference clock from a stable | |
| REFb | 62 | I | source (eg. TCXO or OCXO) that is used to determine free-run freque accuracy and stability during free-run or holdover of the DSPLL or DC These inputs can accept differential or single-ended connections. Rei to the Si534x/8x Recommended Crystal, TCXO, and OCXOs Referen Manual for information on recommended TCXOs and OCXOs. | |
| Outputs | | | | |
| OUT0 | 31 | 0 | Output Clocks. These output clocks support a programmable signal arr | |
| OUT0b | 30 | 0 | plitude and common mode voltage. Desired output signal format is confi urable using register control. Termination recommendations are provided | |
| OUT1 | 35 | 0 | in 4.9 Outputs. Unused outputs should be left unconnected. | |
| OUT1b | 34 | 0 | | |
| OUT2 | 38 | 0 | | |
| OUT2b | 37 | 0 | | |
| OUT3 | 45 | 0 | | |
| OUT3b | 44 | 0 | | |
| OUT4 | 51 | 0 | | |
| OUT4b | 50 | 0 | | |
| OUT5 | 54 | 0 | | |
| OUT5b | 53 | 0 | | |
| OUT6 | 59 | 0 | | |
| OUT6b | 58 | 0 | | |

| Pin Name ¹ | Pin Number | Pin Type ² | Function |
|-----------------------|------------|-----------------------|--|
| I2C_SEL | 39 | I | I ² C Select ³ . This pin selects the serial interface mode as I ² C (I2C_SEL = 1) or SPI (I2C_SEL = 0). This pin is internally pulled up to the voltage selected by the IO_VDD_SEL register bit. This pin is 3.3 V tolerant. |
| SDA/SDIO | 18 | I/O | Serial Data Interface ³ . This is the bidirectional data pin (SDA) for the I ² C mode, or the bidirectional data pin (SDIO) in the 3-wire SPI mode, or the input data pin (SDI) in 4-wire SPI mode. When not in SPI mode, this pin must be pulled-up using an external resistor of at least 1 k Ω . No pull-up resistor is needed when in SPI mode unless the master SPI driver is open drain. This pin is 3.3 V tolerant. |
| A1/SDO | 17 | I/O | Address Select 1/Serial Data Output ³ . In I ² C mode this pin functions as the A1 address input pin and does not have an internal pull up or pull down resistor. In 4-wire SPI mode, this is the serial data output (SDO) pin. and drives high to the voltage selected by the IO_VDD_SEL pin. This pin is 3.3 V tolerant. This pin must be pulled up externally when unused. |
| SCLK | 16 | Ι | Serial Clock Input³ . This pin functions as the serial clock input for both I ² C and SPI modes. This pin does not have an internal pull-up or pull-down. When in I ² C mode or unused, this pin must be pulled-up using an external resistor of at least 1 k Ω . No pull-up resistor is needed when in SPI mode unless the SPI master driver is open drain. This pin is 3.3 V tolerant. |
| A0/CSb | 19 | I | Address Select 0/Chip Select ³ . This pin functions as the hardware controlled address A0 input pin in I ² C mode. In SPI mode, this pin functions as the chip select input (active low). This pin is internally pulled-up by a 20 k Ω resistor to the voltage selected by the IO_VDD_SEL register bit. This pin is 3.3 V tolerant. |
| Control/Status | | | |
| INTRb | 12 | 0 | Interrupt³ . This pin is asserted low when a change in device status has occurred. It should be left unconnected when not in use. |
| RSTb | 6 | I | Device Reset ³ . Active low input that performs power-on reset (POR) of the device. Resets all internal logic to a known state and forces the device registers to their default values. Clock outputs are disabled during reset. This pin is internally pulled-up. |
| OE0b | 11 | I | Output Enable 0-2 ³ . These output enable pins have a programmable |
| OE1b | 26 | I | register mask which allows them to control any of the output clocks. By default the OE0b pin enables all output clocks and OE1b, OE2b have no |
| OE2b | 27 | I | control over the output clocks until register configured. These pins are internally pulled low and can be left unconnected when not in use. |
| LOL_Ab | 21 | 0 | Loss of Lock_Ab ⁴ /Cb ³ /Db ³ . These output pins indicate when DSPLL A, |
| LOL_Cb | 3 | 0 | C, D is out-of-lock (low) or locked (high). They can be left unconnected when not in use. |
| LOL_Db | 28 | 0 | |
| LOS0b | 20 | 0 | Loss of Signal for 0b ⁴ , 1b ³ , 2b ³ . These pins reflect the loss of signal |
| LOS1b | 47 | 0 | register status bits for inputs (0b, 1b, 2b). These pins can be left uncon- nected when not in use. |
| LOS2b | 55 | 0 | |
| FDEC | 25 | I | Frequency Decrement Pin ⁴ . This pin is used to step-down the output frequency of a selected DSPLL. The frequency change step size is register configurable. This pin does not have an internal pullup/pulldown and must be externally pulled high or low when unused. |

| Pin Name ¹ | Pin Number | Pin Type ² | Function |
|-----------------------|------------|-----------------------|---|
| FINC | 48 | I | Frequency Increment Pin³ . This pin is used to step-up the output fre- quency of a selected DSPLL. The frequency change step size is register configurable. The DSPLL(s) affected by the frequency change is deter- mined by the M_FSTEP_MSK_PLLx register settings. This pin is pulled low internally and can be left unconnected when not in use. |
| RSVD | 24 | - | Reserved. These pins are connected to the die. Leave disconnected. |
| | 40 | - | |
| | 41 | - | |
| | 42 | - | |
| NC | 23 | - | No Connect. These pins are not connected to the die. Leave disconnected |
| | 56 | - | ted. |
| Power | 1 1 | | |
| VDD | 32 | Р | Core Supply Voltage . The device core operates from a 1.8 V supply. See the Si5348 Rev E Reference Manual for power supply filtering recommendations. A 0402 1 µF capacitor should be placed very near each |
| | 46 | - | |
| | 60 | | of these pins. |
| VDDA | 13 | Р | Core Supply Voltage 3.3 V . This core supply pin requires a 3.3 V power source. See the Si5348 Rev E Reference Manual for power supply filtering recommendations. A 0402 1 µF capacitor should be placed very near each of these pins. |
| VDDS | 22 | Ρ | Status Output Voltage. The voltage on this pin determines VOL/VOH o the LOL_Ab and LOS0b status output pins, as well as the FDEC input. Connect to either 3.3 V or 1.8 V. A 0.1 μ F bypass capacitor should be placed very close to this pin. |
| VDDO0 | 29 | Р | Output Clock Supply Voltage 0-6. Supply voltage (3.3 V, 2.5 V, 1.8 V) |
| VDDO1 | 33 | Р | for OUTn outputs. Leave VDDO pins of unused output drivers unconnec ted. An alternate option is to connect the VDDO pin to a power supply |
| VDDO2 | 36 | Р | and disable the output driver to minimize current consumption. A 0402 1 μ F capacitor should be placed very near each of these pins. |
| VDDO3 | 43 | Р | |
| VDDO4 | 49 | Р | |
| VDDO5 | 52 | Р | |
| VDDO6 | 57 | Р | |
| gnd pad | - | Р | Ground Pad . This pad provides connection to ground and must be connected for proper operation. Use as many vias as practical and keep the via length to an internal ground plan as short as possible. |

Note:

1. Refer to the Si5348 Rev E Reference Manual for more information on register setting names.

2. I = Input, O = Output, P = Power.

3. The IO_VDD_SEL control bit (0x0943 bit 0) selects 3.3 V or 1.8 V operation.

4. The voltage on the VDDS pin(s) determines 3.3 V or 1.8 V operation.

Si5348 Rev E Data Sheet • Package Outline

11. Package Outline

The figure below illustrates the package details for the Si5348. The table below lists the values for the dimensions shown in the illustration.




Figure 11.1. Si5348 9x9 mm 64-Pin Quad Flat No-Lead (QFN)

| Dimension | Min | Nom | Мах |
|-----------|----------|----------|------|
| A | 0.80 | 0.85 | 0.90 |
| A1 | 0.00 | 0.02 | 0.05 |
| b | 0.18 | 0.25 | 0.30 |
| D | | 9.00 BSC | |
| D2 | 5.10 | 5.20 | 5.30 |
| e | 0.50 BSC | | |
| E | 9.00 BSC | | |
| E2 | 5.10 | 5.20 | 5.30 |
| L | 0.30 | 0.40 | 0.50 |
| aaa | _ | _ | 0.15 |
| bbb | _ | _ | 0.10 |
| CCC | — | — | 0.08 |
| ddd | _ | _ | 0.10 |
| eee | _ | _ | 0.05 |

Table 11.1. Package Dimensions

Note:

1. All dimensions shown are in millimeters (mm) unless otherwise noted.


2. Dimensioning and Tolerancing per ANSI Y14.5M-1994.

3. This drawing conforms to the JEDEC Solid State Outline MO-220.

4. Recommended card reflow profile is per the JEDEC/IPC J-STD-020 specification for Small Body Components.

12. PCB Land Pattern

The figure below illustrates the PCB land pattern details for the devices. The table below lists the values for the dimensions shown in the illustration. Refer to the Si5348 Rev E Reference Manual for information about thermal via recommendations.






Table 12.1. PCB Land Pattern Dimensions

| Dimension | Si5348 (Max) |
|-----------|--------------|
| C1 | 8.90 |
| C2 | 8.90 |
| E | 0.50 |
| X1 | 0.30 |
| Y1 | 0.85 |
| X2 | 5.30 |
| Y2 | 5.30 |

Note:

General

- 1. All dimensions shown are in millimeters (mm) unless otherwise noted.
- 2. This Land Pattern Design is based on the IPC-7351 guidelines.
- 3. All dimensions shown are at Maximum Material Condition (MMC). Least Material Condition is calculated based on a fabrication Allowance of 0.05 mm.

Solder Mask Design

1. All metal pads are to be non-solder mask defined (NSMD). Clearance between the solder mask and the metal pad is to be 60 µm minimum, all the way around the pad.

Stencil Design

- 1. A stainless steel, laser-cut and electro-polished stencil with trapezoidal walls should be used to assure good solder paste release.
- 2. The stencil thickness should be 0.125 mm (5 mils).
- 3. The ratio of stencil aperture to land pad size should be 1:1 for all perimeter pads.
- 4. A 3x3 array of 1.25 mm square openings on 1.80 mm pitch should be used for the center ground pad.

Card Assembly

- 1. A No-Clean, Type-3 solder paste is recommended.
- 2. The recommended card reflow profile is per the JEDEC/IPC J-STD-020 specification for Small Body Components.

13. Top Marking



Figure 13.1. Si5348 Top Marking

Table 13.1. Top Marking

| Line | Characters | Description |
|------|---|---|
| 1 | Si5348g- | Base part number and Device Grade. |
| | | Si5348: Packet Network Synchronizer for SyncE/1588; 64-QFN |
| | | g = Device Grade. See 3. Ordering Guide for more information. |
| | | – = Dash character. |
| 2 | Rxxxxx-GM | R = Product revision. (See 3. Ordering Guide for current revision.) |
| | | xxxxx = Customer specific NVM sequence number. (Optional NVM code assigned for custom, factory pre-programmed devices. Characters are not included for standard, factory default configured devices). See 3. Ordering Guide for more information. |
| | | -GM = Package (QFN) and temperature range (–40 to +85 °C). |
| 3 | YYWWTTTTTT | YYWW = Characters correspond to the year (YY) and work week (WW) of package assembly. |
| | | TTTTTT = Manufacturing trace code. |
| 4 | Circle w/ 1.6 mm (64-QFN) diam- eter | Pin 1 indicator; left-justified |
| | e4 | Pb-free symbol; Center-Justified |
| | TW | TW = Taiwan; Country of Origin (ISO Abbreviation) |

Si5348 Rev E Data Sheet • Device Errata

14. Device Errata

Please log in or register at www.skyworksinc.com to access device errata documents.

Si5348 Rev E Data Sheet • Revision History

15. Revision History

Revision 0.95

September, 2018

Initial release Revision E.

SKYWORKS

ClockBuilder Pro

Customize Skyworks clock generators, jitter attenuators and network synchronizers with a single tool. With CBPro you can control evaluation boards, access documentation, request a custom part number, export for in-system programming and more!

www.skyworksinc.com/CBPro



C

Portfolio www.skyworksinc.com/ia/timing

www.skyworksinc.com/CBPro



Quality www.skyworksinc.com/quality



Support & Resources www.skyworksinc.com/support

Copyright © 2021 Skyworks Solutions, Inc. All Rights Reserved.

Information in this document is provided in connection with Skyworks Solutions, Inc. ("Skyworks") products or services. These materials, including the information contained herein, are provided by Skyworks as a service to its customers and may be used for informational purposes only by the customer. Skyworks assumes no responsibility for errors or omissions in these materials or the information contained herein. Skyworks may change its documentation, products, services, specifications or product descriptions at any time, without notice. Skyworks makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Skyworks assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Skyworks products, information or materials, except as may be provided in Skyworks' Terms and Conditions of Sale.

THE MATERIALS, PRODUCTS AND INFORMATION ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. SKYWORKS DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. SKYWORKS SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Skyworks products are not intended for use in medical, lifesaving or life-sustaining applications, or other equipment in which the failure of the Skyworks products could lead to personal injury, death, physical or environmental damage. Skyworks customers using or selling Skyworks products for use in such applications do so at their own risk and agree to fully indemnify Skyworks for any damages resulting from such improper use or sale.

Customers are responsible for their products and applications using Skyworks products, which may deviate from published specifications as a result of design defects, errors, or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Skyworks assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Skyworks products outside of Skyworks' published specifications or parameters.

Skyworks, the Skyworks symbol, Sky5[®], SkyOne[®], SkyBlue[™], Skyworks Green[™], Clockbuilder[®], DSPLL[®], ISOmodem[®], ProSLIC[®], and SiPHY[®] are trademarks or registered trademarks of Skyworks Solutions, Inc. or its subsidiaries in the United States and other countries. Third-party brands and names are for identification purposes only and are the property of their respective owners. Additional information, including relevant terms and conditions, posted at www.skyworksinc.com, are incorporated by reference.

