# RENESAS

### HS310x-MCx

High Performance Relative Humidity and Temperature Sensor Module

The HS310x-MCx series module enables quick application integration with a standard 4-pin connector and fully calibrated relative humidity and temperature sensor (HS3101 and HS3103). It is available two different versions, HS310x-MC1 and HS310x-MC2, which differ only in the I<sup>2</sup>C address.

The HS310x relative humidity and temperature sensor features a hydrophobic membrane protecting it from environmental dusts, particles, and liquids with IP67 rating.

Integrated calibration and temperature-compensation logic provides fully corrected RH and temperature values via a standard I<sup>2</sup>C output. No user calibration of the output data is required.

The HS310x-MCx series is fully coated with HumiSeal, for corrosion resistance.

### Applications

- Climate control systems
- Home appliances
- Weather stations
- Industrial automation
- Medical equipment

#### **Physical Characteristics**

- Supply voltage: 2.3V to 5.5V
- Extended supply voltage: 1.8V (-20°C to +125°C)
- Operating temperature (HS310x sensor): -40°C to +125°C
- Operating temperature (Module connector): -20°C to +85°C
- 16.0 × 24.0 × 6.5 mm module

#### Features

- Humidity range: 0% to 100% RH
- HumiSeal coating for moisture protection
- Humidity accuracy: ±1.5% RH, typical
- 14-bit resolution: 0.01% RH, typical
- Independent programmable resolution settings: 8, 10, 12, 14 bits
- Fast RH response time: 1 second time constant, typical (with 1m/sec air flow), 4 seconds time constant, typical (in still air)
- Temperature sensor accuracy: ±0.2°C, typical
- Low current consumption: 1.0µA average (8-bit resolution, 1.8V supply), 24.4µA average (14-bit resolution, 3.3V supply), one RH and temperature measurement per second
- Excellent stability against aging
- Highly robust protection from harsh environmental conditions and mechanical shock
- Very low power consumption

#### **Product Image**



# Contents

13.	Revi	sion History	16			
12.	Ordering Information10					
11.	Marking Diagram1					
10.	Pack	cage Outline Drawings	15			
9.	Quality and Reliability					
8.		age and Handling				
7.	••	lication Circuit				
6.		ulating Humidity and Temperature Output				
c		-				
	5.9 5.10	-				
	5.8 5.0	Accessing the Non-volatile Memory Setting the Measurement Resolution				
	5.7	Status Bits				
	5.6	Data Fetch (DF)				
	5.5	Measurement Requests (MR)				
	5.4	Measurement Mode	10			
	5.3	I <sup>2</sup> C Communication	10			
	5.2	Sensor Slave Address				
•	5.1	I <sup>2</sup> C Features and Timing				
5.	Sens	sor Interface				
	4.2	Temperature Sensor Accuracy Graphs				
	4.1	Humidity Sensor Accuracy Graphs				
4.	Typi	cal Performance Graphs				
	3.3	Sleep Current				
	3.2	Temperature Sensor Specification				
з.	<b>пи</b> 3.1	Humidity Sensor Specification				
3.		idity and Temperature Specifications				
	2.1	Recommended Operating Conditions				
2.	<b>Spec</b> 2.1	cifications Absolute Maximum Ratings				
-						
	1.2 1.3	Pin Descriptions Pin Connector				
	1.1	Pin Assignments				
1.	Pin I	nformation				

# Figures

Figure 1. Pin Assignments	4
Figure 2. Pin Connector	4
Figure 3. Sleep Current Variation over Temperature, $V_{DD}$ at 3.3V	7
Figure 4. HS3101-MCx RH Accuracy Tolerance at 25°C	8
Figure 5. HS3101-MCx RH Accuracy over Temperature	8
Figure 6. HS3103-MCx RH Accuracy Tolerance at 25°C	8
Figure 7. HS3103-MCx RH Accuracy over Temperature	8
Figure 8. HS3101-MCx Temperature Sensor Accuracy Tolerance	8
Figure 9. HS3103-MCx Temperature Sensor Accuracy Tolerance	8
Figure 10. Timing Diagram	9
Figure 11. START and STOP Condition Waveform	
Figure 12. Measurement Request	11
Figure 13. Data Fetch	12
Figure 14. Sequence of Commands to Enter Programming Mode	12
Figure 15. Sequence of Commands to Change the Relative Humidity Resolution	13
Figure 16. HS310x-MCx Application Circuit	15

# Tables

Table 1. Absolute Maximum Ratings	5
Table 2. Recommended Operating Conditions	5
Table 3. Humidity Sensor Specification, T <sub>A</sub> = +25°C, V <sub>DD</sub> = 2.3V to 5.5V	6
Table 4. Temperature Sensor Specification, $T_A = +25^{\circ}C$ , $V_{DD} = 2.3V$ to 5.5V	7
Table 5. I <sup>2</sup> C Timing Parameters	9
Table 6. Status Bits	12
Table 7. Non-volatile Memory Registers	13
Table 8. Register Values for Different Resolution Settings	14

# 1. Pin Information

#### 1.1 Pin Assignments




Figure 1. Pin Assignments

### 1.2 Pin Descriptions

Pin Number	Pin Name	Туре	Description
1	VDD	In	Supply voltage.
2	SCL	In/Out	Serial clock.
3	SDA	In/Out	Serial data.
4	VSS	In	Ground.

### 1.3 Pin Connector

The 4-pin connector pitch is 0.079 inch (2.00 mm). Part reference is JST, S4B-PH-K-S. For easy product part number differentiation, the HS310x-MC1 has a white connector and the HS310x-MC2 has a blue connector mounted.




Figure 2. Pin Connector

# 2. Specifications

#### 2.1 Absolute Maximum Ratings

**CAUTION**: Do not operate at or near the maximum ratings listed for extended periods of time. Exposure to such conditions can adversely impact product reliability and result in failures not covered by warranty.

Symbol	Parameter	Conditions	Minimum	Maximum	Unit
-	Analog Supply Voltage	-	-0.3	6.0	V
-	Storage Temperature Range	-	-55	125	°C

**Table 1. Absolute Maximum Ratings** 

### 2.2 Recommended Operating Conditions

*Important*: The HS310x-MCx series sensors are optimized to perform best in the more common temperature and humidity ranges of 10°C to 50°C and 20% RH to 80% RH, respectively. If operated outside of these conditions for extended periods, especially at high humidity levels, the sensors may exhibit an offset. In most cases, this offset is temporary and will gradually disappear once the sensor is returned to normal temperature and humidity conditions. The amount of the shift and the duration of the offset vary depending on the duration of exposure and the severity of the relative humidity and temperature conditions. The time needed for the offset to disappear can also be decreased by using the procedures described in "Storage and Handling".

Parameter	Condition		Minimum	Typical	Maximum	Unit
Operating Supply Voltage	-		-	3.3	5.5	V
Extended Operating Supply Voltage	Operating temperature fr 125°C	rom -20°C to	1.8	-	5.5	V
Operating Humidity Range	-		0	-	100	%RH
Operating Temperature, Sensor	HS310x sensor only		-40	-	125	°C
Operating Temperature, Board	Limited to module conne	ector	-20	-	85	°C
Sloop Current	Sleep Mode	-40°C to 85°C	-	0.6	1	μA
Sleep Current		-40°C to 125°C	-	1	3	
	One RH + temperature measurement/second	8-bit resolution	1.0	1.5	1.7	μA
Average Current <sup>[1]</sup>		10-bit resolution	2.0	2.6	2.8	
Average Current <sup>13</sup>		12-bit resolution	5.5	7.0	7.1	
		14-bit resolution	20.1	24.4	24.4	
	Wake-up		-	0.10	-	
		8-bit resolution	-	0.55	-	
Measurement Time	Humidity or temperature including the digital compensation	10-bit resolution	-	1.31	-	ms
		12-bit resolution	-	4.50	-	
		14-bit resolution	-	16.90	-	

**Table 2. Recommended Operating Conditions** 

1. Minimum, typical, and maximum average currents are given at 1.8V, 3.3V, and 5.5V V<sub>DD</sub>, respectively.

# 3. Humidity and Temperature Specifications

# 3.1 Humidity Sensor Specification

Table 3. Humidity Sensor Specification,  $T_A = +25^{\circ}C$ ,  $V_{DD} = 2.3V$  to 5.5V

Parameter	Condition		Minimum	Typical	Maximum	Unit
Operating Range		-	0	-	100	%RH
Accuracy <sup>[1]</sup>	HS3101-MCx	10% to 90% RH	-	±1.5	±1.8	%RH
Acculacy	HS3103-MCx	20% to 80% RH	-	±2.5	±3.5	70КП
Resolution	8-bit		-	0.7	1.0	%RH
Resolution	14- bit		-	0.01	0.015	<u>%</u> КП
Hysteresis	-		-	-	±1.0	%RH
Noise in Humidity (RMS)	14-bit		-	0.014	-	%RH
Non Linearity from Posponso Cunyo	HS3101-MCx	10% to 90% RH		±0.15	±0.25	%RH
Non-Linearity from Response Curve	HS3103-MCx	20% to 80% RH	-	±0.15	±0.25	70КП
Long-Term Stability	-		-	±0.1	±0.25	%RH/Yr
Response Time Constant <sup>[1]</sup> ( $\tau_{H}$ )	20% to 80% RH, 1 meter/sec air flow		-	1	-	sec
	20% to 80% R	H Still Air	3.0	4.0	6.0	

1. Monotonic increases from 10 to 90%RH after sensor has been stabilized at 50% RH.

2. Initial value to 63% of total variation.

### 3.2 Temperature Sensor Specification

Table 4. Temperature Sensor Specification,  $T_A = +25^{\circ}C$ ,  $V_{DD} = 2.3V$  to 5.5V

Parameter	Parameter Condition Minimum Typical Maximum Un						
Range		-	-40	-	125	°C	
		-10°C to 80°C	-	±0.2	±0.3		
	HS3101-MCx	-40°C to -10°C	-	±0.4	±0.5		
		80°C to 125°C	-	±0.5	±0.6		
		0°C to 70°C	-	±0.25	±0.35		
Accuracy		-10°C to 0°C	-	±0.3	±0.5	°C	
	HS3103-MCx	-20°C to -10°C	-	±0.35	±0.55		
		-30°C to -20°C	-	±0.4	±0.6		
		-40°C to -30°C	-	±0.55	±0.8		
		70°C to 125°C	-	±0.8	±1.0		
Resolution	8-bit		0.6	0.9	1.5	°C	
Resolution	14-bit		0.01	0.015	0.025		
Response Time Constant $^{[1]}\left( \tau_{T}\right)$	-		20	-	-	Sec.	
Long-Term Stability	-		-	-	0.02	°C/Yr	
Supply Voltage Dependency <sup>[2]</sup>	VDD ≥ 2.8V		-	0.03	0.1	°C/V	
Supply vollage Dependency	1.8V < VDD < 2.8V		-	1.25	2.25	°C/V	

1. Response time depends on system thermal mass and air flow.

2. Temperature accuracy can be optimized for specified supply voltages upon request.

### 3.3 Sleep Current

The sleep current of the HS310x-MCx series depends on the operating temperature, as shown in the following figure. Note that there is no significant dependence of the sleep current on the supply voltage.




Figure 3. Sleep Current Variation over Temperature, V<sub>DD</sub> at 3.3V

# 4. Typical Performance Graphs

#### 4.1 Humidity Sensor Accuracy Graphs

The typical and maximum relative humidity sensor accuracy tolerances are shown in the following figures.




Figure 4. HS3101-MCx RH Accuracy Tolerance at 25°C




Figure 6. HS3103-MCx RH Accuracy Tolerance at 25°C




Figure 5. HS3101-MCx RH Accuracy over Temperature






Figure 7. HS3103-MCx RH Accuracy over Temperature

#### 4.2 Temperature Sensor Accuracy Graphs

The typical and maximum temperature sensor accuracy tolerances are shown in the following figures.









# 5. Sensor Interface

The HS310x-MCx series sensor uses a digital l<sup>2</sup>C-compatible communication protocol. To accommodate multiple devices, the protocol uses two bi-directional open-drain lines: The Serial Data Line (SDA) and the Serial Clock Line (SCL). Pull-up resistors to  $V_{DD}$  are required on customers host PCB side. Several slave devices can share the bus; however only one master device can be present on the line.

### 5.1 I<sup>2</sup>C Features and Timing

The HS310x-MCx series sensor operates as a slave device on the I<sup>2</sup>C bus with support for 100kHz and 400kHz bit rates. Each transmission is initiated when the master sends a 0 START bit (S), and the transmission is terminated when the master sends a 1 STOP bit (P). These bits are only transmitted while the SCL line is HIGH.




Figure 10. Timing Diagram

Parameter	Symbol	Minimum	Typical	Maximum	Unit
SCL Clock Frequency <sup>[1]</sup>	f <sub>SCL</sub>	20	-	400	kHz
START Condition Hold Time Relative to SCL Edge	t <sub>HDSTA</sub>	0.1	-	-	μs
Minimum SCL Clock LOW Width <sup>[2]</sup>	t <sub>LOW</sub>	0.6	-	-	μs
Minimum SCL Clock HIGH Width <sup>[2]</sup>	t <sub>ніGн</sub>	0.6	-	-	μs
START Condition Setup Time Relative to SCL Edge	t <sub>susta</sub>	0.1	-	-	μs
Data Hold Time on SDA Relative to SCL Edge	t <sub>HDDAT</sub>	0	-	0.5	μs
Data Setup Time on SDA Relative to SCL Edge	t <sub>SUDAT</sub>	0.1	-	-	μs
STOP Condition Setup Time on SCL	t <sub>susto</sub>	0.1	-	-	μs
Bus Free Time Between STOP Condition and START Condition	t <sub>BUS</sub>	1	-	-	μs

Table 5. I<sup>2</sup>C Timing Parameters

1. The minimum frequency of 20kHz applies to test only; no minimum under normal operations.

2. Combined LOW and HIGH widths must equal or exceed the minimum SCL period.

#### 5.2 Sensor Slave Address

The HS310x-MCx series is available in two product variants, which technical differ only in their I<sup>2</sup>C address:

- HS310x-MC1 default I<sup>2</sup>C address is 44<sub>HEX</sub>
- HS310x-MC2 default I<sup>2</sup>C address is 50<sub>HEX</sub>

Each device will respond only to its respective 7-bit address. For more information, see "I<sup>2</sup>C Communication."

#### 5.3 I<sup>2</sup>C Communication

The sensor transmission is initiated when the master sends a 0 START bit (S). The transmission is terminated when the master sends a 1 STOP bit (P). These bits are only transmitted while the SCL line is HIGH (see Figure 11 for waveforms).

When the START condition has been set, the SCL line is toggled at the prescribed data rate, clocking subsequent data transfers. Data on the SDA line is always sampled on the rising edge of the SCL line and must remain stable while SCL is HIGH to prevent false START or STOP conditions.




Figure 11. START and STOP Condition Waveform

After the START bit, the master device sends the 7-bit slave address (see "Sensor Slave Address") to the HS310x-MCx, followed by the read/write bit, which indicates the transfer direction of any subsequent data. This bit is set to 1 to indicate a read from slave to master or set to 0 to indicate a write from master to slave.

All transfers consist of 8 bits and a response bit: 0 for Acknowledge (ACK) or 1 for Not Acknowledge (NACK). After the ACK is received, another data byte can be transferred or the communication can be stopped with a STOP bit.

#### 5.4 Measurement Mode


The HS310x-MCx is factory-programmed to operate in Sleep Mode. In Sleep Mode, the sensor waits for commands from the master before taking measurements. The digital core only performs conversions when it receives a *Measurement Request* command (MR); otherwise, it is always powered down.


#### 5.5 Measurement Requests (MR)

The MR command is required to wake up the HS310x-MCx from its Sleep Mode. Initiate the Measurement Request by sending the 7-bit slave address followed by an eighth bit = 0 (WRITE).

A measurement cycle consists of a humidity and temperature conversion followed by the digital signal processor (DSP) correction calculations. At the end of a measurement cycle, the digital output register will be updated before powering down.

The output is always scaled to 14 bits. The order of the bits is big-endian.





### 5.6 Data Fetch (DF)

At the end of a measurement cycle, valid data can be fetched. The status bits of the DF results can be used to detect if the data is valid or stale (see "Status Bits"); otherwise, wait for the measurements to complete before performing the DF.

The DF command starts with the 7-bit slave address followed by an eighth bit = 1 (READ). The HS310x-MCx as a slave sends an acknowledge (ACK) indicating success.

The number of data bytes returned by the HS310x-MCx is determined by when the master sends the NACK and STOP condition. The full 14 bits of the humidity data are fetched in the first two bytes. The two MSBs of the first byte are the status bits.

The 14 bits of temperature data follow the humidity data. The last two bits (LSBs) of the fourth data byte are undetermined and should be masked off. In the event that the temperature data is not needed, the read can be terminated by sending a NACK after the second byte.

Alternatively, if only 8-bit resolution is desired for the temperature output, the read can be terminated after the 3<sup>rd</sup> byte by issuing a NACK followed by a stop bit. The measurement time depends on the configured sensor resolution. The following table lists examples when the resolutions for the relative humidity and temperature measurements are the same. For different relative humidity and temperature resolution settings, the measurement times in 3 should be used, along with the 0.1ms wake-up time.


For example, an 8-bit relative humidity measurement and a 12-bit temperature measurement results in a total measurement time of:

0.1ms + 0.55ms + 4.5ms = 5.15ms.

RH+T measurement times (including wake-up time) at different resolution settings.

Resolution <sup>[1]</sup> (Bits)	Measurement Time (ms)
8	1.20
10	2.72
12	9.10
14	33.90

1. Same resolutions are assumed for both relative humidity and temperature.



### 5.7 Status Bits


The status bits are used to indicate the current state of the fetched data. The two MSBs of the humidity data byte are the status bits (see the following table).

Status Bits	Definition
00 <sub>B</sub>	Valid Data: Data that has not been fetched since the last measurement cycle.
01 <sub>B</sub>	Stale Data: Data that has already been fetched since the last measurement cycle. <i>Note</i> : If a data fetch is performed before or during the first measurement after power-on reset, then the stale status will be returned, but this data is actually invalid since the first measurement has not been completed.

#### Table 6. Status Bits

#### 5.8 Accessing the Non-volatile Memory

The HS310x-MCx series non-volatile memory stores its measurement resolution setting and its ID number. To change the sensor resolution or read the ID number, the master must place the HS310x-MCx into programming mode while the device is powering up. The following figure shows the sequence of commands needed to enter the programming mode, which must be sent within 10ms after applying power to the sensor. The master must send the I<sup>2</sup>C address and a Write bit followed by the command **0xA0|0x00**.





This command takes  $120\mu s$  to process, after which the master has access to the non-volatile memory registers listed in the following table. All of these registers are 16 bits wide.

To return to normal sensor operation and perform measurements, the master must send the I<sup>2</sup>C address and a Write bit, followed by the command: **0x80|0x00|0x00**.

Address	Register Description
0x06	Humidity Sensor Resolution – Read Register (bits 11:10).
0x46	Humidity Sensor Resolution – Write Register (bits 11:10).
0x11	Temperature Sensor Resolution – Read Register (bits 11:10).
0x51	Temperature Sensor Resolution – Write Register (bits 11:10).
0x1E	Read Sensor ID – Upper 2 bytes.
0x1F	Read Sensor ID – Lower 2 bytes.

#### Table 7. Non-volatile Memory Registers


#### 5.9 Setting the Measurement Resolution

The HS310x-MCx series relative humidity and temperature measurement resolutions can be set *independently* to 8, 10, 12, or 14-bits by writing to the non-volatile memory, and are initially set to **14 bits by default**. The procedure to set the humidity sensor resolution is illustrated in the following figure. The relative humidity and temperature resolution can be read in registers **0x06 and 0x11**, respectively, or written in registers **0x46 or 0x51**. The resolution information is stored in bits [11:10] of these registers, as listed in Table 8. All of the other bits in these registers must be left unchanged. As such, before writing new resolution settings, the contents of the read registers must be read, and only bits [11:10] can be changed in the write registers. Once bits [11:10] are changed to set the desired resolution, *the entire register must be written back* to the HS310x-MCx sensor.

#### Step 1



#### <u>Step 2</u>



#### Step 3

Change bits [11:10] of the register to the desired resolution setting, without changing the other bits

#### <u>Step 4</u>




Figure 15. Sequence of Commands to Change the Relative Humidity Resolution

Resolution Register Bits [11:10]	Resolution (Bits)
00 <sub>B</sub>	8
01 <sub>B</sub>	10
10 <sub>B</sub>	12
11 <sub>B</sub>	14

#### Table 8. Register Values for Different Resolution Settings

The sensor non-volatile memory requires 120µs to load the data into the registers after step 1, and requires 14ms to write the data after step 4. *Failure to comply with these processing times may result in data corruption and introduce errors in sensor measurements.* The procedure to change the temperature sensor resolution is the same as that displayed in Figure 16, except the register address in Step 1 must be set to **0x11** and the register address in Step 4 will be **0x51**.

#### 5.10 Reading the HS310x-MCx ID Number

The sensor ID is a 32-bit number and can be read in a similar fashion as illustrated in steps 1 and 2 of Figure 16, using the appropriate register address values. The ID number is stored in two registers, with the upper and lower 16 bits stored in register addresses **0x1E and 0x1F**, respectively.

# 6. Calculating Humidity and Temperature Output

The entire output of the HS310x-MCx is 4 bytes. The relative humidity (in percent) and the temperature (in degrees Celsius) are calculated with Equation 1 and Equation 2, respectively.

Humidity [% RH] = 
$$\left(\frac{Humidity [13:0]}{2^{14} - 1}\right) * 100$$

Equation 1

Temperature 
$$[{}^{0}C] = \left(\frac{Temperature [15:2]}{2^{14} - 1}\right) * 165 - 40$$

**Equation 2** 

# 7. Application Circuit




Figure 16. HS310x-MCx Application Circuit

# 8. Storage and Handling

*Recommendation*: Once the sensors are removed from their original packaging, store them in metal-in antistatic bags.

Avoid using polyethylene antistatic bags as they may affect sensor accuracy.

The nominal storage conditions are 10°C to 50°C and humidity levels within 20% to 60% RH. If stored outside of these conditions for extended periods of time, the sensor readings may exhibit an offset. The sensor can be reconditioned and brought back to its calibration state by applying the following procedure:

- 1. Bake at a temperature of 100°C with a humidity < 10% RH for 10 to 12 hours.
- 2. Rehydrate the sensor at a humidity of 75% RH and a temperature between 20°C to 30°C for 12 to 14 hours.


# 9. Quality and Reliability

The HS310x-MCx series is available as a qualified product for consumer and industrial market applications. All data specified parameters are confirmed if not stated otherwise.

# **10. Package Outline Drawings**

The package outline drawings are located at the end of this document and are accessible from the Renesas website. The package information is the most current data available and is subject to change without revision of this document.

# 11. Marking Diagram



- The top line indicates the following:
  - The first three digits, "123" (YWW), indicate the last digit of the year and last two digits of the week that the part was assembled.
  - The last three digits, "456", indicate lot traceability.
  - The bottom line indicates the part number.

# **12. Ordering Information**

Part Number [1]	Description and Package	Carrier Type	Temperature Range
HS3101-MC1 HS3101-MC2	Digital Relative Humidity and Temperature Sensor, with membrane $\pm 1.5\%$ RH (Typical), <u>16.0 × 24.0 × 6.5 mm module, MOD1</u>	Tray	-20°C to +85°C
HS3103-MC1 HS3103-MC2	Digital Relative Humidity and Temperature Sensor, with membrane $\pm 2.5\%$ RH (Typical), <u>16.0 × 24.0 × 6.5 mm module, MOD1</u>	Tray	-20°C to +85°C

1. The -MC1 and -MC2 parts differ in  $I^2C$  address, silkscreen part number marking, and connector color.


# 13. Revision History

Revision	Date	Description
1.06	Mar 28, 2023	<ul> <li>Removed Pull-up resistors in Application Circuit; replaced diagram</li> <li>Removed EOL parts HS3102-MC1/MC2 and HS3104-MC1/MC2 from Ordering Information</li> <li>Removed HS3102-MCx RH Accuracy Tolerance at 25°C and HS3102-MCx RH Accuracy over Temperature figures from Typical Performance Graphs section</li> <li>Removed HS3102-MCx and HS3104-MCx Temperature Sensor Accuracy Tolerance figures from Temperature Sensor Accuracy Graphs section</li> <li>Added package (module) outline drawing links in Ordering Information</li> </ul>
1.05	Feb 13, 2023	<ul> <li>Updated the color of connector</li> </ul>
1.04	Dec 12, 2022	<ul> <li>Updated the part numbers in Ordering Information</li> </ul>
1.03	Dec 8, 2022	<ul><li>Added marking diagram information</li><li>Corrected the package information</li></ul>
1.02	Dec 7, 2022	<ul> <li>Changed to HS3101-MCx</li> <li>Added with HS3101-MC2 with different I2C address</li> <li>Added package links to Ordering Information</li> <li>Completed other minor updates</li> </ul>
1.01	Jul 12, 2022	<ul> <li>Expanded Table 4, temperature specification</li> <li>Updated Package Outline Drawings section</li> </ul>
1.00	Nov 9, 2021	Initial release.



#### **Package Outline Drawing**

Package Code: BD0 HS300X-MCX Series, 16.0 x 24.0 x 6.5 mm Module PSC-4912-01, Revision: 06, Date Created: April 25, 2023



- 1. All dimension are in mm, angles in degrees.
- 2. Warpage shall not exceed 0.10mm.

6.40

6.30

6.60

6.50

1.60

3.4 REF

6.80

6.70

1.80

L

Н

t

h

#### IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES ("RENESAS") PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers skilled in the art designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only for development of an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising out of your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use o any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Disclaimer Rev.1.0 Mar 2020)

#### **Corporate Headquarters**

TOYOSU FORESIA, 3-2-24 Toyosu, Koto-ku, Tokyo 135-0061, Japan www.renesas.com

#### **Trademarks**

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners. **Contact Information** 

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit: <u>www.renesas.com/contact/</u>