ESPC3-32

Product Specification

Features

General

- Chip: ESP32-C3
- Module Size:18mm*25.5mm*3mm
- 4MByte embedded flash (default)
- 384KB ROM
- 400KB SRAM
- Wi-Fi Features
 - IEEE 802.11 b/g/n-compliant
 - Center frequency range of operating channel: 2412 ~ 2484 MHz
 - Supports 20 MHz, 40 MHz bandwidth in 2.4 GHz band
 - 1T1R mode with data rate up to 150 Mbps
 - TX/RX A-MPDU, TX/RX A-MSDU
 - Immediate Block ACK
 - Fragmentation and defragmentation
 - Automatic Beacon monitoring (hardware TSF)
 - 4 X virtual Wi-Fi interfaces
 - Simultaneous support for Infrastructure BSS in Station mode, Soft-AP mode, Station + Soft-AP mode, and promiscuous mode

Bluetooth Features

- Bluetooth LE: Bluetooth 5, Bluetooth mesh
- Speed: 125 Kbps, 500 Kbps, 1 Mbps, 2 Mbps
- Advertising extensions
- Multiple advertisement sets
- Channel selection algorithm #2

Peripheral Interfaces

- GPIO * 15;
- UART * 2;
- IIC ;

-2.4GHz Wi-Fi and BLE5.0 Combo Module

Version: 1.0

Date: Feb.20, 2023

- SPI;
- EN;
- PWM x 6 ;
- ADC;
- **Working Temperature:** -40℃-85℃


Applications

- Serial transparent transmission;
- Wi-Fi prober;
- Smart power plug/Smart LED light;
- Mesh networks;
- Sensor networks;
- Over-the-top (OTT) devices;
- Wireless location system beacon;
- Industrial field bus;

Module Type

Name	Antenna Type PCB ANT U.FL Ipex		
ESPC3-32	PCB ANT		
ESPC3-32E	U.FL Ipex		

Module Structure



Update Record

Date Version		Update
2023-02-20	V1.0	First released

Table of Contents

1. Introduction	1
2. Interface Definition	
3. Size and Layout	5
4. Electronica Characteristics	6
5. Power Consumption	7
6. Wi-Fi RF Characteristics	7
7. Bluetooth LE Radio	9
8. Recommended Sold Temperature Curve	11
9. Minimum User System	11
10. Recommended Layout Design	12
11. Peripheral Design Suggestion	13
12. Product Handling	14
13. U.F.L RF Connector	14
14. Packing Instruction	15


1. Introduction

ESPC3-32 Wi-Fi and BLE coexistence Module is a highly integrated single-chip low power 802.11bgn Wireless LAN (WLAN) network controller. It combines a RISC CPU, WLAN MAC, a 1T1R capable WLAN baseband, RF, and Bluetooth in a single chip. It also provides a bunch of configurable GPIO, which are configured as digital peripherals for different applications and control usage.

ESPC3-32 Module use ESP32-C3 as Wi-Fi and BLE coexistence SOC chip.

ESPC3-32 Module integrates internal memories for complete Wi-Fi protocol functions. The embedded memory configuration also provides convenient application developments.

ESPC3-32 module supports the standard IEEE802.11 b/g/n/e/i protocol and the complete TCP/IP protocol stack. User can use it to add the Wi-Fi function for the installed devices, and also can be viewed as an independent network controller. Anyway, ESPC3-32 Wi-Fi module provides many probabilities with the best price.



Technical parameters for ESPC3-32 are listed as follows.

Туре	Item	Parameter	
	Frequency	2.4G~2.5G (2412M~2484M)	
		802.11b: +20.5 dBm	
	Transmit power	802.11g: +19 dBm	
	a oblig	802.11n: +17.5 dBm	
	10/15	802.11b: -89 dBm (11Mbps)	
Wi-Fi	Receiver sensitivity	802.11g: -77 dBm (54Mbps)	
		802.11n: -74 dBm (MCS7)	
		-25dB @802.11b,11Mbps @21dBm	
	EVM	-28dB @802.11n,54Mbps @19dBm	
		-30dB @802.11n,HT40,MCS7 @18.5dBm	
	Antenna	PCB antenna / U.FL	
BLE	RF power control range	-27~18dBm	
	СРИ	32-bit RISC CPU	
	Interface	UART/SDIO/SPI/I2C/GPIO/PWM	
TT 1	Working voltage	3.0V ~ 3.6V	
Hardware	Working temperature	-40°C ~ 85°C	
	Environment temperature	-40°C ~ 105°C	
n^{0}	Shape	18mm x 25.5mm x 3mm	
	Wi-Fi working mode	STA, Soft-AP and sniffer modes	
	Security mode	WPS / WEP / WPA / WPA2 / WPA3	
Software	Update firmware	UART Download	
	Software develop	SDK	
	Network protocol	IPv4, TCP/UDP/HTTP/FTP/MQTT	

Table.1.1 ESPC3-32 Parameters

2. Interface Definition

ESPC3-32 Wi-Fi & BLE module interface definition is shown as below $_{\circ}$




Fig.2.1 ESPC3-32 Pins Definition

Working modes and pins function is shown in Table 2.1.

Table.2.1Working Mode

Mode	IO9 Voltage Level
UART Download Mode	LOW
Flash Boot Mode	HIGH (Default)

Table.2.2 Pins Function Definition

Num.	Pin Name	Туре	Function		
1.15.38	GND	Р	Power, 3.3V/500mA Recommended		
2	3V3	Р	Power, 3.3V/500mA Recommended		
3	EN	I/O	Chip enable; Internal Pull-up. HIGH: enable the chip		
4.16.23-24.26- 29.32-33.36-37	NC	-	Not Connected		

Doctors of Intelligence & Technology (www.doit.am) Copyright@2014-2023

5	IO0	I/O	GPIO0,ADC1_CH1,XTAL_32K_P
6	IO1	I/O	GPIO1,ADC1_CH1, XTAL_32K_N
7	IO2	I/O	GPIO2, ADC1_CH2, FSPIQ, Internal Pull-up
8	IO3	I/O	GPIO3, ADC1_CH3
9	IO4	I/O	GPIO4, ADC1_CH4, MTMS, FSPIHD
10	IO5	I/O	GPIO5, ADC2_CH0, MTDI, FSPIWP
11	IO6	I/O	GPIO6,FSPICLK,MTCK
12	I07	I/O	GPIO7,FSPID,MTDO
13	IO8	I/O	GPIO8
14	IO10	I/O	GPIO10, FSPICS0. When the value of eFuse bi EFUSE_JTAG_SEL_ENABLE is 0, JTAG signals cannot be used 1, if IO10 is 0, JTAG signals come from chip pins; if IO10 is 1 JTAG signals cannot be used
17	SPIHD	I/O	SPIHD, GPIO12, Connect With Internal Flash
18	SPIWP	I/O	SPIWP, GPIO13, Connect With Internal Flash
19	SPICS	I/O	SPICS, GPIO14, Connect With Internal Flash
20	SPICLK	I/O	SPICLK, GPIO15, Connect With Internal Flash
21	SPIQ	I/O	SPIQ, GPIO17, Connect With Internal Flash
22	SPID	I/O	SPID, GPIO16, Connect With Internal Flash
25	IO9	I/O	GPIO9
30	IO18	I/O	GPIO18,USB-D-
31	IO19	I/O	GPIO19,USB-D+
34	RX0	I/O	GPIO20,U0RXD
35	TX0	I/O	GPIO21,U0TXD

3. Size and Layout

Size for ESPC3-32 can be shown as follows.





Fig.3.1 Shape for ESPC3-32



(a) Vertical View




Fig. 3.3 PCB Layout for ESPC3-32

4. Electronica Characteristics

Table.4.1 Electronica Characteristics	s
---------------------------------------	---

Parameter		Condition	Min	Classical	Max	Unit
Store Temperature			-40	Normal	150	°C
Sold Tem	perature	IPC/JEDEC J-STD-020	-	-	260	°C
Working Voltage		-	3.0	3.3	3.6	V
	V _{IL}	-	-0.3	-	0.25*VDD	
I/O	V _{IH}	-	0.75*VDD	-	VDD+0.3	V
1/0	V _{OL}	-	-	-	0.1*VDD	v
	V _{OH}	-	0.8*VDD	-	-	

Electrostatic Release Quantity (Human model)	TAMB=25℃	-	-	2	KV
Electrostatic Release Quantity (Machine model)	TAMB=25 ℃	-	-	0.5	KV

5. Power Consumption

Parameter	Min	Classical	Max	Unit
RX 11b /g/n, HT20	-	-	82	mA
RX 11n, HT40		-	84	mA
TX 11b, 1Mbps @21dBm		-	350	mA
TX 11g, 54Mbps @19dBm	-	-	295	mA
TX 11n, HT20, MCS7, @18.5dBm	-	-	290	mA
TX 11n, HT40, MCS7, @18.5dBm	-	-	290	mA
Modem-sleep, CPU is powered on @80MHz	-	15	-	mA
Light-sleep	-	130	-	uA
Deep-sleep, RTC timer + RTC memory	-	5	-	uA
Power off, CHIP_PU is set to low level	-	1	0	uA

Table.5.1 Power Consumption

The peak current consumption of ESPC3-32 exceed 400mA when the module start work (RF calibration work consumes maximum current). Therefore, the recommended power supply is no less than 500mA.

Note:

1. Active Mode: CPU and RF are all turned on.

2. Modem-sleep Mode: CPU is turned on. RF and baseband are turned off, but the communication is still connected.

3. Light-sleep Mode: CPU is turned off. RTC/external interrupt/MAC can wake up the chip. The communication is still connected.

4. Deep-sleep Mode: Only RTC is turned on.

6. Wi-Fi RF Characteristics

The data in the following table is gotten when voltage is 3.3V in the indoor temperature environment.

Parameter	Min	Classical	Max	Unit
Input frequency	2412	-	2484	MHz
802.11b @1Mbps,11Mbps	-	20.5	-	dBm
802.11g @6Mbps	-	20.0	-	dBm
802.11g @54Mbps	-	18.0	-	dBm
802.11n,HT20 MCS0	-	19.0	-	dBm
802.11n,HT40 MCS0	-	18.5	-	dBm
EVM @11b,1Mbps@20dBm	-	-24.5	-	dBm
EVM @11g,54Mbps@19dBm	-	-28	-	dBm
EVM @11n,MCS7@18.5dBm	-	-30	-	dBm
EVM @11n, HT40, MCS7@18.5dBm	-	-30.5	-	dBm

Table.6.1 Wi-Fi TX Characteristics

Table.6.2 Wi-Fi RX Sensitivity

Parameter	Min	Classical	Max	Unit		
802.11b,1Mbps	-	-98	-	dBm		
802.11b,11Mbps	-	-88	-	dBm		
802.11g,6Mbps	-	-92	-	dBm		
802.11g,54Mbps	-	-76	-DI-	dBm		
802.11n,HT20,MCS0	- 0	-92	-	dBm		
802.11n,HT20,MCS3	- 0 0	-85	-	dBm		
802.11n,HT20,MCS7	-	-74	2	dBm		
802.11n,HT40,MCS0	- 15	-90	-	dBm		
802.11n,HT40,MCS3	27	-81	-	dBm		
802.11n,HT40,MCS7	-	-71	-	dBm		
Table.6.3 Wi-Fi RX Characteristics						
-	20	<u> </u>	24	TT T		

Table.6.3 Wi-Fi RX Characteristics

-	Parameter	Min	Classical	Max	Unit
	MAX RX Level @11b,1Mbps	-	5	-	dBm
	MAX RX Level @11b,11Mbps	-	5	-	dBm

MAX RX Level @11g,6Mbps	-	5	-	dBm
MAX RX Level @11g,54Mbps	-	0	-	dBm
MAX RX Level @11n,HT20,MCS0	-	5	-	dBm
MAX RX Level @11n,HT20,MCS7	-	0	-	dBm
MAX RX Level @11n,HT40,MCS0	-	5	-	dBm
MAX RX Level @11n,HT40,MCS7	-	0	-	dBm
RX Adjacent Channel Rejection@11b,1Mbps	-	35	-	dB
RX Adjacent Channel Rejection@11b,11Mbps	-	35	-	dB
RX Adjacent Channel Rejection@11g,6Mbps	-	31	-	dB
RX Adjacent Channel Rejection@11g,54Mbps	-	14	-	dB
RX Adjacent Channel Rejection@11n,HT20,MCS0	-	31	-	dB
RX Adjacent Channel Rejection@11n,HT20,MCS7	-	13	-	dB
RX Adjacent Channel Rejection@11n,HT40,MCS0	-	19	-	dB

7. Bluetooth LE Radio

Parameter	Min	Classical	Max	Unit
Gain control power	-	3	-	dBm
RF power control range	-27	-	18	dBm
In-band emissions @F-F0±3MHz, LE 1M	-	-41.95	-	dBm
In-band emissions @F-F0±>3MHz, LE 1M	-2	-44.48	-	dBm
Modulation characteristics @ \triangle flavg, LE 1M	-	245	-	kHz
Modulation characteristics @ \triangle f2max, LE 1M	X	208	-	kHz
Carrier frequency offset, LE 1M	5	-9	-	kHz
In-band emissions @F-F0±5MHz, LE 2M	-	-45.26	-	dBm
In-band emissions @F-F0±>5MHz, LE 2M	-	-47	-	dBm
Modulation characteristics @ \triangle flavg, LE 2M	-	497	-	kHz
Modulation characteristics @ \triangle f2max, LE 2M	-	398	-	kHz
Carrier frequency offset, LE 2M	-	-9	-	kHz
In-band emissions @F-F0±3MHz, LE 500K	-	-41.3	-	dBm

Table.7.1 TX Transmitter General Characteristics

In-band emissions @F-F0±>3MHz, LE 500K	-	-42.8	-	dBm
Modulation characteristics @ \triangle f1avg, LE 500K	-	220	-	kHz
Modulation characteristics @ \triangle f2max, LE 500K	-	205	-	kHz
Carrier frequency offset, LE 500K	-	-11.9	-	kHz
Maximum received signal @30.8% PER	-	10	-	dBm

Par	Parameter		Classical	Max	Unit
	Sensitivity @30.8% PER	-	-96	-	dBm
	Maximum received signal @30.8% PER	-	10	-	dBm
	Co-channel C/I	-	8	-	dB
	Image frequency	-	-29	-	dB
1	Adjacent channel to image frequency $@F = F_{image} + 1$	-	-38	-	dB
Μ	Adjacent channel to image frequency @F =Fimage-1	-	-34	-	dB
	Adjacent channel selectivity @ F =F0+1	-	-4	-	dB
	Adjacent channel selectivity @ F =F0-1	-	-3	-	dB
	Adjacent channel selectivity @ $F \ge F0+3$	-	-	-	dB
	Adjacent channel selectivity @ $F \leq F0-3$	-	-39	-	dB
	Sensitivity @30.8% PER	-	-93	~O)	dBm
	Maximum received signal @30.8% PER	-	0	7	dBm
	Co-channel C/I	21	10	-	dB
	Image frequency	0	-27	-	dB
2	Adjacent channel to image frequency $@F = F_{image} + 2$		-39	-	dB
М	Adjacent channel to image frequency $@F = F_{image}-2$	5	-	-	dB
	Adjacent channel selectivity @ F =F0+2	-	-7	-	dB
	Adjacent channel selectivity @ F =F0-2	-	-7	-	dB
	Adjacent channel selectivity @ $F \ge F0+6$	-	-39	-	dB
	Adjacent channel selectivity @ $F \leq F0-6$	-	-39	-	dB
1	Sensitivity @30.8% PER	-	-104	-	dBm
2 5	Maximum received signal @30.8% PER	-	10	-	dBm
K	Co-channel C/I	-	2	-	dB


Table.7.2 RX Transmitter General Characteristics

Doctors of Intelligence & Technology (www.doit.am)

Image frequency	-	-34	-	dB
Adjacent channel to image frequency $@F = F_{image} + 1$	-	-44	-	dB
Adjacent channel to image frequency $@F = F_{image}-1$	-	-37	-	dB
Adjacent channel selectivity @ F =F0+2	-	-40	-	dB
Adjacent channel selectivity @ F =F0-2	-	-42	-	dB
Adjacent channel selectivity @ $F \ge F0+3$	-	-	-	dB
Adjacent channel selectivity @ F \leq F0-3	-	-46	-	dB

8. Recommended Sold Temperature Curve

- (1) Reflow Times <= 2 times (Max.)
- (2) Max Rising Slope: 3°C/sec
- (3) Max Falling Slope: -3°C/sec
- (4) Over 217°C Time: 60~120sec
- (5) Peak Temp:240°C ~250°C



9. Minimum User System

This module can work just at 3.3V voltage condition:




Fig.9.1 Minimum System

Note:

(1) The working voltage for module is DC 3.3V;

(2) The max current from IO of this module is 40mA;

(3) Wi-Fi module is at download mode: IO9 is LOW level, then module reset to power;

(4) Wi-Fi module is connected to RXD of the other MCU, and TXD is connected to RXD of the other MCU.


10. Recommended Layout Design

ESPC3-32 module can be sold on PCB board directly. For the high RF performance for the device, please notice the placement of the module. There are three ways to use the module for Wi-Fi Module with PCB antenna.

Solution 1: optical solution. The Wi-Fi module is placed on the side of the board, and the antennas are all exposed, and there is no metal material around the antenna, including wires, metal casings, weight plates, and the like.

Solution 2: sub-optical solution. The Wi-Fi module is placed on the side of the board, and the antenna below is hollowed out. There is a gap of not less than 5 mm reserved with the PCB, and there is no metal material around the antenna, including wires, metal casings, weight plates, and the like.

Solution 3: The Wi-Fi module is placed on the side of the board, and the PCB area under the antenna is empty, and copper cannot be laid.



11. Peripheral Design Suggestion

Wi-Fi module is already integrated into high-speed GPIO and Peripheral interface, which may be generated the switch noise. If there is a high request for the power consumption and EMI characteristics,

it is suggested to connect a serial 10~100 ohm resistance, which can suppress overshoot when switching power supply, and can smooth signal. At the same time, it also can prevent electrostatic discharge (ESD).

12. Product Handling

12.1 Storage Conditions


The products sealed in moisture barrier bags (MBB) should be stored in a non-condensing atmospheric environment of < 40 °C and 90%RH. The module is rated at the moisture sensitivity level (MSL) of 3. After unpacking, the module must be soldered within 168 hours with the factory conditions 25±5 °C and 60%RH. If the above conditions are not met, the module needs to be baked.


12.2 Electrostatic Discharge (ESD)

- Human body model (HBM): $\pm 2000 \text{ V}$
- Charged-device model (CDM): $\pm 500 \text{ V}$

13. U.FL RF Connector

ESPC3-32 module use U.FL type RF connector for external antenna connection. (IPEX V1.0).





14. Packing Instruction

The product is packed in a tray, as shown in the following figure.

The size of the single box is: $340 \times 360 \times 60$ mm, and 550 pieces module is in the box. And the outer box size is $355 \times 375 \times 325$ mm, including 5 single box which include 2750 pieces module.



Fig.14.1 Module Package

FCC WARNING

FCC Caution: Any changes or modifications not expressly

Approved by the party responsible for compliance could void the user's authority to operate this equipment.

This device complies with Part 15 of the FCC Rules.

Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

This device and its antenna(s) must not be co-located or operating in conjunction with any other antenna or transmitter.

15.105 Information to the user.

(b) For a Class B digital device or peripheral, the instructions furnished the user shall include the following or similar statement, placed in a prominent location in the text of the manual:

Note: This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

-Reorient or relocate the receiving antenna.

-Increase the separation between the equipment and receiver.

-Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.

-Consult the dealer or an experienced radio/TV technician for help.

This equipment complies with FCC radiation exposure limits set forth for an uncontrolled environment. This equipment should be installed and operated with minimum distance 20 cm between the radiator and your body. Radiation Exposure Statement:

This equipment complies with FCC radiation exposure limits set forth for an uncontrolled environment.

This transmitter must not be co-located or operating in conjunction with any other antenna or transmitter.

The availability of some specific channels and/or operational frequency bands are country dependent and are firmware programmed at the factory to match the intended destination. The firmware setting is not accessible by the end user.

The final end product must be labelled in a visible area with the following: "Contains Transmitter Module "2BAGT-YOOAI-T1"