

## **High Speed Current Sensor IC**

#### Datasheet

#### 1. Features and Benefits

- End-of-line programmable sensor
- Selectable analog ratiometric output
- Measurement range from ±15 to ±450mT
- Wideband sensing: DC to 250kHz
- Very short response time (2μs)
- High linearity down to ±0.2% full scale
- Very low thermal drift
  - Offset drift (<5mV)</li>
  - Sensitivity drift (<1%)</li>
- Programmable output clamping levels
- Broken wire detection and diagnostics
- AEC-Q100 Grade 0 Automotive Qualified
- RoHS compliant
- SIP4-VA package
- MSL-1

## 2. Application Examples

- High Voltage Traction Motor Inverter
- 48V Boost Recuperation Inverter
- DCDC Converter
- Smart Battery Junction Boxes
- Smart Fuse Overcurrent Detection

## 3. Description

The MLX91217 is a monolithic Hall-effect sensor which is sensitive to the flux density applied orthogonally to the IC surface. The sensor provides an analog output voltage proportional to the applied magnetic flux density.

The transfer characteristic of the MLX91217 is factory trimmed over temperature, and is programmable (offset, sensitivity, clamping, filtering) during end-of-line customer calibration. The output clamping levels and on-chip filtering

are also programmable as a function of application needs. With the 250kHz bandwidth and fast response time, it is particularly adapted for high-speed applications such as inverters and converters where fast response time due to fast switching is required.

In a typical current sensing application, the sensor is used in combination with a ring shaped soft ferromagnetic core. This core is recommended to be laminated for high bandwidth applications. The MLX91217 is placed in a small air gap and the current conductor — a bus bar or a cable — is passed through the inner part of the ferromagnetic ring. On the one hand the ring concentrates and amplifies the magnetic flux seen by the sensor IC, and at the same time it attenuates external magnetic field disturbances.




Figure 1. Typical Current Sensing Application




Figure 2. General Block Diagram

# **High Speed High Accuracy Conventional Hall Current Sensor IC with Diagnostics**Datasheet



#### **Contents**

1. Features and Benefits	1
2. Application Examples	1
3. Description	1
4. Ordering Information	3
5. Functional Diagram	4
6. Glossary of Terms	4
7. Pin Definitions and Descriptions	4
8. Absolute Maximum Ratings	5
9. General Electrical Specifications	6
10. Magnetic specification	7
11. Analog output specification	7
11.1. Accuracy specifications	7
11.2. Timing specifications	8
12. Self-diagnostic	8
13. Programmable Parameters	9
14. Recommended Application Diagram	10
15. Standard Information	11
16. ESD Precautions	11
17. Packaging Information	12
17.1. Sensor active measurement direction	12
17.2. Package Marking & Hall Plate Position	12
17.3. VA Straight leads (ACA-xxx)	13
17.4. Trim and form type: 90° 2x2x91.3 (h=5.34mm); Bending-STD2 (ACR-xxx)	14
17.5. Trim and form type: 90° 2x2x91.3 (h=3.7mm); Bending-STD3 (ACS-xxx)	15
17.6. Trim and form type: 90° 2x2x91.8 (h=1.68mm); Bending-STD4 (ACT-xxx)	16
17.7. Trim and form type: SMD style TFT4K1 (ACZ-xxx)	17
18. Contact	18
10 Disalaimar	10



Datasheet

## 4. Ordering Information

Product	Temperature	Package	Option Code	Packing Form	Typical Sensitivity
MLX91217	L	VA	ACA - 000	BU/CR	10mV/mT (prog: 5150mV/mT)
MLX91217	L	VA	ACA - 001	BU/CR	15 mV/mT (prog: 5150mV/mT)
MLX91217	L	VA	ACA - 002 <sup>1</sup>	BU/CR	17 mV/mT (prog: 5150mV/mT)
MLX91217	L	VA	ACA - 003	BU/CR	9 mV/mT (prog: 5150mV/mT)
MLX91217	L	VA	ACA - 004	BU/CR	7 mV/mT (prog: 5150mV/mT)
MLX91217	L	VA	ACA - 005	BU/CR	13 mV/mT (prog: 5150mV/mT)

Table 1: Available ordering codes.

#### Legend:

Temperature Code:	L	from -40°C to 150°C ambient temperature				
Package Code:	VA	IP4-VA package, refer to <i>Chapter 17</i> for detailed drawings				
Option Code:	ACx-000	for factory trimmed sensitivity 10mV/mT;				
	ACx-001	for factory trimmed sensitivity 15mV/mT;				
	ACx-002 <sup>1</sup>	for factory trimmed sensitivity 17mV/mT;				
	ACx-003	for factory trimmed sensitivity 9mV/mT;				
	ACx-004	for factory trimmed sensitivity 7mV/mT;				
	ACx-005	for factory trimmed sensitivity 13mV/mT;				
	ACA-xxx	default straight leads (see chapter 17)				
	ACR-xxx	for Trim and Form shape: 90° 2x2x91.3 (h=5.34mm) Bending-STD2 (see chapter 17)				
	ACS-xxx	for Trim and Form shape: 90° 2x2x91.3 (h=3.7mm) Bending-STD3 (see chapter 17)				
	ACT-xxx	for Trim and Form shape: 90° 2x2x91.8 (h=1.68mm) Bending-STD4 (see chapter 17)				
	ACZ-xxx	for Trim and Form shape: SMD style TFT4K1 (see chapter 17)				
Packing Form:	BU	for Bulk,				
	CR	for Carton Reel - Radial taping – available for straight leads only				
	CA	for Carton Reel – Ammopack – available for straight leads only				
	RE	for Plastic Reel – available for selected Trim & Form options only				
Ordering	"MLX91217LVA-	ACA-005-CR"				
Example:						

Melexis is continuously expanding its portfolio to serve our customer's needs. Please contact your local sales representative in case your desired ordering code is not part of the above table.

<sup>&</sup>lt;sup>1</sup> MLX91217-LVA-ACA-002 : customized sensitivity drift, VOQ = 1V



## 5. Functional Diagram




Figure 3: Block Diagram of the MLX91217:

## 6. Glossary of Terms

Terms	Definition
TC	Temperature Coefficient
FS	Full Scale, output referred. Corresponds to 2V excursion around 2.5V VOQ point
T, mT	Tesla, milliTesla = units for the magnetic flux density
G	Gauss = unit for the magnetic flux density [1mT = 10G]
PTC	Programming Through Connector
IMC	Integrated Magnetic Concentrator (IMC-Hall®)
FS	Full scale. If FS=2000mV, 0.4%FS = 8mV

Table 2: Glossary of Terms

## 7. Pin Definitions and Descriptions

Note: MLX91217 is pin-to-pin compatible with MLX91209.

Pin #	Name	Туре	Description
1	VDD	Supply	Supply Voltage
2	OUT	Analog	Current Sensor Output
3	TEST	Digital	Test and Factory Calibration
4	GND	Ground	Supply Voltage




Table 3: Pin definitions and descriptions

For optimal EMC results, it is recommended to connect the TEST pin to the Ground (see section 13).



## 8. Absolute Maximum Ratings

Parameter	Symbol	Value	Unit
Positive Supply Voltage (overvoltage)	$V_{DD}$	+10	V
Reverse Voltage Protection	VS <sub>REV</sub>	-0.3	V
Positive Output Voltage	V <sub>OUT</sub>	+10	V
Output Current	Гоит	±70	mA
Reverse Output Voltage	VO <sub>REV</sub>	-0.3	V
Reverse Output Current	IO <sub>REV</sub>	-50	mA
Operating Ambient Temperature Range	T <sub>A</sub>	-40 to +150	°C
Maximum Junction Temperature	$T_{j,max}$	-55 to +155	°C
Package Thermal Resistance $ \mbox{(junction-to-ambient)} \; \theta_{\text{ja}} \; \mbox{is defined according JEDEC} \\ \mbox{1sOp board} $	$\theta_{ja}$	205	°C
Storage Temperature Range	Ts	-55 to +165	°C
Magnetic Flux Density	B <sub>MAX</sub>	±3	Т
ESD – Human Body Model	ESD <sub>нвм</sub>	2	kV

Table 4: Absolute maximum ratings

Exceeding the absolute maximum ratings may cause permanent damage. Exposure to absolute maximum-rated conditions for extended periods of time may affect device reliability.



## 9. General Electrical Specifications

Operating Parameters  $T_A$  = -40 to 150°C,  $V_{DD}$  = 5V±10%, unless otherwise specified.

Parameter	Symbol	Test Conditions		Тур.	Max.	Units
Nominal Supply Voltage	$V_{DD}$		4.5	5	5.5	V
Supply	$I_{DD}$	No R <sub>load</sub> LOW_POWER_MODE=0 <sup>2</sup> LOW_POWER_MODE=1		12.5 10	15 13	mA mA
Output Impedance	Rout	Vout = 50% Vdd		1	5	Ω
Output Capacitive Load	$C_L$	OUT_MODE=0 OUT_MODE=1	1 10		10 47	nF nF
Output Resistive Load	$R_{Load}$	Output resistive load for high linearity and diagnostic band.	10	25	200	kΩ
Output Short Circuit Current	Ishort	Output shorted permanent to VDD. Output shorted permanent to GND.		Not Destr Not Destr	•	
Linear Output Range	VOLIN	pull-down $\geq$ 10 k $\Omega$	10		90	%Vdd
Diagnostic Band <sup>3</sup>	DIAG	$R_L \ge 10k\Omega$ , $R_L \le 200 k\Omega$ , $V_{DD} = 5V$ DIAG_LEVEL = 0 DIAG_LEVEL = 1	0 96		4 100	%Vdd %Vdd
BrokenGND Output Level <sup>3</sup>		$R_L \ge 10k\Omega$ , $V_{DD} = 5V$	96		100	%Vdd
BrokenVDD Output Level <sup>3</sup>		$R_L \ge 10k\Omega$ , $V_{DD} = 5V$	0		4	%Vdd
Under-voltage detection <sup>3</sup>	$V_{DD\_UVD}$	Detected Voltage (Low to High)	4.0		4.5	V
onder-voltage detection	$V_{DD\_UVH}$	Hysteresis	0.01		0.2	V
Over-voltage detection 1 <sup>3</sup>	$V_{\text{DD\_OVD1}}$	Detected Voltage (Low to High)	6.7		7.4	V
over voltage detection 1	$V_{DD\_OVH1}$	Hysteresis	0.37		0.66	V
Over-voltage detection 2 <sup>3</sup>	$V_{DD\_OVD2}$	Detected Voltage (Low to High)	8.3		9.5	V
	$V_{DD\_OVH2}$	Hysteresis	0.2		0.8	V
	Clamp_lo0	CLAMP_LEVEL=0	5	6	7	%Vdd
	Clamp_hi0	CLAMP_LEVEL=0	92	93	94	%Vdd
	Clamp_lo1	CLAMP_LEVEL=1	5	6	7	%Vdd
Clamped Output Level	Clamp_hi1	CLAMP_LEVEL=1	93	94	95	%Vdd
	Clamp_lo2	CLAMP_LEVEL=2	7	8	9	%Vdd
	Clamp_hi2	CLAMP_LEVEL=2	91	92	93	%Vdd
	Clamp_lo3	CLAMP_LEVEL=3	9	10	11	%Vdd
	Clamp_hi3	CLAMP_LEVEL=3	89	90	91	%Vdd

Table 5: General electrical parameters

<sup>&</sup>lt;sup>2</sup> Default Factory Calibration

<sup>&</sup>lt;sup>3</sup> Please refer to section 12 for more information on self-diagnostic modes.



Datasheet

## 10. Magnetic specification

Operating Parameters  $T_A$  = -40 to 150°C,  $V_{DD}$  = 5V±10%, unless otherwise specified.

Parameter	Symbol	Test Conditions	Min	Тур	Max	Units
Operational Magnetic Field Range	Вор		±15	±130	±450	mT
Linearity Error	NL	Vout in [10%VDD, 90%VDD],  TA = 25°C  LOW_POWER_MODE=0  LOW_POWER_MODE=1			±0.4 ±0.2	%FS %FS
Programmable Sensitivity	S		5	15	150	mV/mT
Sensitivity programming Resolution	Sres	B = B <sub>OP</sub>		0.1		%

Table 6: Magnetic specification

## 11. Analog output specification

#### 11.1. Accuracy specifications

Operating Parameters  $T_A$  = -40 to 150°C,  $V_{DD}$  = 5V±10%, unless otherwise specified.

Parameter	Symbol	Test Conditions	Min	Тур	Max	Units
Thermal Offset Drift	$\Delta^T V_{OQ}$	T <sub>A</sub> = -40 to 125°C T <sub>A</sub> = -40 to 150°C			±5 ±8	mV mV
Thermal Sensitivity Drift <sup>4</sup>	$\Delta^{T}S$	T <sub>A</sub> = -40 to 125°C T <sub>A</sub> = -40 to 150°C			±1.0 ±1.2	%S %S
RMS Output Noise	N <sub>RMS</sub>	Values for 50mV/mT sensitivity Scales with typical sensitivity of Table 1 NOISE_FILTER=0 NOISE_FILTER=1 NOISE_FILTER=2 NOISE_FILTER=3		10 7 5 3		mV <sub>RMS</sub> mV <sub>RMS</sub> mV <sub>RMS</sub>
$V_{\text{OQ}}$ Ratiometry	$\Delta^R V_{OQ}$	$V_{DD}$ = 5V±5%, (for all option codes) $V_{OQ}$ = 20% $V_{DD}$ MLX91217LVA-ACA-002) $V_{OQ}$ = 50% $V_{DD}$ – (all other option codes)			±0.4 ±0.4	%Voq %Voq
Sensitivity Ratiometry	$\Delta^{R}S$	$V_{DD} = 5V \pm 5\%, B = B_{OP}$			±0.4	%S
Clamped output accuracy	CLACC				±1	%Vdd

Table 6: Accuracy specifications – analog parameters

The accuracy specifications are defined for the factory calibrated sensitivity. The achievable accuracy is dependent on the user's end-of-line calibration. Resolution for offset and offset drift calibration is better

\_

<sup>&</sup>lt;sup>4</sup> Except MLX91217-LVA-ACA-002

#### High Speed High Accuracy Conventional Hall Current Sensor IC with Diagnostics



Datasheet

than  $0.02\%V_{DD}$ . Trimming capability is higher than measurement accuracy. End-user calibration can therefore increase the accuracy of the system.

#### 11.2. Timing specifications

Operating Parameters  $T_A = -40$  to 150°C, Vdd = 5V $\pm$ 10%, unless otherwise specified.

Parameter	Symbol	Test Conditions	Min	Тур	Max	Units
Refresh rate	Trr		0.8	1	2	μs
Step Response Time	Tr	C <sub>L</sub> =10nF  NOISE_FILTER=0, LOW_POWER_MODE=0  NOISE_FILTER=0, LOW_POWER_MODE=1  NOISE_FILTER=1, LOW_POWER_MODE=0  NOISE_FILTER=1, LOW_POWER_MODE=1  NOISE_FILTER=2, LOW_POWER_MODE=0  NOISE_FILTER=3, LOW_POWER_MODE=1  NOISE_FILTER=3, LOW_POWER_MODE=0  NOISE_FILTER=3, LOW_POWER_MODE=1		2 3 3 5 4 6 8	3 4 4 6 5 7 9	μs μs μs μs μs μs μs
Power on Delay	$T_{POD}$	Vout =100% of F.S.			1	ms
Ratiometry Cut-off Frequency	F <sub>RAT</sub>			250		Hz

Table 7: Timing specifications of the high-speed analog output

## 12. Self-diagnostic

MLX91217 provides several self-diagnostic features, which prevent the IC from providing erroneous output signal in case of internal or external failure modes.

Error	Effect on Output	Remarks
Calibration data CRC Error	DIAG_LEVEL=0 $\rightarrow$ active pull-down to GND DIAG_LEVEL=1 $\rightarrow$ active pull-up to VDD	at power up and in normal mode
Power-On Delay	Pull-down to GND	1ms max followed by settling
Over-voltage Mode 1	Active pull-down to GND	
Over-voltage Mode 2	DIAG_LEVEL=0 $\rightarrow$ active pull-down to GND DIAG_LEVEL=1 $\rightarrow$ active pull-up to VDD	
Under-voltage Mode	DIAG_LEVEL=0 $\rightarrow$ active pull-down to GND DIAG_LEVEL=1 $\rightarrow$ active pull-up to VDD	Valid with enabled ratiometry (Default: RATIOEN = 1)
Broken OUT	Active pull-down to GND	
Broken GND	Output pulled up to VDD	IC is switched off
Broken VDD	Output pulled down to GND	IC is switched off

Table 8: Description of the self-diagnostic modes in MLX91217

## **High Speed High Accuracy Conventional Hall Current Sensor IC with Diagnostics**Datasheet



13. Programmable Parameters

Customers can re-program the parameters described in the table below by using the PTC-04 hardware and the Product Specific Functions (PSF) libraries provided by Melexis. We recommend using the latest version of the PSF and the firmware, with a communication speed of 10kbps (maximum output capacitor of 47nF). Please contact your sales representative to get access to Melexis SoftDist platform and download the latest software.

Parameter	Bits	Factory Setting	Function
ROUGHGAIN	3	Trimmed	Rough gain trimming
FINEGAIN	10	Trimmed	Fine gain trimming
VOQ	12	Trimmed	Offset trimming
OUT_MODE	1	0	<ul><li>0: low capacitive load (see section 14)</li><li>1: high capacitive load (see section 14)</li></ul>
DIAG_LEVEL	1	0	<ul><li>0: in diagnostic, output is pulled down to GND</li><li>1: in diagnostic, output is pulled up to Vdd</li></ul>
LOW_POWER_MODE	1	0	0: normal mode 1: low power mode with slower response time
CLAMP_LEVEL	2	1	Select clamping level (%VDD) 0: 6%/93%, 1: 6%/94%, 2: 8%/92%, 3: 10%/90%
NOISE FILTER	2	0/15	0: Noise filter: deactivated 1: Noise filter: 120kHz 2: Noise filter: 60kHz 3: Noise filter: 15kHz
CSTID	17	N/A	Customer ID

\_

<sup>&</sup>lt;sup>5</sup> The Noise Filter parameter is set to 1 for MLX91216LDC-ACV-002 IC version. The Noise Filter is deactivated for all other option codes.



## 14. Recommended Application Diagram




Figure 4: Application Diagram with external Pull-Down resistance

Part	Description	Value	Unit
C1	Supply capacitor, EMI, ESD	100	nF
C2	Decoupling, EMI, ESD, OUT_MODE=0	1-10	nF
	Decoupling, EMI, ESD, OUT_MODE=1	8-47	nF
R1	Pull down resistor	10-200	kΩ

Table 7: Resistor and capacitor values

#### High Speed High Accuracy Conventional Hall Current Sensor IC with Diagnostics



Datasheet

#### 15. Standard Information

Our products are classified and qualified regarding soldering technology, solderability and moisture sensitivity level according to standards in place in Semiconductor industry.

#### Reflow Soldering SMD's (Surface Mount Devices)

- IPC/JEDEC J-STD-020
  - Moisture/Reflow Sensitivity Classification for Nonhermetic Solid State Surface Mount Devices (classification reflow profiles according to table 5-2)
- EIA/JEDEC JESD22-A113
  - Preconditioning of Nonhermetic Surface Mount Devices Prior to Reliability Testing (reflow profiles according to table 2)

#### Wave Soldering SMD's (Surface Mount Devices) and THD's (Through Hole Devices)

- EN60749-20
  - Resistance of plastic- encapsulated SMD's to combined effect of moisture and soldering heat
- EIA/JEDEC JESD22-B106 and EN60749-15
   Resistance to soldering temperature for through-hole mounted devices

#### Iron Soldering THD's (Through Hole Devices)

EN60749-15
 Resistance to soldering temperature for through-hole mounted devices

#### Solderability SMD's (Surface Mount Devices) and THD's (Through Hole Devices)

 EIA/JEDEC JESD22-B102 and EN60749-21 Solderability

For further details about test method references and for compliance verification of selected soldering method for product integration, Melexis recommends reviewing on our web site the General Guidelines soldering recommendation. For all soldering technologies deviating from the one mentioned in above document (regarding peak temperature, temperature gradient, temperature profile etc), additional classification and qualification tests have to be agreed upon with Melexis.

For package technology embedding trim and form post-delivery capability, Melexis recommends to consult the dedicated trim&form recommendation application note: <u>lead trimming and forming recommendations.</u>

Melexis is contributing to global environmental conservation by promoting **lead free** solutions. For more information on qualifications of **RoHS** compliant products (RoHS = European directive on the Restriction Of the use of certain Hazardous Substances) please visit the quality page on our website: <a href="http://www.melexis.com/en/quality-environment">http://www.melexis.com/en/quality-environment</a>

#### 16. ESD Precautions

Electronic semiconductor products are sensitive to Electro Static Discharge (ESD). Always observe Electro Static Discharge control procedures whenever handling semiconductor products.



## 17. Packaging Information

#### 17.1. Sensor active measurement direction




Figure 5. VA/SIP 4L Package. Sensor's active measurement direction


## 17.2. Package Marking & Hall Plate Position

# Package marking FRONT SIDE 91217 XXXXXXX ZZ YYWW Line 1: Product ID Line 2: Wafer Lot Number Line 3: IC Revision Line 4: Assembly Date Code (year = yy; week = ww)

Figure 6. VA/SIP 4L (single in-line package) / 18mm lead length - Package Information



## 17.3. VA Straight leads (ACA-xxx)





SYMBOLS	DIMENSIONS IN MILLIMETERS			
3 IMDOL3	MIM	NOM	MAX	
A	3.30	3.38	3.46	
A1	3.63	3.71	3.79	
D	5.08	5.16	5.24	
D1	5.33	5.38	5.43	
E	1.10		1.20	
J	4.10	4.30	4.50	
J1	1.00 REF			
K	0.00		0.15	
K1	0.25	0.30	0.35	
L	17.5	18.0	18.5	
L1	0.48	0.53	0.58	
S	0.24		0.29	
T	0.61		0.66	
b1	0.35		0.48	
b2	0.40		0.60	
С	0.18		0.34	
е	3.76		3.86	
e1	1.22	1.27	1.32	
⊝1	5° REF			
⊕2	45° REF			

- Note:
  1. DIMENSIONS "A" AND "D" DO NOT INCLUDE MOLD FLASH, PROTRUSIONS AND GATE BURRS.
- 2. DIMENSIONS "A1" DOES NOT INCLUDE GATE BURRS BUT INCLUDES MOLD FLASH AT BOTH ENDS.
- 3. MOLD GATE BURRS SHALL NOT EXCEED 0.15 mm MEASURED FROM EDGE OF MOLD FLASH (FLANGE).
- 4. DIMENSION "D1" INCLUDES MOLD FLASH AT BOTH ENDS.
- 5. LEAD PLATING; MATTE TIN PLATING THICKNESS 7.62 15.42 um.



## 17.4. Trim and form type: 90° 2x2x91.3 (h=5.34mm); Bending-STD2 (ACR-xxx)









Datasheet

#### 17.5. Trim and form type: 90° 2x2x91.3 (h=3.7mm); Bending-STD3 (ACS-xxx)







#### 17.6. Trim and form type: 90° 2x2x91.8 (h=1.68mm); Bending-STD4 (ACT-xxx)





## 17.7. Trim and form type: SMD style TFT4K1 (ACZ-xxx)





Parameter				
Dim# 1 [mm]	Dim# 2 [mm]	Dim# 3 [mm]	Dim# 4 [mm]	Dim# 5 [mm]
1.27 +/- 0.10	2.15 +/- 0.25	6.37 +/- 0.33	min. 0.51	0 -0.051/+0.10

## High Speed High Accuracy Conventional Hall Current Sensor IC with Diagnostics



Datasheet

#### 18. Contact

For the latest version of this document, go to our website at www.melexis.com.

For additional information, please contact our Direct Sales team and get help for your specific needs:

Europe, Africa	Telephone: +32 13 67 04 95
	Email: sales_europe@melexis.com
Americas	Telephone: +1 603 223 2362
	Email : sales_usa@melexis.com
Asia	Email: sales_asia@melexis.com

#### 19. Disclaimer

The content of this document is believed to be correct and accurate. However, the content of this document is furnished "as is" for informational use only and no representation, nor warranty is provided by Melexis about its accuracy, nor about the results of its implementation. Melexis assumes no responsibility or liability for any errors or inaccuracies that may appear in this document. Customer will follow the practices contained in this document under its sole responsibility. This documentation is in fact provided without warranty, term, or condition of any kind, either implied or expressed, including but not limited to warranties of merchantability, satisfactory quality, non-infringement, and fitness for purpose. Melexis, its employees and agents and its affiliates' and their employees and agents will not be responsible for any loss, however arising, from the use of, or reliance on this document. Notwithstanding the foregoing, contractual obligations expressly undertaken in writing by Melexis prevail over this disclaimer.

This document is subject to change without notice, and should not be construed as a commitment by Melexis. Therefore, before placing orders or prior to designing the product into a system, users or any third party should obtain the latest version of the relevant information.

Users or any third party must determine the suitability of the product described in this document for its application, including the level of reliability required and determine whether it is fit for a particular purpose.

This document as well as the product here described may be subject to export control regulations. Be aware that export might require a prior authorization from competent authorities. The product is not designed, authorized or warranted to be suitable in applications requiring extended temperature range and/or unusual environmental requirements. High reliability applications, such as medical life-support or life-sustaining equipment or avionics application are specifically excluded by Melexis. The product may not be used for the following applications subject to export control regulations: the development, production, processing, operation, maintenance, storage, recognition or proliferation of:

- 1. chemical, biological or nuclear weapons, or for the development, production, maintenance or storage of missiles for such weapons;
- 2. civil firearms, including spare parts or ammunition for such arms;
- 3. defense related products, or other material for military use or for law enforcement;
- 4. any applications that, alone or in combination with other goods, substances or organisms could cause serious harm to persons or goods and that can be used as a means of violence in an armed conflict or any similar violent situation.

No license nor any other right or interest is granted to any of Melexis' or third party's intellectual property rights.

If this document is marked "restricted" or with similar words, or if in any case the content of this document is to be reasonably understood as being confidential, the recipient of this document shall not communicate, nor disclose to any third party, any part of the document without Melexis' express written consent. The recipient shall take all necessary measures to apply and preserve the confidential character of the document. In particular, the recipient shall (i) hold document in confidence with at least the same degree of care by which it maintains the confidentiality of its own proprietary and confidential information, but no less than reasonable care; (ii) restrict the disclosure of the document solely to its employees, agents, professional advisors and contractors for the purpose for which this document was received, on a strictly need to know basis and providing that such persons to whom the document is disclosed are bound by confidentiality terms substantially similar to those in this disclaimer; (iii) use the document only in connection with the purpose for which this document was received, and reproduce document only to the extent necessary for such purposes; (iv) not use the document for commercial purposes or to the detriment of Melexis or its customers. The confidentiality obligations set forth in this disclaimer will have indefinite duration and in any case they will be effective for no less than 10 years from the receipt of this document.

This disclaimer will be governed by and construed in accordance with Belgian law and any disputes relating to this disclaimer will be subject to the exclusive jurisdiction of the courts of Brussels, Belgium.

The invalidity or ineffectiveness of any of the provisions of this disclaimer does not affect the validity or effectiveness of the other provisions. The previous versions of this document are repealed.

Melexis © - No part of this document may be reproduced without the prior written consent of Melexis. (2020)

IATF 16949 and ISO 14001 Certified