

#### **TECHNICAL DATA SHEET**

Description: 2X LTE, 2XWiFi Vehicular

Antenna

**PART NUMBER: LPMB40X** 



#### Features:

- 2xMiMo 698-960/1710-2690MHz
- WiFi 2400-2500/4900-5900MHz
- Size 145x135x25mm
- Adhesive mount on plastic and glass fiber surfaces
- Mounting accessory for metallic surfaces



## **Applications:**

- · Vehicle mount multiband antenna
- · High Speed LTE data and WiFi
- Fleet management
- Utility Vans (Gas, Water, Electricity)

All dimensions are in mm / inches

Issue: 1922

In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION

This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other state and federal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden. For more information:

Pulse Worldwide Headquarters 15255 Innovation Drive #100 San Diego, CA 92128 USA Tel:1-858-674-8100 Pulse/Larsen Antennas 18110 SE 34th St Bldg 2 Suite 250 Vancouver, WA 98683 USA Tel: 1-360-944-7551 Europe Headquarters Pulse GmbH & Do, KG Zeppelinstrasse 15 Herrenberg, Germany Tel: 49 7032 7806 0 Pulse (Suzhou) Wireless Products Co, Inc. 99 Huo Ju Road(#29 Bldg,4<sup>th</sup> Phase Suzhou New District Jiangsu Province, Suzhou 215009 PR China Tel: 86 512 6807 9998



Description: 2X LTE, 2XWiFi Vehicular

**Antenna** 

**PART NUMBER: LPMB40X** 

# Series: Low Profile MB

#### **ELECTRICAL SPECIFICATIONS**

Frequency	698-960/1710-2690 MHz		
Nominal Impedance	50 Ω		
VSWR(*)	2.5 Max		
A F((' ' (000 000 ALL ) (**)	04.0/		

Average Efficiency(698-960MHz)(\*\*) 64 %

Average Efficiency(1710-2690MHz) (\*\*) 57 %

Peak Gain(698-960MHz) (\*\*) 2.0 dBi

Peak Gain(1710-2690MHz) (\*\*) 4.4 dBi

#### **WIFI Antenna**

LTE Antenna

Frequency	2400-2500/4900-5900 MHz
Nominal Impedance	50 Ω
VSWR (*)	2 Max
Average Efficiency(2400-2500MHz) (**)	63 %
Average Efficiency(4900-5900MHz) (**)	73 %
Peak Gain(2400-2500MHz) (**)	3.5 dBi
Peak Gain(4900-5900MHz) (**)	4.7 dBi

<sup>\*</sup> Measured on 500mm ground plane with LMR195 3m cable

<sup>\*\*</sup> Measured on 500mm ground plane with LMR195 320mm cable



#### **TECHNICAL DATA SHEET**

Description: 2X LTE, 2XWiFi Vehicular

Antenna

**PART NUMBER: LPMB40X** 

## **MECHANICAL SPECIFICATIONS**

Antenna P/N	Antenna Color / Material	Weight	Cable and Connector type		Cable length	Mounting System
		607g	LTE-1	LMR195* SMA Male	3Meters / 118.11Inchs	Adhesive Tape - 3mmThick 3M VHB 4959
L DN 4D 404			LTE-2	LMR195* SMA Male		
LPMB401			WiFi-1	LMR195* RP-SMA Male		
			WiFi-2	LMR195* RP-SMA Male		
	SABIC PC943, Black		LTE-1	LMR195* SMA Male		
LPMB405	402 -	LTE-2	LMR195* SMA Male	2Meters /		
		492g	WiFi-1	LMR195* RP-SMA Male	78.74Inchs	
			W/IFI-/	LMR195* RP-SMA Male		

<sup>\*</sup> Or Equivalent

#### **ENVIRONMENTAL SPECIFICATIONS**

Operating Temperature  $-40 \sim +85^{\circ}$  C Ingress Protection IP67 RoHS Compliant Yes




Description: 2X LTE, 2XWiFi Vehicular

**Antenna** 

**PART NUMBER: LPMB40X** 

# Series: Low Profile MB

#### **MECHANICAL DRAWING**



LPMB401	P.N.	CABLE	CABLE LENGTH	CONNECTOR
1 LTE-1 Cable Assy	125-01188.001	L MD 40E	3 Meters 9.84FT/118.11"	SMA Male
2. WiFi-1 Cable Assy	125-01190.001			RP-SMA Male
3. WiFi-2 Cable Assy	125-01191.001	LMK-195		RP-SMA Male
4. LTE-2 Cable Assy	125-01189.001			SMA Male

· OR EQUIVALENT

In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION






Description: 2X LTE, 2XWiFi Vehicular

**Antenna** 

**PART NUMBER: LPMB40X** 

# Series: Low Profile MB

#### **MECHANICAL DRAWING**






Description: 2X LTE, 2XWiFi Vehicular

**Antenna** 

**PART NUMBER: LPMB40X** 

# **Series:** Low Profile MB

#### **MECHANICAL DRAWING**



LPMB405	5 P.N.		CABLE LENGTH	CONNECTOR
1 LTE-1 Cable Assy	125-00436.001	LMR-195 <sup>,</sup> 2 Meters [78.74 <sup>-</sup> ]	2 Meters	SMA Male
2 WiFi-1 Cable Assy	125-00438.001			RP-SMA Male
3. WIFT-2 Cable Assy	125-00439.001		RP-SMA Male	
4. LTE-2 Cable Assy	125-00437.001			SMA Male

· OR EQUIVALENT






Description: 2X LTE, 2XWiFi Vehicular

**Antenna** 

**PART NUMBER: LPMB40X** 

## **Series:** Low Profile MB

#### **MECHANICAL DRAWING**





#### **TECHNICAL DATA SHEET**

Description: 2X LTE, 2XWiFi Vehicular

**Antenna** 

**PART NUMBER: LPMB40X** 

#### **TEST SETUP**

Below performance test in two situation

Situation 1. Test in free space.

Situation 2. Test on 1 inch bracket with \$600mm (19.7inch) ground.

#### Situation 1

Free space

#### Situation 2



**Ground plane φ** =500mm(19.7inch) Bracket height=1inch



#### **TECHNICAL DATA SHEET**

Description: 2X LTE, 2XWiFi Vehicular

**Antenna** 


**PART NUMBER: LPMB40X** 

#### **CHARTS**

# Situation 1: Performance in free space



## LTE 1 & LTE 2 VSWR



Note: Measured with 3m cable







#### **TECHNICAL DATA SHEET**


Description: 2X LTE, 2XWiFi Vehicular

**Antenna** 


**PART NUMBER: LPMB40X** 

#### **CHARTS**

#### WiFi1 & WiFi2 VSWR



#### **Isolation**



Note: Measured with 3m cable







#### **TECHNICAL DATA SHEET**


Description: 2X LTE, 2XWiFi Vehicular

**Antenna** 


**PART NUMBER: LPMB40X** 

## CHARTS

#### LTE 1 and LTE2 Efficiency



## WiFi 1 and WiFi 2 Efficiency



Note: Measured with 320mm cable

Issue: 1922



#### **TECHNICAL DATA SHEET**


Description: 2X LTE, 2XWiFi Vehicular

**Antenna** 


**PART NUMBER: LPMB40X** 

## **CHARTS**

#### LTE 1 and LTE2 Peak Gain



#### WiFi 1 and WiFi 2 Peak Gain



Note: Measured with 320mm cable






Description: 2X LTE, 2XWiFi Vehicular

**Antenna** 

**PART NUMBER: LPMB40X** 


Series: Low Profile MB

#### **CHARTS**



#### **Gain Plots LTE 1**

#### **Gain Plots LTE 1**



**Gain Plots LTE 1** 

Issue: 1922




**Description**: 2X LTE, 2XWiFi Vehicular


**Antenna** 

**PART NUMBER: LPMB40X** 

Series: Low Profile MB

#### **CHARTS**










Description: 2X LTE, 2XWiFi Vehicular

**Antenna** 

**PART NUMBER: LPMB40X** 


Series: Low Profile MB

#### **CHARTS**



#### **Gain Plots LTE 2**

#### **Gain Plots LTE 2**



**Gain Plots LTE 2** 

Issue: 1922




Description: 2X LTE, 2XWiFi Vehicular

**Antenna** 

**PART NUMBER: LPMB40X** 


## **Series:** Low Profile MB

#### **CHARTS**



**Gain Plots LTE 2** 

#### **Gain Plots LTE 2**



**Gain Plots LTE 2** 






Description: 2X LTE, 2XWiFi Vehicular

Antenna

PART NUMBER: LPMB40X


**Series:** Low Profile MB

#### **CHARTS**



**Gain Plots WiFi 1** 

Gain Plots WiFi 1








Description: 2X LTE, 2XWiFi Vehicular

Antenna


PART NUMBER: LPMB40X

**Series:** Low Profile MB

#### **CHARTS**



#### Gain Plots WiFi 1






Description: 2X LTE, 2XWiFi Vehicular

Antenna

PART NUMBER: LPMB40X


**Series:** Low Profile MB

#### **CHARTS**



#### Gain Plots WiFi 2

#### **Gain Plots WiFi 2**



**Gain Plots WiFi 2** 




Description: 2X LTE, 2XWiFi Vehicular

Antenna


PART NUMBER: LPMB40X

**Series:** Low Profile MB

#### **CHARTS**



Gain Plots WiFi 2



Gain Plots WiFi 2



#### **TECHNICAL DATA SHEET**


Description: 2X LTE, 2XWiFi Vehicular

**Antenna** 


**PART NUMBER: LPMB40X** 

## CHARTS

# Situation 2: Performance on 1 inch bracket with φ500mm(19.7inch) ground



## LTE 1& LTE 2 VSWR



Note: Measured on 500mm ground plane with 3m cable







#### **TECHNICAL DATA SHEET**


Description: 2X LTE, 2XWiFi Vehicular

**Antenna** 


**PART NUMBER: LPMB40X** 

## **CHARTS**

#### WiFi 1& WiFi 2 VSWR



#### **Isolation**



Note: Measured on 500mm ground plane with 3m cable







#### TECHNICAL DATA SHEET


Description: 2X LTE, 2XWiFi Vehicular

**Antenna** 


**PART NUMBER: LPMB40X** 

## LTE 1 and LTE2 Efficiency

**CHARTS** 



## WiFi 1 and WiFi 2 Efficiency



Note: Measured on 500mm ground plane with 322mm cable





#### **TECHNICAL DATA SHEET**


Description: 2X LTE, 2XWiFi Vehicular

**Antenna** 


**PART NUMBER: LPMB40X** 

**CHARTS** 

### LTE 1 and LTE2 Peak Gain



#### WiFi 1 and WiFi 2 Peak Gain



Note: Measured on 500mm ground plane with 322mm cable






Description: 2X LTE, 2XWiFi Vehicular


**Antenna** 

**PART NUMBER: LPMB40X** 

Series: Low Profile MB

#### **CHARTS**








**Description**: 2X LTE, 2XWiFi Vehicular


**Antenna** 

**PART NUMBER: LPMB40X** 

Series: Low Profile MB

#### **CHARTS**





**Gain Plots LTE 1** 






Description: 2X LTE, 2XWiFi Vehicular

**Antenna** 

**PART NUMBER: LPMB40X** 


Series: Low Profile MB

#### **CHARTS**



#### **Gain Plots LTE 2**

#### **Gain Plots LTE 2**



**Gain Plots LTE 2** 

Issue: 1922




Description: 2X LTE, 2XWiFi Vehicular

Antenna


PART NUMBER: LPMB40X

**Series:** Low Profile MB

#### **CHARTS**



### Gain Plots LTE 2



**Gain Plots LTE 2** 

Gain (dBi)




Description: 2X LTE, 2XWiFi Vehicular

Antenna


PART NUMBER: LPMB40X

**Series:** Low Profile MB

#### **CHARTS**







**Gain Plots WiFi 1** 

Issue: 1922

Gain (dBi)




Description: 2X LTE, 2XWiFi Vehicular

**Antenna** 

**PART NUMBER: LPMB40X** 


Series: Low Profile MB

#### **CHARTS**



### **Gain Plots WiFi 1**

#### **Gain Plots WiFi 1**








Description: 2X LTE, 2XWiFi Vehicular

Antenna


PART NUMBER: LPMB40X

**Series:** Low Profile MB

#### **CHARTS**



**Gain Plots WiFi 2** 



Gain Plots WiFi 2




**Description**: 2X LTE, 2XWiFi Vehicular

**Antenna** 

**PART NUMBER: LPMB40X** 


Series: Low Profile MB

#### **CHARTS**



#### **Gain Plots WiFi 2**

#### **Gain Plots WiFi 2**



Gain Plots WiFi 2



Gain (dBi)



Description: 2X LTE, 2XWiFi Vehicular

Antenna

PART NUMBER: LPMB40X

Series: Low Profile MB


#### **PACKAGING**

- Each antenna packed in a plastic bag
- 18 bags(TBD) of antennas packed in a cardboard box.
- 1 label on each box with qty, part number, date code.

#### **ASSEMBLY**

Option 1, Apply to the surface of the glass fiber or plastic material, the antenna could

be adhered on the surface directly.





#### TECHNICAL DATA SHEET

Description: 2X LTE, 2XWiFi Vehicular


**Antenna** 

**PART NUMBER: LPMB40X** 

## **ASSEMBLY**

Option 2, Apply to the surface of the Iron metals like normal steel/iron, a bracket(GPSLPMM) is needed to elevate the antenna 1" for the optimum RF performance

Firstly, The antenna adhered on a magnetic bracket by the adhesive tape, then the whole assemble could "stick" on the magnetic metals by magnets, and also could be removed from the metals easily.



In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION

34



#### **TECHNICAL DATA SHEET**

Description: 2X LTE, 2XWiFi Vehicular

**Antenna** 


**PART NUMBER: LPMB40X** 

#### **ASSEMBLY**

Option 3, Apply to the surface of the non-iron metals like aluminum, a bracket(GPSLPAM) is needed to elevate the antenna 1" for the optimum RF performance

Firstly, the antenna adhered on a bracket by the adhesive tape,

then the whole assemble could adhere on the aluminum by the 3MVHB adhesive tape



Issue: 1922
In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION