



# RP173x Series

## 11 V Input 150 mA LDO

No. EA-256-230802

### OUTLINE

The RP173x is a voltage regulator featuring 150 mA output and low supply current of Typ. 2.0  $\mu$ A. It consists of a voltage reference unit, an error amplifier, a resistor-net for voltage setting, a current limit circuit, a chip enable circuit and a Reverse Current Protection Circuit. RP173x is suitable for the power source such as the equipment being in the standby-mode. The A version with CE input pin has reduced CE pull-up resistance to make its supply current ultra low.

The RP173x has Max.11 V Input voltage and is applicable to the portable communication equipment that requires the 2-cell Li-ion battery. Also it is applicable to the non-portable communication equipments. As the RP173x includes Reverse Current Protection Circuit, there is little leakage current, if it is used as back-up circuit.

Packages are available in SOT-23-5, SC-88A, and 1-mm square DFN(PL)1010-4 packages. High density mounting of the ICs on boards is possible.

### FEATURES

- Output Current ..... Typ. 150 mA
- Supply Current ..... Typ. 2.0  $\mu$ A
- Standby Current ..... Typ. 0.2  $\mu$ A
- Dropout Voltage ..... Typ. 0.13 V ( $I_{OUT} = 30$  mA,  $V_{OUT} = 3.0$  V)  
Typ. 0.90 V ( $I_{OUT} = 150$  mA,  $V_{OUT} = 3.0$  V)
- Output Voltage Accuracy .....  $\pm 1.0\%$  ( $1.5$  V  $< V_{OUT} \leq 5.5$  V,  $T_a = 25^\circ$ C)
- Line Regulation ..... Typ. 0.02%/V
- Packages ..... DFN(PL)1010-4, SC-88A, SOT-23-5
- Input Voltage Range ..... 2.5 V to Set  $V_{OUT} + 6.5$  V (Max. 11 V)
- Output Voltage Range ..... 1.2 V to 5.5 V (0.1 V step)
- Built-in Reverse Current Protection Circuit
- Short Current Limit ..... Typ. 45 mA
- Built-in Peak Current Limit Circuit
- Output capacitors ..... 0.1  $\mu$ F or more

### APPLICATIONS

- Power source for portable communication equipments.
- Power source for battery-powered equipments.
- Power source for electrical appliances such as cameras, VSRs and camcorders.
- Power source for digital home appliances.

## SELECTION GUIDE

The output voltage, the auto-discharge function<sup>(1)</sup>, and the package for the ICs are user-selectable options.

### Selection Guide

| Product Name     | Package       | Quantity per Reel | Pb Free | Halogen Free |
|------------------|---------------|-------------------|---------|--------------|
| RP173Kxx1*-TR    | DFN(PL)1010-4 | 10,000 pcs        | Yes     | Yes          |
| RP173Qxx2*-TR-FE | SC-88A        | 3,000 pcs         | Yes     | Yes          |
| RP173Nxx1*-TR-FE | SOT-23-5      | 3,000 pcs         | Yes     | Yes          |


xx: The output voltage can be designated in the range of 1.2 V (12) to 5.5 V (55) in 0.1 V step.

\* : The auto discharge function at off state are options as follows.


- (A) "L" active, without auto discharge function at off state (Pull-up resistance is not built-in)
- (B) "H" active, without auto discharge function at off state
- (D) "H" active, with auto discharge function at off state

<sup>(1)</sup> Auto-discharge function quickly lowers the output voltage to 0 V, when the chip enable signal is switched from the active mode to the standby mode, by releasing the electrical charge accumulated in the external capacitor.

## BLOCK DIAGRAMS



## PIN DESCRIPTIONS



### RP173K Pin Descriptions

| Pin No. | Symbol               | Description     |
|---------|----------------------|-----------------|
| 1       | $V_{OUT}$            | Output Pin      |
| 2       | GND                  | Ground Pin      |
| 3       | $\overline{CE} / CE$ | Chip Enable Pin |
| 4       | $V_{DD}$             | Input Pin       |

### RP173Q Pin Descriptions

| Pin No.          | Symbol               | Description     |
|------------------|----------------------|-----------------|
| 1                | $\overline{CE} / CE$ | Chip Enable Pin |
| 2 <sup>(2)</sup> | NC                   | No Connection   |
| 3                | GND                  | Ground Pin      |
| 4                | $V_{OUT}$            | Output Pin      |
| 5                | $V_{DD}$             | Input Pin       |

### RP173N Pin Descriptions

| Pin No. | Symbol               | Description     |
|---------|----------------------|-----------------|
| 1       | $V_{DD}$             | Input Pin       |
| 2       | GND                  | Ground Pin      |
| 3       | $\overline{CE} / CE$ | Chip Enable Pin |
| 4       | NC                   | No Connection   |
| 5       | $V_{OUT}$            | Output Pin      |

<sup>(1)</sup> The tab on the bottom of the package enhances thermal performance and is electrically connected to GND (substrate level). It is recommended that the tab be connected to the ground plane on the board, or otherwise be left floating.

<sup>(2)</sup> Pin No. 2 is connected to the bottom of the IC. It is recommended that the pin be connected to the ground plane on the board, or otherwise be left floating so that there is no contact with other potentials.

## ABSOLUTE MAXIMUM RATINGS

### Absolute Maximum Ratings

| Symbol           | Item                             |               | Rating                            | Unit |    |
|------------------|----------------------------------|---------------|-----------------------------------|------|----|
| V <sub>IN</sub>  | Input Voltage                    |               | 12                                | V    |    |
| V <sub>CE</sub>  | Input Voltage (CE pin)           |               | 12                                | V    |    |
| V <sub>OUT</sub> | Output Voltage                   |               | -0.3 to 6.0                       | V    |    |
| I <sub>OUT</sub> | Output Current                   |               | 165                               | mA   |    |
| P <sub>D</sub>   | Power Dissipation <sup>(1)</sup> | DFN(PL)1010-4 | JEDEC STD. 51-7 Test Land Pattern | 800  | mW |
|                  |                                  | SC-88A        | Standard Test Land Pattern        | 380  |    |
|                  |                                  | SOT-23-5      | JEDEC STD. 51-7 Test Land Pattern | 660  |    |
| T <sub>j</sub>   | Junction Temperature Range       |               | -40 to 125                        | °C   |    |
| T <sub>stg</sub> | Storage Temperature Range        |               | -55 to 125                        | °C   |    |

### ABSOLUTE MAXIMUM RATINGS

Electronic and mechanical stress momentarily exceeded absolute maximum ratings may cause permanent damage and may degrade the lifetime and safety for both device and system using the device in the field. The functional operation at or over these absolute maximum ratings is not assured.

## RECOMMENDED OPERATING CONDITIONS

### Recommended Operating Conditions

| Symbol          | Item                        | Rating                     | Unit |
|-----------------|-----------------------------|----------------------------|------|
| V <sub>IN</sub> | Input Voltage               | 2.5 to 11.0 <sup>(2)</sup> | V    |
| T <sub>a</sub>  | Operating Temperature Range | -40 to 85                  | °C   |

### RECOMMENDED OPERATING CONDITIONS

All of electronic equipment should be designed that the mounted semiconductor devices operate within the recommended operating conditions. The semiconductor devices cannot operate normally over the recommended operating conditions, even if they are used over such conditions by momentary electronic noise or surge. And the semiconductor devices may receive serious damage when they continue to operate over the recommended operating conditions.

<sup>(1)</sup> Refer to *POWER DISSIPATION* for detailed information.

<sup>(2)</sup> V<sub>SET</sub> + 6.5 V ≤ 11.0 V

## ELECTRICAL CHARACTERISTICS

Unless otherwise noted,  $V_{IN} = \text{Set } V_{OUT} + 1.0 \text{ V}$ ,  $I_{OUT} = 1 \text{ mA}$ ,  $C_{IN} = C_{OUT} = 0.1 \mu\text{F}$ .

The specifications surrounded by   are guaranteed by design engineering at  $-40^\circ\text{C} \leq T_a \leq 85^\circ\text{C}$ .

RP173xxxxA

( $T_a = 25^\circ\text{C}$ )

| Symbol                          | Item   | Conditions  | Min.  | Typ.   | Max.   | Unit   |    |
|---------------------------------|--|---|---|--|--|--|----|
| $V_{OUT}$                       | Output Voltage   | $T_a = 25^\circ\text{C}$  | $V_{OUT} > 1.5 \text{ V}$   | x0.99  |  | x1.01  | V  |
|                                 |  |   | $V_{OUT} \leq 1.5 \text{ V}$                                      | -15  |  | 15   | mV |
|                                 |  | $-40^\circ\text{C} \leq T_a \leq 85^\circ\text{C}$  | $V_{OUT} > 1.5 \text{ V}$   | <span style="border: 1px solid black; padding: 0 2px;">x0.982</span> |  | <span style="border: 1px solid black; padding: 0 2px;">x1.018</span> | V  |
|                                 |  |   | $V_{OUT} \leq 1.5 \text{ V}$                                      | <span style="border: 1px solid black; padding: 0 2px;">-28</span>    |  | <span style="border: 1px solid black; padding: 0 2px;">27</span>     | mV |
| $I_{OUT}$                       | Output Current   |   | <span style="border: 1px solid black; padding: 0 2px;">150</span> |  |  | mA   |    |
| $\Delta V_{OUT}/\Delta I_{OUT}$ | Load Regulation  | $0.1 \text{ mA} \leq I_{OUT} \leq 150 \text{ mA}$   | <span style="border: 1px solid black; padding: 0 2px;">-30</span> | -3   | <span style="border: 1px solid black; padding: 0 2px;">35</span>                         | mV   |    |
| $V_{DIF}$                       | Dropout Voltage  | $I_{OUT} = 150 \text{ mA}$  | Refer to the <i>PRODUCT-SPECIFIC ELECTRICAL CHARACTERISTICS</i>   |  |  |  |    |
| $I_{SS}$                        | Supply Current   | $I_{OUT} = 0 \text{ mA}$  |   | 2.0  | <span style="border: 1px solid black; padding: 0 2px;">3.7</span>                        | $\mu\text{A}$  |    |
| $I_{standby}$                   | Standby Current  | $V_{IN} = V_{IN} (\text{Max.})$<br>$V_{CE} = V_{IN}$  |   | 0.2  | 0.6  | $\mu\text{A}$  |    |
| $\Delta V_{OUT}/\Delta V_{IN}$  | Load Regulation  | Set $V_{OUT} + 0.5 \text{ V} \leq V_{IN} \leq V_{IN} (\text{Max.})$<br>When $V_{OUT} \leq 2.0 \text{ V}$ ,<br>$2.5 \text{ V} \leq V_{IN} \leq V_{IN} (\text{Max.})$ |   | 0.02   | <span style="border: 1px solid black; padding: 0 2px;">0.20</span>                       | %/V  |    |
| RR                              | Ripple Rejection   | $f = 1 \text{ kHz}$ ,<br>Ripple $0.2 \text{ V}_{p-p}$ , $I_{OUT} = 10 \text{ mA}$<br>*When $V_{OUT} < 2.0 \text{ V}$ , $V_{IN} = 3.0 \text{ V}$                     |   | 30   |  | dB   |    |
| $V_{IN}$                        | Input Voltage  | $1.2 \leq V_{OUT} < 4.5$  | <span style="border: 1px solid black; padding: 0 2px;">2.5</span> |  | <span style="border: 1px solid black; padding: 0 2px;"><math>V_{SET} + 6.5</math></span> | V  |    |
|                                 |  | $4.5 \leq V_{OUT} \leq 5.5$   | <span style="border: 1px solid black; padding: 0 2px;">2.5</span> |  | <span style="border: 1px solid black; padding: 0 2px;">11</span>                         |  |    |
| $I_{SC}$                        | Short Current Limit Circuit  | $V_{OUT} = 0 \text{ V}$   |   | 45   |  | mA   |    |
| $V_{CEH}$                       | $\overline{\text{CE}}$ Input Voltage "H"                                       |   | <span style="border: 1px solid black; padding: 0 2px;">1.7</span> |  |  | V  |    |
| $V_{CEL}$                       | $\overline{\text{CE}}$ Input Voltage "L"                                       |   |   |  | <span style="border: 1px solid black; padding: 0 2px;">0.8</span>                        | V  |    |
| $I_{REV}$                       | Reverse Current  | $0 \leq V_{IN} \leq 11.0 \text{ V}$ , $V_{OUT} \geq 1.5 \text{ V}$  |   | 0  | 0.16   | $\mu\text{A}$  |    |
| $V_{REV\_DET}^{(1)}$            | Reverse Current Protection Mode Detection Offset, $V_{REV} = V_{DD} - V_{OUT}$ | $0 \leq V_{IN} \leq 11.0 \text{ V}$ , $V_{OUT} \geq 1.5 \text{ V}$  |   | 55   | <span style="border: 1px solid black; padding: 0 2px;">100</span>                        | mV   |    |
| $V_{REV\_REL}^{(1)}$            | Reverse Current Protection Mode Release Offset                                 | $0 \leq V_{IN} \leq 11.0 \text{ V}$ , $V_{OUT} \geq 1.5 \text{ V}$  |   | 70   | <span style="border: 1px solid black; padding: 0 2px;">120</span>                        | mV   |    |

All of units are tested and specified under the pulse load conditions such that  $T_j \approx T_a = 25^\circ\text{C}$  except for Ripple Rejection.

<sup>(1)</sup> The operation coverage of the Reverse Current Protection Circuit is  $V_{OUT} \geq 1.5 \text{ V}$ . However, under the condition of  $V_{IN} = V_{OUT} = 0 \text{ V}$ , always the Reverse Current Protection Circuit is operating.

Unless otherwise noted,  $V_{IN} = \text{Set } V_{OUT} + 1.0 \text{ V}$ ,  $I_{OUT} = 1 \text{ mA}$ ,  $C_{IN} = C_{OUT} = 0.1 \mu\text{F}$ .

The specifications surrounded by   are guaranteed by design engineering at  $-40^\circ\text{C} \leq T_a \leq 85^\circ\text{C}$ .

**RP173xxxxB/D**

( $T_a = 25^\circ\text{C}$ )

| Symbol                          | Item   | Conditions  | Min.  | Typ.   | Max.   | Unit   |    |
|---------------------------------|--|---|---|--|--|--|----|
| $V_{OUT}$                       | Output Voltage   | $T_a = 25^\circ\text{C}$  | $V_{OUT} > 1.5 \text{ V}$   | x0.99  |  | x1.01  | V  |
|                                 |  |   | $V_{OUT} \leq 1.5 \text{ V}$                                      | -15  |  | 15   | mV |
|                                 |  | $-40^\circ\text{C} \leq T_a \leq 85^\circ\text{C}$  | $V_{OUT} > 1.5 \text{ V}$   | <span style="border: 1px solid black; padding: 0 2px;">x0.982</span> |  | <span style="border: 1px solid black; padding: 0 2px;">x1.018</span> | V  |
|                                 |  |   | $V_{OUT} \leq 1.5 \text{ V}$                                      | <span style="border: 1px solid black; padding: 0 2px;">-28</span>    |  | <span style="border: 1px solid black; padding: 0 2px;">27</span>     | mV |
| $I_{OUT}$                       | Output Current   |   | <span style="border: 1px solid black; padding: 0 2px;">150</span> |  |  | mA   |    |
| $\Delta V_{OUT}/\Delta I_{OUT}$ | Load Regulation  | $0.1 \text{ mA} \leq I_{OUT} \leq 150 \text{ mA}$   | <span style="border: 1px solid black; padding: 0 2px;">-30</span> | -3   | <span style="border: 1px solid black; padding: 0 2px;">35</span>   | mV   |    |
| $V_{DIF}$                       | Dropout Voltage  | $I_{OUT} = 150 \text{ mA}$  | Refer to the <i>PRODUCT-SPECIFIC ELECTRICAL CHARACTERISTICS</i>   |  |  |  |    |
| $I_{SS}$                        | Supply Current   | $I_{OUT} = 0 \text{ mA}$  |   | 2.0  | <span style="border: 1px solid black; padding: 0 2px;">3.7</span>  | $\mu\text{A}$  |    |
| $I_{standby}$                   | Standby Current  | $V_{IN} = V_{IN} (\text{Max.})$<br>$V_{CE} = 0 \text{ V}$   |   | 0.2  | 0.6  | $\mu\text{A}$  |    |
| $\Delta V_{OUT}/\Delta V_{IN}$  | Load Regulation  | Set $V_{OUT} + 0.5 \text{ V} \leq V_{IN} \leq V_{IN} (\text{Max.})$<br>When $V_{OUT} \leq 2.0 \text{ V}$ ,<br>$2.5 \text{ V} \leq V_{IN} \leq V_{IN} (\text{Max.})$ |   | 0.02   | <span style="border: 1px solid black; padding: 0 2px;">0.20</span> | %/V  |    |
| RR                              | Ripple Rejection   | $f = 1\text{kHz}$ ,<br>Ripple $0.2 \text{ V}_{p-p}$ , $I_{OUT} = 10 \text{ mA}$<br>*When $V_{OUT} < 2.0 \text{ V}$ , $V_{IN} = 3.0 \text{ V}$                       |   | 30   |  | dB   |    |
| $V_{IN}$                        | Input Voltage  | $1.2 \leq V_{OUT} < 4.5$  | <span style="border: 1px solid black; padding: 0 2px;">2.5</span> |  | $V_{SET} + 6.5$  | V  |    |
|                                 |  | $4.5 \leq V_{OUT} \leq 5.5$   | <span style="border: 1px solid black; padding: 0 2px;">2.5</span> |  | <span style="border: 1px solid black; padding: 0 2px;">11</span>   |  |    |
| $I_{SC}$                        | Short Current Limit Circuit  | $V_{OUT} = 0 \text{ V}$   |   | 45   |  | mA   |    |
| $I_{PD}$                        | CE Pull-down Current   |   |   | 0.30   | <span style="border: 1px solid black; padding: 0 2px;">0.90</span> | $\mu\text{A}$  |    |
| $V_{CEH}$                       | CE Input Voltage "H"   |   | <span style="border: 1px solid black; padding: 0 2px;">1.7</span> |  |  | V  |    |
| $V_{CEL}$                       | CE Input Voltage "L"   |   |   |  | <span style="border: 1px solid black; padding: 0 2px;">0.8</span>  | V  |    |
| $I_{REV}$                       | Reverse Current  | $0 \leq V_{IN} \leq 11.0 \text{ V}$ , $V_{OUT} \geq 1.5 \text{ V}$  |   | 0  | 0.16   | $\mu\text{A}$  |    |
| $V_{REV\_DET}^{(1)}$            | Reverse Current Protection Mode Detection Offset, $V_{REV} = V_{DD} - V_{OUT}$ | $0 \leq V_{IN} \leq 11.0 \text{ V}$ , $V_{OUT} \geq 1.5 \text{ V}$  |   | 55   | <span style="border: 1px solid black; padding: 0 2px;">100</span>  | mV   |    |
| $V_{REV\_REL}^{(1)}$            | Reverse Current Protection Mode Release Offset                                 | $0 \leq V_{IN} \leq 11.0 \text{ V}$ , $V_{OUT} \geq 1.5 \text{ V}$  |   | 70   | <span style="border: 1px solid black; padding: 0 2px;">120</span>  | mV   |    |
| $R_{LOW}$                       | Auto-discharge Nch Tr. ON Resistance (RP173xxxxD only)                         | $V_{IN} = 7.0 \text{ V}$ , $V_{CE} = 0 \text{ V}$   |   | 380  |  | $\Omega$   |    |

All of units are tested and specified under the pulse load conditions such that  $T_j \approx T_a = 25^\circ\text{C}$  except for Ripple Rejection.

<sup>(1)</sup> The operation coverage of the Reverse Current Protection Circuit is  $V_{OUT} \geq 1.5 \text{ V}$ . However, under the condition of  $V_{IN} = V_{OUT} = 0 \text{ V}$ , always the Reverse Current Protection Circuit is operating.

**PRODUCT-SPECIFIC ELECTRICAL CHARACTERISTICS**

**RP173x Product-specific Electrical Characteristics**

| Product Name | V <sub>OUT</sub> |       |       |                   |       |       | V <sub>DIF</sub> |       |
|--------------|------------------|-------|-------|-------------------|-------|-------|------------------|-------|
|              | Ta = 25°C        |       |       | -40°C ≤ Ta ≤ 85°C |       |       | Typ.             | Max.  |
|              | Min.             | Typ.  | Max.  | Min.              | Typ.  | Max.  |                  |       |
| RP173x12xx   | 1.185            | 1.200 | 1.215 | 1.172             | 1.200 | 1.227 | 1.680            | 2.590 |
| RP173x12xx5  | 1.235            | 1.250 | 1.265 | 1.222             | 1.250 | 1.277 | 1.680            | 2.590 |
| RP173x13xx   | 1.285            | 1.300 | 1.315 | 1.272             | 1.300 | 1.327 | 1.630            | 2.490 |
| RP173x14xx   | 1.385            | 1.400 | 1.415 | 1.372             | 1.400 | 1.427 | 1.630            | 2.490 |
| RP173x15xx   | 1.485            | 1.500 | 1.515 | 1.472             | 1.500 | 1.527 | 1.480            | 2.230 |
| RP173x16xx   | 1.584            | 1.600 | 1.616 | 1.571             | 1.600 | 1.629 | 1.480            | 2.230 |
| RP173x17xx   | 1.683            | 1.700 | 1.717 | 1.669             | 1.700 | 1.731 | 1.480            | 2.230 |
| RP173x17xx5  | 1.733            | 1.750 | 1.768 | 1.719             | 1.750 | 1.782 | 1.480            | 2.230 |
| RP173x18xx   | 1.782            | 1.800 | 1.818 | 1.768             | 1.800 | 1.832 | 1.160            | 2.190 |
| RP173x18xx5  | 1.832            | 1.850 | 1.869 | 1.817             | 1.850 | 1.883 | 1.160            | 2.190 |
| RP173x19xx   | 1.881            | 1.900 | 1.919 | 1.866             | 1.900 | 1.934 | 1.160            | 2.190 |
| RP173x20xx   | 1.980            | 2.000 | 2.020 | 1.964             | 2.000 | 2.036 | 1.160            | 2.190 |
| RP173x21xx   | 2.079            | 2.100 | 2.121 | 2.062             | 2.100 | 2.138 | 1.160            | 2.190 |
| RP173x22xx   | 2.178            | 2.200 | 2.222 | 2.160             | 2.200 | 2.240 | 1.160            | 2.190 |
| RP173x23xx   | 2.277            | 2.300 | 2.323 | 2.259             | 2.300 | 2.341 | 0.900            | 1.470 |
| RP173x24xx   | 2.376            | 2.400 | 2.424 | 2.357             | 2.400 | 2.443 | 0.900            | 1.470 |
| RP173x25xx   | 2.475            | 2.500 | 2.525 | 2.455             | 2.500 | 2.545 | 0.900            | 1.470 |
| RP173x26xx   | 2.574            | 2.600 | 2.626 | 2.553             | 2.600 | 2.647 | 0.900            | 1.470 |
| RP173x27xx   | 2.673            | 2.700 | 2.727 | 2.651             | 2.700 | 2.749 | 0.900            | 1.470 |
| RP173x28xx   | 2.772            | 2.800 | 2.828 | 2.750             | 2.800 | 2.850 | 0.900            | 1.470 |
| RP173x28xx5  | 2.822            | 2.850 | 2.879 | 2.799             | 2.850 | 2.901 | 0.900            | 1.470 |
| RP173x29xx   | 2.871            | 2.900 | 2.929 | 2.848             | 2.900 | 2.952 | 0.900            | 1.470 |
| RP173x30xx   | 2.970            | 3.000 | 3.030 | 2.946             | 3.000 | 3.054 | 0.610            | 1.050 |
| RP173x31xx   | 3.069            | 3.100 | 3.131 | 3.044             | 3.100 | 3.156 | 0.610            | 1.050 |
| RP173x32xx   | 3.168            | 3.200 | 3.232 | 3.142             | 3.200 | 3.258 | 0.610            | 1.050 |
| RP173x33xx   | 3.267            | 3.300 | 3.333 | 3.241             | 3.300 | 3.359 | 0.610            | 1.050 |
| RP173x34xx   | 3.366            | 3.400 | 3.434 | 3.339             | 3.400 | 3.461 | 0.610            | 1.050 |
| RP173x35xx   | 3.465            | 3.500 | 3.535 | 3.437             | 3.500 | 3.563 | 0.610            | 1.050 |
| RP173x36xx   | 3.564            | 3.600 | 3.636 | 3.535             | 3.600 | 3.665 | 0.610            | 1.050 |
| RP173x37xx   | 3.663            | 3.700 | 3.737 | 3.633             | 3.700 | 3.767 | 0.610            | 1.050 |
| RP173x38xx   | 3.762            | 3.800 | 3.838 | 3.732             | 3.800 | 3.868 | 0.610            | 1.050 |
| RP173x39xx   | 3.861            | 3.900 | 3.939 | 3.830             | 3.900 | 3.970 | 0.610            | 1.050 |
| RP173x40xx   | 3.960            | 4.000 | 4.040 | 3.928             | 4.000 | 4.072 | 0.390            | 0.760 |
| RP173x41xx   | 4.059            | 4.100 | 4.141 | 4.026             | 4.100 | 4.174 | 0.390            | 0.760 |
| RP173x42xx   | 4.158            | 4.200 | 4.242 | 4.124             | 4.200 | 4.276 | 0.390            | 0.760 |
| RP173x43xx   | 4.257            | 4.300 | 4.343 | 4.223             | 4.300 | 4.377 | 0.390            | 0.760 |
| RP173x44xx   | 4.356            | 4.400 | 4.444 | 4.321             | 4.400 | 4.479 | 0.390            | 0.760 |
| RP173x45xx   | 4.455            | 4.500 | 4.545 | 4.419             | 4.500 | 4.581 | 0.390            | 0.760 |
| RP173x46xx   | 4.554            | 4.600 | 4.646 | 4.517             | 4.600 | 4.683 | 0.390            | 0.760 |
| RP173x47xx   | 4.653            | 4.700 | 4.747 | 4.615             | 4.700 | 4.785 | 0.390            | 0.760 |
| RP173x48xx   | 4.752            | 4.800 | 4.848 | 4.714             | 4.800 | 4.886 | 0.390            | 0.760 |
| RP173x49xx   | 4.851            | 4.900 | 4.949 | 4.812             | 4.900 | 4.988 | 0.390            | 0.760 |
| RP173x50xx   | 4.950            | 5.000 | 5.050 | 4.910             | 5.000 | 5.090 | 0.390            | 0.760 |
| RP173x51xx   | 5.049            | 5.100 | 5.151 | 5.008             | 5.100 | 5.192 | 0.390            | 0.760 |
| RP173x52xx   | 5.148            | 5.200 | 5.252 | 5.106             | 5.200 | 5.294 | 0.390            | 0.760 |
| RP173x53xx   | 5.247            | 5.300 | 5.353 | 5.205             | 5.300 | 5.395 | 0.390            | 0.760 |
| RP173x54xx   | 5.346            | 5.400 | 5.454 | 5.303             | 5.400 | 5.497 | 0.390            | 0.760 |
| RP173x55xx   | 5.445            | 5.500 | 5.555 | 5.401             | 5.500 | 5.599 | 0.390            | 0.760 |



## THEORY OF OPERATION

### REVERSE CURRENT PROTECTION CIRCUIT

The RP173 Series include a Reverse Current Protection Circuit, which stops the reverse current from  $V_{OUT}$  pin to  $V_{DD}$  pin or to GND pin when  $V_{OUT}$  becomes higher than  $V_{IN}$ .


Usually, the LDO using Pch output transistor contains a parasitic diode between  $V_{DD}$  pin and  $V_{OUT}$  pin. Therefore, if  $V_{OUT}$  is higher than  $V_{IN}$ , the parasitic diode becomes forward direction. As a result, the current flows from  $V_{OUT}$  pin to  $V_{DD}$  pin.

The ICs of this series switches the mode to the reverse current protection mode before  $V_{IN}$  becomes lower than  $V_{OUT}$  by connecting the parasitic diode of Pch output transistor to the backward direction, and connecting the gate to  $V_{OUT}$  pin. As a result, the Pch output transistor is turned off and the all the current pathways from  $V_{OUT}$  pin to GND pin are shut down to maintain the reverse current lower than  $[I_{REV}]$  of the Electrical Characteristics.


Switching to either the normal mode or to the reverse current protection mode is determined by the magnitude of  $V_{IN}$  voltage and  $V_{OUT}$  voltage. For the stable operation, offset and hysteresis are set as the threshold. The detection/ release thresholds of both normal and reverse current protection modes are specified by  $[V_{REV\_DET}]$  and  $[V_{REV\_REL}]$  of the Electrical Characteristics. Therefore, the minimum dropout voltage under the small load current condition is restricted by the value of  $[V_{REV\_REL}]$ .

Fig.1 and Fig.2 show the diagrams of each mode, and Fig.3 shows the load characteristics of each mode. When giving the  $V_{OUT}$  pin a constant-voltage and decreasing the  $V_{IN}$  voltage, the dropout voltage will become lower than the  $[V_{REV\_DET}]$ . As a result, the reverse current protection starts to function to stop the load current. By increasing the dropout voltage higher than the  $[V_{REV\_REL}]$ , the protection mode will be released to let the load current to flow. If the dropout voltage to be used is lower than  $[V_{REV\_REL}]$ , the detection and the release may be repeated.

The operation coverage of the Reverse Current Protection Circuit is  $V_{OUT} \geq 1.5V$ . However, under the condition of  $V_{IN}=0V$ , always the reverse current protection mode is operating.



**Fig. 1 Normal Mode**



**Fig. 2 Reverse Current Protection Mode**





Fig. 3 Reverse Current Protection Mode Detection/ Release & Reverse Current/ Output Current Characteristics

## APPLICATION INFORMATION

### TYPICAL APPLICATIONS



### Recommended External Components

| Symbol                 | Description                        |
|------------------------|------------------------------------|
| C2 (C <sub>OUT</sub> ) | 0.1 μF, GRM155B31C104KA87D, MURATA |

### NOTES ON SELECTING EXTERNAL COMPONENTS

#### Phase Compensation

In these ICs, phase compensation is made for securing stable operation even if the load current is varied. For this purpose, use a 0.1 μF or more capacitor C2.

In case of using a tantalum capacitor, the output may be unstable due to inappropriate ESR. Therefore, the full range of operating conditions for the capacitor in the application should be considered.

#### PCB Layout

Make V<sub>DD</sub> and GND lines sufficient. If their impedance is high, noise pickup or unstable operation may result. Connect a capacitor C1 with a capacitance value as much as 0.1 μF or more between V<sub>DD</sub> and GND pin, and as close as possible to the pins.

Set external components, especially the output capacitor C2, as close as possible to the ICs, and make wiring as short as possible.

## TECHNICAL NOTES

### POWER ACTIVATION

If the ICs are started up with  $V_{IN}$  and  $V_{CE}$  under the no-load condition, the both pin voltages have to be started up with faster than 2.0V/s. If the IC is started up with slower than 2.0V/s under the no-load condition, start up the IC only with  $V_{CE}$ .

### ESR vs. Output Current




When using these ICs, consider the following points: The relations between  $I_{OUT}$  (Output Current) and ESR of an output capacitor are shown below. The conditions when the white noise level is under 40  $\mu$ V (Avg.) are marked as the hatched area in the graph.

#### Measurement Conditions

Frequency Band: 10 Hz to 2 MHz

Temperature : -40°C to 85°C

C1, C2 : 0.1  $\mu$ F




## TYPICAL CHARACTERISTICS


Note: Typical Characteristics are intended to be used as reference data; they are not guaranteed.

### 1) Output Voltage vs. Output Current (C1 = Ceramic 0.1 $\mu$ F, C2 = Ceramic 0.1 $\mu$ F, Ta = 25°C)


**RP173x12xx**




**RP173x18xx**



**RP173x30xx**




**RP173x55xx**




### 2) Output Voltage vs. Input Voltage (C1 = Ceramic 0.1 $\mu$ F, C2 = Ceramic 0.1 $\mu$ F, Ta = 25°C)


**RP173x12xx**




**RP173x18xx**



**RP173x30xx**




**RP173x55xx**




**3) Supply Current vs. Input Voltage (C1 = Ceramic 0.1  $\mu$ F, C2 = Ceramic 0.1  $\mu$ F, Ta = 25°C)**


**RP173x12xx**




**RP173x18xx**



**RP173x30xx**




**RP173x55xx**




**4) Output Voltage vs. Temperature (C1 = Ceramic 0.1  $\mu$ F, C2 = Ceramic 0.1  $\mu$ F,  $I_{OUT} = 1$  mA)**


**RP173x12xx**




**RP173x18xx**



**RP173x30xx**




**RP173x55xx**




**5) Dropout Voltage vs. Output Current (C1 = Ceramic 0.1  $\mu$ F, C2 = Ceramic 0.1  $\mu$ F)**


**RP173x12xx**



**RP173x30xx**




**RP173x55xx**




**6) Dropout Voltage vs. Set Output Voltage (C1 = Ceramic 0.1  $\mu$ F, C2 = Ceramic 0.1  $\mu$ F, Ta = 25°C)**

**RP173x**






**7) Minimum Operating Voltage (C1 = Ceramic 0.1  $\mu$ F, C2 = Ceramic 0.1  $\mu$ F, Ta = -40 to 85°C)**








**8) Ripple Rejection vs. Input Bias Voltage (C1 = none, C2 = Ceramic 0.1  $\mu$ F, Ripple = 0.2 Vp-p, Ta = 25°C)**




**9) Ripple Rejection vs. Temperature (C1 = none, C2 = Ceramic 0.1  $\mu$ F, Ripple = 0.2 Vp-p, Ta = 25°C)**



**RP173x30xx**




**RP173x55xx**




**10) Input Transient Response (C1 = none, C2 = Ceramic 0.1  $\mu F$ ,  $t_r = t_f = 5.0 \mu s$ ,  $T_a = 25^\circ C$ )**


**RP173x12xx**




**RP173x18xx**




**RP173x30xx**




**RP173x55xx**




**RP173x12xx**




**RP173x18xx**



**RP173x30xx**




**RP173x55xx**




**11) Load Transient Response (C1 = Ceramic 0.1  $\mu$ F, C2 = Ceramic 0.1  $\mu$ F,  $t_r = t_f = 0.5 \mu$ s,  $T_a = 25^\circ$ C)**


**RP173x12xx**




**RP173x18xx**




**RP173x30xx**




**RP173x55xx**




**RP173x12xx**




**RP173x18xx**







**RP173x30xx**





**RP173x55xx**




**12) Turn on Speed (C1 = Ceramic 0.1  $\mu$ F, C2 = Ceramic 0.1  $\mu$ F, Ta = 25°C)**




**13) Turn off Speed with CE pin (C1 = Ceramic 0.1  $\mu$ F, C2 = Ceramic 0.1  $\mu$ F, Ta = 25°C)**



RP173x30xx



RP173x55xx



# POWER DISSIPATION

# DFN(PL)1010-4

PD-DFN(PL)1010-4-(85125)-JE-C

The power dissipation of the package is dependent on PCB material, layout, and environmental conditions. The following measurement conditions are based on JEDEC STD. 51.

### Measurement Conditions

| Item             | Measurement Conditions   |
|------------------|--|
| Environment      | Mounting on Board (Wind Velocity = 0 m/s)  |
| Board Material   | Glass Cloth Epoxy Plastic (Four-Layer Board)   |
| Board Dimensions | 76.2 mm × 114.3 mm × 0.8 mm  |
| Copper Ratio     | Outer Layer (First Layer): Less than 95% of 50 mm Square<br>Inner Layers (Second and Third Layers): Approx. 100% of 50 mm Square<br>Outer Layer (Fourth Layer): Approx. 100% of 50 mm Square |
| Through-holes    | φ 0.2 mm × 21 pcs  |


### Measurement Result

(Ta = 25°C, Tjmax = 125°C)


| Item                                     | Measurement Result |
|--|--------------------|
| Power Dissipation                        | 800 mW             |
| Thermal Resistance (θja)                 | θja = 125°C/W      |
| Thermal Characterization Parameter (ψjt) | ψjt = 58°C/W       |

θja: Junction-to-Ambient Thermal Resistance

ψjt: Junction-to-Top Thermal Characterization Parameter



Power Dissipation vs. Ambient Temperature




Measurement Board Pattern

**PACKAGE DIMENSIONS**

**DFN(PL)1010-4**

Ver. A



**DFN(PL)1010-4 Package Dimensions (Unit: mm)**

\* The tab on the bottom of the package shown by blue circle is a substrate potential (GND). It is recommended that this tab be connected to the ground plane on the board but it is possible to leave the tab floating.



# POWER DISSIPATION

# SC-88A

Ver. B

The power dissipation of the package is dependent on PCB material, layout, and environmental conditions. The following conditions are used in this measurement.

### Measurement Conditions

| Item             | Standard Test Land Pattern                        |
|------------------|---|
| Environment      | Mounting on Board (Wind Velocity = 0 m/s)         |
| Board Material   | Glass Cloth Epoxy Plastic (Double-Sided Board)    |
| Board Dimensions | 40 mm × 40 mm × 1.6 mm                            |
| Copper Ratio     | Top Side: Approx. 50%<br>Bottom Side: Approx. 50% |
| Through-holes    | φ 0.5 mm × 44 pcs                                 |


### Measurement Result

(Ta = 25°C, Tjmax = 125°C)


| Item   | Standard Test Land Pattern                   |
|--|--|
| Power Dissipation                                  | 380 mW                                       |
| Thermal Resistance ( $\theta_{ja}$ )               | $\theta_{ja} = 263^{\circ}\text{C}/\text{W}$ |
| Thermal Characterization Parameter ( $\psi_{jt}$ ) | $\psi_{jt} = 75^{\circ}\text{C}/\text{W}$    |

$\theta_{ja}$ : Junction-to-Ambient Thermal Resistance

$\psi_{jt}$ : Junction-to-Top Thermal Characterization Parameter



Power Dissipation vs. Ambient Temperature




Measurement Board Pattern

# PACKAGE DIMENSIONS

# SC-88A

Ver. A



UNIT: mm

SC-88A Package Dimensions

# POWER DISSIPATION

# SOT-23-5

Ver. A

The power dissipation of the package is dependent on PCB material, layout, and environmental conditions. The following measurement conditions are based on JEDEC STD. 51-7.

### Measurement Conditions

| Item             | Measurement Conditions   |
|------------------|--|
| Environment      | Mounting on Board (Wind Velocity = 0 m/s)  |
| Board Material   | Glass Cloth Epoxy Plastic (Four-Layer Board)   |
| Board Dimensions | 76.2 mm × 114.3 mm × 0.8 mm  |
| Copper Ratio     | Outer Layer (First Layer): Less than 95% of 50 mm Square<br>Inner Layers (Second and Third Layers): Approx. 100% of 50 mm Square<br>Outer Layer (Fourth Layer): Approx. 100% of 50 mm Square |
| Through-holes    | φ 0.3 mm × 7 pcs   |


### Measurement Result

(Ta = 25°C, Tjmax = 125°C)


| Item                                     | Measurement Result |
|--|--------------------|
| Power Dissipation                        | 660 mW             |
| Thermal Resistance (θja)                 | θja = 150°C/W      |
| Thermal Characterization Parameter (ψjt) | ψjt = 51°C/W       |

θja: Junction-to-Ambient Thermal Resistance

ψjt: Junction-to-Top Thermal Characterization Parameter



Power Dissipation vs. Ambient Temperature




Measurement Board Pattern

# PACKAGE DIMENSIONS

# SOT-23-5

Ver. A



UNIT: mm

SOT-23-5 Package Dimensions

1. The products and the product specifications described in this document are subject to change or discontinuation of production without notice for reasons such as improvement. Therefore, before deciding to use the products, please refer to our sales representatives for the latest information thereon.
2. The materials in this document may not be copied or otherwise reproduced in whole or in part without the prior written consent of us.
3. This product and any technical information relating thereto are subject to complementary export controls (so-called KNOW controls) under the Foreign Exchange and Foreign Trade Law, and related politics ministerial ordinance of the law. (Note that the complementary export controls are inapplicable to any application-specific products, except rockets and pilotless aircraft, that are insusceptible to design or program changes.) Accordingly, when exporting or carrying abroad this product, follow the Foreign Exchange and Foreign Trade Control Law and its related regulations with respect to the complementary export controls.
4. The technical information described in this document shows typical characteristics and example application circuits for the products. The release of such information is not to be construed as a warranty of or a grant of license under our or any third party's intellectual property rights or any other rights.
5. The products listed in this document are intended and designed for use as general electronic components in standard applications (office equipment, telecommunication equipment, measuring instruments, consumer electronic products, amusement equipment etc.). Those customers intending to use a product in an application requiring extreme quality and reliability, for example, in a highly specific application where the failure or misoperation of the product could result in human injury or death should first contact us.
  - Aerospace Equipment
  - Equipment Used in the Deep Sea
  - Power Generator Control Equipment (nuclear, steam, hydraulic, etc.)
  - Life Maintenance Medical Equipment
  - Fire Alarms / Intruder Detectors
  - Vehicle Control Equipment (automotive, airplane, railroad, ship, etc.)
  - Various Safety Devices
  - Traffic control system
  - Combustion equipment

In case your company desires to use this product for any applications other than general electronic equipment mentioned above, make sure to contact our company in advance. Note that the important requirements mentioned in this section are not applicable to cases where operation requirements such as application conditions are confirmed by our company in writing after consultation with your company.

6. We are making our continuous effort to improve the quality and reliability of our products, but semiconductor products are likely to fail with certain probability. In order to prevent any injury to persons or damages to property resulting from such failure, customers should be careful enough to incorporate safety measures in their design, such as redundancy feature, fire containment feature and fail-safe feature. We do not assume any liability or responsibility for any loss or damage arising from misuse or inappropriate use of the products.
7. The products have been designed and tested to function within controlled environmental conditions. Do not use products under conditions that deviate from methods or applications specified in this datasheet. Failure to employ the products in the proper applications can lead to deterioration, destruction or failure of the products. We shall not be responsible for any bodily injury, fires or accident, property damage or any consequential damages resulting from misuse or misapplication of the products.
8. **Quality Warranty**
  - 8-1. **Quality Warranty Period**

In the case of a product purchased through an authorized distributor or directly from us, the warranty period for this product shall be one (1) year after delivery to your company. For defective products that occurred during this period, we will take the quality warranty measures described in section 8-2. However, if there is an agreement on the warranty period in the basic transaction agreement, quality assurance agreement, delivery specifications, etc., it shall be followed.
  - 8-2. **Quality Warranty Remedies**

When it has been proved defective due to manufacturing factors as a result of defect analysis by us, we will either deliver a substitute for the defective product or refund the purchase price of the defective product.

Note that such delivery or refund is sole and exclusive remedies to your company for the defective product.
  - 8-3. **Remedies after Quality Warranty Period**

With respect to any defect of this product found after the quality warranty period, the defect will be analyzed by us. On the basis of the defect analysis results, the scope and amounts of damage shall be determined by mutual agreement of both parties. Then we will deal with upper limit in Section 8-2. This provision is not intended to limit any legal rights of your company.
9. Anti-radiation design is not implemented in the products described in this document.
10. The X-ray exposure can influence functions and characteristics of the products. Confirm the product functions and characteristics in the evaluation stage.
11. WLCSP products should be used in light shielded environments. The light exposure can influence functions and characteristics of the products under operation or storage.
12. Warning for handling Gallium and Arsenic (GaAs) products (Applying to GaAs MMIC, Photo Reflector). These products use Gallium (Ga) and Arsenic (As) which are specified as poisonous chemicals by law. For the prevention of a hazard, do not burn, destroy, or process chemically to make them as gas or power. When the product is disposed of, please follow the related regulation and do not mix this with general industrial waste or household waste.
13. Please contact our sales representatives should you have any questions or comments concerning the products or the technical information.



**Nisshinbo Micro Devices Inc.**

**Official website**

<https://www.nisshinbo-microdevices.co.jp/en/>

**Purchase information**

<https://www.nisshinbo-microdevices.co.jp/en/buy/>