

TOSHIBA Zener Diode Silicon Epitaxial Planar Type

MSZ Series


Applications

Voltage surge protection

Features

- Small package
- The typical voltage of Vz is accorded to E24 series

Packaging and Internal Circuit



Absolute Maximum Ratings 1 (Note) (Unless otherwise specified, Ta = 25°C)

Characteristics	Symbol	Rating	Unit
Power dissipation	PD	200	mW
	PD ^{*1}	600	mW
Junction temperature	Tj	150	°C
Storage temperature	T _{stg}	−55 to 150	°C

Absolute Maximum Ratings 2 (Note) (Unless otherwise specified, Ta = 25°C)

Type No.	Electrostatic discharge voltage *2		Peak pulse Peak pulse		Type No. Electrostatic discharge voltage *2		Peak pulse	Peak pulse	
	Contact	Air	power *3	current*3		Contact	Air	power*3	current*3
	V _{ESD} (kV)		P _{PK} (W)	Ipp(A)		V _{ESD} (kV)		P _{PK} (W)	I _{PP} (A)
MSZ5V6	± 30		155	12	MSZ16V	± 30		200	5.5
MSZ6V2	± 30		175	11	MSZ20V	± 30		200	5
MSZ6V8	± 30		180	10	MSZ24V	± 30		200	4.5
MSZ8V2	±;	30	200	8.5	MSZ30V	± 20		200	4
MSZ12V	±	30	200	7	MSZ36V	± 12		200	3

Note: Using continuously under heavy loads (e.g. the application of high temperature/current/voltage and the significant change in temperature, etc.) may cause this product to decrease in the reliability significantly even if the operating conditions (i.e. operating temperature/current/voltage, etc.) are within the absolute maximum ratings. Please design the appropriate reliability upon reviewing the Toshiba Semiconductor Reliability Handbook ("Handling Precautions"/"Derating Concept and Methods") and individual reliability data (i.e. reliability test report and estimated failure rate, etc.).

- *1: Mounted on a glass epoxy circuit board of 25.4 mm × 25.4 mm, Cu pad: 645 mm²
- *2: according to IEC61000-4-2
- *3: according to IEC61000-4-5, tp = $8 / 20 \mu s$

Start of commercial production 2020-07



MSZ series Electrical Characteristics (Unless otherwise specified, Ta = 25°C)


Type No.	Zener Voltage			Dynamic Impedance		Dynamic resistance	Clamp voltage	Total Reverse Curren capacitance		rse Current	
		V _Z (V)	(V) Test Current		$Z_{Z}(\Omega)$	Test Current	$R_{DYN}(\Omega)^{*1}$	V _C (V) *1*2	C _t (pF) *3	I _R (µA)	Test Voltage
	Min	Тур.	Max	I _Z (mA)	Max	I _Z (mA)	Тур.	Тур.	Тур.	Max	V _R (V)
MSZ5V6	5.3	5.6	6.0	5	30	5	0.16	9	125	1	3.5
MSZ6V2	5.8	6.2	6.6	5	30	5	0.21	10	105	2.5	5.0
MSZ6V8	6.4	6.8	7.2	5	30	5	0.27	13	88	1.5	5.5
MSZ8V2	7.7	8.2	8.7	5	30	5	0.37	16.5	67	0.1	7
MSZ12V	11.4	12	12.6	5	30	5	0.7	26	44	0.1	10
MSZ16V	15.3	16	17.1	5	35	5	0.5	27	35	0.1	14
MSZ20V	18.8	20	21.2	5	70	5	0.35	30.5	29	0.1	17.6
MSZ24V	22.8	24	25.6	5	70	5	0.6	36.5	26	0.1	19
MSZ30V	28.0	30	32.0	2	100	2	1.25	47.5	21	0.1	27
MSZ36V	34.0	36	38.0	2	100	2	2.6	63	18	0.1	32.5

^{*1:} TLP parameters: $Z_0 = 50 \Omega$, $t_p = 100 \text{ ns}$, $t_r = 300 \text{ ps}$, averaging window: $t_1 = 30 \text{ ns}$ to $t_2 = 60 \text{ ns}$, extraction of dynamic resistance using least squares fit of TLP characteristics between ITLP1 = 16 A and ITLP2 = 30 A.


Marking List

Type No.	Marking	Type No.	Marking
MSZ5V6	ZLL	MSZ16V	ZM7
MSZ6V2	ZLM	MSZ20V	ZM9
MSZ6V8	ZLN	MSZ24V	ZMB
MSZ8V2	ZLQ	MSZ30V	ZMD
MSZ12V	ZM4	MSZ36V	ZMF

Marking (MSZ5V6)



Land Pattern Dimensions (for reference only) (Unit: mm)




^{*2:} ITLP = 16 A

^{*3:} VR = 0 V, f = 1 MHz




MSZ series Characteristics Curves (Note 1)




Note 1: The above characteristics curves are presented for reference only and not guaranteed by production test, unless otherwise noted.




MSZ series Characteristics Curves (Note 1)





PRSM - tw






rth(j-a) - tw

Note 1: The above characteristics curves are presented for reference only and not guaranteed by production test, unless otherwise noted.




MSZ5V6 Characteristics Curves (Note 1)



(Note 2) Peak Pulse Current (V_C - I_{PP})

(Note 3) Clamp waveform measurement circuit

IEC61000-4-2 (Contact)



Note 1: The above characteristics curves are presented for reference only and not guaranteed by production test, unless otherwise noted.


Oscilloscope

50 Ω


Based on IEC61000-4-5 8/20 µs pulse.




MSZ6V2 Characteristics Curves (Note 1)
















Clamp Waveform -8 kV (Note 3)

(Note 2) Peak Pulse Current (V_C - I_{PP})



Based on IEC61000-4-5 8/20 μs pulse.




IEC61000-4-2 (Contact)

Note 1: The above characteristics curves are presented for reference only and not guaranteed by production test, unless otherwise noted.




MSZ6V8 Characteristics Curves (Note 1)



(Note 2) Peak Pulse Current (V_C - I_{PP})

(Note 3) Clamp waveform measurement circuit

IEC61000-4-2 (Contact)




Note 1: The above characteristics curves are presented for reference only and not guaranteed by production test, unless otherwise noted.


Based on IEC61000-4-5 8/20 µs pulse.




MSZ8V2 Characteristics Curves (Note 1)




ITLP - VTLP



Clamp Waveform +8 kV (Note 3)




V_C - I_{PP} (Note 2)




Clamp Waveform -8 kV (Note 3)

(Note 2) Peak Pulse Current (V_C - I_{PP})



Based on IEC61000-4-5 8/20 μs pulse.




IEC61000-4-2 (Contact)


Note 1: The above characteristics curves are presented for reference only and not guaranteed by production test, unless otherwise noted.





MSZ12V Characteristics Curves (Note 1)
















Clamp Waveform -8 kV (Note 3)

(Note 2) Peak Pulse Current (V_C - I_{PP})



Based on IEC61000-4-5 8/20 μs pulse.




IEC61000-4-2 (Contact)


Note 1: The above characteristics curves are presented for reference only and not guaranteed by production test, unless otherwise noted.




MSZ16V Characteristics Curves (Note 1)








Clamp Waveform +8 kV (Note 3)




V_C - I_{PP} (Note 2)




Clamp Waveform -8 kV (Note 3)

(Note 2) Peak Pulse Current (V_C - I_{PP})



Based on IEC61000-4-5 8/20 μs pulse.





IEC61000-4-2 (Contact)


Note 1: The above characteristics curves are presented for reference only and not guaranteed by production test, unless otherwise noted.




MSZ20V Characteristics Curves (Note 1)











(Note 2) Peak Pulse Current (V_C - I_{PP})



(Note 3) Clamp waveform measurement circuit




Based on IEC61000-4-5 8/20 µs pulse.

IEC61000-4-2 (Contact)


Note 1: The above characteristics curves are presented for reference only and not guaranteed by production test, unless otherwise noted.




MSZ24V Characteristics Curves (Note 1)








Clamp Waveform +8 kV (Note 3)




V_C - I_{PP} (Note 2)




Clamp Waveform -8 kV (Note 3)

(Note 2) Peak Pulse Current (V_C - I_{PP})



Based on IEC61000-4-5 8/20 µs pulse.




IEC61000-4-2 (Contact)


Note 1: The above characteristics curves are presented for reference only and not guaranteed by production test, unless otherwise noted.




MSZ30V Characteristics Curves (Note 1)








Clamp Waveform +8 kV (Note 3)




V_C - I_{PP} (Note 2)




Clamp Waveform -8 kV (Note 3)

(Note 2) Peak Pulse Current (V_C - I_{PP})



Based on IEC61000-4-5 8/20 μs pulse.




IEC61000-4-2 (Contact)


Note 1: The above characteristics curves are presented for reference only and not guaranteed by production test, unless otherwise noted.




MSZ36V Characteristics Curves (Note 1)




ITLP - VTLP



Clamp Waveform +8 kV (Note 3)




V_C - I_{PP} (Note 2)




Clamp Waveform -8 kV (Note 3)

(Note 2) Peak Pulse Current (V_C - I_{PP})



Based on IEC61000-4-5 8/20 μs pulse.



IEC61000-4-2 (Contact)

Note 1: The above characteristics curves are presented for reference only and not guaranteed by production test, unless otherwise noted.



Package Dimensions

2.9 ± 0.2

A

3

0.16 +0.16

0.05

0.29 ± 0.2

0.4 +0.16

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.10

0.7 +0.1

Weight: 12mg (typ.)



RESTRICTIONS ON PRODUCT USE

Toshiba Corporation and its subsidiaries and affiliates are collectively referred to as "TOSHIBA". Hardware, software and systems described in this document are collectively referred to as "Product".

- TOSHIBA reserves the right to make changes to the information in this document and related Product without notice.
- This document and any information herein may not be reproduced without prior written permission from TOSHIBA. Even with TOSHIBA's written permission, reproduction is permissible only if reproduction is without alteration/omission.
- Though TOSHIBA works continually to improve Product's quality and reliability, Product can malfunction or fail. Customers are responsible for complying with safety standards and for providing adequate designs and safeguards for their hardware, software and systems which minimize risk and avoid situations in which a malfunction or failure of Product could cause loss of human life, bodily injury or damage to property, including data loss or corruption. Before customers use the Product, create designs including the Product, or incorporate the Product into their own applications, customers must also refer to and comply with (a) the latest versions of all relevant TOSHIBA information, including without limitation, this document, the specifications, the data sheets and application notes for Product and the precautions and conditions set forth in the "TOSHIBA Semiconductor Reliability Handbook" and (b) the instructions for the application with which the Product will be used with or for. Customers are solely responsible for all aspects of their own product design or applications, including but not limited to (a) determining the appropriateness of the use of this Product in such design or applications; (b) evaluating and determining the applicability of any information contained in this document, or in charts, diagrams, programs, algorithms, sample application circuits, or any other referenced documents; and (c) validating all operating parameters for such designs and applications. TOSHIBA ASSUMES NO LIABILITY FOR CUSTOMERS' PRODUCT DESIGN OR APPLICATIONS.
- PRODUCT IS NEITHER INTENDED NOR WARRANTED FOR USE IN EQUIPMENTS OR SYSTEMS THAT REQUIRE
 EXTRAORDINARILY HIGH LEVELS OF QUALITY AND/OR RELIABILITY, AND/OR A MALFUNCTION OR FAILURE OF WHICH MAY
 CAUSE LOSS OF HUMAN LIFE, BODILY INJURY, SERIOUS PROPERTY DAMAGE AND/OR SERIOUS PUBLIC IMPACT
 ("UNINTENDED USE"). Except for specific applications as expressly stated in this document, Unintended Use includes, without limitation,
 equipment used in nuclear facilities, equipment used in the aerospace industry, lifesaving and/or life supporting medical equipment,
 equipment used for automobiles, trains, ships and other transportation, traffic signaling equipment, equipment used to control combustions or
 explosions, safety devices, elevators and escalators, and devices related to power plant. IF YOU USE PRODUCT FOR UNINTENDED USE,
 TOSHIBA ASSUMES NO LIABILITY FOR PRODUCT. For details, please contact your TOSHIBA sales representative or contact us via our
 website.
- Do not disassemble, analyze, reverse-engineer, alter, modify, translate or copy Product, whether in whole or in part.
- Product shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any
 applicable laws or regulations.
- The information contained herein is presented only as guidance for Product use. No responsibility is assumed by TOSHIBA for any infringement of patents or any other intellectual property rights of third parties that may result from the use of Product. No license to any intellectual property right is granted by this document, whether express or implied, by estoppel or otherwise.
- ABSENT A WRITTEN SIGNED AGREEMENT, EXCEPT AS PROVIDED IN THE RELEVANT TERMS AND CONDITIONS OF SALE FOR
 PRODUCT, AND TO THE MAXIMUM EXTENT ALLOWABLE BY LAW, TOSHIBA (1) ASSUMES NO LIABILITY WHATSOEVER,
 INCLUDING WITHOUT LIMITATION, INDIRECT, CONSEQUENTIAL, SPECIAL, OR INCIDENTAL DAMAGES OR LOSS, INCLUDING
 WITHOUT LIMITATION, LOSS OF PROFITS, LOSS OF OPPORTUNITIES, BUSINESS INTERRUPTION AND LOSS OF DATA, AND (2)
 DISCLAIMS ANY AND ALL EXPRESS OR IMPLIED WARRANTIES AND CONDITIONS RELATED TO SALE, USE OF PRODUCT, OR
 INFORMATION, INCLUDING WARRANTIES OR CONDITIONS OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE,
 ACCURACY OF INFORMATION, OR NONINFRINGEMENT.
- Do not use or otherwise make available Product or related software or technology for any military purposes, including without limitation, for the design, development, use, stockpiling or manufacturing of nuclear, chemical, or biological weapons or missile technology products (mass destruction weapons). Product and related software and technology may be controlled under the applicable export laws and regulations including, without limitation, the Japanese Foreign Exchange and Foreign Trade Law and the U.S. Export Administration Regulations. Export and re-export of Product or related software or technology are strictly prohibited except in compliance with all applicable export laws and regulations.
- Please contact your TOSHIBA sales representative for details as to environmental matters such as the RoHS compatibility of Product. Please
 use Product in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including
 without limitation, the EU RoHS Directive. TOSHIBA ASSUMES NO LIABILITY FOR DAMAGES OR LOSSES OCCURRING AS A RESULT
 OF NONCOMPLIANCE WITH APPLICABLE LAWS AND REGULATIONS.

TOSHIBA ELECTRONIC DEVICES & STORAGE CORPORATION

https://toshiba.semicon-storage.com/