



High-Supply-Voltage, Precision Voltage Reference in SOT23

MAX6035

General Description

The MAX6035 is a high-voltage, precision micropower voltage reference. This three-terminal device is available with output voltage options of 2.5V, 3.0V, and 5.0V. It is an excellent upgrade for industry-standard devices such as the REF02 and REF43. The MAX6035 offers 14x lower power than the REF02 and 5x lower power than the REF43, as well as a reduced package size from an 8-pin SO to a 3-pin SOT23. The MAX6035 features a proprietary temperature coefficient curvature-correction circuit and laser-trimmed, thin-film resistors that result in a very low temperature coefficient of 25ppm/°C (max) and an initial accuracy of ±0.2% (max).


The MAX6035 typically draws only 73µA of supply current and can source 10mA or sink 2mA of load current. Unlike conventional shunt-mode (two-terminal) references that waste supply current and require an external resistor, this device offers a supply current that is virtually independent of the supply voltage and does not require an external resistor. Additionally, this internally compensated device does not require an external compensation capacitor, but is also stable with capacitive loads up to 5µF. Eliminating the external compensation capacitor saves valuable board area in space-critical applications. The supply independent, ultra-low supply current makes this device ideal for battery-operated, high-performance systems.

The MAX6035 is available in a 3-pin SOT23 package and is specified for operation from -40°C to +125°C.

Applications

- | | |
|--------------------------------------|-----------------------------------|
| 4mA to 20mA Industrial Control Loops | Digital Multimeters |
| Li+ Battery Chargers | Portable Data-Acquisition Systems |
| 12-Bit A/D and D/A Converters | Low-Power Test Equipment |

Typical Operating Circuit



Features

- ◆ Wide Supply Voltage Range: Up to 33V
- ◆ 25ppm/°C (max) Temperature Coefficient (-40°C to +85°C)
- ◆ ±0.2% (max) Initial Accuracy
- ◆ 95µA (max) Quiescent Supply Current
- ◆ 10mA Source Current, 2mA Sink Current
- ◆ No Output Capacitor Required
- ◆ Stable with Capacitive Loads up to 5µF

Ordering Information


| PART | TEMP RANGE | PIN-PACKAGE | TOP MARK |
|-----------------|-----------------|-------------|----------|
| MAX6035AAUR25-T | -40°C to +125°C | 3 SOT23-3 | FZMW |
| MAX6035BAUR25-T | -40°C to +125°C | 3 SOT23-3 | FZMX |
| MAX6035ESA25 | -40°C to +85°C | 8 SO | — |
| MAX6035AAUR30-T | -40°C to +125°C | 3 SOT23-3 | FZMY |
| MAX6035BAUR30-T | -40°C to +125°C | 3 SOT23-3 | FZMZ |
| MAX6035AAUR50-T | -40°C to +125°C | 3 SOT23-3 | FZNA |
| MAX6035BAUR50-T | -40°C to +125°C | 3 SOT23-3 | FZNB |

Note: The 3-pin SOT23 package code is U3-1. The 8-pin SO package code is S8-2.

Selector Guide

| PART | MAXIMUM TEMPCO (ppm/°C) (-40°C to +85°C) | MAXIMUM INITIAL ACCURACY (%) | OUTPUT VOLTAGE (V) |
|---------------|--|------------------------------|--------------------|
| MAX6035AAUR25 | 25 | 0.20 | 2.5 |
| MAX6035BAUR25 | 65 | 0.50 | 2.5 |
| MAX6035ESA25 | 40 | 0.20 | 2.5 |
| MAX6035AAUR30 | 25 | 0.20 | 3.0 |
| MAX6035BAUR30 | 65 | 0.50 | 3.0 |
| MAX6035AAUR50 | 25 | 0.20 | 5.0 |
| MAX6035BAUR50 | 65 | 0.50 | 5.0 |

Pin Configurations



For pricing, delivery, and ordering information, please contact Maxim/Dallas Direct! at 1-888-629-4642, or visit Maxim's website at www.maxim-ic.com.

High-Supply-Voltage, Precision Voltage Reference in SOT23

ABSOLUTE MAXIMUM RATINGS

(Voltages referenced to GND)

| | |
|--|-----------------------------------|
| IN | -0.3V to +36V |
| OUT | -0.3V to (V _{IN} + 0.3V) |
| OUT Short-Circuit Duration to GND or IN (Note 1) | Continuous |
| Current into Any Pin | ±20mA |
| Continuous Power Dissipation | |
| 3-Pin SOT23 (derate 4.0mW/°C above +70°C) | 320mW |
| 8-Pin SO (derate 5.9mW/°C above +70°C) | 470.6mW |

Operating Temperature Range:

| | |
|-----------------------------------|-----------------|
| MAX6035ESA | -40°C to +85°C |
| MAX6035_AUR | -40°C to +125°C |
| Storage Temperature Range | -65°C to +150°C |
| Junction Temperature | +150°C |
| Lead Temperature (soldering, 10s) | +300°C |

Note 1: Continuous power dissipation should also be observed.

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

ELECTRICAL CHARACTERISTICS—MAX6035_AUR25 and MAX6035ESA25 (2.5V)

(V_{IN} = 5V, I_{OUT} = 0, T_A = T_{MIN} to T_{MAX}, unless otherwise noted. Typical values are at T_A = +25°C.) (Note 2)

| PARAMETER | SYMBOL | CONDITIONS | | MIN | TYP | MAX | UNITS | | |
|--|--|--|---|--------------|--------|--------|-------|--------|----|
| Output Voltage | V _{OUT} | T _A = +25°C | MAX6035AAUR, MAX6035ESA (0.2%) | 2.4950 | 2.5000 | 2.5050 | V | | |
| | | | MAX6035BAUR | 2.4875 | 2.5000 | 2.5125 | | | |
| Output Voltage Temperature Coefficient (Notes 3 and 6) | TCV _{OUT} | T _A = 0°C to +70°C | MAX6035AAUR | | | | 20 | ppm/°C | |
| | | | MAX6035BAUR | | | | 50 | | |
| | | T _A = -40°C to +85°C | MAX6035AAUR | | | | 25 | | |
| | | | MAX6035ESA | | | | 40 | | |
| | | T _A = -40°C to +125°C | MAX6035BAUR | | | | 65 | | |
| | | | MAX6035AAUR | | | | 30 | | |
| Line Regulation (Note 4) | ΔV _{OUT} /ΔV _{IN} | (V _{OUT} + 2V) ≤ V _{IN} ≤ 33V | T _A = +25°C | | | 4 | μV/V | | |
| | | | T _A = T _{MIN} to T _{MAX} | | | 20 | | | |
| Load Regulation (Note 4) | ΔV _{OUT} / ΔI _{OUT} | T _A = +25°C, MAX6035_AUR | Sourcing: 0 ≤ I _{OUT} ≤ 10mA | | | 25 | μV/mA | | |
| | | | Sinking: -2mA ≤ I _{OUT} ≤ 0 | | | 45 | | | |
| | | T _A = T _{MIN} to T _{MAX} , MAX6035_AUR | Sourcing: 0 ≤ I _{OUT} ≤ 10mA | | | 85 | | | |
| | | | Sinking: -2mA ≤ I _{OUT} ≤ 0 | | | 225 | | | |
| | | T _A = +25°C, MAX6035ESA | Sourcing: 0 ≤ I _{OUT} ≤ 10mA | | | 105 | | 175 | |
| | | | Sinking: -2mA ≤ I _{OUT} ≤ 0 | | | 205 | | 375 | |
| | | T _A = T _{MIN} to T _{MAX} , MAX6035ESA | Sourcing: 0 ≤ I _{OUT} ≤ 10mA | | | 350 | | | |
| | | | Sinking: -2mA ≤ I _{OUT} ≤ 0 | | | 500 | | | |
| | | OUT Short-Circuit Current | I _{SC} | Short to GND | | | | 27 | mA |
| | | | | Short to IN | | | | -4 | |

High-Supply-Voltage, Precision Voltage Reference in SOT23

MAX6035

ELECTRICAL CHARACTERISTICS—MAX6035_AUR25 and MAX6035ESA25 (2.5V) (continued)

($V_{IN} = 5V$, $I_{OUT} = 0$, $T_A = T_{MIN}$ to T_{MAX} , unless otherwise noted. Typical values are at $T_A = +25^\circ C$.) (Note 2)

| PARAMETER | SYMBOL | CONDITIONS | MIN | TYP | MAX | UNITS |
|------------------------------------|--------------------------------|---|--------------------|-----|------|----------------|
| Dropout Voltage (Note 7) | $V_{IN} - V_{OUT}$ | $I_{OUT} = 10\mu A$ | | | 1.9 | V |
| | | $I_{OUT} = 10mA$ | | | 2.25 | |
| Thermal Hysteresis (Note 5) | $\Delta V_{OUT}/cycle$ | | | 135 | | ppm |
| Long-Term Stability | $\Delta V_{OUT}/time$ | 1000hr at $+25^\circ C$ | | 110 | | ppm/ 1000hr |
| DYNAMIC CHARACTERISTICS | | | | | | |
| Output Noise Voltage | e_n | $f = 0.1Hz$ to $10Hz$ | | 21 | | μV_{P-P} |
| | | $f = 10Hz$ to $1kHz$ | | 20 | | μV_{RMS} |
| Ripple Rejection | $\Delta V_{OUT}/\Delta V_{IN}$ | $V_{IN} = 5V \pm 100mV$, $f = 120Hz$ | | 86 | | dB |
| Turn-On Settling Time | t_R | $T_o V_{OUT} = 0.1\%$ of final value | $C_{OUT} = 50pF$ | | 35 | μs |
| | | | $C_{OUT} = 1\mu F$ | | 240 | |
| Capacitive-Load Stability (Note 6) | C_{OUT} | | 0 | | 5 | μF |
| INPUT CHARACTERISTICS | | | | | | |
| Supply Voltage Range | V_{IN} | Inferred from line regulation and dropout voltage | 4.4 | | 33 | V |
| Quiescent Supply Current | I_{IN} | | | 73 | 95 | μA |
| Change in Supply Current | $\Delta I_{IN}/\Delta V_{IN}$ | $4.4V \leq V_{IN} \leq 33V$ | | 0.4 | 0.7 | $\mu A/V$ |

ELECTRICAL CHARACTERISTICS—MAX6035_AUR30 (3.0V)

($V_{IN} = 5V$, $I_{OUT} = 0$, $T_A = T_{MIN}$ to T_{MAX} , unless otherwise noted. Typical values are at $T_A = +25^\circ C$.) (Note 2)

| PARAMETER | SYMBOL | CONDITIONS | MIN | TYP | MAX | UNITS | |
|---|---------------------------------|--|--|--------|--------|--------|-----------------|
| Output Voltage | V_{OUT} | $T_A = +25^\circ C$ | MAX6035A (0.2%) | 2.9940 | 3.0000 | 3.0060 | V |
| | | | MAX6035B (0.5%) | 2.9850 | 3.0000 | 3.0150 | |
| Output Voltage Temperature Coefficient (Note 3) | TCV_{OUT} | $T_A = 0^\circ C$ to $+70^\circ C$ | MAX6035A | | | 20 | ppm/ $^\circ C$ |
| | | | MAX6035B | | | 50 | |
| | | $T_A = -40^\circ C$ to $+85^\circ C$ | MAX6035A | | | 25 | |
| | | | MAX6035B | | | 65 | |
| | | $T_A = -40^\circ C$ to $+125^\circ C$ | MAX6035A | | | 30 | |
| | | | MAX6035B | | | 75 | |
| Line Regulation (Note 4) | $\Delta V_{OUT}/\Delta V_{IN}$ | $(V_{OUT} + 1.75V) \leq V_{IN} \leq 33V$ | $T_A = +25^\circ C$ | | 4.5 | 15 | $\mu V/V$ |
| | | | $T_A = 0^\circ C$ to $+125^\circ C$ | | | 24 | |
| | | $(V_{OUT} + 2V) \leq V_{IN} \leq 33V$ | $T_A = -40^\circ C$ to $+125^\circ C$ | | | 24 | |
| Load Regulation (Note 4) | $\Delta V_{OUT}/\Delta I_{OUT}$ | $T_A = +25^\circ C$ | Sourcing: $0 \leq I_{OUT} \leq 10mA$ | | 30 | 81 | $\mu V/mA$ |
| | | | Sinking: $-2mA \leq I_{OUT} \leq 0mA$ | | 54 | 170 | |
| | | $T_A = -40^\circ C$ to $+125^\circ C$ | Sourcing: $0 \leq I_{OUT} \leq 10mA$ | | | 96 | |
| | | | Sinking: $-2mA \leq I_{OUT} \leq 0mA$ | | | 230 | |

High-Supply-Voltage, Precision Voltage Reference in SOT23

ELECTRICAL CHARACTERISTICS—MAX6035_AUR30 (3.0V) (continued)

($V_{IN} = 5V$, $I_{OUT} = 0$, $T_A = T_{MIN}$ to T_{MAX} , unless otherwise noted. Typical values are at $T_A = +25^\circ C$.) (Note 2)

| PARAMETER | SYMBOL | CONDITIONS | | MIN | TYP | MAX | UNITS |
|------------------------------------|---|---|-------------------------|------|-----|------|-------------------|
| OUT Short-Circuit Current | I _{SC} | Short to GND | | | 27 | | mA |
| | | Short to IN | | | -4 | | |
| Dropout Voltage (Note 7) | V _{IN} - V _{OUT} | T _A = 0°C to +125°C | I _{OUT} = 10μA | | | 1.75 | V |
| | | T _A = -40°C to +125°C | I _{OUT} = 10μA | | | 1.9 | |
| | | | I _{OUT} = 10mA | | | 2.25 | |
| Thermal Hysteresis (Note 5) | ΔV _{OUT} /cycle | | | | 135 | | ppm |
| Long-Term Stability | ΔV _{OUT} /time | 1000hr at +25°C | | | 120 | | ppm/ 1000hr |
| DYNAMIC CHARACTERISTICS | | | | | | | |
| Output Noise Voltage | e _n | f = 0.1Hz to 10Hz | | | 25 | | μV _{P-P} |
| | | f = 10Hz to 1kHz | | | 25 | | μV _{RMS} |
| Ripple Rejection | ΔV _{OUT} / ΔV _{IN} | V _{IN} = 5V ±100mV, f = 120Hz | | | 80 | | dB |
| Turn-On Settling Time | t _R | V _{OUT} = 0.1% of final value | C _{OUT} = 50pF | | 40 | | μs |
| | | | C _{OUT} = 1μF | | 250 | | |
| Capacitive-Load Stability (Note 6) | C _{OUT} | | | 0 | | 5 | μF |
| INPUT CHARACTERISTICS | | | | | | | |
| Supply Voltage Range | V _{IN} | T _A = 0°C to +125°C, inferred from line regulation and dropout voltage | | 4.75 | | 33 | V |
| | | T _A = -40°C to +125°C, inferred from line regulation and dropout voltage | | 4.9 | | 33 | |
| Quiescent Current Supply | I _{IN} | | | | 73 | 95 | μA |
| Change in Supply Current | ΔI _{IN} /ΔV _{IN} | 4.9V ≤ V _{IN} ≤ 33V | | | 0.4 | 0.7 | μA/V |

ELECTRICAL CHARACTERISTICS—MAX6035_AUR50 (5.0V)

($V_{IN} = 5V$, $I_{OUT} = 0$, $T_A = T_{MIN}$ to T_{MAX} , unless otherwise noted. Typical values are at $T_A = +25^\circ C$.) (Note 2)

| PARAMETER | SYMBOL | CONDITIONS | | MIN | TYP | MAX | UNITS |
|---|-------------------------------------|--|----------------------------------|--------|--------|--------|--------|
| Output Voltage | V _{OUT} | T _A = +25°C | MAX6035A (0.2%) | 4.9900 | 5.0000 | 5.0100 | V |
| | | | MAX6035B (0.5%) | 4.9750 | 5.0000 | 5.0250 | |
| Output Voltage Temperature Coefficient (Note 3) | TCV _{OUT} | T _A = 0°C to +70°C | MAX6035A | | | 20 | ppm/°C |
| | | | MAX6035B | | | 50 | |
| | | T _A = -40°C to +85°C | MAX6035A | | | 25 | |
| | | | MAX6035B | | | 65 | |
| | | T _A = -40°C to +125°C | MAX6035A | | | 30 | |
| MAX6035B | | | | 75 | | | |
| Line Regulation (Note 4) | ΔV _{OUT} /ΔV _{IN} | (V _{OUT} + 2V) ≤ V _{OUT} ≤ 33V | T _A = +25°C | | 7.5 | 25 | μV/V |
| | | | T _A = -40°C to +125°C | | 8 | 40 | |

High-Supply-Voltage, Precision Voltage Reference in SOT23

MAX6035

ELECTRICAL CHARACTERISTICS—MAX6035_AUR50 (5.0V) (continued)

($V_{IN} = 5V$, $I_{OUT} = 0$, $T_A = T_{MIN}$ to T_{MAX} , unless otherwise noted. Typical values are at $T_A = +25^\circ C$.) (Note 2)

| PARAMETER | SYMBOL | CONDITIONS | MIN | TYP | MAX | UNITS | |
|------------------------------------|---------------------------------|---|--|-----|------|----------------|--|
| Load Regulation (Note 4) | $\Delta V_{OUT}/\Delta I_{OUT}$ | $T_A = +25^\circ C$ | Sourcing: $0 \leq I_{OUT} \leq 10mA$ | 50 | 135 | $\mu V/mA$ | |
| | | | Sinking: $-2mA \leq I_{OUT} \leq 0mA$ | 90 | 215 | | |
| | | $T_A = -40^\circ C$ to $+125^\circ C$ | Sourcing: $0 \leq I_{OUT} \leq 10mA$ | | 160 | | |
| | | | Sinking: $-2mA \leq I_{OUT} \leq 0mA$ | | 300 | | |
| OUT Short-Circuit Current | I _{SC} | Shorted to GND | | 27 | | mA | |
| | | Shorted to I _N | | -4 | | | |
| Dropout Voltage (Note 7) | $V_{IN} - V_{OUT}$ | $I_{OUT} = 10\mu A$ | | | 1.9 | V | |
| | | $I_{OUT} = 10mA$ | | | 2.25 | | |
| Thermal Hysteresis (Note 5) | $\Delta V_{OUT}/cycle$ | | | 135 | | ppm | |
| Long-Term Stability | $\Delta V_{OUT}/time$ | 1000hr at $+25^\circ C$ | | 160 | | ppm/ 1000hr | |
| DYNAMIC CHARACTERISTICS | | | | | | | |
| Output Noise Voltage | e_n | $f = 0.1Hz$ to $10Hz$ | | 68 | | μV_{P-P} | |
| | | $f = 10Hz$ to $1kHz$ | | 48 | | μV_{RMS} | |
| Ripple Rejection | $\Delta V_{OUT}/\Delta V_{IN}$ | $V_{IN} = 15V \pm 100mV$, $f = 120Hz$ | | 72 | | dB | |
| Turn-On Settling Time | t_R | To $V_{OUT} = 0.1\%$ of final value | $C_{OUT} = 50pF$ | 140 | | μs | |
| | | | $C_{OUT} = 1\mu F$ | 300 | | | |
| Capacitive-Load Stability (Note 6) | C_{OUT} | | 0 | | 5 | μF | |
| INPUT CHARACTERISTICS | | | | | | | |
| Supply Voltage Range | V_{IN} | Inferred by line regulation and dropout voltage | 6.9 | | 33 | V | |
| Quiescent Current Supply | I_{IN} | | | 80 | 100 | μA | |
| Change in Supply Current | $\Delta I_{IN}/\Delta V_{IN}$ | $6.9V \leq V_{IN} \leq 33V$ | | 0.4 | 0.7 | $\mu A/V$ | |

Note 2: All devices are 100% production tested at $T_A = +25^\circ C$ and are guaranteed by design for $T_A = T_{MIN}$ to T_{MAX} , as specified.

Note 3: Temperature Coefficient is measured by the "box" method, i.e., the maximum ΔV_{OUT} is divided by the maximum ΔT .

Note 4: Line and load regulation are measured with pulses and do not include output voltage fluctuation due to die-temperature changes.

Note 5: Thermal Hysteresis is defined as the change in the output voltage at $T_A = +25^\circ C$ before and after cycling the device from T_{MAX} to T_{MIN} .










Note 6: Guaranteed by design.

Note 7: Although the source current is guaranteed to be 10mA, exercise caution to ensure that the package's absolute power dissipation rating is not exceeded.

High-Supply-Voltage, Precision Voltage Reference in SOT23

Typical Operating Characteristics

($V_{IN} = 5V$ for MAX6035AAUR25/MAX6035AAUR30, $V_{IN} = 15V$ for MAX6035AAUR50, $I_{OUT} = 0$, $T_A = +25^\circ C$, unless otherwise noted.)












High-Supply-Voltage, Precision Voltage Reference in SOT23

MAX6035

Typical Operating Characteristics (continued)

($V_{IN} = 5V$ for MAX6035AAUR25/MAX6035AAUR30, $V_{IN} = 15V$ for MAX6035AAUR50, $I_{OUT} = 0$, $T_A = +25^\circ C$, unless otherwise noted.)




High-Supply-Voltage, Precision Voltage Reference in SOT23


Typical Operating Characteristics (continued)

($V_{IN} = 5V$ for MAX6035AAUR25/MAX6035AAUR30, $V_{IN} = 15V$ for MAX6035AAUR50, $I_{OUT} = 0$, $T_A = +25^\circ C$, unless otherwise noted.)


MAX6035
0.1Hz to 10Hz OUTPUT NOISE
($V_{OUT} = 2.5V$)




MAX6035
0.1Hz to 10Hz OUTPUT NOISE
($V_{OUT} = 3V$)




MAX6035
0.1Hz to 10Hz OUTPUT NOISE
($V_{OUT} = 5V$)




MAX6035
10Hz to 1kHz OUTPUT NOISE
($V_{OUT} = 2.5V$)




MAX6035
10Hz to 1kHz OUTPUT NOISE
($V_{OUT} = 3V$)




MAX6035
10Hz to 1kHz OUTPUT NOISE
($V_{OUT} = 5V$)




MAX6035
TURN-ON TRANSIENT ($V_{OUT} = 2.5V$)



MAX6035
TURN-ON TRANSIENT ($V_{OUT} = 3V$)



MAX6035
TURN-ON TRANSIENT ($V_{OUT} = 5V$)












High-Supply-Voltage, Precision Voltage Reference in SOT23

MAX6035

Typical Operating Characteristics (continued)

($V_{IN} = 5V$ for MAX6035AAUR25/MAX6035AAUR30, $V_{IN} = 15V$ for MAX6035AAUR50, $I_{OUT} = 0$, $T_A = +25^\circ C$, unless otherwise noted.)









High-Supply-Voltage, Precision Voltage Reference in SOT23

MAX6035

Typical Operating Characteristics (continued)

($V_{IN} = 5V$ for MAX6035AAUR25/MAX6035AAUR30, $V_{IN} = 15V$ for MAX6035AAUR50, $I_{OUT} = 0$, $T_A = +25^\circ C$, unless otherwise noted.)



High-Supply-Voltage, Precision Voltage Reference in SOT23

MAX6035

Typical Operating Characteristics (continued)

($V_{IN} = 5V$ for MAX6035AAUR25/MAX6035AAUR30, $V_{IN} = 15V$ for MAX6035AAUR50, $I_{OUT} = 0$, $T_A = +25^\circ C$, unless otherwise noted.)





Figure 1. Load-Transient Test Circuit




Figure 2. Load-Transient Test Circuit

High-Supply-Voltage, Precision Voltage Reference in SOT23

Pin Description

| PIN | | NAME | FUNCTION |
|-------|------------------|------|--|
| SOT23 | SO | | |
| 1 | 2 | IN | Input Voltage |
| 2 | 6 | OUT | Reference Output |
| 3 | 4 | GND | Ground |
| | 1, 3, 5, 7, 8 | N.C. | No Connection. Not internally connected. |

Applications Information

Input Bypassing

For the best line-transient performance, decouple the input with a 0.1 μ F ceramic capacitor as shown in the *Typical Operating Circuit*. Locate the capacitor as close to the device as possible. Where transient performance is less important, no capacitor is necessary.

Output/Load Capacitance

Devices in the MAX6035 family do not require any output capacitance for frequency stability. In applications where the load or the supply can experience step changes, an output capacitor of at least 0.1 μ F reduces the amount of overshoot (undershoot) and improves the circuit's transient response. Many applications do not require an external capacitor, and the MAX6035 family can offer a significant advantage in these applications when board space is critical.

Supply Current

The quiescent supply current of the MAX6035 series-mode family is typically 73 μ A and is virtually independent of the supply voltage, with only a 0.7 μ A/V (max) variation with supply voltage. In contrast, the quiescent current of a shunt-mode reference is a function of the input voltage due to a series resistor connected to the

power supply. Additionally, shunt-mode references have to be biased at the maximum expected load current, even if the load current is not present at the time. In the MAX6035 family, the load current is drawn from the input voltage only when required, so supply current is not wasted and efficiency is maximized at all input voltages. This improved efficiency reduces power dissipation and extends battery life.

Thermal Hysteresis

Thermal hysteresis is the change of output voltage at $T_A = +25^\circ\text{C}$ before and after the device is cycled over its entire operating temperature range. The typical temperature hysteresis value is 135ppm.

Turn-On Time

These devices typically turn on and settle to within 0.1% of their final value in 240 μ s. Increased output capacitance also increases turn-on time.

Temperature Coefficient vs. Operating Temperature Range for a 1 LSB Maximum Error

In a data converter application, the reference voltage of the converter must stay within a certain limit to keep the error in the data converter smaller than the resolution limit through the operating temperature range. Figure 3 shows the maximum allowable reference-voltage temperature coefficient to keep the conversion error to less than 1LSB, as a function of the operating temperature range ($T_{MAX} - T_{MIN}$) with the converter resolution as a parameter. The graph assumes the reference-voltage temperature coefficient as the only parameter affecting accuracy.

In reality, the absolute static accuracy of a data converter is dependent on the combination of many parameters such as integral nonlinearity, differential nonlinearity, offset error, gain error, as well as voltage reference changes

High-Supply-Voltage, Precision Voltage Reference in SOT23

MAX6035




Figure 3. Temperature Coefficient vs. Operating Temperature Range for a 1 LSB Maximum Error



Chip Information

TRANSISTOR COUNT: 84
 PROCESS: BiCMOS

High-Supply-Voltage, Precision Voltage Reference in SOT23

Package Information

(The package drawing(s) in this data sheet may not reflect the most current specifications. For the latest package outline information, go to www.maxim-ic.com/packages.



High-Supply-Voltage, Precision Voltage Reference in SOT23

Package Information (continued)

(The package drawing(s) in this data sheet may not reflect the most current specifications. For the latest package outline information go to www.maxim-ic.com/packages.)

MAX6035

SOICN.EPS

| DIM | INCHES | | MILLIMETERS | |
|-----|-----------|-------|-------------|------|
| | MIN | MAX | MIN | MAX |
| A | 0.053 | 0.069 | 1.35 | 1.75 |
| A1 | 0.004 | 0.010 | 0.10 | 0.25 |
| B | 0.014 | 0.019 | 0.35 | 0.49 |
| C | 0.007 | 0.010 | 0.19 | 0.25 |
| e | 0.050 BSC | | 1.27 BSC | |
| E | 0.150 | 0.157 | 3.80 | 4.00 |
| H | 0.228 | 0.244 | 5.80 | 6.20 |
| L | 0.016 | 0.050 | 0.40 | 1.27 |

VARIATIONS:

| DIM | INCHES | | MILLIMETERS | | N | MS012 |
|-----|--------|-------|-------------|-------|----|-------|
| | MIN | MAX | MIN | MAX | | |
| D | 0.189 | 0.197 | 4.80 | 5.00 | 8 | AA |
| D | 0.337 | 0.344 | 8.55 | 8.75 | 14 | AB |
| D | 0.386 | 0.394 | 9.80 | 10.00 | 16 | AC |

NOTES:

1. D&E DO NOT INCLUDE MOLD FLASH.
2. MOLD FLASH OR PROTRUSIONS NOT TO EXCEED 0.15mm (.006").
3. LEADS TO BE COPLANAR WITHIN 0.10mm (.004").
4. CONTROLLING DIMENSION: MILLIMETERS.
5. MEETS JEDEC MS012.
6. N = NUMBER OF PINS.

| | |
|--|---------------------------------|
| | |
| <small>PROPRIETARY INFORMATION</small> | |
| TITLE: PACKAGE OUTLINE, .150" SOIC | |
| APPROVAL | DOCUMENT CONTROL NO. 21-0041 |
| REV. B | 1/1 |

Revision History

Pages changed at Rev 2: 1, 2, 3, 12, 15

Pages changed at Rev 3: 1, 2, 15

Maxim cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim product. No circuit patent licenses are implied. Maxim reserves the right to change the circuitry and specifications without notice at any time.

Maxim Integrated Products, 120 San Gabriel Drive, Sunnyvale, CA 94086 408-737-7600 _____ 15

SITE
SEARCHPART NO.
SEARCH

WHAT'S NEW

PRODUCTS

SOLUTIONS

DESIGN

APPNOTES

SUPPORT

BUY

COMPANY

MEMBERS

[Maxim](#) > [Products](#) > [Voltage References](#)

MAX6035

High-Supply-Voltage, Precision Voltage Reference in SOT23

Low-Power Voltage Reference in SOT23 Replaces Industry-Standard Ref02 and Ref43

[QuickView](#)[Technical Documents](#)[Ordering Info](#)[More Information](#)[All](#)

Ordering Information

Notes:

1. Other options and links for purchasing parts are listed at: <http://www.maxim-ic.com/sales>.
2. [Didn't Find What You Need?](#) Ask our applications engineers. Expert assistance in finding parts, usually within one business day.
3. Part number suffixes: T or T&R = tape and reel; + = RoHS/lead-free; # = RoHS/lead-exempt. More: See [Full Data Sheet](#) or [Part Naming Conventions](#).
4. * Some packages have variations, listed on the drawing. "PkgCode/Variation" tells which variation the product uses.

Devices: 1-26 of 26

| MAX6035 | Free Sample | Buy | Package: TYPE PINS FOOTPRINT DRAWING CODE/VAR * | Temp | RoHS/Lead-Free? Materials Analysis |
|----------------|-------------|-----|--|---------------|--|
| MAX6035ESA25+T | | | SOIC;8 pin;31 mm Dwg: 21-0041B (PDF) Use pkgcode/variation: S8+2* | -40C to +85C | RoHS/Lead-Free: Lead Free Materials Analysis |
| MAX6035ESA25+ | | | SOIC;8 pin;31 mm Dwg: 21-0041B (PDF) Use pkgcode/variation: S8+2* | -40C to +85C | RoHS/Lead-Free: Lead Free Materials Analysis |
| MAX6035AAUR30+ | | | SOT-23;3 pin;8 mm Dwg: 21-0051H (PDF) Use pkgcode/variation: U3+1* | -40C to +125C | RoHS/Lead-Free: Lead Free Materials Analysis |
| MAX6035AAUR30 | | | SOT-23;3 pin;8 mm Dwg: 21-0051H (PDF) Use pkgcode/variation: U3-1* | -40C to +125C | RoHS/Lead-Free: No Materials Analysis |
| MAX6035AAUR50+ | | | SOT-23;3 pin;8 mm Dwg: 21-0051H (PDF) Use pkgcode/variation: U3+1* | -40C to +125C | RoHS/Lead-Free: Lead Free Materials Analysis |
| MAX6035AAUR50 | | | SOT-23;3 pin;8 mm Dwg: 21-0051H (PDF) Use pkgcode/variation: U3-1* | -40C to +125C | RoHS/Lead-Free: No Materials Analysis |
| MAX6035BAUR25+ | | | SOT-23;3 pin;8 mm Dwg: 21-0051H (PDF) Use pkgcode/variation: U3+1* | -40C to +125C | RoHS/Lead-Free: Lead Free Materials Analysis |
| MAX6035BAUR25 | | | SOT-23;3 pin;8 mm Dwg: 21-0051H (PDF) Use pkgcode/variation: U3-1* | -40C to +125C | RoHS/Lead-Free: No Materials Analysis |
| MAX6035BAUR30+ | | | SOT-23;3 pin;8 mm Dwg: 21-0051H (PDF) Use pkgcode/variation: U3+1* | -40C to +125C | RoHS/Lead-Free: Lead Free Materials Analysis |
| MAX6035BAUR30 | | | SOT-23;3 pin;8 mm Dwg: 21-0051H (PDF) Use pkgcode/variation: U3-1* | -40C to +125C | RoHS/Lead-Free: No Materials Analysis |
| MAX6035BAUR50+ | | | SOT-23;3 pin;8 mm Dwg: 21-0051H (PDF) Use pkgcode/variation: U3+1* | -40C to +125C | RoHS/Lead-Free: Lead Free Materials Analysis |
| MAX6035BAUR50 | | | SOT-23;3 pin;8 mm Dwg: 21-0051H (PDF) Use pkgcode/variation: U3-1* | -40C to +125C | RoHS/Lead-Free: No Materials Analysis |

| | | | | | |
|-----------------|--|--|--|---------------|--|
| MAX6035AAUR25 | | | SOT-23;3 pin;8 mm Dwg: 21-0051H (PDF) Use pkgcode/variation: U3-1* | -40C to +125C | RoHS/Lead-Free: No Materials Analysis |
| MAX6035AAUR25+ | | | SOT-23;3 pin;8 mm Dwg: 21-0051H (PDF) Use pkgcode/variation: U3+1* | -40C to +125C | RoHS/Lead-Free: Lead Free Materials Analysis |
| MAX6035BAUR50-T | | | SOT-23;3 pin;8 mm Dwg: 21-0051H (PDF) Use pkgcode/variation: U3-1* | -40C to +125C | RoHS/Lead-Free: No Materials Analysis |
| MAX6035AAUR25-T | | | SOT-23;3 pin;8 mm Dwg: 21-0051H (PDF) Use pkgcode/variation: U3-1* | -40C to +125C | RoHS/Lead-Free: No Materials Analysis |
| MAX6035AAUR30-T | | | SOT-23;3 pin;8 mm Dwg: 21-0051H (PDF) Use pkgcode/variation: U3-1* | -40C to +125C | RoHS/Lead-Free: No Materials Analysis |
| MAX6035BAUR25-T | | | SOT-23;3 pin;8 mm Dwg: 21-0051H (PDF) Use pkgcode/variation: U3-1* | -40C to +125C | RoHS/Lead-Free: No Materials Analysis |
| MAX6035BAUR30-T | | | SOT-23;3 pin;8 mm Dwg: 21-0051H (PDF) Use pkgcode/variation: U3-1* | -40C to +125C | RoHS/Lead-Free: No Materials Analysis |
| MAX6035AAUR25+T | | | SOT-23;3 pin;8 mm Dwg: 21-0051H (PDF) Use pkgcode/variation: U3+1* | -40C to +125C | RoHS/Lead-Free: Lead Free Materials Analysis |
| MAX6035AAUR30+T | | | SOT-23;3 pin;8 mm Dwg: 21-0051H (PDF) Use pkgcode/variation: U3+1* | -40C to +125C | RoHS/Lead-Free: Lead Free Materials Analysis |
| MAX6035AAUR50+T | | | SOT-23;3 pin;8 mm Dwg: 21-0051H (PDF) Use pkgcode/variation: U3+1* | -40C to +125C | RoHS/Lead-Free: Lead Free Materials Analysis |
| MAX6035BAUR25+T | | | SOT-23;3 pin;8 mm Dwg: 21-0051H (PDF) Use pkgcode/variation: U3+1* | -40C to +125C | RoHS/Lead-Free: Lead Free Materials Analysis |
| MAX6035BAUR30+T | | | SOT-23;3 pin;8 mm Dwg: 21-0051H (PDF) Use pkgcode/variation: U3+1* | -40C to +125C | RoHS/Lead-Free: Lead Free Materials Analysis |
| MAX6035BAUR50+T | | | SOT-23;3 pin;8 mm Dwg: 21-0051H (PDF) Use pkgcode/variation: U3+1* | -40C to +125C | RoHS/Lead-Free: Lead Free Materials Analysis |
| MAX6035AAUR50-T | | | SOT-23;3 pin;8 mm Dwg: 21-0051H (PDF) Use pkgcode/variation: U3-1* | -40C to +125C | RoHS/Lead-Free: No Materials Analysis |

Didn't Find What You Need?

- [Next Day Product Selection Assistance from Applications Engineers](#)
- [Parametric Search](#)
- [Applications Help](#)

QuickView

[Description](#)
[Key Features](#)
[Applications/Uses](#)
[Key Specifications](#)
[Diagram](#)

Technical Documents

[Data Sheet](#)
[Application Notes](#)
[Design Guides](#)
[Engineering Journals](#)
[Reliability Reports](#)
[Software/Models](#)
[Evaluation Kits](#)

Ordering Info

[Price and Availability](#)
[Samples](#)
[Buy Online](#)
[Package Information](#)
[Lead-Free Information](#)

More Information

[Related Products](#)
[Notes and Comments](#)
[Evaluation Kits](#)

Document Ref.: 19-2606; Rev 3; 2006-11-20
This page last modified: 2007-08-01

[CONTACT US: SEND US AN EMAIL](#)