
LE UW S2WN

OSRAM OSTAR® Stage

Outstanding brightness and luminance due to surface emission and low Rth







Applications

- Architecture

Area Lights

Downlights/Spotlights

— Mood Lighting

Stage Lighting (LED & Laser)

Features:

- Package: compact lightsource in multi chip SMT technology with glass window on top

- Chip technology: UX:3

- Typ. Radiation: 120°

- Color: Cx = 0.31, Cy = 0.32 acc. to CIE 1931 (● ultra white)

Corrosion Robustness Class: 3B

Ordering Information

Type Luminous Flux $^{1)}$ Ordering Code $I_F = 1000 \text{ mA}$ Φ_V LE UW S2WN-RASA-CQ 1120 ... 2240 lm Q65112A7619



LE UW S2WN

Maximum Ratings			
Parameter	Symbol		Values
Operating Temperature	T _{op}	min. max.	-40 °C 125 °C
Storage Temperature	T _{stg}	min. max.	-40 °C 125 °C
Junction Temperature	T _i	max.	150 °C
Forward Current T _S = 25 °C; per chip	I _F	min. max.	40 mA 3000 mA
Reverse current ²⁾	I _R	max.	200 mA



Characteristics

 I_F = 1000 mA; T_S = 25 °C; per chip


Parameter	Symbol		Values
Chromaticity Coordinate 3)	Сх	typ.	0.31
	Су	typ.	0.32
Viewing angle at 50% $\rm I_{\rm V}$	2φ	typ.	130 °
Radiating surface	A_{color}	typ.	2.1 x 2.1 mm ²
Partial Flux acc. CIE 127:2007 $^{4)}$ I _F = 1000 mA	Φ _{E/V, 120°}	typ.	0.77
Forward Voltage 5)	V _F	min.	2.70 V
I _F = 1000 mA; per Chip	·	typ.	3.00 V
		max.	3.40 V
Reverse voltage (ESD device)	V_{RESD}	min.	45 V
Reverse voltage ²⁾ I _R = 20 mA	V_R	max.	1.2 V
Real thermal resistance junction/solderpoint 6)	R _{thJS real}	typ.	1.20 K / W
		max.	1.40 K / W
Electrical thermal resistance junction/solderpoint ⁶⁾	R _{thJS elec.}	typ.	0.85 K / W
with efficiency η_e = 29 %		max.	0.99 K / W

Brightness Groups

Group	Luminous Flux ¹⁾ $I_F = 1000 \text{ mA}$ min. Φ_V	Luminous Flux ¹⁾ $I_F = 1000 \text{ mA}$ max. Φ_V
RA	1120 lm	1400 lm
RB	1400 lm	1800 lm
SA	1800 lm	2240 lm



Chromaticity Coordinate Groups



Chromaticity Coordinate Groups 3)

Group	Cx	Су
CQ	0.3190	0.3507
	0.3267	0.3370
	0.3107	0.3043
	0.3020	0.3178

Group Name on Label


Example: RA-CQ

Brightness Color Chromaticity

RA CQ


Relative Spectral Emission 4)

 Φ_{rel} = f (\lambda); I $_{_{\rm F}}$ = 1000 mA; T $_{_{\rm J}}$ = 25 °C; per Chip



Radiation Characteristics 4)


$$I_{rel} = f(\phi); T_J = 25 °C$$






Relative Partial Flux 4)

 $\Phi_{V}(2\phi)/\Phi_{V}(180^{\circ}) = f(\phi); T_{J} = 25 {\circ}C$




Forward current 4), 7)

$$I_F = f(V_F); T_J = 25 °C; per Chip$$




Relative Luminous Flux 4), 7)

 $\Phi_{V}/\Phi_{V}(1000 \text{ mA}) = f(I_{F}); T_{J} = 25 \text{ °C}; per Chip}$



Chromaticity Coordinate Shift 4)


 ΔCx , $\Delta Cy = f(I_F)$; $T_J = 25$ °C; per Chip



 I_{F} / mA


Forward Voltage 4)

 $\Delta V_{_F} = V_{_F} - V_{_F} (25~^{\circ}\text{C}) = f(T_{_j}); I_{_F} = 1000~\text{mA}; per Chip}$




Relative Luminous Flux 4)

 $\Phi_{v}/\Phi_{v}(25~^{\circ}\text{C}) = f(T_{i}); I_{F} = 1000~\text{mA}; per Chip}$




Chromaticity Coordinate Shift 4)

 ΔCx , $\Delta Cy = f(T_j)$; $I_F = 1000$ mA; per Chip



Dimensional Drawing 8)



C67062-A0251-A1-03

Further Information:

Approximate Weight: 91.0 mg

Corrosion test: Class: 3B

Test condition: 40°C / 90 % RH / 15 ppm H₂S / 14 days (stricter than IEC

60068-2-43)

ESD advice: The device is protected by ESD device which is connected in parallel to the

Chip.




Electrical Internal Circuit


Pinning:

P1 Anode die 1 P5 Cathode die 3 P2 Cathode die 1 P6 Anode die 3

P3 Cathode die 2 P7 Cathode die 4 P4 Anode die 2 P8 Anode die 4



Recommended Solder Pad 8)




For superior solder joint connectivity results we recommend soldering under standard nitrogen atmosphere. Package not suitable for any kind of wet cleaning or ultrasonic cleaning.



Reflow Soldering Profile

Product complies to MSL Level 2 acc. to JEDEC J-STD-020E




Profile Feature	Symbol Pb-Free (SnAgCu) Assembly			Unit	
		Minimum	Recommendation	Maximum	
Ramp-up rate to preheat*)			2	3	K/s
25 °C to 150 °C					
Time t _s	$t_{\scriptscriptstyle{S}}$	60	100	120	S
T_{Smin} to T_{Smax}					
Ramp-up rate to peak*)			2	3	K/s
T_{Smax} to T_{P}					
Liquidus temperature	T_{L}		217		°C
Time above liquidus temperature	$t_{\scriptscriptstyle L}$		80	100	S
Peak temperature	T_{P}		245	260	°C
Time within 5 °C of the specified peak temperature T _P - 5 K	t _P	10	20	30	S
Ramp-down rate*			3	6	K/s
T _P to 100 °C					
Time				480	S
25 °C to T _P					


All temperatures refer to the center of the package, measured on the top of the component



^{*} slope calculation DT/Dt: Dt max. 5 s; fulfillment for the whole T-range


Taping 8)





C63062-A4278-B8-01

Tape and Reel 9)




Reel Dimensions

Α	W	N_{\min}	W ₁	W_{2max}	Pieces per PU
180 mm	12 + 0.3 / - 0.1 mm	60 mm	12.4 + 2 mm	18.4 mm	500

Barcode-Product-Label (BPL)




Dry Packing Process and Materials 8)



Moisture-sensitive product is packed in a dry bag containing desiccant and a humidity card according JEDEC-STD-033.



Type Designation System





Notes

The evaluation of eye safety occurs according to the standard IEC 62471:2006 (photo biological safety of lamps and lamp systems). Within the risk grouping system of this IEC standard, the device specified in this data sheet falls into the class moderate risk (exposure time 0.25 s). Under real circumstances (for exposure time, conditions of the eye pupils, observation distance), it is assumed that no endangerment to the eye exists from these devices. As a matter of principle, however, it should be mentioned that intense light sources have a high secondary exposure potential due to their blinding effect. When looking at bright light sources (e.g. headlights), temporary reduction in visual acuity and afterimages can occur, leading to irritation, annoyance, visual impairment, and even accidents, depending on the situation.

Subcomponents of this device contain, in addition to other substances, metal filled materials including silver. Metal filled materials can be affected by environments that contain traces of aggressive substances. Therefore, we recommend that customers minimize device exposure to aggressive substances during storage, production, and use. Devices that showed visible discoloration when tested using the described tests above did show no performance deviations within failure limits during the stated test duration. Respective failure limits are described in the IEC60810.

For further application related information please visit www.osram-os.com/appnotes



Disclaimer

Attention please!

The information describes the type of component and shall not be considered as assured characteristics. Terms of delivery and rights to change design reserved. Due to technical requirements components may contain dangerous substances.

For information on the types in question please contact our Sales Organization.

If printed or downloaded, please find the latest version on the OSRAM OS website.

Packing

Please use the recycling operators known to you. We can also help you – get in touch with your nearest sales office. By agreement we will take packing material back, if it is sorted. You must bear the costs of transport. For packing material that is returned to us unsorted or which we are not obliged to accept, we shall have to invoice you for any costs incurred.

Product and functional safety devices/applications or medical devices/applications

OSRAM OS components are not developed, constructed or tested for the application as safety relevant component or for the application in medical devices.

OSRAM OS products are not qualified at module and system level for such application.

In case buyer – or customer supplied by buyer – considers using OSRAM OS components in product safety devices/applications or medical devices/applications, buyer and/or customer has to inform the local sales partner of OSRAM OS immediately and OSRAM OS and buyer and /or customer will analyze and coordinate the customer-specific request between OSRAM OS and buyer and/or customer.



Glossary

- Brightness: Brightness values are measured during a current pulse of typically 25 ms, with an internal reproducibility of ± 8 % and an expanded uncertainty of ± 11 % (acc. to GUM with a coverage factor of k = 3).
- Reverse Operation: This product is intended to be operated applying a forward current within the specified range. Applying any continuous reverse bias or forward bias below the voltage range of light emission shall be avoided because it may cause migration which can change the electro-optical characteristics or damage the LED.
- Chromaticity coordinate groups: Chromaticity coordinates are measured during a current pulse of typically 25 ms, with an internal reproducibility of ± 0.005 and an expanded uncertainty of ± 0.01 (acc. to GUM with a coverage factor of k = 3).
- Typical Values: Due to the special conditions of the manufacturing processes of semiconductor devices, the typical data or calculated correlations of technical parameters can only reflect statistical figures. These do not necessarily correspond to the actual parameters of each single product, which could differ from the typical data and calculated correlations or the typical characteristic line. If requested, e.g. because of technical improvements, these typ. data will be changed without any further notice.
- Forward Voltage: The forward voltage is measured during a current pulse of typically 8 ms, with an internal reproducibility of ± 0.05 V and an expanded uncertainty of ± 0.1 V (acc. to GUM with a coverage factor of k = 3).
- Thermal Resistance: Rth max is based on statistic values (6σ) .
- Characteristic curve: In the range where the line of the graph is broken, you must expect higher differences between single devices within one packing unit.
- Tolerance of Measure: Unless otherwise noted in drawing, tolerances are specified with ±0.1 and dimensions are specified in mm.
- Tape and Reel: All dimensions and tolerances are specified acc. IEC 60286-3 and specified in mm.



LE UW S2WN

Revision	Revision History			
Version	Date	Change		
1.1	2019-06-27	Dimensional Drawing		
1.2	2020-06-03	Schematic Transportation Box Dimensions of Transportation Box		



Published by OSRAM Opto Semiconductors GmbH EU RoHS and China RoHS compliant product Leibnizstraße 4, D-93055 Regensburg www.osram-os.com © All Rights Reserved.

此产品符合欧盟 RoHS 指令的要求; 按照中国的相关法规和标准,不含有毒有害物质或元素。

