Data sheet

BMF055 Custom programmable 9-axis motion sensor



BMF055: data sheet	
Document revision	0.4
Document release date	November 2020
Document number	BST-BMF055-DS000-04
Technical reference code(s)	0 273 141 235
Notes	Data in this document are subject to change without notice. Product photos and pictures are for illustration purposes only and may differ from the real product's appearance.



BMF055

Custom programmable 9-axis motion sensor

Basic Description

Key features:

•	3 sensors in one device	an advanced triaxial 16bit gyroscope, a versatile, leading edge triaxial 14bit accelerometer and a full performance geomagnetic sensor
•	Small package	LGA package 28 pins Footprint 3.8 x 5.2 mm², height 1.13 mm²
•	Common voltage supplies	V_{DD} voltage range: 2.4V to 3.6V
•	Consumer electronics suite	MSL1, RoHS compliant, halogen-free Operating temperature: -40°C +85°C

Key features of integrated sensors:

Accelerometer features

Programmable functionality

Acceleration ranges ±2g/±4g/±8g/±16g Low-pass filter bandwidths 1kHz - <8Hz Operation modes:

- Normal
- Suspend
- Low power
- Standby
- Deep suspend
- On-chip interrupt controller
- Motion-triggered interrupt-signal generation for any-motion (slope) detection
- slow or no motion recognition
- high-g detection

BST-BMF055-DS000-04 | Revision 0.4 | November 2020

[©] Bosch Sensortec GmbH reserves all rights even in the event of industrial property rights. We reserve all rights of disposal such as copying and passing on to third parties. BOSCH and the symbol are registered trademarks of Robert Bosch GmbH, Germany. Note: Specifications within this document are subject to change without notice.



Gyroscope features

• Programmable functionality

On-chip interrupt controller

Ranges switchable from ±125°/s to ±2000°/s Low-pass filter bandwidths 523Hz - 12Hz Operation modes:

- Normal
- Fast power up
- Deep suspend
- Suspend
- Advanced power save
- Motion-triggered interrupt-signal generation for
 - any-motion (slope) detection
 - high rate

Magnetometer features

Flexible functionality

Magnetic field range typical $\pm 1300\mu$ T (x-, y-axis); $\pm 2500\mu$ T (z-axis) Magnetic field resolution of ~0.3 μ T Operating modes:

- Low power
- Regular
- Enhanced regular
- High Accuracy

Power modes:

- Normal
- Sleep
- Suspend
- Force

Typical applications

- Navigation
- Robotics
- Fitness and well-being
- Augmented reality
- Context awareness
- Tablets and ultra-books

[©] Bosch Sensortec GmbH reserves all rights even in the event of industrial property rights. We reserve all rights of disposal such as copying and passing on to third parties. BOSCH and the symbol are registered trademarks of Robert Bosch GmbH, Germany. Note: Specifications within this document are subject to change without notice.



General description

The BMF055 is a System in Package (SiP), integrating a triaxial 14-bit accelerometer, a triaxial 16-bit gyroscope with a range of ± 2000 degrees per second, a triaxial geomagnetic sensor and a 32-bit cortex M0+ microcontroller in a single package.

The corresponding chip-sets are integrated into one single 28-pin LGA 3.8mm x 5.2mm x 1.1 mm housing.

BST-BMF055-DS000-04 | Revision 0.4 | November 2020

© Bosch Sensortec GmbH reserves all rights even in the event of industrial property rights. We reserve all rights of disposal such as copying and passing on to third parties. BOSCH and the symbol are registered trademarks of Robert Bosch GmbH, Germany. Note: Specifications within this document are subject to change without notice.



Contents

BASIC DESCRIPTION	2
1. SPECIFICATION	7
1.1 ELECTRICAL SPECIFICATION	7
1.2 ELECTRICAL AND PHYSICAL CHARACTERISTICS, MEASUREMENT PERFORMANCE	8
2. ABSOLUTE MAXIMUM RATINGS	12
3. FUNCTIONAL DESCRIPTION	13
3.1 ARCHITECTURE	13
3.2 POWER MANAGEMENT	13
4. ACCELEROMETER	14
5. GYROSCOPE	14
6. MAGNETOMETER	14
7. MICROCONTROLLER	14
8. SYSTEM SETUP	15
8.1 INTERNAL SENSOR CONNECTION	15
8.2 PROGRAMMING AND DEBUG INTERFACE	15
8.3 Sensing Axes Orientation	15
9. PIN-OUT AND CONNECTION DIAGRAM	16
9.1 PIN DESCRIPTION	16
9.2 CONNECTION DIAGRAM	17
10. PACKAGE	18
10.1 OUTLINE DIMENSIONS	18
10.2 LANDING PATTERN RECOMMENDATION	19
10.3 Marking	19
10.4 Soldering Guidelines	19
10.5 HANDLING INSTRUCTIONS	19
10.6 TAPE AND REEL SPECIFICATION	20
10.7 Environmental safety	20
10.7.1 HALOGEN CONTENT	20
11. LEGAL DISCLAIMER	21
11.1 ENGINEERING SAMPLES	

BST-BMF055-DS000-04 | Revision 0.4 | November 2020

Bosch Sensortec

© Bosch Sensortec GmbH reserves all rights even in the event of industrial property rights. We reserve all rights of disposal such as copying and passing on to third parties. BOSCH and the symbol are registered trademarks of Robert Bosch GmbH, Germany. Note: Specifications within this document are subject to change without notice.

BOSCH	BMF055 Data sheet	Page 6	
11.2 PRODUCT	USE	2	!1
11.3 APPLICATION	ON EXAMPLES AND HINTS	2	1

12. DOCUMENT HISTORY AN	D MODIFICATIONS	 22

BST-BMF055-DS000-04 | Revision 0.4 | November 2020

© Bosch Sensortec GmbH reserves all rights even in the event of industrial property rights. We reserve all rights of disposal such as copying and passing on to third parties. BOSCH and the symbol are registered trademarks of Robert Bosch GmbH, Germany. Note: Specifications within this document are subject to change without notice.



1. Specification

If not stated otherwise, the given values are over lifetime and full performance temperature and voltage ranges, minimum/maximum values are ± 3 sigma.

1.1 Electrical specification

OPERATING CONDITIONS BMF055						
Parameter	Symbol	Condition	Min	Тур	Мах	Unit
Supply Voltage (only Sensors)	Vdd	-	2.4		3.6	V
Supply Voltage (µC and I/O Domain)	V _{DDIO}		1.7		3.6	V
Voltage Input Low Level (UART, I2C)	V _{DDIO_VIL}	V _{DDIO} = 1.7-2.7V			0.25	VDDIO
LOW LEVEL (UAITI, 120)		V _{DDIO} = 2.7-3.6V			0.3	Vddio
Voltage Input High Level (UART, I2C)	Vddio_vih	V _{DDIO} = 1.7-2.7V	0.7			VDDIO
High Level (UART, 12C)		V _{DDIO} = 2.7-3.6V	0.55			V _{DDIO}
Voltage Output Low Level (UART, I2C)	V _{DDIO_VOL}	$V_{DDIO} > 3V$, I_{OL} = 20mA		0.1	0.2	V _{DDIO}
Voltage Output High Level (UART, I2C)	Vddio_voh	$V_{DDIO} > 3V$, $I_{OH} = 10mA$	0.9	0.8		V _{DDIO}
POR Voltage threshold on VDDIO-IN rising	V _{DDIO_POT+}	V _{DDIO} falls at 1V/ms or slower		1.45		V
POR Voltage threshold on VDDIO-IN falling	VDDIO_POT-			0.99		V
Operating Temperature	TA	Min and Max are in this case min and max and not 3s value	-40		+85	°C
Total supply current normal mode at T₄ (9DOF @100Hz output data rate)	Idd + Iddio	V_{DD} = 3V, V_{DDIO} = 2.5V			13.7	mA
Total supply current Low power mode; interrupt driven at T _A (80% suspend mode and 20% normal mode with 9DOF @100Hz output data rate)	Idd_lpm	$V_{DD} = 3V, V_{DDIO} = 2.5V$		2.6		mA
Total supply current suspend mode at $T_{\rm A}$	IDD_SuM	V_{DD} = 3V, V_{DDIO} = 2.5V			0.12	mA

Table 1-1: Electrical parameter specification

Note: The resulting total supply current is subject to vary depending on the custom specific firmware which runs in the sensor. For additional information with respect to the individual sensors (accelerometer, gyroscope and magnetometer) and to the MCU please refer the respective datasheet.

[©] Bosch Sensortec GmbH reserves all rights even in the event of industrial property rights. We reserve all rights of disposal such as copying and passing on to third parties. BOSCH and the symbol are registered trademarks of Robert Bosch GmbH, Germany. Note: Specifications within this document are subject to change without notice.

1.2 Electrical and physical characteristics, measurement performance

Table 1-2: Electrical	characteristics	BMF055
-----------------------	-----------------	--------

OPERATING CONDITIONS ACCELEROMETER							
Parameter	Symbol	Condition	Min	Тур	Max	Units	
Acceleration Range	g FS2g	Selectable		±2		g	
	g FS4g	via serial digital interface		±4		g	
	g FS8g			±8		g	
	g FS16g			±16		g	
		OUTPUT SIGNAL ACCELERO	METER				
Parameter	Symbol	Condition	Min	Тур	Max	Units	
Sensitivity	S	All g_{FSXg} Values, $T_A=25^{\circ}C$		1		LSB/mg	
Sensitivity tolerance	Stol	Ta=25°C, g _{FS2g}		±1	±4	%	
Sensitivity Temperature Drift	TCS	g_{FS2g} , Nominal V _{DD} supplies, Temp operating conditions		±0.03	±0.02	%/K	
Sensitivity Supply Volt. Drift	S_{VDD}	g_{FS2g} , T_A =25°C, V _{DD_min} \leq V _{DD} \leq V _{DD_max}		0.05	0.2	%/V	
Zero-g Offset (x,y.z)	Off _{xyz}	g_{FS2g} , T_A =25°C, nominal V_{DD} supplies, over life-time	-150	±80	+150	mg	
Zero-g Offset Temperature Drift	тсо	g_{FS2g} , Nominal V _{DD} supplies		±1	+/-3.5	mg/K	
Zero-g Offset Supply Volt. Drift	Offvdd	g_{FS2g} , $T_A=25^{\circ}C$, $V_{DD_min} \le V_{DD} \le V_{DD_max}$		0.5		mg/V	
Bandwidth	bw ₈	2 nd order filter, bandwidth programmable		8		Hz	
	bw ₁₆	programmable		16		Hz	
	bw ₃₁			31		Hz	
	bw ₆₃			63		Hz	
	bw ₁₂₅			125		Hz	
	bw ₂₅₀			250		Hz	
	bw ₅₀₀			500		Hz	
	bw1000			1,000		Hz	
Nonlinearity	NL	best fit straight line, g_{FS2g}		±0.5	+/-2	%FS	
Output Noise Density	Nrms	g _{FS2g} , T _A =25°C Nominal V _{DD} supplies Normal mode		150	190	µg/√Hz	
	r	MECHANICAL CHARACTERISTICS ACC	CELEROMETER				
Parameter	Symbol	Condition	Min	Тур	Max	Units	
Cross Axis Sensitivity	CAS	relative contribution between any two of the three axes		1	2	%	

BST-BMF055-DS000-04 | Revision 0.4 | November 2020

 E_A

Alignment Error

Bosch Sensortec

2

±0.5

© Bosch Sensortec GmbH reserves all rights even in the event of industrial property rights. We reserve all rights of disposal such as copying and passing on to third parties. BOSCH and the symbol are registered trademarks of Robert Bosch GmbH, Germany. Note: Specifications within this document are subject to change without notice.

relative to package outline



BMF055 Data sheet

OPERATING CONDITIONS GYROSCOPE							
Parameter	Symbol	Condition	Min	Тур	Max	Unit	
Rate Range	R _{FS125}	Selectable via serial digital interface		125		°/s	
	R _{FS250}	via serial digital interface		250		°/s	
	R _{FS500}			500		°/s	
	R _{FS1000}			1,000		°/s	
	R _{FS2000}			2,000		°/s	
	OUTPUT SIGNAL GYROSCOPE						
Sensitivity via register Map	S	Ta=25°C		16.0 900		LSB/°/s rad/s	
Sensitivity tolerance	Stol	Ta=25°C, R _{FS2000}		±1	±3	%	
Sensitivity Change over Temperature	TCS	Nominal V _{DD} supplies -40°C $\leq T_A \leq +85$ °C R _{FS2000}		±0.03	±0.07	%/K	
Sensitivity Supply Volt. Drift	Svdd	$T_A=25^{\circ}C$, $V_{DD_{min}} \le V_{DD} \le V_{DD_{max}}$		<0.4		%/V	
Nonlinearity	NL	best fit straight line R _{FS1000} , R _{FS2000}		±0.05	±0.2	%FS	
Zero-rate Offset	$\begin{array}{c} \text{Off} \ \Omega_x \ \ \Omega_y \ \text{and} \\ \Omega_z \end{array}$	Nominal V_{DD} supplies T_{A}^{-} =25°C, Slow and fast offset cancellation off	-3	±1	+3	°/s	
Zero-Ω Offset Change over Temperature	тсо	Nominal V _{DD} supplies -40°C $\leq T_A \leq$ +85°C R _{FS2000}		±0.015	±0.03	°/s per K	
Zero-Ω Offset Supply Volt. Drift	$Off\Omega$ VDD	$T_A=25^{\circ}C$, $V_{DD_{min}} \le V_{DD} \le V_{DD_{max}}$		0.1		°/s /V	
Output Noise	n ms	rms, BW=47Hz (@ 0.014°/s/					

© Bosch Sensortec GmbH reserves all rights even in the event of industrial property rights. We reserve all rights of disposal such as copying and passing on to third parties. BOSCH and the symbol are registered trademarks of Robert Bosch GmbH, Germany. Note: Specifications within this document are subject to change without notice.

BOSCH	BMF055 Data sheet						
Bandwidth BW	f _{-3dB}			523 230 116 64 47 32 23 12		Hz	
MECHANICAL CHARACTERISTICS GYROSCOPE							
Cross Axis Sensitivity	CAS	Sensitivity to stimuli in non-sense-direction		±1	±3	%	
OPERATING CONDITIONS MAGNETOMETER							
Parameter	Symbol	Condition	Min	Тур	Max	Units	
Magnetic field range ¹	Brg,xy	TA=25°C	±1200	±1300		μT	
	Brg,z		±2000	±2500		μΤ	
Magnetometer heading accuracy ²	As heading	30µT horizontal geomagnetic field component, TA=25°C			±2.5	deg	
		MAGNETOMETER OUTPUT SI	GNAL				
Parameter	Symbol	Condition	Min	Тур	Max	Unit	
Device Resolution	D _{res,m}	T _A =25°C		0.3		μT	
Gain error ³	Gerr,m	After API compensation T _A =25°C Nominal V _{DD} supplies		±5	±8	%	
Sensitivity Temperature Drift	TCSm	After API compensation $-40^{\circ}C \le T_A \le +85^{\circ}C$ Nominal V _{DD} supplies		±0.01	±0.03	%/K	
Zero-B offset	OFFm	T _A =25°C		±40		μT	
Zero-B offset Temperature Drift	TCOm	$\text{-40°C} \leq T_{\text{A}} \leq \text{+85°C}$		±0.23	±0.37	μT/K	
Full-scale Nonlinearity	NL _{m, FS}	best fit straight line			1	%FS	

³ Definition:

 $^{^1}$ Full linear measurement range considering sensor offsets. 2 The heading accuracy depends on hardware and software. A fully calibrated sensor and ideal tilt compensation are assumed. - 1

BST-BMF055-DS000-04 | Revision 0.4 | November 2020

[©] Bosch Sensortec GmbH reserves all rights even in the event of industrial property rights. We reserve all rights of disposal such as copying and passing on to third parties. BOSCH and the symbol are registered trademarks of Robert Bosch GmbH, Germany. Note: Specifications within this document are subject to change without notice.

BOSCH	BMF055 Data sheet					9 11
Output Noise	Nrms,lp,m,xy	Low power preset x, y-axis, $T_A=25^{\circ}C$ Nominal V _{DD} supplies		1.0		μT
	Nrms,Ip,m,z	Low power preset z-axis, $T_A=25^{\circ}C$ Nominal V _{DD} supplies		1.4		μT
	Nrms,rg,m	Regular preset T₄=25°C Nominal V _{DD} supplies		0.6		μT
	n _{rms,eh,m}	Enhanced regular preset T _A =25°C Nominal V _{DD} supplies		0.5		μT
	n _{rms,ha,m}	High accuracy preset T _A =25°C Nominal V _{DD} supplies		0.3		μT
Power Supply Rejection Rate	PSRRm	$T_A=25^{\circ}C$ Nominal V_{DD} supplies		±0.5		μT/V

[©] Bosch Sensortec GmbH reserves all rights even in the event of industrial property rights. We reserve all rights of disposal such as copying and passing on to third parties. BOSCH and the symbol are registered trademarks of Robert Bosch GmbH, Germany. Note: Specifications within this document are subject to change without notice.



2. Absolute Maximum Ratings

Table 2-1: Absolute maximum ratings (preliminary target values)

Parameter	Symbol	Condition	Min	Мах	Units
Voltage at Supply Pin	V _{DD} Pin		-0.3	4.2	V
			-0.3	3.6	V
Voltage at any Logic Pin	$V_{\text{non-supply}} Pin$		-0.3	V _{DDIO} +0.3	V
Passive Storage Temp. Range	Trps	≤ 65% rel. H.	-50	+150	°C
Mechanical Shock	MechShock _{200µs}	Duration ≤ 200µs		10,000	g
	MechShock _{1ms}	Duration ≤ 1.0ms		2,000	g
	$MechShock_{\text{freefall}}$	Free fall onto hard surfaces		1.8	m
ESD	ESDHBM	HBM, at any Pin		2	kV
	ESDCDM	CDM		400	V
	ESD _{MM}	ММ		200	V

Note:

Stress above these limits may cause damage to the device. Exceeding the specified electrical limits may affect the device reliability or cause malfunction.

© Bosch Sensortec GmbH reserves all rights even in the event of industrial property rights. We reserve all rights of disposal such as copying and passing on to third parties. BOSCH and the symbol are registered trademarks of Robert Bosch GmbH, Germany. Note: Specifications within this document are subject to change without notice.



3. Functional Description

3.1 Architecture

The following figure shows the basic building blocks of the BMF055 device.




Figure 1: system architecture

3.2 Power management

The BMF055 has two distinct power supply pins:

- V_{DD} is the main power supply for the internal sensors
- V_{DDIO} is a separate power supply pin used for the supply of the μ C and the digital interfaces

For the switching sequence of power supply V_{DD} and V_{DDIO} it is mandatory that V_{DD} is powered on and driven to the specified level before or at the same time as V_{DDIO} is powered ON. Otherwise there are no limitations on the voltage levels of both pins relative to each other, as long as they are used within the specified operating range.

When the V_{DDIO} supply is switched off, all interface pins (CSB, MOSI, MISO, SCLK) must be kept close to GND_{IO} potential.

BST-BMF055-DS000-04 | Revision 0.4 | November 2020

[©] Bosch Sensortec GmbH reserves all rights even in the event of industrial property rights. We reserve all rights of disposal such as copying and passing on to third parties. BOSCH and the symbol are registered trademarks of Robert Bosch GmbH, Germany. Note: Specifications within this document are subject to change without notice.



4. Accelerometer

The accelerometer built into the BMF055 is equivalent to the BMA280. Please refer to the appropriate data sheet of that sensor for the functional description. The datasheet can be found at <u>https://www.bosch-sensortec.com/products/downloads/</u>.

The performance values of the in-built accelerometer differ from the values stated at the BMA280 data sheet and can be found in this document.

5. Gyroscope

The gyroscope built into the BMF055 is equivalent to the gyroscope in the BMI055. Please refer to the appropriate data sheet of that sensor for the functional description. The datasheet can be found at https://www.bosch-sensortec.com/products/downloads/.

The performance values of the in-built gyroscope differ from the values stated at the BMG160 data sheet and can be found in this document.

6. Magnetometer

The magnetometer built into the BMF055 is equivalent to the BMM150. Please refer to the appropriate data sheet of that sensor for the functional description. The datasheet can be found at <u>https://www.bosch-sensortec.com/products/downloads/</u>.

The performance values of the in-built magnetometer differ from the values stated at the BMM150 data sheet and can be found in this document.

7. Microcontroller

The microcontroller built into the BMF055 is a **Cortex-M0+** from Atmel:

- Atmel product family / series: **SAMD20** (general purpose microcontroller)
- Flash memory size: 256kB
- SRAM memory size: 32kB

Please refer to the appropriate data sheet from Atmel (<u>SAM D20 datasheet</u>) for further information.

[©] Bosch Sensortec GmbH reserves all rights even in the event of industrial property rights. We reserve all rights of disposal such as copying and passing on to third parties. BOSCH and the symbol are registered trademarks of Robert Bosch GmbH, Germany. Note: Specifications within this document are subject to change without notice.



8. System setup

8.1 Internal sensor connection


The sensors are connected to the MCU via SPI interface.

8.2 Programming and debug interface

The MCU can be programmed and debugged via $\ensuremath{\mathsf{Atmel}}$ debugging tools using the SWD interface.

8.3 Sensing Axes Orientation

The axis orientation is shown below.



BST-BMF055-DS000-04 | Revision 0.4 | November 2020

[©] Bosch Sensortec GmbH reserves all rights even in the event of industrial property rights. We reserve all rights of disposal such as copying and passing on to third parties. BOSCH and the symbol are registered trademarks of Robert Bosch GmbH, Germany. Note: Specifications within this document are subject to change without notice.

9. Pin-out and connection diagram

9.1 Pin description

BOSCH

If no port function is mentioned, the pin can be generally used as a general purpose IO. Details can be found in the Atmel SAM D20 datasheet. The pin names in this document are the same as in the microcontroller datasheet.


Pin No.	Pin Name	Internal connection	Port Function	
1	PB03	X	Accelerometer / gyroscope INT2	
2	GND	Х	GND	
3	VDD	Х	VDD	
4	PB02			
5	PB01			
6	PB00			
7	PA31		SWDIO	
8	PA30		SWCLK	
9	CAP		external capacitor	
10	PA28			
11	RESETN		RESETN	
12	PA27	Х	Gyroscope CSB	
13	PB23	Х	Accelerometer / gyroscope INT1	
14	PA24			
15	PA23			
16	PA22			
17	PA21			
18	PA20			
19	PB17			
20	PB16			
21	PA19	Х	Internal SPI: MISO	
22	PA18	Х	Accelerometer / magnetometer CSB	
23	PA17	Х	Internal SPI: SCLK	
24	PA16	Х	Internal SPI: MOSI	
25	GNDIO	Х	GNDIO	
26	PA01		optional: 32kHz Crystal Output	
27	PA00		optional: 32kHz Crystal Input	
28	VDDIO	Х	VDDIO	

[©] Bosch Sensortec GmbH reserves all rights even in the event of industrial property rights. We reserve all rights of disposal such as copying and passing on to third parties. BOSCH and the symbol are registered trademarks of Robert Bosch GmbH, Germany. Note: Specifications within this document are subject to change without notice.



BMF055 Data sheet

9.2 Connection diagram



nRESET

BST-BMF055-DS000-04 | Revision 0.4 | November 2020

Bosch Sensortec


© Bosch Sensortec GmbH reserves all rights even in the event of industrial property rights. We reserve all rights of disposal such as copying and passing on to third parties. BOSCH and the symbol are registered trademarks of Robert Bosch GmbH, Germany. Note: Specifications within this document are subject to change without notice.



10. Package

10.1 Outline dimensions

The sensor package is a standard LGA package; dimensions are shown in the following diagram. Units are in mm. Note: Unless otherwise specified tolerance = decimal ±0.1mm.



BOTTOM VIEW

[©] Bosch Sensortec GmbH reserves all rights even in the event of industrial property rights. We reserve all rights of disposal such as copying and passing on to third parties. BOSCH and the symbol are registered trademarks of Robert Bosch GmbH, Germany. Note: Specifications within this document are subject to change without notice.



10.2 Landing pattern recommendation

Please refer to the Handling, mounting and soldering instructions document for BNO055.

10.3 Marking

Labeling	Name	Symbol	Remark
	Pin 1 identifier	•	
SSS	First Row	S	Internal use
ссс	Second Row	Т	Internal use
	Third Row	С	Numerical counter

Table 10-1: Marking of mass production parts

10.4 Soldering Guidelines

The moisture sensitivity level of the BMF055 sensors corresponds to JEDEC Level 1, see also

- IPC/JEDEC J-STD-020C "Joint Industry Standard: Moisture/Reflow Sensitivity Classification for non-hermetic Solid State Surface Mount Devices"
- IPC/JEDEC J-STD-033A "Joint Industry Standard: Handling, Packing, Shipping and Use of Moisture/Reflow Sensitive Surface Mount Devices"

The sensor fulfils the lead-free soldering requirements of the above-mentioned IPC/JEDEC standard, i.e. reflow soldering with a peak temperature up to 260°C.

10.5 Handling instructions

Micromechanical sensors are designed to sense acceleration with high accuracy even at low amplitudes and contain highly sensitive structures inside the sensor element. The MEMS sensor can tolerate mechanical shocks up to several thousand g's. However, these limits might be exceeded in conditions with extreme shock loads such as e.g. hammer blow on or next to the sensor, dropping of the sensor onto hard surfaces etc.

We recommend avoiding g-forces beyond the specified limits during transport, handling and mounting of the sensors in a defined and qualified installation process.

This device has built-in protections against high electrostatic discharges or electric fields (e.g. 2kV HBM); however, anti-static precautions should be taken as for any other CMOS component. Unless otherwise specified, proper operation can only occur when all terminal voltages are kept within the supply voltage range. Unused inputs must always be tied to a defined logic voltage level.

BST-BMF055-DS000-04 | Revision 0.4 | November 2020

[©] Bosch Sensortec GmbH reserves all rights even in the event of industrial property rights. We reserve all rights of disposal such as copying and passing on to third parties. BOSCH and the symbol are registered trademarks of Robert Bosch GmbH, Germany. Note: Specifications within this document are subject to change without notice.



For more details on recommended handling, soldering and mounting please contact your local Bosch Sensortec sales representative and ask for the "Handling, soldering and mounting instructions" document.

10.6 Tape and reel specification

The BMF055 is shipped in a standard cardboard box. For details please refer to the BNO055 shipment details document.

10.7 Environmental safety

The BMF055 sensor meets the requirements of the EC restriction of hazardous substances (RoHS and RoHS2) directive, see also:

10.7.1 Halogen content

The BMF055 is halogen-free. For more details on the analysis results please contact your Bosch Sensortec representative.

[©] Bosch Sensortec GmbH reserves all rights even in the event of industrial property rights. We reserve all rights of disposal such as copying and passing on to third parties. BOSCH and the symbol are registered trademarks of Robert Bosch GmbH, Germany. Note: Specifications within this document are subject to change without notice.



11. Legal disclaimer

11.1 Engineering samples

Engineering Samples are marked with an asterisk (*), (E) or (e). Samples may vary from the valid technical specifications of the product series contained in this data sheet. They are therefore not intended or fit for resale to third parties or for use in end products. Their sole purpose is internal client testing. The testing of an engineering sample may in no way replace the testing of a product series. Bosch Sensortec assumes no liability for the use of engineering samples. The Purchaser shall indemnify Bosch Sensortec from all claims arising from the use of engineering samples.

11.2 Product use

Bosch Sensortec products are developed for the consumer goods industry. They may only be used within the parameters of this product data sheet. They are not fit for use in lifesustaining or safety-critical systems. Safety-critical systems are those for which a malfunction is expected to lead to bodily harm, death or severe property damage. In addition, they shall not be used directly or indirectly for military purposes (including but not limited to nuclear, chemical or biological proliferation of weapons or development of missile technology), nuclear power, deep sea or space applications (including but not limited to satellite technology).

Bosch Sensortec products are released on the basis of the legal and normative requirements relevant to the Bosch Sensortec product for use in the following geographical target market: BE, BG, DK, DE, EE, FI, FR, GR, IE, IT, HR, LV, LT, LU, MT, NL, AT, PL, PT, RO, SE, SK, SI, ES, CZ, HU, CY, US, CN, JP, KR, TW. If you need further information or have further requirements, please contact your local sales contact.

The resale and/or use of Bosch Sensortec products are at the purchaser's own risk and his own responsibility. The examination of fitness for the intended use is the sole responsibility of the purchaser.

The purchaser shall indemnify Bosch Sensortec from all third party claims arising from any product use not covered by the parameters of this product data sheet or not approved by Bosch Sensortec and reimburse Bosch Sensortec for all costs in connection with such claims.

The purchaser accepts the responsibility to monitor the market for the purchased products, particularly with regard to product safety, and to inform Bosch Sensortec without delay of all safety-critical incidents.

11.3 Application examples and hints

With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Bosch Sensortec hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights or copyrights of any third party. The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. They are provided for illustrative purposes only and no evaluation regarding infringement of intellectual property rights or copyrights or regarding functionality, performance or error has been made.

BST-BMF055-DS000-04 | Revision 0.4 | November 2020

[©] Bosch Sensortec GmbH reserves all rights even in the event of industrial property rights. We reserve all rights of disposal such as copying and passing on to third parties. BOSCH and the symbol are registered trademarks of Robert Bosch GmbH, Germany. Note: Specifications within this document are subject to change without notice.

12. Document history and modifications

Rev. No	Chapter	Description of modification/changes	Date
0.1		Initial version	2015-10-26
0.3		Fixed links datasheets	2020-04-15
0.4	11	Disclaimer update	2020-11-24

Bosch Sensortec GmbH Gerhard-Kindler-Strasse 9 72770 Reutlingen / Germany

contact@bosch-sensortec.com www.bosch-sensortec.com

Modifications reserved | Printed in Germany Specifications subject to change without notice Document number: BST-BMF055-DS000-04 Revision_0.4

BST-BMF055-DS000-04 | Revision 0.4 | November 2020

© Bosch Sensortec GmbH reserves all rights even in the event of industrial property rights. We reserve all rights of disposal such as copying and passing on to third parties. BOSCH and the symbol are registered trademarks of Robert Bosch GmbH, Germany. Note: Specifications within this document are subject to change without notice.