

taoglas SGGP.25A

Datasheet

### Part No: SGGP.25.4.A.02

**Description** GPS/GLONASS/GALILEO SMD Patch Antenna

#### Features:

Dimensions: 25mm\*25mm\*4mm Single Feed SMD Mount GPS/GALILEO: 1575MHz GLONASS: 1602MHz RoHS & REACH Compliant





| 1. | Introduction              | 2  |
|----|---------------------------|----|
| 2. | Specification             | 3  |
| 3. | Antenna Characteristics   | 5  |
| 4. | Radiation Patterns        | 11 |
| 5. | Mechanical Drawing        | 14 |
| 6. | Packaging                 | 15 |
| 7. | Antenna Integration Guide | 17 |
| 8. | Solder Reflow Profile     | 25 |
|    |                           |    |

Changelog

26

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.





# Introduction

1.



The Taoglas SGGP.25 is a ceramic GPS/GLONASS/Galileo passive patch antenna designed for optimal performance on GPS L1/Galileo E1 band (1575.42 MHz) and GLONASS L1 band (1602 MHz). With a low-profile thickness of just 4mm and convenient mounting via standard SMD process, it is ideal for high-volume, low-cost assembly applications.

SGGP.18 is designed for applications in navigation devices, vehicle tracking/fleet management systems, and telematics devices. It is an excellent choice for applications in transportation, defense, marine, agriculture, and navigation industries.


The SGGP.25 is manufactured and tested in an IATF16949 first tier automotive approved facility. For further optimization to customer-specific device environments, custom tuned patch antennas can be supplied, subject to NRE and MOQ.

For further information or support with integrating this antenna into your device, please contact your regional Taoglas customer support team.



# 2. Specification

| GNSS Frequency Bands |                         |                           |                    |                    |                   |
|----------------------|-------------------------|---------------------------|--------------------|--------------------|-------------------|
| GPS                  | L1<br>1575.42 MHz       | L2<br>1227.6 MHz          | L5<br>1176.45 MHz  |                    |                   |
|                      |                         |                           |                    |                    |                   |
| GLONASS              | G1<br>1602 MHz          | G2<br>1248 MHz            | G3<br>1207 MHz     |                    |                   |
|                      |                         |                           |                    |                    |                   |
| Galileo              | E1<br>1575.42 MHz       | E5a<br>1176.45 MHz        | E5b<br>1201.5 MHz  | E6<br>1278.75 MHz  |                   |
|                      | -                       |                           |                    |                    |                   |
| BeiDou               | B1C<br>1575.42 MHz      | B1I<br>1561 MHz           | B2a<br>1176.45 MHz | B2b<br>1207.14 MHz | B3<br>1268.52 MHz |
|                      | -                       | -                         |                    |                    |                   |
| L-Band               | L-Band<br>1542 MHz      |                           |                    |                    |                   |
|                      |                         |                           |                    |                    |                   |
| QZSS (Regional)      | L1<br>1575.42 MHz       | L2C<br>1227.6 MHz         | L5<br>1176.45 MHz  | L6<br>1278.75e6    |                   |
|                      |                         |                           |                    |                    |                   |
| IRNSS (Regional)     | L5<br>1176.45 MHz       |                           |                    |                    |                   |
|                      |                         |                           |                    |                    |                   |
| SBAS                 | L1/E1/B1<br>1575.42 MHz | L5/B2a/E5a<br>1176.45 MHz | G1<br>1602 MHz     | G2<br>1248 MHz     | G3<br>1207 MHz    |
|                      | -                       |                           | -                  |                    |                   |



**GNSS Bands and Constellations** 



| GNSS Electrical                          |       |         |       |
|--|-------|---------|-------|
| Frequency (MHz)                          | 1561  | 1575.42 | 1603  |
| VSWR (max.)                              | 3:1   | 3:1     | 5:1   |
| Passive Antenna Efficiency<br>(%)        | 78.49 | 78.41   | 73.49 |
| Passive Antenna Gain at<br>Zenith (dBic) | 3.66  | 3.66    | 3.04  |
| Polarization                             |       | RHCP    |       |
| Impedance                                |       | 50 Ω    |       |


| Mechanical |           |  |
|------------|-----------|--|
| Dimensions | 25*25*4mm |  |
| Weight     | 7g        |  |
| Material   | Ceramic   |  |


| Environmental                    |                |  |
|----------------------------------|----------------|--|
| Operating Temperature            | -40ºC to +85ºC |  |
| Storage Temperature              | -40ºC to +85ºC |  |
| Moisture Sensitivity Level (MSL) | 3 (168 Hours)  |  |





























































4.









### 4.2 SGGP.25.4.A.02 - Patterns at 1575 MHz









### 4.3 SGGP.25.4.A.02 - Patterns at 1602 MHz












BOTTOM VIEW



# 6. Packaging








350 mm

340mm

1 pc reel in small anti-static bag Dimensions - 340\*350\*70mm Weight – 2.63Kg



4 Layers



# 7. Antenna Integration Guide








### 7.1 Schematic and Symbol Definition

The circuit symbol for the antenna is shown below. The antenna has 9 pins as indicated below.

| Pin | Description |
|-----|-------------|
| 1   | RF Feed     |
| 2-9 | Ground      |






### 7.2 Antenna Integration

The antenna should be placed at the center of the ground plane with a length and width of 50mm. Maintaining a square symmetric ground plane shape and symmetric environment around the antenna is critical to maintaining the excellent axial ratio and phase center performance shown in this datasheet.



#### Top Side W/Solder Mask



#### Top Side W/O Solder Mask




## 7.3 PCB Layout

The clearance on the PCB must comply with the antenna specification. The PCB layout shown in the diagram below demonstrates the antenna clearance.


| · • •     | TAOGLAS<br>ANT1   |       |
|-----------|---|-------|
|           |   |       |
| н н.<br>С |   |       |
|           |   | · · · |
|           |   |       |
| S S       | GGPD.25A Standard Evaluation Board<br>BPS-Glonass Patch Antenna |       |


Top Side



Bottom Side








7.4




## 7.5 Footprint






## 7.6 Copper Keep-Out





## Top Solder Paste


7.7



TOP SOLDER PASTE

8.

The SGGP.25.4.A.02 can be assembled by following the recommended soldering temperatures are as follows:



\*Temperatures listed within a tolerance of +/- 10º C

Smaller components are typically mounted on the first pass, however, we do advise mounting the SGGP.25.4.A.02 when placing larger components on the board during subsequent reflows.

25

TAOGL



Changelog for the datasheet

SPE-13-8-031 – SGGP.25.4.A.02

| Revision: J (Current Version) |                       |  |
|-------------------------------|-----------------------|--|
| Date:                         | 2023-08-16            |  |
| Changes:                      | Full datasheet update |  |
| Changes Made by:              | Gary West             |  |

#### **Previous Revisions**

| Revision: I      |            | Revision: D      | Revision: D        |  |
|------------------|------------|------------------|--------------------|--|
| Date:            | 2021-10-15 | Date:            | 2013-10-23         |  |
| Changes:         |            | Changes:         | Amended dimensions |  |
| Changes Made by: | Unknown    | Changes Made by: | Aine Doyle         |  |

| Revision: H      |                                      |  |
|------------------|--------------------------------------|--|
| Date:            | 2018-06-25                           |  |
| Changes:         | Adding plots and updating footprints |  |
| Changes Made by: | Jack Conroy                          |  |

| Revision: C      |                                   |
|------------------|-----------------------------------|
| Date:            | 2013-05-21                        |
| Changes:         | Removed footprint drawing for now |
| Changes Made by: | Aine Doyle                        |

| Revision: G      |                      |
|------------------|----------------------|
| Date:            | 2014-05-21           |
| Changes:         | Added updated reflow |
| Changes Made by: | Aine Doyle           |

| Revision: B      |                 |  |
|------------------|-----------------|--|
| Date:            | 2013-05-15      |  |
| Changes:         | Amended Drawing |  |
| Changes Made by: | Aine Doyle      |  |

| Revision: F      |                          |
|------------------|--------------------------|
| Date:            | 2014-03-27               |
| Changes:         | Added Footprint from Jon |
| Changes Made by: | Aine Doyle               |

| Revision: E      |                 |
|------------------|-----------------|
| Date:            | 2013-12-03      |
| Changes:         | Amended op temp |
| Changes Made by: | Aine Doyle      |

| Revision: A (Original First Release) |            |  |
|--------------------------------------|------------|--|
| Date:                                | 2013-04-16 |  |
| Notes:                               |            |  |
| Author:                              | SS         |  |





# www.taoglas.com