Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: http://www.renesas.com

April 1st, 2010 Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (http://www.renesas.com)

Send any inquiries to http://www.renesas.com/inquiry.



Notice

- 1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
- Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights
 of third parties by or arising from the use of Renesas Electronics products or technical information described in this document.
 No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights
 of Renesas Electronics or others.
- 3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
- 4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
- 5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
- 6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
- 7. Renesas Electronics products are classified according to the following three quality grades: "Standard", "High Quality", and "Specific". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as "Specific" or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is "Standard" unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - "Specific": Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
- 8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
- 9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
- 10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
- 11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics
- 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.





BIPOLAR ANALOG INTEGRATED CIRCUIT

μ PC2745TB, μ PC2746TB

3 V, SUPER MINIMOLD SILICON MMIC WIDEBAND AMPLIFIER FOR MOBILE COMMUNICATIONS

DESCRIPTION

The μ PC2745TB and μ PC2746TB are silicon monolithic integrated circuits designed as buffer amplifier for mobile communications. These low current amplifiers operate on 3.0 V (1.8 V MIN.).

These ICs are manufactured using our 20 GHz ft NESATIII silicon bipolar process. This process uses silicon nitride passivation film and gold electrodes. These materials can protect chip surface from external pollution and prevent corrosion/migration. Thus, these IC have excellent performance, uniformity and reliability.

FEATURES

Supply voltage : Recommended Vcc = 2.7 to 3.3 V

Circuit operation Vcc = 1.8 to 3.3 V

• Upper limit operating frequency : μ PC2745TB; fu = 2.7 GHz TYP.@3 dB bandwidth

 μ PC2746TB; fu = 1.5 GHz TYP.@3 dB bandwidth

• High isolation : μ PC2745TB; ISL = 38 dB TYP.@f = 500 MHz

 μ PC2746TB; ISL = 45 dB TYP.@f = 500 MHz

Power gain : μ PC2745TB; G_P = 12 dB TYP.@f = 500 MHz

 μ PC2746TB; G_P = 19 dB TYP.@f = 500 MHz

• Saturated output power : μ PC2745TB; Po(sat) = -1 dBm TYP.@f = 500 MHz

 μ PC2746TB; Po(sat) = 0 dBm TYP.@f = 500 MHz

High-density surface mounting : 6-pin super minimold package (2.0 × 1.25 × 0.9 mm)

APPLICATIONS

• 1.5 GHz to 2.5 GHz communication system : μ PC2745TB • 800 MHz to 900 MHz communication system : μ PC2746TB

ORDERING INFORMATION

Part Number	Package	Marking	Supplying Form
μPC2745TB-E3	6-pin super minimold	C1Q	Embossed tape 8 mm wide
μPC2746TB-E3		C1R	1, 2, 3 pins face the perforation side of the tapeQty 3 kpcs/reel

Remark To order evaluation samples, contact your nearby sales office.


Part number for sample order: μ PC2745TB, μ PC2746TB

Caution Observe precautions when handling because these devices are sensitive to electrostatic discharge.

The information in this document is subject to change without notice. Before using this document, please confirm that this is the latest version.

Not all devices/types available in every country. Please check with local NEC Compound Semiconductor Devices representative for availability and additional information.

PIN CONNECTION



Pin No.	Pin Name
1	INPUT
2	GND
3	GND
4	OUTPUT
5	GND
6	Vcc

PRODUCT LINE-UP (TA = +25°C, Vcc = 3.0 V, Zs = ZL = 50 Ω)


Part No.	fu (GHz)	Po(sat) (dBm)	G _P (dB)	NF (dB)	Icc (mA)	Package	Making
μPC2745T	2.7	-1.0	12	6.0	7.5	6-pin minimold	C1Q
μPC2745TB						6-pin super minimold	
μPC2746T	1.5	0	19	4.0	7.5	6-pin minimold	C1R
μPC2746TB						6-pin super minimold	
μPC2747T	1.8	-7.0	12	3.3	5.0	6-pin minimold	C1S
μPC2747TB						6-pin super minimold	
μPC2748T	0.2 to 1.5	-3.5	19	2.8	6.0	6-pin minimold	C1T
μPC2748TB						6-pin super minimold	
μPC2749T	2.9	-6.0	16	4.0	6.0	6-pin minimold	C1U
μPC2749TB						6-pin super minimold	

Remark Typical performance. Please refer to ELECTRICAL CHARACTERISTICS in detail.

Caution The package size distinguish between minimold and super minimold.

SYSTEM APPLICATION EXAMPLE

DIGITAL CELLULAR SYSTEM BLOCK DIAGRAM





PIN EXPLANATION

Pin No.	Pin Name	Applied Voltage (V)	Pin Voltage (V) ^{Note}	Function and Applications	Internal Equivalent Circuit
1	INPUT		0.87 0.82	Signal input pin. A internal matching circuit, configured with resistors, enables $50~\Omega$ connection over a wide band. this pin must be coupled to signal source with capacitor for DC cut.	(6)
2 3 5	GND	0		Ground pin. This pin should be connected to system ground with minimum inductance. Ground pattern on the board should be formed as wide as possible. All the ground pins must be connected together with wide ground pattern to decrease impedance difference.	
4	OUTPUT	_	1.95 2.54	Signal output pin. A internal matching circuit, configured with resistors, enables $50~\Omega$ connection over a wide band. This pin must be coupled to next stage with capacitor for DC cut.	3 2 5
6	Vcc	2.7 to 3.3	_	Power supply pin. This pin should be externally equipped with bypass capacity to minimize ground impedance.	

Note Pin voltage is measured at Vcc = 3.0 V. Above: μ PC2745TB, Below: μ PC2746TB



ABSOLUTE MAXIMUM RATINGS

Parameter	Symbol	Conditions	Ratings	Unit
Supply Voltage	Vcc	T _A = +25°C	4.0	V
Circuit Current	Icc	T _A = +25°C	16	mA
Power Dissipation	Po	T _A = +85°C Note	270	mW
Operating Ambient Temperature	TA		-40 to +85	°C
Storage Temperature	T _{stg}		-55 to +150	°C
Input Power	Pin	T _A = +25°C	0	dBm

Note Mounted on double-sided copper-clad $50 \times 50 \times 1.6$ mm epoxy glass PWB

RECOMMENDED OPERATING RANGE

Parameter	Symbol	MIN.	TYP.	MAX.	Unit
Supply Voltage	Vcc	2.7	3.0	3.3	V

ELECTRICAL CHARACTERISTICS

(TA = +25°C, Vcc = 3.0 V, Zs = ZL = 50 Ω , unless otherwise specified)


Donomoton	Courselle al	Test Conditions	μ	μPC2745TB			μPC2746TB		
Parameter	Symbol		MIN.	TYP.	MAX.	MIN.	TYP.	MAX.	Unit
Circuit Current	Icc	No signal	5.0	7.5	10.0	5.0	7.5	10.0	mA
Power Gain	G₽	f = 500 MHz	9	12	14	16	19	21	dB
Noise Figure	NF	f = 500 MHz	_	6.0	7.5	_	4.0	5.5	dB
Upper Limit Operating Frequency	fu	3 dB down below from gain at f = 0.1 GHz	2.3	2.7	_	1.1	1.5	_	GHz
Isolation	ISL	f = 500 MHz	33	38	_	40	45	_	dB
Input Return Loss	RLin	f = 500 MHz	8	11	_	10	13	_	dB
Output Return Loss	RLout	f = 500 MHz	2.5	5.5	_	5.5	8.5	_	dB
Saturated Output Power	Po(sat)	f = 500 MHz, P _{in} = -6 dBm	-4.0	-1.0	_	-3.0	0		dBm

STANDARD CHARACTERISTICS FOR REFERENCE (TA = +25°C, Vcc = 3.0 V, Zs = ZL = 50 Ω)


Parameter	Symbol	Test Conditions Reference		ce Value	Unit
			μPC2745TB	μPC2746TB	
Circuit Current	Icc	Vcc = 1.8 V, No signal	4.5	4.5	mA
Power Gain	G₽	Vcc = 3.0 V, f = 1.0 GHz Vcc = 3.0 V, f = 2.0 GHz Vcc = 1.8 V, f = 0.5 GHz	12.0 11.0 7.0	18.5 — 14.0	dB
Noise Figure	NF	Vcc = 3.0 V, f = 1.0 GHz Vcc = 3.0 V, f = 2.0 GHz Vcc = 1.8 V, f = 0.5 GHz	5.5 5.7 8.0	4.2 — 5.0	dB
Upper Limit Operating Frequency	fu	Vcc = 1.8 V, 3 dB down below from gain at f = 0.1 GHz	1.8	1.1	GHz
Isolation	ISL	Vcc = 3.0 V, f = 1.0 GHz Vcc = 3.0 V, f = 2.0 GHz Vcc = 1.8 V, f = 0.5 GHz	33 30 35	38 — 37	dB
Input Return Loss	RLin	Vcc = 3.0 V, f = 1.0 GHz Vcc = 3.0 V, f = 2.0 GHz Vcc = 1.8 V, f = 0.5 GHz	13.0 14.0 6.5	10.0 — 10.0	dB
Output Return Loss	RLout	Vcc = 3.0 V, f = 1.0 GHz Vcc = 3.0 V, f = 2.0 GHz Vcc = 1.8 V, f = 0.5 GHz	6.5 8.5 6.0	8.5 — 9.5	dB
Saturated Output Power	Po(sat)	$Vcc = 3.0 \text{ V, } f = 1.0 \text{ GHz, } P_{in} = -6 \text{ dBm}$ $Vcc = 3.0 \text{ V, } f = 2.0 \text{ GHz, } P_{in} = -6 \text{ dBm}$ $Vcc = 1.8 \text{ V, } f = 0.5 \text{ GHz, } P_{in} = -10 \text{ dBm}$	-2.5 -3.5 -11.0	-1.0 -8.0	dBm
3rd Order Intermodulation Distortion	IMз	$\begin{split} &\text{Vcc} = 3.0 \text{ V, } \text{P}_{\text{out}} = -10 \text{ dBm, } \text{f}_1 = 500 \text{ MHz, } \text{f}_2 = 502 \text{ MHz} \\ &\text{Vcc} = 1.8 \text{ V, } \text{P}_{\text{out}} = -20 \text{ dBm, } \text{f}_1 = 500 \text{ MHz, } \text{f}_2 = 502 \text{ MHz} \\ &\text{Vcc} = 3.0 \text{ V, } \text{P}_{\text{out}} = -10 \text{ dBm, } \text{f}_1 = 1000 \text{ MHz, } \text{f}_2 = 1002 \text{ MHz} \end{split}$	-30.0 -31.0 -26.0	-26.0 -37.0 	dBc

*

TEST CIRCUIT



EXAMPLE OF APPLICATION CIRCUIT



The application circuits and their parameters are for references only and are not intended for use in actual design-ins.

CAPACITORS FOR THE Vcc, INPUT, AND OUTPUT PINS


Capacitors of 1 000 pF are recommendable as the bypass capacitor for the Vcc pin and the coupling capacitors for the input and output pins.

The bypass capacitor connected to the Vcc pin is used to minimize ground impedance of Vcc pin. So, stable bias can be supplied against Vcc fluctuation.

The coupling capacitors, connected to the input and output pins, are used to cut the DC and minimize RF serial impedance. Their capacitance are therefore selected as lower impedance against a 50 Ω load. The capacitors thus perform as high pass filters, suppressing low frequencies to DC.

To obtain a flat gain from 100 MHz upwards, 1 000 pF capacitors are used in the test circuit. In the case of under 10 MHz operation, increase the value of coupling capacitor such as 10 000 pF. Because the coupling capacitors are determined by equation, fc = $1/(2\pi RC)$.

ILLUSTRATION OF THE TEST CIRCUIT ASSEMBLED ON EVALUATION BOARD



	Value
С	1 000 pF


Notes


1. $30 \times 30 \times 0.4$ mm double sided copper clad polyimide board.


For more information on the use of this IC, refer to the following application note: **USAGE AND APPLICATIONS OF 6-PIN MINI-MOLD, 6-PIN SUPER MINI-MOLD SILICON HIGH-FREQUENCY WIDEBAND AMPLIFIER MMIC (P11976E).**


TYPICAL CHARACTERISTICS (TA = +25°C, unless otherwise specified)


— μPC2745TB —


















Remark The graphs indicate nominal characteristics.


— μPC2745TB —















Remark The graphs indicate nominal characteristics.


SMITH CHART (TA = +25°C, Vcc = 3.0 V)

— μPC2745TB —

S₁₁-FREQUENCY



S₂₂-FREQUENCY



S-PARAMETERS

S-parameters/Noise parameters are provided on the NEC Compound Semiconductor Devices Web site in a form (S2P) that enables direct import to a microwave circuit simulator without keyboard input.

Click here to download S-parameters.


 $[\mathsf{RF} \ \mathsf{and} \ \mathsf{Microwave}] \to [\mathsf{Device} \ \mathsf{Parameters}]$

URL http://www.ncsd.necel.com/


TYPICAL CHARACTERISTICS (TA = +25°C, unless otherwise specified)

— μPC2746TB —


CIRCUIT CURRENT vs. SUPPLY VOLTAGE




CIRCUIT CURRENT vs. **OPERATING AMBIENT TEMPERATURE**




NOISE FIGURE, POWER GAIN vs. FREQUENCY




POWER GAIN vs. FREQUENCY



ISOLATION vs. FREQUENCY





INPUT RETURN LOSS, OUTPUT RETURN LOSS vs. FREQUENCY




Remark The graphs indicate nominal characteristics.


— μPC2746TB —









OUTPUT POWER vs. INPUT POWER



OUTPUT POWER vs. INPUT POWER



3RD ORDER INTERMODULATION DISTORTION vs. OUTPUT POWER OF EACH TONE




Remark The graphs indicate nominal characteristics.


SMITH CHART (TA = +25°C, Vcc = 3.0 V)

— μPC2746TB —

S₁₁-FREQUENCY



S₂₂-FREQUENCY



S-PARAMETERS

S-parameters/Noise parameters are provided on the NEC Compound Semiconductor Devices Web site in a form (S2P) that enables direct import to a microwave circuit simulator without keyboard input.


Click here to download S-parameters.

 $[\mathsf{RF} \ \mathsf{and} \ \mathsf{Microwave}] \to [\mathsf{Device} \ \mathsf{Parameters}]$

URL http://www.ncsd.necel.com/

PACKAGE DIMENSIONS

6-PIN SUPER MINIMOLD (UNIT: mm)



NOTES ON CORRECT USE

- (1) Observe precautions for handling because of electro-static sensitive devices.
- (2) Form a ground pattern as widely as possible to minimize ground impedance (to prevent undesired oscillation). All the ground pins must be connected together with wide ground pattern to decrease impedance difference.
- (3) The bypass capacitor should be attached to the Vcc pin.
- (4) The DC cut capacitor must be attached to input pin and output pin.

RECOMMENDED SOLDERING CONDITIONS

This product should be soldered and mounted under the following recommended conditions. For soldering methods and conditions other than those recommended below, contact your nearby sales office.

Soldering Method	Soldering Conditions		Condition Symbol
Infrared Reflow	Peak temperature (package surface temperature) Time at peak temperature Time at temperature of 220°C or higher Preheating time at 120 to 180°C Maximum number of reflow processes Maximum chlorine content of rosin flux (% mass)	: 260°C or below : 10 seconds or less : 60 seconds or less : 120±30 seconds : 3 times : 0.2%(Wt.) or below	IR260
VPS	Peak temperature (package surface temperature) Time at temperature of 200°C or higher Preheating time at 120 to 150°C Maximum number of reflow processes Maximum chlorine content of rosin flux (% mass)	: 215°C or below : 25 to 40 seconds : 30 to 60 seconds : 3 times : 0.2%(Wt.) or below	VP215
Wave Soldering	Peak temperature (molten solder temperature) Time at peak temperature Preheating temperature (package surface temperature) Maximum number of flow processes Maximum chlorine content of rosin flux (% mass)	: 260°C or below : 10 seconds or less : 120°C or below : 1 time : 0.2%(Wt.) or below	WS260
Partial Heating	Peak temperature (pin temperature) Soldering time (per side of device) Maximum chlorine content of rosin flux (% mass)	: 350°C or below : 3 seconds or less : 0.2%(Wt.) or below	H\$350

Caution Do not use different soldering methods together (except for partial heating).

- The information in this document is current as of November, 2003. The information is subject to change without notice. For actual design-in, refer to the latest publications of NEC's data sheets or data books, etc., for the most up-to-date specifications of NEC semiconductor products. Not all products and/or types are available in every country. Please check with an NEC sales representative for availability and additional information.
- No part of this document may be copied or reproduced in any form or by any means without prior written consent of NEC. NEC assumes no responsibility for any errors that may appear in this document.
- NEC does not assume any liability for infringement of patents, copyrights or other intellectual property rights of
 third parties by or arising from the use of NEC semiconductor products listed in this document or any other
 liability arising from the use of such products. No license, express, implied or otherwise, is granted under any
 patents, copyrights or other intellectual property rights of NEC or others.
- Descriptions of circuits, software and other related information in this document are provided for illustrative purposes in semiconductor product operation and application examples. The incorporation of these circuits, software and information in the design of customer's equipment shall be done under the full responsibility of customer. NEC assumes no responsibility for any losses incurred by customers or third parties arising from the use of these circuits, software and information.
- While NEC endeavours to enhance the quality, reliability and safety of NEC semiconductor products, customers
 agree and acknowledge that the possibility of defects thereof cannot be eliminated entirely. To minimize
 risks of damage to property or injury (including death) to persons arising from defects in NEC
 semiconductor products, customers must incorporate sufficient safety measures in their design, such as
 redundancy, fire-containment, and anti-failure features.
- NEC semiconductor products are classified into the following three quality grades:
 "Standard", "Special" and "Specific". The "Specific" quality grade applies only to semiconductor products
 developed based on a customer-designated "quality assurance program" for a specific application. The
 recommended applications of a semiconductor product depend on its quality grade, as indicated below.
 Customers must check the quality grade of each semiconductor product before using it in a particular
 - "Standard": Computers, office equipment, communications equipment, test and measurement equipment, audio and visual equipment, home electronic appliances, machine tools, personal electronic equipment and industrial robots
 - "Special": Transportation equipment (automobiles, trains, ships, etc.), traffic control systems, anti-disaster systems, anti-crime systems, safety equipment and medical equipment (not specifically designed for life support)
 - "Specific": Aircraft, aerospace equipment, submersible repeaters, nuclear reactor control systems, life support systems and medical equipment for life support, etc.

The quality grade of NEC semiconductor products is "Standard" unless otherwise expressly specified in NEC's data sheets or data books, etc. If customers wish to use NEC semiconductor products in applications not intended by NEC, they must contact an NEC sales representative in advance to determine NEC's willingness to support a given application.

(Note)

- (1) "NEC" as used in this statement means NEC Corporation, NEC Compound Semiconductor Devices, Ltd. and also includes its majority-owned subsidiaries.
- (2) "NEC semiconductor products" means any semiconductor product developed or manufactured by or for NEC (as defined above).

M8E 00.4-0110

▶For further information, please contact

NEC Compound Semiconductor Devices, Ltd. http://www.ncsd.necel.com/

E-mail: salesinfo@ml.ncsd.necel.com (sales and general)

techinfo@ml.ncsd.necel.com (technical)

5th Sales Group, Sales Division TEL: +81-44-435-1588 FAX: +81-44-435-1579

NEC Compound Semiconductor Devices Hong Kong Limited

E-mail: ncsd-hk@elhk.nec.com.hk (sales, technical and general)

 Hong Kong Head Office
 TEL: +852-3107-7303
 FAX: +852-3107-7309

 Taipei Branch Office
 TEL: +886-2-8712-0478
 FAX: +886-2-2545-3859

 Korea Branch Office
 TEL: +82-2-558-2120
 FAX: +82-2-558-5209

NEC Electronics (Europe) GmbH http://www.ee.nec.de/

TEL: +49-211-6503-01 FAX: +49-211-6503-487

California Eastern Laboratories, Inc. http://www.cel.com/

TEL: +1-408-988-3500 FAX: +1-408-988-0279