

Series: SMD Helical Antenna

TECHNICAL DATA SHEET

Description: 860-930MHz Embedded

Helical Antenna

PART NUMBER: W3139



Features:

- Antenna type: Helix with molded plastic support
- Fully SMD compatible
- Size 14x3mm
- Minimum keep out 4.2mm
- RoHS compliant

Applications:

- ISM 868MHz and 915MHz radio systems
- Sensors
- · Remote controls
- Security
- IoT

All dimensions are in mm / inches

Issue: 1924

In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION

This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other state and federal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden. For more information:



Description: 860-930MHz Embedded

Helical Antenna

PART NUMBER: W3139

Series: SMD Helical Antenna

ELECTRICAL SPECIFICATIONS

Antenna Type Helical

Frequency 860-930MHz

 $\begin{array}{ccc} \text{Nominal Impedance} & & 50 \ \Omega \\ \text{Radiation Pattern} & & \text{Omni} \\ \text{Polarization} & & \text{Linear} \\ \text{Power Withstanding} & & 2W \\ \end{array}$

	Frequency band	Return Loss	Gain	Efficiency
PWB 1 (small clearance, 4.2mm copper free area from the PCB edge)	ISM868±5MHz	<-8dB	-2.5	35%
	ISM915±13MHz	<-8dB	-2.5	30%
PWB 2 (big clearance, 9.5mm copper free area from the PCB edge)	ISM868±5MHz	<-10dB	-0.5	55%
	ISM915±13MHz	<-10dB	-1	45% 2



Description: 860-930MHz Embedded

Helical Antenna

PART NUMBER: W3139

Series: SMD Helical Antenna

MECHANICAL SPECIFICATIONS

Overall Length / Height 14 mm / 3 mm

Weight 0.52 g

Antenna Color / Material White

Fix system SMD+Glue

Recommended Glue Resinlab EP1320LV Black

Solder Paste Thickness Min 0.15mm

ENVIRONMENTAL SPECIFICATIONS

Operating Temperature -40° C~+85 ° C

Storage Temperature -40 ° C ~+85° C

RoHS Compliant Yes

OTHER SPECIFICATIONS





Description: 860-930MHz Embedded


Helical Antenna


PART NUMBER: W3139

Series:

SMD Helical Antenna

MECHANICAL DRAWING





Suction Pick Area



Description: 860-930MHz Embedded

Helical Antenna


PART NUMBER: W3139

Series: SMD Helical Antenna

FIX SYSTEM RECOMMENDATION

Fix system

- 1. SMD process
- 2. Solder paste thickness: minimum 0.15mm
- 3. Glue is required, Recommended Glue: Resinlab EP1320LV Black, usage and position see below recommended area.



Recommended Glue Type





Description: 860-930MHz Embedded

Helical Antenna

PART NUMBER: W3139

Series:


SMD Helical Antenna

FIX SYSTEM RECOMMENDATION

Fix system

1. Glue position on PCB for recommendation

Glue position on PCB for recommendation








Description: 860-930MHz Embedded

Helical Antenna

PART NUMBER: W3139

Series: SMD Helical Antenna

FIX SYSTEM RECOMMENDATION



Solder effect



Description: 860-930MHz Embedded

Helical Antenna


PART NUMBER: W3139


Series:

SMD Helical Antenna

TEST SETUP

PWB 1 Layout for W3139 SMD Helical Antenna





Issue: 1924



Description: 860-930MHz Embedded

Helical Antenna

PART NUMBER: W3139


Series:

SMD Helical Antenna

TEST SETUP

PWB 1 ground clearance area (Top):40x4.2mm

PWB 1 ground clearance area (Bottom):40x4.2mm



Issue: 1924





Description: 860-930MHz Embedded

Helical Antenna


PART NUMBER: W3139

Series:

SMD Helical Antenna

TEST SETUP

PWB 1 Pad dimension in top copper









Description: 860-930MHz Embedded

Helical Antenna


PART NUMBER: W3139


Series:

SMD Helical Antenna

TEST SETUP

PWB 1 Pad dimension in top copper







Description: 860-930MHz Embedded

Helical Antenna


PART NUMBER: W3139


Series:

SMD Helical Antenna

TEST SETUP

PWB 2 Layout for W3139 SMD Helical Antenna





Issue: 1924





Description: 860-930MHz Embedded

Helical Antenna

PART NUMBER: W3139


Series:

SMD Helical Antenna

TEST SETUP

PWB 2 ground clearance area (Top):40x9.5mm

PWB 2 ground clearance area (Bottom):40x9.5mm



Issue: 1924





Description: 860-930MHz Embedded

Helical Antenna


PART NUMBER: W3139

Series:

SMD Helical Antenna

TEST SETUP

PWB 2 Pad dimension in top copper







Description: 860-930MHz Embedded

Helical Antenna


PART NUMBER: W3139


Series:

SMD Helical Antenna

TEST SETUP

PWB 2 Pad dimension in top copper









Description: 860-930MHz Embedded

Helical Antenna

PART NUMBER: W3139

Series:


SMD Helical Antenna

TEST SETUP

ISM 868MHz matching circuit.

(PWB 2 big clearance)


Antenna feed point



Capacitance for S11 matching, 6.8pF, shunt

(PWB 1 small clearance)

Antenna feed point



Capacitance for S11 matching, 9.1pF, shunt

Note: Exact matching and tuning components value depend on application, board size, cover etc.



Description: 860-930MHz Embedded

Helical Antenna


PART NUMBER: W3139


Series:

SMD Helical Antenna

CHARTS

ISM 868MHz two version performance, test in free space.







Description: 860-930MHz Embedded

Helical Antenna


PART NUMBER: W3139

Series:

SMD Helical Antenna

CHARTS

ISM 868MHz two version performance ,test in free space.







Description: 860-930MHz Embedded

Helical Antenna


PART NUMBER: W3139

Series:

SMD Helical Antenna

CHARTS

ISM 868MHz two version performance, test in free space.





Description: 860-930MHz Embedded

Helical Antenna


PART NUMBER: W3139


Series: SMD Helical Antenna


CHARTS

ISM 868MHz two version performance, test in free space.

Typical radiation pattern in free space







Issue: 1924



Description: 860-930MHz Embedded

Helical Antenna

PART NUMBER: W3139

Series:


SMD Helical Antenna

TEST SETUP

ISM 915MHz matching circuit.

(PWB 2 big clearance)


Antenna feed point



Capacitance for S11 matching, 5.1pF, shunt

(PWB 1 small clearance)

Antenna feed point



Capacitance for S11 matching, 9.1pF, shunt

Note: Exact matching and tuning components value depend on application, board size, cover etc.



Description: 860-930MHz Embedded

Helical Antenna

PART NUMBER: W3139

Series:

SMD Helical Antenna

CHARTS

ISM 915MHz two version performance, test in free space.







Description: 860-930MHz Embedded

Helical Antenna


PART NUMBER: W3139

Series:

SMD Helical Antenna

CHARTS

ISM 915MHz two version performance, test in free space.







Description: 860-930MHz Embedded

Helical Antenna


PART NUMBER: W3139

Series:

SMD Helical Antenna

CHARTS

ISM 915MHz two version performance, test in free space.







Description: 860-930MHz Embedded

Helical Antenna


PART NUMBER: W3139


Series:


SMD Helical Antenna

CHARTS

ISM 915MHz two version performance. Typical radiation pattern in free space









Description: 860-930MHz Embedded

Helical Antenna


PART NUMBER: W3139

Series: SMD Helical Antenna

Recommendation for reflow soldering process

Printing stencil thickness 0,15 - 0,25 mm is recommended for the solder paste. The maximum soldering temperature should not exceed 260°C. The temperature profile recommendations for reflow soldering process is presented in the Figures 1 and 2. The reflow profile presented in figure 1 describes minimum reflow temperatures. The reflow profile presented in figure 2 describes maximum reflow temperatures. located at the center of the coverage area.

	Method of heat transfer	Controlled hot air convection
1	Average temperature gradient in preheating	2.5 °C/s
2	Soak time	2-3 minutes
3	Max temperature gradient in reflow	3 °C/s
4	Time above 217 °C	Max 30 sec
5	Peak temperature in reflow	230 ℃ for 10 seconds
6	Temperature gradient in cooling	Max -5 °C/s







Description: 860-930MHz Embedded


Helical Antenna

PART NUMBER: W3139

Series: SMD Helical Antenna

Recommendation for reflow soldering process

	Method of heat transfer	Controlled hot air convection
1	Average temperature gradient in preheating	2.5 °C/s
2	Soak time	2-3 minutes
3	Max temperature gradient in reflow	3 °C/s
4	Time above 217 °C	Max 60 sec
5	Time above 230 °C	Max 50 sec
6	Time above 250 °C	Max 10 sec
7	Peak temperature in reflow	260 °C for 5 seconds
8	Temperature gradient in cooling	Max -5 °C/s





Description: 860-930MHz Embedded


Helical Antenna


PART NUMBER: W3139


Series:

SMD Helical Antenna

PACKAGING








5. All the size design with reference to the EIA - 481 - C - 2003.

6. Loading within 250 mm length maximum curvature is less than



Notes:


1. 10 side hole of the cumulative tolerance cannot be more than $+\ /\ -$ 0.2 mm.

+ / - 0. 2 mm.

2. Material specifications: PS black antistatic, thickness of

3.13 inches (100) axis reel package length: 4.6 m. (the front air bag length: 0.33 m, parts packing length: 4 m, after a period of empty packet length: 0.33 meters).

4.13 inches (100) axis reel packaging components to the total number of stars: 1056. (the front air bag star count: 28, actual packing parts the number: 1000, after a period of empty bag star count: 28).



Total 1000 PCS In Reel

Reel Size: 330MM[13INCH]

Total 2 PCS Reel In Package Box

Package Box Size:350x350x120mm