

# **MIC833**

## **Comparator and Reference with Adjustable Hysteresis**

#### Features

- Optimized for Handheld Electronics, Cellular Telephones, and Other Battery-Powered Devices
- Inputs and Output Can Pull-Up to 6V Regardless of Supply Voltage
- Independently Adjustable High- and Low-Voltage Thresholds
- High ±1.5% Voltage Threshold Accuracy
- Extremely Low 1 µA Typical Supply Current
- Immune to Brief Input Transients
- 5-Lead SOT-23 Package

#### Applications


- Handheld Electronics
- Mobile Phones
- Consumer Electronics
- Embedded Controllers
- Personal Electronics

## **General Description**


The MIC833 is a micropower precision dual-voltage comparator with an on-chip reference and latch. High-voltage and low-voltage thresholds are adjusted independently, allowing for wide hysteresis. Three external resistors determine the threshold voltages. Voltage detection thresholds are accurate to 1.5%. Supply current is extremely low (1 µA, typical), making it ideal for portable applications.

The MIC833 is supplied in a 5-lead SOT-23 package. See the MIC2778 for applications that require an output delay.


#### Package Type




## **Typical Application Circuit**



## **Functional Diagram**



#### **Timing Diagram**



## 1.0 ELECTRICAL CHARACTERISTICS

#### Absolute Maximum Ratings †

Supply Voltage (V <sub>DD</sub> )	–0.3V to +7V
Input Voltages (V <sub>I TH</sub> , V <sub>HTH</sub> ).	
Output Current (I <sub>OUT</sub> )	
Output Voltage (V <sub>OUT</sub> )	
ESD Rating (Note 1)	

## **Operating Ratings ††**

Supply Voltage (V <sub>DD</sub> )	+1.5V to +5.5V
Input Voltage (V <sub>I TH</sub> , V <sub>HTH</sub> )	
Output Voltage (V <sub>OUT</sub> )	
<b>† Notice:</b> Exceeding the absolute maximum rating may damage the device.	
the Martines. The electric is used as constant of the function statistic its an exciting writing	

**†† Notice:** The device is not guaranteed to function outside its operating rating.

Note 1: Devices are ESD sensitive. Handling precautions recommended. Human body model, 1.5 k $\Omega$  in series with 100 pF.

## **ELECTRICAL CHARACTERISTICS**

<b>Electrical Characteristics:</b> $1.5V \le V_{DD} \le 5.5V$ ; $T_A = +25^{\circ}C$ , unless noted.							
Parameters	Sym.	Min.	Тур.	Max.	Units	Conditions	
Supply Current	I <sub>DD</sub>		1	2	μA	Outputs not asserted, –40°C ≤ T <sub>A</sub> ≤ +85°C	
Input Leakage Current	I <sub>LTH</sub> , I <sub>HTH</sub>		0.005	10	nA	$-40^{\circ}C \le T_A \le +85^{\circ}C$	
Reference Voltage	V <sub>REF</sub>	1.221	1.240	1.259	V	$-40^{\circ}C \le T_A \le +85^{\circ}C$	
Dranagation Dalay	t <sub>D</sub>		5		μs	V <sub>LTH</sub> = 1.352V to 1.128V	
Propagation Delay			5			V <sub>HTH</sub> = 1.128V to 1.352V	
Output Voltage-Low	V <sub>OUT</sub>	_		0.3	V	OUT de-asserted, $I_{SINK}$ = 1.6 mA, $V_{DD} \ge 1.6V$ , $-40^{\circ}C \le T_A \le +85^{\circ}C$	
(Note 1)			_	0.4		OUT de-asserted, $I_{SINK}$ = 100 $\mu A,$ $V_{DD} \ge$ 1.2V, $-40^{\circ}C$ $\le$ $T_A$ $\le$ +85 $^{\circ}C$	

Note 1:  $V_{DD}$  operating range is 1.5V to 5.5V. Output is guaranteed to be held low down to  $V_{DD}$  = 1.2V.

## **TEMPERATURE SPECIFICATIONS**

Parameters	Sym.	Min.	Тур.	Max.	Units	Conditions	
Temperature Ranges							
Lead Temperature			_	+260	°C	Soldering, 10s	
Storage Temperature Range	Τ <sub>S</sub>	-65	—	+150	°C	—	
Ambient Temperature	T <sub>A</sub>	-40	—	+85	°C	—	
Package Thermal Resistances							
Thermal Resistance, SOT-23-5Ld	θ <sub>JA</sub>	—	260	—	°C/W	—	

## 2.0 PIN DESCRIPTIONS

The descriptions of the pins are listed in Table 2-1.

Pin Number	Symbol	Description			
1	НТН	High-Voltage Threshold (Input): Analog input to a comparator. This is the voltage input assigned to detect a high-voltage condition when the level on this pin exceeds $V_{REF}$ , OUT is asserted and the condition is latched until $V_{LTH} < V_{REF}$ .			
2	GND	Ground			
3	LTH	Low-Voltage Threshold (Input): Analog input to a comparator. This is the voltage input assigned to detect a low voltage condition. When the level on this pin falls below $V_{REF}$ , OUT is de-asserted and the condition is latched until $V_{HTH} > V_{REF}$ .			
4	OUT	Output: Active-high, open-drain output. This output is de-asserted and latched when $V_{LTH} < V_{REF}$ , indicating a low voltage condition. This state remains latched until $V_{HTH} > V_{REF}$ .			
5	VDD	Power Supply (Input): Independent supply input for internal circuitry.			

## 3.0 FUNCTIONAL DESCRIPTION

The MIC833 monitors a voltage and detects when it is below or above two independently programmed levels.




FIGURE 3-1: MIC833 Block Diagram.

#### 3.1 Voltage Low Output

The output (OUT) is an active-high, open-drain output that sinks current when the MIC833 detects a low input voltage at its LTH input. This condition is latched until the HTH input is presented with a voltage higher than the internal  $V_{\text{REF}}$  (+1.24V).

#### 3.2 Trip Points

Input voltage is monitored by the comparators via a voltage divider network. The divided voltage is compared to an internal reference voltage. When the voltage at the LTH input pin drops below the internal reference voltage, the output pulls low. Because of the voltage divider, the voltage at HTH is assured to be below the reference voltage.

## 4.0 APPLICATION INFORMATION


#### 4.1 Output

Because the MIC833 output is an open-drain MOSFET, most applications will require a pull-up resistor. The value of the resistor should not be too large or leakage effects may dominate. 470 k $\Omega$  is the maximum recommended value. Note that the output may be pulled up as high as 6V regardless of IC supply voltage. See the Electrical Characteristics section for details.

#### 4.2 **Programming the Thresholds**

The low-voltage threshold is calculated by Equation 4-1.

#### **EQUATION 4-1:**



The high-voltage threshold is calculated by Equation 4-2.

#### **EQUATION 4-2:**

$$V_{IN(HI)} = V_{REF} \left[ \frac{R1 + R2 + R3}{R3} \right]$$
  
Where:  
$$V_{REF} = 1.240V$$

In order to provide the additional criteria needed to solve for the resistor values, the resistors can be selected such that they have a given total value of

R1 + R2 + R3 = R<sub>TOTAL</sub>. A value such as 1 M $\Omega$  for R<sub>TOTAL</sub> is a reasonable value because it draws minimum current but has no significant effect on accuracy.

When working with large resistors, a small amount of leakage current can cause voltage offsets that degrade system accuracy. The maximum recommended total resistance from  $V_{\text{IN}}$  to ground is 3 M $\Omega$ .




FIGURE 4-1: Example Circuit.

Once the desired trip points are determined, set the  $V_{\text{IN(HI)}}$  threshold first.

For example, use a total of  $1 \text{ M}\Omega = \text{R1} + \text{R2} + \text{R3}$ . For a typical single-cell lithium ion battery, 3.6V is a good high threshold because at 3.6V the battery is moderately charged. Solving for R3:

#### **EQUATION 4-3:**

$$V_{IN(HI)} = 3.6V = 1.24V \left(\frac{1M\Omega}{R3}\right)$$
  
Where:  
R3 = 344 kΩ

Once R3 is determined, the equation for  $V_{IN(LO)}$  can be used to determine R2. A single lithium-ion cell, for example, should not be discharged below 2.5V. Many applications limit the drain to 3.1V. Using 3.1V for the  $V_{IN(LO)}$  threshold allows calculation of the two remaining resistor values.

#### **EQUATION 4-4:**

$V_{IN(LO)} = 3.1V = 1.2$	$4V\left(\frac{1M\Omega}{R2+344k\Omega}\right)$
Where:	
R2	= 56 kΩ
1 MΩ–(R2–R3)	= R1
R1	= 600 kΩ


The accuracy of the resistors can be chosen based upon the accuracy required by the system.

The inputs may be subjected to voltages as high as 6V steady state without adverse effects of any kind, regardless of the IC supply voltage. This applies even if the supply voltage is zero. This permits the situation in which the IC supply is turned off, but voltage is still present on the inputs. See Electrical Characteristics.

#### 4.3 Input Transients

The MIC833 is inherently immune to very short negative going glitches. Very brief transients may exceed the  $V_{\rm IN(LO)}$  threshold without tripping the output.

As shown in Figure 4-2, the narrower the transient, the deeper the threshold overdrive that will be ignored by the MIC833. The graph represents the typical allowable transient duration for a given amount of threshold overdrive that will not toggle the output.



#### 4.4 Initialization Behavior

When the MIC833 is powered up, the comparators and latch become active before the reference voltage reaches its final value. In most applications, this presents no problems. However, the user should be aware of applying power to the part; if the input voltage is between the two thresholds, the output of the part will be high because input HTH will have been higher than the 1.24V reference during initialization.

It is not very likely the part would be powered up in this state. It is more likely the same power supply will power the part and develop its inputs. However, if the above-described condition should occur, the next HTH threshold crossing would not be processed because the latch would have been already set. The next valid input condition would have to be a crossing of the LTH threshold, which resets the latch, after which "normal" operation is restored.

#### 4.5 Example Application

The battery charger of Figure 4-3 uses the MIC833 to detect a low-battery voltage condition (V<sub>DIS</sub>) and enables a constant-current source (I<sub>CHG</sub>). Charging current is enabled until a charged-battery voltage condition (V<sub>CHG</sub>) is detected; at which time the charging-current source is disabled.

Diode D1 was added to Figure 4-3 to ensure the disabled current source does not draw battery current. Whether or not D1 is required is a function of the output stage of the current source and how it is disabled.

The circuitry of Figure 4-3 is deliberately generalized to imply flexibility of application. Depending on the application, it may not be possibly to power the MIC833 from the charger supply voltage, see Note 2 in Figure 4-3. It may be necessary to provide a separate voltage regulator, or a resistive voltage divider to reduce the V<sub>DD</sub> applied to the MIC833. The part can be supplied by the battery voltage (V<sub>BAT</sub>) if this voltage is never lower than 1.5V, the minimum operating V<sub>DD</sub> of the part.

Voltage thresholds,  $V_{DIS}$  and  $V_{CHG}$ , are programmed as described in the appropriate above paragraph.






FIGURE 4-3: Battery Charger.

## 5.0 PACKAGING INFORMATION

#### 5.1 Package Marking Information



Legend:	Y YY WW NNN @3 *	Product code or customer-specific information Year code (last digit of calendar year) Year code (last 2 digits of calendar year) Week code (week of January 1 is week '01') Alphanumeric traceability code Pb-free JEDEC <sup>®</sup> designator for Matte Tin (Sn) This package is Pb-free. The Pb-free JEDEC designator (e3) can be found on the outer packaging for this package. ' Pin one index is identified by a dot, delta up, or delta down (triangle
	be carried characters the corpor	5
	Underbar	(_) and/or Overbar (⁻) symbol may not be to scale.



#### 5-Lead SOT-23 Package Outline & Recommended Land Pattern

NOTES:

## APPENDIX A: REVISION HISTORY

### Revision A (April 2020)

- Converted Micrel document MIC833 to Microchip data sheet template DS20006336A.
- Minor grammatical text changes throughout.

NOTES:

## **PRODUCT IDENTIFICATION SYSTEM**

To order or obtain information, e.g., on pricing or delivery, contact your local Microchip representative or sales office.

PART NO	. x	XX	- <u>XX</u>	Ex	ample	es:	
Device	Temper Ranç	rature Package	Media Type	a)	MIC	:833YM5-TR:	Comparator and Refer- ence with Adjustable Hysteresis, -40°C to +85°C (ROHS Compliant),
Device:	MIC833:	Comparator and Re Hysteresis	ference with Adjustable	No	te 1:		5LD SOT-23, 3,000/Reel. dentifier only appears in the nber description. This identifier is
Temperature Range:	Y =	–40°C to +85°C (Ro⊦	IS Compliant)			used for orderin the device pack	g purposes and is not printed on age. Check with your Microchip package availability with the
Packages:	M5 =	5-Lead SOT-23				·	
Media Type:	TR =	3,000/Reel					

NOTES:

#### Note the following details of the code protection feature on Microchip devices:

- · Microchip products meet the specification contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is one of the most secure families of its kind on the market today, when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods used to breach the code protection feature. All of these methods, to our knowledge, require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Most likely, the person doing so is engaged in theft of intellectual property.
- Microchip is willing to work with the customer who is concerned about the integrity of their code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of their code. Code protection does not mean that we are guaranteeing the product as "unbreakable."

Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION, INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

#### Trademarks

The Microchip name and logo, the Microchip logo, Adaptec, AnyRate, AVR, AVR logo, AVR Freaks, BesTime, BitCloud, chipKIT, chipKIT logo, CryptoMemory, CryptoRF, dsPIC, FlashFlex, flexPWR, HELDO, IGLOO, JukeBlox, KeeLoq, Kleer, LANCheck, LinkMD, maXStylus, maXTouch, MediaLB, megaAVR, Microsemi, Microsemi logo, MOST, MOST logo, MPLAB, OptoLyzer, PackeTime, PIC, picoPower, PICSTART, PIC32 logo, PolarFire, Prochip Designer, QTouch, SAM-BA, SenGenuity, SpyNIC, SST, SST Logo, SuperFlash, Symmetricom, SyncServer, Tachyon, TempTrackr, TimeSource, tinyAVR, UNI/O, Vectron, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

APT, ClockWorks, The Embedded Control Solutions Company, EtherSynch, FlashTec, Hyper Speed Control, HyperLight Load, IntelliMOS, Libero, motorBench, mTouch, Powermite 3, Precision Edge, ProASIC, ProASIC Plus, ProASIC Plus logo, Quiet-Wire, SmartFusion, SyncWorld, Temux, TimeCesium, TimeHub, TimePictra, TimeProvider, Vite, WinPath, and ZL are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, BlueSky, BodyCom, CodeGuard, CryptoAuthentication, CryptoAutomotive, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, EtherGREEN, In-Circuit Serial Programming, ICSP, INICnet, Inter-Chip Connectivity, JitterBlocker, KleerNet, KleerNet Iogo, memBrain, Mindi, MiWi, MPASM, MPF, MPLAB Certified Iogo, MPLIB, MPLINK, MultiTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, PowerSmart, PureSilicon, QMatrix, REAL ICE, Ripple Blocker, SAM-ICE, Serial Quad I/O, SMART-I.S., SQI, SuperSwitcher, SuperSwitcher II, Total Endurance, TSHARC, USBCheck, VariSense, ViewSpan, WiperLock, Wireless DNA, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

The Adaptec logo, Frequency on Demand, Silicon Storage Technology, and Symmcom are registered trademarks of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2020, Microchip Technology Incorporated, All Rights Reserved.

ISBN: 978-1-5224-5916-3

For information regarding Microchip's Quality Management Systems, please visit www.microchip.com/quality.



# Worldwide Sales and Service

#### AMERICAS

**Corporate Office** 2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200 Fax: 480-792-7277 Technical Support: http://www.microchip.com/ support

Web Address: www.microchip.com

Atlanta Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455

Austin, TX Tel: 512-257-3370

**Boston** Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL Tel: 630-285-0071 Fax: 630-285-0075

Dallas Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

Detroit Novi, MI Tel: 248-848-4000

Houston, TX Tel: 281-894-5983

Indianapolis Noblesville, IN Tel: 317-773-8323 Fax: 317-773-5453 Tel: 317-536-2380

Los Angeles Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608 Tel: 951-273-7800

Raleigh, NC Tel: 919-844-7510

New York, NY Tel: 631-435-6000

San Jose, CA Tel: 408-735-9110 Tel: 408-436-4270

Canada - Toronto Tel: 905-695-1980 Fax: 905-695-2078

#### ASIA/PACIFIC

Australia - Sydney Tel: 61-2-9868-6733

China - Beijing Tel: 86-10-8569-7000 China - Chengdu

Tel: 86-28-8665-5511 China - Chongqing Tel: 86-23-8980-9588

China - Dongguan Tel: 86-769-8702-9880

China - Guangzhou Tel: 86-20-8755-8029

China - Hangzhou Tel: 86-571-8792-8115

China - Hong Kong SAR Tel: 852-2943-5100

China - Nanjing Tel: 86-25-8473-2460

China - Qingdao Tel: 86-532-8502-7355

China - Shanghai Tel: 86-21-3326-8000

China - Shenyang Tel: 86-24-2334-2829

China - Shenzhen Tel: 86-755-8864-2200

China - Suzhou Tel: 86-186-6233-1526

China - Wuhan Tel: 86-27-5980-5300

China - Xian Tel: 86-29-8833-7252

China - Xiamen Tel: 86-592-2388138 China - Zhuhai

Tel: 86-756-3210040

#### ASIA/PACIFIC

India - Bangalore Tel: 91-80-3090-4444

India - New Delhi Tel: 91-11-4160-8631 India - Pune

Tel: 91-20-4121-0141 Japan - Osaka

Tel: 81-6-6152-7160 Japan - Tokyo

Tel: 81-3-6880- 3770 Korea - Daegu

Tel: 82-53-744-4301 Korea - Seoul

Tel: 82-2-554-7200

Malaysia - Kuala Lumpur Tel: 60-3-7651-7906

Malaysia - Penang Tel: 60-4-227-8870

Tel: 63-2-634-9065

Singapore Tel: 65-6334-8870

Taiwan - Hsin Chu Tel: 886-3-577-8366

Taiwan - Kaohsiung

Taiwan - Taipei

Thailand - Bangkok

Vietnam - Ho Chi Minh Tel: 84-28-5448-2100

Tel: 31-416-690399 Fax: 31-416-690340

Italy - Padova

**EUROPE** 

Austria - Wels

Tel: 43-7242-2244-39

Tel: 45-4485-5910

Fax: 45-4485-2829

Tel: 358-9-4520-820

Tel: 33-1-69-53-63-20

Fax: 33-1-69-30-90-79

Germany - Garching

Tel: 49-2129-3766400

Germany - Heilbronn

Germany - Karlsruhe

Tel: 49-7131-72400

Tel: 49-721-625370

Germany - Munich

Tel: 49-89-627-144-0

Fax: 49-89-627-144-44

Germany - Rosenheim

Tel: 49-8031-354-560

Israel - Ra'anana

Italy - Milan

Tel: 972-9-744-7705

Tel: 39-0331-742611

Fax: 39-0331-466781

Tel: 39-049-7625286

**Netherlands - Drunen** 

Tel: 49-8931-9700

Germany - Haan

Finland - Espoo

France - Paris

Fax: 43-7242-2244-393

Denmark - Copenhagen

Norway - Trondheim Tel: 47-7288-4388

Poland - Warsaw Tel: 48-22-3325737

Romania - Bucharest Tel: 40-21-407-87-50

Spain - Madrid Tel: 34-91-708-08-90 Fax: 34-91-708-08-91

Sweden - Gothenberg Tel: 46-31-704-60-40

Sweden - Stockholm Tel: 46-8-5090-4654

**UK - Wokingham** Tel: 44-118-921-5800 Fax: 44-118-921-5820

Philippines - Manila

Tel: 886-7-213-7830

Tel: 886-2-2508-8600

Tel: 66-2-694-1351