

Apex Right Angle TG.30 Part No:

TG.30.8112

Features:

600-6000MHz Covers 5G/4G Bands Typical 50%+ Efficiency and 3dBi+ Peak Gain Dipole Terminal Antenna 90° termination with SMA(M) Connector RoHS and REACH Compliant

www.taoglas.com



1.	Introduction	2
2.	Specification	3
3.	Antenna Characteristics	6
4.	Radiation Patterns	9
5.	Mechanical Drawing	43
6.	Packaging	44
	Changelog	45

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.





Introduction

1.



The Apex TG.30 is a Wideband Dipole 5G/4G Antenna – is primarily designed for use with 5G/4G modules, routers and devices that require the highest possible efficiency and peak gain to deliver best in class throughput on all major cellular bands worldwide between 600MHz and 6GHz.

This fixed 90 degree, connector mount, dipole antenna is primarily designed for use with 5G/4G modules and devices that require the highest possible efficiency and peak gain in order to deliver best-in-class throughput.

Typical Applications include:

- Routers and Gateways
- Access Points
- Remote Monitoring

With very high efficiency on every cellular band globally it is an ideal solution for any device requiring high, reliable performance. It is also guaranteed to meet any type approval or carrier certification requirements from a RF standpoint.

This patented antenna is available in White and Black versions. It is also available with swivel 90 degrees and straight connectors.

For further information please contact your regional Taoglas customer support team.



Specification

2.

				Electric	al				
Band	Frequency (MHz)	Measurement	Efficiency (%)	Average Gain (dB)	Peak Gain (dBi)	Impedance	Polarization	Radiation Pattern	Max. input power
5GNR/4G Band		30X30cm Ground plane (Centre)	18.8	-7.26	1.40		Linear	Omni	2W
5,8,12,13,14,17,		In Free Space	58.5	-2.33	2.58				
18,20,26,27,28, 29,71		30X30cm Ground plane (Edge)	54.5	-2.64	2.77				
5GNR/4G		30X30cm Ground plane (Centre)	66.3	-1.79	7.25				
Band	1427-1518	In Free Space	50.4	-2.98	5.64				
21,32,74,75,76		30X30cm Ground plane (Edge)	67.0	-1.74	2.49				
4G/3G		30X30cm Ground plane (Centre)	62.8	-2.02	7.79				
Band 1,2,3,4,9,23,25,	1710-2200	In Free Space	82.7	-0.82	4.29				
35,39,66	,	30X30cm Ground plane (Edge)	68.7	-1.63	2.99	50 Ω ι			
	2300-2400	30X30cm Ground plane (Centre)	42.3	-3.73	4.59				
4G/3G Band 40		In Free Space	81.7	-0.88	4.41				
		30X30cm Ground plane (Edge)	68.1	-1.67	3.50				
	2400-2500	30X30cm Ground plane (Centre)	30.9	-5.10	3.10				
Wi-Fi 2400		In Free Space	70.9	-1.49	4.18				
		30X30cm Ground plane (Edge)	64.0	-1.94	3.94				
		30X30cm Ground plane (Centre)	55.4	-2.56	7.06				
4G/3G Band 7,38,41		In Free Space	68.1	-1.67	4.41				
bana 7,30,41		30X30cm Ground plane (Edge)	49.8	-3.03	4.55				
5GNR/4G	3300-3800	30X30cm Ground plane (Centre)	42.1	-3.76	6.60				
Band 22,42,43,48,77		In Free Space	42.1	-3.76	3.94				
78		30X30cm Ground plane (Edge)	33.7	-4.72	4.06				
	5150-5925	30X30cm Ground plane (Centre)	34.5	-4.62	7.09				
LTE5200/ Wi-Fi 5800		In Free Space	67.1	-1.73	5.69				
5000		30X30cm Ground plane (Edge)	43.2	-3.65	4.69				



		5G/4G	Bands			
Band Number			Advanced / WCDMA / HSPA / HSPA+ / TD-SCDMA			
	Uplink	Downlink	30X30cm Ground plane (Centre)	In Free space	30X30cm Ground plane (Edge)	
B1	B1 1920 to 1980		✓	✓	✓	
B2	B2 1850 to 1910		4	√	√	
B3	B3 1710 to 1785		4	√	√	
B4	1710 to 1755	2110 to 2155	1	√	√	
B5			1	4	1	
	B7 2500 to 2570		4	4	1	
B8	880 to 915	925 to 960	1	1	1	
B9*	1749.9 to 1784.9	1844.9 to 1879.9	1	4	1	
B11	1427.9 to 1447.9	1475.9 to 1495.9	4	4	1	
B12	699 to 716	729 to 746	*	4	4	
B13	777 to 787	746 to 756	4	1	1	
B14	788 to 798	758 to 768	✓ ×	√ √	4	
B17 B18	704 to 716	734 to 746	↓	↓	↓	
B18 B19	815 to 830 830 to 845	860 to 875	1	↓	↓	
B19 B20	830 to 845 832 to 862	875 to 890 791 to 821	↓	↓	↓	
			1	↓ ↓	1	
B21 B22*	1447.9 to 1462.9 3410 to 3490	1495.9 to 1510.9	4	↓ ↓	*	
B22* B23*	2000 to 2020	3510 to 3590 2180 to 2200	4	↓	▲	
B23*	1626.5 to 1660.5	1525 to 1559	1	↓	↓	
B24 B25	1850 to 1915	1930 to 1995	1	1	1	
B26	814 to 849	859 to 894	1	√	√	
B27*	807 to 824	852 to 869	√	√	√	
B28	703 to 748	758 to 803	*	√	√	
B29		0 728	*	1	√	
B30	2305 to 2315	2350 to 2360	1	1	1	
B31	452.5 to 457.5	462.5 to 467.5	*	×	×	
B32		o 1496	1	1	1	
B34		o 2025	1	1	1	
B35		o 1910	1	1	✓	
B36		o 1990	1	1	1	
B37	1910 to 1930		1	1	1	
B38	2570 t	o 2620	1	✓	✓	
B39	1880 to 1920		✓	✓	✓	
B40	2300 t	o 2400	1	✓	✓	
B41	2496 t	o 2690	1	✓	✓	
B42	3400 t	o 3600	1	√	√	
B43	3600 t	o 3800	✓	✓	✓	
B45	1447 t	o 1467	✓	✓	✓	
B46	5150 t	o 5925	1	1	√	
B47	5855 t	o 5925	1	√	1	
B48	3550 t	o 3700	1	√	√	
B49	3550 t	o 3700	√	✓	√	
B50		o 1517	1	4	1	
B51		0 1432	4	4	4	
B52		0 3400	*	1	*	
B53		2110 to 2295	4	4	1	
B65	1920 to 2010	2110 to 2200	4	1	4	
B66	1710 to 1780	2110 to 2200	√ ×	✓ ✓	4	
B68	698 to 728	753 to 783 to 2620	*	↓	4	
B69 B70	1695 to 1710	1995 to 2020	↓ ↓	↓ ↓	↓	
B70 B71	663 to 698	617 to 652	1	1	↓	
B71 B72	451 to 456	461 to 466	*	*	×	
B72 B73	450 to 455	460 to 465	*	*	*	
B73	1427 to 1470	1475 to 1518				
B75	1427 to 1470 1475 to 1518 1432 to 1517		1	1	1	
B76	1432 to 1517 1427 to 1432		1	1	√	
B77	3300 to 4200		1	1	1	
B78	3300 to 3800		1	✓	1	
B79		o 5000	1	✓	1	
B85	698 to 716	728 to 746	*	✓	√	
B87	410 to 415	420 to 425	*	*	×	
B88	412 to 417	422 to 427	*	*	*	




Mechanical				
Dimensions	142 x 49mm			
Casing	UV Resistant PC/ABS			
Flammability Rating	UL-94			
Connector	SMA Male			


Environmental				
Temperature Range	-40°C to 85°C			
Humidity	Non-condensing 65°C 95% RH			














3.



















4.






Free space


Ground plane (Centre)

Ground plane (Edge)





4.2 30x30cm Ground Plane (Centre) - Patterns at 650 MHz



















4.4 30x30cm Ground Plane (Edge) - Patterns at 650 MHz










4.5 30x30cm Ground Plane (Centre) - Patterns at 750 MHz



















4.7 30x30cm Ground Plane (Edge) - Patterns at 750 MHz









4.8 30x30cm Ground Plane (Centre) - Patterns at 890 MHz



















4.10 30x30cm Ground Plane (Edge) - Patterns at 890 MHz









4.11 30x30cm Ground Plane (Centre) - Patterns at 960 MHz



















4.13 30x30cm Ground Plane (Edge) - Patterns at 960 MHz










4.14 30x30cm Ground Plane (Centre) - Patterns at 1470 MHz



















4.16 30x30cm Ground Plane (Edge) - Patterns at 1470 MHz









4.17 30x30cm Ground Plane (Centre) - Patterns at 1805 MHz



















4.19 30x30cm Ground Plane (Edge) - Patterns at 1805 MHz









4.20 30x30cm Ground Plane (Centre) - Patterns at 1920 MHz



















4.22 30x30cm Ground Plane (Edge) - Patterns at 1920 MHz









4.23 30x30cm Ground Plane (Centre) - Patterns at 2595 MHz



















4.25 30x30cm Ground Plane (Edge) - Patterns at 2595 MHz









4.26 30x30cm Ground Plane (Centre) - Patterns at 3500 MHz



















4.28 30x30cm Ground Plane (Edge) - Patterns at 3500 MHz









4.29 30x30cm Ground Plane (Centre) - Patterns at 5150 MHz



















4.31 30x30cm Ground Plane (Edge) - Patterns at 5150 MHz









4.32 30x30cm Ground Plane (Centre) - Patterns at 5550 MHz



















4.34 30x30cm Ground Plane (Edge) - Patterns at 5550 MHz










5.



Packaging

6.





SPE-12-8-120 - TG.30.8112

Revision: L (Current	Version)
Date:	2023-11-15
Changes:	Updated 5G/4G Bands Table
Changes Made by:	Cesar Sousa

Previous Revisions

Revision: K		Revision: F	
Date:	2023-01-24	Date:	2018-11-30
Changes:	Adding dimensions to mechanical table	Changes:	Removed IP rating
Changes Made by:	Cesar Sousa	Changes Made by:	Jack Conroy

Revision: E

Date:

Revision: J	
Date:	2023-01-17
Changes:	Adding band 40 to spec table (full datasheet update)
Changes Made by:	Gary West

Changes Made by:	Andy Mahoney
Revision: D	
Date:	2017-01-13

2015-03-30 Changes: Updated Spec with LTE table

Revision: I	
Date:	2022-09-26
Changes:	Updated specifications
Changes Made by:	Cesar Sousa

Revision: H	
Date:	2022-05-05
Changes:	Full datasheet template update and show data 600-6000.
Changes Made by:	Gary West

Date:	2017-01-13
Changes:	
Changes Made by:	Technical Writer

Revision: C	
Date:	2012-10-04
Changes:	
Changes Made by:	Technical Writer

Revision: G	
Date:	2021-07-09
Changes:	Added IP Rating
Changes Made by:	Gary West

Revision: B	
Date:	2012-09-27
Changes:	
Changes Made by:	Technical Writer



Revision: A (Original First Release)		
Date:	2012-09-19	
Notes:		
Author:	Technical Writer	





www.taoglas.com