

Specification

Part Number: iDAS.W.001

Product Name: iDAS LTE MIMO Wall Mount Panel Antenna

Features: 2*LTE MIMO Antenna for Indoor Distributed Antenna

Systems

High Performance, Low PIM Antenna

Wall Mounted Rectangular Panel Design

Covers Worldwide LTE Bands (Including 3G/2G)

698-960MHz / 1710-2170MHz / 2500-2690MHz

IP54 Rated Enclosure

Cables: 300mm Low Loss Plenum Rated RG-402 Equivalent

Connector: 4.3-10 mini-DIN [F]

Fully customizable cables and connectors

Dimensions: 308 * 190 * 72mm

RoHS Compliant





1. Introduction

This Taoglas iDAS LTE MIMO antenna is a compact antenna with high performance and low Passive Inter-Modulation (PIM) designed for use in Indoor Distributed Antenna Systems (iDAS) to address in-building coverage issues and the increasing demand for constant connectivity.

The iDAS delivers powerful worldwide 4G LTE MIMO coverage while also covering the 3G and 2G bands and features a compact, easy-to-install wall mounted bracket.

iDAS networks are an excellent solution to bring LTE coverage to areas traditional base stations cannot reach, for example;

- Stadiums, Arenas, Convention Centres
- Hotels, Shopping Malls, Hospitals
- Factories, Warehouses
- Airports, Train Stations, Bus Stations
- Schools, College Campuses
- Office Buildings, High Density Residential Complexes

LTE 4G applications demand high speed data uplink and downlink. High efficiency and high gain MIMO antennas are necessary to achieve the signal to noise ratio and throughput required to solve these challenges. The iDAS antenna is also designed for high isolation and low PIM between the two MIMO antennas to prevent self-interference. Low loss plenum rated cables are used to keep efficiency high while complying with stringent fire rating standards.

The product ships with an RG-402 equivalent plenum rated cable with a temperature spec of up to 150C. The PTFE/FEP jacket is flexible yet chemical and fire resistant. Taoglas offers customizable cable lengths, cable types and connector types, contact your regional Taoglas sales office for support.



2. Specification2.1. Antenna Specifications

Electrical								
Band		LTE 700) GSM		DCS	PCS	UMTS	LTE2600
		Band 12,	13 850/90	00	1800	1900	1700/1800 1900/2100	Band 7
Frequency (MHz)	Port	699~75	6 824~96	50	1710~1880	1850~1990	1710~2170	2500~2690
Peak Gain (dBi)	1	7.2	7.1		7.0	7.1	7.0	7.1
reak Gaill (ubi)	2	7.0	7.6		7.0	7.2	7.0	7.3
Average Gain (dB)	1	-0.6	-0.8		-1.2	-1.1	-1.0	-1.0
Average Gain (ub)	2	-0.7	-0.8		-1.2	-1.1	-1.0	-1.0
Efficiency (%)	1	86	83		75	77	79	79
Efficiency (%)	2	85	83		76	78	79	79
Detum Loca (dP)	1	-17	-17		-21	-20	-22	-23
Return Loss (dB)	2	-15	-17		-22	-21	-22	-22
Front to Back Ratio	1	17	19		14	17	22	20
FIGHT TO BACK RATIO	2	16	17		16	18	21	19
Horizontal HPBW	1	88	80		72	71	82	83
(degrees)	2	85	78		87	82	83	74
Vertical HPBW	1	72	64		68	71	69	66
(degrees)	2	71	60		57	64	66	73
Impedance	50 Ω							
Polarisation	Linear (+45/-45 degree)							
Radiation Pattern	Directional							
Frequency (MHz)	699	9~756 824~960		17	10~1880	1850~1990	1710~2170	2500~2900
PIM Avg. Rating @ 2*43dBm	-161dBc				-160dBc			
PIM Max. Rating @ 2*43dBm	-153dBc				-154dBc			
Max Input Power	2*50W							



Mechanical Mechanical			
Dimensions (L*W*H)	308*190*72mm		
Casing	UV Resistant ABS		
Connector	4.3-10 mini-DIN (F)		
Cable	2*300mm Low Loss Plenum Rated RG-402 Equivalent		
Weight	0.9Kg		
Colour	RAL 9003 White		

Environmental			
Flammability Rating	UL 94-V0		
IP rating	IP54		
Operating Temperature range	-40°C to +85°C		
Storage Temperature range	-40°C to +90°C		
Humidity	Non-condensing 65°C 95%RH		



2.2 Cable Specifications



Part Designation	Material	Outer Diameter (mm)
Inner Conductor	Silver Plated Copper	0.94±0.01
Dielectric	PTFE	2.98±0.05
Outer Conductor	Tin Plated Copper Wire (16*6*0.12)	3.55±0.05
Jacket	FEP Blue	4.10±0.05

Electrical Characteristics			
Performance Property	Spec.		
Capacitance (pF/m)	98		
Impedance(Ohm)	50±2		
Cutoff Frquency (GHz)	34		
Time delay (ns/m)	4.7		
Max Operating Voltage (KVrms)	3000		

Mechanical Specifications				
Performance Properties	Spec.			
Min. bending radius static, single(mm)	8			
Weight (kg/km)	48			
Environmental Specifications				
Operating Temperature (°C)	-65~150			



Attenuation @ 20 °C			
Frequency (GHz)	Attenuation (dB/m)		
0.5	0.27		
1	0.41		
2	0.62		
3	0.78		
5	1.05		
10	1.58		
18	2.22		




Figure 1 Attenuation vs. Frequency



3. Test Setup




Figure 2. VNA test setup (left) and anechoic chamber test setup (right)



4. Antenna Performance

4.1. Return Loss S11 (dB)




Figure 3. Return Loss (dB) S11

4.2 Isolation S21(dB)




Figure 4. Isolation (dB) S21



4.3 Envelope Correlation Coefficient




Figure 5. Envelope Correlation Coefficient (ECC)

4.4 Efficiency (%)




Figure 6. Efficiency (%)



4.5 Peak Gain (dBi)




Figure 7. Peak gain (dBi)

4.6 Average Gain (dB)




Figure 8. Average gain (dB)



5. 2D Radiation Patterns

5.1 2D Radiation Patterns (Freq. range: 698 to 960MHz), Port 1




Figure 9. X-Y polar plot on target bands

Figure 10. Z-X polar plot on target bands




Figure 11. Z-Y polar plot on target bands



5.2 2D Radiation Patterns (Freq. range: 1710 to 2690MHz), Port 1




Figure 12. X-Y polar plots on target bands

Figure 13. Z-X polar plots on target bands




Figure 14. Z-Y polar plots on target bands



5.3 2D Radiation Patterns (Freq. range: 698 to 960MHz), Port 2




Figure 15. X-Y polar plots on target bands bands

Figure 16. Z-X polar plots on target




Figure 17. Z-Y polar plot on target bands



5.4 2D Radiation Patterns (Freq. range: 1710 to 2690MHz), Port.2




Figure 18. X-Y polar plot on target bands

Figure 19. Z-X polar plot on target bands





Figure 20. Z-Y polar plot on target bands




6. 3D Radiation Patterns


6.1 3D Radiation Patterns Port 1

















SPE-18-8-118/A/AW Page **18** of **21**



7. Mechanical Drawing (Unit: mm)







8. Packaging

1pcs iDAS.W.001 per Box Dimensions - 455*320*110mm Weight - 1.5Kg

10pcs iDAS.W.001 per Carton Dimensions - 1155*465*340mm Weight - 17Kg



Pallet Dimensions: 1200mm*1000mm*1220mm 6 Cartons per Pallet 2 Cartons per Layer, 3 Layers





Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein.

Reproduction, use or disclosure to third parties without express permission is strictly prohibited. Copyright © 2012, Taoglas Ltd.