

**NOT RECOMMENDED FOR NEW DESIGNS
RECOMMENDED REPLACEMENT PARTS
KAD2708L-17Q68 OR KAD2708C-17Q68**

September 7, 2010

FN4717.3

8-Bit, 160MSPS, Flash A/D Converter

The HI3276 is an 8-bit, high-speed, flash analog-to-digital converter optimized for high speed, low power, and ease of use. With a 160MSPS encode rate capability and full-power analog bandwidth of 250MHz, this component is ideal for applications requiring the highest possible dynamic performance.

To minimize system cost and power dissipation, only a +5V power supply is required. The HI3276 clock input interfaces directly to TTL, ECL or PECL logic and will operate with single-ended inputs. The user may select 16-bit demultiplexed output or 8-bit single channel digital outputs. The demultiplexed mode interleaves the data through two 8-bit channels at 1/2 the clock rate. Operation in demultiplexed mode reduces the speed and cost of external digital interfaces, while allowing the A/D converter to be clocked to the full 160MSPS conversion rate.

Fabricated with an advanced Bipolar process, the HI3276 is provided in a space-saving 48 lead MQFP surface mount plastic package and is specified over the -20°C to +75°C temperature range.

Ordering Information

| PART NUMBER (Note) | TEMP. RANGE (°C) | PACKAGE (Pb-Free) | PKG. DWG # |
|-----------------------|---------------------|----------------------|-------------|
| HI3276JCQ | -20 to +75 | 48 Ld MQFP | Q48.12x12-S |

NOTE: These Intersil Pb-free plastic packaged products employ special Pb-free material sets; molding compounds/die attach materials and NiPdAu plate - e4 termination finish, which is RoHS compliant and compatible with both SnPb and Pb-free soldering operations. Intersil Pb-free products are MSL classified at Pb-free peak reflow temperatures that meet or exceed the Pb-free requirements of IPC/JEDEC J STD-020.


Features


- Differential Linearity Error ±0.5 LSB
- Integral Linearity Error ±0.5 LSB
- Low Input Capacitance 10pF
- Wide Analog Input Bandwidth 250MHz
- Low Power Consumption 550mW
- 1:2 Demultiplexed Output Pin
- Internal 1/2 Frequency Divider Circuit (w/Reset Function)
- CLK/2 Clock Output
- Compatible with PECL, ECL and TTL Digital Input Levels
- Direct Replacement for Sony CXA3276Q

Applications

- LCD/PDP Monitors and Projectors (RGB Video)
- Digital Oscilloscopes
- Digital Communications (QPSK, QAM)
- Magnetic Recording (PRML)
- Pb-Free (RoHS Compliant)

Pinout



Block Diagram

Absolute Maximum Ratings $T_A = +25^\circ\text{C}$

| | |
|--|--|
| Supply Voltage (AV_{CC} , $\text{DV}_{\text{CC}1}$, $\text{DV}_{\text{CC}2}$) | -0.5V to +7.0V |
| (DGND_3) | -0.5V to +7.0V |
| ($\text{DV}_{\text{EE}3}$) | -7.0V to +0.5V |
| (DGND_3 - $\text{DV}_{\text{EE}3}$) | -0.5V to +7.0V |
| Analog Input Voltage (V_{IN}) | V_{RT} - 2.7V to AV_{CC} |
| Reference Input Voltage (V_{RT}) | +2.7V to AV_{CC} |
| (V_{RB}) | V_{IN} - 2.7V to AV_{CC} |
| ($ \text{V}_{\text{RT}} - \text{V}_{\text{RB}} $) | +2.5V |
| Digital Input Voltage | |
| PECL/ECL | $\text{DV}_{\text{EE}3}$ - 0.5 to DGND_3 + 0.5 |
| TTL | DGND_3 - 0.5 to $\text{DV}_{\text{CC}1}$ + 0.5 |
| V_{ID} (***/E - ***/N/E (Note 1)) | 2.7V |

Recommended Operating Conditions

| WITH A SINGLE POWER SUPPLY | MIN | TYP | MAX |
|---|--------------------------------|-------------------------------|------------------------|
| Supply Voltage | | | |
| $\text{DV}_{\text{CC}1}$, $\text{DV}_{\text{CC}2}$, AV_{CC} | +4.75 | +5.0 | +5.25V |
| DGND_1 , DGND_2 , AGND | -0.05 | 0 | +0.05V |
| DGND_3 | +4.75 | +5.0 | +5.25V |
| $\text{DV}_{\text{EE}3}$ | -0.05 | 0 | +0.05V |
| Analog Input Voltage (V_{IN}) | V_{RB} | - | V_{RT} |
| Reference Input Voltage | | | |
| V_{RT} | +2.9 | - | +4.1V |
| V_{RB} | +1.4 | - | +2.6V |
| $ \text{V}_{\text{RT}} - \text{V}_{\text{RB}} $ | +1.5 | - | +2.1V |
| Digital Input Voltage | | | |
| PECL (***/E) V_{IH} | $\text{DV}_{\text{EE}3}$ + 1.5 | | DGND_3 |
| PECL (***/E) V_{IL} | $\text{DV}_{\text{EE}3}$ + 1.1 | V_{IH} - 0.4V | |
| TTL (***/T, INV) V_{IH} | +2.0V | - | - |
| TTL (***/T, INV) V_{IL} | - | - | +0.8V |
| Other (SELECT) V_{IH} | - | $\text{DV}_{\text{CC}1}$ | - |
| Other (SELECT) V_{IL} | - | DGND_1 | - |
| V_{ID} (Note 1) (***/E - ***/N/E) | +0.4 | +0.8 | - |
| Max Conversion Rate (f_{C} , Straight Mode) | 125 | - | - |
| | | MSPS | |
| Max Conversion Rate (f_{C} , DMUX Mode) | 160 | - | - |
| | | MSPS | |
| Ambient Temperature (T_A) | -20°C to +75°C | | |

Thermal Information

| | |
|-----------------------------------|---|
| Maximum Junction Temperature | 150°C |
| Maximum Storage Temperature Range | -65°C to 150°C |
| Pb-Free Reflow Profile | see link below http://www.intersil.com/pbfree/Pb-FreeReflow.asp |

| WITH DUAL POWER SUPPLIES | MIN | TYP | MAX |
|---|--------------------------------|--------------------------|------------------------|
| Supply Voltage | | | |
| $\text{DV}_{\text{CC}1}$, $\text{DV}_{\text{CC}2}$, AV_{CC} | +4.75 | +5.0 | +5.25V |
| DGND_1 , DGND_2 , AGND | -0.05 | 0 | +0.05V |
| DGND_3 | -0.05 | 0 | +0.05V |
| $\text{DV}_{\text{EE}3}$ | -5.5 | -5.0 | -4.75V |
| Analog Input Voltage (V_{IN}) | V_{RB} | - | V_{RT} |
| Reference Input Voltage | | | |
| V_{RT} | +2.9 | - | +4.1V |
| V_{RB} | +1.4 | - | +2.6V |
| $ \text{V}_{\text{RT}} - \text{V}_{\text{RB}} $ | +1.5 | - | +2.1V |
| Digital Input Voltage | | | |
| PECL/ECL V_{IH} | $\text{DV}_{\text{EE}3}$ + 1.5 | | DGND_3 |
| PECL/ECL V_{IL} | $\text{DV}_{\text{EE}3}$ + 1.1 | V_{IH} - | |
| 0.4 | | | |
| TTL (***/T, INV) V_{IH} | 2.0 | - | - |
| TTL (***/T, INV) V_{IL} | - | - | +0.8V |
| Other (SELECT) V_{IH} | - | $\text{DV}_{\text{CC}1}$ | - |
| Other (SELECT) V_{IL} | - | DGND_1 | - |
| V_{ID} (Note 1) (***/E - ***/N/E) | +0.4 | 0.8 | - |
| Max Conversion Rate (f_{C} , Straight Mode) | 125 | - | - |
| | | MSPS | |
| Max Conversion Rate (f_{C} , DMUX Mode) | 160 | - | - |
| | | MSPS | |
| Ambient Temperature (T_A) | -20°C to +75°C | | |

CAUTION: Do not operate at or near the maximum ratings listed for extended periods of time. Exposure to such conditions may adversely impact product reliability and result in failures not covered by warranty.

NOTES:

1. V_{ID} : Input Voltage Differential.

Electrical Specifications $\text{DV}_{\text{CC}1,2}$, AV_{CC} , $\text{DGND}_3 = +5\text{V}$, $\text{DGND}_1, 2$, AGND , $\text{DV}_{\text{EE}3} = 0\text{V}$, $\text{V}_{\text{RT}} = 4\text{V}$, $\text{V}_{\text{RB}} = 2\text{V}$, $T_A = +25^\circ\text{C}$

| PARAMETER | TEST CONDITIONS | MIN | TYP | MAX | UNITS |
|---|---|-----|-----|-----------|---------------|
| Resolution | | - | 8 | - | Bits |
| DC CHARACTERISTICS | | | | | |
| Integral Linearity Error, INL | $\text{V}_{\text{IN}} = 2\text{V}_{\text{P-P}}$, $f_{\text{C}} = 5\text{MSPS}$ | - | - | ± 0.5 | LSB |
| Differential Linearity Error, DNL | | - | - | ± 0.5 | LSB |
| ANALOG INPUT | | | | | |
| Analog Input Capacitance, C_{IN} | $\text{V}_{\text{IN}} = +3.0\text{V}$, $+0.07\text{V}_{\text{RMS}}$ | - | 10 | - | pF |
| Analog Input Resistance, R_{IN} | | 7 | 15 | 35 | k Ω |
| Analog Input Current, I_{IN} | | 0 | 100 | 285 | μA |
| REFERENCE INPUT | | | | | |
| Reference Resistance (Note 2), R_{REF} | | 400 | 600 | 740 | Ω |
| Reference Current (Note 3), I_{REF} | | 2.7 | 3.3 | 5.0 | mA |
| Offset Voltage V_{RT} Side, EOT | | 6 | 8 | 10 | mV |

HI3276

Electrical Specifications DV_{CC1, 2}, AV_{CC}, DGND3 = +5V, DGND1, 2, AGND, DV_{EE3} = 0V, V_{RT} = 4V, V_{RB} = 2V, T_A = +25°C (Continued)

| PARAMETER | TEST CONDITIONS | MIN | TYP | MAX | UNITS |
|--|---|-------------------------|-------------|-----------------------|-------|
| Offset Voltage V _{RB} Side, EOB | | 0 | 1.5 | 3 | mV |
| DIGITAL INPUT (PECL/ECL) | | | | | |
| Digital Input Voltage: High, V _{IH} | | DV _{EE3} + 1.5 | - | DGND3 | V |
| Digital Input Voltage: Low, V _{IL} | | DV _{EE3} + 1.1 | - | V _{IH} - 0.4 | V |
| Threshold Voltage, V _{TH} | | - | DGND3 - 1.2 | - | V |
| Digital Input Current: High, I _{IH} | V _{IH} = DGND3 - 0.8V | -50 | - | 20 | µA |
| Digital Input Current: Low, I _{IL} | V _{IL} = DGND3 - 1.6V | -50 | - | 20 | µA |
| Digital Input Capacitance | | - | - | 5 | pF |
| DIGITAL INPUT (TTL) | | | | | |
| Digital Input Voltage: High, V _{IH} | | 2.0 | - | - | V |
| Digital Input Voltage: Low, V _{IL} | | - | - | 0.8 | V |
| Threshold Voltage, V _{TH} | | - | 1.5 | - | V |
| Digital Input Current: High, I _{IH} | V _{IH} = 3.5V | -10 | - | 0 | µA |
| Digital Input Current: Low, I _{IL} | V _{IL} = 0.2V | -20 | - | 0 | µA |
| Digital Input Capacitance | | - | - | 5 | pF |
| DIGITAL OUTPUT (TTL) | | | | | |
| Digital Output Voltage: High, V _{OH} | I _{OH} = -2mA | 2.4 | - | - | V |
| Digital Output Voltage: Low, V _{OL} | I _{OL} = 1mA | - | - | 0.5 | V |
| SWITCHING CHARACTERISTICS | | | | | |
| Maximum Conversion Rate, f _C | DMUX Mode | 160 | - | - | MSPS |
| Aperture Jitter, t _{AJ} | | - | 10 | - | ps |
| Sampling Delay, t _{DS} | | 1.2 | 1.3 | 1.5 | ns |
| Clock High Pulse Width, t _{PW1} | CLK | 2.5 | - | - | ns |
| Clock Low Pulse Width, t _{PW0} | CLK | 2.9 | - | - | ns |
| RESET Signal Setup Time, t _{RS} | RESETN-CLK | 1.0 | - | - | ns |
| RESET Signal Hold Time, t _{RH} | RESETN-CLK | -0.5 | - | - | ns |
| CLKOUT Output Delay, t _{DCLK} | C _L = 5pF | 3.0 | 4.5 | 6.5 | ns |
| Data Output Delay (Note 4), t _{DO1} t _{DO2} | DMUX Mode (C _L = 5pF) | - | t + 0.5 | - | ns |
| | (C _L = 5pF) | 3.5 | 4.5 | 7.0 | ns |
| Output Rise Time, t _r | 0.8 to 2.0V (C _L = 5pF) | - | 1 | - | ns |
| Output Fall Time, t _f | 0.8 to 2.0V (C _L = 5pF) | - | 1 | - | ns |
| DYNAMIC CHARACTERISTICS | | | | | |
| Input Bandwidth | V _{IN} = 2V _{P-P} , -3dB | 250 | - | - | MHz |
| S/N Ratio | f _C = 160MSPS, f _{IN} = 1kHz Full Scale, DMUX Mode | - | 46 | - | dB |
| | f _C = 160MSPS, f _{IN} = 29.999MHz Full Scale, DMUX Mode | - | 42 | - | dB |
| Error Rate (Note 5) | f _C = 160MSPS, f _{IN} = 1kHz Full Scale, DMUX Mode, Error > 16 LSB | - | - | 10 ⁻¹² | TPS |
| | f _C = 160MSPS, f _{IN} = 29.999MHz Full Scale, DMUX Mode, Error > 16 LSB | - | - | 2 x 10 ⁻⁸ | TPS |
| | f _C = 125MSPS, f _{IN} = 24.999MHz Full Scale, Straight Mode, Error > 16 LSB | - | - | 10 ⁻⁹ | TPS |
| POWER SUPPLY OPERATING | | | | | |
| Total Supply Current, I _{CC} + I _{EE} | | 89 | 108 | 140 | mA |
| AV _{CC} Pin Supply Current, A _{1CC} | | 62 | - | 87 | mA |
| DV _{CC1} Pin Supply Current, D _{1CC1} | | 22 | - | 36 | mA |
| DV _{CC2} Pin Supply Current, D _{1CC2} | | 4.0 | - | 15 | mA |

Electrical Specifications DV_{CC1, 2}, AV_{CC}, DGND3 = +5V, DGND1, 2, AGND, DV_{EE3} = 0V, V_{RT} = 4V, V_{RB} = 2V, T_A = +25°C (Continued)

| PARAMETER | TEST CONDITIONS | MIN | TYP | MAX | UNITS |
|---|-----------------|-----|-----|-----|-------|
| DGND3 Pin Supply Current, I _{EE} | | 0.5 | - | 1.5 | mA |
| Power Consumption, PD ^{*6} | | 480 | 550 | 700 | mW |

NOTES:


2. R_{REF}: Resistance value between V_{RT} and V_{RB}

$$3. I_{REF} = \frac{V_{RT} - V_{RB}}{R_{REF}}$$

$$4. t = \frac{1}{f_C}$$

5. The unit of measure TPS: Times Per Sample

$$6. P_D = (I_{CC} + I_{EE}) \cdot V_{CC} + \frac{(V_{RT} - V_{RB})^2}{V_{REF}}$$

Timing DiagramsFIGURE 1. DMUX MODE TIMING CHART (SELECT = V_{CC})


Timing Diagrams (Continued)

FIGURE 2. STRAIGHT MODE TIMING CHART (SELECT = GND)




FIGURE 3. PECL SWITCHING LEVEL

Pin Descriptions

| PIN NO | SYMBOL | I/O | TYPICAL VOLTAGE LEVEL | EQUIVALENT CIRCUIT | DESCRIPTION |
|------------|-------------------|-----|--|--------------------|--|
| 3, 10 | AGND | | GND | | Analog Ground. Separated from the digital ground. |
| 5, 8 | AV _{CC} | | +5V (Typ) | | Analog Power Supply. Separated from the digital power supply |
| 29 | DGND1 | | GND | | Digital Ground |
| 20, 32, 41 | DGND2 | | | | |
| 30 | DV _{CC1} | | +5V (Typ) | | Digital Power Supply |
| 19, 31, 42 | DV _{CC2} | | | | |
| 12 | DGND3 | | +5V (Typ) (with a Single Power Supply) GND (with Dual Power Supplies) | | Digital Power Supply. Ground for ECL input. +5V for PECL and TTL inputs. |

Pin Descriptions (Continued)

| PIN NO | SYMBOL | I/O | TYPICAL VOLTAGE LEVEL | EQUIVALENT CIRCUIT | DESCRIPTION |
|------------|-------------------|-----|--------------------------------------|--------------------|--|
| 1 | DV _{EE3} | | GND (With a Single Power Supply) | | Digital Power Supply. Apply -5V for PECL and TTL input. |
| | | | +5V (Typ) (With Dual Power Supplies) | | |
| 16, 17, 18 | NC | | | | No Connect Pin |
| 13 | CLK/E | I | PECL/ECL | | Clock Input |
| 14 | CLK/NE | I | | | CLK/E Complementary Input. When left open, this pin goes to the threshold potential. Only CLK/E can be used for operation, but complementary input is recommended to attain fast and stable operation. |
| 48 | RESETN/E | I | | | Reset Input. When the input is set to low level, the built-in CLK frequency divider circuit can be reset. |
| 47 | RESET/E | I | | | RESETN/E Complementary Input. When left open, this pin goes to the threshold voltage. Only RESETN/E can be used for operation. |
| 15 | CLK/T | I | | | Clock input |
| 46 | RESETN/T | I | TTL | | Reset Input. When left open, this input goes to high level. When the input is set to low level, the built-in CLK frequency divider circuit can be reset. |
| 44 | INV | I | | | Data Output Polarity Inversion Input. When left open, this input goes to high level. (See Table 1; I/O Correspondence Table). |
| 45 | SELECT | | | | Data Output Mode Selection. (See Table 2; Operating Mode Table). |

Pin Descriptions (Continued)




| PIN NO | SYMBOL | I/O | TYPICAL VOLTAGE LEVEL | EQUIVALENT CIRCUIT | DESCRIPTION |
|----------|------------------|-----|--|--|---|
| 11 | V _{RT} | I | 4.0V (Typ) | | Top Reference Voltage. Bypass to AGND with a 1µF tantal capacitor and a 0.1µF chip capacitor. |
| 9 | V _{RM3} | | V _{RB} + 3/4 (V _{RT} - V _{RB}) | | Reference Voltage Mid Point. Bypass to AGND with a 0.1µF chip capacitor. |
| 7 | V _{RM2} | | V _{RB} + 2/4 (V _{RT} - V _{RB}) | | Reference Voltage Mid Point. Bypass to AGND with a 0.1µF chip capacitor. |
| 4 | V _{RM1} | | V _{RB} + 1/4 (V _{RT} - V _{RB}) | | Reference Voltage Mid Point. Bypass to AGND with a 0.1µF chip capacitor. |
| 2 | V _{RB} | I | 2.0V (Typ) |  | Bottom Reference Voltage. Bypass to AGND with a 1µF tantal capacitor and a 0.1µF chip capacitor. |
| 6 | V _{IN} | I | V _{RT} to V _{RB} |  | Analog Input. |
| 21 to 28 | PAD0 to PAD7 | O | TTL | | Port A side data output. TTL output; the high level is clamped to approximately 2.8V. |
| 33 to 40 | PBD0 to PBD7 | O | | | Port B side data output. TTL output; the high level is clamped to approximately 2.8V. |
| 43 | CLKOUT | O | |  | Clock Output. (See Table 2; Operating Mode Table). TTL output; the high level is clamped to approximately 2.8V. |

TABLE 1. A/D CODE

| V _{IN} | STEP | INV | | | |
|------------------|------|-----------------|----|-----------------|----|
| | | 1 | | 0 | |
| | | D7 | D0 | D7 | D0 |
| V _{RT} | 255 | 1 1 1 1 1 1 1 1 | 1 | 0 0 0 0 0 0 0 0 | 0 |
| | 254 | 1 1 1 1 1 1 1 0 | 0 | 0 0 0 0 0 0 0 1 | 1 |
| | • | • | • | • | • |
| | • | • | • | • | • |
| | 128 | 1 0 0 0 0 0 0 0 | 0 | 0 1 1 1 1 1 1 1 | 1 |
| | 127 | 0 1 1 1 1 1 1 1 | 1 | 0 0 0 0 0 0 0 0 | 0 |
| V _{RM2} | • | • | • | • | • |
| | • | • | • | • | • |
| | 1 | 0 0 0 0 0 0 0 1 | 1 | 1 1 1 1 1 1 1 0 | 0 |
| V _{RB} | 0 | 0 0 0 0 0 0 0 0 | 1 | 1 1 1 1 1 1 1 1 | 1 |

Notes on Operation

- The HI3276 is a high-speed A/D converter which is capable of TTL, ECL and PECL level clock input. Characteristic impedance should be properly matched to ensure optimum performance during high-speed operation.
- The power supply and grounding have a profound influence on converter performance. The power supply and grounding method are particularly important during high-speed operation. General points for caution are as follows:
 - The ground pattern should be as large as possible. It is recommended to make the power supply and ground patterns wider at an inner layer using a multi-layer board.
 - To prevent interference between AGND and DGND and between AV_{CC} and DV_{CC}, make sure the respective patterns are separated. To prevent a DC offset in the power supply pattern, connect the AV_{CC} and DV_{CC} lines

Test Circuits




FIGURE 4. CURRENT CONSUMPTION MEASUREMENT CIRCUIT

at one point each, via a ferrite-bead filter. Shorting the AGND and DGND patterns in one place immediately under the A/D converter improves A/D converter performance.

- Ground the power supply pins (AV_{CC}, DV_{CC1}, DV_{CC2}, DV_{EE3}) as close to each pin as possible with a 0.1μF or larger ceramic chip capacitor. (Connect the AV_{CC} pin to the AGND pattern and the DV_{CC1}, DV_{CC2}, DV_{EE3} pins to the DGND pattern).
- The digital output wiring should be as short as possible. If the digital output wiring is long, the wiring capacitance will increase, deteriorating the output slew rate and resulting in reflection to the output waveform since the original output slew rate is quite fast.
- The analog input pin V_{IN} has an input capacitance of approximately 10pF. To drive the A/D converter with proper frequency response, it is necessary to prevent performance deterioration due to parasitic capacitance or parasitic inductance by using a large capacity drive circuit; keeping wiring as short as possible, and using chip parts for resistors and capacitors, etc.

- The V_{RT} and V_{RB} pins must have adequate bypass to protect them from high-frequency noise. Bypass them to AGND with approximately 1μF tantalum capacitor and, 0.1μF capacitor. At this time, approximately DGND3 - 1.2V voltage is generated. However, this is not recommended for use as threshold voltage V_{BB} as it is too weak.
- The TTL output high level is clamped to approximately 2.8V in the IC. This makes it possible to directly interface with 3.3V CMOS ICs.

When the digital input level is PECL level, ***/E pins should be used and ***/T pins left open. When the digital input level is TTL, ***/T pins should be used and III/E pins left open.




FIGURE 5. INTEGRAL LINEARITY ERROR/DIFFERENTIAL LINEARITY ERROR MEASUREMENT CIRCUIT


Test Circuits (Continued)

FIGURE 6. ERROR RATE MEASUREMENT CIRCUIT





FIGURE 7. SAMPLING DELAY/APERTURE JITTER MEASUREMENT CIRCUIT



NOTE: Where σ (LSB) is the deviation of the output codes when the largest slew rate point is sampled at the clock which has exactly the same frequency as the analog input signal, the aperture jitter t_{AJ} is shown in Equation 1.

$$t_{AJ} = \left(\sigma / \frac{\Delta V}{\Delta t} \right) = \sigma / \left(\frac{256}{2} \times 2\pi f \right) \quad (\text{EQ. 1})$$

FIGURE 8. APERTURE JITTER MEASUREMENT METHOD

Operating Modes

The HI3276 has two types of operating modes which are selected with Pin 45 (SELECT).

TABLE 2. OPERATING MODE

| OPERATING MODE | SELECT | MAXIMUM CONVERSIONRATE | DATA OUTPUT | CLOCK OUTPUT |
|----------------|-----------------|------------------------|-----------------------------|---|
| DMUX Mode | V _{CC} | 160MSPS | Demultiplexed Output 80MBPS | The input clock is 1/2 frequency divided and output at 80MHz. |
| Straight Mode | GND | 125MSPS | Straight Output 125MBPS | The input clock is inverted and output at 100MHz. |

DMUX Mode (See Application Circuits, Figures 18, 19)

Set the SELECT pin to V_{CC} for this mode. In this mode, the clock frequency is divided by 2 in the IC, and the data is output after being demultiplexed by this 1/2 frequency divided clock. The 1/2 frequency divided clock, which has adequate setup time and hold time for the output data, is output from the CLKOUT pin.

When using multiple HI3276 units in parallel in this mode, differences in the start timing of the 1/2 frequency divided clock may cause operation as shown in Figure 9. As a countermeasure, the HI3276 is equipped with a function which resets the 1/2 frequency divided clock. When resetting this clock, the RESET pulse must be input to the RESET pin. See the "Timing Diagrams" on page 5 for the RESET pulse

input timing. The A/D converter can operate at f_C (Min) = 160MSPS in this mode.

Straight Mode (See Application Circuits, Figures 20, 21)

Set the SELECT pin to GND for this mode. In this mode, data output can be obtained in accordance with the clock frequency applied to the A/D converter for applications which use the clock applied to the A/D converter as the system clock.

The A/D converter can operate at f_C (Min) = 100MSPS in this mode.

Digital Input Level and Supply Voltage Settings

The logic input level for the HI3276 supports PECL and TTL levels. The power supplies (DV_{EE3}, DGND3) for the logic input block must be set to match the logic input (CLK and RESET signals) level.

TABLE 3. LOGIC INPUT LEVEL AND POWER SUPPLY SETTINGS

| DIGITAL INPUT LEVEL | DV _{EE3} | DGND3 | SUPPLY VOLTAGE | APPLICATION CIRCUITS |
|---------------------|-------------------|-------|----------------|----------------------|
| PECL | 0V | +5V | +5V | Figures 18, 20 |
| TTL | 0V | +5V | +5V | Figures 19, 21 |




FIGURE 9. WHEN THE RESET PULSE IS NOT USED




FIGURE 10. WHEN THE RESET PULSE IS USED

Typical Performance Curves




FIGURE 11. CURRENT CONSUMPTION vs AMBIENT TEMPERATURE CHARACTERISTICS




FIGURE 12. CURRENT CONSUMPTION vs CONVERSION RATE CHARACTERISTICS RESPONSE


Typical Performance Curves (Continued)

FIGURE 13. ANALOG INPUT CURRENT vs ANALOG INPUT VOLTAGE CHARACTERISTICS




FIGURE 14. REFERENCE CURRENT vs AMBIENT TEMPERATURE CHARACTERISTICS




FIGURE 15. SNR vs INPUT FREQUENCY RESPONSE




FIGURE 16. ERROR RATE vs CONVERSION RATE CHARACTERISTICS




FIGURE 17. MAXIMUM CONVERSION RATE vs AMBIENT TEMPERATURE CHARACTERISTICS


Application Circuits

FIGURE 18. DMUX PECL INPUT




FIGURE 19. DMUX TTL INPUT


Application Circuits (Continued)

FIGURE 20. STRAIGHT PECL INPUT




FIGURE 21. STRAIGHT TTL INPUT



Application Circuits (Continued)

FIGURE 22. STRAIGHT MODE TTL I/O (WHEN A SINGLE POWER SUPPLY IS USED)

Metric Plastic Quad Flatpack Packages (MQFP/PQFP)

Q48.12x12-S
48 LEAD METRIC PLASTIC QUAD FLATPACK PACKAGE

| SYMBOL | INCHES | | MILLIMETERS | | NOTES |
|--------|-----------|-------|-------------|-------|-------|
| | MIN | MAX | MIN | MAX | |
| A | 0.081 | 0.100 | 2.05 | 2.55 | - |
| A1 | 0.000 | 0.011 | 0.00 | 0.30 | - |
| B | 0.008 | 0.017 | 0.20 | 0.45 | 5 |
| D | 0.587 | 0.618 | 14.90 | 15.70 | 2 |
| D1 | 0.469 | 0.488 | 11.90 | 12.40 | 3, 4 |
| E | 0.587 | 0.618 | 14.90 | 15.70 | 2 |
| E1 | 0.469 | 0.488 | 11.90 | 12.40 | 3, 4 |
| L | 0.028 | 0.043 | 0.70 | 1.10 | - |
| N | 48 | | 48 | | 6 |
| e | 0.032 BSC | | 0.80 BSC | | - |

Rev. 0 2/96

NOTES:

1. Controlling dimension: MILLIMETER. Converted inch dimensions are not necessarily exact.
2. Dimensions D and E to be determined at seating plane [-C-].
3. Dimensions D1 and E1 to be determined at datum plane [-H-].
4. Dimensions D1 and E1 do not include mold protrusion.
5. Dimension B does not include dambar protrusion.
6. "N" is the number of terminal positions.

All Intersil U.S. products are manufactured, assembled and tested utilizing ISO9000 quality systems.
Intersil Corporation's quality certifications can be viewed at www.intersil.com/design/quality

Intersil products are sold by description only. Intersil Corporation reserves the right to make changes in circuit design, software and/or specifications at any time without notice. Accordingly, the reader is cautioned to verify that data sheets are current before placing orders. Information furnished by Intersil is believed to be accurate and reliable. However, no responsibility is assumed by Intersil or its subsidiaries for its use; nor for any infringements of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Intersil or its subsidiaries.

For information regarding Intersil Corporation and its products, see www.intersil.com