

SPECIFICATION

Part No. : MAT.500.B

Product Name : MAT.500.B 5in1 Multi-Band Antenna Board

LTE MIMO + GPS/GLONASS +Wi-Fi MIMO

Features : 2* LTE MIMO 698-960MHz/1710-2170MHz/

2490-2690MHz


2* Wi-Fi MIMO 2.4GHz/5GHz 1* GPS-GLONASS Antenna

Worldwide 4G Bands including 3G and 2G

Dims: 157.32mm*103.19mm*30mm

IPEX connectors, 1.37mm cables

RoHS Compliant





1. Introduction

The MAT.500.B embedded antenna board combines LTE MIMO antennas, Wi-Fi MIMO antennas, plus GPS/GLONASS antenna. It can be used as a reference design or actual embedded antenna for telematics applications such as fleet management, asset tracking, and security/surveillance.

The board comes with five IPEX connectors and 1.37mm coax cables for LTE, Wi-Fi, and GPS/GLONASS antennas.

Typical applications:

- Automotive and Heavy Equipment Vehicle Tracking and Telematics
- Remote Asset and Pipeline Monitoring
- HD Video over LTE
- First Responder and Emergency Services
- Global Data Communications/IoT

LTE 4G applications demand high speed data uplink and downlink. High efficiency and high gain MIMO antennas are necessary to achieve the required signal to noise ratio and throughput required to solve these challenges. Taoglas also takes care to have high isolation between the two MIMO antennas to prevent self-interference. Low loss cables are used to keep efficiency high over long cable lengths.

The GPS-GLONASS passive antenna receives efficiently on all two bands, leading to higher location accuracy and stability of tracking in urban environments.

The unique omnidirectional Wi-Fi antennas provide high efficiency and high isolation between antenna elements in a heavy-duty low profile compact structure, delivering powerful MIMO antenna technology for Wi-Fi 802.11n and emerging 802.11ac.

Cable length and connector types are customizable. Contact your regional Taoglas sales office for support.



2. Specification

GPS-GLONASS				
Center Frequency	GPS:1575.42±1.023 MHz GLONASS:1602±5 MHz			
Passive Antenna Efficiency	GPS: 75% GLONASS: 68%			
Average gain	GPS: -1.2dBi GLONASS: -1.6dBi			
Peak gain	GPS: 5.47dBi GLONASS: 4.9dBi			
VSWR	2:1 Max			
Impedance	50Ω			
Axial Ratio	GPS:< 5.1 GLONASS:< 6.3			
Polarization	RHCP			
Cable	ψ1.37 Micro Coax. 68mm standard, fully customizable			
Connector	IPEX standard, fully customizable			

4G/3G/2G LTE Antenna							
Frequency (MHz)	LTE700	GSM850	GSM900	DCS	PCS	UMTS1	LTE2600
	698~803	824~894	880~960	1710~1880	1850~1990	1920~2170	2490~2690
Efficiency (%)							
MIMO_1	44.65	50.40	28.06	68.20	67.23	56.83	33.30
MIMO_2	40.43	35.92	25.54	66.06	60.22	56.20	29.30
	Average Gain(dBi)						
MIMO_1	-3.58	-3.04	-5.70	-1.67	-1.74	-2.55	-4.78
MIMO_2	-4.00	-4.60	-5.93	-1.83	-2.21	-2.51	-5.34
Peak Gain(dBi)							
MIMO_1	0.28	1.70	1.70	6.79	7.06	6.81	1.35
MIMO_2	0.55	1.07	-1.42	5.23	5.23	4.64	1.38
Envelope Correlation Coefficient (ECC)			< 0.33				
Impedance			50Ω				
Polarization			Linear				
VSWR			< 4				
Cable			ψ1.37 78mm/MIMO_1, 133mm/MIMO_2 standard, fully customizable				
Connector			I-PEX standard, fully customizable				



2.4GHz/5GHz Wi-Fi Antenna					
Frequency (MHz)	2400~2500	4900~5850			
Efficiency (%)					
MIMO_1	50.51	61.87			
MIMO_2	65.72	60.18			
Average Gain(dBi)					
MIMO_1	-2.97	-2.10			
MIMO_2	-1.84	-2.22			
Peak Gain(dBi)					
MIMO_1	5.14	4.77			
MIMO_2	5.82	4.96			
Impedance	50Ω				
Polarization	Linear				
VSWR	< 2.2				
Cable	ψ1.37 Micro Coax. 68mm for MIMO_1, 118mm for MIMO_2 standard, fully customizable				
Connector	I-PEX standard, fully customizable				

MECHANICAL				
Antenna Dimensions 157.32mm*103.19mm*30mm				
Weight	66g			
ENVIRONMENTAL				
Operation Temperature	-40°C to 85°C			
Storage Temperature	-40°C to 90°C			
Humidity	Non-condensing 65°C 95% RH			






3. Antenna Characteristics

3.1 GPS-GLONASS Antenna

3.1.1 Test Setup




3.1.2 GPS-GLONASS Return Loss






3.1.3 GPS-GLONASS Smith Chart




3.1.4 GPS-GLONASS VSWR






3.1.5 GPS-GLONASS Efficiency




3.1.6 GPS-GLONASS Average Gain






3.1.7 GPS-GLONASS Peak Gain






3.1.8 Test Setup for Antenna Radiation Pattern



In ZRM 500 Housing




3.1.9 GPS-GLONASS 2D Radiation Pattern 2D Radiation Pattern @ 1575.42MHz




XZ Plane (phi=0°, T YZ Plane (phi=90°, Theta=0~360°)

3.1.10 GPS-GLONASS 3D Radiation Pattern 3D Radiation pattern @ 1575.42MHz






3.1.11 GPS-GLONASS 2D Radiation Pattern 2D Radiation pattern @ 1602MHz




3.1.12 GPS-GLONASS 3D Radiation Pattern 3D Radiation pattern @ 1602MHz






3.1.13 Axial Ratio Pattern Frequency: 1575.42MHz



XZ Plane (phi=0°, Theta= -180~180°), 0 degree face Zenith

Frequency: 1602MHz



XZ Plane (phi=0 $^{\circ}\,$, Theta= -180~180 $^{\circ}\,$), 0 degree face Zenith




3.2 LTE_MIMO/Wi-Fi_MIMO Antenna

3.3.1 Test Setup






3.3.2 LTE MIMO Antenna S-parameters




3.3.3 Envelope Correlation Coefficient (LTE)






3.3.4 LTE Antenna Efficiency




3.3.5 LTE Antenna Peak Gain






3.3.6 LTE Antenna Average Gain




3.3.7 Wi-Fi Antenna Return Loss






3.3.8 Envelope Correlation Coefficient




3.3.9 Wi-Fi Antenna Efficiency






3.3.10 Wi-Fi Antenna Peak Gain




3.3.11 Wi-Fi Antenna Average Gain





3.3.12 Test Setup For Antenna Radiation Pattern (ETS Anechoic chamber)





In ZRM500 Housing



3.3.13 2D Radiation Pattern (LTE_MIMO1)


XY Plane









XZ Plane









YZ Plane









3.3.14 3D Radiation Pattern (LTE_MIMO1)




704MHz







1710MHz



2170MHz









3.3.15 2D Radiation Pattern (LTE_MIMO2)

XY Plane







XZ Plane






YZ Plane









3.3.16 3D Radiation Pattern (LTE_MIMO2)






704MHz


960MHz






1710MHz

2170MHz






2690MHz

3500MHz




3.3.17 2D Radiation Pattern (Wi-Fi_MIMO1)


XY Plane



XZ Plane





YZ Plane





3.3.18 3D Radiation Pattern (Wi-Fi_MIMO1)






2450MHz 5550MHz




3.3.19 2D Radiation Pattern (Wi-Fi_MIMO2)


XY Plane



XZ Plane




YZ Plane






3.3.20 3D Radiation Pattern (Wi-Fi_MIMO2)




2450MHz




5550MHz



4. Mechanical Drawing (Unit: mm)





	Name	P/N	Material	Finish	QTY
1	MAT.500B Antenna Carry Board	100216C020000A	Composite t=1.0	Black	1
2	MAT.500 LTE Antenna Board	100216C030000A	Composite t=1.0	Black	2
3	MAT.500 WiFi Antenna	000515A000095A	Cu-Ni-Zn Alloy,t=0.25	N/A	2
4	GNSS Antenna (36x36x4)	CGGP.36.4.Z.02	Ceramic patch	Clear	1
5	1.37 Coaxial Cable	300515C010000A	FEP	Black	5
6	IPEX.MHFHT	204511G000002A	Brass	Au plated	5



6. Packaging

Packaging Specifications


1 pc MAT.500.B per PE bag Dimensions - 155*240mm Total Weight - 80g


8 pc MAT.500.B per inner carton Dimensions - 285*175*120 Weight - 831g

Dimensions - 370*370*300 Weight - 5Kg

48 pc MAT.500.B per outer carton

Pallet Dimensions 1200mm*1000mm*1360mm 24 Cartons per pallet 6 Cartons per layer 4 Layers 1400mm







Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice.

Taoglas reserves the rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

Copyright © Taoglas Ltd.