CUSTOMER: Doc No: MES003227

Rev: A0

RoHS Comp.
Halogen Free

Customer P/N

承認書

APPROVAL SHEET

Specifications description	:	AVEA Series
APAQ P/N	;	

Date	Approved by	Checked by
2017.03.07 APPROVAL	煤明系	林軒逸

Approved by Customer		
(Signing or stamping here)	:	
Approved Date	:	



鈺邦科技股份有限公司

APAQ TECHNOLOGY CO., LTD

竹南科學園區

苗栗縣竹南鎮科東三路 2&6 號 4 樓

4F., No.2 & 6, Kedong 3rd Rd., Chunan

Science Park, Miaoli County 350,

Taiwan ,(R.O.C.)

AP-CON AVEA SERIES SPECIFICATION

1. Application

This specification shall be specified to conductive polymer aluminum solid electrolytic capacitors of AVEA series.

2. Composition of part number

2R5

<u>AVEA</u>

331

M

0606

Rated voltage Series code Capacitance Cap tolerance Size code

2.1 Rated voltage code

Table 1 Rated voltage and surge voltage

		<u> </u>
Rated voltage code	Rated voltage (V)	Surge voltage (V)
2R5	2.5	2.9
4R0	4	4.6
6R3	6.3	7.2
160	16	18.4
250	25	28.8

2.2 Capacitance code

Table 2 Rated capacitance

Capacitance code	Capacitance (uF)
100	10
270	27
101	100
471	470
122	1200

2.3 Capacitance tolerance code

Table 3 Capacitance tolerance

Cap tolerance code	Cap tolerance
M	±20%

	TIONS ARE THE PROPERTY OF APAQ LL NOT BE REPRODUCT OR USED	Δ	鈺邦科技	股份	有限公司	
AS THE BASIC FOR THE MANUFA DEVICES WITHOUT PERMISSION.	L. IPAQ	APA	AQ TE	CHNOLOGY CO., LT	D	
DESIGNED BY:陳明宗 DRAWN BY: 施雅瑄		CHECKED B	BY:林軒逸 APPROVED BY:高良日		月身	
THE E . AD CON AVEA CEDIES S	DOCUMENT		MES00	2227	REV	
TITLE: AP-CON AVEA SERIES SPECIFICATION		NO.	ľ	VIESUU	3221	A0

2.4 Size code

Table 4 Dimension of radial type capacitors

Size code	Diameter	Case length
Size code	(mm)	(mm)
0545	5	4.2
0506	5	5.8
0645	6.3	4.3
0606	6.3	5.8
0608	6.3	7.5
0610	6.3	9.7
0807	8	6.8
0810	8	9.7
0812	8	11.7
1008	10	7.5
1012	10	12.3

3. Rating

3.1 Category temperature range

-55 to +105 °C

3.2 Surge voltage

Rated voltage x 1.15

3.3 Rated ripple current

Rated ripple current shall be in accordance with standard ratings list. These current are rms values for sine wave of 100kHz at 105 $^{\circ}$ C.

THIS DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF APAC TECHNOLOGY CO. LTD AND SHALL NOT BE REPRODUCT OR USED	A	鈺邦科技股份	有限公司	
AS THE BASIC FOR THE MANUFACTURE OR SALE OF APPARATUS OR DEVICES WITHOUT PERMISSION.	X. PAQ	APAQ TE	CHNOLOGY CO., LT	D
DESIGNED BY: 陳明宗 DRAWN BY: 施雅瑄	CHECKED B	BY:林軒逸	APPROVED BY: 高	長民
TITLE : AP-CON AVEA SERIES SPECIFICATION	DOCUMENT	MESO	2227	REV
IIILE · Ar-CON AVEA SERIES SPECIFICATION	NO.	NO. MES003227		A0

3.4 Standard ratings

Table 5 Standard ratings

WV/Vdc (SV)	Cap (µF)	Size Code	Leakage Current (µA)	tanδ	ESR (mΩmax/20%, 100k to300kHz)	Rated Ripple Current (mArms/ 105°ℂ/100kHz)	Part No.
	330	0506	165	0.12	21	2,670	2R5AVEA331M0506
	330	0645	700	0.12	17	2,300	2R5AVEA331M0645
	330	0606	413	0.12	15	3,160	2R5AVEA331M0606
2.5	390	0506	700	0.12	10	3,900	2R5AVEA391M0506
2.5 (2.9)	390	0606	292	0.12	10	3,900	2R5AVEA391M0606
(2.9)	560	0606	700	0.12	10	3,900	2R5AVEA561M0606
	560	0607	700	0.12	10	4,000	2R5AVEA561M0607
	820	0610	500	0.12	9	4,500	2R5AVEA821M0610
	820	0810	500	0.12	9	5,380	2R5AVEA821M0810
	100	0645	200	0.12	25	2,000	4R0AVEA101M0645
	220	0606	440	0.12	25	2,500	4R0AVEA221M0606
1	330	0606	660	0.12	15	3,160	4R0AVEA331M0606
4 (4.6)	560	0807	500	0.12	22	3,220	4R0AVEA561M0807
(4.0)	560	0810	500	0.12	9	5,380	4R0AVEA561M0810
	560	0812	500	0.12	9	5,380	4R0AVEA561M0812
	680	1008	544	0.12	25	3,700	4R0AVEA681M1008

	TIONS ARE THE PROPERTY OF APAQ LL NOT BE REPRODUCT OR USED	A	鈺邦科.	技股份	有限公司		
AS THE BASIC FOR THE MANUFA DEVICES WITHOUT PERMISSION	L. IPAQ		APAQ TE	CHNOLOGY CO., LT	Œ		
DESIGNED BY:陳明宗	DRAWN BY: 施雅瑄	CHECKED I	BY:林軒逸		APPROVED BY:高	良民	
TEVEL E . AD CON AVEA CEDIEC C	DOCUMENT		MEGOO	2225	F	REV	
TITLE: AP-CON AVEA SERIES SPECIFICATION		NO.		MES00	13421	A	A 0

WV/Vdc (SV)	Cap (µF)	Size Code	Leakage Current (µA)	tanδ	ESR (mΩmax/20%, 100k to300kHz)	Rated Ripple Current (mArms/ 105°C/100kHz)	Part No.
	47	0506	148	0.12	35	1,380	6R3AVEA470M0506
	100	0645	315	0.12	19	2,300	6R3AVEA101M0645
	100	0606	315	0.12	27	2,400	6R3AVEA101M0606
	150	0606	473	0.12	15	2,700	6R3AVEA151M0606
	150	0645	472	0.12	19	2,780	6R3AVEA151M0645
	180	0506	226	0.12	17	3,100	6R3AVEA181M0506
	220	0506	500	0.12	15	3,150	6R3AVEA221M0506
0.0	220	0645	700	0.12	17	2,300	6R3AVEA221M0645
6.3	220	0606	277	0.12	15	3,160	6R3AVEA221M0606
(7.2)	330	0606	416	0.12	17	3,390	6R3AVEA331M0606
	330	1008	416	0.12	20	4,130	6R3AVEA331M1008
	470	0807	592	0.12	10	4,300	6R3AVEA471M0807
	560	0610	705	0.12	10	4,300	6R3AVEA561M0610
	560	0808	705	0.12	9	4,500	6R3AVEA561M0808
	560	0810	705	0.12	10	4,500	6R3AVEA561M0810
	820	0810	1,033	0.12	12	5,440	6R3AVEA821M0810
	1000	0810	1,260	0.12	10	5,440	6R3AVEA102M0810
	120	0606	600	0.12	25	2,530	100AVEA121M0606
	150	0606	300	0.12	21	2,880	100AVEA151M0606
40	220	0606	440	0.12	25	2,530	100AVEA221M0606
10 (11.5)	220	0610	440	0.12	15	3,100	100AVEA221M0610
(11.5)	330	0807	660	0.12	19	3,550	100AVEA331M0807
	330	0810	660	0.12	17	3,950	100AVEA331M0810
	330	0812	660	0.12	17	3,950	100AVEA331M0812

THIS DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF APAQ TECHNOLOGY CO. LTD AND SHALL NOT BE REPRODUCT OR USED	A	鈺邦科技股份	有限公司	
AS THE BASIC FOR THE MANUFACTURE OR SALE OF APPARATUS OR DEVICES WITHOUT PERMISSION.	L. IPAQ	APAQ TE	CHNOLOGY CO., LT	D
DESIGNED BY: 陳明宗 DRAWN BY: 施雅瑄	CHECKED B	HECKED BY:林軒逸 APPROVED BY:高良民		
TITLE : AP-CON AVEA SERIES SPECIFICATION	SERIES SPECIFICATION DOCUMENT MES003227		REV	
TITLE - AT-CON AVEA SERIES SPECIFICATION	NO.	MESO	13441	A0

WV/Vdc (SV)	Cap (µF)	Size Code	Leakage Current (µA)	tanδ	ESR (mΩmax/20%, 100k to300kHz)	Rated Ripple Current (mArms/ 105°C/100kHz)	Part No.
	22	0645	176	0.12	45	1,490	160AVEA220M0645
	47	0506	376	0.12	35	2,070	160AVEA470M0506
	47	0606	376	0.12	25	2,500	160AVEA470M0606
	68	0645	544	0.12	40	2,450	160AVEA680M0645
	68	0606	300	0.12	25	2,440	160AVEA680M0606
	82	0506	262	0.12	27	3,000	160AVEA820M0506
	82	0807	262	0.12	40	2,120	160AVEA820M0807
	100	0506	320	0.12	27	3,000	160AVEA101M0506
	100	0606	320	0.12	24	2,490	160AVEA101M0606
	120	0807	384	0.12	24	3,010	160AVEA121M0807
40	150	0807	500	0.12	22	3,220	160AVEA151M0807
16 (18.4)	150	1008	480	0.12	26	3,430	160AVEA151M1008
(10.4)	180	0606	576	0.12	22	3,300	160AVEA181M0606
	180	0608	1,440	0.12	16	3,300	160AVEA181M0608
	180	0610	576	0.12	16	3,500	160AVEA181M0610
	220	0608	704	0.12	22	3,300	160AVEA221M0608
	220	0810	704	0.12	18	3,890	160AVEA221M0810
	270	0610	864	0.12	16	3,500	160AVEA271M0610
	270	0807	864	0.12	22	3,300	160AVEA271M0807
	270	0810	864	0.12	16	4,070	160AVEA271M0810
	270	0812	864	0.12	16	4,070	160AVEA271M0812
	330	0810	1,056	0.12	22	3,150	160AVEA331M0810
	470	1012	1,504	0.12	10	6,100	160AVEA471M1012
	47	0807	188	0.12	45	1,890	200AVEA470M0807
20	56	0506	224	0.12	30	2,800	200AVEA560M0506
(23)	120	0606	480	0.12	25	3,200	200AVEA121M0606
	120	0810	480	0.12	22	3,320	200AVEA121M0810

TITLE: AP-CON AVEA SERIES S	NO.		MES00	3441	A0	
TENTE LA DONANTE A GEDNEG G	DECIPICATION:	DOCUMENT		MEGOO	2225	REV
DESIGNED BY:陳明宗	DRAWN BY: 施雅瑄	CHECKED BY:林軒逸 APPROVED BY:高良民			5良民	
DEVICES WITHOUT PERMISSION.	NAME OF THE PARTY		APAQ ID	CHNOLOGI CO., LI	ע	
AS THE BASIC FOR THE MANUFA	PAQ		ል DAO ጥር	CHNOLOGY CO., LT	T)	
TECHNOLOGY CO. LTD AND SHA	A	<i>y</i> = / 1 1	~/~~ //	77 17-24		
THIS DRAWINGS AND SPECIFICA		鈺邦科技	す股份	有限公司		

WV/Vdc (SV)	Cap (µF)	Size Code	Leakage Current (µA)	tanδ	ESR (mΩmax/20%, 100k to300kHz)	Rated Ripple Current (mArms/ 105°C/100kHz)	Part No.
	15	0645	300	0.12	55	1,650	250AVEA150M0645
25	22	0645	275	0.12	45	2,350	250AVEA220M0645
25 (28.8)	27	0506	338	0.12	40	2,450	250AVEA270M0506
(20.0)	27	0606	338	0.12	40	2,100	250AVEA270M0606
	47	0606	235	0.12	30	2,500	250AVEA470M0606

4. Construction and dimensions.

4.1 Construction

Vertical type capacitors shall be enclosed wound element, where anode and cathode foils with lead wire termination shall be winded together with separator, with conductive polymer electrolyte in a plastic coated aluminum case and sealed up tightly with rubber.




Fig. 1 Cross-section view


TITLE : AP-CON AVEA SERIES SPECIFICATION		NO.	MES	003227	A0
THE E . AD CON AVEA CEDIES S	DECIFICATION	DOCUMENT	MES	002227	REV
DESIGNED BY:陳明宗	DRAWN BY: 施雅瑄	CHECKED BY:林軒逸 APPROVED BY:高良民		高良民	
DEVICES WITHOUT PERMISSION.	MAG	APAQ .	ECHNOLOGY CO., LT	ע	
AS THE BASIC FOR THE MANUFA	PAQ	ADAO 7	ידיטוואסן ספע פס ניז	n .	
TECHNOLOGY CO. LTD AND SHA	A	<i>y</i> = // 1/ 1/ 1/ 1/ 1/ 1/ 1/ 1/ 1/ 1/ 1/ 1/	74 74 17-24 4		
THIS DRAWINGS AND SPECIFICAT		鈺邦科技股/	分有限 公司		

	Table 6 Construction					
	Compositions		Materials			
		Anode foil	Aluminum			
1	1 Element	Cathode foil	Aluminum			
ļ '		Separator	Synthetic fiber			
		Fixing tape	Adhesive tape			
2	Seal		Rubber			
3	Aluminum	ı tab	Aluminum			
4	Lead wire		Tinned Lead			
5	Case	·	Plastic coated aluminum			
6	Base plate		Resin			

4.2 Outer dimensions

Outer dimensions shall be in accordance with Fig. 2, and the dimensions in each size shall be specified on Table 7.

Fig. 2 Dimension



TITLE: AP-CON AVEA SERIES SPECIFICATION		NO.	MES00) 3227	A0
THE F A P CON AND A CEPTIC C	DE CHEK CATHON	DOCUMENT	MERCO	2225	REV
DESIGNED BY:陳明宗	DRAWN BY: 施雅瑄	CHECKED BY:林軒逸 APPROVED BY:高良民		高良民	
AS THE BASIC FOR THE MANUFACTURE OR SALE OF APPARATUS OR DEVICES WITHOUT PERMISSION.		X. IPAQ	APAQ TE	CHNOLOGY CO., LT	TD CT
TECHNOLOGY CO. LTD AND SHA	A	亚升· 们	7月16公司		
THIS DRAWINGS AND SPECIFICAT	TIONS ARE THE PROPERTY OF APAO	SAME.	鈺邦科技股份	·右限八司	

Table 7 Dimension									
Size	ϕ D±0.5max	L	α	Е	W±0.2	H±0.2	C±0.2	R	P±0.3
code	(mm)	(mm)	(mm)	(mm)	(mm)	(mm)	(mm)	(mm)	(mm)
0545	5	4.2	+0.4~-0.3	0.00~0.20	5.3	5.3	6	0.5~0.8	1.4
0506	5	5.8	0.2	0.00~0.20	5.3	5.3	6	0.5~0.8	1.4
0645	6.3	4.3	0.2	0.00~0.20	6.6	6.6	7.3	0.5~0.8	2.1
0606	6.3	5.8	0.2	0.00~0.20	6.6	6.6	7.3	0.5~0.8	2.1
0608	6.3	7.5	0.5	0.00~0.20	6.6	6.6	7.3	0.5~0.8	2.1
0610	6.3	9.7	0.3	0.00~0.20	6.6	6.6	7.3	0.6~0.9	2.1
0807	8	6.8	0.2	0.00~0.20	8.3	8.3	9	0.8~1.1	2.9
0810	8	9.7	0.3	0.00~0.20	8.3	8.3	9	0.8~1.1	2.9
0812	8	11.7	0.3	0.00~0.20	8.3	8.3	9	0.8~1.1	3.2
1008	10	7.5	0.5	0.00~0.20	10.3	10.3	11	0.8~1.1	4.6
1012	10	12.3	0.2	0.00~0.20	10.3	10.3	11	0.8~1.1	4.6

5. Marking

The following items shall be marked on each capacitor, as showed in Fig. 3.

- (1) Polarity
- (2) Series
- (3) Year code: U-2014,V-2015,W-2016,I-2017
- (4) Production period code
- (5) Manufacturer's identification mark
- (6) Rated capacitance
- (7) Rated voltage
- (8) The color of marking ink is red




Figure 3 Marking

TITLE : AP-CON AVEA SERIES SPECIFICATION		NO.	MII	ES00322	.,,	A 0
THE E . AD CON AVEA SEDIES S	DECIFICATION	DOCUMENT	M	EC00222	.7	REV
DESIGNED BY:陳明宗	DRAWN BY: 施雅瑄	CHECKED BY:林軒逸 APPROVED BY:高良民		良民		
DEVICES WITHOUT PERMISSION.	MAG	APAQ	LECHN	OLOGY CO., LTI	J	
AS THE BASIC FOR THE MANUFA	PAQ	ADAO	TECHN	וחו חביע ביח וידיו		
TECHNOLOGY CO. LTD AND SHA	A		C 1/4 /.	, ,,,,,,,		
THIS DRAWINGS AND SPECIFICAT		鈺邦科技服	分分布	1限公司		

6. Reflow soldering

Soldering condition (temperature and time) should be within the following ranges.




Figure 4 Reflow profile

Table 8 Recommended condition

Peak temperature (max)	260℃
220°C over time (max)	90sec
230°C over time (max)	60sec
Reflow number	Only 1 time

7. Soldering pad dimensions




Figure 5 Soldering pad
Table 9 Recommended pad dimensions

Size code	Α	b	С	
0545/0506	1.4	3	1.6	
0645/0606/	2.1	3.5	1.6	
0608/0610	2.1	3.3	1.0	
0807/0810/	2.8	4.2	1.9	
0812	2.0	4.2	1.9	
1008/1012	4.3	4.4	1.9	

THIS DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF APAQ TECHNOLOGY CO. LTD AND SHALL NOT BE REPRODUCT OR USED AS THE BASIC FOR THE MANUFACTURE OR SALE OF APPARATUS OR DEVICES WITHOUT PERMISSION.

DESIGNED BY: 陳明宗

DRAWN BY: 施雅瑄

CHECKED BY: 林軒逸

APPROVED BY: 高良民

TITLE: AP-CON AVEA SERIES SPECIFICATION

MES003227

A0

8. Taping packing and label marking

8.1 Carrier tape dimensions




Fig. 6 Carrier tape

Table 10 Carrier tape dimensions

Size	W±0.3	A±0.2	B±0.2	F±0.1	E±0.1	P±0.1	T±0.2	t ±0.05
code	(mm)							
0545	12	5.7	5.7	5.5	1.75	12	4.8	0.4
0506	12	5.7	5.7	5.5	1.75	12	6.2	0.4
0645	16	7	7	7.5	1.75	12	4.8	0.4
0606	16	7	7	7.5	1.75	12	6.3	0.4
0608	16	7	7	7.5	1.75	12	8.2	0.5
0610	16	7	7	7.5	1.75	12	10	0.5
0807	24	8.7	8.7	11.5	1.75	16	7.2	0.4
0810	24	8.7	8.7	11.5	1.75	16	10	0.5
0812	24	8.7	8.7	11.5	1.75	16	12	0.5
1008	24	10.7	10.7	11.5	1.75	16	8.2	0.5
1012	24	10.7	10.7	11.5	1.75	16	13	0.5

THIS DRAWINGS AND SPECIFICATECHNOLOGY CO. LTD AND SHA	A	鈺邦科.	技股份	有限公司			
AS THE BASIC FOR THE MANUFACTURE OR SALE OF APPARATUS OR DEVICES WITHOUT PERMISSION.		L. IPAQ		APAQ TE	CHNOLOGY CO., LT	Œ	
DESIGNED BY:陳明宗	DRAWN BY: 施雅瑄	CHECKED BY: 林軒逸 APPROVED BY: 高		良民			
		DOCUMENT	MES00322		2225	F	REV
TITLE: AP-CON AVEA SERIES SPECIFICATION		NO.		MESOU	13421	A	A 0

8.2 Reel dimensions




Fig. 7 Reel

Table 11 Reel dimensions

Size code	A ± 2	B ± 0.5	C±0.5	W±0.8	T±0.3				
Size code	(mm) (mm) (mm)		(mm)	(mm)	(mm)				
0545/0506	381	100	13	13.5	2.5				
0645/0606/	381	100	12	16.5	2.5				
0608/0610	301	100 13		100 10		100 10		10.5	2.5
0807/0810/	381	100	13	25.9	2.5				
0812	301	100	13	25.9	2.5				
1008/1012	381	100	13	25.9	2.5				

8.3 Taping method and polarity

Direction of feed




Fig. 8 Taping method and polarity

THIS DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF APAQ TECHNOLOGY CO. LTD AND SHALL NOT BE REPRODUCT OR USED	A	鈺邦科技股份	有限公司	
AS THE BASIC FOR THE MANUFACTURE OR SALE OF APPARATUS OR DEVICES WITHOUT PERMISSION.	X. PAQ	APAQ TE	CHNOLOGY CO., LT	D
DESIGNED BY: 陳明宗 DRAWN BY: 施雅瑄	CHECKED BY: 林軒逸 APPROVED BY: 高		5良民	
TITLE : AP-CON AVEA SERIES SPECIFICATION	DOCUMENT MES003227		2227	REV
IIILE - AF-CON AVEA SERIES SPECIFICATION	NO.	MESO	13441	A0

8.4 Label Marking

The label specified as follows shall be put on the side of reel.

- (1) Part No.
- (2) Quantity.
- (3) Lot No.

8.5 Package

The capacitors should be packed in the following quantities listed in Table 12

Table 12 Quantity of package

		or paoriago
Case size	1 Reel	1 Box
0545	1.5K pcs	9K pcs(6 reels)
0506	1.2K pcs	7.2K pcs(6 reels)
0645	1.5K pcs	9K pcs(6 reels)
0606	1.2k pcs	7.2K pcs(6 reels)
0608	900 pcs	5.4K pcs(6 reels)
0610	750 pcs	4.5K pcs(6 reels)
0807	750 pcs	3.75K pcs(5 reels)
0810	500 pcs	2.5K pcs(5 reels)
0812	400 pcs	2K pcs(5 reels)
1008	500 pcs	2.5K pcs(5 reels)
1012	400 pcs	2K pcs(5 reels)

THIS DRAWINGS AND SPECIFICATECHNOLOGY CO. LTD AND SHA	Δ	鈺邦科技	股份	有限公司		
AS THE BASIC FOR THE MANUFACTURE OR SALE OF APPARATUS OR DEVICES WITHOUT PERMISSION.		L. IPAQ	APA	AQ TE	CHNOLOGY CO., LT	D
DESIGNED BY:陳明宗	DRAWN BY: 施雅瑄	CHECKED BY: 林軒逸 APPROVED BY: 高		月身		
TITLE: AP-CON AVEA SERIES SPECIFICATION		DOCUMENT	MES002227		REV	
		NO. MES003227		3221	A0	

9. The electrical and mechanical performance and testing method

9.1 Measurement condition

Each measurement shall be conducted at a temperature of 15 to 35°C, and relative humidity of 45 to 85%. Furthermore, these measurements shall be preferably conducted at a temperature of 20±2°C, and relative humidity of 60 to 70%, while the capacitors shall be kept enough time in the measuring temperature.

9.2 Voltage treatment

If leakage current is doubtful, measure it after performing voltage treatment, which shall contain the following steps:

- (1) Applied DC rated voltage to the capacitors for 60 minutes at 105±2°C.
- (2) Cooled down to room temperature with applying voltage.
- (3) Discharged through a resistor of approximately $1\Omega/V$.

9.3 Electrical performance

9.3.1 Tolerance on rated capacitance

Rated capacitance shall meet within -20% to +20% (M) tolerance against the rated capacitance measured at 120Hz \pm 10% at 20 \pm 2 $^{\circ}$ C.

9.3.2 Leakage current

DC rated voltage shall be applied between anode and cathode lead wire terminations of a capacitor through $1k\Omega$ protective resistance, and the leakage current shall be less than or equal to the value listed in table 5 after 2 minutes with the voltage reaching the rated value at $20\pm2^{\circ}C$.

If the value is doubtful, measure the leakage current after performing voltage treatment as described in section 6.2.

9.3.3 Tangent of loss angle ($tan\delta$)

Tan δ values shall be less than or equal to 0.12 measured at 120Hz±10% at 20±2°C.

9.3.4 Equivalent Series Resistance (ESR)

ESR at 100kHz measured under the following conditions listed in Table 13 shall be less than or equal to the value in Table 5.

TITLE: AP-CON AVEA SERIES SPECIFICATION		DOCUMENT NO.		MES00	3227	A0
						REV
DESIGNED BY:陳明宗	DRAWN BY: 施雅瑄	CHECKED BY: 林軒逸 APPROVE		APPROVED BY:高	5良民	
DEVICES WITHOUT PERMISSION.		MAG		APAQ IE	CHNOLOGI CO., LI	ע
AS THE BASIC FOR THE MANUFACTURE OR SALE OF APPARATUS OR		PAQ		ADAO TE	CHNOLOGY CO., LT	n
TECHNOLOGY CO. LTD AND SHALL NOT BE REPRODUCT OR USED		A	<i>y</i> = // // \	12/VC 1/4	77 11-24	
THIS DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF APAQ			鈺邦科	技股份	有限公司	

Table 13 Measurement requirement of ESR

	·
Equipment	Agilent Technology 4263B or equivalent
Test Fixture	Agilent Technology 16047E or equivalent
Compensation	Short and Open compensation would be required.
	Short correction is performed using the shorting
	plate made of 0.5 thickness copper plate with gold
	coating.
Signal Level	500mV
Frequency	100kHz
Measurement Point	Point of lead wire within 1mm form the body

9.3.5 Impedance at high and low temperature

Impedance at 100kHz at -55±3°C or 105±2°C shall meet the values listed in Table 14.

Table 14 Impedance at low or high temperature

Impedance ratio	Performance
Z(-55°C)/Z(+20°C)	≤ 1.25
Z(105°C)/Z(+20°C)	≤ 1.25

9.4 Mechanical performance

9.4.1 Adhesion by soldering

A force of 5N shall be applied for 10 seconds to the capacitor, which was mounted on a print circuit board, in the perpendicular direction to the seal side of the capacitor. After this test, the soldered terminals shall not be damaged.

9.4.2 Vibration

Vibration cycle should vary from 10 to 55Hz with total amplitude of 1.5mm and return to 10Hz in about 1 minute. Vibration applied to a capacitor should be three directions, which each perpendicular to the other two as longitudinal axis of capacitor set as z axis, and last for 2 hours in each direction. During this test, measured electrical value shall be stabilized when that capacitor is measured 5 times within 30 minutes before completion of test, and the appearance shall not appear any remarkable abnormality. Capacitance change shall be within $\pm 10\%$ of the initial measured value.

9.4.3 Solder ability

The lead surface shall be immersed for 2 ± 0.5 seconds in the flux of ethanol or isopropyl alcohol solution ($25\pm2\%$) of colophonium. Then that lead surface shall be immersed to a solder (H60A, H60S or H63A) of $235\pm5^{\circ}$ C and up to the point 1.5 to 2.0mm from the body and kept for 2 ± 0.5 seconds, and pulling it out. After this test, solder shall cover at least 3/4 of the lead surface immersed.

	TIONS ARE THE PROPERTY OF APAQ LL NOT BE REPRODUCT OR USED	A	鈺邦科技股份	介有限公司	
AS THE BASIC FOR THE MANUFACTURE OR SALE OF APPARATUS OR DEVICES WITHOUT PERMISSION.		L. IPAQ	APAQ TE	CHNOLOGY CO., LT	D
DESIGNED BY:陳明宗	DRAWN BY: 施雅瑄	CHECKED BY:林軒逸 APPROVED BY:高良		5良民	
TWO E A A D GOV AVELA GERVEG GREGIVICATION		DOCUMENT	MES003227		REV
TITLE: AP-CON AVEA SERIES SPECIFICATION		NO.	MESOC)322 <i>1</i>	A0

9.4.4 Soldering heat

After the capacitors are soldered by the recommended soldering conditions below, the tests of the item Humidity resistance and Load life shall be conducted. After this test, the capacitors shall satisfy their test criteria.

9.5 Environmental performance

9.5.1 Damp heat, steady state

A capacitor shall be subjected to a temperature of $60\pm2^{\circ}$ C and relative humidity of 90 to 95% without voltage applied for a period of 1000+48/-0 hours. Then that capacitor shall be taken out from the above condition to a temperature of 20°C and it shall meet the characteristics in Table 15.

Table 15 Damp heat performance

Characteristics	Performance
Appearance	No significant damage
Capacitance change	≤ ±20% of the initial value
tanδ	≤ 150% of the initial specified value
ESR	≤ 150% of the initial specified value
Leakage current	≤ the initial specified value

9.5.2 Endurance

A capacitor shall be subjected to a temperature of $105\pm2^{\circ}$ C with test voltage applied for a period of 2,000+72/-0 hours and take out from the above condition to a temperature of 20° C. After this test, that capacitor shall meet the characteristics in Table 16.

Besides, the applied voltage shall increase up from 0V to test voltage step by step (maximum 5 minutes), and the impedance of the source shall be equal to about 3Ω /V.

Table 16 Endurance performance

Characteristics	Performance
Appearance	No significant damage
Capacitance change	≤ ±20% of the initial value
tanδ	≤ 150% of the initial specified value
ESR	≤ 150% of the initial specified value
Leakage current	≤ the initial specified value


THIS DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF APAQ TECHNOLOGY CO. LTD AND SHALL NOT BE REPRODUCT OR USED	A	鈺邦科技股份	有限公司	
AS THE BASIC FOR THE MANUFACTURE OR SALE OF APPARATUS OR DEVICES WITHOUT PERMISSION.	X. PAQ	APAQ TE	CHNOLOGY CO., LT	D
DESIGNED BY: 陳明宗 DRAWN BY: 施雅瑄	CHECKED BY: 林軒逸 APPROVED BY: 高		5良民	
TITLE : AP-CON AVEA SERIES SPECIFICATION	DOCUMENT MES003227		2227	REV
IIILE - AF-CON AVEA SERIES SPECIFICATION	NO.	MESO	13441	A0

9.5.3 Surge voltage

The following specifications in Table 17 shall be satisfied when the capacitors are restored to $+20^{\circ}$ C after the surge voltage is applied at a cycle of 360 seconds which consists charge for 30 ± 5 seconds through a protective resistor of $1\text{k}\Omega$ and discharge for 330 seconds, for 1000 cycles at $105\pm2^{\circ}$ C.

Table 17 Surge voltage performance

	0 0 1
Characteristics	Performance
Appearance	No significant damage
Capacitance change	≤ ±20% of the initial value
tanδ	≤ 150% of the initial specified value
ESR	≤ 150% of the initial specified value
Leakage current	≤ the initial specified value



R1: Protective resistor 1kΩ

R2 Discharging resistor 1kΩ

Cx :Capacitor under test

Fig. 9 Surge voltage circuit

10. Instructions of Capacitors

10.1 Cautions on use of Capacitor

10.1.1 Polarity

Solid electrolytic capacitors are polarized capacitors. Use capacitors after verifying their positive and negative polarities. If these capacitors are installed in the reverse polarity, its life may shorten because of increasing leakage current or short circuit.

- 10.1.2 Types of circuits in which capacitors are prohibited from being used AVEA series may be heated by soldering to increase in its leakage current slightly. This may have some influence on the characteristics capacitors in the following circuits.
 - (1) Time constant circuit
 - (2) Coupling circuit
 - (3) High impedance voltage holding circuit
 - (4) Connection of two or more capacitors in series for higher withstand voltage.

THIS DRAWINGS AND SPECIFICATECHNOLOGY CO. LTD AND SHA	A	鈺邦科	技股份	有限公司			
AS THE BASIC FOR THE MANUFACTURE OR SALE OF APPARATUS OR DEVICES WITHOUT PERMISSION.		L. IPAQ	APAQ TECHNOLOGY CO., LT		ď		
DESIGNED BY:陳明宗	DRAWN BY: 施雅瑄	CHECKED BY: 林軒逸 APPROVED BY: 高良		高良民			
THEY E . AD CON AVEA SERVES SPECIFICATION		DOCUMENT		MEGOO	2227	REV	V
TITLE: AP-CON AVEA SERIES SPECIFICATION		NO.		MES00	13421	A0	

10.1.3 Over voltage

If AVEA series is applied a voltage higher than the rated voltage for an instantaneous period, it may be defected due to short circuit. Note that the voltage over the rated voltage must not be applied to capacitors.

10.1.4 Repeat of rapid charging and discharging

If AVEA series is used in a rapid charging and discharging circuit or receive the flow of excess rush current, its life may shorten by large leakage current or short circuit. The charging and discharging current through AVEA series should be less than 10A.

10.1.5 Reflow soldering

High soldering temperature and long soldering time will affect the characteristics of the capacitors. Use reflow soldering condition within the recommended range. Also, the temperature varies with the location and population of the components, the material and the thickness of printed circuit board. Verify temperature profiles prior to actual production run.

10.1.6 Use of capacitors for industrial equipment

When capacitors are used for industrial equipment, the circuits should be designed to have sufficient margins in the ratings of capacitors including capacitance and impedance. Without sufficient margins in the characteristics, the reliability of the capacitors may be reduced by their shorter life. Always contact us if you want to use capacitors for equipment affecting human lives such as space, aviation, atomic power, and medical devices. Never use capacitors for the used without our prior approval.

10.2 Notes on circuit designs for capacitors

10.2.1 Rating and performance

Use capacitors within the rating and performance ranges defined in the brochures and delivery specification of capacitors after checking the operating and installation environments.

10.2.2 Operating temperature

If AVEA series is used at a temperature higher than the upper specified temperature (105°C), its life may be remarkably shortened or the leakage current may increase to cause defective.

TITLE: AP-CON AVEA SERIES SPECIFICATION		DOCUMENT MES003227		3227	A0	
						REV
DESIGNED BY:陳明宗	DRAWN BY: 施雅瑄	CHECKED BY: 林軒逸 APPROVED BY		APPROVED BY:高	另身	
DEVICES WITHOUT PERMISSION.		MAG	APAQ TECHNOLOGY CO., LTD		ע	
AS THE BASIC FOR THE MANUFACTURE OR SALE OF APPARATUS OR		PAQ	ADAO TECHNOLOGY CO LT		n	
TECHNOLOGY CO. LTD AND SHALL NOT BE REPRODUCT OR USED		A	<i>y</i> = <i>y</i> 1 1	X/VC / V	77 11-24	
THIS DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF APAQ		鈺邦科技股份有限公司				

10.2.3 Ripple current

Never make current larger than the rated ripple current through AVEA series. If excess ripple current flows through AVEA series, internal heat may be generated largely to make its life shortened or cause it to be defected due to short circuit.

10.2.4 Leakage current

Depending on the reflow soldering conditions, the leakage current of AVEA series may increase slightly. The application of DC voltage enables the capacitors to be repaired by itself. This leads the leakage current to be smaller gradually. The leakage current can be reduced fast if the DC voltage, which is less than the rating voltage, is applied at the temperature close to the upper specified temperature.

10.2.5 Applied voltage

Do not apply voltages exceeding the full rated voltage. If such voltage is applied, it may cause short circuit even though it is just a moment.

- (1) Sum of DC voltage and the peak of ripple voltage AC voltage shall not exceed the rated voltage or category voltage.
- (2) The sum of the DC voltage plus the negative peak AC voltage shall not allow reverse voltage.
- (3) Do not apply reverse voltage.
- (4) For 25V products, the applied voltage shall follow the following figure as the temperature is higher than 85 $^{\circ}$ C $^{\circ}$

10.2.6 Failure mode

AVEA series contains a conductive polymer as material of cathode electrode. Therefore, like other solid electrolyte capacitors, the life ends mostly due to random failure mode, mainly short circuit. If a current continuously flow through the capacitor due to short circuit, the capacitor would be overheated higher than 300 °C and then aluminum case of the capacitor would be removed by increasing internal pressure due to the vaporization of materials.

10.2.7 Insulation

- (1) Plastic coated case of capacitors is not secured to insulate. Do not use capacitors in areas requiring insulation.
- (2) Isolate the case of AVEA series from the positive and negative terminals and adjacent circuit patterns.

	TIONS ARE THE PROPERTY OF APAQ LL NOT BE REPRODUCT OR USED	A	鈺邦科技股份	分有限公司	
AS THE BASIC FOR THE MANUFACTURE OR SALE OF APPARATUS OR DEVICES WITHOUT PERMISSION.		Y. IPAQ	APAQ TECHNOLOGY CO., LT		'D
DESIGNED BY:陳明宗	DRAWN BY: 施雅瑄	CHECKED BY: 林軒逸 APPROVED BY: 高良		長民	
THE E A D CON AVEA SERVES SPECIFICATION		DOCUMENT	MEGO	02227	REV
TITLE: AP-CON AVEA SERIES SPECIFICATION		NO.	MES003227		A0

10.2.8 Design of printed circuit board

Take note on the subjects when capacitors are installed on printed circuit boards:

- (1) For surface mount capacitors, design the copper pads/lands of a printed circuit board according to the catalog or product specifications.
- (2) Do not place heating components on boards to be close to capacitors or in the backside of them.

10.2.9 Parallel connection

If AVEA series is connected with another type of a capacitor in parallel, larger ripple current may flow through one of capacitors. Take the current balance among them into account in circuit designs.

10.2.10 Using temperature and frequency

The electric characteristics of capacitors depend on the variations of the ambient temperature and frequency. Check the variations in designing circuits.

10.3 Notes on installation of capacitors

10.3.1 Notes on pre-installation of capacitors

- (1) Do not reuse capacitors installed in a unit with the power supply turned on for another unit. No used capacitors shall be reused excluding those removed to measure their electric characteristics in periodical inspection.
- (2) If AVEA series stored for a long period may often increase in its leakage current, connect a resistor of approximately $1k\Omega$ to the capacitors for voltage treatment.

10.3.2 Notes at installation of capacitors

- (1) Install capacitors in a unit after confirming that their ratings (rated capacitance and rated voltages) meet the conditions of the unit.
- (2) Install capacitors in the correct polarities.
- (3) Take care not to drop capacitors on floors. Do not use capacitors dropped on floors.
- (4) Do not deform capacitors to install them in units.
- (5) Note capacitors may be damaged by mechanical shocks caused by the vacuum head, component checker or centering operation of an automatic mounting machine.
- (6) Do not dip the body of a capacitor into the solder bath.
- (7) Do not solder capacitors more than once by reflow. Consult us for reflow-soldering them twice over.
- (8) Do not apply mechanical stress to the capacitor after soldering to the printed circuit board.
- (9) Do not use adhesives and coating materials containing halogenated solvents.

	TIONS ARE THE PROPERTY OF APAQ LL NOT BE REPRODUCT OR USED	A	鈺邦科技股份	介有限公司	
AS THE BASIC FOR THE MANUFACTURE OR SALE OF APPARATUS OR DEVICES WITHOUT PERMISSION.		L. IPAQ	APAQ TECHNOLOGY CO., LT		D
DESIGNED BY:陳明宗	DRAWN BY: 施雅瑄	CHECKED BY: 林軒逸 APPROVED BY: 高良		5良民	
THE LAD CON AVEA SERVES SPECIFICATION		DOCUMENT	MEGO	2227	REV
TITLE: AP-CON AVEA SERIES SPECIFICATION		NO.	MES00)322 <i>1</i>	A0

10.4 Notes on use of capacitors in unit

- (1) Never make your fingers contact with the capacitor terminals.
- (2) Do not make capacitor terminals to be in contact with each other through a conductor. Do not put conductive liquid such as acid and alkali solutions on capacitors.
- (3) Confirm that the unit including capacitors is placed in proper conditions. Do not place the unit in the following areas:
 - (a) Area in which they are directly exposed to water, brine, or oil or in condensation status.
 - (b) Area filled with poisonous gases including hydrogen sulfide, sulfurous acid, nitrous acid, chlorine and ammonia.
 - (c) Area to which ultraviolet and/or radial rays are radiated
- (4) Provide aging for a unit containing capacitors within the period defined for them.
- (5) It is recommended to use a unit containing capacitors in the normal temperature range of 15°C to 35°C and the normal humidity range of 75% or less.

10.5 Action at emergency

- (1) At the occurrence of short circuit in AVEA series, some heat is generated from it if the short-current rather small. If the short current exceeds the above value, the capacitors are heated excessively. If so, turn off the power of the unit without your face and hands being close to the capacitors.
- (2) If you should expose your eyes to smoke from the capacitor or inhale it, immediately flush the open eyes and gargle with water.

10.6 Storage

- (1) Store capacitors in an area in the temperature range between 15 °C to 35 °C and the relative humidity of 75% or less without direct sunshine. In addition, store them in the package states if possible.
- (2)SMD products are sealed in a special laminated aluminum bag. Use all capacitors once the bag is opened. Return unused capacitors to the bag, and seal it with a zipper.

 After the bag is opened, please use all capacitors within 6 month.
- (3) Store capacitors in an airtight bag to keep the terminals in good condition.
- (4)Store in a location where the capacitor is not exposed to ozone, ultraviolet radiation, or other radiation.
- (5)Never store capacitors in any area in which they are directly exposed to water, brine, or oil or in condensation status.

THIS DRAWINGS AND SPECIFICATECHNOLOGY CO. LTD AND SHA	♀				
AS THE BASIC FOR THE MANUFACTURE OR SALE OF APPARATUS OR DEVICES WITHOUT PERMISSION.		L. IPAQ	APAQ TECHNOLOGY CO., LT		D
DESIGNED BY:陳明宗	DRAWN BY: 施雅瑄	CHECKED BY: 林軒逸 APPROVED BY: 高		良民	
TITLE: AP-CON AVEA SERIES SPECIFICATION		DOCUMENT	MES003227		REV
		NO.			A0

10.7 Exhaustion of capacitors

Capacitors are composed of organic compounds, resins and metals. Request an industrial dispose company to dispose of used Capacitors.

11. Export trade control ordinance

Item 41-4 in Section 2 of Appendix Table 1 (Section 49 in Chapter 1 of MITI's Ordinance) and Item 7 in Section 7 of Appendix Table 1 (Section 6 in Chapter 6 of MITI's Ordinance) state export regulations on pulse use capacitors (750V of higher) and high voltage use capacitors (5,000V or higher).

However, aluminum electrolytic capacitors are less than 750V in their voltage range, so that the regulations do not apply to the aluminum electrolytic capacitors.

TITLE : AP-CON AVEA SERIES SPECIFICATION		NO.	MES00	3227	A0
		DOCUMENT			REV
DESIGNED BY:陳明宗	DRAWN BY: 施雅瑄	CHECKED BY:林軒逸 APPROVED BY:高良			長民
AS THE BASIC FOR THE MANUFACTURE OR SALE OF APPARATUS OR DEVICES WITHOUT PERMISSION.		X. PAQ	APAQ TECHNOLOGY CO., LTI		D
TECHNOLOGY CO. LTD AND SHA	A	鈺邦科技股份	有限公司		
THIS DRAWINGS AND SPECIFICAT	ΓΙΟΝS ARE THE PROPERTY OF APAQ		红机纸牡肥化	*右阻八司	