

# Low Noise, Low Power Precision Voltage Reference

#### **Features**

• Low noise (0.1 Hz to 10 Hz): 2.5 ppm\_peak-peak

• Low temperature coefficient: 5 ppm/°C max

• Initial accuracy: ± 0.05 % max

Quiescent current: 130 μA
 Shutdown current: 3 μA

Supply voltage: Vout + 0.3 V to 5.5 V

Line regulation: 10 ppm/V max

• Load regulation: 10 ppm/mA max

Small package: SOT23-6

• Temperature range: - 40 °C to +125 °C

ZJR1001 has noise filter option

Pin compatible with industry standard products

Fully AEC-Q100 qualified

## **Applications**


- Industrial control
- Precision data acquisition
- Optical Communication
- Precision instrument
- Smart grid
- Medical equipment
- Portable Devices

### **General Description**

The ZJR1001 and ZJR1002 offer a low noise, low power and low-drift voltage reference in a small 6-pin SOT23 package. They are suitable for data acquisition applications with high resolution (14-bit or more), such as precision instruments and test equipment. Because of the low dropout feature, ZJR1001 and ZJR1002's input voltage can start from 300 mV higher than the output voltage, which can simplify the system power supply design. The supply current is just 130  $\mu\text{A}$ , making them suitable for portable devices while maintaining high performances. By optimized design and proprietary trimming, ZJR1001 and ZJR1002 achieve the temperature coefficient within 5 ppm/°C and initial accuracy within  $\pm 0.05$  %. This simplifies or even allows the user to skip system calibration for most applications. ZJR1001 offers noise filter option for wideband applications, and ZJR1002 can enable the output in Kelvin connection.

The ZJR1001 and ZJR1002 are available in a 6-lead SOT23 package and are specified over the extended industrial temperature range of - 40 °C to +125 °C.

## **Typical Application**



ZJR1001/ZJR1002

## **Table of contents**

Features	1
Applications	1
General Description	1
Typical Application	1
Table of contents	2
Version (Release B )	3
Revision History	3
Pin Configurations and Function Descriptions	4
Absolute Maximum Ratings	5
Thermal Resistance	5
Specifications	6
Typical Performance Characteristics	7
Terminology	11
Temperature Coefficient	11
Long-term Stability	11
Thermal Hysteresis	11
Line Regulation	11
Load Regulation	11
Theory of Operation	12

Applications	13
ZJR1001, ZJR1002 Basic Connections	13
Power on and Shutdown Mode	13
Supply Voltage	14
Noise Performance	14
Power Dissipation	14
Product Applications	15
Voltage Reference Noise to ADC Resolution	15
Using ZJR1002 and ZJC2542 to Build up to 18	-bit Signa
Sources	15
Layout Guidelines	17
Layout Example	17
Outline Dimensions	19
Ordering Guide	20
Orderable Device Explanation	20
Related Device	21

**Data Sheet** 

# Version (Release B) 1

**Revision History** 

January 2024 —— Release B

Add AEC-Q100 qualification

May 2023 — Release A

<sup>1</sup> Information furnished by ZJW Microelectronics is believed to be accurate and reliable. However, no responsibility is assumed by ZJW Microelectronics for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of ZJW Microelectronics. Trademarks and registered trademarks are the property of their respective owners.

# **Pin Configurations and Function Descriptions**




Figure 1. ZJR1001 Pin Configuration (6-lead SOT23)

Mnemonic	Pin No.	Description		
FILTER	Filter Input. Connect a 0.1 capacitor from FILTER to grout to provide high-frequency bypast Leave unconnected, if not used			
GND	2	Ground		
ENABLE	Enable. Drive high to enable device. Drive low to disable device.			
IN	4	Supply voltage input		
OUTS	5	Voltage Reference Sense Output		
OUTF	6	Voltage Reference Force Output. Short OUTF to OUTS as close as possible to the load. Bypass OUTF with a capacitor (0.1 µF to 10 µF) to GND.		




Figure 2. ZJR1002 Pin Configuration (6-lead SOT23)

Mnemonic	Pin No.	Description		
GNDF	1	Ground Force		
GNDS	2	Ground Sense. Connect to ground connection at the load.		
ENABLE	3	Enable. Drive high to enable the device. Drive low to disable the device.		
IN	4	Supply voltage input		
OUTS	5	Voltage Reference Sense Output		
OUTF	6	Voltage Reference Force Output. Short OUTF to OUTS as close as possible to the load. Bypass OUTF with a capacitor (0.1 µF to 10 µF) to GND.		

## **Absolute Maximum Ratings 1**

Parameter	Rating
Input Voltage	- 0.2 V to 6 V
Output Short-Circuit Current to GND	± 30 mA
Operating Temperature Range	- 40 °C to +125 °C
Storage Temperature Range	- 65 °C to +150 °C
Junction Temperature Range	- 65 °C to +150 °C
Maximum Reflow Temperature <sup>2</sup>	260 °C
Lead Temperature (Soldering, 10 sec)	300 °C
Electrostatic Discharge (ESD) 1	
Human Body Model (HBM) <sup>2</sup>	8 kV
Charging Device Model (CDM) <sup>3</sup>	1 kV

### Thermal Resistance 6

Package Type	θ <sub>JA</sub>	θЈС	Unit
SOT23	230	76	°C/W

These ratings apply at 25 °C, unless otherwise noted. Stresses above these ratings may cause permanent damage. Exposure to absolute maximum conditions for extended periods may degrade device reliability. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those specified is not implied.

<sup>&</sup>lt;sup>2</sup> IPC/JEDECJ-STD-020 Compliant.

<sup>&</sup>lt;sup>1</sup> Charged devices and circuit boards can discharge without detection.

Although this product features patented or proprietary protection circuitry, damage may occur on devices subjected to high energy ESD. Therefore, proper ESD precautions should be taken to avoid performance degradation or loss of functionality.

<sup>&</sup>lt;sup>2</sup> ANSI/ESDA/JEDEC JS-001 Compliant.

<sup>&</sup>lt;sup>3</sup> ANSI / ESDA /JEDEC JS-002 Compliant

 $<sup>^{\</sup>rm 6}~\theta_{\text{JA}}$  addresses the conditions for soldering devices onto circuit boards to achieve surface mount packaging.

# Specifications <sup>1</sup>

The " $\bullet$ " denotes the specification which apply over the full specified temperature range, unless otherwise specified, VIN = V<sub>OUT</sub>+0.3 V, I<sub>LOAD</sub> = 0, C<sub>L</sub> = 0.1  $\mu$ F, T<sub>A</sub> = 25 °C.

Parameter	Symbol	Conditions/Package		Min	Тур	Max	Unit
		ZJR1001/1002-9			2.5		V
0 ( ) () ()		ZJR1001/1002-3			3		V
Output Voltage	V <sub>OUT</sub>	ZJR1001/1002-4			4.096		V
		ZJR1001/1002-5			5		V
Initial Accuracy				- 0.05		+ 0.05	%
Temperature Coefficient	TCV <sub>OUT</sub>						
B Grade A Grade			•			5 8	ppm / °C ppm / °C
Voltage Noise	e <sub>n</sub> p-p	0.1 Hz to 10 Hz			2.5		ppm_peak-to-peak
		ZJR1001-9, C <sub>FILTER</sub> =0.1 μF, f = 1 kHz			60		nV/√Hz
		Z JR1002-9, f=1 kHz			200		nV/√Hz
		ZJR1001-3, C <sub>FILTER</sub> =0.1 μF, f = 1 kHz			92		nV/√Hz
Valtage Naise Density		ZJR1002-3, f=1 kHz			250		nV/√Hz
Voltage Noise Density	en	ZJR1001-4, C <sub>FILTER</sub> = 0.1 μF, f = 1 kHz			85		nV/√Hz
		ZJR1002-4, f = 1 kHz			320		nV/√Hz
		ZJR1001-5, C <sub>FILTER</sub> = 0.1 μF, f = 1 kHz			108		nV/√Hz
		ZJR1002-5, f = 1 kHz			308		nV/√Hz
Line Regulation			•		2 5	10	ppm/V ppm/V
Load Regulation		-10 mA <i<sub>LOAD&lt;10 mA</i<sub>			1.5	10	ppm/mA
			•		6		ppm/mA
Supply Voltage		I <sub>LOAD</sub> = 5 mA, output voltage error < 0.1 %		V <sub>OUT</sub> + 0.3		5.5	V
Supply Current	ΙQ		•		130		μΑ
Shutdown Current			•		3		μΑ
Dropout Voltage		$I_{LOAD} = 0$	•		5		mV
		I <sub>LOAD</sub> = 5mA	•		50		mV
Enable Pin (ENABLE)		Input Current	•	- 1		1	μΑ
		Logic High Voltage	•	2			V
		Logic Low Voltage	•			8.0	V
Short-Circuit Current	IL	V <sub>OUT</sub> = GND/VIN		16	20		mA
Ripple Rejection Ratio		Frequency = 60 Hz			- 95		dB
Turn-on Settling Time		Stable to 0.1 %, C <sub>L</sub> = 0.1 µF			220		μs
Long-Term Stability		1000 hours, SOT23-6			TBD		ppm / 1000 hours
Temperature Range		Specified Temperature Range		- 40		125	°C
		Operating Temperature Range		- 55		125	°C

<sup>&</sup>lt;sup>1</sup> Each parameter is explained in the terminology section of this data sheet.

## **Typical Performance Characteristics**

Unless otherwise stated, VIN =  $V_{OUT}$  + 0.3 V,  $I_{LOAD}$  = 0,  $C_L$  = 0.1  $\mu$ F,  $T_A$  = 25 °C.




Figure 3. ZJR1002-9 Typical Output Voltage vs. Temperature




Figure 4. ZJR1002-3 Typical Output Voltage vs. Temperature




Figure 5. ZJR1002-4 Typical Output Voltage vs. Temperature




Figure 6. ZJR1002-5 Typical Output Voltage vs. Temperature




Figure 7. ZJR1002-9 Supply Current vs. Input Voltage







Figure 8. ZJR1002-9 Shutdown Current vs. Input Voltage







### **Terminology**

### **Temperature Coefficient**

The change of output voltage over the operating temperature range is normalized by the output voltage at 25 °C, and expressed in ppm/°C as

$$dV_{OUT}/dT = \frac{V_{OUT}(max) - V_{OUT}(min)}{V_{OUT}(25) \times (T2 - T1)} \times 10^{6}$$

Where:

V<sub>OUT</sub> (25): Output voltage at 25 °C.

V<sub>OUT</sub> (min): The lowest output voltage over temperature T1 to T2 range.

 $V_{\text{OUT}}$  (max): The highest output voltage over temperature range T1 to T2.

For ZJW Micro voltage references, temperature T1 is - 40  $^{\circ}$ C, and T2 is + 125  $^{\circ}$ C.

### **Long-term Stability**

This is the measurement of the change in output voltage of the measured device at 25 °C after 1000 hours (approximately 42 days) of operation at a constant ambient temperature. Generally measured in ppm. Long-term stability is not only affected by variations in the device itself, but also by soldering and board materials. Long-term stability generally exhibits a logarithmic characteristic, therefore the change in the second 1000 hours will be much smaller than the change in the first 1000 hours.

LTD = 
$$\frac{V_{OUT}(t0) - V_{OUT}(t1)}{V_{OUT}(t0)} \times 10^6$$

where:

V<sub>OUT</sub> (t0): Output voltage at 25 °C at Time 0.

V<sub>OUT</sub> (t1): Output voltage at 25 °C at Time 1 after 1000 hours of operation under constant ambient temperature.

#### **Thermal Hysteresis**

The change of output voltage after the device is cycled through temperatures from + 25 °C to - 40 °C to + 125 °C and back to +25 °C. This is a typical value from a sample of parts put through such a cycle. It is normally in ppm using the following equation:

TH = 
$$\frac{V_{OUT}(25) - V_{OUT}(TC)}{V_{OUT}(25)} \times 10^6$$

where:

V<sub>OUT</sub> (25): Output voltage at 25 °C.

V<sub>OUT</sub> (TC): Output voltage at 25 °C after the temperature cycle.

### **Line Regulation**

The change in output voltage due to a specified change in input voltage. It includes the effects of self-heating. Line regulation is expressed in either percent per volt, parts per million per volt, or microvolts per volt change in input voltage, such as ppm/V.

#### **Load Regulation**

The change in output voltage due to a specified change in load current. It includes the effects of self-heating. Load regulation is expressed in either microvolts per milliampere or parts per million per milliampere, such as ppm/mA.

### **Theory of Operation**

ZJR1001, ZJR1002 series of precision voltage reference products is based on state-of-the-art CMOS technology, Figure 22 & Figure 23 shows ZJR1001 & ZJR1002's internal blocks respectively. The bandgap reference is the core, which has been carefully designed and can deliver the key performances by proprietary post-package trimming. All pins have the internal protection circuit in order to make ZJR1001 & ZJR1002 reliable parts, and their ESD level reaches 8 kV HBM.




Figure 22. Simplified Schematic of ZJR1001




Figure 23. Simplified Schematic of ZJR1002

### **Applications**

#### **ZJR1001, ZJR1002 Basic Connections**

Voltage references, including ZJR1001 & ZJR1002, normally require a capacitor at the output between OUTF and GND. Figure 24 is the basic connection of ZJR1001/2. Other than a 0.1 µF capacitor at the output, no further component is needed for normal operation. To reduce noise further, an additional capacitor can be connected to the FILTER pin of ZJR1001.

However, in actual system, the power supply may change rapidly. Adding a 1  $\mu$ F to 10  $\mu$ F capacitor at the input can help the performances of the voltage reference. An additional 0.1  $\mu$ F capacitor in parallel can reduce power supply noise further.

The output capacitance ranges from  $0.1 \mu F$  to  $10 \mu F$ . Too big capacitive load can cause output oscillation. Capacitor equivalent series resistance (ESR) within  $1.5 \Omega$  is recommended to ensure its stability. Meanwhile, larger output capacitor results in longer turn-on time.

Capacitance value depends on the load of the voltage reference, source or sink current et al. New SAR ADC, such as ZJC2000, requires its voltage reference can source and sink current.

It is recommended to use surface-mounted ceramic capacitors (such as X5R, X7R). If an electrolytic capacitor is used at the output, a 0.1 µF ceramic capacitor should be placed in parallel to reduce the overall ESR at the output. In addition, the capacitors' operating temperature range should be wider, or at least the same as the system's temperature range.




Figure 24. ZJR1001 /2 Basic Connections

#### **Power on and Shutdown Mode**

Figure 15 shows the turn-on process of ZJR1002 and ZJR1001 has the similar turn-on process. The value of the load capacitance affects the turn-on time. In general, the larger the load capacitance, the longer the settling time. Settling to higher accuracy sees exponentially longer turn-on time.

For power sensitive high precision applications, ZJR1001 and ZJR1002 have shutdown mode, which has the supply current of 3  $\mu$ A cross the specified temperature range. Drive pin 3 (ENABLE) low, the part will enter shutdown mode & high will be in normal operation as can be found in Figure 17. Leave pin 3 unconnected (there is a weak internal pull-up circuit) or connect to IN, ZJR1001 or ZJR1002 will be in normal operation.

### **Supply Voltage**

The supply voltage of ZJR1001 and ZJR1002 ranges from 300 mV higher than the output voltage to 5.5 V. It is recommended to power ZJR1001 & ZJR1002 by linear power supplies, such as LDO, in order to get high performances.

#### **Noise Performance**

ZJR1001 and ZJR1002 have very low output noise. The noise of ZJR1002-9 is typically within 2.5 ppm\_peak-to-peak over the 0.1 Hz to 10 Hz band. The noise measurement is made with a band-pass filter made of a high-pass filter with a corner frequency at 0.1 Hz and a low-pass filter with a corner frequency at 10 Hz.

Connect an external capacitor to pin 1 of ZJR1001 (FILTER) can further reduce its noise. By adding a 0.1  $\mu$ F capacitor, ZJR1001-9's noise at 1 kHz dropped from 200 nV/ $\sqrt{\text{Hz}}$  without capacitor to 60 nV/ $\sqrt{\text{Hz}}$ . If the noise reduction is not needed, leave pin 1 unconnected.

### **Power Dissipation**

ZJR1001 and ZJR1002 are low power dissipation devices with a typical supply current of 130 μA. In case of heavy load, it is necessary to calculate the power dissipation of the device, and take into account the performance changes caused by it. The temperature of the device increases according to the equation below.

$$T_J = P_D \times \theta_{JA} + T_A$$

where:

 $T_J$  = Junction temperature (°C)

 $T_A$  = Ambient temperature (°C)

P<sub>D</sub> = Power dissipated (W)

 $\theta_{JA}$  = Junction-to-ambient thermal resistance (°C/W)

The junction temperature of ZJR1001 and ZJR1002 must not exceed the absolute maximum rating of 150 °C.

### **Product Applications**

### **Voltage Reference Noise to ADC Resolution**

In general, the voltage reference's 0.1 Hz to 10 Hz noise should be within ADC's 1/2 LSB. With the same resolution, the larger the full-scale voltage, the lower the noise requirement to the voltage reference as can be found in Table 1. ZJR1001 and ZJR1002 are able to be used as 16-bit ADC voltage reference.

Decolution (bit)	0.1 Hz to 10 Hz Noise (μV <sub>P-P</sub> )				
Resolution (bit)	2.5 V full scale	5 V full scale			
8	4,882.8	9,765.6			
10	1,220.7	2,441.4			
12	305.2	610.4			
14	76.3	152.6			
16	19.1	38.1			
18	4.8	9.5			

Table 1. ADC Resolution vs. Voltage Reference Noise

### Using ZJR1002 and ZJC2542 to Build up to 18-bit Signal Sources

It is a great challenge to generate a programmable high-precision signal source with more than 16-bit accuracy. The high-performance voltage reference is required to ensure the noise and temperature performances of both voltage and current output signals. Also, for some systems, the performances over time (also known as time drift) are required. Based on ZJW Micro's complete high-performance signal chain products, the reference design is developed as shown in Figure 25. It can achieve up to 18-bit accuracy if ZJC2542-18 will be used together with ZJR1002. The Kelvin connection of ZJR1002 and the Kelvin connection requirement of 18-bit precision digital-to-analog converter (DAC) ZJC2542 matches well to improve the system's resistance to load changes and easy implementation. ZJR1002's low noise and temperature drift within 5ppm/ °C are critical to ensure the performance of the whole design.




Figure 25. ZJR1002 and ZJC2542 build 18-bit programmable signal source

### **Layout Guidelines**

- Place the power-supply bypass capacitor as closely as possible to the supply and ground pins. The recommended value of this
  bypass capacitor is from 1 μF to 10 μF. If necessary, additional decoupling capacitance can be added to compensate for noisy
  or high-impedance power supplies.
- The output must be decoupled with a bigger than 0.1  $\mu$ F capacitor. For better noise performance, the recommended ESR on the output capacitor is from 1  $\Omega$  to 1.5  $\Omega$ . For even lower noise, a larger capacitor in parallel or an RC filter can be added.
- Use large area ground plane if possible. Keep fast-changing or high-frequency interference signals far from ZJR1001 or ZJR1002.

### **Layout Example**




Figure 26. ZJR1001 Evaluation Board Schematic




Figure 27. ZJR1001 Evaluation Board Layout (Top Layer)




Figure 28. ZJR1001 Evaluation Board Layout (Bottom Layer)

## **Outline Dimensions**





Figure 29. 6-Lead SOT23 Package Dimensions shown in millimeters

## **Ordering Guide**

Model	Orderable Device	Package	Output Voltage (V)	Max TempCo (ppm/°C)	Mark	External Package
7.104004.0	ZJR1001-9BUTBR	SOT23-6	2.5	5	1001-9	7" reel
ZJR1001-9	ZJR1001-9AUTBR	SOT23-6	2.5	8	1001-9	7" reel
ZJR1001-3	ZJR1001-3BUTBR	SOT23-6	3	5	1001-3	7" reel
ZJK 1001-3	ZJR1001-3AUTBR	SOT23-6	<u>ئ</u>	8	1001-3	7" reel
ZJR1001-4	ZJR1001-4 BUTBR	SOT23-6	4.096	5	1001-4	7" reel
ZJR 1001-4	ZJR1001-4 AUTBR	SOT23-6	4.090	8	1001-4	7" reel
ZJR1001-5	ZJR1001-5 BUTBR	SOT23-6	5	5	1001-5	7" reel
ZJK 1001-5	ZJR1001-5 AUTBR	SOT23-6	5	8	1001-5	7" reel
ZJR1002-9	ZJR1002-9BUTBR	SOT23-6	2.5	5	1002-9	7" reel
	ZJR1002-9AUTBR	SOT23-6		8	1002-9	7" reel
	ZJR1002-9AUTARQ1	SOT23-6		8	1002Q9	7" reel
	ZJR1002-3BUTBR	SOT23-6		5	1002-3	7" reel
ZJR1002-3	ZJR1002-3AUTBR	SOT23-6	3	8	1002-3	7" reel
	ZJR1002-3AUTARQ1	SOT23-6		8	1002Q3	7" reel
	ZJR1002-4BUTBR	SOT23-6		5	1002-4	7" reel
ZJR1002-4	ZJR1002-4AUTBR	SOT23-6	4.096	8	1002-4	7" reel
	ZJR1002-4AUTARQ1	SOT23-6		8	1002Q4	7" reel
	ZJR1002-5BUTBR	SOT23-6	5	5	1002-5	7" reel
ZJR1002-5	ZJR1002 -5AUTBR	SOT23-6		8	1002-5	7" reel
	ZJR1002-5AUTARQ1	SOT23-6		8	1002Q5	7" reel

# **Orderable Device Explanation**



Q1: Automotive Grade

External Package: T = tube; R = reel

Temperature range: A = -40 °C to 125 °C Automotive Grade 1; B = -40 °C to 125 °C;

E = - 40 °C to 85 °C

Number of Pins: T = 6, A = 8; B = 10; D = 14; E = 16; P = 20;

Package type: S = SOIC; U = MSOP, TSSOP, SOT; T = DFN, QFN

Grade: B grade is better than A grade (Default)

Base: R = Voltage reference; A = Amplifier; C = Data Converter; G = Switches and Multiplexers

## **Related Device**

Part Number	Description	Comments			
ADC					
ZJC2000/2010	18-bit 400 kSPS/200 kSPS SAR ADC	Fully differential input, SINAD 99.3 dB, THD - 113 dB			
ZJC2001/2011	16-bit 500 kSPS/250 kSPS SAR ADC	Fully differential input, SINAD 95.3 dB, THD - 113 dB			
ZJC2002/2012	40.4400.40.00.40.40.40.40.40.40.40.40.40.40.4	Pseudo-differential unipolar input, SINAD 91.7 dB, THD - 105 dB			
ZJC2003/2013	16-bit 500 kSPS/250 kSPS SAR ADC	Pseudo-differential bipolar input, SINAD 91.7 dB, THD - 105 dB			
ZJC2004/2014	40 17 400 1000 1000 1000 040 400	Pseudo-differential unipolar input, SINAD 94.2 dB, THD - 105 dB			
ZJC2005/2015	18-bit 400 kSPS/200 kSPS SAR ADC	Pseudo-differential bipolar input, SINAD 94.2 dB, THD - 105 dB			
ZJC2007/2017	44 hit coo long/200 long can and	Pseudo-differential unipolar input, SINAD 85 dB, THD - 105 dB			
ZJC2008/2018	14-bit 600 kSPS/300 kSPS SAR ADC	Pseudo-differential bipolar input, SINAD 85 dB, THD - 105 dB			
ZJC2100/1-18	18-bit 400 kSPS/200 kSPS 4-ch differential SAR A	DC, SINAD 99.3 dB, THD - 113 dB			
ZJC2100/1-16	16-bit 500 kSPS/250 kSPS 4-ch differential SAR A	DC, SINAD 95.3 dB, THD - 113 dB			
ZJC2102/3-18	18-bit 400 kSPS/200 kSPS 8-ch pseudo-differentia	al SAR ADC, SINAD 94.2 dB, THD - 105 dB			
ZJC2102/3-16	16-bit 500 kSPS/250 kSPS 8-ch pseudo-differentia	al SAR ADC, SINAD 91.7 dB, THD - 105 dB			
ZJC2102/3-14	14-bit 600 kSPS/300 kSPS 8-ch pseudo-differentia	al SAR ADC, SINAD 85 dB, THD - 105 dB			
ZJC2104/5-18	18-bit 400 kSPS/200 kSPS 4-ch pseudo-differentia	al SAR ADC, SINAD 94.2 dB, THD - 105 dB			
ZJC2104/5-16	16-bit 500 kSPS/250 kSPS 4-ch pseudo-differentia	al SAR ADC, SINAD 91.7 dB, THD - 105 dB			
DAC					
ZJC2541-18/16/14	18/16/14-bit 1 MSPS single channel DAC	Power on reset to 0 V (ZJC2541) or V <sub>REF</sub> /2 (ZJC2543), 1 nV-S glitch,			
ZJC2543-18/16/14	with unipolar output	SOIC-8/MSOP-10/DFN-10 packages			
ZJC2542-18/16/14	18/16/14-bit 1 MSPS single channel DAC	Power on reset to 0 V (ZJC2542) or V <sub>REF</sub> /2 (ZJC2544), 1 nV-S glitch,			
ZJC2544-18/16/14	with bipolar output	SOIC-14/TSSOP-16/QFN-16 packages			
Amplifier					
ZJA3000-1/2/4	Single/Dual/Quad 36 V low bias current	3 MHz GBW, 35 μV max Vos, 0.5 μV/°C max Vos drift, 25 pA max Ibias,			
	precision Op Amps	1 mA/Amplifier, input to V-, RRO, 4.5 V to 36 V			
ZJA3001-1/2/4	Single/Dual/Quad 36 V low bias current	3 MHz GBW, 35 μV max Vos, 0.5 μV/°C max Vos drift, 25 pA max Ibias,			
	precision Op Amps	1 mA/Amplifier, RRO, 4.5 V to 36 V			
ZJA3512-2/4	Dual/Quad 36 V 7 MHz precision JFET Op Amps	7 MHz GBW, 35 V/ $\mu$ S SR, 50 $\mu$ V max Vos, 1 $\mu$ V/°C max Vos drift, 2 mA/Amplifier, RRO, 4.5V to 35 V			
ZJA3600/1	36 V ultra-high precision in-amp	CMRR 105 dB min (G = 1), 25 pA max lbias, 25 $\mu$ V max Vosi, gain error 0.001 % max (G = 1), 625 kHz BW (G = 10), 3.3 mA/Amplifier, $\pm$ 2.4 V to			
		± 18 V, - 40 °C to 125 °C specified			
ZJA3622/8	36 V low cost precision in-amp	CMRR 93 dB min (G = 10), 0.5 nA max Ibias, 125 $\mu$ V max Vosi, 625 kHz BW (G = 10), 3.3 mA/Amplifier, $\pm$ 2.4 V to $\pm$ 18 V			
ZJA3611, ZJA3609	36 V ultra-high precision wider bandwidth precision in-amp (min gain of 10)	CMRR 120 dB min (G = 10), 25 pA max Ibias, 25 $\mu$ V max Vosi, 1.2 MHz BW (G = 10), 3.3 mA/Amplifier, $\pm$ 2.4 V to $\pm$ 18 V, $-$ 40 °C to 125 °C specified			
ZJA3676/7	Low power, G = 1 Single/Dual 36 V difference amplifier	Input protection to ± 65 V, CMRR 104 dB min, Vos 100 μV max, gain error 15 ppm max, 500 kHz BW, 330 μA, 2.7 to 36 V			
Voltage Reference	• •				
Totago Hororono		V <sub>OUT</sub> = 1.25/2.048/2.5/3/4.096/5 V, 5 ppm/°C max drift - 40 °C to 125 °C,			
ZJR1000	15 V supply precision voltage reference	± 0.05 % initial error			
ZJR1001	5.5V low power voltage reference	V <sub>OUT</sub> = 2.5/3/4.096/5 V, 5 ppm/°C max drift - 40 °C to 125 °C, ± 0.05 % initial			
ZJR1002	(ZJR1001 with noise filter option)	error, 130 µA, ZJR1001/2 in SOT23-6, ZJR1003 in SOIC/MS-8			
ZJR1003	03				
Switches and Mul	tiplexers 				
ZJG4438/4439	36V fault protection 8:1/dual 4:1 multiplexer	Protection to $\pm$ 50 V power on & off, latch-up immune, Ron 270 $\Omega$ , 14.8 pC charge injection, to 166 nS, 10 V to 36 V			