



# **Specification**

Part No.	:	FS.700.A.10WW111
Product Name	:	I-Bar Response FirstNet Band 14 Adhesive Mount Antenna
Features	:	FirstNet Band 14 Ready 3M Adhesive Cable: 1 metre TGC-200 Connector: SMA(M) Straight RoHS Compliant







# **1. Introduction**

The Response FS.700 FirstNet Wideband I-Bar Antenna is an external adhesive mount solution on glass and plastic for automotive and telematics applications. It covers not only FirstNet, but all Cellular, ISM and Wi-Fi working frequencies in the 700-6000 MHz spectrum. It has the highest wide-band efficiency in its range of any antenna in its category today.

FirstNet is a dedicated communications tool for First Responders in the US. It is an isolated network to provide faster critical information and data-sharing between First Responders and their agencies. New FirstNet devices are being deployed to allow for the multitude of services and applications which will be using the network for the following mission critical applications:

- Computer-aided dispatch (vehicle location)
- EMS Electronic Patient Care Reporting
- Vehicle Mounted RMS/ Citations/ Scanners
- Video Streaming

The FS.700 has been primarily designed for use with FirstNet modules, routers and devices that require the highest possible efficiency and peak gain to deliver best in class throughput on the FirstNet Band 14 for Public Safety applications.

It comes with 1 meter of coaxial cable and SMA (M) connector, in a low profile compact format for mounting via high quality first tier automotive approved 3M adhesive foam. Stable radiation is observed on both glass and plastic.

The FS.700 is backward compatible with all FirstNet applications and can be used in other required bands.





It is an ideal solution for any device requiring high, reliable performance. It will meet nearly all carrier certification requirements from an efficiency standpoint. The antenna also makes an excellent reference antenna for test purposes. It has been designed as an omni-directional antenna and the radiation patterns show this and are stable across all bands.

Cable and connectors are customizable, contact your regional Taoglas sales office for customization and additional support.





# 2. Specification

					ELECTRIC	CAL				
Standar	<sup>.</sup> d	LTE/GSM/ CDMA 700/800/ 850/900	GNSS	LTE/GSM/ HSPA/CDM A 1700/1800 / 1900	UMTS/ HSPA 2100	LTE 2300	Wi-Fi 2400	LTE 2600	LTE 3500	Wi-Fi 5800
Frequency (	(MHz)	698~960	1565 ~1612	1710 ~1990	1920 ~2170	2305 ~2360	2400 ~2500	2500 ~2700	3400 ~3600	4800~600 0
					Efficiency	(%)				
	30cm	71.88	62.03	67.62	67.81		68.79	71.08		48.73
	1M	68.64	56.57	61.77	62.39		62.74	64.83		43.43
In free	2M	63.75	51.59	55.33	56.02		54.64	55.89		36.76
space	3M	59.34	45.98	48.75	49.59		47.06	47.47		30.75
	5M	50.54	36.53	37.87	39.04		36.10	36.30		22.34
	30cm	74.99	64.23	70.69	70.33		69.68	73.11		49.39
On the 2mm	1M	71.62	58.58	64.58	64.68		63.55	66.67		44.02
ABS Base	2M	66.53	53.42	57.85	58.07		55.35	57.49		37.25
ADD Dase	3M	61.93	47.61	50.97	51.41		47.67	48.82		31.16
	5M	52.78	37.82	39.60	40.45		36.57	37.33		22.63
	30cm	74.73	73.00	80.37	77.79		64.27	69.10		55.18
On the	1M	71.86	66.58	73.41	71.51		58.62	63.02		49.18
Glass Base	2M	67.23	60.72	65.79	64.21		51.05	54.33		41.44
0.000 2000	3M	64.50	54.12	57.94	56.81		43.97	46.14		34.81
	5M	55.06	42.99	45.03	44.67		33.73	35.28		24.97
					verage Gai	n(dBi)				
	30cm	-1.46	-2.08	-1.72	-1.71		-1.63	-1.49		-3.22
In free	1M	-1.66	-2.48	-2.12	-2.07		-2.03	-1.89		-3.72
space	2M	-1.98	-2.88	-2.59	-2.54		-2.63	-2.53		-4.45
	3M	-2.29	-3.38	-3.14	-3.07		-3.28	-3.24		-5.22
	5M	-2.99	-4.38	-4.23	-4.11		-4.43	-4.41		-6.62
	30cm	-1.29	-1.93	-1.52	-1.55		-1.57	-1.37		-3.13
On the 2mm	1M	-1.49	-2.33	-1.92	-1.91		-1.97	-1.77		-3.63
ABS Base	2M	-1.81	-2.73	-2.39	-2.38		-2.57	-2.41		-4.37
1.00 0000	3M	-2.12	-3.23	-2.94	-2.91		-3.22	-3.12		-5.13
	5M	-2.82	-4.23	-4.04	-3.95		-4.37	-4.28		-6.53
	30cm	-1.33	-1.37	-0.96	-1.11		-1.92	-1.62		-2.62
On the Glass	1M	-1.50	-1.77	-1.35	-1.47		-2.32	-2.02		-3.12
Base	2M	-1.80	-2.17	-1.83	-1.94		-2.92	-2.66		-3.87
Dase	3M	-2.02	-2.67	-2.38	-2.47		-3.57	-3.37		-4.62
	5M	-2.72	-3.67	-3.47	-3.51		-4.72	-4.53		-6.07





					Peak Gai	n(dBi)						
Standar	d	LTE/GS M/CDMA 700/800 / 850/900	GNSS	LTE/GSM/H SPA/CDMA 1700/1800 / 1900	UMTS/ HSPA 2100	LTE 2300	Wi-Fi 2400	LTE 2600	LTE 3500	Wi-Fi 5800		
Frequency (	MHz)	698~96 0	1565~1612	1710~1990	1920~2170	2305 ~2360	2400~2500	2500~2700	3400 ~3600	4800~6000		
	30cm	1.56	1.38	3.79	3.06		4.25	4.70		2.56		
In free	1M	1.36	0.98	3.40	2.69		3.85	4.30		2.06		
space	2M	1.04	0.58	2.92	2.23		3.25	3.66		1.33		
space	3M	0.73	0.08	2.37	1.70		2.60	2.95		0.56		
	5M	0.03	-0.92	1.28	0.66		1.45	1.79		-0.84		
	30cm	1.65	1.74	3.85	3.13		5.00	5.27		2.08		
On the	1M	1.45	1.34	3.46	2.76		4.60	4.87		1.58		
2mm ABS	2M	1.13	0.94	2.99	2.30		4.00	4.23		0.84		
Base	3M	0.81	0.44	2.44	1.77		3.35	3.52		0.08		
	5M	0.11	-0.56	1.34	0.73		2.20	2.35		-1.32		
	30cm	1.52	3.20	4.76	4.12		5.75	5.35		4.14		
	1M	1.32	2.80	4.37	3.76		5.35	4.95		3.64		
On the Glass Base	2M	0.99	2.40	3.89	3.29		4.75	4.31		2.89		
Glass Dase	3M	0.68	1.90	3.34	2.76		4.10	3.60		2.14		
	5M	-0.02	0.90	2.25	1.72		2.95	2.44		0.69		
	Impe	dance					50Ω					
	Polari	zation		Linear								
Ra	diatio	n Patterr	า	Omni								
]	Input	Power					5 W					
					MECHAN	NICAL						
	Cas	sing		ABS								
C	Coaxia	l Cable		TGC-200 Low Loss Cable								
C	Cable	Length		1 Meter Standard, Fully Customizable								
	Conn	ector		SMA Male Standard, Fully Customizable								
Wa	ter Pr	oof Leve	el	IP65								
	Adhesive			3M9448+CR4305 Double Sided Adhesive								
	We	ight		127g								
					ENVIRONN	<b>JENTAL</b>						
Operation	Temp	erature	Range			-4	0°C to 85°0	2				
-			_	-40°C to 85°C								
Storage Temperature Range Humidity				Non-condensing 65°C 95% RH								

SPE-18-8-075/A/TH Page 5 of 30





LTE BANDS							
Band Number	LTE / LTE-Advanc	ed / WCDMA / HSPA / HSPA+ / TD	-SCDMA				
	Uplink	Downlink	Covered				
1	UL: 1920 to 1980	DL: 2110 to 2170	$\checkmark$				
2	UL: 1850 to 1910	DL: 1930 to 1990	$\checkmark$				
3	UL: 1710 to 1785	DL: 1805 to 1880	$\checkmark$				
4	UL: 1710 to 1755	DL: 2110 to 2155	$\checkmark$				
5	UL: 824 to 849	DL: 869 to 894	$\checkmark$				
7	UL: 2500 to 2570	DL:2620 to 2690	$\checkmark$				
8	UL: 880 to 915	DL: 925 to 960	$\checkmark$				
9	UL: 1749.9 to 1784.9	DL: 1844.9 to 1879.9	$\checkmark$				
11	UL: 1427.9 to 1447.9	DL: 1475.9 to 1495.9	×				
12	UL: 699 to 716	DL: 729 to 746	$\checkmark$				
13	UL: 777 to 787	DL: 746 to 756	$\checkmark$				
14	UL: 788 to 798	DL: 758 to 768	$\checkmark$				
17	UL: 704 to 716	DL: 734 to 746 (LTE only)	$\checkmark$				
18	UL: 815 to 830	DL: 860 to 875 (LET only)	$\checkmark$				
19	UL: 830 to 845	DL: 875 to 890	$\checkmark$				
20	UL: 832 to 862	DL: 791 to 821	$\checkmark$				
21	UL: 1447.9 to 1462.9	DL: 1495.9 to 1510.9	×				
22	UL: 3410 to 3490	DL: 3510 to 3590	×				
23	UL:2000 to 2020	DL: 2180 to 2200 (LTE only)	$\checkmark$				
24	UL:1625.5 to 1660.5	DL: 1525 to 1559 (LTE only)	$\checkmark$				
25	UL: 1850 to 1915	DL: 1930 to 1995	$\checkmark$				
26	UL: 814 to 849	DL: 859 to 894	$\checkmark$				
27	UL: 807 to 824	DL: 852 to 869 (LTE only)	✓				
28	UL: 703 to 748	DL: 758 to 803 (LTE only)	$\checkmark$				
29	UL: -	DL: 717 to 728 (LTE only)	$\checkmark$				
30	UL: 2305 to 2315	DL: 2350 to 2360 (LTE only)	$\checkmark$				
31	UL: 452.5 to 457.5	DL: 462.5 to 467.5 (LTE	×				
32	UL: -	DL: 1452 - 1496	×				
35	1850 t	to 1910	$\checkmark$				
38	2570 t	to 2620	$\checkmark$				
39	1880 t	to 1920	✓				
40	2300 t	to 2400	$\checkmark$				
41	2496 1	to 2690	✓				
42	3400 t	to 3600	$\checkmark$				
43	3600 t	to 3800	×				

\*Covered bands represent an efficiency greater than 20%






# 3. Antenna Characteristics

### 3.1 Testing setup



In free space



On 2mm ABS Base



On Glass Base

Figure.1 Test setup; a) In free space, b) On 2mm ABS Base, c) On the Glass Base





### 3.2 Return loss




Figure2. Return loss of FS.700 with 1 meter cable length in free space




Figure3. Return loss of FS.700 with 1 meter cable length on the 2mm ABS base









Figure4. Return loss of FS.700 with 1 meter cable length on the glass base




### **3.3 Efficiency**

SPE-18-8-075/A/TH Page 9 of 30










Figure7. Efficiency of FS.700 with 1 meter cable length on the glass base.

#### SPE-18-8-075/A/TH Page 10 of 30





### 3.4 Peak gain





Figure8. Peak gain of FS.700 with 1 meter cable length in free space











Figure10. Peak gain of FS.700 with 1 meter cable length on the glass base



### 3.5 Average gain

Figure11. Average gain of FS.700 with 1 meter cable length in free space

#### SPE-18-8-075/A/TH Page 12 of 30








Figure12. Average gain of FS.700 with 1 meter cable length on the 2mm ABS base




Figure13. Average gain of FS.700 with 1 meter cable length on the glass base

SPE-18-8-075/A/TH Page 13 of 30






# 4. Antenna Radiation Patterns

The antenna radiation patterns were measured in ETS Anechoic Chamber. The measurement setup as below,



In free space

On 2mm ABS base




On glass baseFigure.14The measurement setup; a) In free space, b) On the 2mm ABS base, c) On the glass base






## 4.1 1 Meter Cable in Free Space



#### SPE-18-8-075/A/TH Page 15 of 30








#### SPE-18-8-075/A/TH Page 16 of 30



## 4.2 1 Meter Cable Length on 2mm ABS Base

**FIRST**NET. Built with AT&T

180



#### SPE-18-8-075/A/TH Page 17 of 30

180

(dBi)

\*FirstNet® and related logos are trademarks of the U.S. Department of Commerce, First Responder Network Authority. AT&T® is a registered trademark of AT&T Intellectual Property, LLC. Neither the U.S. Department of Commerce nor AT&T have authorized, approved, or endorsed Taoglas or the identified Taoglas products.


180

(dBi)



180





#### SPE-18-8-075/A/TH Page 18 of 30

180


\*FirstNet® and related logos are trademarks of the U.S. Department of Commerce, First Responder Network Authority. AT&T® is a registered trademark of AT&T Intellectual Property, LLC. Neither the U.S. Department of Commerce nor AT&T have authorized, approved, or endorsed Taoglas or the identified Taoglas products.

180



## 4.3 1 Meter Cable Length on Glass Base

FIRSTNET<sub>™</sub> Built with AT&T



#### SPE-18-8-075/A/TH Page 19 of 30

180

—2170MHz

(dB)

\*FirstNet® and related logos are trademarks of the U.S. Department of Commerce, First Responder Network Authority. AT&T® is a registered trademark of AT&T Intellectual Property, LLC. Neither the U.S. Department of Commerce nor AT&T have authorized, approved, or endorsed Taoglas or the identified Taoglas products.

180

-2170MHz

(dB)


-2170MHz

(dB)

180








#### SPE-18-8-075/A/TH Page 20 of 30





# **5** Drawing

Front View



3M	3M	SN	SN	SN	SN	SN	3NJ	314	
		SN							
-		3M		•		13400	•	3M	)
3M	3M	3N	SN	3M	3NJ	SN	3NJ	314	

	Name	Material	Finish	QTY
1	Housing Top GSA8841	ABS	Black	1
2	Housing Bottom GSA8841	ABS	Black	1
3	Double Sided Adhesive With Foam(Black Foam)	3M9448HK+CR4305	White Liner	1
4	Heat Shrink Tube	PE	Black	1
5	TGC200 Coaxial Cable	PE.	Black	1
6	SMA(M)ST	Brass	Au Plated	1

#### SPE-18-8-075/A/TH Page 21 of 30






# 6 Packaging

1pc FS.700.A.10WW111 per PE bag Bag Dimensions - 300\*100mm Weight - 127g

5pcs FS.700.A.10WW111 per Small Bag Small Bag Dimensions - 450\*280mm Weight - 0.635Kg

50pcs FS.700.A.10WW111 per carton Carton Dimensions - 330\*260\*240 mm Weight - 6.5Kg




#### SPE-18-8-075/A/TH Page 22 of 30





# **7** Application Note

The FS.700 antenna measurement with difference cable length and difference environments, the performance is shown as below,




## 7.1 Return Loss (in free space)

Figure 15. Measured the return loss of FS.700 Antenna with difference cable length








### 7.2 Efficiency (In free space)

Figure 16. Measured the efficiency of FS.700 Antenna with difference cable length




## 7.3 Average Gain (In free space)

Figure 17. Measured the Average Gain of FS.700 Antenna with difference cable length








### 7.4 Peak Gain (In free space)

Figure 18. Measured the Peak Gain of FS.700 Antenna with difference cable length




## 7.5 Return loss (On the 2mm ABS base)

Figure 19. Measured the return loss of FS.700 Antenna with difference cable length







## 7.6 Efficiency (On the 2mm ABS base)

### 7.7 Average Gain (On the 2mm ABS base)





Figure 21. Measured the Average Gain of FS.700 Antenna with difference cable length

SPE-18-8-075/A/TH Page 26 of 30








### 7.8 Peak Gain (On the 2mm ABS base)

Figure 22. Measured the Peak Gain of FS.700 Antenna with difference cable length




# 7.9 Return loss (On the glass base)

Figure 23. Measured the return loss of FS.700 Antenna with difference cable length








### 7.10Efficiency (On the glass base)

Figure 24. Measured the efficiency of FS.700 Antenna with difference cable length




## 7.11Average Gain (On the glass base)

Figure 25. Measured the Average Gain of FS.700 Antenna with difference cable length







## 7.12Peak Gain (On the glass base)

Figure 26. Measured the Peak Gain of FS.700 Antenna with difference cable length





Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein.

Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

Copyright © Taoglas Ltd.