

# I<sup>2</sup>C/3-Wire Real-Time Clock / Calendar with EEPROM

## **Feature**

- Real-Time Clock (RTC) / Calendar functions
  - Includes: Sec, Minutes, Hours, Day, Date, Month, and year in BCD format
- Clock operating voltage: 2.0V~5.5V
- Supply voltage  $V_{DD}$ =2.7V $\sim$ 5.5V
- Automatic leap year correction, valid until year 2099
- · Automatic supply switch over
- Integrated oscillator load capacitors C<sub>L</sub>=12.5pF
- · Clock compensation
- Programmable alarm and interrupt function
- 15 selectable frequency outputs
- 4 Bytes EEPROM for user
- Serial commutation via I<sup>2</sup>C or 3-wire interface
- 8-pin SOP package for I<sup>2</sup>C interface
- 10-pin MSOP package for 3-wire interface

## **Applications**

- · Utility meters
- Consumer electronics
- · Portable equipment
- · Wireless equipment
- · POS equipment
- · Computer products
- Other industrial/Medical/Automotive applications


## **General Description**

The HT1382 is a low power real time clock device with two serial interface: I<sup>2</sup>C or 3-wire. The interface mode is selected by the chosen chip version. The device provides both clock and calendar information in BCD format and also includes alarm functions. The calendar is accurate until the year 2099 and includes automatic leap year correction.

An external 32768Hz crystal is used as the device oscillator for device timing for which is provided an integrated crystal load capacitance of 12.5pF. The device includes a crystal oscillator temperature compensation function and internal power control circuitry detects power failures and automatically switches to the battery supply when a power failure occurs.



# **Block Diagram**



Note: IFS pin is used for selecting I<sup>2</sup>C interface or 3-wire interface.

I<sup>2</sup>C interface is selected when IFS is unconnected.


3-wire interface is selected when IFS is connected to VSS.

# **Pin Assignment**





# **Pad Assignment**



Chip size:  $1245 \times 1520 \; (\mu m)^2$ 

# **Pad Coordinates**

Unit: mm

Pad No.	Х	Y
1	-520.005	-161.460
2	-520.005	-256.460
3	-520.005	-360.130
4	-520.005	-455.130
5	-520.005	-550.130

Pad No.	X	Y
6	-520.005	-646.610
7	521.000	-625.000
8	521.000	-530.000
9	521.000	-425.300
10	516.450	-288.400


# **Pin Description**

Pin Name	I/O	Description
X1	I	32768Hz crystal input pin
X2	0	32768Hz crystal output pin
VBAT	_	Battery power supply
CE	I	Not used for I <sup>2</sup> C interface Chip Enable for 3-Wire interface
IFS	I	Interface selection pin.  I <sup>2</sup> C interface is selected when IFS is unconnected, 3-wire interface is selected when IFS is connected to VSS.
VSS	_	Negative power supply, ground
SDA/I/O	I/O	Serial Data Input/Output for I <sup>2</sup> C and 3wire interfaces
SCL/SCLK	I/O	Serial Clock input for I <sup>2</sup> C and 3-wire interfaces
IRQ/FOUT	0	Interrupt/Frequency Output, this pin is open drain output
VDD	_	Positive power supply

<sup>\*</sup> The IC substrate should be connected to VSS in the PCB layout artwork.



## **Approximate Internal Connections**



# **Absolute Maximum Ratings**

Supply Voltage	$V_{SS}$ -0.3V to $V_{SS}$ +6.0V
Input Voltage	$V_{SS}$ -0.3V to $V_{DD}$ +0.3V
Storage Temperature	-60°C to 150°C
Operating Temperature	40°C to 85°C

Note: These are stress ratings only. Stresses exceeding the range specified under "Absolute Maximum Ratings" may cause substantial damage to the device. Functional operation of this device at other conditions beyond those listed in the specification is not implied and prolonged exposure to extreme conditions may affect device reliability.

## D.C. Characteristics

Ta=-40°C~85°C

Symbol	Bonomoton		Test Conditions	Min	T	Mary	Unit
	Parameter	V <sub>DD</sub>	Conditions	Min.	Тур.	Max.	Unit
$V_{DD}$	Supply Voltage	_	_	2.7	_	5.5	V
V <sub>BAT</sub>	Battery Supply Voltage		_	2.0	_	5.5	V
I <sub>STB</sub>	Standby Current	_	V <sub>BAT</sub> =3V, "CH"=1	_	_	0.1	μA
I <sub>BAT</sub>	Battery Supply Current	_	V <sub>BAT</sub> =3V, "CH"=0	_	0.8	1.2	μA
I <sub>DD1</sub>	Constitution of the second sec	3V	SCL/SCLK=0Hz,	_	5	15	
	Supply Current (Low Power Mode)	5V	"LPM"=1	_	15	30	μA



Courselle and	Downworton		Test Conditions	NA:	Torre	Mari	I I m i 6
Symbol	Parameter	<b>V</b> <sub>DD</sub>	Conditions	Min.	Тур.	Max.	Unit
	Supply Current	3V	SCL/SCLK=0Hz,	_	50	100	^
I <sub>DD2</sub>	Supply Current	5V	"LPM"=0	_	70	150	μA
	Supply Current with 12C Active	3V	SCLK=400kHz	_	80	150	
I <sub>DD3</sub>	Supply Current with I <sup>2</sup> C Active	5V	30LN-400KHZ	_	150	300	μA
	Supply Current with 2 wire Active	3V	SCLK=1MHz	_	100	200	
I <sub>DD4</sub>	Supply Current with 3-wire Active	5V	SCLK=2MHz	_	300	500	μA
V <sub>IH</sub>	"H" Input Voltage		_	0.7V <sub>DD</sub>	_	_	V
VIL	"L" Input Voltage	_	_	_	_	0.3V <sub>DD</sub>	V
.,	I/O High Lavel Output Valtage	3V	I <sub>ОН1</sub> =-1.5mA	2.7	_	_	V
V <sub>он</sub>	I/O High Level Output Voltage	5V	I <sub>OH1</sub> =-3.0mA	4.5	_	_	V
V <sub>OL1</sub>	I/O, SCL and SDA Low Level	3V	I <sub>OL1</sub> =3.0mA	0	_	0.4	V
VOL1	Output Voltage	5V	I <sub>OL1</sub> =6.0mA	0	_	0.4	V
V	IDO Love Love Cutaut Voltage	3V	I <sub>OL2</sub> =1.5mA	0	_	0.4	V
V <sub>OL2</sub>	IRQ Low Level Output Voltage	5V	I <sub>OL2</sub> =3.0mA	0	_	0.4	V
.,	V <sub>BAT</sub> Mode Compared Voltage	_	_	2.40	2.55	2.70	V
V <sub>COMP</sub>	Hysteresis		_	_	25	_	mV
V <sub>BATHYS</sub>	V <sub>BAT</sub> Hysteresis	_			40		mV

## A.C. Characteristics

## **Power-Down Timing**

V<sub>DD</sub>=2.7V~5.5V, Ta=-40°C~85°C

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
t <sub>FSR</sub>	VDD Falling Slew Rate	_	_	_	10	V/ms

Note: In order to ensure proper time keeping, the  $t_{\mbox{\scriptsize FSR}}$  specification must be followed.

## I<sup>2</sup>C Interface

Symbol	Parameter	Remark	Min.	Тур.	Max.	Unit
f <sub>SCL</sub>	Clock frequency	_	_	_	400	kHz
t <sub>HIGH</sub>	Clock High Time	_	600	_	_	ns
t <sub>LOW</sub>	Clock Low Time	_	1300	_	_	ns
t <sub>r</sub>	SDA and SCL Rise Time	Note	_	_	300	ns
t <sub>f</sub>	SDA and SCL Fall Time	Note	_	_	300	ns
t <sub>HD:STA</sub>	START Condition Hold Time	After this period, the first clock pulse is generated.	600	_	_	ns
t <sub>su:sta</sub>	START Condition Setup Time	Only relevant for repeated START condition.	600	_	_	ns
t <sub>HD:DAT</sub>	Data Input Hold Time	_	0	_	_	ns
t <sub>SU:DAT</sub>	Data Input Setup Time	_	100	_	_	ns
t <sub>SU:STO</sub>	STOP Condition Setup Time	_	600	_	_	ns
t <sub>AA</sub>	Output Valid from Clock	_	_	_	900	ns
t <sub>BUF</sub>	Bus Free Time	Time in which the bus must be free before a new transmission can start	1300	_	_	ns
t <sub>SP</sub>	Input Filter Time Constant (SDA and SCL Pins)	Noise suppression time	_	_	50	ns

Note: These parameters are periodically sampled but not 100% tested.



## 3-Wire Interface

Ta=-40°C~85 °C


Cumbal	Parameter		Test Conditions	Min.	Tren	Max.	Unit	
Symbol	Parameter	V <sub>DD</sub> Conditions		iviin.	Тур.	IVIAX.	Unit	
f <sub>SCLK</sub>	Serial Clock	3V	_	_	_	1	MHz	
ISCLK	Serial Clock	5V	_	_	_	2	IVITIZ	
<b>t</b>	Data to Clask Catus		_	100	_	_	no	
t <sub>DC</sub>	Data to Clock Setup	5V	_	50	_	_	ns	
	Clock to Data Hold	3V	_	140	_	_	ns	
t <sub>CDH</sub>	Clock to Data Hold	5V	_	70	_	_	115	
4	Cleak to Data Dalay	3V	_	_	_	400	20	
t <sub>CDD</sub>	Clock to Data Delay	5V	_	_	_	200	ns	
	Clock Low Time	3V	_	500	_	_		
t <sub>CL</sub>	Clock Low Time	5V	_	250	_	_	ns	
	Clask High Time	3V	_	500	_	_		
t <sub>сн</sub>	Clock High Time	5V	_	250	_	_	ns	
tr	Clock Rise and Fall time	3V	_	_	_	1000		
tf	Clock Rise and Fall time	5V	_	_	_	500	ns	
_	OF to Cloub Setum	3V	_	2	_	_		
tcc	CE to Clock Setup	5V	_	1	_	_	μs	
	Clask to CE Hald	3V	_	120	_	_		
t <sub>CCH</sub>	Clock to CE Hold	5V	_	60	_	_	ns	
	CE Inactive Time	3V	_	2	_	_		
t <sub>CWH</sub>	CE mactive time	5V	_	1	_	_	μs	
	CE to I/O High Improduces	3V	_	_	_	140		
t <sub>CDZ</sub>	CE to I/O High Impedance	5V	_	_	_	70	ns	

# **Timing Diagrams**

# **Power-Down Timing**




# I<sup>2</sup>C Interface






## 3-Wire Interface

### **Read Data Transfer**



#### **Write Data Transfer**



### **Crystal Specifications**

Symbol	Parameter	Min.	Тур.	Max.	Unit
f <sub>0</sub>	Nominal Frequency	_	32.768	_	kHz
ESR	Series Resistance	_	35	50	kΩ
CL	Load Capacitance	_	12.5	_	pF

Note: 1. It is strongly recommended to use a crystal with load capacitance 12.5pF.

 The oscillator selection can be optimized using a high quality resonator with small ESR value. Refer to crystal manufacturer for more details: www.microcrystal.com

## **Functional Description**

The HT1382 is a low power real time clock device which provides full date and time functions. Communication with the device is provided through two integral serial interfaces, I<sup>2</sup>C or 3-wire. The device version selects the type of interface. The clock and calendar information is generated in BCD format and also has alarm features. The calendar is accurate until the year 2099, with automatic leap year correction.

Basic timing is provided using an external 32768Hz crystal, for which the device includes load capacitances of 12.5pF. An oscillator compensation function is provided to compensate for crystal oscillator temperatures. With fully integrated power control circuitry which can detect power failures, the device can automatically switch to a reserve battery supply when a power failure occurs.

### **Power Control Function**

The internal battery switchover circuit continually monitors the main power supply on the VDD pin and automatically switches to the backup battery supply when a power failure condition is detected.

In the battery backup mode, the interface is disabled to minimise power consumption. The interface inputs will not be recognised which prevents extraneous data being written to the device. The interface outputs are high-impedance. All RTC functions are operational when the device is in the battery backup mode.

# Normal Mode ( $V_{DD}$ ) to Battery Backup Mode ( $V_{BAT}$ )

To switch from the  $V_{\text{DD}}$  to  $V_{\text{BAT}}$  mode, both of the following conditions must be valid:

 $V_{\text{DD}}\!\!<\!\!V_{\text{BAT-}}\!V_{\text{BATHYS}}$  and  $V_{\text{DD}}\!\!<\!\!V_{\text{COMP}}$ 




## Battery Backup Mode (V<sub>BAT</sub>) to Normal Mode (V<sub>DD</sub>)


To switch from the  $V_{\text{BAT}}$  to  $V_{\text{DD}}$  mode, one of the following conditions must be valid:

$$V_{DD}>V_{BAT}+V_{BATHYS}$$
 or  $V_{DD}>V_{COMP}+V_{COMPHYS}$ 

The power control situation is illustrated graphically below:



Note: Battery switchover when  $V_{BAT} < V_{COMP}$ 



Note: Battery switchover when  $V_{BAT} > V_{COMP}$ 


#### **Low Power Mode**

In normal mode, the HT1382 switched into battery backup mode when the  $V_{\text{DD}}$  power is lost. This will ensure that the device can accept a wide range of backup voltages from many types of sources while reliably switching into backup mode. Another mode, called Low Power Mode, is available to allow direct switching from  $V_{\text{DD}}$  to  $V_{\text{BAT}}$  without requiring  $V_{\text{DD}}$  to drop below  $V_{\text{COMP}}.$  The power switchover circuit is disabled and less power is used while operating from  $V_{\text{DD}}.$  The Low Power Mode is activated using the LPM bit.

The Low Power Mode is useful when  $V_{DD}$  is normally higher than  $V_{BAT}$ . The device will switch from  $V_{DD}$  to  $V_{BAT}$  when  $V_{DD}$  drops below  $V_{BAT}$ , with about 40mV of hysteresis to prevent any switchback of  $V_{DD}$  after switchover. In a system with  $V_{DD}$ =5V and  $V_{BAT}$ =3V, the Low Power Mode can be used. However, it is not recommended to use the Low Power Mode in  $V_{DD}$ =3.3V±10%,  $V_{BAT}$ ≥3V.

### **Clock Compensation**

The device includes a digital trimming method for clock error correction due to temperature variations of the crystal oscillator. This can be implemented as manufacturing calibration or user active calibration. The crystal accuracy to temperature characteristic is similar to that shown in the accompanying diagram.



The Digital Trimming Register, DT, is used for clock compensation. Correction is performed once every 10 seconds or 30 seconds. The minimum resolution is 3.052ppm or 1.017ppm and the device has a correction in the range of  $\pm 192.276$ ppm or  $\pm 64.071$ ppm.


Set FO3~FO0="1010", the FOUT pin will have 1Hz clock pulse output. Measure the FOUT frequency using a high-accuracy frequency counter with 7 or more digits. The correction value is calculated using the formula shown below.

Correction value = integral value

When clock compensation is used, set FO3~FO0= "1010", and the FOUT pin will have 1Hz clock pulse output. The cycle changes once in 10 seconds or in 30 seconds as shown below. In the diagram "a" denotes a non-correctional cycle, and "b" denotes a correctional cycle. Measure "a" and "b" using a high-accuracy frequency counter of 7 or more digits. Calculate the average frequency based on the measured result.

For DTS=0, the average period =  $(a \times 9 + b) \div 10$ 

For DTS=1, the average period =  $(a\times29+b)\div30$ 





## **Register Description**

The device includes 16 registers which are used to control functions such as the RTC, Status, Alarm, Frequency output etc. There are also five bytes of EEPROM which contain the clock compensation settings and stored user data. The RTC and Alarm register data is stored in BCD format, while other data is stored in binary format. The register map shows the address definitions for the I<sup>2</sup>C interface. The command byte and R/W bit are used for the 3-wire interface.

		Register Definition							Register	Range		Bit	Command
Address	D7	D6	D5	D4	D3	D2	D1	D0	Name	Data	Default	R/W	Byte
00H	СН		10 S	EC		SE	EC		Seconds	00~59	80H	W R	10000000 10000001
01H	0		10 N	IIN		М	IN		Minutes	00~59	00H	W R	10000010 10000011
02H	12/ 24	0	AP 10	HR HR		НО	UR		Hours	01~12 00~23	12H	W R	10000100 10000101
03H	0	0	10	DATE		DA	TE		Date	01~31	01H	W R	10000110 10000111
04H	0	0	0	10M		MOI	NTH		Month	01~12	01H	W R	10001000 10001001
05H	0	0	0	0	0		DAY		Day	01~07	01H	W R	10001010 10001011
06H		10 Y	ÆAR			YE	AR		Year	00~99	00H	W R	10001100 10001101
07H	WP	0	0	0	0	0	0	0	ST	_	80H	W R	10001110 10001111
08H	ARE	0	0	EWE	EB	AI	BE	0	ST	_	00H	W R	10010000 10010001
09H	IME	AE	LPM	OEOBM	FO3	FO2	FO1	FO0	INT	_	00H	W R	10010010 10010011
0AH	SECEN	AL. 10SEC		AL. 10SEC		AL.	SEC		Seconds Alarm	00~59	00H	W R	10010100 10010101
0BH	MINEN		AL. 10	MIN		AL.	MIN		Minutes Alarm	00~59	00H	W R	10010110 10010111
0CH	HREN	0	AL	. 10HR		AL. F	IOUR		Hours Alarm	01~12 00~23	00H	W R	10011000 10011001
0DH	DTEN	0	AL	10DT		AL. [	DATE		Date Alarm	01~31	00H	W R	10011010 10011011
0EH	MOEN	0	0	AL. 10M		AL. M	ONTH		Month Alarm	01~12	00H	W R	10011100 10011101
0FH	DAYEN	0	0	0	0	A	L. DA	Y	Day Alarm	01~07	00H	W R	10011110 10011111
EEPROM	Data												
10H	DTS	DT6	DT5	DT4	DT3	DT2	DT1	DT0	DT	_	_	W R	10100000 10100001
11H			EEF	PROM Use	er Data			USR	_	_	W R	10100010 10100011	
12H			EEF	PROM Use	er Data			USR	_	_	W R	10100100 10100101	
13H			EE	PROM Use	er Data	1			USR	_	_	W R	10100110 10100111
14H			EEF	PROM Use	er Data	1			USR	_	_	W R	10101000 10101001



### **Real Time Clock Register**

The RTC register stores the Year, Day, Month, Date, Hours, Minutes and Second data inBCDformat.

#### 12/24 Hour Mode

Bit D7 of the hour register is defined as the 12-hour or 24-hour mode select bit. If the bit is "1", the RTC uses a 24-hour format. If "0", the RTC uses a 12-hour format. The default value is "0.

#### AM/PM Mode

There are two function for the D5 bit in the hour register which is determined by the D7 bit. In the 12-hour mode the bit is used for AM/PM selection. When D5 is "1", it will be PM, otherwise it will be AM. In the 24-hour mode, the bit is used to set the second 10-hour bit (20~23 hours).

#### **Leap Years**

Leap years add an extra day for February 29 and are defined as those years that are divisible by 4. The device will provide automatic correction for leap years until the year 2099.

#### Clock HALT Bit - CH

This bit enables/disables the oscillator. The CH bit is set high to disable the oscillator and cleared to zero is enable it. The default value is defined as "1".

#### Write Protect Bit - WP

The WP bit is set high to prevent data writes and cleared to zero to allow data to be written. The default value is define as "1".

### Battery Enable Bit - BE

When the device enters the battery backup mode, the BE bit is set to "1". This bit can be cleared to "0" either manually by the user or automatically reset by the ARE pin. Only a "0" an be written to this bit, not a "1".

## Alarm Interrupt Bit - Al

When the RTC register values match the alarm register values, the AI bit will be set to "1". This bit can be reset to "0" either manually by the user or automatically reset by the ARE pin. Only a "0" an be written to this bit, not a "1". The AI bit will be set by an alarm occurring during a read operation ad will remain set until after the read operation is complete.

#### Auto Reset Enable Bit - ARE

This bit enables/disables the automatic reset of the BE and AI status bits only. When ARE is set to "1", BE and AI will be reset to "0" after reading these registers. When ARE is cleared to "0", the user must manually reset the BE and AI bits.

#### Alarm Enable Bit - AE

This bit enables/disables the alarm function. When the AE bit is set to "1", the alarm function is enabled. When the AE bit is cleared to "0", the alarm function is disabled.

#### **EEPROM Write Enable Bit - EWE**

When EWE is cleared to "0", the EEPROM is read only, and the user can not write data to the EEPROM. When EWE is set to "1", the user can write data to the EEPROM. Before writing data to the EEPROM, this bit must be set to "1".

#### **EEPROM Busy Status Bit - EB**

This bit is set to "1" when a write operation to the EEPROM has not completed. When this bit is set to "1", reading data from the EEPROM or writing data to the EEPROM is invalid. After an EEPROM write operation has finished, this bit will be cleared to "0" and the user can read data from the EEPROM or write data to the EEPROM.

#### Output Enable On Battery Mode Bit - OEOBM

This bit enables/disables the  $\overline{IRQ}/FOUT$  pin in the battery mode. When the OEOBM bit is set to "1", the  $\overline{IRQ}/FOUT$  pin is disabled in the battery mode and the frequency output and alarm function are disabled. When the OEOBMbit is cleared to "0", the  $\overline{IRQ}/FOUT$  pin is enabled in the battery mode.

#### Low Power Mode Bit - LPM

This bit enables/disables the Low Power Mode. When the LPM bit is cleared to "0", the device will be in the normal mode and will use the  $V_{\rm BAT}$  supply when  $V_{\rm DD}$  <  $V_{\rm BAT}$  and  $V_{\rm DD}$  <  $V_{\rm COMP}.$  When the LPM bit is set to "1", the device is in the Low Power Mode and uses the  $V_{\rm BAT}$  supply when  $V_{\rm DD}$  <  $V_{\rm BAT}.$ 

## Frequency Output Bits - FO3~FO0

These bits enable/disable the frequency output function and select the output frequency at the FOUT pin. The frequency selection table is shown below. It overrides the alarm mode. The 1, 1/2, 1/4, 1/8, 1/16, 1/32 frequency outputs are compensated.

FOUT (Hz)	FO3	FO2	FO1	FO0
_	0	0	0	0
32768	0	0	0	1
4096	0	0	1	0
1024	0	0	1	1
64	0	1	0	0
32	0	1	0	1
16	0	1	1	0
8	0	1	1	1
4	1	0	0	0



FOUT (Hz)	FO3	FO2	FO1	FO0
2	1	0	0	1
1	1	0	1	0
1/2	1	0	1	1
1/4	1	1	0	0
1/8	1	1	0	1
1/16	1	1	1	0
1/32	1	1	1	1

#### Interrupt Mode Enable Bit - IME

This bit enables/disables the interrupt mode of the alarm function. When the IME bit is set to "1", the interrupt mode is enabled and when the IME bit is cleared to "0", the interrupt mode is disabled and the alarm operates in single mode.

### **Alarm Register**

The addresses of alarm registers are 0Bh to 10h. The data is stored in the BCD format. The MSB of each alarm register is an enable bit. (enable="1"). These enable bits specify which alarm registers are used to make the comparison between the alarm registers and the RTC registers. There is no alarm byte for year. When a compare match condition exists, the AI bit is set to "1", and the  $\overline{IRQ}$  pin is activated.

To clear an alarm, the AI bit must be cleared to "0". If the ARE bit is set to "1", the AI bit will automatically be cleared when the status register is read.

There are two alarm operation modes: Single mode and Interrupt Mode.

Single mode: set the AE bit to "1", the IME bit to "0", and disable the frequency output. When the RTC register values match the alarm registers values, the AI bit will be set to "1" and the alarm condition activates the  $\overline{IRQ}$  pin. The  $\overline{IRQ}$  pin will remain low until the AI bit is cleared to "0".

Interrupt mode: set the AE bit to "1", the IME bit to "1", and disable the frequency output. When the RTC registers values match the alarm registers values, the  $\overline{IRQ}$  pin will be pulled low for 250ms and the AI bit will be set to "1". This mode allows for a repetitive or recurring alarm function. When the alarm is set, the device will continue to activate an alarm for each match of the alarm and the present time. For example, if only the seconds are set, it will activate an alarm every minute, if only the minutes are set, it will activate an alarm every hour.

#### **EEPROM User Data**

The HT1382 provides 4 bytes EEPROM for user. The EEPROM will continue to operate in battery backup mode. However, it should be noted that the I<sup>2</sup>C/3-wire interface is disabled in battery backup mode. User must detect the status of EB bit before reading data or writing data. If the EB bit is "0", it is valid to read data or write data. If the EB bit is "1", it is invalid to read data or write data.

#### **Digital Trimming Setting Bits - DTS**

This bit sets the digital trimming resolution and adjustment time. The user must detect the status of the EB bit before reading data or writing data. If the EB bit is "0", it is valid to read data or write data. If the EB bit is "1", it is invalid to read data or write data.

#### Digital Trimming Bits - DT6~DT0

This digital trimming bit, DT6, is the sign bit. A "0" indicates positive calibration and a "1" indicates negative calibration. DT5~DT0 are the calibration values and the adjustable range is -63 ~ +63. If DTS is cleared to "0", the correction range is -192.276ppm to +192.276ppm and if DTS is set to "1", the correction range is -64.071ppm to +64.071ppm. The user must detect the status of EB bit before reading data or writing data. If the EB bit is "0", it is valid to read data or write data. If the EB bit is "1", it is invalid to read data or write data.

	DTS="0"	DTS="1"
Adjustment time	Every 10 seconds	Every 30 seconds
Minimum resolution	3.052ppm	1.017ppm
Correction range	-192.276ppm to +192.276ppm	-64.071ppm to + 64.071ppm



DTO	DTF	DT4 DT	рто		DT4 D	БТО	Value	Correction Value (ppm)	
DT6	DT5	DT4	DT3	DT2	DT1	DT0		DTS="0"	DTS="1"
0	1	1	1	1	1	1	+63	+192.276	+64.071
0	1	1	1	1	1	0	+62	+189.224	+63.054
0	1	1	1	1	0	1	+61	+186.172	+62.037
0	1	1	1	1	0	0	+60	+183.120	+61.020
				•				:	
0	0	0	0	0	1	1	+3	+9.156	+3.051
0	0	0	0	0	1	0	+2	+6.104	+2.034
0	0	0	0	0	0	1	+1	+3.052	+1.017
0	0	0	0	0	0	0	0	0	0
1	0	0	0	0	0	0	0	0	0
1	0	0	0	0	0	1	-1	-3.052	-1.07
1	0	0	0	0	1	0	-2	-6.104	-2.034
1	0	0	0	0	1	1	-3	-9.156	-3.051
				:				:	:
1	1	1	1	1	0	0	-60	-183.120	-61.020
1	1	1	1	1	0	1	-61	-186.172	-62.037
1	1	1	1	1	1	0	-62	-189.224	-63.054
1	1	1	1	1	1	1	-63	-192.276	-64.071


#### I<sup>2</sup>C Serial Interface

The HT1382 includes an I<sup>2</sup>C serial interface. The I<sup>2</sup>C bus is used for bidirectional, two-line communication between multiple I<sup>2</sup>C devices. The two lines of the interface are the serial data line (SDA) and the serial clock line (SCL). Both lines are connected to the positive supply via a pull-up resistor externally.

When the bus is free, both lines will be high. The output stages of the devices connected to the bus must have open-drain or open-collector output types to implement the wired-AND function necessary for connection. Data transfer is initiated only when the bus is not busy.

#### **Data Validity**


The data on the SDAline must be stable during the HIGH period of the clock. The HIGH or LOWstate of the data line can only change when the clock signal on the SCL line is LOW.



## **START and STOP Conditions**


A HIGH to LOW transition on the SDA line while SCL is HIGH defines a START condition. A LOW

to HIGH transition on the SDA line while SCL is HIGH defines a STOP condition. START and STOP conditions are always generated by the master. The bus is considered to be busy after the START condition. The bus is considered to be free again a certain time after the STOP condition. The bus stays busy if a repeated START(Sr) is generated instead of a STOP condition. In this respect, a START(S) and repeated START(Sr) conditions are functionally identical.



### **Byte Format**

Every byte put on the SDA line must be 8-bits long. The number of bytes that can be transmitted per transfer is unrestricted. Each byte has to be followed by an acknowledge bit. Data is transferred with the most significant bit (MSB) first.






## Acknowledge


Each bytes of eight bits is followed by one acknowledge bit. This acknowledge bit is a low level placed on the bus by the receiver. The master generates an extra acknowledge related clock pulse. A slave receiver which is addressed must generate an acknowledge (ACK) after the reception of each byte.

The acknowledging device must first pull down the SDA line during the acknowledge clock pulse so that it remains LOW during the HIGH period of this clock pulse. Amaster receiver must signal an end of data to the slave by generating a not-acknowledge (NACK) bit on the last byte that has been clocked out of the slave. In this case, the master receiver must leave the data line HIGH during the 9th pulse to not acknowledge. The master will generate a STOP or repeated START condition.



#### **Device Addressing**

The slave address byte is the first byte received following the START condition from the master device. The first seven bits of the first byte make up the slave address. The eighth bit defines a read or write operation to be performed. When this  $R/\overline{W}$  bit is "1", then a read operation is selected. A "0" selects a write operation. The device address bits are "1101000". When an address byte is sent, the device compares the first seven bits after the START condition. If they match, the device outputs an acknowledge on the SDA line.



The first byte after the START

### **Write Operation**

· Byte Write Operation

A byte write operation requires a START condition, a slave address with R/W bit, a valid Register Address, the required Data and a STOP condition. After each of the three byte transfers, the device responds with an ACK.




### • Page Write Operation

Following a START condition and slave address, a  $R/\overline{W}$  bit is placed on the bus which indicates to the addressed device that a Register Address will follow which is to be written to the address pointer. The data to be written to the memory follows next and the internal address pointer is incremented to the next address location on the reception of an acknowledge clock. After reaching memory location 0Fh, the pointer will be reset to 00h.



## **Read Operation**

In this mode, the master reads the device data after setting the slave address. Following the  $R/\overline{W}$  bit (="0") and the acknowledge bit, the register address (An) is written to the address  $\overline{W}$  pointer. Next the START condition and slave address are repeated followed by the  $R/\overline{W}$  bit (="1"). The data which was addressed is then transmitted. The address pointer is only incremented on reception of an acknowledge clock. The device will then place the data at address An+1 on the bus. The master reads and acknowledges the new byte and the address pointer is incremented to "An+2". After reaching the memory location 0Fh, the pointer will be reset to 00h. This cycle of reading consecutive addresses will continue until the master sends a STOP condition. This cycle of reading consecutive addresses will continue until the master sends a STOP condition.



## 3-wire Serial Interface

The device also support a 3-wire serial interface. The CE pin is used to identify the transmitted data. The transmission is controlled by the active HIGH signal CE. Each data transfer is a byte, with the LSB sent first. The first byte transmitted is the Command Byte.

### **Command Byte**

For each data transfer, a Command Byte is initiated to specify which register is accessed. This is to determine whether a read or write cycle is operational and whether a single byte or burst mode transfer is to occur.



## R/W Signal

The LSB of the Command Byte determines whether the data in the register is to be read or be written to. If it is "0" then this means that it is a write cycle. If it is "1" then this means that it is a read cycle.


### **Burst Mode**

When the Command Byte is 101111110 or 101111111, the device is configured in the burst mode. In this mode, the address of registers from 00h to 0Fh can be written or read in series, starting with bit 0 of register address 0.


### **Data Input and Data Out**

In writing a data byte,  $R/\overline{W}$  is cleared to "0" in the Command Byte and is then followed by the corresponding data register address on the rising edge of the next eight SCLK. Additional SCLK cycles are ignored. Data inputs are entered starting with bit 0. In reading data from the register, the  $R/\overline{W}$  is set to "1" in the Command Byte. The data bits are output on the falling edge of the next eight SCLK cycles. Note that the first data bit to be transmitted on the first falling edge after the last bit of the read command byte is written. Additional SCLK cycles re-transmit the data bytes as long as CE remains at high level. Data outputs are read starting with bit 0.

## · Single Byte Transfer




#### · Burst Mode Transfer






# **Application Circuit**

## I<sup>2</sup>C Serial Interface



## 3-wire Serial Interface





# **Package Information**


Note that the package information provided here is for consultation purposes only. As this information may be updated at regular intervals users are reminded to consult the <u>Holtek website</u> for the latest version of the <u>Package/Carton Information</u>.

Additional supplementary information with regard to packaging is listed below. Click on the relevant section to be transferred to the relevant website page.

- Package Information (include Outline Dimensions, Product Tape and Reel Specifications)
- Packing Meterials Information
- Carton information



# 8-pin SOP (150mil) Outline Dimensions








Symbol	Dimensions in inch				
	Min.	Nom.	Max.		
A	_	0.236 BSC	_		
В	_	0.154 BSC	_		
С	0.012	_	0.020		
C'	_	0.193 BSC	_		
D	_	_	0.069		
E	_	0.050 BSC	_		
F	0.004	_	0.010		
G	0.016	_	0.050		
Н	0.004	_	0.010		
α	0°	_	8°		


Symbol	Dimensions in mm				
	Min.	Nom.	Max.		
A	_	6.00 BSC	_		
В	_	3.90 BSC	_		
С	0.31	_	0.51		
C'	_	4.90 BSC	_		
D	_	_	1.75		
E	_	1.27 BSC	_		
F	0.10	_	0.25		
G	0.40	_	1.27		
Н	0.10	_	0.25		
α	0°	_	8°		



# 10-pin MSOP Outline Dimensions







Symbol	Dimensions in inch				
	Min.	Nom.	Max.		
Α	_	_	0.043		
A1	0.000	_	0.006		
A2	0.030	0.033	0.037		
В	0.007	_	0.013		
С	0.003	_	0.009		
D	_	0.118 BSC	_		
E	_	0.193 BSC	_		
E1	_	0.118 BSC	_		
е	_	0.020 BSC	_		
L	0.016	0.024	0.031		
L1	_	0.037 BSC	_		
у	_	0.004	_		
θ	0°	_	8°		

Symbol	Dimensions in mm				
Symbol	Min.	Min. Nom.			
A	_	_	1.10		
A1	0.00	_	0.15		
A2	0.75	0.85	0.95		
В	0.17	_	0.33		
С	0.08	_	0.23		
D	_	3.00 BSC	_		
E	_	4.90 BSC	_		
E1	_	3.00 BSC	_		
е	_	0.50 BSC	_		
L	0.40	0.60	0.80		
L1	_	0.95 BSC	_		
У	_	0.10	_		
θ	0°	_	8°		



Copyright<sup>©</sup> 2022 by HOLTEK SEMICONDUCTOR INC. All Rights Reserved.

The information provided in this document has been produced with reasonable care and attention before publication, however, HOLTEK does not guarantee that the information is completely accurate. The information contained in this publication is provided for reference only and may be superseded by updates. HOLTEK disclaims any expressed, implied or statutory warranties, including but not limited to suitability for commercialization, satisfactory quality, specifications, characteristics, functions, fitness for a particular purpose, and non-infringement of any third-party's rights. HOLTEK disclaims all liability arising from the information and its application. In addition, HOLTEK does not recommend the use of HOLTEK's products where there is a risk of personal hazard due to malfunction or other reasons. HOLTEK hereby declares that it does not authorise the use of these products in life-saving, life-sustaining or safety critical components. Any use of HOLTEK's products in life-saving/sustaining or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold HOLTEK harmless from any damages, claims, suits, or expenses resulting from such use. The information provided in this document, including but not limited to the content, data, examples, materials, graphs, and trademarks, is the intellectual property of HOLTEK (and its licensors, where applicable) and is protected by copyright law and other intellectual property laws. No license, express or implied, to any intellectual property right, is granted by HOLTEK herein. HOLTEK reserves the right to revise the information described in the document at any time without prior notice. For the latest information, please contact us.