



Datasheet

GPS/GLONASS/Galileo SMD Patch Antenna

Part No:
SGGP.18.4.A.08

Description:
18*18*4mm GPS/GLONASS/Galileo SMD Patch Antenna

Features:

SMD Direct Mount Ceramic Patch Antenna
GPS/Galileo/GLONASS Antenna
GPS L1/Galileo E1 (1575.42 MHz) – 78% Efficiency
GLONASS L1 (1602 MHz) – 80% Efficiency
Dimensions: 18*18*4mm
RoHS & Reach Compliant

| | | |
|----|---------------------------|----|
| 1. | Introduction | 3 |
| 2. | Specifications | 4 |
| 3. | Antenna Characteristics | 5 |
| 4. | Radiation Patterns | 7 |
| 5. | Mechanical Drawing | 10 |
| 6. | Antenna Integration Guide | 11 |
| 7. | Packaging | 17 |
| 8. | Soldering Recommendations | 19 |
| | Changelog | |

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein.

Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

Copyright © Taoglas Ltd.



1. Introduction



The Taoglas SGGP.18 is a ceramic GPS/GLONASS/Galileo passive patch antenna designed for optimal performance on GPS L1/Galileo E1 band (1575.42 MHz) and GLONASS L1 band (1602 MHz). With a low-profile thickness of just 4mm and convenient mounting via standard SMD process, it is ideal for high-volume, low-cost assembly applications. SGGP.18 is designed for applications in navigation devices, vehicle tracking/fleet management systems, and telematics devices. It is an excellent choice for applications in transportation, defense, marine, agriculture, and navigation industries.

This antenna has been tuned for use on a 50mm*50mm ground plane to achieve 2.86 dBi gain at 1575.42 MHz and 3.04 dBi gain at 1602 MHz. In addition to excellent efficiency, it also offers a broadly hemispherical radiation pattern with stable gain across elevations.

SGGP.18 is manufactured and tested in an IATF16949 first tier automotive approved facility. For further optimization to customer-specific device environments, custom tuned patch antennas can be supplied, subject to NRE and MOQ.

For further information or support with integrating this antenna into your device, please contact your regional Taoglas customer support team.

2. Specifications


| GNSS Frequency Bands Covered | | | | | | | |
|------------------------------|-----------------|-------------|------------|------------|------------|---------|------------|
| GPS/QZSS | L1 | L2 | L5 | L6 | | | |
| | 1575.42MHz | 1227.6MHz | 1176.45MHz | 1278.75MHz | | | |
| | ■ | □ | □ | □ | | | |
| GLONASS | L5R | L3PT | L2PT | L1CR | L1PT | | |
| | 1176.45MHz | 1201.5MHz | 1246MHz | 1575.42MHz | 1602MHz | | |
| | □ | □ | □ | ■ | ■ | | |
| Galileo | E5a | E5b | E4 | E3 | E6 | E2 | E1 |
| | 1176.45MHz | 1201.5MHz | 1215MHz | 1256MHz | 1278.75MHz | 1561MHz | 1575.42MHz |
| | □ | □ | □ | □ | □ | □ | ■ |
| BeiDou | B1 | B2 | B3 | | | | |
| | 1561MHz | 1207.14MHz | 1268.52MHz | | | | |
| | □ | □ | □ | | | | |
| Compass | E5B(B2)/ E6(B3) | E2(B1) | | | | | |
| | 1268.56MHz | 1561MHz | | | | | |
| | □ | □ | | | | | |
| SBAS | Omnistar | WAAS/EGN OS | | | | | |
| | 1542.5MHz | 1575.42MHz | | | | | |
| | □ | ■ | | | | | |

| GNSS Electrical | | |
|----------------------------------|----------------------------|---------|
| Application Bands | GPS/Galileo | GLONASS |
| Operation Frequency (MHz) | 1575.42 ±1.023 | 1602±5 |
| Return Loss (dB) | < -10 | < -10 |
| Efficiency (%) | 78 | 80 |
| Average Gain (dB) | -1.07 | -0.98 |
| Peak Gain (dBi) | 2.86 | 3.04 |
| Impedance | 50 ohms | |
| Polarization | RHCP | |
| Mechanical | | |
| Ceramic Dimension | 18*18*4mm | |
| Weight | 5.8g | |
| Environmental | | |
| Operation Temperature | -40°C to 85°C | |
| Humidity | Non-condensing 65°C 95% RH | |
| Moisture Sensitivity Level (MSL) | 3 (168 Hours) | |


*Measurements tested on 50*50mm ground plane

3. Antenna Characteristics


3.1 Return Loss




3.2 Efficiency



3.3 Average Gain




3.4 Peak Gain




4. Radiation Patterns

4.1 Test Setup



The SGGP.18.4.A.08 antenna is tested with 50mm*50mm ground plane in a CTIA certified ETS-Lindgren Anechoic Chamber. The test setup is shown above.




4.2 1575.42MHz 3D and 2D Radiation Patterns




XY Plane

XZ Plane

YZ Plane






1602MHz







XY Plane

XZ Plane


YZ Plane



5. Mechanical Drawing (Units: mm)



6. Antenna Integration Guide




6.1 Schematic Symbol and Pin Definition

The circuit symbol for the antenna is shown below. The antenna has 9 pins as indicated below.

| Pin | Description |
|-----|-------------|
| 1 | RF Feed |
| 2-9 | Ground |

TAOGLAS_SGGP.18.4.A.08
ANT1



Please note you can download the design files, 3D model, 2D drawings and CST simulation files from the website here:


<https://www.taoglas.com/product/sggp-18-4-a-08-gps-glonass-galileo-smd-18184mm-mount-patch/>

6.2 Antenna Integration

The antenna should be placed at the center of the ground plane with a length and width of 50mm. Maintaining a square symmetric ground plane shape and symmetric environment around the antenna is critical to maintaining the excellent axial ratio and phase center performance shown in this datasheet.




Top Side w/ Solder Mask




Top Side w/o Solder Mask

6.3 PCB Layout

The footprint and clearance on the PCB must comply with the antenna specification. The PCB layout shown in the diagram below demonstrates the antenna footprint.




Topside




Bottom Side

6.4 Evaluation Board



6.5 Footprint




FOOTPRINT PCB


| PIN | DESCRIPTION: |
|-----|------------------|
| 1 | RF FEED (50 Ohm) |
| 2 | GROUND |
| 3 | GROUND |
| 4 | GROUND |
| 5 | GROUND |
| 6 | GROUND |
| 7 | GROUND |
| 8 | GROUND |
| 9 | GROUND |

7. Packaging


200 pc SGGP.18.4.A.08 per reel
 Dimensions - Ø330*33mm
 Weight - 2.125Kg



200 pc SGGP.18.4.A.08 per small box
Dimensions - 350*340*67mm
Weight - 2.125Kg




800 pcs SGGP.18.4.A.08 per carton
Dimensions - 370*360*305mm
Weight - 8.5Kg



8. Soldering Recommendations

The SGGP.18.4.A.08 can be assembled by following the recommended soldering temperatures are as follows:



*Temperatures listed within a tolerance of $\pm 10^{\circ}\text{C}$

Smaller components are typically mounted on the first pass, however, we do advise mounting the SGGP.18.4.A.08 when placing larger components on the board during subsequent reflows.

Note: Soldering flux classified ROL0 under IPC J-STD-004 is recommended.

Changelog for the datasheet

SPE-18-8-067 - SGGP.18.4.A.08

Revision: F (Current Version)

| | |
|------------------|------------------------------------|
| Date: | 2023-01-05 |
| Changes: | Updated Solder Reflow Information. |
| Changes Made by: | Cesar Sousa |

Previous Revisions

Revision: E

| | |
|------------------|---------------------------------------------------------------|
| Date: | 2023-01-05 |
| Changes: | Updated PCB Mechanical Footprint Drawing & Integration Guide. |
| Changes Made by: | Gary West |

Revision: D

| | |
|------------------|------------------------------|
| Date: | 2023-01-05 |
| Changes: | Updated PCB Keep Out Drawing |
| Changes Made by: | Gary West |

Revision: C

| | |
|------------------|-----------------------------------------------------------|
| Date: | 2022-05-27 |
| Changes: | Added dimension to footprint drawing between pad 1 and 5. |
| Changes Made by: | Gary West |

Revision: B

| | |
|------------------|------------------------------------------------------------------------------------|
| Date: | 2021-10-20 |
| Changes: | Full datasheet template update, Addition of MSL to spec table & Integration guide. |
| Changes Made by: | Gary West |

Revision: A (Original First Release)

| | |
|---------|---------------|
| Date: | 2018-07-02 |
| Notes: | First Release |
| Author: | MC |



www.taoglas.com

